

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P333285-840

Luminaire Tested: **S125DIP-S1090D1035U840-4F0-1E-UDD-F4**

Issue Date: 3/3/2020

Test Information

Test Method: LM-79-08
Report Number: P333285-840
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-19,
Test Lab: INNOVATION CENTER
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: NEO-RAY
Catalog Number: S125DIP-S1090D1035U840-4F0-1E-UDD-F4
Description: DEFINE 5 DIRECT-INDIRECT PENDANT LED LUMINAIRE
DOWNLIGHT 1090 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER
UPLIGHT 1035 LUMENS PER FOOT, BATWING OPTIC
Light Source: -
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 8236.6 lumens
Efficiency: N/A
Efficacy: 136.1 lumens/watt
Spacing Criteria (0/90/45): 1.21 / 1.18 / 1.31
Luminous Opening: Rectangular (W 0.42' x L: 4' x H: 0')
CIE Type: General Diffuse


Input Watts (W): 60.5
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P333285-840

CATALOG NUMBER: S125DIP-S1090D1035U840-4F0-1E-UDD-F4

Luminous Intensity Polar Plot





TEST NUMBER: P333285-840

CATALOG NUMBER: S125DIP-S1090D1035U840-4F0-1E-UDD-F4

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	108	108	108	108	100	100	100	100	86	86	86	72	72	72	60	60	60	54
1	99	94	90	87	91	88	84	81	75	73	70	64	62	60	53	52	51	46
2	90	82	76	71	83	77	71	67	66	62	58	56	53	50	47	45	43	38
3	82	72	65	59	76	67	61	56	58	53	49	49	46	42	41	39	36	32
4	75	64	56	50	69	60	53	47	52	46	42	44	40	36	37	34	31	28
5	69	57	49	43	64	53	46	40	46	40	36	40	35	32	33	30	27	24
6	63	51	43	37	59	48	41	35	42	36	31	36	31	28	30	27	24	21
7	59	46	38	33	54	43	36	31	38	32	28	32	28	24	28	24	21	19
8	54	42	34	29	50	39	32	27	34	29	25	30	25	22	25	22	19	17
9	51	38	31	26	47	36	29	24	32	26	22	27	23	20	23	20	17	15
10	47	35	28	23	44	33	26	22	29	24	20	25	21	18	22	18	16	14

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	11129	11129	11129
5°	11154	11048	11119
10°	11086	10970	11032
15°	10965	10838	10884
20°	10794	10653	10672
25°	10608	10434	10424
30°	10380	10197	10147
35°	10136	9942	9802
40°	9885	9666	9528
45°	9613	9414	9227
50°	9315	9109	8835
55°	9026	8765	8519
60°	8681	8418	8117
65°	8270	8000	7728
70°	7878	7517	7260
75°	7177	6939	6700
80°	6390	6289	6133
85°	5550	5654	5350



TEST NUMBER: P333285-840

CATALOG NUMBER: S125DIP-S1090D1035U840-4F0-1E-UDD-F4

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	162.5	2.0
10°-20°	459.0	5.6
20°-30°	677.7	8.2
30°-40°	790.7	9.6
40°-50°	794.2	9.6
50°-60°	697.1	8.5
60°-70°	519.5	6.3
70°-80°	297.0	3.6
80°-90°	89.2	1.1
90°-100°	362.4	4.4
100°-110°	779.1	9.5
110°-120°	731.2	8.9
120°-130°	592.6	7.2
130°-140°	475.6	5.8
140°-150°	358.9	4.4
150°-160°	252.6	3.1
160°-170°	148.9	1.8
170°-180°	48.4	0.6
0°-30°	1299.1	15.8
0°-40°	2089.8	25.4
0°-60°	3581.2	43.5
0°-90°	4486.8	54.5
90°-120°	1872.8	22.7
90°-150°	3299.8	40.1
90°-180°	3750.0	45.5
0°-180°	8236.6	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	1723	1723	1723	1723	1723	
5°	1720	1717	1704	1716	1715	163
15°	1640	1635	1621	1627	1628	462
25°	1489	1481	1464	1466	1463	685
35°	1286	1279	1261	1254	1243	804
45°	1052	1046	1031	1015	1010	811
55°	802	797	778	766	757	715
65°	541	538	524	512	506	537
75°	288	285	278	274	268	307
85°	75	76	76	75	72	84
90°	1	9	16	21	23	6
95°	33	98	893	405	237	35
105°	114	159	731	1439	1336	120
115°	204	246	587	1265	1488	200
125°	282	331	562	1006	1172	250
135°	331	398	558	843	974	257
145°	385	441	560	698	768	241
155°	440	473	546	618	644	202
165°	480	493	524	556	564	135
175°	499	499	503	509	507	47
180°	500	500	500	500	500	



TEST NUMBER: P333285-840

CATALOG NUMBER: S125DIP-S1090D1035U840-4F0-1E-UDD-F4

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	1723.2	1723.2	1723.2	1723.2	1723.2	1723.2	1723.2	1723.2	1723.2	1723.2	1723.2
2.5°	1727.6	1726.9	1726.1	1725.4	1724.6	1723.0	1720.6	1718.2	1715.8	1713.3	1715.8
5°	1720.5	1719.9	1719.3	1718.7	1718.1	1716.3	1713.2	1710.2	1707.2	1704.1	1706.9
7.5°	1704.7	1704.0	1703.4	1702.8	1702.2	1700.2	1696.9	1693.5	1690.2	1686.9	1689.6
10°	1690.5	1689.9	1689.3	1688.7	1688.1	1686.1	1682.7	1679.4	1676.1	1672.7	1675.2
12.5°	1673.0	1671.9	1670.8	1669.7	1668.7	1666.6	1663.4	1660.4	1657.3	1654.2	1656.2
15°	1640.0	1639.1	1638.2	1637.3	1636.4	1634.3	1630.9	1627.6	1624.3	1620.9	1622.4
17.5°	1602.2	1600.8	1599.4	1598.1	1596.8	1594.4	1590.9	1587.5	1584.1	1580.5	1582.5
20°	1570.5	1569.9	1569.3	1568.7	1568.1	1565.8	1561.9	1557.9	1554.0	1550.0	1552.2
22.5°	1538.8	1537.8	1536.7	1535.6	1534.5	1532.1	1528.4	1524.7	1521.1	1517.3	1518.7
25°	1488.7	1487.2	1485.7	1484.2	1482.7	1480.0	1476.0	1472.1	1468.1	1464.2	1464.8
27.5°	1430.1	1429.2	1428.3	1427.3	1426.4	1424.0	1419.9	1415.8	1411.8	1407.8	1407.9
30°	1391.9	1391.0	1390.1	1389.2	1388.3	1385.5	1381.0	1376.4	1371.9	1367.4	1366.8
32.5°	1350.5	1349.1	1347.7	1346.3	1344.9	1342.2	1338.1	1334.0	1330.0	1326.0	1324.8
35°	1285.6	1284.3	1283.1	1281.9	1280.7	1278.0	1273.7	1269.5	1265.3	1261.0	1259.5
37.5°	1218.2	1216.7	1215.2	1213.7	1212.1	1209.4	1205.4	1201.4	1197.4	1193.5	1191.1
40°	1172.5	1170.9	1169.4	1167.9	1166.4	1163.5	1159.2	1155.0	1150.7	1146.5	1143.8
42.5°	1123.4	1122.1	1120.8	1119.5	1118.2	1115.5	1111.3	1107.0	1102.8	1098.5	1096.0
45°	1052.5	1051.3	1050.1	1048.8	1047.6	1045.2	1041.6	1037.9	1034.3	1030.7	1027.0
47.5°	976.1	976.1	976.2	976.3	976.3	974.2	969.9	965.4	961.1	956.7	953.0
50°	927.1	926.1	925.2	924.3	923.4	921.1	917.5	913.8	910.2	906.6	902.6
52.5°	876.9	876.2	875.6	874.8	874.2	871.9	868.1	864.1	860.3	856.4	852.9
55°	801.6	800.7	799.8	798.9	798.0	795.4	791.1	786.9	782.6	778.4	775.7
57.5°	722.3	721.8	721.3	720.8	720.3	718.3	714.7	711.1	707.6	704.0	700.4
60°	672.1	670.9	669.6	668.4	667.2	665.0	661.7	658.3	655.0	651.7	648.6
62.5°	619.8	618.7	617.8	616.8	615.9	614.0	611.1	608.2	605.4	602.6	599.3
65°	541.2	540.6	540.0	539.4	538.8	536.8	533.5	530.2	526.8	523.5	520.8
67.5°	465.1	463.8	462.6	461.3	460.1	458.2	455.7	453.2	450.7	448.3	446.0
70°	417.2	415.7	414.1	412.6	411.1	409.0	406.3	403.5	400.8	398.1	396.3
72.5°	364.9	363.8	362.7	361.7	360.7	359.3	357.6	355.8	354.1	352.2	350.2
75°	287.6	287.0	286.4	285.8	285.2	284.2	282.7	281.1	279.6	278.1	277.2
77.5°	216.5	216.2	216.0	215.8	215.5	215.0	214.1	213.3	212.5	211.6	211.1
80°	171.8	171.8	171.8	171.8	171.8	171.5	170.9	170.3	169.7	169.1	168.7
82.5°	132.5	132.0	131.6	131.1	130.6	130.3	130.2	130.1	129.9	129.8	129.3
85°	74.9	75.2	75.5	75.8	76.1	76.3	76.3	76.3	76.3	76.3	76.0
87.5°	29.7	29.9	30.3	30.7	31.1	31.3	31.3	31.5	31.4	31.6	31.8
90°	1.0	2.0	4.0	6.1	8.1	10.1	11.1	13.1	14.1	16.2	17.2
92.5°	12.3	14.9	23.4	35.9	53.2	82.7	137.7	230.0	330.2	325.0	263.1
95°	33.2	34.2	42.3	53.4	75.6	121.0	228.8	450.6	728.9	893.2	874.0
97.5°	55.2	56.5	62.1	73.2	93.1	125.8	197.2	359.7	650.9	953.9	1105.9
100°	70.6	72.6	76.6	87.7	106.8	137.1	195.6	326.6	580.7	910.3	1162.4
102.5°	87.6	88.7	91.9	103.8	121.4	150.8	202.9	313.0	527.5	833.7	1128.5
105°	113.9	113.9	119.0	129.1	145.2	173.4	217.7	307.5	475.8	730.8	1020.3
107.5°	139.8	141.8	146.5	154.8	171.6	197.0	239.9	316.8	454.0	660.1	909.7
110°	158.2	160.3	164.3	173.4	188.5	214.7	256.1	325.6	447.6	627.0	846.8



TEST NUMBER: P333285-840

CATALOG NUMBER: S125DIP-S1090D1035U840-4F0-1E-UDD-F4

CANDELA DISTRIBUTION (continued):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	176.8	178.8	182.1	191.2	206.2	231.7	271.4	336.9	447.6	607.7	800.0
115°	203.7	205.6	208.6	217.7	232.9	258.1	295.4	353.9	450.6	586.7	749.0
117.5°	227.8	230.9	234.1	243.2	260.3	284.7	320.0	373.2	457.3	576.4	718.6
120°	244.0	247.0	251.1	260.1	277.2	302.5	337.7	386.1	463.7	571.6	701.7
122.5°	260.9	263.1	266.3	275.4	294.2	319.4	354.7	400.6	469.4	567.5	687.1
125°	282.3	284.3	289.3	298.4	317.6	343.8	377.1	420.4	478.9	562.5	667.4
127.5°	299.0	302.1	308.5	320.0	340.3	366.6	398.6	438.5	489.6	560.1	649.2
130°	309.5	312.6	320.6	333.7	354.9	381.0	412.3	450.6	496.0	558.5	637.1
132.5°	317.6	321.3	331.0	345.8	367.8	393.9	425.3	461.1	503.2	558.5	627.4
135°	330.6	334.7	346.8	362.9	384.1	411.3	442.5	475.8	513.1	558.5	615.9
137.5°	347.2	350.2	361.5	377.7	398.4	426.5	454.8	486.8	522.2	559.7	605.7
140°	356.9	359.9	372.0	388.1	407.3	434.5	463.7	494.0	526.2	560.5	600.9
142.5°	368.2	370.4	381.6	397.8	416.2	441.7	469.4	498.0	528.7	561.3	596.8
145°	385.1	387.1	397.2	411.3	429.5	452.6	478.9	504.0	531.3	560.5	590.8
147.5°	402.8	404.0	412.7	425.9	441.5	461.9	484.9	507.7	532.3	557.8	584.5
150°	413.3	415.4	422.4	435.6	449.6	466.8	489.0	510.1	532.3	555.4	579.7
152.5°	424.6	425.9	432.1	443.5	456.9	472.4	493.0	511.7	531.5	552.3	574.0
155°	439.5	439.5	445.6	455.7	465.7	479.9	497.0	513.1	529.3	546.4	564.5
157.5°	452.8	452.6	457.5	466.2	475.0	485.7	500.4	514.1	526.6	540.4	555.6
160°	461.7	460.7	464.7	471.8	479.9	489.0	502.0	514.1	524.2	536.3	548.5
162.5°	469.0	468.0	472.0	478.3	484.7	492.2	503.6	513.3	521.8	531.5	542.0
165°	479.9	477.9	480.9	485.9	490.0	496.0	504.0	512.1	518.2	524.2	532.3
167.5°	487.2	486.1	488.0	490.8	493.6	497.4	504.0	509.7	512.5	517.2	522.8
170°	492.0	491.0	492.0	494.0	496.0	499.0	504.0	508.1	510.1	513.1	517.2
172.5°	495.2	493.4	494.4	496.3	497.6	499.0	503.2	506.4	506.9	508.3	511.5
175°	499.0	497.0	498.0	499.0	499.0	499.0	502.0	504.0	503.0	503.0	504.0
177.5°	500.8	499.2	499.2	500.0	499.2	499.2	500.8	501.6	500.0	500.0	500.8
180°	500.0	500.0	500.0	500.0	500.0	500.0	500.0	500.0	500.0	500.0	500.0



TEST NUMBER: P333285-840

CATALOG NUMBER: S125DIP-S1090D1035U840-4F0-1E-UDD-F4

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°
0°	1723.2	1723.2	1723.2	1723.2	1723.2	1723.2	1723.2	1723.2
2.5°	1718.2	1720.6	1723.0	1724.1	1723.9	1723.6	1723.4	1723.2
5°	1709.6	1712.3	1715.1	1716.3	1716.0	1715.7	1715.4	1715.1
7.5°	1692.2	1695.0	1697.6	1698.8	1698.5	1698.2	1697.9	1697.6
10°	1677.6	1680.0	1682.4	1683.5	1683.2	1682.9	1682.6	1682.3
12.5°	1658.1	1660.0	1661.9	1662.9	1662.8	1662.7	1662.7	1662.6
15°	1624.0	1625.5	1627.0	1627.8	1627.8	1627.8	1627.8	1627.8
17.5°	1584.4	1586.2	1588.1	1588.3	1586.8	1585.3	1583.8	1582.3
20°	1554.3	1556.4	1558.5	1558.8	1557.3	1555.8	1554.3	1552.8
22.5°	1520.1	1521.6	1522.9	1523.1	1522.1	1521.1	1520.0	1518.9
25°	1465.4	1466.0	1466.6	1466.4	1465.5	1464.6	1463.7	1462.8
27.5°	1408.0	1408.1	1408.3	1407.9	1406.9	1406.0	1405.1	1404.2
30°	1366.1	1365.5	1364.9	1364.2	1363.3	1362.4	1361.5	1360.6
32.5°	1323.7	1322.6	1321.6	1320.2	1318.6	1317.0	1315.2	1313.6
35°	1258.0	1256.5	1255.0	1253.0	1250.6	1248.2	1245.8	1243.3
37.5°	1188.9	1186.7	1184.5	1182.7	1181.2	1179.8	1178.4	1177.1
40°	1141.0	1138.3	1135.6	1133.8	1132.9	1132.0	1131.0	1130.1
42.5°	1093.6	1091.1	1088.6	1086.6	1085.3	1083.9	1082.5	1081.1
45°	1023.4	1019.8	1016.1	1013.8	1012.9	1012.0	1011.1	1010.2
47.5°	949.4	945.6	942.0	939.1	937.0	934.8	932.7	930.6
50°	898.7	894.7	890.8	887.8	885.7	883.5	881.4	879.3
52.5°	849.5	846.1	842.6	839.7	837.3	835.0	832.6	830.2
55°	773.0	770.2	767.5	765.1	763.0	760.8	758.7	756.6
57.5°	697.0	693.5	689.9	687.6	686.5	685.3	684.2	683.0
60°	645.6	642.6	639.5	636.9	634.8	632.7	630.6	628.4
62.5°	596.0	592.8	589.5	587.0	585.4	583.8	582.1	580.5
65°	518.1	515.3	512.6	510.6	509.4	508.2	507.0	505.7
67.5°	443.6	441.3	439.0	437.5	436.8	436.1	435.4	434.6
70°	394.5	392.6	390.8	389.3	388.1	386.9	385.7	384.5
72.5°	348.2	346.1	344.1	342.4	341.2	340.0	338.8	337.6
75°	276.3	275.4	274.5	273.4	272.2	270.9	269.7	268.5
77.5°	210.5	210.0	209.4	208.7	207.8	207.0	206.1	205.3
80°	168.4	168.1	167.8	167.3	166.7	166.1	165.5	164.9
82.5°	128.7	128.2	127.6	127.2	127.1	127.0	126.9	126.7
85°	75.7	75.4	75.1	74.6	74.0	73.4	72.8	72.2
87.5°	32.0	32.2	32.4	32.5	32.1	31.6	31.3	30.8
90°	18.2	19.2	20.2	22.2	22.2	22.2	23.2	23.2
92.5°	178.6	129.7	97.6	82.7	69.8	67.4	65.9	64.3
95°	724.9	571.6	447.6	362.9	291.3	261.2	253.1	236.9
97.5°	1079.5	972.0	851.2	733.5	671.3	614.7	585.5	572.6
100°	1240.0	1190.6	1086.7	981.9	912.3	839.8	802.4	786.4
102.5°	1294.0	1324.4	1274.7	1203.7	1129.3	1077.7	1037.1	1025.0
105°	1262.1	1400.3	1444.6	1433.5	1401.3	1368.1	1347.9	1335.7
107.5°	1148.4	1332.7	1446.6	1499.2	1515.6	1515.4	1508.7	1500.7
110°	1064.6	1256.1	1398.3	1484.0	1529.3	1548.4	1555.5	1555.5



TEST NUMBER: P333285-840

CATALOG NUMBER: S125DIP-S1090D1035U840-4F0-1E-UDD-F4

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°
112.5°	998.5	1180.3	1324.0	1425.1	1491.4	1524.3	1541.9	1549.0
115°	915.3	1071.7	1209.7	1319.6	1398.3	1446.6	1474.9	1488.0
117.5°	861.7	996.4	1115.4	1216.2	1294.8	1344.8	1372.8	1380.9
120°	832.7	953.7	1064.6	1153.3	1227.9	1276.3	1303.5	1311.6
122.5°	810.9	923.0	1021.8	1104.9	1171.4	1215.8	1243.0	1250.3
125°	779.3	882.1	969.8	1042.4	1098.8	1140.1	1162.4	1172.5
127.5°	747.0	843.0	924.8	992.8	1044.0	1080.5	1101.5	1105.9
130°	726.9	815.6	894.2	959.8	1010.2	1043.4	1063.6	1069.6
132.5°	706.7	789.7	861.1	924.2	974.6	1007.9	1026.4	1033.3
135°	680.4	750.0	814.6	872.0	916.4	949.7	967.8	973.8
137.5°	658.3	714.6	768.2	817.0	856.7	887.0	903.7	910.3
140°	646.2	693.6	739.9	782.3	819.6	845.9	860.9	866.0
142.5°	635.7	675.8	715.8	752.5	784.2	806.3	820.6	824.9
145°	622.0	653.3	684.5	711.8	735.9	753.1	764.2	768.2
147.5°	609.2	634.5	658.5	679.0	698.2	712.0	718.4	720.2
150°	601.9	624.0	643.2	661.4	676.4	688.5	692.6	693.6
152.5°	593.8	613.5	631.1	645.2	657.9	667.6	671.6	672.6
155°	581.7	597.8	612.0	623.0	633.1	640.2	643.2	644.2
157.5°	569.6	582.9	593.8	602.5	610.4	616.1	618.9	618.7
160°	561.5	571.6	581.7	588.8	595.8	600.9	602.9	601.9
162.5°	552.7	561.9	570.4	576.6	582.1	586.3	586.7	586.5
165°	540.4	547.4	553.5	558.5	562.5	564.5	564.5	564.5
167.5°	528.7	533.3	538.0	541.6	543.6	545.4	544.6	544.4
170°	522.2	525.2	528.3	530.3	532.3	533.3	533.3	532.3
172.5°	514.9	518.0	520.2	521.4	521.8	523.6	522.0	521.0
175°	507.1	507.1	509.1	509.1	509.1	510.1	508.1	507.1
177.5°	501.6	502.4	502.4	502.4	501.6	502.4	500.0	500.0
180°	500.0	500.0	500.0	500.0	500.0	500.0	500.0	500.0

(END OF REPORT)