

Scaled data based on original data using  
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State  
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P331681-927

Luminaire Tested: **SA2XXRDIP-C675D530U927-4F0-1E-UDD-A**

Issue Date: 10/7/2019

**Test Information**

Test Method: LM-79-08  
Report Number: P331681-927  
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-2,  
Test Lab: INNOVATION CENTER  
Issue Date: 10/7/2019  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: NEO-RAY  
Catalog Number: SA2XXRDIP-C675D530U927-4F0-1E-UDD-A  
Description: DEFINE 2 DIRECT-INDIRECT PENDANT LED LUMINAIRE  
DOWNLIGHT 675 LUMENS PER FOOT, ASYMMETRIC DIFFUSER, REGRESSED HOUSING  
UPLIGHT 530 LUMENS PER FOOT, NO LENS  
Light Source: -  
Ballast/Driver: ELECTRONIC DRIVER

**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 3687.0 lumens  
Efficiency: N/A  
Efficacy: 91.5 lumens/watt  
Spacing Criteria (0/90/45): 0.86 / 1.16 / 1.02  
Luminous Opening: Rectangular (W 4' x L: 0.17' x H: 0')  
CIE Type: General Diffuse


Input Watts (W): 40.3  
Input Voltage (V): 120  
Input Current (Ain): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 25 FT



TEST NUMBER: P331681-927

CATALOG NUMBER: SA2XXRDIP-C675D530U927-4F0-1E-UDD-A

### Luminous Intensity Polar Plot





TEST NUMBER: P331681-927

CATALOG NUMBER: SA2XXRDIP-C675D530U927-4F0-1E-UDD-A

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20					20					20					20					20	
RC	80					70					50					30					10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0	
RCR																						
0	108	108	108	108	100	100	100	100	86	86	86	73	73	73	60	60	60	55				55
1	100	96	92	89	92	89	86	83	77	74	72	65	64	62	55	54	53				48	
2	91	85	79	74	85	79	74	70	68	64	61	58	56	53	49	47	46				41	
3	84	75	68	63	78	70	64	59	61	56	53	52	49	46	44	42	40				36	
4	77	67	60	54	72	63	56	51	55	50	46	47	44	40	40	38	35				32	
5	71	60	53	47	66	57	50	45	50	44	40	43	39	36	37	34	31				28	
6	66	55	47	41	62	51	44	39	45	40	36	39	35	32	34	31	28				25	
7	62	50	42	37	57	47	40	35	41	36	32	36	32	29	31	28	26				23	
8	57	46	38	33	53	43	36	32	38	33	29	33	29	26	29	26	23				21	
9	54	42	35	30	50	40	33	29	35	30	26	31	27	24	27	24	21				19	
10	50	39	32	27	47	37	30	26	33	27	24	29	25	22	25	22	20				18	

**AVERAGE LUMINANCE (cd/sqm):**

	0°	90°	180°	270°
0°	18791	18791	18791	18791
5°	20985	18908	16765	18908
10°	23282	18775	14532	18775
15°	24428	18501	11450	18501
20°	21179	18093	9907	18093
25°	13890	17533	8845	17533
30°	9350	16858	8006	16858
35°	7571	16005	7222	16005
40°	6734	15076	6681	15076
45°	6094	13988	5966	13988
50°	5546	12911	5526	12911
55°	5213	11713	5146	11713
60°	4363	10618	4308	10618
65°	3679	9639	4172	9639
70°	3399	8611	3932	8611
75°	3175	7492	3631	7492
80°	2929	6165	3236	6165
85°	2705	4872	2853	4872



TEST NUMBER: P331681-927

CATALOG NUMBER: SA2XXRDIP-C675D530U927-4F0-1E-UDD-A

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	110.3	3.0
10°-20°	307.4	8.3
20°-30°	396.1	10.7
30°-40°	376.4	10.2
40°-50°	322.5	8.7
50°-60°	245.6	6.7
60°-70°	155.2	4.2
70°-80°	77.5	2.1
80°-90°	21.6	0.6
90°-100°	19.1	0.5
100°-110°	69.9	1.9
110°-120°	186.8	5.1
120°-130°	308.4	8.4
130°-140°	328.0	8.9
140°-150°	304.8	8.3
150°-160°	245.1	6.6
160°-170°	157.9	4.3
170°-180°	54.4	1.5
0°-30°	813.8	22.1
0°-40°	1190.3	32.3
0°-60°	1758.3	47.7
0°-90°	2012.7	54.6
90°-120°	275.8	7.5
90°-150°	1217.0	33.0
90°-180°	1674.0	45.4
0°-180°	3687.0	100.0

**CANDELA DISTRIBUTION:**

	0°	90°	180°	270°	360°	Flux
0°	1164	1164	1164	1164	1164	
5°	1295	1167	1034	1167	1295	128
15°	1461	1107	685	1107	1461	394
25°	780	984	496	984	780	370
35°	384	812	366	812	384	246
45°	267	613	261	613	267	207
55°	185	416	183	416	185	163
65°	96	252	109	252	96	98
75°	51	120	58	120	51	54
85°	15	26	15	26	15	16
90°	11	0	11	0	11	6
95°	18	27	18	27	18	17
105°	31	126	31	126	31	33
115°	34	238	34	238	34	85
125°	354	336	354	336	354	306
135°	430	416	430	416	430	331
145°	490	482	490	482	490	306
155°	532	531	532	531	532	245
165°	558	560	558	560	558	158
175°	569	573	569	573	569	54
180°	571	571	571	571	571	



TEST NUMBER: P331681-927

CATALOG NUMBER: SA2XXRDIP-C675D530U927-4F0-1E-UDD-A

**CANDELA DISTRIBUTION (FULL):**

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	1163.8	1163.8	1163.8	1163.8	1163.8	1163.8	1163.8	1163.8	1163.8	1163.8	1163.8
2.5°	1211.0	1212.0	1213.0	1210.7	1210.7	1208.7	1204.5	1201.3	1192.2	1191.0	1191.0
5°	1294.8	1294.0	1295.6	1290.4	1283.1	1281.4	1273.7	1263.7	1253.2	1241.4	1239.0
7.5°	1378.1	1376.9	1373.6	1372.8	1367.1	1354.9	1342.6	1329.4	1311.9	1294.9	1286.3
10°	1420.1	1433.5	1425.4	1411.3	1414.1	1395.1	1385.0	1367.6	1353.0	1327.5	1321.9
12.5°	1461.6	1466.8	1464.3	1456.2	1452.5	1439.4	1425.8	1410.6	1383.8	1360.9	1341.0
15°	1461.4	1469.1	1471.1	1468.7	1470.7	1469.9	1462.6	1450.1	1426.6	1401.5	1379.7
17.5°	1353.5	1358.8	1372.1	1381.1	1392.4	1416.3	1428.1	1432.7	1429.3	1415.0	1399.6
20°	1232.6	1223.6	1260.8	1279.8	1296.0	1336.4	1371.2	1384.6	1406.0	1405.6	1401.5
22.5°	1061.0	1063.2	1098.4	1121.0	1168.2	1208.6	1248.3	1298.5	1340.0	1367.4	1383.5
25°	779.7	795.0	830.2	860.9	913.5	988.7	1057.0	1136.3	1211.1	1270.1	1326.4
27.5°	585.5	586.7	614.6	642.9	674.1	735.8	821.8	916.5	1023.1	1111.1	1212.4
30°	501.5	499.0	510.7	528.1	554.8	602.5	667.2	760.3	866.6	999.2	1117.3
32.5°	441.9	442.0	450.9	463.7	485.9	518.1	562.4	637.9	738.5	868.9	1007.3
35°	384.1	383.7	390.2	399.5	408.8	429.4	459.8	499.4	568.5	690.2	831.8
37.5°	342.8	344.5	347.7	353.5	363.8	375.3	393.5	420.1	469.3	541.3	660.3
40°	319.5	320.3	324.7	329.5	335.6	344.5	359.5	380.9	416.9	474.4	561.3
42.5°	298.1	298.9	302.1	306.6	311.3	320.3	332.6	351.2	380.3	425.2	496.9
45°	266.9	266.9	269.7	271.7	277.0	285.1	295.2	310.5	330.8	363.9	411.6
47.5°	237.6	237.7	239.6	243.0	246.4	252.6	262.6	275.1	289.9	315.5	356.2
50°	220.8	221.2	222.4	225.2	227.3	232.9	240.6	251.5	266.9	286.7	320.7
52.5°	207.2	206.9	208.5	209.7	211.1	215.2	220.9	230.5	244.2	261.5	289.6
55°	185.2	183.5	186.0	188.1	189.3	190.8	194.1	200.2	211.9	226.5	247.5
57.5°	157.7	157.1	158.8	160.7	164.5	168.8	171.5	175.4	181.5	191.9	212.8
60°	135.1	135.1	138.7	139.9	144.3	150.0	155.7	158.9	165.0	171.8	187.2
62.5°	115.0	115.3	117.0	118.3	120.7	127.7	135.6	142.8	148.5	155.0	165.2
65°	96.3	97.0	97.0	97.8	99.5	101.1	104.3	110.0	120.1	129.4	137.0
67.5°	81.7	81.9	82.1	82.9	83.4	85.2	86.4	89.0	91.3	100.1	109.6
70°	72.0	73.2	72.8	73.6	74.0	74.8	76.4	77.6	81.3	83.3	89.0
72.5°	62.9	63.8	63.7	64.2	65.3	65.4	66.7	68.0	70.3	72.0	75.0
75°	50.9	50.5	50.9	51.7	52.1	52.6	52.6	54.2	55.4	57.0	59.0
77.5°	39.3	39.7	39.6	39.7	39.8	40.5	40.4	41.2	42.4	43.2	44.1
80°	31.5	31.9	31.5	31.9	32.3	32.7	32.3	32.7	34.0	34.8	34.8
82.5°	24.4	24.5	24.7	24.8	24.9	25.0	25.6	25.7	26.5	26.4	26.7
85°	14.6	14.2	14.2	14.2	14.6	15.0	14.6	14.6	15.0	15.0	15.0
87.5°	7.4	7.7	7.7	7.6	7.6	7.5	7.4	7.7	7.2	7.4	7.0
90°	11.2	11.0	10.8	10.6	10.5	10.1	9.7	9.2	8.7	8.2	7.5
92.5°	11.2	11.1	10.9	10.9	10.7	10.5	10.3	10.1	9.8	9.6	9.2
95°	17.7	17.9	18.0	18.1	18.1	18.0	17.5	17.0	16.6	16.2	15.4
97.5°	23.8	23.6	23.5	23.4	23.3	23.1	22.7	22.3	21.9	21.5	20.1
100°	27.7	27.5	27.3	27.2	26.9	26.5	25.7	25.0	24.3	23.5	22.0
102.5°	29.7	29.4	29.2	28.9	28.7	28.0	27.1	26.1	25.2	24.2	37.3
105°	31.4	31.1	30.7	30.3	29.9	29.2	28.3	27.3	26.2	25.2	50.3
107.5°	32.3	31.9	31.6	31.2	30.9	31.2	32.2	33.3	34.3	35.3	65.4
110°	32.6	32.3	31.9	31.5	31.2	35.6	44.8	53.9	63.1	72.3	98.9



TEST NUMBER: P331681-927

CATALOG NUMBER: SA2XXRDIP-C675D530U927-4F0-1E-UDD-A

**CANDELA DISTRIBUTION (continued):**

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	33.0	32.7	32.4	32.1	31.8	48.4	81.9	115.4	148.9	182.5	189.0
115°	33.9	40.5	47.1	53.7	60.4	84.9	127.5	170.0	212.5	255.1	252.8
117.5°	138.4	160.2	181.9	203.6	225.4	241.4	251.7	262.0	272.3	282.5	281.0
120°	252.2	264.6	277.0	289.4	301.8	307.4	306.3	305.2	304.1	303.0	301.3
122.5°	314.7	317.1	319.5	321.9	324.3	325.2	324.6	323.8	323.2	322.6	320.8
125°	353.5	353.2	352.9	352.7	352.4	351.9	351.3	350.6	350.0	349.4	347.6
127.5°	378.0	377.9	377.9	377.8	377.7	377.2	376.3	375.3	374.4	373.5	372.2
130°	393.2	393.2	393.3	393.4	393.6	393.1	392.1	391.0	390.1	389.0	388.0
132.5°	408.1	408.1	408.2	408.3	408.4	408.1	407.2	406.3	405.4	404.6	403.5
135°	429.5	429.8	429.9	430.1	430.3	429.9	429.0	428.1	427.1	426.2	425.4
137.5°	449.2	449.5	449.7	450.0	450.4	450.1	449.2	448.3	447.4	446.5	445.5
140°	461.4	461.8	462.3	462.7	463.2	463.0	462.2	461.4	460.6	459.7	458.7
142.5°	473.2	473.7	474.2	474.7	475.2	475.0	474.2	473.5	472.7	472.0	470.8
145°	489.9	490.4	490.8	491.3	491.7	491.6	491.0	490.4	489.7	489.1	487.5
147.5°	504.5	504.9	505.3	505.7	506.0	506.0	505.6	505.1	504.6	504.1	502.6
150°	513.5	513.9	514.4	514.8	515.3	515.2	514.7	514.1	513.6	513.0	511.6
152.5°	521.1	521.7	522.3	522.9	523.5	523.6	523.0	522.4	521.9	521.3	519.9
155°	531.6	532.4	533.1	533.9	534.6	534.7	534.2	533.6	533.1	532.5	531.4
157.5°	541.3	542.0	542.7	543.4	544.2	544.2	543.6	543.0	542.3	541.8	541.0
160°	546.9	547.6	548.3	548.9	549.5	549.5	549.0	548.4	548.0	547.4	546.8
162.5°	551.6	552.4	553.2	554.0	554.8	554.8	554.2	553.6	552.9	552.3	551.8
165°	558.5	559.2	559.8	560.5	561.1	561.1	560.5	559.8	559.2	558.5	558.3
167.5°	562.9	563.7	564.6	565.4	566.3	566.3	565.7	565.0	564.4	563.7	563.5
170°	565.5	566.4	567.2	568.0	568.9	568.9	568.3	567.7	567.0	566.4	566.2
172.5°	567.5	568.4	569.2	570.1	570.8	570.9	570.3	569.7	569.0	568.4	568.2
175°	569.3	570.2	571.1	572.0	573.0	573.1	572.4	571.8	571.2	570.5	570.3
177.5°	570.4	571.0	571.6	572.4	573.0	573.1	572.6	572.0	571.6	571.0	570.9
180°	571.3	571.3	571.3	571.3	571.3	571.3	571.3	571.3	571.3	571.3	571.3



TEST NUMBER: P331681-927

CATALOG NUMBER: SA2XXRDIP-C675D530U927-4F0-1E-UDD-A

**CANDELA DISTRIBUTION (continued):**

	55°	60°	65°	70°	75°	80°	85°	90°	95°	100°	105°
0°	1163.8	1163.8	1163.8	1163.8	1163.8	1163.8	1163.8	1163.8	1163.8	1163.8	1163.8
2.5°	1191.6	1189.0	1186.8	1180.9	1178.1	1171.6	1170.6	1170.3	1161.8	1153.7	1151.5
5°	1232.6	1226.1	1216.3	1205.0	1193.3	1181.1	1173.1	1166.6	1150.4	1135.0	1126.2
7.5°	1273.7	1259.9	1243.1	1221.7	1203.8	1183.8	1168.9	1155.6	1132.6	1110.6	1095.7
10°	1304.5	1281.8	1259.6	1230.1	1207.0	1184.4	1163.4	1145.2	1119.3	1090.2	1069.5
12.5°	1323.6	1298.7	1268.0	1239.1	1209.3	1180.5	1152.4	1129.0	1098.6	1068.5	1044.0
15°	1349.4	1322.7	1285.5	1244.3	1205.9	1168.2	1135.9	1106.8	1067.1	1031.2	1001.2
17.5°	1370.5	1333.8	1293.8	1246.1	1201.7	1153.8	1112.1	1075.0	1030.9	987.5	952.2
20°	1377.3	1340.9	1294.8	1247.1	1194.5	1138.3	1093.4	1053.0	1005.7	958.4	917.9
22.5°	1373.1	1344.8	1293.5	1236.4	1182.6	1123.7	1073.0	1026.1	973.7	925.3	878.5
25°	1344.6	1334.8	1286.3	1224.0	1162.6	1094.2	1035.6	984.2	924.4	872.7	821.7
27.5°	1277.9	1298.9	1268.8	1202.5	1134.2	1060.9	995.0	936.5	874.4	816.2	765.4
30°	1213.9	1262.0	1249.1	1187.6	1111.2	1039.3	965.3	904.2	837.9	778.0	727.9
32.5°	1126.2	1205.8	1218.4	1167.0	1087.9	1008.8	931.3	870.5	801.3	738.2	689.4
35°	986.7	1105.6	1160.2	1127.4	1048.1	962.8	882.7	812.0	742.4	680.2	631.6
37.5°	820.1	982.1	1073.0	1075.4	1002.6	913.9	826.7	756.5	685.2	624.1	571.6
40°	712.1	887.6	1006.1	1032.4	970.9	875.0	786.9	715.3	645.8	585.9	525.7
42.5°	615.1	789.9	935.6	981.3	932.4	837.2	748.8	673.9	606.3	549.7	488.1
45°	497.4	650.2	810.8	892.5	865.4	777.2	683.8	612.6	549.1	500.2	441.2
47.5°	419.5	527.3	682.6	793.1	792.7	712.2	620.3	552.2	493.3	447.4	399.6
50°	375.3	469.1	600.5	725.9	736.3	668.8	581.5	514.0	459.0	410.8	372.4
52.5°	335.5	412.8	530.9	651.1	681.0	622.6	537.8	475.5	422.1	377.9	344.9
55°	283.4	343.3	433.1	545.5	590.8	549.5	474.4	416.1	372.8	335.6	307.3
57.5°	239.8	284.7	356.7	447.3	499.9	474.0	411.9	364.6	327.6	294.0	271.6
60°	212.3	249.1	310.1	385.8	444.0	425.8	372.8	328.8	297.2	268.1	247.1
62.5°	186.4	218.0	270.4	331.8	385.2	377.6	334.3	297.4	269.7	243.2	225.4
65°	150.0	173.1	213.9	262.1	304.9	308.6	277.4	252.3	227.7	206.6	190.8
67.5°	119.5	134.5	163.3	203.8	235.9	247.4	228.4	209.2	189.6	173.4	159.7
70°	100.7	112.8	133.9	166.6	196.1	208.3	197.3	182.4	165.4	152.0	140.3
72.5°	81.6	93.4	108.9	132.9	158.3	171.3	167.5	156.9	143.1	132.0	120.9
75°	61.5	65.1	75.7	91.8	111.6	122.9	125.8	120.1	109.2	100.7	94.2
77.5°	45.5	47.6	52.7	61.2	74.1	84.2	88.3	87.7	80.2	75.2	69.2
80°	36.4	37.6	40.0	43.6	53.4	63.5	66.3	66.3	61.1	59.0	53.0
82.5°	27.6	28.5	30.0	32.0	36.5	45.4	48.6	49.2	45.9	43.2	38.4
85°	15.8	15.4	16.2	17.3	18.2	20.6	25.5	26.3	25.5	22.3	21.0
87.5°	6.9	7.1	6.9	6.4	6.5	6.7	8.1	9.4	8.4	7.6	7.1
90°	6.8	6.1	5.3	4.4	3.4	2.5	1.4	0.4	1.4	2.5	3.4
92.5°	8.9	8.5	8.2	8.0	8.1	8.2	8.2	8.3	8.2	8.2	8.1
95°	14.8	14.2	13.5	14.7	17.7	20.8	23.8	26.9	23.8	20.8	17.7
97.5°	18.6	17.1	15.6	19.2	27.7	36.3	44.8	53.3	44.8	36.3	27.7
100°	20.4	18.9	17.3	22.8	35.4	48.0	60.6	73.2	60.6	48.0	35.4
102.5°	50.4	63.5	76.4	84.4	87.0	89.7	92.4	95.0	92.4	89.7	87.0
105°	75.4	100.4	125.6	136.7	134.0	131.2	128.4	125.6	128.4	131.2	134.0
107.5°	95.5	125.6	155.6	169.5	167.3	165.1	162.9	160.7	162.9	165.1	167.3
110°	125.5	152.0	178.6	190.8	188.9	187.0	185.1	183.2	185.1	187.0	188.9





TEST NUMBER: P331681-927

CATALOG NUMBER: SA2XXRDIP-C675D530U927-4F0-1E-UDD-A

**CANDELA DISTRIBUTION (continued):**

	55°	60°	65°	70°	75°	80°	85°	90°	95°	100°	105°
112.5°	195.6	202.2	208.7	211.1	209.5	207.7	206.0	204.3	206.0	207.7	209.5
115°	250.5	248.2	245.9	244.0	242.4	240.8	239.2	237.7	239.2	240.8	242.4
117.5°	279.4	277.8	276.2	274.6	272.8	271.1	269.3	267.6	269.3	271.1	272.8
120°	299.8	298.1	296.4	294.9	293.5	292.2	290.7	289.4	290.7	292.2	293.5
122.5°	318.9	317.1	315.4	313.7	312.3	310.9	309.3	307.9	309.3	310.9	312.3
125°	345.9	344.1	342.4	340.9	339.7	338.5	337.3	336.1	337.3	338.5	339.7
127.5°	370.9	369.6	368.3	366.9	365.6	364.3	363.0	361.6	363.0	364.3	365.6
130°	387.0	386.0	385.0	383.7	382.3	380.8	379.3	377.9	379.3	380.8	382.3
132.5°	402.6	401.6	400.5	399.4	398.2	396.9	395.6	394.4	395.6	396.9	398.2
135°	424.6	423.7	422.9	421.8	420.3	418.8	417.4	415.9	417.4	418.8	420.3
137.5°	444.7	443.7	442.8	441.7	440.7	439.7	438.6	437.7	438.6	439.7	440.7
140°	457.7	456.7	455.7	454.8	454.1	453.4	452.6	451.9	452.6	453.4	454.1
142.5°	469.6	468.5	467.3	466.4	465.7	465.1	464.5	463.7	464.5	465.1	465.7
145°	485.9	484.4	482.8	482.1	482.2	482.3	482.4	482.4	482.4	482.3	482.2
147.5°	501.1	499.5	498.0	497.3	497.7	498.0	498.4	498.8	498.4	498.0	497.7
150°	510.1	508.7	507.2	506.8	507.4	508.0	508.7	509.3	508.7	508.0	507.4
152.5°	518.6	517.1	515.7	515.4	516.1	516.8	517.5	518.2	517.5	516.8	516.1
155°	530.3	529.2	528.1	527.9	528.8	529.6	530.4	531.2	530.4	529.6	528.8
157.5°	540.2	539.4	538.7	538.6	539.3	540.0	540.7	541.4	540.7	540.0	539.3
160°	546.3	545.7	545.2	545.2	545.7	546.3	546.8	547.4	546.8	546.3	545.7
162.5°	551.4	550.9	550.4	550.5	551.0	551.5	552.1	552.6	552.1	551.5	551.0
165°	557.9	557.7	557.5	557.5	558.1	558.6	559.2	559.8	559.2	558.6	558.1
167.5°	563.2	562.9	562.7	562.8	563.4	564.0	564.5	565.1	564.5	564.0	563.4
170°	566.0	565.9	565.6	565.9	566.4	567.0	567.5	568.0	567.5	567.0	566.4
172.5°	568.0	567.8	567.6	567.8	568.4	568.9	569.5	570.1	569.5	568.9	568.4
175°	570.1	570.0	569.8	570.0	570.7	571.3	572.0	572.6	572.0	571.3	570.7
177.5°	570.8	570.8	570.7	570.9	571.5	572.0	572.5	573.0	572.5	572.0	571.5
180°	571.3	571.3	571.3	571.3	571.3	571.3	571.3	571.3	571.3	571.3	571.3



TEST NUMBER: P331681-927

CATALOG NUMBER: SA2XXRDIP-C675D530U927-4F0-1E-UDD-A

**CANDELA DISTRIBUTION (continued):**

	110°	115°	120°	125°	130°	135°	140°	145°	150°	155°	160°
0°	1163.8	1163.8	1163.8	1163.8	1163.8	1163.8	1163.8	1163.8	1163.8	1163.8	1163.8
2.5°	1147.3	1145.0	1140.8	1134.3	1130.4	1123.6	1119.1	1121.7	1122.4	1121.7	1121.1
5°	1116.5	1107.9	1096.2	1084.9	1074.4	1063.1	1056.6	1053.8	1048.1	1044.9	1043.3
7.5°	1079.2	1064.5	1048.0	1028.3	1011.5	994.0	985.0	980.5	968.9	962.7	957.1
10°	1051.4	1028.3	1011.8	985.9	970.1	947.1	931.3	931.7	915.9	907.0	900.6
12.5°	1020.6	995.3	967.7	944.4	922.5	904.0	885.0	877.3	860.5	852.0	834.6
15°	969.7	940.2	911.1	879.5	857.3	828.5	801.1	767.5	740.4	716.9	710.5
17.5°	914.0	877.5	848.3	811.3	773.2	724.8	693.0	673.5	657.2	644.8	635.6
20°	875.8	838.7	807.6	751.7	700.4	667.7	644.2	629.2	612.2	598.9	591.6
22.5°	835.8	796.9	754.5	692.2	652.2	625.9	605.0	587.8	576.3	565.9	559.3
25°	778.8	736.3	666.4	623.5	591.2	563.7	549.1	538.6	526.5	512.3	505.9
27.5°	718.7	651.1	600.9	569.0	538.1	520.2	507.2	491.5	480.6	474.3	467.5
30°	673.7	606.2	567.0	532.2	510.3	490.5	475.2	466.3	455.7	444.8	440.4
32.5°	623.5	569.6	532.0	503.0	480.9	464.0	451.9	437.4	429.8	423.1	413.8
35°	561.3	520.5	486.1	462.6	441.6	427.9	413.7	405.2	391.4	385.8	382.1
37.5°	508.5	473.1	447.5	422.7	406.1	390.9	382.2	368.7	362.7	354.9	347.2
40°	478.8	444.0	419.3	399.1	380.5	369.2	358.3	347.4	338.4	334.9	325.5
42.5°	448.4	420.1	395.4	373.2	360.8	348.8	335.0	327.0	317.7	311.9	306.1
45°	406.4	381.4	360.3	342.1	328.4	315.8	306.9	293.6	288.4	276.6	271.7
47.5°	369.6	346.2	326.1	308.9	295.4	287.2	274.3	263.8	255.4	248.2	242.0
50°	343.3	323.9	304.5	289.1	277.0	265.3	251.9	246.7	233.7	230.0	226.5
52.5°	319.4	301.0	283.1	268.1	256.0	244.5	232.8	225.9	217.2	213.6	211.0
55°	285.9	268.1	251.1	237.7	225.6	213.9	206.6	198.1	194.1	191.2	188.1
57.5°	252.2	236.2	223.2	209.7	197.5	188.2	179.7	174.7	170.5	166.8	162.9
60°	230.9	215.6	203.8	191.2	178.7	171.0	164.6	158.5	153.7	148.0	146.4
62.5°	208.3	194.8	184.1	171.8	161.0	153.9	147.7	142.0	136.2	127.9	125.6
65°	177.1	166.6	155.3	145.2	135.5	128.6	119.7	113.2	110.8	110.0	109.6
67.5°	149.0	139.0	129.3	119.0	110.1	103.8	99.3	98.2	96.6	96.1	95.0
70°	130.2	120.9	111.2	101.5	93.0	91.8	90.2	88.6	86.5	85.7	84.9
72.5°	113.4	103.8	94.0	86.3	82.6	81.1	79.5	77.9	76.5	75.7	75.2
75°	86.9	78.0	71.6	68.8	66.7	65.5	63.1	61.9	61.1	59.8	59.4
77.5°	62.6	57.6	54.6	52.8	50.7	49.4	48.0	46.8	45.9	45.7	45.1
80°	47.7	45.3	43.3	40.9	40.0	38.4	38.0	36.8	37.2	36.0	36.0
82.5°	37.1	34.0	32.2	31.1	30.3	29.1	28.6	28.0	28.1	27.3	27.3
85°	19.0	18.2	17.3	16.6	16.6	15.4	15.8	15.4	15.4	14.6	14.2
87.5°	7.1	6.9	6.4	6.6	6.7	6.5	6.6	6.3	6.5	6.6	6.3
90°	4.4	5.3	6.1	6.8	7.5	8.2	8.7	9.2	9.7	10.1	10.5
92.5°	8.0	8.2	8.5	8.9	9.2	9.6	9.8	10.1	10.3	10.5	10.7
95°	14.7	13.5	14.2	14.8	15.4	16.2	16.6	17.0	17.5	18.0	18.1
97.5°	19.2	15.6	17.1	18.6	20.1	21.5	21.9	22.3	22.7	23.1	23.3
100°	22.8	17.3	18.9	20.4	22.0	23.5	24.3	25.0	25.7	26.5	26.9
102.5°	84.4	76.4	63.5	50.4	37.3	24.2	25.2	26.1	27.1	28.0	28.7
105°	136.7	125.6	100.4	75.4	50.3	25.2	26.2	27.3	28.3	29.2	29.9
107.5°	169.5	155.6	125.6	95.5	65.4	35.3	34.3	33.3	32.2	31.2	30.9
110°	190.8	178.6	152.0	125.5	98.9	72.3	63.1	53.9	44.8	35.6	31.2



TEST NUMBER: P331681-927

CATALOG NUMBER: SA2XXRDIP-C675D530U927-4F0-1E-UDD-A

**CANDELA DISTRIBUTION (continued):**

	110°	115°	120°	125°	130°	135°	140°	145°	150°	155°	160°
112.5°	211.1	208.7	202.2	195.6	189.0	182.5	148.9	115.4	81.9	48.4	31.8
115°	244.0	245.9	248.2	250.5	252.8	255.1	212.5	170.0	127.5	84.9	60.4
117.5°	274.6	276.2	277.8	279.4	281.0	282.5	272.3	262.0	251.7	241.4	225.4
120°	294.9	296.4	298.1	299.8	301.3	303.0	304.1	305.2	306.3	307.4	301.8
122.5°	313.7	315.4	317.1	318.9	320.8	322.6	323.2	323.8	324.6	325.2	324.3
125°	340.9	342.4	344.1	345.9	347.6	349.4	350.0	350.6	351.3	351.9	352.4
127.5°	366.9	368.3	369.6	370.9	372.2	373.5	374.4	375.3	376.3	377.2	377.7
130°	383.7	385.0	386.0	387.0	388.0	389.0	390.1	391.0	392.1	393.1	393.6
132.5°	399.4	400.5	401.6	402.6	403.5	404.6	405.4	406.3	407.2	408.1	408.4
135°	421.8	422.9	423.7	424.6	425.4	426.2	427.1	428.1	429.0	429.9	430.3
137.5°	441.7	442.8	443.7	444.7	445.5	446.5	447.4	448.3	449.2	450.1	450.4
140°	454.8	455.7	456.7	457.7	458.7	459.7	460.6	461.4	462.2	463.0	463.2
142.5°	466.4	467.3	468.5	469.6	470.8	472.0	472.7	473.5	474.2	475.0	475.2
145°	482.1	482.8	484.4	485.9	487.5	489.1	489.7	490.4	491.0	491.6	491.7
147.5°	497.3	498.0	499.5	501.1	502.6	504.1	504.6	505.1	505.6	506.0	506.0
150°	506.8	507.2	508.7	510.1	511.6	513.0	513.6	514.1	514.7	515.2	515.3
152.5°	515.4	515.7	517.1	518.6	519.9	521.3	521.9	522.4	523.0	523.6	523.5
155°	527.9	528.1	529.2	530.3	531.4	532.5	533.1	533.6	534.2	534.7	534.6
157.5°	538.6	538.7	539.4	540.2	541.0	541.8	542.3	543.0	543.6	544.2	544.2
160°	545.2	545.2	545.7	546.3	546.8	547.4	548.0	548.4	549.0	549.5	549.5
162.5°	550.5	550.4	550.9	551.4	551.8	552.3	552.9	553.6	554.2	554.8	554.8
165°	557.5	557.5	557.7	557.9	558.3	558.5	559.2	559.8	560.5	561.1	561.1
167.5°	562.8	562.7	562.9	563.2	563.5	563.7	564.4	565.0	565.7	566.3	566.3
170°	565.9	565.6	565.9	566.0	566.2	566.4	567.0	567.7	568.3	568.9	568.9
172.5°	567.8	567.6	567.8	568.0	568.2	568.4	569.0	569.7	570.3	570.9	570.8
175°	570.0	569.8	570.0	570.1	570.3	570.5	571.2	571.8	572.4	573.1	573.0
177.5°	570.9	570.7	570.8	570.8	570.9	571.0	571.6	572.0	572.6	573.1	573.0
180°	571.3	571.3	571.3	571.3	571.3	571.3	571.3	571.3	571.3	571.3	571.3



TEST NUMBER: P331681-927

CATALOG NUMBER: SA2XXRDIP-C675D530U927-4F0-1E-UDD-A

**CANDELA DISTRIBUTION (continued):**

	165°	170°	175°	180°	185°	190°	195°	200°	205°	210°	215°
0°	1163.8	1163.8	1163.8	1163.8	1163.8	1163.8	1163.8	1163.8	1163.8	1163.8	1163.8
2.5°	1117.5	1118.2	1117.2	1117.8	1117.2	1118.2	1117.5	1121.1	1121.7	1122.4	1121.7
5°	1041.2	1036.4	1035.6	1034.4	1035.6	1036.4	1041.2	1043.3	1044.9	1048.1	1053.8
7.5°	950.2	949.4	947.5	944.6	947.5	949.4	950.2	957.1	962.7	968.9	980.5
10°	891.6	889.6	889.2	886.4	889.2	889.6	891.6	900.6	907.0	915.9	931.7
12.5°	823.1	810.0	808.7	801.6	808.7	810.0	823.1	834.6	852.0	860.5	877.3
15°	700.8	698.4	690.2	685.0	690.2	698.4	700.8	710.5	716.9	740.4	767.5
17.5°	630.9	623.0	620.4	619.3	620.4	623.0	630.9	635.6	644.8	657.2	673.5
20°	585.9	578.7	577.4	576.6	577.4	578.7	585.9	591.6	598.9	612.2	629.2
22.5°	554.8	547.2	544.2	541.7	544.2	547.2	554.8	559.3	565.9	576.3	587.8
25°	501.8	499.0	497.4	496.5	497.4	499.0	501.8	505.9	512.3	526.5	538.6
27.5°	460.3	454.1	452.9	450.8	452.9	454.1	460.3	467.5	474.3	480.6	491.5
30°	436.7	434.7	431.9	429.4	431.9	434.7	436.7	440.4	444.8	455.7	466.3
32.5°	408.9	407.2	404.7	403.5	404.7	407.2	408.9	413.8	423.1	429.8	437.4
35°	378.1	372.4	370.0	366.4	370.0	372.4	378.1	382.1	385.8	391.4	405.2
37.5°	345.5	342.5	339.1	340.3	339.1	342.5	345.5	347.2	354.9	362.7	368.7
40°	320.3	318.2	317.4	317.0	317.4	318.2	320.3	325.5	334.9	338.4	347.4
42.5°	300.2	294.6	292.6	292.5	292.6	294.6	300.2	306.1	311.9	317.7	327.0
45°	269.7	264.4	260.8	261.3	260.8	264.4	269.7	271.7	276.6	288.4	293.6
47.5°	238.5	238.4	236.1	236.8	236.1	238.4	238.5	242.0	248.2	255.4	263.8
50°	223.6	221.2	219.6	220.0	219.6	221.2	223.6	226.5	230.0	233.7	246.7
52.5°	209.4	207.3	206.0	207.7	206.0	207.3	209.4	211.0	213.6	217.2	225.9
55°	186.0	183.5	183.2	182.8	183.2	183.5	186.0	188.1	191.2	194.1	198.1
57.5°	159.9	158.3	155.8	154.8	155.8	158.3	159.9	162.9	166.8	170.5	174.7
60°	141.1	137.9	133.9	133.4	133.9	137.9	141.1	146.4	148.0	153.7	158.5
62.5°	124.0	123.3	122.6	122.5	122.6	123.3	124.0	125.6	127.9	136.2	142.0
65°	108.8	108.4	108.8	109.2	108.8	108.4	108.8	109.6	110.0	110.8	113.2
67.5°	94.8	94.0	93.3	93.6	93.3	94.0	94.8	95.0	96.1	96.6	98.2
70°	84.1	83.7	83.3	83.3	83.3	83.7	84.1	84.9	85.7	86.5	88.6
72.5°	73.8	73.7	73.3	73.0	73.3	73.7	73.8	75.2	75.7	76.5	77.9
75°	59.0	58.2	58.2	58.2	58.2	58.2	59.0	59.4	59.8	61.1	61.9
77.5°	45.0	44.6	44.1	43.8	44.1	44.6	45.0	45.1	45.7	45.9	46.8
80°	35.6	35.2	34.8	34.8	34.8	35.2	35.6	36.0	36.0	37.2	36.8
82.5°	27.2	26.8	26.7	26.4	26.7	26.8	27.2	27.3	27.3	28.1	28.0
85°	14.6	15.0	14.6	15.4	14.6	15.0	14.6	14.2	14.6	15.4	15.4
87.5°	6.3	6.0	6.4	6.1	6.4	6.0	6.3	6.3	6.6	6.5	6.3
90°	10.6	10.8	11.0	11.2	11.0	10.8	10.6	10.5	10.1	9.7	9.2
92.5°	10.9	10.9	11.1	11.2	11.1	10.9	10.9	10.7	10.5	10.3	10.1
95°	18.1	18.0	17.9	17.7	17.9	18.0	18.1	18.1	18.0	17.5	17.0
97.5°	23.4	23.5	23.6	23.8	23.6	23.5	23.4	23.3	23.1	22.7	22.3
100°	27.2	27.3	27.5	27.7	27.5	27.3	27.2	26.9	26.5	25.7	25.0
102.5°	28.9	29.2	29.4	29.7	29.4	29.2	28.9	28.7	28.0	27.1	26.1
105°	30.3	30.7	31.1	31.4	31.1	30.7	30.3	29.9	29.2	28.3	27.3
107.5°	31.2	31.6	31.9	32.3	31.9	31.6	31.2	30.9	31.2	32.2	33.3
110°	31.5	31.9	32.3	32.6	32.3	31.9	31.5	31.2	35.6	44.8	53.9



TEST NUMBER: P331681-927

CATALOG NUMBER: SA2XXRDIP-C675D530U927-4F0-1E-UDD-A

**CANDELA DISTRIBUTION (continued):**

	165°	170°	175°	180°	185°	190°	195°	200°	205°	210°	215°
112.5°	32.1	32.4	32.7	33.0	32.7	32.4	32.1	31.8	48.4	81.9	115.4
115°	53.7	47.1	40.5	33.9	40.5	47.1	53.7	60.4	84.9	127.5	170.0
117.5°	203.6	181.9	160.2	138.4	160.2	181.9	203.6	225.4	241.4	251.7	262.0
120°	289.4	277.0	264.6	252.2	264.6	277.0	289.4	301.8	307.4	306.3	305.2
122.5°	321.9	319.5	317.1	314.7	317.1	319.5	321.9	324.3	325.2	324.6	323.8
125°	352.7	352.9	353.2	353.5	353.2	352.9	352.7	352.4	351.9	351.3	350.6
127.5°	377.8	377.9	377.9	378.0	377.9	377.9	377.8	377.7	377.2	376.3	375.3
130°	393.4	393.3	393.2	393.2	393.2	393.3	393.4	393.6	393.1	392.1	391.0
132.5°	408.3	408.2	408.1	408.1	408.1	408.2	408.3	408.4	408.1	407.2	406.3
135°	430.1	429.9	429.8	429.5	429.8	429.9	430.1	430.3	429.9	429.0	428.1
137.5°	450.0	449.7	449.5	449.2	449.5	449.7	450.0	450.4	450.1	449.2	448.3
140°	462.7	462.3	461.8	461.4	461.8	462.3	462.7	463.2	463.0	462.2	461.4
142.5°	474.7	474.2	473.7	473.2	473.7	474.2	474.7	475.2	475.0	474.2	473.5
145°	491.3	490.8	490.4	489.9	490.4	490.8	491.3	491.7	491.6	491.0	490.4
147.5°	505.7	505.3	504.9	504.5	504.9	505.3	505.7	506.0	506.0	505.6	505.1
150°	514.8	514.4	513.9	513.5	513.9	514.4	514.8	515.3	515.2	514.7	514.1
152.5°	522.9	522.3	521.7	521.1	521.7	522.3	522.9	523.5	523.6	523.0	522.4
155°	533.9	533.1	532.4	531.6	532.4	533.1	533.9	534.6	534.7	534.2	533.6
157.5°	543.4	542.7	542.0	541.3	542.0	542.7	543.4	544.2	544.2	543.6	543.0
160°	548.9	548.3	547.6	546.9	547.6	548.3	548.9	549.5	549.5	549.0	548.4
162.5°	554.0	553.2	552.4	551.6	552.4	553.2	554.0	554.8	554.8	554.2	553.6
165°	560.5	559.8	559.2	558.5	559.2	559.8	560.5	561.1	561.1	560.5	559.8
167.5°	565.4	564.6	563.7	562.9	563.7	564.6	565.4	566.3	566.3	565.7	565.0
170°	568.0	567.2	566.4	565.5	566.4	567.2	568.0	568.9	568.9	568.3	567.7
172.5°	570.1	569.2	568.4	567.5	568.4	569.2	570.1	570.8	570.9	570.3	569.7
175°	572.0	571.1	570.2	569.3	570.2	571.1	572.0	573.0	573.1	572.4	571.8
177.5°	572.4	571.6	571.0	570.4	571.0	571.6	572.4	573.0	573.1	572.6	572.0
180°	571.3	571.3	571.3	571.3	571.3	571.3	571.3	571.3	571.3	571.3	571.3



TEST NUMBER: P331681-927

CATALOG NUMBER: SA2XXRDIP-C675D530U927-4F0-1E-UDD-A

**CANDELA DISTRIBUTION (continued):**

	220°	225°	230°	235°	240°	245°	250°	255°	260°	265°	270°
0°	1163.8	1163.8	1163.8	1163.8	1163.8	1163.8	1163.8	1163.8	1163.8	1163.8	1163.8
2.5°	1119.1	1123.6	1130.4	1134.3	1140.8	1145.0	1147.3	1151.5	1153.7	1161.8	1170.3
5°	1056.6	1063.1	1074.4	1084.9	1096.2	1107.9	1116.5	1126.2	1135.0	1150.4	1166.6
7.5°	985.0	994.0	1011.5	1028.3	1048.0	1064.5	1079.2	1095.7	1110.6	1132.6	1155.6
10°	931.3	947.1	970.1	985.9	1011.8	1028.3	1051.4	1069.5	1090.2	1119.3	1145.2
12.5°	885.0	904.0	922.5	944.4	967.7	995.3	1020.6	1044.0	1068.5	1098.6	1129.0
15°	801.1	828.5	857.3	879.5	911.1	940.2	969.7	1001.2	1031.2	1067.1	1106.8
17.5°	693.0	724.8	773.2	811.3	848.3	877.5	914.0	952.2	987.5	1030.9	1075.0
20°	644.2	667.7	700.4	751.7	807.6	838.7	875.8	917.9	958.4	1005.7	1053.0
22.5°	605.0	625.9	652.2	692.2	754.5	796.9	835.8	878.5	925.3	973.7	1026.1
25°	549.1	563.7	591.2	623.5	666.4	736.3	778.8	821.7	872.7	924.4	984.2
27.5°	507.2	520.2	538.1	569.0	600.9	651.1	718.7	765.4	816.2	874.4	936.5
30°	475.2	490.5	510.3	532.2	567.0	606.2	673.7	727.9	778.0	837.9	904.2
32.5°	451.9	464.0	480.9	503.0	532.0	569.6	623.5	689.4	738.2	801.3	870.5
35°	413.7	427.9	441.6	462.6	486.1	520.5	561.3	631.6	680.2	742.4	812.0
37.5°	382.2	390.9	406.1	422.7	447.5	473.1	508.5	571.6	624.1	685.2	756.5
40°	358.3	369.2	380.5	399.1	419.3	444.0	478.8	525.7	585.9	645.8	715.3
42.5°	335.0	348.8	360.8	373.2	395.4	420.1	448.4	488.1	549.7	606.3	673.9
45°	306.9	315.8	328.4	342.1	360.3	381.4	406.4	441.2	500.2	549.1	612.6
47.5°	274.3	287.2	295.4	308.9	326.1	346.2	369.6	399.6	447.4	493.3	552.2
50°	251.9	265.3	277.0	289.1	304.5	323.9	343.3	372.4	410.8	459.0	514.0
52.5°	232.8	244.5	256.0	268.1	283.1	301.0	319.4	344.9	377.9	422.1	475.5
55°	206.6	213.9	225.6	237.7	251.1	268.1	285.9	307.3	335.6	372.8	416.1
57.5°	179.7	188.2	197.5	209.7	223.2	236.2	252.2	271.6	294.0	327.6	364.6
60°	164.6	171.0	178.7	191.2	203.8	215.6	230.9	247.1	268.1	297.2	328.8
62.5°	147.7	153.9	161.0	171.8	184.1	194.8	208.3	225.4	243.2	269.7	297.4
65°	119.7	128.6	135.5	145.2	155.3	166.6	177.1	190.8	206.6	227.7	252.3
67.5°	99.3	103.8	110.1	119.0	129.3	139.0	149.0	159.7	173.4	189.6	209.2
70°	90.2	91.8	93.0	101.5	111.2	120.9	130.2	140.3	152.0	165.4	182.4
72.5°	79.5	81.1	82.6	86.3	94.0	103.8	113.4	120.9	132.0	143.1	156.9
75°	63.1	65.5	66.7	68.8	71.6	78.0	86.9	94.2	100.7	109.2	120.1
77.5°	48.0	49.4	50.7	52.8	54.6	57.6	62.6	69.2	75.2	80.2	87.7
80°	38.0	38.4	40.0	40.9	43.3	45.3	47.7	53.0	59.0	61.1	66.3
82.5°	28.6	29.1	30.3	31.1	32.2	34.0	37.1	38.4	43.2	45.9	49.2
85°	15.8	15.4	16.6	16.6	17.3	18.2	19.0	21.0	22.3	25.5	26.3
87.5°	6.6	6.5	6.7	6.6	6.4	6.9	7.1	7.1	7.6	8.4	9.4
90°	8.7	8.2	7.5	6.8	6.1	5.3	4.4	3.4	2.5	1.4	0.4
92.5°	9.8	9.6	9.2	8.9	8.5	8.2	8.0	8.1	8.2	8.2	8.3
95°	16.6	16.2	15.4	14.8	14.2	13.5	14.7	17.7	20.8	23.8	26.9
97.5°	21.9	21.5	20.1	18.6	17.1	15.6	19.2	27.7	36.3	44.8	53.3
100°	24.3	23.5	22.0	20.4	18.9	17.3	22.8	35.4	48.0	60.6	73.2
102.5°	25.2	24.2	37.3	50.4	63.5	76.4	84.4	87.0	89.7	92.4	95.0
105°	26.2	25.2	50.3	75.4	100.4	125.6	136.7	134.0	131.2	128.4	125.6
107.5°	34.3	35.3	65.4	95.5	125.6	155.6	169.5	167.3	165.1	162.9	160.7
110°	63.1	72.3	98.9	125.5	152.0	178.6	190.8	188.9	187.0	185.1	183.2



TEST NUMBER: P331681-927

CATALOG NUMBER: SA2XXRDIP-C675D530U927-4F0-1E-UDD-A

**CANDELA DISTRIBUTION (continued):**

	220°	225°	230°	235°	240°	245°	250°	255°	260°	265°	270°
112.5°	148.9	182.5	189.0	195.6	202.2	208.7	211.1	209.5	207.7	206.0	204.3
115°	212.5	255.1	252.8	250.5	248.2	245.9	244.0	242.4	240.8	239.2	237.7
117.5°	272.3	282.5	281.0	279.4	277.8	276.2	274.6	272.8	271.1	269.3	267.6
120°	304.1	303.0	301.3	299.8	298.1	296.4	294.9	293.5	292.2	290.7	289.4
122.5°	323.2	322.6	320.8	318.9	317.1	315.4	313.7	312.3	310.9	309.3	307.9
125°	350.0	349.4	347.6	345.9	344.1	342.4	340.9	339.7	338.5	337.3	336.1
127.5°	374.4	373.5	372.2	370.9	369.6	368.3	366.9	365.6	364.3	363.0	361.6
130°	390.1	389.0	388.0	387.0	386.0	385.0	383.7	382.3	380.8	379.3	377.9
132.5°	405.4	404.6	403.5	402.6	401.6	400.5	399.4	398.2	396.9	395.6	394.4
135°	427.1	426.2	425.4	424.6	423.7	422.9	421.8	420.3	418.8	417.4	415.9
137.5°	447.4	446.5	445.5	444.7	443.7	442.8	441.7	440.7	439.7	438.6	437.7
140°	460.6	459.7	458.7	457.7	456.7	455.7	454.8	454.1	453.4	452.6	451.9
142.5°	472.7	472.0	470.8	469.6	468.5	467.3	466.4	465.7	465.1	464.5	463.7
145°	489.7	489.1	487.5	485.9	484.4	482.8	482.1	482.2	482.3	482.4	482.4
147.5°	504.6	504.1	502.6	501.1	499.5	498.0	497.3	497.7	498.0	498.4	498.8
150°	513.6	513.0	511.6	510.1	508.7	507.2	506.8	507.4	508.0	508.7	509.3
152.5°	521.9	521.3	519.9	518.6	517.1	515.7	515.4	516.1	516.8	517.5	518.2
155°	533.1	532.5	531.4	530.3	529.2	528.1	527.9	528.8	529.6	530.4	531.2
157.5°	542.3	541.8	541.0	540.2	539.4	538.7	538.6	539.3	540.0	540.7	541.4
160°	548.0	547.4	546.8	546.3	545.7	545.2	545.2	545.7	546.3	546.8	547.4
162.5°	552.9	552.3	551.8	551.4	550.9	550.4	550.5	551.0	551.5	552.1	552.6
165°	559.2	558.5	558.3	557.9	557.7	557.5	557.5	558.1	558.6	559.2	559.8
167.5°	564.4	563.7	563.5	563.2	562.9	562.7	562.8	563.4	564.0	564.5	565.1
170°	567.0	566.4	566.2	566.0	565.9	565.6	565.9	566.4	567.0	567.5	568.0
172.5°	569.0	568.4	568.2	568.0	567.8	567.6	567.8	568.4	568.9	569.5	570.1
175°	571.2	570.5	570.3	570.1	570.0	569.8	570.0	570.7	571.3	572.0	572.6
177.5°	571.6	571.0	570.9	570.8	570.8	570.7	570.9	571.5	572.0	572.5	573.0
180°	571.3	571.3	571.3	571.3	571.3	571.3	571.3	571.3	571.3	571.3	571.3



TEST NUMBER: P331681-927

CATALOG NUMBER: SA2XXRDIP-C675D530U927-4F0-1E-UDD-A

**CANDELA DISTRIBUTION (continued):**

	275°	280°	285°	290°	295°	300°	305°	310°	315°	320°	325°
0°	1163.8	1163.8	1163.8	1163.8	1163.8	1163.8	1163.8	1163.8	1163.8	1163.8	1163.8
2.5°	1170.6	1171.6	1178.1	1180.9	1186.8	1189.0	1191.6	1191.0	1191.0	1192.2	1201.3
5°	1173.1	1181.1	1193.3	1205.0	1216.3	1226.1	1232.6	1239.0	1241.4	1253.2	1263.7
7.5°	1168.9	1183.8	1203.8	1221.7	1243.1	1259.9	1273.7	1286.3	1294.9	1311.9	1329.4
10°	1163.4	1184.4	1207.0	1230.1	1259.6	1281.8	1304.5	1321.9	1327.5	1353.0	1367.6
12.5°	1152.4	1180.5	1209.3	1239.1	1268.0	1298.7	1323.6	1341.0	1360.9	1383.8	1410.6
15°	1135.9	1168.2	1205.9	1244.3	1285.5	1322.7	1349.4	1379.7	1401.5	1426.6	1450.1
17.5°	1112.1	1153.8	1201.7	1246.1	1293.8	1333.8	1370.5	1399.6	1415.0	1429.3	1432.7
20°	1093.4	1138.3	1194.5	1247.1	1294.8	1340.9	1377.3	1401.5	1405.6	1406.0	1384.6
22.5°	1073.0	1123.7	1182.6	1236.4	1293.5	1344.8	1373.1	1383.5	1367.4	1340.0	1298.5
25°	1035.6	1094.2	1162.6	1224.0	1286.3	1334.8	1344.6	1326.4	1270.1	1211.1	1136.3
27.5°	995.0	1060.9	1134.2	1202.5	1268.8	1298.9	1277.9	1212.4	1111.1	1023.1	916.5
30°	965.3	1039.3	1111.2	1187.6	1249.1	1262.0	1213.9	1117.3	999.2	866.6	760.3
32.5°	931.3	1008.8	1087.9	1167.0	1218.4	1205.8	1126.2	1007.3	868.9	738.5	637.9
35°	882.7	962.8	1048.1	1127.4	1160.2	1105.6	986.7	831.8	690.2	568.5	499.4
37.5°	826.7	913.9	1002.6	1075.4	1073.0	982.1	820.1	660.3	541.3	469.3	420.1
40°	786.9	875.0	970.9	1032.4	1006.1	887.6	712.1	561.3	474.4	416.9	380.9
42.5°	748.8	837.2	932.4	981.3	935.6	789.9	615.1	496.9	425.2	380.3	351.2
45°	683.8	777.2	865.4	892.5	810.8	650.2	497.4	411.6	363.9	330.8	310.5
47.5°	620.3	712.2	792.7	793.1	682.6	527.3	419.5	356.2	315.5	289.9	275.1
50°	581.5	668.8	736.3	725.9	600.5	469.1	375.3	320.7	286.7	266.9	251.5
52.5°	537.8	622.6	681.0	651.1	530.9	412.8	335.5	289.6	261.5	244.2	230.5
55°	474.4	549.5	590.8	545.5	433.1	343.3	283.4	247.5	226.5	211.9	200.2
57.5°	411.9	474.0	499.9	447.3	356.7	284.7	239.8	212.8	191.9	181.5	175.4
60°	372.8	425.8	444.0	385.8	310.1	249.1	212.3	187.2	171.8	165.0	158.9
62.5°	334.3	377.6	385.2	331.8	270.4	218.0	186.4	165.2	155.0	148.5	142.8
65°	277.4	308.6	304.9	262.1	213.9	173.1	150.0	137.0	129.4	120.1	110.0
67.5°	228.4	247.4	235.9	203.8	163.3	134.5	119.5	109.6	100.1	91.3	89.0
70°	197.3	208.3	196.1	166.6	133.9	112.8	100.7	89.0	83.3	81.3	77.6
72.5°	167.5	171.3	158.3	132.9	108.9	93.4	81.6	75.0	72.0	70.3	68.0
75°	125.8	122.9	111.6	91.8	75.7	65.1	61.5	59.0	57.0	55.4	54.2
77.5°	88.3	84.2	74.1	61.2	52.7	47.6	45.5	44.1	43.2	42.4	41.2
80°	66.3	63.5	53.4	43.6	40.0	37.6	36.4	34.8	34.8	34.0	32.7
82.5°	48.6	45.4	36.5	32.0	30.0	28.5	27.6	26.7	26.4	26.5	25.7
85°	25.5	20.6	18.2	17.3	16.2	15.4	15.8	15.0	15.0	15.0	14.6
87.5°	8.1	6.7	6.5	6.4	6.9	7.1	6.9	7.0	7.4	7.2	7.7
90°	1.4	2.5	3.4	4.4	5.3	6.1	6.8	7.5	8.2	8.7	9.2
92.5°	8.2	8.2	8.1	8.0	8.2	8.5	8.9	9.2	9.6	9.8	10.1
95°	23.8	20.8	17.7	14.7	13.5	14.2	14.8	15.4	16.2	16.6	17.0
97.5°	44.8	36.3	27.7	19.2	15.6	17.1	18.6	20.1	21.5	21.9	22.3
100°	60.6	48.0	35.4	22.8	17.3	18.9	20.4	22.0	23.5	24.3	25.0
102.5°	92.4	89.7	87.0	84.4	76.4	63.5	50.4	37.3	24.2	25.2	26.1
105°	128.4	131.2	134.0	136.7	125.6	100.4	75.4	50.3	25.2	26.2	27.3
107.5°	162.9	165.1	167.3	169.5	155.6	125.6	95.5	65.4	35.3	34.3	33.3
110°	185.1	187.0	188.9	190.8	178.6	152.0	125.5	98.9	72.3	63.1	53.9





TEST NUMBER: P331681-927

CATALOG NUMBER: SA2XXRDIP-C675D530U927-4F0-1E-UDD-A

**CANDELA DISTRIBUTION (continued):**

	275°	280°	285°	290°	295°	300°	305°	310°	315°	320°	325°
112.5°	206.0	207.7	209.5	211.1	208.7	202.2	195.6	189.0	182.5	148.9	115.4
115°	239.2	240.8	242.4	244.0	245.9	248.2	250.5	252.8	255.1	212.5	170.0
117.5°	269.3	271.1	272.8	274.6	276.2	277.8	279.4	281.0	282.5	272.3	262.0
120°	290.7	292.2	293.5	294.9	296.4	298.1	299.8	301.3	303.0	304.1	305.2
122.5°	309.3	310.9	312.3	313.7	315.4	317.1	318.9	320.8	322.6	323.2	323.8
125°	337.3	338.5	339.7	340.9	342.4	344.1	345.9	347.6	349.4	350.0	350.6
127.5°	363.0	364.3	365.6	366.9	368.3	369.6	370.9	372.2	373.5	374.4	375.3
130°	379.3	380.8	382.3	383.7	385.0	386.0	387.0	388.0	389.0	390.1	391.0
132.5°	395.6	396.9	398.2	399.4	400.5	401.6	402.6	403.5	404.6	405.4	406.3
135°	417.4	418.8	420.3	421.8	422.9	423.7	424.6	425.4	426.2	427.1	428.1
137.5°	438.6	439.7	440.7	441.7	442.8	443.7	444.7	445.5	446.5	447.4	448.3
140°	452.6	453.4	454.1	454.8	455.7	456.7	457.7	458.7	459.7	460.6	461.4
142.5°	464.5	465.1	465.7	466.4	467.3	468.5	469.6	470.8	472.0	472.7	473.5
145°	482.4	482.3	482.2	482.1	482.8	484.4	485.9	487.5	489.1	489.7	490.4
147.5°	498.4	498.0	497.7	497.3	498.0	499.5	501.1	502.6	504.1	504.6	505.1
150°	508.7	508.0	507.4	506.8	507.2	508.7	510.1	511.6	513.0	513.6	514.1
152.5°	517.5	516.8	516.1	515.4	515.7	517.1	518.6	519.9	521.3	521.9	522.4
155°	530.4	529.6	528.8	527.9	528.1	529.2	530.3	531.4	532.5	533.1	533.6
157.5°	540.7	540.0	539.3	538.6	538.7	539.4	540.2	541.0	541.8	542.3	543.0
160°	546.8	546.3	545.7	545.2	545.2	545.7	546.3	546.8	547.4	548.0	548.4
162.5°	552.1	551.5	551.0	550.5	550.4	550.9	551.4	551.8	552.3	552.9	553.6
165°	559.2	558.6	558.1	557.5	557.5	557.7	557.9	558.3	558.5	559.2	559.8
167.5°	564.5	564.0	563.4	562.8	562.7	562.9	563.2	563.5	563.7	564.4	565.0
170°	567.5	567.0	566.4	565.9	565.6	565.9	566.0	566.2	566.4	567.0	567.7
172.5°	569.5	568.9	568.4	567.8	567.6	567.8	568.0	568.2	568.4	569.0	569.7
175°	572.0	571.3	570.7	570.0	569.8	570.0	570.1	570.3	570.5	571.2	571.8
177.5°	572.5	572.0	571.5	570.9	570.7	570.8	570.8	570.9	571.0	571.6	572.0
180°	571.3	571.3	571.3	571.3	571.3	571.3	571.3	571.3	571.3	571.3	571.3



TEST NUMBER: P331681-927

CATALOG NUMBER: SA2XXRDIP-C675D530U927-4F0-1E-UDD-A

**CANDELA DISTRIBUTION (continued):**

	330°	335°	340°	345°	350°	355°	360°
0°	1163.8	1163.8	1163.8	1163.8	1163.8	1163.8	1163.8
2.5°	1204.5	1208.7	1210.7	1210.7	1213.0	1212.0	1211.0
5°	1273.7	1281.4	1283.1	1290.4	1295.6	1294.0	1294.8
7.5°	1342.6	1354.9	1367.1	1372.8	1373.6	1376.9	1378.1
10°	1385.0	1395.1	1414.1	1411.3	1425.4	1433.5	1420.1
12.5°	1425.8	1439.4	1452.5	1456.2	1464.3	1466.8	1461.6
15°	1462.6	1469.9	1470.7	1468.7	1471.1	1469.1	1461.4
17.5°	1428.1	1416.3	1392.4	1381.1	1372.1	1358.8	1353.5
20°	1371.2	1336.4	1296.0	1279.8	1260.8	1223.6	1232.6
22.5°	1248.3	1208.6	1168.2	1121.0	1098.4	1063.2	1061.0
25°	1057.0	988.7	913.5	860.9	830.2	795.0	779.7
27.5°	821.8	735.8	674.1	642.9	614.6	586.7	585.5
30°	667.2	602.5	554.8	528.1	510.7	499.0	501.5
32.5°	562.4	518.1	485.9	463.7	450.9	442.0	441.9
35°	459.8	429.4	408.8	399.5	390.2	383.7	384.1
37.5°	393.5	375.3	363.8	353.5	347.7	344.5	342.8
40°	359.5	344.5	335.6	329.5	324.7	320.3	319.5
42.5°	332.6	320.3	311.3	306.6	302.1	298.9	298.1
45°	295.2	285.1	277.0	271.7	269.7	266.9	266.9
47.5°	262.6	252.6	246.4	243.0	239.6	237.7	237.6
50°	240.6	232.9	227.3	225.2	222.4	221.2	220.8
52.5°	220.9	215.2	211.1	209.7	208.5	206.9	207.2
55°	194.1	190.8	189.3	188.1	186.0	183.5	185.2
57.5°	171.5	168.8	164.5	160.7	158.8	157.1	157.7
60°	155.7	150.0	144.3	139.9	138.7	135.1	135.1
62.5°	135.6	127.7	120.7	118.3	117.0	115.3	115.0
65°	104.3	101.1	99.5	97.8	97.0	97.0	96.3
67.5°	86.4	85.2	83.4	82.9	82.1	81.9	81.7
70°	76.4	74.8	74.0	73.6	72.8	73.2	72.0
72.5°	66.7	65.4	65.3	64.2	63.7	63.8	62.9
75°	52.6	52.6	52.1	51.7	50.9	50.5	50.9
77.5°	40.4	40.5	39.8	39.7	39.6	39.7	39.3
80°	32.3	32.7	32.3	31.9	31.5	31.9	31.5
82.5°	25.6	25.0	24.9	24.8	24.7	24.5	24.4
85°	14.6	15.0	14.6	14.2	14.2	14.2	14.6
87.5°	7.4	7.5	7.6	7.6	7.7	7.7	7.4
90°	9.7	10.1	10.5	10.6	10.8	11.0	11.2
92.5°	10.3	10.5	10.7	10.9	10.9	11.1	11.2
95°	17.5	18.0	18.1	18.1	18.0	17.9	17.7
97.5°	22.7	23.1	23.3	23.4	23.5	23.6	23.8
100°	25.7	26.5	26.9	27.2	27.3	27.5	27.7
102.5°	27.1	28.0	28.7	28.9	29.2	29.4	29.7
105°	28.3	29.2	29.9	30.3	30.7	31.1	31.4
107.5°	32.2	31.2	30.9	31.2	31.6	31.9	32.3
110°	44.8	35.6	31.2	31.5	31.9	32.3	32.6



TEST NUMBER: P331681-927

CATALOG NUMBER: SA2XXRDIP-C675D530U927-4F0-1E-UDD-A

**CANDELA DISTRIBUTION (continued):**

	330°	335°	340°	345°	350°	355°	360°
112.5°	81.9	48.4	31.8	32.1	32.4	32.7	33.0
115°	127.5	84.9	60.4	53.7	47.1	40.5	33.9
117.5°	251.7	241.4	225.4	203.6	181.9	160.2	138.4
120°	306.3	307.4	301.8	289.4	277.0	264.6	252.2
122.5°	324.6	325.2	324.3	321.9	319.5	317.1	314.7
125°	351.3	351.9	352.4	352.7	352.9	353.2	353.5
127.5°	376.3	377.2	377.7	377.8	377.9	377.9	378.0
130°	392.1	393.1	393.6	393.4	393.3	393.2	393.2
132.5°	407.2	408.1	408.4	408.3	408.2	408.1	408.1
135°	429.0	429.9	430.3	430.1	429.9	429.8	429.5
137.5°	449.2	450.1	450.4	450.0	449.7	449.5	449.2
140°	462.2	463.0	463.2	462.7	462.3	461.8	461.4
142.5°	474.2	475.0	475.2	474.7	474.2	473.7	473.2
145°	491.0	491.6	491.7	491.3	490.8	490.4	489.9
147.5°	505.6	506.0	506.0	505.7	505.3	504.9	504.5
150°	514.7	515.2	515.3	514.8	514.4	513.9	513.5
152.5°	523.0	523.6	523.5	522.9	522.3	521.7	521.1
155°	534.2	534.7	534.6	533.9	533.1	532.4	531.6
157.5°	543.6	544.2	544.2	543.4	542.7	542.0	541.3
160°	549.0	549.5	549.5	548.9	548.3	547.6	546.9
162.5°	554.2	554.8	554.8	554.0	553.2	552.4	551.6
165°	560.5	561.1	561.1	560.5	559.8	559.2	558.5
167.5°	565.7	566.3	566.3	565.4	564.6	563.7	562.9
170°	568.3	568.9	568.9	568.0	567.2	566.4	565.5
172.5°	570.3	570.9	570.8	570.1	569.2	568.4	567.5
175°	572.4	573.1	573.0	572.0	571.1	570.2	569.3
177.5°	572.6	573.1	573.0	572.4	571.6	571.0	570.4
180°	571.3	571.3	571.3	571.3	571.3	571.3	571.3

(END OF REPORT)