

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P333294-840

Luminaire Tested: **S125DIP-S1090D1205U840-4F0-1E-UDD-F4**

Issue Date: 3/3/2020

Test Information

Test Method: LM-79-08
Report Number: P333294-840
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-19,
Test Lab: INNOVATION CENTER
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: NEO-RAY
Catalog Number: S125DIP-S1090D1205U840-4F0-1E-UDD-F4
Description: DEFINE 5 DIRECT-INDIRECT PENDANT LED LUMINAIRE
DOWNLIGHT 1090 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER
UPLIGHT 1205 LUMENS PER FOOT, BATWING OPTIC
Light Source: -
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 8851.9 lumens
Efficiency: N/A
Efficacy: 135.3 lumens/watt
Spacing Criteria (0/90/45): 1.21 / 1.18 / 1.31
Luminous Opening: Rectangular (W 0.42' x L: 4' x H: 0')
CIE Type: General Diffuse


Input Watts (W): 65.4
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P333294-840

CATALOG NUMBER: S125DIP-S1090D1205U840-4F0-1E-UDD-F4

Luminous Intensity Polar Plot





TEST NUMBER: P333294-840

CATALOG NUMBER: S125DIP-S1090D1205U840-4F0-1E-UDD-F4

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20					20					20					20					20					
RC	80					70					50					30					10					0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0		
RCR																										
0	107	107	107	107	99	99	99	99	84	84	84	70	70	70	57	57	57	51					51			
1	98	94	90	86	90	86	83	80	73	71	69	61	59	58	50	49	48	43					43			
2	89	82	75	70	82	76	70	66	64	60	57	54	51	48	44	42	40	36					36			
3	81	72	64	58	75	66	60	55	57	52	48	47	44	41	39	36	34	30					30			
4	74	63	56	49	68	59	52	46	50	45	41	42	38	35	35	32	29	26					26			
5	68	57	48	42	63	53	45	40	45	39	35	38	34	30	31	28	26	22					22			
6	63	51	43	37	58	47	40	35	41	35	31	34	30	27	28	25	23	20					20			
7	58	46	38	32	53	43	35	30	37	31	27	31	27	23	26	23	20	17					17			
8	54	42	34	28	50	39	32	27	33	28	24	29	24	21	24	20	18	16					16			
9	50	38	30	25	46	35	29	24	31	25	21	26	22	19	22	19	16	14					14			
10	47	35	28	23	43	33	26	22	28	23	19	24	20	17	20	17	15	13					13			

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	11129	11129	11129
5°	11154	11048	11119
10°	11086	10970	11032
15°	10965	10838	10884
20°	10794	10653	10672
25°	10608	10434	10424
30°	10380	10197	10147
35°	10136	9942	9802
40°	9885	9666	9528
45°	9613	9414	9227
50°	9315	9109	8835
55°	9026	8765	8519
60°	8681	8418	8117
65°	8270	8000	7728
70°	7878	7517	7260
75°	7177	6939	6700
80°	6390	6289	6133
85°	5550	5654	5350



TEST NUMBER: P333294-840

CATALOG NUMBER: S125DIP-S1090D1205U840-4F0-1E-UDD-F4

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	162.5	1.8
10°-20°	459.0	5.2
20°-30°	677.7	7.7
30°-40°	790.7	8.9
40°-50°	794.2	9.0
50°-60°	697.1	7.9
60°-70°	519.5	5.9
70°-80°	297.0	3.4
80°-90°	89.6	1.0
90°-100°	421.9	4.8
100°-110°	906.9	10.2
110°-120°	851.1	9.6
120°-130°	689.8	7.8
130°-140°	553.5	6.3
140°-150°	417.7	4.7
150°-160°	294.0	3.3
160°-170°	173.3	2.0
170°-180°	56.4	0.6
0°-30°	1299.1	14.7
0°-40°	2089.8	23.6
0°-60°	3581.2	40.5
0°-90°	4487.3	50.7
90°-120°	2179.9	24.6
90°-150°	3840.9	43.4
90°-180°	4365.0	49.3
0°-180°	8851.9	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	1723	1723	1723	1723	1723	
5°	1720	1717	1704	1716	1715	163
15°	1640	1635	1621	1627	1628	462
25°	1489	1481	1464	1466	1463	685
35°	1286	1279	1261	1254	1243	804
45°	1052	1046	1031	1015	1010	811
55°	802	797	778	766	757	715
65°	541	538	524	512	506	537
75°	288	285	278	274	268	307
85°	75	76	76	75	72	84
90°	1	11	19	25	27	6
95°	39	114	1040	472	276	41
105°	133	185	851	1675	1555	140
115°	237	286	683	1472	1732	233
125°	328	385	655	1171	1365	291
135°	385	463	650	982	1134	299
145°	448	513	652	813	894	281
155°	512	550	636	719	750	236
165°	559	574	610	647	657	157
175°	581	581	586	593	590	55
180°	582	582	582	582	582	



TEST NUMBER: P333294-840

CATALOG NUMBER: S125DIP-S1090D1205U840-4F0-1E-UDD-F4

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	1723.2	1723.2	1723.2	1723.2	1723.2	1723.2	1723.2	1723.2	1723.2	1723.2	1723.2
2.5°	1727.6	1726.9	1726.1	1725.4	1724.6	1723.0	1720.6	1718.2	1715.8	1713.3	1715.8
5°	1720.5	1719.9	1719.3	1718.7	1718.1	1716.3	1713.2	1710.2	1707.2	1704.1	1706.9
7.5°	1704.7	1704.0	1703.4	1702.8	1702.2	1700.2	1696.9	1693.5	1690.2	1686.9	1689.6
10°	1690.5	1689.9	1689.3	1688.7	1688.1	1686.1	1682.7	1679.4	1676.1	1672.7	1675.2
12.5°	1673.0	1671.9	1670.8	1669.7	1668.7	1666.6	1663.4	1660.4	1657.3	1654.2	1656.2
15°	1640.0	1639.1	1638.2	1637.3	1636.4	1634.3	1630.9	1627.6	1624.3	1620.9	1622.4
17.5°	1602.2	1600.8	1599.4	1598.1	1596.8	1594.4	1590.9	1587.5	1584.1	1580.5	1582.5
20°	1570.5	1569.9	1569.3	1568.7	1568.1	1565.8	1561.9	1557.9	1554.0	1550.0	1552.2
22.5°	1538.8	1537.8	1536.7	1535.6	1534.5	1532.1	1528.4	1524.7	1521.1	1517.3	1518.7
25°	1488.7	1487.2	1485.7	1484.2	1482.7	1480.0	1476.0	1472.1	1468.1	1464.2	1464.8
27.5°	1430.1	1429.2	1428.3	1427.3	1426.4	1424.0	1419.9	1415.8	1411.8	1407.8	1407.9
30°	1391.9	1391.0	1390.1	1389.2	1388.3	1385.5	1381.0	1376.4	1371.9	1367.4	1366.8
32.5°	1350.5	1349.1	1347.7	1346.3	1344.9	1342.2	1338.1	1334.0	1330.0	1326.0	1324.8
35°	1285.6	1284.3	1283.1	1281.9	1280.7	1278.0	1273.7	1269.5	1265.3	1261.0	1259.5
37.5°	1218.2	1216.7	1215.2	1213.7	1212.1	1209.4	1205.4	1201.4	1197.4	1193.5	1191.1
40°	1172.5	1170.9	1169.4	1167.9	1166.4	1163.5	1159.2	1155.0	1150.7	1146.5	1143.8
42.5°	1123.4	1122.1	1120.8	1119.5	1118.2	1115.5	1111.3	1107.0	1102.8	1098.5	1096.0
45°	1052.5	1051.3	1050.1	1048.8	1047.6	1045.2	1041.6	1037.9	1034.3	1030.7	1027.0
47.5°	976.1	976.1	976.2	976.3	976.3	974.2	969.9	965.4	961.1	956.7	953.0
50°	927.1	926.1	925.2	924.3	923.4	921.1	917.5	913.8	910.2	906.6	902.6
52.5°	876.9	876.2	875.6	874.8	874.2	871.9	868.1	864.1	860.3	856.4	852.9
55°	801.6	800.7	799.8	798.9	798.0	795.4	791.1	786.9	782.6	778.4	775.7
57.5°	722.3	721.8	721.3	720.8	720.3	718.3	714.7	711.1	707.6	704.0	700.4
60°	672.1	670.9	669.6	668.4	667.2	665.0	661.7	658.3	655.0	651.7	648.6
62.5°	619.8	618.7	617.8	616.8	615.9	614.0	611.1	608.2	605.4	602.6	599.3
65°	541.2	540.6	540.0	539.4	538.8	536.8	533.5	530.2	526.8	523.5	520.8
67.5°	465.1	463.8	462.6	461.3	460.1	458.2	455.7	453.2	450.7	448.3	446.0
70°	417.2	415.7	414.1	412.6	411.1	409.0	406.3	403.5	400.8	398.1	396.3
72.5°	364.9	363.8	362.7	361.7	360.7	359.3	357.6	355.8	354.1	352.2	350.2
75°	287.6	287.0	286.4	285.8	285.2	284.2	282.7	281.1	279.6	278.1	277.2
77.5°	216.5	216.2	216.0	215.8	215.5	215.0	214.1	213.3	212.5	211.6	211.1
80°	171.8	171.8	171.8	171.8	171.8	171.5	170.9	170.3	169.7	169.1	168.7
82.5°	132.5	132.0	131.6	131.1	130.6	130.3	130.2	130.1	129.9	129.8	129.3
85°	74.9	75.2	75.5	75.8	76.1	76.3	76.3	76.3	76.3	76.3	76.0
87.5°	29.7	29.9	30.4	30.9	31.3	31.7	31.7	31.9	31.9	32.1	32.3
90°	1.2	2.3	4.6	7.1	9.4	11.7	12.9	15.2	16.5	18.8	20.0
92.5°	14.3	17.4	27.3	41.8	62.0	96.2	160.3	267.8	384.5	378.3	306.3
95°	38.7	39.9	49.3	62.2	88.0	140.8	266.4	524.5	848.4	1039.7	1017.3
97.5°	64.3	65.7	72.3	85.2	108.5	146.4	229.5	418.7	757.6	1110.2	1287.3
100°	82.1	84.5	89.2	102.1	124.4	159.6	227.6	380.2	675.9	1059.6	1352.9
102.5°	101.9	103.3	107.0	120.9	141.3	175.5	236.1	364.3	613.9	970.4	1313.5
105°	132.6	132.6	138.5	150.2	169.0	201.9	253.5	357.9	553.8	850.7	1187.5
107.5°	162.6	165.0	170.6	180.3	199.8	229.2	279.2	368.7	528.5	768.3	1058.9
110°	184.2	186.6	191.3	201.9	219.4	249.9	298.0	379.0	521.0	729.8	985.6



TEST NUMBER: P333294-840

CATALOG NUMBER: S125DIP-S1090D1205U840-4F0-1E-UDD-F4

CANDELA DISTRIBUTION (continued):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	205.8	208.1	211.9	222.5	240.0	269.6	315.9	392.1	521.0	707.3	931.2
115°	237.0	239.3	242.9	253.5	271.0	300.4	343.9	411.8	524.5	683.0	871.8
117.5°	265.2	268.7	272.5	283.1	303.0	331.3	372.4	434.4	532.3	671.0	836.4
120°	284.0	287.5	292.2	302.8	322.7	352.0	393.1	449.4	539.8	665.3	816.7
122.5°	303.7	306.3	310.0	320.5	342.4	371.7	412.8	466.4	546.3	660.7	799.8
125°	328.5	330.9	336.8	347.3	369.6	400.1	438.9	489.3	557.3	654.8	776.8
127.5°	348.0	351.5	359.1	372.4	396.2	426.7	463.9	510.5	569.8	652.0	755.7
130°	360.2	363.8	373.1	388.4	413.0	443.5	479.9	524.5	577.3	650.1	741.6
132.5°	369.6	374.1	385.4	402.5	428.1	458.6	494.9	536.7	585.7	650.1	730.3
135°	384.9	389.6	403.6	422.4	447.1	478.8	515.1	553.8	597.2	650.1	717.0
137.5°	404.1	407.7	420.8	439.6	463.7	496.3	529.5	566.5	607.8	651.5	705.0
140°	415.4	418.9	433.0	451.8	474.0	505.7	539.8	575.0	612.5	652.4	699.3
142.5°	428.5	431.1	444.2	463.0	484.4	514.2	546.3	579.7	615.3	653.4	694.7
145°	448.3	450.6	462.3	478.8	499.9	526.8	557.3	586.7	618.4	652.4	687.6
147.5°	468.9	470.3	480.4	495.6	513.9	537.7	564.4	591.0	619.6	649.3	680.3
150°	481.1	483.4	491.7	507.0	523.3	543.3	569.1	593.8	619.6	646.5	674.7
152.5°	494.2	495.6	502.9	516.3	531.8	549.9	573.8	595.6	618.6	642.8	668.1
155°	511.6	511.6	518.7	530.4	542.1	558.6	578.5	597.2	616.0	636.0	657.1
157.5°	527.1	526.8	532.5	542.6	552.9	565.3	582.5	598.4	613.0	628.9	646.8
160°	537.5	536.2	541.0	549.2	558.6	569.1	584.4	598.4	610.2	624.3	638.3
162.5°	545.8	544.7	549.4	556.6	564.2	572.9	586.2	597.5	607.3	618.6	630.9
165°	558.6	556.2	559.8	565.6	570.3	577.3	586.7	596.1	603.1	610.2	619.6
167.5°	567.0	565.8	567.9	571.2	574.5	579.0	586.7	593.3	596.5	602.0	608.5
170°	572.6	571.5	572.6	575.0	577.3	580.9	586.7	591.4	593.8	597.2	602.0
172.5°	576.4	574.3	575.4	577.7	579.2	580.9	585.7	589.6	590.0	591.7	595.4
175°	580.9	578.5	579.7	580.9	580.9	580.9	584.4	586.7	585.5	585.5	586.7
177.5°	583.0	581.1	581.1	582.0	581.1	581.1	583.0	583.9	582.0	582.0	583.0
180°	582.0	582.0	582.0	582.0	582.0	582.0	582.0	582.0	582.0	582.0	582.0



TEST NUMBER: P333294-840

CATALOG NUMBER: S125DIP-S1090D1205U840-4F0-1E-UDD-F4

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°
0°	1723.2	1723.2	1723.2	1723.2	1723.2	1723.2	1723.2	1723.2
2.5°	1718.2	1720.6	1723.0	1724.1	1723.9	1723.6	1723.4	1723.2
5°	1709.6	1712.3	1715.1	1716.3	1716.0	1715.7	1715.4	1715.1
7.5°	1692.2	1695.0	1697.6	1698.8	1698.5	1698.2	1697.9	1697.6
10°	1677.6	1680.0	1682.4	1683.5	1683.2	1682.9	1682.6	1682.3
12.5°	1658.1	1660.0	1661.9	1662.9	1662.8	1662.7	1662.7	1662.6
15°	1624.0	1625.5	1627.0	1627.8	1627.8	1627.8	1627.8	1627.8
17.5°	1584.4	1586.2	1588.1	1588.3	1586.8	1585.3	1583.8	1582.3
20°	1554.3	1556.4	1558.5	1558.8	1557.3	1555.8	1554.3	1552.8
22.5°	1520.1	1521.6	1522.9	1523.1	1522.1	1521.1	1520.0	1518.9
25°	1465.4	1466.0	1466.6	1466.4	1465.5	1464.6	1463.7	1462.8
27.5°	1408.0	1408.1	1408.3	1407.9	1406.9	1406.0	1405.1	1404.2
30°	1366.1	1365.5	1364.9	1364.2	1363.3	1362.4	1361.5	1360.6
32.5°	1323.7	1322.6	1321.6	1320.2	1318.6	1317.0	1315.2	1313.6
35°	1258.0	1256.5	1255.0	1253.0	1250.6	1248.2	1245.8	1243.3
37.5°	1188.9	1186.7	1184.5	1182.7	1181.2	1179.8	1178.4	1177.1
40°	1141.0	1138.3	1135.6	1133.8	1132.9	1132.0	1131.0	1130.1
42.5°	1093.6	1091.1	1088.6	1086.6	1085.3	1083.9	1082.5	1081.1
45°	1023.4	1019.8	1016.1	1013.8	1012.9	1012.0	1011.1	1010.2
47.5°	949.4	945.6	942.0	939.1	937.0	934.8	932.7	930.6
50°	898.7	894.7	890.8	887.8	885.7	883.5	881.4	879.3
52.5°	849.5	846.1	842.6	839.7	837.3	835.0	832.6	830.2
55°	773.0	770.2	767.5	765.1	763.0	760.8	758.7	756.6
57.5°	697.0	693.5	689.9	687.6	686.5	685.3	684.2	683.0
60°	645.6	642.6	639.5	636.9	634.8	632.7	630.6	628.4
62.5°	596.0	592.8	589.5	587.0	585.4	583.8	582.1	580.5
65°	518.1	515.3	512.6	510.6	509.4	508.2	507.0	505.7
67.5°	443.6	441.3	439.0	437.5	436.8	436.1	435.4	434.6
70°	394.5	392.6	390.8	389.3	388.1	386.9	385.7	384.5
72.5°	348.2	346.1	344.1	342.4	341.2	340.0	338.8	337.6
75°	276.3	275.4	274.5	273.4	272.2	270.9	269.7	268.5
77.5°	210.5	210.0	209.4	208.7	207.8	207.0	206.1	205.3
80°	168.4	168.1	167.8	167.3	166.7	166.1	165.5	164.9
82.5°	128.7	128.2	127.6	127.2	127.1	127.0	126.9	126.7
85°	75.7	75.4	75.1	74.6	74.0	73.4	72.8	72.2
87.5°	32.6	32.8	33.0	33.3	32.8	32.3	32.0	31.6
90°	21.1	22.3	23.4	25.9	25.9	25.9	27.0	27.0
92.5°	207.9	150.9	113.6	96.2	81.2	78.4	76.7	74.8
95°	843.6	665.3	521.0	422.4	339.1	303.9	294.6	275.8
97.5°	1256.5	1131.5	990.9	853.7	781.2	715.6	681.6	666.5
100°	1443.3	1385.8	1265.0	1142.9	1062.0	977.4	934.0	915.2
102.5°	1506.2	1541.7	1483.7	1401.1	1314.4	1254.4	1207.2	1193.2
105°	1469.2	1629.9	1681.5	1668.6	1631.0	1592.4	1568.8	1554.8
107.5°	1336.8	1551.3	1683.8	1745.1	1764.1	1763.9	1756.2	1746.8
110°	1239.1	1462.1	1627.5	1727.3	1780.1	1802.4	1810.6	1810.6



TEST NUMBER: P333294-840

CATALOG NUMBER: S125DIP-S1090D1205U840-4F0-1E-UDD-F4

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°
112.5°	1162.2	1373.8	1541.2	1658.7	1736.0	1774.2	1794.6	1803.1
115°	1065.5	1247.4	1408.1	1536.0	1627.5	1683.8	1716.7	1731.9
117.5°	1003.0	1159.8	1298.3	1415.6	1507.1	1565.4	1598.0	1607.3
120°	969.3	1110.0	1239.1	1342.4	1429.3	1485.5	1517.2	1526.6
122.5°	943.9	1074.4	1189.4	1286.1	1363.5	1415.1	1446.8	1455.3
125°	907.1	1026.7	1128.8	1213.4	1279.0	1327.2	1352.9	1364.7
127.5°	869.5	981.2	1076.5	1155.6	1215.2	1257.7	1282.1	1287.3
130°	846.1	949.3	1040.9	1117.1	1175.8	1214.5	1238.0	1245.0
132.5°	822.5	919.3	1002.3	1075.8	1134.5	1173.2	1194.8	1202.7
135°	792.0	873.0	948.2	1015.0	1066.6	1105.4	1126.5	1133.6
137.5°	766.3	831.7	894.1	951.0	997.1	1032.4	1051.9	1059.6
140°	752.1	807.3	861.3	910.6	954.0	984.5	1002.1	1007.9
142.5°	739.9	786.7	833.1	875.9	912.7	938.5	955.1	960.1
145°	724.0	760.3	796.8	828.4	856.6	876.6	889.5	894.1
147.5°	709.0	738.5	766.5	790.4	812.7	828.7	836.2	838.3
150°	700.5	726.4	748.6	769.7	787.4	801.4	806.2	807.3
152.5°	691.2	714.2	734.6	751.0	765.8	777.0	781.7	782.9
155°	677.0	695.8	712.3	725.2	736.9	745.1	748.6	749.8
157.5°	663.0	678.4	691.2	701.3	710.3	717.2	720.4	720.2
160°	653.6	665.3	677.0	685.3	693.5	699.3	701.8	700.5
162.5°	643.3	654.1	663.9	671.2	677.5	682.5	683.0	682.7
165°	628.9	637.1	644.2	650.1	654.8	657.1	657.1	657.1
167.5°	615.3	620.8	626.1	630.4	632.7	634.8	633.9	633.7
170°	607.8	611.4	614.9	617.2	619.6	620.8	620.8	619.6
172.5°	599.4	602.9	605.5	606.9	607.3	609.5	607.6	606.4
175°	590.3	590.3	592.6	592.6	592.6	593.8	591.4	590.3
177.5°	583.9	584.8	584.8	584.8	583.9	584.8	582.0	582.0
180°	582.0	582.0	582.0	582.0	582.0	582.0	582.0	582.0

(END OF REPORT)