

Scaled data based on original data using  
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State  
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P331697-927

Luminaire Tested: **SA2XXRDIP-C675D925U927-4F0-1E-UDD-F1**

Issue Date: 10/7/2019

**Test Information**

Test Method: LM-79-08  
Report Number: P331697-927  
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-8,  
Test Lab: INNOVATION CENTER  
Issue Date: 10/7/2019  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: NEO-RAY  
Catalog Number: SA2XXRDIP-C675D925U927-4F0-1E-UDD-F1  
Description: DEFINE 2 DIRECT-INDIRECT PENDANT LED LUMINAIRE  
DOWNLIGHT 675 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER, REGRESSED  
HOUSING  
UPLIGHT 925 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER  
Light Source: -  
Ballast/Driver: ELECTRONIC DRIVER

**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 4461.2 lumens  
Efficiency: N/A  
Efficacy: 85.8 lumens/watt  
Spacing Criteria (0/90/45): 1.2 / 0.99 / 1.16  
Luminous Opening: Rectangular (W 0.17' x L: 4' x H: 0')  
CIE Type: General Diffuse


Input Watts (W): 52  
Input Voltage (V): 120  
Input Current (Ain): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 25 FT



TEST NUMBER: P331697-927

CATALOG NUMBER: SA2XXRDIP-C675D925U927-4F0-1E-UDD-F1

### Luminous Intensity Polar Plot





TEST NUMBER: P331697-927

CATALOG NUMBER: SA2XXRDIP-C675D925U927-4F0-1E-UDD-F1

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20					20					20					20					20	
RC	80					70					50					30					10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0	
RCR																						
0	105	105	105	105	96	96	96	96	78	78	78	63	63	63	48	48	48	41				
1	96	92	88	85	88	84	81	78	69	67	65	56	54	53	43	42	41	36				
2	88	81	75	70	80	74	69	65	61	58	55	49	47	45	38	37	35	30				
3	80	71	64	59	73	65	59	55	54	50	46	44	41	38	34	32	31	26				
4	74	63	56	50	67	58	52	47	48	44	40	39	36	33	31	29	27	23				
5	68	57	49	43	62	52	45	40	44	38	34	36	32	29	28	26	23	20				
6	63	51	43	37	57	47	40	35	39	34	30	32	28	25	26	23	21	18				
7	58	46	38	33	53	42	36	31	36	31	27	29	26	23	23	21	19	16				
8	54	42	34	29	49	39	32	27	33	27	24	27	23	20	22	19	17	14				
9	50	38	31	26	46	35	29	24	30	25	21	25	21	18	20	17	15	13				
10	47	35	28	23	43	33	26	22	28	23	19	23	19	17	19	16	14	12				

**AVERAGE LUMINANCE (cd/sqm):**

	0°	45°	90°
0°	14428	14428	14428
5°	14483	14248	14326
10°	14372	14014	13895
15°	14206	13600	13207
20°	13979	13005	12352
25°	13744	12332	11526
30°	13420	11639	10465
35°	13102	10886	9532
40°	12783	10108	8454
45°	12408	9232	7478
50°	12024	8349	6521
55°	11634	7398	5599
60°	11176	6397	4647
65°	10659	5375	4233
70°	10041	4428	3895
75°	9283	4036	3631
80°	8201	3608	3310
85°	6447	2853	2853



TEST NUMBER: P331697-927

CATALOG NUMBER: SA2XXRDIP-C675D925U927-4F0-1E-UDD-F1

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	83.6	1.9
10°-20°	229.7	5.1
20°-30°	322.5	7.2
30°-40°	351.7	7.9
40°-50°	323.4	7.2
50°-60°	254.0	5.7
60°-70°	165.6	3.7
70°-80°	85.4	1.9
80°-90°	25.9	0.6
90°-100°	59.4	1.3
100°-110°	184.4	4.1
110°-120°	315.1	7.1
120°-130°	414.4	9.3
130°-140°	465.2	10.4
140°-150°	456.1	10.2
150°-160°	382.5	8.6
160°-170°	253.7	5.7
170°-180°	88.7	2.0
0°-30°	635.8	14.3
0°-40°	987.5	22.1
0°-60°	1564.8	35.1
0°-90°	1841.7	41.3
90°-120°	558.9	12.5
90°-150°	1894.5	42.5
90°-180°	2620.0	58.7
0°-180°	4461.2	100.0

**CANDELA DISTRIBUTION:**

	0°	22.5°	45°	67.5°	90°	Flux
0°	894	894	894	894	894	
5°	894	889	879	886	884	85
15°	850	840	814	799	790	239
25°	772	744	692	660	647	355
35°	665	622	552	503	484	416
45°	543	488	404	349	328	419
55°	413	349	263	216	199	369
65°	279	213	141	115	111	277
75°	149	94	65	59	58	158
85°	35	19	15	15	15	41
90°	1	11	28	26	27	4
95°	41	49	51	50	49	47
105°	170	172	174	175	176	180
115°	316	321	319	318	316	313
125°	460	467	465	463	462	411
135°	595	604	606	605	602	460
145°	722	728	733	733	730	451
155°	826	828	831	834	832	380
165°	899	898	898	903	900	253
175°	935	933	931	936	932	89
180°	937	937	937	937	937	



TEST NUMBER: P331697-927

CATALOG NUMBER: SA2XXRDIP-C675D925U927-4F0-1E-UDD-F1

**CANDELA DISTRIBUTION (FULL):**

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	893.6	893.6	893.6	893.6	893.6	893.6	893.6	893.6	893.6	893.6	893.6
2.5°	896.8	896.1	895.4	894.7	894.0	892.8	891.2	889.6	888.1	886.5	888.0
5°	893.6	892.7	891.8	890.9	890.0	888.4	886.1	883.8	881.4	879.1	880.7
7.5°	884.4	883.3	882.2	881.1	880.0	878.0	875.3	872.6	869.8	867.1	867.5
10°	876.6	875.4	874.1	872.8	871.6	869.2	865.5	862.0	858.4	854.8	854.3
12.5°	866.9	865.4	863.8	862.3	860.7	857.7	853.1	848.5	843.8	839.2	838.3
15°	849.9	848.0	846.0	844.0	842.0	838.0	831.9	825.8	819.7	813.6	810.2
17.5°	829.1	826.1	823.1	820.0	817.0	811.6	803.7	795.9	788.1	780.2	776.2
20°	813.6	809.9	806.4	802.8	799.2	792.9	783.9	774.9	766.0	756.9	752.4
22.5°	796.7	792.7	788.7	784.7	780.6	773.6	763.4	753.3	743.1	733.0	727.2
25°	771.5	765.7	760.0	754.2	748.5	739.7	727.9	716.0	704.1	692.2	684.8
27.5°	741.1	734.8	728.6	722.3	716.1	706.2	692.9	679.5	666.1	652.8	644.2
30°	719.8	712.9	706.1	699.3	692.4	681.8	667.4	653.1	638.7	624.3	615.1
32.5°	699.0	691.0	683.1	675.1	667.1	655.8	641.1	626.5	611.8	597.1	586.7
35°	664.7	655.6	646.4	637.2	628.1	615.6	599.8	584.0	568.2	552.3	541.0
37.5°	630.5	620.4	610.3	600.2	590.2	576.7	559.9	543.0	526.2	509.3	496.9
40°	606.5	595.7	584.9	574.2	563.4	549.3	531.9	514.4	497.0	479.6	466.8
42.5°	581.9	570.6	559.2	547.9	536.5	521.8	503.8	485.8	467.8	449.8	436.6
45°	543.4	531.4	519.4	507.3	495.3	479.8	461.0	442.1	423.2	404.3	391.6
47.5°	505.9	493.1	480.4	467.6	454.9	438.8	419.3	399.8	380.3	360.8	348.2
50°	478.7	466.0	453.2	440.5	427.7	411.5	391.7	371.9	352.1	332.4	320.0
52.5°	452.3	438.9	425.6	412.3	398.9	382.5	363.2	343.9	324.6	305.2	293.3
55°	413.3	399.3	385.2	371.2	357.2	340.5	321.1	301.7	282.3	262.8	252.1
57.5°	373.3	358.9	344.5	330.2	315.8	299.3	280.6	262.0	243.3	224.7	214.8
60°	346.1	331.8	317.3	303.0	288.6	272.2	253.7	235.1	216.7	198.1	188.9
62.5°	319.6	305.2	290.8	276.5	262.1	246.1	228.5	210.8	193.1	175.5	166.8
65°	279.0	264.4	249.9	235.4	220.8	205.4	189.3	173.1	156.9	140.7	134.6
67.5°	239.9	225.4	211.0	196.5	182.0	167.5	153.0	138.5	123.9	109.3	106.5
70°	212.7	198.7	184.7	170.6	156.6	143.4	131.0	118.6	106.2	93.8	92.0
72.5°	186.8	173.3	159.9	146.5	133.0	121.4	111.4	101.4	91.5	81.5	80.0
75°	148.8	136.3	123.7	111.1	98.5	89.1	83.0	76.9	70.8	64.7	63.5
77.5°	111.5	100.4	89.4	78.3	67.3	60.3	57.4	54.4	51.5	48.6	47.8
80°	88.2	79.0	69.8	60.7	51.5	46.0	44.2	42.4	40.6	38.8	38.1
82.5°	66.8	59.7	52.5	45.3	38.2	34.0	32.8	31.5	30.3	29.2	28.7
85°	34.8	31.0	27.3	23.4	19.6	17.5	17.0	16.5	15.9	15.4	15.4
87.5°	10.5	9.7	9.0	8.3	7.6	7.6	8.4	9.2	9.9	10.7	10.5
90°	0.8	2.9	5.0	7.1	9.2	12.2	16.1	20.0	23.8	27.6	27.3
92.5°	14.1	15.6	17.2	18.7	20.3	21.5	22.4	23.3	24.2	25.1	25.2
95°	41.1	42.9	44.6	46.3	48.2	49.2	49.5	49.9	50.2	50.6	50.6
97.5°	75.1	76.7	78.2	79.8	81.3	82.4	83.1	83.7	84.4	85.1	85.1
100°	100.4	101.8	103.2	104.6	106.0	107.0	107.5	108.1	108.6	109.1	109.1
102.5°	127.0	128.1	129.2	130.3	131.4	132.4	133.0	133.7	134.4	135.1	135.1
105°	170.0	170.5	171.0	171.6	172.1	172.5	172.9	173.3	173.6	173.9	174.3
107.5°	213.3	214.0	214.8	215.6	216.4	216.7	216.7	216.7	216.7	216.7	216.9
110°	241.1	242.2	243.2	244.3	245.3	245.9	245.9	245.9	245.9	245.9	245.9



TEST NUMBER: P331697-927

CATALOG NUMBER: SA2XXRDIP-C675D925U927-4F0-1E-UDD-F1

**CANDELA DISTRIBUTION (continued):**

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	271.5	272.5	273.6	274.6	275.7	276.2	276.0	275.8	275.8	275.6	275.2
115°	316.2	317.3	318.3	319.4	320.4	320.8	320.4	320.1	319.7	319.4	319.2
117.5°	360.8	362.2	363.6	365.0	366.5	366.6	365.7	364.6	363.7	362.7	362.3
120°	390.5	392.0	393.3	394.7	396.2	396.2	394.7	393.3	392.0	390.5	390.5
122.5°	417.7	419.4	421.1	422.8	424.5	424.8	423.8	422.9	421.9	420.9	420.5
125°	460.1	461.7	463.3	464.9	466.4	467.0	466.4	465.9	465.4	464.9	464.3
127.5°	501.4	503.4	505.4	507.4	509.4	510.1	509.5	508.8	508.2	507.6	506.9
130°	527.3	529.6	531.9	534.2	536.5	537.4	537.0	536.7	536.4	536.0	535.7
132.5°	556.4	558.3	560.2	562.0	563.9	564.8	564.9	565.0	565.0	565.1	564.4
135°	595.3	597.2	599.1	601.1	603.0	604.2	604.5	604.8	605.2	605.5	605.4
137.5°	636.3	637.8	639.4	641.0	642.5	643.6	644.0	644.5	645.0	645.4	645.3
140°	660.9	662.5	664.1	665.7	667.3	668.4	669.3	670.2	671.1	672.0	672.0
142.5°	686.2	687.8	689.4	690.9	692.5	693.6	694.2	694.8	695.4	696.0	696.2
145°	722.5	723.8	725.0	726.3	727.5	728.6	729.7	730.7	731.8	732.8	733.0
147.5°	754.9	756.5	758.0	759.4	760.9	762.0	762.7	763.3	764.1	764.8	765.2
150°	777.1	778.2	779.2	780.3	781.3	782.2	782.9	783.6	784.3	785.1	785.5
152.5°	796.7	797.8	798.8	799.9	801.0	801.9	802.7	803.6	804.4	805.3	806.0
155°	826.2	826.6	827.2	827.8	828.2	828.8	829.3	829.8	830.4	830.8	831.8
157.5°	851.3	851.6	852.0	852.3	852.7	853.0	853.3	853.7	854.0	854.3	855.5
160°	866.5	866.8	867.1	867.5	867.8	868.2	868.3	868.5	868.6	868.8	869.9
162.5°	880.4	880.4	880.5	880.6	880.7	880.7	881.0	881.1	881.3	881.5	882.6
165°	898.9	898.7	898.5	898.3	898.2	898.1	898.1	898.1	898.1	898.1	899.3
167.5°	914.3	913.9	913.3	912.8	912.3	912.0	912.0	911.9	911.9	911.8	913.1
170°	922.6	922.0	921.5	921.0	920.4	920.1	920.0	919.8	919.6	919.4	920.7
172.5°	928.3	927.7	927.2	926.7	926.1	925.8	925.7	925.4	925.3	925.1	926.4
175°	935.3	934.7	934.1	933.7	933.1	932.7	932.3	932.0	931.6	931.3	932.5
177.5°	938.1	937.6	937.2	936.8	936.4	936.0	935.7	935.5	935.2	934.9	935.7
180°	936.8	936.8	936.8	936.8	936.8	936.8	936.8	936.8	936.8	936.8	936.8



TEST NUMBER: P331697-927

CATALOG NUMBER: SA2XXRDIP-C675D925U927-4F0-1E-UDD-F1

**CANDELA DISTRIBUTION (continued):**

	55°	60°	65°	70°	75°	80°	85°	90°
0°	893.6	893.6	893.6	893.6	893.6	893.6	893.6	893.6
2.5°	889.4	890.8	892.2	892.8	892.6	892.2	892.0	891.7
5°	882.3	883.9	885.5	886.1	885.5	884.9	884.5	883.9
7.5°	868.0	868.5	868.9	868.7	867.8	866.9	865.9	865.0
10°	853.7	853.2	852.6	851.8	850.7	849.7	848.6	847.5
12.5°	837.3	836.4	835.4	834.0	832.2	830.4	828.6	826.8
15°	806.8	803.3	799.9	797.3	795.5	793.7	791.9	790.1
17.5°	772.1	768.0	764.0	760.4	757.3	754.2	751.1	748.1
20°	748.0	743.5	738.9	734.7	730.8	726.8	722.9	718.9
22.5°	721.4	715.7	709.9	705.5	702.5	699.6	696.6	693.7
25°	677.5	670.1	662.7	657.7	655.1	652.4	649.7	647.0
27.5°	635.6	627.0	618.5	612.0	607.7	603.4	599.1	594.8
30°	606.0	596.8	587.6	580.7	575.8	570.9	566.1	561.3
32.5°	576.2	565.8	555.3	547.8	543.2	538.7	534.1	529.6
35°	529.7	518.4	507.1	499.4	495.4	491.5	487.6	483.6
37.5°	484.3	471.9	459.5	450.9	446.4	441.9	437.4	432.8
40°	454.0	441.2	428.5	419.8	415.1	410.4	405.8	401.1
42.5°	423.4	410.2	397.0	388.2	383.7	379.1	374.6	370.0
45°	378.8	366.1	353.3	344.8	340.5	336.1	331.8	327.5
47.5°	335.5	322.8	310.1	301.8	297.9	294.0	290.0	286.1
50°	307.6	295.2	282.8	274.6	270.9	267.1	263.4	259.6
52.5°	281.3	269.3	257.3	249.6	246.1	242.6	239.2	235.7
55°	241.3	230.4	219.7	212.6	209.2	205.7	202.3	198.9
57.5°	204.9	195.0	185.1	178.7	175.9	173.0	170.1	167.2
60°	179.8	170.6	161.4	155.4	152.6	149.7	146.8	143.9
62.5°	158.0	149.2	140.5	135.3	133.6	131.9	130.2	128.4
65°	128.5	122.4	116.3	113.0	112.4	111.9	111.3	110.8
67.5°	103.7	100.9	98.2	96.4	95.9	95.3	94.7	94.1
70°	90.2	88.4	86.6	85.4	84.6	83.9	83.2	82.5
72.5°	78.5	77.0	75.5	74.5	74.1	73.7	73.2	72.8
75°	62.2	60.9	59.7	58.9	58.8	58.6	58.4	58.2
77.5°	47.1	46.3	45.6	45.2	44.8	44.6	44.3	44.0
80°	37.4	36.7	36.0	35.6	35.6	35.6	35.6	35.6
82.5°	28.3	27.8	27.4	27.2	27.2	27.2	27.2	27.2
85°	15.4	15.4	15.4	15.4	15.4	15.4	15.4	15.4
87.5°	10.3	10.1	9.8	9.7	9.8	9.8	9.9	9.9
90°	26.9	26.6	26.3	26.1	26.4	26.5	26.7	26.9
92.5°	25.3	25.3	25.4	25.5	25.5	25.5	25.6	25.6
95°	50.6	50.6	50.6	50.4	50.1	49.7	49.4	49.0
97.5°	85.1	85.1	85.1	85.1	85.0	85.0	84.9	84.9
100°	109.1	109.1	109.1	109.0	108.8	108.7	108.4	108.3
102.5°	135.3	135.5	135.6	135.5	135.4	135.2	135.1	134.9
105°	174.6	175.0	175.3	175.5	175.5	175.5	175.5	175.5
107.5°	217.1	217.2	217.3	217.0	216.2	215.4	214.6	213.7
110°	245.9	245.9	245.9	245.6	245.1	244.5	244.0	243.5





TEST NUMBER: P331697-927

CATALOG NUMBER: SA2XXRDIP-C675D925U927-4F0-1E-UDD-F1

**CANDELA DISTRIBUTION (continued):**

	55°	60°	65°	70°	75°	80°	85°	90°
112.5°	274.7	274.3	273.9	273.5	273.1	272.7	272.4	272.0
115°	319.0	318.9	318.7	318.3	317.8	317.3	316.7	316.2
117.5°	361.9	361.5	361.0	360.5	360.0	359.5	358.9	358.5
120°	390.5	390.5	390.5	390.3	389.8	389.2	388.7	388.2
122.5°	420.0	419.6	419.2	418.8	418.4	418.0	417.6	417.2
125°	463.8	463.3	462.7	462.4	462.2	462.0	461.8	461.7
127.5°	506.3	505.6	505.0	504.4	503.8	503.3	502.7	502.2
130°	535.3	535.0	534.6	534.1	533.4	532.7	532.0	531.2
132.5°	563.6	562.8	562.0	561.3	560.8	560.2	559.7	559.1
135°	605.2	605.1	604.8	604.5	604.0	603.5	602.9	602.4
137.5°	645.2	645.0	644.8	644.4	643.7	643.0	642.3	641.6
140°	672.0	672.0	672.0	671.6	670.9	670.2	669.6	668.8
142.5°	696.3	696.4	696.6	696.3	695.6	694.9	694.2	693.5
145°	733.2	733.4	733.6	733.3	732.6	731.9	731.2	730.5
147.5°	765.6	766.0	766.4	766.2	765.6	764.9	764.2	763.5
150°	786.1	786.6	787.1	787.1	786.6	786.1	785.5	785.1
152.5°	806.6	807.2	807.9	807.9	807.2	806.6	806.0	805.3
155°	832.7	833.5	834.4	834.6	834.0	833.5	833.0	832.4
157.5°	856.7	857.9	859.0	859.2	858.4	857.5	856.7	855.9
160°	870.9	872.0	873.1	873.2	872.5	871.8	871.1	870.4
162.5°	883.8	885.0	886.2	886.5	885.6	884.7	883.9	883.0
165°	900.6	901.7	903.0	903.2	902.3	901.4	900.6	899.7
167.5°	914.3	915.5	916.7	916.9	916.0	915.0	914.2	913.2
170°	921.9	923.1	924.3	924.4	923.4	922.3	921.2	920.2
172.5°	927.6	928.8	930.0	930.1	929.1	928.0	926.9	925.9
175°	933.7	934.9	936.2	936.3	935.3	934.1	933.1	932.1
177.5°	936.6	937.5	938.3	938.3	937.5	936.6	935.7	934.9
180°	936.8	936.8	936.8	936.8	936.8	936.8	936.8	936.8

(END OF REPORT)