

Scaled data based on original data using  
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State  
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P333331-840

Luminaire Tested: **S125DIP-S1270D1205U840-4F0-1E-UDD-A**

Issue Date: 3/3/2020

**Test Information**

Test Method: LM-79-08  
Report Number: P333331-840  
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-7,  
Test Lab: INNOVATION CENTER  
Issue Date: 3/3/2020  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: NEO-RAY  
Catalog Number: S125DIP-S1270D1205U840-4F0-1E-UDD-A  
Description: DEFINE 5 DIRECT-INDIRECT PENDANT LED LUMINAIRE  
DOWNLIGHT 1270 LUMENS PER FOOT, ASYMMETRIC DIFFUSER  
UPLIGHT 1205 LUMENS PER FOOT, NO LENS  
Light Source: -  
Ballast/Driver: ELECTRONIC DRIVER

**Summary**


Lumens per Lamp: N/A  
Luminaire Lumens: 10098.7 lumens  
Efficiency: N/A  
Efficacy: 140.8 lumens/watt  
Spacing Criteria (0/90/45): 1.43 / 1.23 / 1.52  
Luminous Opening: Rectangular (W 4' x L: 0.42' x H: 0')  
CIE Type: General Diffuse  
  
Input Watts (W): 71.7  
Input Voltage (V): 120  
Input Current (Ain): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 25 FT



TEST NUMBER: P333331-840

CATALOG NUMBER: S125DIP-S1270D1205U840-4F0-1E-UDD-A

### Luminous Intensity Polar Plot





TEST NUMBER: P333331-840

CATALOG NUMBER: S125DIP-S1270D1205U840-4F0-1E-UDD-A

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	108	108	108	108	99	99	99	99	84	84	84	71	71	71	58	58	58	52
1	98	94	90	87	91	87	84	81	74	72	70	62	61	59	51	50	49	44
2	90	83	76	71	83	77	71	67	65	61	58	55	52	50	46	44	42	37
3	82	73	65	60	76	68	61	56	58	53	49	49	45	42	41	38	36	32
4	75	64	57	51	69	60	53	48	51	46	42	44	40	36	36	33	31	27
5	69	57	49	43	64	54	46	41	46	41	36	39	35	32	33	30	27	24
6	64	52	44	38	59	48	41	36	42	36	32	35	31	28	30	26	24	21
7	59	47	39	33	54	44	36	31	38	32	28	32	28	25	27	24	21	19
8	55	42	35	29	50	40	33	28	34	29	25	30	25	22	25	22	19	17
9	51	39	31	26	47	36	29	25	32	26	22	27	23	20	23	20	17	15
10	47	35	28	23	44	33	27	22	29	24	20	25	21	18	21	18	16	14

**AVERAGE LUMINANCE (cd/sqm):**

	0°	90°	180°	270°
0°	11978	11978	11978	11978
5°	13871	12019	10524	12019
10°	16138	11956	9220	11956
15°	17864	11869	8505	11869
20°	19996	11730	7932	11730
25°	23426	11573	7652	11573
30°	25302	11419	7409	11419
35°	20805	11129	7250	11129
40°	14787	10725	7075	10725
45°	11359	10181	6974	10181
50°	9697	9507	6961	9507
55°	8634	8847	7020	8847
60°	7789	8123	7198	8123
65°	7195	7398	7386	7398
70°	6541	6643	7493	6643
75°	5777	5854	7426	5854
80°	4861	4775	6791	4775
85°	3846	3446	5483	3446



TEST NUMBER: P333331-840

CATALOG NUMBER: S125DIP-S1270D1205U840-4F0-1E-UDD-A

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	178.6	1.8
10°-20°	531.6	5.3
20°-30°	863.2	8.5
30°-40°	1053.0	10.4
40°-50°	957.9	9.5
50°-60°	763.0	7.6
60°-70°	531.4	5.3
70°-80°	283.4	2.8
80°-90°	74.8	0.7
90°-100°	57.5	0.6
100°-110°	354.6	3.5
110°-120°	643.1	6.4
120°-130°	825.3	8.2
130°-140°	887.7	8.8
140°-150°	833.2	8.3
150°-160°	674.0	6.7
160°-170°	435.9	4.3
170°-180°	150.4	1.5
0°-30°	1573.4	15.6
0°-40°	2626.3	26.0
0°-60°	4347.2	43.0
0°-90°	5236.8	51.9
90°-120°	1055.2	10.4
90°-150°	3601.6	35.7
90°-180°	4862.0	48.1
0°-180°	10098.7	100.0

**CANDELA DISTRIBUTION:**

	0°	90°	180°	270°	360°	Flux
0°	1855	1855	1855	1855	1855	
5°	2140	1854	1623	1854	2140	216
15°	2672	1775	1272	1775	2672	765
25°	3287	1624	1074	1624	3287	1502
35°	2639	1412	920	1412	2639	1615
45°	1244	1115	764	1115	1244	995
55°	767	786	624	786	767	691
65°	471	484	483	484	471	467
75°	232	235	298	235	232	249
85°	52	46	74	46	52	61
90°	28	1	28	1	28	14
95°	25	67	25	67	25	20
105°	349	345	349	345	349	315
115°	643	648	643	648	643	638
125°	921	921	921	921	921	820
135°	1144	1149	1144	1149	1144	883
145°	1329	1332	1329	1332	1329	830
155°	1456	1467	1456	1467	1456	671
165°	1540	1548	1540	1548	1540	435
175°	1576	1583	1576	1583	1576	150
180°	1583	1583	1583	1583	1583	



TEST NUMBER: P333331-840

CATALOG NUMBER: S125DIP-S1270D1205U840-4F0-1E-UDD-A

**CANDELA DISTRIBUTION (FULL):**

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	1854.7	1854.7	1854.7	1854.7	1854.7	1854.7	1854.7	1854.7	1854.7	1854.7	1854.7
2.5°	1961.8	1959.2	1956.7	1951.7	1955.4	1944.7	1939.6	1930.9	1920.2	1916.4	1912.0
5°	2139.6	2143.5	2147.5	2131.0	2132.5	2121.5	2096.4	2075.9	2059.3	2038.1	2023.2
7.5°	2353.8	2344.5	2343.7	2333.0	2314.6	2299.8	2273.3	2239.6	2207.1	2169.9	2139.2
10°	2460.8	2461.6	2454.6	2442.0	2422.3	2408.1	2373.5	2340.4	2300.3	2253.0	2219.2
12.5°	2541.4	2544.8	2535.8	2518.8	2509.1	2477.4	2450.2	2411.0	2363.2	2325.4	2273.9
15°	2671.8	2663.1	2656.9	2635.5	2619.1	2586.0	2542.7	2501.7	2449.8	2401.8	2353.8
17.5°	2797.4	2804.4	2792.6	2773.2	2721.9	2683.3	2625.2	2569.1	2504.5	2440.0	2382.8
20°	2909.5	2915.9	2897.7	2863.9	2802.5	2763.9	2687.6	2615.1	2540.3	2457.7	2394.7
22.5°	3049.4	3044.3	3019.9	2968.4	2915.2	2843.9	2761.3	2673.0	2579.4	2486.0	2402.3
25°	3287.4	3254.3	3239.3	3175.6	3105.5	3000.8	2887.5	2758.3	2641.9	2518.3	2411.3
27.5°	3419.3	3408.9	3392.2	3347.9	3274.2	3162.2	3028.6	2871.2	2706.9	2550.9	2410.7
30°	3392.8	3394.5	3396.1	3381.8	3334.7	3250.4	3117.4	2948.1	2752.9	2577.4	2415.2
32.5°	3158.7	3187.2	3214.7	3247.1	3260.3	3244.1	3160.8	3008.0	2807.0	2607.6	2412.7
35°	2638.8	2647.4	2736.3	2824.5	2944.2	3037.1	3099.3	3031.5	2862.3	2633.2	2409.6
37.5°	2057.5	2100.0	2161.5	2261.2	2433.9	2588.5	2787.3	2878.8	2824.2	2641.6	2404.2
40°	1753.9	1793.3	1833.4	1935.0	2080.6	2268.0	2493.9	2686.7	2731.6	2615.1	2385.3
42.5°	1519.6	1550.8	1595.4	1671.7	1793.4	1959.3	2175.2	2427.3	2582.3	2538.3	2345.6
45°	1243.7	1263.4	1298.1	1358.8	1446.9	1576.8	1767.3	2042.9	2282.9	2362.4	2251.4
47.5°	1064.6	1064.5	1091.4	1133.3	1196.9	1307.3	1448.1	1664.1	1920.5	2110.2	2101.4
50°	965.1	961.2	982.4	1018.7	1069.0	1142.3	1276.9	1449.3	1695.7	1910.6	1970.3
52.5°	879.5	879.9	893.0	919.8	962.0	1024.5	1125.1	1280.5	1491.0	1711.5	1824.3
55°	766.8	763.6	778.5	796.7	827.4	868.3	940.7	1059.6	1230.4	1447.6	1594.1
57.5°	663.5	672.2	678.1	690.7	716.2	743.6	804.7	891.9	1027.4	1213.9	1368.7
60°	603.0	611.7	616.4	628.9	649.4	673.1	720.3	791.1	905.3	1065.9	1219.4
62.5°	548.9	555.6	557.1	568.6	585.2	608.2	645.4	704.9	795.1	935.5	1085.9
65°	470.8	470.8	473.9	485.7	493.6	514.0	542.4	585.7	658.1	767.5	895.9
67.5°	395.5	399.3	398.5	403.6	410.9	426.9	447.2	482.9	536.5	616.4	719.0
70°	346.4	349.5	348.7	352.6	360.5	370.8	387.3	421.1	459.7	528.3	616.4
72.5°	302.3	303.6	301.5	306.7	311.4	320.4	338.8	356.9	392.9	450.8	523.2
75°	231.5	233.0	234.6	237.7	242.5	247.2	256.6	274.8	298.3	341.6	388.1
77.5°	173.5	170.5	174.3	173.8	176.5	180.2	188.4	198.0	217.4	244.8	280.7
80°	130.7	131.5	131.5	132.3	136.2	138.6	145.6	152.7	167.6	188.1	213.4
82.5°	95.4	97.5	96.2	97.7	100.9	102.6	106.5	112.4	121.1	137.1	155.4
85°	51.9	48.1	49.6	51.2	51.2	51.9	55.1	57.5	62.2	68.5	75.5
87.5°	20.7	21.8	22.3	22.2	22.6	22.4	24.6	24.4	26.1	27.7	29.8
90°	28.2	27.4	26.6	25.9	25.0	24.0	22.7	21.4	20.1	18.8	17.0
92.5°	26.3	26.0	25.5	25.1	24.8	24.0	22.7	21.4	20.1	18.8	17.2
95°	24.6	24.6	24.6	24.6	24.6	24.0	22.7	21.4	20.1	18.8	28.7
97.5°	24.6	24.6	24.6	24.6	24.6	28.3	35.6	43.0	50.4	57.8	77.4
100°	24.6	25.7	26.8	27.8	28.8	48.8	87.7	126.5	165.3	204.2	203.2
102.5°	147.6	165.4	183.1	200.9	218.6	231.2	238.5	245.8	253.2	260.5	259.9
105°	348.6	348.8	349.1	349.3	349.6	349.7	349.7	349.7	349.7	349.7	349.7
107.5°	439.4	440.2	441.0	441.7	442.5	442.9	442.8	442.8	442.7	442.7	442.2
110°	502.3	502.1	501.8	501.5	501.3	501.5	502.3	503.1	503.9	504.6	504.1



TEST NUMBER: P333331-840

CATALOG NUMBER: S125DIP-S1270D1205U840-4F0-1E-UDD-A

**CANDELA DISTRIBUTION (continued):**

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	558.7	559.1	559.4	559.8	560.1	560.8	561.8	562.8	563.8	564.7	564.4
115°	643.2	644.7	646.3	647.8	649.4	650.8	651.8	652.8	653.9	654.9	654.6
117.5°	733.3	734.0	734.7	735.3	736.0	737.0	738.4	739.7	741.1	742.5	741.4
120°	788.7	790.0	791.3	792.6	794.0	794.9	795.4	795.9	796.4	796.9	796.1
122.5°	841.3	842.8	844.2	845.8	847.3	848.4	848.9	849.4	849.9	850.4	850.1
125°	921.3	922.1	922.9	923.6	924.4	925.3	926.3	927.5	928.5	929.5	929.5
127.5°	988.7	990.6	992.5	994.5	996.4	997.6	998.3	998.8	999.4	1000.0	1000.1
130°	1037.5	1038.8	1040.2	1041.4	1042.7	1043.8	1044.5	1045.3	1046.1	1046.9	1046.6
132.5°	1082.6	1083.9	1085.2	1086.5	1087.8	1088.5	1088.6	1088.8	1089.0	1089.1	1089.7
135°	1144.3	1145.9	1147.4	1149.0	1150.5	1151.7	1152.2	1152.7	1153.2	1153.7	1154.2
137.5°	1206.3	1207.6	1209.0	1210.3	1211.7	1212.3	1212.2	1212.1	1212.0	1211.9	1212.3
140°	1242.9	1244.5	1246.1	1247.6	1249.1	1249.7	1249.1	1248.6	1248.1	1247.6	1247.9
142.5°	1277.7	1279.2	1280.8	1282.3	1283.9	1284.6	1284.5	1284.4	1284.3	1284.2	1283.8
145°	1328.6	1330.1	1331.7	1333.2	1334.8	1335.4	1335.2	1334.9	1334.7	1334.4	1334.4
147.5°	1370.6	1372.5	1374.3	1376.2	1378.1	1378.9	1378.6	1378.3	1378.0	1377.7	1377.4
150°	1397.9	1399.9	1402.0	1404.1	1406.1	1406.9	1406.4	1405.9	1405.3	1404.8	1404.3
152.5°	1423.2	1425.0	1426.9	1428.8	1430.7	1431.4	1430.9	1430.3	1429.8	1429.3	1428.8
155°	1456.5	1458.5	1460.7	1462.8	1464.8	1465.5	1464.7	1463.9	1463.2	1462.4	1461.9
157.5°	1484.4	1486.5	1488.6	1490.7	1492.8	1493.4	1492.6	1491.8	1490.9	1490.1	1490.1
160°	1502.3	1504.4	1506.4	1508.5	1510.7	1511.2	1510.1	1509.0	1508.0	1506.9	1506.7
162.5°	1518.2	1520.6	1522.8	1525.1	1527.4	1527.8	1526.4	1524.9	1523.5	1522.0	1521.8
165°	1539.8	1541.9	1544.0	1546.1	1548.1	1548.4	1546.9	1545.3	1543.8	1542.2	1541.9
167.5°	1554.9	1557.2	1559.5	1561.9	1564.3	1564.5	1562.6	1560.7	1558.8	1557.0	1556.7
170°	1563.3	1565.7	1568.0	1570.3	1572.7	1572.9	1570.7	1568.6	1566.6	1564.5	1564.2
172.5°	1568.9	1571.2	1573.7	1576.0	1578.3	1578.5	1576.7	1574.8	1573.0	1571.0	1570.5
175°	1576.2	1578.5	1580.9	1583.3	1585.6	1585.7	1583.7	1581.5	1579.4	1577.4	1577.1
177.5°	1580.4	1582.1	1583.8	1585.5	1587.1	1587.2	1585.8	1584.3	1582.9	1581.3	1581.1
180°	1583.3	1583.3	1583.3	1583.3	1583.3	1583.3	1583.3	1583.3	1583.3	1583.3	1583.3



TEST NUMBER: P333331-840

CATALOG NUMBER: S125DIP-S1270D1205U840-4F0-1E-UDD-A

**CANDELA DISTRIBUTION (continued):**

	55°	60°	65°	70°	75°	80°	85°	90°	95°	100°	105°
0°	1854.7	1854.7	1854.7	1854.7	1854.7	1854.7	1854.7	1854.7	1854.7	1854.7	1854.7
2.5°	1908.2	1903.8	1898.7	1890.0	1879.3	1873.6	1864.7	1859.1	1847.8	1838.3	1828.3
5°	2005.0	1984.6	1965.7	1941.3	1914.5	1897.1	1876.7	1853.9	1830.3	1805.8	1779.1
7.5°	2105.4	2069.1	2029.7	1987.4	1946.0	1907.8	1871.5	1835.7	1802.4	1762.1	1728.0
10°	2172.7	2127.1	2078.2	2020.7	1964.9	1916.1	1866.4	1823.2	1779.1	1731.8	1690.1
12.5°	2240.1	2179.3	2110.3	2047.2	1980.0	1921.1	1862.7	1807.5	1752.0	1699.7	1651.1
15°	2287.6	2234.1	2170.3	2080.6	2005.0	1924.0	1846.8	1775.1	1708.3	1650.0	1588.6
17.5°	2319.0	2250.0	2181.5	2095.4	1996.4	1905.7	1818.3	1736.3	1660.8	1587.0	1527.8
20°	2324.6	2253.8	2182.1	2097.9	1996.4	1892.5	1805.0	1706.7	1625.6	1549.2	1476.8
22.5°	2322.8	2242.4	2164.5	2077.8	1978.7	1883.0	1777.4	1677.1	1589.0	1514.0	1438.4
25°	2304.9	2219.2	2121.5	2034.2	1936.5	1835.0	1728.0	1624.1	1534.3	1448.4	1373.7
27.5°	2290.2	2178.9	2068.3	1966.4	1872.2	1779.1	1676.6	1570.1	1470.7	1383.7	1313.2
30°	2271.9	2149.9	2025.5	1919.2	1822.4	1731.8	1635.1	1531.2	1427.2	1342.2	1266.7
32.5°	2255.5	2113.3	1982.1	1866.3	1763.8	1675.8	1586.5	1487.6	1385.6	1299.4	1223.8
35°	2223.9	2059.3	1908.9	1778.3	1668.9	1578.3	1503.6	1411.5	1317.8	1234.4	1162.0
37.5°	2183.7	1988.5	1827.1	1690.1	1570.1	1474.8	1405.1	1334.4	1244.6	1164.2	1098.6
40°	2152.2	1938.1	1767.3	1627.2	1502.8	1403.6	1339.1	1272.1	1197.4	1122.6	1053.3
42.5°	2112.5	1892.8	1706.9	1556.0	1432.9	1336.3	1268.5	1211.6	1145.7	1076.0	1011.7
45°	2039.6	1810.6	1609.0	1446.9	1322.5	1227.3	1157.2	1114.7	1065.1	999.0	944.6
47.5°	1932.5	1711.8	1503.4	1336.1	1207.7	1119.4	1053.8	1013.0	978.1	928.9	879.6
50°	1837.3	1638.2	1427.2	1261.1	1132.8	1043.8	983.2	946.2	916.4	878.5	836.8
52.5°	1730.9	1545.6	1352.3	1188.1	1061.0	973.3	913.9	881.4	856.5	829.4	788.3
55°	1561.9	1404.4	1224.9	1069.0	951.7	866.0	814.0	785.7	765.2	744.7	719.5
57.5°	1375.5	1252.4	1093.5	951.0	842.9	764.9	716.4	688.8	672.9	662.4	647.5
60°	1244.6	1139.1	1002.1	872.2	766.8	697.5	650.3	628.9	615.6	606.9	595.9
62.5°	1123.1	1036.4	909.6	791.0	698.7	633.2	591.1	570.4	557.6	553.4	544.3
65°	943.8	877.0	772.2	673.9	595.1	539.3	503.8	484.1	476.3	471.5	472.3
67.5°	767.4	726.6	642.5	558.6	495.7	448.9	420.5	405.5	401.5	395.2	395.1
70°	659.6	628.9	558.2	484.9	429.0	392.8	367.6	351.8	347.9	344.8	344.1
72.5°	564.6	537.7	476.3	417.6	367.3	335.5	314.8	305.3	298.8	296.9	296.8
75°	424.3	409.4	360.5	314.1	279.4	257.4	243.3	234.6	229.8	229.0	229.8
77.5°	301.6	288.6	257.6	224.7	202.8	186.1	174.1	171.2	165.8	165.9	165.1
80°	226.7	218.0	198.3	172.4	154.3	140.2	133.8	128.4	126.7	124.4	126.7
82.5°	164.4	155.1	141.7	125.1	110.2	101.7	95.4	93.7	92.7	91.6	92.1
85°	81.1	81.9	74.0	61.4	55.1	50.4	46.5	46.5	45.6	44.8	45.6
87.5°	30.7	29.1	26.3	23.9	20.4	18.1	17.1	17.3	15.8	15.6	16.6
90°	15.1	13.3	11.5	9.5	7.5	5.4	3.2	1.2	3.2	5.4	7.5
92.5°	15.6	13.9	12.3	12.2	13.7	15.1	16.7	18.1	16.7	15.1	13.7
95°	38.6	48.5	58.5	63.7	64.5	65.3	66.1	66.9	66.1	65.3	64.5
97.5°	96.9	116.5	136.2	145.3	143.9	142.5	141.1	139.7	141.1	142.5	143.9
100°	202.2	201.1	200.1	199.1	198.3	197.5	196.8	196.0	196.8	197.5	198.3
102.5°	259.3	258.6	258.0	257.2	256.2	255.3	254.3	253.3	254.3	255.3	256.2
105°	349.7	349.7	349.7	349.2	348.2	347.1	346.1	345.1	346.1	347.1	348.2
107.5°	441.6	441.1	440.6	440.4	440.4	440.4	440.4	440.4	440.4	440.4	440.4
110°	503.6	503.1	502.6	502.3	502.3	502.3	502.3	502.3	502.3	502.3	502.3





TEST NUMBER: P333331-840

CATALOG NUMBER: S125DIP-S1270D1205U840-4F0-1E-UDD-A

**CANDELA DISTRIBUTION (continued):**

	55°	60°	65°	70°	75°	80°	85°	90°	95°	100°	105°
112.5°	564.1	563.8	563.5	563.0	562.4	561.8	561.2	560.6	561.2	561.8	562.4
115°	654.4	654.1	653.9	653.1	651.8	650.5	649.1	647.8	649.1	650.5	651.8
117.5°	740.4	739.5	738.5	738.0	738.1	738.1	738.2	738.2	738.2	738.1	738.1
120°	795.4	794.6	793.8	793.6	793.8	794.1	794.3	794.6	794.3	794.1	793.8
122.5°	849.7	849.3	849.0	848.3	847.3	846.3	845.4	844.3	845.4	846.3	847.3
125°	929.5	929.5	929.5	928.6	926.8	924.9	923.1	921.3	923.1	924.9	926.8
127.5°	1000.3	1000.4	1000.6	1000.0	998.7	997.3	996.1	994.8	996.1	997.3	998.7
130°	1046.4	1046.1	1045.8	1045.1	1043.8	1042.5	1041.2	1039.9	1041.2	1042.5	1043.8
132.5°	1090.3	1090.9	1091.5	1091.0	1089.4	1087.9	1086.4	1084.9	1086.4	1087.9	1089.4
135°	1154.8	1155.3	1155.8	1155.3	1153.7	1152.2	1150.5	1149.0	1150.5	1152.2	1153.7
137.5°	1212.8	1213.4	1213.8	1213.4	1211.9	1210.6	1209.3	1207.9	1209.3	1210.6	1211.9
140°	1248.1	1248.4	1248.6	1248.5	1248.0	1247.5	1247.0	1246.4	1247.0	1247.5	1248.0
142.5°	1283.4	1283.1	1282.7	1282.4	1282.1	1281.8	1281.4	1281.1	1281.4	1281.8	1282.1
145°	1334.4	1334.4	1334.4	1334.1	1333.6	1333.1	1332.6	1332.1	1332.6	1333.1	1333.6
147.5°	1377.0	1376.6	1376.3	1376.2	1376.3	1376.4	1376.5	1376.6	1376.5	1376.4	1376.3
150°	1403.8	1403.3	1402.8	1402.8	1403.3	1403.8	1404.3	1404.8	1404.3	1403.8	1403.3
152.5°	1428.3	1427.7	1427.1	1427.4	1428.7	1429.8	1431.0	1432.1	1431.0	1429.8	1428.7
155°	1461.3	1460.8	1460.3	1460.8	1462.4	1463.9	1465.5	1467.0	1465.5	1463.9	1462.4
157.5°	1490.0	1490.0	1489.9	1490.3	1491.3	1492.2	1493.1	1494.1	1493.1	1492.2	1491.3
160°	1506.4	1506.2	1505.9	1506.6	1508.1	1509.7	1511.3	1512.9	1511.3	1509.7	1508.1
162.5°	1521.5	1521.2	1521.0	1521.6	1523.2	1524.7	1526.3	1527.8	1526.3	1524.7	1523.2
165°	1541.7	1541.4	1541.2	1541.8	1543.4	1544.9	1546.5	1548.0	1546.5	1544.9	1543.4
167.5°	1556.4	1556.2	1555.9	1556.6	1558.2	1559.8	1561.5	1563.1	1561.5	1559.8	1558.2
170°	1564.0	1563.7	1563.5	1564.2	1566.0	1567.8	1569.7	1571.6	1569.7	1567.8	1566.0
172.5°	1570.1	1569.6	1569.1	1569.8	1571.7	1573.5	1575.3	1577.1	1575.3	1573.5	1571.7
175°	1576.9	1576.6	1576.3	1577.0	1578.5	1580.1	1581.7	1583.3	1581.7	1580.1	1578.5
177.5°	1580.9	1580.7	1580.5	1581.0	1582.4	1583.6	1584.8	1586.1	1584.8	1583.6	1582.4
180°	1583.3	1583.3	1583.3	1583.3	1583.3	1583.3	1583.3	1583.3	1583.3	1583.3	1583.3



TEST NUMBER: P333331-840

CATALOG NUMBER: S125DIP-S1270D1205U840-4F0-1E-UDD-A

**CANDELA DISTRIBUTION (continued):**

	110°	115°	120°	125°	130°	135°	140°	145°	150°	155°	160°
0°	1854.7	1854.7	1854.7	1854.7	1854.7	1854.7	1854.7	1854.7	1854.7	1854.7	1854.7
2.5°	1822.5	1815.6	1810.0	1797.4	1790.4	1781.0	1773.4	1781.6	1772.8	1776.6	1770.9
5°	1765.7	1743.6	1728.0	1705.1	1685.5	1667.3	1654.0	1651.5	1645.3	1642.1	1632.6
7.5°	1697.4	1669.8	1642.7	1612.9	1587.6	1562.0	1545.6	1532.1	1523.1	1511.3	1503.3
10°	1657.1	1620.1	1588.6	1552.4	1520.9	1493.4	1471.3	1460.3	1450.1	1435.1	1429.6
12.5°	1607.3	1569.0	1530.7	1492.0	1461.7	1431.0	1412.1	1395.4	1388.4	1371.5	1369.8
15°	1547.6	1490.2	1452.4	1413.0	1371.3	1346.2	1330.4	1312.3	1304.4	1292.6	1283.9
17.5°	1476.5	1425.1	1378.0	1337.2	1301.4	1280.2	1260.6	1248.2	1234.7	1227.0	1212.7
20°	1424.8	1376.0	1328.8	1285.6	1258.0	1233.6	1217.8	1206.0	1191.8	1187.9	1173.8
22.5°	1381.4	1327.6	1282.2	1245.9	1215.8	1188.2	1171.2	1163.2	1153.5	1141.3	1138.4
25°	1310.7	1254.9	1216.3	1180.0	1153.3	1128.1	1116.3	1106.0	1096.6	1087.9	1084.8
27.5°	1249.6	1199.7	1153.9	1121.2	1097.8	1074.9	1064.5	1052.1	1045.1	1038.1	1029.7
30°	1206.8	1155.6	1115.5	1084.0	1058.8	1038.3	1027.3	1018.7	1012.4	1006.0	1001.4
32.5°	1162.8	1115.3	1076.4	1045.6	1020.4	1004.9	995.2	989.1	982.1	974.5	968.6
35°	1104.5	1052.5	1014.7	988.0	968.3	956.4	945.4	939.9	932.1	932.1	925.7
37.5°	1038.8	993.9	960.6	936.1	918.5	908.0	896.1	892.2	887.2	883.8	881.7
40°	999.8	958.1	926.6	902.1	883.2	874.5	865.2	858.9	855.7	851.7	850.2
42.5°	959.5	919.6	889.4	866.9	850.5	843.1	834.2	829.9	823.5	818.4	817.5
45°	898.2	859.6	832.1	814.0	799.8	791.1	785.7	776.2	773.1	766.8	766.0
47.5°	840.1	803.1	776.1	761.2	748.8	741.7	733.1	723.6	720.0	716.8	716.5
50°	796.7	762.9	737.6	723.5	711.7	701.5	692.8	686.4	684.1	684.1	685.7
52.5°	752.6	723.8	702.4	685.0	673.9	663.0	655.0	651.2	647.5	651.4	654.2
55°	688.0	658.9	643.2	626.6	615.6	603.0	599.1	597.5	595.1	601.5	604.6
57.5°	619.7	599.3	580.8	564.4	554.5	547.2	541.9	541.0	545.4	548.4	558.6
60°	576.2	552.6	536.1	523.5	511.7	507.0	505.4	503.8	507.0	515.6	529.0
62.5°	528.4	509.2	491.4	481.9	473.2	465.4	465.0	466.1	472.3	482.2	495.6
65°	458.2	441.6	429.8	418.8	411.7	407.0	408.6	411.7	418.8	432.2	447.2
67.5°	386.9	375.5	365.0	356.0	349.2	349.2	350.8	355.5	363.9	379.3	392.9
70°	340.8	328.3	319.6	315.7	310.1	307.0	311.7	319.6	326.7	340.8	352.6
72.5°	294.9	284.2	277.4	274.8	272.4	269.8	271.5	279.9	289.5	303.7	317.4
75°	226.7	222.8	218.0	214.9	212.6	214.1	215.7	223.6	231.5	246.4	262.2
77.5°	165.5	161.4	158.5	157.7	156.5	157.2	161.7	167.5	175.2	186.1	198.0
80°	125.1	123.6	122.0	121.2	121.2	122.0	128.4	132.3	139.4	149.6	159.1
82.5°	91.2	90.2	89.9	89.8	90.4	90.5	94.3	99.5	105.3	113.0	121.2
85°	48.1	46.5	48.8	49.6	48.1	50.4	51.9	55.1	57.5	61.4	65.3
87.5°	17.7	19.3	19.0	20.0	20.4	22.0	21.6	24.4	26.0	27.5	27.1
90°	9.5	11.5	13.3	15.1	17.0	18.8	20.1	21.4	22.7	24.0	25.0
92.5°	12.2	12.3	13.9	15.6	17.2	18.8	20.1	21.4	22.7	24.0	24.8
95°	63.7	58.5	48.5	38.6	28.7	18.8	20.1	21.4	22.7	24.0	24.6
97.5°	145.3	136.2	116.5	96.9	77.4	57.8	50.4	43.0	35.6	28.3	24.6
100°	199.1	200.1	201.1	202.2	203.2	204.2	165.3	126.5	87.7	48.8	28.8
102.5°	257.2	258.0	258.6	259.3	259.9	260.5	253.2	245.8	238.5	231.2	218.6
105°	349.2	349.7	349.7	349.7	349.7	349.7	349.7	349.7	349.7	349.7	349.6
107.5°	440.4	440.6	441.1	441.6	442.2	442.7	442.7	442.8	442.8	442.9	442.5
110°	502.3	502.6	503.1	503.6	504.1	504.6	503.9	503.1	502.3	501.5	501.3



TEST NUMBER: P333331-840

CATALOG NUMBER: S125DIP-S1270D1205U840-4F0-1E-UDD-A

**CANDELA DISTRIBUTION (continued):**

	110°	115°	120°	125°	130°	135°	140°	145°	150°	155°	160°
112.5°	563.0	563.5	563.8	564.1	564.4	564.7	563.8	562.8	561.8	560.8	560.1
115°	653.1	653.9	654.1	654.4	654.6	654.9	653.9	652.8	651.8	650.8	649.4
117.5°	738.0	738.5	739.5	740.4	741.4	742.5	741.1	739.7	738.4	737.0	736.0
120°	793.6	793.8	794.6	795.4	796.1	796.9	796.4	795.9	795.4	794.9	794.0
122.5°	848.3	849.0	849.3	849.7	850.1	850.4	849.9	849.4	848.9	848.4	847.3
125°	928.6	929.5	929.5	929.5	929.5	929.5	928.5	927.5	926.3	925.3	924.4
127.5°	1000.0	1000.6	1000.4	1000.3	1000.1	1000.0	999.4	998.8	998.3	997.6	996.4
130°	1045.1	1045.8	1046.1	1046.4	1046.6	1046.9	1046.1	1045.3	1044.5	1043.8	1042.7
132.5°	1091.0	1091.5	1090.9	1090.3	1089.7	1089.1	1089.0	1088.8	1088.6	1088.5	1087.8
135°	1155.3	1155.8	1155.3	1154.8	1154.2	1153.7	1153.2	1152.7	1152.2	1151.7	1150.5
137.5°	1213.4	1213.8	1213.4	1212.8	1212.3	1211.9	1212.0	1212.1	1212.2	1212.3	1211.7
140°	1248.5	1248.6	1248.4	1248.1	1247.9	1247.6	1248.1	1248.6	1249.1	1249.7	1249.1
142.5°	1282.4	1282.7	1283.1	1283.4	1283.8	1284.2	1284.3	1284.4	1284.5	1284.6	1283.9
145°	1334.1	1334.4	1334.4	1334.4	1334.4	1334.4	1334.7	1334.9	1335.2	1335.4	1334.8
147.5°	1376.2	1376.3	1376.6	1377.0	1377.4	1377.7	1378.0	1378.3	1378.6	1378.9	1378.1
150°	1402.8	1402.8	1403.3	1403.8	1404.3	1404.8	1405.3	1405.9	1406.4	1406.9	1406.1
152.5°	1427.4	1427.1	1427.7	1428.3	1428.8	1429.3	1429.8	1430.3	1430.9	1431.4	1430.7
155°	1460.8	1460.3	1460.8	1461.3	1461.9	1462.4	1463.2	1463.9	1464.7	1465.5	1464.8
157.5°	1490.3	1489.9	1490.0	1490.0	1490.1	1490.1	1490.9	1491.8	1492.6	1493.4	1492.8
160°	1506.6	1505.9	1506.2	1506.4	1506.7	1506.9	1508.0	1509.0	1510.1	1511.2	1510.7
162.5°	1521.6	1521.0	1521.2	1521.5	1521.8	1522.0	1523.5	1524.9	1526.4	1527.8	1527.4
165°	1541.8	1541.2	1541.4	1541.7	1541.9	1542.2	1543.8	1545.3	1546.9	1548.4	1548.1
167.5°	1556.6	1555.9	1556.2	1556.4	1556.7	1557.0	1558.8	1560.7	1562.6	1564.5	1564.3
170°	1564.2	1563.5	1563.7	1564.0	1564.2	1564.5	1566.6	1568.6	1570.7	1572.9	1572.7
172.5°	1569.8	1569.1	1569.6	1570.1	1570.5	1571.0	1573.0	1574.8	1576.7	1578.5	1578.3
175°	1577.0	1576.3	1576.6	1576.9	1577.1	1577.4	1579.4	1581.5	1583.7	1585.7	1585.6
177.5°	1581.0	1580.5	1580.7	1580.9	1581.1	1581.3	1582.9	1584.3	1585.8	1587.2	1587.1
180°	1583.3	1583.3	1583.3	1583.3	1583.3	1583.3	1583.3	1583.3	1583.3	1583.3	1583.3



TEST NUMBER: P333331-840

CATALOG NUMBER: S125DIP-S1270D1205U840-4F0-1E-UDD-A

**CANDELA DISTRIBUTION (continued):**

	165°	170°	175°	180°	185°	190°	195°	200°	205°	210°	215°
0°	1854.7	1854.7	1854.7	1854.7	1854.7	1854.7	1854.7	1854.7	1854.7	1854.7	1854.7
2.5°	1767.2	1771.5	1767.8	1772.8	1767.8	1771.5	1767.2	1770.9	1776.6	1772.8	1781.6
5°	1628.7	1621.6	1626.4	1623.3	1626.4	1621.6	1628.7	1632.6	1642.1	1645.3	1651.5
7.5°	1500.9	1494.1	1486.4	1482.8	1486.4	1494.1	1500.9	1503.3	1511.3	1523.1	1532.1
10°	1420.9	1412.3	1411.5	1405.9	1411.5	1412.3	1420.9	1429.6	1435.1	1450.1	1460.3
12.5°	1362.3	1354.3	1345.3	1343.0	1345.3	1354.3	1362.3	1369.8	1371.5	1388.4	1395.4
15°	1279.2	1272.9	1267.4	1272.1	1267.4	1272.9	1279.2	1283.9	1292.6	1304.4	1312.3
17.5°	1210.1	1204.9	1204.0	1198.1	1204.0	1204.9	1210.1	1212.7	1227.0	1234.7	1248.2
20°	1166.7	1162.8	1164.3	1154.1	1164.3	1162.8	1166.7	1173.8	1187.9	1191.8	1206.0
22.5°	1132.1	1124.3	1123.4	1121.4	1123.4	1124.3	1132.1	1138.4	1141.3	1153.5	1163.2
25°	1077.7	1073.8	1069.9	1073.8	1069.9	1073.8	1077.7	1084.8	1087.9	1096.6	1106.0
27.5°	1030.3	1025.6	1024.5	1024.9	1024.5	1025.6	1030.3	1029.7	1038.1	1045.1	1052.1
30°	1001.4	993.5	994.2	993.5	994.2	993.5	1001.4	1001.4	1006.0	1012.4	1018.7
32.5°	969.9	964.5	963.4	962.0	963.4	964.5	969.9	968.6	974.5	982.1	989.1
35°	923.4	923.4	919.5	919.5	919.5	923.4	923.4	925.7	932.1	932.1	939.9
37.5°	879.8	879.0	876.7	877.0	876.7	879.0	879.8	881.7	883.8	887.2	892.2
40°	847.1	846.3	843.8	839.2	843.8	846.3	847.1	850.2	851.7	855.7	858.9
42.5°	815.6	812.8	811.7	810.2	811.7	812.8	815.6	817.5	818.4	823.5	829.9
45°	766.0	766.0	764.4	763.6	764.4	766.0	766.0	766.0	766.8	773.1	776.2
47.5°	717.8	719.2	722.2	721.8	722.2	719.2	717.8	716.5	716.8	720.0	723.6
50°	688.8	689.6	692.0	692.8	692.0	689.6	688.8	685.7	684.1	684.1	686.4
52.5°	656.7	661.3	664.3	663.8	664.3	661.3	656.7	654.2	651.4	647.5	651.2
55°	611.7	617.1	622.7	623.5	622.7	617.1	611.7	604.6	601.5	595.1	597.5
57.5°	567.1	574.8	580.7	582.5	580.7	574.8	567.1	558.6	548.4	545.4	541.0
60°	536.8	547.1	554.2	557.3	554.2	547.1	536.8	529.0	515.6	507.0	503.8
62.5°	507.9	519.4	526.4	527.1	526.4	519.4	507.9	495.6	482.2	472.3	466.1
65°	460.5	472.3	478.6	483.3	478.6	472.3	460.5	447.2	432.2	418.8	411.7
67.5°	409.5	421.3	428.3	432.0	428.3	421.3	409.5	392.9	379.3	363.9	355.5
70°	372.3	384.2	393.6	396.8	393.6	384.2	372.3	352.6	340.8	326.7	319.6
72.5°	335.8	346.4	354.0	357.7	354.0	346.4	335.8	317.4	303.7	289.5	279.9
75°	272.4	286.5	293.7	297.6	293.7	286.5	272.4	262.2	246.4	231.5	223.6
77.5°	210.1	223.0	227.2	229.2	227.2	223.0	210.1	198.0	186.1	175.2	167.5
80°	168.4	176.3	181.9	182.6	181.9	176.3	168.4	159.1	149.6	139.4	132.3
82.5°	129.5	136.0	137.7	139.8	137.7	136.0	129.5	121.2	113.0	105.3	99.5
85°	70.9	74.0	74.8	74.0	74.8	74.0	70.9	65.3	61.4	57.5	55.1
87.5°	28.5	28.0	28.2	29.6	28.2	28.0	28.5	27.1	27.5	26.0	24.4
90°	25.9	26.6	27.4	28.2	27.4	26.6	25.9	25.0	24.0	22.7	21.4
92.5°	25.1	25.5	26.0	26.3	26.0	25.5	25.1	24.8	24.0	22.7	21.4
95°	24.6	24.6	24.6	24.6	24.6	24.6	24.6	24.6	24.0	22.7	21.4
97.5°	24.6	24.6	24.6	24.6	24.6	24.6	24.6	24.6	28.3	35.6	43.0
100°	27.8	26.8	25.7	24.6	25.7	26.8	27.8	28.8	48.8	87.7	126.5
102.5°	200.9	183.1	165.4	147.6	165.4	183.1	200.9	218.6	231.2	238.5	245.8
105°	349.3	349.1	348.8	348.6	348.8	349.1	349.3	349.6	349.7	349.7	349.7
107.5°	441.7	441.0	440.2	439.4	440.2	441.0	441.7	442.5	442.9	442.8	442.8
110°	501.5	501.8	502.1	502.3	502.1	501.8	501.5	501.3	501.5	502.3	503.1



TEST NUMBER: P333331-840

CATALOG NUMBER: S125DIP-S1270D1205U840-4F0-1E-UDD-A

**CANDELA DISTRIBUTION (continued):**

	165°	170°	175°	180°	185°	190°	195°	200°	205°	210°	215°
112.5°	559.8	559.4	559.1	558.7	559.1	559.4	559.8	560.1	560.8	561.8	562.8
115°	647.8	646.3	644.7	643.2	644.7	646.3	647.8	649.4	650.8	651.8	652.8
117.5°	735.3	734.7	734.0	733.3	734.0	734.7	735.3	736.0	737.0	738.4	739.7
120°	792.6	791.3	790.0	788.7	790.0	791.3	792.6	794.0	794.9	795.4	795.9
122.5°	845.8	844.2	842.8	841.3	842.8	844.2	845.8	847.3	848.4	848.9	849.4
125°	923.6	922.9	922.1	921.3	922.1	922.9	923.6	924.4	925.3	926.3	927.5
127.5°	994.5	992.5	990.6	988.7	990.6	992.5	994.5	996.4	997.6	998.3	998.8
130°	1041.4	1040.2	1038.8	1037.5	1038.8	1040.2	1041.4	1042.7	1043.8	1044.5	1045.3
132.5°	1086.5	1085.2	1083.9	1082.6	1083.9	1085.2	1086.5	1087.8	1088.5	1088.6	1088.8
135°	1149.0	1147.4	1145.9	1144.3	1145.9	1147.4	1149.0	1150.5	1151.7	1152.2	1152.7
137.5°	1210.3	1209.0	1207.6	1206.3	1207.6	1209.0	1210.3	1211.7	1212.3	1212.2	1212.1
140°	1247.6	1246.1	1244.5	1242.9	1244.5	1246.1	1247.6	1249.1	1249.7	1249.1	1248.6
142.5°	1282.3	1280.8	1279.2	1277.7	1279.2	1280.8	1282.3	1283.9	1284.6	1284.5	1284.4
145°	1333.2	1331.7	1330.1	1328.6	1330.1	1331.7	1333.2	1334.8	1335.4	1335.2	1334.9
147.5°	1376.2	1374.3	1372.5	1370.6	1372.5	1374.3	1376.2	1378.1	1378.9	1378.6	1378.3
150°	1404.1	1402.0	1399.9	1397.9	1399.9	1402.0	1404.1	1406.1	1406.9	1406.4	1405.9
152.5°	1428.8	1426.9	1425.0	1423.2	1425.0	1426.9	1428.8	1430.7	1431.4	1430.9	1430.3
155°	1462.8	1460.7	1458.5	1456.5	1458.5	1460.7	1462.8	1464.8	1465.5	1464.7	1463.9
157.5°	1490.7	1488.6	1486.5	1484.4	1486.5	1488.6	1490.7	1492.8	1493.4	1492.6	1491.8
160°	1508.5	1506.4	1504.4	1502.3	1504.4	1506.4	1508.5	1510.7	1511.2	1510.1	1509.0
162.5°	1525.1	1522.8	1520.6	1518.2	1520.6	1522.8	1525.1	1527.4	1527.8	1526.4	1524.9
165°	1546.1	1544.0	1541.9	1539.8	1541.9	1544.0	1546.1	1548.1	1548.4	1546.9	1545.3
167.5°	1561.9	1559.5	1557.2	1554.9	1557.2	1559.5	1561.9	1564.3	1564.5	1562.6	1560.7
170°	1570.3	1568.0	1565.7	1563.3	1565.7	1568.0	1570.3	1572.7	1572.9	1570.7	1568.6
172.5°	1576.0	1573.7	1571.2	1568.9	1571.2	1573.7	1576.0	1578.3	1578.5	1576.7	1574.8
175°	1583.3	1580.9	1578.5	1576.2	1578.5	1580.9	1583.3	1585.6	1585.7	1583.7	1581.5
177.5°	1585.5	1583.8	1582.1	1580.4	1582.1	1583.8	1585.5	1587.1	1587.2	1585.8	1584.3
180°	1583.3	1583.3	1583.3	1583.3	1583.3	1583.3	1583.3	1583.3	1583.3	1583.3	1583.3



TEST NUMBER: P333331-840

CATALOG NUMBER: S125DIP-S1270D1205U840-4F0-1E-UDD-A

**CANDELA DISTRIBUTION (continued):**

	220°	225°	230°	235°	240°	245°	250°	255°	260°	265°	270°
0°	1854.7	1854.7	1854.7	1854.7	1854.7	1854.7	1854.7	1854.7	1854.7	1854.7	1854.7
2.5°	1773.4	1781.0	1790.4	1797.4	1810.0	1815.6	1822.5	1828.3	1838.3	1847.8	1859.1
5°	1654.0	1667.3	1685.5	1705.1	1728.0	1743.6	1765.7	1779.1	1805.8	1830.3	1853.9
7.5°	1545.6	1562.0	1587.6	1612.9	1642.7	1669.8	1697.4	1728.0	1762.1	1802.4	1835.7
10°	1471.3	1493.4	1520.9	1552.4	1588.6	1620.1	1657.1	1690.1	1731.8	1779.1	1823.2
12.5°	1412.1	1431.0	1461.7	1492.0	1530.7	1569.0	1607.3	1651.1	1699.7	1752.0	1807.5
15°	1330.4	1346.2	1371.3	1413.0	1452.4	1490.2	1547.6	1588.6	1650.0	1708.3	1775.1
17.5°	1260.6	1280.2	1301.4	1337.2	1378.0	1425.1	1476.5	1527.8	1587.0	1660.8	1736.3
20°	1217.8	1233.6	1258.0	1285.6	1328.8	1376.0	1424.8	1476.8	1549.2	1625.6	1706.7
22.5°	1171.2	1188.2	1215.8	1245.9	1282.2	1327.6	1381.4	1438.4	1514.0	1589.0	1677.1
25°	1116.3	1128.1	1153.3	1180.0	1216.3	1254.9	1310.7	1373.7	1448.4	1534.3	1624.1
27.5°	1064.5	1074.9	1097.8	1121.2	1153.9	1199.7	1249.6	1313.2	1383.7	1470.7	1570.1
30°	1027.3	1038.3	1058.8	1084.0	1115.5	1155.6	1206.8	1266.7	1342.2	1427.2	1531.2
32.5°	995.2	1004.9	1020.4	1045.6	1076.4	1115.3	1162.8	1223.8	1299.4	1385.6	1487.6
35°	945.4	956.4	968.3	988.0	1014.7	1052.5	1104.5	1162.0	1234.4	1317.8	1411.5
37.5°	896.1	908.0	918.5	936.1	960.6	993.9	1038.8	1098.6	1164.2	1244.6	1334.4
40°	865.2	874.5	883.2	902.1	926.6	958.1	999.8	1053.3	1122.6	1197.4	1272.1
42.5°	834.2	843.1	850.5	866.9	889.4	919.6	959.5	1011.7	1076.0	1145.7	1211.6
45°	785.7	791.1	799.8	814.0	832.1	859.6	898.2	944.6	999.0	1065.1	1114.7
47.5°	733.1	741.7	748.8	761.2	776.1	803.1	840.1	879.6	928.9	978.1	1013.0
50°	692.8	701.5	711.7	723.5	737.6	762.9	796.7	836.8	878.5	916.4	946.2
52.5°	655.0	663.0	673.9	685.0	702.4	723.8	752.6	788.3	829.4	856.5	881.4
55°	599.1	603.0	615.6	626.6	643.2	658.9	688.0	719.5	744.7	765.2	785.7
57.5°	541.9	547.2	554.5	564.4	580.8	599.3	619.7	647.5	662.4	672.9	688.8
60°	505.4	507.0	511.7	523.5	536.1	552.6	576.2	595.9	606.9	615.6	628.9
62.5°	465.0	465.4	473.2	481.9	491.4	509.2	528.4	544.3	553.4	557.6	570.4
65°	408.6	407.0	411.7	418.8	429.8	441.6	458.2	472.3	471.5	476.3	484.1
67.5°	350.8	349.2	349.2	356.0	365.0	375.5	386.9	395.1	395.2	401.5	405.5
70°	311.7	307.0	310.1	315.7	319.6	328.3	340.8	344.1	344.8	347.9	351.8
72.5°	271.5	269.8	272.4	274.8	277.4	284.2	294.9	296.8	296.9	298.8	305.3
75°	215.7	214.1	212.6	214.9	218.0	222.8	226.7	229.8	229.0	229.8	234.6
77.5°	161.7	157.2	156.5	157.7	158.5	161.4	165.5	165.1	165.9	165.8	171.2
80°	128.4	122.0	121.2	121.2	122.0	123.6	125.1	126.7	124.4	126.7	128.4
82.5°	94.3	90.5	90.4	89.8	89.9	90.2	91.2	92.1	91.6	92.7	93.7
85°	51.9	50.4	48.1	49.6	48.8	46.5	48.1	45.6	44.8	45.6	46.5
87.5°	21.6	22.0	20.4	20.0	19.0	19.3	17.7	16.6	15.6	15.8	17.3
90°	20.1	18.8	17.0	15.1	13.3	11.5	9.5	7.5	5.4	3.2	1.2
92.5°	20.1	18.8	17.2	15.6	13.9	12.3	12.2	13.7	15.1	16.7	18.1
95°	20.1	18.8	28.7	38.6	48.5	58.5	63.7	64.5	65.3	66.1	66.9
97.5°	50.4	57.8	77.4	96.9	116.5	136.2	145.3	143.9	142.5	141.1	139.7
100°	165.3	204.2	203.2	202.2	201.1	200.1	199.1	198.3	197.5	196.8	196.0
102.5°	253.2	260.5	259.9	259.3	258.6	258.0	257.2	256.2	255.3	254.3	253.3
105°	349.7	349.7	349.7	349.7	349.7	349.7	349.2	348.2	347.1	346.1	345.1
107.5°	442.7	442.7	442.2	441.6	441.1	440.6	440.4	440.4	440.4	440.4	440.4
110°	503.9	504.6	504.1	503.6	503.1	502.6	502.3	502.3	502.3	502.3	502.3



TEST NUMBER: P333331-840

CATALOG NUMBER: S125DIP-S1270D1205U840-4F0-1E-UDD-A

**CANDELA DISTRIBUTION (continued):**

	220°	225°	230°	235°	240°	245°	250°	255°	260°	265°	270°
112.5°	563.8	564.7	564.4	564.1	563.8	563.5	563.0	562.4	561.8	561.2	560.6
115°	653.9	654.9	654.6	654.4	654.1	653.9	653.1	651.8	650.5	649.1	647.8
117.5°	741.1	742.5	741.4	740.4	739.5	738.5	738.0	738.1	738.1	738.2	738.2
120°	796.4	796.9	796.1	795.4	794.6	793.8	793.6	793.8	794.1	794.3	794.6
122.5°	849.9	850.4	850.1	849.7	849.3	849.0	848.3	847.3	846.3	845.4	844.3
125°	928.5	929.5	929.5	929.5	929.5	929.5	928.6	926.8	924.9	923.1	921.3
127.5°	999.4	1000.0	1000.1	1000.3	1000.4	1000.6	1000.0	998.7	997.3	996.1	994.8
130°	1046.1	1046.9	1046.6	1046.4	1046.1	1045.8	1045.1	1043.8	1042.5	1041.2	1039.9
132.5°	1089.0	1089.1	1089.7	1090.3	1090.9	1091.5	1091.0	1089.4	1087.9	1086.4	1084.9
135°	1153.2	1153.7	1154.2	1154.8	1155.3	1155.8	1155.3	1153.7	1152.2	1150.5	1149.0
137.5°	1212.0	1211.9	1212.3	1212.8	1213.4	1213.8	1213.4	1211.9	1210.6	1209.3	1207.9
140°	1248.1	1247.6	1247.9	1248.1	1248.4	1248.6	1248.5	1248.0	1247.5	1247.0	1246.4
142.5°	1284.3	1284.2	1283.8	1283.4	1283.1	1282.7	1282.4	1282.1	1281.8	1281.4	1281.1
145°	1334.7	1334.4	1334.4	1334.4	1334.4	1334.4	1334.1	1333.6	1333.1	1332.6	1332.1
147.5°	1378.0	1377.7	1377.4	1377.0	1376.6	1376.3	1376.2	1376.3	1376.4	1376.5	1376.6
150°	1405.3	1404.8	1404.3	1403.8	1403.3	1402.8	1402.8	1403.3	1403.8	1404.3	1404.8
152.5°	1429.8	1429.3	1428.8	1428.3	1427.7	1427.1	1427.4	1428.7	1429.8	1431.0	1432.1
155°	1463.2	1462.4	1461.9	1461.3	1460.8	1460.3	1460.8	1462.4	1463.9	1465.5	1467.0
157.5°	1490.9	1490.1	1490.1	1490.0	1490.0	1489.9	1490.3	1491.3	1492.2	1493.1	1494.1
160°	1508.0	1506.9	1506.7	1506.4	1506.2	1505.9	1506.6	1508.1	1509.7	1511.3	1512.9
162.5°	1523.5	1522.0	1521.8	1521.5	1521.2	1521.0	1521.6	1523.2	1524.7	1526.3	1527.8
165°	1543.8	1542.2	1541.9	1541.7	1541.4	1541.2	1541.8	1543.4	1544.9	1546.5	1548.0
167.5°	1558.8	1557.0	1556.7	1556.4	1556.2	1555.9	1556.6	1558.2	1559.8	1561.5	1563.1
170°	1566.6	1564.5	1564.2	1564.0	1563.7	1563.5	1564.2	1566.0	1567.8	1569.7	1571.6
172.5°	1573.0	1571.0	1570.5	1570.1	1569.6	1569.1	1569.8	1571.7	1573.5	1575.3	1577.1
175°	1579.4	1577.4	1577.1	1576.9	1576.6	1576.3	1577.0	1578.5	1580.1	1581.7	1583.3
177.5°	1582.9	1581.3	1581.1	1580.9	1580.7	1580.5	1581.0	1582.4	1583.6	1584.8	1586.1
180°	1583.3	1583.3	1583.3	1583.3	1583.3	1583.3	1583.3	1583.3	1583.3	1583.3	1583.3



TEST NUMBER: P333331-840

CATALOG NUMBER: S125DIP-S1270D1205U840-4F0-1E-UDD-A

**CANDELA DISTRIBUTION (continued):**

	275°	280°	285°	290°	295°	300°	305°	310°	315°	320°	325°
0°	1854.7	1854.7	1854.7	1854.7	1854.7	1854.7	1854.7	1854.7	1854.7	1854.7	1854.7
2.5°	1864.7	1873.6	1879.3	1890.0	1898.7	1903.8	1908.2	1912.0	1916.4	1920.2	1930.9
5°	1876.7	1897.1	1914.5	1941.3	1965.7	1984.6	2005.0	2023.2	2038.1	2059.3	2075.9
7.5°	1871.5	1907.8	1946.0	1987.4	2029.7	2069.1	2105.4	2139.2	2169.9	2207.1	2239.6
10°	1866.4	1916.1	1964.9	2020.7	2078.2	2127.1	2172.7	2219.2	2253.0	2300.3	2340.4
12.5°	1862.7	1921.1	1980.0	2047.2	2110.3	2179.3	2240.1	2273.9	2325.4	2363.2	2411.0
15°	1846.8	1924.0	2005.0	2080.6	2170.3	2234.1	2287.6	2353.8	2401.8	2449.8	2501.7
17.5°	1818.3	1905.7	1996.4	2095.4	2181.5	2250.0	2319.0	2382.8	2440.0	2504.5	2569.1
20°	1805.0	1892.5	1996.4	2097.9	2182.1	2253.8	2324.6	2394.7	2457.7	2540.3	2615.1
22.5°	1777.4	1883.0	1978.7	2077.8	2164.5	2242.4	2322.8	2402.3	2486.0	2579.4	2673.0
25°	1728.0	1835.0	1936.5	2034.2	2121.5	2219.2	2304.9	2411.3	2518.3	2641.9	2758.3
27.5°	1676.6	1779.1	1872.2	1966.4	2068.3	2178.9	2290.2	2410.7	2550.9	2706.9	2871.2
30°	1635.1	1731.8	1822.4	1919.2	2025.5	2149.9	2271.9	2415.2	2577.4	2752.9	2948.1
32.5°	1586.5	1675.8	1763.8	1866.3	1982.1	2113.3	2255.5	2412.7	2607.6	2807.0	3008.0
35°	1503.6	1578.3	1668.9	1778.3	1908.9	2059.3	2223.9	2409.6	2633.2	2862.3	3031.5
37.5°	1405.1	1474.8	1570.1	1690.1	1827.1	1988.5	2183.7	2404.2	2641.6	2824.2	2878.8
40°	1339.1	1403.6	1502.8	1627.2	1767.3	1938.1	2152.2	2385.3	2615.1	2731.6	2686.7
42.5°	1268.5	1336.3	1432.9	1556.0	1706.9	1892.8	2112.5	2345.6	2538.3	2582.3	2427.3
45°	1157.2	1227.3	1322.5	1446.9	1609.0	1810.6	2039.6	2251.4	2362.4	2282.9	2042.9
47.5°	1053.8	1119.4	1207.7	1336.1	1503.4	1711.8	1932.5	2101.4	2110.2	1920.5	1664.1
50°	983.2	1043.8	1132.8	1261.1	1427.2	1638.2	1837.3	1970.3	1910.6	1695.7	1449.3
52.5°	913.9	973.3	1061.0	1188.1	1352.3	1545.6	1730.9	1824.3	1711.5	1491.0	1280.5
55°	814.0	866.0	951.7	1069.0	1224.9	1404.4	1561.9	1594.1	1447.6	1230.4	1059.6
57.5°	716.4	764.9	842.9	951.0	1093.5	1252.4	1375.5	1368.7	1213.9	1027.4	891.9
60°	650.3	697.5	766.8	872.2	1002.1	1139.1	1244.6	1219.4	1065.9	905.3	791.1
62.5°	591.1	633.2	698.7	791.0	909.6	1036.4	1123.1	1085.9	935.5	795.1	704.9
65°	503.8	539.3	595.1	673.9	772.2	877.0	943.8	895.9	767.5	658.1	585.7
67.5°	420.5	448.9	495.7	558.6	642.5	726.6	767.4	719.0	616.4	536.5	482.9
70°	367.6	392.8	429.0	484.9	558.2	628.9	659.6	616.4	528.3	459.7	421.1
72.5°	314.8	335.5	367.3	417.6	476.3	537.7	564.6	523.2	450.8	392.9	356.9
75°	243.3	257.4	279.4	314.1	360.5	409.4	424.3	388.1	341.6	298.3	274.8
77.5°	174.1	186.1	202.8	224.7	257.6	288.6	301.6	280.7	244.8	217.4	198.0
80°	133.8	140.2	154.3	172.4	198.3	218.0	226.7	213.4	188.1	167.6	152.7
82.5°	95.4	101.7	110.2	125.1	141.7	155.1	164.4	155.4	137.1	121.1	112.4
85°	46.5	50.4	55.1	61.4	74.0	81.9	81.1	75.5	68.5	62.2	57.5
87.5°	17.1	18.1	20.4	23.9	26.3	29.1	30.7	29.8	27.7	26.1	24.4
90°	3.2	5.4	7.5	9.5	11.5	13.3	15.1	17.0	18.8	20.1	21.4
92.5°	16.7	15.1	13.7	12.2	12.3	13.9	15.6	17.2	18.8	20.1	21.4
95°	66.1	65.3	64.5	63.7	58.5	48.5	38.6	28.7	18.8	20.1	21.4
97.5°	141.1	142.5	143.9	145.3	136.2	116.5	96.9	77.4	57.8	50.4	43.0
100°	196.8	197.5	198.3	199.1	200.1	201.1	202.2	203.2	204.2	165.3	126.5
102.5°	254.3	255.3	256.2	257.2	258.0	258.6	259.3	259.9	260.5	253.2	245.8
105°	346.1	347.1	348.2	349.2	349.7	349.7	349.7	349.7	349.7	349.7	349.7
107.5°	440.4	440.4	440.4	440.4	440.6	441.1	441.6	442.2	442.7	442.7	442.8
110°	502.3	502.3	502.3	502.3	502.6	503.1	503.6	504.1	504.6	503.9	503.1





TEST NUMBER: P333331-840

CATALOG NUMBER: S125DIP-S1270D1205U840-4F0-1E-UDD-A

**CANDELA DISTRIBUTION (continued):**

	275°	280°	285°	290°	295°	300°	305°	310°	315°	320°	325°
112.5°	561.2	561.8	562.4	563.0	563.5	563.8	564.1	564.4	564.7	563.8	562.8
115°	649.1	650.5	651.8	653.1	653.9	654.1	654.4	654.6	654.9	653.9	652.8
117.5°	738.2	738.1	738.1	738.0	738.5	739.5	740.4	741.4	742.5	741.1	739.7
120°	794.3	794.1	793.8	793.6	793.8	794.6	795.4	796.1	796.9	796.4	795.9
122.5°	845.4	846.3	847.3	848.3	849.0	849.3	849.7	850.1	850.4	849.9	849.4
125°	923.1	924.9	926.8	928.6	929.5	929.5	929.5	929.5	929.5	928.5	927.5
127.5°	996.1	997.3	998.7	1000.0	1000.6	1000.4	1000.3	1000.1	1000.0	999.4	998.8
130°	1041.2	1042.5	1043.8	1045.1	1045.8	1046.1	1046.4	1046.6	1046.9	1046.1	1045.3
132.5°	1086.4	1087.9	1089.4	1091.0	1091.5	1090.9	1090.3	1089.7	1089.1	1089.0	1088.8
135°	1150.5	1152.2	1153.7	1155.3	1155.8	1155.3	1154.8	1154.2	1153.7	1153.2	1152.7
137.5°	1209.3	1210.6	1211.9	1213.4	1213.8	1213.4	1212.8	1212.3	1211.9	1212.0	1212.1
140°	1247.0	1247.5	1248.0	1248.5	1248.6	1248.4	1248.1	1247.9	1247.6	1248.1	1248.6
142.5°	1281.4	1281.8	1282.1	1282.4	1282.7	1283.1	1283.4	1283.8	1284.2	1284.3	1284.4
145°	1332.6	1333.1	1333.6	1334.1	1334.4	1334.4	1334.4	1334.4	1334.4	1334.7	1334.9
147.5°	1376.5	1376.4	1376.3	1376.2	1376.3	1376.6	1377.0	1377.4	1377.7	1378.0	1378.3
150°	1404.3	1403.8	1403.3	1402.8	1402.8	1403.3	1403.8	1404.3	1404.8	1405.3	1405.9
152.5°	1431.0	1429.8	1428.7	1427.4	1427.1	1427.7	1428.3	1428.8	1429.3	1429.8	1430.3
155°	1465.5	1463.9	1462.4	1460.8	1460.3	1460.8	1461.3	1461.9	1462.4	1463.2	1463.9
157.5°	1493.1	1492.2	1491.3	1490.3	1489.9	1490.0	1490.0	1490.1	1490.1	1490.9	1491.8
160°	1511.3	1509.7	1508.1	1506.6	1505.9	1506.2	1506.4	1506.7	1506.9	1508.0	1509.0
162.5°	1526.3	1524.7	1523.2	1521.6	1521.0	1521.2	1521.5	1521.8	1522.0	1523.5	1524.9
165°	1546.5	1544.9	1543.4	1541.8	1541.2	1541.4	1541.7	1541.9	1542.2	1543.8	1545.3
167.5°	1561.5	1559.8	1558.2	1556.6	1555.9	1556.2	1556.4	1556.7	1557.0	1558.8	1560.7
170°	1569.7	1567.8	1566.0	1564.2	1563.5	1563.7	1564.0	1564.2	1564.5	1566.6	1568.6
172.5°	1575.3	1573.5	1571.7	1569.8	1569.1	1569.6	1570.1	1570.5	1571.0	1573.0	1574.8
175°	1581.7	1580.1	1578.5	1577.0	1576.3	1576.6	1576.9	1577.1	1577.4	1579.4	1581.5
177.5°	1584.8	1583.6	1582.4	1581.0	1580.5	1580.7	1580.9	1581.1	1581.3	1582.9	1584.3
180°	1583.3	1583.3	1583.3	1583.3	1583.3	1583.3	1583.3	1583.3	1583.3	1583.3	1583.3



TEST NUMBER: P333331-840

CATALOG NUMBER: S125DIP-S1270D1205U840-4F0-1E-UDD-A

**CANDELA DISTRIBUTION (continued):**

	330°	335°	340°	345°	350°	355°	360°
0°	1854.7	1854.7	1854.7	1854.7	1854.7	1854.7	1854.7
2.5°	1939.6	1944.7	1955.4	1951.7	1956.7	1959.2	1961.8
5°	2096.4	2121.5	2132.5	2131.0	2147.5	2143.5	2139.6
7.5°	2273.3	2299.8	2314.6	2333.0	2343.7	2344.5	2353.8
10°	2373.5	2408.1	2422.3	2442.0	2454.6	2461.6	2460.8
12.5°	2450.2	2477.4	2509.1	2518.8	2535.8	2544.8	2541.4
15°	2542.7	2586.0	2619.1	2635.5	2656.9	2663.1	2671.8
17.5°	2625.2	2683.3	2721.9	2773.2	2792.6	2804.4	2797.4
20°	2687.6	2763.9	2802.5	2863.9	2897.7	2915.9	2909.5
22.5°	2761.3	2843.9	2915.2	2968.4	3019.9	3044.3	3049.4
25°	2887.5	3000.8	3105.5	3175.6	3239.3	3254.3	3287.4
27.5°	3028.6	3162.2	3274.2	3347.9	3392.2	3408.9	3419.3
30°	3117.4	3250.4	3334.7	3381.8	3396.1	3394.5	3392.8
32.5°	3160.8	3244.1	3260.3	3247.1	3214.7	3187.2	3158.7
35°	3099.3	3037.1	2944.2	2824.5	2736.3	2647.4	2638.8
37.5°	2787.3	2588.5	2433.9	2261.2	2161.5	2100.0	2057.5
40°	2493.9	2268.0	2080.6	1935.0	1833.4	1793.3	1753.9
42.5°	2175.2	1959.3	1793.4	1671.7	1595.4	1550.8	1519.6
45°	1767.3	1576.8	1446.9	1358.8	1298.1	1263.4	1243.7
47.5°	1448.1	1307.3	1196.9	1133.3	1091.4	1064.5	1064.6
50°	1276.9	1142.3	1069.0	1018.7	982.4	961.2	965.1
52.5°	1125.1	1024.5	962.0	919.8	893.0	879.9	879.5
55°	940.7	868.3	827.4	796.7	778.5	763.6	766.8
57.5°	804.7	743.6	716.2	690.7	678.1	672.2	663.5
60°	720.3	673.1	649.4	628.9	616.4	611.7	603.0
62.5°	645.4	608.2	585.2	568.6	557.1	555.6	548.9
65°	542.4	514.0	493.6	485.7	473.9	470.8	470.8
67.5°	447.2	426.9	410.9	403.6	398.5	399.3	395.5
70°	387.3	370.8	360.5	352.6	348.7	349.5	346.4
72.5°	338.8	320.4	311.4	306.7	301.5	303.6	302.3
75°	256.6	247.2	242.5	237.7	234.6	233.0	231.5
77.5°	188.4	180.2	176.5	173.8	174.3	170.5	173.5
80°	145.6	138.6	136.2	132.3	131.5	131.5	130.7
82.5°	106.5	102.6	100.9	97.7	96.2	97.5	95.4
85°	55.1	51.9	51.2	51.2	49.6	48.1	51.9
87.5°	24.6	22.4	22.6	22.2	22.3	21.8	20.7
90°	22.7	24.0	25.0	25.9	26.6	27.4	28.2
92.5°	22.7	24.0	24.8	25.1	25.5	26.0	26.3
95°	22.7	24.0	24.6	24.6	24.6	24.6	24.6
97.5°	35.6	28.3	24.6	24.6	24.6	24.6	24.6
100°	87.7	48.8	28.8	27.8	26.8	25.7	24.6
102.5°	238.5	231.2	218.6	200.9	183.1	165.4	147.6
105°	349.7	349.7	349.6	349.3	349.1	348.8	348.6
107.5°	442.8	442.9	442.5	441.7	441.0	440.2	439.4
110°	502.3	501.5	501.3	501.5	501.8	502.1	502.3



TEST NUMBER: P333331-840

CATALOG NUMBER: S125DIP-S1270D1205U840-4F0-1E-UDD-A

**CANDELA DISTRIBUTION (continued):**

	330°	335°	340°	345°	350°	355°	360°
112.5°	561.8	560.8	560.1	559.8	559.4	559.1	558.7
115°	651.8	650.8	649.4	647.8	646.3	644.7	643.2
117.5°	738.4	737.0	736.0	735.3	734.7	734.0	733.3
120°	795.4	794.9	794.0	792.6	791.3	790.0	788.7
122.5°	848.9	848.4	847.3	845.8	844.2	842.8	841.3
125°	926.3	925.3	924.4	923.6	922.9	922.1	921.3
127.5°	998.3	997.6	996.4	994.5	992.5	990.6	988.7
130°	1044.5	1043.8	1042.7	1041.4	1040.2	1038.8	1037.5
132.5°	1088.6	1088.5	1087.8	1086.5	1085.2	1083.9	1082.6
135°	1152.2	1151.7	1150.5	1149.0	1147.4	1145.9	1144.3
137.5°	1212.2	1212.3	1211.7	1210.3	1209.0	1207.6	1206.3
140°	1249.1	1249.7	1249.1	1247.6	1246.1	1244.5	1242.9
142.5°	1284.5	1284.6	1283.9	1282.3	1280.8	1279.2	1277.7
145°	1335.2	1335.4	1334.8	1333.2	1331.7	1330.1	1328.6
147.5°	1378.6	1378.9	1378.1	1376.2	1374.3	1372.5	1370.6
150°	1406.4	1406.9	1406.1	1404.1	1402.0	1399.9	1397.9
152.5°	1430.9	1431.4	1430.7	1428.8	1426.9	1425.0	1423.2
155°	1464.7	1465.5	1464.8	1462.8	1460.7	1458.5	1456.5
157.5°	1492.6	1493.4	1492.8	1490.7	1488.6	1486.5	1484.4
160°	1510.1	1511.2	1510.7	1508.5	1506.4	1504.4	1502.3
162.5°	1526.4	1527.8	1527.4	1525.1	1522.8	1520.6	1518.2
165°	1546.9	1548.4	1548.1	1546.1	1544.0	1541.9	1539.8
167.5°	1562.6	1564.5	1564.3	1561.9	1559.5	1557.2	1554.9
170°	1570.7	1572.9	1572.7	1570.3	1568.0	1565.7	1563.3
172.5°	1576.7	1578.5	1578.3	1576.0	1573.7	1571.2	1568.9
175°	1583.7	1585.7	1585.6	1583.3	1580.9	1578.5	1576.2
177.5°	1585.8	1587.2	1587.1	1585.5	1583.8	1582.1	1580.4
180°	1583.3	1583.3	1583.3	1583.3	1583.3	1583.3	1583.3

(END OF REPORT)