

Scaled data based on original data using  
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State  
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P333333-840

Luminaire Tested: **S125DIP-S1270D1205U840-4F0-1E-UDD-A4**

Issue Date: 3/3/2020

**Test Information**

Test Method: LM-79-08  
Report Number: P333333-840  
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-19,  
Test Lab: INNOVATION CENTER  
Issue Date: 3/3/2020  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: NEO-RAY  
Catalog Number: S125DIP-S1270D1205U840-4F0-1E-UDD-A4  
Description: DEFINE 5 DIRECT-INDIRECT PENDANT LED LUMINAIRE  
DOWNLIGHT 1270 LUMENS PER FOOT, ASYMMETRIC DIFFUSER  
UPLIGHT 1205 LUMENS PER FOOT, BATWING OPTIC  
Light Source: -  
Ballast/Driver: ELECTRONIC DRIVER

**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 9601.4 lumens  
Efficiency: N/A  
Efficacy: 133.9 lumens/watt  
Spacing Criteria (0/90/45): 1.43 / 1.23 / 1.52  
Luminous Opening: Rectangular (W 4' x L: 0.42' x H: 0')  
CIE Type: General Diffuse


Input Watts (W): 71.7  
Input Voltage (V): 120  
Input Current (Ain): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 25 FT



TEST NUMBER: P333333-840

CATALOG NUMBER: S125DIP-S1270D1205U840-4F0-1E-UDD-A4

### Luminous Intensity Polar Plot





TEST NUMBER: P333333-840

CATALOG NUMBER: S125DIP-S1270D1205U840-4F0-1E-UDD-A4

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	108	108	108	108	100	100	100	100	86	86	86	73	73	73	60	60	60	55
1	99	95	91	88	92	88	85	82	76	73	71	64	63	61	54	53	51	46
2	90	83	77	72	84	77	72	68	67	63	59	57	54	51	48	45	44	39
3	83	73	66	60	76	68	62	57	59	54	50	50	47	44	42	40	37	33
4	76	65	57	51	70	61	54	48	52	47	43	45	41	37	38	35	32	29
5	69	58	50	44	64	54	47	42	47	41	37	40	36	33	34	31	28	25
6	64	52	44	38	59	49	41	36	42	37	32	37	32	29	31	28	25	22
7	59	47	39	33	55	44	37	32	38	33	29	33	29	25	28	25	22	20
8	55	43	35	30	51	40	33	28	35	29	25	30	26	23	26	22	20	18
9	51	39	31	26	48	37	30	25	32	27	23	28	24	20	24	20	18	16
10	48	36	28	24	44	34	27	23	30	24	20	26	21	18	22	19	16	14

**AVERAGE LUMINANCE (cd/sqm):**

	0°	90°	180°	270°
0°	11978	11978	11978	11978
5°	13871	12019	10524	12019
10°	16138	11956	9220	11956
15°	17864	11869	8505	11869
20°	19996	11730	7932	11730
25°	23426	11573	7652	11573
30°	25302	11419	7409	11419
35°	20805	11129	7250	11129
40°	14787	10725	7075	10725
45°	11359	10181	6974	10181
50°	9697	9507	6961	9507
55°	8634	8847	7020	8847
60°	7789	8123	7198	8123
65°	7195	7398	7386	7398
70°	6541	6643	7493	6643
75°	5777	5854	7426	5854
80°	4861	4775	6791	4775
85°	3846	3446	5483	3446



TEST NUMBER: P333333-840

CATALOG NUMBER: S125DIP-S1270D1205U840-4F0-1E-UDD-A4

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	178.6	1.9
10°-20°	531.6	5.5
20°-30°	863.2	9.0
30°-40°	1053.0	11.0
40°-50°	957.9	10.0
50°-60°	763.0	7.9
60°-70°	531.4	5.5
70°-80°	283.4	3.0
80°-90°	74.8	0.8
90°-100°	421.9	4.4
100°-110°	906.9	9.4
110°-120°	851.1	8.9
120°-130°	689.8	7.2
130°-140°	553.5	5.8
140°-150°	417.7	4.4
150°-160°	294.0	3.1
160°-170°	173.3	1.8
170°-180°	56.4	0.6
0°-30°	1573.4	16.4
0°-40°	2626.3	27.4
0°-60°	4347.2	45.3
0°-90°	5236.8	54.5
90°-120°	2179.9	22.7
90°-150°	3840.9	40.0
90°-180°	4365.0	45.5
0°-180°	9601.4	100.0

**CANDELA DISTRIBUTION:**

	0°	90°	180°	270°	360°	Flux
0°	1855	1855	1855	1855	1855	
5°	2140	1854	1623	1854	2140	216
15°	2672	1775	1272	1775	2672	765
25°	3287	1624	1074	1624	3287	1502
35°	2639	1412	920	1412	2639	1615
45°	1244	1115	764	1115	1244	995
55°	767	786	624	786	767	691
65°	471	484	483	484	471	467
75°	232	235	298	235	232	249
85°	52	46	74	46	52	61
90°	27	1	27	1	27	20
95°	276	39	276	39	276	391
105°	1555	133	1555	133	1555	1545
115°	1732	237	1732	237	1732	1692
125°	1365	328	1365	328	1365	1235
135°	1134	385	1134	385	1134	878
145°	894	448	894	448	894	568
155°	750	512	750	512	750	349
165°	657	559	657	559	657	188
175°	590	581	590	581	590	57
180°	582	582	582	582	582	



TEST NUMBER: P333333-840

CATALOG NUMBER: S125DIP-S1270D1205U840-4F0-1E-UDD-A4

**CANDELA DISTRIBUTION (FULL):**

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	1854.7	1854.7	1854.7	1854.7	1854.7	1854.7	1854.7	1854.7	1854.7	1854.7	1854.7
2.5°	1961.8	1959.2	1956.7	1951.7	1955.4	1944.7	1939.6	1930.9	1920.2	1916.4	1912.0
5°	2139.6	2143.5	2147.5	2131.0	2132.5	2121.5	2096.4	2075.9	2059.3	2038.1	2023.2
7.5°	2353.8	2344.5	2343.7	2333.0	2314.6	2299.8	2273.3	2239.6	2207.1	2169.9	2139.2
10°	2460.8	2461.6	2454.6	2442.0	2422.3	2408.1	2373.5	2340.4	2300.3	2253.0	2219.2
12.5°	2541.4	2544.8	2535.8	2518.8	2509.1	2477.4	2450.2	2411.0	2363.2	2325.4	2273.9
15°	2671.8	2663.1	2656.9	2635.5	2619.1	2586.0	2542.7	2501.7	2449.8	2401.8	2353.8
17.5°	2797.4	2804.4	2792.6	2773.2	2721.9	2683.3	2625.2	2569.1	2504.5	2440.0	2382.8
20°	2909.5	2915.9	2897.7	2863.9	2802.5	2763.9	2687.6	2615.1	2540.3	2457.7	2394.7
22.5°	3049.4	3044.3	3019.9	2968.4	2915.2	2843.9	2761.3	2673.0	2579.4	2486.0	2402.3
25°	3287.4	3254.3	3239.3	3175.6	3105.5	3000.8	2887.5	2758.3	2641.9	2518.3	2411.3
27.5°	3419.3	3408.9	3392.2	3347.9	3274.2	3162.2	3028.6	2871.2	2706.9	2550.9	2410.7
30°	3392.8	3394.5	3396.1	3381.8	3334.7	3250.4	3117.4	2948.1	2752.9	2577.4	2415.2
32.5°	3158.7	3187.2	3214.7	3247.1	3260.3	3244.1	3160.8	3008.0	2807.0	2607.6	2412.7
35°	2638.8	2647.4	2736.3	2824.5	2944.2	3037.1	3099.3	3031.5	2862.3	2633.2	2409.6
37.5°	2057.5	2100.0	2161.5	2261.2	2433.9	2588.5	2787.3	2878.8	2824.2	2641.6	2404.2
40°	1753.9	1793.3	1833.4	1935.0	2080.6	2268.0	2493.9	2686.7	2731.6	2615.1	2385.3
42.5°	1519.6	1550.8	1595.4	1671.7	1793.4	1959.3	2175.2	2427.3	2582.3	2538.3	2345.6
45°	1243.7	1263.4	1298.1	1358.8	1446.9	1576.8	1767.3	2042.9	2282.9	2362.4	2251.4
47.5°	1064.6	1064.5	1091.4	1133.3	1196.9	1307.3	1448.1	1664.1	1920.5	2110.2	2101.4
50°	965.1	961.2	982.4	1018.7	1069.0	1142.3	1276.9	1449.3	1695.7	1910.6	1970.3
52.5°	879.5	879.9	893.0	919.8	962.0	1024.5	1125.1	1280.5	1491.0	1711.5	1824.3
55°	766.8	763.6	778.5	796.7	827.4	868.3	940.7	1059.6	1230.4	1447.6	1594.1
57.5°	663.5	672.2	678.1	690.7	716.2	743.6	804.7	891.9	1027.4	1213.9	1368.7
60°	603.0	611.7	616.4	628.9	649.4	673.1	720.3	791.1	905.3	1065.9	1219.4
62.5°	548.9	555.6	557.1	568.6	585.2	608.2	645.4	704.9	795.1	935.5	1085.9
65°	470.8	470.8	473.9	485.7	493.6	514.0	542.4	585.7	658.1	767.5	895.9
67.5°	395.5	399.3	398.5	403.6	410.9	426.9	447.2	482.9	536.5	616.4	719.0
70°	346.4	349.5	348.7	352.6	360.5	370.8	387.3	421.1	459.7	528.3	616.4
72.5°	302.3	303.6	301.5	306.7	311.4	320.4	338.8	356.9	392.9	450.8	523.2
75°	231.5	233.0	234.6	237.7	242.5	247.2	256.6	274.8	298.3	341.6	388.1
77.5°	173.5	170.5	174.3	173.8	176.5	180.2	188.4	198.0	217.4	244.8	280.7
80°	130.7	131.5	131.5	132.3	136.2	138.6	145.6	152.7	167.6	188.1	213.4
82.5°	95.4	97.5	96.2	97.7	100.9	102.6	106.5	112.4	121.1	137.1	155.4
85°	51.9	48.1	49.6	51.2	51.2	51.9	55.1	57.5	62.2	68.5	75.5
87.5°	20.5	21.8	22.2	22.2	22.8	22.3	24.6	24.3	26.1	27.7	29.7
90°	27.0	27.0	25.9	25.9	25.9	23.4	22.3	21.1	20.0	18.8	16.5
92.5°	74.8	76.7	78.4	81.2	96.2	113.6	150.9	207.9	306.3	378.3	384.5
95°	275.8	294.6	303.9	339.1	422.4	521.0	665.3	843.6	1017.3	1039.7	848.4
97.5°	666.5	681.6	715.6	781.2	853.7	990.9	1131.5	1256.5	1287.3	1110.2	757.6
100°	915.2	934.0	977.4	1062.0	1142.9	1265.0	1385.8	1443.3	1352.9	1059.6	675.9
102.5°	1193.2	1207.2	1254.4	1314.4	1401.1	1483.7	1541.7	1506.2	1313.5	970.4	613.9
105°	1554.8	1568.8	1592.4	1631.0	1668.6	1681.5	1629.9	1469.2	1187.5	850.7	553.8
107.5°	1746.8	1756.2	1763.9	1764.1	1745.1	1683.8	1551.3	1336.8	1058.9	768.3	528.5
110°	1810.6	1810.6	1802.4	1780.1	1727.3	1627.5	1462.1	1239.1	985.6	729.8	521.0



TEST NUMBER: P333333-840

CATALOG NUMBER: S125DIP-S1270D1205U840-4F0-1E-UDD-A4

**CANDELA DISTRIBUTION (continued):**

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	1803.1	1794.6	1774.2	1736.0	1658.7	1541.2	1373.8	1162.2	931.2	707.3	521.0
115°	1731.9	1716.7	1683.8	1627.5	1536.0	1408.1	1247.4	1065.5	871.8	683.0	524.5
117.5°	1607.3	1598.0	1565.4	1507.1	1415.6	1298.3	1159.8	1003.0	836.4	671.0	532.3
120°	1526.6	1517.2	1485.5	1429.3	1342.4	1239.1	1110.0	969.3	816.7	665.3	539.8
122.5°	1455.3	1446.8	1415.1	1363.5	1286.1	1189.4	1074.4	943.9	799.8	660.7	546.3
125°	1364.7	1352.9	1327.2	1279.0	1213.4	1128.8	1026.7	907.1	776.8	654.8	557.3
127.5°	1287.3	1282.1	1257.7	1215.2	1155.6	1076.5	981.2	869.5	755.7	652.0	569.8
130°	1245.0	1238.0	1214.5	1175.8	1117.1	1040.9	949.3	846.1	741.6	650.1	577.3
132.5°	1202.7	1194.8	1173.2	1134.5	1075.8	1002.3	919.3	822.5	730.3	650.1	585.7
135°	1133.6	1126.5	1105.4	1066.6	1015.0	948.2	873.0	792.0	717.0	650.1	597.2
137.5°	1059.6	1051.9	1032.4	997.1	951.0	894.1	831.7	766.3	705.0	651.5	607.8
140°	1007.9	1002.1	984.5	954.0	910.6	861.3	807.3	752.1	699.3	652.4	612.5
142.5°	960.1	955.1	938.5	912.7	875.9	833.1	786.7	739.9	694.7	653.4	615.3
145°	894.1	889.5	876.6	856.6	828.4	796.8	760.3	724.0	687.6	652.4	618.4
147.5°	838.3	836.2	828.7	812.7	790.4	766.5	738.5	709.0	680.3	649.3	619.6
150°	807.3	806.2	801.4	787.4	769.7	748.6	726.4	700.5	674.7	646.5	619.6
152.5°	782.9	781.7	777.0	765.8	751.0	734.6	714.2	691.2	668.1	642.8	618.6
155°	749.8	748.6	745.1	736.9	725.2	712.3	695.8	677.0	657.1	636.0	616.0
157.5°	720.2	720.4	717.2	710.3	701.3	691.2	678.4	663.0	646.8	628.9	613.0
160°	700.5	701.8	699.3	693.5	685.3	677.0	665.3	653.6	638.3	624.3	610.2
162.5°	682.7	683.0	682.5	677.5	671.2	663.9	654.1	643.3	630.9	618.6	607.3
165°	657.1	657.1	657.1	654.8	650.1	644.2	637.1	628.9	619.6	610.2	603.1
167.5°	633.7	633.9	634.8	632.7	630.4	626.1	620.8	615.3	608.5	602.0	596.5
170°	619.6	620.8	620.8	619.6	617.2	614.9	611.4	607.8	602.0	597.2	593.8
172.5°	606.4	607.6	609.5	607.3	606.9	605.5	602.9	599.4	595.4	591.7	590.0
175°	590.3	591.4	593.8	592.6	592.6	592.6	590.3	590.3	586.7	585.5	585.5
177.5°	582.0	582.0	584.8	583.9	584.8	584.8	584.8	583.9	583.0	582.0	582.0
180°	582.0	582.0	582.0	582.0	582.0	582.0	582.0	582.0	582.0	582.0	582.0



TEST NUMBER: P333333-840

CATALOG NUMBER: S125DIP-S1270D1205U840-4F0-1E-UDD-A4

**CANDELA DISTRIBUTION (continued):**

	55°	60°	65°	70°	75°	80°	85°	90°	95°	100°	105°
0°	1854.7	1854.7	1854.7	1854.7	1854.7	1854.7	1854.7	1854.7	1854.7	1854.7	1854.7
2.5°	1908.2	1903.8	1898.7	1890.0	1879.3	1873.6	1864.7	1859.1	1847.8	1838.3	1828.3
5°	2005.0	1984.6	1965.7	1941.3	1914.5	1897.1	1876.7	1853.9	1830.3	1805.8	1779.1
7.5°	2105.4	2069.1	2029.7	1987.4	1946.0	1907.8	1871.5	1835.7	1802.4	1762.1	1728.0
10°	2172.7	2127.1	2078.2	2020.7	1964.9	1916.1	1866.4	1823.2	1779.1	1731.8	1690.1
12.5°	2240.1	2179.3	2110.3	2047.2	1980.0	1921.1	1862.7	1807.5	1752.0	1699.7	1651.1
15°	2287.6	2234.1	2170.3	2080.6	2005.0	1924.0	1846.8	1775.1	1708.3	1650.0	1588.6
17.5°	2319.0	2250.0	2181.5	2095.4	1996.4	1905.7	1818.3	1736.3	1660.8	1587.0	1527.8
20°	2324.6	2253.8	2182.1	2097.9	1996.4	1892.5	1805.0	1706.7	1625.6	1549.2	1476.8
22.5°	2322.8	2242.4	2164.5	2077.8	1978.7	1883.0	1777.4	1677.1	1589.0	1514.0	1438.4
25°	2304.9	2219.2	2121.5	2034.2	1936.5	1835.0	1728.0	1624.1	1534.3	1448.4	1373.7
27.5°	2290.2	2178.9	2068.3	1966.4	1872.2	1779.1	1676.6	1570.1	1470.7	1383.7	1313.2
30°	2271.9	2149.9	2025.5	1919.2	1822.4	1731.8	1635.1	1531.2	1427.2	1342.2	1266.7
32.5°	2255.5	2113.3	1982.1	1866.3	1763.8	1675.8	1586.5	1487.6	1385.6	1299.4	1223.8
35°	2223.9	2059.3	1908.9	1778.3	1668.9	1578.3	1503.6	1411.5	1317.8	1234.4	1162.0
37.5°	2183.7	1988.5	1827.1	1690.1	1570.1	1474.8	1405.1	1334.4	1244.6	1164.2	1098.6
40°	2152.2	1938.1	1767.3	1627.2	1502.8	1403.6	1339.1	1272.1	1197.4	1122.6	1053.3
42.5°	2112.5	1892.8	1706.9	1556.0	1432.9	1336.3	1268.5	1211.6	1145.7	1076.0	1011.7
45°	2039.6	1810.6	1609.0	1446.9	1322.5	1227.3	1157.2	1114.7	1065.1	999.0	944.6
47.5°	1932.5	1711.8	1503.4	1336.1	1207.7	1119.4	1053.8	1013.0	978.1	928.9	879.6
50°	1837.3	1638.2	1427.2	1261.1	1132.8	1043.8	983.2	946.2	916.4	878.5	836.8
52.5°	1730.9	1545.6	1352.3	1188.1	1061.0	973.3	913.9	881.4	856.5	829.4	788.3
55°	1561.9	1404.4	1224.9	1069.0	951.7	866.0	814.0	785.7	765.2	744.7	719.5
57.5°	1375.5	1252.4	1093.5	951.0	842.9	764.9	716.4	688.8	672.9	662.4	647.5
60°	1244.6	1139.1	1002.1	872.2	766.8	697.5	650.3	628.9	615.6	606.9	595.9
62.5°	1123.1	1036.4	909.6	791.0	698.7	633.2	591.1	570.4	557.6	553.4	544.3
65°	943.8	877.0	772.2	673.9	595.1	539.3	503.8	484.1	476.3	471.5	472.3
67.5°	767.4	726.6	642.5	558.6	495.7	448.9	420.5	405.5	401.5	395.2	395.1
70°	659.6	628.9	558.2	484.9	429.0	392.8	367.6	351.8	347.9	344.8	344.1
72.5°	564.6	537.7	476.3	417.6	367.3	335.5	314.8	305.3	298.8	296.9	296.8
75°	424.3	409.4	360.5	314.1	279.4	257.4	243.3	234.6	229.8	229.0	229.8
77.5°	301.6	288.6	257.6	224.7	202.8	186.1	174.1	171.2	165.8	165.9	165.1
80°	226.7	218.0	198.3	172.4	154.3	140.2	133.8	128.4	126.7	124.4	126.7
82.5°	164.4	155.1	141.7	125.1	110.2	101.7	95.4	93.7	92.7	91.6	92.1
85°	81.1	81.9	74.0	61.4	55.1	50.4	46.5	46.5	45.6	44.8	45.6
87.5°	30.8	29.0	26.3	23.9	20.3	18.0	16.9	17.3	15.6	15.5	16.6
90°	15.2	12.9	11.7	9.4	7.1	4.6	2.3	1.2	2.3	4.6	7.1
92.5°	267.8	160.3	96.2	62.0	41.8	27.3	17.4	14.3	17.4	27.3	41.8
95°	524.5	266.4	140.8	88.0	62.2	49.3	39.9	38.7	39.9	49.3	62.2
97.5°	418.7	229.5	146.4	108.5	85.2	72.3	65.7	64.3	65.7	72.3	85.2
100°	380.2	227.6	159.6	124.4	102.1	89.2	84.5	82.1	84.5	89.2	102.1
102.5°	364.3	236.1	175.5	141.3	120.9	107.0	103.3	101.9	103.3	107.0	120.9
105°	357.9	253.5	201.9	169.0	150.2	138.5	132.6	132.6	132.6	138.5	150.2
107.5°	368.7	279.2	229.2	199.8	180.3	170.6	165.0	162.6	165.0	170.6	180.3
110°	379.0	298.0	249.9	219.4	201.9	191.3	186.6	184.2	186.6	191.3	201.9





TEST NUMBER: P333333-840

CATALOG NUMBER: S125DIP-S1270D1205U840-4F0-1E-UDD-A4

**CANDELA DISTRIBUTION (continued):**

	55°	60°	65°	70°	75°	80°	85°	90°	95°	100°	105°
112.5°	392.1	315.9	269.6	240.0	222.5	211.9	208.1	205.8	208.1	211.9	222.5
115°	411.8	343.9	300.4	271.0	253.5	242.9	239.3	237.0	239.3	242.9	253.5
117.5°	434.4	372.4	331.3	303.0	283.1	272.5	268.7	265.2	268.7	272.5	283.1
120°	449.4	393.1	352.0	322.7	302.8	292.2	287.5	284.0	287.5	292.2	302.8
122.5°	466.4	412.8	371.7	342.4	320.5	310.0	306.3	303.7	306.3	310.0	320.5
125°	489.3	438.9	400.1	369.6	347.3	336.8	330.9	328.5	330.9	336.8	347.3
127.5°	510.5	463.9	426.7	396.2	372.4	359.1	351.5	348.0	351.5	359.1	372.4
130°	524.5	479.9	443.5	413.0	388.4	373.1	363.8	360.2	363.8	373.1	388.4
132.5°	536.7	494.9	458.6	428.1	402.5	385.4	374.1	369.6	374.1	385.4	402.5
135°	553.8	515.1	478.8	447.1	422.4	403.6	389.6	384.9	389.6	403.6	422.4
137.5°	566.5	529.5	496.3	463.7	439.6	420.8	407.7	404.1	407.7	420.8	439.6
140°	575.0	539.8	505.7	474.0	451.8	433.0	418.9	415.4	418.9	433.0	451.8
142.5°	579.7	546.3	514.2	484.4	463.0	444.2	431.1	428.5	431.1	444.2	463.0
145°	586.7	557.3	526.8	499.9	478.8	462.3	450.6	448.3	450.6	462.3	478.8
147.5°	591.0	564.4	537.7	513.9	495.6	480.4	470.3	468.9	470.3	480.4	495.6
150°	593.8	569.1	543.3	523.3	507.0	491.7	483.4	481.1	483.4	491.7	507.0
152.5°	595.6	573.8	549.9	531.8	516.3	502.9	495.6	494.2	495.6	502.9	516.3
155°	597.2	578.5	558.6	542.1	530.4	518.7	511.6	511.6	511.6	518.7	530.4
157.5°	598.4	582.5	565.3	552.9	542.6	532.5	526.8	527.1	526.8	532.5	542.6
160°	598.4	584.4	569.1	558.6	549.2	541.0	536.2	537.5	536.2	541.0	549.2
162.5°	597.5	586.2	572.9	564.2	556.6	549.4	544.7	545.8	544.7	549.4	556.6
165°	596.1	586.7	577.3	570.3	565.6	559.8	556.2	558.6	556.2	559.8	565.6
167.5°	593.3	586.7	579.0	574.5	571.2	567.9	565.8	567.0	565.8	567.9	571.2
170°	591.4	586.7	580.9	577.3	575.0	572.6	571.5	572.6	571.5	572.6	575.0
172.5°	589.6	585.7	580.9	579.2	577.7	575.4	574.3	576.4	574.3	575.4	577.7
175°	586.7	584.4	580.9	580.9	580.9	579.7	578.5	580.9	578.5	579.7	580.9
177.5°	583.9	583.0	581.1	581.1	582.0	581.1	581.1	583.0	581.1	581.1	582.0
180°	582.0	582.0	582.0	582.0	582.0	582.0	582.0	582.0	582.0	582.0	582.0



TEST NUMBER: P333333-840

CATALOG NUMBER: S125DIP-S1270D1205U840-4F0-1E-UDD-A4

**CANDELA DISTRIBUTION (continued):**

	110°	115°	120°	125°	130°	135°	140°	145°	150°	155°	160°
0°	1854.7	1854.7	1854.7	1854.7	1854.7	1854.7	1854.7	1854.7	1854.7	1854.7	1854.7
2.5°	1822.5	1815.6	1810.0	1797.4	1790.4	1781.0	1773.4	1781.6	1772.8	1776.6	1770.9
5°	1765.7	1743.6	1728.0	1705.1	1685.5	1667.3	1654.0	1651.5	1645.3	1642.1	1632.6
7.5°	1697.4	1669.8	1642.7	1612.9	1587.6	1562.0	1545.6	1532.1	1523.1	1511.3	1503.3
10°	1657.1	1620.1	1588.6	1552.4	1520.9	1493.4	1471.3	1460.3	1450.1	1435.1	1429.6
12.5°	1607.3	1569.0	1530.7	1492.0	1461.7	1431.0	1412.1	1395.4	1388.4	1371.5	1369.8
15°	1547.6	1490.2	1452.4	1413.0	1371.3	1346.2	1330.4	1312.3	1304.4	1292.6	1283.9
17.5°	1476.5	1425.1	1378.0	1337.2	1301.4	1280.2	1260.6	1248.2	1234.7	1227.0	1212.7
20°	1424.8	1376.0	1328.8	1285.6	1258.0	1233.6	1217.8	1206.0	1191.8	1187.9	1173.8
22.5°	1381.4	1327.6	1282.2	1245.9	1215.8	1188.2	1171.2	1163.2	1153.5	1141.3	1138.4
25°	1310.7	1254.9	1216.3	1180.0	1153.3	1128.1	1116.3	1106.0	1096.6	1087.9	1084.8
27.5°	1249.6	1199.7	1153.9	1121.2	1097.8	1074.9	1064.5	1052.1	1045.1	1038.1	1029.7
30°	1206.8	1155.6	1115.5	1084.0	1058.8	1038.3	1027.3	1018.7	1012.4	1006.0	1001.4
32.5°	1162.8	1115.3	1076.4	1045.6	1020.4	1004.9	995.2	989.1	982.1	974.5	968.6
35°	1104.5	1052.5	1014.7	988.0	968.3	956.4	945.4	939.9	932.1	932.1	925.7
37.5°	1038.8	993.9	960.6	936.1	918.5	908.0	896.1	892.2	887.2	883.8	881.7
40°	999.8	958.1	926.6	902.1	883.2	874.5	865.2	858.9	855.7	851.7	850.2
42.5°	959.5	919.6	889.4	866.9	850.5	843.1	834.2	829.9	823.5	818.4	817.5
45°	898.2	859.6	832.1	814.0	799.8	791.1	785.7	776.2	773.1	766.8	766.0
47.5°	840.1	803.1	776.1	761.2	748.8	741.7	733.1	723.6	720.0	716.8	716.5
50°	796.7	762.9	737.6	723.5	711.7	701.5	692.8	686.4	684.1	684.1	685.7
52.5°	752.6	723.8	702.4	685.0	673.9	663.0	655.0	651.2	647.5	651.4	654.2
55°	688.0	658.9	643.2	626.6	615.6	603.0	599.1	597.5	595.1	601.5	604.6
57.5°	619.7	599.3	580.8	564.4	554.5	547.2	541.9	541.0	545.4	548.4	558.6
60°	576.2	552.6	536.1	523.5	511.7	507.0	505.4	503.8	507.0	515.6	529.0
62.5°	528.4	509.2	491.4	481.9	473.2	465.4	465.0	466.1	472.3	482.2	495.6
65°	458.2	441.6	429.8	418.8	411.7	407.0	408.6	411.7	418.8	432.2	447.2
67.5°	386.9	375.5	365.0	356.0	349.2	349.2	350.8	355.5	363.9	379.3	392.9
70°	340.8	328.3	319.6	315.7	310.1	307.0	311.7	319.6	326.7	340.8	352.6
72.5°	294.9	284.2	277.4	274.8	272.4	269.8	271.5	279.9	289.5	303.7	317.4
75°	226.7	222.8	218.0	214.9	212.6	214.1	215.7	223.6	231.5	246.4	262.2
77.5°	165.5	161.4	158.5	157.7	156.5	157.2	161.7	167.5	175.2	186.1	198.0
80°	125.1	123.6	122.0	121.2	121.2	122.0	128.4	132.3	139.4	149.6	159.1
82.5°	91.2	90.2	89.9	89.8	90.4	90.5	94.3	99.5	105.3	113.0	121.2
85°	48.1	46.5	48.8	49.6	48.1	50.4	51.9	55.1	57.5	61.4	65.3
87.5°	17.6	19.4	19.0	20.1	20.3	22.0	21.6	24.3	25.9	27.4	27.2
90°	9.4	11.7	12.9	15.2	16.5	18.8	20.0	21.1	22.3	23.4	25.9
92.5°	62.0	96.2	160.3	267.8	384.5	378.3	306.3	207.9	150.9	113.6	96.2
95°	88.0	140.8	266.4	524.5	848.4	1039.7	1017.3	843.6	665.3	521.0	422.4
97.5°	108.5	146.4	229.5	418.7	757.6	1110.2	1287.3	1256.5	1131.5	990.9	853.7
100°	124.4	159.6	227.6	380.2	675.9	1059.6	1352.9	1443.3	1385.8	1265.0	1142.9
102.5°	141.3	175.5	236.1	364.3	613.9	970.4	1313.5	1506.2	1541.7	1483.7	1401.1
105°	169.0	201.9	253.5	357.9	553.8	850.7	1187.5	1469.2	1629.9	1681.5	1668.6
107.5°	199.8	229.2	279.2	368.7	528.5	768.3	1058.9	1336.8	1551.3	1683.8	1745.1
110°	219.4	249.9	298.0	379.0	521.0	729.8	985.6	1239.1	1462.1	1627.5	1727.3



TEST NUMBER: P333333-840

CATALOG NUMBER: S125DIP-S1270D1205U840-4F0-1E-UDD-A4

**CANDELA DISTRIBUTION (continued):**

	110°	115°	120°	125°	130°	135°	140°	145°	150°	155°	160°
112.5°	240.0	269.6	315.9	392.1	521.0	707.3	931.2	1162.2	1373.8	1541.2	1658.7
115°	271.0	300.4	343.9	411.8	524.5	683.0	871.8	1065.5	1247.4	1408.1	1536.0
117.5°	303.0	331.3	372.4	434.4	532.3	671.0	836.4	1003.0	1159.8	1298.3	1415.6
120°	322.7	352.0	393.1	449.4	539.8	665.3	816.7	969.3	1110.0	1239.1	1342.4
122.5°	342.4	371.7	412.8	466.4	546.3	660.7	799.8	943.9	1074.4	1189.4	1286.1
125°	369.6	400.1	438.9	489.3	557.3	654.8	776.8	907.1	1026.7	1128.8	1213.4
127.5°	396.2	426.7	463.9	510.5	569.8	652.0	755.7	869.5	981.2	1076.5	1155.6
130°	413.0	443.5	479.9	524.5	577.3	650.1	741.6	846.1	949.3	1040.9	1117.1
132.5°	428.1	458.6	494.9	536.7	585.7	650.1	730.3	822.5	919.3	1002.3	1075.8
135°	447.1	478.8	515.1	553.8	597.2	650.1	717.0	792.0	873.0	948.2	1015.0
137.5°	463.7	496.3	529.5	566.5	607.8	651.5	705.0	766.3	831.7	894.1	951.0
140°	474.0	505.7	539.8	575.0	612.5	652.4	699.3	752.1	807.3	861.3	910.6
142.5°	484.4	514.2	546.3	579.7	615.3	653.4	694.7	739.9	786.7	833.1	875.9
145°	499.9	526.8	557.3	586.7	618.4	652.4	687.6	724.0	760.3	796.8	828.4
147.5°	513.9	537.7	564.4	591.0	619.6	649.3	680.3	709.0	738.5	766.5	790.4
150°	523.3	543.3	569.1	593.8	619.6	646.5	674.7	700.5	726.4	748.6	769.7
152.5°	531.8	549.9	573.8	595.6	618.6	642.8	668.1	691.2	714.2	734.6	751.0
155°	542.1	558.6	578.5	597.2	616.0	636.0	657.1	677.0	695.8	712.3	725.2
157.5°	552.9	565.3	582.5	598.4	613.0	628.9	646.8	663.0	678.4	691.2	701.3
160°	558.6	569.1	584.4	598.4	610.2	624.3	638.3	653.6	665.3	677.0	685.3
162.5°	564.2	572.9	586.2	597.5	607.3	618.6	630.9	643.3	654.1	663.9	671.2
165°	570.3	577.3	586.7	596.1	603.1	610.2	619.6	628.9	637.1	644.2	650.1
167.5°	574.5	579.0	586.7	593.3	596.5	602.0	608.5	615.3	620.8	626.1	630.4
170°	577.3	580.9	586.7	591.4	593.8	597.2	602.0	607.8	611.4	614.9	617.2
172.5°	579.2	580.9	585.7	589.6	590.0	591.7	595.4	599.4	602.9	605.5	606.9
175°	580.9	580.9	584.4	586.7	585.5	585.5	586.7	590.3	590.3	592.6	592.6
177.5°	581.1	581.1	583.0	583.9	582.0	582.0	583.0	583.9	584.8	584.8	584.8
180°	582.0	582.0	582.0	582.0	582.0	582.0	582.0	582.0	582.0	582.0	582.0



TEST NUMBER: P333333-840

CATALOG NUMBER: S125DIP-S1270D1205U840-4F0-1E-UDD-A4

**CANDELA DISTRIBUTION (continued):**

	165°	170°	175°	180°	185°	190°	195°	200°	205°	210°	215°
0°	1854.7	1854.7	1854.7	1854.7	1854.7	1854.7	1854.7	1854.7	1854.7	1854.7	1854.7
2.5°	1767.2	1771.5	1767.8	1772.8	1767.8	1771.5	1767.2	1770.9	1776.6	1772.8	1781.6
5°	1628.7	1621.6	1626.4	1623.3	1626.4	1621.6	1628.7	1632.6	1642.1	1645.3	1651.5
7.5°	1500.9	1494.1	1486.4	1482.8	1486.4	1494.1	1500.9	1503.3	1511.3	1523.1	1532.1
10°	1420.9	1412.3	1411.5	1405.9	1411.5	1412.3	1420.9	1429.6	1435.1	1450.1	1460.3
12.5°	1362.3	1354.3	1345.3	1343.0	1345.3	1354.3	1362.3	1369.8	1371.5	1388.4	1395.4
15°	1279.2	1272.9	1267.4	1272.1	1267.4	1272.9	1279.2	1283.9	1292.6	1304.4	1312.3
17.5°	1210.1	1204.9	1204.0	1198.1	1204.0	1204.9	1210.1	1212.7	1227.0	1234.7	1248.2
20°	1166.7	1162.8	1164.3	1154.1	1164.3	1162.8	1166.7	1173.8	1187.9	1191.8	1206.0
22.5°	1132.1	1124.3	1123.4	1121.4	1123.4	1124.3	1132.1	1138.4	1141.3	1153.5	1163.2
25°	1077.7	1073.8	1069.9	1073.8	1069.9	1073.8	1077.7	1084.8	1087.9	1096.6	1106.0
27.5°	1030.3	1025.6	1024.5	1024.9	1024.5	1025.6	1030.3	1029.7	1038.1	1045.1	1052.1
30°	1001.4	993.5	994.2	993.5	994.2	993.5	1001.4	1001.4	1006.0	1012.4	1018.7
32.5°	969.9	964.5	963.4	962.0	963.4	964.5	969.9	968.6	974.5	982.1	989.1
35°	923.4	923.4	919.5	919.5	919.5	923.4	923.4	925.7	932.1	932.1	939.9
37.5°	879.8	879.0	876.7	877.0	876.7	879.0	879.8	881.7	883.8	887.2	892.2
40°	847.1	846.3	843.8	839.2	843.8	846.3	847.1	850.2	851.7	855.7	858.9
42.5°	815.6	812.8	811.7	810.2	811.7	812.8	815.6	817.5	818.4	823.5	829.9
45°	766.0	766.0	764.4	763.6	764.4	766.0	766.0	766.0	766.8	773.1	776.2
47.5°	717.8	719.2	722.2	721.8	722.2	719.2	717.8	716.5	716.8	720.0	723.6
50°	688.8	689.6	692.0	692.8	692.0	689.6	688.8	685.7	684.1	684.1	686.4
52.5°	656.7	661.3	664.3	663.8	664.3	661.3	656.7	654.2	651.4	647.5	651.2
55°	611.7	617.1	622.7	623.5	622.7	617.1	611.7	604.6	601.5	595.1	597.5
57.5°	567.1	574.8	580.7	582.5	580.7	574.8	567.1	558.6	548.4	545.4	541.0
60°	536.8	547.1	554.2	557.3	554.2	547.1	536.8	529.0	515.6	507.0	503.8
62.5°	507.9	519.4	526.4	527.1	526.4	519.4	507.9	495.6	482.2	472.3	466.1
65°	460.5	472.3	478.6	483.3	478.6	472.3	460.5	447.2	432.2	418.8	411.7
67.5°	409.5	421.3	428.3	432.0	428.3	421.3	409.5	392.9	379.3	363.9	355.5
70°	372.3	384.2	393.6	396.8	393.6	384.2	372.3	352.6	340.8	326.7	319.6
72.5°	335.8	346.4	354.0	357.7	354.0	346.4	335.8	317.4	303.7	289.5	279.9
75°	272.4	286.5	293.7	297.6	293.7	286.5	272.4	262.2	246.4	231.5	223.6
77.5°	210.1	223.0	227.2	229.2	227.2	223.0	210.1	198.0	186.1	175.2	167.5
80°	168.4	176.3	181.9	182.6	181.9	176.3	168.4	159.1	149.6	139.4	132.3
82.5°	129.5	136.0	137.7	139.8	137.7	136.0	129.5	121.2	113.0	105.3	99.5
85°	70.9	74.0	74.8	74.0	74.8	74.0	70.9	65.3	61.4	57.5	55.1
87.5°	28.5	27.9	28.1	29.3	28.1	27.9	28.5	27.2	27.4	25.9	24.3
90°	25.9	25.9	27.0	27.0	27.0	25.9	25.9	25.9	23.4	22.3	21.1
92.5°	81.2	78.4	76.7	74.8	76.7	78.4	81.2	96.2	113.6	150.9	207.9
95°	339.1	303.9	294.6	275.8	294.6	303.9	339.1	422.4	521.0	665.3	843.6
97.5°	781.2	715.6	681.6	666.5	681.6	715.6	781.2	853.7	990.9	1131.5	1256.5
100°	1062.0	977.4	934.0	915.2	934.0	977.4	1062.0	1142.9	1265.0	1385.8	1443.3
102.5°	1314.4	1254.4	1207.2	1193.2	1207.2	1254.4	1314.4	1401.1	1483.7	1541.7	1506.2
105°	1631.0	1592.4	1568.8	1554.8	1568.8	1592.4	1631.0	1668.6	1681.5	1629.9	1469.2
107.5°	1764.1	1763.9	1756.2	1746.8	1756.2	1763.9	1764.1	1745.1	1683.8	1551.3	1336.8
110°	1780.1	1802.4	1810.6	1810.6	1810.6	1802.4	1780.1	1727.3	1627.5	1462.1	1239.1



TEST NUMBER: P333333-840

CATALOG NUMBER: S125DIP-S1270D1205U840-4F0-1E-UDD-A4

**CANDELA DISTRIBUTION (continued):**

	165°	170°	175°	180°	185°	190°	195°	200°	205°	210°	215°
112.5°	1736.0	1774.2	1794.6	1803.1	1794.6	1774.2	1736.0	1658.7	1541.2	1373.8	1162.2
115°	1627.5	1683.8	1716.7	1731.9	1716.7	1683.8	1627.5	1536.0	1408.1	1247.4	1065.5
117.5°	1507.1	1565.4	1598.0	1607.3	1598.0	1565.4	1507.1	1415.6	1298.3	1159.8	1003.0
120°	1429.3	1485.5	1517.2	1526.6	1517.2	1485.5	1429.3	1342.4	1239.1	1110.0	969.3
122.5°	1363.5	1415.1	1446.8	1455.3	1446.8	1415.1	1363.5	1286.1	1189.4	1074.4	943.9
125°	1279.0	1327.2	1352.9	1364.7	1352.9	1327.2	1279.0	1213.4	1128.8	1026.7	907.1
127.5°	1215.2	1257.7	1282.1	1287.3	1282.1	1257.7	1215.2	1155.6	1076.5	981.2	869.5
130°	1175.8	1214.5	1238.0	1245.0	1238.0	1214.5	1175.8	1117.1	1040.9	949.3	846.1
132.5°	1134.5	1173.2	1194.8	1202.7	1194.8	1173.2	1134.5	1075.8	1002.3	919.3	822.5
135°	1066.6	1105.4	1126.5	1133.6	1126.5	1105.4	1066.6	1015.0	948.2	873.0	792.0
137.5°	997.1	1032.4	1051.9	1059.6	1051.9	1032.4	997.1	951.0	894.1	831.7	766.3
140°	954.0	984.5	1002.1	1007.9	1002.1	984.5	954.0	910.6	861.3	807.3	752.1
142.5°	912.7	938.5	955.1	960.1	955.1	938.5	912.7	875.9	833.1	786.7	739.9
145°	856.6	876.6	889.5	894.1	889.5	876.6	856.6	828.4	796.8	760.3	724.0
147.5°	812.7	828.7	836.2	838.3	836.2	828.7	812.7	790.4	766.5	738.5	709.0
150°	787.4	801.4	806.2	807.3	806.2	801.4	787.4	769.7	748.6	726.4	700.5
152.5°	765.8	777.0	781.7	782.9	781.7	777.0	765.8	751.0	734.6	714.2	691.2
155°	736.9	745.1	748.6	749.8	748.6	745.1	736.9	725.2	712.3	695.8	677.0
157.5°	710.3	717.2	720.4	720.2	720.4	717.2	710.3	701.3	691.2	678.4	663.0
160°	693.5	699.3	701.8	700.5	701.8	699.3	693.5	685.3	677.0	665.3	653.6
162.5°	677.5	682.5	683.0	682.7	683.0	682.5	677.5	671.2	663.9	654.1	643.3
165°	654.8	657.1	657.1	657.1	657.1	657.1	654.8	650.1	644.2	637.1	628.9
167.5°	632.7	634.8	633.9	633.7	633.9	634.8	632.7	630.4	626.1	620.8	615.3
170°	619.6	620.8	620.8	619.6	620.8	620.8	619.6	617.2	614.9	611.4	607.8
172.5°	607.3	609.5	607.6	606.4	607.6	609.5	607.3	606.9	605.5	602.9	599.4
175°	592.6	593.8	591.4	590.3	591.4	593.8	592.6	592.6	592.6	590.3	590.3
177.5°	583.9	584.8	582.0	582.0	582.0	584.8	583.9	584.8	584.8	584.8	583.9
180°	582.0	582.0	582.0	582.0	582.0	582.0	582.0	582.0	582.0	582.0	582.0



TEST NUMBER: P333333-840

CATALOG NUMBER: S125DIP-S1270D1205U840-4F0-1E-UDD-A4

**CANDELA DISTRIBUTION (continued):**

	220°	225°	230°	235°	240°	245°	250°	255°	260°	265°	270°
0°	1854.7	1854.7	1854.7	1854.7	1854.7	1854.7	1854.7	1854.7	1854.7	1854.7	1854.7
2.5°	1773.4	1781.0	1790.4	1797.4	1810.0	1815.6	1822.5	1828.3	1838.3	1847.8	1859.1
5°	1654.0	1667.3	1685.5	1705.1	1728.0	1743.6	1765.7	1779.1	1805.8	1830.3	1853.9
7.5°	1545.6	1562.0	1587.6	1612.9	1642.7	1669.8	1697.4	1728.0	1762.1	1802.4	1835.7
10°	1471.3	1493.4	1520.9	1552.4	1588.6	1620.1	1657.1	1690.1	1731.8	1779.1	1823.2
12.5°	1412.1	1431.0	1461.7	1492.0	1530.7	1569.0	1607.3	1651.1	1699.7	1752.0	1807.5
15°	1330.4	1346.2	1371.3	1413.0	1452.4	1490.2	1547.6	1588.6	1650.0	1708.3	1775.1
17.5°	1260.6	1280.2	1301.4	1337.2	1378.0	1425.1	1476.5	1527.8	1587.0	1660.8	1736.3
20°	1217.8	1233.6	1258.0	1285.6	1328.8	1376.0	1424.8	1476.8	1549.2	1625.6	1706.7
22.5°	1171.2	1188.2	1215.8	1245.9	1282.2	1327.6	1381.4	1438.4	1514.0	1589.0	1677.1
25°	1116.3	1128.1	1153.3	1180.0	1216.3	1254.9	1310.7	1373.7	1448.4	1534.3	1624.1
27.5°	1064.5	1074.9	1097.8	1121.2	1153.9	1199.7	1249.6	1313.2	1383.7	1470.7	1570.1
30°	1027.3	1038.3	1058.8	1084.0	1115.5	1155.6	1206.8	1266.7	1342.2	1427.2	1531.2
32.5°	995.2	1004.9	1020.4	1045.6	1076.4	1115.3	1162.8	1223.8	1299.4	1385.6	1487.6
35°	945.4	956.4	968.3	988.0	1014.7	1052.5	1104.5	1162.0	1234.4	1317.8	1411.5
37.5°	896.1	908.0	918.5	936.1	960.6	993.9	1038.8	1098.6	1164.2	1244.6	1334.4
40°	865.2	874.5	883.2	902.1	926.6	958.1	999.8	1053.3	1122.6	1197.4	1272.1
42.5°	834.2	843.1	850.5	866.9	889.4	919.6	959.5	1011.7	1076.0	1145.7	1211.6
45°	785.7	791.1	799.8	814.0	832.1	859.6	898.2	944.6	999.0	1065.1	1114.7
47.5°	733.1	741.7	748.8	761.2	776.1	803.1	840.1	879.6	928.9	978.1	1013.0
50°	692.8	701.5	711.7	723.5	737.6	762.9	796.7	836.8	878.5	916.4	946.2
52.5°	655.0	663.0	673.9	685.0	702.4	723.8	752.6	788.3	829.4	856.5	881.4
55°	599.1	603.0	615.6	626.6	643.2	658.9	688.0	719.5	744.7	765.2	785.7
57.5°	541.9	547.2	554.5	564.4	580.8	599.3	619.7	647.5	662.4	672.9	688.8
60°	505.4	507.0	511.7	523.5	536.1	552.6	576.2	595.9	606.9	615.6	628.9
62.5°	465.0	465.4	473.2	481.9	491.4	509.2	528.4	544.3	553.4	557.6	570.4
65°	408.6	407.0	411.7	418.8	429.8	441.6	458.2	472.3	471.5	476.3	484.1
67.5°	350.8	349.2	349.2	356.0	365.0	375.5	386.9	395.1	395.2	401.5	405.5
70°	311.7	307.0	310.1	315.7	319.6	328.3	340.8	344.1	344.8	347.9	351.8
72.5°	271.5	269.8	272.4	274.8	277.4	284.2	294.9	296.8	296.9	298.8	305.3
75°	215.7	214.1	212.6	214.9	218.0	222.8	226.7	229.8	229.0	229.8	234.6
77.5°	161.7	157.2	156.5	157.7	158.5	161.4	165.5	165.1	165.9	165.8	171.2
80°	128.4	122.0	121.2	121.2	122.0	123.6	125.1	126.7	124.4	126.7	128.4
82.5°	94.3	90.5	90.4	89.8	89.9	90.2	91.2	92.1	91.6	92.7	93.7
85°	51.9	50.4	48.1	49.6	48.8	46.5	48.1	45.6	44.8	45.6	46.5
87.5°	21.6	22.0	20.3	20.1	19.0	19.4	17.6	16.6	15.5	15.6	17.3
90°	20.0	18.8	16.5	15.2	12.9	11.7	9.4	7.1	4.6	2.3	1.2
92.5°	306.3	378.3	384.5	267.8	160.3	96.2	62.0	41.8	27.3	17.4	14.3
95°	1017.3	1039.7	848.4	524.5	266.4	140.8	88.0	62.2	49.3	39.9	38.7
97.5°	1287.3	1110.2	757.6	418.7	229.5	146.4	108.5	85.2	72.3	65.7	64.3
100°	1352.9	1059.6	675.9	380.2	227.6	159.6	124.4	102.1	89.2	84.5	82.1
102.5°	1313.5	970.4	613.9	364.3	236.1	175.5	141.3	120.9	107.0	103.3	101.9
105°	1187.5	850.7	553.8	357.9	253.5	201.9	169.0	150.2	138.5	132.6	132.6
107.5°	1058.9	768.3	528.5	368.7	279.2	229.2	199.8	180.3	170.6	165.0	162.6
110°	985.6	729.8	521.0	379.0	298.0	249.9	219.4	201.9	191.3	186.6	184.2



TEST NUMBER: P333333-840

CATALOG NUMBER: S125DIP-S1270D1205U840-4F0-1E-UDD-A4

**CANDELA DISTRIBUTION (continued):**

	220°	225°	230°	235°	240°	245°	250°	255°	260°	265°	270°
112.5°	931.2	707.3	521.0	392.1	315.9	269.6	240.0	222.5	211.9	208.1	205.8
115°	871.8	683.0	524.5	411.8	343.9	300.4	271.0	253.5	242.9	239.3	237.0
117.5°	836.4	671.0	532.3	434.4	372.4	331.3	303.0	283.1	272.5	268.7	265.2
120°	816.7	665.3	539.8	449.4	393.1	352.0	322.7	302.8	292.2	287.5	284.0
122.5°	799.8	660.7	546.3	466.4	412.8	371.7	342.4	320.5	310.0	306.3	303.7
125°	776.8	654.8	557.3	489.3	438.9	400.1	369.6	347.3	336.8	330.9	328.5
127.5°	755.7	652.0	569.8	510.5	463.9	426.7	396.2	372.4	359.1	351.5	348.0
130°	741.6	650.1	577.3	524.5	479.9	443.5	413.0	388.4	373.1	363.8	360.2
132.5°	730.3	650.1	585.7	536.7	494.9	458.6	428.1	402.5	385.4	374.1	369.6
135°	717.0	650.1	597.2	553.8	515.1	478.8	447.1	422.4	403.6	389.6	384.9
137.5°	705.0	651.5	607.8	566.5	529.5	496.3	463.7	439.6	420.8	407.7	404.1
140°	699.3	652.4	612.5	575.0	539.8	505.7	474.0	451.8	433.0	418.9	415.4
142.5°	694.7	653.4	615.3	579.7	546.3	514.2	484.4	463.0	444.2	431.1	428.5
145°	687.6	652.4	618.4	586.7	557.3	526.8	499.9	478.8	462.3	450.6	448.3
147.5°	680.3	649.3	619.6	591.0	564.4	537.7	513.9	495.6	480.4	470.3	468.9
150°	674.7	646.5	619.6	593.8	569.1	543.3	523.3	507.0	491.7	483.4	481.1
152.5°	668.1	642.8	618.6	595.6	573.8	549.9	531.8	516.3	502.9	495.6	494.2
155°	657.1	636.0	616.0	597.2	578.5	558.6	542.1	530.4	518.7	511.6	511.6
157.5°	646.8	628.9	613.0	598.4	582.5	565.3	552.9	542.6	532.5	526.8	527.1
160°	638.3	624.3	610.2	598.4	584.4	569.1	558.6	549.2	541.0	536.2	537.5
162.5°	630.9	618.6	607.3	597.5	586.2	572.9	564.2	556.6	549.4	544.7	545.8
165°	619.6	610.2	603.1	596.1	586.7	577.3	570.3	565.6	559.8	556.2	558.6
167.5°	608.5	602.0	596.5	593.3	586.7	579.0	574.5	571.2	567.9	565.8	567.0
170°	602.0	597.2	593.8	591.4	586.7	580.9	577.3	575.0	572.6	571.5	572.6
172.5°	595.4	591.7	590.0	589.6	585.7	580.9	579.2	577.7	575.4	574.3	576.4
175°	586.7	585.5	585.5	586.7	584.4	580.9	580.9	580.9	579.7	578.5	580.9
177.5°	583.0	582.0	582.0	583.9	583.0	581.1	581.1	582.0	581.1	581.1	583.0
180°	582.0	582.0	582.0	582.0	582.0	582.0	582.0	582.0	582.0	582.0	582.0



TEST NUMBER: P333333-840

CATALOG NUMBER: S125DIP-S1270D1205U840-4F0-1E-UDD-A4

**CANDELA DISTRIBUTION (continued):**

	275°	280°	285°	290°	295°	300°	305°	310°	315°	320°	325°
0°	1854.7	1854.7	1854.7	1854.7	1854.7	1854.7	1854.7	1854.7	1854.7	1854.7	1854.7
2.5°	1864.7	1873.6	1879.3	1890.0	1898.7	1903.8	1908.2	1912.0	1916.4	1920.2	1930.9
5°	1876.7	1897.1	1914.5	1941.3	1965.7	1984.6	2005.0	2023.2	2038.1	2059.3	2075.9
7.5°	1871.5	1907.8	1946.0	1987.4	2029.7	2069.1	2105.4	2139.2	2169.9	2207.1	2239.6
10°	1866.4	1916.1	1964.9	2020.7	2078.2	2127.1	2172.7	2219.2	2253.0	2300.3	2340.4
12.5°	1862.7	1921.1	1980.0	2047.2	2110.3	2179.3	2240.1	2273.9	2325.4	2363.2	2411.0
15°	1846.8	1924.0	2005.0	2080.6	2170.3	2234.1	2287.6	2353.8	2401.8	2449.8	2501.7
17.5°	1818.3	1905.7	1996.4	2095.4	2181.5	2250.0	2319.0	2382.8	2440.0	2504.5	2569.1
20°	1805.0	1892.5	1996.4	2097.9	2182.1	2253.8	2324.6	2394.7	2457.7	2540.3	2615.1
22.5°	1777.4	1883.0	1978.7	2077.8	2164.5	2242.4	2322.8	2402.3	2486.0	2579.4	2673.0
25°	1728.0	1835.0	1936.5	2034.2	2121.5	2219.2	2304.9	2411.3	2518.3	2641.9	2758.3
27.5°	1676.6	1779.1	1872.2	1966.4	2068.3	2178.9	2290.2	2410.7	2550.9	2706.9	2871.2
30°	1635.1	1731.8	1822.4	1919.2	2025.5	2149.9	2271.9	2415.2	2577.4	2752.9	2948.1
32.5°	1586.5	1675.8	1763.8	1866.3	1982.1	2113.3	2255.5	2412.7	2607.6	2807.0	3008.0
35°	1503.6	1578.3	1668.9	1778.3	1908.9	2059.3	2223.9	2409.6	2633.2	2862.3	3031.5
37.5°	1405.1	1474.8	1570.1	1690.1	1827.1	1988.5	2183.7	2404.2	2641.6	2824.2	2878.8
40°	1339.1	1403.6	1502.8	1627.2	1767.3	1938.1	2152.2	2385.3	2615.1	2731.6	2686.7
42.5°	1268.5	1336.3	1432.9	1556.0	1706.9	1892.8	2112.5	2345.6	2538.3	2582.3	2427.3
45°	1157.2	1227.3	1322.5	1446.9	1609.0	1810.6	2039.6	2251.4	2362.4	2282.9	2042.9
47.5°	1053.8	1119.4	1207.7	1336.1	1503.4	1711.8	1932.5	2101.4	2110.2	1920.5	1664.1
50°	983.2	1043.8	1132.8	1261.1	1427.2	1638.2	1837.3	1970.3	1910.6	1695.7	1449.3
52.5°	913.9	973.3	1061.0	1188.1	1352.3	1545.6	1730.9	1824.3	1711.5	1491.0	1280.5
55°	814.0	866.0	951.7	1069.0	1224.9	1404.4	1561.9	1594.1	1447.6	1230.4	1059.6
57.5°	716.4	764.9	842.9	951.0	1093.5	1252.4	1375.5	1368.7	1213.9	1027.4	891.9
60°	650.3	697.5	766.8	872.2	1002.1	1139.1	1244.6	1219.4	1065.9	905.3	791.1
62.5°	591.1	633.2	698.7	791.0	909.6	1036.4	1123.1	1085.9	935.5	795.1	704.9
65°	503.8	539.3	595.1	673.9	772.2	877.0	943.8	895.9	767.5	658.1	585.7
67.5°	420.5	448.9	495.7	558.6	642.5	726.6	767.4	719.0	616.4	536.5	482.9
70°	367.6	392.8	429.0	484.9	558.2	628.9	659.6	616.4	528.3	459.7	421.1
72.5°	314.8	335.5	367.3	417.6	476.3	537.7	564.6	523.2	450.8	392.9	356.9
75°	243.3	257.4	279.4	314.1	360.5	409.4	424.3	388.1	341.6	298.3	274.8
77.5°	174.1	186.1	202.8	224.7	257.6	288.6	301.6	280.7	244.8	217.4	198.0
80°	133.8	140.2	154.3	172.4	198.3	218.0	226.7	213.4	188.1	167.6	152.7
82.5°	95.4	101.7	110.2	125.1	141.7	155.1	164.4	155.4	137.1	121.1	112.4
85°	46.5	50.4	55.1	61.4	74.0	81.9	81.1	75.5	68.5	62.2	57.5
87.5°	16.9	18.0	20.3	23.9	26.3	29.0	30.8	29.7	27.7	26.1	24.3
90°	2.3	4.6	7.1	9.4	11.7	12.9	15.2	16.5	18.8	20.0	21.1
92.5°	17.4	27.3	41.8	62.0	96.2	160.3	267.8	384.5	378.3	306.3	207.9
95°	39.9	49.3	62.2	88.0	140.8	266.4	524.5	848.4	1039.7	1017.3	843.6
97.5°	65.7	72.3	85.2	108.5	146.4	229.5	418.7	757.6	1110.2	1287.3	1256.5
100°	84.5	89.2	102.1	124.4	159.6	227.6	380.2	675.9	1059.6	1352.9	1443.3
102.5°	103.3	107.0	120.9	141.3	175.5	236.1	364.3	613.9	970.4	1313.5	1506.2
105°	132.6	138.5	150.2	169.0	201.9	253.5	357.9	553.8	850.7	1187.5	1469.2
107.5°	165.0	170.6	180.3	199.8	229.2	279.2	368.7	528.5	768.3	1058.9	1336.8
110°	186.6	191.3	201.9	219.4	249.9	298.0	379.0	521.0	729.8	985.6	1239.1





TEST NUMBER: P333333-840

CATALOG NUMBER: S125DIP-S1270D1205U840-4F0-1E-UDD-A4

**CANDELA DISTRIBUTION (continued):**

	275°	280°	285°	290°	295°	300°	305°	310°	315°	320°	325°
112.5°	208.1	211.9	222.5	240.0	269.6	315.9	392.1	521.0	707.3	931.2	1162.2
115°	239.3	242.9	253.5	271.0	300.4	343.9	411.8	524.5	683.0	871.8	1065.5
117.5°	268.7	272.5	283.1	303.0	331.3	372.4	434.4	532.3	671.0	836.4	1003.0
120°	287.5	292.2	302.8	322.7	352.0	393.1	449.4	539.8	665.3	816.7	969.3
122.5°	306.3	310.0	320.5	342.4	371.7	412.8	466.4	546.3	660.7	799.8	943.9
125°	330.9	336.8	347.3	369.6	400.1	438.9	489.3	557.3	654.8	776.8	907.1
127.5°	351.5	359.1	372.4	396.2	426.7	463.9	510.5	569.8	652.0	755.7	869.5
130°	363.8	373.1	388.4	413.0	443.5	479.9	524.5	577.3	650.1	741.6	846.1
132.5°	374.1	385.4	402.5	428.1	458.6	494.9	536.7	585.7	650.1	730.3	822.5
135°	389.6	403.6	422.4	447.1	478.8	515.1	553.8	597.2	650.1	717.0	792.0
137.5°	407.7	420.8	439.6	463.7	496.3	529.5	566.5	607.8	651.5	705.0	766.3
140°	418.9	433.0	451.8	474.0	505.7	539.8	575.0	612.5	652.4	699.3	752.1
142.5°	431.1	444.2	463.0	484.4	514.2	546.3	579.7	615.3	653.4	694.7	739.9
145°	450.6	462.3	478.8	499.9	526.8	557.3	586.7	618.4	652.4	687.6	724.0
147.5°	470.3	480.4	495.6	513.9	537.7	564.4	591.0	619.6	649.3	680.3	709.0
150°	483.4	491.7	507.0	523.3	543.3	569.1	593.8	619.6	646.5	674.7	700.5
152.5°	495.6	502.9	516.3	531.8	549.9	573.8	595.6	618.6	642.8	668.1	691.2
155°	511.6	518.7	530.4	542.1	558.6	578.5	597.2	616.0	636.0	657.1	677.0
157.5°	526.8	532.5	542.6	552.9	565.3	582.5	598.4	613.0	628.9	646.8	663.0
160°	536.2	541.0	549.2	558.6	569.1	584.4	598.4	610.2	624.3	638.3	653.6
162.5°	544.7	549.4	556.6	564.2	572.9	586.2	597.5	607.3	618.6	630.9	643.3
165°	556.2	559.8	565.6	570.3	577.3	586.7	596.1	603.1	610.2	619.6	628.9
167.5°	565.8	567.9	571.2	574.5	579.0	586.7	593.3	596.5	602.0	608.5	615.3
170°	571.5	572.6	575.0	577.3	580.9	586.7	591.4	593.8	597.2	602.0	607.8
172.5°	574.3	575.4	577.7	579.2	580.9	585.7	589.6	590.0	591.7	595.4	599.4
175°	578.5	579.7	580.9	580.9	580.9	584.4	586.7	585.5	585.5	586.7	590.3
177.5°	581.1	581.1	582.0	581.1	581.1	583.0	583.9	582.0	582.0	583.0	583.9
180°	582.0	582.0	582.0	582.0	582.0	582.0	582.0	582.0	582.0	582.0	582.0



TEST NUMBER: P333333-840

CATALOG NUMBER: S125DIP-S1270D1205U840-4F0-1E-UDD-A4

**CANDELA DISTRIBUTION (continued):**

	330°	335°	340°	345°	350°	355°	360°
0°	1854.7	1854.7	1854.7	1854.7	1854.7	1854.7	1854.7
2.5°	1939.6	1944.7	1955.4	1951.7	1956.7	1959.2	1961.8
5°	2096.4	2121.5	2132.5	2131.0	2147.5	2143.5	2139.6
7.5°	2273.3	2299.8	2314.6	2333.0	2343.7	2344.5	2353.8
10°	2373.5	2408.1	2422.3	2442.0	2454.6	2461.6	2460.8
12.5°	2450.2	2477.4	2509.1	2518.8	2535.8	2544.8	2541.4
15°	2542.7	2586.0	2619.1	2635.5	2656.9	2663.1	2671.8
17.5°	2625.2	2683.3	2721.9	2773.2	2792.6	2804.4	2797.4
20°	2687.6	2763.9	2802.5	2863.9	2897.7	2915.9	2909.5
22.5°	2761.3	2843.9	2915.2	2968.4	3019.9	3044.3	3049.4
25°	2887.5	3000.8	3105.5	3175.6	3239.3	3254.3	3287.4
27.5°	3028.6	3162.2	3274.2	3347.9	3392.2	3408.9	3419.3
30°	3117.4	3250.4	3334.7	3381.8	3396.1	3394.5	3392.8
32.5°	3160.8	3244.1	3260.3	3247.1	3214.7	3187.2	3158.7
35°	3099.3	3037.1	2944.2	2824.5	2736.3	2647.4	2638.8
37.5°	2787.3	2588.5	2433.9	2261.2	2161.5	2100.0	2057.5
40°	2493.9	2268.0	2080.6	1935.0	1833.4	1793.3	1753.9
42.5°	2175.2	1959.3	1793.4	1671.7	1595.4	1550.8	1519.6
45°	1767.3	1576.8	1446.9	1358.8	1298.1	1263.4	1243.7
47.5°	1448.1	1307.3	1196.9	1133.3	1091.4	1064.5	1064.6
50°	1276.9	1142.3	1069.0	1018.7	982.4	961.2	965.1
52.5°	1125.1	1024.5	962.0	919.8	893.0	879.9	879.5
55°	940.7	868.3	827.4	796.7	778.5	763.6	766.8
57.5°	804.7	743.6	716.2	690.7	678.1	672.2	663.5
60°	720.3	673.1	649.4	628.9	616.4	611.7	603.0
62.5°	645.4	608.2	585.2	568.6	557.1	555.6	548.9
65°	542.4	514.0	493.6	485.7	473.9	470.8	470.8
67.5°	447.2	426.9	410.9	403.6	398.5	399.3	395.5
70°	387.3	370.8	360.5	352.6	348.7	349.5	346.4
72.5°	338.8	320.4	311.4	306.7	301.5	303.6	302.3
75°	256.6	247.2	242.5	237.7	234.6	233.0	231.5
77.5°	188.4	180.2	176.5	173.8	174.3	170.5	173.5
80°	145.6	138.6	136.2	132.3	131.5	131.5	130.7
82.5°	106.5	102.6	100.9	97.7	96.2	97.5	95.4
85°	55.1	51.9	51.2	51.2	49.6	48.1	51.9
87.5°	24.6	22.3	22.8	22.2	22.2	21.8	20.5
90°	22.3	23.4	25.9	25.9	25.9	27.0	27.0
92.5°	150.9	113.6	96.2	81.2	78.4	76.7	74.8
95°	665.3	521.0	422.4	339.1	303.9	294.6	275.8
97.5°	1131.5	990.9	853.7	781.2	715.6	681.6	666.5
100°	1385.8	1265.0	1142.9	1062.0	977.4	934.0	915.2
102.5°	1541.7	1483.7	1401.1	1314.4	1254.4	1207.2	1193.2
105°	1629.9	1681.5	1668.6	1631.0	1592.4	1568.8	1554.8
107.5°	1551.3	1683.8	1745.1	1764.1	1763.9	1756.2	1746.8
110°	1462.1	1627.5	1727.3	1780.1	1802.4	1810.6	1810.6



TEST NUMBER: P333333-840

CATALOG NUMBER: S125DIP-S1270D1205U840-4F0-1E-UDD-A4

**CANDELA DISTRIBUTION (continued):**

	330°	335°	340°	345°	350°	355°	360°
112.5°	1373.8	1541.2	1658.7	1736.0	1774.2	1794.6	1803.1
115°	1247.4	1408.1	1536.0	1627.5	1683.8	1716.7	1731.9
117.5°	1159.8	1298.3	1415.6	1507.1	1565.4	1598.0	1607.3
120°	1110.0	1239.1	1342.4	1429.3	1485.5	1517.2	1526.6
122.5°	1074.4	1189.4	1286.1	1363.5	1415.1	1446.8	1455.3
125°	1026.7	1128.8	1213.4	1279.0	1327.2	1352.9	1364.7
127.5°	981.2	1076.5	1155.6	1215.2	1257.7	1282.1	1287.3
130°	949.3	1040.9	1117.1	1175.8	1214.5	1238.0	1245.0
132.5°	919.3	1002.3	1075.8	1134.5	1173.2	1194.8	1202.7
135°	873.0	948.2	1015.0	1066.6	1105.4	1126.5	1133.6
137.5°	831.7	894.1	951.0	997.1	1032.4	1051.9	1059.6
140°	807.3	861.3	910.6	954.0	984.5	1002.1	1007.9
142.5°	786.7	833.1	875.9	912.7	938.5	955.1	960.1
145°	760.3	796.8	828.4	856.6	876.6	889.5	894.1
147.5°	738.5	766.5	790.4	812.7	828.7	836.2	838.3
150°	726.4	748.6	769.7	787.4	801.4	806.2	807.3
152.5°	714.2	734.6	751.0	765.8	777.0	781.7	782.9
155°	695.8	712.3	725.2	736.9	745.1	748.6	749.8
157.5°	678.4	691.2	701.3	710.3	717.2	720.4	720.2
160°	665.3	677.0	685.3	693.5	699.3	701.8	700.5
162.5°	654.1	663.9	671.2	677.5	682.5	683.0	682.7
165°	637.1	644.2	650.1	654.8	657.1	657.1	657.1
167.5°	620.8	626.1	630.4	632.7	634.8	633.9	633.7
170°	611.4	614.9	617.2	619.6	620.8	620.8	619.6
172.5°	602.9	605.5	606.9	607.3	609.5	607.6	606.4
175°	590.3	592.6	592.6	592.6	593.8	591.4	590.3
177.5°	584.8	584.8	584.8	583.9	584.8	582.0	582.0
180°	582.0	582.0	582.0	582.0	582.0	582.0	582.0

(END OF REPORT)