

Scaled data based on original data using  
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State  
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P333337-840

Luminaire Tested: **S125DIP-S1270D1205U840-4F0-1E-UDD-F**

Issue Date: 3/3/2020

**Test Information**

Test Method: LM-79-08  
Report Number: P333337-840  
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-7,  
Test Lab: INNOVATION CENTER  
Issue Date: 3/3/2020  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: NEO-RAY  
Catalog Number: S125DIP-S1270D1205U840-4F0-1E-UDD-F  
Description: DEFINE 5 DIRECT-INDIRECT PENDANT LED LUMINAIRE  
DOWNLIGHT 1270 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER  
UPLIGHT 1205 LUMENS PER FOOT, NO LENS  
Light Source: -  
Ballast/Driver: ELECTRONIC DRIVER

**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 10044.0 lumens  
Efficiency: N/A  
Efficacy: 140.1 lumens/watt  
Spacing Criteria (0/90/45): 1.21 / 1.18 / 1.31  
Luminous Opening: Rectangular (W 0.42' x L: 4' x H: 0')  
CIE Type: General Diffuse


Input Watts (W): 71.7  
Input Voltage (V): 120  
Input Current (Ain): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 25 FT



TEST NUMBER: P333337-840

CATALOG NUMBER: S125DIP-S1270D1205U840-4F0-1E-UDD-F

### Luminous Intensity Polar Plot





TEST NUMBER: P333337-840

CATALOG NUMBER: S125DIP-S1270D1205U840-4F0-1E-UDD-F

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	108	108	108	108	99	99	99	99	84	84	84	70	70	70	58	58	58	52
1	98	94	90	86	91	87	83	80	74	71	69	62	60	58	51	50	48	43
2	89	82	76	70	82	76	70	66	65	61	57	54	51	49	45	43	41	36
3	81	72	64	59	75	67	60	55	57	52	48	48	44	41	40	37	35	31
4	74	64	56	50	69	59	52	47	51	45	41	43	39	35	35	32	30	26
5	68	57	48	42	63	53	45	40	45	40	35	38	34	31	32	29	26	23
6	63	51	43	37	58	47	40	35	41	35	31	35	30	27	29	26	23	20
7	58	46	38	32	54	43	36	31	37	31	27	31	27	24	26	23	20	18
8	54	42	34	29	50	39	32	27	34	28	24	29	24	21	24	21	18	16
9	50	38	31	25	46	36	29	24	31	25	22	27	22	19	22	19	16	14
10	47	35	28	23	43	33	26	22	28	23	19	24	20	17	21	17	15	13

**AVERAGE LUMINANCE (cd/sqm):**

	0°	45°	90°
0°	12853	12853	12853
5°	12882	12759	12841
10°	12804	12669	12742
15°	12664	12517	12570
20°	12466	12304	12325
25°	12252	12050	12039
30°	11989	11777	11718
35°	11706	11483	11321
40°	11415	11163	11005
45°	11102	10872	10656
50°	10758	10520	10203
55°	10424	10124	9839
60°	10026	9722	9376
65°	9553	9239	8926
70°	9098	8682	8384
75°	8289	8015	7738
80°	7375	7260	7089
85°	6417	6536	6180



TEST NUMBER: P333337-840

CATALOG NUMBER: S125DIP-S1270D1205U840-4F0-1E-UDD-F

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	187.6	1.9
10°-20°	530.1	5.3
20°-30°	782.7	7.8
30°-40°	913.3	9.1
40°-50°	917.2	9.1
50°-60°	805.1	8.0
60°-70°	599.9	6.0
70°-80°	343.0	3.4
80°-90°	103.1	1.0
90°-100°	57.5	0.6
100°-110°	354.6	3.5
110°-120°	643.1	6.4
120°-130°	825.3	8.2
130°-140°	887.7	8.8
140°-150°	833.2	8.3
150°-160°	674.0	6.7
160°-170°	435.9	4.3
170°-180°	150.4	1.5
0°-30°	1500.4	14.9
0°-40°	2413.6	24.0
0°-60°	4136.0	41.2
0°-90°	5182.1	51.6
90°-120°	1055.2	10.5
90°-150°	3601.6	35.9
90°-180°	4862.0	48.4
0°-180°	10044.0	100.0

**CANDELA DISTRIBUTION:**

	0°	22.5°	45°	67.5°	90°	Flux
0°	1990	1990	1990	1990	1990	
5°	1987	1983	1968	1981	1981	188
15°	1894	1889	1872	1880	1880	534
25°	1719	1711	1691	1694	1689	791
35°	1485	1478	1456	1448	1436	928
45°	1216	1208	1190	1172	1167	936
55°	926	920	899	885	874	826
65°	625	621	605	591	584	620
75°	332	329	321	316	310	354
85°	87	88	88	86	83	97
90°	1	10	19	24	28	7
95°	67	61	19	24	25	85
105°	345	349	350	350	349	366
115°	648	654	655	650	643	642
125°	921	929	930	925	921	823
135°	1149	1156	1154	1151	1144	885
145°	1332	1334	1334	1335	1329	833
155°	1467	1461	1462	1465	1456	676
165°	1548	1542	1542	1548	1540	437
175°	1583	1577	1577	1586	1576	151
180°	1583	1583	1583	1583	1583	



TEST NUMBER: P333337-840

CATALOG NUMBER: S125DIP-S1270D1205U840-4F0-1E-UDD-F

**CANDELA DISTRIBUTION (FULL):**

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	1990.1	1990.1	1990.1	1990.1	1990.1	1990.1	1990.1	1990.1	1990.1	1990.1	1990.1
2.5°	1995.2	1994.4	1993.6	1992.7	1991.9	1990.0	1987.2	1984.4	1981.7	1978.8	1981.7
5°	1987.0	1986.3	1985.6	1984.9	1984.2	1982.2	1978.6	1975.1	1971.7	1968.1	1971.3
7.5°	1968.7	1968.0	1967.3	1966.6	1965.9	1963.7	1959.8	1956.0	1952.2	1948.3	1951.4
10°	1952.4	1951.7	1951.0	1950.3	1949.5	1947.3	1943.5	1939.6	1935.7	1931.9	1934.7
12.5°	1932.2	1931.0	1929.8	1928.4	1927.2	1924.8	1921.2	1917.6	1914.1	1910.5	1912.8
15°	1894.1	1893.1	1892.0	1891.0	1890.0	1887.4	1883.6	1879.8	1875.9	1872.1	1873.8
17.5°	1850.4	1848.9	1847.2	1845.7	1844.2	1841.4	1837.4	1833.4	1829.5	1825.4	1827.7
20°	1813.8	1813.1	1812.4	1811.7	1811.0	1808.4	1803.8	1799.3	1794.7	1790.2	1792.6
22.5°	1777.3	1776.0	1774.7	1773.5	1772.2	1769.5	1765.2	1761.0	1756.7	1752.4	1754.0
25°	1719.4	1717.6	1715.9	1714.1	1712.3	1709.2	1704.7	1700.1	1695.6	1691.0	1691.7
27.5°	1651.6	1650.6	1649.5	1648.5	1647.5	1644.6	1639.9	1635.2	1630.5	1625.8	1626.0
30°	1607.6	1606.5	1605.5	1604.4	1603.4	1600.2	1595.0	1589.7	1584.5	1579.2	1578.5
32.5°	1559.7	1558.1	1556.5	1554.9	1553.3	1550.1	1545.4	1540.8	1536.0	1531.4	1530.1
35°	1484.7	1483.4	1482.0	1480.6	1479.1	1476.0	1471.1	1466.2	1461.3	1456.4	1454.7
37.5°	1406.9	1405.2	1403.5	1401.7	1400.0	1396.7	1392.2	1387.6	1382.9	1378.4	1375.7
40°	1354.0	1352.3	1350.6	1348.8	1347.1	1343.7	1338.9	1333.9	1329.1	1324.1	1321.0
42.5°	1297.4	1296.0	1294.4	1292.9	1291.5	1288.3	1283.4	1278.5	1273.6	1268.7	1265.9
45°	1215.5	1214.2	1212.7	1211.3	1209.9	1207.1	1203.0	1198.7	1194.6	1190.3	1186.1
47.5°	1127.3	1127.4	1127.5	1127.5	1127.6	1125.1	1120.1	1115.1	1110.0	1105.0	1100.8
50°	1070.7	1069.6	1068.5	1067.5	1066.4	1063.8	1059.7	1055.4	1051.3	1047.0	1042.5
52.5°	1012.7	1012.0	1011.2	1010.4	1009.7	1007.0	1002.5	998.0	993.6	989.1	985.1
55°	925.8	924.7	923.7	922.6	921.6	918.7	913.7	908.9	903.9	899.1	895.9
57.5°	834.1	833.6	833.0	832.5	831.9	829.6	825.5	821.3	817.2	813.0	809.0
60°	776.2	774.9	773.5	772.0	770.6	768.0	764.2	760.3	756.5	752.7	749.1
62.5°	715.8	714.7	713.6	712.4	711.2	709.1	705.8	702.5	699.2	695.9	692.2
65°	625.1	624.4	623.7	623.0	622.3	620.0	616.1	612.3	608.4	604.6	601.5
67.5°	537.2	535.7	534.3	532.8	531.4	529.2	526.3	523.4	520.6	517.7	515.0
70°	481.8	480.1	478.3	476.6	474.8	472.3	469.2	466.1	462.9	459.8	457.7
72.5°	421.3	420.1	419.0	417.8	416.6	415.0	412.9	410.9	408.9	406.9	404.5
75°	332.2	331.5	330.8	330.1	329.4	328.2	326.5	324.7	323.0	321.2	320.1
77.5°	250.0	249.7	249.4	249.2	248.9	248.3	247.3	246.3	245.3	244.4	243.8
80°	198.3	198.3	198.3	198.3	198.3	198.0	197.3	196.6	195.9	195.2	194.9
82.5°	153.0	152.5	151.9	151.4	150.8	150.5	150.3	150.2	150.1	149.9	149.3
85°	86.6	86.9	87.3	87.7	88.0	88.2	88.2	88.2	88.2	88.2	87.9
87.5°	34.2	34.6	35.0	35.4	36.0	36.2	36.3	36.4	36.5	36.5	36.8
90°	1.2	3.2	5.4	7.5	9.5	11.5	13.3	15.1	17.0	18.8	20.1
92.5°	18.1	16.7	15.1	13.7	12.2	12.3	13.9	15.6	17.2	18.8	20.1
95°	66.9	66.1	65.3	64.5	63.7	58.5	48.5	38.6	28.7	18.8	20.1
97.5°	139.7	141.1	142.5	143.9	145.3	136.2	116.5	96.9	77.4	57.8	50.4
100°	196.0	196.8	197.5	198.3	199.1	200.1	201.1	202.2	203.2	204.2	165.3
102.5°	253.3	254.3	255.3	256.2	257.2	258.0	258.6	259.3	259.9	260.5	253.2
105°	345.1	346.1	347.1	348.2	349.2	349.7	349.7	349.7	349.7	349.7	349.7
107.5°	440.4	440.4	440.4	440.4	440.4	440.6	441.1	441.6	442.2	442.7	442.7
110°	502.3	502.3	502.3	502.3	502.3	502.6	503.1	503.6	504.1	504.6	503.9



TEST NUMBER: P333337-840

CATALOG NUMBER: S125DIP-S1270D1205U840-4F0-1E-UDD-F

**CANDELA DISTRIBUTION (continued):**

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	560.6	561.2	561.8	562.4	563.0	563.5	563.8	564.1	564.4	564.7	563.8
115°	647.8	649.1	650.5	651.8	653.1	653.9	654.1	654.4	654.6	654.9	653.9
117.5°	738.2	738.2	738.1	738.1	738.0	738.5	739.5	740.4	741.4	742.5	741.1
120°	794.6	794.3	794.1	793.8	793.6	793.8	794.6	795.4	796.1	796.9	796.4
122.5°	844.3	845.4	846.3	847.3	848.3	849.0	849.3	849.7	850.1	850.4	849.9
125°	921.3	923.1	924.9	926.8	928.6	929.5	929.5	929.5	929.5	929.5	928.5
127.5°	994.8	996.1	997.3	998.7	1000.0	1000.6	1000.4	1000.3	1000.1	1000.0	999.4
130°	1039.9	1041.2	1042.5	1043.8	1045.1	1045.8	1046.1	1046.4	1046.6	1046.9	1046.1
132.5°	1084.9	1086.4	1087.9	1089.4	1091.0	1091.5	1090.9	1090.3	1089.7	1089.1	1089.0
135°	1149.0	1150.5	1152.2	1153.7	1155.3	1155.8	1155.3	1154.8	1154.2	1153.7	1153.2
137.5°	1207.9	1209.3	1210.6	1211.9	1213.4	1213.8	1213.4	1212.8	1212.3	1211.9	1212.0
140°	1246.4	1247.0	1247.5	1248.0	1248.5	1248.6	1248.4	1248.1	1247.9	1247.6	1248.1
142.5°	1281.1	1281.4	1281.8	1282.1	1282.4	1282.7	1283.1	1283.4	1283.8	1284.2	1284.3
145°	1332.1	1332.6	1333.1	1333.6	1334.1	1334.4	1334.4	1334.4	1334.4	1334.4	1334.7
147.5°	1376.6	1376.5	1376.4	1376.3	1376.2	1376.3	1376.6	1377.0	1377.4	1377.7	1378.0
150°	1404.8	1404.3	1403.8	1403.3	1402.8	1402.8	1403.3	1403.8	1404.3	1404.8	1405.3
152.5°	1432.1	1431.0	1429.8	1428.7	1427.4	1427.1	1427.7	1428.3	1428.8	1429.3	1429.8
155°	1467.0	1465.5	1463.9	1462.4	1460.8	1460.3	1460.8	1461.3	1461.9	1462.4	1463.2
157.5°	1494.1	1493.1	1492.2	1491.3	1490.3	1489.9	1490.0	1490.0	1490.1	1490.1	1490.9
160°	1512.9	1511.3	1509.7	1508.1	1506.6	1505.9	1506.2	1506.4	1506.7	1506.9	1508.0
162.5°	1527.8	1526.3	1524.7	1523.2	1521.6	1521.0	1521.2	1521.5	1521.8	1522.0	1523.5
165°	1548.0	1546.5	1544.9	1543.4	1541.8	1541.2	1541.4	1541.7	1541.9	1542.2	1543.8
167.5°	1563.1	1561.5	1559.8	1558.2	1556.6	1555.9	1556.2	1556.4	1556.7	1557.0	1558.8
170°	1571.6	1569.7	1567.8	1566.0	1564.2	1563.5	1563.7	1564.0	1564.2	1564.5	1566.6
172.5°	1577.1	1575.3	1573.5	1571.7	1569.8	1569.1	1569.6	1570.1	1570.5	1571.0	1573.0
175°	1583.3	1581.7	1580.1	1578.5	1577.0	1576.3	1576.6	1576.9	1577.1	1577.4	1579.4
177.5°	1586.1	1584.8	1583.6	1582.4	1581.0	1580.5	1580.7	1580.9	1581.1	1581.3	1582.9
180°	1583.3	1583.3	1583.3	1583.3	1583.3	1583.3	1583.3	1583.3	1583.3	1583.3	1583.3



TEST NUMBER: P333337-840

CATALOG NUMBER: S125DIP-S1270D1205U840-4F0-1E-UDD-F

**CANDELA DISTRIBUTION (continued):**

	55°	60°	65°	70°	75°	80°	85°	90°
0°	1990.1	1990.1	1990.1	1990.1	1990.1	1990.1	1990.1	1990.1
2.5°	1984.4	1987.2	1990.0	1991.3	1991.0	1990.7	1990.4	1990.1
5°	1974.4	1977.6	1980.7	1982.2	1981.8	1981.5	1981.1	1980.7
7.5°	1954.4	1957.5	1960.6	1962.0	1961.7	1961.3	1961.0	1960.6
10°	1937.5	1940.4	1943.1	1944.3	1944.0	1943.6	1943.3	1943.0
12.5°	1915.0	1917.2	1919.5	1920.6	1920.5	1920.4	1920.4	1920.3
15°	1875.6	1877.3	1879.1	1880.0	1880.0	1880.0	1880.0	1880.0
17.5°	1829.8	1832.0	1834.1	1834.3	1832.6	1830.9	1829.1	1827.4
20°	1795.1	1797.6	1800.0	1800.4	1798.6	1796.9	1795.1	1793.3
22.5°	1755.7	1757.3	1758.9	1759.1	1757.9	1756.7	1755.4	1754.3
25°	1692.4	1693.1	1693.8	1693.6	1692.6	1691.5	1690.5	1689.4
27.5°	1626.1	1626.3	1626.4	1625.9	1624.9	1623.9	1622.8	1621.7
30°	1577.8	1577.1	1576.4	1575.6	1574.5	1573.5	1572.4	1571.3
32.5°	1528.8	1527.6	1526.3	1524.7	1522.9	1521.0	1519.0	1517.2
35°	1452.9	1451.2	1449.5	1447.1	1444.3	1441.6	1438.8	1435.9
37.5°	1373.1	1370.6	1368.0	1365.8	1364.2	1362.6	1361.0	1359.4
40°	1317.9	1314.7	1311.5	1309.5	1308.4	1307.4	1306.3	1305.3
42.5°	1263.0	1260.1	1257.3	1255.1	1253.4	1251.8	1250.2	1248.6
45°	1181.9	1177.7	1173.6	1170.9	1169.8	1168.8	1167.7	1166.7
47.5°	1096.4	1092.2	1087.9	1084.6	1082.1	1079.6	1077.2	1074.8
50°	1037.9	1033.4	1028.9	1025.3	1022.9	1020.5	1018.0	1015.5
52.5°	981.1	977.1	973.1	969.8	967.0	964.3	961.6	958.9
55°	892.7	889.6	886.5	883.6	881.2	878.8	876.3	873.8
57.5°	805.0	800.9	796.9	794.2	792.8	791.5	790.1	788.8
60°	745.6	742.1	738.6	735.7	733.2	730.7	728.3	725.9
62.5°	688.3	684.6	680.9	678.0	676.1	674.2	672.3	670.4
65°	598.3	595.1	592.0	589.8	588.3	586.9	585.5	584.1
67.5°	512.4	509.7	507.1	505.3	504.4	503.6	502.8	501.9
70°	455.6	453.4	451.3	449.6	448.2	446.8	445.5	444.0
72.5°	402.1	399.7	397.4	395.5	394.0	392.6	391.2	389.8
75°	319.1	318.0	317.0	315.8	314.4	313.0	311.5	310.1
77.5°	243.1	242.5	241.9	241.1	240.0	239.0	238.1	237.1
80°	194.5	194.2	193.8	193.3	192.6	191.9	191.2	190.6
82.5°	148.7	148.0	147.3	147.0	146.8	146.7	146.5	146.4
85°	87.5	87.2	86.7	86.2	85.5	84.8	84.1	83.4
87.5°	37.1	37.3	37.6	37.5	37.1	36.7	36.3	35.9
90°	21.4	22.7	24.0	25.0	25.9	26.6	27.4	28.2
92.5°	21.4	22.7	24.0	24.8	25.1	25.5	26.0	26.3
95°	21.4	22.7	24.0	24.6	24.6	24.6	24.6	24.6
97.5°	43.0	35.6	28.3	24.6	24.6	24.6	24.6	24.6
100°	126.5	87.7	48.8	28.8	27.8	26.8	25.7	24.6
102.5°	245.8	238.5	231.2	218.6	200.9	183.1	165.4	147.6
105°	349.7	349.7	349.7	349.6	349.3	349.1	348.8	348.6
107.5°	442.8	442.8	442.9	442.5	441.7	441.0	440.2	439.4
110°	503.1	502.3	501.5	501.3	501.5	501.8	502.1	502.3





TEST NUMBER: P333337-840

CATALOG NUMBER: S125DIP-S1270D1205U840-4F0-1E-UDD-F

**CANDELA DISTRIBUTION (continued):**

	55°	60°	65°	70°	75°	80°	85°	90°
112.5°	562.8	561.8	560.8	560.1	559.8	559.4	559.1	558.7
115°	652.8	651.8	650.8	649.4	647.8	646.3	644.7	643.2
117.5°	739.7	738.4	737.0	736.0	735.3	734.7	734.0	733.3
120°	795.9	795.4	794.9	794.0	792.6	791.3	790.0	788.7
122.5°	849.4	848.9	848.4	847.3	845.8	844.2	842.8	841.3
125°	927.5	926.3	925.3	924.4	923.6	922.9	922.1	921.3
127.5°	998.8	998.3	997.6	996.4	994.5	992.5	990.6	988.7
130°	1045.3	1044.5	1043.8	1042.7	1041.4	1040.2	1038.8	1037.5
132.5°	1088.8	1088.6	1088.5	1087.8	1086.5	1085.2	1083.9	1082.6
135°	1152.7	1152.2	1151.7	1150.5	1149.0	1147.4	1145.9	1144.3
137.5°	1212.1	1212.2	1212.3	1211.7	1210.3	1209.0	1207.6	1206.3
140°	1248.6	1249.1	1249.7	1249.1	1247.6	1246.1	1244.5	1242.9
142.5°	1284.4	1284.5	1284.6	1283.9	1282.3	1280.8	1279.2	1277.7
145°	1334.9	1335.2	1335.4	1334.8	1333.2	1331.7	1330.1	1328.6
147.5°	1378.3	1378.6	1378.9	1378.1	1376.2	1374.3	1372.5	1370.6
150°	1405.9	1406.4	1406.9	1406.1	1404.1	1402.0	1399.9	1397.9
152.5°	1430.3	1430.9	1431.4	1430.7	1428.8	1426.9	1425.0	1423.2
155°	1463.9	1464.7	1465.5	1464.8	1462.8	1460.7	1458.5	1456.5
157.5°	1491.8	1492.6	1493.4	1492.8	1490.7	1488.6	1486.5	1484.4
160°	1509.0	1510.1	1511.2	1510.7	1508.5	1506.4	1504.4	1502.3
162.5°	1524.9	1526.4	1527.8	1527.4	1525.1	1522.8	1520.6	1518.2
165°	1545.3	1546.9	1548.4	1548.1	1546.1	1544.0	1541.9	1539.8
167.5°	1560.7	1562.6	1564.5	1564.3	1561.9	1559.5	1557.2	1554.9
170°	1568.6	1570.7	1572.9	1572.7	1570.3	1568.0	1565.7	1563.3
172.5°	1574.8	1576.7	1578.5	1578.3	1576.0	1573.7	1571.2	1568.9
175°	1581.5	1583.7	1585.7	1585.6	1583.3	1580.9	1578.5	1576.2
177.5°	1584.3	1585.8	1587.2	1587.1	1585.5	1583.8	1582.1	1580.4
180°	1583.3	1583.3	1583.3	1583.3	1583.3	1583.3	1583.3	1583.3

(END OF REPORT)