

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P333339-840

Luminaire Tested: **S125DIP-S1270D1205U840-4F0-1E-UDD-F4**

Issue Date: 3/3/2020

Test Information

Test Method: LM-79-08
Report Number: P333339-840
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-19,
Test Lab: INNOVATION CENTER
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: NEO-RAY
Catalog Number: S125DIP-S1270D1205U840-4F0-1E-UDD-F4
Description: DEFINE 5 DIRECT-INDIRECT PENDANT LED LUMINAIRE
DOWNLIGHT 1270 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER
UPLIGHT 1205 LUMENS PER FOOT, BATWING OPTIC
Light Source: -
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 9546.6 lumens
Efficiency: N/A
Efficacy: 133.1 lumens/watt
Spacing Criteria (0/90/45): 1.21 / 1.18 / 1.31
Luminous Opening: Rectangular (W 0.42' x L: 4' x H: 0')
CIE Type: General Diffuse


Input Watts (W): 71.7
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P333339-840

CATALOG NUMBER: S125DIP-S1270D1205U840-4F0-1E-UDD-F4

Luminous Intensity Polar Plot





TEST NUMBER: P333339-840

CATALOG NUMBER: S125DIP-S1270D1205U840-4F0-1E-UDD-F4

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	108	108	108	108	100	100	100	100	86	86	86	72	72	72	60	60	60	54
1	99	94	90	87	91	88	84	81	75	73	70	64	62	60	53	52	51	46
2	90	82	76	71	83	77	71	67	66	62	58	56	53	50	47	44	43	38
3	82	72	65	59	76	67	61	56	58	53	49	49	46	42	41	39	36	32
4	75	64	56	50	69	60	53	47	52	46	42	44	40	36	37	34	31	28
5	69	57	49	43	64	53	46	40	46	40	36	39	35	31	33	30	27	24
6	63	51	43	37	59	48	41	35	42	36	31	36	31	28	30	27	24	21
7	59	46	38	33	54	43	36	31	38	32	28	32	28	24	28	24	21	19
8	54	42	34	29	50	39	32	27	34	29	25	30	25	22	25	22	19	17
9	51	38	31	26	47	36	29	24	32	26	22	27	23	20	23	20	17	15
10	47	35	28	23	44	33	26	22	29	24	20	25	21	18	22	18	16	14

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	12853	12853	12853
5°	12882	12759	12841
10°	12804	12669	12742
15°	12664	12517	12570
20°	12466	12304	12325
25°	12252	12050	12039
30°	11989	11777	11718
35°	11706	11483	11321
40°	11415	11163	11005
45°	11102	10872	10656
50°	10758	10520	10203
55°	10424	10124	9839
60°	10026	9722	9376
65°	9553	9239	8926
70°	9098	8682	8384
75°	8289	8015	7738
80°	7375	7260	7089
85°	6417	6536	6180



TEST NUMBER: P333339-840

CATALOG NUMBER: S125DIP-S1270D1205U840-4F0-1E-UDD-F4

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	187.6	2.0
10°-20°	530.1	5.6
20°-30°	782.7	8.2
30°-40°	913.3	9.6
40°-50°	917.2	9.6
50°-60°	805.1	8.4
60°-70°	599.9	6.3
70°-80°	343.0	3.6
80°-90°	103.0	1.1
90°-100°	421.9	4.4
100°-110°	906.9	9.5
110°-120°	851.1	8.9
120°-130°	689.8	7.2
130°-140°	553.5	5.8
140°-150°	417.7	4.4
150°-160°	294.0	3.1
160°-170°	173.3	1.8
170°-180°	56.4	0.6
0°-30°	1500.4	15.7
0°-40°	2413.6	25.3
0°-60°	4136.0	43.3
0°-90°	5182.0	54.3
90°-120°	2179.9	22.8
90°-150°	3840.9	40.2
90°-180°	4365.0	45.7
0°-180°	9546.6	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	1990	1990	1990	1990	1990	
5°	1987	1983	1968	1981	1981	188
15°	1894	1889	1872	1880	1880	534
25°	1719	1711	1691	1694	1689	791
35°	1485	1478	1456	1448	1436	928
45°	1216	1208	1190	1172	1167	936
55°	926	920	899	885	874	826
65°	625	621	605	591	584	620
75°	332	329	321	316	310	354
85°	87	88	88	86	83	97
90°	1	11	19	25	27	7
95°	39	114	1040	472	276	41
105°	133	185	851	1675	1555	140
115°	237	286	683	1472	1732	233
125°	328	385	655	1171	1365	291
135°	385	463	650	982	1134	299
145°	448	513	652	813	894	281
155°	512	550	636	719	750	236
165°	559	574	610	647	657	157
175°	581	581	586	593	590	55
180°	582	582	582	582	582	



TEST NUMBER: P333339-840

CATALOG NUMBER: S125DIP-S1270D1205U840-4F0-1E-UDD-F4

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	1990.1	1990.1	1990.1	1990.1	1990.1	1990.1	1990.1	1990.1	1990.1	1990.1	1990.1
2.5°	1995.2	1994.4	1993.6	1992.7	1991.9	1990.0	1987.2	1984.4	1981.7	1978.8	1981.7
5°	1987.0	1986.3	1985.6	1984.9	1984.2	1982.2	1978.6	1975.1	1971.7	1968.1	1971.3
7.5°	1968.7	1968.0	1967.3	1966.6	1965.9	1963.7	1959.8	1956.0	1952.2	1948.3	1951.4
10°	1952.4	1951.7	1951.0	1950.3	1949.5	1947.3	1943.5	1939.6	1935.7	1931.9	1934.7
12.5°	1932.2	1931.0	1929.8	1928.4	1927.2	1924.8	1921.2	1917.6	1914.1	1910.5	1912.8
15°	1894.1	1893.1	1892.0	1891.0	1890.0	1887.4	1883.6	1879.8	1875.9	1872.1	1873.8
17.5°	1850.4	1848.9	1847.2	1845.7	1844.2	1841.4	1837.4	1833.4	1829.5	1825.4	1827.7
20°	1813.8	1813.1	1812.4	1811.7	1811.0	1808.4	1803.8	1799.3	1794.7	1790.2	1792.6
22.5°	1777.3	1776.0	1774.7	1773.5	1772.2	1769.5	1765.2	1761.0	1756.7	1752.4	1754.0
25°	1719.4	1717.6	1715.9	1714.1	1712.3	1709.2	1704.7	1700.1	1695.6	1691.0	1691.7
27.5°	1651.6	1650.6	1649.5	1648.5	1647.5	1644.6	1639.9	1635.2	1630.5	1625.8	1626.0
30°	1607.6	1606.5	1605.5	1604.4	1603.4	1600.2	1595.0	1589.7	1584.5	1579.2	1578.5
32.5°	1559.7	1558.1	1556.5	1554.9	1553.3	1550.1	1545.4	1540.8	1536.0	1531.4	1530.1
35°	1484.7	1483.4	1482.0	1480.6	1479.1	1476.0	1471.1	1466.2	1461.3	1456.4	1454.7
37.5°	1406.9	1405.2	1403.5	1401.7	1400.0	1396.7	1392.2	1387.6	1382.9	1378.4	1375.7
40°	1354.0	1352.3	1350.6	1348.8	1347.1	1343.7	1338.9	1333.9	1329.1	1324.1	1321.0
42.5°	1297.4	1296.0	1294.4	1292.9	1291.5	1288.3	1283.4	1278.5	1273.6	1268.7	1265.9
45°	1215.5	1214.2	1212.7	1211.3	1209.9	1207.1	1203.0	1198.7	1194.6	1190.3	1186.1
47.5°	1127.3	1127.4	1127.5	1127.5	1127.6	1125.1	1120.1	1115.1	1110.0	1105.0	1100.8
50°	1070.7	1069.6	1068.5	1067.5	1066.4	1063.8	1059.7	1055.4	1051.3	1047.0	1042.5
52.5°	1012.7	1012.0	1011.2	1010.4	1009.7	1007.0	1002.5	998.0	993.6	989.1	985.1
55°	925.8	924.7	923.7	922.6	921.6	918.7	913.7	908.9	903.9	899.1	895.9
57.5°	834.1	833.6	833.0	832.5	831.9	829.6	825.5	821.3	817.2	813.0	809.0
60°	776.2	774.9	773.5	772.0	770.6	768.0	764.2	760.3	756.5	752.7	749.1
62.5°	715.8	714.7	713.6	712.4	711.2	709.1	705.8	702.5	699.2	695.9	692.2
65°	625.1	624.4	623.7	623.0	622.3	620.0	616.1	612.3	608.4	604.6	601.5
67.5°	537.2	535.7	534.3	532.8	531.4	529.2	526.3	523.4	520.6	517.7	515.0
70°	481.8	480.1	478.3	476.6	474.8	472.3	469.2	466.1	462.9	459.8	457.7
72.5°	421.3	420.1	419.0	417.8	416.6	415.0	412.9	410.9	408.9	406.9	404.5
75°	332.2	331.5	330.8	330.1	329.4	328.2	326.5	324.7	323.0	321.2	320.1
77.5°	250.0	249.7	249.4	249.2	248.9	248.3	247.3	246.3	245.3	244.4	243.8
80°	198.3	198.3	198.3	198.3	198.3	198.0	197.3	196.6	195.9	195.2	194.9
82.5°	153.0	152.5	151.9	151.4	150.8	150.5	150.3	150.2	150.1	149.9	149.3
85°	86.6	86.9	87.3	87.7	88.0	88.2	88.2	88.2	88.2	88.2	87.9
87.5°	34.2	34.4	34.9	35.4	35.9	36.3	36.2	36.4	36.4	36.5	36.8
90°	1.2	2.3	4.6	7.1	9.4	11.7	12.9	15.2	16.5	18.8	20.0
92.5°	14.3	17.4	27.3	41.8	62.0	96.2	160.3	267.8	384.5	378.3	306.3
95°	38.7	39.9	49.3	62.2	88.0	140.8	266.4	524.5	848.4	1039.7	1017.3
97.5°	64.3	65.7	72.3	85.2	108.5	146.4	229.5	418.7	757.6	1110.2	1287.3
100°	82.1	84.5	89.2	102.1	124.4	159.6	227.6	380.2	675.9	1059.6	1352.9
102.5°	101.9	103.3	107.0	120.9	141.3	175.5	236.1	364.3	613.9	970.4	1313.5
105°	132.6	132.6	138.5	150.2	169.0	201.9	253.5	357.9	553.8	850.7	1187.5
107.5°	162.6	165.0	170.6	180.3	199.8	229.2	279.2	368.7	528.5	768.3	1058.9
110°	184.2	186.6	191.3	201.9	219.4	249.9	298.0	379.0	521.0	729.8	985.6



TEST NUMBER: P333339-840

CATALOG NUMBER: S125DIP-S1270D1205U840-4F0-1E-UDD-F4

CANDELA DISTRIBUTION (continued):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	205.8	208.1	211.9	222.5	240.0	269.6	315.9	392.1	521.0	707.3	931.2
115°	237.0	239.3	242.9	253.5	271.0	300.4	343.9	411.8	524.5	683.0	871.8
117.5°	265.2	268.7	272.5	283.1	303.0	331.3	372.4	434.4	532.3	671.0	836.4
120°	284.0	287.5	292.2	302.8	322.7	352.0	393.1	449.4	539.8	665.3	816.7
122.5°	303.7	306.3	310.0	320.5	342.4	371.7	412.8	466.4	546.3	660.7	799.8
125°	328.5	330.9	336.8	347.3	369.6	400.1	438.9	489.3	557.3	654.8	776.8
127.5°	348.0	351.5	359.1	372.4	396.2	426.7	463.9	510.5	569.8	652.0	755.7
130°	360.2	363.8	373.1	388.4	413.0	443.5	479.9	524.5	577.3	650.1	741.6
132.5°	369.6	374.1	385.4	402.5	428.1	458.6	494.9	536.7	585.7	650.1	730.3
135°	384.9	389.6	403.6	422.4	447.1	478.8	515.1	553.8	597.2	650.1	717.0
137.5°	404.1	407.7	420.8	439.6	463.7	496.3	529.5	566.5	607.8	651.5	705.0
140°	415.4	418.9	433.0	451.8	474.0	505.7	539.8	575.0	612.5	652.4	699.3
142.5°	428.5	431.1	444.2	463.0	484.4	514.2	546.3	579.7	615.3	653.4	694.7
145°	448.3	450.6	462.3	478.8	499.9	526.8	557.3	586.7	618.4	652.4	687.6
147.5°	468.9	470.3	480.4	495.6	513.9	537.7	564.4	591.0	619.6	649.3	680.3
150°	481.1	483.4	491.7	507.0	523.3	543.3	569.1	593.8	619.6	646.5	674.7
152.5°	494.2	495.6	502.9	516.3	531.8	549.9	573.8	595.6	618.6	642.8	668.1
155°	511.6	511.6	518.7	530.4	542.1	558.6	578.5	597.2	616.0	636.0	657.1
157.5°	527.1	526.8	532.5	542.6	552.9	565.3	582.5	598.4	613.0	628.9	646.8
160°	537.5	536.2	541.0	549.2	558.6	569.1	584.4	598.4	610.2	624.3	638.3
162.5°	545.8	544.7	549.4	556.6	564.2	572.9	586.2	597.5	607.3	618.6	630.9
165°	558.6	556.2	559.8	565.6	570.3	577.3	586.7	596.1	603.1	610.2	619.6
167.5°	567.0	565.8	567.9	571.2	574.5	579.0	586.7	593.3	596.5	602.0	608.5
170°	572.6	571.5	572.6	575.0	577.3	580.9	586.7	591.4	593.8	597.2	602.0
172.5°	576.4	574.3	575.4	577.7	579.2	580.9	585.7	589.6	590.0	591.7	595.4
175°	580.9	578.5	579.7	580.9	580.9	580.9	584.4	586.7	585.5	585.5	586.7
177.5°	583.0	581.1	581.1	582.0	581.1	581.1	583.0	583.9	582.0	582.0	583.0
180°	582.0	582.0	582.0	582.0	582.0	582.0	582.0	582.0	582.0	582.0	582.0



TEST NUMBER: P333339-840

CATALOG NUMBER: S125DIP-S1270D1205U840-4F0-1E-UDD-F4

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°
0°	1990.1	1990.1	1990.1	1990.1	1990.1	1990.1	1990.1	1990.1
2.5°	1984.4	1987.2	1990.0	1991.3	1991.0	1990.7	1990.4	1990.1
5°	1974.4	1977.6	1980.7	1982.2	1981.8	1981.5	1981.1	1980.7
7.5°	1954.4	1957.5	1960.6	1962.0	1961.7	1961.3	1961.0	1960.6
10°	1937.5	1940.4	1943.1	1944.3	1944.0	1943.6	1943.3	1943.0
12.5°	1915.0	1917.2	1919.5	1920.6	1920.5	1920.4	1920.4	1920.3
15°	1875.6	1877.3	1879.1	1880.0	1880.0	1880.0	1880.0	1880.0
17.5°	1829.8	1832.0	1834.1	1834.3	1832.6	1830.9	1829.1	1827.4
20°	1795.1	1797.6	1800.0	1800.4	1798.6	1796.9	1795.1	1793.3
22.5°	1755.7	1757.3	1758.9	1759.1	1757.9	1756.7	1755.4	1754.3
25°	1692.4	1693.1	1693.8	1693.6	1692.6	1691.5	1690.5	1689.4
27.5°	1626.1	1626.3	1626.4	1625.9	1624.9	1623.9	1622.8	1621.7
30°	1577.8	1577.1	1576.4	1575.6	1574.5	1573.5	1572.4	1571.3
32.5°	1528.8	1527.6	1526.3	1524.7	1522.9	1521.0	1519.0	1517.2
35°	1452.9	1451.2	1449.5	1447.1	1444.3	1441.6	1438.8	1435.9
37.5°	1373.1	1370.6	1368.0	1365.8	1364.2	1362.6	1361.0	1359.4
40°	1317.9	1314.7	1311.5	1309.5	1308.4	1307.4	1306.3	1305.3
42.5°	1263.0	1260.1	1257.3	1255.1	1253.4	1251.8	1250.2	1248.6
45°	1181.9	1177.7	1173.6	1170.9	1169.8	1168.8	1167.7	1166.7
47.5°	1096.4	1092.2	1087.9	1084.6	1082.1	1079.6	1077.2	1074.8
50°	1037.9	1033.4	1028.9	1025.3	1022.9	1020.5	1018.0	1015.5
52.5°	981.1	977.1	973.1	969.8	967.0	964.3	961.6	958.9
55°	892.7	889.6	886.5	883.6	881.2	878.8	876.3	873.8
57.5°	805.0	800.9	796.9	794.2	792.8	791.5	790.1	788.8
60°	745.6	742.1	738.6	735.7	733.2	730.7	728.3	725.9
62.5°	688.3	684.6	680.9	678.0	676.1	674.2	672.3	670.4
65°	598.3	595.1	592.0	589.8	588.3	586.9	585.5	584.1
67.5°	512.4	509.7	507.1	505.3	504.4	503.6	502.8	501.9
70°	455.6	453.4	451.3	449.6	448.2	446.8	445.5	444.0
72.5°	402.1	399.7	397.4	395.5	394.0	392.6	391.2	389.8
75°	319.1	318.0	317.0	315.8	314.4	313.0	311.5	310.1
77.5°	243.1	242.5	241.9	241.1	240.0	239.0	238.1	237.1
80°	194.5	194.2	193.8	193.3	192.6	191.9	191.2	190.6
82.5°	148.7	148.0	147.3	147.0	146.8	146.7	146.5	146.4
85°	87.5	87.2	86.7	86.2	85.5	84.8	84.1	83.4
87.5°	37.0	37.2	37.5	37.7	37.1	36.6	36.2	35.6
90°	21.1	22.3	23.4	25.9	25.9	25.9	27.0	27.0
92.5°	207.9	150.9	113.6	96.2	81.2	78.4	76.7	74.8
95°	843.6	665.3	521.0	422.4	339.1	303.9	294.6	275.8
97.5°	1256.5	1131.5	990.9	853.7	781.2	715.6	681.6	666.5
100°	1443.3	1385.8	1265.0	1142.9	1062.0	977.4	934.0	915.2
102.5°	1506.2	1541.7	1483.7	1401.1	1314.4	1254.4	1207.2	1193.2
105°	1469.2	1629.9	1681.5	1668.6	1631.0	1592.4	1568.8	1554.8
107.5°	1336.8	1551.3	1683.8	1745.1	1764.1	1763.9	1756.2	1746.8
110°	1239.1	1462.1	1627.5	1727.3	1780.1	1802.4	1810.6	1810.6



TEST NUMBER: P333339-840

CATALOG NUMBER: S125DIP-S1270D1205U840-4F0-1E-UDD-F4

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°
112.5°	1162.2	1373.8	1541.2	1658.7	1736.0	1774.2	1794.6	1803.1
115°	1065.5	1247.4	1408.1	1536.0	1627.5	1683.8	1716.7	1731.9
117.5°	1003.0	1159.8	1298.3	1415.6	1507.1	1565.4	1598.0	1607.3
120°	969.3	1110.0	1239.1	1342.4	1429.3	1485.5	1517.2	1526.6
122.5°	943.9	1074.4	1189.4	1286.1	1363.5	1415.1	1446.8	1455.3
125°	907.1	1026.7	1128.8	1213.4	1279.0	1327.2	1352.9	1364.7
127.5°	869.5	981.2	1076.5	1155.6	1215.2	1257.7	1282.1	1287.3
130°	846.1	949.3	1040.9	1117.1	1175.8	1214.5	1238.0	1245.0
132.5°	822.5	919.3	1002.3	1075.8	1134.5	1173.2	1194.8	1202.7
135°	792.0	873.0	948.2	1015.0	1066.6	1105.4	1126.5	1133.6
137.5°	766.3	831.7	894.1	951.0	997.1	1032.4	1051.9	1059.6
140°	752.1	807.3	861.3	910.6	954.0	984.5	1002.1	1007.9
142.5°	739.9	786.7	833.1	875.9	912.7	938.5	955.1	960.1
145°	724.0	760.3	796.8	828.4	856.6	876.6	889.5	894.1
147.5°	709.0	738.5	766.5	790.4	812.7	828.7	836.2	838.3
150°	700.5	726.4	748.6	769.7	787.4	801.4	806.2	807.3
152.5°	691.2	714.2	734.6	751.0	765.8	777.0	781.7	782.9
155°	677.0	695.8	712.3	725.2	736.9	745.1	748.6	749.8
157.5°	663.0	678.4	691.2	701.3	710.3	717.2	720.4	720.2
160°	653.6	665.3	677.0	685.3	693.5	699.3	701.8	700.5
162.5°	643.3	654.1	663.9	671.2	677.5	682.5	683.0	682.7
165°	628.9	637.1	644.2	650.1	654.8	657.1	657.1	657.1
167.5°	615.3	620.8	626.1	630.4	632.7	634.8	633.9	633.7
170°	607.8	611.4	614.9	617.2	619.6	620.8	620.8	619.6
172.5°	599.4	602.9	605.5	606.9	607.3	609.5	607.6	606.4
175°	590.3	590.3	592.6	592.6	592.6	593.8	591.4	590.3
177.5°	583.9	584.8	584.8	584.8	583.9	584.8	582.0	582.0
180°	582.0	582.0	582.0	582.0	582.0	582.0	582.0	582.0

(END OF REPORT)