

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P331708-927

Luminaire Tested: **SA2XXRDIP-C865D330U927-4F0-1E-UDD-F**

Issue Date: 10/7/2019

Test Information

Test Method: LM-79-08
Report Number: P331708-927
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-2,
Test Lab: INNOVATION CENTER
Issue Date: 10/7/2019
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: NEO-RAY
Catalog Number: SA2XXRDIP-C865D330U927-4F0-1E-UDD-F
Description: DEFINE 2 DIRECT-INDIRECT PENDANT LED LUMINAIRE
DOWNLIGHT 865 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER, REGRESSED
HOUSING
UPLIGHT 330 LUMENS PER FOOT, NO LENS
Light Source: -
Ballast/Driver: ELECTRONIC DRIVER

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 3427.2 lumens
Efficiency: N/A
Efficacy: 78.8 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 0.99 / 1.16
Luminous Opening: Rectangular (W 0.17' x L: 4' x H: 0')
CIE Type: Semi-Direct

Input Watts (W): 43.5
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P331708-927
CATALOG NUMBER: SA2XXRDIP-C865D330U927-4F0-1E-UDD-F

Luminous Intensity Polar Plot





TEST NUMBER: P331708-927

CATALOG NUMBER: SA2XXRDIP-C865D330U927-4F0-1E-UDD-F

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20					20					20					20					20	
RC	80					70					50					30					10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0	
RCR																						
0	112	112	112	112	106	106	106	106	94	94	94	84	84	84	74	74	74	74	74	74	70	
1	103	99	95	92	97	93	90	87	84	81	79	75	73	71	67	65	64	64	64	64	60	
2	94	87	81	76	89	83	77	73	74	70	67	67	63	61	60	57	55	55	55	55	51	
3	86	77	70	64	82	73	67	62	66	61	57	60	55	52	53	50	48	48	48	48	44	
4	79	69	61	55	75	65	58	53	59	54	49	54	49	45	48	45	42	42	42	42	39	
5	73	62	54	48	69	59	52	46	53	47	43	48	44	40	44	40	37	37	37	37	34	
6	68	56	48	42	64	53	46	41	49	42	38	44	39	35	40	36	33	33	33	33	30	
7	63	51	43	37	60	49	41	36	44	38	34	40	35	32	37	33	29	29	29	29	27	
8	59	46	39	33	56	44	37	32	41	35	30	37	32	28	34	30	27	27	27	27	24	
9	55	43	35	30	52	41	34	29	37	32	27	34	29	26	31	27	24	24	24	24	22	
10	51	39	32	27	49	38	31	26	35	29	25	32	27	24	29	25	22	22	22	22	20	

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	18755	18755	18755
5°	18827	18519	18621
10°	18682	18216	18061
15°	18467	17677	17167
20°	18170	16905	16057
25°	17865	16030	14982
30°	17443	15129	13601
35°	17030	14152	12390
40°	16617	13139	10989
45°	16130	12001	9720
50°	15631	10854	8475
55°	15122	9619	7279
60°	14528	8315	6042
65°	13857	6988	5501
70°	13053	5755	5061
75°	12071	5246	4722
80°	10646	4695	4305
85°	8373	3705	3705



TEST NUMBER: P331708-927

CATALOG NUMBER: SA2XXRDIP-C865D330U927-4F0-1E-UDD-F

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	108.7	3.2
10°-20°	298.5	8.7
20°-30°	419.2	12.2
30°-40°	457.1	13.3
40°-50°	420.3	12.3
50°-60°	330.1	9.6
60°-70°	215.2	6.3
70°-80°	111.0	3.2
80°-90°	29.7	0.9
90°-100°	11.8	0.3
100°-110°	43.3	1.3
110°-120°	115.7	3.4
120°-130°	191.1	5.6
130°-140°	203.2	5.9
140°-150°	188.9	5.5
150°-160°	151.8	4.4
160°-170°	97.8	2.9
170°-180°	33.7	1.0
0°-30°	826.5	24.1
0°-40°	1283.6	37.5
0°-60°	2034.0	59.3
0°-90°	2389.9	69.7
90°-120°	170.8	5.0
90°-150°	754.0	22.0
90°-180°	1037.0	30.3
0°-180°	3427.2	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	1162	1162	1162	1162	1162	
5°	1162	1156	1143	1151	1149	110
15°	1105	1092	1058	1038	1027	311
25°	1003	967	900	858	841	461
35°	864	808	718	654	629	541
45°	706	634	526	454	426	545
55°	537	453	342	281	259	480
65°	363	277	183	149	144	359
75°	194	122	84	77	76	205
85°	45	24	20	20	20	53
90°	0	3	5	6	7	3
95°	17	9	10	11	11	20
105°	78	81	16	18	20	83
115°	147	152	158	45	21	145
125°	208	212	216	218	219	186
135°	258	262	264	266	266	199
145°	299	299	303	305	304	187
155°	329	327	330	331	329	152
165°	347	345	346	348	346	98
175°	355	353	354	355	353	34
180°	354	354	354	354	354	



TEST NUMBER: P331708-927

CATALOG NUMBER: SA2XXRDIP-C865D330U927-4F0-1E-UDD-F

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	1161.6	1161.6	1161.6	1161.6	1161.6	1161.6	1161.6	1161.6	1161.6	1161.6	1161.6
2.5°	1165.8	1164.8	1163.9	1162.9	1162.1	1160.5	1158.5	1156.4	1154.4	1152.3	1154.2
5°	1161.6	1160.4	1159.2	1158.0	1156.9	1154.8	1151.8	1148.7	1145.7	1142.6	1144.7
7.5°	1149.5	1148.1	1146.7	1145.3	1143.8	1141.3	1137.7	1134.2	1130.6	1127.0	1127.7
10°	1139.5	1137.8	1136.2	1134.6	1132.9	1129.8	1125.1	1120.5	1115.8	1111.1	1110.4
12.5°	1126.9	1124.8	1122.8	1120.9	1118.8	1114.8	1108.8	1102.9	1096.9	1090.9	1089.6
15°	1104.8	1102.2	1099.6	1097.1	1094.5	1089.3	1081.3	1073.4	1065.4	1057.5	1053.0
17.5°	1077.7	1073.7	1069.8	1065.9	1062.0	1054.9	1044.7	1034.5	1024.4	1014.2	1008.9
20°	1057.5	1052.8	1048.1	1043.5	1038.8	1030.6	1018.9	1007.3	995.6	983.9	978.0
22.5°	1035.6	1030.4	1025.2	1019.9	1014.7	1005.5	992.3	979.1	966.0	952.8	945.2
25°	1002.8	995.4	987.9	980.4	973.0	961.5	946.0	930.7	915.2	899.8	890.3
27.5°	963.3	955.1	947.1	938.9	930.8	918.1	900.6	883.3	865.9	848.5	837.3
30°	935.6	926.7	917.8	908.9	900.1	886.3	867.6	848.9	830.2	811.5	799.6
32.5°	908.6	898.3	887.9	877.5	867.1	852.5	833.4	814.3	795.3	776.2	762.6
35°	864.0	852.2	840.3	828.3	816.4	800.2	779.6	759.1	738.6	718.0	703.2
37.5°	819.5	806.4	793.4	780.2	767.1	749.6	727.8	705.8	684.0	662.0	645.8
40°	788.4	774.4	760.3	746.3	732.3	714.0	691.3	668.7	646.0	623.4	606.7
42.5°	756.5	741.6	726.9	712.2	697.4	678.3	654.9	631.4	608.1	584.6	567.5
45°	706.4	690.7	675.1	659.4	643.8	623.7	599.2	574.6	550.1	525.6	509.0
47.5°	657.6	641.0	624.5	607.8	591.3	570.3	545.0	519.7	494.3	469.1	452.6
50°	622.3	605.7	589.1	572.5	556.0	534.8	509.1	483.4	457.7	432.1	415.9
52.5°	587.8	570.5	553.2	535.8	518.5	497.3	472.1	446.9	421.8	396.7	381.1
55°	537.2	519.0	500.7	482.5	464.3	442.5	417.3	392.1	366.9	341.7	327.6
57.5°	485.2	466.5	447.8	429.1	410.5	389.0	364.7	340.5	316.2	292.0	279.2
60°	449.9	431.2	412.6	393.9	375.2	353.8	329.7	305.6	281.6	257.5	245.7
62.5°	415.4	396.7	378.0	359.3	340.6	319.9	296.9	274.0	251.0	228.1	216.7
65°	362.7	343.7	324.8	305.9	287.0	267.0	246.0	225.0	203.9	182.9	175.0
67.5°	311.8	293.0	274.3	255.4	236.6	217.8	198.9	180.0	161.1	142.1	138.5
70°	276.5	258.3	240.0	221.8	203.6	186.4	170.3	154.2	138.1	121.9	119.6
72.5°	242.8	225.4	207.9	190.4	172.9	157.7	144.8	131.8	118.9	106.0	104.0
75°	193.5	177.1	160.7	144.3	128.0	115.9	107.9	100.0	92.1	84.1	82.5
77.5°	144.9	130.5	116.1	101.8	87.5	78.4	74.5	70.7	66.9	63.1	62.1
80°	114.5	102.7	90.8	78.8	66.9	59.8	57.4	55.1	52.8	50.5	49.5
82.5°	86.8	77.6	68.2	58.9	49.7	44.2	42.6	41.0	39.5	37.9	37.3
85°	45.2	40.3	35.4	30.5	25.6	22.8	22.1	21.4	20.7	20.0	20.0
87.5°	13.5	12.1	10.8	9.4	8.0	7.4	7.4	7.6	7.7	7.8	7.6
90°	0.2	0.9	1.5	2.1	2.8	3.3	3.7	4.2	4.7	5.1	5.4
92.5°	5.1	5.1	5.1	5.0	4.9	5.1	5.2	5.5	5.7	5.9	6.1
95°	16.6	14.7	12.9	11.0	9.1	8.4	8.8	9.2	9.6	10.0	10.3
97.5°	33.0	27.7	22.4	17.2	11.9	9.7	10.6	11.5	12.4	13.4	13.6
100°	45.3	37.5	29.7	21.9	14.2	10.7	11.7	12.7	13.6	14.6	15.1
102.5°	58.9	57.2	55.5	53.9	52.3	47.4	39.3	31.2	23.1	15.0	15.6
105°	77.9	79.5	81.3	83.0	84.7	77.8	62.3	46.7	31.1	15.6	16.2
107.5°	99.5	100.9	102.3	103.7	105.0	96.4	77.8	59.2	40.5	21.9	21.2
110°	113.4	114.6	115.9	117.1	118.3	110.6	94.2	77.7	61.2	44.8	39.1



TEST NUMBER: P331708-927

CATALOG NUMBER: SA2XXRDIP-C865D330U927-4F0-1E-UDD-F

CANDELA DISTRIBUTION (continued):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	126.6	127.6	128.7	129.8	130.8	129.3	125.2	121.2	117.1	113.0	92.3
115°	147.3	148.2	149.2	150.2	151.1	152.3	153.8	155.2	156.6	158.0	131.7
117.5°	165.8	166.8	167.9	169.1	170.1	171.1	172.1	173.1	174.0	175.1	168.7
120°	179.3	180.1	181.0	181.9	182.7	183.6	184.7	185.7	186.7	187.7	188.5
122.5°	190.8	191.7	192.6	193.5	194.4	195.4	196.5	197.6	198.8	199.9	200.3
125°	208.3	209.0	209.7	210.5	211.2	212.1	213.2	214.3	215.3	216.4	216.8
127.5°	224.0	224.9	225.7	226.6	227.4	228.1	228.9	229.8	230.6	231.4	232.0
130°	234.1	235.0	235.9	236.9	237.7	238.5	239.2	239.8	240.4	241.1	241.6
132.5°	244.4	245.1	245.9	246.7	247.5	248.1	248.7	249.4	250.0	250.6	251.2
135°	257.7	258.6	259.5	260.4	261.3	262.1	262.5	263.1	263.6	264.1	264.7
137.5°	271.2	271.8	272.4	273.1	273.7	274.3	274.9	275.4	276.1	276.6	277.2
140°	280.0	280.4	280.8	281.3	281.8	282.3	283.0	283.6	284.2	284.8	285.3
142.5°	287.3	287.7	288.1	288.6	289.0	289.5	290.3	291.0	291.7	292.4	292.9
145°	298.9	298.9	298.8	298.7	298.7	299.1	300.1	301.1	302.1	303.0	303.4
147.5°	309.0	308.8	308.6	308.3	308.2	308.5	309.4	310.5	311.4	312.4	312.6
150°	315.5	315.1	314.7	314.3	313.9	314.3	315.1	316.1	317.0	317.9	318.2
152.5°	321.1	320.7	320.2	319.7	319.3	319.5	320.4	321.2	322.1	323.0	323.3
155°	329.2	328.6	328.1	327.6	327.1	327.2	327.9	328.5	329.2	329.9	330.3
157.5°	335.4	335.0	334.5	334.1	333.7	333.7	334.2	334.7	335.2	335.6	336.0
160°	339.1	338.8	338.4	338.1	337.8	337.8	338.1	338.4	338.8	339.1	339.5
162.5°	342.4	342.1	341.7	341.4	341.0	341.0	341.3	341.6	341.9	342.2	342.6
165°	346.8	346.5	346.1	345.8	345.5	345.4	345.5	345.7	345.9	346.0	346.4
167.5°	350.1	349.7	349.4	349.0	348.7	348.6	348.8	349.0	349.1	349.3	349.7
170°	352.0	351.6	351.3	350.9	350.5	350.5	350.5	350.7	350.8	350.9	351.3
172.5°	353.2	352.8	352.4	352.1	351.8	351.6	351.8	351.9	352.0	352.1	352.5
175°	354.7	354.3	353.9	353.6	353.2	353.0	353.2	353.2	353.4	353.5	353.9
177.5°	355.0	354.7	354.3	354.0	353.7	353.6	353.6	353.7	353.7	353.8	354.1
180°	353.9	353.9	353.9	353.9	353.9	353.9	353.9	353.9	353.9	353.9	353.9



TEST NUMBER: P331708-927

CATALOG NUMBER: SA2XXRDIP-C865D330U927-4F0-1E-UDD-F

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°
0°	1161.6	1161.6	1161.6	1161.6	1161.6	1161.6	1161.6	1161.6
2.5°	1156.0	1157.9	1159.8	1160.5	1160.2	1159.8	1159.4	1159.0
5°	1146.8	1148.9	1151.0	1151.8	1151.0	1150.3	1149.6	1148.9
7.5°	1128.3	1128.9	1129.5	1129.2	1128.0	1126.8	1125.5	1124.3
10°	1109.7	1109.0	1108.3	1107.2	1105.8	1104.5	1103.0	1101.6
12.5°	1088.4	1087.1	1085.8	1084.1	1081.7	1079.4	1077.1	1074.8
15°	1048.6	1044.2	1039.7	1036.3	1034.0	1031.7	1029.4	1027.0
17.5°	1003.6	998.3	993.1	988.4	984.4	980.4	976.4	972.3
20°	972.2	966.4	960.5	955.1	949.9	944.8	939.6	934.5
22.5°	937.8	930.3	922.7	917.0	913.2	909.3	905.5	901.7
25°	880.7	871.1	861.5	854.9	851.4	848.0	844.5	841.0
27.5°	826.2	815.0	803.8	795.5	790.0	784.3	778.8	773.2
30°	787.7	775.8	763.8	754.7	748.5	742.1	735.9	729.5
32.5°	749.0	735.4	721.8	712.0	706.2	700.2	694.3	688.3
35°	688.5	673.8	659.1	649.2	644.0	638.9	633.7	628.6
37.5°	629.6	613.4	597.2	586.1	580.3	574.3	568.5	562.6
40°	590.2	573.6	557.0	545.7	539.6	533.5	527.4	521.4
42.5°	550.4	533.2	516.1	504.5	498.7	492.8	486.9	481.0
45°	492.4	475.9	459.2	448.1	442.5	437.0	431.3	425.7
47.5°	436.0	419.5	403.1	392.3	387.2	382.1	377.0	371.9
50°	399.8	383.7	367.6	357.0	352.1	347.2	342.3	337.4
52.5°	365.6	350.1	334.5	324.5	319.9	315.4	310.9	306.3
55°	313.6	299.6	285.6	276.3	271.9	267.4	263.0	258.6
57.5°	266.3	253.5	240.7	232.3	228.6	224.8	221.1	217.4
60°	233.7	221.8	209.8	202.1	198.3	194.6	190.8	187.1
62.5°	205.4	194.1	182.7	175.9	173.6	171.4	169.1	166.9
65°	167.0	159.1	151.1	146.8	146.1	145.4	144.7	144.0
67.5°	134.8	131.2	127.5	125.3	124.6	123.8	123.1	122.4
70°	117.2	114.9	112.6	111.0	110.0	109.1	108.1	107.2
72.5°	102.0	100.1	98.1	96.9	96.3	95.7	95.1	94.6
75°	80.8	79.2	77.6	76.6	76.4	76.1	75.9	75.7
77.5°	61.2	60.3	59.3	58.7	58.3	57.9	57.6	57.2
80°	48.6	47.7	46.7	46.3	46.3	46.3	46.3	46.3
82.5°	36.8	36.1	35.6	35.3	35.3	35.3	35.3	35.3
85°	20.0	20.0	20.0	20.0	20.0	20.0	20.0	20.0
87.5°	7.5	7.4	7.2	7.2	7.2	7.2	7.2	7.3
90°	5.7	5.9	6.3	6.5	6.6	6.7	6.8	6.9
92.5°	6.3	6.4	6.5	6.7	6.7	6.8	6.8	6.9
95°	10.5	10.9	11.1	11.2	11.2	11.1	11.1	11.0
97.5°	13.9	14.0	14.3	14.4	14.5	14.6	14.7	14.7
100°	15.5	16.0	16.4	16.7	16.8	17.0	17.0	17.2
102.5°	16.2	16.8	17.3	17.7	17.9	18.1	18.2	18.4
105°	16.9	17.5	18.1	18.5	18.8	19.0	19.3	19.5
107.5°	20.6	20.0	19.3	19.1	19.3	19.6	19.8	20.0
110°	33.4	27.7	22.0	19.3	19.6	19.8	20.0	20.2



TEST NUMBER: P331708-927

CATALOG NUMBER: SA2XXRDIP-C865D330U927-4F0-1E-UDD-F

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°
112.5°	71.5	50.8	30.0	19.7	19.9	20.0	20.3	20.4
115°	105.4	79.0	52.6	37.4	33.3	29.2	25.1	21.0
117.5°	162.3	155.9	149.6	139.7	126.2	112.7	99.3	85.8
120°	189.1	189.8	190.4	187.0	179.3	171.6	163.9	156.2
122.5°	200.7	201.1	201.5	200.9	199.5	198.0	196.5	195.0
125°	217.2	217.6	218.0	218.3	218.5	218.6	218.8	219.0
127.5°	232.6	233.1	233.7	234.0	234.1	234.1	234.1	234.2
130°	242.2	242.9	243.5	243.8	243.8	243.7	243.7	243.6
132.5°	251.8	252.2	252.8	253.0	252.9	252.9	252.9	252.8
135°	265.2	265.8	266.3	266.6	266.5	266.3	266.3	266.1
137.5°	277.7	278.3	278.8	279.0	278.8	278.7	278.5	278.3
140°	285.8	286.4	286.8	287.0	286.7	286.5	286.1	285.8
142.5°	293.3	293.8	294.3	294.4	294.1	293.8	293.5	293.2
145°	303.8	304.2	304.6	304.7	304.4	304.1	303.8	303.5
147.5°	312.9	313.2	313.5	313.5	313.3	313.1	312.8	312.6
150°	318.5	318.9	319.2	319.2	319.0	318.7	318.4	318.1
152.5°	323.7	324.0	324.3	324.3	323.9	323.6	323.2	322.8
155°	330.6	330.9	331.3	331.2	330.7	330.3	329.9	329.4
157.5°	336.4	336.8	337.2	337.2	336.7	336.3	335.8	335.4
160°	339.8	340.2	340.5	340.5	340.1	339.7	339.3	338.9
162.5°	342.9	343.3	343.7	343.7	343.2	342.7	342.2	341.7
165°	346.8	347.2	347.6	347.6	347.2	346.8	346.4	346.0
167.5°	350.1	350.5	350.9	350.8	350.3	349.7	349.3	348.7
170°	351.7	352.1	352.5	352.4	352.0	351.4	350.9	350.4
172.5°	352.9	353.3	353.7	353.7	353.2	352.7	352.1	351.6
175°	354.3	354.7	355.1	355.0	354.4	353.9	353.2	352.7
177.5°	354.4	354.7	355.1	355.0	354.6	354.2	353.8	353.4
180°	353.9	353.9	353.9	353.9	353.9	353.9	353.9	353.9

(END OF REPORT)