

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P333296-840

Luminaire Tested: **S125DIP-S1270D365U840-4F0-1E-UDD-A1**

Issue Date: 3/3/2020

Test Information

Test Method: LM-79-08
Report Number: P333296-840
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-11,
Test Lab: INNOVATION CENTER
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: NEO-RAY
Catalog Number: S125DIP-S1270D365U840-4F0-1E-UDD-A1
Description: DEFINE 5 DIRECT-INDIRECT PENDANT LED LUMINAIRE
DOWNLIGHT 1270 LUMENS PER FOOT, ASYMMETRIC DIFFUSER
UPLIGHT 365 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER
Light Source: -
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 6514.4 lumens
Efficiency: N/A
Efficacy: 130.8 lumens/watt
Spacing Criteria (0/90/45): 1.43 / 1.23 / 1.52
Luminous Opening: Rectangular (W 4' x L: 0.42' x H: 0')
CIE Type: Semi-Direct


Input Watts (W): 49.8
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P333296-840

CATALOG NUMBER: S125DIP-S1270D365U840-4F0-1E-UDD-A1

Luminous Intensity Polar Plot





TEST NUMBER: P333296-840

CATALOG NUMBER: S125DIP-S1270D365U840-4F0-1E-UDD-A1

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20					20					20					20					20	
RC	80					70					50					30					10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0	
RCR																						
0	114	114	114	114	109	109	109	109	100	100	100	92	92	92	84	84	84	80				
1	105	101	97	93	100	96	93	90	89	86	83	81	79	77	75	73	72	68				
2	96	88	82	77	92	85	79	74	78	74	70	72	68	65	66	63	61	58				
3	88	78	70	64	84	75	68	63	69	64	59	64	59	56	59	55	52	49				
4	80	69	61	55	77	67	59	53	62	56	51	57	52	48	53	49	45	43				
5	74	62	54	47	71	60	52	46	55	49	44	52	46	42	48	43	40	37				
6	68	56	47	41	65	54	46	40	50	44	39	47	41	37	43	39	35	33				
7	63	51	42	37	61	49	41	36	46	39	34	43	37	33	40	35	31	29				
8	59	46	38	33	56	45	37	32	42	35	31	39	33	29	36	32	28	26				
9	55	42	34	29	53	41	34	29	38	32	27	36	30	26	34	29	25	23				
10	52	39	31	26	49	38	31	26	35	29	25	33	28	24	31	26	23	21				

AVERAGE LUMINANCE (cd/sqm):

	0°	90°	180°	270°
0°	11978	11978	11978	11978
5°	13871	12019	10524	12019
10°	16138	11956	9220	11956
15°	17864	11869	8505	11869
20°	19996	11730	7932	11730
25°	23426	11573	7652	11573
30°	25302	11419	7409	11419
35°	20805	11129	7250	11129
40°	14787	10725	7075	10725
45°	11359	10181	6974	10181
50°	9697	9507	6961	9507
55°	8634	8847	7020	8847
60°	7789	8123	7198	8123
65°	7195	7398	7386	7398
70°	6541	6643	7493	6643
75°	5777	5854	7426	5854
80°	4861	4775	6791	4775
85°	3846	3446	5483	3446



TEST NUMBER: P333296-840

CATALOG NUMBER: S125DIP-S1270D365U840-4F0-1E-UDD-A1

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	178.6	2.7
10°-20°	531.6	8.2
20°-30°	863.2	13.3
30°-40°	1053.0	16.2
40°-50°	957.9	14.7
50°-60°	763.0	11.7
60°-70°	531.4	8.2
70°-80°	283.4	4.4
80°-90°	72.5	1.1
90°-100°	30.7	0.5
100°-110°	90.7	1.4
110°-120°	153.6	2.4
120°-130°	202.2	3.1
130°-140°	226.6	3.5
140°-150°	222.1	3.4
150°-160°	186.5	2.9
160°-170°	124.0	1.9
170°-180°	43.4	0.7
0°-30°	1573.4	24.2
0°-40°	2626.3	40.3
0°-60°	4347.2	66.7
0°-90°	5234.6	80.4
90°-120°	275.1	4.2
90°-150°	925.9	14.2
90°-180°	1280.0	19.6
0°-180°	6514.4	100.0

CANDELA DISTRIBUTION:

	0°	90°	180°	270°	360°	Flux
0°	1855	1855	1855	1855	1855	
5°	2140	1854	1623	1854	2140	216
15°	2672	1775	1272	1775	2672	765
25°	3287	1624	1074	1624	3287	1502
35°	2639	1412	920	1412	2639	1615
45°	1244	1115	764	1115	1244	995
55°	767	786	624	786	767	691
65°	471	484	483	484	471	467
75°	232	235	298	235	232	249
85°	52	46	74	46	52	60
90°	9	0	9	0	9	7
95°	31	23	31	23	31	31
105°	89	81	89	81	89	94
115°	155	154	155	154	155	154
125°	226	224	226	224	226	202
135°	293	292	293	292	293	226
145°	355	354	355	354	355	222
155°	405	405	405	405	405	186
165°	439	440	439	440	439	124
175°	456	458	456	458	456	43
180°	459	459	459	459	459	



TEST NUMBER: P333296-840

CATALOG NUMBER: S125DIP-S1270D365U840-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	1854.7	1854.7	1854.7	1854.7	1854.7	1854.7	1854.7	1854.7	1854.7	1854.7	1854.7
2.5°	1961.8	1959.2	1956.7	1951.7	1955.4	1944.7	1939.6	1930.9	1920.2	1916.4	1912.0
5°	2139.6	2143.5	2147.5	2131.0	2132.5	2121.5	2096.4	2075.9	2059.3	2038.1	2023.2
7.5°	2353.8	2344.5	2343.7	2333.0	2314.6	2299.8	2273.3	2239.6	2207.1	2169.9	2139.2
10°	2460.8	2461.6	2454.6	2442.0	2422.3	2408.1	2373.5	2340.4	2300.3	2253.0	2219.2
12.5°	2541.4	2544.8	2535.8	2518.8	2509.1	2477.4	2450.2	2411.0	2363.2	2325.4	2273.9
15°	2671.8	2663.1	2656.9	2635.5	2619.1	2586.0	2542.7	2501.7	2449.8	2401.8	2353.8
17.5°	2797.4	2804.4	2792.6	2773.2	2721.9	2683.3	2625.2	2569.1	2504.5	2440.0	2382.8
20°	2909.5	2915.9	2897.7	2863.9	2802.5	2763.9	2687.6	2615.1	2540.3	2457.7	2394.7
22.5°	3049.4	3044.3	3019.9	2968.4	2915.2	2843.9	2761.3	2673.0	2579.4	2486.0	2402.3
25°	3287.4	3254.3	3239.3	3175.6	3105.5	3000.8	2887.5	2758.3	2641.9	2518.3	2411.3
27.5°	3419.3	3408.9	3392.2	3347.9	3274.2	3162.2	3028.6	2871.2	2706.9	2550.9	2410.7
30°	3392.8	3394.5	3396.1	3381.8	3334.7	3250.4	3117.4	2948.1	2752.9	2577.4	2415.2
32.5°	3158.7	3187.2	3214.7	3247.1	3260.3	3244.1	3160.8	3008.0	2807.0	2607.6	2412.7
35°	2638.8	2647.4	2736.3	2824.5	2944.2	3037.1	3099.3	3031.5	2862.3	2633.2	2409.6
37.5°	2057.5	2100.0	2161.5	2261.2	2433.9	2588.5	2787.3	2878.8	2824.2	2641.6	2404.2
40°	1753.9	1793.3	1833.4	1935.0	2080.6	2268.0	2493.9	2686.7	2731.6	2615.1	2385.3
42.5°	1519.6	1550.8	1595.4	1671.7	1793.4	1959.3	2175.2	2427.3	2582.3	2538.3	2345.6
45°	1243.7	1263.4	1298.1	1358.8	1446.9	1576.8	1767.3	2042.9	2282.9	2362.4	2251.4
47.5°	1064.6	1064.5	1091.4	1133.3	1196.9	1307.3	1448.1	1664.1	1920.5	2110.2	2101.4
50°	965.1	961.2	982.4	1018.7	1069.0	1142.3	1276.9	1449.3	1695.7	1910.6	1970.3
52.5°	879.5	879.9	893.0	919.8	962.0	1024.5	1125.1	1280.5	1491.0	1711.5	1824.3
55°	766.8	763.6	778.5	796.7	827.4	868.3	940.7	1059.6	1230.4	1447.6	1594.1
57.5°	663.5	672.2	678.1	690.7	716.2	743.6	804.7	891.9	1027.4	1213.9	1368.7
60°	603.0	611.7	616.4	628.9	649.4	673.1	720.3	791.1	905.3	1065.9	1219.4
62.5°	548.9	555.6	557.1	568.6	585.2	608.2	645.4	704.9	795.1	935.5	1085.9
65°	470.8	470.8	473.9	485.7	493.6	514.0	542.4	585.7	658.1	767.5	895.9
67.5°	395.5	399.3	398.5	403.6	410.9	426.9	447.2	482.9	536.5	616.4	719.0
70°	346.4	349.5	348.7	352.6	360.5	370.8	387.3	421.1	459.7	528.3	616.4
72.5°	302.3	303.6	301.5	306.7	311.4	320.4	338.8	356.9	392.9	450.8	523.2
75°	231.5	233.0	234.6	237.7	242.5	247.2	256.6	274.8	298.3	341.6	388.1
77.5°	173.5	170.5	174.3	173.8	176.5	180.2	188.4	198.0	217.4	244.8	280.7
80°	130.7	131.5	131.5	132.3	136.2	138.6	145.6	152.7	167.6	188.1	213.4
82.5°	95.4	97.5	96.2	97.7	100.9	102.6	106.5	112.4	121.1	137.1	155.4
85°	51.9	48.1	49.6	51.2	51.2	51.9	55.1	57.5	62.2	68.5	75.5
87.5°	16.9	18.1	18.6	18.6	19.2	19.1	21.5	21.4	23.2	25.0	27.5
90°	8.6	8.3	8.1	7.9	7.6	7.3	6.9	6.5	6.1	5.8	5.2
92.5°	16.9	16.7	16.5	16.4	16.2	15.8	15.2	14.7	14.2	13.7	13.0
95°	30.7	30.5	30.4	30.2	30.1	29.7	29.2	28.6	28.1	27.5	26.7
97.5°	46.6	46.5	46.4	46.3	46.2	45.8	45.3	44.8	44.3	43.7	42.6
100°	58.6	58.4	58.3	58.1	57.9	57.5	56.8	56.0	55.3	54.6	53.6
102.5°	70.5	70.3	70.1	69.9	69.7	69.2	68.4	67.6	66.9	66.0	65.5
105°	88.6	88.3	88.1	87.8	87.6	87.3	86.7	86.2	85.7	85.3	84.8
107.5°	106.9	106.9	106.9	106.9	107.0	106.8	106.6	106.4	106.1	105.9	105.5
110°	120.7	120.7	120.8	120.9	121.0	120.9	120.7	120.4	120.2	120.0	119.7



TEST NUMBER: P333296-840

CATALOG NUMBER: S125DIP-S1270D365U840-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	134.1	134.2	134.3	134.5	134.6	134.6	134.5	134.4	134.3	134.2	133.9
115°	155.2	155.3	155.4	155.5	155.6	155.6	155.7	155.8	155.9	156.0	155.8
117.5°	175.9	176.3	176.6	176.9	177.2	177.3	177.3	177.2	177.1	177.1	176.9
120°	190.3	190.6	190.9	191.2	191.5	191.7	191.7	191.7	191.7	191.7	191.6
122.5°	204.5	204.8	205.0	205.3	205.5	205.7	205.7	205.8	205.9	205.9	205.7
125°	225.9	226.0	226.1	226.2	226.2	226.4	226.5	226.7	226.8	227.0	226.9
127.5°	246.5	246.6	246.8	247.0	247.1	247.2	247.3	247.4	247.5	247.5	247.5
130°	260.2	260.3	260.5	260.6	260.8	260.9	261.1	261.2	261.2	261.3	261.2
132.5°	273.1	273.3	273.5	273.7	274.0	274.1	274.2	274.3	274.3	274.4	274.5
135°	293.1	293.4	293.7	294.0	294.3	294.5	294.5	294.5	294.5	294.5	294.4
137.5°	312.6	313.0	313.4	313.8	314.2	314.4	314.3	314.2	314.1	314.0	313.8
140°	325.2	325.6	326.0	326.4	326.8	326.9	326.7	326.6	326.4	326.2	326.0
142.5°	337.2	337.6	337.9	338.3	338.7	338.9	338.8	338.7	338.6	338.5	338.2
145°	355.2	355.4	355.6	355.9	356.1	356.2	356.2	356.2	356.2	356.2	356.0
147.5°	370.5	371.0	371.5	372.1	372.6	372.8	372.6	372.4	372.2	372.0	371.8
150°	381.9	382.0	382.2	382.4	382.5	382.6	382.6	382.6	382.6	382.6	382.3
152.5°	391.3	391.6	391.9	392.2	392.4	392.5	392.3	392.1	391.9	391.7	391.6
155°	404.8	405.2	405.6	406.0	406.4	406.4	406.1	405.8	405.5	405.2	405.1
157.5°	416.0	416.5	417.0	417.6	418.1	418.2	417.9	417.5	417.2	416.9	416.8
160°	423.6	424.0	424.4	424.9	425.3	425.3	425.0	424.6	424.3	424.0	423.9
162.5°	430.2	430.7	431.1	431.6	432.1	432.1	431.7	431.3	431.0	430.6	430.6
165°	439.0	439.5	440.0	440.4	440.9	441.0	440.7	440.4	440.1	439.7	439.7
167.5°	446.1	446.5	447.0	447.5	448.0	448.0	447.5	447.1	446.6	446.1	446.1
170°	449.7	450.3	450.8	451.4	451.9	452.0	451.5	451.0	450.6	450.1	450.1
172.5°	452.8	453.3	453.8	454.3	454.8	454.8	454.3	453.9	453.4	452.9	452.9
175°	455.8	456.4	456.9	457.5	458.0	458.1	457.6	457.1	456.7	456.2	456.2
177.5°	457.5	458.0	458.4	458.9	459.3	459.3	459.0	458.6	458.2	457.8	457.9
180°	458.7	458.7	458.7	458.7	458.7	458.7	458.7	458.7	458.7	458.7	458.7



TEST NUMBER: P333296-840

CATALOG NUMBER: S125DIP-S1270D365U840-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°	95°	100°	105°
0°	1854.7	1854.7	1854.7	1854.7	1854.7	1854.7	1854.7	1854.7	1854.7	1854.7	1854.7
2.5°	1908.2	1903.8	1898.7	1890.0	1879.3	1873.6	1864.7	1859.1	1847.8	1838.3	1828.3
5°	2005.0	1984.6	1965.7	1941.3	1914.5	1897.1	1876.7	1853.9	1830.3	1805.8	1779.1
7.5°	2105.4	2069.1	2029.7	1987.4	1946.0	1907.8	1871.5	1835.7	1802.4	1762.1	1728.0
10°	2172.7	2127.1	2078.2	2020.7	1964.9	1916.1	1866.4	1823.2	1779.1	1731.8	1690.1
12.5°	2240.1	2179.3	2110.3	2047.2	1980.0	1921.1	1862.7	1807.5	1752.0	1699.7	1651.1
15°	2287.6	2234.1	2170.3	2080.6	2005.0	1924.0	1846.8	1775.1	1708.3	1650.0	1588.6
17.5°	2319.0	2250.0	2181.5	2095.4	1996.4	1905.7	1818.3	1736.3	1660.8	1587.0	1527.8
20°	2324.6	2253.8	2182.1	2097.9	1996.4	1892.5	1805.0	1706.7	1625.6	1549.2	1476.8
22.5°	2322.8	2242.4	2164.5	2077.8	1978.7	1883.0	1777.4	1677.1	1589.0	1514.0	1438.4
25°	2304.9	2219.2	2121.5	2034.2	1936.5	1835.0	1728.0	1624.1	1534.3	1448.4	1373.7
27.5°	2290.2	2178.9	2068.3	1966.4	1872.2	1779.1	1676.6	1570.1	1470.7	1383.7	1313.2
30°	2271.9	2149.9	2025.5	1919.2	1822.4	1731.8	1635.1	1531.2	1427.2	1342.2	1266.7
32.5°	2255.5	2113.3	1982.1	1866.3	1763.8	1675.8	1586.5	1487.6	1385.6	1299.4	1223.8
35°	2223.9	2059.3	1908.9	1778.3	1668.9	1578.3	1503.6	1411.5	1317.8	1234.4	1162.0
37.5°	2183.7	1988.5	1827.1	1690.1	1570.1	1474.8	1405.1	1334.4	1244.6	1164.2	1098.6
40°	2152.2	1938.1	1767.3	1627.2	1502.8	1403.6	1339.1	1272.1	1197.4	1122.6	1053.3
42.5°	2112.5	1892.8	1706.9	1556.0	1432.9	1336.3	1268.5	1211.6	1145.7	1076.0	1011.7
45°	2039.6	1810.6	1609.0	1446.9	1322.5	1227.3	1157.2	1114.7	1065.1	999.0	944.6
47.5°	1932.5	1711.8	1503.4	1336.1	1207.7	1119.4	1053.8	1013.0	978.1	928.9	879.6
50°	1837.3	1638.2	1427.2	1261.1	1132.8	1043.8	983.2	946.2	916.4	878.5	836.8
52.5°	1730.9	1545.6	1352.3	1188.1	1061.0	973.3	913.9	881.4	856.5	829.4	788.3
55°	1561.9	1404.4	1224.9	1069.0	951.7	866.0	814.0	785.7	765.2	744.7	719.5
57.5°	1375.5	1252.4	1093.5	951.0	842.9	764.9	716.4	688.8	672.9	662.4	647.5
60°	1244.6	1139.1	1002.1	872.2	766.8	697.5	650.3	628.9	615.6	606.9	595.9
62.5°	1123.1	1036.4	909.6	791.0	698.7	633.2	591.1	570.4	557.6	553.4	544.3
65°	943.8	877.0	772.2	673.9	595.1	539.3	503.8	484.1	476.3	471.5	472.3
67.5°	767.4	726.6	642.5	558.6	495.7	448.9	420.5	405.5	401.5	395.2	395.1
70°	659.6	628.9	558.2	484.9	429.0	392.8	367.6	351.8	347.9	344.8	344.1
72.5°	564.6	537.7	476.3	417.6	367.3	335.5	314.8	305.3	298.8	296.9	296.8
75°	424.3	409.4	360.5	314.1	279.4	257.4	243.3	234.6	229.8	229.0	229.8
77.5°	301.6	288.6	257.6	224.7	202.8	186.1	174.1	171.2	165.8	165.9	165.1
80°	226.7	218.0	198.3	172.4	154.3	140.2	133.8	128.4	126.7	124.4	126.7
82.5°	164.4	155.1	141.7	125.1	110.2	101.7	95.4	93.7	92.7	91.6	92.1
85°	81.1	81.9	74.0	61.4	55.1	50.4	46.5	46.5	45.6	44.8	45.6
87.5°	28.7	27.3	24.6	22.6	19.4	17.4	16.6	17.1	15.3	14.8	15.6
90°	4.6	4.0	3.5	2.9	2.2	1.6	1.0	0.4	1.0	1.6	2.2
92.5°	12.3	11.6	11.0	10.4	10.0	9.5	9.1	8.7	9.1	9.5	10.0
95°	25.9	25.1	24.3	23.8	23.6	23.5	23.3	23.2	23.3	23.5	23.6
97.5°	41.6	40.5	39.4	38.8	38.8	38.7	38.6	38.6	38.6	38.7	38.8
100°	52.5	51.5	50.5	50.0	50.0	50.0	50.0	50.0	50.0	50.0	50.0
102.5°	64.9	64.4	63.9	63.5	63.2	62.9	62.6	62.2	62.6	62.9	63.2
105°	84.3	83.9	83.4	83.0	82.6	82.2	81.8	81.4	81.8	82.2	82.6
107.5°	105.2	104.8	104.5	104.1	103.7	103.3	102.9	102.5	102.9	103.3	103.7
110°	119.5	119.2	119.0	118.7	118.3	117.9	117.4	117.0	117.4	117.9	118.3



TEST NUMBER: P333296-840

CATALOG NUMBER: S125DIP-S1270D365U840-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°	95°	100°	105°
112.5°	133.6	133.3	133.0	132.7	132.5	132.3	132.1	131.9	132.1	132.3	132.5
115°	155.6	155.5	155.3	155.1	154.8	154.5	154.1	153.8	154.1	154.5	154.8
117.5°	176.8	176.7	176.5	176.4	176.2	176.1	175.9	175.8	175.9	176.1	176.2
120°	191.5	191.5	191.4	191.1	190.8	190.4	190.0	189.6	190.0	190.4	190.8
122.5°	205.5	205.3	205.1	204.9	204.8	204.7	204.5	204.4	204.5	204.7	204.8
125°	226.8	226.8	226.7	226.4	225.9	225.5	225.0	224.5	225.0	225.5	225.9
127.5°	247.4	247.3	247.2	247.0	246.7	246.5	246.2	245.9	246.2	246.5	246.7
130°	260.9	260.7	260.6	260.3	259.9	259.5	259.1	258.7	259.1	259.5	259.9
132.5°	274.5	274.5	274.6	274.2	273.6	273.0	272.3	271.7	272.3	273.0	273.6
135°	294.3	294.3	294.2	293.9	293.4	293.0	292.5	292.0	292.5	293.0	293.4
137.5°	313.6	313.5	313.3	313.0	312.5	312.0	311.5	311.1	311.5	312.0	312.5
140°	325.8	325.5	325.3	325.0	324.6	324.2	323.8	323.4	323.8	324.2	324.6
142.5°	337.9	337.6	337.3	337.0	336.7	336.3	336.0	335.7	336.0	336.3	336.7
145°	355.8	355.5	355.3	355.0	354.7	354.4	354.1	353.8	354.1	354.4	354.7
147.5°	371.7	371.5	371.3	371.1	370.9	370.7	370.6	370.4	370.6	370.7	370.9
150°	382.0	381.6	381.3	381.2	381.3	381.4	381.5	381.5	381.5	381.4	381.3
152.5°	391.5	391.4	391.2	391.1	391.0	390.9	390.8	390.7	390.8	390.9	391.0
155°	405.0	404.9	404.8	404.8	404.8	404.8	404.8	404.8	404.8	404.8	404.8
157.5°	416.8	416.7	416.6	416.7	416.8	417.0	417.2	417.3	417.2	417.0	416.8
160°	423.8	423.8	423.7	423.8	424.0	424.2	424.5	424.7	424.5	424.2	424.0
162.5°	430.6	430.5	430.5	430.6	430.8	431.0	431.1	431.3	431.1	431.0	430.8
165°	439.6	439.5	439.4	439.5	439.6	439.8	439.9	440.1	439.9	439.8	439.6
167.5°	446.1	446.1	446.1	446.3	446.6	446.9	447.2	447.5	447.2	446.9	446.6
170°	450.1	450.1	450.1	450.2	450.6	450.9	451.2	451.5	451.2	450.9	450.6
172.5°	452.9	452.9	452.9	453.1	453.4	453.7	454.0	454.3	454.0	453.7	453.4
175°	456.2	456.2	456.2	456.4	456.7	457.0	457.3	457.6	457.3	457.0	456.7
177.5°	458.0	458.0	458.1	458.2	458.5	458.7	459.0	459.2	459.0	458.7	458.5
180°	458.7	458.7	458.7	458.7	458.7	458.7	458.7	458.7	458.7	458.7	458.7



TEST NUMBER: P333296-840

CATALOG NUMBER: S125DIP-S1270D365U840-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	110°	115°	120°	125°	130°	135°	140°	145°	150°	155°	160°
0°	1854.7	1854.7	1854.7	1854.7	1854.7	1854.7	1854.7	1854.7	1854.7	1854.7	1854.7
2.5°	1822.5	1815.6	1810.0	1797.4	1790.4	1781.0	1773.4	1781.6	1772.8	1776.6	1770.9
5°	1765.7	1743.6	1728.0	1705.1	1685.5	1667.3	1654.0	1651.5	1645.3	1642.1	1632.6
7.5°	1697.4	1669.8	1642.7	1612.9	1587.6	1562.0	1545.6	1532.1	1523.1	1511.3	1503.3
10°	1657.1	1620.1	1588.6	1552.4	1520.9	1493.4	1471.3	1460.3	1450.1	1435.1	1429.6
12.5°	1607.3	1569.0	1530.7	1492.0	1461.7	1431.0	1412.1	1395.4	1388.4	1371.5	1369.8
15°	1547.6	1490.2	1452.4	1413.0	1371.3	1346.2	1330.4	1312.3	1304.4	1292.6	1283.9
17.5°	1476.5	1425.1	1378.0	1337.2	1301.4	1280.2	1260.6	1248.2	1234.7	1227.0	1212.7
20°	1424.8	1376.0	1328.8	1285.6	1258.0	1233.6	1217.8	1206.0	1191.8	1187.9	1173.8
22.5°	1381.4	1327.6	1282.2	1245.9	1215.8	1188.2	1171.2	1163.2	1153.5	1141.3	1138.4
25°	1310.7	1254.9	1216.3	1180.0	1153.3	1128.1	1116.3	1106.0	1096.6	1087.9	1084.8
27.5°	1249.6	1199.7	1153.9	1121.2	1097.8	1074.9	1064.5	1052.1	1045.1	1038.1	1029.7
30°	1206.8	1155.6	1115.5	1084.0	1058.8	1038.3	1027.3	1018.7	1012.4	1006.0	1001.4
32.5°	1162.8	1115.3	1076.4	1045.6	1020.4	1004.9	995.2	989.1	982.1	974.5	968.6
35°	1104.5	1052.5	1014.7	988.0	968.3	956.4	945.4	939.9	932.1	932.1	925.7
37.5°	1038.8	993.9	960.6	936.1	918.5	908.0	896.1	892.2	887.2	883.8	881.7
40°	999.8	958.1	926.6	902.1	883.2	874.5	865.2	858.9	855.7	851.7	850.2
42.5°	959.5	919.6	889.4	866.9	850.5	843.1	834.2	829.9	823.5	818.4	817.5
45°	898.2	859.6	832.1	814.0	799.8	791.1	785.7	776.2	773.1	766.8	766.0
47.5°	840.1	803.1	776.1	761.2	748.8	741.7	733.1	723.6	720.0	716.8	716.5
50°	796.7	762.9	737.6	723.5	711.7	701.5	692.8	686.4	684.1	684.1	685.7
52.5°	752.6	723.8	702.4	685.0	673.9	663.0	655.0	651.2	647.5	651.4	654.2
55°	688.0	658.9	643.2	626.6	615.6	603.0	599.1	597.5	595.1	601.5	604.6
57.5°	619.7	599.3	580.8	564.4	554.5	547.2	541.9	541.0	545.4	548.4	558.6
60°	576.2	552.6	536.1	523.5	511.7	507.0	505.4	503.8	507.0	515.6	529.0
62.5°	528.4	509.2	491.4	481.9	473.2	465.4	465.0	466.1	472.3	482.2	495.6
65°	458.2	441.6	429.8	418.8	411.7	407.0	408.6	411.7	418.8	432.2	447.2
67.5°	386.9	375.5	365.0	356.0	349.2	349.2	350.8	355.5	363.9	379.3	392.9
70°	340.8	328.3	319.6	315.7	310.1	307.0	311.7	319.6	326.7	340.8	352.6
72.5°	294.9	284.2	277.4	274.8	272.4	269.8	271.5	279.9	289.5	303.7	317.4
75°	226.7	222.8	218.0	214.9	212.6	214.1	215.7	223.6	231.5	246.4	262.2
77.5°	165.5	161.4	158.5	157.7	156.5	157.2	161.7	167.5	175.2	186.1	198.0
80°	125.1	123.6	122.0	121.2	121.2	122.0	128.4	132.3	139.4	149.6	159.1
82.5°	91.2	90.2	89.9	89.8	90.4	90.5	94.3	99.5	105.3	113.0	121.2
85°	48.1	46.5	48.8	49.6	48.1	50.4	51.9	55.1	57.5	61.4	65.3
87.5°	16.4	17.7	17.2	17.9	18.1	19.4	18.9	21.4	22.8	24.1	23.5
90°	2.9	3.5	4.0	4.6	5.2	5.8	6.1	6.5	6.9	7.3	7.6
92.5°	10.4	11.0	11.6	12.3	13.0	13.7	14.2	14.7	15.2	15.8	16.2
95°	23.8	24.3	25.1	25.9	26.7	27.5	28.1	28.6	29.2	29.7	30.1
97.5°	38.8	39.4	40.5	41.6	42.6	43.7	44.3	44.8	45.3	45.8	46.2
100°	50.0	50.5	51.5	52.5	53.6	54.6	55.3	56.0	56.8	57.5	57.9
102.5°	63.5	63.9	64.4	64.9	65.5	66.0	66.9	67.6	68.4	69.2	69.7
105°	83.0	83.4	83.9	84.3	84.8	85.3	85.7	86.2	86.7	87.3	87.6
107.5°	104.1	104.5	104.8	105.2	105.5	105.9	106.1	106.4	106.6	106.8	107.0
110°	118.7	119.0	119.2	119.5	119.7	120.0	120.2	120.4	120.7	120.9	121.0



TEST NUMBER: P333296-840

CATALOG NUMBER: S125DIP-S1270D365U840-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	110°	115°	120°	125°	130°	135°	140°	145°	150°	155°	160°
112.5°	132.7	133.0	133.3	133.6	133.9	134.2	134.3	134.4	134.5	134.6	134.6
115°	155.1	155.3	155.5	155.6	155.8	156.0	155.9	155.8	155.7	155.6	155.6
117.5°	176.4	176.5	176.7	176.8	176.9	177.1	177.1	177.2	177.3	177.3	177.2
120°	191.1	191.4	191.5	191.5	191.6	191.7	191.7	191.7	191.7	191.7	191.5
122.5°	204.9	205.1	205.3	205.5	205.7	205.9	205.9	205.8	205.7	205.7	205.5
125°	226.4	226.7	226.8	226.8	226.9	227.0	226.8	226.7	226.5	226.4	226.2
127.5°	247.0	247.2	247.3	247.4	247.5	247.5	247.5	247.4	247.3	247.2	247.1
130°	260.3	260.6	260.7	260.9	261.2	261.3	261.2	261.2	261.1	260.9	260.8
132.5°	274.2	274.6	274.5	274.5	274.5	274.4	274.3	274.3	274.2	274.1	274.0
135°	293.9	294.2	294.3	294.3	294.4	294.5	294.5	294.5	294.5	294.5	294.3
137.5°	313.0	313.3	313.5	313.6	313.8	314.0	314.1	314.2	314.3	314.4	314.2
140°	325.0	325.3	325.5	325.8	326.0	326.2	326.4	326.6	326.7	326.9	326.8
142.5°	337.0	337.3	337.6	337.9	338.2	338.5	338.6	338.7	338.8	338.9	338.7
145°	355.0	355.3	355.5	355.8	356.0	356.2	356.2	356.2	356.2	356.2	356.1
147.5°	371.1	371.3	371.5	371.7	371.8	372.0	372.2	372.4	372.6	372.8	372.6
150°	381.2	381.3	381.6	382.0	382.3	382.6	382.6	382.6	382.6	382.6	382.5
152.5°	391.1	391.2	391.4	391.5	391.6	391.7	391.9	392.1	392.3	392.5	392.4
155°	404.8	404.8	404.9	405.0	405.1	405.2	405.5	405.8	406.1	406.4	406.4
157.5°	416.7	416.6	416.7	416.8	416.8	416.9	417.2	417.5	417.9	418.2	418.1
160°	423.8	423.7	423.8	423.8	423.9	424.0	424.3	424.6	425.0	425.3	425.3
162.5°	430.6	430.5	430.5	430.6	430.6	430.6	431.0	431.3	431.7	432.1	432.1
165°	439.5	439.4	439.5	439.6	439.7	439.7	440.1	440.4	440.7	441.0	440.9
167.5°	446.3	446.1	446.1	446.1	446.1	446.1	446.6	447.1	447.5	448.0	448.0
170°	450.2	450.1	450.1	450.1	450.1	450.1	450.6	451.0	451.5	452.0	451.9
172.5°	453.1	452.9	452.9	452.9	452.9	452.9	453.4	453.9	454.3	454.8	454.8
175°	456.4	456.2	456.2	456.2	456.2	456.2	456.7	457.1	457.6	458.1	458.0
177.5°	458.2	458.1	458.0	458.0	457.9	457.8	458.2	458.6	459.0	459.3	459.3
180°	458.7	458.7	458.7	458.7	458.7	458.7	458.7	458.7	458.7	458.7	458.7



TEST NUMBER: P333296-840

CATALOG NUMBER: S125DIP-S1270D365U840-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	165°	170°	175°	180°	185°	190°	195°	200°	205°	210°	215°
0°	1854.7	1854.7	1854.7	1854.7	1854.7	1854.7	1854.7	1854.7	1854.7	1854.7	1854.7
2.5°	1767.2	1771.5	1767.8	1772.8	1767.8	1771.5	1767.2	1770.9	1776.6	1772.8	1781.6
5°	1628.7	1621.6	1626.4	1623.3	1626.4	1621.6	1628.7	1632.6	1642.1	1645.3	1651.5
7.5°	1500.9	1494.1	1486.4	1482.8	1486.4	1494.1	1500.9	1503.3	1511.3	1523.1	1532.1
10°	1420.9	1412.3	1411.5	1405.9	1411.5	1412.3	1420.9	1429.6	1435.1	1450.1	1460.3
12.5°	1362.3	1354.3	1345.3	1343.0	1345.3	1354.3	1362.3	1369.8	1371.5	1388.4	1395.4
15°	1279.2	1272.9	1267.4	1272.1	1267.4	1272.9	1279.2	1283.9	1292.6	1304.4	1312.3
17.5°	1210.1	1204.9	1204.0	1198.1	1204.0	1204.9	1210.1	1212.7	1227.0	1234.7	1248.2
20°	1166.7	1162.8	1164.3	1154.1	1164.3	1162.8	1166.7	1173.8	1187.9	1191.8	1206.0
22.5°	1132.1	1124.3	1123.4	1121.4	1123.4	1124.3	1132.1	1138.4	1141.3	1153.5	1163.2
25°	1077.7	1073.8	1069.9	1073.8	1069.9	1073.8	1077.7	1084.8	1087.9	1096.6	1106.0
27.5°	1030.3	1025.6	1024.5	1024.9	1024.5	1025.6	1030.3	1029.7	1038.1	1045.1	1052.1
30°	1001.4	993.5	994.2	993.5	994.2	993.5	1001.4	1001.4	1006.0	1012.4	1018.7
32.5°	969.9	964.5	963.4	962.0	963.4	964.5	969.9	968.6	974.5	982.1	989.1
35°	923.4	923.4	919.5	919.5	919.5	923.4	923.4	925.7	932.1	932.1	939.9
37.5°	879.8	879.0	876.7	877.0	876.7	879.0	879.8	881.7	883.8	887.2	892.2
40°	847.1	846.3	843.8	839.2	843.8	846.3	847.1	850.2	851.7	855.7	858.9
42.5°	815.6	812.8	811.7	810.2	811.7	812.8	815.6	817.5	818.4	823.5	829.9
45°	766.0	766.0	764.4	763.6	764.4	766.0	766.0	766.0	766.8	773.1	776.2
47.5°	717.8	719.2	722.2	721.8	722.2	719.2	717.8	716.5	716.8	720.0	723.6
50°	688.8	689.6	692.0	692.8	692.0	689.6	688.8	685.7	684.1	684.1	686.4
52.5°	656.7	661.3	664.3	663.8	664.3	661.3	656.7	654.2	651.4	647.5	651.2
55°	611.7	617.1	622.7	623.5	622.7	617.1	611.7	604.6	601.5	595.1	597.5
57.5°	567.1	574.8	580.7	582.5	580.7	574.8	567.1	558.6	548.4	545.4	541.0
60°	536.8	547.1	554.2	557.3	554.2	547.1	536.8	529.0	515.6	507.0	503.8
62.5°	507.9	519.4	526.4	527.1	526.4	519.4	507.9	495.6	482.2	472.3	466.1
65°	460.5	472.3	478.6	483.3	478.6	472.3	460.5	447.2	432.2	418.8	411.7
67.5°	409.5	421.3	428.3	432.0	428.3	421.3	409.5	392.9	379.3	363.9	355.5
70°	372.3	384.2	393.6	396.8	393.6	384.2	372.3	352.6	340.8	326.7	319.6
72.5°	335.8	346.4	354.0	357.7	354.0	346.4	335.8	317.4	303.7	289.5	279.9
75°	272.4	286.5	293.7	297.6	293.7	286.5	272.4	262.2	246.4	231.5	223.6
77.5°	210.1	223.0	227.2	229.2	227.2	223.0	210.1	198.0	186.1	175.2	167.5
80°	168.4	176.3	181.9	182.6	181.9	176.3	168.4	159.1	149.6	139.4	132.3
82.5°	129.5	136.0	137.7	139.8	137.7	136.0	129.5	121.2	113.0	105.3	99.5
85°	70.9	74.0	74.8	74.0	74.8	74.0	70.9	65.3	61.4	57.5	55.1
87.5°	24.8	24.3	24.3	25.7	24.3	24.3	24.8	23.5	24.1	22.8	21.4
90°	7.9	8.1	8.3	8.6	8.3	8.1	7.9	7.6	7.3	6.9	6.5
92.5°	16.4	16.5	16.7	16.9	16.7	16.5	16.4	16.2	15.8	15.2	14.7
95°	30.2	30.4	30.5	30.7	30.5	30.4	30.2	30.1	29.7	29.2	28.6
97.5°	46.3	46.4	46.5	46.6	46.5	46.4	46.3	46.2	45.8	45.3	44.8
100°	58.1	58.3	58.4	58.6	58.4	58.3	58.1	57.9	57.5	56.8	56.0
102.5°	69.9	70.1	70.3	70.5	70.3	70.1	69.9	69.7	69.2	68.4	67.6
105°	87.8	88.1	88.3	88.6	88.3	88.1	87.8	87.6	87.3	86.7	86.2
107.5°	106.9	106.9	106.9	106.9	106.9	106.9	106.9	107.0	106.8	106.6	106.4
110°	120.9	120.8	120.7	120.7	120.7	120.8	120.9	121.0	120.9	120.7	120.4



TEST NUMBER: P333296-840

CATALOG NUMBER: S125DIP-S1270D365U840-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	165°	170°	175°	180°	185°	190°	195°	200°	205°	210°	215°
112.5°	134.5	134.3	134.2	134.1	134.2	134.3	134.5	134.6	134.6	134.5	134.4
115°	155.5	155.4	155.3	155.2	155.3	155.4	155.5	155.6	155.6	155.7	155.8
117.5°	176.9	176.6	176.3	175.9	176.3	176.6	176.9	177.2	177.3	177.3	177.2
120°	191.2	190.9	190.6	190.3	190.6	190.9	191.2	191.5	191.7	191.7	191.7
122.5°	205.3	205.0	204.8	204.5	204.8	205.0	205.3	205.5	205.7	205.7	205.8
125°	226.2	226.1	226.0	225.9	226.0	226.1	226.2	226.2	226.4	226.5	226.7
127.5°	247.0	246.8	246.6	246.5	246.6	246.8	247.0	247.1	247.2	247.3	247.4
130°	260.6	260.5	260.3	260.2	260.3	260.5	260.6	260.8	260.9	261.1	261.2
132.5°	273.7	273.5	273.3	273.1	273.3	273.5	273.7	274.0	274.1	274.2	274.3
135°	294.0	293.7	293.4	293.1	293.4	293.7	294.0	294.3	294.5	294.5	294.5
137.5°	313.8	313.4	313.0	312.6	313.0	313.4	313.8	314.2	314.4	314.3	314.2
140°	326.4	326.0	325.6	325.2	325.6	326.0	326.4	326.8	326.9	326.7	326.6
142.5°	338.3	337.9	337.6	337.2	337.6	337.9	338.3	338.7	338.9	338.8	338.7
145°	355.9	355.6	355.4	355.2	355.4	355.6	355.9	356.1	356.2	356.2	356.2
147.5°	372.1	371.5	371.0	370.5	371.0	371.5	372.1	372.6	372.8	372.6	372.4
150°	382.4	382.2	382.0	381.9	382.0	382.2	382.4	382.5	382.6	382.6	382.6
152.5°	392.2	391.9	391.6	391.3	391.6	391.9	392.2	392.4	392.5	392.3	392.1
155°	406.0	405.6	405.2	404.8	405.2	405.6	406.0	406.4	406.4	406.1	405.8
157.5°	417.6	417.0	416.5	416.0	416.5	417.0	417.6	418.1	418.2	417.9	417.5
160°	424.9	424.4	424.0	423.6	424.0	424.4	424.9	425.3	425.3	425.0	424.6
162.5°	431.6	431.1	430.7	430.2	430.7	431.1	431.6	432.1	432.1	431.7	431.3
165°	440.4	440.0	439.5	439.0	439.5	440.0	440.4	440.9	441.0	440.7	440.4
167.5°	447.5	447.0	446.5	446.1	446.5	447.0	447.5	448.0	448.0	447.5	447.1
170°	451.4	450.8	450.3	449.7	450.3	450.8	451.4	451.9	452.0	451.5	451.0
172.5°	454.3	453.8	453.3	452.8	453.3	453.8	454.3	454.8	454.8	454.3	453.9
175°	457.5	456.9	456.4	455.8	456.4	456.9	457.5	458.0	458.1	457.6	457.1
177.5°	458.9	458.4	458.0	457.5	458.0	458.4	458.9	459.3	459.3	459.0	458.6
180°	458.7	458.7	458.7	458.7	458.7	458.7	458.7	458.7	458.7	458.7	458.7



TEST NUMBER: P333296-840

CATALOG NUMBER: S125DIP-S1270D365U840-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	220°	225°	230°	235°	240°	245°	250°	255°	260°	265°	270°
0°	1854.7	1854.7	1854.7	1854.7	1854.7	1854.7	1854.7	1854.7	1854.7	1854.7	1854.7
2.5°	1773.4	1781.0	1790.4	1797.4	1810.0	1815.6	1822.5	1828.3	1838.3	1847.8	1859.1
5°	1654.0	1667.3	1685.5	1705.1	1728.0	1743.6	1765.7	1779.1	1805.8	1830.3	1853.9
7.5°	1545.6	1562.0	1587.6	1612.9	1642.7	1669.8	1697.4	1728.0	1762.1	1802.4	1835.7
10°	1471.3	1493.4	1520.9	1552.4	1588.6	1620.1	1657.1	1690.1	1731.8	1779.1	1823.2
12.5°	1412.1	1431.0	1461.7	1492.0	1530.7	1569.0	1607.3	1651.1	1699.7	1752.0	1807.5
15°	1330.4	1346.2	1371.3	1413.0	1452.4	1490.2	1547.6	1588.6	1650.0	1708.3	1775.1
17.5°	1260.6	1280.2	1301.4	1337.2	1378.0	1425.1	1476.5	1527.8	1587.0	1660.8	1736.3
20°	1217.8	1233.6	1258.0	1285.6	1328.8	1376.0	1424.8	1476.8	1549.2	1625.6	1706.7
22.5°	1171.2	1188.2	1215.8	1245.9	1282.2	1327.6	1381.4	1438.4	1514.0	1589.0	1677.1
25°	1116.3	1128.1	1153.3	1180.0	1216.3	1254.9	1310.7	1373.7	1448.4	1534.3	1624.1
27.5°	1064.5	1074.9	1097.8	1121.2	1153.9	1199.7	1249.6	1313.2	1383.7	1470.7	1570.1
30°	1027.3	1038.3	1058.8	1084.0	1115.5	1155.6	1206.8	1266.7	1342.2	1427.2	1531.2
32.5°	995.2	1004.9	1020.4	1045.6	1076.4	1115.3	1162.8	1223.8	1299.4	1385.6	1487.6
35°	945.4	956.4	968.3	988.0	1014.7	1052.5	1104.5	1162.0	1234.4	1317.8	1411.5
37.5°	896.1	908.0	918.5	936.1	960.6	993.9	1038.8	1098.6	1164.2	1244.6	1334.4
40°	865.2	874.5	883.2	902.1	926.6	958.1	999.8	1053.3	1122.6	1197.4	1272.1
42.5°	834.2	843.1	850.5	866.9	889.4	919.6	959.5	1011.7	1076.0	1145.7	1211.6
45°	785.7	791.1	799.8	814.0	832.1	859.6	898.2	944.6	999.0	1065.1	1114.7
47.5°	733.1	741.7	748.8	761.2	776.1	803.1	840.1	879.6	928.9	978.1	1013.0
50°	692.8	701.5	711.7	723.5	737.6	762.9	796.7	836.8	878.5	916.4	946.2
52.5°	655.0	663.0	673.9	685.0	702.4	723.8	752.6	788.3	829.4	856.5	881.4
55°	599.1	603.0	615.6	626.6	643.2	658.9	688.0	719.5	744.7	765.2	785.7
57.5°	541.9	547.2	554.5	564.4	580.8	599.3	619.7	647.5	662.4	672.9	688.8
60°	505.4	507.0	511.7	523.5	536.1	552.6	576.2	595.9	606.9	615.6	628.9
62.5°	465.0	465.4	473.2	481.9	491.4	509.2	528.4	544.3	553.4	557.6	570.4
65°	408.6	407.0	411.7	418.8	429.8	441.6	458.2	472.3	471.5	476.3	484.1
67.5°	350.8	349.2	349.2	356.0	365.0	375.5	386.9	395.1	395.2	401.5	405.5
70°	311.7	307.0	310.1	315.7	319.6	328.3	340.8	344.1	344.8	347.9	351.8
72.5°	271.5	269.8	272.4	274.8	277.4	284.2	294.9	296.8	296.9	298.8	305.3
75°	215.7	214.1	212.6	214.9	218.0	222.8	226.7	229.8	229.0	229.8	234.6
77.5°	161.7	157.2	156.5	157.7	158.5	161.4	165.5	165.1	165.9	165.8	171.2
80°	128.4	122.0	121.2	121.2	122.0	123.6	125.1	126.7	124.4	126.7	128.4
82.5°	94.3	90.5	90.4	89.8	89.9	90.2	91.2	92.1	91.6	92.7	93.7
85°	51.9	50.4	48.1	49.6	48.8	46.5	48.1	45.6	44.8	45.6	46.5
87.5°	18.9	19.4	18.1	17.9	17.2	17.7	16.4	15.6	14.8	15.3	17.1
90°	6.1	5.8	5.2	4.6	4.0	3.5	2.9	2.2	1.6	1.0	0.4
92.5°	14.2	13.7	13.0	12.3	11.6	11.0	10.4	10.0	9.5	9.1	8.7
95°	28.1	27.5	26.7	25.9	25.1	24.3	23.8	23.6	23.5	23.3	23.2
97.5°	44.3	43.7	42.6	41.6	40.5	39.4	38.8	38.8	38.7	38.6	38.6
100°	55.3	54.6	53.6	52.5	51.5	50.5	50.0	50.0	50.0	50.0	50.0
102.5°	66.9	66.0	65.5	64.9	64.4	63.9	63.5	63.2	62.9	62.6	62.2
105°	85.7	85.3	84.8	84.3	83.9	83.4	83.0	82.6	82.2	81.8	81.4
107.5°	106.1	105.9	105.5	105.2	104.8	104.5	104.1	103.7	103.3	102.9	102.5
110°	120.2	120.0	119.7	119.5	119.2	119.0	118.7	118.3	117.9	117.4	117.0



TEST NUMBER: P333296-840

CATALOG NUMBER: S125DIP-S1270D365U840-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	220°	225°	230°	235°	240°	245°	250°	255°	260°	265°	270°
112.5°	134.3	134.2	133.9	133.6	133.3	133.0	132.7	132.5	132.3	132.1	131.9
115°	155.9	156.0	155.8	155.6	155.5	155.3	155.1	154.8	154.5	154.1	153.8
117.5°	177.1	177.1	176.9	176.8	176.7	176.5	176.4	176.2	176.1	175.9	175.8
120°	191.7	191.7	191.6	191.5	191.5	191.4	191.1	190.8	190.4	190.0	189.6
122.5°	205.9	205.9	205.7	205.5	205.3	205.1	204.9	204.8	204.7	204.5	204.4
125°	226.8	227.0	226.9	226.8	226.8	226.7	226.4	225.9	225.5	225.0	224.5
127.5°	247.5	247.5	247.5	247.4	247.3	247.2	247.0	246.7	246.5	246.2	245.9
130°	261.2	261.3	261.2	260.9	260.7	260.6	260.3	259.9	259.5	259.1	258.7
132.5°	274.3	274.4	274.5	274.5	274.5	274.6	274.2	273.6	273.0	272.3	271.7
135°	294.5	294.5	294.4	294.3	294.3	294.2	293.9	293.4	293.0	292.5	292.0
137.5°	314.1	314.0	313.8	313.6	313.5	313.3	313.0	312.5	312.0	311.5	311.1
140°	326.4	326.2	326.0	325.8	325.5	325.3	325.0	324.6	324.2	323.8	323.4
142.5°	338.6	338.5	338.2	337.9	337.6	337.3	337.0	336.7	336.3	336.0	335.7
145°	356.2	356.2	356.0	355.8	355.5	355.3	355.0	354.7	354.4	354.1	353.8
147.5°	372.2	372.0	371.8	371.7	371.5	371.3	371.1	370.9	370.7	370.6	370.4
150°	382.6	382.6	382.3	382.0	381.6	381.3	381.2	381.3	381.4	381.5	381.5
152.5°	391.9	391.7	391.6	391.5	391.4	391.2	391.1	391.0	390.9	390.8	390.7
155°	405.5	405.2	405.1	405.0	404.9	404.8	404.8	404.8	404.8	404.8	404.8
157.5°	417.2	416.9	416.8	416.8	416.7	416.6	416.7	416.8	417.0	417.2	417.3
160°	424.3	424.0	423.9	423.8	423.8	423.7	423.8	424.0	424.2	424.5	424.7
162.5°	431.0	430.6	430.6	430.6	430.5	430.5	430.6	430.8	431.0	431.1	431.3
165°	440.1	439.7	439.7	439.6	439.5	439.4	439.5	439.6	439.8	439.9	440.1
167.5°	446.6	446.1	446.1	446.1	446.1	446.1	446.3	446.6	446.9	447.2	447.5
170°	450.6	450.1	450.1	450.1	450.1	450.1	450.2	450.6	450.9	451.2	451.5
172.5°	453.4	452.9	452.9	452.9	452.9	452.9	453.1	453.4	453.7	454.0	454.3
175°	456.7	456.2	456.2	456.2	456.2	456.2	456.4	456.7	457.0	457.3	457.6
177.5°	458.2	457.8	457.9	458.0	458.0	458.1	458.2	458.5	458.7	459.0	459.2
180°	458.7	458.7	458.7	458.7	458.7	458.7	458.7	458.7	458.7	458.7	458.7



TEST NUMBER: P333296-840

CATALOG NUMBER: S125DIP-S1270D365U840-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	275°	280°	285°	290°	295°	300°	305°	310°	315°	320°	325°
0°	1854.7	1854.7	1854.7	1854.7	1854.7	1854.7	1854.7	1854.7	1854.7	1854.7	1854.7
2.5°	1864.7	1873.6	1879.3	1890.0	1898.7	1903.8	1908.2	1912.0	1916.4	1920.2	1930.9
5°	1876.7	1897.1	1914.5	1941.3	1965.7	1984.6	2005.0	2023.2	2038.1	2059.3	2075.9
7.5°	1871.5	1907.8	1946.0	1987.4	2029.7	2069.1	2105.4	2139.2	2169.9	2207.1	2239.6
10°	1866.4	1916.1	1964.9	2020.7	2078.2	2127.1	2172.7	2219.2	2253.0	2300.3	2340.4
12.5°	1862.7	1921.1	1980.0	2047.2	2110.3	2179.3	2240.1	2273.9	2325.4	2363.2	2411.0
15°	1846.8	1924.0	2005.0	2080.6	2170.3	2234.1	2287.6	2353.8	2401.8	2449.8	2501.7
17.5°	1818.3	1905.7	1996.4	2095.4	2181.5	2250.0	2319.0	2382.8	2440.0	2504.5	2569.1
20°	1805.0	1892.5	1996.4	2097.9	2182.1	2253.8	2324.6	2394.7	2457.7	2540.3	2615.1
22.5°	1777.4	1883.0	1978.7	2077.8	2164.5	2242.4	2322.8	2402.3	2486.0	2579.4	2673.0
25°	1728.0	1835.0	1936.5	2034.2	2121.5	2219.2	2304.9	2411.3	2518.3	2641.9	2758.3
27.5°	1676.6	1779.1	1872.2	1966.4	2068.3	2178.9	2290.2	2410.7	2550.9	2706.9	2871.2
30°	1635.1	1731.8	1822.4	1919.2	2025.5	2149.9	2271.9	2415.2	2577.4	2752.9	2948.1
32.5°	1586.5	1675.8	1763.8	1866.3	1982.1	2113.3	2255.5	2412.7	2607.6	2807.0	3008.0
35°	1503.6	1578.3	1668.9	1778.3	1908.9	2059.3	2223.9	2409.6	2633.2	2862.3	3031.5
37.5°	1405.1	1474.8	1570.1	1690.1	1827.1	1988.5	2183.7	2404.2	2641.6	2824.2	2878.8
40°	1339.1	1403.6	1502.8	1627.2	1767.3	1938.1	2152.2	2385.3	2615.1	2731.6	2686.7
42.5°	1268.5	1336.3	1432.9	1556.0	1706.9	1892.8	2112.5	2345.6	2538.3	2582.3	2427.3
45°	1157.2	1227.3	1322.5	1446.9	1609.0	1810.6	2039.6	2251.4	2362.4	2282.9	2042.9
47.5°	1053.8	1119.4	1207.7	1336.1	1503.4	1711.8	1932.5	2101.4	2110.2	1920.5	1664.1
50°	983.2	1043.8	1132.8	1261.1	1427.2	1638.2	1837.3	1970.3	1910.6	1695.7	1449.3
52.5°	913.9	973.3	1061.0	1188.1	1352.3	1545.6	1730.9	1824.3	1711.5	1491.0	1280.5
55°	814.0	866.0	951.7	1069.0	1224.9	1404.4	1561.9	1594.1	1447.6	1230.4	1059.6
57.5°	716.4	764.9	842.9	951.0	1093.5	1252.4	1375.5	1368.7	1213.9	1027.4	891.9
60°	650.3	697.5	766.8	872.2	1002.1	1139.1	1244.6	1219.4	1065.9	905.3	791.1
62.5°	591.1	633.2	698.7	791.0	909.6	1036.4	1123.1	1085.9	935.5	795.1	704.9
65°	503.8	539.3	595.1	673.9	772.2	877.0	943.8	895.9	767.5	658.1	585.7
67.5°	420.5	448.9	495.7	558.6	642.5	726.6	767.4	719.0	616.4	536.5	482.9
70°	367.6	392.8	429.0	484.9	558.2	628.9	659.6	616.4	528.3	459.7	421.1
72.5°	314.8	335.5	367.3	417.6	476.3	537.7	564.6	523.2	450.8	392.9	356.9
75°	243.3	257.4	279.4	314.1	360.5	409.4	424.3	388.1	341.6	298.3	274.8
77.5°	174.1	186.1	202.8	224.7	257.6	288.6	301.6	280.7	244.8	217.4	198.0
80°	133.8	140.2	154.3	172.4	198.3	218.0	226.7	213.4	188.1	167.6	152.7
82.5°	95.4	101.7	110.2	125.1	141.7	155.1	164.4	155.4	137.1	121.1	112.4
85°	46.5	50.4	55.1	61.4	74.0	81.9	81.1	75.5	68.5	62.2	57.5
87.5°	16.6	17.4	19.4	22.6	24.6	27.3	28.7	27.5	25.0	23.2	21.4
90°	1.0	1.6	2.2	2.9	3.5	4.0	4.6	5.2	5.8	6.1	6.5
92.5°	9.1	9.5	10.0	10.4	11.0	11.6	12.3	13.0	13.7	14.2	14.7
95°	23.3	23.5	23.6	23.8	24.3	25.1	25.9	26.7	27.5	28.1	28.6
97.5°	38.6	38.7	38.8	38.8	39.4	40.5	41.6	42.6	43.7	44.3	44.8
100°	50.0	50.0	50.0	50.0	50.5	51.5	52.5	53.6	54.6	55.3	56.0
102.5°	62.6	62.9	63.2	63.5	63.9	64.4	64.9	65.5	66.0	66.9	67.6
105°	81.8	82.2	82.6	83.0	83.4	83.9	84.3	84.8	85.3	85.7	86.2
107.5°	102.9	103.3	103.7	104.1	104.5	104.8	105.2	105.5	105.9	106.1	106.4
110°	117.4	117.9	118.3	118.7	119.0	119.2	119.5	119.7	120.0	120.2	120.4



TEST NUMBER: P333296-840

CATALOG NUMBER: S125DIP-S1270D365U840-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	275°	280°	285°	290°	295°	300°	305°	310°	315°	320°	325°
112.5°	132.1	132.3	132.5	132.7	133.0	133.3	133.6	133.9	134.2	134.3	134.4
115°	154.1	154.5	154.8	155.1	155.3	155.5	155.6	155.8	156.0	155.9	155.8
117.5°	175.9	176.1	176.2	176.4	176.5	176.7	176.8	176.9	177.1	177.1	177.2
120°	190.0	190.4	190.8	191.1	191.4	191.5	191.5	191.6	191.7	191.7	191.7
122.5°	204.5	204.7	204.8	204.9	205.1	205.3	205.5	205.7	205.9	205.9	205.8
125°	225.0	225.5	225.9	226.4	226.7	226.8	226.8	226.9	227.0	226.8	226.7
127.5°	246.2	246.5	246.7	247.0	247.2	247.3	247.4	247.5	247.5	247.5	247.4
130°	259.1	259.5	259.9	260.3	260.6	260.7	260.9	261.2	261.3	261.2	261.2
132.5°	272.3	273.0	273.6	274.2	274.6	274.5	274.5	274.5	274.4	274.3	274.3
135°	292.5	293.0	293.4	293.9	294.2	294.3	294.3	294.4	294.5	294.5	294.5
137.5°	311.5	312.0	312.5	313.0	313.3	313.5	313.6	313.8	314.0	314.1	314.2
140°	323.8	324.2	324.6	325.0	325.3	325.5	325.8	326.0	326.2	326.4	326.6
142.5°	336.0	336.3	336.7	337.0	337.3	337.6	337.9	338.2	338.5	338.6	338.7
145°	354.1	354.4	354.7	355.0	355.3	355.5	355.8	356.0	356.2	356.2	356.2
147.5°	370.6	370.7	370.9	371.1	371.3	371.5	371.7	371.8	372.0	372.2	372.4
150°	381.5	381.4	381.3	381.2	381.3	381.6	382.0	382.3	382.6	382.6	382.6
152.5°	390.8	390.9	391.0	391.1	391.2	391.4	391.5	391.6	391.7	391.9	392.1
155°	404.8	404.8	404.8	404.8	404.8	404.9	405.0	405.1	405.2	405.5	405.8
157.5°	417.2	417.0	416.8	416.7	416.6	416.7	416.8	416.8	416.9	417.2	417.5
160°	424.5	424.2	424.0	423.8	423.7	423.8	423.8	423.9	424.0	424.3	424.6
162.5°	431.1	431.0	430.8	430.6	430.5	430.5	430.6	430.6	430.6	431.0	431.3
165°	439.9	439.8	439.6	439.5	439.4	439.5	439.6	439.7	439.7	440.1	440.4
167.5°	447.2	446.9	446.6	446.3	446.1	446.1	446.1	446.1	446.1	446.6	447.1
170°	451.2	450.9	450.6	450.2	450.1	450.1	450.1	450.1	450.1	450.6	451.0
172.5°	454.0	453.7	453.4	453.1	452.9	452.9	452.9	452.9	452.9	453.4	453.9
175°	457.3	457.0	456.7	456.4	456.2	456.2	456.2	456.2	456.2	456.7	457.1
177.5°	459.0	458.7	458.5	458.2	458.1	458.0	458.0	457.9	457.8	458.2	458.6
180°	458.7	458.7	458.7	458.7	458.7	458.7	458.7	458.7	458.7	458.7	458.7



TEST NUMBER: P333296-840

CATALOG NUMBER: S125DIP-S1270D365U840-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	330°	335°	340°	345°	350°	355°	360°
0°	1854.7	1854.7	1854.7	1854.7	1854.7	1854.7	1854.7
2.5°	1939.6	1944.7	1955.4	1951.7	1956.7	1959.2	1961.8
5°	2096.4	2121.5	2132.5	2131.0	2147.5	2143.5	2139.6
7.5°	2273.3	2299.8	2314.6	2333.0	2343.7	2344.5	2353.8
10°	2373.5	2408.1	2422.3	2442.0	2454.6	2461.6	2460.8
12.5°	2450.2	2477.4	2509.1	2518.8	2535.8	2544.8	2541.4
15°	2542.7	2586.0	2619.1	2635.5	2656.9	2663.1	2671.8
17.5°	2625.2	2683.3	2721.9	2773.2	2792.6	2804.4	2797.4
20°	2687.6	2763.9	2802.5	2863.9	2897.7	2915.9	2909.5
22.5°	2761.3	2843.9	2915.2	2968.4	3019.9	3044.3	3049.4
25°	2887.5	3000.8	3105.5	3175.6	3239.3	3254.3	3287.4
27.5°	3028.6	3162.2	3274.2	3347.9	3392.2	3408.9	3419.3
30°	3117.4	3250.4	3334.7	3381.8	3396.1	3394.5	3392.8
32.5°	3160.8	3244.1	3260.3	3247.1	3214.7	3187.2	3158.7
35°	3099.3	3037.1	2944.2	2824.5	2736.3	2647.4	2638.8
37.5°	2787.3	2588.5	2433.9	2261.2	2161.5	2100.0	2057.5
40°	2493.9	2268.0	2080.6	1935.0	1833.4	1793.3	1753.9
42.5°	2175.2	1959.3	1793.4	1671.7	1595.4	1550.8	1519.6
45°	1767.3	1576.8	1446.9	1358.8	1298.1	1263.4	1243.7
47.5°	1448.1	1307.3	1196.9	1133.3	1091.4	1064.5	1064.6
50°	1276.9	1142.3	1069.0	1018.7	982.4	961.2	965.1
52.5°	1125.1	1024.5	962.0	919.8	893.0	879.9	879.5
55°	940.7	868.3	827.4	796.7	778.5	763.6	766.8
57.5°	804.7	743.6	716.2	690.7	678.1	672.2	663.5
60°	720.3	673.1	649.4	628.9	616.4	611.7	603.0
62.5°	645.4	608.2	585.2	568.6	557.1	555.6	548.9
65°	542.4	514.0	493.6	485.7	473.9	470.8	470.8
67.5°	447.2	426.9	410.9	403.6	398.5	399.3	395.5
70°	387.3	370.8	360.5	352.6	348.7	349.5	346.4
72.5°	338.8	320.4	311.4	306.7	301.5	303.6	302.3
75°	256.6	247.2	242.5	237.7	234.6	233.0	231.5
77.5°	188.4	180.2	176.5	173.8	174.3	170.5	173.5
80°	145.6	138.6	136.2	132.3	131.5	131.5	130.7
82.5°	106.5	102.6	100.9	97.7	96.2	97.5	95.4
85°	55.1	51.9	51.2	51.2	49.6	48.1	51.9
87.5°	21.5	19.1	19.2	18.6	18.6	18.1	16.9
90°	6.9	7.3	7.6	7.9	8.1	8.3	8.6
92.5°	15.2	15.8	16.2	16.4	16.5	16.7	16.9
95°	29.2	29.7	30.1	30.2	30.4	30.5	30.7
97.5°	45.3	45.8	46.2	46.3	46.4	46.5	46.6
100°	56.8	57.5	57.9	58.1	58.3	58.4	58.6
102.5°	68.4	69.2	69.7	69.9	70.1	70.3	70.5
105°	86.7	87.3	87.6	87.8	88.1	88.3	88.6
107.5°	106.6	106.8	107.0	106.9	106.9	106.9	106.9
110°	120.7	120.9	121.0	120.9	120.8	120.7	120.7



TEST NUMBER: P333296-840

CATALOG NUMBER: S125DIP-S1270D365U840-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	330°	335°	340°	345°	350°	355°	360°
112.5°	134.5	134.6	134.6	134.5	134.3	134.2	134.1
115°	155.7	155.6	155.6	155.5	155.4	155.3	155.2
117.5°	177.3	177.3	177.2	176.9	176.6	176.3	175.9
120°	191.7	191.7	191.5	191.2	190.9	190.6	190.3
122.5°	205.7	205.7	205.5	205.3	205.0	204.8	204.5
125°	226.5	226.4	226.2	226.2	226.1	226.0	225.9
127.5°	247.3	247.2	247.1	247.0	246.8	246.6	246.5
130°	261.1	260.9	260.8	260.6	260.5	260.3	260.2
132.5°	274.2	274.1	274.0	273.7	273.5	273.3	273.1
135°	294.5	294.5	294.3	294.0	293.7	293.4	293.1
137.5°	314.3	314.4	314.2	313.8	313.4	313.0	312.6
140°	326.7	326.9	326.8	326.4	326.0	325.6	325.2
142.5°	338.8	338.9	338.7	338.3	337.9	337.6	337.2
145°	356.2	356.2	356.1	355.9	355.6	355.4	355.2
147.5°	372.6	372.8	372.6	372.1	371.5	371.0	370.5
150°	382.6	382.6	382.5	382.4	382.2	382.0	381.9
152.5°	392.3	392.5	392.4	392.2	391.9	391.6	391.3
155°	406.1	406.4	406.4	406.0	405.6	405.2	404.8
157.5°	417.9	418.2	418.1	417.6	417.0	416.5	416.0
160°	425.0	425.3	425.3	424.9	424.4	424.0	423.6
162.5°	431.7	432.1	432.1	431.6	431.1	430.7	430.2
165°	440.7	441.0	440.9	440.4	440.0	439.5	439.0
167.5°	447.5	448.0	448.0	447.5	447.0	446.5	446.1
170°	451.5	452.0	451.9	451.4	450.8	450.3	449.7
172.5°	454.3	454.8	454.8	454.3	453.8	453.3	452.8
175°	457.6	458.1	458.0	457.5	456.9	456.4	455.8
177.5°	459.0	459.3	459.3	458.9	458.4	458.0	457.5
180°	458.7	458.7	458.7	458.7	458.7	458.7	458.7

(END OF REPORT)