

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P333301-840

Luminaire Tested: **S125DIP-S1270D365U840-4F0-1E-UDD-F**

Issue Date: 3/3/2020

Test Information

Test Method: LM-79-08
Report Number: P333301-840
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-7,
Test Lab: INNOVATION CENTER
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: NEO-RAY
Catalog Number: S125DIP-S1270D365U840-4F0-1E-UDD-F
Description: DEFINE 5 DIRECT-INDIRECT PENDANT LED LUMINAIRE
DOWNLIGHT 1270 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER
UPLIGHT 365 LUMENS PER FOOT, NO LENS
Light Source: -
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 6658.5 lumens
Efficiency: N/A
Efficacy: 133.7 lumens/watt
Spacing Criteria (0/90/45): 1.21 / 1.18 / 1.31
Luminous Opening: Rectangular (W 0.42' x L: 4' x H: 0')
CIE Type: Semi-Direct


Input Watts (W): 49.8
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P333301-840

CATALOG NUMBER: S125DIP-S1270D365U840-4F0-1E-UDD-F

Luminous Intensity Polar Plot





TEST NUMBER: P333301-840

CATALOG NUMBER: S125DIP-S1270D365U840-4F0-1E-UDD-F

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20			
RC	80				70				50				30				10	0		
RW	70	50	30	10	70	50	30	10	50	30	10		50	30	10		50	30	10	0
RCR																				
0	114	114	114	114	109	109	109	109	99	99	99		90	90	90		82	82	82	78
1	104	99	95	92	99	95	91	88	87	84	81		79	77	75		72	70	69	65
2	95	87	80	75	90	83	77	72	76	71	67		69	66	62		63	60	58	55
3	86	76	69	62	82	73	66	60	67	61	57		61	57	53		56	52	49	46
4	79	68	59	53	75	65	57	51	60	53	48		55	50	45		50	46	42	40
5	73	60	52	46	69	58	50	44	53	47	42		49	44	39		45	41	37	34
6	67	54	46	40	64	52	44	39	48	42	37		45	39	35		41	36	33	30
7	62	49	41	35	59	47	40	34	44	37	32		41	35	31		38	33	29	27
8	58	45	37	31	55	43	36	30	40	34	29		37	32	27		35	30	26	24
9	54	41	33	28	51	40	32	27	37	31	26		34	29	25		32	27	24	22
10	51	38	30	25	48	37	30	25	34	28	24		32	26	23		30	25	21	20

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	12853	12853	12853
5°	12882	12759	12841
10°	12804	12669	12742
15°	12664	12517	12570
20°	12466	12304	12325
25°	12252	12050	12039
30°	11989	11777	11718
35°	11706	11483	11321
40°	11415	11163	11005
45°	11102	10872	10656
50°	10758	10520	10203
55°	10424	10124	9839
60°	10026	9722	9376
65°	9553	9239	8926
70°	9098	8682	8384
75°	8289	8015	7738
80°	7375	7260	7089
85°	6417	6536	6180



TEST NUMBER: P333301-840

CATALOG NUMBER: S125DIP-S1270D365U840-4F0-1E-UDD-F

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	187.6	2.8
10°-20°	530.1	8.0
20°-30°	782.7	11.8
30°-40°	913.3	13.7
40°-50°	917.2	13.8
50°-60°	805.1	12.1
60°-70°	599.9	9.0
70°-80°	343.0	5.2
80°-90°	100.8	1.5
90°-100°	17.5	0.3
100°-110°	107.8	1.6
110°-120°	195.6	2.9
120°-130°	251.0	3.8
130°-140°	270.0	4.1
140°-150°	253.4	3.8
150°-160°	205.0	3.1
160°-170°	132.6	2.0
170°-180°	45.7	0.7
0°-30°	1500.4	22.5
0°-40°	2413.6	36.2
0°-60°	4136.0	62.1
0°-90°	5179.8	77.8
90°-120°	321.0	4.8
90°-150°	1095.4	16.5
90°-180°	1479.0	22.2
0°-180°	6658.5	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	1990	1990	1990	1990	1990	
5°	1987	1983	1968	1981	1981	188
15°	1894	1889	1872	1880	1880	534
25°	1719	1711	1691	1694	1689	791
35°	1485	1478	1456	1448	1436	928
45°	1216	1208	1190	1172	1167	936
55°	926	920	899	885	874	826
65°	625	621	605	591	584	620
75°	332	329	321	316	310	354
85°	87	88	88	86	83	97
90°	0	3	6	7	9	6
95°	20	19	6	7	8	26
105°	105	106	106	106	106	111
115°	197	199	199	198	196	195
125°	280	283	283	281	280	250
135°	350	351	351	350	348	269
145°	405	406	406	406	404	253
155°	446	444	445	446	443	206
165°	471	469	469	471	468	133
175°	482	480	480	482	479	46
180°	482	482	482	482	482	



TEST NUMBER: P333301-840

CATALOG NUMBER: S125DIP-S1270D365U840-4F0-1E-UDD-F

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	1990.1	1990.1	1990.1	1990.1	1990.1	1990.1	1990.1	1990.1	1990.1	1990.1	1990.1
2.5°	1995.2	1994.4	1993.6	1992.7	1991.9	1990.0	1987.2	1984.4	1981.7	1978.8	1981.7
5°	1987.0	1986.3	1985.6	1984.9	1984.2	1982.2	1978.6	1975.1	1971.7	1968.1	1971.3
7.5°	1968.7	1968.0	1967.3	1966.6	1965.9	1963.7	1959.8	1956.0	1952.2	1948.3	1951.4
10°	1952.4	1951.7	1951.0	1950.3	1949.5	1947.3	1943.5	1939.6	1935.7	1931.9	1934.7
12.5°	1932.2	1931.0	1929.8	1928.4	1927.2	1924.8	1921.2	1917.6	1914.1	1910.5	1912.8
15°	1894.1	1893.1	1892.0	1891.0	1890.0	1887.4	1883.6	1879.8	1875.9	1872.1	1873.8
17.5°	1850.4	1848.9	1847.2	1845.7	1844.2	1841.4	1837.4	1833.4	1829.5	1825.4	1827.7
20°	1813.8	1813.1	1812.4	1811.7	1811.0	1808.4	1803.8	1799.3	1794.7	1790.2	1792.6
22.5°	1777.3	1776.0	1774.7	1773.5	1772.2	1769.5	1765.2	1761.0	1756.7	1752.4	1754.0
25°	1719.4	1717.6	1715.9	1714.1	1712.3	1709.2	1704.7	1700.1	1695.6	1691.0	1691.7
27.5°	1651.6	1650.6	1649.5	1648.5	1647.5	1644.6	1639.9	1635.2	1630.5	1625.8	1626.0
30°	1607.6	1606.5	1605.5	1604.4	1603.4	1600.2	1595.0	1589.7	1584.5	1579.2	1578.5
32.5°	1559.7	1558.1	1556.5	1554.9	1553.3	1550.1	1545.4	1540.8	1536.0	1531.4	1530.1
35°	1484.7	1483.4	1482.0	1480.6	1479.1	1476.0	1471.1	1466.2	1461.3	1456.4	1454.7
37.5°	1406.9	1405.2	1403.5	1401.7	1400.0	1396.7	1392.2	1387.6	1382.9	1378.4	1375.7
40°	1354.0	1352.3	1350.6	1348.8	1347.1	1343.7	1338.9	1333.9	1329.1	1324.1	1321.0
42.5°	1297.4	1296.0	1294.4	1292.9	1291.5	1288.3	1283.4	1278.5	1273.6	1268.7	1265.9
45°	1215.5	1214.2	1212.7	1211.3	1209.9	1207.1	1203.0	1198.7	1194.6	1190.3	1186.1
47.5°	1127.3	1127.4	1127.5	1127.5	1127.6	1125.1	1120.1	1115.1	1110.0	1105.0	1100.8
50°	1070.7	1069.6	1068.5	1067.5	1066.4	1063.8	1059.7	1055.4	1051.3	1047.0	1042.5
52.5°	1012.7	1012.0	1011.2	1010.4	1009.7	1007.0	1002.5	998.0	993.6	989.1	985.1
55°	925.8	924.7	923.7	922.6	921.6	918.7	913.7	908.9	903.9	899.1	895.9
57.5°	834.1	833.6	833.0	832.5	831.9	829.6	825.5	821.3	817.2	813.0	809.0
60°	776.2	774.9	773.5	772.0	770.6	768.0	764.2	760.3	756.5	752.7	749.1
62.5°	715.8	714.7	713.6	712.4	711.2	709.1	705.8	702.5	699.2	695.9	692.2
65°	625.1	624.4	623.7	623.0	622.3	620.0	616.1	612.3	608.4	604.6	601.5
67.5°	537.2	535.7	534.3	532.8	531.4	529.2	526.3	523.4	520.6	517.7	515.0
70°	481.8	480.1	478.3	476.6	474.8	472.3	469.2	466.1	462.9	459.8	457.7
72.5°	421.3	420.1	419.0	417.8	416.6	415.0	412.9	410.9	408.9	406.9	404.5
75°	332.2	331.5	330.8	330.1	329.4	328.2	326.5	324.7	323.0	321.2	320.1
77.5°	250.0	249.7	249.4	249.2	248.9	248.3	247.3	246.3	245.3	244.4	243.8
80°	198.3	198.3	198.3	198.3	198.3	198.0	197.3	196.6	195.9	195.2	194.9
82.5°	153.0	152.5	151.9	151.4	150.8	150.5	150.3	150.2	150.1	149.9	149.3
85°	86.6	86.9	87.3	87.7	88.0	88.2	88.2	88.2	88.2	88.2	87.9
87.5°	34.0	34.2	34.3	34.4	34.6	34.5	34.4	34.2	34.0	33.9	33.9
90°	0.4	1.0	1.6	2.2	2.9	3.5	4.0	4.6	5.2	5.8	6.1
92.5°	5.5	5.0	4.6	4.1	3.7	3.7	4.2	4.7	5.3	5.8	6.1
95°	20.3	20.1	19.9	19.6	19.4	17.8	14.7	11.7	8.7	5.8	6.1
97.5°	42.5	42.9	43.3	43.7	44.2	41.4	35.4	29.5	23.5	17.6	15.3
100°	59.6	59.9	60.1	60.3	60.6	60.8	61.2	61.5	61.8	62.1	50.3
102.5°	77.1	77.4	77.7	78.0	78.3	78.5	78.7	78.9	79.1	79.3	77.1
105°	104.9	105.2	105.6	105.9	106.2	106.3	106.3	106.3	106.3	106.3	106.3
107.5°	133.9	133.9	133.9	133.9	133.9	134.0	134.2	134.3	134.5	134.6	134.6
110°	152.8	152.8	152.8	152.8	152.8	152.9	153.0	153.2	153.3	153.5	153.3



TEST NUMBER: P333301-840

CATALOG NUMBER: S125DIP-S1270D365U840-4F0-1E-UDD-F

CANDELA DISTRIBUTION (continued):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	170.5	170.7	170.9	171.1	171.3	171.4	171.5	171.6	171.7	171.8	171.5
115°	197.0	197.4	197.8	198.2	198.6	198.8	198.9	199.0	199.1	199.1	198.8
117.5°	224.5	224.5	224.5	224.5	224.5	224.6	224.9	225.2	225.5	225.8	225.4
120°	241.7	241.6	241.6	241.5	241.4	241.5	241.7	241.9	242.2	242.4	242.3
122.5°	256.8	257.1	257.4	257.7	258.0	258.2	258.3	258.4	258.5	258.6	258.5
125°	280.2	280.7	281.3	281.9	282.5	282.8	282.8	282.8	282.8	282.8	282.4
127.5°	302.6	303.0	303.4	303.8	304.2	304.4	304.3	304.3	304.2	304.2	304.0
130°	316.3	316.7	317.1	317.5	317.9	318.1	318.2	318.2	318.3	318.4	318.2
132.5°	330.0	330.4	330.9	331.3	331.8	331.9	331.8	331.6	331.4	331.2	331.2
135°	349.5	349.9	350.4	350.9	351.3	351.5	351.3	351.2	351.0	350.9	350.7
137.5°	367.4	367.8	368.2	368.6	369.0	369.2	369.0	368.9	368.7	368.6	368.6
140°	379.1	379.3	379.4	379.6	379.7	379.8	379.7	379.6	379.5	379.5	379.6
142.5°	389.7	389.8	389.9	389.9	390.0	390.1	390.3	390.4	390.5	390.6	390.6
145°	405.2	405.4	405.5	405.7	405.8	405.9	405.9	405.9	405.9	405.9	406.0
147.5°	418.7	418.7	418.7	418.6	418.6	418.6	418.7	418.8	418.9	419.0	419.1
150°	427.3	427.2	427.0	426.8	426.7	426.7	426.8	427.0	427.2	427.3	427.5
152.5°	435.6	435.3	434.8	434.5	434.1	434.0	434.2	434.4	434.5	434.7	434.8
155°	446.3	445.8	445.2	444.7	444.3	444.1	444.3	444.4	444.6	444.7	445.0
157.5°	454.4	454.1	453.8	453.5	453.3	453.1	453.1	453.2	453.2	453.2	453.4
160°	460.1	459.7	459.2	458.7	458.3	458.1	458.1	458.2	458.3	458.4	458.7
162.5°	464.7	464.2	463.7	463.2	462.8	462.6	462.7	462.7	462.8	462.9	463.3
165°	470.8	470.4	469.9	469.4	469.0	468.8	468.8	468.9	469.0	469.1	469.5
167.5°	475.4	474.9	474.4	473.9	473.4	473.2	473.3	473.4	473.5	473.5	474.1
170°	478.0	477.5	476.9	476.4	475.7	475.5	475.6	475.6	475.7	475.8	476.5
172.5°	479.7	479.2	478.6	478.1	477.5	477.3	477.4	477.6	477.7	477.9	478.4
175°	481.5	481.1	480.6	480.1	479.7	479.5	479.5	479.6	479.7	479.8	480.4
177.5°	482.4	482.0	481.6	481.3	480.9	480.7	480.8	480.9	480.9	481.0	481.4
180°	481.5	481.5	481.5	481.5	481.5	481.5	481.5	481.5	481.5	481.5	481.5



TEST NUMBER: P333301-840

CATALOG NUMBER: S125DIP-S1270D365U840-4F0-1E-UDD-F

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°
0°	1990.1	1990.1	1990.1	1990.1	1990.1	1990.1	1990.1	1990.1
2.5°	1984.4	1987.2	1990.0	1991.3	1991.0	1990.7	1990.4	1990.1
5°	1974.4	1977.6	1980.7	1982.2	1981.8	1981.5	1981.1	1980.7
7.5°	1954.4	1957.5	1960.6	1962.0	1961.7	1961.3	1961.0	1960.6
10°	1937.5	1940.4	1943.1	1944.3	1944.0	1943.6	1943.3	1943.0
12.5°	1915.0	1917.2	1919.5	1920.6	1920.5	1920.4	1920.4	1920.3
15°	1875.6	1877.3	1879.1	1880.0	1880.0	1880.0	1880.0	1880.0
17.5°	1829.8	1832.0	1834.1	1834.3	1832.6	1830.9	1829.1	1827.4
20°	1795.1	1797.6	1800.0	1800.4	1798.6	1796.9	1795.1	1793.3
22.5°	1755.7	1757.3	1758.9	1759.1	1757.9	1756.7	1755.4	1754.3
25°	1692.4	1693.1	1693.8	1693.6	1692.6	1691.5	1690.5	1689.4
27.5°	1626.1	1626.3	1626.4	1625.9	1624.9	1623.9	1622.8	1621.7
30°	1577.8	1577.1	1576.4	1575.6	1574.5	1573.5	1572.4	1571.3
32.5°	1528.8	1527.6	1526.3	1524.7	1522.9	1521.0	1519.0	1517.2
35°	1452.9	1451.2	1449.5	1447.1	1444.3	1441.6	1438.8	1435.9
37.5°	1373.1	1370.6	1368.0	1365.8	1364.2	1362.6	1361.0	1359.4
40°	1317.9	1314.7	1311.5	1309.5	1308.4	1307.4	1306.3	1305.3
42.5°	1263.0	1260.1	1257.3	1255.1	1253.4	1251.8	1250.2	1248.6
45°	1181.9	1177.7	1173.6	1170.9	1169.8	1168.8	1167.7	1166.7
47.5°	1096.4	1092.2	1087.9	1084.6	1082.1	1079.6	1077.2	1074.8
50°	1037.9	1033.4	1028.9	1025.3	1022.9	1020.5	1018.0	1015.5
52.5°	981.1	977.1	973.1	969.8	967.0	964.3	961.6	958.9
55°	892.7	889.6	886.5	883.6	881.2	878.8	876.3	873.8
57.5°	805.0	800.9	796.9	794.2	792.8	791.5	790.1	788.8
60°	745.6	742.1	738.6	735.7	733.2	730.7	728.3	725.9
62.5°	688.3	684.6	680.9	678.0	676.1	674.2	672.3	670.4
65°	598.3	595.1	592.0	589.8	588.3	586.9	585.5	584.1
67.5°	512.4	509.7	507.1	505.3	504.4	503.6	502.8	501.9
70°	455.6	453.4	451.3	449.6	448.2	446.8	445.5	444.0
72.5°	402.1	399.7	397.4	395.5	394.0	392.6	391.2	389.8
75°	319.1	318.0	317.0	315.8	314.4	313.0	311.5	310.1
77.5°	243.1	242.5	241.9	241.1	240.0	239.0	238.1	237.1
80°	194.5	194.2	193.8	193.3	192.6	191.9	191.2	190.6
82.5°	148.7	148.0	147.3	147.0	146.8	146.7	146.5	146.4
85°	87.5	87.2	86.7	86.2	85.5	84.8	84.1	83.4
87.5°	34.0	34.1	34.2	34.0	33.5	32.9	32.4	31.9
90°	6.5	6.9	7.3	7.6	7.9	8.1	8.3	8.6
92.5°	6.5	6.9	7.3	7.6	7.7	7.8	7.9	8.0
95°	6.5	6.9	7.3	7.5	7.5	7.5	7.5	7.5
97.5°	13.1	10.8	8.6	7.5	7.5	7.5	7.5	7.5
100°	38.5	26.7	14.8	8.8	8.5	8.2	7.8	7.5
102.5°	74.7	72.5	70.3	66.4	61.1	55.7	50.3	44.9
105°	106.3	106.3	106.3	106.3	106.2	106.1	106.1	106.0
107.5°	134.7	134.7	134.7	134.6	134.4	134.1	133.9	133.6
110°	153.0	152.8	152.6	152.5	152.6	152.6	152.7	152.8



TEST NUMBER: P333301-840

CATALOG NUMBER: S125DIP-S1270D365U840-4F0-1E-UDD-F

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°
112.5°	171.2	170.9	170.6	170.4	170.3	170.2	170.1	170.0
115°	198.5	198.2	197.9	197.5	197.0	196.6	196.1	195.6
117.5°	225.0	224.6	224.2	223.9	223.7	223.5	223.3	223.1
120°	242.1	241.9	241.8	241.5	241.1	240.7	240.2	239.8
122.5°	258.3	258.2	258.0	257.7	257.2	256.8	256.3	255.9
125°	282.1	281.8	281.4	281.1	280.9	280.7	280.4	280.2
127.5°	303.8	303.6	303.5	303.1	302.5	301.8	301.3	300.7
130°	317.9	317.7	317.5	317.1	316.8	316.4	316.0	315.6
132.5°	331.1	331.1	331.0	330.8	330.4	330.0	329.6	329.3
135°	350.6	350.4	350.2	349.9	349.5	349.0	348.5	348.0
137.5°	368.7	368.7	368.7	368.5	368.1	367.7	367.3	366.9
140°	379.8	379.9	380.1	379.9	379.5	379.0	378.5	378.0
142.5°	390.6	390.7	390.7	390.5	390.0	389.5	389.1	388.6
145°	406.1	406.1	406.2	406.0	405.6	405.1	404.6	404.0
147.5°	419.2	419.3	419.4	419.2	418.6	418.0	417.5	416.9
150°	427.6	427.8	427.9	427.7	427.1	426.5	425.8	425.2
152.5°	435.0	435.2	435.4	435.2	434.5	434.0	433.4	432.8
155°	445.2	445.5	445.8	445.6	444.9	444.2	443.6	443.0
157.5°	453.7	453.9	454.2	454.0	453.4	452.7	452.1	451.5
160°	459.0	459.3	459.6	459.5	458.8	458.2	457.6	457.0
162.5°	463.8	464.2	464.7	464.5	463.8	463.1	462.5	461.8
165°	470.0	470.5	471.0	470.9	470.3	469.6	469.0	468.4
167.5°	474.7	475.2	475.8	475.7	475.0	474.3	473.6	472.9
170°	477.1	477.8	478.4	478.4	477.7	477.0	476.2	475.4
172.5°	479.0	479.6	480.1	480.1	479.4	478.6	477.9	477.2
175°	481.0	481.7	482.3	482.3	481.5	480.8	480.1	479.4
177.5°	481.9	482.3	482.7	482.7	482.2	481.7	481.2	480.7
180°	481.5	481.5	481.5	481.5	481.5	481.5	481.5	481.5

(END OF REPORT)