

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P331715-927

Luminaire Tested: **SA2XXRDIP-C865D530U927-4F0-1E-UDD-F1**

Issue Date: 10/7/2019

Test Information

Test Method: LM-79-08
Report Number: P331715-927
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-8,
Test Lab: INNOVATION CENTER
Issue Date: 10/7/2019
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: NEO-RAY
Catalog Number: SA2XXRDIP-C865D530U927-4F0-1E-UDD-F1
Description: DEFINE 2 DIRECT-INDIRECT PENDANT LED LUMINAIRE
DOWNLIGHT 865 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER, REGRESSED
HOUSING
UPLIGHT 530 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER
Light Source: -
Ballast/Driver: ELECTRONIC DRIVER

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 3888.0 lumens
Efficiency: N/A
Efficacy: 79.7 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 0.99 / 1.16
Luminous Opening: Rectangular (W 0.17' x L: 4' x H: 0')
CIE Type: Semi-Direct

Input Watts (W): 48.8
Input Voltage (V): 120
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P331715-927
CATALOG NUMBER: SA2XXRDIP-C865D530U927-4F0-1E-UDD-F1

Luminous Intensity Polar Plot





TEST NUMBER: P331715-927

CATALOG NUMBER: SA2XXRDIP-C865D530U927-4F0-1E-UDD-F1

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20					20					20					20					20	
RC	80					70					50					30					10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0	
RCR																						
0	110	110	110	110	103	103	103	103	90	90	90	78	78	78	67	67	67	62				
1	101	97	93	90	94	91	88	85	80	77	75	69	68	66	60	59	57	53				
2	92	85	79	74	86	80	75	70	70	66	63	62	59	56	53	51	49	45				
3	85	75	68	63	79	71	65	60	63	58	54	55	51	48	48	45	43	39				
4	78	67	59	54	73	63	56	51	56	51	46	49	45	42	43	40	37	34				
5	72	60	52	46	67	57	50	44	51	45	40	45	40	37	39	36	33	30				
6	66	54	46	41	62	51	44	39	46	40	36	41	36	32	36	32	29	27				
7	62	49	41	36	58	47	40	35	42	36	32	37	32	29	33	29	26	24				
8	57	45	37	32	54	43	36	31	38	33	28	34	30	26	30	27	24	22				
9	53	41	34	29	50	39	32	28	35	30	26	32	27	24	28	24	22	20				
10	50	38	31	26	47	36	30	25	33	27	23	29	25	22	26	22	20	18				

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	18755	18755	18755
5°	18827	18519	18621
10°	18682	18216	18061
15°	18467	17677	17167
20°	18170	16905	16057
25°	17865	16030	14982
30°	17443	15129	13601
35°	17030	14152	12390
40°	16617	13139	10989
45°	16130	12001	9720
50°	15631	10854	8475
55°	15122	9619	7279
60°	14528	8315	6042
65°	13857	6988	5501
70°	13053	5755	5061
75°	12071	5246	4722
80°	10646	4695	4305
85°	8373	3705	3705



TEST NUMBER: P331715-927

CATALOG NUMBER: SA2XXRDIP-C865D530U927-4F0-1E-UDD-F1

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	108.7	2.8
10°-20°	298.5	7.7
20°-30°	419.2	10.8
30°-40°	457.1	11.8
40°-50°	420.3	10.8
50°-60°	330.1	8.5
60°-70°	215.2	5.5
70°-80°	111.0	2.9
80°-90°	30.9	0.8
90°-100°	33.9	0.9
100°-110°	105.4	2.7
110°-120°	180.1	4.6
120°-130°	236.8	6.1
130°-140°	265.8	6.8
140°-150°	260.6	6.7
150°-160°	218.6	5.6
160°-170°	145.0	3.7
170°-180°	50.7	1.3
0°-30°	826.5	21.3
0°-40°	1283.6	33.0
0°-60°	2034.0	52.3
0°-90°	2391.2	61.5
90°-120°	319.4	8.2
90°-150°	1082.6	27.8
90°-180°	1497.0	38.5
0°-180°	3888.0	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	1162	1162	1162	1162	1162	
5°	1162	1156	1143	1151	1149	110
15°	1105	1092	1058	1038	1027	311
25°	1003	967	900	858	841	461
35°	864	808	718	654	629	541
45°	706	634	526	454	426	545
55°	537	453	342	281	259	480
65°	363	277	183	149	144	359
75°	194	122	84	77	76	205
85°	45	24	20	20	20	53
90°	0	6	16	15	15	3
95°	24	28	29	29	28	27
105°	97	98	99	100	100	103
115°	181	183	182	182	181	179
125°	263	267	266	264	264	235
135°	340	345	346	346	344	263
145°	413	416	419	419	417	258
155°	472	473	475	477	476	217
165°	514	513	513	516	514	145
175°	534	533	532	535	533	51
180°	535	535	535	535	535	



TEST NUMBER: P331715-927

CATALOG NUMBER: SA2XXRDIP-C865D530U927-4F0-1E-UDD-F1

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	1161.6	1161.6	1161.6	1161.6	1161.6	1161.6	1161.6	1161.6	1161.6	1161.6	1161.6
2.5°	1165.8	1164.8	1163.9	1162.9	1162.1	1160.5	1158.5	1156.4	1154.4	1152.3	1154.2
5°	1161.6	1160.4	1159.2	1158.0	1156.9	1154.8	1151.8	1148.7	1145.7	1142.6	1144.7
7.5°	1149.5	1148.1	1146.7	1145.3	1143.8	1141.3	1137.7	1134.2	1130.6	1127.0	1127.7
10°	1139.5	1137.8	1136.2	1134.6	1132.9	1129.8	1125.1	1120.5	1115.8	1111.1	1110.4
12.5°	1126.9	1124.8	1122.8	1120.9	1118.8	1114.8	1108.8	1102.9	1096.9	1090.9	1089.6
15°	1104.8	1102.2	1099.6	1097.1	1094.5	1089.3	1081.3	1073.4	1065.4	1057.5	1053.0
17.5°	1077.7	1073.7	1069.8	1065.9	1062.0	1054.9	1044.7	1034.5	1024.4	1014.2	1008.9
20°	1057.5	1052.8	1048.1	1043.5	1038.8	1030.6	1018.9	1007.3	995.6	983.9	978.0
22.5°	1035.6	1030.4	1025.2	1019.9	1014.7	1005.5	992.3	979.1	966.0	952.8	945.2
25°	1002.8	995.4	987.9	980.4	973.0	961.5	946.0	930.7	915.2	899.8	890.3
27.5°	963.3	955.1	947.1	938.9	930.8	918.1	900.6	883.3	865.9	848.5	837.3
30°	935.6	926.7	917.8	908.9	900.1	886.3	867.6	848.9	830.2	811.5	799.6
32.5°	908.6	898.3	887.9	877.5	867.1	852.5	833.4	814.3	795.3	776.2	762.6
35°	864.0	852.2	840.3	828.3	816.4	800.2	779.6	759.1	738.6	718.0	703.2
37.5°	819.5	806.4	793.4	780.2	767.1	749.6	727.8	705.8	684.0	662.0	645.8
40°	788.4	774.4	760.3	746.3	732.3	714.0	691.3	668.7	646.0	623.4	606.7
42.5°	756.5	741.6	726.9	712.2	697.4	678.3	654.9	631.4	608.1	584.6	567.5
45°	706.4	690.7	675.1	659.4	643.8	623.7	599.2	574.6	550.1	525.6	509.0
47.5°	657.6	641.0	624.5	607.8	591.3	570.3	545.0	519.7	494.3	469.1	452.6
50°	622.3	605.7	589.1	572.5	556.0	534.8	509.1	483.4	457.7	432.1	415.9
52.5°	587.8	570.5	553.2	535.8	518.5	497.3	472.1	446.9	421.8	396.7	381.1
55°	537.2	519.0	500.7	482.5	464.3	442.5	417.3	392.1	366.9	341.7	327.6
57.5°	485.2	466.5	447.8	429.1	410.5	389.0	364.7	340.5	316.2	292.0	279.2
60°	449.9	431.2	412.6	393.9	375.2	353.8	329.7	305.6	281.6	257.5	245.7
62.5°	415.4	396.7	378.0	359.3	340.6	319.9	296.9	274.0	251.0	228.1	216.7
65°	362.7	343.7	324.8	305.9	287.0	267.0	246.0	225.0	203.9	182.9	175.0
67.5°	311.8	293.0	274.3	255.4	236.6	217.8	198.9	180.0	161.1	142.1	138.5
70°	276.5	258.3	240.0	221.8	203.6	186.4	170.3	154.2	138.1	121.9	119.6
72.5°	242.8	225.4	207.9	190.4	172.9	157.7	144.8	131.8	118.9	106.0	104.0
75°	193.5	177.1	160.7	144.3	128.0	115.9	107.9	100.0	92.1	84.1	82.5
77.5°	144.9	130.5	116.1	101.8	87.5	78.4	74.5	70.7	66.9	63.1	62.1
80°	114.5	102.7	90.8	78.8	66.9	59.8	57.4	55.1	52.8	50.5	49.5
82.5°	86.8	77.6	68.2	58.9	49.7	44.2	42.6	41.0	39.5	37.9	37.3
85°	45.2	40.3	35.4	30.5	25.6	22.8	22.1	21.4	20.7	20.0	20.0
87.5°	13.5	12.3	11.0	9.7	8.6	8.2	8.6	9.0	9.4	9.9	9.7
90°	0.5	1.7	2.9	4.0	5.3	7.0	9.2	11.4	13.6	15.8	15.6
92.5°	8.1	9.0	9.8	10.7	11.6	12.3	12.8	13.3	13.9	14.3	14.4
95°	23.5	24.5	25.5	26.5	27.5	28.1	28.3	28.5	28.7	28.9	28.9
97.5°	42.9	43.8	44.7	45.6	46.4	47.1	47.5	47.8	48.2	48.6	48.6
100°	57.4	58.1	58.9	59.8	60.6	61.2	61.5	61.7	62.0	62.3	62.3
102.5°	72.6	73.2	73.8	74.5	75.1	75.7	76.0	76.4	76.8	77.2	77.2
105°	97.1	97.4	97.8	98.0	98.3	98.5	98.8	98.9	99.2	99.4	99.6
107.5°	121.9	122.3	122.8	123.2	123.7	123.9	123.9	123.9	123.9	123.9	124.0
110°	137.8	138.4	138.9	139.6	140.2	140.5	140.5	140.5	140.5	140.5	140.5



TEST NUMBER: P331715-927

CATALOG NUMBER: SA2XXRDIP-C865D530U927-4F0-1E-UDD-F1

CANDELA DISTRIBUTION (continued):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	155.1	155.7	156.3	156.9	157.6	157.8	157.7	157.6	157.6	157.5	157.2
115°	180.7	181.3	181.9	182.5	183.1	183.3	183.1	182.9	182.7	182.5	182.4
117.5°	206.2	207.0	207.8	208.6	209.4	209.5	209.0	208.3	207.8	207.2	207.0
120°	223.2	223.9	224.7	225.5	226.4	226.4	225.5	224.7	223.9	223.2	223.2
122.5°	238.7	239.6	240.7	241.6	242.6	242.7	242.2	241.6	241.1	240.5	240.3
125°	262.9	263.8	264.7	265.6	266.5	266.8	266.5	266.3	265.9	265.6	265.3
127.5°	286.5	287.6	288.8	289.9	291.0	291.4	291.1	290.7	290.4	290.0	289.6
130°	301.3	302.6	303.9	305.2	306.5	307.0	306.9	306.7	306.5	306.3	306.1
132.5°	317.9	319.0	320.0	321.2	322.2	322.7	322.8	322.8	322.9	322.9	322.5
135°	340.2	341.3	342.4	343.5	344.6	345.2	345.4	345.6	345.9	346.0	345.9
137.5°	363.5	364.5	365.4	366.3	367.2	367.7	368.0	368.3	368.5	368.8	368.7
140°	377.6	378.6	379.5	380.3	381.3	382.0	382.5	382.9	383.5	384.0	384.0
142.5°	392.1	393.0	394.0	394.8	395.7	396.3	396.7	397.0	397.4	397.7	397.8
145°	412.9	413.6	414.3	415.0	415.7	416.4	416.9	417.6	418.2	418.7	418.8
147.5°	431.4	432.2	433.1	434.0	434.7	435.4	435.8	436.2	436.6	437.0	437.2
150°	444.1	444.7	445.3	445.8	446.5	446.9	447.3	447.7	448.1	448.6	448.9
152.5°	455.3	455.9	456.5	457.1	457.6	458.2	458.7	459.1	459.6	460.2	460.5
155°	472.1	472.4	472.7	472.9	473.2	473.6	473.9	474.2	474.4	474.8	475.3
157.5°	486.4	486.6	486.8	487.0	487.3	487.4	487.6	487.8	488.0	488.1	488.9
160°	495.1	495.3	495.5	495.7	495.9	496.1	496.1	496.2	496.4	496.5	497.1
162.5°	503.0	503.1	503.1	503.2	503.2	503.3	503.4	503.5	503.6	503.7	504.4
165°	513.7	513.5	513.4	513.3	513.3	513.2	513.2	513.2	513.2	513.2	513.9
167.5°	522.4	522.2	521.9	521.6	521.3	521.1	521.1	521.1	521.0	521.0	521.7
170°	527.2	526.9	526.6	526.2	526.0	525.8	525.7	525.5	525.5	525.4	526.1
172.5°	530.4	530.1	529.8	529.5	529.3	529.0	528.9	528.9	528.7	528.6	529.3
175°	534.4	534.1	533.8	533.5	533.2	533.0	532.7	532.6	532.3	532.1	532.8
177.5°	536.1	535.8	535.5	535.3	535.0	534.9	534.7	534.6	534.4	534.2	534.7
180°	535.3	535.3	535.3	535.3	535.3	535.3	535.3	535.3	535.3	535.3	535.3



TEST NUMBER: P331715-927

CATALOG NUMBER: SA2XXRDIP-C865D530U927-4F0-1E-UDD-F1

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°
0°	1161.6	1161.6	1161.6	1161.6	1161.6	1161.6	1161.6	1161.6
2.5°	1156.0	1157.9	1159.8	1160.5	1160.2	1159.8	1159.4	1159.0
5°	1146.8	1148.9	1151.0	1151.8	1151.0	1150.3	1149.6	1148.9
7.5°	1128.3	1128.9	1129.5	1129.2	1128.0	1126.8	1125.5	1124.3
10°	1109.7	1109.0	1108.3	1107.2	1105.8	1104.5	1103.0	1101.6
12.5°	1088.4	1087.1	1085.8	1084.1	1081.7	1079.4	1077.1	1074.8
15°	1048.6	1044.2	1039.7	1036.3	1034.0	1031.7	1029.4	1027.0
17.5°	1003.6	998.3	993.1	988.4	984.4	980.4	976.4	972.3
20°	972.2	966.4	960.5	955.1	949.9	944.8	939.6	934.5
22.5°	937.8	930.3	922.7	917.0	913.2	909.3	905.5	901.7
25°	880.7	871.1	861.5	854.9	851.4	848.0	844.5	841.0
27.5°	826.2	815.0	803.8	795.5	790.0	784.3	778.8	773.2
30°	787.7	775.8	763.8	754.7	748.5	742.1	735.9	729.5
32.5°	749.0	735.4	721.8	712.0	706.2	700.2	694.3	688.3
35°	688.5	673.8	659.1	649.2	644.0	638.9	633.7	628.6
37.5°	629.6	613.4	597.2	586.1	580.3	574.3	568.5	562.6
40°	590.2	573.6	557.0	545.7	539.6	533.5	527.4	521.4
42.5°	550.4	533.2	516.1	504.5	498.7	492.8	486.9	481.0
45°	492.4	475.9	459.2	448.1	442.5	437.0	431.3	425.7
47.5°	436.0	419.5	403.1	392.3	387.2	382.1	377.0	371.9
50°	399.8	383.7	367.6	357.0	352.1	347.2	342.3	337.4
52.5°	365.6	350.1	334.5	324.5	319.9	315.4	310.9	306.3
55°	313.6	299.6	285.6	276.3	271.9	267.4	263.0	258.6
57.5°	266.3	253.5	240.7	232.3	228.6	224.8	221.1	217.4
60°	233.7	221.8	209.8	202.1	198.3	194.6	190.8	187.1
62.5°	205.4	194.1	182.7	175.9	173.6	171.4	169.1	166.9
65°	167.0	159.1	151.1	146.8	146.1	145.4	144.7	144.0
67.5°	134.8	131.2	127.5	125.3	124.6	123.8	123.1	122.4
70°	117.2	114.9	112.6	111.0	110.0	109.1	108.1	107.2
72.5°	102.0	100.1	98.1	96.9	96.3	95.7	95.1	94.6
75°	80.8	79.2	77.6	76.6	76.4	76.1	75.9	75.7
77.5°	61.2	60.3	59.3	58.7	58.3	57.9	57.6	57.2
80°	48.6	47.7	46.7	46.3	46.3	46.3	46.3	46.3
82.5°	36.8	36.1	35.6	35.3	35.3	35.3	35.3	35.3
85°	20.0	20.0	20.0	20.0	20.0	20.0	20.0	20.0
87.5°	9.4	9.2	9.0	8.9	8.9	9.0	9.0	9.0
90°	15.4	15.2	15.0	15.0	15.1	15.1	15.3	15.4
92.5°	14.4	14.5	14.5	14.6	14.6	14.6	14.7	14.7
95°	28.9	28.9	28.9	28.8	28.6	28.4	28.2	28.0
97.5°	48.6	48.6	48.6	48.6	48.6	48.6	48.6	48.5
100°	62.3	62.3	62.3	62.3	62.2	62.1	62.0	61.9
102.5°	77.3	77.4	77.5	77.5	77.4	77.2	77.2	77.1
105°	99.8	100.0	100.2	100.3	100.3	100.3	100.3	100.3
107.5°	124.1	124.1	124.2	124.0	123.5	123.1	122.6	122.2
110°	140.5	140.5	140.5	140.4	140.1	139.7	139.4	139.1



TEST NUMBER: P331715-927

CATALOG NUMBER: SA2XXRDIP-C865D530U927-4F0-1E-UDD-F1

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°
112.5°	157.0	156.8	156.5	156.3	156.1	155.8	155.6	155.4
115°	182.3	182.2	182.1	181.9	181.6	181.3	181.0	180.7
117.5°	206.8	206.5	206.3	206.0	205.7	205.4	205.1	204.8
120°	223.2	223.2	223.2	223.0	222.7	222.4	222.1	221.8
122.5°	240.0	239.8	239.6	239.3	239.1	238.8	238.7	238.4
125°	265.0	264.7	264.4	264.2	264.1	264.0	263.9	263.8
127.5°	289.3	288.9	288.6	288.2	287.9	287.6	287.2	286.9
130°	305.9	305.7	305.5	305.1	304.8	304.4	304.0	303.6
132.5°	322.0	321.5	321.2	320.8	320.4	320.1	319.8	319.5
135°	345.9	345.7	345.6	345.4	345.2	344.8	344.5	344.2
137.5°	368.6	368.5	368.4	368.2	367.8	367.4	367.0	366.6
140°	384.0	384.0	384.0	383.8	383.3	382.9	382.5	382.1
142.5°	397.8	397.9	398.0	397.8	397.4	397.0	396.6	396.2
145°	419.0	419.1	419.1	419.0	418.6	418.2	417.8	417.4
147.5°	437.4	437.7	437.9	437.8	437.4	437.0	436.7	436.3
150°	449.2	449.5	449.8	449.8	449.5	449.2	448.9	448.6
152.5°	460.9	461.3	461.7	461.7	461.3	460.9	460.5	460.2
155°	475.8	476.3	476.8	476.9	476.6	476.3	475.9	475.7
157.5°	489.5	490.2	490.9	491.0	490.5	490.0	489.6	489.0
160°	497.6	498.3	498.8	499.0	498.6	498.2	497.7	497.3
162.5°	505.0	505.7	506.4	506.5	506.0	505.6	505.1	504.6
165°	514.6	515.3	515.9	516.1	515.6	515.1	514.6	514.0
167.5°	522.4	523.2	523.9	523.9	523.4	522.9	522.4	521.8
170°	526.8	527.5	528.1	528.2	527.6	527.0	526.4	525.9
172.5°	530.0	530.8	531.4	531.5	530.9	530.3	529.7	529.1
175°	533.5	534.2	535.0	535.0	534.4	533.8	533.2	532.6
177.5°	535.2	535.7	536.1	536.1	535.7	535.2	534.7	534.2
180°	535.3	535.3	535.3	535.3	535.3	535.3	535.3	535.3

(END OF REPORT)