

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P333304-840

Luminaire Tested: **S125DIP-S1270D590U840-4F0-1E-UDD-A**

Issue Date: 3/3/2020

Test Information

Test Method: LM-79-08
Report Number: P333304-840
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-7,
Test Lab: INNOVATION CENTER
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: NEO-RAY
Catalog Number: S125DIP-S1270D590U840-4F0-1E-UDD-A
Description: DEFINE 5 DIRECT-INDIRECT PENDANT LED LUMINAIRE
DOWNLIGHT 1270 LUMENS PER FOOT, ASYMMETRIC DIFFUSER
UPLIGHT 590 LUMENS PER FOOT, NO LENS
Light Source: -
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 7622.0 lumens
Efficiency: N/A
Efficacy: 138.3 lumens/watt
Spacing Criteria (0/90/45): 1.43 / 1.23 / 1.52
Luminous Opening: Rectangular (W 4' x L: 0.42' x H: 0')
CIE Type: Semi-Direct


Input Watts (W): 55.1
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P333304-840

CATALOG NUMBER: S125DIP-S1270D590U840-4F0-1E-UDD-A

Luminous Intensity Polar Plot





TEST NUMBER: P333304-840

CATALOG NUMBER: S125DIP-S1270D590U840-4F0-1E-UDD-A

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	112	112	112	112	105	105	105	105	94	94	94	83	83	83	73	73	73	69
1	102	98	94	91	96	93	89	86	83	80	78	74	72	70	65	64	63	59
2	93	86	80	75	88	81	76	71	73	69	65	65	62	59	58	55	53	49
3	85	76	68	62	80	72	65	60	65	59	55	58	54	50	51	48	46	42
4	78	67	59	53	74	64	57	51	58	52	47	52	47	43	46	42	39	36
5	72	60	52	46	68	57	50	44	52	46	41	46	42	38	42	38	34	32
6	66	54	46	40	63	52	44	38	47	40	36	42	37	33	38	34	30	28
7	62	49	41	35	58	47	39	34	42	36	32	38	33	29	35	30	27	25
8	57	45	37	31	54	43	35	30	39	33	28	35	30	26	32	27	24	22
9	53	41	33	28	50	39	32	27	36	30	25	32	27	24	29	25	22	20
10	50	37	30	25	47	36	29	24	33	27	23	30	25	21	27	23	20	18

AVERAGE LUMINANCE (cd/sqm):

	0°	90°	180°	270°
0°	11978	11978	11978	11978
5°	13871	12019	10524	12019
10°	16138	11956	9220	11956
15°	17864	11869	8505	11869
20°	19996	11730	7932	11730
25°	23426	11573	7652	11573
30°	25302	11419	7409	11419
35°	20805	11129	7250	11129
40°	14787	10725	7075	10725
45°	11359	10181	6974	10181
50°	9697	9507	6961	9507
55°	8634	8847	7020	8847
60°	7789	8123	7198	8123
65°	7195	7398	7386	7398
70°	6541	6643	7493	6643
75°	5777	5854	7426	5854
80°	4861	4775	6791	4775
85°	3846	3446	5483	3446



TEST NUMBER: P333304-840

CATALOG NUMBER: S125DIP-S1270D590U840-4F0-1E-UDD-A

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	178.6	2.3
10°-20°	531.6	7.0
20°-30°	863.2	11.3
30°-40°	1053.0	13.8
40°-50°	957.9	12.6
50°-60°	763.0	10.0
60°-70°	531.4	7.0
70°-80°	283.4	3.7
80°-90°	73.1	1.0
90°-100°	28.3	0.4
100°-110°	174.1	2.3
110°-120°	315.7	4.1
120°-130°	405.2	5.3
130°-140°	435.8	5.7
140°-150°	409.1	5.4
150°-160°	330.9	4.3
160°-170°	214.0	2.8
170°-180°	73.8	1.0
0°-30°	1573.4	20.6
0°-40°	2626.3	34.5
0°-60°	4347.2	57.0
0°-90°	5235.2	68.7
90°-120°	518.0	6.8
90°-150°	1768.1	23.2
90°-180°	2387.0	31.3
0°-180°	7622.0	100.0

CANDELA DISTRIBUTION:

	0°	90°	180°	270°	360°	Flux
0°	1855	1855	1855	1855	1855	
5°	2140	1854	1623	1854	2140	216
15°	2672	1775	1272	1775	2672	765
25°	3287	1624	1074	1624	3287	1502
35°	2639	1412	920	1412	2639	1615
45°	1244	1115	764	1115	1244	995
55°	767	786	624	786	767	691
65°	471	484	483	484	471	467
75°	232	235	298	235	232	249
85°	52	46	74	46	52	60
90°	14	1	14	1	14	8
95°	12	33	12	33	12	10
105°	171	169	171	169	171	155
115°	316	318	316	318	316	313
125°	452	452	452	452	452	402
135°	562	564	562	564	562	434
145°	652	654	652	654	652	407
155°	715	720	715	720	715	330
165°	756	760	756	760	756	213
175°	774	777	774	777	774	74
180°	777	777	777	777	777	



TEST NUMBER: P333304-840

CATALOG NUMBER: S125DIP-S1270D590U840-4F0-1E-UDD-A

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	1854.7	1854.7	1854.7	1854.7	1854.7	1854.7	1854.7	1854.7	1854.7	1854.7	1854.7
2.5°	1961.8	1959.2	1956.7	1951.7	1955.4	1944.7	1939.6	1930.9	1920.2	1916.4	1912.0
5°	2139.6	2143.5	2147.5	2131.0	2132.5	2121.5	2096.4	2075.9	2059.3	2038.1	2023.2
7.5°	2353.8	2344.5	2343.7	2333.0	2314.6	2299.8	2273.3	2239.6	2207.1	2169.9	2139.2
10°	2460.8	2461.6	2454.6	2442.0	2422.3	2408.1	2373.5	2340.4	2300.3	2253.0	2219.2
12.5°	2541.4	2544.8	2535.8	2518.8	2509.1	2477.4	2450.2	2411.0	2363.2	2325.4	2273.9
15°	2671.8	2663.1	2656.9	2635.5	2619.1	2586.0	2542.7	2501.7	2449.8	2401.8	2353.8
17.5°	2797.4	2804.4	2792.6	2773.2	2721.9	2683.3	2625.2	2569.1	2504.5	2440.0	2382.8
20°	2909.5	2915.9	2897.7	2863.9	2802.5	2763.9	2687.6	2615.1	2540.3	2457.7	2394.7
22.5°	3049.4	3044.3	3019.9	2968.4	2915.2	2843.9	2761.3	2673.0	2579.4	2486.0	2402.3
25°	3287.4	3254.3	3239.3	3175.6	3105.5	3000.8	2887.5	2758.3	2641.9	2518.3	2411.3
27.5°	3419.3	3408.9	3392.2	3347.9	3274.2	3162.2	3028.6	2871.2	2706.9	2550.9	2410.7
30°	3392.8	3394.5	3396.1	3381.8	3334.7	3250.4	3117.4	2948.1	2752.9	2577.4	2415.2
32.5°	3158.7	3187.2	3214.7	3247.1	3260.3	3244.1	3160.8	3008.0	2807.0	2607.6	2412.7
35°	2638.8	2647.4	2736.3	2824.5	2944.2	3037.1	3099.3	3031.5	2862.3	2633.2	2409.6
37.5°	2057.5	2100.0	2161.5	2261.2	2433.9	2588.5	2787.3	2878.8	2824.2	2641.6	2404.2
40°	1753.9	1793.3	1833.4	1935.0	2080.6	2268.0	2493.9	2686.7	2731.6	2615.1	2385.3
42.5°	1519.6	1550.8	1595.4	1671.7	1793.4	1959.3	2175.2	2427.3	2582.3	2538.3	2345.6
45°	1243.7	1263.4	1298.1	1358.8	1446.9	1576.8	1767.3	2042.9	2282.9	2362.4	2251.4
47.5°	1064.6	1064.5	1091.4	1133.3	1196.9	1307.3	1448.1	1664.1	1920.5	2110.2	2101.4
50°	965.1	961.2	982.4	1018.7	1069.0	1142.3	1276.9	1449.3	1695.7	1910.6	1970.3
52.5°	879.5	879.9	893.0	919.8	962.0	1024.5	1125.1	1280.5	1491.0	1711.5	1824.3
55°	766.8	763.6	778.5	796.7	827.4	868.3	940.7	1059.6	1230.4	1447.6	1594.1
57.5°	663.5	672.2	678.1	690.7	716.2	743.6	804.7	891.9	1027.4	1213.9	1368.7
60°	603.0	611.7	616.4	628.9	649.4	673.1	720.3	791.1	905.3	1065.9	1219.4
62.5°	548.9	555.6	557.1	568.6	585.2	608.2	645.4	704.9	795.1	935.5	1085.9
65°	470.8	470.8	473.9	485.7	493.6	514.0	542.4	585.7	658.1	767.5	895.9
67.5°	395.5	399.3	398.5	403.6	410.9	426.9	447.2	482.9	536.5	616.4	719.0
70°	346.4	349.5	348.7	352.6	360.5	370.8	387.3	421.1	459.7	528.3	616.4
72.5°	302.3	303.6	301.5	306.7	311.4	320.4	338.8	356.9	392.9	450.8	523.2
75°	231.5	233.0	234.6	237.7	242.5	247.2	256.6	274.8	298.3	341.6	388.1
77.5°	173.5	170.5	174.3	173.8	176.5	180.2	188.4	198.0	217.4	244.8	280.7
80°	130.7	131.5	131.5	132.3	136.2	138.6	145.6	152.7	167.6	188.1	213.4
82.5°	95.4	97.5	96.2	97.7	100.9	102.6	106.5	112.4	121.1	137.1	155.4
85°	51.9	48.1	49.6	51.2	51.2	51.9	55.1	57.5	62.2	68.5	75.5
87.5°	17.9	19.1	19.6	19.5	20.1	20.0	22.4	22.2	24.0	25.8	28.1
90°	13.8	13.4	13.0	12.7	12.3	11.8	11.1	10.5	9.9	9.2	8.3
92.5°	12.9	12.7	12.5	12.3	12.2	11.8	11.1	10.5	9.9	9.2	8.4
95°	12.1	12.1	12.1	12.1	12.1	11.8	11.1	10.5	9.9	9.2	14.0
97.5°	12.1	12.1	12.1	12.1	12.1	13.9	17.5	21.1	24.7	28.4	38.0
100°	12.1	12.6	13.1	13.6	14.1	23.9	43.0	62.1	81.2	100.3	99.8
102.5°	72.5	81.2	89.9	98.6	107.3	113.5	117.0	120.7	124.3	127.9	127.6
105°	171.1	171.3	171.4	171.5	171.7	171.7	171.7	171.7	171.7	171.7	171.7
107.5°	215.7	216.1	216.5	216.9	217.2	217.4	217.4	217.4	217.3	217.3	217.1
110°	246.6	246.5	246.3	246.2	246.1	246.2	246.6	247.0	247.4	247.7	247.5



TEST NUMBER: P333304-840

CATALOG NUMBER: S125DIP-S1270D590U840-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	274.3	274.5	274.6	274.8	275.0	275.3	275.8	276.3	276.8	277.2	277.1
115°	315.8	316.5	317.3	318.0	318.8	319.4	319.9	320.4	321.0	321.5	321.3
117.5°	360.0	360.3	360.6	361.0	361.3	361.8	362.4	363.1	363.9	364.5	364.0
120°	387.2	387.8	388.5	389.1	389.7	390.2	390.4	390.7	390.9	391.2	390.8
122.5°	413.0	413.7	414.4	415.3	416.0	416.5	416.8	417.0	417.3	417.5	417.3
125°	452.3	452.7	453.0	453.4	453.8	454.2	454.7	455.3	455.9	456.4	456.4
127.5°	485.3	486.4	487.3	488.2	489.2	489.8	490.1	490.3	490.6	490.9	491.0
130°	509.4	510.0	510.6	511.3	511.9	512.4	512.8	513.2	513.5	513.9	513.8
132.5°	531.5	532.1	532.7	533.4	534.0	534.4	534.4	534.5	534.6	534.7	534.9
135°	561.8	562.5	563.3	564.1	564.8	565.3	565.6	565.8	566.1	566.3	566.6
137.5°	592.2	592.9	593.5	594.2	594.8	595.1	595.1	595.0	595.0	594.9	595.2
140°	610.2	611.0	611.7	612.5	613.2	613.5	613.2	613.0	612.7	612.5	612.6
142.5°	627.2	627.9	628.7	629.5	630.3	630.7	630.6	630.6	630.5	630.5	630.3
145°	652.2	653.0	653.8	654.5	655.3	655.6	655.5	655.4	655.2	655.1	655.1
147.5°	672.9	673.8	674.7	675.6	676.5	676.9	676.8	676.6	676.5	676.3	676.1
150°	686.2	687.2	688.2	689.3	690.3	690.6	690.4	690.1	689.9	689.6	689.4
152.5°	698.6	699.5	700.5	701.5	702.4	702.7	702.5	702.2	702.0	701.7	701.4
155°	715.0	716.1	717.1	718.1	719.1	719.4	719.0	718.7	718.3	717.9	717.6
157.5°	728.7	729.7	730.7	731.8	732.9	733.2	732.8	732.4	732.0	731.5	731.4
160°	737.5	738.5	739.5	740.5	741.5	741.8	741.3	740.8	740.3	739.8	739.6
162.5°	745.3	746.5	747.6	748.7	749.8	750.0	749.3	748.6	747.9	747.2	747.0
165°	755.9	757.0	758.0	759.0	760.0	760.1	759.4	758.6	757.8	757.1	757.0
167.5°	763.3	764.5	765.6	766.8	767.9	768.0	767.1	766.2	765.3	764.4	764.2
170°	767.5	768.6	769.7	770.9	772.0	772.1	771.1	770.1	769.0	768.0	767.9
172.5°	770.2	771.3	772.5	773.7	774.9	775.0	774.1	773.1	772.1	771.2	771.0
175°	773.8	775.0	776.1	777.3	778.4	778.5	777.4	776.4	775.4	774.4	774.3
177.5°	775.9	776.7	777.5	778.3	779.1	779.2	778.5	777.8	777.1	776.3	776.2
180°	777.3	777.3	777.3	777.3	777.3	777.3	777.3	777.3	777.3	777.3	777.3



TEST NUMBER: P333304-840

CATALOG NUMBER: S125DIP-S1270D590U840-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°	95°	100°	105°
0°	1854.7	1854.7	1854.7	1854.7	1854.7	1854.7	1854.7	1854.7	1854.7	1854.7	1854.7
2.5°	1908.2	1903.8	1898.7	1890.0	1879.3	1873.6	1864.7	1859.1	1847.8	1838.3	1828.3
5°	2005.0	1984.6	1965.7	1941.3	1914.5	1897.1	1876.7	1853.9	1830.3	1805.8	1779.1
7.5°	2105.4	2069.1	2029.7	1987.4	1946.0	1907.8	1871.5	1835.7	1802.4	1762.1	1728.0
10°	2172.7	2127.1	2078.2	2020.7	1964.9	1916.1	1866.4	1823.2	1779.1	1731.8	1690.1
12.5°	2240.1	2179.3	2110.3	2047.2	1980.0	1921.1	1862.7	1807.5	1752.0	1699.7	1651.1
15°	2287.6	2234.1	2170.3	2080.6	2005.0	1924.0	1846.8	1775.1	1708.3	1650.0	1588.6
17.5°	2319.0	2250.0	2181.5	2095.4	1996.4	1905.7	1818.3	1736.3	1660.8	1587.0	1527.8
20°	2324.6	2253.8	2182.1	2097.9	1996.4	1892.5	1805.0	1706.7	1625.6	1549.2	1476.8
22.5°	2322.8	2242.4	2164.5	2077.8	1978.7	1883.0	1777.4	1677.1	1589.0	1514.0	1438.4
25°	2304.9	2219.2	2121.5	2034.2	1936.5	1835.0	1728.0	1624.1	1534.3	1448.4	1373.7
27.5°	2290.2	2178.9	2068.3	1966.4	1872.2	1779.1	1676.6	1570.1	1470.7	1383.7	1313.2
30°	2271.9	2149.9	2025.5	1919.2	1822.4	1731.8	1635.1	1531.2	1427.2	1342.2	1266.7
32.5°	2255.5	2113.3	1982.1	1866.3	1763.8	1675.8	1586.5	1487.6	1385.6	1299.4	1223.8
35°	2223.9	2059.3	1908.9	1778.3	1668.9	1578.3	1503.6	1411.5	1317.8	1234.4	1162.0
37.5°	2183.7	1988.5	1827.1	1690.1	1570.1	1474.8	1405.1	1334.4	1244.6	1164.2	1098.6
40°	2152.2	1938.1	1767.3	1627.2	1502.8	1403.6	1339.1	1272.1	1197.4	1122.6	1053.3
42.5°	2112.5	1892.8	1706.9	1556.0	1432.9	1336.3	1268.5	1211.6	1145.7	1076.0	1011.7
45°	2039.6	1810.6	1609.0	1446.9	1322.5	1227.3	1157.2	1114.7	1065.1	999.0	944.6
47.5°	1932.5	1711.8	1503.4	1336.1	1207.7	1119.4	1053.8	1013.0	978.1	928.9	879.6
50°	1837.3	1638.2	1427.2	1261.1	1132.8	1043.8	983.2	946.2	916.4	878.5	836.8
52.5°	1730.9	1545.6	1352.3	1188.1	1061.0	973.3	913.9	881.4	856.5	829.4	788.3
55°	1561.9	1404.4	1224.9	1069.0	951.7	866.0	814.0	785.7	765.2	744.7	719.5
57.5°	1375.5	1252.4	1093.5	951.0	842.9	764.9	716.4	688.8	672.9	662.4	647.5
60°	1244.6	1139.1	1002.1	872.2	766.8	697.5	650.3	628.9	615.6	606.9	595.9
62.5°	1123.1	1036.4	909.6	791.0	698.7	633.2	591.1	570.4	557.6	553.4	544.3
65°	943.8	877.0	772.2	673.9	595.1	539.3	503.8	484.1	476.3	471.5	472.3
67.5°	767.4	726.6	642.5	558.6	495.7	448.9	420.5	405.5	401.5	395.2	395.1
70°	659.6	628.9	558.2	484.9	429.0	392.8	367.6	351.8	347.9	344.8	344.1
72.5°	564.6	537.7	476.3	417.6	367.3	335.5	314.8	305.3	298.8	296.9	296.8
75°	424.3	409.4	360.5	314.1	279.4	257.4	243.3	234.6	229.8	229.0	229.8
77.5°	301.6	288.6	257.6	224.7	202.8	186.1	174.1	171.2	165.8	165.9	165.1
80°	226.7	218.0	198.3	172.4	154.3	140.2	133.8	128.4	126.7	124.4	126.7
82.5°	164.4	155.1	141.7	125.1	110.2	101.7	95.4	93.7	92.7	91.6	92.1
85°	81.1	81.9	74.0	61.4	55.1	50.4	46.5	46.5	45.6	44.8	45.6
87.5°	29.2	27.8	25.0	23.0	19.6	17.6	16.7	17.2	15.5	15.0	15.9
90°	7.5	6.6	5.7	4.6	3.6	2.6	1.6	0.6	1.6	2.6	3.6
92.5°	7.7	6.9	6.1	6.0	6.8	7.5	8.2	8.9	8.2	7.5	6.8
95°	19.0	23.8	28.7	31.3	31.7	32.1	32.4	32.8	32.4	32.1	31.7
97.5°	47.6	57.3	66.9	71.3	70.6	70.0	69.3	68.6	69.3	70.0	70.6
100°	99.3	98.8	98.2	97.8	97.4	96.9	96.6	96.2	96.6	96.9	97.4
102.5°	127.3	126.9	126.6	126.2	125.8	125.3	124.8	124.3	124.8	125.3	125.8
105°	171.7	171.7	171.7	171.5	171.0	170.5	169.9	169.4	169.9	170.5	171.0
107.5°	216.8	216.5	216.3	216.2	216.2	216.2	216.2	216.2	216.2	216.2	216.2
110°	247.2	247.0	246.7	246.6	246.6	246.6	246.6	246.6	246.6	246.6	246.6



TEST NUMBER: P333304-840

CATALOG NUMBER: S125DIP-S1270D590U840-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°	95°	100°	105°
112.5°	276.9	276.8	276.6	276.4	276.1	275.8	275.5	275.2	275.5	275.8	276.1
115°	321.2	321.1	321.0	320.6	319.9	319.3	318.7	318.0	318.7	319.3	319.9
117.5°	363.6	363.0	362.5	362.3	362.3	362.3	362.3	362.4	362.3	362.3	362.3
120°	390.4	390.1	389.7	389.5	389.7	389.8	389.9	390.1	389.9	389.8	389.7
122.5°	417.2	417.0	416.8	416.5	416.0	415.5	415.0	414.4	415.0	415.5	416.0
125°	456.4	456.4	456.4	455.9	454.9	454.0	453.2	452.3	453.2	454.0	454.9
127.5°	491.1	491.1	491.2	490.9	490.3	489.7	489.0	488.4	489.0	489.7	490.3
130°	513.7	513.5	513.4	513.0	512.4	511.8	511.1	510.5	511.1	511.8	512.4
132.5°	535.2	535.5	535.8	535.5	534.8	534.1	533.3	532.6	533.3	534.1	534.8
135°	566.8	567.1	567.4	567.1	566.3	565.6	564.8	564.1	564.8	565.6	566.3
137.5°	595.4	595.6	595.9	595.6	595.0	594.3	593.7	593.0	593.7	594.3	595.0
140°	612.7	612.9	613.0	612.9	612.7	612.4	612.2	611.9	612.2	612.4	612.7
142.5°	630.1	630.0	629.8	629.5	629.4	629.2	629.1	628.9	629.1	629.2	629.4
145°	655.1	655.1	655.1	655.0	654.7	654.5	654.2	654.0	654.2	654.5	654.7
147.5°	676.0	675.8	675.7	675.6	675.7	675.7	675.8	675.8	675.8	675.7	675.7
150°	689.1	688.9	688.6	688.6	688.9	689.1	689.4	689.6	689.4	689.1	688.9
152.5°	701.1	700.8	700.6	700.7	701.4	702.0	702.5	703.1	702.5	702.0	701.4
155°	717.4	717.1	716.9	717.1	717.9	718.7	719.4	720.2	719.4	718.7	717.9
157.5°	731.4	731.4	731.4	731.6	732.1	732.6	733.0	733.5	733.0	732.6	732.1
160°	739.5	739.4	739.3	739.6	740.3	741.1	741.9	742.7	741.9	741.1	740.3
162.5°	746.9	746.8	746.7	747.0	747.7	748.5	749.3	750.0	749.3	748.5	747.7
165°	756.8	756.7	756.6	756.9	757.7	758.4	759.2	759.9	759.2	758.4	757.7
167.5°	764.1	764.0	763.9	764.2	765.0	765.8	766.6	767.3	766.6	765.8	765.0
170°	767.8	767.6	767.5	767.9	768.8	769.7	770.6	771.5	770.6	769.7	768.8
172.5°	770.8	770.5	770.3	770.6	771.5	772.4	773.4	774.3	773.4	772.4	771.5
175°	774.2	774.0	773.9	774.2	775.0	775.7	776.5	777.3	776.5	775.7	775.0
177.5°	776.1	776.0	775.9	776.2	776.8	777.4	778.0	778.6	778.0	777.4	776.8
180°	777.3	777.3	777.3	777.3	777.3	777.3	777.3	777.3	777.3	777.3	777.3



TEST NUMBER: P333304-840

CATALOG NUMBER: S125DIP-S1270D590U840-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	110°	115°	120°	125°	130°	135°	140°	145°	150°	155°	160°
0°	1854.7	1854.7	1854.7	1854.7	1854.7	1854.7	1854.7	1854.7	1854.7	1854.7	1854.7
2.5°	1822.5	1815.6	1810.0	1797.4	1790.4	1781.0	1773.4	1781.6	1772.8	1776.6	1770.9
5°	1765.7	1743.6	1728.0	1705.1	1685.5	1667.3	1654.0	1651.5	1645.3	1642.1	1632.6
7.5°	1697.4	1669.8	1642.7	1612.9	1587.6	1562.0	1545.6	1532.1	1523.1	1511.3	1503.3
10°	1657.1	1620.1	1588.6	1552.4	1520.9	1493.4	1471.3	1460.3	1450.1	1435.1	1429.6
12.5°	1607.3	1569.0	1530.7	1492.0	1461.7	1431.0	1412.1	1395.4	1388.4	1371.5	1369.8
15°	1547.6	1490.2	1452.4	1413.0	1371.3	1346.2	1330.4	1312.3	1304.4	1292.6	1283.9
17.5°	1476.5	1425.1	1378.0	1337.2	1301.4	1280.2	1260.6	1248.2	1234.7	1227.0	1212.7
20°	1424.8	1376.0	1328.8	1285.6	1258.0	1233.6	1217.8	1206.0	1191.8	1187.9	1173.8
22.5°	1381.4	1327.6	1282.2	1245.9	1215.8	1188.2	1171.2	1163.2	1153.5	1141.3	1138.4
25°	1310.7	1254.9	1216.3	1180.0	1153.3	1128.1	1116.3	1106.0	1096.6	1087.9	1084.8
27.5°	1249.6	1199.7	1153.9	1121.2	1097.8	1074.9	1064.5	1052.1	1045.1	1038.1	1029.7
30°	1206.8	1155.6	1115.5	1084.0	1058.8	1038.3	1027.3	1018.7	1012.4	1006.0	1001.4
32.5°	1162.8	1115.3	1076.4	1045.6	1020.4	1004.9	995.2	989.1	982.1	974.5	968.6
35°	1104.5	1052.5	1014.7	988.0	968.3	956.4	945.4	939.9	932.1	932.1	925.7
37.5°	1038.8	993.9	960.6	936.1	918.5	908.0	896.1	892.2	887.2	883.8	881.7
40°	999.8	958.1	926.6	902.1	883.2	874.5	865.2	858.9	855.7	851.7	850.2
42.5°	959.5	919.6	889.4	866.9	850.5	843.1	834.2	829.9	823.5	818.4	817.5
45°	898.2	859.6	832.1	814.0	799.8	791.1	785.7	776.2	773.1	766.8	766.0
47.5°	840.1	803.1	776.1	761.2	748.8	741.7	733.1	723.6	720.0	716.8	716.5
50°	796.7	762.9	737.6	723.5	711.7	701.5	692.8	686.4	684.1	684.1	685.7
52.5°	752.6	723.8	702.4	685.0	673.9	663.0	655.0	651.2	647.5	651.4	654.2
55°	688.0	658.9	643.2	626.6	615.6	603.0	599.1	597.5	595.1	601.5	604.6
57.5°	619.7	599.3	580.8	564.4	554.5	547.2	541.9	541.0	545.4	548.4	558.6
60°	576.2	552.6	536.1	523.5	511.7	507.0	505.4	503.8	507.0	515.6	529.0
62.5°	528.4	509.2	491.4	481.9	473.2	465.4	465.0	466.1	472.3	482.2	495.6
65°	458.2	441.6	429.8	418.8	411.7	407.0	408.6	411.7	418.8	432.2	447.2
67.5°	386.9	375.5	365.0	356.0	349.2	349.2	350.8	355.5	363.9	379.3	392.9
70°	340.8	328.3	319.6	315.7	310.1	307.0	311.7	319.6	326.7	340.8	352.6
72.5°	294.9	284.2	277.4	274.8	272.4	269.8	271.5	279.9	289.5	303.7	317.4
75°	226.7	222.8	218.0	214.9	212.6	214.1	215.7	223.6	231.5	246.4	262.2
77.5°	165.5	161.4	158.5	157.7	156.5	157.2	161.7	167.5	175.2	186.1	198.0
80°	125.1	123.6	122.0	121.2	121.2	122.0	128.4	132.3	139.4	149.6	159.1
82.5°	91.2	90.2	89.9	89.8	90.4	90.5	94.3	99.5	105.3	113.0	121.2
85°	48.1	46.5	48.8	49.6	48.1	50.4	51.9	55.1	57.5	61.4	65.3
87.5°	16.7	18.2	17.7	18.5	18.7	20.1	19.6	22.2	23.6	25.0	24.5
90°	4.6	5.7	6.6	7.5	8.3	9.2	9.9	10.5	11.1	11.8	12.3
92.5°	6.0	6.1	6.9	7.7	8.4	9.2	9.9	10.5	11.1	11.8	12.2
95°	31.3	28.7	23.8	19.0	14.0	9.2	9.9	10.5	11.1	11.8	12.1
97.5°	71.3	66.9	57.3	47.6	38.0	28.4	24.7	21.1	17.5	13.9	12.1
100°	97.8	98.2	98.8	99.3	99.8	100.3	81.2	62.1	43.0	23.9	14.1
102.5°	126.2	126.6	126.9	127.3	127.6	127.9	124.3	120.7	117.0	113.5	107.3
105°	171.5	171.7	171.7	171.7	171.7	171.7	171.7	171.7	171.7	171.7	171.7
107.5°	216.2	216.3	216.5	216.8	217.1	217.3	217.3	217.4	217.4	217.4	217.2
110°	246.6	246.7	247.0	247.2	247.5	247.7	247.4	247.0	246.6	246.2	246.1



TEST NUMBER: P333304-840

CATALOG NUMBER: S125DIP-S1270D590U840-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	110°	115°	120°	125°	130°	135°	140°	145°	150°	155°	160°
112.5°	276.4	276.6	276.8	276.9	277.1	277.2	276.8	276.3	275.8	275.3	275.0
115°	320.6	321.0	321.1	321.2	321.3	321.5	321.0	320.4	319.9	319.4	318.8
117.5°	362.3	362.5	363.0	363.6	364.0	364.5	363.9	363.1	362.4	361.8	361.3
120°	389.5	389.7	390.1	390.4	390.8	391.2	390.9	390.7	390.4	390.2	389.7
122.5°	416.5	416.8	417.0	417.2	417.3	417.5	417.3	417.0	416.8	416.5	416.0
125°	455.9	456.4	456.4	456.4	456.4	456.4	455.9	455.3	454.7	454.2	453.8
127.5°	490.9	491.2	491.1	491.1	491.0	490.9	490.6	490.3	490.1	489.8	489.2
130°	513.0	513.4	513.5	513.7	513.8	513.9	513.5	513.2	512.8	512.4	511.9
132.5°	535.5	535.8	535.5	535.2	534.9	534.7	534.6	534.5	534.4	534.4	534.0
135°	567.1	567.4	567.1	566.8	566.6	566.3	566.1	565.8	565.6	565.3	564.8
137.5°	595.6	595.9	595.6	595.4	595.2	594.9	595.0	595.0	595.1	595.1	594.8
140°	612.9	613.0	612.9	612.7	612.6	612.5	612.7	613.0	613.2	613.5	613.2
142.5°	629.5	629.8	630.0	630.1	630.3	630.5	630.5	630.6	630.6	630.7	630.3
145°	655.0	655.1	655.1	655.1	655.1	655.1	655.2	655.4	655.5	655.6	655.3
147.5°	675.6	675.7	675.8	676.0	676.1	676.3	676.5	676.6	676.8	676.9	676.5
150°	688.6	688.6	688.9	689.1	689.4	689.6	689.9	690.1	690.4	690.6	690.3
152.5°	700.7	700.6	700.8	701.1	701.4	701.7	702.0	702.2	702.5	702.7	702.4
155°	717.1	716.9	717.1	717.4	717.6	717.9	718.3	718.7	719.0	719.4	719.1
157.5°	731.6	731.4	731.4	731.4	731.4	731.5	732.0	732.4	732.8	733.2	732.9
160°	739.6	739.3	739.4	739.5	739.6	739.8	740.3	740.8	741.3	741.8	741.5
162.5°	747.0	746.7	746.8	746.9	747.0	747.2	747.9	748.6	749.3	750.0	749.8
165°	756.9	756.6	756.7	756.8	757.0	757.1	757.8	758.6	759.4	760.1	760.0
167.5°	764.2	763.9	764.0	764.1	764.2	764.4	765.3	766.2	767.1	768.0	767.9
170°	767.9	767.5	767.6	767.8	767.9	768.0	769.0	770.1	771.1	772.1	772.0
172.5°	770.6	770.3	770.5	770.8	771.0	771.2	772.1	773.1	774.1	775.0	774.9
175°	774.2	773.9	774.0	774.2	774.3	774.4	775.4	776.4	777.4	778.5	778.4
177.5°	776.2	775.9	776.0	776.1	776.2	776.3	777.1	777.8	778.5	779.2	779.1
180°	777.3	777.3	777.3	777.3	777.3	777.3	777.3	777.3	777.3	777.3	777.3



TEST NUMBER: P333304-840

CATALOG NUMBER: S125DIP-S1270D590U840-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	165°	170°	175°	180°	185°	190°	195°	200°	205°	210°	215°
0°	1854.7	1854.7	1854.7	1854.7	1854.7	1854.7	1854.7	1854.7	1854.7	1854.7	1854.7
2.5°	1767.2	1771.5	1767.8	1772.8	1767.8	1771.5	1767.2	1770.9	1776.6	1772.8	1781.6
5°	1628.7	1621.6	1626.4	1623.3	1626.4	1621.6	1628.7	1632.6	1642.1	1645.3	1651.5
7.5°	1500.9	1494.1	1486.4	1482.8	1486.4	1494.1	1500.9	1503.3	1511.3	1523.1	1532.1
10°	1420.9	1412.3	1411.5	1405.9	1411.5	1412.3	1420.9	1429.6	1435.1	1450.1	1460.3
12.5°	1362.3	1354.3	1345.3	1343.0	1345.3	1354.3	1362.3	1369.8	1371.5	1388.4	1395.4
15°	1279.2	1272.9	1267.4	1272.1	1267.4	1272.9	1279.2	1283.9	1292.6	1304.4	1312.3
17.5°	1210.1	1204.9	1204.0	1198.1	1204.0	1204.9	1210.1	1212.7	1227.0	1234.7	1248.2
20°	1166.7	1162.8	1164.3	1154.1	1164.3	1162.8	1166.7	1173.8	1187.9	1191.8	1206.0
22.5°	1132.1	1124.3	1123.4	1121.4	1123.4	1124.3	1132.1	1138.4	1141.3	1153.5	1163.2
25°	1077.7	1073.8	1069.9	1073.8	1069.9	1073.8	1077.7	1084.8	1087.9	1096.6	1106.0
27.5°	1030.3	1025.6	1024.5	1024.9	1024.5	1025.6	1030.3	1029.7	1038.1	1045.1	1052.1
30°	1001.4	993.5	994.2	993.5	994.2	993.5	1001.4	1001.4	1006.0	1012.4	1018.7
32.5°	969.9	964.5	963.4	962.0	963.4	964.5	969.9	968.6	974.5	982.1	989.1
35°	923.4	923.4	919.5	919.5	919.5	923.4	923.4	925.7	932.1	932.1	939.9
37.5°	879.8	879.0	876.7	877.0	876.7	879.0	879.8	881.7	883.8	887.2	892.2
40°	847.1	846.3	843.8	839.2	843.8	846.3	847.1	850.2	851.7	855.7	858.9
42.5°	815.6	812.8	811.7	810.2	811.7	812.8	815.6	817.5	818.4	823.5	829.9
45°	766.0	766.0	764.4	763.6	764.4	766.0	766.0	766.0	766.8	773.1	776.2
47.5°	717.8	719.2	722.2	721.8	722.2	719.2	717.8	716.5	716.8	720.0	723.6
50°	688.8	689.6	692.0	692.8	692.0	689.6	688.8	685.7	684.1	684.1	686.4
52.5°	656.7	661.3	664.3	663.8	664.3	661.3	656.7	654.2	651.4	647.5	651.2
55°	611.7	617.1	622.7	623.5	622.7	617.1	611.7	604.6	601.5	595.1	597.5
57.5°	567.1	574.8	580.7	582.5	580.7	574.8	567.1	558.6	548.4	545.4	541.0
60°	536.8	547.1	554.2	557.3	554.2	547.1	536.8	529.0	515.6	507.0	503.8
62.5°	507.9	519.4	526.4	527.1	526.4	519.4	507.9	495.6	482.2	472.3	466.1
65°	460.5	472.3	478.6	483.3	478.6	472.3	460.5	447.2	432.2	418.8	411.7
67.5°	409.5	421.3	428.3	432.0	428.3	421.3	409.5	392.9	379.3	363.9	355.5
70°	372.3	384.2	393.6	396.8	393.6	384.2	372.3	352.6	340.8	326.7	319.6
72.5°	335.8	346.4	354.0	357.7	354.0	346.4	335.8	317.4	303.7	289.5	279.9
75°	272.4	286.5	293.7	297.6	293.7	286.5	272.4	262.2	246.4	231.5	223.6
77.5°	210.1	223.0	227.2	229.2	227.2	223.0	210.1	198.0	186.1	175.2	167.5
80°	168.4	176.3	181.9	182.6	181.9	176.3	168.4	159.1	149.6	139.4	132.3
82.5°	129.5	136.0	137.7	139.8	137.7	136.0	129.5	121.2	113.0	105.3	99.5
85°	70.9	74.0	74.8	74.0	74.8	74.0	70.9	65.3	61.4	57.5	55.1
87.5°	25.9	25.2	25.3	26.7	25.3	25.2	25.9	24.5	25.0	23.6	22.2
90°	12.7	13.0	13.4	13.8	13.4	13.0	12.7	12.3	11.8	11.1	10.5
92.5°	12.3	12.5	12.7	12.9	12.7	12.5	12.3	12.2	11.8	11.1	10.5
95°	12.1	12.1	12.1	12.1	12.1	12.1	12.1	12.1	11.8	11.1	10.5
97.5°	12.1	12.1	12.1	12.1	12.1	12.1	12.1	12.1	13.9	17.5	21.1
100°	13.6	13.1	12.6	12.1	12.6	13.1	13.6	14.1	23.9	43.0	62.1
102.5°	98.6	89.9	81.2	72.5	81.2	89.9	98.6	107.3	113.5	117.0	120.7
105°	171.5	171.4	171.3	171.1	171.3	171.4	171.5	171.7	171.7	171.7	171.7
107.5°	216.9	216.5	216.1	215.7	216.1	216.5	216.9	217.2	217.4	217.4	217.4
110°	246.2	246.3	246.5	246.6	246.5	246.3	246.2	246.1	246.2	246.6	247.0



TEST NUMBER: P333304-840

CATALOG NUMBER: S125DIP-S1270D590U840-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	165°	170°	175°	180°	185°	190°	195°	200°	205°	210°	215°
112.5°	274.8	274.6	274.5	274.3	274.5	274.6	274.8	275.0	275.3	275.8	276.3
115°	318.0	317.3	316.5	315.8	316.5	317.3	318.0	318.8	319.4	319.9	320.4
117.5°	361.0	360.6	360.3	360.0	360.3	360.6	361.0	361.3	361.8	362.4	363.1
120°	389.1	388.5	387.8	387.2	387.8	388.5	389.1	389.7	390.2	390.4	390.7
122.5°	415.3	414.4	413.7	413.0	413.7	414.4	415.3	416.0	416.5	416.8	417.0
125°	453.4	453.0	452.7	452.3	452.7	453.0	453.4	453.8	454.2	454.7	455.3
127.5°	488.2	487.3	486.4	485.3	486.4	487.3	488.2	489.2	489.8	490.1	490.3
130°	511.3	510.6	510.0	509.4	510.0	510.6	511.3	511.9	512.4	512.8	513.2
132.5°	533.4	532.7	532.1	531.5	532.1	532.7	533.4	534.0	534.4	534.4	534.5
135°	564.1	563.3	562.5	561.8	562.5	563.3	564.1	564.8	565.3	565.6	565.8
137.5°	594.2	593.5	592.9	592.2	592.9	593.5	594.2	594.8	595.1	595.1	595.0
140°	612.5	611.7	611.0	610.2	611.0	611.7	612.5	613.2	613.5	613.2	613.0
142.5°	629.5	628.7	627.9	627.2	627.9	628.7	629.5	630.3	630.7	630.6	630.6
145°	654.5	653.8	653.0	652.2	653.0	653.8	654.5	655.3	655.6	655.5	655.4
147.5°	675.6	674.7	673.8	672.9	673.8	674.7	675.6	676.5	676.9	676.8	676.6
150°	689.3	688.2	687.2	686.2	687.2	688.2	689.3	690.3	690.6	690.4	690.1
152.5°	701.5	700.5	699.5	698.6	699.5	700.5	701.5	702.4	702.7	702.5	702.2
155°	718.1	717.1	716.1	715.0	716.1	717.1	718.1	719.1	719.4	719.0	718.7
157.5°	731.8	730.7	729.7	728.7	729.7	730.7	731.8	732.9	733.2	732.8	732.4
160°	740.5	739.5	738.5	737.5	738.5	739.5	740.5	741.5	741.8	741.3	740.8
162.5°	748.7	747.6	746.5	745.3	746.5	747.6	748.7	749.8	750.0	749.3	748.6
165°	759.0	758.0	757.0	755.9	757.0	758.0	759.0	760.0	760.1	759.4	758.6
167.5°	766.8	765.6	764.5	763.3	764.5	765.6	766.8	767.9	768.0	767.1	766.2
170°	770.9	769.7	768.6	767.5	768.6	769.7	770.9	772.0	772.1	771.1	770.1
172.5°	773.7	772.5	771.3	770.2	771.3	772.5	773.7	774.9	775.0	774.1	773.1
175°	777.3	776.1	775.0	773.8	775.0	776.1	777.3	778.4	778.5	777.4	776.4
177.5°	778.3	777.5	776.7	775.9	776.7	777.5	778.3	779.1	779.2	778.5	777.8
180°	777.3	777.3	777.3	777.3	777.3	777.3	777.3	777.3	777.3	777.3	777.3



TEST NUMBER: P333304-840

CATALOG NUMBER: S125DIP-S1270D590U840-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	220°	225°	230°	235°	240°	245°	250°	255°	260°	265°	270°
0°	1854.7	1854.7	1854.7	1854.7	1854.7	1854.7	1854.7	1854.7	1854.7	1854.7	1854.7
2.5°	1773.4	1781.0	1790.4	1797.4	1810.0	1815.6	1822.5	1828.3	1838.3	1847.8	1859.1
5°	1654.0	1667.3	1685.5	1705.1	1728.0	1743.6	1765.7	1779.1	1805.8	1830.3	1853.9
7.5°	1545.6	1562.0	1587.6	1612.9	1642.7	1669.8	1697.4	1728.0	1762.1	1802.4	1835.7
10°	1471.3	1493.4	1520.9	1552.4	1588.6	1620.1	1657.1	1690.1	1731.8	1779.1	1823.2
12.5°	1412.1	1431.0	1461.7	1492.0	1530.7	1569.0	1607.3	1651.1	1699.7	1752.0	1807.5
15°	1330.4	1346.2	1371.3	1413.0	1452.4	1490.2	1547.6	1588.6	1650.0	1708.3	1775.1
17.5°	1260.6	1280.2	1301.4	1337.2	1378.0	1425.1	1476.5	1527.8	1587.0	1660.8	1736.3
20°	1217.8	1233.6	1258.0	1285.6	1328.8	1376.0	1424.8	1476.8	1549.2	1625.6	1706.7
22.5°	1171.2	1188.2	1215.8	1245.9	1282.2	1327.6	1381.4	1438.4	1514.0	1589.0	1677.1
25°	1116.3	1128.1	1153.3	1180.0	1216.3	1254.9	1310.7	1373.7	1448.4	1534.3	1624.1
27.5°	1064.5	1074.9	1097.8	1121.2	1153.9	1199.7	1249.6	1313.2	1383.7	1470.7	1570.1
30°	1027.3	1038.3	1058.8	1084.0	1115.5	1155.6	1206.8	1266.7	1342.2	1427.2	1531.2
32.5°	995.2	1004.9	1020.4	1045.6	1076.4	1115.3	1162.8	1223.8	1299.4	1385.6	1487.6
35°	945.4	956.4	968.3	988.0	1014.7	1052.5	1104.5	1162.0	1234.4	1317.8	1411.5
37.5°	896.1	908.0	918.5	936.1	960.6	993.9	1038.8	1098.6	1164.2	1244.6	1334.4
40°	865.2	874.5	883.2	902.1	926.6	958.1	999.8	1053.3	1122.6	1197.4	1272.1
42.5°	834.2	843.1	850.5	866.9	889.4	919.6	959.5	1011.7	1076.0	1145.7	1211.6
45°	785.7	791.1	799.8	814.0	832.1	859.6	898.2	944.6	999.0	1065.1	1114.7
47.5°	733.1	741.7	748.8	761.2	776.1	803.1	840.1	879.6	928.9	978.1	1013.0
50°	692.8	701.5	711.7	723.5	737.6	762.9	796.7	836.8	878.5	916.4	946.2
52.5°	655.0	663.0	673.9	685.0	702.4	723.8	752.6	788.3	829.4	856.5	881.4
55°	599.1	603.0	615.6	626.6	643.2	658.9	688.0	719.5	744.7	765.2	785.7
57.5°	541.9	547.2	554.5	564.4	580.8	599.3	619.7	647.5	662.4	672.9	688.8
60°	505.4	507.0	511.7	523.5	536.1	552.6	576.2	595.9	606.9	615.6	628.9
62.5°	465.0	465.4	473.2	481.9	491.4	509.2	528.4	544.3	553.4	557.6	570.4
65°	408.6	407.0	411.7	418.8	429.8	441.6	458.2	472.3	471.5	476.3	484.1
67.5°	350.8	349.2	349.2	356.0	365.0	375.5	386.9	395.1	395.2	401.5	405.5
70°	311.7	307.0	310.1	315.7	319.6	328.3	340.8	344.1	344.8	347.9	351.8
72.5°	271.5	269.8	272.4	274.8	277.4	284.2	294.9	296.8	296.9	298.8	305.3
75°	215.7	214.1	212.6	214.9	218.0	222.8	226.7	229.8	229.0	229.8	234.6
77.5°	161.7	157.2	156.5	157.7	158.5	161.4	165.5	165.1	165.9	165.8	171.2
80°	128.4	122.0	121.2	121.2	122.0	123.6	125.1	126.7	124.4	126.7	128.4
82.5°	94.3	90.5	90.4	89.8	89.9	90.2	91.2	92.1	91.6	92.7	93.7
85°	51.9	50.4	48.1	49.6	48.8	46.5	48.1	45.6	44.8	45.6	46.5
87.5°	19.6	20.1	18.7	18.5	17.7	18.2	16.7	15.9	15.0	15.5	17.2
90°	9.9	9.2	8.3	7.5	6.6	5.7	4.6	3.6	2.6	1.6	0.6
92.5°	9.9	9.2	8.4	7.7	6.9	6.1	6.0	6.8	7.5	8.2	8.9
95°	9.9	9.2	14.0	19.0	23.8	28.7	31.3	31.7	32.1	32.4	32.8
97.5°	24.7	28.4	38.0	47.6	57.3	66.9	71.3	70.6	70.0	69.3	68.6
100°	81.2	100.3	99.8	99.3	98.8	98.2	97.8	97.4	96.9	96.6	96.2
102.5°	124.3	127.9	127.6	127.3	126.9	126.6	126.2	125.8	125.3	124.8	124.3
105°	171.7	171.7	171.7	171.7	171.7	171.7	171.5	171.0	170.5	169.9	169.4
107.5°	217.3	217.3	217.1	216.8	216.5	216.3	216.2	216.2	216.2	216.2	216.2
110°	247.4	247.7	247.5	247.2	247.0	246.7	246.6	246.6	246.6	246.6	246.6



TEST NUMBER: P333304-840

CATALOG NUMBER: S125DIP-S1270D590U840-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	220°	225°	230°	235°	240°	245°	250°	255°	260°	265°	270°
112.5°	276.8	277.2	277.1	276.9	276.8	276.6	276.4	276.1	275.8	275.5	275.2
115°	321.0	321.5	321.3	321.2	321.1	321.0	320.6	319.9	319.3	318.7	318.0
117.5°	363.9	364.5	364.0	363.6	363.0	362.5	362.3	362.3	362.3	362.3	362.4
120°	390.9	391.2	390.8	390.4	390.1	389.7	389.5	389.7	389.8	389.9	390.1
122.5°	417.3	417.5	417.3	417.2	417.0	416.8	416.5	416.0	415.5	415.0	414.4
125°	455.9	456.4	456.4	456.4	456.4	456.4	455.9	454.9	454.0	453.2	452.3
127.5°	490.6	490.9	491.0	491.1	491.1	491.2	490.9	490.3	489.7	489.0	488.4
130°	513.5	513.9	513.8	513.7	513.5	513.4	513.0	512.4	511.8	511.1	510.5
132.5°	534.6	534.7	534.9	535.2	535.5	535.8	535.5	534.8	534.1	533.3	532.6
135°	566.1	566.3	566.6	566.8	567.1	567.4	567.1	566.3	565.6	564.8	564.1
137.5°	595.0	594.9	595.2	595.4	595.6	595.9	595.6	595.0	594.3	593.7	593.0
140°	612.7	612.5	612.6	612.7	612.9	613.0	612.9	612.7	612.4	612.2	611.9
142.5°	630.5	630.5	630.3	630.1	630.0	629.8	629.5	629.4	629.2	629.1	628.9
145°	655.2	655.1	655.1	655.1	655.1	655.1	655.0	654.7	654.5	654.2	654.0
147.5°	676.5	676.3	676.1	676.0	675.8	675.7	675.6	675.7	675.7	675.8	675.8
150°	689.9	689.6	689.4	689.1	688.9	688.6	688.6	688.9	689.1	689.4	689.6
152.5°	702.0	701.7	701.4	701.1	700.8	700.6	700.7	701.4	702.0	702.5	703.1
155°	718.3	717.9	717.6	717.4	717.1	716.9	717.1	717.9	718.7	719.4	720.2
157.5°	732.0	731.5	731.4	731.4	731.4	731.4	731.6	732.1	732.6	733.0	733.5
160°	740.3	739.8	739.6	739.5	739.4	739.3	739.6	740.3	741.1	741.9	742.7
162.5°	747.9	747.2	747.0	746.9	746.8	746.7	747.0	747.7	748.5	749.3	750.0
165°	757.8	757.1	757.0	756.8	756.7	756.6	756.9	757.7	758.4	759.2	759.9
167.5°	765.3	764.4	764.2	764.1	764.0	763.9	764.2	765.0	765.8	766.6	767.3
170°	769.0	768.0	767.9	767.8	767.6	767.5	767.9	768.8	769.7	770.6	771.5
172.5°	772.1	771.2	771.0	770.8	770.5	770.3	770.6	771.5	772.4	773.4	774.3
175°	775.4	774.4	774.3	774.2	774.0	773.9	774.2	775.0	775.7	776.5	777.3
177.5°	777.1	776.3	776.2	776.1	776.0	775.9	776.2	776.8	777.4	778.0	778.6
180°	777.3	777.3	777.3	777.3	777.3	777.3	777.3	777.3	777.3	777.3	777.3



TEST NUMBER: P333304-840

CATALOG NUMBER: S125DIP-S1270D590U840-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	275°	280°	285°	290°	295°	300°	305°	310°	315°	320°	325°
0°	1854.7	1854.7	1854.7	1854.7	1854.7	1854.7	1854.7	1854.7	1854.7	1854.7	1854.7
2.5°	1864.7	1873.6	1879.3	1890.0	1898.7	1903.8	1908.2	1912.0	1916.4	1920.2	1930.9
5°	1876.7	1897.1	1914.5	1941.3	1965.7	1984.6	2005.0	2023.2	2038.1	2059.3	2075.9
7.5°	1871.5	1907.8	1946.0	1987.4	2029.7	2069.1	2105.4	2139.2	2169.9	2207.1	2239.6
10°	1866.4	1916.1	1964.9	2020.7	2078.2	2127.1	2172.7	2219.2	2253.0	2300.3	2340.4
12.5°	1862.7	1921.1	1980.0	2047.2	2110.3	2179.3	2240.1	2273.9	2325.4	2363.2	2411.0
15°	1846.8	1924.0	2005.0	2080.6	2170.3	2234.1	2287.6	2353.8	2401.8	2449.8	2501.7
17.5°	1818.3	1905.7	1996.4	2095.4	2181.5	2250.0	2319.0	2382.8	2440.0	2504.5	2569.1
20°	1805.0	1892.5	1996.4	2097.9	2182.1	2253.8	2324.6	2394.7	2457.7	2540.3	2615.1
22.5°	1777.4	1883.0	1978.7	2077.8	2164.5	2242.4	2322.8	2402.3	2486.0	2579.4	2673.0
25°	1728.0	1835.0	1936.5	2034.2	2121.5	2219.2	2304.9	2411.3	2518.3	2641.9	2758.3
27.5°	1676.6	1779.1	1872.2	1966.4	2068.3	2178.9	2290.2	2410.7	2550.9	2706.9	2871.2
30°	1635.1	1731.8	1822.4	1919.2	2025.5	2149.9	2271.9	2415.2	2577.4	2752.9	2948.1
32.5°	1586.5	1675.8	1763.8	1866.3	1982.1	2113.3	2255.5	2412.7	2607.6	2807.0	3008.0
35°	1503.6	1578.3	1668.9	1778.3	1908.9	2059.3	2223.9	2409.6	2633.2	2862.3	3031.5
37.5°	1405.1	1474.8	1570.1	1690.1	1827.1	1988.5	2183.7	2404.2	2641.6	2824.2	2878.8
40°	1339.1	1403.6	1502.8	1627.2	1767.3	1938.1	2152.2	2385.3	2615.1	2731.6	2686.7
42.5°	1268.5	1336.3	1432.9	1556.0	1706.9	1892.8	2112.5	2345.6	2538.3	2582.3	2427.3
45°	1157.2	1227.3	1322.5	1446.9	1609.0	1810.6	2039.6	2251.4	2362.4	2282.9	2042.9
47.5°	1053.8	1119.4	1207.7	1336.1	1503.4	1711.8	1932.5	2101.4	2110.2	1920.5	1664.1
50°	983.2	1043.8	1132.8	1261.1	1427.2	1638.2	1837.3	1970.3	1910.6	1695.7	1449.3
52.5°	913.9	973.3	1061.0	1188.1	1352.3	1545.6	1730.9	1824.3	1711.5	1491.0	1280.5
55°	814.0	866.0	951.7	1069.0	1224.9	1404.4	1561.9	1594.1	1447.6	1230.4	1059.6
57.5°	716.4	764.9	842.9	951.0	1093.5	1252.4	1375.5	1368.7	1213.9	1027.4	891.9
60°	650.3	697.5	766.8	872.2	1002.1	1139.1	1244.6	1219.4	1065.9	905.3	791.1
62.5°	591.1	633.2	698.7	791.0	909.6	1036.4	1123.1	1085.9	935.5	795.1	704.9
65°	503.8	539.3	595.1	673.9	772.2	877.0	943.8	895.9	767.5	658.1	585.7
67.5°	420.5	448.9	495.7	558.6	642.5	726.6	767.4	719.0	616.4	536.5	482.9
70°	367.6	392.8	429.0	484.9	558.2	628.9	659.6	616.4	528.3	459.7	421.1
72.5°	314.8	335.5	367.3	417.6	476.3	537.7	564.6	523.2	450.8	392.9	356.9
75°	243.3	257.4	279.4	314.1	360.5	409.4	424.3	388.1	341.6	298.3	274.8
77.5°	174.1	186.1	202.8	224.7	257.6	288.6	301.6	280.7	244.8	217.4	198.0
80°	133.8	140.2	154.3	172.4	198.3	218.0	226.7	213.4	188.1	167.6	152.7
82.5°	95.4	101.7	110.2	125.1	141.7	155.1	164.4	155.4	137.1	121.1	112.4
85°	46.5	50.4	55.1	61.4	74.0	81.9	81.1	75.5	68.5	62.2	57.5
87.5°	16.7	17.6	19.6	23.0	25.0	27.8	29.2	28.1	25.8	24.0	22.2
90°	1.6	2.6	3.6	4.6	5.7	6.6	7.5	8.3	9.2	9.9	10.5
92.5°	8.2	7.5	6.8	6.0	6.1	6.9	7.7	8.4	9.2	9.9	10.5
95°	32.4	32.1	31.7	31.3	28.7	23.8	19.0	14.0	9.2	9.9	10.5
97.5°	69.3	70.0	70.6	71.3	66.9	57.3	47.6	38.0	28.4	24.7	21.1
100°	96.6	96.9	97.4	97.8	98.2	98.8	99.3	99.8	100.3	81.2	62.1
102.5°	124.8	125.3	125.8	126.2	126.6	126.9	127.3	127.6	127.9	124.3	120.7
105°	169.9	170.5	171.0	171.5	171.7	171.7	171.7	171.7	171.7	171.7	171.7
107.5°	216.2	216.2	216.2	216.2	216.3	216.5	216.8	217.1	217.3	217.3	217.4
110°	246.6	246.6	246.6	246.6	246.7	247.0	247.2	247.5	247.7	247.4	247.0



TEST NUMBER: P333304-840

CATALOG NUMBER: S125DIP-S1270D590U840-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	275°	280°	285°	290°	295°	300°	305°	310°	315°	320°	325°
112.5°	275.5	275.8	276.1	276.4	276.6	276.8	276.9	277.1	277.2	276.8	276.3
115°	318.7	319.3	319.9	320.6	321.0	321.1	321.2	321.3	321.5	321.0	320.4
117.5°	362.3	362.3	362.3	362.3	362.5	363.0	363.6	364.0	364.5	363.9	363.1
120°	389.9	389.8	389.7	389.5	389.7	390.1	390.4	390.8	391.2	390.9	390.7
122.5°	415.0	415.5	416.0	416.5	416.8	417.0	417.2	417.3	417.5	417.3	417.0
125°	453.2	454.0	454.9	455.9	456.4	456.4	456.4	456.4	456.4	455.9	455.3
127.5°	489.0	489.7	490.3	490.9	491.2	491.1	491.1	491.0	490.9	490.6	490.3
130°	511.1	511.8	512.4	513.0	513.4	513.5	513.7	513.8	513.9	513.5	513.2
132.5°	533.3	534.1	534.8	535.5	535.8	535.5	535.2	534.9	534.7	534.6	534.5
135°	564.8	565.6	566.3	567.1	567.4	567.1	566.8	566.6	566.3	566.1	565.8
137.5°	593.7	594.3	595.0	595.6	595.9	595.6	595.4	595.2	594.9	595.0	595.0
140°	612.2	612.4	612.7	612.9	613.0	612.9	612.7	612.6	612.5	612.7	613.0
142.5°	629.1	629.2	629.4	629.5	629.8	630.0	630.1	630.3	630.5	630.5	630.6
145°	654.2	654.5	654.7	655.0	655.1	655.1	655.1	655.1	655.1	655.2	655.4
147.5°	675.8	675.7	675.7	675.6	675.7	675.8	676.0	676.1	676.3	676.5	676.6
150°	689.4	689.1	688.9	688.6	688.6	688.9	689.1	689.4	689.6	689.9	690.1
152.5°	702.5	702.0	701.4	700.7	700.6	700.8	701.1	701.4	701.7	702.0	702.2
155°	719.4	718.7	717.9	717.1	716.9	717.1	717.4	717.6	717.9	718.3	718.7
157.5°	733.0	732.6	732.1	731.6	731.4	731.4	731.4	731.4	731.5	732.0	732.4
160°	741.9	741.1	740.3	739.6	739.3	739.4	739.5	739.6	739.8	740.3	740.8
162.5°	749.3	748.5	747.7	747.0	746.7	746.8	746.9	747.0	747.2	747.9	748.6
165°	759.2	758.4	757.7	756.9	756.6	756.7	756.8	757.0	757.1	757.8	758.6
167.5°	766.6	765.8	765.0	764.2	763.9	764.0	764.1	764.2	764.4	765.3	766.2
170°	770.6	769.7	768.8	767.9	767.5	767.6	767.8	767.9	768.0	769.0	770.1
172.5°	773.4	772.4	771.5	770.6	770.3	770.5	770.8	771.0	771.2	772.1	773.1
175°	776.5	775.7	775.0	774.2	773.9	774.0	774.2	774.3	774.4	775.4	776.4
177.5°	778.0	777.4	776.8	776.2	775.9	776.0	776.1	776.2	776.3	777.1	777.8
180°	777.3	777.3	777.3	777.3	777.3	777.3	777.3	777.3	777.3	777.3	777.3



TEST NUMBER: P333304-840

CATALOG NUMBER: S125DIP-S1270D590U840-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	330°	335°	340°	345°	350°	355°	360°
0°	1854.7	1854.7	1854.7	1854.7	1854.7	1854.7	1854.7
2.5°	1939.6	1944.7	1955.4	1951.7	1956.7	1959.2	1961.8
5°	2096.4	2121.5	2132.5	2131.0	2147.5	2143.5	2139.6
7.5°	2273.3	2299.8	2314.6	2333.0	2343.7	2344.5	2353.8
10°	2373.5	2408.1	2422.3	2442.0	2454.6	2461.6	2460.8
12.5°	2450.2	2477.4	2509.1	2518.8	2535.8	2544.8	2541.4
15°	2542.7	2586.0	2619.1	2635.5	2656.9	2663.1	2671.8
17.5°	2625.2	2683.3	2721.9	2773.2	2792.6	2804.4	2797.4
20°	2687.6	2763.9	2802.5	2863.9	2897.7	2915.9	2909.5
22.5°	2761.3	2843.9	2915.2	2968.4	3019.9	3044.3	3049.4
25°	2887.5	3000.8	3105.5	3175.6	3239.3	3254.3	3287.4
27.5°	3028.6	3162.2	3274.2	3347.9	3392.2	3408.9	3419.3
30°	3117.4	3250.4	3334.7	3381.8	3396.1	3394.5	3392.8
32.5°	3160.8	3244.1	3260.3	3247.1	3214.7	3187.2	3158.7
35°	3099.3	3037.1	2944.2	2824.5	2736.3	2647.4	2638.8
37.5°	2787.3	2588.5	2433.9	2261.2	2161.5	2100.0	2057.5
40°	2493.9	2268.0	2080.6	1935.0	1833.4	1793.3	1753.9
42.5°	2175.2	1959.3	1793.4	1671.7	1595.4	1550.8	1519.6
45°	1767.3	1576.8	1446.9	1358.8	1298.1	1263.4	1243.7
47.5°	1448.1	1307.3	1196.9	1133.3	1091.4	1064.5	1064.6
50°	1276.9	1142.3	1069.0	1018.7	982.4	961.2	965.1
52.5°	1125.1	1024.5	962.0	919.8	893.0	879.9	879.5
55°	940.7	868.3	827.4	796.7	778.5	763.6	766.8
57.5°	804.7	743.6	716.2	690.7	678.1	672.2	663.5
60°	720.3	673.1	649.4	628.9	616.4	611.7	603.0
62.5°	645.4	608.2	585.2	568.6	557.1	555.6	548.9
65°	542.4	514.0	493.6	485.7	473.9	470.8	470.8
67.5°	447.2	426.9	410.9	403.6	398.5	399.3	395.5
70°	387.3	370.8	360.5	352.6	348.7	349.5	346.4
72.5°	338.8	320.4	311.4	306.7	301.5	303.6	302.3
75°	256.6	247.2	242.5	237.7	234.6	233.0	231.5
77.5°	188.4	180.2	176.5	173.8	174.3	170.5	173.5
80°	145.6	138.6	136.2	132.3	131.5	131.5	130.7
82.5°	106.5	102.6	100.9	97.7	96.2	97.5	95.4
85°	55.1	51.9	51.2	51.2	49.6	48.1	51.9
87.5°	22.4	20.0	20.1	19.5	19.6	19.1	17.9
90°	11.1	11.8	12.3	12.7	13.0	13.4	13.8
92.5°	11.1	11.8	12.2	12.3	12.5	12.7	12.9
95°	11.1	11.8	12.1	12.1	12.1	12.1	12.1
97.5°	17.5	13.9	12.1	12.1	12.1	12.1	12.1
100°	43.0	23.9	14.1	13.6	13.1	12.6	12.1
102.5°	117.0	113.5	107.3	98.6	89.9	81.2	72.5
105°	171.7	171.7	171.7	171.5	171.4	171.3	171.1
107.5°	217.4	217.4	217.2	216.9	216.5	216.1	215.7
110°	246.6	246.2	246.1	246.2	246.3	246.5	246.6



TEST NUMBER: P333304-840

CATALOG NUMBER: S125DIP-S1270D590U840-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	330°	335°	340°	345°	350°	355°	360°
112.5°	275.8	275.3	275.0	274.8	274.6	274.5	274.3
115°	319.9	319.4	318.8	318.0	317.3	316.5	315.8
117.5°	362.4	361.8	361.3	361.0	360.6	360.3	360.0
120°	390.4	390.2	389.7	389.1	388.5	387.8	387.2
122.5°	416.8	416.5	416.0	415.3	414.4	413.7	413.0
125°	454.7	454.2	453.8	453.4	453.0	452.7	452.3
127.5°	490.1	489.8	489.2	488.2	487.3	486.4	485.3
130°	512.8	512.4	511.9	511.3	510.6	510.0	509.4
132.5°	534.4	534.4	534.0	533.4	532.7	532.1	531.5
135°	565.6	565.3	564.8	564.1	563.3	562.5	561.8
137.5°	595.1	595.1	594.8	594.2	593.5	592.9	592.2
140°	613.2	613.5	613.2	612.5	611.7	611.0	610.2
142.5°	630.6	630.7	630.3	629.5	628.7	627.9	627.2
145°	655.5	655.6	655.3	654.5	653.8	653.0	652.2
147.5°	676.8	676.9	676.5	675.6	674.7	673.8	672.9
150°	690.4	690.6	690.3	689.3	688.2	687.2	686.2
152.5°	702.5	702.7	702.4	701.5	700.5	699.5	698.6
155°	719.0	719.4	719.1	718.1	717.1	716.1	715.0
157.5°	732.8	733.2	732.9	731.8	730.7	729.7	728.7
160°	741.3	741.8	741.5	740.5	739.5	738.5	737.5
162.5°	749.3	750.0	749.8	748.7	747.6	746.5	745.3
165°	759.4	760.1	760.0	759.0	758.0	757.0	755.9
167.5°	767.1	768.0	767.9	766.8	765.6	764.5	763.3
170°	771.1	772.1	772.0	770.9	769.7	768.6	767.5
172.5°	774.1	775.0	774.9	773.7	772.5	771.3	770.2
175°	777.4	778.5	778.4	777.3	776.1	775.0	773.8
177.5°	778.5	779.2	779.1	778.3	777.5	776.7	775.9
180°	777.3	777.3	777.3	777.3	777.3	777.3	777.3

(END OF REPORT)