

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P333315-840

Luminaire Tested: **S125DIP-S1270D810U840-4F0-1E-UDD-A4**

Issue Date: 3/3/2020

Test Information

Test Method: LM-79-08
Report Number: P333315-840
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-19,
Test Lab: INNOVATION CENTER
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: NEO-RAY
Catalog Number: S125DIP-S1270D810U840-4F0-1E-UDD-A4
Description: DEFINE 5 DIRECT-INDIRECT PENDANT LED LUMINAIRE
DOWNLIGHT 1270 LUMENS PER FOOT, ASYMMETRIC DIFFUSER
UPLIGHT 810 LUMENS PER FOOT, BATWING OPTIC
Light Source: -
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 8172.8 lumens
Efficiency: N/A
Efficacy: 134.6 lumens/watt
Spacing Criteria (0/90/45): 1.43 / 1.23 / 1.52
Luminous Opening: Rectangular (W 4' x L: 0.42' x H: 0')
CIE Type: Semi-Direct


Input Watts (W): 60.7
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P333315-840

CATALOG NUMBER: S125DIP-S1270D810U840-4F0-1E-UDD-A4

Luminous Intensity Polar Plot





TEST NUMBER: P333315-840

CATALOG NUMBER: S125DIP-S1270D810U840-4F0-1E-UDD-A4

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	110	110	110	110	104	104	104	104	91	91	91	80	80	80	69	69	69	64
1	101	97	93	90	95	91	88	85	80	78	76	71	69	67	62	60	59	55
2	92	85	79	74	87	80	75	70	71	67	63	62	59	56	54	52	50	46
3	84	75	68	62	79	71	64	59	63	58	53	55	51	48	48	45	43	39
4	77	67	59	52	72	63	56	50	56	50	46	49	45	41	43	40	37	34
5	71	59	51	45	67	56	49	43	50	44	40	44	40	36	39	35	32	30
6	66	53	45	39	61	51	43	38	45	39	35	40	35	32	36	32	29	26
7	61	48	40	35	57	46	38	33	41	35	31	37	32	28	33	29	25	23
8	56	44	36	31	53	42	35	30	38	32	27	34	29	25	30	26	23	21
9	53	40	33	27	49	38	31	26	34	29	24	31	26	23	28	24	21	19
10	49	37	30	25	46	35	28	24	32	26	22	29	24	20	26	22	19	17

AVERAGE LUMINANCE (cd/sqm):

	0°	90°	180°	270°
0°	11978	11978	11978	11978
5°	13871	12019	10524	12019
10°	16138	11956	9220	11956
15°	17864	11869	8505	11869
20°	19996	11730	7932	11730
25°	23426	11573	7652	11573
30°	25302	11419	7409	11419
35°	20805	11129	7250	11129
40°	14787	10725	7075	10725
45°	11359	10181	6974	10181
50°	9697	9507	6961	9507
55°	8634	8847	7020	8847
60°	7789	8123	7198	8123
65°	7195	7398	7386	7398
70°	6541	6643	7493	6643
75°	5777	5854	7426	5854
80°	4861	4775	6791	4775
85°	3846	3446	5483	3446



TEST NUMBER: P333315-840

CATALOG NUMBER: S125DIP-S1270D810U840-4F0-1E-UDD-A4

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	178.6	2.2
10°-20°	531.6	6.5
20°-30°	863.2	10.6
30°-40°	1053.0	12.9
40°-50°	957.9	11.7
50°-60°	763.0	9.3
60°-70°	531.4	6.5
70°-80°	283.4	3.5
80°-90°	73.7	0.9
90°-100°	283.9	3.5
100°-110°	610.3	7.5
110°-120°	572.7	7.0
120°-130°	464.2	5.7
130°-140°	372.5	4.6
140°-150°	281.1	3.4
150°-160°	197.9	2.4
160°-170°	116.6	1.4
170°-180°	37.9	0.5
0°-30°	1573.4	19.3
0°-40°	2626.3	32.1
0°-60°	4347.2	53.2
0°-90°	5235.7	64.1
90°-120°	1466.9	17.9
90°-150°	2584.6	31.6
90°-180°	2937.0	35.9
0°-180°	8172.8	100.0

CANDELA DISTRIBUTION:

	0°	90°	180°	270°	360°	Flux
0°	1855	1855	1855	1855	1855	
5°	2140	1854	1623	1854	2140	216
15°	2672	1775	1272	1775	2672	765
25°	3287	1624	1074	1624	3287	1502
35°	2639	1412	920	1412	2639	1615
45°	1244	1115	764	1115	1244	995
55°	767	786	624	786	767	691
65°	471	484	483	484	471	467
75°	232	235	298	235	232	249
85°	52	46	74	46	52	60
90°	18	1	18	1	18	14
95°	186	26	186	26	186	263
105°	1046	89	1046	89	1046	1040
115°	1166	160	1166	160	1166	1139
125°	918	221	918	221	918	831
135°	763	259	763	259	763	591
145°	602	302	602	302	602	382
155°	504	344	504	344	504	235
165°	442	376	442	376	442	126
175°	397	391	397	391	397	39
180°	392	392	392	392	392	



TEST NUMBER: P333315-840

CATALOG NUMBER: S125DIP-S1270D810U840-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	1854.7	1854.7	1854.7	1854.7	1854.7	1854.7	1854.7	1854.7	1854.7	1854.7	1854.7
2.5°	1961.8	1959.2	1956.7	1951.7	1955.4	1944.7	1939.6	1930.9	1920.2	1916.4	1912.0
5°	2139.6	2143.5	2147.5	2131.0	2132.5	2121.5	2096.4	2075.9	2059.3	2038.1	2023.2
7.5°	2353.8	2344.5	2343.7	2333.0	2314.6	2299.8	2273.3	2239.6	2207.1	2169.9	2139.2
10°	2460.8	2461.6	2454.6	2442.0	2422.3	2408.1	2373.5	2340.4	2300.3	2253.0	2219.2
12.5°	2541.4	2544.8	2535.8	2518.8	2509.1	2477.4	2450.2	2411.0	2363.2	2325.4	2273.9
15°	2671.8	2663.1	2656.9	2635.5	2619.1	2586.0	2542.7	2501.7	2449.8	2401.8	2353.8
17.5°	2797.4	2804.4	2792.6	2773.2	2721.9	2683.3	2625.2	2569.1	2504.5	2440.0	2382.8
20°	2909.5	2915.9	2897.7	2863.9	2802.5	2763.9	2687.6	2615.1	2540.3	2457.7	2394.7
22.5°	3049.4	3044.3	3019.9	2968.4	2915.2	2843.9	2761.3	2673.0	2579.4	2486.0	2402.3
25°	3287.4	3254.3	3239.3	3175.6	3105.5	3000.8	2887.5	2758.3	2641.9	2518.3	2411.3
27.5°	3419.3	3408.9	3392.2	3347.9	3274.2	3162.2	3028.6	2871.2	2706.9	2550.9	2410.7
30°	3392.8	3394.5	3396.1	3381.8	3334.7	3250.4	3117.4	2948.1	2752.9	2577.4	2415.2
32.5°	3158.7	3187.2	3214.7	3247.1	3260.3	3244.1	3160.8	3008.0	2807.0	2607.6	2412.7
35°	2638.8	2647.4	2736.3	2824.5	2944.2	3037.1	3099.3	3031.5	2862.3	2633.2	2409.6
37.5°	2057.5	2100.0	2161.5	2261.2	2433.9	2588.5	2787.3	2878.8	2824.2	2641.6	2404.2
40°	1753.9	1793.3	1833.4	1935.0	2080.6	2268.0	2493.9	2686.7	2731.6	2615.1	2385.3
42.5°	1519.6	1550.8	1595.4	1671.7	1793.4	1959.3	2175.2	2427.3	2582.3	2538.3	2345.6
45°	1243.7	1263.4	1298.1	1358.8	1446.9	1576.8	1767.3	2042.9	2282.9	2362.4	2251.4
47.5°	1064.6	1064.5	1091.4	1133.3	1196.9	1307.3	1448.1	1664.1	1920.5	2110.2	2101.4
50°	965.1	961.2	982.4	1018.7	1069.0	1142.3	1276.9	1449.3	1695.7	1910.6	1970.3
52.5°	879.5	879.9	893.0	919.8	962.0	1024.5	1125.1	1280.5	1491.0	1711.5	1824.3
55°	766.8	763.6	778.5	796.7	827.4	868.3	940.7	1059.6	1230.4	1447.6	1594.1
57.5°	663.5	672.2	678.1	690.7	716.2	743.6	804.7	891.9	1027.4	1213.9	1368.7
60°	603.0	611.7	616.4	628.9	649.4	673.1	720.3	791.1	905.3	1065.9	1219.4
62.5°	548.9	555.6	557.1	568.6	585.2	608.2	645.4	704.9	795.1	935.5	1085.9
65°	470.8	470.8	473.9	485.7	493.6	514.0	542.4	585.7	658.1	767.5	895.9
67.5°	395.5	399.3	398.5	403.6	410.9	426.9	447.2	482.9	536.5	616.4	719.0
70°	346.4	349.5	348.7	352.6	360.5	370.8	387.3	421.1	459.7	528.3	616.4
72.5°	302.3	303.6	301.5	306.7	311.4	320.4	338.8	356.9	392.9	450.8	523.2
75°	231.5	233.0	234.6	237.7	242.5	247.2	256.6	274.8	298.3	341.6	388.1
77.5°	173.5	170.5	174.3	173.8	176.5	180.2	188.4	198.0	217.4	244.8	280.7
80°	130.7	131.5	131.5	132.3	136.2	138.6	145.6	152.7	167.6	188.1	213.4
82.5°	95.4	97.5	96.2	97.7	100.9	102.6	106.5	112.4	121.1	137.1	155.4
85°	51.9	48.1	49.6	51.2	51.2	51.9	55.1	57.5	62.2	68.5	75.5
87.5°	18.8	20.0	20.5	20.5	21.1	20.8	23.1	23.0	24.7	26.5	28.7
90°	18.2	18.2	17.4	17.4	17.4	15.8	15.0	14.2	13.4	12.6	11.0
92.5°	50.4	51.6	52.7	54.6	64.7	76.4	101.6	140.0	206.1	254.6	258.6
95°	185.5	198.2	204.5	228.2	284.3	350.6	447.7	567.7	684.6	699.6	570.9
97.5°	448.5	458.6	481.5	525.7	574.5	666.7	761.3	845.6	866.2	747.1	509.8
100°	615.9	628.5	657.7	714.6	769.1	851.2	932.5	971.2	910.4	713.1	454.8
102.5°	802.8	812.3	844.0	884.5	942.8	998.4	1037.4	1013.5	883.9	653.0	413.1
105°	1046.2	1055.7	1071.5	1097.5	1122.9	1131.6	1096.8	988.6	799.1	572.5	372.7
107.5°	1175.4	1181.7	1186.9	1187.1	1174.3	1133.1	1043.9	899.5	712.6	517.1	355.7
110°	1218.4	1218.4	1212.8	1197.8	1162.3	1095.2	983.8	833.8	663.3	491.1	350.6



TEST NUMBER: P333315-840

CATALOG NUMBER: S125DIP-S1270D810U840-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	1213.4	1207.6	1193.9	1168.1	1116.2	1037.0	924.4	782.0	626.6	475.9	350.6
115°	1165.5	1155.2	1133.1	1095.2	1033.6	947.6	839.4	717.0	586.6	459.6	352.9
117.5°	1081.6	1075.3	1053.3	1014.2	952.6	873.6	780.4	675.0	562.8	451.5	358.2
120°	1027.2	1021.0	999.7	961.7	903.3	833.8	747.0	652.2	549.6	447.7	363.2
122.5°	979.3	973.6	952.3	917.6	865.5	800.3	723.0	635.2	538.2	444.5	367.6
125°	918.3	910.4	893.0	860.7	816.5	759.6	690.9	610.4	522.7	440.6	375.1
127.5°	866.2	862.7	846.3	817.7	777.6	724.4	660.2	585.1	508.5	438.7	383.4
130°	837.8	833.0	817.3	791.2	751.7	700.3	638.8	569.3	499.1	437.5	388.5
132.5°	809.3	804.0	789.4	763.4	723.9	674.5	618.5	553.5	491.5	437.5	394.2
135°	762.8	758.0	743.8	717.7	683.0	638.0	587.4	533.0	482.4	437.5	401.9
137.5°	713.1	707.8	694.7	671.1	639.9	601.7	559.7	515.6	474.4	438.4	409.0
140°	678.2	674.3	662.5	642.0	612.7	579.6	543.2	506.1	470.6	439.0	412.1
142.5°	646.0	642.8	631.6	614.2	589.4	560.6	529.4	498.0	467.5	439.7	414.0
145°	601.7	598.5	589.9	576.4	557.4	536.1	511.7	487.2	462.7	439.0	416.2
147.5°	564.1	562.7	557.6	546.8	531.9	515.7	497.0	477.1	457.8	437.0	416.9
150°	543.2	542.5	539.3	529.9	518.0	503.7	488.8	471.4	454.0	435.0	416.9
152.5°	526.8	526.0	522.9	515.3	505.3	494.3	480.6	465.0	449.6	432.5	416.3
155°	504.5	503.7	501.4	495.8	488.0	479.3	468.3	455.7	442.2	428.0	414.5
157.5°	484.6	484.8	482.6	478.1	471.9	465.0	456.6	446.2	435.3	423.2	412.5
160°	471.4	472.2	470.6	466.7	461.1	455.7	447.7	439.8	429.6	420.1	410.6
162.5°	459.4	459.6	459.2	456.0	451.6	446.8	440.1	432.8	424.4	416.3	408.7
165°	442.2	442.2	442.2	440.6	437.5	433.5	428.8	423.2	416.9	410.6	405.9
167.5°	426.4	426.6	427.2	425.8	424.1	421.3	417.7	414.0	409.5	405.1	401.4
170°	416.9	417.7	417.7	416.9	415.4	413.7	411.4	409.0	405.1	401.9	399.5
172.5°	408.1	408.9	410.1	408.7	408.4	407.5	405.7	403.3	400.6	398.1	397.0
175°	397.2	398.0	399.5	398.8	398.8	398.8	397.2	397.2	394.8	394.0	394.0
177.5°	391.6	391.6	393.5	392.9	393.5	393.5	393.5	392.9	392.2	391.6	391.6
180°	391.6	391.6	391.6	391.6	391.6	391.6	391.6	391.6	391.6	391.6	391.6



TEST NUMBER: P333315-840

CATALOG NUMBER: S125DIP-S1270D810U840-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°	95°	100°	105°
0°	1854.7	1854.7	1854.7	1854.7	1854.7	1854.7	1854.7	1854.7	1854.7	1854.7	1854.7
2.5°	1908.2	1903.8	1898.7	1890.0	1879.3	1873.6	1864.7	1859.1	1847.8	1838.3	1828.3
5°	2005.0	1984.6	1965.7	1941.3	1914.5	1897.1	1876.7	1853.9	1830.3	1805.8	1779.1
7.5°	2105.4	2069.1	2029.7	1987.4	1946.0	1907.8	1871.5	1835.7	1802.4	1762.1	1728.0
10°	2172.7	2127.1	2078.2	2020.7	1964.9	1916.1	1866.4	1823.2	1779.1	1731.8	1690.1
12.5°	2240.1	2179.3	2110.3	2047.2	1980.0	1921.1	1862.7	1807.5	1752.0	1699.7	1651.1
15°	2287.6	2234.1	2170.3	2080.6	2005.0	1924.0	1846.8	1775.1	1708.3	1650.0	1588.6
17.5°	2319.0	2250.0	2181.5	2095.4	1996.4	1905.7	1818.3	1736.3	1660.8	1587.0	1527.8
20°	2324.6	2253.8	2182.1	2097.9	1996.4	1892.5	1805.0	1706.7	1625.6	1549.2	1476.8
22.5°	2322.8	2242.4	2164.5	2077.8	1978.7	1883.0	1777.4	1677.1	1589.0	1514.0	1438.4
25°	2304.9	2219.2	2121.5	2034.2	1936.5	1835.0	1728.0	1624.1	1534.3	1448.4	1373.7
27.5°	2290.2	2178.9	2068.3	1966.4	1872.2	1779.1	1676.6	1570.1	1470.7	1383.7	1313.2
30°	2271.9	2149.9	2025.5	1919.2	1822.4	1731.8	1635.1	1531.2	1427.2	1342.2	1266.7
32.5°	2255.5	2113.3	1982.1	1866.3	1763.8	1675.8	1586.5	1487.6	1385.6	1299.4	1223.8
35°	2223.9	2059.3	1908.9	1778.3	1668.9	1578.3	1503.6	1411.5	1317.8	1234.4	1162.0
37.5°	2183.7	1988.5	1827.1	1690.1	1570.1	1474.8	1405.1	1334.4	1244.6	1164.2	1098.6
40°	2152.2	1938.1	1767.3	1627.2	1502.8	1403.6	1339.1	1272.1	1197.4	1122.6	1053.3
42.5°	2112.5	1892.8	1706.9	1556.0	1432.9	1336.3	1268.5	1211.6	1145.7	1076.0	1011.7
45°	2039.6	1810.6	1609.0	1446.9	1322.5	1227.3	1157.2	1114.7	1065.1	999.0	944.6
47.5°	1932.5	1711.8	1503.4	1336.1	1207.7	1119.4	1053.8	1013.0	978.1	928.9	879.6
50°	1837.3	1638.2	1427.2	1261.1	1132.8	1043.8	983.2	946.2	916.4	878.5	836.8
52.5°	1730.9	1545.6	1352.3	1188.1	1061.0	973.3	913.9	881.4	856.5	829.4	788.3
55°	1561.9	1404.4	1224.9	1069.0	951.7	866.0	814.0	785.7	765.2	744.7	719.5
57.5°	1375.5	1252.4	1093.5	951.0	842.9	764.9	716.4	688.8	672.9	662.4	647.5
60°	1244.6	1139.1	1002.1	872.2	766.8	697.5	650.3	628.9	615.6	606.9	595.9
62.5°	1123.1	1036.4	909.6	791.0	698.7	633.2	591.1	570.4	557.6	553.4	544.3
65°	943.8	877.0	772.2	673.9	595.1	539.3	503.8	484.1	476.3	471.5	472.3
67.5°	767.4	726.6	642.5	558.6	495.7	448.9	420.5	405.5	401.5	395.2	395.1
70°	659.6	628.9	558.2	484.9	429.0	392.8	367.6	351.8	347.9	344.8	344.1
72.5°	564.6	537.7	476.3	417.6	367.3	335.5	314.8	305.3	298.8	296.9	296.8
75°	424.3	409.4	360.5	314.1	279.4	257.4	243.3	234.6	229.8	229.0	229.8
77.5°	301.6	288.6	257.6	224.7	202.8	186.1	174.1	171.2	165.8	165.9	165.1
80°	226.7	218.0	198.3	172.4	154.3	140.2	133.8	128.4	126.7	124.4	126.7
82.5°	164.4	155.1	141.7	125.1	110.2	101.7	95.4	93.7	92.7	91.6	92.1
85°	81.1	81.9	74.0	61.4	55.1	50.4	46.5	46.5	45.6	44.8	45.6
87.5°	29.8	28.2	25.5	23.3	19.8	17.7	16.7	17.2	15.5	15.1	16.1
90°	10.3	8.7	7.9	6.4	4.7	3.1	1.6	0.8	1.6	3.1	4.7
92.5°	180.2	107.9	64.7	41.7	28.1	18.3	11.7	9.6	11.7	18.3	28.1
95°	352.9	179.3	94.7	59.2	41.8	33.1	26.9	26.1	26.9	33.1	41.8
97.5°	281.8	154.4	98.6	72.9	57.4	48.7	44.2	43.2	44.2	48.7	57.4
100°	255.8	153.2	107.3	83.7	68.7	60.0	56.9	55.2	56.9	60.0	68.7
102.5°	245.1	158.9	118.2	95.0	81.3	72.0	69.5	68.6	69.5	72.0	81.3
105°	240.9	170.6	135.8	113.7	101.1	93.2	89.3	89.3	89.3	93.2	101.1
107.5°	248.1	187.9	154.3	134.4	121.3	114.8	111.0	109.5	111.0	114.8	121.3
110°	255.1	200.6	168.1	147.6	135.8	128.7	125.5	124.0	125.5	128.7	135.8



TEST NUMBER: P333315-840

CATALOG NUMBER: S125DIP-S1270D810U840-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°	95°	100°	105°
112.5°	263.9	212.6	181.5	161.6	149.7	142.6	140.1	138.5	140.1	142.6	149.7
115°	277.1	231.4	202.2	182.4	170.6	163.5	161.1	159.5	161.1	163.5	170.6
117.5°	292.4	250.6	223.0	203.9	190.5	183.4	180.9	178.4	180.9	183.4	190.5
120°	302.5	264.5	236.9	217.1	203.7	196.6	193.5	191.1	193.5	196.6	203.7
122.5°	313.8	277.8	250.1	230.5	215.7	208.6	206.1	204.4	206.1	208.6	215.7
125°	329.2	295.3	269.2	248.7	233.7	226.6	222.7	221.1	222.7	226.6	233.7
127.5°	343.5	312.3	287.1	266.6	250.6	241.7	236.6	234.2	236.6	241.7	250.6
130°	352.9	323.0	298.5	277.9	261.4	251.1	244.8	242.4	244.8	251.1	261.4
132.5°	361.1	333.1	308.6	288.0	270.8	259.3	251.8	248.7	251.8	259.3	270.8
135°	372.7	346.7	322.1	300.8	284.3	271.7	262.2	259.0	262.2	271.7	284.3
137.5°	381.2	356.3	334.0	312.0	295.8	283.2	274.3	272.0	274.3	283.2	295.8
140°	386.9	363.2	340.3	319.0	304.0	291.3	281.9	279.5	281.9	291.3	304.0
142.5°	390.1	367.6	346.0	326.0	311.5	298.9	290.1	288.3	290.1	298.9	311.5
145°	394.8	375.1	354.6	336.4	322.1	311.1	303.2	301.6	303.2	311.1	322.1
147.5°	397.7	379.8	361.8	345.9	333.6	323.3	316.5	315.5	316.5	323.3	333.6
150°	399.5	382.9	365.6	352.1	341.1	330.8	325.3	323.8	325.3	330.8	341.1
152.5°	400.8	386.1	370.0	357.9	347.4	338.4	333.6	332.5	333.6	338.4	347.4
155°	401.9	389.3	375.9	364.8	356.9	349.0	344.3	344.3	344.3	349.0	356.9
157.5°	402.7	391.9	380.4	372.0	365.1	358.3	354.6	354.7	354.6	358.3	365.1
160°	402.7	393.2	382.9	375.9	369.5	364.1	360.8	361.6	360.8	364.1	369.5
162.5°	402.0	394.5	385.5	379.6	374.6	369.7	366.6	367.3	366.6	369.7	374.6
165°	401.1	394.8	388.5	383.7	380.6	376.7	374.3	375.9	374.3	376.7	380.6
167.5°	399.2	394.8	389.6	386.6	384.4	382.1	380.7	381.5	380.7	382.1	384.4
170°	398.0	394.8	390.8	388.5	386.9	385.4	384.6	385.4	384.6	385.4	386.9
172.5°	396.7	394.2	390.8	389.7	388.8	387.2	386.5	387.9	386.5	387.2	388.8
175°	394.8	393.2	390.8	390.8	390.8	390.1	389.3	390.8	389.3	390.1	390.8
177.5°	392.9	392.2	391.0	391.0	391.6	391.0	391.0	392.2	391.0	391.0	391.6
180°	391.6	391.6	391.6	391.6	391.6	391.6	391.6	391.6	391.6	391.6	391.6



TEST NUMBER: P333315-840

CATALOG NUMBER: S125DIP-S1270D810U840-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	110°	115°	120°	125°	130°	135°	140°	145°	150°	155°	160°
0°	1854.7	1854.7	1854.7	1854.7	1854.7	1854.7	1854.7	1854.7	1854.7	1854.7	1854.7
2.5°	1822.5	1815.6	1810.0	1797.4	1790.4	1781.0	1773.4	1781.6	1772.8	1776.6	1770.9
5°	1765.7	1743.6	1728.0	1705.1	1685.5	1667.3	1654.0	1651.5	1645.3	1642.1	1632.6
7.5°	1697.4	1669.8	1642.7	1612.9	1587.6	1562.0	1545.6	1532.1	1523.1	1511.3	1503.3
10°	1657.1	1620.1	1588.6	1552.4	1520.9	1493.4	1471.3	1460.3	1450.1	1435.1	1429.6
12.5°	1607.3	1569.0	1530.7	1492.0	1461.7	1431.0	1412.1	1395.4	1388.4	1371.5	1369.8
15°	1547.6	1490.2	1452.4	1413.0	1371.3	1346.2	1330.4	1312.3	1304.4	1292.6	1283.9
17.5°	1476.5	1425.1	1378.0	1337.2	1301.4	1280.2	1260.6	1248.2	1234.7	1227.0	1212.7
20°	1424.8	1376.0	1328.8	1285.6	1258.0	1233.6	1217.8	1206.0	1191.8	1187.9	1173.8
22.5°	1381.4	1327.6	1282.2	1245.9	1215.8	1188.2	1171.2	1163.2	1153.5	1141.3	1138.4
25°	1310.7	1254.9	1216.3	1180.0	1153.3	1128.1	1116.3	1106.0	1096.6	1087.9	1084.8
27.5°	1249.6	1199.7	1153.9	1121.2	1097.8	1074.9	1064.5	1052.1	1045.1	1038.1	1029.7
30°	1206.8	1155.6	1115.5	1084.0	1058.8	1038.3	1027.3	1018.7	1012.4	1006.0	1001.4
32.5°	1162.8	1115.3	1076.4	1045.6	1020.4	1004.9	995.2	989.1	982.1	974.5	968.6
35°	1104.5	1052.5	1014.7	988.0	968.3	956.4	945.4	939.9	932.1	932.1	925.7
37.5°	1038.8	993.9	960.6	936.1	918.5	908.0	896.1	892.2	887.2	883.8	881.7
40°	999.8	958.1	926.6	902.1	883.2	874.5	865.2	858.9	855.7	851.7	850.2
42.5°	959.5	919.6	889.4	866.9	850.5	843.1	834.2	829.9	823.5	818.4	817.5
45°	898.2	859.6	832.1	814.0	799.8	791.1	785.7	776.2	773.1	766.8	766.0
47.5°	840.1	803.1	776.1	761.2	748.8	741.7	733.1	723.6	720.0	716.8	716.5
50°	796.7	762.9	737.6	723.5	711.7	701.5	692.8	686.4	684.1	684.1	685.7
52.5°	752.6	723.8	702.4	685.0	673.9	663.0	655.0	651.2	647.5	651.4	654.2
55°	688.0	658.9	643.2	626.6	615.6	603.0	599.1	597.5	595.1	601.5	604.6
57.5°	619.7	599.3	580.8	564.4	554.5	547.2	541.9	541.0	545.4	548.4	558.6
60°	576.2	552.6	536.1	523.5	511.7	507.0	505.4	503.8	507.0	515.6	529.0
62.5°	528.4	509.2	491.4	481.9	473.2	465.4	465.0	466.1	472.3	482.2	495.6
65°	458.2	441.6	429.8	418.8	411.7	407.0	408.6	411.7	418.8	432.2	447.2
67.5°	386.9	375.5	365.0	356.0	349.2	349.2	350.8	355.5	363.9	379.3	392.9
70°	340.8	328.3	319.6	315.7	310.1	307.0	311.7	319.6	326.7	340.8	352.6
72.5°	294.9	284.2	277.4	274.8	272.4	269.8	271.5	279.9	289.5	303.7	317.4
75°	226.7	222.8	218.0	214.9	212.6	214.1	215.7	223.6	231.5	246.4	262.2
77.5°	165.5	161.4	158.5	157.7	156.5	157.2	161.7	167.5	175.2	186.1	198.0
80°	125.1	123.6	122.0	121.2	121.2	122.0	128.4	132.3	139.4	149.6	159.1
82.5°	91.2	90.2	89.9	89.8	90.4	90.5	94.3	99.5	105.3	113.0	121.2
85°	48.1	46.5	48.8	49.6	48.1	50.4	51.9	55.1	57.5	61.4	65.3
87.5°	17.0	18.6	18.1	19.1	19.2	20.8	20.3	23.0	24.4	25.9	25.5
90°	6.4	7.9	8.7	10.3	11.0	12.6	13.4	14.2	15.0	15.8	17.4
92.5°	41.7	64.7	107.9	180.2	258.6	254.6	206.1	140.0	101.6	76.4	64.7
95°	59.2	94.7	179.3	352.9	570.9	699.6	684.6	567.7	447.7	350.6	284.3
97.5°	72.9	98.6	154.4	281.8	509.8	747.1	866.2	845.6	761.3	666.7	574.5
100°	83.7	107.3	153.2	255.8	454.8	713.1	910.4	971.2	932.5	851.2	769.1
102.5°	95.0	118.2	158.9	245.1	413.1	653.0	883.9	1013.5	1037.4	998.4	942.8
105°	113.7	135.8	170.6	240.9	372.7	572.5	799.1	988.6	1096.8	1131.6	1122.9
107.5°	134.4	154.3	187.9	248.1	355.7	517.1	712.6	899.5	1043.9	1133.1	1174.3
110°	147.6	168.1	200.6	255.1	350.6	491.1	663.3	833.8	983.8	1095.2	1162.3



TEST NUMBER: P333315-840

CATALOG NUMBER: S125DIP-S1270D810U840-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	110°	115°	120°	125°	130°	135°	140°	145°	150°	155°	160°
112.5°	161.6	181.5	212.6	263.9	350.6	475.9	626.6	782.0	924.4	1037.0	1116.2
115°	182.4	202.2	231.4	277.1	352.9	459.6	586.6	717.0	839.4	947.6	1033.6
117.5°	203.9	223.0	250.6	292.4	358.2	451.5	562.8	675.0	780.4	873.6	952.6
120°	217.1	236.9	264.5	302.5	363.2	447.7	549.6	652.2	747.0	833.8	903.3
122.5°	230.5	250.1	277.8	313.8	367.6	444.5	538.2	635.2	723.0	800.3	865.5
125°	248.7	269.2	295.3	329.2	375.1	440.6	522.7	610.4	690.9	759.6	816.5
127.5°	266.6	287.1	312.3	343.5	383.4	438.7	508.5	585.1	660.2	724.4	777.6
130°	277.9	298.5	323.0	352.9	388.5	437.5	499.1	569.3	638.8	700.3	751.7
132.5°	288.0	308.6	333.1	361.1	394.2	437.5	491.5	553.5	618.5	674.5	723.9
135°	300.8	322.1	346.7	372.7	401.9	437.5	482.4	533.0	587.4	638.0	683.0
137.5°	312.0	334.0	356.3	381.2	409.0	438.4	474.4	515.6	559.7	601.7	639.9
140°	319.0	340.3	363.2	386.9	412.1	439.0	470.6	506.1	543.2	579.6	612.7
142.5°	326.0	346.0	367.6	390.1	414.0	439.7	467.5	498.0	529.4	560.6	589.4
145°	336.4	354.6	375.1	394.8	416.2	439.0	462.7	487.2	511.7	536.1	557.4
147.5°	345.9	361.8	379.8	397.7	416.9	437.0	457.8	477.1	497.0	515.7	531.9
150°	352.1	365.6	382.9	399.5	416.9	435.0	454.0	471.4	488.8	503.7	518.0
152.5°	357.9	370.0	386.1	400.8	416.3	432.5	449.6	465.0	480.6	494.3	505.3
155°	364.8	375.9	389.3	401.9	414.5	428.0	442.2	455.7	468.3	479.3	488.0
157.5°	372.0	380.4	391.9	402.7	412.5	423.2	435.3	446.2	456.6	465.0	471.9
160°	375.9	382.9	393.2	402.7	410.6	420.1	429.6	439.8	447.7	455.7	461.1
162.5°	379.6	385.5	394.5	402.0	408.7	416.3	424.4	432.8	440.1	446.8	451.6
165°	383.7	388.5	394.8	401.1	405.9	410.6	416.9	423.2	428.8	433.5	437.5
167.5°	386.6	389.6	394.8	399.2	401.4	405.1	409.5	414.0	417.7	421.3	424.1
170°	388.5	390.8	394.8	398.0	399.5	401.9	405.1	409.0	411.4	413.7	415.4
172.5°	389.7	390.8	394.2	396.7	397.0	398.1	400.6	403.3	405.7	407.5	408.4
175°	390.8	390.8	393.2	394.8	394.0	394.0	394.8	397.2	397.2	398.8	398.8
177.5°	391.0	391.0	392.2	392.9	391.6	391.6	392.2	392.9	393.5	393.5	393.5
180°	391.6	391.6	391.6	391.6	391.6	391.6	391.6	391.6	391.6	391.6	391.6



TEST NUMBER: P333315-840

CATALOG NUMBER: S125DIP-S1270D810U840-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	165°	170°	175°	180°	185°	190°	195°	200°	205°	210°	215°
0°	1854.7	1854.7	1854.7	1854.7	1854.7	1854.7	1854.7	1854.7	1854.7	1854.7	1854.7
2.5°	1767.2	1771.5	1767.8	1772.8	1767.8	1771.5	1767.2	1770.9	1776.6	1772.8	1781.6
5°	1628.7	1621.6	1626.4	1623.3	1626.4	1621.6	1628.7	1632.6	1642.1	1645.3	1651.5
7.5°	1500.9	1494.1	1486.4	1482.8	1486.4	1494.1	1500.9	1503.3	1511.3	1523.1	1532.1
10°	1420.9	1412.3	1411.5	1405.9	1411.5	1412.3	1420.9	1429.6	1435.1	1450.1	1460.3
12.5°	1362.3	1354.3	1345.3	1343.0	1345.3	1354.3	1362.3	1369.8	1371.5	1388.4	1395.4
15°	1279.2	1272.9	1267.4	1272.1	1267.4	1272.9	1279.2	1283.9	1292.6	1304.4	1312.3
17.5°	1210.1	1204.9	1204.0	1198.1	1204.0	1204.9	1210.1	1212.7	1227.0	1234.7	1248.2
20°	1166.7	1162.8	1164.3	1154.1	1164.3	1162.8	1166.7	1173.8	1187.9	1191.8	1206.0
22.5°	1132.1	1124.3	1123.4	1121.4	1123.4	1124.3	1132.1	1138.4	1141.3	1153.5	1163.2
25°	1077.7	1073.8	1069.9	1073.8	1069.9	1073.8	1077.7	1084.8	1087.9	1096.6	1106.0
27.5°	1030.3	1025.6	1024.5	1024.9	1024.5	1025.6	1030.3	1029.7	1038.1	1045.1	1052.1
30°	1001.4	993.5	994.2	993.5	994.2	993.5	1001.4	1001.4	1006.0	1012.4	1018.7
32.5°	969.9	964.5	963.4	962.0	963.4	964.5	969.9	968.6	974.5	982.1	989.1
35°	923.4	923.4	919.5	919.5	919.5	923.4	923.4	925.7	932.1	932.1	939.9
37.5°	879.8	879.0	876.7	877.0	876.7	879.0	879.8	881.7	883.8	887.2	892.2
40°	847.1	846.3	843.8	839.2	843.8	846.3	847.1	850.2	851.7	855.7	858.9
42.5°	815.6	812.8	811.7	810.2	811.7	812.8	815.6	817.5	818.4	823.5	829.9
45°	766.0	766.0	764.4	763.6	764.4	766.0	766.0	766.0	766.8	773.1	776.2
47.5°	717.8	719.2	722.2	721.8	722.2	719.2	717.8	716.5	716.8	720.0	723.6
50°	688.8	689.6	692.0	692.8	692.0	689.6	688.8	685.7	684.1	684.1	686.4
52.5°	656.7	661.3	664.3	663.8	664.3	661.3	656.7	654.2	651.4	647.5	651.2
55°	611.7	617.1	622.7	623.5	622.7	617.1	611.7	604.6	601.5	595.1	597.5
57.5°	567.1	574.8	580.7	582.5	580.7	574.8	567.1	558.6	548.4	545.4	541.0
60°	536.8	547.1	554.2	557.3	554.2	547.1	536.8	529.0	515.6	507.0	503.8
62.5°	507.9	519.4	526.4	527.1	526.4	519.4	507.9	495.6	482.2	472.3	466.1
65°	460.5	472.3	478.6	483.3	478.6	472.3	460.5	447.2	432.2	418.8	411.7
67.5°	409.5	421.3	428.3	432.0	428.3	421.3	409.5	392.9	379.3	363.9	355.5
70°	372.3	384.2	393.6	396.8	393.6	384.2	372.3	352.6	340.8	326.7	319.6
72.5°	335.8	346.4	354.0	357.7	354.0	346.4	335.8	317.4	303.7	289.5	279.9
75°	272.4	286.5	293.7	297.6	293.7	286.5	272.4	262.2	246.4	231.5	223.6
77.5°	210.1	223.0	227.2	229.2	227.2	223.0	210.1	198.0	186.1	175.2	167.5
80°	168.4	176.3	181.9	182.6	181.9	176.3	168.4	159.1	149.6	139.4	132.3
82.5°	129.5	136.0	137.7	139.8	137.7	136.0	129.5	121.2	113.0	105.3	99.5
85°	70.9	74.0	74.8	74.0	74.8	74.0	70.9	65.3	61.4	57.5	55.1
87.5°	26.8	26.2	26.3	27.6	26.3	26.2	26.8	25.5	25.9	24.4	23.0
90°	17.4	17.4	18.2	18.2	18.2	17.4	17.4	17.4	15.8	15.0	14.2
92.5°	54.6	52.7	51.6	50.4	51.6	52.7	54.6	64.7	76.4	101.6	140.0
95°	228.2	204.5	198.2	185.5	198.2	204.5	228.2	284.3	350.6	447.7	567.7
97.5°	525.7	481.5	458.6	448.5	458.6	481.5	525.7	574.5	666.7	761.3	845.6
100°	714.6	657.7	628.5	615.9	628.5	657.7	714.6	769.1	851.2	932.5	971.2
102.5°	884.5	844.0	812.3	802.8	812.3	844.0	884.5	942.8	998.4	1037.4	1013.5
105°	1097.5	1071.5	1055.7	1046.2	1055.7	1071.5	1097.5	1122.9	1131.6	1096.8	988.6
107.5°	1187.1	1186.9	1181.7	1175.4	1181.7	1186.9	1187.1	1174.3	1133.1	1043.9	899.5
110°	1197.8	1212.8	1218.4	1218.4	1218.4	1212.8	1197.8	1162.3	1095.2	983.8	833.8



TEST NUMBER: P333315-840

CATALOG NUMBER: S125DIP-S1270D810U840-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	165°	170°	175°	180°	185°	190°	195°	200°	205°	210°	215°
112.5°	1168.1	1193.9	1207.6	1213.4	1207.6	1193.9	1168.1	1116.2	1037.0	924.4	782.0
115°	1095.2	1133.1	1155.2	1165.5	1155.2	1133.1	1095.2	1033.6	947.6	839.4	717.0
117.5°	1014.2	1053.3	1075.3	1081.6	1075.3	1053.3	1014.2	952.6	873.6	780.4	675.0
120°	961.7	999.7	1021.0	1027.2	1021.0	999.7	961.7	903.3	833.8	747.0	652.2
122.5°	917.6	952.3	973.6	979.3	973.6	952.3	917.6	865.5	800.3	723.0	635.2
125°	860.7	893.0	910.4	918.3	910.4	893.0	860.7	816.5	759.6	690.9	610.4
127.5°	817.7	846.3	862.7	866.2	862.7	846.3	817.7	777.6	724.4	660.2	585.1
130°	791.2	817.3	833.0	837.8	833.0	817.3	791.2	751.7	700.3	638.8	569.3
132.5°	763.4	789.4	804.0	809.3	804.0	789.4	763.4	723.9	674.5	618.5	553.5
135°	717.7	743.8	758.0	762.8	758.0	743.8	717.7	683.0	638.0	587.4	533.0
137.5°	671.1	694.7	707.8	713.1	707.8	694.7	671.1	639.9	601.7	559.7	515.6
140°	642.0	662.5	674.3	678.2	674.3	662.5	642.0	612.7	579.6	543.2	506.1
142.5°	614.2	631.6	642.8	646.0	642.8	631.6	614.2	589.4	560.6	529.4	498.0
145°	576.4	589.9	598.5	601.7	598.5	589.9	576.4	557.4	536.1	511.7	487.2
147.5°	546.8	557.6	562.7	564.1	562.7	557.6	546.8	531.9	515.7	497.0	477.1
150°	529.9	539.3	542.5	543.2	542.5	539.3	529.9	518.0	503.7	488.8	471.4
152.5°	515.3	522.9	526.0	526.8	526.0	522.9	515.3	505.3	494.3	480.6	465.0
155°	495.8	501.4	503.7	504.5	503.7	501.4	495.8	488.0	479.3	468.3	455.7
157.5°	478.1	482.6	484.8	484.6	484.8	482.6	478.1	471.9	465.0	456.6	446.2
160°	466.7	470.6	472.2	471.4	472.2	470.6	466.7	461.1	455.7	447.7	439.8
162.5°	456.0	459.2	459.6	459.4	459.6	459.2	456.0	451.6	446.8	440.1	432.8
165°	440.6	442.2	442.2	442.2	442.2	442.2	440.6	437.5	433.5	428.8	423.2
167.5°	425.8	427.2	426.6	426.4	426.6	427.2	425.8	424.1	421.3	417.7	414.0
170°	416.9	417.7	417.7	416.9	417.7	417.7	416.9	415.4	413.7	411.4	409.0
172.5°	408.7	410.1	408.9	408.1	408.9	410.1	408.7	408.4	407.5	405.7	403.3
175°	398.8	399.5	398.0	397.2	398.0	399.5	398.8	398.8	398.8	397.2	397.2
177.5°	392.9	393.5	391.6	391.6	391.6	393.5	392.9	393.5	393.5	393.5	392.9
180°	391.6	391.6	391.6	391.6	391.6	391.6	391.6	391.6	391.6	391.6	391.6



TEST NUMBER: P333315-840

CATALOG NUMBER: S125DIP-S1270D810U840-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	220°	225°	230°	235°	240°	245°	250°	255°	260°	265°	270°
0°	1854.7	1854.7	1854.7	1854.7	1854.7	1854.7	1854.7	1854.7	1854.7	1854.7	1854.7
2.5°	1773.4	1781.0	1790.4	1797.4	1810.0	1815.6	1822.5	1828.3	1838.3	1847.8	1859.1
5°	1654.0	1667.3	1685.5	1705.1	1728.0	1743.6	1765.7	1779.1	1805.8	1830.3	1853.9
7.5°	1545.6	1562.0	1587.6	1612.9	1642.7	1669.8	1697.4	1728.0	1762.1	1802.4	1835.7
10°	1471.3	1493.4	1520.9	1552.4	1588.6	1620.1	1657.1	1690.1	1731.8	1779.1	1823.2
12.5°	1412.1	1431.0	1461.7	1492.0	1530.7	1569.0	1607.3	1651.1	1699.7	1752.0	1807.5
15°	1330.4	1346.2	1371.3	1413.0	1452.4	1490.2	1547.6	1588.6	1650.0	1708.3	1775.1
17.5°	1260.6	1280.2	1301.4	1337.2	1378.0	1425.1	1476.5	1527.8	1587.0	1660.8	1736.3
20°	1217.8	1233.6	1258.0	1285.6	1328.8	1376.0	1424.8	1476.8	1549.2	1625.6	1706.7
22.5°	1171.2	1188.2	1215.8	1245.9	1282.2	1327.6	1381.4	1438.4	1514.0	1589.0	1677.1
25°	1116.3	1128.1	1153.3	1180.0	1216.3	1254.9	1310.7	1373.7	1448.4	1534.3	1624.1
27.5°	1064.5	1074.9	1097.8	1121.2	1153.9	1199.7	1249.6	1313.2	1383.7	1470.7	1570.1
30°	1027.3	1038.3	1058.8	1084.0	1115.5	1155.6	1206.8	1266.7	1342.2	1427.2	1531.2
32.5°	995.2	1004.9	1020.4	1045.6	1076.4	1115.3	1162.8	1223.8	1299.4	1385.6	1487.6
35°	945.4	956.4	968.3	988.0	1014.7	1052.5	1104.5	1162.0	1234.4	1317.8	1411.5
37.5°	896.1	908.0	918.5	936.1	960.6	993.9	1038.8	1098.6	1164.2	1244.6	1334.4
40°	865.2	874.5	883.2	902.1	926.6	958.1	999.8	1053.3	1122.6	1197.4	1272.1
42.5°	834.2	843.1	850.5	866.9	889.4	919.6	959.5	1011.7	1076.0	1145.7	1211.6
45°	785.7	791.1	799.8	814.0	832.1	859.6	898.2	944.6	999.0	1065.1	1114.7
47.5°	733.1	741.7	748.8	761.2	776.1	803.1	840.1	879.6	928.9	978.1	1013.0
50°	692.8	701.5	711.7	723.5	737.6	762.9	796.7	836.8	878.5	916.4	946.2
52.5°	655.0	663.0	673.9	685.0	702.4	723.8	752.6	788.3	829.4	856.5	881.4
55°	599.1	603.0	615.6	626.6	643.2	658.9	688.0	719.5	744.7	765.2	785.7
57.5°	541.9	547.2	554.5	564.4	580.8	599.3	619.7	647.5	662.4	672.9	688.8
60°	505.4	507.0	511.7	523.5	536.1	552.6	576.2	595.9	606.9	615.6	628.9
62.5°	465.0	465.4	473.2	481.9	491.4	509.2	528.4	544.3	553.4	557.6	570.4
65°	408.6	407.0	411.7	418.8	429.8	441.6	458.2	472.3	471.5	476.3	484.1
67.5°	350.8	349.2	349.2	356.0	365.0	375.5	386.9	395.1	395.2	401.5	405.5
70°	311.7	307.0	310.1	315.7	319.6	328.3	340.8	344.1	344.8	347.9	351.8
72.5°	271.5	269.8	272.4	274.8	277.4	284.2	294.9	296.8	296.9	298.8	305.3
75°	215.7	214.1	212.6	214.9	218.0	222.8	226.7	229.8	229.0	229.8	234.6
77.5°	161.7	157.2	156.5	157.7	158.5	161.4	165.5	165.1	165.9	165.8	171.2
80°	128.4	122.0	121.2	121.2	122.0	123.6	125.1	126.7	124.4	126.7	128.4
82.5°	94.3	90.5	90.4	89.8	89.9	90.2	91.2	92.1	91.6	92.7	93.7
85°	51.9	50.4	48.1	49.6	48.8	46.5	48.1	45.6	44.8	45.6	46.5
87.5°	20.3	20.8	19.2	19.1	18.1	18.6	17.0	16.1	15.1	15.5	17.2
90°	13.4	12.6	11.0	10.3	8.7	7.9	6.4	4.7	3.1	1.6	0.8
92.5°	206.1	254.6	258.6	180.2	107.9	64.7	41.7	28.1	18.3	11.7	9.6
95°	684.6	699.6	570.9	352.9	179.3	94.7	59.2	41.8	33.1	26.9	26.1
97.5°	866.2	747.1	509.8	281.8	154.4	98.6	72.9	57.4	48.7	44.2	43.2
100°	910.4	713.1	454.8	255.8	153.2	107.3	83.7	68.7	60.0	56.9	55.2
102.5°	883.9	653.0	413.1	245.1	158.9	118.2	95.0	81.3	72.0	69.5	68.6
105°	799.1	572.5	372.7	240.9	170.6	135.8	113.7	101.1	93.2	89.3	89.3
107.5°	712.6	517.1	355.7	248.1	187.9	154.3	134.4	121.3	114.8	111.0	109.5
110°	663.3	491.1	350.6	255.1	200.6	168.1	147.6	135.8	128.7	125.5	124.0



TEST NUMBER: P333315-840

CATALOG NUMBER: S125DIP-S1270D810U840-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	220°	225°	230°	235°	240°	245°	250°	255°	260°	265°	270°
112.5°	626.6	475.9	350.6	263.9	212.6	181.5	161.6	149.7	142.6	140.1	138.5
115°	586.6	459.6	352.9	277.1	231.4	202.2	182.4	170.6	163.5	161.1	159.5
117.5°	562.8	451.5	358.2	292.4	250.6	223.0	203.9	190.5	183.4	180.9	178.4
120°	549.6	447.7	363.2	302.5	264.5	236.9	217.1	203.7	196.6	193.5	191.1
122.5°	538.2	444.5	367.6	313.8	277.8	250.1	230.5	215.7	208.6	206.1	204.4
125°	522.7	440.6	375.1	329.2	295.3	269.2	248.7	233.7	226.6	222.7	221.1
127.5°	508.5	438.7	383.4	343.5	312.3	287.1	266.6	250.6	241.7	236.6	234.2
130°	499.1	437.5	388.5	352.9	323.0	298.5	277.9	261.4	251.1	244.8	242.4
132.5°	491.5	437.5	394.2	361.1	333.1	308.6	288.0	270.8	259.3	251.8	248.7
135°	482.4	437.5	401.9	372.7	346.7	322.1	300.8	284.3	271.7	262.2	259.0
137.5°	474.4	438.4	409.0	381.2	356.3	334.0	312.0	295.8	283.2	274.3	272.0
140°	470.6	439.0	412.1	386.9	363.2	340.3	319.0	304.0	291.3	281.9	279.5
142.5°	467.5	439.7	414.0	390.1	367.6	346.0	326.0	311.5	298.9	290.1	288.3
145°	462.7	439.0	416.2	394.8	375.1	354.6	336.4	322.1	311.1	303.2	301.6
147.5°	457.8	437.0	416.9	397.7	379.8	361.8	345.9	333.6	323.3	316.5	315.5
150°	454.0	435.0	416.9	399.5	382.9	365.6	352.1	341.1	330.8	325.3	323.8
152.5°	449.6	432.5	416.3	400.8	386.1	370.0	357.9	347.4	338.4	333.6	332.5
155°	442.2	428.0	414.5	401.9	389.3	375.9	364.8	356.9	349.0	344.3	344.3
157.5°	435.3	423.2	412.5	402.7	391.9	380.4	372.0	365.1	358.3	354.6	354.7
160°	429.6	420.1	410.6	402.7	393.2	382.9	375.9	369.5	364.1	360.8	361.6
162.5°	424.4	416.3	408.7	402.0	394.5	385.5	379.6	374.6	369.7	366.6	367.3
165°	416.9	410.6	405.9	401.1	394.8	388.5	383.7	380.6	376.7	374.3	375.9
167.5°	409.5	405.1	401.4	399.2	394.8	389.6	386.6	384.4	382.1	380.7	381.5
170°	405.1	401.9	399.5	398.0	394.8	390.8	388.5	386.9	385.4	384.6	385.4
172.5°	400.6	398.1	397.0	396.7	394.2	390.8	389.7	388.8	387.2	386.5	387.9
175°	394.8	394.0	394.0	394.8	393.2	390.8	390.8	390.8	390.1	389.3	390.8
177.5°	392.2	391.6	391.6	392.9	392.2	391.0	391.0	391.6	391.0	391.0	392.2
180°	391.6	391.6	391.6	391.6	391.6	391.6	391.6	391.6	391.6	391.6	391.6



TEST NUMBER: P333315-840

CATALOG NUMBER: S125DIP-S1270D810U840-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	275°	280°	285°	290°	295°	300°	305°	310°	315°	320°	325°
0°	1854.7	1854.7	1854.7	1854.7	1854.7	1854.7	1854.7	1854.7	1854.7	1854.7	1854.7
2.5°	1864.7	1873.6	1879.3	1890.0	1898.7	1903.8	1908.2	1912.0	1916.4	1920.2	1930.9
5°	1876.7	1897.1	1914.5	1941.3	1965.7	1984.6	2005.0	2023.2	2038.1	2059.3	2075.9
7.5°	1871.5	1907.8	1946.0	1987.4	2029.7	2069.1	2105.4	2139.2	2169.9	2207.1	2239.6
10°	1866.4	1916.1	1964.9	2020.7	2078.2	2127.1	2172.7	2219.2	2253.0	2300.3	2340.4
12.5°	1862.7	1921.1	1980.0	2047.2	2110.3	2179.3	2240.1	2273.9	2325.4	2363.2	2411.0
15°	1846.8	1924.0	2005.0	2080.6	2170.3	2234.1	2287.6	2353.8	2401.8	2449.8	2501.7
17.5°	1818.3	1905.7	1996.4	2095.4	2181.5	2250.0	2319.0	2382.8	2440.0	2504.5	2569.1
20°	1805.0	1892.5	1996.4	2097.9	2182.1	2253.8	2324.6	2394.7	2457.7	2540.3	2615.1
22.5°	1777.4	1883.0	1978.7	2077.8	2164.5	2242.4	2322.8	2402.3	2486.0	2579.4	2673.0
25°	1728.0	1835.0	1936.5	2034.2	2121.5	2219.2	2304.9	2411.3	2518.3	2641.9	2758.3
27.5°	1676.6	1779.1	1872.2	1966.4	2068.3	2178.9	2290.2	2410.7	2550.9	2706.9	2871.2
30°	1635.1	1731.8	1822.4	1919.2	2025.5	2149.9	2271.9	2415.2	2577.4	2752.9	2948.1
32.5°	1586.5	1675.8	1763.8	1866.3	1982.1	2113.3	2255.5	2412.7	2607.6	2807.0	3008.0
35°	1503.6	1578.3	1668.9	1778.3	1908.9	2059.3	2223.9	2409.6	2633.2	2862.3	3031.5
37.5°	1405.1	1474.8	1570.1	1690.1	1827.1	1988.5	2183.7	2404.2	2641.6	2824.2	2878.8
40°	1339.1	1403.6	1502.8	1627.2	1767.3	1938.1	2152.2	2385.3	2615.1	2731.6	2686.7
42.5°	1268.5	1336.3	1432.9	1556.0	1706.9	1892.8	2112.5	2345.6	2538.3	2582.3	2427.3
45°	1157.2	1227.3	1322.5	1446.9	1609.0	1810.6	2039.6	2251.4	2362.4	2282.9	2042.9
47.5°	1053.8	1119.4	1207.7	1336.1	1503.4	1711.8	1932.5	2101.4	2110.2	1920.5	1664.1
50°	983.2	1043.8	1132.8	1261.1	1427.2	1638.2	1837.3	1970.3	1910.6	1695.7	1449.3
52.5°	913.9	973.3	1061.0	1188.1	1352.3	1545.6	1730.9	1824.3	1711.5	1491.0	1280.5
55°	814.0	866.0	951.7	1069.0	1224.9	1404.4	1561.9	1594.1	1447.6	1230.4	1059.6
57.5°	716.4	764.9	842.9	951.0	1093.5	1252.4	1375.5	1368.7	1213.9	1027.4	891.9
60°	650.3	697.5	766.8	872.2	1002.1	1139.1	1244.6	1219.4	1065.9	905.3	791.1
62.5°	591.1	633.2	698.7	791.0	909.6	1036.4	1123.1	1085.9	935.5	795.1	704.9
65°	503.8	539.3	595.1	673.9	772.2	877.0	943.8	895.9	767.5	658.1	585.7
67.5°	420.5	448.9	495.7	558.6	642.5	726.6	767.4	719.0	616.4	536.5	482.9
70°	367.6	392.8	429.0	484.9	558.2	628.9	659.6	616.4	528.3	459.7	421.1
72.5°	314.8	335.5	367.3	417.6	476.3	537.7	564.6	523.2	450.8	392.9	356.9
75°	243.3	257.4	279.4	314.1	360.5	409.4	424.3	388.1	341.6	298.3	274.8
77.5°	174.1	186.1	202.8	224.7	257.6	288.6	301.6	280.7	244.8	217.4	198.0
80°	133.8	140.2	154.3	172.4	198.3	218.0	226.7	213.4	188.1	167.6	152.7
82.5°	95.4	101.7	110.2	125.1	141.7	155.1	164.4	155.4	137.1	121.1	112.4
85°	46.5	50.4	55.1	61.4	74.0	81.9	81.1	75.5	68.5	62.2	57.5
87.5°	16.7	17.7	19.8	23.3	25.5	28.2	29.8	28.7	26.5	24.7	23.0
90°	1.6	3.1	4.7	6.4	7.9	8.7	10.3	11.0	12.6	13.4	14.2
92.5°	11.7	18.3	28.1	41.7	64.7	107.9	180.2	258.6	254.6	206.1	140.0
95°	26.9	33.1	41.8	59.2	94.7	179.3	352.9	570.9	699.6	684.6	567.7
97.5°	44.2	48.7	57.4	72.9	98.6	154.4	281.8	509.8	747.1	866.2	845.6
100°	56.9	60.0	68.7	83.7	107.3	153.2	255.8	454.8	713.1	910.4	971.2
102.5°	69.5	72.0	81.3	95.0	118.2	158.9	245.1	413.1	653.0	883.9	1013.5
105°	89.3	93.2	101.1	113.7	135.8	170.6	240.9	372.7	572.5	799.1	988.6
107.5°	111.0	114.8	121.3	134.4	154.3	187.9	248.1	355.7	517.1	712.6	899.5
110°	125.5	128.7	135.8	147.6	168.1	200.6	255.1	350.6	491.1	663.3	833.8



TEST NUMBER: P333315-840

CATALOG NUMBER: S125DIP-S1270D810U840-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	275°	280°	285°	290°	295°	300°	305°	310°	315°	320°	325°
112.5°	140.1	142.6	149.7	161.6	181.5	212.6	263.9	350.6	475.9	626.6	782.0
115°	161.1	163.5	170.6	182.4	202.2	231.4	277.1	352.9	459.6	586.6	717.0
117.5°	180.9	183.4	190.5	203.9	223.0	250.6	292.4	358.2	451.5	562.8	675.0
120°	193.5	196.6	203.7	217.1	236.9	264.5	302.5	363.2	447.7	549.6	652.2
122.5°	206.1	208.6	215.7	230.5	250.1	277.8	313.8	367.6	444.5	538.2	635.2
125°	222.7	226.6	233.7	248.7	269.2	295.3	329.2	375.1	440.6	522.7	610.4
127.5°	236.6	241.7	250.6	266.6	287.1	312.3	343.5	383.4	438.7	508.5	585.1
130°	244.8	251.1	261.4	277.9	298.5	323.0	352.9	388.5	437.5	499.1	569.3
132.5°	251.8	259.3	270.8	288.0	308.6	333.1	361.1	394.2	437.5	491.5	553.5
135°	262.2	271.7	284.3	300.8	322.1	346.7	372.7	401.9	437.5	482.4	533.0
137.5°	274.3	283.2	295.8	312.0	334.0	356.3	381.2	409.0	438.4	474.4	515.6
140°	281.9	291.3	304.0	319.0	340.3	363.2	386.9	412.1	439.0	470.6	506.1
142.5°	290.1	298.9	311.5	326.0	346.0	367.6	390.1	414.0	439.7	467.5	498.0
145°	303.2	311.1	322.1	336.4	354.6	375.1	394.8	416.2	439.0	462.7	487.2
147.5°	316.5	323.3	333.6	345.9	361.8	379.8	397.7	416.9	437.0	457.8	477.1
150°	325.3	330.8	341.1	352.1	365.6	382.9	399.5	416.9	435.0	454.0	471.4
152.5°	333.6	338.4	347.4	357.9	370.0	386.1	400.8	416.3	432.5	449.6	465.0
155°	344.3	349.0	356.9	364.8	375.9	389.3	401.9	414.5	428.0	442.2	455.7
157.5°	354.6	358.3	365.1	372.0	380.4	391.9	402.7	412.5	423.2	435.3	446.2
160°	360.8	364.1	369.5	375.9	382.9	393.2	402.7	410.6	420.1	429.6	439.8
162.5°	366.6	369.7	374.6	379.6	385.5	394.5	402.0	408.7	416.3	424.4	432.8
165°	374.3	376.7	380.6	383.7	388.5	394.8	401.1	405.9	410.6	416.9	423.2
167.5°	380.7	382.1	384.4	386.6	389.6	394.8	399.2	401.4	405.1	409.5	414.0
170°	384.6	385.4	386.9	388.5	390.8	394.8	398.0	399.5	401.9	405.1	409.0
172.5°	386.5	387.2	388.8	389.7	390.8	394.2	396.7	397.0	398.1	400.6	403.3
175°	389.3	390.1	390.8	390.8	390.8	393.2	394.8	394.0	394.0	394.8	397.2
177.5°	391.0	391.0	391.6	391.0	391.0	392.2	392.9	391.6	391.6	392.2	392.9
180°	391.6	391.6	391.6	391.6	391.6	391.6	391.6	391.6	391.6	391.6	391.6



TEST NUMBER: P333315-840

CATALOG NUMBER: S125DIP-S1270D810U840-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	330°	335°	340°	345°	350°	355°	360°
0°	1854.7	1854.7	1854.7	1854.7	1854.7	1854.7	1854.7
2.5°	1939.6	1944.7	1955.4	1951.7	1956.7	1959.2	1961.8
5°	2096.4	2121.5	2132.5	2131.0	2147.5	2143.5	2139.6
7.5°	2273.3	2299.8	2314.6	2333.0	2343.7	2344.5	2353.8
10°	2373.5	2408.1	2422.3	2442.0	2454.6	2461.6	2460.8
12.5°	2450.2	2477.4	2509.1	2518.8	2535.8	2544.8	2541.4
15°	2542.7	2586.0	2619.1	2635.5	2656.9	2663.1	2671.8
17.5°	2625.2	2683.3	2721.9	2773.2	2792.6	2804.4	2797.4
20°	2687.6	2763.9	2802.5	2863.9	2897.7	2915.9	2909.5
22.5°	2761.3	2843.9	2915.2	2968.4	3019.9	3044.3	3049.4
25°	2887.5	3000.8	3105.5	3175.6	3239.3	3254.3	3287.4
27.5°	3028.6	3162.2	3274.2	3347.9	3392.2	3408.9	3419.3
30°	3117.4	3250.4	3334.7	3381.8	3396.1	3394.5	3392.8
32.5°	3160.8	3244.1	3260.3	3247.1	3214.7	3187.2	3158.7
35°	3099.3	3037.1	2944.2	2824.5	2736.3	2647.4	2638.8
37.5°	2787.3	2588.5	2433.9	2261.2	2161.5	2100.0	2057.5
40°	2493.9	2268.0	2080.6	1935.0	1833.4	1793.3	1753.9
42.5°	2175.2	1959.3	1793.4	1671.7	1595.4	1550.8	1519.6
45°	1767.3	1576.8	1446.9	1358.8	1298.1	1263.4	1243.7
47.5°	1448.1	1307.3	1196.9	1133.3	1091.4	1064.5	1064.6
50°	1276.9	1142.3	1069.0	1018.7	982.4	961.2	965.1
52.5°	1125.1	1024.5	962.0	919.8	893.0	879.9	879.5
55°	940.7	868.3	827.4	796.7	778.5	763.6	766.8
57.5°	804.7	743.6	716.2	690.7	678.1	672.2	663.5
60°	720.3	673.1	649.4	628.9	616.4	611.7	603.0
62.5°	645.4	608.2	585.2	568.6	557.1	555.6	548.9
65°	542.4	514.0	493.6	485.7	473.9	470.8	470.8
67.5°	447.2	426.9	410.9	403.6	398.5	399.3	395.5
70°	387.3	370.8	360.5	352.6	348.7	349.5	346.4
72.5°	338.8	320.4	311.4	306.7	301.5	303.6	302.3
75°	256.6	247.2	242.5	237.7	234.6	233.0	231.5
77.5°	188.4	180.2	176.5	173.8	174.3	170.5	173.5
80°	145.6	138.6	136.2	132.3	131.5	131.5	130.7
82.5°	106.5	102.6	100.9	97.7	96.2	97.5	95.4
85°	55.1	51.9	51.2	51.2	49.6	48.1	51.9
87.5°	23.1	20.8	21.1	20.5	20.5	20.0	18.8
90°	15.0	15.8	17.4	17.4	17.4	18.2	18.2
92.5°	101.6	76.4	64.7	54.6	52.7	51.6	50.4
95°	447.7	350.6	284.3	228.2	204.5	198.2	185.5
97.5°	761.3	666.7	574.5	525.7	481.5	458.6	448.5
100°	932.5	851.2	769.1	714.6	657.7	628.5	615.9
102.5°	1037.4	998.4	942.8	884.5	844.0	812.3	802.8
105°	1096.8	1131.6	1122.9	1097.5	1071.5	1055.7	1046.2
107.5°	1043.9	1133.1	1174.3	1187.1	1186.9	1181.7	1175.4
110°	983.8	1095.2	1162.3	1197.8	1212.8	1218.4	1218.4



TEST NUMBER: P333315-840

CATALOG NUMBER: S125DIP-S1270D810U840-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	330°	335°	340°	345°	350°	355°	360°
112.5°	924.4	1037.0	1116.2	1168.1	1193.9	1207.6	1213.4
115°	839.4	947.6	1033.6	1095.2	1133.1	1155.2	1165.5
117.5°	780.4	873.6	952.6	1014.2	1053.3	1075.3	1081.6
120°	747.0	833.8	903.3	961.7	999.7	1021.0	1027.2
122.5°	723.0	800.3	865.5	917.6	952.3	973.6	979.3
125°	690.9	759.6	816.5	860.7	893.0	910.4	918.3
127.5°	660.2	724.4	777.6	817.7	846.3	862.7	866.2
130°	638.8	700.3	751.7	791.2	817.3	833.0	837.8
132.5°	618.5	674.5	723.9	763.4	789.4	804.0	809.3
135°	587.4	638.0	683.0	717.7	743.8	758.0	762.8
137.5°	559.7	601.7	639.9	671.1	694.7	707.8	713.1
140°	543.2	579.6	612.7	642.0	662.5	674.3	678.2
142.5°	529.4	560.6	589.4	614.2	631.6	642.8	646.0
145°	511.7	536.1	557.4	576.4	589.9	598.5	601.7
147.5°	497.0	515.7	531.9	546.8	557.6	562.7	564.1
150°	488.8	503.7	518.0	529.9	539.3	542.5	543.2
152.5°	480.6	494.3	505.3	515.3	522.9	526.0	526.8
155°	468.3	479.3	488.0	495.8	501.4	503.7	504.5
157.5°	456.6	465.0	471.9	478.1	482.6	484.8	484.6
160°	447.7	455.7	461.1	466.7	470.6	472.2	471.4
162.5°	440.1	446.8	451.6	456.0	459.2	459.6	459.4
165°	428.8	433.5	437.5	440.6	442.2	442.2	442.2
167.5°	417.7	421.3	424.1	425.8	427.2	426.6	426.4
170°	411.4	413.7	415.4	416.9	417.7	417.7	416.9
172.5°	405.7	407.5	408.4	408.7	410.1	408.9	408.1
175°	397.2	398.8	398.8	398.8	399.5	398.0	397.2
177.5°	393.5	393.5	393.5	392.9	393.5	391.6	391.6
180°	391.6	391.6	391.6	391.6	391.6	391.6	391.6

(END OF REPORT)