

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P333319-840

Luminaire Tested: **S125DIP-S1270D810U840-4F0-1E-UDD-F**

Issue Date: 3/3/2020

Test Information

Test Method: LM-79-08
Report Number: P333319-840
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-7,
Test Lab: INNOVATION CENTER
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: NEO-RAY
Catalog Number: S125DIP-S1270D810U840-4F0-1E-UDD-F
Description: DEFINE 5 DIRECT-INDIRECT PENDANT LED LUMINAIRE
DOWNLIGHT 1270 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER
UPLIGHT 810 LUMENS PER FOOT, NO LENS
Light Source: -
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 8452.6 lumens
Efficiency: N/A
Efficacy: 139.3 lumens/watt
Spacing Criteria (0/90/45): 1.21 / 1.18 / 1.31
Luminous Opening: Rectangular (W 0.42' x L: 4' x H: 0')
CIE Type: Semi-Direct


Input Watts (W): 60.7
Input Voltage (V): 120
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P333319-840

CATALOG NUMBER: S125DIP-S1270D810U840-4F0-1E-UDD-F

Luminous Intensity Polar Plot





TEST NUMBER: P333319-840

CATALOG NUMBER: S125DIP-S1270D810U840-4F0-1E-UDD-F

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	110	110	110	110	103	103	103	103	90	90	90	78	78	78	66	66	66	61
1	100	96	92	88	94	90	86	83	79	76	74	68	66	65	59	57	56	51
2	91	84	77	72	85	78	73	68	69	65	61	60	57	54	52	49	47	43
3	83	74	66	60	78	69	62	57	61	55	51	53	49	46	46	43	40	36
4	76	65	57	51	71	61	54	48	54	48	44	47	43	39	41	37	35	31
5	70	58	50	44	65	55	47	42	48	42	38	42	38	34	37	33	30	27
6	65	52	44	38	60	49	42	36	44	37	33	38	33	30	33	30	27	24
7	60	47	39	33	56	45	37	32	40	33	29	35	30	26	30	27	24	21
8	55	43	35	30	52	41	33	28	36	30	26	32	27	23	28	24	21	19
9	52	39	32	26	48	37	30	25	33	27	23	29	25	21	26	22	19	17
10	48	36	29	24	45	34	27	23	31	25	21	27	22	19	24	20	17	15

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	12853	12853	12853
5°	12882	12759	12841
10°	12804	12669	12742
15°	12664	12517	12570
20°	12466	12304	12325
25°	12252	12050	12039
30°	11989	11777	11718
35°	11706	11483	11321
40°	11415	11163	11005
45°	11102	10872	10656
50°	10758	10520	10203
55°	10424	10124	9839
60°	10026	9722	9376
65°	9553	9239	8926
70°	9098	8682	8384
75°	8289	8015	7738
80°	7375	7260	7089
85°	6417	6536	6180



TEST NUMBER: P333319-840

CATALOG NUMBER: S125DIP-S1270D810U840-4F0-1E-UDD-F

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	187.6	2.2
10°-20°	530.1	6.3
20°-30°	782.7	9.3
30°-40°	913.3	10.8
40°-50°	917.2	10.9
50°-60°	805.1	9.5
60°-70°	599.9	7.1
70°-80°	343.0	4.1
80°-90°	102.0	1.2
90°-100°	38.7	0.5
100°-110°	238.6	2.8
110°-120°	432.8	5.1
120°-130°	555.4	6.6
130°-140°	597.4	7.1
140°-150°	560.7	6.6
150°-160°	453.6	5.4
160°-170°	293.3	3.5
170°-180°	101.2	1.2
0°-30°	1500.4	17.8
0°-40°	2413.6	28.6
0°-60°	4136.0	48.9
0°-90°	5181.0	61.3
90°-120°	710.1	8.4
90°-150°	2423.5	28.7
90°-180°	3272.0	38.7
0°-180°	8452.6	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	1990	1990	1990	1990	1990	
5°	1987	1983	1968	1981	1981	188
15°	1894	1889	1872	1880	1880	534
25°	1719	1711	1691	1694	1689	791
35°	1485	1478	1456	1448	1436	928
45°	1216	1208	1190	1172	1167	936
55°	926	920	899	885	874	826
65°	625	621	605	591	584	620
75°	332	329	321	316	310	354
85°	87	88	88	86	83	97
90°	1	7	13	17	19	7
95°	45	41	13	16	17	57
105°	232	235	235	235	235	246
115°	436	440	441	437	433	432
125°	620	625	626	622	620	554
135°	773	778	776	775	770	596
145°	896	898	898	898	894	560
155°	987	983	984	986	980	455
165°	1042	1037	1038	1042	1036	294
175°	1065	1061	1062	1067	1061	101
180°	1065	1065	1065	1065	1065	



TEST NUMBER: P333319-840

CATALOG NUMBER: S125DIP-S1270D810U840-4F0-1E-UDD-F

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	1990.1	1990.1	1990.1	1990.1	1990.1	1990.1	1990.1	1990.1	1990.1	1990.1	1990.1
2.5°	1995.2	1994.4	1993.6	1992.7	1991.9	1990.0	1987.2	1984.4	1981.7	1978.8	1981.7
5°	1987.0	1986.3	1985.6	1984.9	1984.2	1982.2	1978.6	1975.1	1971.7	1968.1	1971.3
7.5°	1968.7	1968.0	1967.3	1966.6	1965.9	1963.7	1959.8	1956.0	1952.2	1948.3	1951.4
10°	1952.4	1951.7	1951.0	1950.3	1949.5	1947.3	1943.5	1939.6	1935.7	1931.9	1934.7
12.5°	1932.2	1931.0	1929.8	1928.4	1927.2	1924.8	1921.2	1917.6	1914.1	1910.5	1912.8
15°	1894.1	1893.1	1892.0	1891.0	1890.0	1887.4	1883.6	1879.8	1875.9	1872.1	1873.8
17.5°	1850.4	1848.9	1847.2	1845.7	1844.2	1841.4	1837.4	1833.4	1829.5	1825.4	1827.7
20°	1813.8	1813.1	1812.4	1811.7	1811.0	1808.4	1803.8	1799.3	1794.7	1790.2	1792.6
22.5°	1777.3	1776.0	1774.7	1773.5	1772.2	1769.5	1765.2	1761.0	1756.7	1752.4	1754.0
25°	1719.4	1717.6	1715.9	1714.1	1712.3	1709.2	1704.7	1700.1	1695.6	1691.0	1691.7
27.5°	1651.6	1650.6	1649.5	1648.5	1647.5	1644.6	1639.9	1635.2	1630.5	1625.8	1626.0
30°	1607.6	1606.5	1605.5	1604.4	1603.4	1600.2	1595.0	1589.7	1584.5	1579.2	1578.5
32.5°	1559.7	1558.1	1556.5	1554.9	1553.3	1550.1	1545.4	1540.8	1536.0	1531.4	1530.1
35°	1484.7	1483.4	1482.0	1480.6	1479.1	1476.0	1471.1	1466.2	1461.3	1456.4	1454.7
37.5°	1406.9	1405.2	1403.5	1401.7	1400.0	1396.7	1392.2	1387.6	1382.9	1378.4	1375.7
40°	1354.0	1352.3	1350.6	1348.8	1347.1	1343.7	1338.9	1333.9	1329.1	1324.1	1321.0
42.5°	1297.4	1296.0	1294.4	1292.9	1291.5	1288.3	1283.4	1278.5	1273.6	1268.7	1265.9
45°	1215.5	1214.2	1212.7	1211.3	1209.9	1207.1	1203.0	1198.7	1194.6	1190.3	1186.1
47.5°	1127.3	1127.4	1127.5	1127.5	1127.6	1125.1	1120.1	1115.1	1110.0	1105.0	1100.8
50°	1070.7	1069.6	1068.5	1067.5	1066.4	1063.8	1059.7	1055.4	1051.3	1047.0	1042.5
52.5°	1012.7	1012.0	1011.2	1010.4	1009.7	1007.0	1002.5	998.0	993.6	989.1	985.1
55°	925.8	924.7	923.7	922.6	921.6	918.7	913.7	908.9	903.9	899.1	895.9
57.5°	834.1	833.6	833.0	832.5	831.9	829.6	825.5	821.3	817.2	813.0	809.0
60°	776.2	774.9	773.5	772.0	770.6	768.0	764.2	760.3	756.5	752.7	749.1
62.5°	715.8	714.7	713.6	712.4	711.2	709.1	705.8	702.5	699.2	695.9	692.2
65°	625.1	624.4	623.7	623.0	622.3	620.0	616.1	612.3	608.4	604.6	601.5
67.5°	537.2	535.7	534.3	532.8	531.4	529.2	526.3	523.4	520.6	517.7	515.0
70°	481.8	480.1	478.3	476.6	474.8	472.3	469.2	466.1	462.9	459.8	457.7
72.5°	421.3	420.1	419.0	417.8	416.6	415.0	412.9	410.9	408.9	406.9	404.5
75°	332.2	331.5	330.8	330.1	329.4	328.2	326.5	324.7	323.0	321.2	320.1
77.5°	250.0	249.7	249.4	249.2	248.9	248.3	247.3	246.3	245.3	244.4	243.8
80°	198.3	198.3	198.3	198.3	198.3	198.0	197.3	196.6	195.9	195.2	194.9
82.5°	153.0	152.5	151.9	151.4	150.8	150.5	150.3	150.2	150.1	149.9	149.3
85°	86.6	86.9	87.3	87.7	88.0	88.2	88.2	88.2	88.2	88.2	87.9
87.5°	34.1	34.4	34.7	35.0	35.2	35.4	35.3	35.3	35.3	35.2	35.4
90°	0.8	2.2	3.6	5.0	6.4	7.7	9.0	10.2	11.4	12.6	13.5
92.5°	12.1	11.2	10.2	9.2	8.3	8.3	9.4	10.5	11.5	12.6	13.5
95°	45.0	44.5	43.9	43.4	42.9	39.3	32.6	26.0	19.3	12.6	13.5
97.5°	94.0	94.9	95.8	96.8	97.8	91.7	78.5	65.2	52.0	38.9	33.9
100°	131.9	132.4	132.9	133.5	134.0	134.6	135.3	136.0	136.7	137.4	111.3
102.5°	170.5	171.1	171.8	172.4	173.1	173.6	174.1	174.5	174.9	175.3	170.4
105°	232.2	232.9	233.6	234.3	235.0	235.3	235.3	235.3	235.3	235.3	235.3
107.5°	296.3	296.3	296.3	296.3	296.3	296.5	296.8	297.2	297.5	297.9	297.9
110°	338.0	338.0	338.0	338.0	338.0	338.2	338.5	338.9	339.2	339.6	339.1



TEST NUMBER: P333319-840

CATALOG NUMBER: S125DIP-S1270D810U840-4F0-1E-UDD-F

CANDELA DISTRIBUTION (continued):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	377.2	377.6	378.0	378.5	378.9	379.2	379.4	379.6	379.8	380.0	379.4
115°	436.0	436.9	437.7	438.6	439.5	440.0	440.2	440.3	440.5	440.7	440.0
117.5°	496.8	496.8	496.7	496.7	496.7	497.0	497.6	498.3	499.0	499.6	498.7
120°	534.6	534.5	534.3	534.1	533.9	534.1	534.6	535.2	535.7	536.2	535.9
122.5°	568.2	568.9	569.5	570.2	570.8	571.3	571.5	571.8	572.0	572.3	571.9
125°	620.0	621.2	622.4	623.7	624.9	625.5	625.5	625.5	625.5	625.5	624.8
127.5°	669.4	670.2	671.2	672.1	672.9	673.3	673.2	673.1	673.0	672.9	672.5
130°	699.7	700.6	701.5	702.4	703.3	703.8	704.0	704.1	704.3	704.5	704.0
132.5°	730.0	731.0	732.1	733.1	734.2	734.5	734.1	733.7	733.3	732.9	732.8
135°	773.2	774.3	775.3	776.4	777.4	777.7	777.4	777.0	776.7	776.4	776.0
137.5°	812.8	813.7	814.7	815.6	816.5	816.8	816.5	816.2	815.9	815.5	815.6
140°	838.7	839.1	839.4	839.8	840.1	840.2	840.0	839.9	839.7	839.5	839.9
142.5°	862.1	862.3	862.5	862.7	862.9	863.1	863.4	863.6	863.9	864.1	864.2
145°	896.4	896.8	897.1	897.5	897.8	898.0	898.0	898.0	898.0	898.0	898.2
147.5°	926.3	926.3	926.2	926.1	926.1	926.1	926.3	926.6	926.9	927.1	927.3
150°	945.3	945.0	944.6	944.3	943.9	943.9	944.3	944.6	945.0	945.3	945.7
152.5°	963.7	962.9	962.1	961.4	960.6	960.4	960.7	961.1	961.4	961.8	962.1
155°	987.2	986.1	985.1	984.0	983.0	982.6	983.0	983.3	983.7	984.0	984.5
157.5°	1005.3	1004.7	1004.1	1003.5	1002.8	1002.5	1002.6	1002.6	1002.6	1002.7	1003.2
160°	1018.0	1016.9	1015.9	1014.8	1013.8	1013.4	1013.5	1013.7	1013.9	1014.0	1014.7
162.5°	1028.1	1027.0	1026.0	1024.9	1023.9	1023.5	1023.6	1023.8	1024.0	1024.2	1025.1
165°	1041.7	1040.7	1039.6	1038.5	1037.4	1037.0	1037.2	1037.4	1037.5	1037.7	1038.8
167.5°	1051.8	1050.8	1049.7	1048.5	1047.4	1047.0	1047.1	1047.3	1047.5	1047.7	1048.9
170°	1057.5	1056.2	1055.0	1053.8	1052.6	1052.1	1052.2	1052.4	1052.6	1052.8	1054.2
172.5°	1061.3	1060.1	1058.8	1057.6	1056.3	1055.9	1056.2	1056.5	1056.8	1057.1	1058.4
175°	1065.4	1064.3	1063.3	1062.3	1061.2	1060.8	1060.9	1061.1	1061.3	1061.5	1062.9
177.5°	1067.3	1066.4	1065.6	1064.8	1063.9	1063.6	1063.7	1063.8	1064.0	1064.1	1065.1
180°	1065.4	1065.4	1065.4	1065.4	1065.4	1065.4	1065.4	1065.4	1065.4	1065.4	1065.4



TEST NUMBER: P333319-840

CATALOG NUMBER: S125DIP-S1270D810U840-4F0-1E-UDD-F

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°
0°	1990.1	1990.1	1990.1	1990.1	1990.1	1990.1	1990.1	1990.1
2.5°	1984.4	1987.2	1990.0	1991.3	1991.0	1990.7	1990.4	1990.1
5°	1974.4	1977.6	1980.7	1982.2	1981.8	1981.5	1981.1	1980.7
7.5°	1954.4	1957.5	1960.6	1962.0	1961.7	1961.3	1961.0	1960.6
10°	1937.5	1940.4	1943.1	1944.3	1944.0	1943.6	1943.3	1943.0
12.5°	1915.0	1917.2	1919.5	1920.6	1920.5	1920.4	1920.4	1920.3
15°	1875.6	1877.3	1879.1	1880.0	1880.0	1880.0	1880.0	1880.0
17.5°	1829.8	1832.0	1834.1	1834.3	1832.6	1830.9	1829.1	1827.4
20°	1795.1	1797.6	1800.0	1800.4	1798.6	1796.9	1795.1	1793.3
22.5°	1755.7	1757.3	1758.9	1759.1	1757.9	1756.7	1755.4	1754.3
25°	1692.4	1693.1	1693.8	1693.6	1692.6	1691.5	1690.5	1689.4
27.5°	1626.1	1626.3	1626.4	1625.9	1624.9	1623.9	1622.8	1621.7
30°	1577.8	1577.1	1576.4	1575.6	1574.5	1573.5	1572.4	1571.3
32.5°	1528.8	1527.6	1526.3	1524.7	1522.9	1521.0	1519.0	1517.2
35°	1452.9	1451.2	1449.5	1447.1	1444.3	1441.6	1438.8	1435.9
37.5°	1373.1	1370.6	1368.0	1365.8	1364.2	1362.6	1361.0	1359.4
40°	1317.9	1314.7	1311.5	1309.5	1308.4	1307.4	1306.3	1305.3
42.5°	1263.0	1260.1	1257.3	1255.1	1253.4	1251.8	1250.2	1248.6
45°	1181.9	1177.7	1173.6	1170.9	1169.8	1168.8	1167.7	1166.7
47.5°	1096.4	1092.2	1087.9	1084.6	1082.1	1079.6	1077.2	1074.8
50°	1037.9	1033.4	1028.9	1025.3	1022.9	1020.5	1018.0	1015.5
52.5°	981.1	977.1	973.1	969.8	967.0	964.3	961.6	958.9
55°	892.7	889.6	886.5	883.6	881.2	878.8	876.3	873.8
57.5°	805.0	800.9	796.9	794.2	792.8	791.5	790.1	788.8
60°	745.6	742.1	738.6	735.7	733.2	730.7	728.3	725.9
62.5°	688.3	684.6	680.9	678.0	676.1	674.2	672.3	670.4
65°	598.3	595.1	592.0	589.8	588.3	586.9	585.5	584.1
67.5°	512.4	509.7	507.1	505.3	504.4	503.6	502.8	501.9
70°	455.6	453.4	451.3	449.6	448.2	446.8	445.5	444.0
72.5°	402.1	399.7	397.4	395.5	394.0	392.6	391.2	389.8
75°	319.1	318.0	317.0	315.8	314.4	313.0	311.5	310.1
77.5°	243.1	242.5	241.9	241.1	240.0	239.0	238.1	237.1
80°	194.5	194.2	193.8	193.3	192.6	191.9	191.2	190.6
82.5°	148.7	148.0	147.3	147.0	146.8	146.7	146.5	146.4
85°	87.5	87.2	86.7	86.2	85.5	84.8	84.1	83.4
87.5°	35.6	35.9	36.0	35.9	35.3	34.9	34.4	34.0
90°	14.4	15.2	16.2	16.9	17.4	17.9	18.4	19.0
92.5°	14.4	15.2	16.2	16.7	17.0	17.2	17.5	17.7
95°	14.4	15.2	16.2	16.6	16.6	16.6	16.6	16.6
97.5°	29.0	24.0	19.1	16.6	16.6	16.6	16.6	16.6
100°	85.1	59.0	32.8	19.4	18.7	18.0	17.3	16.6
102.5°	165.4	160.5	155.5	147.1	135.1	123.2	111.3	99.4
105°	235.3	235.3	235.3	235.3	235.1	234.9	234.7	234.6
107.5°	298.0	298.0	298.0	297.8	297.3	296.7	296.2	295.7
110°	338.5	338.0	337.5	337.3	337.5	337.7	337.8	338.0



TEST NUMBER: P333319-840

CATALOG NUMBER: S125DIP-S1270D810U840-4F0-1E-UDD-F

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°
112.5°	378.7	378.0	377.4	376.9	376.7	376.4	376.2	376.0
115°	439.3	438.6	437.9	437.0	436.0	434.8	433.8	432.8
117.5°	497.8	496.9	495.9	495.2	494.8	494.3	493.9	493.4
120°	535.5	535.2	534.8	534.2	533.3	532.5	531.6	530.7
122.5°	571.6	571.2	570.9	570.2	569.2	568.2	567.1	566.1
125°	624.1	623.4	622.7	622.1	621.6	621.0	620.5	620.0
127.5°	672.1	671.8	671.4	670.4	669.2	667.9	666.6	665.3
130°	703.4	702.9	702.4	701.7	700.7	699.9	699.0	698.1
132.5°	732.7	732.6	732.5	732.0	731.1	730.2	729.3	728.5
135°	775.7	775.3	775.0	774.3	773.2	772.1	771.0	770.0
137.5°	815.7	815.7	815.8	815.4	814.5	813.5	812.6	811.7
140°	840.2	840.6	840.9	840.6	839.5	838.5	837.4	836.4
142.5°	864.3	864.3	864.4	863.9	862.9	861.8	860.8	859.7
145°	898.3	898.5	898.7	898.2	897.2	896.2	895.0	894.0
147.5°	927.5	927.7	927.9	927.4	926.0	924.8	923.5	922.3
150°	946.0	946.4	946.7	946.2	944.8	943.4	942.0	940.6
152.5°	962.5	962.8	963.2	962.7	961.5	960.2	959.0	957.7
155°	985.1	985.6	986.1	985.7	984.3	982.9	981.5	980.1
157.5°	1003.8	1004.4	1004.9	1004.5	1003.1	1001.7	1000.3	998.9
160°	1015.4	1016.1	1016.8	1016.5	1015.1	1013.7	1012.3	1010.9
162.5°	1026.1	1027.1	1028.0	1027.8	1026.2	1024.7	1023.2	1021.7
165°	1039.9	1040.9	1042.0	1041.8	1040.4	1038.9	1037.5	1036.1
167.5°	1050.3	1051.5	1052.8	1052.6	1051.0	1049.5	1047.8	1046.3
170°	1055.5	1056.9	1058.3	1058.2	1056.7	1055.1	1053.5	1052.0
172.5°	1059.7	1061.0	1062.3	1062.1	1060.5	1058.9	1057.3	1055.7
175°	1064.2	1065.6	1067.0	1066.9	1065.4	1063.8	1062.3	1060.7
177.5°	1066.1	1067.0	1068.0	1068.0	1066.8	1065.7	1064.6	1063.5
180°	1065.4	1065.4	1065.4	1065.4	1065.4	1065.4	1065.4	1065.4

(END OF REPORT)