

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P331464-830

Luminaire Tested: **SA2XXDIP-C1005D1080U830-4F0-1E-UDD-F4**

Issue Date: 10/7/2019

Test Information

Test Method: LM-79-08
Report Number: P331464-830
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-16,
Test Lab: INNOVATION CENTER
Issue Date: 10/7/2019
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: NEO-RAY
Catalog Number: SA2XXDIP-C1005D1080U830-4F0-1E-UDD-F4
Description: DEFINE 2 DIRECT-INDIRECT PENDANT LED LUMINAIRE
DOWNLIGHT 1005 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER
UPLIGHT 1080 LUMENS PER FOOT, BATWING OPTIC
Light Source: -
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 7789.1 lumens
Efficiency: N/A
Efficacy: 108.6 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 1.16 / 1.3
Luminous Opening: Rectangular (W 0.17' x L: 4' x H: 0')
CIE Type: General Diffuse


Input Watts (W): 71.7
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P331464-830

CATALOG NUMBER: SA2XXDIP-C1005D1080U830-4F0-1E-UDD-F4

Luminous Intensity Polar Plot





TEST NUMBER: P331464-830

CATALOG NUMBER: SA2XXDIP-C1005D1080U830-4F0-1E-UDD-F4

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	107	107	107	107	99	99	99	99	83	83	83	69	69	69	55	55	55	49
1	98	93	89	86	90	86	83	80	73	70	68	60	59	57	49	48	47	41
2	89	81	75	70	82	75	70	65	64	60	56	53	50	48	43	41	39	35
3	81	72	64	58	74	66	60	55	56	51	47	47	43	40	38	36	33	29
4	74	63	55	49	68	59	52	46	50	45	40	42	38	35	34	31	29	25
5	68	56	48	42	62	52	45	40	45	39	35	37	33	30	31	28	25	22
6	63	51	43	37	58	47	40	35	40	35	30	34	30	26	28	25	22	19
7	58	46	38	32	53	43	35	30	36	31	27	31	26	23	25	22	20	17
8	54	41	34	28	49	39	32	27	33	28	24	28	24	21	23	20	18	15
9	50	38	30	25	46	35	29	24	30	25	21	26	22	19	22	18	16	14
10	47	35	28	23	43	32	26	22	28	23	19	24	20	17	20	17	14	13

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	24254	24254	24254
5°	24347	23995	24136
10°	24202	23753	23871
15°	23903	23445	23422
20°	23479	22983	22957
25°	23058	22413	22413
30°	22514	21893	21705
35°	22007	21268	20954
40°	21372	20643	20244
45°	20747	20021	19527
50°	20065	19376	18686
55°	19356	18624	17931
60°	18564	17725	17073
65°	17712	16829	16061
70°	16636	15753	15002
75°	15140	14504	14148
80°	13436	13036	12357
85°	10967	10448	9355



TEST NUMBER: P331464-830

CATALOG NUMBER: SA2XXDIP-C1005D1080U830-4F0-1E-UDD-F4

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	141.3	1.8
10°-20°	397.5	5.1
20°-30°	584.2	7.5
30°-40°	678.6	8.7
40°-50°	677.9	8.7
50°-60°	591.2	7.6
60°-70°	437.1	5.6
70°-80°	247.6	3.2
80°-90°	71.7	0.9
90°-100°	227.7	2.9
100°-110°	772.5	9.9
110°-120°	820.7	10.5
120°-130°	675.6	8.7
130°-140°	542.5	7.0
140°-150°	410.0	5.3
150°-160°	288.1	3.7
160°-170°	169.6	2.2
170°-180°	55.2	0.7
0°-30°	1123.0	14.4
0°-40°	1801.6	23.1
0°-60°	3070.7	39.4
0°-90°	3827.1	49.1
90°-120°	1820.9	23.4
90°-150°	3449.0	44.3
90°-180°	3962.0	50.9
0°-180°	7789.1	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	1502	1502	1502	1502	1502	
5°	1502	1496	1480	1491	1489	142
15°	1430	1421	1403	1408	1401	402
25°	1294	1282	1258	1261	1258	595
35°	1116	1102	1079	1070	1063	697
45°	909	898	877	862	855	701
55°	688	678	662	645	637	615
65°	464	455	440	428	420	458
75°	243	240	232	225	227	259
85°	59	58	56	52	50	68
90°	1	15	37	36	36	5
95°	38	94	429	162	125	41
105°	134	202	811	1450	1234	142
115°	235	297	679	1401	1624	233
125°	328	389	653	1135	1317	292
135°	385	460	645	954	1092	298
145°	440	506	642	797	872	276
155°	500	540	623	705	732	230
165°	545	562	597	633	643	154
175°	568	569	574	581	579	54
180°	569	569	569	569	569	



TEST NUMBER: P331464-830

CATALOG NUMBER: SA2XXDIP-C1005D1080U830-4F0-1E-UDD-F4

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	1502.2	1502.2	1502.2	1502.2	1502.2	1502.2	1502.2	1502.2	1502.2	1502.2	1502.2
2.5°	1509.2	1507.9	1506.7	1505.3	1504.0	1502.0	1499.2	1496.4	1493.6	1490.7	1493.3
5°	1502.2	1501.0	1499.7	1498.4	1497.1	1494.7	1491.2	1487.6	1484.1	1480.5	1483.2
7.5°	1488.9	1487.0	1485.0	1483.0	1481.0	1478.2	1474.6	1471.0	1467.4	1463.9	1466.4
10°	1476.2	1474.0	1471.8	1469.5	1467.3	1464.2	1460.4	1456.5	1452.6	1448.8	1451.4
12.5°	1459.0	1456.9	1454.9	1452.9	1451.0	1448.0	1444.2	1440.3	1436.5	1432.7	1434.5
15°	1430.0	1428.1	1426.2	1424.3	1422.3	1419.3	1415.1	1410.9	1406.7	1402.6	1403.9
17.5°	1393.1	1391.1	1389.2	1387.2	1385.3	1382.2	1378.0	1373.8	1369.5	1365.4	1366.8
20°	1366.5	1364.5	1362.6	1360.7	1358.8	1355.6	1351.0	1346.6	1342.1	1337.6	1338.5
22.5°	1339.9	1337.2	1334.5	1331.8	1329.1	1325.7	1321.4	1317.2	1313.0	1308.7	1308.9
25°	1294.3	1291.7	1289.1	1286.6	1284.0	1280.0	1274.5	1269.0	1263.6	1258.1	1258.8
27.5°	1242.3	1239.9	1237.7	1235.3	1233.0	1229.7	1225.4	1221.1	1216.8	1212.5	1211.5
30°	1207.6	1205.0	1202.4	1199.9	1197.3	1193.6	1188.8	1184.0	1179.2	1174.3	1173.4
32.5°	1170.6	1168.6	1166.5	1164.4	1162.3	1158.9	1153.8	1148.7	1143.6	1138.5	1136.8
35°	1116.5	1113.3	1110.1	1106.9	1103.7	1099.6	1094.4	1089.3	1084.2	1079.0	1077.1
37.5°	1055.6	1052.8	1050.0	1047.2	1044.3	1040.4	1035.2	1030.1	1024.9	1019.8	1017.4
40°	1014.0	1011.4	1008.9	1006.4	1003.7	999.9	994.8	989.7	984.5	979.4	976.5
42.5°	973.6	971.0	968.5	965.9	963.3	959.4	954.3	949.1	944.1	938.9	935.8
45°	908.6	906.3	904.1	901.8	899.6	896.1	891.3	886.5	881.7	876.8	873.3
47.5°	843.9	841.8	839.6	837.5	835.4	831.8	826.8	821.8	816.8	811.8	808.0
50°	798.8	797.2	795.6	794.0	792.4	789.3	784.9	780.3	775.8	771.4	766.9
52.5°	754.9	752.8	750.6	748.6	746.4	743.2	739.0	734.7	730.6	726.3	722.6
55°	687.6	685.6	683.7	681.8	679.9	676.9	673.2	669.3	665.4	661.6	657.7
57.5°	620.0	618.4	616.9	615.4	613.8	611.0	606.7	602.5	598.2	594.0	590.2
60°	574.9	573.6	572.3	571.1	569.8	566.8	562.4	557.9	553.4	548.9	545.4
62.5°	531.0	529.0	526.9	524.8	522.7	520.0	516.5	513.1	509.6	506.1	502.8
65°	463.6	461.8	459.9	457.9	456.0	453.4	450.2	447.0	443.7	440.5	437.7
67.5°	395.2	393.7	392.1	390.6	389.1	386.8	383.9	381.1	378.1	375.3	373.1
70°	352.4	351.2	349.9	348.6	347.3	345.3	342.3	339.4	336.6	333.7	331.4
72.5°	308.5	307.3	305.9	304.7	303.4	301.8	300.0	298.1	296.2	294.4	292.1
75°	242.7	242.0	241.4	240.7	240.1	238.9	237.3	235.7	234.1	232.5	230.6
77.5°	183.7	182.7	181.5	180.5	179.4	178.5	177.9	177.2	176.5	176.0	174.9
80°	144.5	144.1	143.8	143.5	143.2	142.7	142.0	141.4	140.7	140.2	139.1
82.5°	107.4	107.4	107.4	107.3	107.2	107.0	106.6	106.2	105.8	105.5	104.2
85°	59.2	58.9	58.6	58.2	58.0	57.6	57.3	56.9	56.6	56.4	55.3
87.5°	21.0	21.2	21.5	21.5	21.4	21.5	22.1	23.1	23.9	23.7	22.6
90°	1.1	4.3	8.8	10.9	13.1	16.4	21.9	29.6	36.1	37.2	36.1
92.5°	13.4	19.2	27.1	32.0	39.4	49.7	74.5	109.2	140.3	142.3	120.3
95°	38.4	42.7	53.6	63.5	81.1	107.3	157.7	252.9	379.9	429.2	375.6
97.5°	62.4	68.3	79.9	94.8	115.0	144.8	208.0	340.7	551.9	732.7	768.6
100°	84.3	87.6	97.5	115.0	136.9	167.5	225.6	359.1	595.6	865.0	1022.7
102.5°	104.4	106.9	116.7	134.2	157.0	187.7	241.3	360.1	579.0	869.4	1117.3
105°	133.6	138.0	145.6	162.0	186.2	216.8	268.2	365.7	546.4	811.3	1102.6
107.5°	165.1	168.6	176.1	191.1	215.1	245.9	295.9	380.8	530.2	749.1	1006.4
110°	186.2	190.5	197.1	211.3	234.3	266.1	314.2	393.0	526.7	719.3	946.0



TEST NUMBER: P331464-830

CATALOG NUMBER: SA2XXDIP-C1005D1080U830-4F0-1E-UDD-F4

CANDELA DISTRIBUTION (continued):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	205.4	209.8	217.3	230.5	252.7	285.3	331.8	406.2	527.5	700.1	904.0
115°	235.4	240.9	247.4	260.6	282.5	312.1	359.1	425.9	532.2	678.8	851.9
117.5°	266.6	270.9	277.5	289.1	310.1	340.7	384.3	447.0	540.0	668.5	819.0
120°	285.8	290.1	296.7	306.6	328.5	359.1	401.8	461.0	545.3	662.4	801.4
122.5°	304.2	307.6	314.2	325.0	346.9	378.4	418.5	473.3	551.4	658.9	786.6
125°	328.5	331.8	338.4	351.5	373.3	404.1	443.5	492.8	560.6	652.6	765.3
127.5°	347.7	352.1	361.4	375.8	396.8	428.3	466.7	510.9	570.0	648.8	745.6
130°	359.1	363.5	374.5	389.8	411.7	442.3	480.7	522.3	577.0	647.1	732.5
132.5°	369.7	374.9	386.7	402.9	425.7	456.4	492.9	533.7	584.0	646.2	722.0
135°	385.4	389.8	402.9	419.3	444.5	475.2	510.2	548.6	592.4	644.9	707.3
137.5°	400.3	405.6	418.7	436.2	461.2	489.7	524.2	560.0	599.8	644.7	697.0
140°	411.7	416.0	429.2	446.8	470.8	499.3	532.2	566.1	603.3	643.9	690.9
142.5°	423.1	426.6	438.8	456.4	479.6	506.3	538.3	571.4	606.0	643.9	684.8
145°	440.2	444.5	455.5	471.9	493.8	517.9	547.4	578.2	608.8	641.6	676.7
147.5°	458.5	461.8	472.3	487.5	505.7	527.1	554.9	581.8	609.6	637.7	668.4
150°	470.8	474.1	482.9	497.1	513.5	533.2	558.5	583.6	608.8	635.1	661.3
152.5°	483.1	484.7	493.3	505.9	521.4	539.3	561.9	584.5	607.0	630.7	655.2
155°	500.4	501.4	508.0	520.1	532.2	548.6	567.1	585.8	604.4	623.0	643.9
157.5°	514.8	515.9	521.2	531.7	541.3	555.2	570.9	585.8	599.4	615.1	633.1
160°	524.4	525.6	529.9	538.7	547.4	559.5	572.7	585.8	596.7	609.9	625.2
162.5°	534.1	533.5	537.8	544.8	552.7	562.1	573.5	584.9	594.1	605.5	618.2
165°	545.3	544.2	546.4	552.9	558.5	565.0	574.9	582.5	589.1	596.7	606.6
167.5°	554.5	553.2	555.2	559.3	563.3	567.4	574.6	581.0	584.0	589.1	595.2
170°	560.6	558.5	559.5	562.8	565.0	568.3	573.7	579.2	581.4	584.7	589.1
172.5°	564.1	562.8	562.1	565.4	566.8	569.1	572.9	576.6	577.9	579.5	583.0
175°	568.3	567.1	566.1	568.3	568.3	569.4	571.6	573.7	572.7	573.7	574.9
177.5°	570.2	568.4	567.6	569.4	569.4	569.4	570.2	572.0	570.2	569.4	570.2
180°	569.4	569.4	569.4	569.4	569.4	569.4	569.4	569.4	569.4	569.4	569.4



TEST NUMBER: P331464-830

CATALOG NUMBER: SA2XXDIP-C1005D1080U830-4F0-1E-UDD-F4

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°
0°	1502.2	1502.2	1502.2	1502.2	1502.2	1502.2	1502.2	1502.2
2.5°	1495.8	1498.4	1501.0	1502.0	1501.5	1501.0	1500.4	1500.0
5°	1485.7	1488.3	1490.8	1491.9	1491.2	1490.5	1489.9	1489.2
7.5°	1469.0	1471.5	1474.1	1475.1	1474.3	1473.7	1472.9	1472.3
10°	1454.0	1456.5	1459.1	1459.9	1459.0	1457.9	1457.0	1456.0
12.5°	1436.2	1438.0	1439.8	1440.4	1439.6	1439.0	1438.2	1437.6
15°	1405.1	1406.5	1407.7	1407.6	1406.0	1404.4	1402.8	1401.2
17.5°	1368.3	1369.8	1371.2	1371.2	1369.6	1368.1	1366.6	1365.0
20°	1339.5	1340.5	1341.4	1341.2	1340.0	1338.7	1337.5	1336.1
22.5°	1309.1	1309.3	1309.5	1309.2	1308.4	1307.7	1306.8	1306.1
25°	1259.4	1260.1	1260.7	1260.7	1260.1	1259.4	1258.8	1258.1
27.5°	1210.6	1209.6	1208.6	1207.4	1205.9	1204.3	1202.8	1201.3
30°	1172.4	1171.5	1170.5	1169.4	1168.1	1166.8	1165.5	1164.2
32.5°	1135.1	1133.3	1131.6	1130.1	1128.8	1127.6	1126.2	1124.9
35°	1075.2	1073.3	1071.3	1069.6	1068.0	1066.4	1064.7	1063.1
37.5°	1015.0	1012.7	1010.3	1008.3	1006.8	1005.2	1003.7	1002.2
40°	973.6	970.7	967.8	965.7	964.4	963.2	961.9	960.5
42.5°	932.6	929.4	926.3	923.9	922.1	920.3	918.5	916.6
45°	869.8	866.2	862.7	860.3	858.9	857.7	856.4	855.2
47.5°	804.4	800.6	796.9	794.1	792.2	790.4	788.5	786.6
50°	762.3	757.9	753.4	750.4	748.8	747.2	745.6	743.9
52.5°	718.9	715.1	711.4	708.5	706.3	704.3	702.1	700.0
55°	653.8	650.0	646.2	643.5	641.9	640.3	638.7	637.0
57.5°	586.4	582.6	578.8	576.3	575.1	573.9	572.7	571.5
60°	541.9	538.3	534.8	532.5	531.6	530.7	529.6	528.7
62.5°	499.6	496.3	493.0	490.8	489.6	488.3	487.1	485.9
65°	434.8	431.9	429.0	426.8	425.2	423.6	422.0	420.4
67.5°	370.8	368.5	366.3	364.5	363.3	361.9	360.7	359.4
70°	329.1	327.0	324.7	322.9	321.6	320.4	319.1	317.8
72.5°	289.9	287.7	285.4	283.8	282.8	281.7	280.7	279.7
75°	228.8	226.8	224.9	224.2	224.9	225.5	226.1	226.8
77.5°	174.0	173.1	172.1	171.2	170.2	169.4	168.4	167.6
80°	138.2	137.2	136.3	135.4	134.8	134.2	133.6	132.9
82.5°	103.0	101.8	100.6	99.9	99.7	99.6	99.5	99.3
85°	54.4	53.4	52.5	51.8	51.6	51.2	50.9	50.5
87.5°	21.7	20.5	20.1	19.8	19.5	19.3	19.0	18.8
90°	35.1	32.9	35.1	36.1	36.1	36.1	36.1	36.1
92.5°	95.5	81.9	72.7	65.9	65.0	61.5	62.4	60.7
95°	286.9	220.1	174.1	150.0	135.7	127.1	123.8	124.8
97.5°	669.4	547.7	429.2	350.2	297.8	270.9	254.9	245.7
100°	999.7	863.9	713.9	581.4	490.5	443.5	411.7	392.0
102.5°	1216.1	1185.3	1075.6	935.3	836.5	756.2	716.5	689.8
105°	1330.3	1454.1	1468.3	1432.2	1364.2	1296.4	1249.3	1234.0
107.5°	1248.0	1434.4	1548.2	1601.2	1609.8	1606.0	1596.6	1576.2
110°	1177.0	1373.0	1513.2	1603.0	1650.0	1670.8	1680.7	1679.6



TEST NUMBER: P331464-830

CATALOG NUMBER: SA2XXDIP-C1005D1080U830-4F0-1E-UDD-F4

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°
112.5°	1112.2	1300.3	1450.1	1553.0	1618.5	1653.3	1672.0	1677.8
115°	1032.6	1201.2	1344.5	1457.4	1535.1	1585.5	1613.9	1623.8
117.5°	972.5	1120.6	1250.7	1356.4	1435.7	1488.8	1518.9	1527.2
120°	942.7	1078.5	1194.6	1294.2	1370.8	1422.3	1454.1	1465.0
122.5°	919.1	1043.5	1153.4	1243.4	1312.1	1362.7	1391.0	1400.1
125°	884.7	997.5	1093.8	1175.9	1239.4	1281.1	1308.4	1317.2
127.5°	850.7	952.8	1043.7	1119.5	1174.9	1213.8	1237.5	1244.5
130°	828.9	923.0	1009.6	1081.8	1135.5	1172.7	1194.6	1203.3
132.5°	807.9	895.0	974.5	1042.4	1095.1	1132.4	1152.5	1160.4
135°	778.4	850.7	923.0	984.3	1031.4	1067.5	1087.2	1091.7
137.5°	755.1	815.5	872.9	926.3	969.2	1000.3	1017.7	1024.2
140°	740.2	792.8	843.1	891.3	926.3	954.8	971.2	977.8
142.5°	727.9	772.6	816.0	856.2	889.5	915.4	930.0	931.3
145°	710.6	746.8	780.7	812.5	838.7	857.3	868.3	871.6
147.5°	697.3	725.8	752.2	775.4	797.1	812.0	819.4	821.4
150°	687.6	711.7	734.7	754.4	770.8	784.0	790.5	791.6
152.5°	678.0	700.3	719.8	736.9	749.8	761.2	766.0	766.2
155°	664.6	682.1	698.5	710.6	722.6	730.3	734.7	732.5
157.5°	649.0	663.7	677.5	686.9	695.5	701.8	703.8	703.8
160°	639.4	651.5	663.5	671.2	678.8	684.3	685.4	685.4
162.5°	629.8	640.1	650.4	656.3	663.9	667.7	668.7	667.9
165°	615.4	623.0	630.7	635.1	639.4	643.9	643.9	642.7
167.5°	601.5	607.5	612.7	616.7	618.6	621.0	620.9	619.5
170°	594.6	597.9	602.2	604.4	605.5	608.8	607.7	605.5
172.5°	586.6	589.1	592.6	593.9	595.0	596.5	595.4	594.1
175°	578.2	579.2	580.3	581.4	581.4	582.5	581.4	579.2
177.5°	572.0	572.0	572.9	572.9	572.9	572.9	572.0	570.2
180°	569.4	569.4	569.4	569.4	569.4	569.4	569.4	569.4

(END OF REPORT)