

Scaled data based on original data using  
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State  
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P331446-830

Luminaire Tested: **SA2XXDIP-C1005D725U830-4F0-1E-UDD-F4**

Issue Date: 10/7/2019

**Test Information**

Test Method: LM-79-08  
Report Number: P331446-830  
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-16,  
Test Lab: INNOVATION CENTER  
Issue Date: 10/7/2019  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: NEO-RAY  
Catalog Number: SA2XXDIP-C1005D725U830-4F0-1E-UDD-F4  
Description: DEFINE 2 DIRECT-INDIRECT PENDANT LED LUMINAIRE  
DOWNLIGHT 1005 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER  
UPLIGHT 725 LUMENS PER FOOT, BATWING OPTIC  
Light Source: -  
Ballast/Driver: ELECTRONIC DRIVER

**Summary**


Lumens per Lamp: N/A  
Luminaire Lumens: 6491.5 lumens  
Efficiency: N/A  
Efficacy: 106.9 lumens/watt  
Spacing Criteria (0/90/45): 1.2 / 1.16 / 1.3  
Luminous Opening: Rectangular (W 0.17' x L: 4' x H: 0')  
CIE Type: General Diffuse

Input Watts (W): 60.7  
Input Voltage (V): 120  
Input Current (Ain): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 25 FT



TEST NUMBER: P331446-830  
CATALOG NUMBER: SA2XXDIP-C1005D725U830-4F0-1E-UDD-F4

### Luminous Intensity Polar Plot





TEST NUMBER: P331446-830

CATALOG NUMBER: SA2XXDIP-C1005D725U830-4F0-1E-UDD-F4

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	109	109	109	109	102	102	102	102	88	88	88	76	76	76	64	64	64	59
1	100	95	91	88	93	89	86	83	77	75	73	67	65	63	57	56	54	50
2	91	83	77	72	85	78	72	68	68	64	60	59	56	53	50	48	46	42
3	83	73	66	60	77	69	62	57	60	55	51	52	48	45	44	41	39	35
4	76	65	57	51	71	61	54	48	53	48	43	46	42	38	40	36	34	30
5	70	58	50	44	65	54	47	41	48	42	37	42	37	33	36	32	29	26
6	64	52	44	38	60	49	41	36	43	37	33	38	33	29	32	29	26	23
7	59	47	39	33	55	44	37	32	39	33	29	34	29	26	30	26	23	20
8	55	43	35	29	51	40	33	28	36	30	26	31	27	23	27	23	21	18
9	51	39	31	26	48	37	30	25	33	27	23	29	24	21	25	21	19	17
10	48	36	29	24	45	34	27	23	30	25	21	27	22	19	23	20	17	15

**AVERAGE LUMINANCE (cd/sqm):**

	0°	45°	90°
0°	24254	24254	24254
5°	24347	23995	24136
10°	24202	23753	23871
15°	23903	23445	23422
20°	23479	22983	22957
25°	23058	22413	22413
30°	22514	21893	21705
35°	22007	21268	20954
40°	21372	20643	20244
45°	20747	20021	19527
50°	20065	19376	18686
55°	19356	18624	17931
60°	18564	17725	17073
65°	17712	16829	16061
70°	16636	15753	15002
75°	15140	14504	14148
80°	13436	13036	12357
85°	10967	10448	9355



TEST NUMBER: P331446-830

CATALOG NUMBER: SA2XXDIP-C1005D725U830-4F0-1E-UDD-F4

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	141.3	2.2
10°-20°	397.5	6.1
20°-30°	584.2	9.0
30°-40°	678.6	10.5
40°-50°	677.9	10.4
50°-60°	591.2	9.1
60°-70°	437.1	6.7
70°-80°	247.6	3.8
80°-90°	70.0	1.1
90°-100°	153.2	2.4
100°-110°	519.8	8.0
110°-120°	552.3	8.5
120°-130°	454.6	7.0
130°-140°	365.1	5.6
140°-150°	275.9	4.2
150°-160°	193.9	3.0
160°-170°	114.1	1.8
170°-180°	37.1	0.6
0°-30°	1123.0	17.3
0°-40°	1801.6	27.8
0°-60°	3070.7	47.3
0°-90°	3825.4	58.9
90°-120°	1225.3	18.9
90°-150°	2320.9	35.8
90°-180°	2666.0	41.1
0°-180°	6491.5	100.0

**CANDELA DISTRIBUTION:**

	0°	22.5°	45°	67.5°	90°	Flux
0°	1502	1502	1502	1502	1502	
5°	1502	1496	1480	1491	1489	142
15°	1430	1421	1403	1408	1401	402
25°	1294	1282	1258	1261	1258	595
35°	1116	1102	1079	1070	1063	697
45°	909	898	877	862	855	701
55°	688	678	662	645	637	615
65°	464	455	440	428	420	458
75°	243	240	232	225	227	259
85°	59	58	56	52	50	68
90°	1	10	25	24	24	4
95°	26	63	289	109	84	27
105°	90	136	546	976	830	96
115°	158	200	457	943	1093	157
125°	221	262	439	764	886	196
135°	259	310	434	642	735	200
145°	296	340	432	536	586	186
155°	337	364	419	474	493	155
165°	367	378	402	426	432	103
175°	382	383	386	391	390	36
180°	383	383	383	383	383	



TEST NUMBER: P331446-830

CATALOG NUMBER: SA2XXDIP-C1005D725U830-4F0-1E-UDD-F4

**CANDELA DISTRIBUTION (FULL):**

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	1502.2	1502.2	1502.2	1502.2	1502.2	1502.2	1502.2	1502.2	1502.2	1502.2	1502.2
2.5°	1509.2	1507.9	1506.7	1505.3	1504.0	1502.0	1499.2	1496.4	1493.6	1490.7	1493.3
5°	1502.2	1501.0	1499.7	1498.4	1497.1	1494.7	1491.2	1487.6	1484.1	1480.5	1483.2
7.5°	1488.9	1487.0	1485.0	1483.0	1481.0	1478.2	1474.6	1471.0	1467.4	1463.9	1466.4
10°	1476.2	1474.0	1471.8	1469.5	1467.3	1464.2	1460.4	1456.5	1452.6	1448.8	1451.4
12.5°	1459.0	1456.9	1454.9	1452.9	1451.0	1448.0	1444.2	1440.3	1436.5	1432.7	1434.5
15°	1430.0	1428.1	1426.2	1424.3	1422.3	1419.3	1415.1	1410.9	1406.7	1402.6	1403.9
17.5°	1393.1	1391.1	1389.2	1387.2	1385.3	1382.2	1378.0	1373.8	1369.5	1365.4	1366.8
20°	1366.5	1364.5	1362.6	1360.7	1358.8	1355.6	1351.0	1346.6	1342.1	1337.6	1338.5
22.5°	1339.9	1337.2	1334.5	1331.8	1329.1	1325.7	1321.4	1317.2	1313.0	1308.7	1308.9
25°	1294.3	1291.7	1289.1	1286.6	1284.0	1280.0	1274.5	1269.0	1263.6	1258.1	1258.8
27.5°	1242.3	1239.9	1237.7	1235.3	1233.0	1229.7	1225.4	1221.1	1216.8	1212.5	1211.5
30°	1207.6	1205.0	1202.4	1199.9	1197.3	1193.6	1188.8	1184.0	1179.2	1174.3	1173.4
32.5°	1170.6	1168.6	1166.5	1164.4	1162.3	1158.9	1153.8	1148.7	1143.6	1138.5	1136.8
35°	1116.5	1113.3	1110.1	1106.9	1103.7	1099.6	1094.4	1089.3	1084.2	1079.0	1077.1
37.5°	1055.6	1052.8	1050.0	1047.2	1044.3	1040.4	1035.2	1030.1	1024.9	1019.8	1017.4
40°	1014.0	1011.4	1008.9	1006.4	1003.7	999.9	994.8	989.7	984.5	979.4	976.5
42.5°	973.6	971.0	968.5	965.9	963.3	959.4	954.3	949.1	944.1	938.9	935.8
45°	908.6	906.3	904.1	901.8	899.6	896.1	891.3	886.5	881.7	876.8	873.3
47.5°	843.9	841.8	839.6	837.5	835.4	831.8	826.8	821.8	816.8	811.8	808.0
50°	798.8	797.2	795.6	794.0	792.4	789.3	784.9	780.3	775.8	771.4	766.9
52.5°	754.9	752.8	750.6	748.6	746.4	743.2	739.0	734.7	730.6	726.3	722.6
55°	687.6	685.6	683.7	681.8	679.9	676.9	673.2	669.3	665.4	661.6	657.7
57.5°	620.0	618.4	616.9	615.4	613.8	611.0	606.7	602.5	598.2	594.0	590.2
60°	574.9	573.6	572.3	571.1	569.8	566.8	562.4	557.9	553.4	548.9	545.4
62.5°	531.0	529.0	526.9	524.8	522.7	520.0	516.5	513.1	509.6	506.1	502.8
65°	463.6	461.8	459.9	457.9	456.0	453.4	450.2	447.0	443.7	440.5	437.7
67.5°	395.2	393.7	392.1	390.6	389.1	386.8	383.9	381.1	378.1	375.3	373.1
70°	352.4	351.2	349.9	348.6	347.3	345.3	342.3	339.4	336.6	333.7	331.4
72.5°	308.5	307.3	305.9	304.7	303.4	301.8	300.0	298.1	296.2	294.4	292.1
75°	242.7	242.0	241.4	240.7	240.1	238.9	237.3	235.7	234.1	232.5	230.6
77.5°	183.7	182.7	181.5	180.5	179.4	178.5	177.9	177.2	176.5	176.0	174.9
80°	144.5	144.1	143.8	143.5	143.2	142.7	142.0	141.4	140.7	140.2	139.1
82.5°	107.4	107.4	107.4	107.3	107.2	107.0	106.6	106.2	105.8	105.5	104.2
85°	59.2	58.9	58.6	58.2	58.0	57.6	57.3	56.9	56.6	56.4	55.3
87.5°	20.9	20.8	20.9	20.7	20.5	20.5	20.6	21.2	21.6	21.2	20.3
90°	0.8	2.9	5.9	7.4	8.9	11.0	14.7	19.9	24.3	25.1	24.3
92.5°	9.0	13.0	18.3	21.5	26.5	33.5	50.1	73.5	94.4	95.8	80.9
95°	25.8	28.7	36.1	42.7	54.5	72.2	106.1	170.2	255.7	288.8	252.7
97.5°	42.0	46.0	53.8	63.8	77.4	97.4	140.0	229.3	371.4	493.0	517.3
100°	56.7	58.9	65.6	77.4	92.1	112.7	151.7	241.7	400.8	582.0	688.2
102.5°	70.3	71.9	78.5	90.3	105.7	126.3	162.4	242.2	389.6	585.0	751.8
105°	89.9	92.8	98.0	109.1	125.3	145.9	180.5	246.1	367.7	545.9	742.0
107.5°	111.1	113.5	118.5	128.7	144.7	165.5	199.1	256.3	356.8	504.1	677.2
110°	125.3	128.2	132.6	142.2	157.7	179.1	211.4	264.5	354.4	484.1	636.6



TEST NUMBER: P331446-830

CATALOG NUMBER: SA2XXDIP-C1005D725U830-4F0-1E-UDD-F4

**CANDELA DISTRIBUTION (continued):**

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	138.2	141.2	146.2	155.1	170.0	192.0	223.3	273.3	355.0	471.1	608.3
115°	158.4	162.1	166.5	175.3	190.1	210.0	241.7	286.6	358.1	456.9	573.3
117.5°	179.4	182.3	186.7	194.5	208.7	229.3	258.6	300.8	363.4	449.9	551.1
120°	192.3	195.3	199.6	206.3	221.0	241.7	270.4	310.2	366.9	445.7	539.3
122.5°	204.7	207.1	211.4	218.7	233.4	254.7	281.6	318.5	371.1	443.4	529.3
125°	221.0	223.3	227.6	236.5	251.3	271.8	298.4	331.6	377.2	439.1	515.0
127.5°	234.0	237.0	243.2	252.9	267.0	288.2	314.1	343.7	383.6	436.6	501.7
130°	241.7	244.6	251.9	262.3	277.0	297.7	323.5	351.5	388.3	435.5	492.9
132.5°	248.7	252.3	260.2	271.2	286.4	307.1	331.7	359.1	393.0	434.9	485.9
135°	259.4	262.3	271.2	282.2	299.2	319.8	343.4	369.1	398.6	433.9	476.0
137.5°	269.4	272.9	281.7	293.5	310.4	329.5	352.8	376.8	403.6	433.9	469.0
140°	277.0	279.9	288.8	300.6	316.8	336.0	358.1	380.9	406.0	433.2	465.0
142.5°	284.6	287.1	295.3	307.1	322.7	340.7	362.2	384.5	407.7	433.2	460.8
145°	296.1	299.2	306.5	317.5	332.2	348.5	368.4	389.0	409.6	431.8	455.3
147.5°	308.6	310.8	317.8	328.0	340.3	354.7	373.4	391.5	410.3	429.1	449.8
150°	316.8	319.1	324.9	334.5	345.5	358.8	375.8	392.7	409.6	427.3	445.0
152.5°	325.1	326.1	332.0	340.4	350.8	363.0	378.1	393.3	408.5	424.4	440.9
155°	336.7	337.4	341.9	350.0	358.1	369.1	381.6	394.2	406.7	419.2	433.2
157.5°	346.5	347.1	350.7	357.8	364.3	373.5	384.2	394.2	403.3	414.0	426.0
160°	352.9	353.6	356.6	362.5	368.4	376.5	385.3	394.2	401.5	410.4	420.8
162.5°	359.4	358.9	361.9	366.6	371.9	378.2	386.0	393.6	399.8	407.5	415.9
165°	366.9	366.2	367.7	372.1	375.8	380.2	386.8	392.0	396.4	401.5	408.2
167.5°	373.2	372.2	373.5	376.4	379.0	381.8	386.6	391.0	393.0	396.4	400.5
170°	377.2	375.8	376.5	378.7	380.2	382.4	386.1	389.7	391.2	393.4	396.4
172.5°	379.6	378.7	378.2	380.5	381.4	383.0	385.5	388.0	388.9	389.9	392.3
175°	382.4	381.6	380.9	382.4	382.4	383.1	384.6	386.1	385.3	386.1	386.8
177.5°	383.7	382.6	381.9	383.1	383.1	383.1	383.7	384.9	383.7	383.1	383.7
180°	383.1	383.1	383.1	383.1	383.1	383.1	383.1	383.1	383.1	383.1	383.1



TEST NUMBER: P331446-830

CATALOG NUMBER: SA2XXDIP-C1005D725U830-4F0-1E-UDD-F4

**CANDELA DISTRIBUTION (continued):**

	55°	60°	65°	70°	75°	80°	85°	90°
0°	1502.2	1502.2	1502.2	1502.2	1502.2	1502.2	1502.2	1502.2
2.5°	1495.8	1498.4	1501.0	1502.0	1501.5	1501.0	1500.4	1500.0
5°	1485.7	1488.3	1490.8	1491.9	1491.2	1490.5	1489.9	1489.2
7.5°	1469.0	1471.5	1474.1	1475.1	1474.3	1473.7	1472.9	1472.3
10°	1454.0	1456.5	1459.1	1459.9	1459.0	1457.9	1457.0	1456.0
12.5°	1436.2	1438.0	1439.8	1440.4	1439.6	1439.0	1438.2	1437.6
15°	1405.1	1406.5	1407.7	1407.6	1406.0	1404.4	1402.8	1401.2
17.5°	1368.3	1369.8	1371.2	1371.2	1369.6	1368.1	1366.6	1365.0
20°	1339.5	1340.5	1341.4	1341.2	1340.0	1338.7	1337.5	1336.1
22.5°	1309.1	1309.3	1309.5	1309.2	1308.4	1307.7	1306.8	1306.1
25°	1259.4	1260.1	1260.7	1260.7	1260.1	1259.4	1258.8	1258.1
27.5°	1210.6	1209.6	1208.6	1207.4	1205.9	1204.3	1202.8	1201.3
30°	1172.4	1171.5	1170.5	1169.4	1168.1	1166.8	1165.5	1164.2
32.5°	1135.1	1133.3	1131.6	1130.1	1128.8	1127.6	1126.2	1124.9
35°	1075.2	1073.3	1071.3	1069.6	1068.0	1066.4	1064.7	1063.1
37.5°	1015.0	1012.7	1010.3	1008.3	1006.8	1005.2	1003.7	1002.2
40°	973.6	970.7	967.8	965.7	964.4	963.2	961.9	960.5
42.5°	932.6	929.4	926.3	923.9	922.1	920.3	918.5	916.6
45°	869.8	866.2	862.7	860.3	858.9	857.7	856.4	855.2
47.5°	804.4	800.6	796.9	794.1	792.2	790.4	788.5	786.6
50°	762.3	757.9	753.4	750.4	748.8	747.2	745.6	743.9
52.5°	718.9	715.1	711.4	708.5	706.3	704.3	702.1	700.0
55°	653.8	650.0	646.2	643.5	641.9	640.3	638.7	637.0
57.5°	586.4	582.6	578.8	576.3	575.1	573.9	572.7	571.5
60°	541.9	538.3	534.8	532.5	531.6	530.7	529.6	528.7
62.5°	499.6	496.3	493.0	490.8	489.6	488.3	487.1	485.9
65°	434.8	431.9	429.0	426.8	425.2	423.6	422.0	420.4
67.5°	370.8	368.5	366.3	364.5	363.3	361.9	360.7	359.4
70°	329.1	327.0	324.7	322.9	321.6	320.4	319.1	317.8
72.5°	289.9	287.7	285.4	283.8	282.8	281.7	280.7	279.7
75°	228.8	226.8	224.9	224.2	224.9	225.5	226.1	226.8
77.5°	174.0	173.1	172.1	171.2	170.2	169.4	168.4	167.6
80°	138.2	137.2	136.3	135.4	134.8	134.2	133.6	132.9
82.5°	103.0	101.8	100.6	99.9	99.7	99.6	99.5	99.3
85°	54.4	53.4	52.5	51.8	51.6	51.2	50.9	50.5
87.5°	19.3	18.3	17.8	17.4	17.2	17.0	16.7	16.4
90°	23.6	22.1	23.6	24.3	24.3	24.3	24.3	24.3
92.5°	64.3	55.1	48.9	44.4	43.7	41.4	42.0	40.8
95°	193.0	148.1	117.2	100.9	91.3	85.5	83.2	84.0
97.5°	450.4	368.5	288.8	235.6	200.4	182.3	171.5	165.3
100°	672.7	581.4	480.4	391.2	330.1	298.4	277.0	263.7
102.5°	818.3	797.7	723.8	629.3	562.9	508.8	482.1	464.2
105°	895.2	978.5	988.1	963.7	918.0	872.3	840.7	830.4
107.5°	839.8	965.2	1041.8	1077.5	1083.3	1080.7	1074.4	1060.6
110°	792.0	924.0	1018.2	1078.6	1110.3	1124.4	1131.0	1130.2





TEST NUMBER: P331446-830

CATALOG NUMBER: SA2XXDIP-C1005D725U830-4F0-1E-UDD-F4

**CANDELA DISTRIBUTION (continued):**

	55°	60°	65°	70°	75°	80°	85°	90°
112.5°	748.5	875.0	975.8	1045.1	1089.1	1112.6	1125.1	1129.1
115°	694.7	808.2	904.7	980.6	1032.9	1066.9	1086.0	1092.7
117.5°	654.4	754.0	841.6	912.8	966.1	1001.9	1022.1	1027.7
120°	634.3	725.8	803.8	870.9	922.5	957.1	978.5	985.8
122.5°	618.5	702.2	776.1	836.7	883.0	917.0	936.0	942.2
125°	595.3	671.2	736.0	791.3	834.1	862.0	880.4	886.4
127.5°	572.5	641.1	702.3	753.3	790.6	816.8	832.7	837.4
130°	557.7	621.1	679.3	727.9	764.0	789.1	803.8	809.7
132.5°	543.6	602.3	655.7	701.4	737.0	762.0	775.5	780.8
135°	523.9	572.5	621.1	662.3	694.1	718.4	731.6	734.6
137.5°	508.1	548.7	587.4	623.3	652.2	673.2	684.8	689.2
140°	498.0	533.5	567.3	599.7	623.3	642.4	653.6	658.0
142.5°	489.8	519.9	549.0	576.2	598.6	616.0	625.8	626.7
145°	478.2	502.5	525.4	546.7	564.4	576.9	584.3	586.4
147.5°	469.2	488.3	506.1	521.8	536.4	546.4	551.4	552.7
150°	462.7	478.9	494.4	507.7	518.7	527.5	532.0	532.7
152.5°	456.2	471.3	484.4	495.9	504.5	512.2	515.5	515.6
155°	447.2	459.0	470.0	478.2	486.3	491.4	494.4	492.9
157.5°	436.8	446.7	455.9	462.2	468.0	472.3	473.6	473.6
160°	430.3	438.4	446.5	451.7	456.9	460.5	461.2	461.2
162.5°	423.8	430.7	437.6	441.7	446.8	449.3	450.1	449.4
165°	414.1	419.2	424.4	427.3	430.3	433.2	433.2	432.5
167.5°	404.8	408.8	412.3	415.0	416.3	417.9	417.7	416.9
170°	400.1	402.3	405.2	406.7	407.5	409.6	408.9	407.5
172.5°	394.7	396.4	398.8	399.6	400.4	401.4	400.7	399.8
175°	389.0	389.7	390.5	391.2	391.2	392.0	391.2	389.7
177.5°	384.9	384.9	385.5	385.5	385.5	385.5	384.9	383.7
180°	383.1	383.1	383.1	383.1	383.1	383.1	383.1	383.1

(END OF REPORT)