

Scaled data based on original data using  
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State  
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P333152-840

Luminaire Tested: **S125DIP-S375D1205U840-4F0-1E-UDD-A1**

Issue Date: 3/3/2020

**Test Information**

Test Method: LM-79-08  
Report Number: P333152-840  
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-11,  
Test Lab: INNOVATION CENTER  
Issue Date: 3/3/2020  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: NEO-RAY  
Catalog Number: S125DIP-S375D1205U840-4F0-1E-UDD-A1  
Description: DEFINE 5 DIRECT-INDIRECT PENDANT LED LUMINAIRE  
DOWNLIGHT 375 LUMENS PER FOOT, ASYMMETRIC DIFFUSER  
UPLIGHT 1205 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER  
Light Source: -  
Ballast/Driver: ELECTRONIC DRIVER

**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 5762.5 lumens  
Efficiency: N/A  
Efficacy: 136.6 lumens/watt  
Spacing Criteria (0/90/45): 1.43 / 1.23 / 1.52  
Luminous Opening: Rectangular (W 4' x L: 0.42' x H: 0')  
CIE Type: Semi-Indirect


Input Watts (W): 42.2  
Input Voltage (V): 120  
Input Current (Ain): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 25 FT



TEST NUMBER: P333152-840

CATALOG NUMBER: S125DIP-S375D1205U840-4F0-1E-UDD-A1

### Luminous Intensity Polar Plot





TEST NUMBER: P333152-840

CATALOG NUMBER: S125DIP-S375D1205U840-4F0-1E-UDD-A1

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20				20				20			20			20			20
RC	80				70				50			30			10			0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	102	102	102	102	91	91	91	91	71	71	71	52	52	52	35	35	35	27
1	93	89	85	82	83	79	76	73	62	60	58	46	45	43	31	30	30	23
2	84	77	72	67	75	69	65	60	54	51	48	40	38	36	27	26	25	19
3	77	68	61	56	69	61	55	50	48	44	40	36	33	31	24	23	22	17
4	70	60	53	47	63	54	48	43	43	38	34	32	29	26	22	20	19	14
5	65	53	46	40	57	48	41	37	38	33	30	28	25	23	20	18	16	12
6	59	48	40	35	53	43	36	32	34	29	26	26	22	20	18	16	14	11
7	55	43	35	30	49	39	32	28	31	26	22	23	20	17	16	14	13	10
8	51	39	32	26	45	35	29	24	28	23	20	21	18	16	15	13	11	9
9	47	35	28	23	42	32	26	21	26	21	18	19	16	14	14	12	10	8
10	44	32	25	21	39	29	23	19	23	19	16	18	15	12	13	11	9	7

**AVERAGE LUMINANCE (cd/sqm):**

	0°	90°	180°	270°
0°	3551	3551	3551	3551
5°	4112	3563	3120	3563
10°	4783	3545	2733	3545
15°	5295	3518	2521	3518
20°	5927	3477	2351	3477
25°	6944	3430	2268	3430
30°	7500	3384	2196	3384
35°	6166	3299	2149	3299
40°	4383	3179	2097	3179
45°	3368	3018	2067	3018
50°	2875	2817	2063	2817
55°	2559	2622	2081	2622
60°	2308	2408	2134	2408
65°	2133	2193	2190	2193
70°	1939	1969	2221	1969
75°	1712	1737	2201	1737
80°	1443	1417	2012	1417
85°	1149	1015	1623	1015



TEST NUMBER: P333152-840

CATALOG NUMBER: S125DIP-S375D1205U840-4F0-1E-UDD-A1

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	52.9	0.9
10°-20°	157.6	2.7
20°-30°	255.9	4.4
30°-40°	312.1	5.4
40°-50°	283.9	4.9
50°-60°	226.2	3.9
60°-70°	157.5	2.7
70°-80°	84.0	1.5
80°-90°	24.5	0.4
90°-100°	101.0	1.8
100°-110°	298.2	5.2
110°-120°	505.2	8.8
120°-130°	664.8	11.5
130°-140°	745.0	12.9
140°-150°	730.1	12.7
150°-160°	613.2	10.6
160°-170°	407.6	7.1
170°-180°	142.7	2.5
0°-30°	466.4	8.1
0°-40°	778.5	13.5
0°-60°	1288.6	22.4
0°-90°	1554.6	27.0
90°-120°	904.4	15.7
90°-150°	3044.3	52.8
90°-180°	4208.0	73.0
0°-180°	5762.5	100.0

**CANDELA DISTRIBUTION:**

	0°	90°	180°	270°	360°	Flux
0°	550	550	550	550	550	
5°	634	550	481	550	634	64
15°	792	526	377	526	792	227
25°	974	481	318	481	974	445
35°	782	418	273	418	782	479
45°	369	330	226	330	369	295
55°	227	233	185	233	227	205
65°	140	144	143	144	140	138
75°	69	70	88	70	69	74
85°	16	14	22	14	16	19
90°	28	1	28	1	28	17
95°	101	76	101	76	101	103
105°	291	268	291	268	291	308
115°	510	506	510	506	510	505
125°	743	738	743	738	743	663
135°	963	960	963	960	963	743
145°	1168	1163	1168	1163	1168	729
155°	1331	1331	1331	1331	1331	612
165°	1443	1447	1443	1447	1443	407
175°	1498	1504	1498	1504	1498	142
180°	1508	1508	1508	1508	1508	



TEST NUMBER: P333152-840

CATALOG NUMBER: S125DIP-S375D1205U840-4F0-1E-UDD-A1

**CANDELA DISTRIBUTION (FULL):**

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	549.8	549.8	549.8	549.8	549.8	549.8	549.8	549.8	549.8	549.8	549.8
2.5°	581.5	580.8	580.0	578.6	579.7	576.4	575.0	572.4	569.2	568.0	566.7
5°	634.2	635.4	636.6	631.7	632.2	628.8	621.4	615.3	610.5	604.1	599.7
7.5°	697.7	695.0	694.7	691.6	686.1	681.7	673.9	663.9	654.2	643.2	634.1
10°	729.4	729.7	727.6	723.9	718.0	713.8	703.6	693.8	681.9	667.8	657.8
12.5°	753.4	754.4	751.6	746.6	743.8	734.4	726.3	714.7	700.5	689.3	674.1
15°	791.9	789.4	787.6	781.2	776.4	766.6	753.8	741.5	726.2	712.0	697.7
17.5°	829.2	831.3	827.8	822.0	806.8	795.4	778.2	761.5	742.4	723.3	706.3
20°	862.4	864.3	859.0	848.9	830.7	819.3	796.7	775.2	753.1	728.5	709.8
22.5°	903.9	902.4	895.1	879.9	864.1	843.0	818.5	792.3	764.6	736.9	712.1
25°	974.4	964.6	960.2	941.3	920.6	889.5	856.0	817.7	783.2	746.5	714.8
27.5°	1013.6	1010.5	1005.5	992.4	970.6	937.4	897.8	851.1	802.4	756.2	714.6
30°	1005.7	1006.2	1006.6	1002.5	988.5	963.5	924.0	873.9	816.0	764.0	715.9
32.5°	936.2	944.7	952.9	962.5	966.4	961.6	937.0	891.6	832.0	773.0	715.2
35°	782.1	784.8	811.1	837.3	872.7	900.3	918.7	898.6	848.5	780.5	714.3
37.5°	609.9	622.5	640.8	670.2	721.4	767.3	826.3	853.3	837.2	783.0	712.7
40°	519.9	531.6	543.5	573.6	616.7	672.3	739.2	796.4	809.7	775.2	707.0
42.5°	450.5	459.7	472.9	495.5	531.6	580.8	644.8	719.5	765.5	752.5	695.3
45°	368.7	374.6	384.8	402.7	428.9	467.4	523.8	605.5	676.7	700.2	667.4
47.5°	315.6	315.6	323.6	335.9	354.8	387.5	429.3	493.2	569.3	625.5	622.9
50°	286.1	284.9	291.2	301.9	316.9	338.6	378.5	429.6	502.6	566.3	584.1
52.5°	260.6	260.8	264.7	272.7	285.2	303.7	333.5	379.6	441.9	507.4	540.8
55°	227.3	226.3	230.8	236.1	245.3	257.4	278.8	314.1	364.8	429.1	472.5
57.5°	196.6	199.2	201.0	204.7	212.3	220.5	238.5	264.4	304.6	359.8	405.7
60°	178.7	181.3	182.7	186.4	192.5	199.5	213.5	234.5	268.3	316.0	361.4
62.5°	162.7	164.7	165.2	168.5	173.5	180.3	191.3	208.9	235.7	277.3	321.8
65°	139.6	139.6	140.5	144.0	146.3	152.4	160.8	173.6	195.1	227.5	265.6
67.5°	117.2	118.4	118.2	119.7	121.8	126.5	132.5	143.1	159.1	182.7	213.2
70°	102.7	103.6	103.4	104.5	106.8	109.9	114.8	124.8	136.2	156.5	182.7
72.5°	89.6	90.0	89.4	90.9	92.3	94.9	100.5	105.8	116.4	133.6	155.1
75°	68.6	69.1	69.6	70.5	71.9	73.3	76.0	81.4	88.5	101.3	115.0
77.5°	51.4	50.5	51.7	51.5	52.3	53.4	55.8	58.7	64.4	72.6	83.2
80°	38.8	39.0	39.0	39.2	40.4	41.1	43.1	45.2	49.7	55.7	63.2
82.5°	28.3	28.9	28.5	29.0	29.9	30.4	31.6	33.3	35.9	40.7	46.0
85°	15.5	14.2	14.7	15.1	15.1	15.5	16.4	17.1	18.5	20.3	22.4
87.5°	10.1	10.3	10.4	10.2	10.2	10.0	10.5	10.3	10.5	10.8	11.2
90°	28.2	27.4	26.6	25.9	25.0	24.0	22.7	21.4	20.1	18.8	17.0
92.5°	55.3	54.8	54.2	53.6	53.1	51.9	50.2	48.5	46.8	45.0	42.8
95°	100.9	100.4	99.9	99.4	98.9	97.7	95.8	94.0	92.2	90.4	87.8
97.5°	153.0	152.7	152.4	152.1	151.8	150.8	149.1	147.3	145.6	143.9	140.3
100°	192.5	192.0	191.4	190.9	190.4	188.9	186.6	184.2	181.9	179.6	176.1
102.5°	231.9	231.2	230.5	229.7	228.9	227.3	224.8	222.2	219.6	217.1	215.4
105°	291.0	290.2	289.4	288.7	287.9	286.7	285.2	283.6	282.1	280.4	278.9
107.5°	351.5	351.6	351.7	351.7	351.8	351.4	350.6	349.8	349.1	348.3	347.1
110°	396.7	396.9	397.2	397.4	397.7	397.4	396.7	395.9	395.1	394.3	393.5



TEST NUMBER: P333152-840

CATALOG NUMBER: S125DIP-S375D1205U840-4F0-1E-UDD-A1

**CANDELA DISTRIBUTION (continued):**

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	440.8	441.2	441.7	442.2	442.6	442.7	442.3	442.0	441.6	441.2	440.2
115°	510.5	510.7	511.0	511.3	511.5	511.8	512.0	512.3	512.6	512.8	512.3
117.5°	578.6	579.6	580.7	581.7	582.7	583.1	582.9	582.7	582.5	582.3	581.8
120°	625.5	626.5	627.5	628.6	629.7	630.2	630.2	630.2	630.2	630.2	630.0
122.5°	672.5	673.3	674.1	674.9	675.8	676.3	676.5	676.7	676.9	677.1	676.4
125°	742.9	743.1	743.4	743.7	743.9	744.3	744.8	745.3	745.8	746.4	746.1
127.5°	810.4	810.9	811.4	812.0	812.5	812.9	813.1	813.4	813.6	814.0	813.6
130°	855.5	856.0	856.6	857.1	857.6	858.0	858.2	858.5	858.8	859.0	858.5
132.5°	897.8	898.5	899.2	899.9	900.7	901.1	901.4	901.7	901.9	902.2	902.3
135°	963.4	964.5	965.5	966.5	967.7	968.2	968.2	968.2	968.2	968.2	967.9
137.5°	1027.7	1029.1	1030.4	1031.7	1033.0	1033.5	1033.2	1032.9	1032.5	1032.2	1031.7
140°	1069.0	1070.4	1071.7	1073.0	1074.3	1074.7	1074.2	1073.6	1073.1	1072.6	1071.8
142.5°	1108.5	1109.8	1111.2	1112.4	1113.7	1114.2	1113.9	1113.6	1113.3	1113.0	1112.0
145°	1167.6	1168.4	1169.2	1170.0	1170.7	1171.1	1171.1	1171.1	1171.1	1171.1	1170.3
147.5°	1218.1	1219.9	1221.6	1223.5	1225.2	1225.8	1225.2	1224.6	1223.9	1223.2	1222.6
150°	1255.7	1256.2	1256.7	1257.2	1257.8	1258.0	1258.0	1258.0	1258.0	1258.0	1257.0
152.5°	1286.7	1287.6	1288.5	1289.5	1290.4	1290.5	1289.9	1289.3	1288.7	1288.1	1287.7
155°	1330.8	1332.1	1333.3	1334.6	1336.0	1336.2	1335.0	1334.0	1333.0	1331.9	1331.7
157.5°	1367.7	1369.4	1371.1	1372.8	1374.5	1374.8	1373.8	1372.7	1371.7	1370.7	1370.4
160°	1393.0	1394.2	1395.5	1396.8	1398.2	1398.3	1397.2	1396.2	1395.1	1394.1	1393.9
162.5°	1414.5	1416.0	1417.5	1419.1	1420.6	1420.8	1419.5	1418.3	1416.9	1415.7	1415.6
165°	1443.4	1445.0	1446.5	1448.1	1449.7	1450.0	1448.9	1447.8	1446.8	1445.7	1445.5
167.5°	1466.4	1468.0	1469.7	1471.3	1472.9	1472.9	1471.4	1469.8	1468.2	1466.6	1466.6
170°	1478.6	1480.5	1482.3	1484.1	1485.9	1486.0	1484.5	1482.9	1481.4	1479.8	1479.8
172.5°	1488.9	1490.6	1492.2	1493.8	1495.4	1495.4	1493.9	1492.3	1490.8	1489.1	1489.1
175°	1498.5	1500.4	1502.3	1504.1	1505.9	1506.0	1504.4	1502.9	1501.3	1499.8	1499.8
177.5°	1504.2	1505.7	1507.1	1508.6	1510.1	1510.2	1508.9	1507.6	1506.4	1505.1	1505.3
180°	1507.9	1507.9	1507.9	1507.9	1507.9	1507.9	1507.9	1507.9	1507.9	1507.9	1507.9



TEST NUMBER: P333152-840

CATALOG NUMBER: S125DIP-S375D1205U840-4F0-1E-UDD-A1

**CANDELA DISTRIBUTION (continued):**

	55°	60°	65°	70°	75°	80°	85°	90°	95°	100°	105°
0°	549.8	549.8	549.8	549.8	549.8	549.8	549.8	549.8	549.8	549.8	549.8
2.5°	565.6	564.3	562.8	560.2	557.0	555.3	552.8	551.1	547.8	544.9	541.9
5°	594.3	588.2	582.7	575.4	567.5	562.4	556.3	549.6	542.5	535.3	527.4
7.5°	624.1	613.3	601.7	589.2	576.8	565.5	554.7	544.2	534.3	522.3	512.2
10°	644.0	630.5	616.0	599.1	582.4	567.9	553.3	540.5	527.4	513.4	501.0
12.5°	664.0	646.0	625.5	606.8	586.9	569.5	552.2	535.7	519.4	503.8	489.4
15°	678.1	662.3	643.4	616.7	594.3	570.3	547.4	526.2	506.3	489.1	470.9
17.5°	687.4	666.9	646.6	621.2	591.8	564.9	539.0	514.6	492.3	470.4	452.9
20°	689.0	668.0	646.8	621.9	591.8	561.0	535.0	505.9	481.9	459.2	437.8
22.5°	688.5	664.7	641.6	615.9	586.5	558.2	526.8	497.2	471.0	448.8	426.4
25°	683.3	657.8	628.8	603.0	574.0	543.9	512.2	481.4	454.8	429.4	407.2
27.5°	678.8	645.9	613.1	582.9	554.9	527.4	497.0	465.4	436.0	410.2	389.3
30°	673.5	637.2	600.4	568.9	540.2	513.4	484.6	453.8	423.0	397.9	375.5
32.5°	668.6	626.4	587.5	553.2	522.8	496.8	470.3	441.0	410.7	385.2	362.7
35°	659.2	610.5	565.8	527.1	494.7	467.9	445.7	418.4	390.6	365.9	344.5
37.5°	647.3	589.5	541.6	501.0	465.4	437.2	416.6	395.6	368.9	345.1	325.7
40°	637.9	574.5	523.8	482.3	445.5	416.1	396.9	377.1	355.0	332.8	312.3
42.5°	626.2	561.1	505.9	461.2	424.7	396.1	376.0	359.2	339.6	318.9	299.9
45°	604.6	536.7	477.0	428.9	392.0	363.8	343.1	330.4	315.7	296.1	280.0
47.5°	572.8	507.5	445.7	396.1	358.0	331.8	312.4	300.2	289.9	275.4	260.7
50°	544.6	485.6	423.0	373.9	335.8	309.4	291.4	280.4	271.7	260.4	248.0
52.5°	513.1	458.2	400.8	352.1	314.5	288.5	270.9	261.3	253.9	245.9	233.7
55°	462.9	416.3	363.0	316.9	282.2	256.7	241.3	232.9	226.8	220.8	213.3
57.5°	407.8	371.2	324.2	281.9	249.8	226.7	212.4	204.2	199.4	196.3	192.0
60°	368.9	337.7	297.1	258.5	227.3	206.7	192.8	186.4	182.5	180.0	176.6
62.5°	332.9	307.2	269.6	234.5	207.1	187.7	175.2	169.1	165.3	164.0	161.4
65°	279.8	259.9	228.9	199.8	176.4	159.9	149.4	143.5	141.2	139.8	140.0
67.5°	227.4	215.4	190.5	165.6	146.9	133.1	124.6	120.2	119.0	117.1	117.1
70°	195.5	186.4	165.4	143.7	127.1	116.4	109.0	104.3	103.1	102.2	102.0
72.5°	167.3	159.4	141.2	123.8	108.9	99.5	93.3	90.5	88.6	88.1	88.0
75°	125.7	121.4	106.8	93.1	82.8	76.3	72.1	69.6	68.2	67.9	68.2
77.5°	89.4	85.5	76.3	66.6	60.1	55.1	51.6	50.7	49.2	49.2	49.0
80°	67.2	64.6	58.8	51.1	45.7	41.5	39.7	38.1	37.6	36.9	37.6
82.5°	48.7	45.9	42.0	37.1	32.6	30.2	28.3	27.8	27.5	27.2	27.3
85°	24.0	24.2	21.9	18.2	16.4	14.9	13.7	13.7	13.5	13.3	13.5
87.5°	11.2	10.5	9.4	8.5	7.1	6.1	5.6	5.3	5.2	5.4	6.0
90°	15.1	13.3	11.5	9.5	7.5	5.4	3.2	1.2	3.2	5.4	7.5
92.5°	40.6	38.4	36.1	34.2	32.8	31.3	29.9	28.4	29.9	31.3	32.8
95°	85.1	82.5	79.9	78.4	77.9	77.4	76.7	76.2	76.7	77.4	77.9
97.5°	136.6	133.1	129.5	127.5	127.3	127.1	126.9	126.7	126.9	127.1	127.3
100°	172.8	169.4	166.0	164.3	164.3	164.3	164.3	164.3	164.3	164.3	164.3
102.5°	213.7	212.0	210.3	208.8	207.8	206.7	205.7	204.7	205.7	206.7	207.8
105°	277.3	275.8	274.2	272.8	271.5	270.1	268.8	267.5	268.8	270.1	271.5
107.5°	345.9	344.7	343.5	342.2	340.9	339.6	338.3	337.0	338.3	339.6	340.9
110°	392.7	391.9	391.1	390.1	388.8	387.5	386.2	385.0	386.2	387.5	388.8





TEST NUMBER: P333152-840

CATALOG NUMBER: S125DIP-S375D1205U840-4F0-1E-UDD-A1

**CANDELA DISTRIBUTION (continued):**

	55°	60°	65°	70°	75°	80°	85°	90°	95°	100°	105°
112.5°	439.3	438.3	437.3	436.5	435.8	435.0	434.4	433.7	434.4	435.0	435.8
115°	511.8	511.3	510.7	510.0	508.9	507.9	506.9	505.7	506.9	507.9	508.9
117.5°	581.4	580.9	580.4	580.0	579.5	579.1	578.6	578.0	578.6	579.1	579.5
120°	629.7	629.3	629.1	628.3	627.0	625.7	624.4	623.1	624.4	625.7	627.0
122.5°	675.8	675.1	674.4	673.8	673.4	672.9	672.5	672.0	672.5	672.9	673.4
125°	745.8	745.6	745.3	744.4	742.9	741.2	739.7	738.1	739.7	741.2	742.9
127.5°	813.3	813.0	812.7	812.1	811.2	810.3	809.4	808.6	809.4	810.3	811.2
130°	858.0	857.5	857.0	856.0	854.7	853.4	852.1	850.8	852.1	853.4	854.7
132.5°	902.4	902.5	902.6	901.6	899.5	897.4	895.1	893.0	895.1	897.4	899.5
135°	967.7	967.3	967.1	966.2	964.6	963.1	961.5	960.0	961.5	963.1	964.6
137.5°	1031.1	1030.5	1030.0	1028.9	1027.3	1025.8	1024.3	1022.8	1024.3	1025.8	1027.3
140°	1071.1	1070.3	1069.4	1068.4	1067.1	1065.8	1064.5	1063.2	1064.5	1065.8	1067.1
142.5°	1111.0	1109.9	1109.0	1107.9	1106.8	1105.8	1104.7	1103.6	1104.7	1105.8	1106.8
145°	1169.6	1168.8	1168.0	1167.1	1166.1	1165.1	1164.0	1163.0	1164.0	1165.1	1166.1
147.5°	1222.0	1221.4	1220.7	1220.1	1219.6	1219.0	1218.4	1217.9	1218.4	1219.0	1219.6
150°	1255.9	1254.9	1253.8	1253.4	1253.7	1253.9	1254.3	1254.5	1254.3	1253.9	1253.7
152.5°	1287.2	1286.8	1286.4	1286.0	1285.7	1285.3	1284.9	1284.5	1284.9	1285.3	1285.7
155°	1331.4	1331.2	1330.9	1330.8	1330.8	1330.8	1330.8	1330.8	1330.8	1330.8	1330.8
157.5°	1370.2	1369.9	1369.6	1369.8	1370.4	1370.9	1371.5	1372.1	1371.5	1370.9	1370.4
160°	1393.6	1393.3	1393.1	1393.3	1394.1	1394.9	1395.7	1396.4	1395.7	1394.9	1394.1
162.5°	1415.6	1415.5	1415.5	1415.7	1416.3	1416.9	1417.5	1418.1	1417.5	1416.9	1416.3
165°	1445.2	1445.0	1444.7	1444.8	1445.4	1445.9	1446.4	1446.9	1446.4	1445.9	1445.4
167.5°	1466.6	1466.6	1466.6	1467.1	1468.2	1469.3	1470.3	1471.4	1470.3	1469.3	1468.2
170°	1479.8	1479.8	1479.8	1480.4	1481.4	1482.4	1483.5	1484.5	1483.5	1482.4	1481.4
172.5°	1489.1	1489.1	1489.1	1489.8	1490.8	1491.8	1492.9	1493.9	1492.9	1491.8	1490.8
175°	1499.8	1499.8	1499.8	1500.3	1501.3	1502.4	1503.4	1504.4	1503.4	1502.4	1501.3
177.5°	1505.6	1505.8	1506.0	1506.5	1507.3	1508.1	1509.0	1509.8	1509.0	1508.1	1507.3
180°	1507.9	1507.9	1507.9	1507.9	1507.9	1507.9	1507.9	1507.9	1507.9	1507.9	1507.9



TEST NUMBER: P333152-840

CATALOG NUMBER: S125DIP-S375D1205U840-4F0-1E-UDD-A1

**CANDELA DISTRIBUTION (continued):**

	110°	115°	120°	125°	130°	135°	140°	145°	150°	155°	160°
0°	549.8	549.8	549.8	549.8	549.8	549.8	549.8	549.8	549.8	549.8	549.8
2.5°	540.3	538.2	536.5	532.8	530.7	528.0	525.7	528.2	525.5	526.6	524.9
5°	523.4	516.8	512.2	505.4	499.6	494.2	490.3	489.6	487.7	486.8	483.9
7.5°	503.1	494.9	487.0	478.1	470.6	463.0	458.2	454.1	451.5	448.0	445.6
10°	491.2	480.2	470.9	460.2	450.8	442.6	436.2	432.8	429.8	425.4	423.7
12.5°	476.5	465.1	453.7	442.2	433.2	424.1	418.6	413.6	411.5	406.6	406.1
15°	458.8	441.7	430.5	418.9	406.5	399.0	394.4	389.0	386.7	383.1	380.6
17.5°	437.7	422.4	408.5	396.4	385.8	379.5	373.7	370.0	366.0	363.7	359.5
20°	422.3	407.9	393.8	381.0	372.8	365.7	361.0	357.5	353.3	352.1	347.9
22.5°	409.5	393.5	380.1	369.3	360.4	352.2	347.2	344.8	341.9	338.3	337.5
25°	388.5	371.9	360.5	349.8	341.8	334.4	330.9	327.9	325.1	322.4	321.5
27.5°	370.4	355.6	342.0	332.3	325.4	318.6	315.6	311.8	309.8	307.7	305.2
30°	357.7	342.5	330.6	321.3	313.9	307.8	304.5	301.9	300.1	298.2	296.8
32.5°	344.7	330.6	319.1	309.9	302.5	297.9	295.0	293.2	291.1	288.9	287.1
35°	327.4	311.9	300.7	292.9	287.0	283.5	280.2	278.6	276.3	276.3	274.4
37.5°	307.9	294.6	284.7	277.5	272.3	269.1	265.6	264.5	263.0	262.0	261.4
40°	296.4	284.0	274.7	267.4	261.9	259.2	256.4	254.6	253.7	252.5	252.1
42.5°	284.4	272.6	263.7	257.0	252.1	249.9	247.3	246.0	244.1	242.6	242.3
45°	266.2	254.8	246.6	241.3	237.1	234.5	232.9	230.0	229.1	227.3	227.0
47.5°	249.0	238.0	230.0	225.6	222.0	219.8	217.3	214.5	213.4	212.5	212.4
50°	236.1	226.1	218.6	214.5	211.0	207.9	205.3	203.5	202.8	202.8	203.3
52.5°	223.1	214.5	208.2	203.1	199.8	196.5	194.1	193.0	192.0	193.1	193.9
55°	204.0	195.3	190.7	185.7	182.5	178.7	177.5	177.1	176.4	178.2	179.3
57.5°	183.7	177.6	172.2	167.3	164.4	162.2	160.7	160.4	161.7	162.6	165.6
60°	170.8	163.8	159.0	155.2	151.7	150.3	149.8	149.4	150.3	152.8	156.8
62.5°	156.6	151.0	145.6	142.9	140.3	137.9	137.8	138.1	140.0	143.0	146.9
65°	135.8	130.9	127.4	124.1	122.0	120.7	121.1	122.0	124.1	128.2	132.5
67.5°	114.6	111.3	108.2	105.5	103.5	103.5	104.0	105.4	107.9	112.4	116.4
70°	101.1	97.4	94.7	93.6	91.9	91.0	92.4	94.7	96.8	101.1	104.5
72.5°	87.5	84.2	82.2	81.4	80.7	80.0	80.5	83.0	85.8	90.0	94.1
75°	67.2	66.0	64.6	63.7	63.0	63.5	63.9	66.2	68.6	73.0	77.7
77.5°	49.1	47.9	47.0	46.8	46.4	46.7	48.0	49.7	51.9	55.1	58.7
80°	37.1	36.7	36.2	36.0	36.0	36.2	38.1	39.2	41.3	44.3	47.2
82.5°	27.1	26.8	26.7	26.6	26.8	26.9	28.0	29.5	31.2	33.5	36.0
85°	14.2	13.7	14.4	14.7	14.2	14.9	15.5	16.4	17.1	18.2	19.4
87.5°	6.6	7.4	7.5	8.1	8.4	9.2	9.3	10.3	10.9	11.5	11.5
90°	9.5	11.5	13.3	15.1	17.0	18.8	20.1	21.4	22.7	24.0	25.0
92.5°	34.2	36.1	38.4	40.6	42.8	45.0	46.8	48.5	50.2	51.9	53.1
95°	78.4	79.9	82.5	85.1	87.8	90.4	92.2	94.0	95.8	97.7	98.9
97.5°	127.5	129.5	133.1	136.6	140.3	143.9	145.6	147.3	149.1	150.8	151.8
100°	164.3	166.0	169.4	172.8	176.1	179.6	181.9	184.2	186.6	188.9	190.4
102.5°	208.8	210.3	212.0	213.7	215.4	217.1	219.6	222.2	224.8	227.3	228.9
105°	272.8	274.2	275.8	277.3	278.9	280.4	282.1	283.6	285.2	286.7	287.9
107.5°	342.2	343.5	344.7	345.9	347.1	348.3	349.1	349.8	350.6	351.4	351.8
110°	390.1	391.1	391.9	392.7	393.5	394.3	395.1	395.9	396.7	397.4	397.7



TEST NUMBER: P333152-840

CATALOG NUMBER: S125DIP-S375D1205U840-4F0-1E-UDD-A1

**CANDELA DISTRIBUTION (continued):**

	110°	115°	120°	125°	130°	135°	140°	145°	150°	155°	160°
112.5°	436.5	437.3	438.3	439.3	440.2	441.2	441.6	442.0	442.3	442.7	442.6
115°	510.0	510.7	511.3	511.8	512.3	512.8	512.6	512.3	512.0	511.8	511.5
117.5°	580.0	580.4	580.9	581.4	581.8	582.3	582.5	582.7	582.9	583.1	582.7
120°	628.3	629.1	629.3	629.7	630.0	630.2	630.2	630.2	630.2	630.2	629.7
122.5°	673.8	674.4	675.1	675.8	676.4	677.1	676.9	676.7	676.5	676.3	675.8
125°	744.4	745.3	745.6	745.8	746.1	746.4	745.8	745.3	744.8	744.3	743.9
127.5°	812.1	812.7	813.0	813.3	813.6	814.0	813.6	813.4	813.1	812.9	812.5
130°	856.0	857.0	857.5	858.0	858.5	859.0	858.8	858.5	858.2	858.0	857.6
132.5°	901.6	902.6	902.5	902.4	902.3	902.2	901.9	901.7	901.4	901.1	900.7
135°	966.2	967.1	967.3	967.7	967.9	968.2	968.2	968.2	968.2	968.2	967.7
137.5°	1028.9	1030.0	1030.5	1031.1	1031.7	1032.2	1032.5	1032.9	1033.2	1033.5	1033.0
140°	1068.4	1069.4	1070.3	1071.1	1071.8	1072.6	1073.1	1073.6	1074.2	1074.7	1074.3
142.5°	1107.9	1109.0	1109.9	1111.0	1112.0	1113.0	1113.3	1113.6	1113.9	1114.2	1113.7
145°	1167.1	1168.0	1168.8	1169.6	1170.3	1171.1	1171.1	1171.1	1171.1	1171.1	1170.7
147.5°	1220.1	1220.7	1221.4	1222.0	1222.6	1223.2	1223.9	1224.6	1225.2	1225.8	1225.2
150°	1253.4	1253.8	1254.9	1255.9	1257.0	1258.0	1258.0	1258.0	1258.0	1258.0	1257.8
152.5°	1286.0	1286.4	1286.8	1287.2	1287.7	1288.1	1288.7	1289.3	1289.9	1290.5	1290.4
155°	1330.8	1330.9	1331.2	1331.4	1331.7	1331.9	1333.0	1334.0	1335.0	1336.2	1336.0
157.5°	1369.8	1369.6	1369.9	1370.2	1370.4	1370.7	1371.7	1372.7	1373.8	1374.8	1374.5
160°	1393.3	1393.1	1393.3	1393.6	1393.9	1394.1	1395.1	1396.2	1397.2	1398.3	1398.2
162.5°	1415.7	1415.5	1415.5	1415.6	1415.6	1415.7	1416.9	1418.3	1419.5	1420.8	1420.6
165°	1444.8	1444.7	1445.0	1445.2	1445.5	1445.7	1446.8	1447.8	1448.9	1450.0	1449.7
167.5°	1467.1	1466.6	1466.6	1466.6	1466.6	1466.6	1468.2	1469.8	1471.4	1472.9	1472.9
170°	1480.4	1479.8	1479.8	1479.8	1479.8	1479.8	1481.4	1482.9	1484.5	1486.0	1485.9
172.5°	1489.8	1489.1	1489.1	1489.1	1489.1	1489.1	1490.8	1492.3	1493.9	1495.4	1495.4
175°	1500.3	1499.8	1499.8	1499.8	1499.8	1499.8	1501.3	1502.9	1504.4	1506.0	1505.9
177.5°	1506.5	1506.0	1505.8	1505.6	1505.3	1505.1	1506.4	1507.6	1508.9	1510.2	1510.1
180°	1507.9	1507.9	1507.9	1507.9	1507.9	1507.9	1507.9	1507.9	1507.9	1507.9	1507.9



TEST NUMBER: P333152-840

CATALOG NUMBER: S125DIP-S375D1205U840-4F0-1E-UDD-A1

**CANDELA DISTRIBUTION (continued):**

	165°	170°	175°	180°	185°	190°	195°	200°	205°	210°	215°
0°	549.8	549.8	549.8	549.8	549.8	549.8	549.8	549.8	549.8	549.8	549.8
2.5°	523.8	525.1	524.0	525.5	524.0	525.1	523.8	524.9	526.6	525.5	528.2
5°	482.8	480.7	482.1	481.2	482.1	480.7	482.8	483.9	486.8	487.7	489.6
7.5°	444.9	442.9	440.6	439.5	440.6	442.9	444.9	445.6	448.0	451.5	454.1
10°	421.2	418.6	418.4	416.8	418.4	418.6	421.2	423.7	425.4	429.8	432.8
12.5°	403.8	401.4	398.8	398.1	398.8	401.4	403.8	406.1	406.6	411.5	413.6
15°	379.2	377.3	375.7	377.1	375.7	377.3	379.2	380.6	383.1	386.7	389.0
17.5°	358.7	357.2	356.9	355.2	356.9	357.2	358.7	359.5	363.7	366.0	370.0
20°	345.8	344.7	345.2	342.0	345.2	344.7	345.8	347.9	352.1	353.3	357.5
22.5°	335.6	333.3	333.0	332.3	333.0	333.3	335.6	337.5	338.3	341.9	344.8
25°	319.4	318.3	317.1	318.3	317.1	318.3	319.4	321.5	322.4	325.1	327.9
27.5°	305.4	304.0	303.7	303.9	303.7	304.0	305.4	305.2	307.7	309.8	311.8
30°	296.8	294.5	294.7	294.5	294.7	294.5	296.8	296.8	298.2	300.1	301.9
32.5°	287.5	285.9	285.6	285.2	285.6	285.9	287.5	287.1	288.9	291.1	293.2
35°	273.7	273.7	272.6	272.6	272.6	273.7	273.7	274.4	276.3	276.3	278.6
37.5°	260.7	260.5	259.8	259.9	259.8	260.5	260.7	261.4	262.0	263.0	264.5
40°	251.1	250.9	250.1	248.7	250.1	250.9	251.1	252.1	252.5	253.7	254.6
42.5°	241.8	241.0	240.7	240.1	240.7	241.0	241.8	242.3	242.6	244.1	246.0
45°	227.0	227.0	226.6	226.3	226.6	227.0	227.0	227.0	227.3	229.1	230.0
47.5°	212.8	213.2	214.1	213.9	214.1	213.2	212.8	212.4	212.5	213.4	214.5
50°	204.2	204.4	205.1	205.3	205.1	204.4	204.2	203.3	202.8	202.8	203.5
52.5°	194.7	196.0	196.9	196.7	196.9	196.0	194.7	193.9	193.1	192.0	193.0
55°	181.3	183.0	184.6	184.8	184.6	183.0	181.3	179.3	178.2	176.4	177.1
57.5°	168.1	170.4	172.1	172.7	172.1	170.4	168.1	165.6	162.6	161.7	160.4
60°	159.2	162.2	164.3	165.2	164.3	162.2	159.2	156.8	152.8	150.3	149.4
62.5°	150.6	154.0	156.0	156.2	156.0	154.0	150.6	146.9	143.0	140.0	138.1
65°	136.5	140.0	141.9	143.3	141.9	140.0	136.5	132.5	128.2	124.1	122.0
67.5°	121.4	124.9	126.9	128.1	126.9	124.9	121.4	116.4	112.4	107.9	105.4
70°	110.4	113.9	116.6	117.6	116.6	113.9	110.4	104.5	101.1	96.8	94.7
72.5°	99.6	102.7	104.9	106.0	104.9	102.7	99.6	94.1	90.0	85.8	83.0
75°	80.7	84.9	87.1	88.2	87.1	84.9	80.7	77.7	73.0	68.6	66.2
77.5°	62.2	66.0	67.4	68.0	67.4	66.0	62.2	58.7	55.1	51.9	49.7
80°	49.9	52.3	53.9	54.1	53.9	52.3	49.9	47.2	44.3	41.3	39.2
82.5°	38.4	40.3	40.8	41.4	40.8	40.3	38.4	36.0	33.5	31.2	29.5
85°	21.0	21.9	22.2	21.9	22.2	21.9	21.0	19.4	18.2	17.1	16.4
87.5°	12.1	12.0	12.2	12.7	12.2	12.0	12.1	11.5	11.5	10.9	10.3
90°	25.9	26.6	27.4	28.2	27.4	26.6	25.9	25.0	24.0	22.7	21.4
92.5°	53.6	54.2	54.8	55.3	54.8	54.2	53.6	53.1	51.9	50.2	48.5
95°	99.4	99.9	100.4	100.9	100.4	99.9	99.4	98.9	97.7	95.8	94.0
97.5°	152.1	152.4	152.7	153.0	152.7	152.4	152.1	151.8	150.8	149.1	147.3
100°	190.9	191.4	192.0	192.5	192.0	191.4	190.9	190.4	188.9	186.6	184.2
102.5°	229.7	230.5	231.2	231.9	231.2	230.5	229.7	228.9	227.3	224.8	222.2
105°	288.7	289.4	290.2	291.0	290.2	289.4	288.7	287.9	286.7	285.2	283.6
107.5°	351.7	351.7	351.6	351.5	351.6	351.7	351.7	351.8	351.4	350.6	349.8
110°	397.4	397.2	396.9	396.7	396.9	397.2	397.4	397.7	397.4	396.7	395.9



TEST NUMBER: P333152-840

CATALOG NUMBER: S125DIP-S375D1205U840-4F0-1E-UDD-A1

**CANDELA DISTRIBUTION (continued):**

	165°	170°	175°	180°	185°	190°	195°	200°	205°	210°	215°
112.5°	442.2	441.7	441.2	440.8	441.2	441.7	442.2	442.6	442.7	442.3	442.0
115°	511.3	511.0	510.7	510.5	510.7	511.0	511.3	511.5	511.8	512.0	512.3
117.5°	581.7	580.7	579.6	578.6	579.6	580.7	581.7	582.7	583.1	582.9	582.7
120°	628.6	627.5	626.5	625.5	626.5	627.5	628.6	629.7	630.2	630.2	630.2
122.5°	674.9	674.1	673.3	672.5	673.3	674.1	674.9	675.8	676.3	676.5	676.7
125°	743.7	743.4	743.1	742.9	743.1	743.4	743.7	743.9	744.3	744.8	745.3
127.5°	812.0	811.4	810.9	810.4	810.9	811.4	812.0	812.5	812.9	813.1	813.4
130°	857.1	856.6	856.0	855.5	856.0	856.6	857.1	857.6	858.0	858.2	858.5
132.5°	899.9	899.2	898.5	897.8	898.5	899.2	899.9	900.7	901.1	901.4	901.7
135°	966.5	965.5	964.5	963.4	964.5	965.5	966.5	967.7	968.2	968.2	968.2
137.5°	1031.7	1030.4	1029.1	1027.7	1029.1	1030.4	1031.7	1033.0	1033.5	1033.2	1032.9
140°	1073.0	1071.7	1070.4	1069.0	1070.4	1071.7	1073.0	1074.3	1074.7	1074.2	1073.6
142.5°	1112.4	1111.2	1109.8	1108.5	1109.8	1111.2	1112.4	1113.7	1114.2	1113.9	1113.6
145°	1170.0	1169.2	1168.4	1167.6	1168.4	1169.2	1170.0	1170.7	1171.1	1171.1	1171.1
147.5°	1223.5	1221.6	1219.9	1218.1	1219.9	1221.6	1223.5	1225.2	1225.8	1225.2	1224.6
150°	1257.2	1256.7	1256.2	1255.7	1256.2	1256.7	1257.2	1257.8	1258.0	1258.0	1258.0
152.5°	1289.5	1288.5	1287.6	1286.7	1287.6	1288.5	1289.5	1290.4	1290.5	1289.9	1289.3
155°	1334.6	1333.3	1332.1	1330.8	1332.1	1333.3	1334.6	1336.0	1336.2	1335.0	1334.0
157.5°	1372.8	1371.1	1369.4	1367.7	1369.4	1371.1	1372.8	1374.5	1374.8	1373.8	1372.7
160°	1396.8	1395.5	1394.2	1393.0	1394.2	1395.5	1396.8	1398.2	1398.3	1397.2	1396.2
162.5°	1419.1	1417.5	1416.0	1414.5	1416.0	1417.5	1419.1	1420.6	1420.8	1419.5	1418.3
165°	1448.1	1446.5	1445.0	1443.4	1445.0	1446.5	1448.1	1449.7	1450.0	1448.9	1447.8
167.5°	1471.3	1469.7	1468.0	1466.4	1468.0	1469.7	1471.3	1472.9	1472.9	1471.4	1469.8
170°	1484.1	1482.3	1480.5	1478.6	1480.5	1482.3	1484.1	1485.9	1486.0	1484.5	1482.9
172.5°	1493.8	1492.2	1490.6	1488.9	1490.6	1492.2	1493.8	1495.4	1495.4	1493.9	1492.3
175°	1504.1	1502.3	1500.4	1498.5	1500.4	1502.3	1504.1	1505.9	1506.0	1504.4	1502.9
177.5°	1508.6	1507.1	1505.7	1504.2	1505.7	1507.1	1508.6	1510.1	1510.2	1508.9	1507.6
180°	1507.9	1507.9	1507.9	1507.9	1507.9	1507.9	1507.9	1507.9	1507.9	1507.9	1507.9



TEST NUMBER: P333152-840

CATALOG NUMBER: S125DIP-S375D1205U840-4F0-1E-UDD-A1

**CANDELA DISTRIBUTION (continued):**

	220°	225°	230°	235°	240°	245°	250°	255°	260°	265°	270°
0°	549.8	549.8	549.8	549.8	549.8	549.8	549.8	549.8	549.8	549.8	549.8
2.5°	525.7	528.0	530.7	532.8	536.5	538.2	540.3	541.9	544.9	547.8	551.1
5°	490.3	494.2	499.6	505.4	512.2	516.8	523.4	527.4	535.3	542.5	549.6
7.5°	458.2	463.0	470.6	478.1	487.0	494.9	503.1	512.2	522.3	534.3	544.2
10°	436.2	442.6	450.8	460.2	470.9	480.2	491.2	501.0	513.4	527.4	540.5
12.5°	418.6	424.1	433.2	442.2	453.7	465.1	476.5	489.4	503.8	519.4	535.7
15°	394.4	399.0	406.5	418.9	430.5	441.7	458.8	470.9	489.1	506.3	526.2
17.5°	373.7	379.5	385.8	396.4	408.5	422.4	437.7	452.9	470.4	492.3	514.6
20°	361.0	365.7	372.8	381.0	393.8	407.9	422.3	437.8	459.2	481.9	505.9
22.5°	347.2	352.2	360.4	369.3	380.1	393.5	409.5	426.4	448.8	471.0	497.2
25°	330.9	334.4	341.8	349.8	360.5	371.9	388.5	407.2	429.4	454.8	481.4
27.5°	315.6	318.6	325.4	332.3	342.0	355.6	370.4	389.3	410.2	436.0	465.4
30°	304.5	307.8	313.9	321.3	330.6	342.5	357.7	375.5	397.9	423.0	453.8
32.5°	295.0	297.9	302.5	309.9	319.1	330.6	344.7	362.7	385.2	410.7	441.0
35°	280.2	283.5	287.0	292.9	300.7	311.9	327.4	344.5	365.9	390.6	418.4
37.5°	265.6	269.1	272.3	277.5	284.7	294.6	307.9	325.7	345.1	368.9	395.6
40°	256.4	259.2	261.9	267.4	274.7	284.0	296.4	312.3	332.8	355.0	377.1
42.5°	247.3	249.9	252.1	257.0	263.7	272.6	284.4	299.9	318.9	339.6	359.2
45°	232.9	234.5	237.1	241.3	246.6	254.8	266.2	280.0	296.1	315.7	330.4
47.5°	217.3	219.8	222.0	225.6	230.0	238.0	249.0	260.7	275.4	289.9	300.2
50°	205.3	207.9	211.0	214.5	218.6	226.1	236.1	248.0	260.4	271.7	280.4
52.5°	194.1	196.5	199.8	203.1	208.2	214.5	223.1	233.7	245.9	253.9	261.3
55°	177.5	178.7	182.5	185.7	190.7	195.3	204.0	213.3	220.8	226.8	232.9
57.5°	160.7	162.2	164.4	167.3	172.2	177.6	183.7	192.0	196.3	199.4	204.2
60°	149.8	150.3	151.7	155.2	159.0	163.8	170.8	176.6	180.0	182.5	186.4
62.5°	137.8	137.9	140.3	142.9	145.6	151.0	156.6	161.4	164.0	165.3	169.1
65°	121.1	120.7	122.0	124.1	127.4	130.9	135.8	140.0	139.8	141.2	143.5
67.5°	104.0	103.5	103.5	105.5	108.2	111.3	114.6	117.1	117.1	119.0	120.2
70°	92.4	91.0	91.9	93.6	94.7	97.4	101.1	102.0	102.2	103.1	104.3
72.5°	80.5	80.0	80.7	81.4	82.2	84.2	87.5	88.0	88.1	88.6	90.5
75°	63.9	63.5	63.0	63.7	64.6	66.0	67.2	68.2	67.9	68.2	69.6
77.5°	48.0	46.7	46.4	46.8	47.0	47.9	49.1	49.0	49.2	49.2	50.7
80°	38.1	36.2	36.0	36.0	36.2	36.7	37.1	37.6	36.9	37.6	38.1
82.5°	28.0	26.9	26.8	26.6	26.7	26.8	27.1	27.3	27.2	27.5	27.8
85°	15.5	14.9	14.2	14.7	14.4	13.7	14.2	13.5	13.3	13.5	13.7
87.5°	9.3	9.2	8.4	8.1	7.5	7.4	6.6	6.0	5.4	5.2	5.3
90°	20.1	18.8	17.0	15.1	13.3	11.5	9.5	7.5	5.4	3.2	1.2
92.5°	46.8	45.0	42.8	40.6	38.4	36.1	34.2	32.8	31.3	29.9	28.4
95°	92.2	90.4	87.8	85.1	82.5	79.9	78.4	77.9	77.4	76.7	76.2
97.5°	145.6	143.9	140.3	136.6	133.1	129.5	127.5	127.3	127.1	126.9	126.7
100°	181.9	179.6	176.1	172.8	169.4	166.0	164.3	164.3	164.3	164.3	164.3
102.5°	219.6	217.1	215.4	213.7	212.0	210.3	208.8	207.8	206.7	205.7	204.7
105°	282.1	280.4	278.9	277.3	275.8	274.2	272.8	271.5	270.1	268.8	267.5
107.5°	349.1	348.3	347.1	345.9	344.7	343.5	342.2	340.9	339.6	338.3	337.0
110°	395.1	394.3	393.5	392.7	391.9	391.1	390.1	388.8	387.5	386.2	385.0



TEST NUMBER: P333152-840

CATALOG NUMBER: S125DIP-S375D1205U840-4F0-1E-UDD-A1

**CANDELA DISTRIBUTION (continued):**

	220°	225°	230°	235°	240°	245°	250°	255°	260°	265°	270°
112.5°	441.6	441.2	440.2	439.3	438.3	437.3	436.5	435.8	435.0	434.4	433.7
115°	512.6	512.8	512.3	511.8	511.3	510.7	510.0	508.9	507.9	506.9	505.7
117.5°	582.5	582.3	581.8	581.4	580.9	580.4	580.0	579.5	579.1	578.6	578.0
120°	630.2	630.2	630.0	629.7	629.3	629.1	628.3	627.0	625.7	624.4	623.1
122.5°	676.9	677.1	676.4	675.8	675.1	674.4	673.8	673.4	672.9	672.5	672.0
125°	745.8	746.4	746.1	745.8	745.6	745.3	744.4	742.9	741.2	739.7	738.1
127.5°	813.6	814.0	813.6	813.3	813.0	812.7	812.1	811.2	810.3	809.4	808.6
130°	858.8	859.0	858.5	858.0	857.5	857.0	856.0	854.7	853.4	852.1	850.8
132.5°	901.9	902.2	902.3	902.4	902.5	902.6	901.6	899.5	897.4	895.1	893.0
135°	968.2	968.2	967.9	967.7	967.3	967.1	966.2	964.6	963.1	961.5	960.0
137.5°	1032.5	1032.2	1031.7	1031.1	1030.5	1030.0	1028.9	1027.3	1025.8	1024.3	1022.8
140°	1073.1	1072.6	1071.8	1071.1	1070.3	1069.4	1068.4	1067.1	1065.8	1064.5	1063.2
142.5°	1113.3	1113.0	1112.0	1111.0	1109.9	1109.0	1107.9	1106.8	1105.8	1104.7	1103.6
145°	1171.1	1171.1	1170.3	1169.6	1168.8	1168.0	1167.1	1166.1	1165.1	1164.0	1163.0
147.5°	1223.9	1223.2	1222.6	1222.0	1221.4	1220.7	1220.1	1219.6	1219.0	1218.4	1217.9
150°	1258.0	1258.0	1257.0	1255.9	1254.9	1253.8	1253.4	1253.7	1253.9	1254.3	1254.5
152.5°	1288.7	1288.1	1287.7	1287.2	1286.8	1286.4	1286.0	1285.7	1285.3	1284.9	1284.5
155°	1333.0	1331.9	1331.7	1331.4	1331.2	1330.9	1330.8	1330.8	1330.8	1330.8	1330.8
157.5°	1371.7	1370.7	1370.4	1370.2	1369.9	1369.6	1369.8	1370.4	1370.9	1371.5	1372.1
160°	1395.1	1394.1	1393.9	1393.6	1393.3	1393.1	1393.3	1394.1	1394.9	1395.7	1396.4
162.5°	1416.9	1415.7	1415.6	1415.6	1415.5	1415.5	1415.7	1416.3	1416.9	1417.5	1418.1
165°	1446.8	1445.7	1445.5	1445.2	1445.0	1444.7	1444.8	1445.4	1445.9	1446.4	1446.9
167.5°	1468.2	1466.6	1466.6	1466.6	1466.6	1466.6	1467.1	1468.2	1469.3	1470.3	1471.4
170°	1481.4	1479.8	1479.8	1479.8	1479.8	1479.8	1480.4	1481.4	1482.4	1483.5	1484.5
172.5°	1490.8	1489.1	1489.1	1489.1	1489.1	1489.1	1489.8	1490.8	1491.8	1492.9	1493.9
175°	1501.3	1499.8	1499.8	1499.8	1499.8	1499.8	1500.3	1501.3	1502.4	1503.4	1504.4
177.5°	1506.4	1505.1	1505.3	1505.6	1505.8	1506.0	1506.5	1507.3	1508.1	1509.0	1509.8
180°	1507.9	1507.9	1507.9	1507.9	1507.9	1507.9	1507.9	1507.9	1507.9	1507.9	1507.9



TEST NUMBER: P333152-840

CATALOG NUMBER: S125DIP-S375D1205U840-4F0-1E-UDD-A1

**CANDELA DISTRIBUTION (continued):**

	275°	280°	285°	290°	295°	300°	305°	310°	315°	320°	325°
0°	549.8	549.8	549.8	549.8	549.8	549.8	549.8	549.8	549.8	549.8	549.8
2.5°	552.8	555.3	557.0	560.2	562.8	564.3	565.6	566.7	568.0	569.2	572.4
5°	556.3	562.4	567.5	575.4	582.7	588.2	594.3	599.7	604.1	610.5	615.3
7.5°	554.7	565.5	576.8	589.2	601.7	613.3	624.1	634.1	643.2	654.2	663.9
10°	553.3	567.9	582.4	599.1	616.0	630.5	644.0	657.8	667.8	681.9	693.8
12.5°	552.2	569.5	586.9	606.8	625.5	646.0	664.0	674.1	689.3	700.5	714.7
15°	547.4	570.3	594.3	616.7	643.4	662.3	678.1	697.7	712.0	726.2	741.5
17.5°	539.0	564.9	591.8	621.2	646.6	666.9	687.4	706.3	723.3	742.4	761.5
20°	535.0	561.0	591.8	621.9	646.8	668.0	689.0	709.8	728.5	753.1	775.2
22.5°	526.8	558.2	586.5	615.9	641.6	664.7	688.5	712.1	736.9	764.6	792.3
25°	512.2	543.9	574.0	603.0	628.8	657.8	683.3	714.8	746.5	783.2	817.7
27.5°	497.0	527.4	554.9	582.9	613.1	645.9	678.8	714.6	756.2	802.4	851.1
30°	484.6	513.4	540.2	568.9	600.4	637.2	673.5	715.9	764.0	816.0	873.9
32.5°	470.3	496.8	522.8	553.2	587.5	626.4	668.6	715.2	773.0	832.0	891.6
35°	445.7	467.9	494.7	527.1	565.8	610.5	659.2	714.3	780.5	848.5	898.6
37.5°	416.6	437.2	465.4	501.0	541.6	589.5	647.3	712.7	783.0	837.2	853.3
40°	396.9	416.1	445.5	482.3	523.8	574.5	637.9	707.0	775.2	809.7	796.4
42.5°	376.0	396.1	424.7	461.2	505.9	561.1	626.2	695.3	752.5	765.5	719.5
45°	343.1	363.8	392.0	428.9	477.0	536.7	604.6	667.4	700.2	676.7	605.5
47.5°	312.4	331.8	358.0	396.1	445.7	507.5	572.8	622.9	625.5	569.3	493.2
50°	291.4	309.4	335.8	373.9	423.0	485.6	544.6	584.1	566.3	502.6	429.6
52.5°	270.9	288.5	314.5	352.1	400.8	458.2	513.1	540.8	507.4	441.9	379.6
55°	241.3	256.7	282.2	316.9	363.0	416.3	462.9	472.5	429.1	364.8	314.1
57.5°	212.4	226.7	249.8	281.9	324.2	371.2	407.8	405.7	359.8	304.6	264.4
60°	192.8	206.7	227.3	258.5	297.1	337.7	368.9	361.4	316.0	268.3	234.5
62.5°	175.2	187.7	207.1	234.5	269.6	307.2	332.9	321.8	277.3	235.7	208.9
65°	149.4	159.9	176.4	199.8	228.9	259.9	279.8	265.6	227.5	195.1	173.6
67.5°	124.6	133.1	146.9	165.6	190.5	215.4	227.4	213.2	182.7	159.1	143.1
70°	109.0	116.4	127.1	143.7	165.4	186.4	195.5	182.7	156.5	136.2	124.8
72.5°	93.3	99.5	108.9	123.8	141.2	159.4	167.3	155.1	133.6	116.4	105.8
75°	72.1	76.3	82.8	93.1	106.8	121.4	125.7	115.0	101.3	88.5	81.4
77.5°	51.6	55.1	60.1	66.6	76.3	85.5	89.4	83.2	72.6	64.4	58.7
80°	39.7	41.5	45.7	51.1	58.8	64.6	67.2	63.2	55.7	49.7	45.2
82.5°	28.3	30.2	32.6	37.1	42.0	45.9	48.7	46.0	40.7	35.9	33.3
85°	13.7	14.9	16.4	18.2	21.9	24.2	24.0	22.4	20.3	18.5	17.1
87.5°	5.6	6.1	7.1	8.5	9.4	10.5	11.2	11.2	10.8	10.5	10.3
90°	3.2	5.4	7.5	9.5	11.5	13.3	15.1	17.0	18.8	20.1	21.4
92.5°	29.9	31.3	32.8	34.2	36.1	38.4	40.6	42.8	45.0	46.8	48.5
95°	76.7	77.4	77.9	78.4	79.9	82.5	85.1	87.8	90.4	92.2	94.0
97.5°	126.9	127.1	127.3	127.5	129.5	133.1	136.6	140.3	143.9	145.6	147.3
100°	164.3	164.3	164.3	164.3	166.0	169.4	172.8	176.1	179.6	181.9	184.2
102.5°	205.7	206.7	207.8	208.8	210.3	212.0	213.7	215.4	217.1	219.6	222.2
105°	268.8	270.1	271.5	272.8	274.2	275.8	277.3	278.9	280.4	282.1	283.6
107.5°	338.3	339.6	340.9	342.2	343.5	344.7	345.9	347.1	348.3	349.1	349.8
110°	386.2	387.5	388.8	390.1	391.1	391.9	392.7	393.5	394.3	395.1	395.9





TEST NUMBER: P333152-840

CATALOG NUMBER: S125DIP-S375D1205U840-4F0-1E-UDD-A1

**CANDELA DISTRIBUTION (continued):**

	275°	280°	285°	290°	295°	300°	305°	310°	315°	320°	325°
112.5°	434.4	435.0	435.8	436.5	437.3	438.3	439.3	440.2	441.2	441.6	442.0
115°	506.9	507.9	508.9	510.0	510.7	511.3	511.8	512.3	512.8	512.6	512.3
117.5°	578.6	579.1	579.5	580.0	580.4	580.9	581.4	581.8	582.3	582.5	582.7
120°	624.4	625.7	627.0	628.3	629.1	629.3	629.7	630.0	630.2	630.2	630.2
122.5°	672.5	672.9	673.4	673.8	674.4	675.1	675.8	676.4	677.1	676.9	676.7
125°	739.7	741.2	742.9	744.4	745.3	745.6	745.8	746.1	746.4	745.8	745.3
127.5°	809.4	810.3	811.2	812.1	812.7	813.0	813.3	813.6	814.0	813.6	813.4
130°	852.1	853.4	854.7	856.0	857.0	857.5	858.0	858.5	859.0	858.8	858.5
132.5°	895.1	897.4	899.5	901.6	902.6	902.5	902.4	902.3	902.2	901.9	901.7
135°	961.5	963.1	964.6	966.2	967.1	967.3	967.7	967.9	968.2	968.2	968.2
137.5°	1024.3	1025.8	1027.3	1028.9	1030.0	1030.5	1031.1	1031.7	1032.2	1032.5	1032.9
140°	1064.5	1065.8	1067.1	1068.4	1069.4	1070.3	1071.1	1071.8	1072.6	1073.1	1073.6
142.5°	1104.7	1105.8	1106.8	1107.9	1109.0	1109.9	1111.0	1112.0	1113.0	1113.3	1113.6
145°	1164.0	1165.1	1166.1	1167.1	1168.0	1168.8	1169.6	1170.3	1171.1	1171.1	1171.1
147.5°	1218.4	1219.0	1219.6	1220.1	1220.7	1221.4	1222.0	1222.6	1223.2	1223.9	1224.6
150°	1254.3	1253.9	1253.7	1253.4	1253.8	1254.9	1255.9	1257.0	1258.0	1258.0	1258.0
152.5°	1284.9	1285.3	1285.7	1286.0	1286.4	1286.8	1287.2	1287.7	1288.1	1288.7	1289.3
155°	1330.8	1330.8	1330.8	1330.8	1330.9	1331.2	1331.4	1331.7	1331.9	1333.0	1334.0
157.5°	1371.5	1370.9	1370.4	1369.8	1369.6	1369.9	1370.2	1370.4	1370.7	1371.7	1372.7
160°	1395.7	1394.9	1394.1	1393.3	1393.1	1393.3	1393.6	1393.9	1394.1	1395.1	1396.2
162.5°	1417.5	1416.9	1416.3	1415.7	1415.5	1415.5	1415.6	1415.6	1415.7	1416.9	1418.3
165°	1446.4	1445.9	1445.4	1444.8	1444.7	1445.0	1445.2	1445.5	1445.7	1446.8	1447.8
167.5°	1470.3	1469.3	1468.2	1467.1	1466.6	1466.6	1466.6	1466.6	1466.6	1468.2	1469.8
170°	1483.5	1482.4	1481.4	1480.4	1479.8	1479.8	1479.8	1479.8	1479.8	1481.4	1482.9
172.5°	1492.9	1491.8	1490.8	1489.8	1489.1	1489.1	1489.1	1489.1	1489.1	1490.8	1492.3
175°	1503.4	1502.4	1501.3	1500.3	1499.8	1499.8	1499.8	1499.8	1499.8	1501.3	1502.9
177.5°	1509.0	1508.1	1507.3	1506.5	1506.0	1505.8	1505.6	1505.3	1505.1	1506.4	1507.6
180°	1507.9	1507.9	1507.9	1507.9	1507.9	1507.9	1507.9	1507.9	1507.9	1507.9	1507.9



TEST NUMBER: P333152-840

CATALOG NUMBER: S125DIP-S375D1205U840-4F0-1E-UDD-A1

**CANDELA DISTRIBUTION (continued):**

	330°	335°	340°	345°	350°	355°	360°
0°	549.8	549.8	549.8	549.8	549.8	549.8	549.8
2.5°	575.0	576.4	579.7	578.6	580.0	580.8	581.5
5°	621.4	628.8	632.2	631.7	636.6	635.4	634.2
7.5°	673.9	681.7	686.1	691.6	694.7	695.0	697.7
10°	703.6	713.8	718.0	723.9	727.6	729.7	729.4
12.5°	726.3	734.4	743.8	746.6	751.6	754.4	753.4
15°	753.8	766.6	776.4	781.2	787.6	789.4	791.9
17.5°	778.2	795.4	806.8	822.0	827.8	831.3	829.2
20°	796.7	819.3	830.7	848.9	859.0	864.3	862.4
22.5°	818.5	843.0	864.1	879.9	895.1	902.4	903.9
25°	856.0	889.5	920.6	941.3	960.2	964.6	974.4
27.5°	897.8	937.4	970.6	992.4	1005.5	1010.5	1013.6
30°	924.0	963.5	988.5	1002.5	1006.6	1006.2	1005.7
32.5°	937.0	961.6	966.4	962.5	952.9	944.7	936.2
35°	918.7	900.3	872.7	837.3	811.1	784.8	782.1
37.5°	826.3	767.3	721.4	670.2	640.8	622.5	609.9
40°	739.2	672.3	616.7	573.6	543.5	531.6	519.9
42.5°	644.8	580.8	531.6	495.5	472.9	459.7	450.5
45°	523.8	467.4	428.9	402.7	384.8	374.6	368.7
47.5°	429.3	387.5	354.8	335.9	323.6	315.6	315.6
50°	378.5	338.6	316.9	301.9	291.2	284.9	286.1
52.5°	333.5	303.7	285.2	272.7	264.7	260.8	260.6
55°	278.8	257.4	245.3	236.1	230.8	226.3	227.3
57.5°	238.5	220.5	212.3	204.7	201.0	199.2	196.6
60°	213.5	199.5	192.5	186.4	182.7	181.3	178.7
62.5°	191.3	180.3	173.5	168.5	165.2	164.7	162.7
65°	160.8	152.4	146.3	144.0	140.5	139.6	139.6
67.5°	132.5	126.5	121.8	119.7	118.2	118.4	117.2
70°	114.8	109.9	106.8	104.5	103.4	103.6	102.7
72.5°	100.5	94.9	92.3	90.9	89.4	90.0	89.6
75°	76.0	73.3	71.9	70.5	69.6	69.1	68.6
77.5°	55.8	53.4	52.3	51.5	51.7	50.5	51.4
80°	43.1	41.1	40.4	39.2	39.0	39.0	38.8
82.5°	31.6	30.4	29.9	29.0	28.5	28.9	28.3
85°	16.4	15.5	15.1	15.1	14.7	14.2	15.5
87.5°	10.5	10.0	10.2	10.2	10.4	10.3	10.1
90°	22.7	24.0	25.0	25.9	26.6	27.4	28.2
92.5°	50.2	51.9	53.1	53.6	54.2	54.8	55.3
95°	95.8	97.7	98.9	99.4	99.9	100.4	100.9
97.5°	149.1	150.8	151.8	152.1	152.4	152.7	153.0
100°	186.6	188.9	190.4	190.9	191.4	192.0	192.5
102.5°	224.8	227.3	228.9	229.7	230.5	231.2	231.9
105°	285.2	286.7	287.9	288.7	289.4	290.2	291.0
107.5°	350.6	351.4	351.8	351.7	351.7	351.6	351.5
110°	396.7	397.4	397.7	397.4	397.2	396.9	396.7



TEST NUMBER: P333152-840

CATALOG NUMBER: S125DIP-S375D1205U840-4F0-1E-UDD-A1

**CANDELA DISTRIBUTION (continued):**

	330°	335°	340°	345°	350°	355°	360°
112.5°	442.3	442.7	442.6	442.2	441.7	441.2	440.8
115°	512.0	511.8	511.5	511.3	511.0	510.7	510.5
117.5°	582.9	583.1	582.7	581.7	580.7	579.6	578.6
120°	630.2	630.2	629.7	628.6	627.5	626.5	625.5
122.5°	676.5	676.3	675.8	674.9	674.1	673.3	672.5
125°	744.8	744.3	743.9	743.7	743.4	743.1	742.9
127.5°	813.1	812.9	812.5	812.0	811.4	810.9	810.4
130°	858.2	858.0	857.6	857.1	856.6	856.0	855.5
132.5°	901.4	901.1	900.7	899.9	899.2	898.5	897.8
135°	968.2	968.2	967.7	966.5	965.5	964.5	963.4
137.5°	1033.2	1033.5	1033.0	1031.7	1030.4	1029.1	1027.7
140°	1074.2	1074.7	1074.3	1073.0	1071.7	1070.4	1069.0
142.5°	1113.9	1114.2	1113.7	1112.4	1111.2	1109.8	1108.5
145°	1171.1	1171.1	1170.7	1170.0	1169.2	1168.4	1167.6
147.5°	1225.2	1225.8	1225.2	1223.5	1221.6	1219.9	1218.1
150°	1258.0	1258.0	1257.8	1257.2	1256.7	1256.2	1255.7
152.5°	1289.9	1290.5	1290.4	1289.5	1288.5	1287.6	1286.7
155°	1335.0	1336.2	1336.0	1334.6	1333.3	1332.1	1330.8
157.5°	1373.8	1374.8	1374.5	1372.8	1371.1	1369.4	1367.7
160°	1397.2	1398.3	1398.2	1396.8	1395.5	1394.2	1393.0
162.5°	1419.5	1420.8	1420.6	1419.1	1417.5	1416.0	1414.5
165°	1448.9	1450.0	1449.7	1448.1	1446.5	1445.0	1443.4
167.5°	1471.4	1472.9	1472.9	1471.3	1469.7	1468.0	1466.4
170°	1484.5	1486.0	1485.9	1484.1	1482.3	1480.5	1478.6
172.5°	1493.9	1495.4	1495.4	1493.8	1492.2	1490.6	1488.9
175°	1504.4	1506.0	1505.9	1504.1	1502.3	1500.4	1498.5
177.5°	1508.9	1510.2	1510.1	1508.6	1507.1	1505.7	1504.2
180°	1507.9	1507.9	1507.9	1507.9	1507.9	1507.9	1507.9

(END OF REPORT)