

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P331454-830

Luminaire Tested: **SA2XXDIP-C1005D925U830-4F0-1E-UDD-F1**

Issue Date: 10/7/2019

Test Information

Test Method: LM-79-08
Report Number: P331454-830
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-8,
Test Lab: INNOVATION CENTER
Issue Date: 10/7/2019
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: NEO-RAY
Catalog Number: SA2XXDIP-C1005D925U830-4F0-1E-UDD-F1
Description: DEFINE 2 DIRECT-INDIRECT PENDANT LED LUMINAIRE
DOWNLIGHT 1005 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER
UPLIGHT 925 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER
Light Source: -
Ballast/Driver: ELECTRONIC DRIVER

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 6943.1 lumens
Efficiency: N/A
Efficacy: 103.9 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 1.16 / 1.3
Luminous Opening: Rectangular (W 0.17' x L: 4' x H: 0')
CIE Type: General Diffuse

Input Watts (W): 66.8
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P331454-830
CATALOG NUMBER: SA2XXDIP-C1005D925U830-4F0-1E-UDD-F1

Luminous Intensity Polar Plot





TEST NUMBER: P331454-830

CATALOG NUMBER: SA2XXDIP-C1005D925U830-4F0-1E-UDD-F1

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	108	108	108	108	101	101	101	101	86	86	86	73	73	73	61	61	61	55
1	99	95	91	87	92	88	85	81	76	73	71	64	62	61	54	52	51	46
2	90	83	76	71	83	77	71	67	66	62	59	56	53	51	47	45	43	39
3	82	73	65	59	76	68	61	56	58	53	49	50	46	43	42	39	37	33
4	75	64	56	50	70	60	53	47	52	46	42	44	40	37	37	34	32	28
5	69	57	49	43	64	54	46	41	47	41	36	40	35	32	34	30	28	25
6	64	51	43	37	59	48	41	35	42	36	32	36	32	28	31	27	24	22
7	59	46	38	33	55	44	36	31	38	32	28	33	28	25	28	24	22	19
8	55	42	34	29	51	40	33	28	35	29	25	30	25	22	26	22	19	17
9	51	39	31	26	47	36	29	25	32	26	22	28	23	20	24	20	18	15
10	48	35	28	23	44	33	27	22	29	24	20	26	21	18	22	19	16	14

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	24254	24254	24254
5°	24347	23995	24136
10°	24202	23753	23871
15°	23903	23445	23422
20°	23479	22983	22957
25°	23058	22413	22413
30°	22514	21893	21705
35°	22007	21268	20954
40°	21372	20643	20244
45°	20747	20021	19527
50°	20065	19376	18686
55°	19356	18624	17931
60°	18564	17725	17073
65°	17712	16829	16061
70°	16636	15753	15002
75°	15140	14504	14148
80°	13436	13036	12357
85°	10967	10448	9355



TEST NUMBER: P331454-830

CATALOG NUMBER: SA2XXDIP-C1005D925U830-4F0-1E-UDD-F1

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	141.3	2.0
10°-20°	397.5	5.7
20°-30°	584.2	8.4
30°-40°	678.6	9.8
40°-50°	677.9	9.8
50°-60°	591.2	8.5
60°-70°	437.1	6.3
70°-80°	247.6	3.6
80°-90°	71.0	1.0
90°-100°	70.6	1.0
100°-110°	219.4	3.2
110°-120°	375.0	5.4
120°-130°	493.1	7.1
130°-140°	553.4	8.0
140°-150°	542.7	7.8
150°-160°	455.2	6.6
160°-170°	301.9	4.3
170°-180°	105.5	1.5
0°-30°	1123.0	16.2
0°-40°	1801.6	25.9
0°-60°	3070.7	44.2
0°-90°	3826.4	55.1
90°-120°	665.0	9.6
90°-150°	2254.1	32.5
90°-180°	3117.0	44.9
0°-180°	6943.1	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	1502	1502	1502	1502	1502	
5°	1502	1496	1480	1491	1489	142
15°	1430	1421	1403	1408	1401	402
25°	1294	1282	1258	1261	1258	595
35°	1116	1102	1079	1070	1063	697
45°	909	898	877	862	855	701
55°	688	678	662	645	637	615
65°	464	455	440	428	420	458
75°	243	240	232	225	227	259
85°	59	58	56	52	50	68
90°	1	13	33	31	32	5
95°	49	58	60	60	58	56
105°	202	205	207	209	209	214
115°	376	381	380	379	376	372
125°	547	555	553	550	549	489
135°	708	718	720	719	717	547
145°	860	866	872	873	869	537
155°	983	986	988	993	990	452
165°	1070	1069	1069	1074	1070	301
175°	1113	1110	1108	1114	1109	106
180°	1115	1115	1115	1115	1115	



TEST NUMBER: P331454-830

CATALOG NUMBER: SA2XXDIP-C1005D925U830-4F0-1E-UDD-F1

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	1502.2	1502.2	1502.2	1502.2	1502.2	1502.2	1502.2	1502.2	1502.2	1502.2	1502.2
2.5°	1509.2	1507.9	1506.7	1505.3	1504.0	1502.0	1499.2	1496.4	1493.6	1490.7	1493.3
5°	1502.2	1501.0	1499.7	1498.4	1497.1	1494.7	1491.2	1487.6	1484.1	1480.5	1483.2
7.5°	1488.9	1487.0	1485.0	1483.0	1481.0	1478.2	1474.6	1471.0	1467.4	1463.9	1466.4
10°	1476.2	1474.0	1471.8	1469.5	1467.3	1464.2	1460.4	1456.5	1452.6	1448.8	1451.4
12.5°	1459.0	1456.9	1454.9	1452.9	1451.0	1448.0	1444.2	1440.3	1436.5	1432.7	1434.5
15°	1430.0	1428.1	1426.2	1424.3	1422.3	1419.3	1415.1	1410.9	1406.7	1402.6	1403.9
17.5°	1393.1	1391.1	1389.2	1387.2	1385.3	1382.2	1378.0	1373.8	1369.5	1365.4	1366.8
20°	1366.5	1364.5	1362.6	1360.7	1358.8	1355.6	1351.0	1346.6	1342.1	1337.6	1338.5
22.5°	1339.9	1337.2	1334.5	1331.8	1329.1	1325.7	1321.4	1317.2	1313.0	1308.7	1308.9
25°	1294.3	1291.7	1289.1	1286.6	1284.0	1280.0	1274.5	1269.0	1263.6	1258.1	1258.8
27.5°	1242.3	1239.9	1237.7	1235.3	1233.0	1229.7	1225.4	1221.1	1216.8	1212.5	1211.5
30°	1207.6	1205.0	1202.4	1199.9	1197.3	1193.6	1188.8	1184.0	1179.2	1174.3	1173.4
32.5°	1170.6	1168.6	1166.5	1164.4	1162.3	1158.9	1153.8	1148.7	1143.6	1138.5	1136.8
35°	1116.5	1113.3	1110.1	1106.9	1103.7	1099.6	1094.4	1089.3	1084.2	1079.0	1077.1
37.5°	1055.6	1052.8	1050.0	1047.2	1044.3	1040.4	1035.2	1030.1	1024.9	1019.8	1017.4
40°	1014.0	1011.4	1008.9	1006.4	1003.7	999.9	994.8	989.7	984.5	979.4	976.5
42.5°	973.6	971.0	968.5	965.9	963.3	959.4	954.3	949.1	944.1	938.9	935.8
45°	908.6	906.3	904.1	901.8	899.6	896.1	891.3	886.5	881.7	876.8	873.3
47.5°	843.9	841.8	839.6	837.5	835.4	831.8	826.8	821.8	816.8	811.8	808.0
50°	798.8	797.2	795.6	794.0	792.4	789.3	784.9	780.3	775.8	771.4	766.9
52.5°	754.9	752.8	750.6	748.6	746.4	743.2	739.0	734.7	730.6	726.3	722.6
55°	687.6	685.6	683.7	681.8	679.9	676.9	673.2	669.3	665.4	661.6	657.7
57.5°	620.0	618.4	616.9	615.4	613.8	611.0	606.7	602.5	598.2	594.0	590.2
60°	574.9	573.6	572.3	571.1	569.8	566.8	562.4	557.9	553.4	548.9	545.4
62.5°	531.0	529.0	526.9	524.8	522.7	520.0	516.5	513.1	509.6	506.1	502.8
65°	463.6	461.8	459.9	457.9	456.0	453.4	450.2	447.0	443.7	440.5	437.7
67.5°	395.2	393.7	392.1	390.6	389.1	386.8	383.9	381.1	378.1	375.3	373.1
70°	352.4	351.2	349.9	348.6	347.3	345.3	342.3	339.4	336.6	333.7	331.4
72.5°	308.5	307.3	305.9	304.7	303.4	301.8	300.0	298.1	296.2	294.4	292.1
75°	242.7	242.0	241.4	240.7	240.1	238.9	237.3	235.7	234.1	232.5	230.6
77.5°	183.7	182.7	181.5	180.5	179.4	178.5	177.9	177.2	176.5	176.0	174.9
80°	144.5	144.1	143.8	143.5	143.2	142.7	142.0	141.4	140.7	140.2	139.1
82.5°	107.4	107.4	107.4	107.3	107.2	107.0	106.6	106.2	105.8	105.5	104.2
85°	59.2	58.9	58.6	58.2	58.0	57.6	57.3	56.9	56.6	56.4	55.3
87.5°	21.0	21.0	20.9	20.9	20.9	21.1	21.6	22.0	22.3	22.8	21.9
90°	0.9	3.5	5.9	8.5	10.9	14.5	19.1	23.8	28.3	32.9	32.5
92.5°	16.8	18.6	20.5	22.2	24.1	25.5	26.7	27.7	28.8	29.9	30.0
95°	48.9	51.0	53.1	55.1	57.3	58.5	58.9	59.4	59.8	60.2	60.2
97.5°	89.4	91.2	93.0	94.9	96.7	98.0	98.9	99.6	100.4	101.2	101.2
100°	119.4	121.1	122.8	124.5	126.1	127.3	127.9	128.6	129.2	129.8	129.8
102.5°	151.1	152.4	153.7	155.0	156.4	157.5	158.3	159.1	159.9	160.7	160.8
105°	202.3	202.8	203.5	204.2	204.7	205.3	205.7	206.1	206.5	206.9	207.4
107.5°	253.7	254.7	255.6	256.6	257.5	257.9	257.9	257.9	257.9	257.9	258.1
110°	286.9	288.1	289.4	290.7	291.9	292.6	292.6	292.6	292.6	292.6	292.6



TEST NUMBER: P331454-830

CATALOG NUMBER: SA2XXDIP-C1005D925U830-4F0-1E-UDD-F1

CANDELA DISTRIBUTION (continued):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	323.0	324.2	325.6	326.8	328.0	328.6	328.4	328.2	328.1	327.9	327.4
115°	376.3	377.5	378.7	380.0	381.3	381.6	381.3	380.9	380.4	380.0	379.8
117.5°	429.3	430.9	432.6	434.3	436.0	436.2	435.1	433.9	432.7	431.6	431.0
120°	464.7	466.4	468.0	469.7	471.4	471.4	469.7	468.0	466.4	464.7	464.7
122.5°	497.0	499.0	501.1	503.0	505.0	505.5	504.3	503.1	502.0	500.8	500.3
125°	547.4	549.3	551.2	553.1	555.0	555.6	555.0	554.3	553.7	553.1	552.4
127.5°	596.5	598.9	601.3	603.7	606.1	606.9	606.1	605.4	604.6	603.9	603.1
130°	627.4	630.1	632.8	635.6	638.3	639.4	638.9	638.6	638.2	637.7	637.3
132.5°	662.0	664.2	666.5	668.6	670.9	672.0	672.1	672.2	672.2	672.3	671.5
135°	708.3	710.6	712.8	715.2	717.5	718.9	719.3	719.6	720.1	720.5	720.3
137.5°	757.1	758.8	760.7	762.6	764.5	765.7	766.3	766.9	767.4	767.9	767.8
140°	786.4	788.2	790.1	792.0	793.9	795.3	796.4	797.4	798.5	799.6	799.6
142.5°	816.4	818.3	820.2	822.1	824.0	825.3	826.0	826.7	827.4	828.1	828.3
145°	859.7	861.2	862.6	864.1	865.5	867.0	868.2	869.4	870.7	871.9	872.1
147.5°	898.2	900.0	901.8	903.5	905.3	906.6	907.5	908.2	909.1	909.9	910.4
150°	924.6	925.9	927.1	928.4	929.6	930.7	931.5	932.4	933.2	934.1	934.6
152.5°	947.9	949.2	950.5	951.7	953.0	954.1	955.1	956.1	957.1	958.1	958.9
155°	983.0	983.5	984.2	984.9	985.4	986.1	986.7	987.3	988.0	988.5	989.7
157.5°	1012.9	1013.2	1013.7	1014.1	1014.6	1014.9	1015.3	1015.7	1016.1	1016.4	1017.9
160°	1031.0	1031.3	1031.7	1032.2	1032.6	1032.9	1033.1	1033.3	1033.5	1033.7	1035.0
162.5°	1047.4	1047.5	1047.6	1047.7	1047.8	1047.9	1048.2	1048.4	1048.6	1048.8	1050.2
165°	1069.5	1069.3	1069.0	1068.8	1068.7	1068.6	1068.6	1068.6	1068.6	1068.6	1070.0
167.5°	1087.9	1087.3	1086.7	1086.0	1085.4	1085.1	1085.1	1085.0	1085.0	1084.9	1086.4
170°	1097.7	1097.0	1096.5	1095.8	1095.1	1094.8	1094.6	1094.4	1094.1	1093.9	1095.4
172.5°	1104.5	1103.8	1103.2	1102.6	1101.9	1101.5	1101.4	1101.1	1100.9	1100.7	1102.2
175°	1112.8	1112.1	1111.4	1110.9	1110.2	1109.7	1109.3	1108.9	1108.4	1108.1	1109.5
177.5°	1116.2	1115.6	1115.1	1114.7	1114.1	1113.7	1113.3	1113.0	1112.7	1112.4	1113.3
180°	1114.7	1114.7	1114.7	1114.7	1114.7	1114.7	1114.7	1114.7	1114.7	1114.7	1114.7



TEST NUMBER: P331454-830
 CATALOG NUMBER: SA2XXDIP-C1005D925U830-4F0-1E-UDD-F1

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°
0°	1502.2	1502.2	1502.2	1502.2	1502.2	1502.2	1502.2	1502.2
2.5°	1495.8	1498.4	1501.0	1502.0	1501.5	1501.0	1500.4	1500.0
5°	1485.7	1488.3	1490.8	1491.9	1491.2	1490.5	1489.9	1489.2
7.5°	1469.0	1471.5	1474.1	1475.1	1474.3	1473.7	1472.9	1472.3
10°	1454.0	1456.5	1459.1	1459.9	1459.0	1457.9	1457.0	1456.0
12.5°	1436.2	1438.0	1439.8	1440.4	1439.6	1439.0	1438.2	1437.6
15°	1405.1	1406.5	1407.7	1407.6	1406.0	1404.4	1402.8	1401.2
17.5°	1368.3	1369.8	1371.2	1371.2	1369.6	1368.1	1366.6	1365.0
20°	1339.5	1340.5	1341.4	1341.2	1340.0	1338.7	1337.5	1336.1
22.5°	1309.1	1309.3	1309.5	1309.2	1308.4	1307.7	1306.8	1306.1
25°	1259.4	1260.1	1260.7	1260.7	1260.1	1259.4	1258.8	1258.1
27.5°	1210.6	1209.6	1208.6	1207.4	1205.9	1204.3	1202.8	1201.3
30°	1172.4	1171.5	1170.5	1169.4	1168.1	1166.8	1165.5	1164.2
32.5°	1135.1	1133.3	1131.6	1130.1	1128.8	1127.6	1126.2	1124.9
35°	1075.2	1073.3	1071.3	1069.6	1068.0	1066.4	1064.7	1063.1
37.5°	1015.0	1012.7	1010.3	1008.3	1006.8	1005.2	1003.7	1002.2
40°	973.6	970.7	967.8	965.7	964.4	963.2	961.9	960.5
42.5°	932.6	929.4	926.3	923.9	922.1	920.3	918.5	916.6
45°	869.8	866.2	862.7	860.3	858.9	857.7	856.4	855.2
47.5°	804.4	800.6	796.9	794.1	792.2	790.4	788.5	786.6
50°	762.3	757.9	753.4	750.4	748.8	747.2	745.6	743.9
52.5°	718.9	715.1	711.4	708.5	706.3	704.3	702.1	700.0
55°	653.8	650.0	646.2	643.5	641.9	640.3	638.7	637.0
57.5°	586.4	582.6	578.8	576.3	575.1	573.9	572.7	571.5
60°	541.9	538.3	534.8	532.5	531.6	530.7	529.6	528.7
62.5°	499.6	496.3	493.0	490.8	489.6	488.3	487.1	485.9
65°	434.8	431.9	429.0	426.8	425.2	423.6	422.0	420.4
67.5°	370.8	368.5	366.3	364.5	363.3	361.9	360.7	359.4
70°	329.1	327.0	324.7	322.9	321.6	320.4	319.1	317.8
72.5°	289.9	287.7	285.4	283.8	282.8	281.7	280.7	279.7
75°	228.8	226.8	224.9	224.2	224.9	225.5	226.1	226.8
77.5°	174.0	173.1	172.1	171.2	170.2	169.4	168.4	167.6
80°	138.2	137.2	136.3	135.4	134.8	134.2	133.6	132.9
82.5°	103.0	101.8	100.6	99.9	99.7	99.6	99.5	99.3
85°	54.4	53.4	52.5	51.8	51.6	51.2	50.9	50.5
87.5°	21.0	20.2	19.3	18.9	18.6	18.4	18.2	17.9
90°	32.0	31.7	31.3	31.1	31.4	31.6	31.8	32.0
92.5°	30.1	30.2	30.3	30.3	30.3	30.3	30.4	30.4
95°	60.2	60.2	60.2	59.9	59.6	59.2	58.7	58.3
97.5°	101.2	101.2	101.2	101.2	101.1	101.1	101.0	101.0
100°	129.8	129.8	129.8	129.7	129.5	129.3	129.0	128.8
102.5°	161.0	161.2	161.4	161.3	161.1	160.9	160.7	160.5
105°	207.7	208.2	208.6	208.8	208.8	208.8	208.8	208.8
107.5°	258.3	258.4	258.5	258.2	257.2	256.3	255.3	254.3
110°	292.6	292.6	292.6	292.2	291.6	291.0	290.3	289.7



TEST NUMBER: P331454-830

CATALOG NUMBER: SA2XXDIP-C1005D925U830-4F0-1E-UDD-F1

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°
112.5°	326.9	326.4	325.9	325.4	325.0	324.5	324.0	323.6
115°	379.6	379.4	379.2	378.7	378.1	377.5	376.8	376.3
117.5°	430.6	430.1	429.5	429.0	428.4	427.7	427.1	426.5
120°	464.7	464.7	464.7	464.4	463.7	463.1	462.5	461.8
122.5°	499.7	499.3	498.8	498.3	497.9	497.4	496.9	496.4
125°	551.9	551.2	550.5	550.2	550.0	549.7	549.5	549.3
127.5°	602.4	601.6	600.9	600.1	599.5	598.8	598.1	597.5
130°	636.9	636.5	636.0	635.5	634.6	633.8	632.9	632.1
132.5°	670.5	669.6	668.6	667.9	667.2	666.6	665.9	665.2
135°	720.1	719.9	719.6	719.3	718.6	718.0	717.4	716.7
137.5°	767.6	767.4	767.2	766.8	765.9	765.1	764.2	763.4
140°	799.6	799.6	799.6	799.1	798.2	797.4	796.6	795.8
142.5°	828.5	828.6	828.8	828.5	827.6	826.8	826.0	825.1
145°	872.3	872.6	872.8	872.5	871.7	870.8	870.0	869.1
147.5°	910.9	911.3	911.8	911.6	910.9	910.0	909.3	908.4
150°	935.3	935.9	936.5	936.5	935.9	935.3	934.6	934.1
152.5°	959.7	960.5	961.3	961.3	960.5	959.7	958.9	958.1
155°	990.7	991.7	992.8	993.0	992.3	991.7	991.1	990.4
157.5°	1019.3	1020.7	1022.1	1022.3	1021.3	1020.3	1019.3	1018.3
160°	1036.2	1037.5	1038.8	1039.0	1038.1	1037.3	1036.4	1035.6
162.5°	1051.6	1053.0	1054.4	1054.7	1053.7	1052.6	1051.7	1050.7
165°	1071.5	1072.9	1074.4	1074.6	1073.6	1072.5	1071.5	1070.4
167.5°	1087.8	1089.3	1090.7	1090.9	1089.9	1088.7	1087.7	1086.6
170°	1096.8	1098.3	1099.8	1099.9	1098.6	1097.4	1096.1	1094.9
172.5°	1103.6	1105.1	1106.5	1106.6	1105.4	1104.2	1102.9	1101.6
175°	1111.0	1112.4	1113.9	1114.0	1112.8	1111.4	1110.2	1109.0
177.5°	1114.4	1115.4	1116.3	1116.3	1115.4	1114.4	1113.3	1112.4
180°	1114.7	1114.7	1114.7	1114.7	1114.7	1114.7	1114.7	1114.7

(END OF REPORT)