

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P333130-840

Luminaire Tested: **S125DIP-S375D590U840-4F0-1E-UDD-F**

Issue Date: 3/3/2020

Test Information

Test Method: LM-79-08
Report Number: P333130-840
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-7,
Test Lab: INNOVATION CENTER
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: NEO-RAY
Catalog Number: S125DIP-S375D590U840-4F0-1E-UDD-F
Description: DEFINE 5 DIRECT-INDIRECT PENDANT LED LUMINAIRE
DOWNLIGHT 375 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER
UPLIGHT 590 LUMENS PER FOOT, NO LENS
Light Source: -
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 3923.5 lumens
Efficiency: N/A
Efficacy: 153.3 lumens/watt
Spacing Criteria (0/90/45): 1.21 / 1.18 / 1.31
Luminous Opening: Rectangular (W 0.42' x L: 4' x H: 0')
CIE Type: Semi-Indirect


Input Watts (W): 25.6
Input Voltage (V): 120
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P333130-840

CATALOG NUMBER: S125DIP-S375D590U840-4F0-1E-UDD-F

Luminous Intensity Polar Plot





TEST NUMBER: P333130-840

CATALOG NUMBER: S125DIP-S375D590U840-4F0-1E-UDD-F

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	105	105	105	105	95	95	95	95	77	77	77	61	61	61	46	46	46	39
1	95	91	87	84	86	83	80	77	68	65	63	54	52	51	41	40	39	33
2	87	79	73	68	79	72	67	63	59	56	52	47	44	42	36	34	33	27
3	79	70	63	57	72	64	57	52	52	48	44	42	38	36	32	30	28	23
4	72	62	54	48	65	56	50	44	46	41	37	37	33	31	28	26	24	20
5	66	55	47	41	60	50	43	38	41	36	32	33	29	26	25	23	21	17
6	61	49	41	35	55	45	38	33	37	32	28	30	26	23	23	20	18	15
7	56	44	36	31	51	41	34	29	34	28	25	27	23	20	21	18	16	13
8	52	40	33	27	47	37	30	25	31	25	22	25	21	18	19	17	15	12
9	49	37	29	24	44	34	27	23	28	23	19	23	19	16	18	15	13	11
10	45	33	26	22	41	31	24	20	26	21	17	21	17	15	17	14	12	10

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	3810	3810	3810
5°	3818	3782	3806
10°	3796	3756	3777
15°	3754	3710	3726
20°	3696	3647	3654
25°	3632	3572	3569
30°	3554	3491	3473
35°	3470	3404	3356
40°	3384	3309	3262
45°	3291	3222	3159
50°	3189	3118	3024
55°	3090	3001	2916
60°	2971	2882	2780
65°	2832	2740	2647
70°	2696	2574	2485
75°	2458	2376	2293
80°	2187	2153	2101
85°	1904	1941	1830



TEST NUMBER: P333130-840

CATALOG NUMBER: S125DIP-S375D590U840-4F0-1E-UDD-F

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	55.6	1.4
10°-20°	157.1	4.0
20°-30°	232.0	5.9
30°-40°	270.7	6.9
40°-50°	271.9	6.9
50°-60°	238.7	6.1
60°-70°	177.8	4.5
70°-80°	101.7	2.6
80°-90°	31.2	0.8
90°-100°	28.3	0.7
100°-110°	174.1	4.4
110°-120°	315.7	8.0
120°-130°	405.2	10.3
130°-140°	435.8	11.1
140°-150°	409.1	10.4
150°-160°	330.9	8.4
160°-170°	214.0	5.5
170°-180°	73.8	1.9
0°-30°	444.7	11.3
0°-40°	715.5	18.2
0°-60°	1226.0	31.2
0°-90°	1536.7	39.2
90°-120°	518.0	13.2
90°-150°	1768.1	45.1
90°-180°	2387.0	60.8
0°-180°	3923.5	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	590	590	590	590	590	
5°	589	588	583	587	587	56
15°	562	560	555	557	557	158
25°	510	507	501	502	501	234
35°	440	438	432	429	426	275
45°	360	358	353	348	346	278
55°	274	273	266	262	259	245
65°	185	184	179	175	173	184
75°	98	98	95	94	92	105
85°	26	26	26	26	25	29
90°	1	5	9	12	14	3
95°	33	30	9	12	12	42
105°	169	172	172	172	171	180
115°	318	321	322	319	316	315
125°	452	456	456	454	452	404
135°	564	567	566	565	562	435
145°	654	655	655	655	652	409
155°	720	717	718	719	715	332
165°	760	757	757	760	756	215
175°	777	774	774	778	774	74
180°	777	777	777	777	777	



TEST NUMBER: P333130-840

CATALOG NUMBER: S125DIP-S375D590U840-4F0-1E-UDD-F

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	590.0	590.0	590.0	590.0	590.0	590.0	590.0	590.0	590.0	590.0	590.0
2.5°	591.4	591.2	591.0	590.7	590.5	589.9	589.1	588.2	587.4	586.5	587.4
5°	589.0	588.8	588.5	588.3	588.1	587.5	586.5	585.5	584.4	583.4	584.3
7.5°	583.6	583.4	583.2	583.0	582.8	582.1	581.0	579.8	578.7	577.5	578.5
10°	578.8	578.6	578.3	578.1	577.9	577.2	576.1	574.9	573.8	572.7	573.5
12.5°	572.8	572.4	572.0	571.7	571.3	570.6	569.5	568.5	567.3	566.3	566.9
15°	561.5	561.2	560.9	560.6	560.2	559.5	558.4	557.2	556.0	554.9	555.4
17.5°	548.5	548.1	547.5	547.1	546.6	545.8	544.6	543.5	542.3	541.1	541.8
20°	537.7	537.5	537.2	537.0	536.8	536.0	534.7	533.3	532.0	530.7	531.4
22.5°	526.8	526.4	526.0	525.7	525.3	524.5	523.2	522.0	520.7	519.5	520.0
25°	509.7	509.2	508.6	508.1	507.6	506.6	505.3	503.9	502.6	501.3	501.5
27.5°	489.6	489.3	489.0	488.7	488.4	487.5	486.1	484.7	483.3	481.9	482.0
30°	476.6	476.3	475.8	475.5	475.2	474.3	472.8	471.2	469.7	468.1	467.9
32.5°	462.3	461.8	461.4	460.9	460.4	459.5	458.1	456.7	455.3	453.9	453.5
35°	440.1	439.7	439.3	438.9	438.5	437.5	436.1	434.6	433.1	431.7	431.2
37.5°	417.1	416.6	416.1	415.5	415.0	414.0	412.6	411.3	409.9	408.6	407.8
40°	401.4	400.8	400.3	399.8	399.3	398.3	396.9	395.5	393.9	392.5	391.6
42.5°	384.6	384.2	383.7	383.2	382.8	381.9	380.4	379.0	377.5	376.1	375.3
45°	360.3	359.9	359.5	359.1	358.6	357.8	356.6	355.4	354.1	352.8	351.6
47.5°	334.2	334.2	334.2	334.3	334.3	333.6	332.0	330.5	329.0	327.5	326.3
50°	317.4	317.1	316.8	316.4	316.1	315.4	314.1	312.9	311.6	310.3	309.0
52.5°	300.2	299.9	299.7	299.5	299.3	298.5	297.2	295.9	294.5	293.2	292.1
55°	274.4	274.1	273.8	273.5	273.2	272.3	270.8	269.4	267.9	266.5	265.6
57.5°	247.3	247.1	246.9	246.8	246.6	245.9	244.7	243.5	242.3	241.1	239.8
60°	230.0	229.6	229.2	228.8	228.4	227.6	226.5	225.4	224.2	223.1	222.1
62.5°	212.2	211.9	211.5	211.2	210.9	210.2	209.2	208.2	207.2	206.3	205.2
65°	185.3	185.1	184.9	184.7	184.5	183.8	182.7	181.5	180.4	179.3	178.2
67.5°	159.3	158.9	158.3	157.9	157.5	156.8	156.0	155.1	154.3	153.5	152.7
70°	142.8	142.3	141.8	141.3	140.8	140.0	139.1	138.1	137.2	136.3	135.6
72.5°	124.9	124.5	124.2	123.8	123.5	123.0	122.4	121.8	121.2	120.6	119.9
75°	98.5	98.3	98.1	97.9	97.7	97.3	96.7	96.2	95.7	95.2	94.9
77.5°	74.1	74.0	73.9	73.8	73.8	73.6	73.3	73.0	72.7	72.4	72.2
80°	58.8	58.8	58.8	58.8	58.8	58.7	58.5	58.3	58.1	57.9	57.8
82.5°	45.3	45.2	45.0	44.8	44.7	44.6	44.5	44.5	44.4	44.4	44.2
85°	25.7	25.8	25.9	26.0	26.1	26.2	26.2	26.2	26.2	26.2	26.1
87.5°	10.2	10.4	10.6	10.8	11.0	11.2	11.3	11.3	11.4	11.5	11.7
90°	0.6	1.6	2.6	3.6	4.6	5.7	6.6	7.5	8.3	9.2	9.9
92.5°	8.9	8.2	7.5	6.8	6.0	6.1	6.9	7.7	8.4	9.2	9.9
95°	32.8	32.4	32.1	31.7	31.3	28.7	23.8	19.0	14.0	9.2	9.9
97.5°	68.6	69.3	70.0	70.6	71.3	66.9	57.3	47.6	38.0	28.4	24.7
100°	96.2	96.6	96.9	97.4	97.8	98.2	98.8	99.3	99.8	100.3	81.2
102.5°	124.3	124.8	125.3	125.8	126.2	126.6	126.9	127.3	127.6	127.9	124.3
105°	169.4	169.9	170.5	171.0	171.5	171.7	171.7	171.7	171.7	171.7	171.7
107.5°	216.2	216.2	216.2	216.2	216.2	216.3	216.5	216.8	217.1	217.3	217.3
110°	246.6	246.6	246.6	246.6	246.6	246.7	247.0	247.2	247.5	247.7	247.4



TEST NUMBER: P333130-840

CATALOG NUMBER: S125DIP-S375D590U840-4F0-1E-UDD-F

CANDELA DISTRIBUTION (continued):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	275.2	275.5	275.8	276.1	276.4	276.6	276.8	276.9	277.1	277.2	276.8
115°	318.0	318.7	319.3	319.9	320.6	321.0	321.1	321.2	321.3	321.5	321.0
117.5°	362.4	362.3	362.3	362.3	362.3	362.5	363.0	363.6	364.0	364.5	363.9
120°	390.1	389.9	389.8	389.7	389.5	389.7	390.1	390.4	390.8	391.2	390.9
122.5°	414.4	415.0	415.5	416.0	416.5	416.8	417.0	417.2	417.3	417.5	417.3
125°	452.3	453.2	454.0	454.9	455.9	456.4	456.4	456.4	456.4	456.4	455.9
127.5°	488.4	489.0	489.7	490.3	490.9	491.2	491.1	491.1	491.0	490.9	490.6
130°	510.5	511.1	511.8	512.4	513.0	513.4	513.5	513.7	513.8	513.9	513.5
132.5°	532.6	533.3	534.1	534.8	535.5	535.8	535.5	535.2	534.9	534.7	534.6
135°	564.1	564.8	565.6	566.3	567.1	567.4	567.1	566.8	566.6	566.3	566.1
137.5°	593.0	593.7	594.3	595.0	595.6	595.9	595.6	595.4	595.2	594.9	595.0
140°	611.9	612.2	612.4	612.7	612.9	613.0	612.9	612.7	612.6	612.5	612.7
142.5°	628.9	629.1	629.2	629.4	629.5	629.8	630.0	630.1	630.3	630.5	630.5
145°	654.0	654.2	654.5	654.7	655.0	655.1	655.1	655.1	655.1	655.1	655.2
147.5°	675.8	675.8	675.7	675.7	675.6	675.7	675.8	676.0	676.1	676.3	676.5
150°	689.6	689.4	689.1	688.9	688.6	688.6	688.9	689.1	689.4	689.6	689.9
152.5°	703.1	702.5	702.0	701.4	700.7	700.6	700.8	701.1	701.4	701.7	702.0
155°	720.2	719.4	718.7	717.9	717.1	716.9	717.1	717.4	717.6	717.9	718.3
157.5°	733.5	733.0	732.6	732.1	731.6	731.4	731.4	731.4	731.4	731.5	732.0
160°	742.7	741.9	741.1	740.3	739.6	739.3	739.4	739.5	739.6	739.8	740.3
162.5°	750.0	749.3	748.5	747.7	747.0	746.7	746.8	746.9	747.0	747.2	747.9
165°	759.9	759.2	758.4	757.7	756.9	756.6	756.7	756.8	757.0	757.1	757.8
167.5°	767.3	766.6	765.8	765.0	764.2	763.9	764.0	764.1	764.2	764.4	765.3
170°	771.5	770.6	769.7	768.8	767.9	767.5	767.6	767.8	767.9	768.0	769.0
172.5°	774.3	773.4	772.4	771.5	770.6	770.3	770.5	770.8	771.0	771.2	772.1
175°	777.3	776.5	775.7	775.0	774.2	773.9	774.0	774.2	774.3	774.4	775.4
177.5°	778.6	778.0	777.4	776.8	776.2	775.9	776.0	776.1	776.2	776.3	777.1
180°	777.3	777.3	777.3	777.3	777.3	777.3	777.3	777.3	777.3	777.3	777.3



TEST NUMBER: P333130-840

CATALOG NUMBER: S125DIP-S375D590U840-4F0-1E-UDD-F

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°
0°	590.0	590.0	590.0	590.0	590.0	590.0	590.0	590.0
2.5°	588.2	589.1	589.9	590.3	590.2	590.1	590.1	590.0
5°	585.2	586.2	587.1	587.5	587.4	587.3	587.2	587.1
7.5°	579.4	580.3	581.2	581.6	581.5	581.4	581.3	581.2
10°	574.3	575.1	576.0	576.3	576.2	576.1	576.0	575.9
12.5°	567.6	568.4	569.0	569.3	569.3	569.3	569.3	569.2
15°	555.9	556.4	557.0	557.2	557.2	557.2	557.2	557.2
17.5°	542.4	543.0	543.7	543.7	543.2	542.7	542.2	541.7
20°	532.1	532.8	533.5	533.7	533.1	532.6	532.1	531.6
22.5°	520.4	520.9	521.4	521.4	521.1	520.7	520.4	520.0
25°	501.7	501.9	502.1	502.0	501.7	501.4	501.1	500.8
27.5°	482.0	482.0	482.1	482.0	481.6	481.3	481.0	480.7
30°	467.7	467.5	467.3	467.1	466.8	466.5	466.1	465.7
32.5°	453.2	452.8	452.4	452.0	451.4	450.8	450.3	449.7
35°	430.7	430.2	429.6	429.0	428.2	427.3	426.5	425.7
37.5°	407.1	406.3	405.5	404.9	404.3	403.9	403.4	402.9
40°	390.6	389.7	388.8	388.2	387.9	387.5	387.2	386.9
42.5°	374.4	373.5	372.6	372.0	371.5	371.0	370.6	370.1
45°	350.3	349.1	347.9	347.1	346.8	346.5	346.2	345.9
47.5°	325.0	323.8	322.4	321.4	320.7	320.0	319.3	318.6
50°	307.7	306.3	305.0	304.0	303.2	302.5	301.7	301.0
52.5°	290.8	289.6	288.4	287.5	286.7	285.9	285.1	284.3
55°	264.6	263.7	262.8	262.0	261.3	260.4	259.7	259.0
57.5°	238.6	237.4	236.2	235.4	235.0	234.6	234.2	233.8
60°	221.1	219.9	218.9	218.0	217.3	216.6	215.9	215.2
62.5°	204.1	202.9	201.8	201.0	200.5	199.9	199.2	198.7
65°	177.3	176.4	175.5	174.8	174.4	174.0	173.6	173.2
67.5°	151.9	151.1	150.3	149.8	149.6	149.3	149.1	148.8
70°	135.0	134.4	133.8	133.3	132.9	132.5	132.0	131.6
72.5°	119.2	118.5	117.8	117.2	116.8	116.4	115.9	115.5
75°	94.6	94.3	93.9	93.6	93.2	92.8	92.4	91.9
77.5°	72.1	71.9	71.7	71.5	71.2	70.9	70.6	70.3
80°	57.7	57.6	57.5	57.3	57.1	56.9	56.7	56.5
82.5°	44.0	43.8	43.7	43.5	43.5	43.5	43.4	43.4
85°	26.0	25.9	25.8	25.5	25.3	25.1	24.9	24.7
87.5°	11.8	11.9	12.0	12.1	12.0	11.9	11.8	11.7
90°	10.5	11.1	11.8	12.3	12.7	13.0	13.4	13.8
92.5°	10.5	11.1	11.8	12.2	12.3	12.5	12.7	12.9
95°	10.5	11.1	11.8	12.1	12.1	12.1	12.1	12.1
97.5°	21.1	17.5	13.9	12.1	12.1	12.1	12.1	12.1
100°	62.1	43.0	23.9	14.1	13.6	13.1	12.6	12.1
102.5°	120.7	117.0	113.5	107.3	98.6	89.9	81.2	72.5
105°	171.7	171.7	171.7	171.7	171.5	171.4	171.3	171.1
107.5°	217.4	217.4	217.4	217.2	216.9	216.5	216.1	215.7
110°	247.0	246.6	246.2	246.1	246.2	246.3	246.5	246.6



TEST NUMBER: P333130-840

CATALOG NUMBER: S125DIP-S375D590U840-4F0-1E-UDD-F

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°
112.5°	276.3	275.8	275.3	275.0	274.8	274.6	274.5	274.3
115°	320.4	319.9	319.4	318.8	318.0	317.3	316.5	315.8
117.5°	363.1	362.4	361.8	361.3	361.0	360.6	360.3	360.0
120°	390.7	390.4	390.2	389.7	389.1	388.5	387.8	387.2
122.5°	417.0	416.8	416.5	416.0	415.3	414.4	413.7	413.0
125°	455.3	454.7	454.2	453.8	453.4	453.0	452.7	452.3
127.5°	490.3	490.1	489.8	489.2	488.2	487.3	486.4	485.3
130°	513.2	512.8	512.4	511.9	511.3	510.6	510.0	509.4
132.5°	534.5	534.4	534.4	534.0	533.4	532.7	532.1	531.5
135°	565.8	565.6	565.3	564.8	564.1	563.3	562.5	561.8
137.5°	595.0	595.1	595.1	594.8	594.2	593.5	592.9	592.2
140°	613.0	613.2	613.5	613.2	612.5	611.7	611.0	610.2
142.5°	630.6	630.6	630.7	630.3	629.5	628.7	627.9	627.2
145°	655.4	655.5	655.6	655.3	654.5	653.8	653.0	652.2
147.5°	676.6	676.8	676.9	676.5	675.6	674.7	673.8	672.9
150°	690.1	690.4	690.6	690.3	689.3	688.2	687.2	686.2
152.5°	702.2	702.5	702.7	702.4	701.5	700.5	699.5	698.6
155°	718.7	719.0	719.4	719.1	718.1	717.1	716.1	715.0
157.5°	732.4	732.8	733.2	732.9	731.8	730.7	729.7	728.7
160°	740.8	741.3	741.8	741.5	740.5	739.5	738.5	737.5
162.5°	748.6	749.3	750.0	749.8	748.7	747.6	746.5	745.3
165°	758.6	759.4	760.1	760.0	759.0	758.0	757.0	755.9
167.5°	766.2	767.1	768.0	767.9	766.8	765.6	764.5	763.3
170°	770.1	771.1	772.1	772.0	770.9	769.7	768.6	767.5
172.5°	773.1	774.1	775.0	774.9	773.7	772.5	771.3	770.2
175°	776.4	777.4	778.5	778.4	777.3	776.1	775.0	773.8
177.5°	777.8	778.5	779.2	779.1	778.3	777.5	776.7	775.9
180°	777.3	777.3	777.3	777.3	777.3	777.3	777.3	777.3

(END OF REPORT)