

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P331284-830

Luminaire Tested: **SA2XXDIP-C290D1080U830-4F0-1E-UDD-F4**

Issue Date: 10/7/2019

Test Information

Test Method: LM-79-08
Report Number: P331284-830
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-16,
Test Lab: INNOVATION CENTER
Issue Date: 10/7/2019
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: NEO-RAY
Catalog Number: SA2XXDIP-C290D1080U830-4F0-1E-UDD-F4
Description: DEFINE 2 DIRECT-INDIRECT PENDANT LED LUMINAIRE
DOWNLIGHT 290 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER
UPLIGHT 1080 LUMENS PER FOOT, BATWING OPTIC
Light Source: -
Ballast/Driver: ELECTRONIC DRIVER

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 5100.0 lumens
Efficiency: N/A
Efficacy: 120.9 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 1.16 / 1.3
Luminous Opening: Rectangular (W 0.17' x L: 4' x H: 0')
CIE Type: Semi-Indirect

Input Watts (W): 42.2
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P331284-830
CATALOG NUMBER: SA2XXDIP-C290D1080U830-4F0-1E-UDD-F4

Luminous Intensity Polar Plot





TEST NUMBER: P331284-830

CATALOG NUMBER: SA2XXDIP-C290D1080U830-4F0-1E-UDD-F4

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20					20					20					20					20	
RC	80					70					50					30					10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0	
RCR																						
0	101	101	101	101	89	89	89	89	68	68	68	49	49	49	31	31	31	22				
1	92	87	84	80	81	78	75	72	59	57	55	43	41	40	27	26	26	19				
2	83	76	70	65	74	68	63	59	52	49	46	37	35	33	24	23	22	16				
3	76	67	60	54	67	60	54	49	46	42	38	33	30	28	21	20	18	13				
4	69	59	52	46	61	53	46	41	41	36	33	29	26	24	19	17	16	11				
5	64	52	45	39	56	47	40	35	36	32	28	26	23	21	17	15	14	10				
6	58	47	39	34	52	42	35	30	32	28	24	24	20	18	15	13	12	9				
7	54	42	35	29	48	38	31	27	29	25	21	21	18	16	14	12	11	8				
8	50	38	31	26	44	34	28	23	27	22	19	19	16	14	13	11	10	7				
9	46	35	27	23	41	31	25	21	24	20	17	18	15	13	12	10	9	6				
10	43	32	25	20	38	28	22	18	22	18	15	16	13	11	11	9	8	6				

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	7190	7190	7190
5°	7217	7112	7156
10°	7174	7040	7076
15°	7086	6950	6944
20°	6959	6813	6806
25°	6834	6645	6645
30°	6674	6490	6434
35°	6524	6303	6211
40°	6336	6119	6001
45°	6149	5934	5786
50°	5948	5745	5541
55°	5737	5520	5315
60°	5503	5254	5060
65°	5249	4989	4760
70°	4928	4669	4447
75°	4485	4298	4192
80°	3980	3868	3663
85°	3242	3094	2779



TEST NUMBER: P331284-830

CATALOG NUMBER: SA2XXDIP-C290D1080U830-4F0-1E-UDD-F4

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	41.9	0.8
10°-20°	117.8	2.3
20°-30°	173.2	3.4
30°-40°	201.2	3.9
40°-50°	200.9	3.9
50°-60°	175.2	3.4
60°-70°	129.6	2.5
70°-80°	73.4	1.4
80°-90°	24.9	0.5
90°-100°	227.7	4.5
100°-110°	772.5	15.1
110°-120°	820.7	16.1
120°-130°	675.6	13.2
130°-140°	542.5	10.6
140°-150°	410.0	8.0
150°-160°	288.1	5.6
160°-170°	169.6	3.3
170°-180°	55.2	1.1
0°-30°	332.9	6.5
0°-40°	534.0	10.5
0°-60°	910.2	17.8
0°-90°	1138.0	22.3
90°-120°	1820.9	35.7
90°-150°	3449.0	67.6
90°-180°	3962.0	77.7
0°-180°	5100.0	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	445	445	445	445	445	
5°	445	443	439	442	442	42
15°	424	421	416	417	415	119
25°	384	380	373	374	373	176
35°	331	327	320	317	315	207
45°	269	266	260	255	253	208
55°	204	201	196	191	189	182
65°	137	135	131	127	125	136
75°	72	71	69	66	67	77
85°	18	17	17	16	15	20
90°	1	15	37	36	36	3
95°	38	94	429	162	125	41
105°	134	202	811	1450	1234	142
115°	235	297	679	1401	1624	233
125°	328	389	653	1135	1317	292
135°	385	460	645	954	1092	298
145°	440	506	642	797	872	276
155°	500	540	623	705	732	230
165°	545	562	597	633	643	154
175°	568	569	574	581	579	54
180°	569	569	569	569	569	



TEST NUMBER: P331284-830

CATALOG NUMBER: SA2XXDIP-C290D1080U830-4F0-1E-UDD-F4

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	445.3	445.3	445.3	445.3	445.3	445.3	445.3	445.3	445.3	445.3	445.3
2.5°	447.3	447.0	446.6	446.2	445.8	445.3	444.4	443.6	442.7	441.9	442.6
5°	445.3	444.9	444.5	444.1	443.7	443.1	442.1	441.0	439.9	438.8	439.6
7.5°	441.4	440.7	440.2	439.6	439.0	438.2	437.2	436.0	435.0	433.9	434.7
10°	437.6	437.0	436.3	435.6	434.9	434.0	432.9	431.8	430.6	429.4	430.2
12.5°	432.4	431.9	431.3	430.6	430.1	429.2	428.1	427.0	425.8	424.7	425.2
15°	423.9	423.3	422.7	422.2	421.6	420.8	419.4	418.2	417.0	415.8	416.1
17.5°	412.9	412.4	411.8	411.2	410.7	409.7	408.5	407.2	406.0	404.7	405.1
20°	405.0	404.4	403.9	403.3	402.7	401.8	400.5	399.2	397.8	396.5	396.8
22.5°	397.2	396.3	395.6	394.7	394.0	392.9	391.7	390.4	389.2	388.0	388.0
25°	383.6	382.9	382.1	381.4	380.6	379.4	377.8	376.2	374.6	373.0	373.2
27.5°	368.3	367.6	366.8	366.2	365.5	364.5	363.3	361.9	360.7	359.4	359.1
30°	358.0	357.2	356.5	355.7	354.9	353.8	352.4	351.0	349.5	348.1	347.8
32.5°	346.9	346.4	345.8	345.2	344.6	343.5	342.0	340.5	339.0	337.5	337.0
35°	331.0	330.0	329.0	328.1	327.2	325.9	324.4	322.9	321.4	319.8	319.2
37.5°	312.9	312.1	311.2	310.4	309.5	308.4	306.9	305.4	303.8	302.3	301.6
40°	300.6	299.8	299.1	298.3	297.6	296.4	294.8	293.3	291.8	290.3	289.5
42.5°	288.6	287.9	287.1	286.3	285.6	284.4	282.9	281.3	279.8	278.3	277.4
45°	269.3	268.6	268.0	267.3	266.6	265.6	264.2	262.8	261.4	259.9	258.8
47.5°	250.2	249.5	248.9	248.3	247.6	246.6	245.1	243.6	242.1	240.6	239.5
50°	236.8	236.3	235.8	235.4	234.9	233.9	232.6	231.3	230.0	228.7	227.3
52.5°	223.8	223.1	222.5	221.9	221.2	220.3	219.0	217.8	216.5	215.3	214.1
55°	203.8	203.2	202.6	202.1	201.5	200.7	199.5	198.4	197.3	196.1	194.9
57.5°	183.8	183.3	182.9	182.4	181.9	181.1	179.8	178.6	177.3	176.1	174.9
60°	170.4	170.0	169.7	169.3	168.9	168.1	166.7	165.4	164.0	162.7	161.6
62.5°	157.4	156.7	156.2	155.6	155.0	154.1	153.1	152.1	151.1	150.1	149.0
65°	137.4	136.9	136.3	135.7	135.2	134.4	133.5	132.5	131.6	130.6	129.7
67.5°	117.2	116.7	116.2	115.7	115.4	114.7	113.8	112.9	112.1	111.2	110.6
70°	104.4	104.1	103.7	103.3	102.9	102.4	101.5	100.7	99.7	98.9	98.2
72.5°	91.4	91.0	90.7	90.3	89.9	89.4	88.9	88.4	87.8	87.3	86.6
75°	71.9	71.7	71.5	71.4	71.2	70.9	70.4	69.8	69.4	68.9	68.3
77.5°	54.5	54.1	53.8	53.5	53.2	52.9	52.7	52.5	52.3	52.1	51.8
80°	42.8	42.7	42.6	42.5	42.4	42.3	42.1	41.9	41.8	41.6	41.3
82.5°	31.9	31.9	31.9	31.8	31.8	31.7	31.6	31.5	31.4	31.3	30.9
85°	17.5	17.4	17.3	17.2	17.2	17.1	17.0	16.9	16.8	16.7	16.4
87.5°	6.4	6.9	7.6	7.9	8.2	8.7	9.6	11.0	12.2	12.3	11.8
90°	1.1	4.3	8.8	10.9	13.1	16.4	21.9	29.6	36.1	37.2	36.1
92.5°	13.4	19.2	27.1	32.0	39.4	49.7	74.5	109.2	140.3	142.3	120.3
95°	38.4	42.7	53.6	63.5	81.1	107.3	157.7	252.9	379.9	429.2	375.6
97.5°	62.4	68.3	79.9	94.8	115.0	144.8	208.0	340.7	551.9	732.7	768.6
100°	84.3	87.6	97.5	115.0	136.9	167.5	225.6	359.1	595.6	865.0	1022.7
102.5°	104.4	106.9	116.7	134.2	157.0	187.7	241.3	360.1	579.0	869.4	1117.3
105°	133.6	138.0	145.6	162.0	186.2	216.8	268.2	365.7	546.4	811.3	1102.6
107.5°	165.1	168.6	176.1	191.1	215.1	245.9	295.9	380.8	530.2	749.1	1006.4
110°	186.2	190.5	197.1	211.3	234.3	266.1	314.2	393.0	526.7	719.3	946.0



TEST NUMBER: P331284-830

CATALOG NUMBER: SA2XXDIP-C290D1080U830-4F0-1E-UDD-F4

CANDELA DISTRIBUTION (continued):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	205.4	209.8	217.3	230.5	252.7	285.3	331.8	406.2	527.5	700.1	904.0
115°	235.4	240.9	247.4	260.6	282.5	312.1	359.1	425.9	532.2	678.8	851.9
117.5°	266.6	270.9	277.5	289.1	310.1	340.7	384.3	447.0	540.0	668.5	819.0
120°	285.8	290.1	296.7	306.6	328.5	359.1	401.8	461.0	545.3	662.4	801.4
122.5°	304.2	307.6	314.2	325.0	346.9	378.4	418.5	473.3	551.4	658.9	786.6
125°	328.5	331.8	338.4	351.5	373.3	404.1	443.5	492.8	560.6	652.6	765.3
127.5°	347.7	352.1	361.4	375.8	396.8	428.3	466.7	510.9	570.0	648.8	745.6
130°	359.1	363.5	374.5	389.8	411.7	442.3	480.7	522.3	577.0	647.1	732.5
132.5°	369.7	374.9	386.7	402.9	425.7	456.4	492.9	533.7	584.0	646.2	722.0
135°	385.4	389.8	402.9	419.3	444.5	475.2	510.2	548.6	592.4	644.9	707.3
137.5°	400.3	405.6	418.7	436.2	461.2	489.7	524.2	560.0	599.8	644.7	697.0
140°	411.7	416.0	429.2	446.8	470.8	499.3	532.2	566.1	603.3	643.9	690.9
142.5°	423.1	426.6	438.8	456.4	479.6	506.3	538.3	571.4	606.0	643.9	684.8
145°	440.2	444.5	455.5	471.9	493.8	517.9	547.4	578.2	608.8	641.6	676.7
147.5°	458.5	461.8	472.3	487.5	505.7	527.1	554.9	581.8	609.6	637.7	668.4
150°	470.8	474.1	482.9	497.1	513.5	533.2	558.5	583.6	608.8	635.1	661.3
152.5°	483.1	484.7	493.3	505.9	521.4	539.3	561.9	584.5	607.0	630.7	655.2
155°	500.4	501.4	508.0	520.1	532.2	548.6	567.1	585.8	604.4	623.0	643.9
157.5°	514.8	515.9	521.2	531.7	541.3	555.2	570.9	585.8	599.4	615.1	633.1
160°	524.4	525.6	529.9	538.7	547.4	559.5	572.7	585.8	596.7	609.9	625.2
162.5°	534.1	533.5	537.8	544.8	552.7	562.1	573.5	584.9	594.1	605.5	618.2
165°	545.3	544.2	546.4	552.9	558.5	565.0	574.9	582.5	589.1	596.7	606.6
167.5°	554.5	553.2	555.2	559.3	563.3	567.4	574.6	581.0	584.0	589.1	595.2
170°	560.6	558.5	559.5	562.8	565.0	568.3	573.7	579.2	581.4	584.7	589.1
172.5°	564.1	562.8	562.1	565.4	566.8	569.1	572.9	576.6	577.9	579.5	583.0
175°	568.3	567.1	566.1	568.3	568.3	569.4	571.6	573.7	572.7	573.7	574.9
177.5°	570.2	568.4	567.6	569.4	569.4	569.4	570.2	572.0	570.2	569.4	570.2
180°	569.4	569.4	569.4	569.4	569.4	569.4	569.4	569.4	569.4	569.4	569.4



TEST NUMBER: P331284-830

CATALOG NUMBER: SA2XXDIP-C290D1080U830-4F0-1E-UDD-F4

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°
0°	445.3	445.3	445.3	445.3	445.3	445.3	445.3	445.3
2.5°	443.4	444.1	444.9	445.3	445.1	444.9	444.8	444.6
5°	440.5	441.2	442.0	442.2	442.1	441.9	441.7	441.5
7.5°	435.5	436.2	437.0	437.2	437.1	436.8	436.6	436.4
10°	431.0	431.8	432.5	432.7	432.4	432.2	431.9	431.6
12.5°	425.7	426.2	426.8	427.0	426.8	426.5	426.3	426.1
15°	416.5	416.9	417.3	417.3	416.8	416.3	415.8	415.4
17.5°	405.6	406.0	406.4	406.4	406.0	405.6	405.1	404.6
20°	397.1	397.4	397.7	397.6	397.2	396.8	396.4	396.1
22.5°	388.0	388.1	388.1	388.0	387.9	387.6	387.4	387.2
25°	373.3	373.5	373.7	373.7	373.5	373.3	373.2	373.0
27.5°	358.8	358.5	358.3	357.9	357.4	356.9	356.6	356.1
30°	347.5	347.2	346.9	346.7	346.3	345.9	345.5	345.1
32.5°	336.5	335.9	335.5	335.0	334.6	334.2	333.8	333.5
35°	318.7	318.1	317.5	317.1	316.6	316.1	315.7	315.1
37.5°	300.9	300.2	299.4	298.9	298.4	297.9	297.6	297.1
40°	288.6	287.8	286.9	286.3	285.9	285.5	285.1	284.7
42.5°	276.4	275.5	274.6	273.8	273.3	272.8	272.3	271.7
45°	257.8	256.7	255.7	255.0	254.6	254.2	253.8	253.4
47.5°	238.5	237.3	236.2	235.4	234.9	234.3	233.8	233.2
50°	226.0	224.6	223.3	222.4	222.0	221.5	221.0	220.6
52.5°	213.1	212.0	210.8	210.0	209.3	208.8	208.1	207.5
55°	193.8	192.7	191.5	190.8	190.3	189.7	189.3	188.8
57.5°	173.8	172.7	171.5	170.8	170.5	170.1	169.8	169.4
60°	160.6	159.6	158.5	157.9	157.6	157.3	157.0	156.7
62.5°	148.1	147.1	146.2	145.5	145.2	144.8	144.4	144.0
65°	128.8	128.0	127.1	126.5	126.0	125.5	125.1	124.6
67.5°	109.9	109.2	108.6	108.0	107.6	107.3	106.9	106.5
70°	97.6	96.9	96.2	95.8	95.4	94.9	94.5	94.2
72.5°	86.0	85.3	84.6	84.1	83.8	83.5	83.2	82.8
75°	67.8	67.2	66.6	66.4	66.6	66.8	67.0	67.2
77.5°	51.6	51.3	51.0	50.7	50.4	50.2	50.0	49.7
80°	41.0	40.7	40.4	40.2	40.0	39.8	39.6	39.4
82.5°	30.5	30.2	29.8	29.6	29.6	29.5	29.5	29.5
85°	16.1	15.8	15.6	15.4	15.3	15.2	15.1	15.0
87.5°	11.3	10.7	10.9	10.9	10.8	10.8	10.7	10.7
90°	35.1	32.9	35.1	36.1	36.1	36.1	36.1	36.1
92.5°	95.5	81.9	72.7	65.9	65.0	61.5	62.4	60.7
95°	286.9	220.1	174.1	150.0	135.7	127.1	123.8	124.8
97.5°	669.4	547.7	429.2	350.2	297.8	270.9	254.9	245.7
100°	999.7	863.9	713.9	581.4	490.5	443.5	411.7	392.0
102.5°	1216.1	1185.3	1075.6	935.3	836.5	756.2	716.5	689.8
105°	1330.3	1454.1	1468.3	1432.2	1364.2	1296.4	1249.3	1234.0
107.5°	1248.0	1434.4	1548.2	1601.2	1609.8	1606.0	1596.6	1576.2
110°	1177.0	1373.0	1513.2	1603.0	1650.0	1670.8	1680.7	1679.6



TEST NUMBER: P331284-830

CATALOG NUMBER: SA2XXDIP-C290D1080U830-4F0-1E-UDD-F4

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°
112.5°	1112.2	1300.3	1450.1	1553.0	1618.5	1653.3	1672.0	1677.8
115°	1032.6	1201.2	1344.5	1457.4	1535.1	1585.5	1613.9	1623.8
117.5°	972.5	1120.6	1250.7	1356.4	1435.7	1488.8	1518.9	1527.2
120°	942.7	1078.5	1194.6	1294.2	1370.8	1422.3	1454.1	1465.0
122.5°	919.1	1043.5	1153.4	1243.4	1312.1	1362.7	1391.0	1400.1
125°	884.7	997.5	1093.8	1175.9	1239.4	1281.1	1308.4	1317.2
127.5°	850.7	952.8	1043.7	1119.5	1174.9	1213.8	1237.5	1244.5
130°	828.9	923.0	1009.6	1081.8	1135.5	1172.7	1194.6	1203.3
132.5°	807.9	895.0	974.5	1042.4	1095.1	1132.4	1152.5	1160.4
135°	778.4	850.7	923.0	984.3	1031.4	1067.5	1087.2	1091.7
137.5°	755.1	815.5	872.9	926.3	969.2	1000.3	1017.7	1024.2
140°	740.2	792.8	843.1	891.3	926.3	954.8	971.2	977.8
142.5°	727.9	772.6	816.0	856.2	889.5	915.4	930.0	931.3
145°	710.6	746.8	780.7	812.5	838.7	857.3	868.3	871.6
147.5°	697.3	725.8	752.2	775.4	797.1	812.0	819.4	821.4
150°	687.6	711.7	734.7	754.4	770.8	784.0	790.5	791.6
152.5°	678.0	700.3	719.8	736.9	749.8	761.2	766.0	766.2
155°	664.6	682.1	698.5	710.6	722.6	730.3	734.7	732.5
157.5°	649.0	663.7	677.5	686.9	695.5	701.8	703.8	703.8
160°	639.4	651.5	663.5	671.2	678.8	684.3	685.4	685.4
162.5°	629.8	640.1	650.4	656.3	663.9	667.7	668.7	667.9
165°	615.4	623.0	630.7	635.1	639.4	643.9	643.9	642.7
167.5°	601.5	607.5	612.7	616.7	618.6	621.0	620.9	619.5
170°	594.6	597.9	602.2	604.4	605.5	608.8	607.7	605.5
172.5°	586.6	589.1	592.6	593.9	595.0	596.5	595.4	594.1
175°	578.2	579.2	580.3	581.4	581.4	582.5	581.4	579.2
177.5°	572.0	572.0	572.9	572.9	572.9	572.9	572.0	570.2
180°	569.4	569.4	569.4	569.4	569.4	569.4	569.4	569.4

(END OF REPORT)