

Scaled data based on original data using  
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State  
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P331246-830

Luminaire Tested: **SA2XXDIP-C290D330U830-4F0-1E-UDD-F**

Issue Date: 10/7/2019

**Test Information**

Test Method: LM-79-08  
Report Number: P331246-830  
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-2,  
Test Lab: INNOVATION CENTER  
Issue Date: 10/7/2019  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: NEO-RAY  
Catalog Number: SA2XXDIP-C290D330U830-4F0-1E-UDD-F  
Description: DEFINE 2 DIRECT-INDIRECT PENDANT LED LUMINAIRE  
DOWNLIGHT 290 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER  
UPLIGHT 330 LUMENS PER FOOT, NO LENS  
Light Source: -  
Ballast/Driver: ELECTRONIC DRIVER

**Summary**


Lumens per Lamp: N/A  
Luminaire Lumens: 2368.2 lumens  
Efficiency: N/A  
Efficacy: 116.7 lumens/watt  
Spacing Criteria (0/90/45): 1.2 / 1.16 / 1.3  
Luminous Opening: Rectangular (W 0.17' x L: 4' x H: 0')  
CIE Type: General Diffuse

Input Watts (W): 20.3  
Input Voltage (V): 120  
Input Current (Ain): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 25 FT



TEST NUMBER: P331246-830  
CATALOG NUMBER: SA2XXDIP-C290D330U830-4F0-1E-UDD-F

### Luminous Intensity Polar Plot





TEST NUMBER: P331246-830

CATALOG NUMBER: SA2XXDIP-C290D330U830-4F0-1E-UDD-F

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20					20					20					20					20	
RC	80					70					50					30					10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0	
RCR																						
0	107	107	107	107	98	98	98	98	82	82	82	68	68	68	54	54	54	48	48	48	48	
1	97	93	89	86	89	86	82	79	72	70	67	59	58	56	48	47	46	40	40	40	40	
2	89	81	75	70	81	75	70	65	63	59	56	52	49	47	42	40	39	34	34	34	34	
3	81	71	64	58	74	66	60	54	56	51	47	46	43	40	37	35	33	29	29	29	29	
4	74	63	55	49	68	58	51	46	49	44	40	41	37	34	33	31	28	25	25	25	25	
5	68	56	48	42	62	52	45	40	44	39	34	37	33	29	30	27	25	21	21	21	21	
6	62	50	42	37	57	47	40	34	40	34	30	33	29	26	27	24	22	19	19	19	19	
7	58	46	38	32	53	42	35	30	36	31	26	30	26	23	25	22	19	17	17	17	17	
8	54	41	34	28	49	38	32	27	33	27	24	28	23	20	23	20	17	15	15	15	15	
9	50	38	30	25	46	35	28	24	30	25	21	26	21	18	21	18	16	13	13	13	13	
10	47	35	27	23	43	32	26	21	28	23	19	24	19	17	20	16	14	12	12	12	12	

**AVERAGE LUMINANCE (cd/sqm):**

	0°	45°	90°
0°	7190	7190	7190
5°	7217	7112	7156
10°	7174	7040	7076
15°	7086	6950	6944
20°	6959	6813	6806
25°	6834	6645	6645
30°	6674	6490	6434
35°	6524	6303	6211
40°	6336	6119	6001
45°	6149	5934	5786
50°	5948	5745	5541
55°	5737	5520	5315
60°	5503	5254	5060
65°	5249	4989	4760
70°	4928	4669	4447
75°	4485	4298	4192
80°	3980	3868	3663
85°	3242	3094	2779



TEST NUMBER: P331246-830

CATALOG NUMBER: SA2XXDIP-C290D330U830-4F0-1E-UDD-F

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	41.9	1.8
10°-20°	117.8	5.0
20°-30°	173.2	7.3
30°-40°	201.2	8.5
40°-50°	200.9	8.5
50°-60°	175.2	7.4
60°-70°	129.6	5.5
70°-80°	73.4	3.1
80°-90°	20.8	0.9
90°-100°	14.0	0.6
100°-110°	51.5	2.2
110°-120°	137.7	5.8
120°-130°	227.3	9.6
130°-140°	241.8	10.2
140°-150°	224.7	9.5
150°-160°	180.7	7.6
160°-170°	116.4	4.9
170°-180°	40.1	1.7
0°-30°	332.9	14.1
0°-40°	534.0	22.6
0°-60°	910.2	38.4
0°-90°	1133.9	47.9
90°-120°	203.3	8.6
90°-150°	897.1	37.9
90°-180°	1234.0	52.1
0°-180°	2368.2	100.0

**CANDELA DISTRIBUTION:**

	0°	22.5°	45°	67.5°	90°	Flux
0°	445	445	445	445	445	
5°	445	443	439	442	442	42
15°	424	421	416	417	415	119
25°	384	380	373	374	373	176
35°	331	327	320	317	315	207
45°	269	266	260	255	253	208
55°	204	201	196	191	189	182
65°	137	135	131	127	125	136
75°	72	71	69	66	67	77
85°	18	17	17	16	15	20
90°	0	4	6	8	8	2
95°	20	10	12	13	13	24
105°	93	97	19	22	23	99
115°	175	181	188	54	25	172
125°	248	252	258	260	260	221
135°	307	311	314	317	317	237
145°	356	356	360	362	361	222
155°	392	389	392	394	392	180
165°	413	411	412	414	412	117
175°	422	420	421	422	420	40
180°	421	421	421	421	421	



TEST NUMBER: P331246-830

CATALOG NUMBER: SA2XXDIP-C290D330U830-4F0-1E-UDD-F

**CANDELA DISTRIBUTION (FULL):**

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	445.3	445.3	445.3	445.3	445.3	445.3	445.3	445.3	445.3	445.3	445.3
2.5°	447.3	447.0	446.6	446.2	445.8	445.3	444.4	443.6	442.7	441.9	442.6
5°	445.3	444.9	444.5	444.1	443.7	443.1	442.1	441.0	439.9	438.8	439.6
7.5°	441.4	440.7	440.2	439.6	439.0	438.2	437.2	436.0	435.0	433.9	434.7
10°	437.6	437.0	436.3	435.6	434.9	434.0	432.9	431.8	430.6	429.4	430.2
12.5°	432.4	431.9	431.3	430.6	430.1	429.2	428.1	427.0	425.8	424.7	425.2
15°	423.9	423.3	422.7	422.2	421.6	420.8	419.4	418.2	417.0	415.8	416.1
17.5°	412.9	412.4	411.8	411.2	410.7	409.7	408.5	407.2	406.0	404.7	405.1
20°	405.0	404.4	403.9	403.3	402.7	401.8	400.5	399.2	397.8	396.5	396.8
22.5°	397.2	396.3	395.6	394.7	394.0	392.9	391.7	390.4	389.2	388.0	388.0
25°	383.6	382.9	382.1	381.4	380.6	379.4	377.8	376.2	374.6	373.0	373.2
27.5°	368.3	367.6	366.8	366.2	365.5	364.5	363.3	361.9	360.7	359.4	359.1
30°	358.0	357.2	356.5	355.7	354.9	353.8	352.4	351.0	349.5	348.1	347.8
32.5°	346.9	346.4	345.8	345.2	344.6	343.5	342.0	340.5	339.0	337.5	337.0
35°	331.0	330.0	329.0	328.1	327.2	325.9	324.4	322.9	321.4	319.8	319.2
37.5°	312.9	312.1	311.2	310.4	309.5	308.4	306.9	305.4	303.8	302.3	301.6
40°	300.6	299.8	299.1	298.3	297.6	296.4	294.8	293.3	291.8	290.3	289.5
42.5°	288.6	287.9	287.1	286.3	285.6	284.4	282.9	281.3	279.8	278.3	277.4
45°	269.3	268.6	268.0	267.3	266.6	265.6	264.2	262.8	261.4	259.9	258.8
47.5°	250.2	249.5	248.9	248.3	247.6	246.6	245.1	243.6	242.1	240.6	239.5
50°	236.8	236.3	235.8	235.4	234.9	233.9	232.6	231.3	230.0	228.7	227.3
52.5°	223.8	223.1	222.5	221.9	221.2	220.3	219.0	217.8	216.5	215.3	214.1
55°	203.8	203.2	202.6	202.1	201.5	200.7	199.5	198.4	197.3	196.1	194.9
57.5°	183.8	183.3	182.9	182.4	181.9	181.1	179.8	178.6	177.3	176.1	174.9
60°	170.4	170.0	169.7	169.3	168.9	168.1	166.7	165.4	164.0	162.7	161.6
62.5°	157.4	156.7	156.2	155.6	155.0	154.1	153.1	152.1	151.1	150.1	149.0
65°	137.4	136.9	136.3	135.7	135.2	134.4	133.5	132.5	131.6	130.6	129.7
67.5°	117.2	116.7	116.2	115.7	115.4	114.7	113.8	112.9	112.1	111.2	110.6
70°	104.4	104.1	103.7	103.3	102.9	102.4	101.5	100.7	99.7	98.9	98.2
72.5°	91.4	91.0	90.7	90.3	89.9	89.4	88.9	88.4	87.8	87.3	86.6
75°	71.9	71.7	71.5	71.4	71.2	70.9	70.4	69.8	69.4	68.9	68.3
77.5°	54.5	54.1	53.8	53.5	53.2	52.9	52.7	52.5	52.3	52.1	51.8
80°	42.8	42.7	42.6	42.5	42.4	42.3	42.1	41.9	41.8	41.6	41.3
82.5°	31.9	31.9	31.9	31.8	31.8	31.7	31.6	31.5	31.4	31.3	30.9
85°	17.5	17.4	17.3	17.2	17.2	17.1	17.0	16.9	16.8	16.7	16.4
87.5°	6.2	6.2	6.2	6.2	6.2	6.2	6.1	6.1	6.0	6.0	5.8
90°	0.3	1.0	1.8	2.5	3.3	4.0	4.4	5.0	5.6	6.1	6.4
92.5°	6.1	6.1	6.0	5.9	5.8	6.0	6.2	6.5	6.8	7.1	7.3
95°	19.8	17.5	15.4	13.1	10.8	10.0	10.5	10.9	11.4	11.9	12.3
97.5°	39.3	33.0	26.7	20.5	14.1	11.5	12.6	13.7	14.8	15.9	16.2
100°	53.9	44.7	35.3	26.1	16.9	12.7	13.9	15.1	16.2	17.3	17.9
102.5°	70.0	68.1	66.1	64.2	62.2	56.4	46.8	37.1	27.5	17.8	18.6
105°	92.7	94.6	96.7	98.8	100.8	92.6	74.1	55.6	37.0	18.6	19.3
107.5°	118.4	120.1	121.7	123.4	125.0	114.7	92.6	70.4	48.2	26.0	25.3
110°	135.0	136.4	137.9	139.3	140.7	131.6	112.1	92.5	72.9	53.3	46.6



TEST NUMBER: P331246-830

CATALOG NUMBER: SA2XXDIP-C290D330U830-4F0-1E-UDD-F

**CANDELA DISTRIBUTION (continued):**

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	150.6	151.8	153.2	154.4	155.6	153.8	149.0	144.2	139.3	134.5	109.8
115°	175.2	176.3	177.6	178.7	179.8	181.3	182.9	184.6	186.3	188.0	156.7
117.5°	197.3	198.5	199.8	201.1	202.4	203.6	204.8	205.9	207.1	208.3	200.7
120°	213.3	214.3	215.4	216.4	217.4	218.5	219.7	220.9	222.2	223.4	224.2
122.5°	227.0	228.1	229.1	230.2	231.3	232.4	233.8	235.1	236.5	237.8	238.3
125°	247.8	248.6	249.5	250.4	251.3	252.4	253.6	255.0	256.2	257.5	258.0
127.5°	266.6	267.6	268.5	269.6	270.5	271.5	272.4	273.4	274.4	275.3	276.0
130°	278.5	279.7	280.7	281.8	282.9	283.8	284.6	285.3	286.1	286.8	287.5
132.5°	290.8	291.6	292.6	293.5	294.5	295.2	296.0	296.7	297.5	298.2	298.9
135°	306.6	307.6	308.8	309.8	310.9	311.8	312.4	313.0	313.6	314.2	314.9
137.5°	322.6	323.4	324.1	324.9	325.6	326.4	327.1	327.7	328.5	329.1	329.8
140°	333.1	333.7	334.1	334.7	335.3	335.9	336.7	337.4	338.2	338.8	339.5
142.5°	341.9	342.3	342.8	343.4	343.8	344.5	345.3	346.2	347.0	347.9	348.5
145°	355.6	355.6	355.5	355.4	355.3	355.9	357.0	358.3	359.4	360.5	361.0
147.5°	367.7	367.4	367.1	366.8	366.6	367.0	368.2	369.4	370.5	371.6	371.9
150°	375.4	374.9	374.5	374.0	373.5	373.9	374.9	376.1	377.1	378.2	378.6
152.5°	382.0	381.5	381.0	380.4	379.9	380.1	381.2	382.2	383.2	384.3	384.7
155°	391.6	391.0	390.4	389.7	389.2	389.3	390.1	390.9	391.7	392.5	392.9
157.5°	399.1	398.6	398.0	397.6	397.0	397.1	397.7	398.2	398.8	399.4	399.8
160°	403.5	403.1	402.7	402.3	401.9	401.9	402.3	402.7	403.1	403.5	403.9
162.5°	407.4	407.0	406.6	406.1	405.8	405.8	406.0	406.4	406.8	407.2	407.6
165°	412.6	412.3	411.8	411.4	411.0	410.9	411.1	411.3	411.5	411.7	412.2
167.5°	416.5	416.1	415.8	415.3	414.9	414.8	415.0	415.2	415.4	415.6	416.0
170°	418.8	418.3	417.9	417.5	417.1	417.0	417.1	417.3	417.4	417.5	418.0
172.5°	420.2	419.8	419.3	419.0	418.6	418.4	418.6	418.7	418.9	419.0	419.4
175°	422.1	421.6	421.1	420.7	420.2	420.0	420.2	420.3	420.5	420.6	421.0
177.5°	422.4	422.0	421.6	421.2	420.8	420.8	420.8	420.8	420.8	420.9	421.3
180°	421.1	421.1	421.1	421.1	421.1	421.1	421.1	421.1	421.1	421.1	421.1



TEST NUMBER: P331246-830

CATALOG NUMBER: SA2XXDIP-C290D330U830-4F0-1E-UDD-F

**CANDELA DISTRIBUTION (continued):**

	55°	60°	65°	70°	75°	80°	85°	90°
0°	445.3	445.3	445.3	445.3	445.3	445.3	445.3	445.3
2.5°	443.4	444.1	444.9	445.3	445.1	444.9	444.8	444.6
5°	440.5	441.2	442.0	442.2	442.1	441.9	441.7	441.5
7.5°	435.5	436.2	437.0	437.2	437.1	436.8	436.6	436.4
10°	431.0	431.8	432.5	432.7	432.4	432.2	431.9	431.6
12.5°	425.7	426.2	426.8	427.0	426.8	426.5	426.3	426.1
15°	416.5	416.9	417.3	417.3	416.8	416.3	415.8	415.4
17.5°	405.6	406.0	406.4	406.4	406.0	405.6	405.1	404.6
20°	397.1	397.4	397.7	397.6	397.2	396.8	396.4	396.1
22.5°	388.0	388.1	388.1	388.0	387.9	387.6	387.4	387.2
25°	373.3	373.5	373.7	373.7	373.5	373.3	373.2	373.0
27.5°	358.8	358.5	358.3	357.9	357.4	356.9	356.6	356.1
30°	347.5	347.2	346.9	346.7	346.3	345.9	345.5	345.1
32.5°	336.5	335.9	335.5	335.0	334.6	334.2	333.8	333.5
35°	318.7	318.1	317.5	317.1	316.6	316.1	315.7	315.1
37.5°	300.9	300.2	299.4	298.9	298.4	297.9	297.6	297.1
40°	288.6	287.8	286.9	286.3	285.9	285.5	285.1	284.7
42.5°	276.4	275.5	274.6	273.8	273.3	272.8	272.3	271.7
45°	257.8	256.7	255.7	255.0	254.6	254.2	253.8	253.4
47.5°	238.5	237.3	236.2	235.4	234.9	234.3	233.8	233.2
50°	226.0	224.6	223.3	222.4	222.0	221.5	221.0	220.6
52.5°	213.1	212.0	210.8	210.0	209.3	208.8	208.1	207.5
55°	193.8	192.7	191.5	190.8	190.3	189.7	189.3	188.8
57.5°	173.8	172.7	171.5	170.8	170.5	170.1	169.8	169.4
60°	160.6	159.6	158.5	157.9	157.6	157.3	157.0	156.7
62.5°	148.1	147.1	146.2	145.5	145.2	144.8	144.4	144.0
65°	128.8	128.0	127.1	126.5	126.0	125.5	125.1	124.6
67.5°	109.9	109.2	108.6	108.0	107.6	107.3	106.9	106.5
70°	97.6	96.9	96.2	95.8	95.4	94.9	94.5	94.2
72.5°	86.0	85.3	84.6	84.1	83.8	83.5	83.2	82.8
75°	67.8	67.2	66.6	66.4	66.6	66.8	67.0	67.2
77.5°	51.6	51.3	51.0	50.7	50.4	50.2	50.0	49.7
80°	41.0	40.7	40.4	40.2	40.0	39.8	39.6	39.4
82.5°	30.5	30.2	29.8	29.6	29.6	29.5	29.5	29.5
85°	16.1	15.8	15.6	15.4	15.3	15.2	15.1	15.0
87.5°	5.7	5.6	5.4	5.3	5.2	5.2	5.1	5.1
90°	6.8	7.1	7.4	7.7	7.8	7.9	8.1	8.2
92.5°	7.4	7.6	7.7	7.9	8.0	8.1	8.1	8.2
95°	12.5	12.9	13.2	13.4	13.3	13.2	13.2	13.1
97.5°	16.5	16.7	17.0	17.2	17.2	17.3	17.4	17.5
100°	18.5	19.0	19.5	19.9	20.0	20.2	20.3	20.5
102.5°	19.2	20.0	20.6	21.1	21.3	21.5	21.7	21.9
105°	20.1	20.8	21.6	22.1	22.3	22.6	22.9	23.2
107.5°	24.5	23.8	23.0	22.7	23.0	23.3	23.6	23.8
110°	39.8	33.0	26.2	23.0	23.3	23.6	23.8	24.0





TEST NUMBER: P331246-830

CATALOG NUMBER: SA2XXDIP-C290D330U830-4F0-1E-UDD-F

**CANDELA DISTRIBUTION (continued):**

	55°	60°	65°	70°	75°	80°	85°	90°
112.5°	85.1	60.4	35.7	23.5	23.7	23.8	24.1	24.3
115°	125.4	94.0	62.6	44.5	39.6	34.8	29.9	25.0
117.5°	193.1	185.5	178.0	166.2	150.1	134.1	118.1	102.1
120°	225.0	225.8	226.6	222.4	213.3	204.2	195.0	185.9
122.5°	238.7	239.2	239.7	239.0	237.3	235.5	233.8	232.0
125°	258.4	258.9	259.4	259.8	260.0	260.1	260.3	260.5
127.5°	276.7	277.4	278.1	278.4	278.5	278.5	278.5	278.6
130°	288.2	289.0	289.7	290.1	290.0	289.9	289.9	289.8
132.5°	299.5	300.1	300.8	301.0	301.0	301.0	300.9	300.8
135°	315.6	316.2	316.9	317.2	317.1	316.9	316.8	316.6
137.5°	330.5	331.1	331.8	332.0	331.8	331.6	331.3	331.1
140°	340.1	340.7	341.3	341.5	341.1	340.8	340.4	340.1
142.5°	349.0	349.6	350.2	350.2	349.9	349.6	349.2	348.8
145°	361.5	361.9	362.4	362.5	362.1	361.8	361.5	361.1
147.5°	372.3	372.7	373.1	373.1	372.8	372.5	372.2	371.9
150°	379.0	379.4	379.8	379.8	379.6	379.2	378.8	378.5
152.5°	385.1	385.5	385.9	385.9	385.4	385.0	384.6	384.1
155°	393.3	393.7	394.2	394.1	393.5	393.0	392.5	391.9
157.5°	400.3	400.8	401.1	401.1	400.6	400.1	399.5	399.1
160°	404.4	404.7	405.1	405.1	404.6	404.2	403.7	403.2
162.5°	408.0	408.5	409.0	409.0	408.3	407.7	407.2	406.6
165°	412.6	413.1	413.6	413.6	413.1	412.6	412.2	411.7
167.5°	416.5	417.0	417.5	417.4	416.8	416.1	415.6	414.9
170°	418.5	419.0	419.4	419.3	418.8	418.1	417.5	416.9
172.5°	419.9	420.4	420.8	420.8	420.2	419.6	419.0	418.4
175°	421.5	422.0	422.4	422.4	421.7	421.0	420.3	419.6
177.5°	421.7	422.1	422.4	422.4	421.9	421.4	420.9	420.5
180°	421.1	421.1	421.1	421.1	421.1	421.1	421.1	421.1

(END OF REPORT)