

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P333141-840

Luminaire Tested: **S125DIP-S375D810U840-4F0-1E-UDD-F4**

Issue Date: 3/3/2020

Test Information

Test Method: LM-79-08
Report Number: P333141-840
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-19,
Test Lab: INNOVATION CENTER
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: NEO-RAY
Catalog Number: S125DIP-S375D810U840-4F0-1E-UDD-F4
Description: DEFINE 5 DIRECT-INDIRECT PENDANT LED LUMINAIRE
DOWNLIGHT 375 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER
UPLIGHT 810 LUMENS PER FOOT, BATWING OPTIC
Light Source: -
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 4474.3 lumens
Efficiency: N/A
Efficacy: 143.4 lumens/watt
Spacing Criteria (0/90/45): 1.21 / 1.18 / 1.31
Luminous Opening: Rectangular (W 0.42' x L: 4' x H: 0')
CIE Type: Semi-Indirect


Input Watts (W): 31.2
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P333141-840

CATALOG NUMBER: S125DIP-S375D810U840-4F0-1E-UDD-F4

Luminous Intensity Polar Plot





TEST NUMBER: P333141-840

CATALOG NUMBER: S125DIP-S375D810U840-4F0-1E-UDD-F4

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10
RCR																	
0	103	103	103	103	93	93	93	93	75	75	75	58	58	58	42	42	42
1	94	90	86	83	85	81	78	75	65	63	61	50	49	48	37	36	35
2	86	79	73	67	77	71	66	62	57	54	50	44	42	40	32	31	30
3	78	69	62	56	70	62	56	51	50	46	42	39	36	34	29	27	25
4	71	61	53	47	64	55	49	43	45	40	36	35	31	29	26	23	22
5	65	54	46	40	59	49	42	37	40	35	31	31	28	25	23	21	19
6	60	48	41	35	54	44	37	32	36	31	27	28	24	22	21	18	16
7	56	44	36	30	50	40	33	28	32	27	24	25	22	19	19	17	15
8	52	40	32	27	46	36	29	25	29	24	21	23	20	17	17	15	13
9	48	36	29	24	43	33	26	22	27	22	19	21	18	15	16	14	12
10	45	33	26	21	40	30	24	20	25	20	17	20	16	14	15	12	11

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	3810	3810	3810
5°	3818	3782	3806
10°	3796	3756	3777
15°	3754	3710	3726
20°	3696	3647	3654
25°	3632	3572	3569
30°	3554	3491	3473
35°	3470	3404	3356
40°	3384	3309	3262
45°	3291	3222	3159
50°	3189	3118	3024
55°	3090	3001	2916
60°	2971	2882	2780
65°	2832	2740	2647
70°	2696	2574	2485
75°	2458	2376	2293
80°	2187	2153	2101
85°	1904	1941	1830



TEST NUMBER: P333141-840

CATALOG NUMBER: S125DIP-S375D810U840-4F0-1E-UDD-F4

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	55.6	1.2
10°-20°	157.1	3.5
20°-30°	232.0	5.2
30°-40°	270.7	6.1
40°-50°	271.9	6.1
50°-60°	238.7	5.3
60°-70°	177.8	4.0
70°-80°	101.7	2.3
80°-90°	31.8	0.7
90°-100°	283.9	6.3
100°-110°	610.3	13.6
110°-120°	572.7	12.8
120°-130°	464.2	10.4
130°-140°	372.5	8.3
140°-150°	281.1	6.3
150°-160°	197.9	4.4
160°-170°	116.6	2.6
170°-180°	37.9	0.8
0°-30°	444.7	9.9
0°-40°	715.5	16.0
0°-60°	1226.0	27.4
0°-90°	1537.3	34.4
90°-120°	1466.9	32.8
90°-150°	2584.6	57.8
90°-180°	2937.0	65.6
0°-180°	4474.3	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	590	590	590	590	590	
5°	589	588	583	587	587	56
15°	562	560	555	557	557	158
25°	510	507	501	502	501	234
35°	440	438	432	429	426	275
45°	360	358	353	348	346	278
55°	274	273	266	262	259	245
65°	185	184	179	175	173	184
75°	98	98	95	94	92	105
85°	26	26	26	26	25	29
90°	1	7	13	17	18	3
95°	26	77	700	317	186	28
105°	89	125	572	1127	1046	94
115°	160	192	460	991	1166	157
125°	221	259	441	788	918	196
135°	259	311	438	660	763	201
145°	302	346	439	547	602	189
155°	344	370	428	484	504	158
165°	376	386	411	436	442	106
175°	391	391	394	399	397	37
180°	392	392	392	392	392	



TEST NUMBER: P333141-840

CATALOG NUMBER: S125DIP-S375D810U840-4F0-1E-UDD-F4

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	590.0	590.0	590.0	590.0	590.0	590.0	590.0	590.0	590.0	590.0	590.0
2.5°	591.4	591.2	591.0	590.7	590.5	589.9	589.1	588.2	587.4	586.5	587.4
5°	589.0	588.8	588.5	588.3	588.1	587.5	586.5	585.5	584.4	583.4	584.3
7.5°	583.6	583.4	583.2	583.0	582.8	582.1	581.0	579.8	578.7	577.5	578.5
10°	578.8	578.6	578.3	578.1	577.9	577.2	576.1	574.9	573.8	572.7	573.5
12.5°	572.8	572.4	572.0	571.7	571.3	570.6	569.5	568.5	567.3	566.3	566.9
15°	561.5	561.2	560.9	560.6	560.2	559.5	558.4	557.2	556.0	554.9	555.4
17.5°	548.5	548.1	547.5	547.1	546.6	545.8	544.6	543.5	542.3	541.1	541.8
20°	537.7	537.5	537.2	537.0	536.8	536.0	534.7	533.3	532.0	530.7	531.4
22.5°	526.8	526.4	526.0	525.7	525.3	524.5	523.2	522.0	520.7	519.5	520.0
25°	509.7	509.2	508.6	508.1	507.6	506.6	505.3	503.9	502.6	501.3	501.5
27.5°	489.6	489.3	489.0	488.7	488.4	487.5	486.1	484.7	483.3	481.9	482.0
30°	476.6	476.3	475.8	475.5	475.2	474.3	472.8	471.2	469.7	468.1	467.9
32.5°	462.3	461.8	461.4	460.9	460.4	459.5	458.1	456.7	455.3	453.9	453.5
35°	440.1	439.7	439.3	438.9	438.5	437.5	436.1	434.6	433.1	431.7	431.2
37.5°	417.1	416.6	416.1	415.5	415.0	414.0	412.6	411.3	409.9	408.6	407.8
40°	401.4	400.8	400.3	399.8	399.3	398.3	396.9	395.5	393.9	392.5	391.6
42.5°	384.6	384.2	383.7	383.2	382.8	381.9	380.4	379.0	377.5	376.1	375.3
45°	360.3	359.9	359.5	359.1	358.6	357.8	356.6	355.4	354.1	352.8	351.6
47.5°	334.2	334.2	334.2	334.3	334.3	333.6	332.0	330.5	329.0	327.5	326.3
50°	317.4	317.1	316.8	316.4	316.1	315.4	314.1	312.9	311.6	310.3	309.0
52.5°	300.2	299.9	299.7	299.5	299.3	298.5	297.2	295.9	294.5	293.2	292.1
55°	274.4	274.1	273.8	273.5	273.2	272.3	270.8	269.4	267.9	266.5	265.6
57.5°	247.3	247.1	246.9	246.8	246.6	245.9	244.7	243.5	242.3	241.1	239.8
60°	230.0	229.6	229.2	228.8	228.4	227.6	226.5	225.4	224.2	223.1	222.1
62.5°	212.2	211.9	211.5	211.2	210.9	210.2	209.2	208.2	207.2	206.3	205.2
65°	185.3	185.1	184.9	184.7	184.5	183.8	182.7	181.5	180.4	179.3	178.2
67.5°	159.3	158.9	158.3	157.9	157.5	156.8	156.0	155.1	154.3	153.5	152.7
70°	142.8	142.3	141.8	141.3	140.8	140.0	139.1	138.1	137.2	136.3	135.6
72.5°	124.9	124.5	124.2	123.8	123.5	123.0	122.4	121.8	121.2	120.6	119.9
75°	98.5	98.3	98.1	97.9	97.7	97.3	96.7	96.2	95.7	95.2	94.9
77.5°	74.1	74.0	73.9	73.8	73.8	73.6	73.3	73.0	72.7	72.4	72.2
80°	58.8	58.8	58.8	58.8	58.8	58.7	58.5	58.3	58.1	57.9	57.8
82.5°	45.3	45.2	45.0	44.8	44.7	44.6	44.5	44.5	44.4	44.4	44.2
85°	25.7	25.8	25.9	26.0	26.1	26.2	26.2	26.2	26.2	26.2	26.1
87.5°	10.2	10.4	10.7	11.0	11.3	11.6	11.7	11.9	12.0	12.2	12.4
90°	0.8	1.6	3.1	4.7	6.4	7.9	8.7	10.3	11.0	12.6	13.4
92.5°	9.6	11.7	18.3	28.1	41.7	64.7	107.9	180.2	258.6	254.6	206.1
95°	26.1	26.9	33.1	41.8	59.2	94.7	179.3	352.9	570.9	699.6	684.6
97.5°	43.2	44.2	48.7	57.4	72.9	98.6	154.4	281.8	509.8	747.1	866.2
100°	55.2	56.9	60.0	68.7	83.7	107.3	153.2	255.8	454.8	713.1	910.4
102.5°	68.6	69.5	72.0	81.3	95.0	118.2	158.9	245.1	413.1	653.0	883.9
105°	89.3	89.3	93.2	101.1	113.7	135.8	170.6	240.9	372.7	572.5	799.1
107.5°	109.5	111.0	114.8	121.3	134.4	154.3	187.9	248.1	355.7	517.1	712.6
110°	124.0	125.5	128.7	135.8	147.6	168.1	200.6	255.1	350.6	491.1	663.3



TEST NUMBER: P333141-840

CATALOG NUMBER: S125DIP-S375D810U840-4F0-1E-UDD-F4

CANDELA DISTRIBUTION (continued):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	138.5	140.1	142.6	149.7	161.6	181.5	212.6	263.9	350.6	475.9	626.6
115°	159.5	161.1	163.5	170.6	182.4	202.2	231.4	277.1	352.9	459.6	586.6
117.5°	178.4	180.9	183.4	190.5	203.9	223.0	250.6	292.4	358.2	451.5	562.8
120°	191.1	193.5	196.6	203.7	217.1	236.9	264.5	302.5	363.2	447.7	549.6
122.5°	204.4	206.1	208.6	215.7	230.5	250.1	277.8	313.8	367.6	444.5	538.2
125°	221.1	222.7	226.6	233.7	248.7	269.2	295.3	329.2	375.1	440.6	522.7
127.5°	234.2	236.6	241.7	250.6	266.6	287.1	312.3	343.5	383.4	438.7	508.5
130°	242.4	244.8	251.1	261.4	277.9	298.5	323.0	352.9	388.5	437.5	499.1
132.5°	248.7	251.8	259.3	270.8	288.0	308.6	333.1	361.1	394.2	437.5	491.5
135°	259.0	262.2	271.7	284.3	300.8	322.1	346.7	372.7	401.9	437.5	482.4
137.5°	272.0	274.3	283.2	295.8	312.0	334.0	356.3	381.2	409.0	438.4	474.4
140°	279.5	281.9	291.3	304.0	319.0	340.3	363.2	386.9	412.1	439.0	470.6
142.5°	288.3	290.1	298.9	311.5	326.0	346.0	367.6	390.1	414.0	439.7	467.5
145°	301.6	303.2	311.1	322.1	336.4	354.6	375.1	394.8	416.2	439.0	462.7
147.5°	315.5	316.5	323.3	333.6	345.9	361.8	379.8	397.7	416.9	437.0	457.8
150°	323.8	325.3	330.8	341.1	352.1	365.6	382.9	399.5	416.9	435.0	454.0
152.5°	332.5	333.6	338.4	347.4	357.9	370.0	386.1	400.8	416.3	432.5	449.6
155°	344.3	344.3	349.0	356.9	364.8	375.9	389.3	401.9	414.5	428.0	442.2
157.5°	354.7	354.6	358.3	365.1	372.0	380.4	391.9	402.7	412.5	423.2	435.3
160°	361.6	360.8	364.1	369.5	375.9	382.9	393.2	402.7	410.6	420.1	429.6
162.5°	367.3	366.6	369.7	374.6	379.6	385.5	394.5	402.0	408.7	416.3	424.4
165°	375.9	374.3	376.7	380.6	383.7	388.5	394.8	401.1	405.9	410.6	416.9
167.5°	381.5	380.7	382.1	384.4	386.6	389.6	394.8	399.2	401.4	405.1	409.5
170°	385.4	384.6	385.4	386.9	388.5	390.8	394.8	398.0	399.5	401.9	405.1
172.5°	387.9	386.5	387.2	388.8	389.7	390.8	394.2	396.7	397.0	398.1	400.6
175°	390.8	389.3	390.1	390.8	390.8	390.8	393.2	394.8	394.0	394.0	394.8
177.5°	392.2	391.0	391.0	391.6	391.0	391.0	392.2	392.9	391.6	391.6	392.2
180°	391.6	391.6	391.6	391.6	391.6	391.6	391.6	391.6	391.6	391.6	391.6



TEST NUMBER: P333141-840

CATALOG NUMBER: S125DIP-S375D810U840-4F0-1E-UDD-F4

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°
0°	590.0	590.0	590.0	590.0	590.0	590.0	590.0	590.0
2.5°	588.2	589.1	589.9	590.3	590.2	590.1	590.1	590.0
5°	585.2	586.2	587.1	587.5	587.4	587.3	587.2	587.1
7.5°	579.4	580.3	581.2	581.6	581.5	581.4	581.3	581.2
10°	574.3	575.1	576.0	576.3	576.2	576.1	576.0	575.9
12.5°	567.6	568.4	569.0	569.3	569.3	569.3	569.3	569.2
15°	555.9	556.4	557.0	557.2	557.2	557.2	557.2	557.2
17.5°	542.4	543.0	543.7	543.7	543.2	542.7	542.2	541.7
20°	532.1	532.8	533.5	533.7	533.1	532.6	532.1	531.6
22.5°	520.4	520.9	521.4	521.4	521.1	520.7	520.4	520.0
25°	501.7	501.9	502.1	502.0	501.7	501.4	501.1	500.8
27.5°	482.0	482.0	482.1	482.0	481.6	481.3	481.0	480.7
30°	467.7	467.5	467.3	467.1	466.8	466.5	466.1	465.7
32.5°	453.2	452.8	452.4	452.0	451.4	450.8	450.3	449.7
35°	430.7	430.2	429.6	429.0	428.2	427.3	426.5	425.7
37.5°	407.1	406.3	405.5	404.9	404.3	403.9	403.4	402.9
40°	390.6	389.7	388.8	388.2	387.9	387.5	387.2	386.9
42.5°	374.4	373.5	372.6	372.0	371.5	371.0	370.6	370.1
45°	350.3	349.1	347.9	347.1	346.8	346.5	346.2	345.9
47.5°	325.0	323.8	322.4	321.4	320.7	320.0	319.3	318.6
50°	307.7	306.3	305.0	304.0	303.2	302.5	301.7	301.0
52.5°	290.8	289.6	288.4	287.5	286.7	285.9	285.1	284.3
55°	264.6	263.7	262.8	262.0	261.3	260.4	259.7	259.0
57.5°	238.6	237.4	236.2	235.4	235.0	234.6	234.2	233.8
60°	221.1	219.9	218.9	218.0	217.3	216.6	215.9	215.2
62.5°	204.1	202.9	201.8	201.0	200.5	199.9	199.2	198.7
65°	177.3	176.4	175.5	174.8	174.4	174.0	173.6	173.2
67.5°	151.9	151.1	150.3	149.8	149.6	149.3	149.1	148.8
70°	135.0	134.4	133.8	133.3	132.9	132.5	132.0	131.6
72.5°	119.2	118.5	117.8	117.2	116.8	116.4	115.9	115.5
75°	94.6	94.3	93.9	93.6	93.2	92.8	92.4	91.9
77.5°	72.1	71.9	71.7	71.5	71.2	70.9	70.6	70.3
80°	57.7	57.6	57.5	57.3	57.1	56.9	56.7	56.5
82.5°	44.0	43.8	43.7	43.5	43.5	43.5	43.4	43.4
85°	26.0	25.9	25.8	25.5	25.3	25.1	24.9	24.7
87.5°	12.5	12.7	12.8	13.1	12.9	12.7	12.7	12.6
90°	14.2	15.0	15.8	17.4	17.4	17.4	18.2	18.2
92.5°	140.0	101.6	76.4	64.7	54.6	52.7	51.6	50.4
95°	567.7	447.7	350.6	284.3	228.2	204.5	198.2	185.5
97.5°	845.6	761.3	666.7	574.5	525.7	481.5	458.6	448.5
100°	971.2	932.5	851.2	769.1	714.6	657.7	628.5	615.9
102.5°	1013.5	1037.4	998.4	942.8	884.5	844.0	812.3	802.8
105°	988.6	1096.8	1131.6	1122.9	1097.5	1071.5	1055.7	1046.2
107.5°	899.5	1043.9	1133.1	1174.3	1187.1	1186.9	1181.7	1175.4
110°	833.8	983.8	1095.2	1162.3	1197.8	1212.8	1218.4	1218.4



TEST NUMBER: P333141-840

CATALOG NUMBER: S125DIP-S375D810U840-4F0-1E-UDD-F4

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°
112.5°	782.0	924.4	1037.0	1116.2	1168.1	1193.9	1207.6	1213.4
115°	717.0	839.4	947.6	1033.6	1095.2	1133.1	1155.2	1165.5
117.5°	675.0	780.4	873.6	952.6	1014.2	1053.3	1075.3	1081.6
120°	652.2	747.0	833.8	903.3	961.7	999.7	1021.0	1027.2
122.5°	635.2	723.0	800.3	865.5	917.6	952.3	973.6	979.3
125°	610.4	690.9	759.6	816.5	860.7	893.0	910.4	918.3
127.5°	585.1	660.2	724.4	777.6	817.7	846.3	862.7	866.2
130°	569.3	638.8	700.3	751.7	791.2	817.3	833.0	837.8
132.5°	553.5	618.5	674.5	723.9	763.4	789.4	804.0	809.3
135°	533.0	587.4	638.0	683.0	717.7	743.8	758.0	762.8
137.5°	515.6	559.7	601.7	639.9	671.1	694.7	707.8	713.1
140°	506.1	543.2	579.6	612.7	642.0	662.5	674.3	678.2
142.5°	498.0	529.4	560.6	589.4	614.2	631.6	642.8	646.0
145°	487.2	511.7	536.1	557.4	576.4	589.9	598.5	601.7
147.5°	477.1	497.0	515.7	531.9	546.8	557.6	562.7	564.1
150°	471.4	488.8	503.7	518.0	529.9	539.3	542.5	543.2
152.5°	465.0	480.6	494.3	505.3	515.3	522.9	526.0	526.8
155°	455.7	468.3	479.3	488.0	495.8	501.4	503.7	504.5
157.5°	446.2	456.6	465.0	471.9	478.1	482.6	484.8	484.6
160°	439.8	447.7	455.7	461.1	466.7	470.6	472.2	471.4
162.5°	432.8	440.1	446.8	451.6	456.0	459.2	459.6	459.4
165°	423.2	428.8	433.5	437.5	440.6	442.2	442.2	442.2
167.5°	414.0	417.7	421.3	424.1	425.8	427.2	426.6	426.4
170°	409.0	411.4	413.7	415.4	416.9	417.7	417.7	416.9
172.5°	403.3	405.7	407.5	408.4	408.7	410.1	408.9	408.1
175°	397.2	397.2	398.8	398.8	398.8	399.5	398.0	397.2
177.5°	392.9	393.5	393.5	393.5	392.9	393.5	391.6	391.6
180°	391.6	391.6	391.6	391.6	391.6	391.6	391.6	391.6

(END OF REPORT)