

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P333189-840

Luminaire Tested: **S125DIP-S610D1035U840-4F0-1E-UDD-A4**

Issue Date: 3/3/2020

Test Information

Test Method: LM-79-08
Report Number: P333189-840
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-19,
Test Lab: INNOVATION CENTER
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: NEO-RAY
Catalog Number: S125DIP-S610D1035U840-4F0-1E-UDD-A4
Description: DEFINE 5 DIRECT-INDIRECT PENDANT LED LUMINAIRE
DOWNLIGHT 610 LUMENS PER FOOT, ASYMMETRIC DIFFUSER
UPLIGHT 1035 LUMENS PER FOOT, BATWING OPTIC
Light Source: -
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 6303.0 lumens
Efficiency: N/A
Efficacy: 141.6 lumens/watt
Spacing Criteria (0/90/45): 1.43 / 1.23 / 1.52
Luminous Opening: Rectangular (W 4' x L: 0.42' x H: 0')
CIE Type: General Diffuse


Input Watts (W): 44.5
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P333189-840

CATALOG NUMBER: S125DIP-S610D1035U840-4F0-1E-UDD-A4

Luminous Intensity Polar Plot





TEST NUMBER: P333189-840

CATALOG NUMBER: S125DIP-S610D1035U840-4F0-1E-UDD-A4

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	105	105	105	105	96	96	96	96	78	78	78	62	62	62	47	47	47	41
1	96	92	88	84	87	84	80	78	69	66	64	55	53	52	42	41	40	34
2	87	80	74	69	79	73	68	64	60	57	54	48	46	44	37	36	34	29
3	80	71	63	58	72	65	58	54	53	49	45	43	40	37	33	31	29	25
4	73	62	55	49	66	57	51	45	47	42	39	38	35	32	30	27	25	21
5	67	56	48	42	61	51	44	39	42	37	33	34	31	28	27	24	22	19
6	62	50	42	36	56	46	39	34	38	33	29	31	27	24	24	22	19	16
7	57	45	37	32	52	41	34	30	35	29	25	28	24	21	22	19	17	15
8	53	41	33	28	48	38	31	26	31	26	23	26	22	19	20	18	15	13
9	49	37	30	25	45	34	28	23	29	24	20	24	20	17	19	16	14	12
10	46	34	27	22	42	31	25	21	26	21	18	22	18	15	17	15	13	11

AVERAGE LUMINANCE (cd/sqm):

	0°	90°	180°	270°
0°	5837	5837	5837	5837
5°	6760	5857	5128	5857
10°	7864	5827	4494	5827
15°	8705	5784	4145	5784
20°	9745	5716	3865	5716
25°	11416	5640	3729	5640
30°	12331	5565	3610	5565
35°	10138	5423	3533	5423
40°	7206	5227	3447	5227
45°	5536	4961	3399	4961
50°	4725	4633	3392	4633
55°	4208	4310	3422	4310
60°	3796	3959	3509	3959
65°	3506	3605	3599	3605
70°	3186	3238	3652	3238
75°	2815	2852	3618	2852
80°	2369	2325	3310	2325
85°	1875	1675	2675	1675



TEST NUMBER: P333189-840

CATALOG NUMBER: S125DIP-S610D1035U840-4F0-1E-UDD-A4

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	87.0	1.4
10°-20°	259.1	4.1
20°-30°	420.7	6.7
30°-40°	513.1	8.1
40°-50°	466.8	7.4
50°-60°	371.8	5.9
60°-70°	259.0	4.1
70°-80°	138.1	2.2
80°-90°	37.6	0.6
90°-100°	362.4	5.8
100°-110°	779.1	12.4
110°-120°	731.2	11.6
120°-130°	592.6	9.4
130°-140°	475.6	7.5
140°-150°	358.9	5.7
150°-160°	252.6	4.0
160°-170°	148.9	2.4
170°-180°	48.4	0.8
0°-30°	766.7	12.2
0°-40°	1279.9	20.3
0°-60°	2118.5	33.6
0°-90°	2553.2	40.5
90°-120°	1872.8	29.7
90°-150°	3299.8	52.4
90°-180°	3750.0	59.5
0°-180°	6303.0	100.0

CANDELA DISTRIBUTION:

	0°	90°	180°	270°	360°	Flux
0°	904	904	904	904	904	
5°	1043	903	791	903	1043	105
15°	1302	865	620	865	1302	373
25°	1602	791	523	791	1602	732
35°	1286	688	448	688	1286	787
45°	606	543	372	543	606	485
55°	374	383	304	383	374	337
65°	229	236	236	236	229	228
75°	113	114	145	114	113	121
85°	25	23	36	23	25	30
90°	23	1	23	1	23	17
95°	237	33	237	33	237	336
105°	1336	114	1336	114	1336	1328
115°	1488	204	1488	204	1488	1454
125°	1172	282	1172	282	1172	1061
135°	974	331	974	331	974	755
145°	768	385	768	385	768	488
155°	644	440	644	440	644	300
165°	564	480	564	480	564	161
175°	507	499	507	499	507	49
180°	500	500	500	500	500	



TEST NUMBER: P333189-840

CATALOG NUMBER: S125DIP-S610D1035U840-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	903.8	903.8	903.8	903.8	903.8	903.8	903.8	903.8	903.8	903.8	903.8
2.5°	956.0	954.7	953.5	951.1	952.9	947.7	945.2	941.0	935.7	933.9	931.7
5°	1042.7	1044.6	1046.5	1038.4	1039.3	1033.9	1021.6	1011.6	1003.6	993.2	985.9
7.5°	1147.0	1142.5	1142.2	1136.9	1127.9	1120.7	1107.8	1091.4	1075.5	1057.4	1042.5
10°	1199.2	1199.6	1196.2	1190.0	1180.4	1173.5	1156.6	1140.5	1121.0	1097.9	1081.5
12.5°	1238.5	1240.1	1235.8	1227.5	1222.7	1207.3	1194.1	1174.9	1151.7	1133.3	1108.1
15°	1302.0	1297.8	1294.7	1284.3	1276.3	1260.2	1239.1	1219.1	1193.9	1170.4	1147.0
17.5°	1363.2	1366.7	1360.9	1351.4	1326.5	1307.6	1279.3	1252.0	1220.4	1189.1	1161.1
20°	1417.9	1421.0	1412.1	1395.6	1365.7	1346.9	1309.7	1274.3	1238.0	1197.7	1167.0
22.5°	1486.0	1483.6	1471.7	1446.5	1420.7	1385.8	1345.6	1302.6	1257.0	1211.4	1170.6
25°	1602.0	1585.9	1578.6	1547.5	1513.4	1462.4	1407.1	1344.2	1287.5	1227.2	1175.1
27.5°	1666.3	1661.2	1653.1	1631.4	1595.6	1541.1	1475.9	1399.3	1319.1	1243.1	1174.8
30°	1653.5	1654.2	1655.0	1648.0	1625.1	1584.0	1519.1	1436.6	1341.5	1256.0	1177.0
32.5°	1539.2	1553.2	1566.6	1582.4	1588.8	1580.9	1540.3	1465.8	1368.0	1270.7	1175.7
35°	1285.9	1290.1	1333.5	1376.4	1434.7	1480.1	1510.4	1477.3	1394.8	1283.2	1174.3
37.5°	1002.6	1023.4	1053.4	1102.0	1186.1	1261.4	1358.4	1402.9	1376.2	1287.3	1171.5
40°	854.7	873.9	893.4	942.9	1013.9	1105.2	1215.3	1309.3	1331.2	1274.3	1162.4
42.5°	740.5	755.8	777.5	814.7	873.9	954.8	1060.1	1182.9	1258.4	1237.0	1143.1
45°	606.1	615.7	632.6	662.2	705.1	768.4	861.2	995.5	1112.5	1151.2	1097.1
47.5°	518.8	518.8	531.9	552.3	583.3	637.0	705.7	810.9	935.8	1028.3	1024.0
50°	470.3	468.4	478.8	496.4	521.0	556.6	622.3	706.3	826.4	931.1	960.2
52.5°	428.6	428.8	435.2	448.2	468.8	499.3	548.3	624.0	726.6	834.0	889.0
55°	373.7	372.1	379.4	388.2	403.2	423.1	458.5	516.3	599.6	705.5	776.8
57.5°	323.4	327.5	330.4	336.6	349.0	362.3	392.1	434.6	500.7	591.6	667.0
60°	293.9	298.1	300.3	306.5	316.5	328.0	351.0	385.6	441.2	519.5	594.2
62.5°	267.4	270.7	271.6	277.0	285.2	296.4	314.5	343.5	387.5	455.9	529.2
65°	229.4	229.4	231.0	236.7	240.5	250.5	264.3	285.4	320.7	374.1	436.6
67.5°	192.7	194.6	194.2	196.7	200.3	208.0	217.9	235.3	261.5	300.3	350.4
70°	168.7	170.4	170.0	171.9	175.7	180.7	188.7	205.2	224.0	257.4	300.3
72.5°	147.3	147.9	146.9	149.5	151.8	156.1	165.1	173.9	191.5	219.6	255.0
75°	112.8	113.5	114.3	115.8	118.2	120.5	125.0	133.9	145.4	166.5	189.1
77.5°	84.5	83.1	84.9	84.7	86.0	87.8	91.8	96.5	105.9	119.3	136.8
80°	63.7	64.0	64.0	64.4	66.3	67.6	71.0	74.4	81.7	91.7	103.9
82.5°	46.5	47.5	46.9	47.6	49.2	50.0	51.9	54.7	59.0	66.9	75.7
85°	25.3	23.4	24.1	24.9	24.9	25.3	26.9	28.0	30.3	33.3	36.9
87.5°	12.0	12.6	12.7	12.7	13.0	12.6	13.6	13.4	14.1	14.8	15.8
90°	23.2	23.2	22.2	22.2	22.2	20.2	19.2	18.2	17.2	16.2	14.1
92.5°	64.3	65.9	67.4	69.8	82.7	97.6	129.7	178.6	263.1	325.0	330.2
95°	236.9	253.1	261.2	291.3	362.9	447.6	571.6	724.9	874.0	893.2	728.9
97.5°	572.6	585.5	614.7	671.3	733.5	851.2	972.0	1079.5	1105.9	953.9	650.9
100°	786.4	802.4	839.8	912.3	981.9	1086.7	1190.6	1240.0	1162.4	910.3	580.7
102.5°	1025.0	1037.1	1077.7	1129.3	1203.7	1274.7	1324.4	1294.0	1128.5	833.7	527.5
105°	1335.7	1347.9	1368.1	1401.3	1433.5	1444.6	1400.3	1262.1	1020.3	730.8	475.8
107.5°	1500.7	1508.7	1515.4	1515.6	1499.2	1446.6	1332.7	1148.4	909.7	660.1	454.0
110°	1555.5	1555.5	1548.4	1529.3	1484.0	1398.3	1256.1	1064.6	846.8	627.0	447.6



TEST NUMBER: P333189-840

CATALOG NUMBER: S125DIP-S610D1035U840-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	1549.0	1541.9	1524.3	1491.4	1425.1	1324.0	1180.3	998.5	800.0	607.7	447.6
115°	1488.0	1474.9	1446.6	1398.3	1319.6	1209.7	1071.7	915.3	749.0	586.7	450.6
117.5°	1380.9	1372.8	1344.8	1294.8	1216.2	1115.4	996.4	861.7	718.6	576.4	457.3
120°	1311.6	1303.5	1276.3	1227.9	1153.3	1064.6	953.7	832.7	701.7	571.6	463.7
122.5°	1250.3	1243.0	1215.8	1171.4	1104.9	1021.8	923.0	810.9	687.1	567.5	469.4
125°	1172.5	1162.4	1140.1	1098.8	1042.4	969.8	882.1	779.3	667.4	562.5	478.9
127.5°	1105.9	1101.5	1080.5	1044.0	992.8	924.8	843.0	747.0	649.2	560.1	489.6
130°	1069.6	1063.6	1043.4	1010.2	959.8	894.2	815.6	726.9	637.1	558.5	496.0
132.5°	1033.3	1026.4	1007.9	974.6	924.2	861.1	789.7	706.7	627.4	558.5	503.2
135°	973.8	967.8	949.7	916.4	872.0	814.6	750.0	680.4	615.9	558.5	513.1
137.5°	910.3	903.7	887.0	856.7	817.0	768.2	714.6	658.3	605.7	559.7	522.2
140°	866.0	860.9	845.9	819.6	782.3	739.9	693.6	646.2	600.9	560.5	526.2
142.5°	824.9	820.6	806.3	784.2	752.5	715.8	675.8	635.7	596.8	561.3	528.7
145°	768.2	764.2	753.1	735.9	711.8	684.5	653.3	622.0	590.8	560.5	531.3
147.5°	720.2	718.4	712.0	698.2	679.0	658.5	634.5	609.2	584.5	557.8	532.3
150°	693.6	692.6	688.5	676.4	661.4	643.2	624.0	601.9	579.7	555.4	532.3
152.5°	672.6	671.6	667.6	657.9	645.2	631.1	613.5	593.8	574.0	552.3	531.5
155°	644.2	643.2	640.2	633.1	623.0	612.0	597.8	581.7	564.5	546.4	529.3
157.5°	618.7	618.9	616.1	610.4	602.5	593.8	582.9	569.6	555.6	540.4	526.6
160°	601.9	602.9	600.9	595.8	588.8	581.7	571.6	561.5	548.5	536.3	524.2
162.5°	586.5	586.7	586.3	582.1	576.6	570.4	561.9	552.7	542.0	531.5	521.8
165°	564.5	564.5	564.5	562.5	558.5	553.5	547.4	540.4	532.3	524.2	518.2
167.5°	544.4	544.6	545.4	543.6	541.6	538.0	533.3	528.7	522.8	517.2	512.5
170°	532.3	533.3	533.3	532.3	530.3	528.3	525.2	522.2	517.2	513.1	510.1
172.5°	521.0	522.0	523.6	521.8	521.4	520.2	518.0	514.9	511.5	508.3	506.9
175°	507.1	508.1	510.1	509.1	509.1	509.1	507.1	507.1	504.0	503.0	503.0
177.5°	500.0	500.0	502.4	501.6	502.4	502.4	502.4	501.6	500.8	500.0	500.0
180°	500.0	500.0	500.0	500.0	500.0	500.0	500.0	500.0	500.0	500.0	500.0



TEST NUMBER: P333189-840

CATALOG NUMBER: S125DIP-S610D1035U840-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°	95°	100°	105°
0°	903.8	903.8	903.8	903.8	903.8	903.8	903.8	903.8	903.8	903.8	903.8
2.5°	929.9	927.8	925.3	921.0	915.7	913.0	908.8	905.9	900.4	895.9	890.9
5°	977.0	967.1	958.0	946.0	933.0	924.5	914.5	903.4	891.9	880.0	867.0
7.5°	1025.9	1008.4	989.2	968.5	948.4	929.8	912.0	894.6	878.4	858.7	842.0
10°	1058.8	1036.5	1012.8	984.7	957.6	933.7	909.6	888.5	867.0	843.9	823.6
12.5°	1091.7	1062.0	1028.4	997.6	964.9	936.2	907.8	880.8	853.8	828.3	804.7
15°	1114.8	1088.7	1057.6	1013.9	977.0	937.6	900.0	865.1	832.4	804.1	774.2
17.5°	1130.0	1096.5	1063.1	1021.2	972.9	928.7	886.1	846.2	809.4	773.4	744.6
20°	1132.9	1098.3	1063.4	1022.4	972.9	922.2	879.7	831.7	792.1	755.0	719.6
22.5°	1132.0	1092.8	1054.8	1012.5	964.3	917.7	866.2	817.3	774.4	737.8	700.9
25°	1123.3	1081.5	1033.9	991.3	943.7	894.2	842.0	791.4	747.7	705.9	669.4
27.5°	1116.0	1061.8	1007.9	958.3	912.3	867.0	817.1	765.2	716.7	674.3	640.0
30°	1107.1	1047.6	987.0	935.2	888.1	843.9	796.8	746.2	695.5	654.1	617.2
32.5°	1099.1	1029.9	965.9	909.5	859.6	816.7	773.2	725.0	675.3	633.2	596.4
35°	1083.8	1003.6	930.3	866.6	813.2	769.2	732.8	687.8	642.2	601.5	566.2
37.5°	1064.2	969.1	890.4	823.6	765.2	718.7	684.8	650.4	606.5	567.3	535.4
40°	1048.8	944.5	861.2	792.9	732.4	684.0	652.6	620.0	583.5	547.0	513.3
42.5°	1029.5	922.4	831.7	758.3	698.3	651.2	618.1	590.5	558.4	524.3	493.0
45°	994.0	882.3	784.2	705.1	644.5	598.0	563.9	543.2	519.1	486.9	460.4
47.5°	941.7	834.2	732.7	651.1	588.5	545.5	513.5	493.6	476.7	452.7	428.7
50°	895.3	798.3	695.5	614.6	552.0	508.7	479.2	461.1	446.6	428.1	407.8
52.5°	843.5	753.2	659.0	579.0	517.1	474.3	445.4	429.5	417.4	404.1	384.2
55°	761.1	684.4	596.9	521.0	463.8	422.0	396.7	382.8	372.8	362.9	350.6
57.5°	670.3	610.4	532.8	463.4	410.8	372.7	349.1	335.7	327.9	322.8	315.6
60°	606.5	555.1	488.4	425.1	373.7	339.9	316.9	306.5	300.0	295.8	290.4
62.5°	547.2	505.0	443.2	385.5	340.5	308.6	288.0	278.0	271.8	269.7	265.2
65°	460.0	427.4	376.4	328.4	290.0	262.8	245.5	235.9	232.1	229.7	230.1
67.5°	374.0	354.1	313.2	272.3	241.6	218.7	204.9	197.5	195.6	192.6	192.5
70°	321.4	306.5	272.0	236.3	209.0	191.5	179.2	171.5	169.6	168.0	167.6
72.5°	275.1	262.1	232.1	203.5	179.0	163.5	153.4	148.8	145.6	144.7	144.6
75°	206.8	199.4	175.7	153.1	136.2	125.4	118.6	114.3	112.0	111.6	112.0
77.5°	147.0	140.7	125.5	109.5	98.9	90.7	84.8	83.4	80.8	80.9	80.5
80°	110.5	106.2	96.6	84.0	75.2	68.3	65.2	62.5	61.8	60.6	61.8
82.5°	80.1	75.5	69.1	61.0	53.7	49.6	46.5	45.6	45.1	44.6	44.8
85°	39.5	39.9	36.1	29.9	26.9	24.5	22.6	22.6	22.2	21.9	22.2
87.5°	16.2	15.1	13.6	12.3	10.4	9.1	8.4	8.5	7.8	7.9	8.6
90°	13.1	11.1	10.1	8.1	6.1	4.0	2.0	1.0	2.0	4.0	6.1
92.5°	230.0	137.7	82.7	53.2	35.9	23.4	14.9	12.3	14.9	23.4	35.9
95°	450.6	228.8	121.0	75.6	53.4	42.3	34.2	33.2	34.2	42.3	53.4
97.5°	359.7	197.2	125.8	93.1	73.2	62.1	56.5	55.2	56.5	62.1	73.2
100°	326.6	195.6	137.1	106.8	87.7	76.6	72.6	70.6	72.6	76.6	87.7
102.5°	313.0	202.9	150.8	121.4	103.8	91.9	88.7	87.6	88.7	91.9	103.8
105°	307.5	217.7	173.4	145.2	129.1	119.0	113.9	113.9	113.9	119.0	129.1
107.5°	316.8	239.9	197.0	171.6	154.8	146.5	141.8	139.8	141.8	146.5	154.8
110°	325.6	256.1	214.7	188.5	173.4	164.3	160.3	158.2	160.3	164.3	173.4



TEST NUMBER: P333189-840

CATALOG NUMBER: S125DIP-S610D1035U840-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°	95°	100°	105°
112.5°	336.9	271.4	231.7	206.2	191.2	182.1	178.8	176.8	178.8	182.1	191.2
115°	353.9	295.4	258.1	232.9	217.7	208.6	205.6	203.7	205.6	208.6	217.7
117.5°	373.2	320.0	284.7	260.3	243.2	234.1	230.9	227.8	230.9	234.1	243.2
120°	386.1	337.7	302.5	277.2	260.1	251.1	247.0	244.0	247.0	251.1	260.1
122.5°	400.6	354.7	319.4	294.2	275.4	266.3	263.1	260.9	263.1	266.3	275.4
125°	420.4	377.1	343.8	317.6	298.4	289.3	284.3	282.3	284.3	289.3	298.4
127.5°	438.5	398.6	366.6	340.3	320.0	308.5	302.1	299.0	302.1	308.5	320.0
130°	450.6	412.3	381.0	354.9	333.7	320.6	312.6	309.5	312.6	320.6	333.7
132.5°	461.1	425.3	393.9	367.8	345.8	331.0	321.3	317.6	321.3	331.0	345.8
135°	475.8	442.5	411.3	384.1	362.9	346.8	334.7	330.6	334.7	346.8	362.9
137.5°	486.8	454.8	426.5	398.4	377.7	361.5	350.2	347.2	350.2	361.5	377.7
140°	494.0	463.7	434.5	407.3	388.1	372.0	359.9	356.9	359.9	372.0	388.1
142.5°	498.0	469.4	441.7	416.2	397.8	381.6	370.4	368.2	370.4	381.6	397.8
145°	504.0	478.9	452.6	429.5	411.3	397.2	387.1	385.1	387.1	397.2	411.3
147.5°	507.7	484.9	461.9	441.5	425.9	412.7	404.0	402.8	404.0	412.7	425.9
150°	510.1	489.0	466.8	449.6	435.6	422.4	415.4	413.3	415.4	422.4	435.6
152.5°	511.7	493.0	472.4	456.9	443.5	432.1	425.9	424.6	425.9	432.1	443.5
155°	513.1	497.0	479.9	465.7	455.7	445.6	439.5	439.5	439.5	445.6	455.7
157.5°	514.1	500.4	485.7	475.0	466.2	457.5	452.6	452.8	452.6	457.5	466.2
160°	514.1	502.0	489.0	479.9	471.8	464.7	460.7	461.7	460.7	464.7	471.8
162.5°	513.3	503.6	492.2	484.7	478.3	472.0	468.0	469.0	468.0	472.0	478.3
165°	512.1	504.0	496.0	490.0	485.9	480.9	477.9	479.9	477.9	480.9	485.9
167.5°	509.7	504.0	497.4	493.6	490.8	488.0	486.1	487.2	486.1	488.0	490.8
170°	508.1	504.0	499.0	496.0	494.0	492.0	491.0	492.0	491.0	492.0	494.0
172.5°	506.4	503.2	499.0	497.6	496.3	494.4	493.4	495.2	493.4	494.4	496.3
175°	504.0	502.0	499.0	499.0	499.0	498.0	497.0	499.0	497.0	498.0	499.0
177.5°	501.6	500.8	499.2	499.2	500.0	499.2	499.2	500.8	499.2	499.2	500.0
180°	500.0	500.0	500.0	500.0	500.0	500.0	500.0	500.0	500.0	500.0	500.0



TEST NUMBER: P333189-840

CATALOG NUMBER: S125DIP-S610D1035U840-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	110°	115°	120°	125°	130°	135°	140°	145°	150°	155°	160°
0°	903.8	903.8	903.8	903.8	903.8	903.8	903.8	903.8	903.8	903.8	903.8
2.5°	888.2	884.7	882.0	875.9	872.5	867.9	864.2	868.2	863.9	865.8	863.0
5°	860.5	849.7	842.0	830.9	821.3	812.5	806.0	804.9	801.7	800.2	795.7
7.5°	827.2	813.7	800.5	786.0	773.7	761.2	753.2	746.6	742.3	736.5	732.6
10°	807.5	789.5	774.2	756.5	741.1	727.7	717.0	711.7	706.6	699.3	696.7
12.5°	783.3	764.7	745.9	727.0	712.4	697.3	688.1	680.0	676.6	668.3	667.5
15°	754.2	726.2	707.8	688.6	668.2	656.0	648.3	639.5	635.7	630.0	625.7
17.5°	719.5	694.5	671.5	651.7	634.2	623.9	614.3	608.2	601.7	597.9	591.0
20°	694.4	670.6	647.5	626.4	613.0	601.2	593.5	587.7	580.8	578.9	572.0
22.5°	673.2	646.9	624.8	607.1	592.5	579.1	570.8	566.8	562.1	556.1	554.8
25°	638.7	611.5	592.7	575.0	562.0	549.8	544.0	539.0	534.4	530.2	528.7
27.5°	608.9	584.6	562.3	546.3	535.0	523.8	518.8	512.7	509.3	505.9	501.8
30°	588.1	563.2	543.6	528.3	515.9	506.0	500.6	496.4	493.3	490.3	488.0
32.5°	566.6	543.5	524.5	509.6	497.3	489.8	484.9	482.0	478.6	474.9	472.0
35°	538.3	512.9	494.5	481.4	471.8	466.1	460.7	458.1	454.2	454.2	451.1
37.5°	506.2	484.3	468.1	456.2	447.6	442.4	436.7	434.8	432.3	430.7	429.7
40°	487.2	466.9	451.5	439.6	430.4	426.2	421.6	418.5	417.0	415.1	414.3
42.5°	467.6	448.2	433.4	422.4	414.4	410.8	406.6	404.5	401.3	398.8	398.4
45°	437.7	418.9	405.5	396.7	389.8	385.6	382.8	378.3	376.7	373.7	373.2
47.5°	409.4	391.3	378.2	370.9	364.9	361.4	357.2	352.6	350.8	349.3	349.2
50°	388.2	371.7	359.4	352.5	346.8	341.8	337.6	334.6	333.4	333.4	334.2
52.5°	366.8	352.7	342.2	333.9	328.4	323.1	319.2	317.3	315.6	317.4	318.8
55°	335.3	321.1	313.5	305.4	300.0	293.9	292.0	291.1	290.0	293.1	294.6
57.5°	301.9	292.1	283.1	275.1	270.2	266.7	264.1	263.7	265.8	267.2	272.3
60°	280.8	269.3	261.3	255.1	249.3	247.0	246.3	245.5	247.0	251.3	257.8
62.5°	257.5	248.1	239.4	234.9	230.7	226.8	226.6	227.1	230.1	235.0	241.6
65°	223.3	215.2	209.4	204.1	200.7	198.3	199.1	200.7	204.1	210.7	217.9
67.5°	188.5	183.0	177.8	173.5	170.2	170.2	171.0	173.3	177.3	184.8	191.5
70°	166.1	160.0	155.7	153.8	151.2	149.7	151.9	155.7	159.2	166.1	171.9
72.5°	143.7	138.5	135.2	133.9	132.7	131.5	132.3	136.4	141.1	148.0	154.7
75°	110.5	108.6	106.2	104.7	103.6	104.3	105.1	109.0	112.8	120.1	127.7
77.5°	80.7	78.7	77.3	76.9	76.2	76.6	78.8	81.6	85.4	90.7	96.5
80°	61.0	60.2	59.5	59.1	59.1	59.5	62.5	64.4	67.9	72.9	77.5
82.5°	44.4	43.9	43.8	43.7	44.0	44.1	45.9	48.5	51.3	55.1	59.1
85°	23.4	22.6	23.8	24.1	23.4	24.5	25.3	26.9	28.0	29.9	31.8
87.5°	9.3	10.3	10.2	10.9	11.1	12.1	12.0	13.4	14.2	15.0	15.1
90°	8.1	10.1	11.1	13.1	14.1	16.2	17.2	18.2	19.2	20.2	22.2
92.5°	53.2	82.7	137.7	230.0	330.2	325.0	263.1	178.6	129.7	97.6	82.7
95°	75.6	121.0	228.8	450.6	728.9	893.2	874.0	724.9	571.6	447.6	362.9
97.5°	93.1	125.8	197.2	359.7	650.9	953.9	1105.9	1079.5	972.0	851.2	733.5
100°	106.8	137.1	195.6	326.6	580.7	910.3	1162.4	1240.0	1190.6	1086.7	981.9
102.5°	121.4	150.8	202.9	313.0	527.5	833.7	1128.5	1294.0	1324.4	1274.7	1203.7
105°	145.2	173.4	217.7	307.5	475.8	730.8	1020.3	1262.1	1400.3	1444.6	1433.5
107.5°	171.6	197.0	239.9	316.8	454.0	660.1	909.7	1148.4	1332.7	1446.6	1499.2
110°	188.5	214.7	256.1	325.6	447.6	627.0	846.8	1064.6	1256.1	1398.3	1484.0



TEST NUMBER: P333189-840

CATALOG NUMBER: S125DIP-S610D1035U840-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	110°	115°	120°	125°	130°	135°	140°	145°	150°	155°	160°
112.5°	206.2	231.7	271.4	336.9	447.6	607.7	800.0	998.5	1180.3	1324.0	1425.1
115°	232.9	258.1	295.4	353.9	450.6	586.7	749.0	915.3	1071.7	1209.7	1319.6
117.5°	260.3	284.7	320.0	373.2	457.3	576.4	718.6	861.7	996.4	1115.4	1216.2
120°	277.2	302.5	337.7	386.1	463.7	571.6	701.7	832.7	953.7	1064.6	1153.3
122.5°	294.2	319.4	354.7	400.6	469.4	567.5	687.1	810.9	923.0	1021.8	1104.9
125°	317.6	343.8	377.1	420.4	478.9	562.5	667.4	779.3	882.1	969.8	1042.4
127.5°	340.3	366.6	398.6	438.5	489.6	560.1	649.2	747.0	843.0	924.8	992.8
130°	354.9	381.0	412.3	450.6	496.0	558.5	637.1	726.9	815.6	894.2	959.8
132.5°	367.8	393.9	425.3	461.1	503.2	558.5	627.4	706.7	789.7	861.1	924.2
135°	384.1	411.3	442.5	475.8	513.1	558.5	615.9	680.4	750.0	814.6	872.0
137.5°	398.4	426.5	454.8	486.8	522.2	559.7	605.7	658.3	714.6	768.2	817.0
140°	407.3	434.5	463.7	494.0	526.2	560.5	600.9	646.2	693.6	739.9	782.3
142.5°	416.2	441.7	469.4	498.0	528.7	561.3	596.8	635.7	675.8	715.8	752.5
145°	429.5	452.6	478.9	504.0	531.3	560.5	590.8	622.0	653.3	684.5	711.8
147.5°	441.5	461.9	484.9	507.7	532.3	557.8	584.5	609.2	634.5	658.5	679.0
150°	449.6	466.8	489.0	510.1	532.3	555.4	579.7	601.9	624.0	643.2	661.4
152.5°	456.9	472.4	493.0	511.7	531.5	552.3	574.0	593.8	613.5	631.1	645.2
155°	465.7	479.9	497.0	513.1	529.3	546.4	564.5	581.7	597.8	612.0	623.0
157.5°	475.0	485.7	500.4	514.1	526.6	540.4	555.6	569.6	582.9	593.8	602.5
160°	479.9	489.0	502.0	514.1	524.2	536.3	548.5	561.5	571.6	581.7	588.8
162.5°	484.7	492.2	503.6	513.3	521.8	531.5	542.0	552.7	561.9	570.4	576.6
165°	490.0	496.0	504.0	512.1	518.2	524.2	532.3	540.4	547.4	553.5	558.5
167.5°	493.6	497.4	504.0	509.7	512.5	517.2	522.8	528.7	533.3	538.0	541.6
170°	496.0	499.0	504.0	508.1	510.1	513.1	517.2	522.2	525.2	528.3	530.3
172.5°	497.6	499.0	503.2	506.4	506.9	508.3	511.5	514.9	518.0	520.2	521.4
175°	499.0	499.0	502.0	504.0	503.0	503.0	504.0	507.1	507.1	509.1	509.1
177.5°	499.2	499.2	500.8	501.6	500.0	500.0	500.8	501.6	502.4	502.4	502.4
180°	500.0	500.0	500.0	500.0	500.0	500.0	500.0	500.0	500.0	500.0	500.0



TEST NUMBER: P333189-840

CATALOG NUMBER: S125DIP-S610D1035U840-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	165°	170°	175°	180°	185°	190°	195°	200°	205°	210°	215°
0°	903.8	903.8	903.8	903.8	903.8	903.8	903.8	903.8	903.8	903.8	903.8
2.5°	861.1	863.3	861.5	863.9	861.5	863.3	861.1	863.0	865.8	863.9	868.2
5°	793.8	790.2	792.5	791.0	792.5	790.2	793.8	795.7	800.2	801.7	804.9
7.5°	731.4	728.1	724.4	722.6	724.4	728.1	731.4	732.6	736.5	742.3	746.6
10°	692.5	688.2	687.8	685.2	687.8	688.2	692.5	696.7	699.3	706.6	711.7
12.5°	663.9	659.9	655.6	654.5	655.6	659.9	663.9	667.5	668.3	676.6	680.0
15°	623.4	620.4	617.6	620.0	617.6	620.4	623.4	625.7	630.0	635.7	639.5
17.5°	589.7	587.1	586.7	583.9	586.7	587.1	589.7	591.0	597.9	601.7	608.2
20°	568.6	566.6	567.3	562.4	567.3	566.6	568.6	572.0	578.9	580.8	587.7
22.5°	551.7	547.9	547.4	546.4	547.4	547.9	551.7	554.8	556.1	562.1	566.8
25°	525.2	523.3	521.4	523.3	521.4	523.3	525.2	528.7	530.2	534.4	539.0
27.5°	502.1	499.8	499.3	499.5	499.3	499.8	502.1	501.8	505.9	509.3	512.7
30°	488.0	484.1	484.5	484.1	484.5	484.1	488.0	488.0	490.3	493.3	496.4
32.5°	472.6	470.0	469.5	468.8	469.5	470.0	472.6	472.0	474.9	478.6	482.0
35°	450.0	450.0	448.1	448.1	448.1	450.0	450.0	451.1	454.2	454.2	458.1
37.5°	428.7	428.4	427.2	427.4	427.2	428.4	428.7	429.7	430.7	432.3	434.8
40°	412.7	412.4	411.2	408.9	411.2	412.4	412.7	414.3	415.1	417.0	418.5
42.5°	397.5	396.2	395.6	394.9	395.6	396.2	397.5	398.4	398.8	401.3	404.5
45°	373.2	373.2	372.5	372.1	372.5	373.2	373.2	373.2	373.7	376.7	378.3
47.5°	349.8	350.5	351.9	351.7	351.9	350.5	349.8	349.2	349.3	350.8	352.6
50°	335.7	336.1	337.2	337.6	337.2	336.1	335.7	334.2	333.4	333.4	334.6
52.5°	320.0	322.2	323.7	323.5	323.7	322.2	320.0	318.8	317.4	315.6	317.3
55°	298.1	300.7	303.5	303.9	303.5	300.7	298.1	294.6	293.1	290.0	291.1
57.5°	276.4	280.1	283.0	283.9	283.0	280.1	276.4	272.3	267.2	265.8	263.7
60°	261.7	266.6	270.0	271.7	270.0	266.6	261.7	257.8	251.3	247.0	245.5
62.5°	247.5	253.1	256.6	256.9	256.6	253.1	247.5	241.6	235.0	230.1	227.1
65°	224.4	230.1	233.3	235.5	233.3	230.1	224.4	217.9	210.7	204.1	200.7
67.5°	199.5	205.3	208.7	210.6	208.7	205.3	199.5	191.5	184.8	177.3	173.3
70°	181.5	187.2	191.8	193.4	191.8	187.2	181.5	171.9	166.1	159.2	155.7
72.5°	163.7	168.7	172.5	174.3	172.5	168.7	163.7	154.7	148.0	141.1	136.4
75°	132.7	139.7	143.1	145.0	143.1	139.7	132.7	127.7	120.1	112.8	109.0
77.5°	102.4	108.7	110.7	111.7	110.7	108.7	102.4	96.5	90.7	85.4	81.6
80°	82.1	85.9	88.7	89.0	88.7	85.9	82.1	77.5	72.9	67.9	64.4
82.5°	63.1	66.2	67.2	68.2	67.2	66.2	63.1	59.1	55.1	51.3	48.5
85°	34.5	36.1	36.5	36.1	36.5	36.1	34.5	31.8	29.9	28.0	26.9
87.5°	15.8	15.5	15.7	16.3	15.7	15.5	15.8	15.1	15.0	14.2	13.4
90°	22.2	22.2	23.2	23.2	23.2	22.2	22.2	22.2	20.2	19.2	18.2
92.5°	69.8	67.4	65.9	64.3	65.9	67.4	69.8	82.7	97.6	129.7	178.6
95°	291.3	261.2	253.1	236.9	253.1	261.2	291.3	362.9	447.6	571.6	724.9
97.5°	671.3	614.7	585.5	572.6	585.5	614.7	671.3	733.5	851.2	972.0	1079.5
100°	912.3	839.8	802.4	786.4	802.4	839.8	912.3	981.9	1086.7	1190.6	1240.0
102.5°	1129.3	1077.7	1037.1	1025.0	1037.1	1077.7	1129.3	1203.7	1274.7	1324.4	1294.0
105°	1401.3	1368.1	1347.9	1335.7	1347.9	1368.1	1401.3	1433.5	1444.6	1400.3	1262.1
107.5°	1515.6	1515.4	1508.7	1500.7	1508.7	1515.4	1515.6	1499.2	1446.6	1332.7	1148.4
110°	1529.3	1548.4	1555.5	1555.5	1555.5	1548.4	1529.3	1484.0	1398.3	1256.1	1064.6



TEST NUMBER: P333189-840

CATALOG NUMBER: S125DIP-S610D1035U840-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	165°	170°	175°	180°	185°	190°	195°	200°	205°	210°	215°
112.5°	1491.4	1524.3	1541.9	1549.0	1541.9	1524.3	1491.4	1425.1	1324.0	1180.3	998.5
115°	1398.3	1446.6	1474.9	1488.0	1474.9	1446.6	1398.3	1319.6	1209.7	1071.7	915.3
117.5°	1294.8	1344.8	1372.8	1380.9	1372.8	1344.8	1294.8	1216.2	1115.4	996.4	861.7
120°	1227.9	1276.3	1303.5	1311.6	1303.5	1276.3	1227.9	1153.3	1064.6	953.7	832.7
122.5°	1171.4	1215.8	1243.0	1250.3	1243.0	1215.8	1171.4	1104.9	1021.8	923.0	810.9
125°	1098.8	1140.1	1162.4	1172.5	1162.4	1140.1	1098.8	1042.4	969.8	882.1	779.3
127.5°	1044.0	1080.5	1101.5	1105.9	1101.5	1080.5	1044.0	992.8	924.8	843.0	747.0
130°	1010.2	1043.4	1063.6	1069.6	1063.6	1043.4	1010.2	959.8	894.2	815.6	726.9
132.5°	974.6	1007.9	1026.4	1033.3	1026.4	1007.9	974.6	924.2	861.1	789.7	706.7
135°	916.4	949.7	967.8	973.8	967.8	949.7	916.4	872.0	814.6	750.0	680.4
137.5°	856.7	887.0	903.7	910.3	903.7	887.0	856.7	817.0	768.2	714.6	658.3
140°	819.6	845.9	860.9	866.0	860.9	845.9	819.6	782.3	739.9	693.6	646.2
142.5°	784.2	806.3	820.6	824.9	820.6	806.3	784.2	752.5	715.8	675.8	635.7
145°	735.9	753.1	764.2	768.2	764.2	753.1	735.9	711.8	684.5	653.3	622.0
147.5°	698.2	712.0	718.4	720.2	718.4	712.0	698.2	679.0	658.5	634.5	609.2
150°	676.4	688.5	692.6	693.6	692.6	688.5	676.4	661.4	643.2	624.0	601.9
152.5°	657.9	667.6	671.6	672.6	671.6	667.6	657.9	645.2	631.1	613.5	593.8
155°	633.1	640.2	643.2	644.2	643.2	640.2	633.1	623.0	612.0	597.8	581.7
157.5°	610.4	616.1	618.9	618.7	618.9	616.1	610.4	602.5	593.8	582.9	569.6
160°	595.8	600.9	602.9	601.9	602.9	600.9	595.8	588.8	581.7	571.6	561.5
162.5°	582.1	586.3	586.7	586.5	586.7	586.3	582.1	576.6	570.4	561.9	552.7
165°	562.5	564.5	564.5	564.5	564.5	564.5	562.5	558.5	553.5	547.4	540.4
167.5°	543.6	545.4	544.6	544.4	544.6	545.4	543.6	541.6	538.0	533.3	528.7
170°	532.3	533.3	533.3	532.3	533.3	533.3	532.3	530.3	528.3	525.2	522.2
172.5°	521.8	523.6	522.0	521.0	522.0	523.6	521.8	521.4	520.2	518.0	514.9
175°	509.1	510.1	508.1	507.1	508.1	510.1	509.1	509.1	509.1	507.1	507.1
177.5°	501.6	502.4	500.0	500.0	500.0	502.4	501.6	502.4	502.4	502.4	501.6
180°	500.0	500.0	500.0	500.0	500.0	500.0	500.0	500.0	500.0	500.0	500.0



TEST NUMBER: P333189-840

CATALOG NUMBER: S125DIP-S610D1035U840-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	220°	225°	230°	235°	240°	245°	250°	255°	260°	265°	270°
0°	903.8	903.8	903.8	903.8	903.8	903.8	903.8	903.8	903.8	903.8	903.8
2.5°	864.2	867.9	872.5	875.9	882.0	884.7	888.2	890.9	895.9	900.4	905.9
5°	806.0	812.5	821.3	830.9	842.0	849.7	860.5	867.0	880.0	891.9	903.4
7.5°	753.2	761.2	773.7	786.0	800.5	813.7	827.2	842.0	858.7	878.4	894.6
10°	717.0	727.7	741.1	756.5	774.2	789.5	807.5	823.6	843.9	867.0	888.5
12.5°	688.1	697.3	712.4	727.0	745.9	764.7	783.3	804.7	828.3	853.8	880.8
15°	648.3	656.0	668.2	688.6	707.8	726.2	754.2	774.2	804.1	832.4	865.1
17.5°	614.3	623.9	634.2	651.7	671.5	694.5	719.5	744.6	773.4	809.4	846.2
20°	593.5	601.2	613.0	626.4	647.5	670.6	694.4	719.6	755.0	792.1	831.7
22.5°	570.8	579.1	592.5	607.1	624.8	646.9	673.2	700.9	737.8	774.4	817.3
25°	544.0	549.8	562.0	575.0	592.7	611.5	638.7	669.4	705.9	747.7	791.4
27.5°	518.8	523.8	535.0	546.3	562.3	584.6	608.9	640.0	674.3	716.7	765.2
30°	500.6	506.0	515.9	528.3	543.6	563.2	588.1	617.2	654.1	695.5	746.2
32.5°	484.9	489.8	497.3	509.6	524.5	543.5	566.6	596.4	633.2	675.3	725.0
35°	460.7	466.1	471.8	481.4	494.5	512.9	538.3	566.2	601.5	642.2	687.8
37.5°	436.7	442.4	447.6	456.2	468.1	484.3	506.2	535.4	567.3	606.5	650.4
40°	421.6	426.2	430.4	439.6	451.5	466.9	487.2	513.3	547.0	583.5	620.0
42.5°	406.6	410.8	414.4	422.4	433.4	448.2	467.6	493.0	524.3	558.4	590.5
45°	382.8	385.6	389.8	396.7	405.5	418.9	437.7	460.4	486.9	519.1	543.2
47.5°	357.2	361.4	364.9	370.9	378.2	391.3	409.4	428.7	452.7	476.7	493.6
50°	337.6	341.8	346.8	352.5	359.4	371.7	388.2	407.8	428.1	446.6	461.1
52.5°	319.2	323.1	328.4	333.9	342.2	352.7	366.8	384.2	404.1	417.4	429.5
55°	292.0	293.9	300.0	305.4	313.5	321.1	335.3	350.6	362.9	372.8	382.8
57.5°	264.1	266.7	270.2	275.1	283.1	292.1	301.9	315.6	322.8	327.9	335.7
60°	246.3	247.0	249.3	255.1	261.3	269.3	280.8	290.4	295.8	300.0	306.5
62.5°	226.6	226.8	230.7	234.9	239.4	248.1	257.5	265.2	269.7	271.8	278.0
65°	199.1	198.3	200.7	204.1	209.4	215.2	223.3	230.1	229.7	232.1	235.9
67.5°	171.0	170.2	170.2	173.5	177.8	183.0	188.5	192.5	192.6	195.6	197.5
70°	151.9	149.7	151.2	153.8	155.7	160.0	166.1	167.6	168.0	169.6	171.5
72.5°	132.3	131.5	132.7	133.9	135.2	138.5	143.7	144.6	144.7	145.6	148.8
75°	105.1	104.3	103.6	104.7	106.2	108.6	110.5	112.0	111.6	112.0	114.3
77.5°	78.8	76.6	76.2	76.9	77.3	78.7	80.7	80.5	80.9	80.8	83.4
80°	62.5	59.5	59.1	59.1	59.5	60.2	61.0	61.8	60.6	61.8	62.5
82.5°	45.9	44.1	44.0	43.7	43.8	43.9	44.4	44.8	44.6	45.1	45.6
85°	25.3	24.5	23.4	24.1	23.8	22.6	23.4	22.2	21.9	22.2	22.6
87.5°	12.0	12.1	11.1	10.9	10.2	10.3	9.3	8.6	7.9	7.8	8.5
90°	17.2	16.2	14.1	13.1	11.1	10.1	8.1	6.1	4.0	2.0	1.0
92.5°	263.1	325.0	330.2	230.0	137.7	82.7	53.2	35.9	23.4	14.9	12.3
95°	874.0	893.2	728.9	450.6	228.8	121.0	75.6	53.4	42.3	34.2	33.2
97.5°	1105.9	953.9	650.9	359.7	197.2	125.8	93.1	73.2	62.1	56.5	55.2
100°	1162.4	910.3	580.7	326.6	195.6	137.1	106.8	87.7	76.6	72.6	70.6
102.5°	1128.5	833.7	527.5	313.0	202.9	150.8	121.4	103.8	91.9	88.7	87.6
105°	1020.3	730.8	475.8	307.5	217.7	173.4	145.2	129.1	119.0	113.9	113.9
107.5°	909.7	660.1	454.0	316.8	239.9	197.0	171.6	154.8	146.5	141.8	139.8
110°	846.8	627.0	447.6	325.6	256.1	214.7	188.5	173.4	164.3	160.3	158.2



TEST NUMBER: P333189-840

CATALOG NUMBER: S125DIP-S610D1035U840-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	220°	225°	230°	235°	240°	245°	250°	255°	260°	265°	270°
112.5°	800.0	607.7	447.6	336.9	271.4	231.7	206.2	191.2	182.1	178.8	176.8
115°	749.0	586.7	450.6	353.9	295.4	258.1	232.9	217.7	208.6	205.6	203.7
117.5°	718.6	576.4	457.3	373.2	320.0	284.7	260.3	243.2	234.1	230.9	227.8
120°	701.7	571.6	463.7	386.1	337.7	302.5	277.2	260.1	251.1	247.0	244.0
122.5°	687.1	567.5	469.4	400.6	354.7	319.4	294.2	275.4	266.3	263.1	260.9
125°	667.4	562.5	478.9	420.4	377.1	343.8	317.6	298.4	289.3	284.3	282.3
127.5°	649.2	560.1	489.6	438.5	398.6	366.6	340.3	320.0	308.5	302.1	299.0
130°	637.1	558.5	496.0	450.6	412.3	381.0	354.9	333.7	320.6	312.6	309.5
132.5°	627.4	558.5	503.2	461.1	425.3	393.9	367.8	345.8	331.0	321.3	317.6
135°	615.9	558.5	513.1	475.8	442.5	411.3	384.1	362.9	346.8	334.7	330.6
137.5°	605.7	559.7	522.2	486.8	454.8	426.5	398.4	377.7	361.5	350.2	347.2
140°	600.9	560.5	526.2	494.0	463.7	434.5	407.3	388.1	372.0	359.9	356.9
142.5°	596.8	561.3	528.7	498.0	469.4	441.7	416.2	397.8	381.6	370.4	368.2
145°	590.8	560.5	531.3	504.0	478.9	452.6	429.5	411.3	397.2	387.1	385.1
147.5°	584.5	557.8	532.3	507.7	484.9	461.9	441.5	425.9	412.7	404.0	402.8
150°	579.7	555.4	532.3	510.1	489.0	466.8	449.6	435.6	422.4	415.4	413.3
152.5°	574.0	552.3	531.5	511.7	493.0	472.4	456.9	443.5	432.1	425.9	424.6
155°	564.5	546.4	529.3	513.1	497.0	479.9	465.7	455.7	445.6	439.5	439.5
157.5°	555.6	540.4	526.6	514.1	500.4	485.7	475.0	466.2	457.5	452.6	452.8
160°	548.5	536.3	524.2	514.1	502.0	489.0	479.9	471.8	464.7	460.7	461.7
162.5°	542.0	531.5	521.8	513.3	503.6	492.2	484.7	478.3	472.0	468.0	469.0
165°	532.3	524.2	518.2	512.1	504.0	496.0	490.0	485.9	480.9	477.9	479.9
167.5°	522.8	517.2	512.5	509.7	504.0	497.4	493.6	490.8	488.0	486.1	487.2
170°	517.2	513.1	510.1	508.1	504.0	499.0	496.0	494.0	492.0	491.0	492.0
172.5°	511.5	508.3	506.9	506.4	503.2	499.0	497.6	496.3	494.4	493.4	495.2
175°	504.0	503.0	503.0	504.0	502.0	499.0	499.0	499.0	498.0	497.0	499.0
177.5°	500.8	500.0	500.0	501.6	500.8	499.2	499.2	500.0	499.2	499.2	500.8
180°	500.0	500.0	500.0	500.0	500.0	500.0	500.0	500.0	500.0	500.0	500.0



TEST NUMBER: P333189-840

CATALOG NUMBER: S125DIP-S610D1035U840-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	275°	280°	285°	290°	295°	300°	305°	310°	315°	320°	325°
0°	903.8	903.8	903.8	903.8	903.8	903.8	903.8	903.8	903.8	903.8	903.8
2.5°	908.8	913.0	915.7	921.0	925.3	927.8	929.9	931.7	933.9	935.7	941.0
5°	914.5	924.5	933.0	946.0	958.0	967.1	977.0	985.9	993.2	1003.6	1011.6
7.5°	912.0	929.8	948.4	968.5	989.2	1008.4	1025.9	1042.5	1057.4	1075.5	1091.4
10°	909.6	933.7	957.6	984.7	1012.8	1036.5	1058.8	1081.5	1097.9	1121.0	1140.5
12.5°	907.8	936.2	964.9	997.6	1028.4	1062.0	1091.7	1108.1	1133.3	1151.7	1174.9
15°	900.0	937.6	977.0	1013.9	1057.6	1088.7	1114.8	1147.0	1170.4	1193.9	1219.1
17.5°	886.1	928.7	972.9	1021.2	1063.1	1096.5	1130.0	1161.1	1189.1	1220.4	1252.0
20°	879.7	922.2	972.9	1022.4	1063.4	1098.3	1132.9	1167.0	1197.7	1238.0	1274.3
22.5°	866.2	917.7	964.3	1012.5	1054.8	1092.8	1132.0	1170.6	1211.4	1257.0	1302.6
25°	842.0	894.2	943.7	991.3	1033.9	1081.5	1123.3	1175.1	1227.2	1287.5	1344.2
27.5°	817.1	867.0	912.3	958.3	1007.9	1061.8	1116.0	1174.8	1243.1	1319.1	1399.3
30°	796.8	843.9	888.1	935.2	987.0	1047.6	1107.1	1177.0	1256.0	1341.5	1436.6
32.5°	773.2	816.7	859.6	909.5	965.9	1029.9	1099.1	1175.7	1270.7	1368.0	1465.8
35°	732.8	769.2	813.2	866.6	930.3	1003.6	1083.8	1174.3	1283.2	1394.8	1477.3
37.5°	684.8	718.7	765.2	823.6	890.4	969.1	1064.2	1171.5	1287.3	1376.2	1402.9
40°	652.6	684.0	732.4	792.9	861.2	944.5	1048.8	1162.4	1274.3	1331.2	1309.3
42.5°	618.1	651.2	698.3	758.3	831.7	922.4	1029.5	1143.1	1237.0	1258.4	1182.9
45°	563.9	598.0	644.5	705.1	784.2	882.3	994.0	1097.1	1151.2	1112.5	995.5
47.5°	513.5	545.5	588.5	651.1	732.7	834.2	941.7	1024.0	1028.3	935.8	810.9
50°	479.2	508.7	552.0	614.6	695.5	798.3	895.3	960.2	931.1	826.4	706.3
52.5°	445.4	474.3	517.1	579.0	659.0	753.2	843.5	889.0	834.0	726.6	624.0
55°	396.7	422.0	463.8	521.0	596.9	684.4	761.1	776.8	705.5	599.6	516.3
57.5°	349.1	372.7	410.8	463.4	532.8	610.4	670.3	667.0	591.6	500.7	434.6
60°	316.9	339.9	373.7	425.1	488.4	555.1	606.5	594.2	519.5	441.2	385.6
62.5°	288.0	308.6	340.5	385.5	443.2	505.0	547.2	529.2	455.9	387.5	343.5
65°	245.5	262.8	290.0	328.4	376.4	427.4	460.0	436.6	374.1	320.7	285.4
67.5°	204.9	218.7	241.6	272.3	313.2	354.1	374.0	350.4	300.3	261.5	235.3
70°	179.2	191.5	209.0	236.3	272.0	306.5	321.4	300.3	257.4	224.0	205.2
72.5°	153.4	163.5	179.0	203.5	232.1	262.1	275.1	255.0	219.6	191.5	173.9
75°	118.6	125.4	136.2	153.1	175.7	199.4	206.8	189.1	166.5	145.4	133.9
77.5°	84.8	90.7	98.9	109.5	125.5	140.7	147.0	136.8	119.3	105.9	96.5
80°	65.2	68.3	75.2	84.0	96.6	106.2	110.5	103.9	91.7	81.7	74.4
82.5°	46.5	49.6	53.7	61.0	69.1	75.5	80.1	75.7	66.9	59.0	54.7
85°	22.6	24.5	26.9	29.9	36.1	39.9	39.5	36.9	33.3	30.3	28.0
87.5°	8.4	9.1	10.4	12.3	13.6	15.1	16.2	15.8	14.8	14.1	13.4
90°	2.0	4.0	6.1	8.1	10.1	11.1	13.1	14.1	16.2	17.2	18.2
92.5°	14.9	23.4	35.9	53.2	82.7	137.7	230.0	330.2	325.0	263.1	178.6
95°	34.2	42.3	53.4	75.6	121.0	228.8	450.6	728.9	893.2	874.0	724.9
97.5°	56.5	62.1	73.2	93.1	125.8	197.2	359.7	650.9	953.9	1105.9	1079.5
100°	72.6	76.6	87.7	106.8	137.1	195.6	326.6	580.7	910.3	1162.4	1240.0
102.5°	88.7	91.9	103.8	121.4	150.8	202.9	313.0	527.5	833.7	1128.5	1294.0
105°	113.9	119.0	129.1	145.2	173.4	217.7	307.5	475.8	730.8	1020.3	1262.1
107.5°	141.8	146.5	154.8	171.6	197.0	239.9	316.8	454.0	660.1	909.7	1148.4
110°	160.3	164.3	173.4	188.5	214.7	256.1	325.6	447.6	627.0	846.8	1064.6



TEST NUMBER: P333189-840

CATALOG NUMBER: S125DIP-S610D1035U840-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	275°	280°	285°	290°	295°	300°	305°	310°	315°	320°	325°
112.5°	178.8	182.1	191.2	206.2	231.7	271.4	336.9	447.6	607.7	800.0	998.5
115°	205.6	208.6	217.7	232.9	258.1	295.4	353.9	450.6	586.7	749.0	915.3
117.5°	230.9	234.1	243.2	260.3	284.7	320.0	373.2	457.3	576.4	718.6	861.7
120°	247.0	251.1	260.1	277.2	302.5	337.7	386.1	463.7	571.6	701.7	832.7
122.5°	263.1	266.3	275.4	294.2	319.4	354.7	400.6	469.4	567.5	687.1	810.9
125°	284.3	289.3	298.4	317.6	343.8	377.1	420.4	478.9	562.5	667.4	779.3
127.5°	302.1	308.5	320.0	340.3	366.6	398.6	438.5	489.6	560.1	649.2	747.0
130°	312.6	320.6	333.7	354.9	381.0	412.3	450.6	496.0	558.5	637.1	726.9
132.5°	321.3	331.0	345.8	367.8	393.9	425.3	461.1	503.2	558.5	627.4	706.7
135°	334.7	346.8	362.9	384.1	411.3	442.5	475.8	513.1	558.5	615.9	680.4
137.5°	350.2	361.5	377.7	398.4	426.5	454.8	486.8	522.2	559.7	605.7	658.3
140°	359.9	372.0	388.1	407.3	434.5	463.7	494.0	526.2	560.5	600.9	646.2
142.5°	370.4	381.6	397.8	416.2	441.7	469.4	498.0	528.7	561.3	596.8	635.7
145°	387.1	397.2	411.3	429.5	452.6	478.9	504.0	531.3	560.5	590.8	622.0
147.5°	404.0	412.7	425.9	441.5	461.9	484.9	507.7	532.3	557.8	584.5	609.2
150°	415.4	422.4	435.6	449.6	466.8	489.0	510.1	532.3	555.4	579.7	601.9
152.5°	425.9	432.1	443.5	456.9	472.4	493.0	511.7	531.5	552.3	574.0	593.8
155°	439.5	445.6	455.7	465.7	479.9	497.0	513.1	529.3	546.4	564.5	581.7
157.5°	452.6	457.5	466.2	475.0	485.7	500.4	514.1	526.6	540.4	555.6	569.6
160°	460.7	464.7	471.8	479.9	489.0	502.0	514.1	524.2	536.3	548.5	561.5
162.5°	468.0	472.0	478.3	484.7	492.2	503.6	513.3	521.8	531.5	542.0	552.7
165°	477.9	480.9	485.9	490.0	496.0	504.0	512.1	518.2	524.2	532.3	540.4
167.5°	486.1	488.0	490.8	493.6	497.4	504.0	509.7	512.5	517.2	522.8	528.7
170°	491.0	492.0	494.0	496.0	499.0	504.0	508.1	510.1	513.1	517.2	522.2
172.5°	493.4	494.4	496.3	497.6	499.0	503.2	506.4	506.9	508.3	511.5	514.9
175°	497.0	498.0	499.0	499.0	499.0	502.0	504.0	503.0	503.0	504.0	507.1
177.5°	499.2	499.2	500.0	499.2	499.2	500.8	501.6	500.0	500.0	500.8	501.6
180°	500.0	500.0	500.0	500.0	500.0	500.0	500.0	500.0	500.0	500.0	500.0



TEST NUMBER: P333189-840

CATALOG NUMBER: S125DIP-S610D1035U840-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	330°	335°	340°	345°	350°	355°	360°
0°	903.8	903.8	903.8	903.8	903.8	903.8	903.8
2.5°	945.2	947.7	952.9	951.1	953.5	954.7	956.0
5°	1021.6	1033.9	1039.3	1038.4	1046.5	1044.6	1042.7
7.5°	1107.8	1120.7	1127.9	1136.9	1142.2	1142.5	1147.0
10°	1156.6	1173.5	1180.4	1190.0	1196.2	1199.6	1199.2
12.5°	1194.1	1207.3	1222.7	1227.5	1235.8	1240.1	1238.5
15°	1239.1	1260.2	1276.3	1284.3	1294.7	1297.8	1302.0
17.5°	1279.3	1307.6	1326.5	1351.4	1360.9	1366.7	1363.2
20°	1309.7	1346.9	1365.7	1395.6	1412.1	1421.0	1417.9
22.5°	1345.6	1385.8	1420.7	1446.5	1471.7	1483.6	1486.0
25°	1407.1	1462.4	1513.4	1547.5	1578.6	1585.9	1602.0
27.5°	1475.9	1541.1	1595.6	1631.4	1653.1	1661.2	1666.3
30°	1519.1	1584.0	1625.1	1648.0	1655.0	1654.2	1653.5
32.5°	1540.3	1580.9	1588.8	1582.4	1566.6	1553.2	1539.2
35°	1510.4	1480.1	1434.7	1376.4	1333.5	1290.1	1285.9
37.5°	1358.4	1261.4	1186.1	1102.0	1053.4	1023.4	1002.6
40°	1215.3	1105.2	1013.9	942.9	893.4	873.9	854.7
42.5°	1060.1	954.8	873.9	814.7	777.5	755.8	740.5
45°	861.2	768.4	705.1	662.2	632.6	615.7	606.1
47.5°	705.7	637.0	583.3	552.3	531.9	518.8	518.8
50°	622.3	556.6	521.0	496.4	478.8	468.4	470.3
52.5°	548.3	499.3	468.8	448.2	435.2	428.8	428.6
55°	458.5	423.1	403.2	388.2	379.4	372.1	373.7
57.5°	392.1	362.3	349.0	336.6	330.4	327.5	323.4
60°	351.0	328.0	316.5	306.5	300.3	298.1	293.9
62.5°	314.5	296.4	285.2	277.0	271.6	270.7	267.4
65°	264.3	250.5	240.5	236.7	231.0	229.4	229.4
67.5°	217.9	208.0	200.3	196.7	194.2	194.6	192.7
70°	188.7	180.7	175.7	171.9	170.0	170.4	168.7
72.5°	165.1	156.1	151.8	149.5	146.9	147.9	147.3
75°	125.0	120.5	118.2	115.8	114.3	113.5	112.8
77.5°	91.8	87.8	86.0	84.7	84.9	83.1	84.5
80°	71.0	67.6	66.3	64.4	64.0	64.0	63.7
82.5°	51.9	50.0	49.2	47.6	46.9	47.5	46.5
85°	26.9	25.3	24.9	24.9	24.1	23.4	25.3
87.5°	13.6	12.6	13.0	12.7	12.7	12.6	12.0
90°	19.2	20.2	22.2	22.2	22.2	23.2	23.2
92.5°	129.7	97.6	82.7	69.8	67.4	65.9	64.3
95°	571.6	447.6	362.9	291.3	261.2	253.1	236.9
97.5°	972.0	851.2	733.5	671.3	614.7	585.5	572.6
100°	1190.6	1086.7	981.9	912.3	839.8	802.4	786.4
102.5°	1324.4	1274.7	1203.7	1129.3	1077.7	1037.1	1025.0
105°	1400.3	1444.6	1433.5	1401.3	1368.1	1347.9	1335.7
107.5°	1332.7	1446.6	1499.2	1515.6	1515.4	1508.7	1500.7
110°	1256.1	1398.3	1484.0	1529.3	1548.4	1555.5	1555.5



TEST NUMBER: P333189-840

CATALOG NUMBER: S125DIP-S610D1035U840-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	330°	335°	340°	345°	350°	355°	360°
112.5°	1180.3	1324.0	1425.1	1491.4	1524.3	1541.9	1549.0
115°	1071.7	1209.7	1319.6	1398.3	1446.6	1474.9	1488.0
117.5°	996.4	1115.4	1216.2	1294.8	1344.8	1372.8	1380.9
120°	953.7	1064.6	1153.3	1227.9	1276.3	1303.5	1311.6
122.5°	923.0	1021.8	1104.9	1171.4	1215.8	1243.0	1250.3
125°	882.1	969.8	1042.4	1098.8	1140.1	1162.4	1172.5
127.5°	843.0	924.8	992.8	1044.0	1080.5	1101.5	1105.9
130°	815.6	894.2	959.8	1010.2	1043.4	1063.6	1069.6
132.5°	789.7	861.1	924.2	974.6	1007.9	1026.4	1033.3
135°	750.0	814.6	872.0	916.4	949.7	967.8	973.8
137.5°	714.6	768.2	817.0	856.7	887.0	903.7	910.3
140°	693.6	739.9	782.3	819.6	845.9	860.9	866.0
142.5°	675.8	715.8	752.5	784.2	806.3	820.6	824.9
145°	653.3	684.5	711.8	735.9	753.1	764.2	768.2
147.5°	634.5	658.5	679.0	698.2	712.0	718.4	720.2
150°	624.0	643.2	661.4	676.4	688.5	692.6	693.6
152.5°	613.5	631.1	645.2	657.9	667.6	671.6	672.6
155°	597.8	612.0	623.0	633.1	640.2	643.2	644.2
157.5°	582.9	593.8	602.5	610.4	616.1	618.9	618.7
160°	571.6	581.7	588.8	595.8	600.9	602.9	601.9
162.5°	561.9	570.4	576.6	582.1	586.3	586.7	586.5
165°	547.4	553.5	558.5	562.5	564.5	564.5	564.5
167.5°	533.3	538.0	541.6	543.6	545.4	544.6	544.4
170°	525.2	528.3	530.3	532.3	533.3	533.3	532.3
172.5°	518.0	520.2	521.4	521.8	523.6	522.0	521.0
175°	507.1	509.1	509.1	509.1	510.1	508.1	507.1
177.5°	502.4	502.4	502.4	501.6	502.4	500.0	500.0
180°	500.0	500.0	500.0	500.0	500.0	500.0	500.0

(END OF REPORT)