

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P331262-830

Luminaire Tested: **SA2XXDIP-C290D725U830-4F0-1E-UDD-D1**

Issue Date: 10/7/2019

Test Information

Test Method: LM-79-08
Report Number: P331262-830
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-8,
Test Lab: INNOVATION CENTER
Issue Date: 10/7/2019
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: NEO-RAY
Catalog Number: SA2XXDIP-C290D725U830-4F0-1E-UDD-D1
Description: DEFINE 2 DIRECT-INDIRECT PENDANT LED LUMINAIRE
DOWNLIGHT 290 LUMENS PER FOOT, DROP SATIN WHITE DIFFUSER
UPLIGHT 725 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER
Light Source: -
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 3571.7 lumens
Efficiency: N/A
Efficacy: 114.5 lumens/watt
Spacing Criteria (0/90/45): 1.21 / 1.31 / 1.42
Luminous Opening: Rectangular w/ Sides (W: 0.17' x L: 4' x H: 0.08')
CIE Type: Semi-Indirect


Input Watts (W): 31.2
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P331262-830

CATALOG NUMBER: SA2XXDIP-C290D725U830-4F0-1E-UDD-D1

Luminous Intensity Polar Plot





TEST NUMBER: P331262-830

CATALOG NUMBER: SA2XXDIP-C290D725U830-4F0-1E-UDD-D1

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	102	102	102	102	91	91	91	91	71	71	71	53	53	53	36	36	36	28
1	92	87	83	80	82	78	75	72	61	59	56	45	44	42	30	30	29	22
2	83	76	70	64	74	68	63	58	53	49	46	39	37	34	26	25	23	18
3	76	66	59	53	67	59	53	48	46	42	38	34	31	29	23	21	20	15
4	69	58	51	44	61	52	46	40	41	36	32	30	27	24	20	18	17	12
5	63	52	44	38	56	46	39	34	36	31	27	27	24	21	18	16	14	11
6	58	46	38	32	52	41	35	29	33	27	24	24	21	18	16	14	12	9
7	54	41	34	28	48	37	30	26	29	24	21	22	18	16	15	13	11	8
8	50	37	30	25	44	34	27	22	27	22	18	20	16	14	14	11	10	7
9	46	34	27	22	41	31	24	20	24	19	16	18	15	12	13	10	9	6
10	43	31	24	19	38	28	22	18	22	18	14	17	13	11	12	9	8	6

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	4771	4771	4771
5°	4794	4593	4573
10°	4763	4457	4407
15°	4698	4312	4229
20°	4614	4159	4059
25°	4533	4009	3902
30°	4418	3857	3747
35°	4301	3711	3638
40°	4178	3584	3528
45°	4060	3473	3434
50°	3936	3371	3343
55°	3802	3261	3248
60°	3643	3149	3150
65°	3474	3016	3031
70°	3286	2872	2904
75°	3050	2735	2786
80°	2669	2592	2667
85°	2319	2468	2574



TEST NUMBER: P331262-830

CATALOG NUMBER: SA2XXDIP-C290D725U830-4F0-1E-UDD-D1

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	28.0	0.8
10°-20°	80.3	2.2
20°-30°	121.6	3.4
30°-40°	148.2	4.1
40°-50°	159.4	4.5
50°-60°	154.8	4.3
60°-70°	135.2	3.8
70°-80°	104.1	2.9
80°-90°	73.3	2.1
90°-100°	103.4	2.9
100°-110°	206.9	5.8
110°-120°	316.9	8.9
120°-130°	399.2	11.2
130°-140°	438.9	12.3
140°-150°	426.0	11.9
150°-160°	356.5	10.0
160°-170°	236.5	6.6
170°-180°	82.6	2.3
0°-30°	229.9	6.4
0°-40°	378.1	10.6
0°-60°	692.3	19.4
0°-90°	1004.8	28.1
90°-120°	627.3	17.6
90°-150°	1891.3	53.0
90°-180°	2567.0	71.9
0°-180°	3571.7	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	296	296	296	296	296	
5°	296	295	292	295	294	28
15°	283	283	283	287	287	80
25°	257	260	264	269	270	118
35°	221	229	237	246	249	138
45°	182	193	208	221	226	140
55°	139	155	177	192	198	124
65°	95	116	141	158	164	94
75°	53	77	104	122	128	56
85°	16	42	69	87	93	17
90°	5	39	82	97	104	5
95°	42	69	96	112	116	47
105°	160	176	199	215	220	170
115°	296	306	323	335	338	293
125°	430	436	448	457	460	384
135°	555	563	569	577	578	429
145°	673	678	683	686	685	421
155°	770	772	774	778	776	354
165°	838	837	837	842	838	236
175°	872	869	868	872	869	83
180°	873	873	873	873	873	



TEST NUMBER: P331262-830

CATALOG NUMBER: SA2XXDIP-C290D725U830-4F0-1E-UDD-D1

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	295.5	295.5	295.5	295.5	295.5	295.5	295.5	295.5	295.5	295.5	295.5
2.5°	297.2	296.9	296.7	296.4	296.2	295.9	295.3	294.8	294.3	293.7	294.1
5°	296.3	296.1	295.8	295.5	295.1	294.7	294.2	293.6	293.0	292.5	293.0
7.5°	293.6	293.4	293.2	293.0	292.8	292.6	292.1	291.7	291.2	290.8	291.5
10°	291.6	291.4	291.2	291.1	290.9	290.6	290.3	290.0	289.7	289.5	290.2
12.5°	288.1	288.2	288.2	288.3	288.3	288.2	288.0	287.9	287.6	287.4	288.1
15°	282.6	282.8	283.0	283.1	283.3	283.4	283.4	283.4	283.4	283.4	284.3
17.5°	275.4	275.8	276.2	276.6	277.0	277.4	277.7	278.0	278.2	278.6	279.5
20°	270.6	271.1	271.5	272.0	272.5	273.0	273.3	273.7	274.1	274.5	275.5
22.5°	265.5	266.0	266.6	267.1	267.7	268.2	268.7	269.3	269.8	270.3	271.4
25°	256.9	257.6	258.3	258.9	259.6	260.3	261.2	262.0	262.9	263.7	264.9
27.5°	246.7	247.7	248.8	249.9	251.0	252.0	253.0	254.0	255.1	256.1	257.5
30°	239.8	241.0	242.2	243.5	244.7	246.0	247.2	248.5	249.7	250.9	252.4
32.5°	232.2	233.7	235.0	236.4	237.8	239.2	240.7	242.1	243.6	245.1	246.9
35°	221.4	223.0	224.6	226.2	227.8	229.5	231.4	233.2	235.0	236.8	238.8
37.5°	209.5	211.4	213.3	215.2	217.0	219.1	221.5	223.8	226.1	228.5	230.8
40°	201.7	203.8	205.9	207.9	210.0	212.4	214.9	217.5	220.1	222.6	225.1
42.5°	194.2	196.2	198.3	200.4	202.6	205.0	208.0	210.9	213.9	216.8	219.5
45°	181.5	184.1	186.7	189.3	191.8	194.7	198.1	201.4	204.7	208.1	211.0
47.5°	169.1	171.9	174.7	177.5	180.3	183.7	187.6	191.4	195.4	199.3	202.4
50°	160.6	163.5	166.5	169.4	172.4	176.0	180.3	184.5	188.8	193.1	196.3
52.5°	152.3	155.4	158.5	161.6	164.8	168.5	173.1	177.6	182.1	186.6	189.9
55°	139.1	142.6	146.0	149.4	152.9	157.0	162.0	166.9	171.9	176.8	180.3
57.5°	126.1	130.0	133.8	137.7	141.6	146.0	151.1	156.1	161.2	166.3	169.9
60°	116.9	121.0	125.1	129.1	133.3	138.0	143.5	148.8	154.3	159.7	163.3
62.5°	108.7	112.9	117.2	121.4	125.6	130.4	135.9	141.3	146.8	152.2	156.0
65°	95.0	99.7	104.3	109.1	113.7	118.9	124.4	130.1	135.7	141.3	145.2
67.5°	82.6	87.5	92.3	97.2	102.1	107.4	113.1	118.9	124.6	130.4	134.3
70°	73.6	78.6	83.5	88.5	93.4	98.9	104.7	110.7	116.6	122.4	126.6
72.5°	65.4	70.5	75.6	80.7	85.9	91.3	97.4	103.3	109.3	115.3	119.3
75°	52.7	58.0	63.3	68.6	74.0	79.6	85.8	91.9	97.9	104.1	108.1
77.5°	40.3	45.9	51.5	57.0	62.7	68.5	74.7	80.9	87.1	93.2	97.4
80°	32.1	37.9	43.7	49.5	55.3	61.4	67.5	73.7	79.8	86.1	90.0
82.5°	25.3	31.0	36.8	42.4	48.2	54.2	60.4	66.7	73.0	79.2	83.2
85°	15.5	21.3	27.2	33.1	39.0	45.0	51.1	57.2	63.2	69.4	73.3
87.5°	8.6	14.6	20.6	26.8	32.8	39.2	46.0	52.9	59.7	66.4	70.3
90°	5.0	12.5	20.0	27.4	35.0	43.5	53.3	63.0	72.6	82.3	85.8
92.5°	17.1	23.7	30.3	36.8	43.4	50.0	56.7	63.4	70.1	76.9	80.7
95°	41.8	47.9	53.9	60.0	66.2	72.2	78.3	84.4	90.4	96.4	100.0
97.5°	73.0	78.4	83.8	89.3	94.6	100.4	106.5	112.6	118.8	124.8	128.4
100°	96.5	101.4	106.2	111.0	115.8	121.2	127.1	132.8	138.6	144.5	148.0
102.5°	120.9	125.3	129.5	133.7	138.0	143.1	148.8	154.7	160.4	166.3	169.8
105°	160.5	163.8	167.0	170.3	173.5	177.8	183.0	188.3	193.6	198.9	202.6
107.5°	200.9	203.8	206.7	209.6	212.5	216.4	221.1	225.8	230.5	235.4	238.7
110°	226.4	229.3	232.1	235.1	238.0	241.8	246.4	251.1	255.7	260.4	263.4



TEST NUMBER: P331262-830

CATALOG NUMBER: SA2XXDIP-C290D725U830-4F0-1E-UDD-D1

CANDELA DISTRIBUTION (continued):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	254.7	257.3	259.9	262.4	265.0	268.4	272.8	277.1	281.3	285.7	288.3
115°	296.4	298.4	300.5	302.5	304.5	307.6	311.5	315.4	319.3	323.3	326.0
117.5°	337.5	339.5	341.5	343.6	345.5	348.0	351.1	354.1	357.1	360.1	362.6
120°	365.2	366.9	368.6	370.3	372.0	374.1	376.5	379.1	381.5	384.1	386.7
122.5°	390.6	392.3	394.0	395.8	397.5	399.6	402.3	405.0	407.6	410.3	412.5
125°	429.6	431.1	432.6	434.0	435.5	437.5	440.1	442.6	445.2	447.8	449.9
127.5°	468.1	469.9	471.6	473.4	475.1	477.0	478.9	480.7	482.6	484.5	486.3
130°	492.3	494.3	496.3	498.3	500.4	502.3	503.9	505.6	507.3	508.9	510.9
132.5°	519.3	521.0	522.6	524.2	525.9	527.5	529.1	530.7	532.3	534.0	535.5
135°	555.2	556.9	558.8	560.6	562.4	563.9	565.2	566.5	567.8	569.0	570.9
137.5°	593.3	594.8	596.3	597.7	599.2	600.3	601.2	602.0	602.9	603.7	605.3
140°	616.3	617.7	619.1	620.5	621.9	623.0	624.1	625.1	626.0	627.1	628.6
142.5°	639.9	641.3	642.6	644.0	645.5	646.4	647.0	647.6	648.2	648.8	650.2
145°	673.4	674.5	675.7	676.8	678.0	679.0	680.0	681.0	681.9	683.0	683.7
147.5°	703.6	704.9	706.3	707.7	709.1	710.1	710.8	711.4	712.1	712.8	713.1
150°	724.2	725.2	726.1	727.2	728.1	729.0	729.6	730.3	730.9	731.6	732.1
152.5°	742.4	743.5	744.4	745.5	746.4	747.2	748.1	748.9	749.6	750.5	751.0
155°	769.9	770.3	770.9	771.4	771.8	772.3	772.8	773.4	773.8	774.3	775.1
157.5°	793.3	793.6	794.0	794.3	794.7	794.9	795.2	795.5	795.8	796.1	797.2
160°	807.5	807.8	808.1	808.4	808.8	809.0	809.2	809.4	809.5	809.6	810.7
162.5°	820.4	820.5	820.6	820.6	820.7	820.8	821.0	821.1	821.3	821.4	822.6
165°	837.6	837.5	837.4	837.2	837.0	836.9	836.9	836.9	836.9	836.9	838.1
167.5°	852.1	851.6	851.1	850.6	850.2	849.9	849.9	849.8	849.8	849.7	850.9
170°	859.8	859.3	858.8	858.3	857.8	857.4	857.3	857.1	857.0	856.8	858.0
172.5°	865.1	864.6	864.1	863.6	863.1	862.8	862.6	862.4	862.3	862.1	863.3
175°	871.6	871.1	870.5	870.1	869.6	869.2	868.8	868.6	868.2	867.9	869.0
177.5°	874.2	873.8	873.5	873.0	872.6	872.3	872.0	871.8	871.5	871.3	872.0
180°	873.0	873.0	873.0	873.0	873.0	873.0	873.0	873.0	873.0	873.0	873.0



TEST NUMBER: P331262-830

CATALOG NUMBER: SA2XXDIP-C290D725U830-4F0-1E-UDD-D1

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°
0°	295.5	295.5	295.5	295.5	295.5	295.5	295.5	295.5
2.5°	294.5	294.8	295.2	295.4	295.2	295.0	294.9	294.7
5°	293.6	294.2	294.7	294.9	294.8	294.7	294.6	294.5
7.5°	292.2	292.8	293.6	293.9	293.8	293.7	293.6	293.5
10°	291.0	291.7	292.5	292.8	292.8	292.7	292.6	292.5
12.5°	288.9	289.6	290.4	290.8	290.7	290.6	290.5	290.4
15°	285.1	286.1	286.9	287.3	287.2	287.1	287.0	286.9
17.5°	280.4	281.3	282.1	282.6	282.6	282.6	282.6	282.6
20°	276.5	277.6	278.6	279.2	279.2	279.2	279.2	279.2
22.5°	272.5	273.5	274.6	275.1	275.3	275.4	275.6	275.8
25°	266.1	267.2	268.3	269.0	269.3	269.6	269.8	270.1
27.5°	258.9	260.4	261.8	262.7	262.9	263.1	263.3	263.5
30°	253.9	255.5	257.0	257.9	258.2	258.4	258.7	259.0
32.5°	248.5	250.3	252.1	253.3	253.7	254.3	254.8	255.2
35°	241.0	243.1	245.2	246.6	247.2	247.9	248.5	249.2
37.5°	233.1	235.4	237.8	239.3	240.0	240.7	241.4	242.0
40°	227.6	230.1	232.5	234.2	235.1	235.9	236.8	237.6
42.5°	222.3	224.9	227.6	229.4	230.3	231.1	232.0	232.8
45°	214.0	217.0	219.9	221.9	222.8	223.8	224.7	225.6
47.5°	205.5	208.5	211.6	213.7	214.7	215.7	216.8	217.8
50°	199.5	202.8	206.0	208.2	209.2	210.3	211.3	212.4
52.5°	193.2	196.5	199.8	202.1	203.2	204.3	205.5	206.5
55°	183.7	187.1	190.6	192.8	194.1	195.4	196.6	197.8
57.5°	173.6	177.3	181.0	183.4	184.7	186.0	187.2	188.5
60°	166.9	170.6	174.2	176.6	178.0	179.3	180.7	182.0
62.5°	159.9	163.7	167.6	170.1	171.4	172.6	173.9	175.1
65°	149.1	153.0	156.9	159.5	160.7	161.9	163.2	164.4
67.5°	138.2	142.1	146.1	148.7	150.0	151.3	152.6	153.9
70°	130.6	134.7	138.8	141.5	142.6	143.7	144.9	146.0
72.5°	123.3	127.3	131.3	134.0	135.3	136.8	138.2	139.5
75°	112.3	116.3	120.5	123.1	124.3	125.5	126.8	128.0
77.5°	101.4	105.5	109.5	112.3	113.6	114.9	116.2	117.5
80°	94.1	98.0	102.1	104.7	106.0	107.4	108.7	110.0
82.5°	87.2	91.2	95.2	97.8	99.1	100.4	101.6	102.8
85°	77.4	81.3	85.4	88.0	89.4	90.7	92.0	93.3
87.5°	74.1	77.9	81.7	84.3	85.5	86.8	88.0	89.3
90°	89.3	92.7	96.2	98.6	99.9	101.2	102.5	103.9
92.5°	84.5	88.2	92.1	94.5	95.7	96.9	98.0	99.2
95°	103.6	107.3	110.8	113.1	113.9	114.7	115.6	116.3
97.5°	131.9	135.3	138.9	141.2	142.3	143.4	144.5	145.6
100°	151.6	155.0	158.5	160.8	161.6	162.5	163.4	164.3
102.5°	173.4	177.0	180.6	182.8	183.7	184.5	185.4	186.3
105°	206.2	209.9	213.6	215.8	217.0	218.0	219.0	220.1
107.5°	242.0	245.3	248.6	250.4	250.7	251.0	251.3	251.7
110°	266.5	269.5	272.6	274.4	274.9	275.5	276.1	276.5



TEST NUMBER: P331262-830

CATALOG NUMBER: SA2XXDIP-C290D725U830-4F0-1E-UDD-D1

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°
112.5°	291.0	293.6	296.3	297.9	298.7	299.4	300.0	300.7
115°	328.7	331.4	334.1	335.7	336.3	336.9	337.3	337.9
117.5°	365.0	367.5	369.9	371.4	371.8	372.3	372.8	373.2
120°	389.4	392.1	394.7	396.3	396.9	397.5	398.0	398.6
122.5°	414.7	416.9	419.1	420.5	420.9	421.5	422.1	422.5
125°	451.9	454.0	456.1	457.4	458.2	458.8	459.5	460.2
127.5°	488.0	489.7	491.5	492.6	492.9	493.2	493.5	493.8
130°	512.8	514.8	516.7	517.7	517.9	518.0	518.1	518.2
132.5°	537.0	538.5	539.9	540.8	541.0	541.3	541.5	541.8
135°	572.7	574.6	576.4	577.4	577.7	578.0	578.2	578.5
137.5°	606.9	608.6	610.2	611.0	611.0	611.0	611.0	611.0
140°	630.1	631.7	633.2	633.9	633.8	633.8	633.7	633.6
142.5°	651.5	652.8	654.2	654.8	654.6	654.5	654.3	654.1
145°	684.4	685.1	685.9	686.2	686.0	685.8	685.6	685.4
147.5°	713.6	714.0	714.4	714.4	714.1	713.7	713.3	712.9
150°	732.5	733.0	733.6	733.6	733.0	732.5	732.1	731.6
152.5°	751.7	752.3	752.9	752.9	752.3	751.7	751.0	750.5
155°	775.9	776.7	777.6	777.8	777.2	776.7	776.3	775.8
157.5°	798.3	799.5	800.6	800.7	799.9	799.2	798.3	797.6
160°	811.6	812.7	813.6	813.8	813.1	812.5	811.8	811.2
162.5°	823.7	824.8	826.0	826.0	825.3	824.5	823.7	822.9
165°	839.2	840.4	841.5	841.7	840.8	840.0	839.2	838.4
167.5°	852.1	853.2	854.3	854.5	853.7	852.8	852.0	851.1
170°	859.1	860.3	861.4	861.5	860.5	859.5	858.6	857.5
172.5°	864.4	865.5	866.7	866.8	865.8	864.8	863.8	862.9
175°	870.2	871.3	872.4	872.5	871.6	870.5	869.6	868.6
177.5°	872.8	873.6	874.4	874.4	873.6	872.8	872.0	871.3
180°	873.0	873.0	873.0	873.0	873.0	873.0	873.0	873.0

(END OF REPORT)