

Scaled data based on original data using  
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State  
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P331265-830

Luminaire Tested: **SA2XXDIP-C290D725U830-4F0-1E-UDD-F1**

Issue Date: 10/7/2019

**Test Information**

Test Method: LM-79-08  
Report Number: P331265-830  
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-8,  
Test Lab: INNOVATION CENTER  
Issue Date: 10/7/2019  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: NEO-RAY  
Catalog Number: SA2XXDIP-C290D725U830-4F0-1E-UDD-F1  
Description: DEFINE 2 DIRECT-INDIRECT PENDANT LED LUMINAIRE  
DOWNLIGHT 290 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER  
UPLIGHT 725 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER  
Light Source: -  
Ballast/Driver: ELECTRONIC DRIVER

**Summary**


Lumens per Lamp: N/A  
Luminaire Lumens: 3577.5 lumens  
Efficiency: N/A  
Efficacy: 114.7 lumens/watt  
Spacing Criteria (0/90/45): 1.2 / 1.16 / 1.3  
Luminous Opening: Rectangular (W 0.17' x L: 4' x H: 0')  
CIE Type: Semi-Indirect

Input Watts (W): 31.2  
Input Voltage (V): 120  
Input Current (Ain): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 25 FT



TEST NUMBER: P331265-830  
CATALOG NUMBER: SA2XXDIP-C290D725U830-4F0-1E-UDD-F1

### Luminous Intensity Polar Plot





TEST NUMBER: P331265-830

CATALOG NUMBER: SA2XXDIP-C290D725U830-4F0-1E-UDD-F1

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	103	103	103	103	92	92	92	92	73	73	73	56	56	56	39	39	39	32
1	94	89	86	82	84	81	77	75	64	62	60	49	47	46	35	34	33	27
2	85	78	72	67	76	70	65	61	56	53	50	43	40	38	31	29	28	22
3	78	69	61	56	70	62	56	51	49	45	42	38	35	32	27	25	24	19
4	71	61	53	47	64	55	48	43	44	39	35	34	30	28	24	22	20	16
5	65	54	46	40	58	49	42	37	39	34	30	30	27	24	22	20	18	14
6	60	48	40	35	54	44	37	32	35	30	26	27	24	21	20	17	16	12
7	55	43	36	30	50	39	33	28	32	27	23	25	21	18	18	16	14	11
8	51	39	32	27	46	36	29	25	29	24	20	23	19	16	16	14	12	10
9	48	36	28	24	43	33	26	22	26	22	18	21	17	15	15	13	11	9
10	44	33	26	21	40	30	24	19	24	20	16	19	16	13	14	12	10	8

**AVERAGE LUMINANCE (cd/sqm):**

	0°	45°	90°
0°	7190	7190	7190
5°	7217	7112	7156
10°	7174	7040	7076
15°	7086	6950	6944
20°	6959	6813	6806
25°	6834	6645	6645
30°	6674	6490	6434
35°	6524	6303	6211
40°	6336	6119	6001
45°	6149	5934	5786
50°	5948	5745	5541
55°	5737	5520	5315
60°	5503	5254	5060
65°	5249	4989	4760
70°	4928	4669	4447
75°	4485	4298	4192
80°	3980	3868	3663
85°	3242	3094	2779



TEST NUMBER: P331265-830

CATALOG NUMBER: SA2XXDIP-C290D725U830-4F0-1E-UDD-F1

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	41.9	1.2
10°-20°	117.8	3.3
20°-30°	173.2	4.8
30°-40°	201.2	5.6
40°-50°	200.9	5.6
50°-60°	175.2	4.9
60°-70°	129.6	3.6
70°-80°	73.4	2.1
80°-90°	23.2	0.6
90°-100°	55.3	1.5
100°-110°	171.8	4.8
110°-120°	293.7	8.2
120°-130°	386.2	10.8
130°-140°	433.5	12.1
140°-150°	425.0	11.9
150°-160°	356.5	10.0
160°-170°	236.5	6.6
170°-180°	82.6	2.3
0°-30°	332.9	9.3
0°-40°	534.0	14.9
0°-60°	910.2	25.4
0°-90°	1136.4	31.8
90°-120°	520.8	14.6
90°-150°	1765.5	49.4
90°-180°	2441.0	68.2
0°-180°	3577.5	100.0

**CANDELA DISTRIBUTION:**

	0°	22.5°	45°	67.5°	90°	Flux
0°	445	445	445	445	445	
5°	445	443	439	442	442	42
15°	424	421	416	417	415	119
25°	384	380	373	374	373	176
35°	331	327	320	317	315	207
45°	269	266	260	255	253	208
55°	204	201	196	191	189	182
65°	137	135	131	127	125	136
75°	72	71	69	66	67	77
85°	18	17	17	16	15	20
90°	1	10	26	24	25	3
95°	38	45	47	47	46	44
105°	158	161	162	163	164	167
115°	295	299	298	297	295	291
125°	429	435	433	431	430	383
135°	555	562	564	564	561	428
145°	673	678	683	683	681	421
155°	770	772	774	778	776	354
165°	838	837	837	842	838	236
175°	872	869	868	872	869	83
180°	873	873	873	873	873	



TEST NUMBER: P331265-830

CATALOG NUMBER: SA2XXDIP-C290D725U830-4F0-1E-UDD-F1

**CANDELA DISTRIBUTION (FULL):**

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	445.3	445.3	445.3	445.3	445.3	445.3	445.3	445.3	445.3	445.3	445.3
2.5°	447.3	447.0	446.6	446.2	445.8	445.3	444.4	443.6	442.7	441.9	442.6
5°	445.3	444.9	444.5	444.1	443.7	443.1	442.1	441.0	439.9	438.8	439.6
7.5°	441.4	440.7	440.2	439.6	439.0	438.2	437.2	436.0	435.0	433.9	434.7
10°	437.6	437.0	436.3	435.6	434.9	434.0	432.9	431.8	430.6	429.4	430.2
12.5°	432.4	431.9	431.3	430.6	430.1	429.2	428.1	427.0	425.8	424.7	425.2
15°	423.9	423.3	422.7	422.2	421.6	420.8	419.4	418.2	417.0	415.8	416.1
17.5°	412.9	412.4	411.8	411.2	410.7	409.7	408.5	407.2	406.0	404.7	405.1
20°	405.0	404.4	403.9	403.3	402.7	401.8	400.5	399.2	397.8	396.5	396.8
22.5°	397.2	396.3	395.6	394.7	394.0	392.9	391.7	390.4	389.2	388.0	388.0
25°	383.6	382.9	382.1	381.4	380.6	379.4	377.8	376.2	374.6	373.0	373.2
27.5°	368.3	367.6	366.8	366.2	365.5	364.5	363.3	361.9	360.7	359.4	359.1
30°	358.0	357.2	356.5	355.7	354.9	353.8	352.4	351.0	349.5	348.1	347.8
32.5°	346.9	346.4	345.8	345.2	344.6	343.5	342.0	340.5	339.0	337.5	337.0
35°	331.0	330.0	329.0	328.1	327.2	325.9	324.4	322.9	321.4	319.8	319.2
37.5°	312.9	312.1	311.2	310.4	309.5	308.4	306.9	305.4	303.8	302.3	301.6
40°	300.6	299.8	299.1	298.3	297.6	296.4	294.8	293.3	291.8	290.3	289.5
42.5°	288.6	287.9	287.1	286.3	285.6	284.4	282.9	281.3	279.8	278.3	277.4
45°	269.3	268.6	268.0	267.3	266.6	265.6	264.2	262.8	261.4	259.9	258.8
47.5°	250.2	249.5	248.9	248.3	247.6	246.6	245.1	243.6	242.1	240.6	239.5
50°	236.8	236.3	235.8	235.4	234.9	233.9	232.6	231.3	230.0	228.7	227.3
52.5°	223.8	223.1	222.5	221.9	221.2	220.3	219.0	217.8	216.5	215.3	214.1
55°	203.8	203.2	202.6	202.1	201.5	200.7	199.5	198.4	197.3	196.1	194.9
57.5°	183.8	183.3	182.9	182.4	181.9	181.1	179.8	178.6	177.3	176.1	174.9
60°	170.4	170.0	169.7	169.3	168.9	168.1	166.7	165.4	164.0	162.7	161.6
62.5°	157.4	156.7	156.2	155.6	155.0	154.1	153.1	152.1	151.1	150.1	149.0
65°	137.4	136.9	136.3	135.7	135.2	134.4	133.5	132.5	131.6	130.6	129.7
67.5°	117.2	116.7	116.2	115.7	115.4	114.7	113.8	112.9	112.1	111.2	110.6
70°	104.4	104.1	103.7	103.3	102.9	102.4	101.5	100.7	99.7	98.9	98.2
72.5°	91.4	91.0	90.7	90.3	89.9	89.4	88.9	88.4	87.8	87.3	86.6
75°	71.9	71.7	71.5	71.4	71.2	70.9	70.4	69.8	69.4	68.9	68.3
77.5°	54.5	54.1	53.8	53.5	53.2	52.9	52.7	52.5	52.3	52.1	51.8
80°	42.8	42.7	42.6	42.5	42.4	42.3	42.1	41.9	41.8	41.6	41.3
82.5°	31.9	31.9	31.9	31.8	31.8	31.7	31.6	31.5	31.4	31.3	30.9
85°	17.5	17.4	17.3	17.2	17.2	17.1	17.0	16.9	16.8	16.7	16.4
87.5°	6.3	6.6	6.8	7.1	7.3	7.6	8.3	8.9	9.4	10.0	9.6
90°	0.8	2.7	4.7	6.6	8.6	11.4	15.0	18.6	22.1	25.8	25.4
92.5°	13.1	14.5	16.0	17.4	18.9	20.0	20.8	21.7	22.6	23.5	23.5
95°	38.3	40.0	41.6	43.3	44.9	45.8	46.2	46.5	46.8	47.1	47.1
97.5°	70.0	71.4	72.9	74.3	75.8	76.8	77.4	78.0	78.6	79.3	79.3
100°	93.6	94.9	96.1	97.5	98.8	99.7	100.2	100.7	101.1	101.7	101.7
102.5°	118.3	119.3	120.5	121.5	122.5	123.4	123.9	124.6	125.2	125.8	125.9
105°	158.4	158.9	159.4	159.9	160.3	160.8	161.1	161.5	161.7	162.1	162.4
107.5°	198.8	199.5	200.2	201.0	201.6	202.0	202.0	202.0	202.0	202.0	202.2
110°	224.7	225.6	226.7	227.6	228.7	229.1	229.1	229.1	229.1	229.1	229.1



TEST NUMBER: P331265-830

CATALOG NUMBER: SA2XXDIP-C290D725U830-4F0-1E-UDD-F1

**CANDELA DISTRIBUTION (continued):**

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	253.0	254.0	255.0	255.9	256.9	257.3	257.2	257.1	256.9	256.8	256.5
115°	294.7	295.7	296.6	297.7	298.6	299.0	298.6	298.3	297.9	297.7	297.5
117.5°	336.2	337.5	338.8	340.2	341.5	341.7	340.7	339.9	338.9	338.0	337.6
120°	363.9	365.2	366.6	367.9	369.2	369.2	367.9	366.6	365.2	363.9	363.9
122.5°	389.3	390.9	392.5	394.0	395.6	395.9	395.0	394.1	393.1	392.2	391.8
125°	428.8	430.3	431.7	433.2	434.7	435.2	434.7	434.1	433.7	433.2	432.7
127.5°	467.2	469.1	471.0	472.9	474.7	475.3	474.8	474.2	473.5	473.0	472.4
130°	491.4	493.5	495.7	497.8	499.9	500.8	500.5	500.1	499.8	499.5	499.2
132.5°	518.5	520.3	522.0	523.7	525.5	526.3	526.4	526.5	526.5	526.6	525.9
135°	554.8	556.6	558.4	560.2	561.9	563.0	563.4	563.6	564.0	564.3	564.2
137.5°	593.0	594.4	595.9	597.4	598.8	599.7	600.2	600.6	601.1	601.4	601.3
140°	616.0	617.4	618.9	620.3	621.8	622.9	623.8	624.6	625.4	626.2	626.2
142.5°	639.5	640.9	642.4	643.9	645.4	646.4	647.0	647.5	648.1	648.7	648.8
145°	673.4	674.5	675.7	676.8	678.0	679.0	680.0	681.0	681.9	683.0	683.2
147.5°	703.6	704.9	706.3	707.7	709.1	710.1	710.8	711.4	712.1	712.8	713.0
150°	724.2	725.2	726.1	727.2	728.1	729.0	729.6	730.3	730.9	731.6	732.1
152.5°	742.4	743.5	744.4	745.5	746.4	747.2	748.1	748.9	749.6	750.5	751.0
155°	769.9	770.3	770.9	771.4	771.8	772.3	772.8	773.4	773.8	774.3	775.1
157.5°	793.3	793.6	794.0	794.3	794.7	794.9	795.2	795.5	795.8	796.1	797.2
160°	807.5	807.8	808.1	808.4	808.8	809.0	809.2	809.4	809.5	809.6	810.7
162.5°	820.4	820.5	820.6	820.6	820.7	820.8	821.0	821.1	821.3	821.4	822.6
165°	837.6	837.5	837.4	837.2	837.0	836.9	836.9	836.9	836.9	836.9	838.1
167.5°	852.1	851.6	851.1	850.6	850.2	849.9	849.9	849.8	849.8	849.7	850.9
170°	859.8	859.3	858.8	858.3	857.8	857.4	857.3	857.1	857.0	856.8	858.0
172.5°	865.1	864.6	864.1	863.6	863.1	862.8	862.6	862.4	862.3	862.1	863.3
175°	871.6	871.1	870.5	870.1	869.6	869.2	868.8	868.6	868.2	867.9	869.0
177.5°	874.2	873.8	873.5	873.0	872.6	872.3	872.0	871.8	871.5	871.3	872.0
180°	873.0	873.0	873.0	873.0	873.0	873.0	873.0	873.0	873.0	873.0	873.0



TEST NUMBER: P331265-830

CATALOG NUMBER: SA2XXDIP-C290D725U830-4F0-1E-UDD-F1

**CANDELA DISTRIBUTION (continued):**

	55°	60°	65°	70°	75°	80°	85°	90°
0°	445.3	445.3	445.3	445.3	445.3	445.3	445.3	445.3
2.5°	443.4	444.1	444.9	445.3	445.1	444.9	444.8	444.6
5°	440.5	441.2	442.0	442.2	442.1	441.9	441.7	441.5
7.5°	435.5	436.2	437.0	437.2	437.1	436.8	436.6	436.4
10°	431.0	431.8	432.5	432.7	432.4	432.2	431.9	431.6
12.5°	425.7	426.2	426.8	427.0	426.8	426.5	426.3	426.1
15°	416.5	416.9	417.3	417.3	416.8	416.3	415.8	415.4
17.5°	405.6	406.0	406.4	406.4	406.0	405.6	405.1	404.6
20°	397.1	397.4	397.7	397.6	397.2	396.8	396.4	396.1
22.5°	388.0	388.1	388.1	388.0	387.9	387.6	387.4	387.2
25°	373.3	373.5	373.7	373.7	373.5	373.3	373.2	373.0
27.5°	358.8	358.5	358.3	357.9	357.4	356.9	356.6	356.1
30°	347.5	347.2	346.9	346.7	346.3	345.9	345.5	345.1
32.5°	336.5	335.9	335.5	335.0	334.6	334.2	333.8	333.5
35°	318.7	318.1	317.5	317.1	316.6	316.1	315.7	315.1
37.5°	300.9	300.2	299.4	298.9	298.4	297.9	297.6	297.1
40°	288.6	287.8	286.9	286.3	285.9	285.5	285.1	284.7
42.5°	276.4	275.5	274.6	273.8	273.3	272.8	272.3	271.7
45°	257.8	256.7	255.7	255.0	254.6	254.2	253.8	253.4
47.5°	238.5	237.3	236.2	235.4	234.9	234.3	233.8	233.2
50°	226.0	224.6	223.3	222.4	222.0	221.5	221.0	220.6
52.5°	213.1	212.0	210.8	210.0	209.3	208.8	208.1	207.5
55°	193.8	192.7	191.5	190.8	190.3	189.7	189.3	188.8
57.5°	173.8	172.7	171.5	170.8	170.5	170.1	169.8	169.4
60°	160.6	159.6	158.5	157.9	157.6	157.3	157.0	156.7
62.5°	148.1	147.1	146.2	145.5	145.2	144.8	144.4	144.0
65°	128.8	128.0	127.1	126.5	126.0	125.5	125.1	124.6
67.5°	109.9	109.2	108.6	108.0	107.6	107.3	106.9	106.5
70°	97.6	96.9	96.2	95.8	95.4	94.9	94.5	94.2
72.5°	86.0	85.3	84.6	84.1	83.8	83.5	83.2	82.8
75°	67.8	67.2	66.6	66.4	66.6	66.8	67.0	67.2
77.5°	51.6	51.3	51.0	50.7	50.4	50.2	50.0	49.7
80°	41.0	40.7	40.4	40.2	40.0	39.8	39.6	39.4
82.5°	30.5	30.2	29.8	29.6	29.6	29.5	29.5	29.5
85°	16.1	15.8	15.6	15.4	15.3	15.2	15.1	15.0
87.5°	9.3	9.0	8.8	8.6	8.6	8.5	8.5	8.4
90°	25.2	24.8	24.5	24.4	24.6	24.7	24.9	25.1
92.5°	23.6	23.7	23.7	23.8	23.8	23.8	23.8	23.8
95°	47.1	47.1	47.1	47.0	46.7	46.4	46.0	45.7
97.5°	79.3	79.3	79.3	79.3	79.3	79.2	79.2	79.1
100°	101.7	101.7	101.7	101.6	101.4	101.2	101.1	100.9
102.5°	126.1	126.2	126.4	126.3	126.2	126.0	125.8	125.6
105°	162.8	163.1	163.4	163.5	163.5	163.5	163.5	163.5
107.5°	202.3	202.4	202.6	202.3	201.5	200.8	200.0	199.3
110°	229.1	229.1	229.1	228.8	228.4	227.9	227.4	226.9





TEST NUMBER: P331265-830

CATALOG NUMBER: SA2XXDIP-C290D725U830-4F0-1E-UDD-F1

**CANDELA DISTRIBUTION (continued):**

	55°	60°	65°	70°	75°	80°	85°	90°
112.5°	256.0	255.6	255.2	254.9	254.5	254.1	253.8	253.4
115°	297.3	297.2	297.0	296.6	296.1	295.7	295.2	294.7
117.5°	337.2	336.9	336.4	336.0	335.5	335.0	334.5	334.0
120°	363.9	363.9	363.9	363.7	363.2	362.7	362.2	361.7
122.5°	391.4	391.1	390.7	390.3	389.9	389.6	389.2	388.9
125°	432.3	431.7	431.2	430.9	430.7	430.6	430.5	430.3
127.5°	471.8	471.2	470.6	470.0	469.6	469.0	468.5	468.0
130°	498.9	498.5	498.2	497.7	497.0	496.4	495.8	495.1
132.5°	525.2	524.4	523.8	523.1	522.5	522.1	521.5	521.0
135°	564.0	563.8	563.6	563.4	562.9	562.4	561.8	561.4
137.5°	601.2	601.1	601.0	600.6	599.9	599.3	598.6	597.9
140°	626.2	626.2	626.2	625.8	625.3	624.6	624.0	623.3
142.5°	648.8	649.0	649.1	648.8	648.2	647.5	647.0	646.3
145°	683.2	683.4	683.6	683.3	682.7	682.0	681.4	680.7
147.5°	713.4	713.8	714.2	714.1	713.4	712.8	712.2	711.5
150°	732.5	733.0	733.6	733.6	733.0	732.5	732.1	731.6
152.5°	751.7	752.3	752.9	752.9	752.3	751.7	751.0	750.5
155°	775.9	776.7	777.6	777.8	777.2	776.7	776.3	775.8
157.5°	798.3	799.5	800.6	800.7	799.9	799.2	798.3	797.6
160°	811.6	812.7	813.6	813.8	813.1	812.5	811.8	811.2
162.5°	823.7	824.8	826.0	826.0	825.3	824.5	823.7	822.9
165°	839.2	840.4	841.5	841.7	840.8	840.0	839.2	838.4
167.5°	852.1	853.2	854.3	854.5	853.7	852.8	852.0	851.1
170°	859.1	860.3	861.4	861.5	860.5	859.5	858.6	857.5
172.5°	864.4	865.5	866.7	866.8	865.8	864.8	863.8	862.9
175°	870.2	871.3	872.4	872.5	871.6	870.5	869.6	868.6
177.5°	872.8	873.6	874.4	874.4	873.6	872.8	872.0	871.3
180°	873.0	873.0	873.0	873.0	873.0	873.0	873.0	873.0

(END OF REPORT)