

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P331271-830

Luminaire Tested: **SA2XXDIP-C290D925U830-4F0-1E-UDD-D1**

Issue Date: 10/7/2019

Test Information

Test Method: LM-79-08
Report Number: P331271-830
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-8,
Test Lab: INNOVATION CENTER
Issue Date: 10/7/2019
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: NEO-RAY
Catalog Number: SA2XXDIP-C290D925U830-4F0-1E-UDD-D1
Description: DEFINE 2 DIRECT-INDIRECT PENDANT LED LUMINAIRE
DOWNLIGHT 290 LUMENS PER FOOT, DROP SATIN WHITE DIFFUSER
UPLIGHT 925 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER
Light Source: -
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 4248.3 lumens
Efficiency: N/A
Efficacy: 113.9 lumens/watt
Spacing Criteria (0/90/45): 1.21 / 1.31 / 1.42
Luminous Opening: Rectangular w/ Sides (W: 0.17' x L: 4' x H: 0.08')
CIE Type: Semi-Indirect


Input Watts (W): 37.3
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P331271-830

CATALOG NUMBER: SA2XXDIP-C290D925U830-4F0-1E-UDD-D1

Luminous Intensity Polar Plot





TEST NUMBER: P331271-830

CATALOG NUMBER: SA2XXDIP-C290D925U830-4F0-1E-UDD-D1

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20					20					20					20					20	
RC	80					70					50					30					10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0	
RCR																						
0	101	101	101	101	90	90	90	90	69	69	69	50	50	50	32	32	32	24				24
1	91	87	83	79	81	77	74	71	59	57	55	42	41	40	27	26	25	18				18
2	83	75	69	64	73	67	62	57	51	48	45	37	34	32	23	22	21	15				15
3	75	66	59	53	66	59	52	47	45	41	37	32	29	27	20	19	17	12				12
4	69	58	50	44	60	52	45	40	40	35	31	28	25	23	18	16	15	10				10
5	63	51	43	38	55	46	39	34	35	30	27	25	22	20	16	14	13	9				9
6	58	46	38	32	51	41	34	29	32	27	23	23	19	17	15	13	11	8				8
7	53	41	33	28	47	37	30	25	28	24	20	21	17	15	13	11	10	7				7
8	49	37	30	24	43	33	27	22	26	21	18	19	15	13	12	10	9	6				6
9	46	34	26	22	40	30	24	20	23	19	16	17	14	12	11	9	8	5				5
10	42	31	24	19	38	28	21	17	21	17	14	16	13	10	10	8	7	5				5

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	4771	4771	4771
5°	4794	4593	4573
10°	4763	4457	4407
15°	4698	4312	4229
20°	4614	4159	4059
25°	4533	4009	3902
30°	4418	3857	3747
35°	4301	3711	3638
40°	4178	3584	3528
45°	4060	3473	3434
50°	3936	3371	3343
55°	3802	3261	3248
60°	3643	3149	3150
65°	3474	3016	3031
70°	3286	2872	2904
75°	3050	2735	2786
80°	2669	2592	2667
85°	2319	2468	2574



TEST NUMBER: P331271-830

CATALOG NUMBER: SA2XXDIP-C290D925U830-4F0-1E-UDD-D1

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	28.0	0.7
10°-20°	80.3	1.9
20°-30°	121.6	2.9
30°-40°	148.2	3.5
40°-50°	159.4	3.8
50°-60°	154.8	3.6
60°-70°	135.2	3.2
70°-80°	104.1	2.4
80°-90°	74.3	1.7
90°-100°	118.7	2.8
100°-110°	254.5	6.0
110°-120°	398.2	9.4
120°-130°	506.0	11.9
130°-140°	558.9	13.2
140°-150°	543.6	12.8
150°-160°	455.2	10.7
160°-170°	301.9	7.1
170°-180°	105.5	2.5
0°-30°	229.9	5.4
0°-40°	378.1	8.9
0°-60°	692.3	16.3
0°-90°	1005.8	23.7
90°-120°	771.4	18.2
90°-150°	2379.9	56.0
90°-180°	3242.0	76.3
0°-180°	4248.3	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	296	296	296	296	296	
5°	296	295	292	295	294	28
15°	283	283	283	287	287	80
25°	257	260	264	269	270	118
35°	221	229	237	246	249	138
45°	182	193	208	221	226	140
55°	139	155	177	192	198	124
65°	95	116	141	158	164	94
75°	53	77	104	122	128	56
85°	16	42	69	87	93	17
90°	5	42	89	104	111	5
95°	52	82	109	125	129	59
105°	204	220	244	260	265	216
115°	378	389	406	417	420	374
125°	548	557	568	576	579	490
135°	709	719	725	733	734	547
145°	860	866	872	875	874	537
155°	983	986	988	993	990	452
165°	1070	1069	1069	1074	1070	301
175°	1113	1110	1108	1114	1109	106
180°	1115	1115	1115	1115	1115	



TEST NUMBER: P331271-830

CATALOG NUMBER: SA2XXDIP-C290D925U830-4F0-1E-UDD-D1

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	295.5	295.5	295.5	295.5	295.5	295.5	295.5	295.5	295.5	295.5	295.5
2.5°	297.2	296.9	296.7	296.4	296.2	295.9	295.3	294.8	294.3	293.7	294.1
5°	296.3	296.1	295.8	295.5	295.1	294.7	294.2	293.6	293.0	292.5	293.0
7.5°	293.6	293.4	293.2	293.0	292.8	292.6	292.1	291.7	291.2	290.8	291.5
10°	291.6	291.4	291.2	291.1	290.9	290.6	290.3	290.0	289.7	289.5	290.2
12.5°	288.1	288.2	288.2	288.3	288.3	288.2	288.0	287.9	287.6	287.4	288.1
15°	282.6	282.8	283.0	283.1	283.3	283.4	283.4	283.4	283.4	283.4	284.3
17.5°	275.4	275.8	276.2	276.6	277.0	277.4	277.7	278.0	278.2	278.6	279.5
20°	270.6	271.1	271.5	272.0	272.5	273.0	273.3	273.7	274.1	274.5	275.5
22.5°	265.5	266.0	266.6	267.1	267.7	268.2	268.7	269.3	269.8	270.3	271.4
25°	256.9	257.6	258.3	258.9	259.6	260.3	261.2	262.0	262.9	263.7	264.9
27.5°	246.7	247.7	248.8	249.9	251.0	252.0	253.0	254.0	255.1	256.1	257.5
30°	239.8	241.0	242.2	243.5	244.7	246.0	247.2	248.5	249.7	250.9	252.4
32.5°	232.2	233.7	235.0	236.4	237.8	239.2	240.7	242.1	243.6	245.1	246.9
35°	221.4	223.0	224.6	226.2	227.8	229.5	231.4	233.2	235.0	236.8	238.8
37.5°	209.5	211.4	213.3	215.2	217.0	219.1	221.5	223.8	226.1	228.5	230.8
40°	201.7	203.8	205.9	207.9	210.0	212.4	214.9	217.5	220.1	222.6	225.1
42.5°	194.2	196.2	198.3	200.4	202.6	205.0	208.0	210.9	213.9	216.8	219.5
45°	181.5	184.1	186.7	189.3	191.8	194.7	198.1	201.4	204.7	208.1	211.0
47.5°	169.1	171.9	174.7	177.5	180.3	183.7	187.6	191.4	195.4	199.3	202.4
50°	160.6	163.5	166.5	169.4	172.4	176.0	180.3	184.5	188.8	193.1	196.3
52.5°	152.3	155.4	158.5	161.6	164.8	168.5	173.1	177.6	182.1	186.6	189.9
55°	139.1	142.6	146.0	149.4	152.9	157.0	162.0	166.9	171.9	176.8	180.3
57.5°	126.1	130.0	133.8	137.7	141.6	146.0	151.1	156.1	161.2	166.3	169.9
60°	116.9	121.0	125.1	129.1	133.3	138.0	143.5	148.8	154.3	159.7	163.3
62.5°	108.7	112.9	117.2	121.4	125.6	130.4	135.9	141.3	146.8	152.2	156.0
65°	95.0	99.7	104.3	109.1	113.7	118.9	124.4	130.1	135.7	141.3	145.2
67.5°	82.6	87.5	92.3	97.2	102.1	107.4	113.1	118.9	124.6	130.4	134.3
70°	73.6	78.6	83.5	88.5	93.4	98.9	104.7	110.7	116.6	122.4	126.6
72.5°	65.4	70.5	75.6	80.7	85.9	91.3	97.4	103.3	109.3	115.3	119.3
75°	52.7	58.0	63.3	68.6	74.0	79.6	85.8	91.9	97.9	104.1	108.1
77.5°	40.3	45.9	51.5	57.0	62.7	68.5	74.7	80.9	87.1	93.2	97.4
80°	32.1	37.9	43.7	49.5	55.3	61.4	67.5	73.7	79.8	86.1	90.0
82.5°	25.3	31.0	36.8	42.4	48.2	54.2	60.4	66.7	73.0	79.2	83.2
85°	15.5	21.3	27.2	33.1	39.0	45.0	51.1	57.2	63.2	69.4	73.3
87.5°	8.6	14.8	20.9	27.1	33.3	39.9	46.8	53.9	60.9	67.9	71.7
90°	5.2	13.3	21.3	29.3	37.3	46.7	57.4	68.1	78.8	89.4	92.8
92.5°	20.6	27.6	34.6	41.7	48.6	55.5	62.5	69.5	76.4	83.3	87.2
95°	52.3	58.9	65.5	72.0	78.6	84.9	91.0	97.2	103.3	109.4	113.0
97.5°	92.4	98.2	104.0	109.8	115.6	121.7	127.9	134.2	140.5	146.8	150.3
100°	122.4	127.6	132.8	138.0	143.3	148.8	154.8	160.7	166.6	172.6	176.2
102.5°	153.7	158.3	162.9	167.4	171.9	177.2	183.1	189.2	195.1	201.0	204.7
105°	204.3	207.7	211.1	214.5	217.9	222.3	227.6	233.0	238.4	243.7	247.5
107.5°	255.8	258.9	262.1	265.2	268.3	272.3	277.0	281.7	286.5	291.2	294.6
110°	288.6	291.7	294.9	298.0	301.2	305.1	309.8	314.4	319.1	323.8	326.9



TEST NUMBER: P331271-830

CATALOG NUMBER: SA2XXDIP-C290D925U830-4F0-1E-UDD-D1

CANDELA DISTRIBUTION (continued):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	324.7	327.5	330.5	333.3	336.1	339.7	343.9	348.3	352.5	356.8	359.3
115°	378.0	380.2	382.6	384.8	387.2	390.2	394.1	397.9	401.8	405.7	408.3
117.5°	430.6	432.9	435.3	437.6	440.0	442.6	445.4	448.2	450.9	453.7	456.0
120°	466.0	468.0	470.0	472.1	474.2	476.3	478.3	480.5	482.7	484.7	487.5
122.5°	498.3	500.5	502.7	504.8	506.9	509.3	511.6	514.1	516.4	518.9	520.9
125°	548.3	550.2	552.0	553.9	555.8	558.0	560.3	562.8	565.2	567.6	569.6
127.5°	597.4	599.6	602.0	604.3	606.5	608.5	610.2	611.9	613.7	615.4	617.0
130°	628.2	630.8	633.5	636.1	638.8	640.8	642.4	644.0	645.5	647.1	649.0
132.5°	662.9	665.0	667.1	669.2	671.4	673.3	674.9	676.5	678.1	679.7	681.0
135°	708.7	711.1	713.3	715.6	717.9	719.7	721.1	722.5	723.9	725.2	727.0
137.5°	757.4	759.3	761.2	763.0	764.9	766.3	767.2	768.2	769.2	770.2	771.8
140°	786.7	788.5	790.3	792.1	793.9	795.4	796.6	797.9	799.2	800.4	801.9
142.5°	816.9	818.7	820.5	822.3	824.1	825.3	826.0	826.8	827.6	828.3	829.6
145°	859.7	861.2	862.6	864.1	865.5	867.0	868.2	869.4	870.7	871.9	872.7
147.5°	898.2	900.0	901.8	903.5	905.3	906.6	907.5	908.2	909.1	909.9	910.5
150°	924.6	925.9	927.1	928.4	929.6	930.7	931.5	932.4	933.2	934.1	934.6
152.5°	947.9	949.2	950.5	951.7	953.0	954.1	955.1	956.1	957.1	958.1	958.9
155°	983.0	983.5	984.2	984.9	985.4	986.1	986.7	987.3	988.0	988.5	989.7
157.5°	1012.9	1013.2	1013.7	1014.1	1014.6	1014.9	1015.3	1015.7	1016.1	1016.4	1017.9
160°	1031.0	1031.3	1031.7	1032.2	1032.6	1032.9	1033.1	1033.3	1033.5	1033.7	1035.0
162.5°	1047.4	1047.5	1047.6	1047.7	1047.8	1047.9	1048.2	1048.4	1048.6	1048.8	1050.2
165°	1069.5	1069.3	1069.0	1068.8	1068.7	1068.6	1068.6	1068.6	1068.6	1068.6	1070.0
167.5°	1087.9	1087.3	1086.7	1086.0	1085.4	1085.1	1085.1	1085.0	1085.0	1084.9	1086.4
170°	1097.7	1097.0	1096.5	1095.8	1095.1	1094.8	1094.6	1094.4	1094.1	1093.9	1095.4
172.5°	1104.5	1103.8	1103.2	1102.6	1101.9	1101.5	1101.4	1101.1	1100.9	1100.7	1102.2
175°	1112.8	1112.1	1111.4	1110.9	1110.2	1109.7	1109.3	1108.9	1108.4	1108.1	1109.5
177.5°	1116.2	1115.6	1115.1	1114.7	1114.1	1113.7	1113.3	1113.0	1112.7	1112.4	1113.3
180°	1114.7	1114.7	1114.7	1114.7	1114.7	1114.7	1114.7	1114.7	1114.7	1114.7	1114.7



TEST NUMBER: P331271-830

CATALOG NUMBER: SA2XXDIP-C290D925U830-4F0-1E-UDD-D1

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°
0°	295.5	295.5	295.5	295.5	295.5	295.5	295.5	295.5
2.5°	294.5	294.8	295.2	295.4	295.2	295.0	294.9	294.7
5°	293.6	294.2	294.7	294.9	294.8	294.7	294.6	294.5
7.5°	292.2	292.8	293.6	293.9	293.8	293.7	293.6	293.5
10°	291.0	291.7	292.5	292.8	292.8	292.7	292.6	292.5
12.5°	288.9	289.6	290.4	290.8	290.7	290.6	290.5	290.4
15°	285.1	286.1	286.9	287.3	287.2	287.1	287.0	286.9
17.5°	280.4	281.3	282.1	282.6	282.6	282.6	282.6	282.6
20°	276.5	277.6	278.6	279.2	279.2	279.2	279.2	279.2
22.5°	272.5	273.5	274.6	275.1	275.3	275.4	275.6	275.8
25°	266.1	267.2	268.3	269.0	269.3	269.6	269.8	270.1
27.5°	258.9	260.4	261.8	262.7	262.9	263.1	263.3	263.5
30°	253.9	255.5	257.0	257.9	258.2	258.4	258.7	259.0
32.5°	248.5	250.3	252.1	253.3	253.7	254.3	254.8	255.2
35°	241.0	243.1	245.2	246.6	247.2	247.9	248.5	249.2
37.5°	233.1	235.4	237.8	239.3	240.0	240.7	241.4	242.0
40°	227.6	230.1	232.5	234.2	235.1	235.9	236.8	237.6
42.5°	222.3	224.9	227.6	229.4	230.3	231.1	232.0	232.8
45°	214.0	217.0	219.9	221.9	222.8	223.8	224.7	225.6
47.5°	205.5	208.5	211.6	213.7	214.7	215.7	216.8	217.8
50°	199.5	202.8	206.0	208.2	209.2	210.3	211.3	212.4
52.5°	193.2	196.5	199.8	202.1	203.2	204.3	205.5	206.5
55°	183.7	187.1	190.6	192.8	194.1	195.4	196.6	197.8
57.5°	173.6	177.3	181.0	183.4	184.7	186.0	187.2	188.5
60°	166.9	170.6	174.2	176.6	178.0	179.3	180.7	182.0
62.5°	159.9	163.7	167.6	170.1	171.4	172.6	173.9	175.1
65°	149.1	153.0	156.9	159.5	160.7	161.9	163.2	164.4
67.5°	138.2	142.1	146.1	148.7	150.0	151.3	152.6	153.9
70°	130.6	134.7	138.8	141.5	142.6	143.7	144.9	146.0
72.5°	123.3	127.3	131.3	134.0	135.3	136.8	138.2	139.5
75°	112.3	116.3	120.5	123.1	124.3	125.5	126.8	128.0
77.5°	101.4	105.5	109.5	112.3	113.6	114.9	116.2	117.5
80°	94.1	98.0	102.1	104.7	106.0	107.4	108.7	110.0
82.5°	87.2	91.2	95.2	97.8	99.1	100.4	101.6	102.8
85°	77.4	81.3	85.4	88.0	89.4	90.7	92.0	93.3
87.5°	75.5	79.3	83.1	85.6	86.9	88.1	89.4	90.7
90°	96.2	99.6	103.0	105.4	106.7	108.1	109.4	110.7
92.5°	91.0	94.8	98.6	101.1	102.3	103.5	104.6	105.8
95°	116.7	120.3	123.9	126.1	126.8	127.5	128.3	128.9
97.5°	153.8	157.3	160.9	163.2	164.2	165.3	166.4	167.5
100°	179.6	183.2	186.7	188.9	189.7	190.6	191.4	192.3
102.5°	208.3	211.9	215.6	217.7	218.6	219.4	220.3	221.1
105°	251.3	255.0	258.7	261.2	262.2	263.3	264.3	265.3
107.5°	297.9	301.3	304.7	306.4	306.5	306.6	306.7	306.7
110°	329.9	332.9	335.9	337.7	338.1	338.6	338.9	339.4



TEST NUMBER: P331271-830

CATALOG NUMBER: SA2XXDIP-C290D925U830-4F0-1E-UDD-D1

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°
112.5°	361.8	364.4	366.9	368.5	369.1	369.7	370.2	370.8
115°	410.9	413.6	416.3	417.8	418.2	418.7	419.1	419.5
117.5°	458.4	460.7	463.0	464.3	464.7	465.1	465.3	465.7
120°	490.1	492.8	495.4	497.0	497.4	497.9	498.2	498.7
122.5°	523.0	525.1	527.2	528.5	528.9	529.3	529.8	530.2
125°	571.6	573.4	575.4	576.7	577.3	578.0	578.6	579.3
127.5°	618.6	620.2	621.8	622.6	622.8	623.0	623.2	623.3
130°	650.9	652.7	654.6	655.5	655.4	655.3	655.3	655.3
132.5°	682.3	683.5	684.9	685.5	685.6	685.7	685.8	685.9
135°	728.8	730.6	732.4	733.3	733.5	733.6	733.8	733.9
137.5°	773.4	774.9	776.5	777.2	777.0	776.7	776.6	776.4
140°	803.4	804.9	806.4	807.1	806.8	806.5	806.3	806.1
142.5°	831.0	832.5	833.9	834.3	834.0	833.7	833.3	833.0
145°	873.5	874.3	875.1	875.2	875.0	874.6	874.2	873.8
147.5°	911.1	911.5	912.1	912.1	911.5	911.0	910.4	909.8
150°	935.3	935.9	936.5	936.5	935.9	935.3	934.6	934.1
152.5°	959.7	960.5	961.3	961.3	960.5	959.7	958.9	958.1
155°	990.7	991.7	992.8	993.0	992.3	991.7	991.1	990.4
157.5°	1019.3	1020.7	1022.1	1022.3	1021.3	1020.3	1019.3	1018.3
160°	1036.2	1037.5	1038.8	1039.0	1038.1	1037.3	1036.4	1035.6
162.5°	1051.6	1053.0	1054.4	1054.7	1053.7	1052.6	1051.7	1050.7
165°	1071.5	1072.9	1074.4	1074.6	1073.6	1072.5	1071.5	1070.4
167.5°	1087.8	1089.3	1090.7	1090.9	1089.9	1088.7	1087.7	1086.6
170°	1096.8	1098.3	1099.8	1099.9	1098.6	1097.4	1096.1	1094.9
172.5°	1103.6	1105.1	1106.5	1106.6	1105.4	1104.2	1102.9	1101.6
175°	1111.0	1112.4	1113.9	1114.0	1112.8	1111.4	1110.2	1109.0
177.5°	1114.4	1115.4	1116.3	1116.3	1115.4	1114.4	1113.3	1112.4
180°	1114.7	1114.7	1114.7	1114.7	1114.7	1114.7	1114.7	1114.7

(END OF REPORT)