

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P333185-840

Luminaire Tested: **S125DIP-S610D810U840-4F0-1E-UDD-F1**

Issue Date: 3/3/2020

Test Information

Test Method: LM-79-08
Report Number: P333185-840
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-11,
Test Lab: INNOVATION CENTER
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: NEO-RAY
Catalog Number: S125DIP-S610D810U840-4F0-1E-UDD-F1
Description: DEFINE 5 DIRECT-INDIRECT PENDANT LED LUMINAIRE
DOWNLIGHT 610 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER
UPLIGHT 810 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER
Light Source: -
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 5357.4 lumens
Efficiency: N/A
Efficacy: 139.5 lumens/watt
Spacing Criteria (0/90/45): 1.21 / 1.18 / 1.31
Luminous Opening: Rectangular (W 0.42' x L: 4' x H: 0')
CIE Type: General Diffuse


Input Watts (W): 38.4
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P333185-840

CATALOG NUMBER: S125DIP-S610D810U840-4F0-1E-UDD-F1

Luminous Intensity Polar Plot





TEST NUMBER: P333185-840

CATALOG NUMBER: S125DIP-S610D810U840-4F0-1E-UDD-F1

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	106	106	106	106	98	98	98	98	82	82	82	67	67	67	54	54	54	47
1	97	93	89	85	89	85	82	79	72	69	67	59	57	56	47	46	45	40
2	88	81	75	70	81	75	69	65	63	59	55	52	49	46	41	40	38	33
3	81	71	64	58	74	66	59	54	55	50	47	46	42	39	37	34	32	28
4	74	63	55	49	67	58	51	46	49	44	40	41	37	34	33	30	28	24
5	68	56	48	42	62	52	45	39	44	38	34	36	32	29	30	27	24	21
6	62	50	42	36	57	47	39	34	39	34	30	33	29	25	27	24	21	18
7	58	45	37	32	53	42	35	30	36	30	26	30	26	22	24	21	19	16
8	53	41	33	28	49	38	31	26	33	27	23	27	23	20	22	19	17	15
9	50	38	30	25	46	35	28	24	30	25	21	25	21	18	21	18	15	13
10	46	34	27	22	43	32	26	21	28	22	19	23	19	16	19	16	14	12

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	6264	6264	6264
5°	6278	6218	6257
10°	6239	6174	6209
15°	6171	6100	6125
20°	6075	5996	6006
25°	5971	5872	5867
30°	5842	5739	5711
35°	5705	5595	5517
40°	5563	5440	5363
45°	5411	5298	5193
50°	5243	5127	4972
55°	5080	4933	4796
60°	4886	4738	4570
65°	4655	4504	4351
70°	4434	4232	4086
75°	4040	3905	3773
80°	3593	3537	3451
85°	3127	3179	3016



TEST NUMBER: P333185-840

CATALOG NUMBER: S125DIP-S610D810U840-4F0-1E-UDD-F1

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	91.4	1.7
10°-20°	258.3	4.8
20°-30°	381.4	7.1
30°-40°	445.0	8.3
40°-50°	447.0	8.3
50°-60°	392.4	7.3
60°-70°	292.4	5.5
70°-80°	167.2	3.1
80°-90°	50.8	0.9
90°-100°	68.0	1.3
100°-110°	200.7	3.7
110°-120°	339.9	6.3
120°-130°	447.4	8.4
130°-140°	501.3	9.4
140°-150°	491.3	9.2
150°-160°	412.7	7.7
160°-170°	274.3	5.1
170°-180°	96.0	1.8
0°-30°	731.2	13.6
0°-40°	1176.2	22.0
0°-60°	2015.6	37.6
0°-90°	2525.9	47.1
90°-120°	608.6	11.4
90°-150°	2048.6	38.2
90°-180°	2832.0	52.9
0°-180°	5357.4	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	970	970	970	970	970	
5°	968	966	959	966	965	92
15°	923	920	912	916	916	260
25°	838	834	824	825	823	385
35°	724	720	710	706	700	452
45°	592	589	580	571	569	456
55°	451	448	438	431	426	403
65°	305	303	295	288	285	302
75°	162	160	156	154	151	173
85°	42	43	43	42	41	47
90°	1	7	13	17	19	5
95°	51	53	61	66	68	55
105°	180	184	189	193	196	192
115°	340	343	345	344	344	336
125°	497	501	502	501	500	445
135°	646	650	652	651	648	498
145°	782	786	788	788	786	489
155°	895	895	896	899	895	412
165°	974	972	973	976	971	275
175°	1012	1009	1009	1013	1008	96
180°	1015	1015	1015	1015	1015	



TEST NUMBER: P333185-840

CATALOG NUMBER: S125DIP-S610D810U840-4F0-1E-UDD-F1

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	969.9	969.9	969.9	969.9	969.9	969.9	969.9	969.9	969.9	969.9	969.9
2.5°	972.3	971.9	971.5	971.1	970.7	969.8	968.5	967.0	965.7	964.3	965.7
5°	968.4	968.0	967.7	967.2	966.9	965.9	964.2	962.5	960.8	959.1	960.7
7.5°	959.4	959.1	958.8	958.4	958.1	956.9	955.0	953.2	951.3	949.5	950.9
10°	951.4	951.1	950.8	950.4	950.1	949.0	947.1	945.2	943.3	941.5	942.8
12.5°	941.6	941.0	940.4	939.8	939.2	938.0	936.2	934.5	932.7	931.0	932.1
15°	923.0	922.5	922.0	921.5	921.0	919.8	918.0	916.0	914.1	912.3	913.1
17.5°	901.7	901.0	900.2	899.5	898.7	897.4	895.4	893.4	891.5	889.6	890.6
20°	883.9	883.5	883.2	882.9	882.5	881.3	879.1	876.9	874.6	872.4	873.6
22.5°	866.1	865.5	864.8	864.2	863.6	862.3	860.2	858.2	856.1	853.9	854.7
25°	837.9	837.0	836.2	835.4	834.5	832.9	830.7	828.5	826.3	824.0	824.5
27.5°	804.9	804.4	803.9	803.3	802.8	801.4	799.1	796.9	794.6	792.3	792.3
30°	783.4	782.8	782.3	781.8	781.3	779.8	777.3	774.7	772.1	769.6	769.2
32.5°	760.0	759.3	758.5	757.7	756.9	755.4	753.2	750.8	748.5	746.3	745.7
35°	723.6	722.9	722.2	721.5	720.8	719.3	716.9	714.5	712.2	709.7	708.9
37.5°	685.6	684.8	684.0	683.1	682.3	680.6	678.4	676.2	673.9	671.7	670.4
40°	659.8	659.0	658.1	657.3	656.4	654.8	652.5	650.1	647.6	645.3	643.8
42.5°	632.3	631.6	630.8	630.1	629.3	627.8	625.4	623.1	620.7	618.2	616.9
45°	592.4	591.7	591.0	590.3	589.7	588.2	586.2	584.2	582.1	580.1	578.0
47.5°	549.4	549.4	549.5	549.5	549.5	548.3	545.8	543.4	541.0	538.5	536.4
50°	521.8	521.2	520.7	520.2	519.7	518.5	516.3	514.3	512.3	510.3	508.1
52.5°	493.5	493.1	492.8	492.4	492.0	490.7	488.6	486.4	484.2	482.0	480.1
55°	451.2	450.6	450.1	449.6	449.1	447.7	445.2	442.9	440.5	438.1	436.6
57.5°	406.5	406.3	406.0	405.7	405.5	404.2	402.2	400.2	398.2	396.3	394.3
60°	378.3	377.6	376.9	376.2	375.6	374.3	372.4	370.5	368.6	366.8	365.1
62.5°	348.8	348.3	347.7	347.2	346.6	345.6	344.0	342.3	340.7	339.1	337.3
65°	304.6	304.3	304.0	303.6	303.3	302.2	300.2	298.4	296.5	294.7	293.1
67.5°	261.8	261.1	260.3	259.6	258.9	257.9	256.5	255.1	253.7	252.3	251.0
70°	234.8	234.0	233.1	232.3	231.4	230.1	228.6	227.1	225.6	224.1	223.0
72.5°	205.3	204.7	204.2	203.6	203.0	202.2	201.3	200.3	199.2	198.2	197.1
75°	161.9	161.6	161.2	160.9	160.6	160.0	159.1	158.2	157.3	156.5	156.0
77.5°	121.9	121.7	121.6	121.4	121.3	121.0	120.5	120.1	119.6	119.1	118.8
80°	96.6	96.6	96.6	96.6	96.6	96.5	96.1	95.8	95.5	95.1	94.9
82.5°	74.6	74.3	74.0	73.7	73.5	73.3	73.2	73.2	73.1	73.0	72.7
85°	42.2	42.4	42.5	42.7	42.9	42.9	42.9	42.9	42.9	42.9	42.8
87.5°	16.8	17.0	17.3	17.6	17.9	18.1	18.2	18.3	18.4	18.5	18.7
90°	0.8	2.2	3.6	5.0	6.4	7.7	9.0	10.2	11.4	12.6	13.5
92.5°	19.1	20.1	21.1	22.0	23.0	24.2	25.8	27.3	28.8	30.3	31.5
95°	51.3	51.7	52.0	52.4	52.7	53.8	55.5	57.3	59.1	60.8	62.0
97.5°	85.3	85.4	85.5	85.7	85.8	87.2	89.6	92.0	94.4	96.8	98.0
100°	110.6	110.6	110.6	110.6	110.6	111.7	114.0	116.2	118.6	120.8	122.4
102.5°	137.7	138.5	139.2	139.9	140.6	141.5	142.6	143.8	144.9	146.1	147.8
105°	180.1	181.0	181.8	182.7	183.6	184.5	185.6	186.6	187.6	188.7	189.8
107.5°	226.8	227.6	228.5	229.4	230.4	231.2	232.0	232.8	233.6	234.4	234.9
110°	259.0	259.9	260.7	261.7	262.6	263.3	263.8	264.3	264.8	265.3	265.9



TEST NUMBER: P333185-840

CATALOG NUMBER: S125DIP-S610D810U840-4F0-1E-UDD-F1

CANDELA DISTRIBUTION (continued):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	291.9	292.4	292.8	293.3	293.7	294.3	294.9	295.6	296.3	296.9	297.2
115°	340.3	341.0	341.7	342.4	343.2	343.7	344.1	344.4	344.8	345.1	344.9
117.5°	389.0	389.3	389.6	389.9	390.2	390.6	390.9	391.2	391.5	391.8	391.9
120°	419.3	420.2	421.1	421.9	422.8	423.3	423.5	423.7	423.8	424.0	424.0
122.5°	452.1	452.5	452.8	453.1	453.4	453.8	454.2	454.7	455.1	455.7	455.4
125°	496.7	497.8	498.8	499.9	500.9	501.5	501.7	501.9	502.0	502.2	501.9
127.5°	544.1	544.7	545.2	545.8	546.4	546.8	547.0	547.2	547.5	547.8	547.5
130°	572.5	573.4	574.3	575.1	576.0	576.6	576.9	577.3	577.6	578.0	577.8
132.5°	601.0	602.4	603.8	605.2	606.7	607.3	607.3	607.2	607.1	607.1	606.9
135°	645.9	647.0	648.0	649.1	650.2	650.8	651.0	651.2	651.3	651.5	651.5
137.5°	688.3	689.3	690.3	691.4	692.4	693.1	693.5	693.8	694.2	694.6	694.8
140°	715.5	716.3	717.2	718.1	718.9	719.6	720.1	720.7	721.2	721.8	722.2
142.5°	742.7	743.4	744.1	744.8	745.6	746.3	746.9	747.6	748.2	748.9	749.1
145°	782.5	783.3	784.0	784.7	785.4	786.0	786.5	787.0	787.6	788.1	788.1
147.5°	819.5	819.9	820.3	820.7	821.0	821.4	821.9	822.3	822.7	823.1	823.5
150°	844.1	843.9	843.8	843.6	843.4	843.7	844.4	845.2	845.9	846.6	846.6
152.5°	864.3	864.6	864.8	865.2	865.4	865.7	865.9	866.2	866.5	866.8	867.2
155°	895.4	895.4	895.4	895.4	895.4	895.5	895.8	896.0	896.1	896.3	897.0
157.5°	923.3	922.9	922.5	922.1	921.7	921.6	921.8	922.0	922.1	922.3	923.0
160°	939.7	939.2	938.7	938.2	937.6	937.5	937.6	937.8	938.0	938.2	938.9
162.5°	954.2	953.8	953.4	953.1	952.7	952.5	952.5	952.6	952.6	952.7	953.5
165°	973.7	973.3	973.0	972.6	972.3	972.2	972.3	972.5	972.7	972.9	973.6
167.5°	990.1	989.4	988.7	988.0	987.2	986.9	986.9	986.9	986.9	986.9	988.0
170°	999.0	998.3	997.5	996.8	996.1	995.7	995.7	995.7	995.7	995.7	996.8
172.5°	1005.2	1004.5	1003.8	1003.1	1002.4	1002.1	1002.1	1002.1	1002.1	1002.1	1003.1
175°	1012.4	1011.7	1011.0	1010.3	1009.6	1009.2	1009.2	1009.2	1009.2	1009.2	1010.3
177.5°	1016.0	1015.4	1014.9	1014.3	1013.7	1013.4	1013.3	1013.1	1013.0	1012.8	1013.7
180°	1014.7	1014.7	1014.7	1014.7	1014.7	1014.7	1014.7	1014.7	1014.7	1014.7	1014.7



TEST NUMBER: P333185-840

CATALOG NUMBER: S125DIP-S610D810U840-4F0-1E-UDD-F1

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°
0°	969.9	969.9	969.9	969.9	969.9	969.9	969.9	969.9
2.5°	967.0	968.5	969.8	970.4	970.3	970.1	970.0	969.9
5°	962.2	963.7	965.2	965.9	965.7	965.6	965.4	965.2
7.5°	952.4	953.9	955.4	956.1	955.9	955.7	955.6	955.4
10°	944.2	945.5	947.0	947.6	947.4	947.2	947.0	946.8
12.5°	933.2	934.3	935.3	935.9	935.8	935.8	935.8	935.7
15°	914.0	914.8	915.7	916.1	916.1	916.1	916.1	916.1
17.5°	891.7	892.7	893.8	893.9	893.0	892.2	891.4	890.5
20°	874.7	876.0	877.2	877.4	876.5	875.7	874.7	873.9
22.5°	855.6	856.4	857.2	857.3	856.7	856.1	855.5	855.0
25°	824.8	825.1	825.5	825.4	824.9	824.4	823.8	823.3
27.5°	792.4	792.5	792.5	792.3	791.8	791.3	790.8	790.3
30°	768.9	768.6	768.2	767.8	767.3	766.8	766.3	765.8
32.5°	745.1	744.4	743.8	743.1	742.1	741.2	740.2	739.3
35°	708.0	707.2	706.3	705.2	703.9	702.5	701.1	699.7
37.5°	669.1	667.9	666.6	665.6	664.8	664.1	663.3	662.5
40°	642.2	640.7	639.1	638.1	637.6	637.1	636.6	636.1
42.5°	615.5	614.1	612.7	611.6	610.8	610.1	609.3	608.4
45°	575.9	573.9	571.9	570.6	570.1	569.6	569.1	568.6
47.5°	534.3	532.2	530.2	528.6	527.4	526.1	524.9	523.7
50°	505.8	503.6	501.4	499.7	498.5	497.3	496.0	494.9
52.5°	478.1	476.2	474.2	472.6	471.3	469.9	468.6	467.3
55°	435.0	433.5	432.0	430.6	429.4	428.2	427.1	425.9
57.5°	392.2	390.3	388.3	387.0	386.4	385.7	385.1	384.5
60°	363.3	361.6	359.9	358.5	357.3	356.1	354.9	353.8
62.5°	335.5	333.7	331.7	330.4	329.5	328.5	327.6	326.7
65°	291.5	290.0	288.5	287.4	286.7	286.0	285.4	284.7
67.5°	249.7	248.4	247.1	246.2	245.8	245.4	245.0	244.6
70°	222.0	221.0	219.9	219.1	218.4	217.7	217.0	216.4
72.5°	195.9	194.8	193.6	192.7	192.0	191.4	190.7	190.0
75°	155.5	155.0	154.5	153.9	153.2	152.5	151.9	151.2
77.5°	118.5	118.2	117.9	117.4	116.9	116.5	116.0	115.5
80°	94.8	94.6	94.4	94.2	93.8	93.5	93.2	92.8
82.5°	72.4	72.1	71.8	71.6	71.6	71.5	71.4	71.4
85°	42.6	42.4	42.3	42.0	41.7	41.3	41.0	40.7
87.5°	18.9	19.0	19.2	19.2	19.0	18.9	18.7	18.5
90°	14.3	15.2	16.2	16.9	17.4	17.9	18.4	19.0
92.5°	32.6	33.8	34.9	35.7	36.2	36.5	36.9	37.3
95°	63.2	64.5	65.7	66.6	66.9	67.3	67.6	67.9
97.5°	99.2	100.3	101.5	102.1	102.3	102.5	102.8	103.0
100°	124.0	125.5	127.1	128.2	128.5	128.8	129.2	129.5
102.5°	149.6	151.3	153.0	154.1	154.6	155.0	155.5	156.0
105°	190.9	191.9	193.0	193.7	194.3	194.8	195.3	195.8
107.5°	235.4	235.9	236.5	236.7	236.7	236.6	236.6	236.6
110°	266.4	266.9	267.4	267.6	267.4	267.2	267.1	266.9



TEST NUMBER: P333185-840

CATALOG NUMBER: S125DIP-S610D810U840-4F0-1E-UDD-F1

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°
112.5°	297.4	297.6	297.9	297.9	297.5	297.2	296.9	296.6
115°	344.8	344.6	344.4	344.2	344.1	343.9	343.7	343.6
117.5°	392.1	392.2	392.4	392.1	391.4	390.7	390.0	389.3
120°	424.0	424.0	424.0	423.7	423.0	422.3	421.6	420.9
122.5°	455.3	455.2	455.0	454.7	454.1	453.6	453.0	452.5
125°	501.5	501.2	500.8	500.6	500.4	500.2	500.1	499.9
127.5°	547.3	547.1	547.0	546.7	546.4	546.0	545.7	545.3
130°	577.6	577.5	577.3	577.0	576.7	576.3	576.0	575.6
132.5°	606.7	606.5	606.4	606.0	605.6	605.1	604.6	604.1
135°	651.5	651.5	651.5	651.2	650.5	649.7	649.0	648.3
137.5°	695.0	695.2	695.4	695.1	694.2	693.4	692.5	691.6
140°	722.5	722.8	723.2	722.9	722.1	721.1	720.2	719.4
142.5°	749.3	749.5	749.7	749.4	748.5	747.7	746.8	745.9
145°	788.1	788.1	788.1	787.8	787.3	786.8	786.3	785.7
147.5°	823.9	824.5	824.9	824.5	823.2	822.0	820.9	819.7
150°	846.6	846.6	846.6	846.4	846.0	845.7	845.3	845.0
152.5°	867.6	868.0	868.4	868.3	867.7	867.1	866.5	865.8
155°	897.7	898.4	899.1	899.0	898.1	897.3	896.4	895.4
157.5°	923.7	924.4	925.1	924.9	923.7	922.6	921.4	920.3
160°	939.6	940.2	940.9	940.9	940.0	939.1	938.2	937.4
162.5°	954.3	955.2	956.0	955.9	954.9	953.9	952.9	951.9
165°	974.3	975.0	975.6	975.5	974.4	973.4	972.3	971.3
167.5°	989.1	990.1	991.2	991.1	990.1	989.0	987.8	986.7
170°	997.8	999.0	1000.0	999.9	998.7	997.4	996.2	995.0
172.5°	1004.2	1005.2	1006.3	1006.3	1005.2	1004.1	1003.0	1001.9
175°	1011.3	1012.4	1013.4	1013.3	1012.1	1010.9	1009.7	1008.5
177.5°	1014.5	1015.3	1016.2	1016.1	1015.1	1014.2	1013.2	1012.2
180°	1014.7	1014.7	1014.7	1014.7	1014.7	1014.7	1014.7	1014.7

(END OF REPORT)