

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P333232-840

Luminaire Tested: **S125DIP-S850D1035U840-4F0-1E-UDD-A**

Issue Date: 3/3/2020

Test Information

Test Method: LM-79-08
Report Number: P333232-840
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-7,
Test Lab: INNOVATION CENTER
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: NEO-RAY
Catalog Number: S125DIP-S850D1035U840-4F0-1E-UDD-A
Description: DEFINE 5 DIRECT-INDIRECT PENDANT LED LUMINAIRE
DOWNLIGHT 850 LUMENS PER FOOT, ASYMMETRIC DIFFUSER
UPLIGHT 1035 LUMENS PER FOOT, NO LENS
Light Source: -
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 7666.0 lumens
Efficiency: N/A
Efficacy: 147.4 lumens/watt
Spacing Criteria (0/90/45): 1.43 / 1.23 / 1.52
Luminous Opening: Rectangular (W 4' x L: 0.42' x H: 0')
CIE Type: General Diffuse


Input Watts (W): 52
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P333232-840

CATALOG NUMBER: S125DIP-S850D1035U840-4F0-1E-UDD-A

Luminous Intensity Polar Plot





TEST NUMBER: P333232-840

CATALOG NUMBER: S125DIP-S850D1035U840-4F0-1E-UDD-A

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	106	106	106	106	97	97	97	97	81	81	81	66	66	66	52	52	52	46
1	97	93	89	86	89	85	82	79	71	69	67	58	57	55	46	45	44	39
2	88	81	75	70	81	75	70	65	63	59	56	51	49	46	41	39	38	33
3	81	72	64	59	74	66	60	55	55	51	47	46	42	39	36	34	32	28
4	74	63	56	50	68	58	52	46	49	44	40	41	37	34	33	30	28	24
5	68	56	48	43	62	52	45	40	44	39	35	36	32	29	29	27	24	21
6	63	51	43	37	57	47	40	35	40	34	30	33	29	26	27	24	21	18
7	58	46	38	32	53	42	35	30	36	31	27	30	26	23	24	21	19	16
8	54	41	34	29	49	38	32	27	33	27	24	27	23	20	22	19	17	15
9	50	38	30	25	46	35	28	24	30	25	21	25	21	18	21	18	15	13
10	47	35	27	23	43	32	26	21	28	22	19	23	19	16	19	16	14	12

AVERAGE LUMINANCE (cd/sqm):

	0°	90°	180°	270°
0°	7979	7979	7979	7979
5°	9240	8006	7010	8006
10°	10750	7965	6142	7965
15°	11900	7906	5666	7906
20°	13320	7813	5283	7813
25°	15605	7709	5097	7709
30°	16855	7607	4935	7607
35°	13858	7413	4829	7413
40°	9850	7144	4713	7144
45°	7567	6783	4646	6783
50°	6459	6333	4636	6333
55°	5751	5892	4677	5892
60°	5187	5412	4795	5412
65°	4792	4927	4919	4927
70°	4358	4426	4991	4426
75°	3848	3898	4946	3898
80°	3239	3176	4526	3176
85°	2564	2290	3653	2290



TEST NUMBER: P333232-840

CATALOG NUMBER: S125DIP-S850D1035U840-4F0-1E-UDD-A

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	118.9	1.6
10°-20°	354.1	4.6
20°-30°	575.0	7.5
30°-40°	701.4	9.1
40°-50°	638.1	8.3
50°-60°	508.2	6.6
60°-70°	354.0	4.6
70°-80°	188.8	2.5
80°-90°	50.5	0.7
90°-100°	49.4	0.6
100°-110°	304.6	4.0
110°-120°	552.5	7.2
120°-130°	709.1	9.2
130°-140°	762.7	9.9
140°-150°	715.9	9.3
150°-160°	579.1	7.6
160°-170°	374.5	4.9
170°-180°	129.2	1.7
0°-30°	1048.1	13.7
0°-40°	1749.5	22.8
0°-60°	2895.8	37.8
0°-90°	3489.0	45.5
90°-120°	906.6	11.8
90°-150°	3094.2	40.4
90°-180°	4177.0	54.5
0°-180°	7666.0	100.0

CANDELA DISTRIBUTION:

	0°	90°	180°	270°	360°	Flux
0°	1236	1236	1236	1236	1236	
5°	1425	1235	1081	1235	1425	144
15°	1780	1182	847	1182	1780	509
25°	2190	1082	715	1082	2190	1000
35°	1758	940	612	940	1758	1076
45°	828	743	509	743	828	663
55°	511	523	415	523	511	460
65°	314	322	322	322	314	311
75°	154	156	198	156	154	166
85°	35	31	49	31	35	41
90°	24	1	24	1	24	12
95°	21	58	21	58	21	18
105°	299	296	299	296	299	271
115°	553	557	553	557	553	549
125°	792	792	792	792	792	704
135°	983	987	983	987	983	759
145°	1142	1144	1142	1144	1142	713
155°	1251	1260	1251	1260	1251	577
165°	1323	1330	1323	1330	1323	373
175°	1354	1360	1354	1360	1354	129
180°	1360	1360	1360	1360	1360	



TEST NUMBER: P333232-840

CATALOG NUMBER: S125DIP-S850D1035U840-4F0-1E-UDD-A

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	1235.5	1235.5	1235.5	1235.5	1235.5	1235.5	1235.5	1235.5	1235.5	1235.5	1235.5
2.5°	1306.8	1305.0	1303.4	1300.0	1302.5	1295.5	1292.0	1286.2	1279.1	1276.6	1273.6
5°	1425.2	1427.8	1430.5	1419.5	1420.6	1413.2	1396.4	1382.8	1371.8	1357.7	1347.7
7.5°	1567.9	1561.7	1561.2	1554.1	1541.8	1532.0	1514.3	1491.9	1470.2	1445.4	1424.9
10°	1639.2	1639.7	1635.0	1626.6	1613.6	1604.1	1581.0	1558.9	1532.3	1500.8	1478.2
12.5°	1692.9	1695.1	1689.1	1677.8	1671.4	1650.2	1632.1	1606.0	1574.2	1549.0	1514.7
15°	1779.8	1773.9	1769.8	1755.7	1744.6	1722.6	1693.7	1666.5	1631.8	1599.8	1567.9
17.5°	1863.4	1868.0	1860.2	1847.2	1813.1	1787.4	1748.7	1711.3	1668.3	1625.4	1587.2
20°	1938.1	1942.3	1930.3	1907.7	1866.8	1841.1	1790.2	1742.0	1692.1	1637.1	1595.2
22.5°	2031.2	2027.9	2011.7	1977.3	1941.9	1894.4	1839.3	1780.6	1718.2	1656.0	1600.2
25°	2189.8	2167.8	2157.8	2115.4	2068.7	1998.9	1923.4	1837.4	1759.8	1677.5	1606.2
27.5°	2277.6	2270.8	2259.7	2230.1	2181.0	2106.5	2017.4	1912.6	1803.1	1699.2	1605.9
30°	2260.1	2261.1	2262.2	2252.7	2221.3	2165.2	2076.6	1963.8	1833.7	1716.8	1608.8
32.5°	2104.1	2123.1	2141.3	2162.9	2171.7	2161.0	2105.5	2003.7	1869.9	1737.0	1607.1
35°	1757.7	1763.5	1822.7	1881.5	1961.2	2023.1	2064.5	2019.4	1906.6	1754.0	1605.1
37.5°	1370.5	1398.9	1439.9	1506.2	1621.2	1724.2	1856.7	1917.6	1881.3	1759.6	1601.4
40°	1168.3	1194.6	1221.2	1288.9	1385.9	1510.8	1661.2	1789.7	1819.6	1742.0	1588.8
42.5°	1012.3	1033.0	1062.7	1113.6	1194.7	1305.1	1449.0	1616.9	1720.2	1690.8	1562.5
45°	828.5	841.6	864.7	905.0	963.8	1050.4	1177.2	1360.8	1520.7	1573.7	1499.8
47.5°	709.1	709.0	727.0	754.9	797.3	870.8	964.6	1108.4	1279.3	1405.6	1399.8
50°	642.9	640.3	654.4	678.5	712.1	760.8	850.5	965.3	1129.5	1272.6	1312.5
52.5°	585.8	586.1	594.8	612.7	640.8	682.5	749.4	852.9	993.2	1140.1	1215.2
55°	510.8	508.7	518.6	530.7	551.1	578.3	626.6	705.8	819.6	964.3	1061.9
57.5°	441.9	447.7	451.7	460.1	477.1	495.3	536.0	594.1	684.4	808.6	911.7
60°	401.6	407.5	410.6	419.0	432.6	448.4	479.8	527.0	603.0	710.0	812.2
62.5°	365.6	370.1	371.1	378.7	389.8	405.2	429.9	469.5	529.6	623.2	723.4
65°	313.6	313.6	315.7	323.6	328.8	342.4	361.3	390.1	438.4	511.3	596.7
67.5°	263.5	266.0	265.4	268.9	273.8	284.3	297.8	321.6	357.4	410.6	479.0
70°	230.8	232.8	232.3	234.9	240.1	247.0	258.0	280.5	306.2	351.8	410.6
72.5°	201.4	202.2	200.9	204.3	207.4	213.4	225.7	237.7	261.8	300.2	348.5
75°	154.2	155.2	156.2	158.3	161.5	164.6	171.0	183.0	198.7	227.6	258.5
77.5°	115.5	113.6	116.1	115.8	117.5	120.0	125.5	131.9	144.8	163.1	187.0
80°	87.1	87.6	87.6	88.1	90.7	92.3	97.0	101.7	111.7	125.3	142.1
82.5°	63.5	64.9	64.1	65.0	67.3	68.4	71.0	74.8	80.7	91.4	103.5
85°	34.6	32.0	33.0	34.1	34.1	34.6	36.7	38.3	41.4	45.6	50.3
87.5°	14.9	15.7	15.9	15.8	16.1	15.9	17.4	17.1	18.2	19.2	20.5
90°	24.2	23.5	22.8	22.2	21.5	20.6	19.5	18.4	17.3	16.2	14.5
92.5°	22.6	22.3	21.9	21.6	21.3	20.6	19.5	18.4	17.3	16.2	14.7
95°	21.2	21.2	21.2	21.2	21.2	20.6	19.5	18.4	17.3	16.2	24.6
97.5°	21.2	21.2	21.2	21.2	21.2	24.3	30.7	37.0	43.3	49.6	66.4
100°	21.2	22.1	22.9	23.8	24.7	41.9	75.3	108.7	142.1	175.4	174.5
102.5°	126.8	142.1	157.3	172.6	187.8	198.5	204.9	211.2	217.5	223.9	223.3
105°	299.4	299.7	299.9	300.1	300.3	300.4	300.4	300.4	300.4	300.4	300.4
107.5°	377.5	378.2	378.9	379.5	380.2	380.5	380.5	380.4	380.4	380.3	379.9
110°	431.5	431.3	431.1	430.9	430.7	430.9	431.5	432.2	432.9	433.5	433.1



TEST NUMBER: P333232-840

CATALOG NUMBER: S125DIP-S850D1035U840-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	480.0	480.3	480.6	480.9	481.2	481.8	482.6	483.5	484.3	485.2	484.9
115°	552.6	553.9	555.2	556.6	558.0	559.1	560.0	560.9	561.8	562.6	562.4
117.5°	630.0	630.6	631.2	631.8	632.3	633.2	634.4	635.5	636.7	637.8	637.0
120°	677.6	678.7	679.8	681.0	682.1	682.9	683.3	683.8	684.2	684.7	684.0
122.5°	722.8	724.1	725.4	726.7	727.9	728.8	729.3	729.7	730.1	730.6	730.3
125°	791.5	792.2	792.8	793.6	794.3	795.0	795.9	796.8	797.7	798.6	798.6
127.5°	849.4	851.1	852.7	854.3	856.1	857.1	857.6	858.1	858.6	859.1	859.2
130°	891.3	892.5	893.6	894.7	895.9	896.8	897.4	898.1	898.8	899.4	899.2
132.5°	930.1	931.2	932.3	933.4	934.5	935.1	935.3	935.4	935.5	935.7	936.2
135°	983.1	984.4	985.8	987.1	988.5	989.4	989.9	990.3	990.7	991.2	991.6
137.5°	1036.3	1037.5	1038.6	1039.9	1041.0	1041.6	1041.5	1041.4	1041.3	1041.2	1041.6
140°	1067.8	1069.1	1070.5	1071.9	1073.2	1073.6	1073.2	1072.8	1072.3	1071.9	1072.1
142.5°	1097.6	1099.0	1100.3	1101.7	1103.1	1103.7	1103.6	1103.5	1103.4	1103.3	1103.0
145°	1141.5	1142.8	1144.1	1145.5	1146.8	1147.3	1147.1	1146.9	1146.7	1146.5	1146.5
147.5°	1177.5	1179.1	1180.7	1182.3	1184.0	1184.7	1184.4	1184.1	1183.9	1183.6	1183.3
150°	1200.9	1202.6	1204.5	1206.3	1208.1	1208.7	1208.3	1207.9	1207.4	1207.0	1206.5
152.5°	1222.6	1224.3	1225.9	1227.5	1229.1	1229.7	1229.3	1228.8	1228.4	1227.9	1227.5
155°	1251.3	1253.1	1254.9	1256.7	1258.5	1259.1	1258.4	1257.7	1257.1	1256.4	1255.9
157.5°	1275.4	1277.1	1278.9	1280.7	1282.5	1283.0	1282.3	1281.6	1280.9	1280.2	1280.1
160°	1290.6	1292.4	1294.2	1296.1	1297.8	1298.3	1297.4	1296.5	1295.6	1294.6	1294.4
162.5°	1304.3	1306.4	1308.3	1310.3	1312.2	1312.6	1311.3	1310.1	1308.9	1307.6	1307.4
165°	1322.9	1324.7	1326.5	1328.3	1330.1	1330.3	1329.0	1327.6	1326.3	1324.9	1324.7
167.5°	1335.8	1337.9	1339.9	1341.9	1343.9	1344.1	1342.5	1340.9	1339.3	1337.7	1337.4
170°	1343.1	1345.1	1347.2	1349.1	1351.1	1351.3	1349.5	1347.7	1345.8	1344.1	1343.8
172.5°	1348.0	1349.9	1351.9	1353.9	1355.9	1356.1	1354.5	1352.9	1351.3	1349.7	1349.3
175°	1354.1	1356.1	1358.2	1360.2	1362.2	1362.3	1360.6	1358.8	1357.0	1355.1	1354.9
177.5°	1357.8	1359.3	1360.7	1362.1	1363.5	1363.6	1362.4	1361.1	1359.9	1358.6	1358.5
180°	1360.2	1360.2	1360.2	1360.2	1360.2	1360.2	1360.2	1360.2	1360.2	1360.2	1360.2



TEST NUMBER: P333232-840

CATALOG NUMBER: S125DIP-S850D1035U840-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°	95°	100°	105°
0°	1235.5	1235.5	1235.5	1235.5	1235.5	1235.5	1235.5	1235.5	1235.5	1235.5	1235.5
2.5°	1271.1	1268.2	1264.8	1258.9	1251.8	1248.0	1242.1	1238.4	1230.8	1224.6	1217.8
5°	1335.5	1321.9	1309.4	1293.1	1275.3	1263.7	1250.1	1234.9	1219.2	1203.0	1185.1
7.5°	1402.4	1378.3	1352.0	1323.8	1296.3	1270.9	1246.7	1222.8	1200.6	1173.8	1151.0
10°	1447.2	1416.8	1384.3	1346.0	1308.9	1276.4	1243.3	1214.5	1185.1	1153.7	1125.8
12.5°	1492.2	1451.7	1405.7	1363.7	1318.9	1279.7	1240.8	1204.0	1167.1	1132.3	1099.8
15°	1523.9	1488.1	1445.7	1385.9	1335.5	1281.6	1230.2	1182.5	1137.9	1099.1	1058.2
17.5°	1544.7	1498.7	1453.2	1395.8	1329.8	1269.4	1211.2	1156.6	1106.3	1057.1	1017.7
20°	1548.5	1501.3	1453.6	1397.5	1329.8	1260.6	1202.4	1136.8	1082.9	1032.0	983.7
22.5°	1547.2	1493.8	1441.8	1384.0	1318.1	1254.4	1184.0	1117.1	1058.5	1008.5	958.2
25°	1535.4	1478.2	1413.2	1355.0	1290.0	1222.3	1151.0	1081.8	1022.0	964.8	915.0
27.5°	1525.5	1451.4	1377.8	1309.9	1247.1	1185.1	1116.8	1045.9	979.7	921.7	874.7
30°	1513.4	1432.1	1349.2	1278.4	1214.0	1153.7	1089.1	1020.0	950.7	894.0	843.7
32.5°	1502.5	1407.8	1320.3	1243.2	1174.9	1116.3	1056.8	991.0	923.0	865.6	815.2
35°	1481.4	1371.8	1271.6	1184.6	1111.7	1051.4	1001.6	940.2	877.8	822.2	774.0
37.5°	1454.6	1324.5	1217.1	1125.8	1045.9	982.4	936.0	888.9	829.0	775.5	731.8
40°	1433.6	1291.0	1177.2	1083.9	1001.1	934.9	892.0	847.4	797.6	747.8	701.7
42.5°	1407.2	1260.8	1137.0	1036.5	954.4	890.1	845.0	807.1	763.2	716.7	673.9
45°	1358.7	1206.1	1071.9	963.8	880.9	817.5	770.8	742.6	709.5	665.4	629.2
47.5°	1287.3	1140.3	1001.5	890.0	804.5	745.7	702.0	674.8	651.5	618.7	585.9
50°	1223.9	1091.3	950.7	840.0	754.6	695.3	655.0	630.3	610.4	585.2	557.4
52.5°	1153.0	1029.6	900.8	791.4	706.8	648.3	608.8	587.1	570.6	552.5	525.1
55°	1040.4	935.5	816.0	712.1	634.0	576.8	542.2	523.3	509.7	496.0	479.3
57.5°	916.3	834.2	728.3	633.5	561.5	509.5	477.2	458.8	448.3	441.2	431.3
60°	829.0	758.8	667.5	581.0	510.8	464.6	433.1	419.0	410.1	404.2	397.0
62.5°	748.1	690.4	605.8	526.8	465.4	421.8	393.7	380.0	371.4	368.6	362.5
65°	628.7	584.2	514.4	448.9	396.5	359.2	335.6	322.4	317.2	314.1	314.7
67.5°	511.2	484.0	428.0	372.1	330.2	299.0	280.1	270.0	267.4	263.3	263.2
70°	439.4	419.0	371.8	323.1	285.8	261.7	244.9	234.4	231.8	229.6	229.1
72.5°	376.1	358.2	317.2	278.1	244.7	223.5	209.6	203.4	199.0	197.8	197.7
75°	282.7	272.7	240.1	209.2	186.1	171.5	162.1	156.2	153.1	152.6	153.1
77.5°	201.0	192.3	171.6	149.7	135.1	124.0	116.0	114.0	110.5	110.6	110.0
80°	151.0	145.2	132.2	114.8	102.8	93.3	89.2	85.4	84.4	82.8	84.4
82.5°	109.5	103.3	94.4	83.4	73.4	67.8	63.5	62.4	61.8	61.0	61.4
85°	54.0	54.5	49.3	40.9	36.7	33.5	30.9	30.9	30.4	29.9	30.4
87.5°	21.1	19.9	17.9	16.4	13.8	12.2	11.5	11.5	10.6	10.6	11.3
90°	13.0	11.4	9.9	8.2	6.4	4.5	2.8	1.0	2.8	4.5	6.4
92.5°	13.3	11.9	10.6	10.5	11.7	13.0	14.2	15.6	14.2	13.0	11.7
95°	33.1	41.7	50.2	54.8	55.4	56.1	56.8	57.5	56.8	56.1	55.4
97.5°	83.3	100.2	117.0	124.8	123.6	122.4	121.2	120.0	121.2	122.4	123.6
100°	173.7	172.8	171.9	171.1	170.4	169.8	169.1	168.3	169.1	169.8	170.4
102.5°	222.8	222.3	221.7	221.0	220.2	219.3	218.4	217.6	218.4	219.3	220.2
105°	300.4	300.4	300.4	300.0	299.1	298.2	297.3	296.4	297.3	298.2	299.1
107.5°	379.4	379.0	378.5	378.3	378.3	378.3	378.3	378.3	378.3	378.3	378.3
110°	432.7	432.2	431.8	431.5	431.5	431.5	431.5	431.5	431.5	431.5	431.5



TEST NUMBER: P333232-840

CATALOG NUMBER: S125DIP-S850D1035U840-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°	95°	100°	105°
112.5°	484.6	484.4	484.1	483.7	483.2	482.6	482.1	481.6	482.1	482.6	483.2
115°	562.2	562.0	561.8	561.1	560.0	558.9	557.7	556.6	557.7	558.9	560.0
117.5°	636.1	635.3	634.5	634.1	634.1	634.1	634.2	634.2	634.2	634.1	634.1
120°	683.3	682.7	682.0	681.8	682.0	682.2	682.4	682.7	682.4	682.2	682.0
122.5°	730.0	729.7	729.3	728.8	727.9	727.1	726.2	725.4	726.2	727.1	727.9
125°	798.6	798.6	798.6	797.8	796.3	794.7	793.0	791.5	793.0	794.7	796.3
127.5°	859.4	859.5	859.6	859.1	858.0	856.9	855.8	854.6	855.8	856.9	858.0
130°	899.0	898.8	898.5	897.9	896.8	895.6	894.5	893.3	894.5	895.6	896.8
132.5°	936.8	937.2	937.7	937.3	935.9	934.7	933.4	932.1	933.4	934.7	935.9
135°	992.1	992.5	993.0	992.5	991.2	989.9	988.5	987.1	988.5	989.9	991.2
137.5°	1042.0	1042.4	1042.8	1042.4	1041.3	1040.1	1038.9	1037.7	1038.9	1040.1	1041.3
140°	1072.3	1072.5	1072.8	1072.6	1072.2	1071.8	1071.3	1070.9	1071.3	1071.8	1072.2
142.5°	1102.7	1102.4	1102.1	1101.8	1101.5	1101.3	1101.0	1100.7	1101.0	1101.3	1101.5
145°	1146.5	1146.5	1146.5	1146.2	1145.8	1145.3	1144.9	1144.5	1144.9	1145.3	1145.8
147.5°	1183.1	1182.8	1182.5	1182.3	1182.5	1182.6	1182.7	1182.8	1182.7	1182.6	1182.5
150°	1206.1	1205.6	1205.2	1205.2	1205.6	1206.1	1206.5	1207.0	1206.5	1206.1	1205.6
152.5°	1227.0	1226.6	1226.2	1226.4	1227.4	1228.4	1229.4	1230.3	1229.4	1228.4	1227.4
155°	1255.5	1255.1	1254.6	1255.1	1256.4	1257.7	1259.1	1260.4	1259.1	1257.7	1256.4
157.5°	1280.1	1280.0	1280.0	1280.4	1281.2	1282.0	1282.7	1283.5	1282.7	1282.0	1281.2
160°	1294.2	1294.0	1293.7	1294.3	1295.7	1297.1	1298.4	1299.7	1298.4	1297.1	1295.7
162.5°	1307.2	1306.9	1306.7	1307.3	1308.6	1309.9	1311.3	1312.6	1311.3	1309.9	1308.6
165°	1324.4	1324.2	1324.0	1324.6	1326.0	1327.3	1328.6	1330.0	1328.6	1327.3	1326.0
167.5°	1337.2	1337.0	1336.8	1337.4	1338.7	1340.1	1341.5	1342.9	1341.5	1340.1	1338.7
170°	1343.6	1343.4	1343.2	1343.8	1345.4	1347.0	1348.6	1350.1	1348.6	1347.0	1345.4
172.5°	1348.9	1348.5	1348.2	1348.7	1350.3	1351.8	1353.4	1354.9	1353.4	1351.8	1350.3
175°	1354.7	1354.5	1354.3	1354.8	1356.1	1357.6	1358.9	1360.2	1358.9	1357.6	1356.1
177.5°	1358.3	1358.1	1357.9	1358.4	1359.4	1360.5	1361.6	1362.6	1361.6	1360.5	1359.4
180°	1360.2	1360.2	1360.2	1360.2	1360.2	1360.2	1360.2	1360.2	1360.2	1360.2	1360.2



TEST NUMBER: P333232-840

CATALOG NUMBER: S125DIP-S850D1035U840-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	110°	115°	120°	125°	130°	135°	140°	145°	150°	155°	160°
0°	1235.5	1235.5	1235.5	1235.5	1235.5	1235.5	1235.5	1235.5	1235.5	1235.5	1235.5
2.5°	1214.1	1209.4	1205.7	1197.3	1192.7	1186.4	1181.3	1186.8	1180.9	1183.5	1179.6
5°	1176.2	1161.5	1151.0	1135.8	1122.7	1110.6	1101.8	1100.1	1095.9	1093.9	1087.5
7.5°	1130.6	1112.3	1094.3	1074.4	1057.5	1040.5	1029.6	1020.6	1014.6	1006.7	1001.4
10°	1103.8	1079.1	1058.2	1034.1	1013.1	994.7	980.1	972.7	965.9	955.9	952.3
12.5°	1070.7	1045.2	1019.6	993.8	973.7	953.2	940.6	929.5	924.8	913.5	912.4
15°	1031.0	992.7	967.5	941.3	913.4	896.7	886.2	874.1	868.9	861.0	855.3
17.5°	983.5	949.4	917.9	890.7	866.9	852.7	839.7	831.4	822.4	817.3	807.9
20°	949.2	916.7	885.1	856.3	838.0	821.7	811.2	803.3	794.0	791.3	781.8
22.5°	920.2	884.3	854.1	829.9	809.8	791.5	780.1	774.9	768.3	760.2	758.3
25°	873.1	835.9	810.2	786.1	768.2	751.4	743.6	736.8	730.4	724.7	722.6
27.5°	832.4	799.1	768.6	746.8	731.3	716.0	709.0	700.7	696.2	691.6	685.9
30°	803.9	769.8	743.1	722.1	705.3	691.7	684.3	678.5	674.4	670.1	667.0
32.5°	774.5	743.0	717.0	696.5	679.7	669.4	662.9	658.8	654.2	649.1	645.2
35°	735.7	701.0	675.9	658.1	645.0	637.1	629.8	626.1	620.9	620.9	616.6
37.5°	692.0	662.1	639.9	623.6	611.9	604.8	596.8	594.3	591.0	588.8	587.3
40°	666.0	638.1	617.2	601.0	588.3	582.6	576.3	572.1	570.0	567.3	566.3
42.5°	639.1	612.6	592.5	577.4	566.5	561.6	555.7	552.8	548.6	545.1	544.5
45°	598.3	572.6	554.3	542.2	532.8	527.0	523.3	517.1	514.9	510.8	510.2
47.5°	559.6	534.9	516.9	507.1	498.8	494.0	488.3	482.0	479.6	477.5	477.3
50°	530.7	508.2	491.3	481.9	474.0	467.3	461.4	457.3	455.7	455.7	456.8
52.5°	501.3	482.1	467.9	456.4	448.9	441.6	436.3	433.7	431.3	433.8	435.8
55°	458.3	438.9	428.4	417.4	410.1	401.6	399.1	398.0	396.5	400.6	402.7
57.5°	412.8	399.2	386.9	376.0	369.4	364.6	361.0	360.3	363.2	365.3	372.1
60°	383.8	368.1	357.1	348.7	340.8	337.7	336.7	335.6	337.7	343.5	352.3
62.5°	351.9	339.2	327.3	321.0	315.3	310.0	309.8	310.4	314.7	321.2	330.1
65°	305.2	294.2	286.3	278.9	274.3	271.1	272.2	274.3	278.9	287.9	297.8
67.5°	257.7	250.1	243.1	237.1	232.6	232.6	233.7	236.8	242.4	252.7	261.8
70°	227.0	218.6	212.9	210.3	206.6	204.5	207.6	212.9	217.6	227.0	234.9
72.5°	196.4	189.3	184.8	183.0	181.5	179.8	180.8	186.4	192.9	202.3	211.5
75°	151.0	148.3	145.2	143.2	141.6	142.6	143.7	149.0	154.2	164.1	174.6
77.5°	110.2	107.4	105.6	105.1	104.2	104.7	107.8	111.6	116.7	124.0	131.9
80°	83.4	82.3	81.3	80.8	80.8	81.3	85.4	88.1	92.8	99.7	105.9
82.5°	60.7	60.1	59.9	59.8	60.2	60.3	62.8	66.2	70.2	75.3	80.8
85°	32.0	30.9	32.5	33.0	32.0	33.5	34.6	36.7	38.3	40.9	43.5
87.5°	12.1	13.3	13.2	13.9	14.2	15.3	15.1	17.1	18.2	19.2	19.0
90°	8.2	9.9	11.4	13.0	14.5	16.2	17.3	18.4	19.5	20.6	21.5
92.5°	10.5	10.6	11.9	13.3	14.7	16.2	17.3	18.4	19.5	20.6	21.3
95°	54.8	50.2	41.7	33.1	24.6	16.2	17.3	18.4	19.5	20.6	21.2
97.5°	124.8	117.0	100.2	83.3	66.4	49.6	43.3	37.0	30.7	24.3	21.2
100°	171.1	171.9	172.8	173.7	174.5	175.4	142.1	108.7	75.3	41.9	24.7
102.5°	221.0	221.7	222.3	222.8	223.3	223.9	217.5	211.2	204.9	198.5	187.8
105°	300.0	300.4	300.4	300.4	300.4	300.4	300.4	300.4	300.4	300.4	300.3
107.5°	378.3	378.5	379.0	379.4	379.9	380.3	380.4	380.4	380.5	380.5	380.2
110°	431.5	431.8	432.2	432.7	433.1	433.5	432.9	432.2	431.5	430.9	430.7



TEST NUMBER: P333232-840

CATALOG NUMBER: S125DIP-S850D1035U840-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	110°	115°	120°	125°	130°	135°	140°	145°	150°	155°	160°
112.5°	483.7	484.1	484.4	484.6	484.9	485.2	484.3	483.5	482.6	481.8	481.2
115°	561.1	561.8	562.0	562.2	562.4	562.6	561.8	560.9	560.0	559.1	558.0
117.5°	634.1	634.5	635.3	636.1	637.0	637.8	636.7	635.5	634.4	633.2	632.3
120°	681.8	682.0	682.7	683.3	684.0	684.7	684.2	683.8	683.3	682.9	682.1
122.5°	728.8	729.3	729.7	730.0	730.3	730.6	730.1	729.7	729.3	728.8	727.9
125°	797.8	798.6	798.6	798.6	798.6	798.6	797.7	796.8	795.9	795.0	794.3
127.5°	859.1	859.6	859.5	859.4	859.2	859.1	858.6	858.1	857.6	857.1	856.1
130°	897.9	898.5	898.8	899.0	899.2	899.4	898.8	898.1	897.4	896.8	895.9
132.5°	937.3	937.7	937.2	936.8	936.2	935.7	935.5	935.4	935.3	935.1	934.5
135°	992.5	993.0	992.5	992.1	991.6	991.2	990.7	990.3	989.9	989.4	988.5
137.5°	1042.4	1042.8	1042.4	1042.0	1041.6	1041.2	1041.3	1041.4	1041.5	1041.6	1041.0
140°	1072.6	1072.8	1072.5	1072.3	1072.1	1071.9	1072.3	1072.8	1073.2	1073.6	1073.2
142.5°	1101.8	1102.1	1102.4	1102.7	1103.0	1103.3	1103.4	1103.5	1103.6	1103.7	1103.1
145°	1146.2	1146.5	1146.5	1146.5	1146.5	1146.5	1146.7	1146.9	1147.1	1147.3	1146.8
147.5°	1182.3	1182.5	1182.8	1183.1	1183.3	1183.6	1183.9	1184.1	1184.4	1184.7	1184.0
150°	1205.2	1205.2	1205.6	1206.1	1206.5	1207.0	1207.4	1207.9	1208.3	1208.7	1208.1
152.5°	1226.4	1226.2	1226.6	1227.0	1227.5	1227.9	1228.4	1228.8	1229.3	1229.7	1229.1
155°	1255.1	1254.6	1255.1	1255.5	1255.9	1256.4	1257.1	1257.7	1258.4	1259.1	1258.5
157.5°	1280.4	1280.0	1280.0	1280.1	1280.1	1280.2	1280.9	1281.6	1282.3	1283.0	1282.5
160°	1294.3	1293.7	1294.0	1294.2	1294.4	1294.6	1295.6	1296.5	1297.4	1298.3	1297.8
162.5°	1307.3	1306.7	1306.9	1307.2	1307.4	1307.6	1308.9	1310.1	1311.3	1312.6	1312.2
165°	1324.6	1324.0	1324.2	1324.4	1324.7	1324.9	1326.3	1327.6	1329.0	1330.3	1330.1
167.5°	1337.4	1336.8	1337.0	1337.2	1337.4	1337.7	1339.3	1340.9	1342.5	1344.1	1343.9
170°	1343.8	1343.2	1343.4	1343.6	1343.8	1344.1	1345.8	1347.7	1349.5	1351.3	1351.1
172.5°	1348.7	1348.2	1348.5	1348.9	1349.3	1349.7	1351.3	1352.9	1354.5	1356.1	1355.9
175°	1354.8	1354.3	1354.5	1354.7	1354.9	1355.1	1357.0	1358.8	1360.6	1362.3	1362.2
177.5°	1358.4	1357.9	1358.1	1358.3	1358.5	1358.6	1359.9	1361.1	1362.4	1363.6	1363.5
180°	1360.2	1360.2	1360.2	1360.2	1360.2	1360.2	1360.2	1360.2	1360.2	1360.2	1360.2



TEST NUMBER: P333232-840

CATALOG NUMBER: S125DIP-S850D1035U840-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	165°	170°	175°	180°	185°	190°	195°	200°	205°	210°	215°
0°	1235.5	1235.5	1235.5	1235.5	1235.5	1235.5	1235.5	1235.5	1235.5	1235.5	1235.5
2.5°	1177.1	1180.0	1177.5	1180.9	1177.5	1180.0	1177.1	1179.6	1183.5	1180.9	1186.8
5°	1084.9	1080.3	1083.4	1081.3	1083.4	1080.3	1084.9	1087.5	1093.9	1095.9	1100.1
7.5°	999.8	995.2	990.2	987.7	990.2	995.2	999.8	1001.4	1006.7	1014.6	1020.6
10°	946.5	940.7	940.2	936.5	940.2	940.7	946.5	952.3	955.9	965.9	972.7
12.5°	907.5	902.1	896.2	894.6	896.2	902.1	907.5	912.4	913.5	924.8	929.5
15°	852.1	847.9	844.2	847.4	844.2	847.9	852.1	855.3	861.0	868.9	874.1
17.5°	806.1	802.6	801.9	798.1	801.9	802.6	806.1	807.9	817.3	822.4	831.4
20°	777.1	774.5	775.6	768.7	775.6	774.5	777.1	781.8	791.3	794.0	803.3
22.5°	754.1	748.9	748.3	746.9	748.3	748.9	754.1	758.3	760.2	768.3	774.9
25°	717.9	715.3	712.7	715.3	712.7	715.3	717.9	722.6	724.7	730.4	736.8
27.5°	686.3	683.2	682.5	682.8	682.5	683.2	686.3	685.9	691.6	696.2	700.7
30°	667.0	661.8	662.3	661.8	662.3	661.8	667.0	667.0	670.1	674.4	678.5
32.5°	646.0	642.5	641.8	640.8	641.8	642.5	646.0	645.2	649.1	654.2	658.8
35°	615.1	615.1	612.5	612.5	612.5	615.1	615.1	616.6	620.9	620.9	626.1
37.5°	586.0	585.5	583.9	584.2	583.9	585.5	586.0	587.3	588.8	591.0	594.3
40°	564.2	563.7	562.1	559.0	562.1	563.7	564.2	566.3	567.3	570.0	572.1
42.5°	543.2	541.5	540.8	539.7	540.8	541.5	543.2	544.5	545.1	548.6	552.8
45°	510.2	510.2	509.2	508.7	509.2	510.2	510.2	510.2	510.8	514.9	517.1
47.5°	478.2	479.1	481.1	480.8	481.1	479.1	478.2	477.3	477.5	479.6	482.0
50°	458.8	459.4	460.9	461.4	460.9	459.4	458.8	456.8	455.7	455.7	457.3
52.5°	437.5	440.5	442.4	442.1	442.4	440.5	437.5	435.8	433.8	431.3	433.7
55°	407.5	411.1	414.8	415.4	414.8	411.1	407.5	402.7	400.6	396.5	398.0
57.5°	377.8	382.9	386.8	388.0	386.8	382.9	377.8	372.1	365.3	363.2	360.3
60°	357.6	364.5	369.2	371.2	369.2	364.5	357.6	352.3	343.5	337.7	335.6
62.5°	338.3	346.0	350.7	351.1	350.7	346.0	338.3	330.1	321.2	314.7	310.4
65°	306.8	314.7	318.8	321.9	318.8	314.7	306.8	297.8	287.9	278.9	274.3
67.5°	272.8	280.6	285.3	287.8	285.3	280.6	272.8	261.8	252.7	242.4	236.8
70°	248.0	255.9	262.2	264.3	262.2	255.9	248.0	234.9	227.0	217.6	212.9
72.5°	223.7	230.8	235.8	238.2	235.8	230.8	223.7	211.5	202.3	192.9	186.4
75°	181.5	190.9	195.6	198.2	195.6	190.9	181.5	174.6	164.1	154.2	149.0
77.5°	139.9	148.6	151.4	152.7	151.4	148.6	139.9	131.9	124.0	116.7	111.6
80°	112.2	117.4	121.1	121.7	121.1	117.4	112.2	105.9	99.7	92.8	88.1
82.5°	86.2	90.6	91.8	93.1	91.8	90.6	86.2	80.8	75.3	70.2	66.2
85°	47.2	49.3	49.8	49.3	49.8	49.3	47.2	43.5	40.9	38.3	36.7
87.5°	20.0	19.7	19.8	20.8	19.8	19.7	20.0	19.0	19.2	18.2	17.1
90°	22.2	22.8	23.5	24.2	23.5	22.8	22.2	21.5	20.6	19.5	18.4
92.5°	21.6	21.9	22.3	22.6	22.3	21.9	21.6	21.3	20.6	19.5	18.4
95°	21.2	21.2	21.2	21.2	21.2	21.2	21.2	21.2	20.6	19.5	18.4
97.5°	21.2	21.2	21.2	21.2	21.2	21.2	21.2	21.2	24.3	30.7	37.0
100°	23.8	22.9	22.1	21.2	22.1	22.9	23.8	24.7	41.9	75.3	108.7
102.5°	172.6	157.3	142.1	126.8	142.1	157.3	172.6	187.8	198.5	204.9	211.2
105°	300.1	299.9	299.7	299.4	299.7	299.9	300.1	300.3	300.4	300.4	300.4
107.5°	379.5	378.9	378.2	377.5	378.2	378.9	379.5	380.2	380.5	380.5	380.4
110°	430.9	431.1	431.3	431.5	431.3	431.1	430.9	430.7	430.9	431.5	432.2



TEST NUMBER: P333232-840

CATALOG NUMBER: S125DIP-S850D1035U840-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	165°	170°	175°	180°	185°	190°	195°	200°	205°	210°	215°
112.5°	480.9	480.6	480.3	480.0	480.3	480.6	480.9	481.2	481.8	482.6	483.5
115°	556.6	555.2	553.9	552.6	553.9	555.2	556.6	558.0	559.1	560.0	560.9
117.5°	631.8	631.2	630.6	630.0	630.6	631.2	631.8	632.3	633.2	634.4	635.5
120°	681.0	679.8	678.7	677.6	678.7	679.8	681.0	682.1	682.9	683.3	683.8
122.5°	726.7	725.4	724.1	722.8	724.1	725.4	726.7	727.9	728.8	729.3	729.7
125°	793.6	792.8	792.2	791.5	792.2	792.8	793.6	794.3	795.0	795.9	796.8
127.5°	854.3	852.7	851.1	849.4	851.1	852.7	854.3	856.1	857.1	857.6	858.1
130°	894.7	893.6	892.5	891.3	892.5	893.6	894.7	895.9	896.8	897.4	898.1
132.5°	933.4	932.3	931.2	930.1	931.2	932.3	933.4	934.5	935.1	935.3	935.4
135°	987.1	985.8	984.4	983.1	984.4	985.8	987.1	988.5	989.4	989.9	990.3
137.5°	1039.9	1038.6	1037.5	1036.3	1037.5	1038.6	1039.9	1041.0	1041.6	1041.5	1041.4
140°	1071.9	1070.5	1069.1	1067.8	1069.1	1070.5	1071.9	1073.2	1073.6	1073.2	1072.8
142.5°	1101.7	1100.3	1099.0	1097.6	1099.0	1100.3	1101.7	1103.1	1103.7	1103.6	1103.5
145°	1145.5	1144.1	1142.8	1141.5	1142.8	1144.1	1145.5	1146.8	1147.3	1147.1	1146.9
147.5°	1182.3	1180.7	1179.1	1177.5	1179.1	1180.7	1182.3	1184.0	1184.7	1184.4	1184.1
150°	1206.3	1204.5	1202.6	1200.9	1202.6	1204.5	1206.3	1208.1	1208.7	1208.3	1207.9
152.5°	1227.5	1225.9	1224.3	1222.6	1224.3	1225.9	1227.5	1229.1	1229.7	1229.3	1228.8
155°	1256.7	1254.9	1253.1	1251.3	1253.1	1254.9	1256.7	1258.5	1259.1	1258.4	1257.7
157.5°	1280.7	1278.9	1277.1	1275.4	1277.1	1278.9	1280.7	1282.5	1283.0	1282.3	1281.6
160°	1296.1	1294.2	1292.4	1290.6	1292.4	1294.2	1296.1	1297.8	1298.3	1297.4	1296.5
162.5°	1310.3	1308.3	1306.4	1304.3	1306.4	1308.3	1310.3	1312.2	1312.6	1311.3	1310.1
165°	1328.3	1326.5	1324.7	1322.9	1324.7	1326.5	1328.3	1330.1	1330.3	1329.0	1327.6
167.5°	1341.9	1339.9	1337.9	1335.8	1337.9	1339.9	1341.9	1343.9	1344.1	1342.5	1340.9
170°	1349.1	1347.2	1345.1	1343.1	1345.1	1347.2	1349.1	1351.1	1351.3	1349.5	1347.7
172.5°	1353.9	1351.9	1349.9	1348.0	1349.9	1351.9	1353.9	1355.9	1356.1	1354.5	1352.9
175°	1360.2	1358.2	1356.1	1354.1	1356.1	1358.2	1360.2	1362.2	1362.3	1360.6	1358.8
177.5°	1362.1	1360.7	1359.3	1357.8	1359.3	1360.7	1362.1	1363.5	1363.6	1362.4	1361.1
180°	1360.2	1360.2	1360.2	1360.2	1360.2	1360.2	1360.2	1360.2	1360.2	1360.2	1360.2



TEST NUMBER: P333232-840

CATALOG NUMBER: S125DIP-S850D1035U840-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	220°	225°	230°	235°	240°	245°	250°	255°	260°	265°	270°
0°	1235.5	1235.5	1235.5	1235.5	1235.5	1235.5	1235.5	1235.5	1235.5	1235.5	1235.5
2.5°	1181.3	1186.4	1192.7	1197.3	1205.7	1209.4	1214.1	1217.8	1224.6	1230.8	1238.4
5°	1101.8	1110.6	1122.7	1135.8	1151.0	1161.5	1176.2	1185.1	1203.0	1219.2	1234.9
7.5°	1029.6	1040.5	1057.5	1074.4	1094.3	1112.3	1130.6	1151.0	1173.8	1200.6	1222.8
10°	980.1	994.7	1013.1	1034.1	1058.2	1079.1	1103.8	1125.8	1153.7	1185.1	1214.5
12.5°	940.6	953.2	973.7	993.8	1019.6	1045.2	1070.7	1099.8	1132.3	1167.1	1204.0
15°	886.2	896.7	913.4	941.3	967.5	992.7	1031.0	1058.2	1099.1	1137.9	1182.5
17.5°	839.7	852.7	866.9	890.7	917.9	949.4	983.5	1017.7	1057.1	1106.3	1156.6
20°	811.2	821.7	838.0	856.3	885.1	916.7	949.2	983.7	1032.0	1082.9	1136.8
22.5°	780.1	791.5	809.8	829.9	854.1	884.3	920.2	958.2	1008.5	1058.5	1117.1
25°	743.6	751.4	768.2	786.1	810.2	835.9	873.1	915.0	964.8	1022.0	1081.8
27.5°	709.0	716.0	731.3	746.8	768.6	799.1	832.4	874.7	921.7	979.7	1045.9
30°	684.3	691.7	705.3	722.1	743.1	769.8	803.9	843.7	894.0	950.7	1020.0
32.5°	662.9	669.4	679.7	696.5	717.0	743.0	774.5	815.2	865.6	923.0	991.0
35°	629.8	637.1	645.0	658.1	675.9	701.0	735.7	774.0	822.2	877.8	940.2
37.5°	596.8	604.8	611.9	623.6	639.9	662.1	692.0	731.8	775.5	829.0	888.9
40°	576.3	582.6	588.3	601.0	617.2	638.1	666.0	701.7	747.8	797.6	847.4
42.5°	555.7	561.6	566.5	577.4	592.5	612.6	639.1	673.9	716.7	763.2	807.1
45°	523.3	527.0	532.8	542.2	554.3	572.6	598.3	629.2	665.4	709.5	742.6
47.5°	488.3	494.0	498.8	507.1	516.9	534.9	559.6	585.9	618.7	651.5	674.8
50°	461.4	467.3	474.0	481.9	491.3	508.2	530.7	557.4	585.2	610.4	630.3
52.5°	436.3	441.6	448.9	456.4	467.9	482.1	501.3	525.1	552.5	570.6	587.1
55°	399.1	401.6	410.1	417.4	428.4	438.9	458.3	479.3	496.0	509.7	523.3
57.5°	361.0	364.6	369.4	376.0	386.9	399.2	412.8	431.3	441.2	448.3	458.8
60°	336.7	337.7	340.8	348.7	357.1	368.1	383.8	397.0	404.2	410.1	419.0
62.5°	309.8	310.0	315.3	321.0	327.3	339.2	351.9	362.5	368.6	371.4	380.0
65°	272.2	271.1	274.3	278.9	286.3	294.2	305.2	314.7	314.1	317.2	322.4
67.5°	233.7	232.6	232.6	237.1	243.1	250.1	257.7	263.2	263.3	267.4	270.0
70°	207.6	204.5	206.6	210.3	212.9	218.6	227.0	229.1	229.6	231.8	234.4
72.5°	180.8	179.8	181.5	183.0	184.8	189.3	196.4	197.7	197.8	199.0	203.4
75°	143.7	142.6	141.6	143.2	145.2	148.3	151.0	153.1	152.6	153.1	156.2
77.5°	107.8	104.7	104.2	105.1	105.6	107.4	110.2	110.0	110.6	110.5	114.0
80°	85.4	81.3	80.8	80.8	81.3	82.3	83.4	84.4	82.8	84.4	85.4
82.5°	62.8	60.3	60.2	59.8	59.9	60.1	60.7	61.4	61.0	61.8	62.4
85°	34.6	33.5	32.0	33.0	32.5	30.9	32.0	30.4	29.9	30.4	30.9
87.5°	15.1	15.3	14.2	13.9	13.2	13.3	12.1	11.3	10.6	10.6	11.5
90°	17.3	16.2	14.5	13.0	11.4	9.9	8.2	6.4	4.5	2.8	1.0
92.5°	17.3	16.2	14.7	13.3	11.9	10.6	10.5	11.7	13.0	14.2	15.6
95°	17.3	16.2	24.6	33.1	41.7	50.2	54.8	55.4	56.1	56.8	57.5
97.5°	43.3	49.6	66.4	83.3	100.2	117.0	124.8	123.6	122.4	121.2	120.0
100°	142.1	175.4	174.5	173.7	172.8	171.9	171.1	170.4	169.8	169.1	168.3
102.5°	217.5	223.9	223.3	222.8	222.3	221.7	221.0	220.2	219.3	218.4	217.6
105°	300.4	300.4	300.4	300.4	300.4	300.4	300.0	299.1	298.2	297.3	296.4
107.5°	380.4	380.3	379.9	379.4	379.0	378.5	378.3	378.3	378.3	378.3	378.3
110°	432.9	433.5	433.1	432.7	432.2	431.8	431.5	431.5	431.5	431.5	431.5



TEST NUMBER: P333232-840

CATALOG NUMBER: S125DIP-S850D1035U840-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	220°	225°	230°	235°	240°	245°	250°	255°	260°	265°	270°
112.5°	484.3	485.2	484.9	484.6	484.4	484.1	483.7	483.2	482.6	482.1	481.6
115°	561.8	562.6	562.4	562.2	562.0	561.8	561.1	560.0	558.9	557.7	556.6
117.5°	636.7	637.8	637.0	636.1	635.3	634.5	634.1	634.1	634.1	634.2	634.2
120°	684.2	684.7	684.0	683.3	682.7	682.0	681.8	682.0	682.2	682.4	682.7
122.5°	730.1	730.6	730.3	730.0	729.7	729.3	728.8	727.9	727.1	726.2	725.4
125°	797.7	798.6	798.6	798.6	798.6	798.6	797.8	796.3	794.7	793.0	791.5
127.5°	858.6	859.1	859.2	859.4	859.5	859.6	859.1	858.0	856.9	855.8	854.6
130°	898.8	899.4	899.2	899.0	898.8	898.5	897.9	896.8	895.6	894.5	893.3
132.5°	935.5	935.7	936.2	936.8	937.2	937.7	937.3	935.9	934.7	933.4	932.1
135°	990.7	991.2	991.6	992.1	992.5	993.0	992.5	991.2	989.9	988.5	987.1
137.5°	1041.3	1041.2	1041.6	1042.0	1042.4	1042.8	1042.4	1041.3	1040.1	1038.9	1037.7
140°	1072.3	1071.9	1072.1	1072.3	1072.5	1072.8	1072.6	1072.2	1071.8	1071.3	1070.9
142.5°	1103.4	1103.3	1103.0	1102.7	1102.4	1102.1	1101.8	1101.5	1101.3	1101.0	1100.7
145°	1146.7	1146.5	1146.5	1146.5	1146.5	1146.5	1146.2	1145.8	1145.3	1144.9	1144.5
147.5°	1183.9	1183.6	1183.3	1183.1	1182.8	1182.5	1182.3	1182.5	1182.6	1182.7	1182.8
150°	1207.4	1207.0	1206.5	1206.1	1205.6	1205.2	1205.2	1205.6	1206.1	1206.5	1207.0
152.5°	1228.4	1227.9	1227.5	1227.0	1226.6	1226.2	1226.4	1227.4	1228.4	1229.4	1230.3
155°	1257.1	1256.4	1255.9	1255.5	1255.1	1254.6	1255.1	1256.4	1257.7	1259.1	1260.4
157.5°	1280.9	1280.2	1280.1	1280.1	1280.0	1280.0	1280.4	1281.2	1282.0	1282.7	1283.5
160°	1295.6	1294.6	1294.4	1294.2	1294.0	1293.7	1294.3	1295.7	1297.1	1298.4	1299.7
162.5°	1308.9	1307.6	1307.4	1307.2	1306.9	1306.7	1307.3	1308.6	1309.9	1311.3	1312.6
165°	1326.3	1324.9	1324.7	1324.4	1324.2	1324.0	1324.6	1326.0	1327.3	1328.6	1330.0
167.5°	1339.3	1337.7	1337.4	1337.2	1337.0	1336.8	1337.4	1338.7	1340.1	1341.5	1342.9
170°	1345.8	1344.1	1343.8	1343.6	1343.4	1343.2	1343.8	1345.4	1347.0	1348.6	1350.1
172.5°	1351.3	1349.7	1349.3	1348.9	1348.5	1348.2	1348.7	1350.3	1351.8	1353.4	1354.9
175°	1357.0	1355.1	1354.9	1354.7	1354.5	1354.3	1354.8	1356.1	1357.6	1358.9	1360.2
177.5°	1359.9	1358.6	1358.5	1358.3	1358.1	1357.9	1358.4	1359.4	1360.5	1361.6	1362.6
180°	1360.2	1360.2	1360.2	1360.2	1360.2	1360.2	1360.2	1360.2	1360.2	1360.2	1360.2



TEST NUMBER: P333232-840

CATALOG NUMBER: S125DIP-S850D1035U840-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	275°	280°	285°	290°	295°	300°	305°	310°	315°	320°	325°
0°	1235.5	1235.5	1235.5	1235.5	1235.5	1235.5	1235.5	1235.5	1235.5	1235.5	1235.5
2.5°	1242.1	1248.0	1251.8	1258.9	1264.8	1268.2	1271.1	1273.6	1276.6	1279.1	1286.2
5°	1250.1	1263.7	1275.3	1293.1	1309.4	1321.9	1335.5	1347.7	1357.7	1371.8	1382.8
7.5°	1246.7	1270.9	1296.3	1323.8	1352.0	1378.3	1402.4	1424.9	1445.4	1470.2	1491.9
10°	1243.3	1276.4	1308.9	1346.0	1384.3	1416.8	1447.2	1478.2	1500.8	1532.3	1558.9
12.5°	1240.8	1279.7	1318.9	1363.7	1405.7	1451.7	1492.2	1514.7	1549.0	1574.2	1606.0
15°	1230.2	1281.6	1335.5	1385.9	1445.7	1488.1	1523.9	1567.9	1599.8	1631.8	1666.5
17.5°	1211.2	1269.4	1329.8	1395.8	1453.2	1498.7	1544.7	1587.2	1625.4	1668.3	1711.3
20°	1202.4	1260.6	1329.8	1397.5	1453.6	1501.3	1548.5	1595.2	1637.1	1692.1	1742.0
22.5°	1184.0	1254.4	1318.1	1384.0	1441.8	1493.8	1547.2	1600.2	1656.0	1718.2	1780.6
25°	1151.0	1222.3	1290.0	1355.0	1413.2	1478.2	1535.4	1606.2	1677.5	1759.8	1837.4
27.5°	1116.8	1185.1	1247.1	1309.9	1377.8	1451.4	1525.5	1605.9	1699.2	1803.1	1912.6
30°	1089.1	1153.7	1214.0	1278.4	1349.2	1432.1	1513.4	1608.8	1716.8	1833.7	1963.8
32.5°	1056.8	1116.3	1174.9	1243.2	1320.3	1407.8	1502.5	1607.1	1737.0	1869.9	2003.7
35°	1001.6	1051.4	1111.7	1184.6	1271.6	1371.8	1481.4	1605.1	1754.0	1906.6	2019.4
37.5°	936.0	982.4	1045.9	1125.8	1217.1	1324.5	1454.6	1601.4	1759.6	1881.3	1917.6
40°	892.0	934.9	1001.1	1083.9	1177.2	1291.0	1433.6	1588.8	1742.0	1819.6	1789.7
42.5°	845.0	890.1	954.4	1036.5	1137.0	1260.8	1407.2	1562.5	1690.8	1720.2	1616.9
45°	770.8	817.5	880.9	963.8	1071.9	1206.1	1358.7	1499.8	1573.7	1520.7	1360.8
47.5°	702.0	745.7	804.5	890.0	1001.5	1140.3	1287.3	1399.8	1405.6	1279.3	1108.4
50°	655.0	695.3	754.6	840.0	950.7	1091.3	1223.9	1312.5	1272.6	1129.5	965.3
52.5°	608.8	648.3	706.8	791.4	900.8	1029.6	1153.0	1215.2	1140.1	993.2	852.9
55°	542.2	576.8	634.0	712.1	816.0	935.5	1040.4	1061.9	964.3	819.6	705.8
57.5°	477.2	509.5	561.5	633.5	728.3	834.2	916.3	911.7	808.6	684.4	594.1
60°	433.1	464.6	510.8	581.0	667.5	758.8	829.0	812.2	710.0	603.0	527.0
62.5°	393.7	421.8	465.4	526.8	605.8	690.4	748.1	723.4	623.2	529.6	469.5
65°	335.6	359.2	396.5	448.9	514.4	584.2	628.7	596.7	511.3	438.4	390.1
67.5°	280.1	299.0	330.2	372.1	428.0	484.0	511.2	479.0	410.6	357.4	321.6
70°	244.9	261.7	285.8	323.1	371.8	419.0	439.4	410.6	351.8	306.2	280.5
72.5°	209.6	223.5	244.7	278.1	317.2	358.2	376.1	348.5	300.2	261.8	237.7
75°	162.1	171.5	186.1	209.2	240.1	272.7	282.7	258.5	227.6	198.7	183.0
77.5°	116.0	124.0	135.1	149.7	171.6	192.3	201.0	187.0	163.1	144.8	131.9
80°	89.2	93.3	102.8	114.8	132.2	145.2	151.0	142.1	125.3	111.7	101.7
82.5°	63.5	67.8	73.4	83.4	94.4	103.3	109.5	103.5	91.4	80.7	74.8
85°	30.9	33.5	36.7	40.9	49.3	54.5	54.0	50.3	45.6	41.4	38.3
87.5°	11.5	12.2	13.8	16.4	17.9	19.9	21.1	20.5	19.2	18.2	17.1
90°	2.8	4.5	6.4	8.2	9.9	11.4	13.0	14.5	16.2	17.3	18.4
92.5°	14.2	13.0	11.7	10.5	10.6	11.9	13.3	14.7	16.2	17.3	18.4
95°	56.8	56.1	55.4	54.8	50.2	41.7	33.1	24.6	16.2	17.3	18.4
97.5°	121.2	122.4	123.6	124.8	117.0	100.2	83.3	66.4	49.6	43.3	37.0
100°	169.1	169.8	170.4	171.1	171.9	172.8	173.7	174.5	175.4	142.1	108.7
102.5°	218.4	219.3	220.2	221.0	221.7	222.3	222.8	223.3	223.9	217.5	211.2
105°	297.3	298.2	299.1	300.0	300.4	300.4	300.4	300.4	300.4	300.4	300.4
107.5°	378.3	378.3	378.3	378.3	378.5	379.0	379.4	379.9	380.3	380.4	380.4
110°	431.5	431.5	431.5	431.5	431.8	432.2	432.7	433.1	433.5	432.9	432.2



TEST NUMBER: P333232-840

CATALOG NUMBER: S125DIP-S850D1035U840-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	275°	280°	285°	290°	295°	300°	305°	310°	315°	320°	325°
112.5°	482.1	482.6	483.2	483.7	484.1	484.4	484.6	484.9	485.2	484.3	483.5
115°	557.7	558.9	560.0	561.1	561.8	562.0	562.2	562.4	562.6	561.8	560.9
117.5°	634.2	634.1	634.1	634.1	634.5	635.3	636.1	637.0	637.8	636.7	635.5
120°	682.4	682.2	682.0	681.8	682.0	682.7	683.3	684.0	684.7	684.2	683.8
122.5°	726.2	727.1	727.9	728.8	729.3	729.7	730.0	730.3	730.6	730.1	729.7
125°	793.0	794.7	796.3	797.8	798.6	798.6	798.6	798.6	798.6	797.7	796.8
127.5°	855.8	856.9	858.0	859.1	859.6	859.5	859.4	859.2	859.1	858.6	858.1
130°	894.5	895.6	896.8	897.9	898.5	898.8	899.0	899.2	899.4	898.8	898.1
132.5°	933.4	934.7	935.9	937.3	937.7	937.2	936.8	936.2	935.7	935.5	935.4
135°	988.5	989.9	991.2	992.5	993.0	992.5	992.1	991.6	991.2	990.7	990.3
137.5°	1038.9	1040.1	1041.3	1042.4	1042.8	1042.4	1042.0	1041.6	1041.2	1041.3	1041.4
140°	1071.3	1071.8	1072.2	1072.6	1072.8	1072.5	1072.3	1072.1	1071.9	1072.3	1072.8
142.5°	1101.0	1101.3	1101.5	1101.8	1102.1	1102.4	1102.7	1103.0	1103.3	1103.4	1103.5
145°	1144.9	1145.3	1145.8	1146.2	1146.5	1146.5	1146.5	1146.5	1146.5	1146.7	1146.9
147.5°	1182.7	1182.6	1182.5	1182.3	1182.5	1182.8	1183.1	1183.3	1183.6	1183.9	1184.1
150°	1206.5	1206.1	1205.6	1205.2	1205.2	1205.6	1206.1	1206.5	1207.0	1207.4	1207.9
152.5°	1229.4	1228.4	1227.4	1226.4	1226.2	1226.6	1227.0	1227.5	1227.9	1228.4	1228.8
155°	1259.1	1257.7	1256.4	1255.1	1254.6	1255.1	1255.5	1255.9	1256.4	1257.1	1257.7
157.5°	1282.7	1282.0	1281.2	1280.4	1280.0	1280.0	1280.1	1280.1	1280.2	1280.9	1281.6
160°	1298.4	1297.1	1295.7	1294.3	1293.7	1294.0	1294.2	1294.4	1294.6	1295.6	1296.5
162.5°	1311.3	1309.9	1308.6	1307.3	1306.7	1306.9	1307.2	1307.4	1307.6	1308.9	1310.1
165°	1328.6	1327.3	1326.0	1324.6	1324.0	1324.2	1324.4	1324.7	1324.9	1326.3	1327.6
167.5°	1341.5	1340.1	1338.7	1337.4	1336.8	1337.0	1337.2	1337.4	1337.7	1339.3	1340.9
170°	1348.6	1347.0	1345.4	1343.8	1343.2	1343.4	1343.6	1343.8	1344.1	1345.8	1347.7
172.5°	1353.4	1351.8	1350.3	1348.7	1348.2	1348.5	1348.9	1349.3	1349.7	1351.3	1352.9
175°	1358.9	1357.6	1356.1	1354.8	1354.3	1354.5	1354.7	1354.9	1355.1	1357.0	1358.8
177.5°	1361.6	1360.5	1359.4	1358.4	1357.9	1358.1	1358.3	1358.5	1358.6	1359.9	1361.1
180°	1360.2	1360.2	1360.2	1360.2	1360.2	1360.2	1360.2	1360.2	1360.2	1360.2	1360.2



TEST NUMBER: P333232-840

CATALOG NUMBER: S125DIP-S850D1035U840-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	330°	335°	340°	345°	350°	355°	360°
0°	1235.5	1235.5	1235.5	1235.5	1235.5	1235.5	1235.5
2.5°	1292.0	1295.5	1302.5	1300.0	1303.4	1305.0	1306.8
5°	1396.4	1413.2	1420.6	1419.5	1430.5	1427.8	1425.2
7.5°	1514.3	1532.0	1541.8	1554.1	1561.2	1561.7	1567.9
10°	1581.0	1604.1	1613.6	1626.6	1635.0	1639.7	1639.2
12.5°	1632.1	1650.2	1671.4	1677.8	1689.1	1695.1	1692.9
15°	1693.7	1722.6	1744.6	1755.7	1769.8	1773.9	1779.8
17.5°	1748.7	1787.4	1813.1	1847.2	1860.2	1868.0	1863.4
20°	1790.2	1841.1	1866.8	1907.7	1930.3	1942.3	1938.1
22.5°	1839.3	1894.4	1941.9	1977.3	2011.7	2027.9	2031.2
25°	1923.4	1998.9	2068.7	2115.4	2157.8	2167.8	2189.8
27.5°	2017.4	2106.5	2181.0	2230.1	2259.7	2270.8	2277.6
30°	2076.6	2165.2	2221.3	2252.7	2262.2	2261.1	2260.1
32.5°	2105.5	2161.0	2171.7	2162.9	2141.3	2123.1	2104.1
35°	2064.5	2023.1	1961.2	1881.5	1822.7	1763.5	1757.7
37.5°	1856.7	1724.2	1621.2	1506.2	1439.9	1398.9	1370.5
40°	1661.2	1510.8	1385.9	1288.9	1221.2	1194.6	1168.3
42.5°	1449.0	1305.1	1194.7	1113.6	1062.7	1033.0	1012.3
45°	1177.2	1050.4	963.8	905.0	864.7	841.6	828.5
47.5°	964.6	870.8	797.3	754.9	727.0	709.0	709.1
50°	850.5	760.8	712.1	678.5	654.4	640.3	642.9
52.5°	749.4	682.5	640.8	612.7	594.8	586.1	585.8
55°	626.6	578.3	551.1	530.7	518.6	508.7	510.8
57.5°	536.0	495.3	477.1	460.1	451.7	447.7	441.9
60°	479.8	448.4	432.6	419.0	410.6	407.5	401.6
62.5°	429.9	405.2	389.8	378.7	371.1	370.1	365.6
65°	361.3	342.4	328.8	323.6	315.7	313.6	313.6
67.5°	297.8	284.3	273.8	268.9	265.4	266.0	263.5
70°	258.0	247.0	240.1	234.9	232.3	232.8	230.8
72.5°	225.7	213.4	207.4	204.3	200.9	202.2	201.4
75°	171.0	164.6	161.5	158.3	156.2	155.2	154.2
77.5°	125.5	120.0	117.5	115.8	116.1	113.6	115.5
80°	97.0	92.3	90.7	88.1	87.6	87.6	87.1
82.5°	71.0	68.4	67.3	65.0	64.1	64.9	63.5
85°	36.7	34.6	34.1	34.1	33.0	32.0	34.6
87.5°	17.4	15.9	16.1	15.8	15.9	15.7	14.9
90°	19.5	20.6	21.5	22.2	22.8	23.5	24.2
92.5°	19.5	20.6	21.3	21.6	21.9	22.3	22.6
95°	19.5	20.6	21.2	21.2	21.2	21.2	21.2
97.5°	30.7	24.3	21.2	21.2	21.2	21.2	21.2
100°	75.3	41.9	24.7	23.8	22.9	22.1	21.2
102.5°	204.9	198.5	187.8	172.6	157.3	142.1	126.8
105°	300.4	300.4	300.3	300.1	299.9	299.7	299.4
107.5°	380.5	380.5	380.2	379.5	378.9	378.2	377.5
110°	431.5	430.9	430.7	430.9	431.1	431.3	431.5



TEST NUMBER: P333232-840

CATALOG NUMBER: S125DIP-S850D1035U840-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	330°	335°	340°	345°	350°	355°	360°
112.5°	482.6	481.8	481.2	480.9	480.6	480.3	480.0
115°	560.0	559.1	558.0	556.6	555.2	553.9	552.6
117.5°	634.4	633.2	632.3	631.8	631.2	630.6	630.0
120°	683.3	682.9	682.1	681.0	679.8	678.7	677.6
122.5°	729.3	728.8	727.9	726.7	725.4	724.1	722.8
125°	795.9	795.0	794.3	793.6	792.8	792.2	791.5
127.5°	857.6	857.1	856.1	854.3	852.7	851.1	849.4
130°	897.4	896.8	895.9	894.7	893.6	892.5	891.3
132.5°	935.3	935.1	934.5	933.4	932.3	931.2	930.1
135°	989.9	989.4	988.5	987.1	985.8	984.4	983.1
137.5°	1041.5	1041.6	1041.0	1039.9	1038.6	1037.5	1036.3
140°	1073.2	1073.6	1073.2	1071.9	1070.5	1069.1	1067.8
142.5°	1103.6	1103.7	1103.1	1101.7	1100.3	1099.0	1097.6
145°	1147.1	1147.3	1146.8	1145.5	1144.1	1142.8	1141.5
147.5°	1184.4	1184.7	1184.0	1182.3	1180.7	1179.1	1177.5
150°	1208.3	1208.7	1208.1	1206.3	1204.5	1202.6	1200.9
152.5°	1229.3	1229.7	1229.1	1227.5	1225.9	1224.3	1222.6
155°	1258.4	1259.1	1258.5	1256.7	1254.9	1253.1	1251.3
157.5°	1282.3	1283.0	1282.5	1280.7	1278.9	1277.1	1275.4
160°	1297.4	1298.3	1297.8	1296.1	1294.2	1292.4	1290.6
162.5°	1311.3	1312.6	1312.2	1310.3	1308.3	1306.4	1304.3
165°	1329.0	1330.3	1330.1	1328.3	1326.5	1324.7	1322.9
167.5°	1342.5	1344.1	1343.9	1341.9	1339.9	1337.9	1335.8
170°	1349.5	1351.3	1351.1	1349.1	1347.2	1345.1	1343.1
172.5°	1354.5	1356.1	1355.9	1353.9	1351.9	1349.9	1348.0
175°	1360.6	1362.3	1362.2	1360.2	1358.2	1356.1	1354.1
177.5°	1362.4	1363.6	1363.5	1362.1	1360.7	1359.3	1357.8
180°	1360.2	1360.2	1360.2	1360.2	1360.2	1360.2	1360.2

(END OF REPORT)