

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P331274-830

Luminaire Tested: **SA2XXDIP-C290D925U830-4F0-1E-UDD-F1**

Issue Date: 10/7/2019

Test Information

Test Method: LM-79-08
Report Number: P331274-830
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-8,
Test Lab: INNOVATION CENTER
Issue Date: 10/7/2019
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: NEO-RAY
Catalog Number: SA2XXDIP-C290D925U830-4F0-1E-UDD-F1
Description: DEFINE 2 DIRECT-INDIRECT PENDANT LED LUMINAIRE
DOWNLIGHT 290 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER
UPLIGHT 925 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER
Light Source: -
Ballast/Driver: ELECTRONIC DRIVER

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 4254.0 lumens
Efficiency: N/A
Efficacy: 114.0 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 1.16 / 1.3
Luminous Opening: Rectangular (W 0.17' x L: 4' x H: 0')
CIE Type: Semi-Indirect

Input Watts (W): 37.3
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P331274-830
CATALOG NUMBER: SA2XXDIP-C290D925U830-4F0-1E-UDD-F1

Luminous Intensity Polar Plot





TEST NUMBER: P331274-830

CATALOG NUMBER: SA2XXDIP-C290D925U830-4F0-1E-UDD-F1

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20					20					20					20					20	
RC	80					70					50					30					10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0	
RCR																						
0	102	102	102	102	91	91	91	91	70	70	70	52	52	52	35	35	35	27				27
1	93	88	85	81	82	79	76	73	62	59	58	45	44	43	31	30	29				22	
2	84	77	71	66	75	69	64	60	54	50	48	40	38	36	27	26	25				19	
3	77	68	61	55	68	61	55	50	47	43	40	35	33	30	24	22	21				16	
4	70	60	52	46	62	54	47	42	42	38	34	31	28	26	21	19	18				14	
5	64	53	45	40	57	48	41	36	38	33	29	28	25	22	19	17	16				12	
6	59	47	40	34	53	43	36	31	34	29	25	25	22	19	17	15	14				10	
7	55	43	35	30	49	38	32	27	30	26	22	23	20	17	16	14	12				9	
8	50	39	31	26	45	35	28	24	28	23	19	21	18	15	15	12	11				8	
9	47	35	28	23	42	32	25	21	25	21	17	19	16	14	13	11	10				7	
10	44	32	25	21	39	29	23	19	23	19	15	18	14	12	12	10	9				7	

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	7190	7190	7190
5°	7217	7112	7156
10°	7174	7040	7076
15°	7086	6950	6944
20°	6959	6813	6806
25°	6834	6645	6645
30°	6674	6490	6434
35°	6524	6303	6211
40°	6336	6119	6001
45°	6149	5934	5786
50°	5948	5745	5541
55°	5737	5520	5315
60°	5503	5254	5060
65°	5249	4989	4760
70°	4928	4669	4447
75°	4485	4298	4192
80°	3980	3868	3663
85°	3242	3094	2779



TEST NUMBER: P331274-830

CATALOG NUMBER: SA2XXDIP-C290D925U830-4F0-1E-UDD-F1

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	41.9	1.0
10°-20°	117.8	2.8
20°-30°	173.2	4.1
30°-40°	201.2	4.7
40°-50°	200.9	4.7
50°-60°	175.2	4.1
60°-70°	129.6	3.0
70°-80°	73.4	1.7
80°-90°	24.2	0.6
90°-100°	70.6	1.7
100°-110°	219.4	5.2
110°-120°	375.0	8.8
120°-130°	493.1	11.6
130°-140°	553.4	13.0
140°-150°	542.7	12.8
150°-160°	455.2	10.7
160°-170°	301.9	7.1
170°-180°	105.5	2.5
0°-30°	332.9	7.8
0°-40°	534.0	12.6
0°-60°	910.2	21.4
0°-90°	1137.3	26.7
90°-120°	665.0	15.6
90°-150°	2254.1	53.0
90°-180°	3117.0	73.3
0°-180°	4254.0	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	445	445	445	445	445	
5°	445	443	439	442	442	42
15°	424	421	416	417	415	119
25°	384	380	373	374	373	176
35°	331	327	320	317	315	207
45°	269	266	260	255	253	208
55°	204	201	196	191	189	182
65°	137	135	131	127	125	136
75°	72	71	69	66	67	77
85°	18	17	17	16	15	20
90°	1	13	33	31	32	3
95°	49	58	60	60	58	56
105°	202	205	207	209	209	214
115°	376	381	380	379	376	372
125°	547	555	553	550	549	489
135°	708	718	720	719	717	547
145°	860	866	872	873	869	537
155°	983	986	988	993	990	452
165°	1070	1069	1069	1074	1070	301
175°	1113	1110	1108	1114	1109	106
180°	1115	1115	1115	1115	1115	



TEST NUMBER: P331274-830

CATALOG NUMBER: SA2XXDIP-C290D925U830-4F0-1E-UDD-F1

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	445.3	445.3	445.3	445.3	445.3	445.3	445.3	445.3	445.3	445.3	445.3
2.5°	447.3	447.0	446.6	446.2	445.8	445.3	444.4	443.6	442.7	441.9	442.6
5°	445.3	444.9	444.5	444.1	443.7	443.1	442.1	441.0	439.9	438.8	439.6
7.5°	441.4	440.7	440.2	439.6	439.0	438.2	437.2	436.0	435.0	433.9	434.7
10°	437.6	437.0	436.3	435.6	434.9	434.0	432.9	431.8	430.6	429.4	430.2
12.5°	432.4	431.9	431.3	430.6	430.1	429.2	428.1	427.0	425.8	424.7	425.2
15°	423.9	423.3	422.7	422.2	421.6	420.8	419.4	418.2	417.0	415.8	416.1
17.5°	412.9	412.4	411.8	411.2	410.7	409.7	408.5	407.2	406.0	404.7	405.1
20°	405.0	404.4	403.9	403.3	402.7	401.8	400.5	399.2	397.8	396.5	396.8
22.5°	397.2	396.3	395.6	394.7	394.0	392.9	391.7	390.4	389.2	388.0	388.0
25°	383.6	382.9	382.1	381.4	380.6	379.4	377.8	376.2	374.6	373.0	373.2
27.5°	368.3	367.6	366.8	366.2	365.5	364.5	363.3	361.9	360.7	359.4	359.1
30°	358.0	357.2	356.5	355.7	354.9	353.8	352.4	351.0	349.5	348.1	347.8
32.5°	346.9	346.4	345.8	345.2	344.6	343.5	342.0	340.5	339.0	337.5	337.0
35°	331.0	330.0	329.0	328.1	327.2	325.9	324.4	322.9	321.4	319.8	319.2
37.5°	312.9	312.1	311.2	310.4	309.5	308.4	306.9	305.4	303.8	302.3	301.6
40°	300.6	299.8	299.1	298.3	297.6	296.4	294.8	293.3	291.8	290.3	289.5
42.5°	288.6	287.9	287.1	286.3	285.6	284.4	282.9	281.3	279.8	278.3	277.4
45°	269.3	268.6	268.0	267.3	266.6	265.6	264.2	262.8	261.4	259.9	258.8
47.5°	250.2	249.5	248.9	248.3	247.6	246.6	245.1	243.6	242.1	240.6	239.5
50°	236.8	236.3	235.8	235.4	234.9	233.9	232.6	231.3	230.0	228.7	227.3
52.5°	223.8	223.1	222.5	221.9	221.2	220.3	219.0	217.8	216.5	215.3	214.1
55°	203.8	203.2	202.6	202.1	201.5	200.7	199.5	198.4	197.3	196.1	194.9
57.5°	183.8	183.3	182.9	182.4	181.9	181.1	179.8	178.6	177.3	176.1	174.9
60°	170.4	170.0	169.7	169.3	168.9	168.1	166.7	165.4	164.0	162.7	161.6
62.5°	157.4	156.7	156.2	155.6	155.0	154.1	153.1	152.1	151.1	150.1	149.0
65°	137.4	136.9	136.3	135.7	135.2	134.4	133.5	132.5	131.6	130.6	129.7
67.5°	117.2	116.7	116.2	115.7	115.4	114.7	113.8	112.9	112.1	111.2	110.6
70°	104.4	104.1	103.7	103.3	102.9	102.4	101.5	100.7	99.7	98.9	98.2
72.5°	91.4	91.0	90.7	90.3	89.9	89.4	88.9	88.4	87.8	87.3	86.6
75°	71.9	71.7	71.5	71.4	71.2	70.9	70.4	69.8	69.4	68.9	68.3
77.5°	54.5	54.1	53.8	53.5	53.2	52.9	52.7	52.5	52.3	52.1	51.8
80°	42.8	42.7	42.6	42.5	42.4	42.3	42.1	41.9	41.8	41.6	41.3
82.5°	31.9	31.9	31.9	31.8	31.8	31.7	31.6	31.5	31.4	31.3	30.9
85°	17.5	17.4	17.3	17.2	17.2	17.1	17.0	16.9	16.8	16.7	16.4
87.5°	6.3	6.7	7.1	7.4	7.7	8.3	9.0	9.8	10.7	11.4	11.0
90°	0.9	3.5	5.9	8.5	10.9	14.5	19.1	23.8	28.3	32.9	32.5
92.5°	16.8	18.6	20.5	22.2	24.1	25.5	26.7	27.7	28.8	29.9	30.0
95°	48.9	51.0	53.1	55.1	57.3	58.5	58.9	59.4	59.8	60.2	60.2
97.5°	89.4	91.2	93.0	94.9	96.7	98.0	98.9	99.6	100.4	101.2	101.2
100°	119.4	121.1	122.8	124.5	126.1	127.3	127.9	128.6	129.2	129.8	129.8
102.5°	151.1	152.4	153.7	155.0	156.4	157.5	158.3	159.1	159.9	160.7	160.8
105°	202.3	202.8	203.5	204.2	204.7	205.3	205.7	206.1	206.5	206.9	207.4
107.5°	253.7	254.7	255.6	256.6	257.5	257.9	257.9	257.9	257.9	257.9	258.1
110°	286.9	288.1	289.4	290.7	291.9	292.6	292.6	292.6	292.6	292.6	292.6



TEST NUMBER: P331274-830

CATALOG NUMBER: SA2XXDIP-C290D925U830-4F0-1E-UDD-F1

CANDELA DISTRIBUTION (continued):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	323.0	324.2	325.6	326.8	328.0	328.6	328.4	328.2	328.1	327.9	327.4
115°	376.3	377.5	378.7	380.0	381.3	381.6	381.3	380.9	380.4	380.0	379.8
117.5°	429.3	430.9	432.6	434.3	436.0	436.2	435.1	433.9	432.7	431.6	431.0
120°	464.7	466.4	468.0	469.7	471.4	471.4	469.7	468.0	466.4	464.7	464.7
122.5°	497.0	499.0	501.1	503.0	505.0	505.5	504.3	503.1	502.0	500.8	500.3
125°	547.4	549.3	551.2	553.1	555.0	555.6	555.0	554.3	553.7	553.1	552.4
127.5°	596.5	598.9	601.3	603.7	606.1	606.9	606.1	605.4	604.6	603.9	603.1
130°	627.4	630.1	632.8	635.6	638.3	639.4	638.9	638.6	638.2	637.7	637.3
132.5°	662.0	664.2	666.5	668.6	670.9	672.0	672.1	672.2	672.2	672.3	671.5
135°	708.3	710.6	712.8	715.2	717.5	718.9	719.3	719.6	720.1	720.5	720.3
137.5°	757.1	758.8	760.7	762.6	764.5	765.7	766.3	766.9	767.4	767.9	767.8
140°	786.4	788.2	790.1	792.0	793.9	795.3	796.4	797.4	798.5	799.6	799.6
142.5°	816.4	818.3	820.2	822.1	824.0	825.3	826.0	826.7	827.4	828.1	828.3
145°	859.7	861.2	862.6	864.1	865.5	867.0	868.2	869.4	870.7	871.9	872.1
147.5°	898.2	900.0	901.8	903.5	905.3	906.6	907.5	908.2	909.1	909.9	910.4
150°	924.6	925.9	927.1	928.4	929.6	930.7	931.5	932.4	933.2	934.1	934.6
152.5°	947.9	949.2	950.5	951.7	953.0	954.1	955.1	956.1	957.1	958.1	958.9
155°	983.0	983.5	984.2	984.9	985.4	986.1	986.7	987.3	988.0	988.5	989.7
157.5°	1012.9	1013.2	1013.7	1014.1	1014.6	1014.9	1015.3	1015.7	1016.1	1016.4	1017.9
160°	1031.0	1031.3	1031.7	1032.2	1032.6	1032.9	1033.1	1033.3	1033.5	1033.7	1035.0
162.5°	1047.4	1047.5	1047.6	1047.7	1047.8	1047.9	1048.2	1048.4	1048.6	1048.8	1050.2
165°	1069.5	1069.3	1069.0	1068.8	1068.7	1068.6	1068.6	1068.6	1068.6	1068.6	1070.0
167.5°	1087.9	1087.3	1086.7	1086.0	1085.4	1085.1	1085.1	1085.0	1085.0	1084.9	1086.4
170°	1097.7	1097.0	1096.5	1095.8	1095.1	1094.8	1094.6	1094.4	1094.1	1093.9	1095.4
172.5°	1104.5	1103.8	1103.2	1102.6	1101.9	1101.5	1101.4	1101.1	1100.9	1100.7	1102.2
175°	1112.8	1112.1	1111.4	1110.9	1110.2	1109.7	1109.3	1108.9	1108.4	1108.1	1109.5
177.5°	1116.2	1115.6	1115.1	1114.7	1114.1	1113.7	1113.3	1113.0	1112.7	1112.4	1113.3
180°	1114.7	1114.7	1114.7	1114.7	1114.7	1114.7	1114.7	1114.7	1114.7	1114.7	1114.7



TEST NUMBER: P331274-830

CATALOG NUMBER: SA2XXDIP-C290D925U830-4F0-1E-UDD-F1

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°
0°	445.3	445.3	445.3	445.3	445.3	445.3	445.3	445.3
2.5°	443.4	444.1	444.9	445.3	445.1	444.9	444.8	444.6
5°	440.5	441.2	442.0	442.2	442.1	441.9	441.7	441.5
7.5°	435.5	436.2	437.0	437.2	437.1	436.8	436.6	436.4
10°	431.0	431.8	432.5	432.7	432.4	432.2	431.9	431.6
12.5°	425.7	426.2	426.8	427.0	426.8	426.5	426.3	426.1
15°	416.5	416.9	417.3	417.3	416.8	416.3	415.8	415.4
17.5°	405.6	406.0	406.4	406.4	406.0	405.6	405.1	404.6
20°	397.1	397.4	397.7	397.6	397.2	396.8	396.4	396.1
22.5°	388.0	388.1	388.1	388.0	387.9	387.6	387.4	387.2
25°	373.3	373.5	373.7	373.7	373.5	373.3	373.2	373.0
27.5°	358.8	358.5	358.3	357.9	357.4	356.9	356.6	356.1
30°	347.5	347.2	346.9	346.7	346.3	345.9	345.5	345.1
32.5°	336.5	335.9	335.5	335.0	334.6	334.2	333.8	333.5
35°	318.7	318.1	317.5	317.1	316.6	316.1	315.7	315.1
37.5°	300.9	300.2	299.4	298.9	298.4	297.9	297.6	297.1
40°	288.6	287.8	286.9	286.3	285.9	285.5	285.1	284.7
42.5°	276.4	275.5	274.6	273.8	273.3	272.8	272.3	271.7
45°	257.8	256.7	255.7	255.0	254.6	254.2	253.8	253.4
47.5°	238.5	237.3	236.2	235.4	234.9	234.3	233.8	233.2
50°	226.0	224.6	223.3	222.4	222.0	221.5	221.0	220.6
52.5°	213.1	212.0	210.8	210.0	209.3	208.8	208.1	207.5
55°	193.8	192.7	191.5	190.8	190.3	189.7	189.3	188.8
57.5°	173.8	172.7	171.5	170.8	170.5	170.1	169.8	169.4
60°	160.6	159.6	158.5	157.9	157.6	157.3	157.0	156.7
62.5°	148.1	147.1	146.2	145.5	145.2	144.8	144.4	144.0
65°	128.8	128.0	127.1	126.5	126.0	125.5	125.1	124.6
67.5°	109.9	109.2	108.6	108.0	107.6	107.3	106.9	106.5
70°	97.6	96.9	96.2	95.8	95.4	94.9	94.5	94.2
72.5°	86.0	85.3	84.6	84.1	83.8	83.5	83.2	82.8
75°	67.8	67.2	66.6	66.4	66.6	66.8	67.0	67.2
77.5°	51.6	51.3	51.0	50.7	50.4	50.2	50.0	49.7
80°	41.0	40.7	40.4	40.2	40.0	39.8	39.6	39.4
82.5°	30.5	30.2	29.8	29.6	29.6	29.5	29.5	29.5
85°	16.1	15.8	15.6	15.4	15.3	15.2	15.1	15.0
87.5°	10.7	10.5	10.1	10.0	9.9	9.9	9.9	9.8
90°	32.0	31.7	31.3	31.1	31.4	31.6	31.8	32.0
92.5°	30.1	30.2	30.3	30.3	30.3	30.3	30.4	30.4
95°	60.2	60.2	60.2	59.9	59.6	59.2	58.7	58.3
97.5°	101.2	101.2	101.2	101.2	101.1	101.1	101.0	101.0
100°	129.8	129.8	129.8	129.7	129.5	129.3	129.0	128.8
102.5°	161.0	161.2	161.4	161.3	161.1	160.9	160.7	160.5
105°	207.7	208.2	208.6	208.8	208.8	208.8	208.8	208.8
107.5°	258.3	258.4	258.5	258.2	257.2	256.3	255.3	254.3
110°	292.6	292.6	292.6	292.2	291.6	291.0	290.3	289.7



TEST NUMBER: P331274-830

CATALOG NUMBER: SA2XXDIP-C290D925U830-4F0-1E-UDD-F1

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°
112.5°	326.9	326.4	325.9	325.4	325.0	324.5	324.0	323.6
115°	379.6	379.4	379.2	378.7	378.1	377.5	376.8	376.3
117.5°	430.6	430.1	429.5	429.0	428.4	427.7	427.1	426.5
120°	464.7	464.7	464.7	464.4	463.7	463.1	462.5	461.8
122.5°	499.7	499.3	498.8	498.3	497.9	497.4	496.9	496.4
125°	551.9	551.2	550.5	550.2	550.0	549.7	549.5	549.3
127.5°	602.4	601.6	600.9	600.1	599.5	598.8	598.1	597.5
130°	636.9	636.5	636.0	635.5	634.6	633.8	632.9	632.1
132.5°	670.5	669.6	668.6	667.9	667.2	666.6	665.9	665.2
135°	720.1	719.9	719.6	719.3	718.6	718.0	717.4	716.7
137.5°	767.6	767.4	767.2	766.8	765.9	765.1	764.2	763.4
140°	799.6	799.6	799.6	799.1	798.2	797.4	796.6	795.8
142.5°	828.5	828.6	828.8	828.5	827.6	826.8	826.0	825.1
145°	872.3	872.6	872.8	872.5	871.7	870.8	870.0	869.1
147.5°	910.9	911.3	911.8	911.6	910.9	910.0	909.3	908.4
150°	935.3	935.9	936.5	936.5	935.9	935.3	934.6	934.1
152.5°	959.7	960.5	961.3	961.3	960.5	959.7	958.9	958.1
155°	990.7	991.7	992.8	993.0	992.3	991.7	991.1	990.4
157.5°	1019.3	1020.7	1022.1	1022.3	1021.3	1020.3	1019.3	1018.3
160°	1036.2	1037.5	1038.8	1039.0	1038.1	1037.3	1036.4	1035.6
162.5°	1051.6	1053.0	1054.4	1054.7	1053.7	1052.6	1051.7	1050.7
165°	1071.5	1072.9	1074.4	1074.6	1073.6	1072.5	1071.5	1070.4
167.5°	1087.8	1089.3	1090.7	1090.9	1089.9	1088.7	1087.7	1086.6
170°	1096.8	1098.3	1099.8	1099.9	1098.6	1097.4	1096.1	1094.9
172.5°	1103.6	1105.1	1106.5	1106.6	1105.4	1104.2	1102.9	1101.6
175°	1111.0	1112.4	1113.9	1114.0	1112.8	1111.4	1110.2	1109.0
177.5°	1114.4	1115.4	1116.3	1116.3	1115.4	1114.4	1113.3	1112.4
180°	1114.7	1114.7	1114.7	1114.7	1114.7	1114.7	1114.7	1114.7

(END OF REPORT)