

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P333238-840

Luminaire Tested: **S125DIP-S850D1035U840-4F0-1E-UDD-F**

Issue Date: 3/3/2020

Test Information

Test Method: LM-79-08
Report Number: P333238-840
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-7,
Test Lab: INNOVATION CENTER
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: NEO-RAY
Catalog Number: S125DIP-S850D1035U840-4F0-1E-UDD-F
Description: DEFINE 5 DIRECT-INDIRECT PENDANT LED LUMINAIRE
DOWNLIGHT 850 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER
UPLIGHT 1035 LUMENS PER FOOT, NO LENS
Light Source: -
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 7629.5 lumens
Efficiency: N/A
Efficacy: 146.7 lumens/watt
Spacing Criteria (0/90/45): 1.21 / 1.18 / 1.31
Luminous Opening: Rectangular (W 0.42' x L: 4' x H: 0')
CIE Type: General Diffuse


Input Watts (W): 52
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P333238-840

CATALOG NUMBER: S125DIP-S850D1035U840-4F0-1E-UDD-F

Luminous Intensity Polar Plot





TEST NUMBER: P333238-840

CATALOG NUMBER: S125DIP-S850D1035U840-4F0-1E-UDD-F

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20			
RC	80				70				50				30				10	0		
RW	70	50	30	10	70	50	30	10	50	30	10		50	30	10		50	30	10	0
RCR																				
0	106	106	106	106	97	97	97	97	81	81	81		66	66	66		52	52	52	45
1	97	92	88	85	88	85	81	78	71	68	66		58	56	54		46	45	44	38
2	88	81	74	69	80	74	69	64	62	58	55		51	48	45		40	38	37	32
3	80	71	63	58	73	65	59	54	55	50	46		45	41	38		36	33	31	27
4	73	63	55	49	67	58	51	45	48	43	39		40	36	33		32	29	27	23
5	67	56	48	42	61	51	44	39	43	38	34		36	32	28		29	26	23	20
6	62	50	42	36	57	46	39	34	39	33	29		32	28	25		26	23	21	18
7	57	45	37	32	52	42	35	30	35	30	26		29	25	22		24	21	18	16
8	53	41	33	28	49	38	31	26	32	27	23		27	23	20		22	19	16	14
9	49	37	30	25	45	35	28	23	29	24	20		25	21	18		20	17	15	13
10	46	34	27	22	42	32	25	21	27	22	18		23	19	16		19	16	13	11

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	8561	8561	8561
5°	8581	8499	8554
10°	8529	8439	8487
15°	8436	8338	8372
20°	8304	8195	8210
25°	8161	8027	8020
30°	7986	7845	7806
35°	7798	7649	7541
40°	7605	7436	7331
45°	7395	7242	7099
50°	7166	7007	6797
55°	6944	6742	6554
60°	6679	6475	6245
65°	6363	6154	5946
70°	6060	5784	5586
75°	5522	5340	5155
80°	4917	4839	4720
85°	4276	4357	4113



TEST NUMBER: P333238-840

CATALOG NUMBER: S125DIP-S850D1035U840-4F0-1E-UDD-F

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	125.0	1.6
10°-20°	353.1	4.6
20°-30°	521.3	6.8
30°-40°	608.3	8.0
40°-50°	611.0	8.0
50°-60°	536.3	7.0
60°-70°	399.6	5.2
70°-80°	228.5	3.0
80°-90°	69.3	0.9
90°-100°	49.4	0.6
100°-110°	304.6	4.0
110°-120°	552.5	7.2
120°-130°	709.1	9.3
130°-140°	762.7	10.0
140°-150°	715.9	9.4
150°-160°	579.1	7.6
160°-170°	374.5	4.9
170°-180°	129.2	1.7
0°-30°	999.4	13.1
0°-40°	1607.8	21.1
0°-60°	2755.1	36.1
0°-90°	3452.5	45.3
90°-120°	906.6	11.9
90°-150°	3094.2	40.6
90°-180°	4177.0	54.7
0°-180°	7629.5	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	1326	1326	1326	1326	1326	
5°	1324	1321	1311	1320	1319	125
15°	1262	1258	1247	1252	1252	355
25°	1145	1140	1126	1128	1125	527
35°	989	984	970	965	956	618
45°	810	805	793	781	777	624
55°	617	613	599	590	582	550
65°	416	414	403	394	389	413
75°	221	219	214	211	207	236
85°	58	59	59	58	56	64
90°	1	9	16	21	24	6
95°	58	52	16	21	21	73
105°	296	300	300	300	299	314
115°	557	561	563	559	553	552
125°	792	798	799	795	792	707
135°	987	993	991	989	983	761
145°	1144	1146	1146	1147	1142	715
155°	1260	1255	1256	1259	1251	580
165°	1330	1324	1325	1330	1323	376
175°	1360	1355	1355	1362	1354	129
180°	1360	1360	1360	1360	1360	



TEST NUMBER: P333238-840

CATALOG NUMBER: S125DIP-S850D1035U840-4F0-1E-UDD-F

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	1325.6	1325.6	1325.6	1325.6	1325.6	1325.6	1325.6	1325.6	1325.6	1325.6	1325.6
2.5°	1329.1	1328.5	1328.0	1327.4	1326.8	1325.5	1323.7	1321.9	1320.0	1318.2	1320.0
5°	1323.6	1323.1	1322.6	1322.2	1321.7	1320.3	1318.0	1315.7	1313.3	1311.0	1313.1
7.5°	1311.4	1311.0	1310.5	1310.0	1309.6	1308.1	1305.5	1302.9	1300.4	1297.8	1299.8
10°	1300.5	1300.1	1299.6	1299.1	1298.7	1297.2	1294.5	1292.0	1289.5	1286.9	1288.8
12.5°	1287.1	1286.3	1285.5	1284.5	1283.7	1282.1	1279.8	1277.4	1275.0	1272.6	1274.1
15°	1261.7	1261.0	1260.3	1259.6	1258.9	1257.3	1254.8	1252.1	1249.6	1247.0	1248.2
17.5°	1232.5	1231.5	1230.5	1229.5	1228.5	1226.6	1224.0	1221.3	1218.6	1216.0	1217.4
20°	1208.2	1207.8	1207.3	1206.8	1206.4	1204.6	1201.5	1198.5	1195.5	1192.4	1194.2
22.5°	1183.9	1183.1	1182.2	1181.3	1180.5	1178.7	1175.9	1173.0	1170.1	1167.3	1168.4
25°	1145.3	1144.2	1143.0	1141.8	1140.6	1138.5	1135.5	1132.5	1129.4	1126.4	1126.9
27.5°	1100.1	1099.5	1098.8	1098.1	1097.4	1095.5	1092.4	1089.2	1086.1	1083.0	1083.1
30°	1070.9	1070.2	1069.4	1068.7	1068.0	1065.9	1062.5	1058.9	1055.4	1052.0	1051.5
32.5°	1038.9	1037.8	1036.8	1035.7	1034.7	1032.6	1029.5	1026.3	1023.2	1020.1	1019.3
35°	989.1	988.1	987.1	986.2	985.3	983.2	980.0	976.6	973.4	970.2	969.0
37.5°	937.3	936.0	934.8	933.7	932.5	930.4	927.4	924.2	921.2	918.2	916.4
40°	902.0	900.8	899.7	898.5	897.3	895.1	891.8	888.6	885.3	882.0	880.0
42.5°	864.2	863.2	862.2	861.3	860.3	858.2	855.0	851.6	848.4	845.2	843.2
45°	809.7	808.7	807.8	806.9	806.0	804.1	801.3	798.5	795.7	792.9	790.1
47.5°	750.9	751.0	751.0	751.0	751.1	749.5	746.1	742.8	739.4	736.1	733.2
50°	713.2	712.5	711.8	711.0	710.4	708.6	705.9	703.1	700.2	697.4	694.4
52.5°	674.6	674.1	673.6	673.1	672.6	670.8	667.8	664.8	661.9	658.8	656.2
55°	616.7	616.0	615.3	614.6	613.9	611.9	608.6	605.4	602.1	598.8	596.7
57.5°	555.6	555.3	554.9	554.5	554.2	552.6	549.9	547.1	544.3	541.6	538.9
60°	517.1	516.1	515.2	514.2	513.3	511.6	509.0	506.4	503.9	501.3	499.0
62.5°	476.8	476.1	475.3	474.5	473.8	472.3	470.2	468.0	465.7	463.5	461.1
65°	416.4	415.9	415.5	415.0	414.5	413.0	410.4	407.9	405.3	402.7	400.6
67.5°	357.9	356.9	355.9	354.9	354.0	352.4	350.6	348.7	346.8	344.9	343.1
70°	320.9	319.7	318.6	317.4	316.3	314.7	312.6	310.4	308.3	306.3	304.9
72.5°	280.6	279.8	279.0	278.3	277.5	276.4	275.1	273.7	272.4	271.0	269.4
75°	221.3	220.9	220.4	219.9	219.4	218.6	217.4	216.3	215.1	214.0	213.3
77.5°	166.5	166.3	166.2	166.0	165.8	165.4	164.7	164.1	163.4	162.8	162.4
80°	132.2	132.2	132.2	132.2	132.2	131.9	131.5	131.0	130.5	130.1	129.9
82.5°	101.9	101.6	101.2	100.8	100.5	100.2	100.1	100.1	100.0	99.9	99.5
85°	57.7	58.0	58.2	58.4	58.6	58.8	58.8	58.8	58.8	58.8	58.5
87.5°	22.8	23.2	23.5	23.9	24.3	24.5	24.6	24.7	24.9	25.0	25.2
90°	1.0	2.8	4.5	6.4	8.2	9.9	11.4	13.0	14.5	16.2	17.3
92.5°	15.6	14.2	13.0	11.7	10.5	10.6	11.9	13.3	14.7	16.2	17.3
95°	57.5	56.8	56.1	55.4	54.8	50.2	41.7	33.1	24.6	16.2	17.3
97.5°	120.0	121.2	122.4	123.6	124.8	117.0	100.2	83.3	66.4	49.6	43.3
100°	168.3	169.1	169.8	170.4	171.1	171.9	172.8	173.7	174.5	175.4	142.1
102.5°	217.6	218.4	219.3	220.2	221.0	221.7	222.3	222.8	223.3	223.9	217.5
105°	296.4	297.3	298.2	299.1	300.0	300.4	300.4	300.4	300.4	300.4	300.4
107.5°	378.3	378.3	378.3	378.3	378.3	378.5	379.0	379.4	379.9	380.3	380.4
110°	431.5	431.5	431.5	431.5	431.5	431.8	432.2	432.7	433.1	433.5	432.9



TEST NUMBER: P333238-840

CATALOG NUMBER: S125DIP-S850D1035U840-4F0-1E-UDD-F

CANDELA DISTRIBUTION (continued):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	481.6	482.1	482.6	483.2	483.7	484.1	484.4	484.6	484.9	485.2	484.3
115°	556.6	557.7	558.9	560.0	561.1	561.8	562.0	562.2	562.4	562.6	561.8
117.5°	634.2	634.2	634.1	634.1	634.1	634.5	635.3	636.1	637.0	637.8	636.7
120°	682.7	682.4	682.2	682.0	681.8	682.0	682.7	683.3	684.0	684.7	684.2
122.5°	725.4	726.2	727.1	727.9	728.8	729.3	729.7	730.0	730.3	730.6	730.1
125°	791.5	793.0	794.7	796.3	797.8	798.6	798.6	798.6	798.6	798.6	797.7
127.5°	854.6	855.8	856.9	858.0	859.1	859.6	859.5	859.4	859.2	859.1	858.6
130°	893.3	894.5	895.6	896.8	897.9	898.5	898.8	899.0	899.2	899.4	898.8
132.5°	932.1	933.4	934.7	935.9	937.3	937.7	937.2	936.8	936.2	935.7	935.5
135°	987.1	988.5	989.9	991.2	992.5	993.0	992.5	992.1	991.6	991.2	990.7
137.5°	1037.7	1038.9	1040.1	1041.3	1042.4	1042.8	1042.4	1042.0	1041.6	1041.2	1041.3
140°	1070.9	1071.3	1071.8	1072.2	1072.6	1072.8	1072.5	1072.3	1072.1	1071.9	1072.3
142.5°	1100.7	1101.0	1101.3	1101.5	1101.8	1102.1	1102.4	1102.7	1103.0	1103.3	1103.4
145°	1144.5	1144.9	1145.3	1145.8	1146.2	1146.5	1146.5	1146.5	1146.5	1146.5	1146.7
147.5°	1182.8	1182.7	1182.6	1182.5	1182.3	1182.5	1182.8	1183.1	1183.3	1183.6	1183.9
150°	1207.0	1206.5	1206.1	1205.6	1205.2	1205.2	1205.6	1206.1	1206.5	1207.0	1207.4
152.5°	1230.3	1229.4	1228.4	1227.4	1226.4	1226.2	1226.6	1227.0	1227.5	1227.9	1228.4
155°	1260.4	1259.1	1257.7	1256.4	1255.1	1254.6	1255.1	1255.5	1255.9	1256.4	1257.1
157.5°	1283.5	1282.7	1282.0	1281.2	1280.4	1280.0	1280.0	1280.1	1280.1	1280.2	1280.9
160°	1299.7	1298.4	1297.1	1295.7	1294.3	1293.7	1294.0	1294.2	1294.4	1294.6	1295.6
162.5°	1312.6	1311.3	1309.9	1308.6	1307.3	1306.7	1306.9	1307.2	1307.4	1307.6	1308.9
165°	1330.0	1328.6	1327.3	1326.0	1324.6	1324.0	1324.2	1324.4	1324.7	1324.9	1326.3
167.5°	1342.9	1341.5	1340.1	1338.7	1337.4	1336.8	1337.0	1337.2	1337.4	1337.7	1339.3
170°	1350.1	1348.6	1347.0	1345.4	1343.8	1343.2	1343.4	1343.6	1343.8	1344.1	1345.8
172.5°	1354.9	1353.4	1351.8	1350.3	1348.7	1348.2	1348.5	1348.9	1349.3	1349.7	1351.3
175°	1360.2	1358.9	1357.6	1356.1	1354.8	1354.3	1354.5	1354.7	1354.9	1355.1	1357.0
177.5°	1362.6	1361.6	1360.5	1359.4	1358.4	1357.9	1358.1	1358.3	1358.5	1358.6	1359.9
180°	1360.2	1360.2	1360.2	1360.2	1360.2	1360.2	1360.2	1360.2	1360.2	1360.2	1360.2



TEST NUMBER: P333238-840

CATALOG NUMBER: S125DIP-S850D1035U840-4F0-1E-UDD-F

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°
0°	1325.6	1325.6	1325.6	1325.6	1325.6	1325.6	1325.6	1325.6
2.5°	1321.9	1323.7	1325.5	1326.5	1326.3	1326.1	1325.9	1325.6
5°	1315.2	1317.3	1319.4	1320.3	1320.1	1319.9	1319.6	1319.4
7.5°	1301.9	1303.9	1306.0	1306.9	1306.7	1306.5	1306.2	1306.0
10°	1290.6	1292.5	1294.3	1295.2	1294.9	1294.6	1294.4	1294.2
12.5°	1275.6	1277.1	1278.6	1279.3	1279.3	1279.2	1279.2	1279.1
15°	1249.4	1250.5	1251.7	1252.2	1252.2	1252.2	1252.2	1252.2
17.5°	1218.9	1220.3	1221.7	1221.9	1220.7	1219.6	1218.4	1217.3
20°	1195.8	1197.4	1199.0	1199.2	1198.1	1196.9	1195.8	1194.6
22.5°	1169.4	1170.5	1171.6	1171.7	1170.9	1170.1	1169.3	1168.6
25°	1127.3	1127.8	1128.3	1128.1	1127.5	1126.8	1126.1	1125.4
27.5°	1083.2	1083.3	1083.4	1083.1	1082.4	1081.7	1081.0	1080.3
30°	1051.1	1050.6	1050.1	1049.6	1048.8	1048.1	1047.4	1046.7
32.5°	1018.3	1017.5	1016.7	1015.6	1014.4	1013.1	1011.9	1010.7
35°	967.9	966.6	965.5	964.0	962.1	960.3	958.4	956.5
37.5°	914.6	912.9	911.2	909.8	908.8	907.7	906.7	905.5
40°	877.9	875.8	873.6	872.2	871.5	870.9	870.2	869.5
42.5°	841.3	839.4	837.5	836.0	835.0	833.8	832.7	831.7
45°	787.3	784.5	781.7	779.9	779.3	778.6	777.9	777.2
47.5°	730.3	727.5	724.7	722.5	720.8	719.2	717.5	715.9
50°	691.4	688.3	685.3	683.0	681.4	679.7	678.1	676.5
52.5°	653.6	650.9	648.2	646.0	644.2	642.4	640.6	638.7
55°	594.7	592.6	590.5	588.7	586.9	585.3	583.7	582.1
57.5°	536.2	533.5	530.8	529.0	528.1	527.3	526.3	525.4
60°	496.7	494.3	492.0	490.0	488.4	486.8	485.1	483.5
62.5°	458.6	456.1	453.5	451.6	450.4	449.1	447.9	446.6
65°	398.6	396.5	394.4	392.8	391.9	391.0	390.0	389.1
67.5°	341.3	339.5	337.8	336.6	336.1	335.5	334.9	334.4
70°	303.5	302.1	300.6	299.5	298.5	297.6	296.7	295.8
72.5°	267.8	266.3	264.7	263.4	262.5	261.6	260.6	259.6
75°	212.6	211.9	211.2	210.4	209.4	208.4	207.5	206.6
77.5°	162.0	161.5	161.1	160.6	159.9	159.3	158.6	157.9
80°	129.6	129.4	129.2	128.8	128.4	127.8	127.3	126.9
82.5°	99.0	98.6	98.2	98.0	97.9	97.8	97.7	97.6
85°	58.3	58.1	57.8	57.5	57.0	56.6	56.0	55.5
87.5°	25.4	25.8	26.0	26.0	25.7	25.4	25.2	24.9
90°	18.4	19.5	20.6	21.5	22.2	22.8	23.5	24.2
92.5°	18.4	19.5	20.6	21.3	21.6	21.9	22.3	22.6
95°	18.4	19.5	20.6	21.2	21.2	21.2	21.2	21.2
97.5°	37.0	30.7	24.3	21.2	21.2	21.2	21.2	21.2
100°	108.7	75.3	41.9	24.7	23.8	22.9	22.1	21.2
102.5°	211.2	204.9	198.5	187.8	172.6	157.3	142.1	126.8
105°	300.4	300.4	300.4	300.3	300.1	299.9	299.7	299.4
107.5°	380.4	380.5	380.5	380.2	379.5	378.9	378.2	377.5
110°	432.2	431.5	430.9	430.7	430.9	431.1	431.3	431.5



TEST NUMBER: P333238-840

CATALOG NUMBER: S125DIP-S850D1035U840-4F0-1E-UDD-F

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°
112.5°	483.5	482.6	481.8	481.2	480.9	480.6	480.3	480.0
115°	560.9	560.0	559.1	558.0	556.6	555.2	553.9	552.6
117.5°	635.5	634.4	633.2	632.3	631.8	631.2	630.6	630.0
120°	683.8	683.3	682.9	682.1	681.0	679.8	678.7	677.6
122.5°	729.7	729.3	728.8	727.9	726.7	725.4	724.1	722.8
125°	796.8	795.9	795.0	794.3	793.6	792.8	792.2	791.5
127.5°	858.1	857.6	857.1	856.1	854.3	852.7	851.1	849.4
130°	898.1	897.4	896.8	895.9	894.7	893.6	892.5	891.3
132.5°	935.4	935.3	935.1	934.5	933.4	932.3	931.2	930.1
135°	990.3	989.9	989.4	988.5	987.1	985.8	984.4	983.1
137.5°	1041.4	1041.5	1041.6	1041.0	1039.9	1038.6	1037.5	1036.3
140°	1072.8	1073.2	1073.6	1073.2	1071.9	1070.5	1069.1	1067.8
142.5°	1103.5	1103.6	1103.7	1103.1	1101.7	1100.3	1099.0	1097.6
145°	1146.9	1147.1	1147.3	1146.8	1145.5	1144.1	1142.8	1141.5
147.5°	1184.1	1184.4	1184.7	1184.0	1182.3	1180.7	1179.1	1177.5
150°	1207.9	1208.3	1208.7	1208.1	1206.3	1204.5	1202.6	1200.9
152.5°	1228.8	1229.3	1229.7	1229.1	1227.5	1225.9	1224.3	1222.6
155°	1257.7	1258.4	1259.1	1258.5	1256.7	1254.9	1253.1	1251.3
157.5°	1281.6	1282.3	1283.0	1282.5	1280.7	1278.9	1277.1	1275.4
160°	1296.5	1297.4	1298.3	1297.8	1296.1	1294.2	1292.4	1290.6
162.5°	1310.1	1311.3	1312.6	1312.2	1310.3	1308.3	1306.4	1304.3
165°	1327.6	1329.0	1330.3	1330.1	1328.3	1326.5	1324.7	1322.9
167.5°	1340.9	1342.5	1344.1	1343.9	1341.9	1339.9	1337.9	1335.8
170°	1347.7	1349.5	1351.3	1351.1	1349.1	1347.2	1345.1	1343.1
172.5°	1352.9	1354.5	1356.1	1355.9	1353.9	1351.9	1349.9	1348.0
175°	1358.8	1360.6	1362.3	1362.2	1360.2	1358.2	1356.1	1354.1
177.5°	1361.1	1362.4	1363.6	1363.5	1362.1	1360.7	1359.3	1357.8
180°	1360.2	1360.2	1360.2	1360.2	1360.2	1360.2	1360.2	1360.2

(END OF REPORT)