

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P333243-840

Luminaire Tested: **S125DIP-S850D1205U840-4F0-1E-UDD-A4**

Issue Date: 3/3/2020

Test Information

Test Method: LM-79-08
Report Number: P333243-840
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-19,
Test Lab: INNOVATION CENTER
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: NEO-RAY
Catalog Number: S125DIP-S850D1205U840-4F0-1E-UDD-A4
Description: DEFINE 5 DIRECT-INDIRECT PENDANT LED LUMINAIRE
DOWNLIGHT 850 LUMENS PER FOOT, ASYMMETRIC DIFFUSER
UPLIGHT 1205 LUMENS PER FOOT, BATWING OPTIC
Light Source: -
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 7854.0 lumens
Efficiency: N/A
Efficacy: 138.0 lumens/watt
Spacing Criteria (0/90/45): 1.43 / 1.23 / 1.52
Luminous Opening: Rectangular (W 4' x L: 0.42' x H: 0')
CIE Type: General Diffuse


Input Watts (W): 56.9
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P333243-840

CATALOG NUMBER: S125DIP-S850D1205U840-4F0-1E-UDD-A4

Luminous Intensity Polar Plot





TEST NUMBER: P333243-840

CATALOG NUMBER: S125DIP-S850D1205U840-4F0-1E-UDD-A4

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	106	106	106	106	97	97	97	97	80	80	80	65	65	65	51	51	51	44
1	97	93	89	85	88	85	82	79	71	68	66	57	56	55	45	44	43	38
2	88	81	75	70	81	74	69	65	62	58	55	51	48	46	40	38	37	32
3	81	71	64	58	74	66	59	54	55	50	47	45	42	39	36	33	32	27
4	74	63	55	50	67	58	51	46	49	44	40	40	36	33	32	29	27	24
5	68	56	48	42	62	52	45	40	44	38	34	36	32	29	29	26	24	20
6	62	50	42	37	57	47	40	34	39	34	30	33	28	25	26	23	21	18
7	58	46	38	32	53	42	35	30	36	30	26	30	25	22	24	21	19	16
8	53	41	34	28	49	38	31	27	32	27	23	27	23	20	22	19	17	14
9	50	38	30	25	46	35	28	24	30	24	21	25	21	18	20	17	15	13
10	46	34	27	23	43	32	26	21	27	22	19	23	19	16	19	16	14	12

AVERAGE LUMINANCE (cd/sqm):

	0°	90°	180°	270°
0°	7979	7979	7979	7979
5°	9240	8006	7010	8006
10°	10750	7965	6142	7965
15°	11900	7906	5666	7906
20°	13320	7813	5283	7813
25°	15605	7709	5097	7709
30°	16855	7607	4935	7607
35°	13858	7413	4829	7413
40°	9850	7144	4713	7144
45°	7567	6783	4646	6783
50°	6459	6333	4636	6333
55°	5751	5892	4677	5892
60°	5187	5412	4795	5412
65°	4792	4927	4919	4927
70°	4358	4426	4991	4426
75°	3848	3898	4946	3898
80°	3239	3176	4526	3176
85°	2564	2290	3653	2290



TEST NUMBER: P333243-840

CATALOG NUMBER: S125DIP-S850D1205U840-4F0-1E-UDD-A4

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	118.9	1.5
10°-20°	354.1	4.5
20°-30°	575.0	7.3
30°-40°	701.4	8.9
40°-50°	638.1	8.1
50°-60°	508.2	6.5
60°-70°	354.0	4.5
70°-80°	188.8	2.4
80°-90°	50.9	0.6
90°-100°	421.9	5.4
100°-110°	906.9	11.5
110°-120°	851.1	10.8
120°-130°	689.8	8.8
130°-140°	553.5	7.0
140°-150°	417.7	5.3
150°-160°	294.0	3.7
160°-170°	173.3	2.2
170°-180°	56.4	0.7
0°-30°	1048.1	13.3
0°-40°	1749.5	22.3
0°-60°	2895.8	36.9
0°-90°	3489.4	44.4
90°-120°	2179.9	27.8
90°-150°	3840.9	48.9
90°-180°	4365.0	55.6
0°-180°	7854.0	100.0

CANDELA DISTRIBUTION:

	0°	90°	180°	270°	360°	Flux
0°	1236	1236	1236	1236	1236	
5°	1425	1235	1081	1235	1425	144
15°	1780	1182	847	1182	1780	509
25°	2190	1082	715	1082	2190	1000
35°	1758	940	612	940	1758	1076
45°	828	743	509	743	828	663
55°	511	523	415	523	511	460
65°	314	322	322	322	314	311
75°	154	156	198	156	154	166
85°	35	31	49	31	35	41
90°	27	1	27	1	27	20
95°	276	39	276	39	276	391
105°	1555	133	1555	133	1555	1545
115°	1732	237	1732	237	1732	1692
125°	1365	328	1365	328	1365	1235
135°	1134	385	1134	385	1134	878
145°	894	448	894	448	894	568
155°	750	512	750	512	750	349
165°	657	559	657	559	657	188
175°	590	581	590	581	590	57
180°	582	582	582	582	582	



TEST NUMBER: P333243-840

CATALOG NUMBER: S125DIP-S850D1205U840-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	1235.5	1235.5	1235.5	1235.5	1235.5	1235.5	1235.5	1235.5	1235.5	1235.5	1235.5
2.5°	1306.8	1305.0	1303.4	1300.0	1302.5	1295.5	1292.0	1286.2	1279.1	1276.6	1273.6
5°	1425.2	1427.8	1430.5	1419.5	1420.6	1413.2	1396.4	1382.8	1371.8	1357.7	1347.7
7.5°	1567.9	1561.7	1561.2	1554.1	1541.8	1532.0	1514.3	1491.9	1470.2	1445.4	1424.9
10°	1639.2	1639.7	1635.0	1626.6	1613.6	1604.1	1581.0	1558.9	1532.3	1500.8	1478.2
12.5°	1692.9	1695.1	1689.1	1677.8	1671.4	1650.2	1632.1	1606.0	1574.2	1549.0	1514.7
15°	1779.8	1773.9	1769.8	1755.7	1744.6	1722.6	1693.7	1666.5	1631.8	1599.8	1567.9
17.5°	1863.4	1868.0	1860.2	1847.2	1813.1	1787.4	1748.7	1711.3	1668.3	1625.4	1587.2
20°	1938.1	1942.3	1930.3	1907.7	1866.8	1841.1	1790.2	1742.0	1692.1	1637.1	1595.2
22.5°	2031.2	2027.9	2011.7	1977.3	1941.9	1894.4	1839.3	1780.6	1718.2	1656.0	1600.2
25°	2189.8	2167.8	2157.8	2115.4	2068.7	1998.9	1923.4	1837.4	1759.8	1677.5	1606.2
27.5°	2277.6	2270.8	2259.7	2230.1	2181.0	2106.5	2017.4	1912.6	1803.1	1699.2	1605.9
30°	2260.1	2261.1	2262.2	2252.7	2221.3	2165.2	2076.6	1963.8	1833.7	1716.8	1608.8
32.5°	2104.1	2123.1	2141.3	2162.9	2171.7	2161.0	2105.5	2003.7	1869.9	1737.0	1607.1
35°	1757.7	1763.5	1822.7	1881.5	1961.2	2023.1	2064.5	2019.4	1906.6	1754.0	1605.1
37.5°	1370.5	1398.9	1439.9	1506.2	1621.2	1724.2	1856.7	1917.6	1881.3	1759.6	1601.4
40°	1168.3	1194.6	1221.2	1288.9	1385.9	1510.8	1661.2	1789.7	1819.6	1742.0	1588.8
42.5°	1012.3	1033.0	1062.7	1113.6	1194.7	1305.1	1449.0	1616.9	1720.2	1690.8	1562.5
45°	828.5	841.6	864.7	905.0	963.8	1050.4	1177.2	1360.8	1520.7	1573.7	1499.8
47.5°	709.1	709.0	727.0	754.9	797.3	870.8	964.6	1108.4	1279.3	1405.6	1399.8
50°	642.9	640.3	654.4	678.5	712.1	760.8	850.5	965.3	1129.5	1272.6	1312.5
52.5°	585.8	586.1	594.8	612.7	640.8	682.5	749.4	852.9	993.2	1140.1	1215.2
55°	510.8	508.7	518.6	530.7	551.1	578.3	626.6	705.8	819.6	964.3	1061.9
57.5°	441.9	447.7	451.7	460.1	477.1	495.3	536.0	594.1	684.4	808.6	911.7
60°	401.6	407.5	410.6	419.0	432.6	448.4	479.8	527.0	603.0	710.0	812.2
62.5°	365.6	370.1	371.1	378.7	389.8	405.2	429.9	469.5	529.6	623.2	723.4
65°	313.6	313.6	315.7	323.6	328.8	342.4	361.3	390.1	438.4	511.3	596.7
67.5°	263.5	266.0	265.4	268.9	273.8	284.3	297.8	321.6	357.4	410.6	479.0
70°	230.8	232.8	232.3	234.9	240.1	247.0	258.0	280.5	306.2	351.8	410.6
72.5°	201.4	202.2	200.9	204.3	207.4	213.4	225.7	237.7	261.8	300.2	348.5
75°	154.2	155.2	156.2	158.3	161.5	164.6	171.0	183.0	198.7	227.6	258.5
77.5°	115.5	113.6	116.1	115.8	117.5	120.0	125.5	131.9	144.8	163.1	187.0
80°	87.1	87.6	87.6	88.1	90.7	92.3	97.0	101.7	111.7	125.3	142.1
82.5°	63.5	64.9	64.1	65.0	67.3	68.4	71.0	74.8	80.7	91.4	103.5
85°	34.6	32.0	33.0	34.1	34.1	34.6	36.7	38.3	41.4	45.6	50.3
87.5°	15.5	16.3	16.5	16.5	16.9	16.5	17.9	17.7	18.7	19.7	20.9
90°	27.0	27.0	25.9	25.9	25.9	23.4	22.3	21.1	20.0	18.8	16.5
92.5°	74.8	76.7	78.4	81.2	96.2	113.6	150.9	207.9	306.3	378.3	384.5
95°	275.8	294.6	303.9	339.1	422.4	521.0	665.3	843.6	1017.3	1039.7	848.4
97.5°	666.5	681.6	715.6	781.2	853.7	990.9	1131.5	1256.5	1287.3	1110.2	757.6
100°	915.2	934.0	977.4	1062.0	1142.9	1265.0	1385.8	1443.3	1352.9	1059.6	675.9
102.5°	1193.2	1207.2	1254.4	1314.4	1401.1	1483.7	1541.7	1506.2	1313.5	970.4	613.9
105°	1554.8	1568.8	1592.4	1631.0	1668.6	1681.5	1629.9	1469.2	1187.5	850.7	553.8
107.5°	1746.8	1756.2	1763.9	1764.1	1745.1	1683.8	1551.3	1336.8	1058.9	768.3	528.5
110°	1810.6	1810.6	1802.4	1780.1	1727.3	1627.5	1462.1	1239.1	985.6	729.8	521.0



TEST NUMBER: P333243-840

CATALOG NUMBER: S125DIP-S850D1205U840-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	1803.1	1794.6	1774.2	1736.0	1658.7	1541.2	1373.8	1162.2	931.2	707.3	521.0
115°	1731.9	1716.7	1683.8	1627.5	1536.0	1408.1	1247.4	1065.5	871.8	683.0	524.5
117.5°	1607.3	1598.0	1565.4	1507.1	1415.6	1298.3	1159.8	1003.0	836.4	671.0	532.3
120°	1526.6	1517.2	1485.5	1429.3	1342.4	1239.1	1110.0	969.3	816.7	665.3	539.8
122.5°	1455.3	1446.8	1415.1	1363.5	1286.1	1189.4	1074.4	943.9	799.8	660.7	546.3
125°	1364.7	1352.9	1327.2	1279.0	1213.4	1128.8	1026.7	907.1	776.8	654.8	557.3
127.5°	1287.3	1282.1	1257.7	1215.2	1155.6	1076.5	981.2	869.5	755.7	652.0	569.8
130°	1245.0	1238.0	1214.5	1175.8	1117.1	1040.9	949.3	846.1	741.6	650.1	577.3
132.5°	1202.7	1194.8	1173.2	1134.5	1075.8	1002.3	919.3	822.5	730.3	650.1	585.7
135°	1133.6	1126.5	1105.4	1066.6	1015.0	948.2	873.0	792.0	717.0	650.1	597.2
137.5°	1059.6	1051.9	1032.4	997.1	951.0	894.1	831.7	766.3	705.0	651.5	607.8
140°	1007.9	1002.1	984.5	954.0	910.6	861.3	807.3	752.1	699.3	652.4	612.5
142.5°	960.1	955.1	938.5	912.7	875.9	833.1	786.7	739.9	694.7	653.4	615.3
145°	894.1	889.5	876.6	856.6	828.4	796.8	760.3	724.0	687.6	652.4	618.4
147.5°	838.3	836.2	828.7	812.7	790.4	766.5	738.5	709.0	680.3	649.3	619.6
150°	807.3	806.2	801.4	787.4	769.7	748.6	726.4	700.5	674.7	646.5	619.6
152.5°	782.9	781.7	777.0	765.8	751.0	734.6	714.2	691.2	668.1	642.8	618.6
155°	749.8	748.6	745.1	736.9	725.2	712.3	695.8	677.0	657.1	636.0	616.0
157.5°	720.2	720.4	717.2	710.3	701.3	691.2	678.4	663.0	646.8	628.9	613.0
160°	700.5	701.8	699.3	693.5	685.3	677.0	665.3	653.6	638.3	624.3	610.2
162.5°	682.7	683.0	682.5	677.5	671.2	663.9	654.1	643.3	630.9	618.6	607.3
165°	657.1	657.1	657.1	654.8	650.1	644.2	637.1	628.9	619.6	610.2	603.1
167.5°	633.7	633.9	634.8	632.7	630.4	626.1	620.8	615.3	608.5	602.0	596.5
170°	619.6	620.8	620.8	619.6	617.2	614.9	611.4	607.8	602.0	597.2	593.8
172.5°	606.4	607.6	609.5	607.3	606.9	605.5	602.9	599.4	595.4	591.7	590.0
175°	590.3	591.4	593.8	592.6	592.6	592.6	590.3	590.3	586.7	585.5	585.5
177.5°	582.0	582.0	584.8	583.9	584.8	584.8	584.8	583.9	583.0	582.0	582.0
180°	582.0	582.0	582.0	582.0	582.0	582.0	582.0	582.0	582.0	582.0	582.0



TEST NUMBER: P333243-840

CATALOG NUMBER: S125DIP-S850D1205U840-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°	95°	100°	105°
0°	1235.5	1235.5	1235.5	1235.5	1235.5	1235.5	1235.5	1235.5	1235.5	1235.5	1235.5
2.5°	1271.1	1268.2	1264.8	1258.9	1251.8	1248.0	1242.1	1238.4	1230.8	1224.6	1217.8
5°	1335.5	1321.9	1309.4	1293.1	1275.3	1263.7	1250.1	1234.9	1219.2	1203.0	1185.1
7.5°	1402.4	1378.3	1352.0	1323.8	1296.3	1270.9	1246.7	1222.8	1200.6	1173.8	1151.0
10°	1447.2	1416.8	1384.3	1346.0	1308.9	1276.4	1243.3	1214.5	1185.1	1153.7	1125.8
12.5°	1492.2	1451.7	1405.7	1363.7	1318.9	1279.7	1240.8	1204.0	1167.1	1132.3	1099.8
15°	1523.9	1488.1	1445.7	1385.9	1335.5	1281.6	1230.2	1182.5	1137.9	1099.1	1058.2
17.5°	1544.7	1498.7	1453.2	1395.8	1329.8	1269.4	1211.2	1156.6	1106.3	1057.1	1017.7
20°	1548.5	1501.3	1453.6	1397.5	1329.8	1260.6	1202.4	1136.8	1082.9	1032.0	983.7
22.5°	1547.2	1493.8	1441.8	1384.0	1318.1	1254.4	1184.0	1117.1	1058.5	1008.5	958.2
25°	1535.4	1478.2	1413.2	1355.0	1290.0	1222.3	1151.0	1081.8	1022.0	964.8	915.0
27.5°	1525.5	1451.4	1377.8	1309.9	1247.1	1185.1	1116.8	1045.9	979.7	921.7	874.7
30°	1513.4	1432.1	1349.2	1278.4	1214.0	1153.7	1089.1	1020.0	950.7	894.0	843.7
32.5°	1502.5	1407.8	1320.3	1243.2	1174.9	1116.3	1056.8	991.0	923.0	865.6	815.2
35°	1481.4	1371.8	1271.6	1184.6	1111.7	1051.4	1001.6	940.2	877.8	822.2	774.0
37.5°	1454.6	1324.5	1217.1	1125.8	1045.9	982.4	936.0	888.9	829.0	775.5	731.8
40°	1433.6	1291.0	1177.2	1083.9	1001.1	934.9	892.0	847.4	797.6	747.8	701.7
42.5°	1407.2	1260.8	1137.0	1036.5	954.4	890.1	845.0	807.1	763.2	716.7	673.9
45°	1358.7	1206.1	1071.9	963.8	880.9	817.5	770.8	742.6	709.5	665.4	629.2
47.5°	1287.3	1140.3	1001.5	890.0	804.5	745.7	702.0	674.8	651.5	618.7	585.9
50°	1223.9	1091.3	950.7	840.0	754.6	695.3	655.0	630.3	610.4	585.2	557.4
52.5°	1153.0	1029.6	900.8	791.4	706.8	648.3	608.8	587.1	570.6	552.5	525.1
55°	1040.4	935.5	816.0	712.1	634.0	576.8	542.2	523.3	509.7	496.0	479.3
57.5°	916.3	834.2	728.3	633.5	561.5	509.5	477.2	458.8	448.3	441.2	431.3
60°	829.0	758.8	667.5	581.0	510.8	464.6	433.1	419.0	410.1	404.2	397.0
62.5°	748.1	690.4	605.8	526.8	465.4	421.8	393.7	380.0	371.4	368.6	362.5
65°	628.7	584.2	514.4	448.9	396.5	359.2	335.6	322.4	317.2	314.1	314.7
67.5°	511.2	484.0	428.0	372.1	330.2	299.0	280.1	270.0	267.4	263.3	263.2
70°	439.4	419.0	371.8	323.1	285.8	261.7	244.9	234.4	231.8	229.6	229.1
72.5°	376.1	358.2	317.2	278.1	244.7	223.5	209.6	203.4	199.0	197.8	197.7
75°	282.7	272.7	240.1	209.2	186.1	171.5	162.1	156.2	153.1	152.6	153.1
77.5°	201.0	192.3	171.6	149.7	135.1	124.0	116.0	114.0	110.5	110.6	110.0
80°	151.0	145.2	132.2	114.8	102.8	93.3	89.2	85.4	84.4	82.8	84.4
82.5°	109.5	103.3	94.4	83.4	73.4	67.8	63.5	62.4	61.8	61.0	61.4
85°	54.0	54.5	49.3	40.9	36.7	33.5	30.9	30.9	30.4	29.9	30.4
87.5°	21.5	20.2	18.3	16.6	14.0	12.2	11.4	11.5	10.5	10.6	11.5
90°	15.2	12.9	11.7	9.4	7.1	4.6	2.3	1.2	2.3	4.6	7.1
92.5°	267.8	160.3	96.2	62.0	41.8	27.3	17.4	14.3	17.4	27.3	41.8
95°	524.5	266.4	140.8	88.0	62.2	49.3	39.9	38.7	39.9	49.3	62.2
97.5°	418.7	229.5	146.4	108.5	85.2	72.3	65.7	64.3	65.7	72.3	85.2
100°	380.2	227.6	159.6	124.4	102.1	89.2	84.5	82.1	84.5	89.2	102.1
102.5°	364.3	236.1	175.5	141.3	120.9	107.0	103.3	101.9	103.3	107.0	120.9
105°	357.9	253.5	201.9	169.0	150.2	138.5	132.6	132.6	132.6	138.5	150.2
107.5°	368.7	279.2	229.2	199.8	180.3	170.6	165.0	162.6	165.0	170.6	180.3
110°	379.0	298.0	249.9	219.4	201.9	191.3	186.6	184.2	186.6	191.3	201.9



TEST NUMBER: P333243-840

CATALOG NUMBER: S125DIP-S850D1205U840-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°	95°	100°	105°
112.5°	392.1	315.9	269.6	240.0	222.5	211.9	208.1	205.8	208.1	211.9	222.5
115°	411.8	343.9	300.4	271.0	253.5	242.9	239.3	237.0	239.3	242.9	253.5
117.5°	434.4	372.4	331.3	303.0	283.1	272.5	268.7	265.2	268.7	272.5	283.1
120°	449.4	393.1	352.0	322.7	302.8	292.2	287.5	284.0	287.5	292.2	302.8
122.5°	466.4	412.8	371.7	342.4	320.5	310.0	306.3	303.7	306.3	310.0	320.5
125°	489.3	438.9	400.1	369.6	347.3	336.8	330.9	328.5	330.9	336.8	347.3
127.5°	510.5	463.9	426.7	396.2	372.4	359.1	351.5	348.0	351.5	359.1	372.4
130°	524.5	479.9	443.5	413.0	388.4	373.1	363.8	360.2	363.8	373.1	388.4
132.5°	536.7	494.9	458.6	428.1	402.5	385.4	374.1	369.6	374.1	385.4	402.5
135°	553.8	515.1	478.8	447.1	422.4	403.6	389.6	384.9	389.6	403.6	422.4
137.5°	566.5	529.5	496.3	463.7	439.6	420.8	407.7	404.1	407.7	420.8	439.6
140°	575.0	539.8	505.7	474.0	451.8	433.0	418.9	415.4	418.9	433.0	451.8
142.5°	579.7	546.3	514.2	484.4	463.0	444.2	431.1	428.5	431.1	444.2	463.0
145°	586.7	557.3	526.8	499.9	478.8	462.3	450.6	448.3	450.6	462.3	478.8
147.5°	591.0	564.4	537.7	513.9	495.6	480.4	470.3	468.9	470.3	480.4	495.6
150°	593.8	569.1	543.3	523.3	507.0	491.7	483.4	481.1	483.4	491.7	507.0
152.5°	595.6	573.8	549.9	531.8	516.3	502.9	495.6	494.2	495.6	502.9	516.3
155°	597.2	578.5	558.6	542.1	530.4	518.7	511.6	511.6	511.6	518.7	530.4
157.5°	598.4	582.5	565.3	552.9	542.6	532.5	526.8	527.1	526.8	532.5	542.6
160°	598.4	584.4	569.1	558.6	549.2	541.0	536.2	537.5	536.2	541.0	549.2
162.5°	597.5	586.2	572.9	564.2	556.6	549.4	544.7	545.8	544.7	549.4	556.6
165°	596.1	586.7	577.3	570.3	565.6	559.8	556.2	558.6	556.2	559.8	565.6
167.5°	593.3	586.7	579.0	574.5	571.2	567.9	565.8	567.0	565.8	567.9	571.2
170°	591.4	586.7	580.9	577.3	575.0	572.6	571.5	572.6	571.5	572.6	575.0
172.5°	589.6	585.7	580.9	579.2	577.7	575.4	574.3	576.4	574.3	575.4	577.7
175°	586.7	584.4	580.9	580.9	580.9	579.7	578.5	580.9	578.5	579.7	580.9
177.5°	583.9	583.0	581.1	581.1	582.0	581.1	581.1	583.0	581.1	581.1	582.0
180°	582.0	582.0	582.0	582.0	582.0	582.0	582.0	582.0	582.0	582.0	582.0



TEST NUMBER: P333243-840

CATALOG NUMBER: S125DIP-S850D1205U840-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	110°	115°	120°	125°	130°	135°	140°	145°	150°	155°	160°
0°	1235.5	1235.5	1235.5	1235.5	1235.5	1235.5	1235.5	1235.5	1235.5	1235.5	1235.5
2.5°	1214.1	1209.4	1205.7	1197.3	1192.7	1186.4	1181.3	1186.8	1180.9	1183.5	1179.6
5°	1176.2	1161.5	1151.0	1135.8	1122.7	1110.6	1101.8	1100.1	1095.9	1093.9	1087.5
7.5°	1130.6	1112.3	1094.3	1074.4	1057.5	1040.5	1029.6	1020.6	1014.6	1006.7	1001.4
10°	1103.8	1079.1	1058.2	1034.1	1013.1	994.7	980.1	972.7	965.9	955.9	952.3
12.5°	1070.7	1045.2	1019.6	993.8	973.7	953.2	940.6	929.5	924.8	913.5	912.4
15°	1031.0	992.7	967.5	941.3	913.4	896.7	886.2	874.1	868.9	861.0	855.3
17.5°	983.5	949.4	917.9	890.7	866.9	852.7	839.7	831.4	822.4	817.3	807.9
20°	949.2	916.7	885.1	856.3	838.0	821.7	811.2	803.3	794.0	791.3	781.8
22.5°	920.2	884.3	854.1	829.9	809.8	791.5	780.1	774.9	768.3	760.2	758.3
25°	873.1	835.9	810.2	786.1	768.2	751.4	743.6	736.8	730.4	724.7	722.6
27.5°	832.4	799.1	768.6	746.8	731.3	716.0	709.0	700.7	696.2	691.6	685.9
30°	803.9	769.8	743.1	722.1	705.3	691.7	684.3	678.5	674.4	670.1	667.0
32.5°	774.5	743.0	717.0	696.5	679.7	669.4	662.9	658.8	654.2	649.1	645.2
35°	735.7	701.0	675.9	658.1	645.0	637.1	629.8	626.1	620.9	620.9	616.6
37.5°	692.0	662.1	639.9	623.6	611.9	604.8	596.8	594.3	591.0	588.8	587.3
40°	666.0	638.1	617.2	601.0	588.3	582.6	576.3	572.1	570.0	567.3	566.3
42.5°	639.1	612.6	592.5	577.4	566.5	561.6	555.7	552.8	548.6	545.1	544.5
45°	598.3	572.6	554.3	542.2	532.8	527.0	523.3	517.1	514.9	510.8	510.2
47.5°	559.6	534.9	516.9	507.1	498.8	494.0	488.3	482.0	479.6	477.5	477.3
50°	530.7	508.2	491.3	481.9	474.0	467.3	461.4	457.3	455.7	455.7	456.8
52.5°	501.3	482.1	467.9	456.4	448.9	441.6	436.3	433.7	431.3	433.8	435.8
55°	458.3	438.9	428.4	417.4	410.1	401.6	399.1	398.0	396.5	400.6	402.7
57.5°	412.8	399.2	386.9	376.0	369.4	364.6	361.0	360.3	363.2	365.3	372.1
60°	383.8	368.1	357.1	348.7	340.8	337.7	336.7	335.6	337.7	343.5	352.3
62.5°	351.9	339.2	327.3	321.0	315.3	310.0	309.8	310.4	314.7	321.2	330.1
65°	305.2	294.2	286.3	278.9	274.3	271.1	272.2	274.3	278.9	287.9	297.8
67.5°	257.7	250.1	243.1	237.1	232.6	232.6	233.7	236.8	242.4	252.7	261.8
70°	227.0	218.6	212.9	210.3	206.6	204.5	207.6	212.9	217.6	227.0	234.9
72.5°	196.4	189.3	184.8	183.0	181.5	179.8	180.8	186.4	192.9	202.3	211.5
75°	151.0	148.3	145.2	143.2	141.6	142.6	143.7	149.0	154.2	164.1	174.6
77.5°	110.2	107.4	105.6	105.1	104.2	104.7	107.8	111.6	116.7	124.0	131.9
80°	83.4	82.3	81.3	80.8	80.8	81.3	85.4	88.1	92.8	99.7	105.9
82.5°	60.7	60.1	59.9	59.8	60.2	60.3	62.8	66.2	70.2	75.3	80.8
85°	32.0	30.9	32.5	33.0	32.0	33.5	34.6	36.7	38.3	40.9	43.5
87.5°	12.3	13.6	13.5	14.3	14.6	16.0	15.8	17.7	18.7	19.8	19.9
90°	9.4	11.7	12.9	15.2	16.5	18.8	20.0	21.1	22.3	23.4	25.9
92.5°	62.0	96.2	160.3	267.8	384.5	378.3	306.3	207.9	150.9	113.6	96.2
95°	88.0	140.8	266.4	524.5	848.4	1039.7	1017.3	843.6	665.3	521.0	422.4
97.5°	108.5	146.4	229.5	418.7	757.6	1110.2	1287.3	1256.5	1131.5	990.9	853.7
100°	124.4	159.6	227.6	380.2	675.9	1059.6	1352.9	1443.3	1385.8	1265.0	1142.9
102.5°	141.3	175.5	236.1	364.3	613.9	970.4	1313.5	1506.2	1541.7	1483.7	1401.1
105°	169.0	201.9	253.5	357.9	553.8	850.7	1187.5	1469.2	1629.9	1681.5	1668.6
107.5°	199.8	229.2	279.2	368.7	528.5	768.3	1058.9	1336.8	1551.3	1683.8	1745.1
110°	219.4	249.9	298.0	379.0	521.0	729.8	985.6	1239.1	1462.1	1627.5	1727.3



TEST NUMBER: P333243-840

CATALOG NUMBER: S125DIP-S850D1205U840-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	110°	115°	120°	125°	130°	135°	140°	145°	150°	155°	160°
112.5°	240.0	269.6	315.9	392.1	521.0	707.3	931.2	1162.2	1373.8	1541.2	1658.7
115°	271.0	300.4	343.9	411.8	524.5	683.0	871.8	1065.5	1247.4	1408.1	1536.0
117.5°	303.0	331.3	372.4	434.4	532.3	671.0	836.4	1003.0	1159.8	1298.3	1415.6
120°	322.7	352.0	393.1	449.4	539.8	665.3	816.7	969.3	1110.0	1239.1	1342.4
122.5°	342.4	371.7	412.8	466.4	546.3	660.7	799.8	943.9	1074.4	1189.4	1286.1
125°	369.6	400.1	438.9	489.3	557.3	654.8	776.8	907.1	1026.7	1128.8	1213.4
127.5°	396.2	426.7	463.9	510.5	569.8	652.0	755.7	869.5	981.2	1076.5	1155.6
130°	413.0	443.5	479.9	524.5	577.3	650.1	741.6	846.1	949.3	1040.9	1117.1
132.5°	428.1	458.6	494.9	536.7	585.7	650.1	730.3	822.5	919.3	1002.3	1075.8
135°	447.1	478.8	515.1	553.8	597.2	650.1	717.0	792.0	873.0	948.2	1015.0
137.5°	463.7	496.3	529.5	566.5	607.8	651.5	705.0	766.3	831.7	894.1	951.0
140°	474.0	505.7	539.8	575.0	612.5	652.4	699.3	752.1	807.3	861.3	910.6
142.5°	484.4	514.2	546.3	579.7	615.3	653.4	694.7	739.9	786.7	833.1	875.9
145°	499.9	526.8	557.3	586.7	618.4	652.4	687.6	724.0	760.3	796.8	828.4
147.5°	513.9	537.7	564.4	591.0	619.6	649.3	680.3	709.0	738.5	766.5	790.4
150°	523.3	543.3	569.1	593.8	619.6	646.5	674.7	700.5	726.4	748.6	769.7
152.5°	531.8	549.9	573.8	595.6	618.6	642.8	668.1	691.2	714.2	734.6	751.0
155°	542.1	558.6	578.5	597.2	616.0	636.0	657.1	677.0	695.8	712.3	725.2
157.5°	552.9	565.3	582.5	598.4	613.0	628.9	646.8	663.0	678.4	691.2	701.3
160°	558.6	569.1	584.4	598.4	610.2	624.3	638.3	653.6	665.3	677.0	685.3
162.5°	564.2	572.9	586.2	597.5	607.3	618.6	630.9	643.3	654.1	663.9	671.2
165°	570.3	577.3	586.7	596.1	603.1	610.2	619.6	628.9	637.1	644.2	650.1
167.5°	574.5	579.0	586.7	593.3	596.5	602.0	608.5	615.3	620.8	626.1	630.4
170°	577.3	580.9	586.7	591.4	593.8	597.2	602.0	607.8	611.4	614.9	617.2
172.5°	579.2	580.9	585.7	589.6	590.0	591.7	595.4	599.4	602.9	605.5	606.9
175°	580.9	580.9	584.4	586.7	585.5	585.5	586.7	590.3	590.3	592.6	592.6
177.5°	581.1	581.1	583.0	583.9	582.0	582.0	583.0	583.9	584.8	584.8	584.8
180°	582.0	582.0	582.0	582.0	582.0	582.0	582.0	582.0	582.0	582.0	582.0



TEST NUMBER: P333243-840

CATALOG NUMBER: S125DIP-S850D1205U840-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	165°	170°	175°	180°	185°	190°	195°	200°	205°	210°	215°
0°	1235.5	1235.5	1235.5	1235.5	1235.5	1235.5	1235.5	1235.5	1235.5	1235.5	1235.5
2.5°	1177.1	1180.0	1177.5	1180.9	1177.5	1180.0	1177.1	1179.6	1183.5	1180.9	1186.8
5°	1084.9	1080.3	1083.4	1081.3	1083.4	1080.3	1084.9	1087.5	1093.9	1095.9	1100.1
7.5°	999.8	995.2	990.2	987.7	990.2	995.2	999.8	1001.4	1006.7	1014.6	1020.6
10°	946.5	940.7	940.2	936.5	940.2	940.7	946.5	952.3	955.9	965.9	972.7
12.5°	907.5	902.1	896.2	894.6	896.2	902.1	907.5	912.4	913.5	924.8	929.5
15°	852.1	847.9	844.2	847.4	844.2	847.9	852.1	855.3	861.0	868.9	874.1
17.5°	806.1	802.6	801.9	798.1	801.9	802.6	806.1	807.9	817.3	822.4	831.4
20°	777.1	774.5	775.6	768.7	775.6	774.5	777.1	781.8	791.3	794.0	803.3
22.5°	754.1	748.9	748.3	746.9	748.3	748.9	754.1	758.3	760.2	768.3	774.9
25°	717.9	715.3	712.7	715.3	712.7	715.3	717.9	722.6	724.7	730.4	736.8
27.5°	686.3	683.2	682.5	682.8	682.5	683.2	686.3	685.9	691.6	696.2	700.7
30°	667.0	661.8	662.3	661.8	662.3	661.8	667.0	667.0	670.1	674.4	678.5
32.5°	646.0	642.5	641.8	640.8	641.8	642.5	646.0	645.2	649.1	654.2	658.8
35°	615.1	615.1	612.5	612.5	612.5	615.1	615.1	616.6	620.9	620.9	626.1
37.5°	586.0	585.5	583.9	584.2	583.9	585.5	586.0	587.3	588.8	591.0	594.3
40°	564.2	563.7	562.1	559.0	562.1	563.7	564.2	566.3	567.3	570.0	572.1
42.5°	543.2	541.5	540.8	539.7	540.8	541.5	543.2	544.5	545.1	548.6	552.8
45°	510.2	510.2	509.2	508.7	509.2	510.2	510.2	510.2	510.8	514.9	517.1
47.5°	478.2	479.1	481.1	480.8	481.1	479.1	478.2	477.3	477.5	479.6	482.0
50°	458.8	459.4	460.9	461.4	460.9	459.4	458.8	456.8	455.7	455.7	457.3
52.5°	437.5	440.5	442.4	442.1	442.4	440.5	437.5	435.8	433.8	431.3	433.7
55°	407.5	411.1	414.8	415.4	414.8	411.1	407.5	402.7	400.6	396.5	398.0
57.5°	377.8	382.9	386.8	388.0	386.8	382.9	377.8	372.1	365.3	363.2	360.3
60°	357.6	364.5	369.2	371.2	369.2	364.5	357.6	352.3	343.5	337.7	335.6
62.5°	338.3	346.0	350.7	351.1	350.7	346.0	338.3	330.1	321.2	314.7	310.4
65°	306.8	314.7	318.8	321.9	318.8	314.7	306.8	297.8	287.9	278.9	274.3
67.5°	272.8	280.6	285.3	287.8	285.3	280.6	272.8	261.8	252.7	242.4	236.8
70°	248.0	255.9	262.2	264.3	262.2	255.9	248.0	234.9	227.0	217.6	212.9
72.5°	223.7	230.8	235.8	238.2	235.8	230.8	223.7	211.5	202.3	192.9	186.4
75°	181.5	190.9	195.6	198.2	195.6	190.9	181.5	174.6	164.1	154.2	149.0
77.5°	139.9	148.6	151.4	152.7	151.4	148.6	139.9	131.9	124.0	116.7	111.6
80°	112.2	117.4	121.1	121.7	121.1	117.4	112.2	105.9	99.7	92.8	88.1
82.5°	86.2	90.6	91.8	93.1	91.8	90.6	86.2	80.8	75.3	70.2	66.2
85°	47.2	49.3	49.8	49.3	49.8	49.3	47.2	43.5	40.9	38.3	36.7
87.5°	20.7	20.3	20.5	21.3	20.5	20.3	20.7	19.9	19.8	18.7	17.7
90°	25.9	25.9	27.0	27.0	27.0	25.9	25.9	25.9	23.4	22.3	21.1
92.5°	81.2	78.4	76.7	74.8	76.7	78.4	81.2	96.2	113.6	150.9	207.9
95°	339.1	303.9	294.6	275.8	294.6	303.9	339.1	422.4	521.0	665.3	843.6
97.5°	781.2	715.6	681.6	666.5	681.6	715.6	781.2	853.7	990.9	1131.5	1256.5
100°	1062.0	977.4	934.0	915.2	934.0	977.4	1062.0	1142.9	1265.0	1385.8	1443.3
102.5°	1314.4	1254.4	1207.2	1193.2	1207.2	1254.4	1314.4	1401.1	1483.7	1541.7	1506.2
105°	1631.0	1592.4	1568.8	1554.8	1568.8	1592.4	1631.0	1668.6	1681.5	1629.9	1469.2
107.5°	1764.1	1763.9	1756.2	1746.8	1756.2	1763.9	1764.1	1745.1	1683.8	1551.3	1336.8
110°	1780.1	1802.4	1810.6	1810.6	1810.6	1802.4	1780.1	1727.3	1627.5	1462.1	1239.1



TEST NUMBER: P333243-840

CATALOG NUMBER: S125DIP-S850D1205U840-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	165°	170°	175°	180°	185°	190°	195°	200°	205°	210°	215°
112.5°	1736.0	1774.2	1794.6	1803.1	1794.6	1774.2	1736.0	1658.7	1541.2	1373.8	1162.2
115°	1627.5	1683.8	1716.7	1731.9	1716.7	1683.8	1627.5	1536.0	1408.1	1247.4	1065.5
117.5°	1507.1	1565.4	1598.0	1607.3	1598.0	1565.4	1507.1	1415.6	1298.3	1159.8	1003.0
120°	1429.3	1485.5	1517.2	1526.6	1517.2	1485.5	1429.3	1342.4	1239.1	1110.0	969.3
122.5°	1363.5	1415.1	1446.8	1455.3	1446.8	1415.1	1363.5	1286.1	1189.4	1074.4	943.9
125°	1279.0	1327.2	1352.9	1364.7	1352.9	1327.2	1279.0	1213.4	1128.8	1026.7	907.1
127.5°	1215.2	1257.7	1282.1	1287.3	1282.1	1257.7	1215.2	1155.6	1076.5	981.2	869.5
130°	1175.8	1214.5	1238.0	1245.0	1238.0	1214.5	1175.8	1117.1	1040.9	949.3	846.1
132.5°	1134.5	1173.2	1194.8	1202.7	1194.8	1173.2	1134.5	1075.8	1002.3	919.3	822.5
135°	1066.6	1105.4	1126.5	1133.6	1126.5	1105.4	1066.6	1015.0	948.2	873.0	792.0
137.5°	997.1	1032.4	1051.9	1059.6	1051.9	1032.4	997.1	951.0	894.1	831.7	766.3
140°	954.0	984.5	1002.1	1007.9	1002.1	984.5	954.0	910.6	861.3	807.3	752.1
142.5°	912.7	938.5	955.1	960.1	955.1	938.5	912.7	875.9	833.1	786.7	739.9
145°	856.6	876.6	889.5	894.1	889.5	876.6	856.6	828.4	796.8	760.3	724.0
147.5°	812.7	828.7	836.2	838.3	836.2	828.7	812.7	790.4	766.5	738.5	709.0
150°	787.4	801.4	806.2	807.3	806.2	801.4	787.4	769.7	748.6	726.4	700.5
152.5°	765.8	777.0	781.7	782.9	781.7	777.0	765.8	751.0	734.6	714.2	691.2
155°	736.9	745.1	748.6	749.8	748.6	745.1	736.9	725.2	712.3	695.8	677.0
157.5°	710.3	717.2	720.4	720.2	720.4	717.2	710.3	701.3	691.2	678.4	663.0
160°	693.5	699.3	701.8	700.5	701.8	699.3	693.5	685.3	677.0	665.3	653.6
162.5°	677.5	682.5	683.0	682.7	683.0	682.5	677.5	671.2	663.9	654.1	643.3
165°	654.8	657.1	657.1	657.1	657.1	657.1	654.8	650.1	644.2	637.1	628.9
167.5°	632.7	634.8	633.9	633.7	633.9	634.8	632.7	630.4	626.1	620.8	615.3
170°	619.6	620.8	620.8	619.6	620.8	620.8	619.6	617.2	614.9	611.4	607.8
172.5°	607.3	609.5	607.6	606.4	607.6	609.5	607.3	606.9	605.5	602.9	599.4
175°	592.6	593.8	591.4	590.3	591.4	593.8	592.6	592.6	592.6	590.3	590.3
177.5°	583.9	584.8	582.0	582.0	582.0	584.8	583.9	584.8	584.8	584.8	583.9
180°	582.0	582.0	582.0	582.0	582.0	582.0	582.0	582.0	582.0	582.0	582.0



TEST NUMBER: P333243-840

CATALOG NUMBER: S125DIP-S850D1205U840-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	220°	225°	230°	235°	240°	245°	250°	255°	260°	265°	270°
0°	1235.5	1235.5	1235.5	1235.5	1235.5	1235.5	1235.5	1235.5	1235.5	1235.5	1235.5
2.5°	1181.3	1186.4	1192.7	1197.3	1205.7	1209.4	1214.1	1217.8	1224.6	1230.8	1238.4
5°	1101.8	1110.6	1122.7	1135.8	1151.0	1161.5	1176.2	1185.1	1203.0	1219.2	1234.9
7.5°	1029.6	1040.5	1057.5	1074.4	1094.3	1112.3	1130.6	1151.0	1173.8	1200.6	1222.8
10°	980.1	994.7	1013.1	1034.1	1058.2	1079.1	1103.8	1125.8	1153.7	1185.1	1214.5
12.5°	940.6	953.2	973.7	993.8	1019.6	1045.2	1070.7	1099.8	1132.3	1167.1	1204.0
15°	886.2	896.7	913.4	941.3	967.5	992.7	1031.0	1058.2	1099.1	1137.9	1182.5
17.5°	839.7	852.7	866.9	890.7	917.9	949.4	983.5	1017.7	1057.1	1106.3	1156.6
20°	811.2	821.7	838.0	856.3	885.1	916.7	949.2	983.7	1032.0	1082.9	1136.8
22.5°	780.1	791.5	809.8	829.9	854.1	884.3	920.2	958.2	1008.5	1058.5	1117.1
25°	743.6	751.4	768.2	786.1	810.2	835.9	873.1	915.0	964.8	1022.0	1081.8
27.5°	709.0	716.0	731.3	746.8	768.6	799.1	832.4	874.7	921.7	979.7	1045.9
30°	684.3	691.7	705.3	722.1	743.1	769.8	803.9	843.7	894.0	950.7	1020.0
32.5°	662.9	669.4	679.7	696.5	717.0	743.0	774.5	815.2	865.6	923.0	991.0
35°	629.8	637.1	645.0	658.1	675.9	701.0	735.7	774.0	822.2	877.8	940.2
37.5°	596.8	604.8	611.9	623.6	639.9	662.1	692.0	731.8	775.5	829.0	888.9
40°	576.3	582.6	588.3	601.0	617.2	638.1	666.0	701.7	747.8	797.6	847.4
42.5°	555.7	561.6	566.5	577.4	592.5	612.6	639.1	673.9	716.7	763.2	807.1
45°	523.3	527.0	532.8	542.2	554.3	572.6	598.3	629.2	665.4	709.5	742.6
47.5°	488.3	494.0	498.8	507.1	516.9	534.9	559.6	585.9	618.7	651.5	674.8
50°	461.4	467.3	474.0	481.9	491.3	508.2	530.7	557.4	585.2	610.4	630.3
52.5°	436.3	441.6	448.9	456.4	467.9	482.1	501.3	525.1	552.5	570.6	587.1
55°	399.1	401.6	410.1	417.4	428.4	438.9	458.3	479.3	496.0	509.7	523.3
57.5°	361.0	364.6	369.4	376.0	386.9	399.2	412.8	431.3	441.2	448.3	458.8
60°	336.7	337.7	340.8	348.7	357.1	368.1	383.8	397.0	404.2	410.1	419.0
62.5°	309.8	310.0	315.3	321.0	327.3	339.2	351.9	362.5	368.6	371.4	380.0
65°	272.2	271.1	274.3	278.9	286.3	294.2	305.2	314.7	314.1	317.2	322.4
67.5°	233.7	232.6	232.6	237.1	243.1	250.1	257.7	263.2	263.3	267.4	270.0
70°	207.6	204.5	206.6	210.3	212.9	218.6	227.0	229.1	229.6	231.8	234.4
72.5°	180.8	179.8	181.5	183.0	184.8	189.3	196.4	197.7	197.8	199.0	203.4
75°	143.7	142.6	141.6	143.2	145.2	148.3	151.0	153.1	152.6	153.1	156.2
77.5°	107.8	104.7	104.2	105.1	105.6	107.4	110.2	110.0	110.6	110.5	114.0
80°	85.4	81.3	80.8	80.8	81.3	82.3	83.4	84.4	82.8	84.4	85.4
82.5°	62.8	60.3	60.2	59.8	59.9	60.1	60.7	61.4	61.0	61.8	62.4
85°	34.6	33.5	32.0	33.0	32.5	30.9	32.0	30.4	29.9	30.4	30.9
87.5°	15.8	16.0	14.6	14.3	13.5	13.6	12.3	11.5	10.6	10.5	11.5
90°	20.0	18.8	16.5	15.2	12.9	11.7	9.4	7.1	4.6	2.3	1.2
92.5°	306.3	378.3	384.5	267.8	160.3	96.2	62.0	41.8	27.3	17.4	14.3
95°	1017.3	1039.7	848.4	524.5	266.4	140.8	88.0	62.2	49.3	39.9	38.7
97.5°	1287.3	1110.2	757.6	418.7	229.5	146.4	108.5	85.2	72.3	65.7	64.3
100°	1352.9	1059.6	675.9	380.2	227.6	159.6	124.4	102.1	89.2	84.5	82.1
102.5°	1313.5	970.4	613.9	364.3	236.1	175.5	141.3	120.9	107.0	103.3	101.9
105°	1187.5	850.7	553.8	357.9	253.5	201.9	169.0	150.2	138.5	132.6	132.6
107.5°	1058.9	768.3	528.5	368.7	279.2	229.2	199.8	180.3	170.6	165.0	162.6
110°	985.6	729.8	521.0	379.0	298.0	249.9	219.4	201.9	191.3	186.6	184.2



TEST NUMBER: P333243-840

CATALOG NUMBER: S125DIP-S850D1205U840-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	220°	225°	230°	235°	240°	245°	250°	255°	260°	265°	270°
112.5°	931.2	707.3	521.0	392.1	315.9	269.6	240.0	222.5	211.9	208.1	205.8
115°	871.8	683.0	524.5	411.8	343.9	300.4	271.0	253.5	242.9	239.3	237.0
117.5°	836.4	671.0	532.3	434.4	372.4	331.3	303.0	283.1	272.5	268.7	265.2
120°	816.7	665.3	539.8	449.4	393.1	352.0	322.7	302.8	292.2	287.5	284.0
122.5°	799.8	660.7	546.3	466.4	412.8	371.7	342.4	320.5	310.0	306.3	303.7
125°	776.8	654.8	557.3	489.3	438.9	400.1	369.6	347.3	336.8	330.9	328.5
127.5°	755.7	652.0	569.8	510.5	463.9	426.7	396.2	372.4	359.1	351.5	348.0
130°	741.6	650.1	577.3	524.5	479.9	443.5	413.0	388.4	373.1	363.8	360.2
132.5°	730.3	650.1	585.7	536.7	494.9	458.6	428.1	402.5	385.4	374.1	369.6
135°	717.0	650.1	597.2	553.8	515.1	478.8	447.1	422.4	403.6	389.6	384.9
137.5°	705.0	651.5	607.8	566.5	529.5	496.3	463.7	439.6	420.8	407.7	404.1
140°	699.3	652.4	612.5	575.0	539.8	505.7	474.0	451.8	433.0	418.9	415.4
142.5°	694.7	653.4	615.3	579.7	546.3	514.2	484.4	463.0	444.2	431.1	428.5
145°	687.6	652.4	618.4	586.7	557.3	526.8	499.9	478.8	462.3	450.6	448.3
147.5°	680.3	649.3	619.6	591.0	564.4	537.7	513.9	495.6	480.4	470.3	468.9
150°	674.7	646.5	619.6	593.8	569.1	543.3	523.3	507.0	491.7	483.4	481.1
152.5°	668.1	642.8	618.6	595.6	573.8	549.9	531.8	516.3	502.9	495.6	494.2
155°	657.1	636.0	616.0	597.2	578.5	558.6	542.1	530.4	518.7	511.6	511.6
157.5°	646.8	628.9	613.0	598.4	582.5	565.3	552.9	542.6	532.5	526.8	527.1
160°	638.3	624.3	610.2	598.4	584.4	569.1	558.6	549.2	541.0	536.2	537.5
162.5°	630.9	618.6	607.3	597.5	586.2	572.9	564.2	556.6	549.4	544.7	545.8
165°	619.6	610.2	603.1	596.1	586.7	577.3	570.3	565.6	559.8	556.2	558.6
167.5°	608.5	602.0	596.5	593.3	586.7	579.0	574.5	571.2	567.9	565.8	567.0
170°	602.0	597.2	593.8	591.4	586.7	580.9	577.3	575.0	572.6	571.5	572.6
172.5°	595.4	591.7	590.0	589.6	585.7	580.9	579.2	577.7	575.4	574.3	576.4
175°	586.7	585.5	585.5	586.7	584.4	580.9	580.9	580.9	579.7	578.5	580.9
177.5°	583.0	582.0	582.0	583.9	583.0	581.1	581.1	582.0	581.1	581.1	583.0
180°	582.0	582.0	582.0	582.0	582.0	582.0	582.0	582.0	582.0	582.0	582.0



TEST NUMBER: P333243-840

CATALOG NUMBER: S125DIP-S850D1205U840-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	275°	280°	285°	290°	295°	300°	305°	310°	315°	320°	325°
0°	1235.5	1235.5	1235.5	1235.5	1235.5	1235.5	1235.5	1235.5	1235.5	1235.5	1235.5
2.5°	1242.1	1248.0	1251.8	1258.9	1264.8	1268.2	1271.1	1273.6	1276.6	1279.1	1286.2
5°	1250.1	1263.7	1275.3	1293.1	1309.4	1321.9	1335.5	1347.7	1357.7	1371.8	1382.8
7.5°	1246.7	1270.9	1296.3	1323.8	1352.0	1378.3	1402.4	1424.9	1445.4	1470.2	1491.9
10°	1243.3	1276.4	1308.9	1346.0	1384.3	1416.8	1447.2	1478.2	1500.8	1532.3	1558.9
12.5°	1240.8	1279.7	1318.9	1363.7	1405.7	1451.7	1492.2	1514.7	1549.0	1574.2	1606.0
15°	1230.2	1281.6	1335.5	1385.9	1445.7	1488.1	1523.9	1567.9	1599.8	1631.8	1666.5
17.5°	1211.2	1269.4	1329.8	1395.8	1453.2	1498.7	1544.7	1587.2	1625.4	1668.3	1711.3
20°	1202.4	1260.6	1329.8	1397.5	1453.6	1501.3	1548.5	1595.2	1637.1	1692.1	1742.0
22.5°	1184.0	1254.4	1318.1	1384.0	1441.8	1493.8	1547.2	1600.2	1656.0	1718.2	1780.6
25°	1151.0	1222.3	1290.0	1355.0	1413.2	1478.2	1535.4	1606.2	1677.5	1759.8	1837.4
27.5°	1116.8	1185.1	1247.1	1309.9	1377.8	1451.4	1525.5	1605.9	1699.2	1803.1	1912.6
30°	1089.1	1153.7	1214.0	1278.4	1349.2	1432.1	1513.4	1608.8	1716.8	1833.7	1963.8
32.5°	1056.8	1116.3	1174.9	1243.2	1320.3	1407.8	1502.5	1607.1	1737.0	1869.9	2003.7
35°	1001.6	1051.4	1111.7	1184.6	1271.6	1371.8	1481.4	1605.1	1754.0	1906.6	2019.4
37.5°	936.0	982.4	1045.9	1125.8	1217.1	1324.5	1454.6	1601.4	1759.6	1881.3	1917.6
40°	892.0	934.9	1001.1	1083.9	1177.2	1291.0	1433.6	1588.8	1742.0	1819.6	1789.7
42.5°	845.0	890.1	954.4	1036.5	1137.0	1260.8	1407.2	1562.5	1690.8	1720.2	1616.9
45°	770.8	817.5	880.9	963.8	1071.9	1206.1	1358.7	1499.8	1573.7	1520.7	1360.8
47.5°	702.0	745.7	804.5	890.0	1001.5	1140.3	1287.3	1399.8	1405.6	1279.3	1108.4
50°	655.0	695.3	754.6	840.0	950.7	1091.3	1223.9	1312.5	1272.6	1129.5	965.3
52.5°	608.8	648.3	706.8	791.4	900.8	1029.6	1153.0	1215.2	1140.1	993.2	852.9
55°	542.2	576.8	634.0	712.1	816.0	935.5	1040.4	1061.9	964.3	819.6	705.8
57.5°	477.2	509.5	561.5	633.5	728.3	834.2	916.3	911.7	808.6	684.4	594.1
60°	433.1	464.6	510.8	581.0	667.5	758.8	829.0	812.2	710.0	603.0	527.0
62.5°	393.7	421.8	465.4	526.8	605.8	690.4	748.1	723.4	623.2	529.6	469.5
65°	335.6	359.2	396.5	448.9	514.4	584.2	628.7	596.7	511.3	438.4	390.1
67.5°	280.1	299.0	330.2	372.1	428.0	484.0	511.2	479.0	410.6	357.4	321.6
70°	244.9	261.7	285.8	323.1	371.8	419.0	439.4	410.6	351.8	306.2	280.5
72.5°	209.6	223.5	244.7	278.1	317.2	358.2	376.1	348.5	300.2	261.8	237.7
75°	162.1	171.5	186.1	209.2	240.1	272.7	282.7	258.5	227.6	198.7	183.0
77.5°	116.0	124.0	135.1	149.7	171.6	192.3	201.0	187.0	163.1	144.8	131.9
80°	89.2	93.3	102.8	114.8	132.2	145.2	151.0	142.1	125.3	111.7	101.7
82.5°	63.5	67.8	73.4	83.4	94.4	103.3	109.5	103.5	91.4	80.7	74.8
85°	30.9	33.5	36.7	40.9	49.3	54.5	54.0	50.3	45.6	41.4	38.3
87.5°	11.4	12.2	14.0	16.6	18.3	20.2	21.5	20.9	19.7	18.7	17.7
90°	2.3	4.6	7.1	9.4	11.7	12.9	15.2	16.5	18.8	20.0	21.1
92.5°	17.4	27.3	41.8	62.0	96.2	160.3	267.8	384.5	378.3	306.3	207.9
95°	39.9	49.3	62.2	88.0	140.8	266.4	524.5	848.4	1039.7	1017.3	843.6
97.5°	65.7	72.3	85.2	108.5	146.4	229.5	418.7	757.6	1110.2	1287.3	1256.5
100°	84.5	89.2	102.1	124.4	159.6	227.6	380.2	675.9	1059.6	1352.9	1443.3
102.5°	103.3	107.0	120.9	141.3	175.5	236.1	364.3	613.9	970.4	1313.5	1506.2
105°	132.6	138.5	150.2	169.0	201.9	253.5	357.9	553.8	850.7	1187.5	1469.2
107.5°	165.0	170.6	180.3	199.8	229.2	279.2	368.7	528.5	768.3	1058.9	1336.8
110°	186.6	191.3	201.9	219.4	249.9	298.0	379.0	521.0	729.8	985.6	1239.1



TEST NUMBER: P333243-840

CATALOG NUMBER: S125DIP-S850D1205U840-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	275°	280°	285°	290°	295°	300°	305°	310°	315°	320°	325°
112.5°	208.1	211.9	222.5	240.0	269.6	315.9	392.1	521.0	707.3	931.2	1162.2
115°	239.3	242.9	253.5	271.0	300.4	343.9	411.8	524.5	683.0	871.8	1065.5
117.5°	268.7	272.5	283.1	303.0	331.3	372.4	434.4	532.3	671.0	836.4	1003.0
120°	287.5	292.2	302.8	322.7	352.0	393.1	449.4	539.8	665.3	816.7	969.3
122.5°	306.3	310.0	320.5	342.4	371.7	412.8	466.4	546.3	660.7	799.8	943.9
125°	330.9	336.8	347.3	369.6	400.1	438.9	489.3	557.3	654.8	776.8	907.1
127.5°	351.5	359.1	372.4	396.2	426.7	463.9	510.5	569.8	652.0	755.7	869.5
130°	363.8	373.1	388.4	413.0	443.5	479.9	524.5	577.3	650.1	741.6	846.1
132.5°	374.1	385.4	402.5	428.1	458.6	494.9	536.7	585.7	650.1	730.3	822.5
135°	389.6	403.6	422.4	447.1	478.8	515.1	553.8	597.2	650.1	717.0	792.0
137.5°	407.7	420.8	439.6	463.7	496.3	529.5	566.5	607.8	651.5	705.0	766.3
140°	418.9	433.0	451.8	474.0	505.7	539.8	575.0	612.5	652.4	699.3	752.1
142.5°	431.1	444.2	463.0	484.4	514.2	546.3	579.7	615.3	653.4	694.7	739.9
145°	450.6	462.3	478.8	499.9	526.8	557.3	586.7	618.4	652.4	687.6	724.0
147.5°	470.3	480.4	495.6	513.9	537.7	564.4	591.0	619.6	649.3	680.3	709.0
150°	483.4	491.7	507.0	523.3	543.3	569.1	593.8	619.6	646.5	674.7	700.5
152.5°	495.6	502.9	516.3	531.8	549.9	573.8	595.6	618.6	642.8	668.1	691.2
155°	511.6	518.7	530.4	542.1	558.6	578.5	597.2	616.0	636.0	657.1	677.0
157.5°	526.8	532.5	542.6	552.9	565.3	582.5	598.4	613.0	628.9	646.8	663.0
160°	536.2	541.0	549.2	558.6	569.1	584.4	598.4	610.2	624.3	638.3	653.6
162.5°	544.7	549.4	556.6	564.2	572.9	586.2	597.5	607.3	618.6	630.9	643.3
165°	556.2	559.8	565.6	570.3	577.3	586.7	596.1	603.1	610.2	619.6	628.9
167.5°	565.8	567.9	571.2	574.5	579.0	586.7	593.3	596.5	602.0	608.5	615.3
170°	571.5	572.6	575.0	577.3	580.9	586.7	591.4	593.8	597.2	602.0	607.8
172.5°	574.3	575.4	577.7	579.2	580.9	585.7	589.6	590.0	591.7	595.4	599.4
175°	578.5	579.7	580.9	580.9	580.9	584.4	586.7	585.5	585.5	586.7	590.3
177.5°	581.1	581.1	582.0	581.1	581.1	583.0	583.9	582.0	582.0	583.0	583.9
180°	582.0	582.0	582.0	582.0	582.0	582.0	582.0	582.0	582.0	582.0	582.0



TEST NUMBER: P333243-840

CATALOG NUMBER: S125DIP-S850D1205U840-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	330°	335°	340°	345°	350°	355°	360°
0°	1235.5	1235.5	1235.5	1235.5	1235.5	1235.5	1235.5
2.5°	1292.0	1295.5	1302.5	1300.0	1303.4	1305.0	1306.8
5°	1396.4	1413.2	1420.6	1419.5	1430.5	1427.8	1425.2
7.5°	1514.3	1532.0	1541.8	1554.1	1561.2	1561.7	1567.9
10°	1581.0	1604.1	1613.6	1626.6	1635.0	1639.7	1639.2
12.5°	1632.1	1650.2	1671.4	1677.8	1689.1	1695.1	1692.9
15°	1693.7	1722.6	1744.6	1755.7	1769.8	1773.9	1779.8
17.5°	1748.7	1787.4	1813.1	1847.2	1860.2	1868.0	1863.4
20°	1790.2	1841.1	1866.8	1907.7	1930.3	1942.3	1938.1
22.5°	1839.3	1894.4	1941.9	1977.3	2011.7	2027.9	2031.2
25°	1923.4	1998.9	2068.7	2115.4	2157.8	2167.8	2189.8
27.5°	2017.4	2106.5	2181.0	2230.1	2259.7	2270.8	2277.6
30°	2076.6	2165.2	2221.3	2252.7	2262.2	2261.1	2260.1
32.5°	2105.5	2161.0	2171.7	2162.9	2141.3	2123.1	2104.1
35°	2064.5	2023.1	1961.2	1881.5	1822.7	1763.5	1757.7
37.5°	1856.7	1724.2	1621.2	1506.2	1439.9	1398.9	1370.5
40°	1661.2	1510.8	1385.9	1288.9	1221.2	1194.6	1168.3
42.5°	1449.0	1305.1	1194.7	1113.6	1062.7	1033.0	1012.3
45°	1177.2	1050.4	963.8	905.0	864.7	841.6	828.5
47.5°	964.6	870.8	797.3	754.9	727.0	709.0	709.1
50°	850.5	760.8	712.1	678.5	654.4	640.3	642.9
52.5°	749.4	682.5	640.8	612.7	594.8	586.1	585.8
55°	626.6	578.3	551.1	530.7	518.6	508.7	510.8
57.5°	536.0	495.3	477.1	460.1	451.7	447.7	441.9
60°	479.8	448.4	432.6	419.0	410.6	407.5	401.6
62.5°	429.9	405.2	389.8	378.7	371.1	370.1	365.6
65°	361.3	342.4	328.8	323.6	315.7	313.6	313.6
67.5°	297.8	284.3	273.8	268.9	265.4	266.0	263.5
70°	258.0	247.0	240.1	234.9	232.3	232.8	230.8
72.5°	225.7	213.4	207.4	204.3	200.9	202.2	201.4
75°	171.0	164.6	161.5	158.3	156.2	155.2	154.2
77.5°	125.5	120.0	117.5	115.8	116.1	113.6	115.5
80°	97.0	92.3	90.7	88.1	87.6	87.6	87.1
82.5°	71.0	68.4	67.3	65.0	64.1	64.9	63.5
85°	36.7	34.6	34.1	34.1	33.0	32.0	34.6
87.5°	17.9	16.5	16.9	16.5	16.5	16.3	15.5
90°	22.3	23.4	25.9	25.9	25.9	27.0	27.0
92.5°	150.9	113.6	96.2	81.2	78.4	76.7	74.8
95°	665.3	521.0	422.4	339.1	303.9	294.6	275.8
97.5°	1131.5	990.9	853.7	781.2	715.6	681.6	666.5
100°	1385.8	1265.0	1142.9	1062.0	977.4	934.0	915.2
102.5°	1541.7	1483.7	1401.1	1314.4	1254.4	1207.2	1193.2
105°	1629.9	1681.5	1668.6	1631.0	1592.4	1568.8	1554.8
107.5°	1551.3	1683.8	1745.1	1764.1	1763.9	1756.2	1746.8
110°	1462.1	1627.5	1727.3	1780.1	1802.4	1810.6	1810.6



TEST NUMBER: P333243-840

CATALOG NUMBER: S125DIP-S850D1205U840-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	330°	335°	340°	345°	350°	355°	360°
112.5°	1373.8	1541.2	1658.7	1736.0	1774.2	1794.6	1803.1
115°	1247.4	1408.1	1536.0	1627.5	1683.8	1716.7	1731.9
117.5°	1159.8	1298.3	1415.6	1507.1	1565.4	1598.0	1607.3
120°	1110.0	1239.1	1342.4	1429.3	1485.5	1517.2	1526.6
122.5°	1074.4	1189.4	1286.1	1363.5	1415.1	1446.8	1455.3
125°	1026.7	1128.8	1213.4	1279.0	1327.2	1352.9	1364.7
127.5°	981.2	1076.5	1155.6	1215.2	1257.7	1282.1	1287.3
130°	949.3	1040.9	1117.1	1175.8	1214.5	1238.0	1245.0
132.5°	919.3	1002.3	1075.8	1134.5	1173.2	1194.8	1202.7
135°	873.0	948.2	1015.0	1066.6	1105.4	1126.5	1133.6
137.5°	831.7	894.1	951.0	997.1	1032.4	1051.9	1059.6
140°	807.3	861.3	910.6	954.0	984.5	1002.1	1007.9
142.5°	786.7	833.1	875.9	912.7	938.5	955.1	960.1
145°	760.3	796.8	828.4	856.6	876.6	889.5	894.1
147.5°	738.5	766.5	790.4	812.7	828.7	836.2	838.3
150°	726.4	748.6	769.7	787.4	801.4	806.2	807.3
152.5°	714.2	734.6	751.0	765.8	777.0	781.7	782.9
155°	695.8	712.3	725.2	736.9	745.1	748.6	749.8
157.5°	678.4	691.2	701.3	710.3	717.2	720.4	720.2
160°	665.3	677.0	685.3	693.5	699.3	701.8	700.5
162.5°	654.1	663.9	671.2	677.5	682.5	683.0	682.7
165°	637.1	644.2	650.1	654.8	657.1	657.1	657.1
167.5°	620.8	626.1	630.4	632.7	634.8	633.9	633.7
170°	611.4	614.9	617.2	619.6	620.8	620.8	619.6
172.5°	602.9	605.5	606.9	607.3	609.5	607.6	606.4
175°	590.3	592.6	592.6	592.6	593.8	591.4	590.3
177.5°	584.8	584.8	584.8	583.9	584.8	582.0	582.0
180°	582.0	582.0	582.0	582.0	582.0	582.0	582.0

(END OF REPORT)