

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P331301-830

Luminaire Tested: **SA2XXDIP-C485D530U830-4F0-1E-UDD-F1**

Issue Date: 10/7/2019

Test Information

Test Method: LM-79-08
Report Number: P331301-830
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-8,
Test Lab: INNOVATION CENTER
Issue Date: 10/7/2019
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: NEO-RAY
Catalog Number: SA2XXDIP-C485D530U830-4F0-1E-UDD-F1
Description: DEFINE 2 DIRECT-INDIRECT PENDANT LED LUMINAIRE
DOWNLIGHT 485 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER
UPLIGHT 530 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER
Light Source: -
Ballast/Driver: ELECTRONIC DRIVER

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 3646.0 lumens
Efficiency: N/A
Efficacy: 111.2 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 1.16 / 1.3
Luminous Opening: Rectangular (W 0.17' x L: 4' x H: 0')
CIE Type: General Diffuse

Input Watts (W): 32.8
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P331301-830
CATALOG NUMBER: SA2XXDIP-C485D530U830-4F0-1E-UDD-F1

Luminous Intensity Polar Plot





TEST NUMBER: P331301-830

CATALOG NUMBER: SA2XXDIP-C485D530U830-4F0-1E-UDD-F1

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20					20					20					20					20	
RC	80					70					50					30					10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0	
RCR																						
0	107	107	107	107	99	99	99	99	84	84	84	70	70	70	57	57	57	51	51	51	51	
1	98	94	90	86	90	87	83	80	74	71	69	62	60	58	51	49	48	43	43	43	43	
2	89	82	76	70	82	76	70	66	65	61	57	54	51	49	44	42	41	36	36	36	36	
3	81	72	65	59	75	67	60	55	57	52	48	48	44	41	39	37	35	31	31	31	31	
4	75	64	56	50	69	59	52	47	51	45	41	43	39	35	35	32	30	26	26	26	26	
5	68	57	49	43	63	53	46	40	45	40	35	38	34	31	32	29	26	23	23	23	23	
6	63	51	43	37	58	47	40	35	41	35	31	35	30	27	29	25	23	20	20	20	20	
7	58	46	38	32	54	43	36	31	37	31	27	31	27	24	26	23	20	18	18	18	18	
8	54	42	34	29	50	39	32	27	34	28	24	29	24	21	24	21	18	16	16	16	16	
9	50	38	31	26	47	36	29	24	31	25	22	27	22	19	22	19	16	14	14	14	14	
10	47	35	28	23	44	33	26	22	29	23	19	24	20	17	21	17	15	13	13	13	13	

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	11820	11820	11820
5°	11866	11694	11763
10°	11795	11576	11632
15°	11649	11425	11413
20°	11442	11201	11187
25°	11236	10922	10922
30°	10972	10670	10577
35°	10724	10364	10212
40°	10416	10060	9866
45°	10111	9757	9515
50°	9779	9442	9105
55°	9433	9073	8740
60°	9045	8638	8318
65°	8630	8202	7824
70°	8105	7676	7312
75°	7380	7068	6900
80°	6546	6341	6025
85°	5335	5076	4557



TEST NUMBER: P331301-830

CATALOG NUMBER: SA2XXDIP-C485D530U830-4F0-1E-UDD-F1

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	68.8	1.9
10°-20°	193.7	5.3
20°-30°	284.7	7.8
30°-40°	330.7	9.1
40°-50°	330.4	9.1
50°-60°	288.1	7.9
60°-70°	213.0	5.8
70°-80°	120.7	3.3
80°-90°	35.0	1.0
90°-100°	40.4	1.1
100°-110°	125.3	3.4
110°-120°	214.3	5.9
120°-130°	281.8	7.7
130°-140°	316.2	8.7
140°-150°	310.1	8.5
150°-160°	260.1	7.1
160°-170°	172.5	4.7
170°-180°	60.3	1.7
0°-30°	547.2	15.0
0°-40°	878.0	24.1
0°-60°	1496.4	41.0
0°-90°	1865.1	51.2
90°-120°	380.0	10.4
90°-150°	1288.0	35.3
90°-180°	1781.0	48.8
0°-180°	3646.0	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	732	732	732	732	732	
5°	732	729	722	727	726	69
15°	697	692	684	686	683	196
25°	631	625	613	614	613	290
35°	544	537	526	522	518	340
45°	443	438	427	420	417	342
55°	335	331	322	314	310	299
65°	226	222	215	208	205	223
75°	118	117	113	109	111	126
85°	29	28	27	25	25	33
90°	1	7	19	18	18	3
95°	28	33	34	34	33	32
105°	116	117	118	119	119	122
115°	215	218	217	217	215	213
125°	313	317	316	314	314	279
135°	405	410	412	411	410	312
145°	491	495	498	499	497	307
155°	562	563	565	567	566	258
165°	611	611	611	614	612	172
175°	636	634	633	637	634	60
180°	637	637	637	637	637	



TEST NUMBER: P331301-830

CATALOG NUMBER: SA2XXDIP-C485D530U830-4F0-1E-UDD-F1

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	732.1	732.1	732.1	732.1	732.1	732.1	732.1	732.1	732.1	732.1	732.1
2.5°	735.5	734.8	734.2	733.6	732.9	732.0	730.6	729.2	727.8	726.4	727.7
5°	732.1	731.4	730.8	730.2	729.6	728.4	726.7	725.0	723.2	721.5	722.7
7.5°	725.6	724.6	723.7	722.6	721.7	720.4	718.6	716.9	715.1	713.3	714.6
10°	719.4	718.3	717.2	716.1	715.0	713.5	711.6	709.8	707.9	706.1	707.3
12.5°	711.0	710.0	709.0	708.0	707.1	705.7	703.8	701.9	700.0	698.1	699.0
15°	696.9	696.0	695.0	694.1	693.1	691.6	689.6	687.6	685.5	683.5	684.1
17.5°	678.8	678.0	677.0	676.1	675.1	673.6	671.6	669.5	667.4	665.3	666.1
20°	665.9	665.0	664.0	663.1	662.1	660.6	658.4	656.2	654.0	651.9	652.3
22.5°	653.0	651.7	650.4	649.0	647.7	646.0	643.9	641.9	639.8	637.7	637.8
25°	630.7	629.4	628.2	627.0	625.8	623.8	621.1	618.4	615.8	613.1	613.4
27.5°	605.4	604.3	603.1	602.0	600.9	599.3	597.2	595.0	593.0	590.9	590.4
30°	588.5	587.2	586.0	584.8	583.4	581.6	579.3	577.0	574.7	572.3	571.8
32.5°	570.4	569.5	568.4	567.4	566.5	564.7	562.2	559.8	557.3	554.9	554.0
35°	544.1	542.5	541.0	539.4	537.9	535.8	533.4	530.8	528.3	525.8	524.9
37.5°	514.4	513.0	511.7	510.3	508.9	507.0	504.4	502.0	499.5	497.0	495.8
40°	494.2	492.9	491.6	490.4	489.2	487.3	484.7	482.3	479.8	477.3	475.9
42.5°	474.5	473.2	471.9	470.7	469.5	467.6	465.1	462.6	460.1	457.5	456.0
45°	442.8	441.7	440.5	439.5	438.4	436.7	434.3	432.0	429.6	427.3	425.6
47.5°	411.2	410.2	409.2	408.1	407.1	405.4	402.9	400.5	398.0	395.6	393.8
50°	389.3	388.5	387.7	386.9	386.2	384.7	382.5	380.3	378.1	375.9	373.7
52.5°	367.9	366.8	365.8	364.8	363.7	362.2	360.1	358.1	356.0	353.9	352.1
55°	335.1	334.1	333.2	332.2	331.3	329.9	328.0	326.1	324.2	322.3	320.6
57.5°	302.1	301.3	300.6	299.9	299.2	297.7	295.7	293.6	291.5	289.5	287.6
60°	280.1	279.6	278.9	278.2	277.7	276.3	274.1	271.8	269.7	267.5	265.8
62.5°	258.7	257.8	256.7	255.7	254.8	253.4	251.8	250.1	248.4	246.7	245.1
65°	225.9	225.0	224.0	223.1	222.3	220.9	219.4	217.8	216.2	214.7	213.3
67.5°	192.6	191.8	191.1	190.3	189.5	188.5	187.1	185.7	184.3	182.9	181.8
70°	171.7	171.2	170.5	169.8	169.3	168.2	166.8	165.4	164.0	162.6	161.6
72.5°	150.3	149.8	149.1	148.5	147.9	147.1	146.2	145.2	144.4	143.5	142.3
75°	118.3	117.9	117.6	117.3	117.0	116.5	115.6	114.9	114.1	113.3	112.4
77.5°	89.5	89.0	88.5	87.9	87.4	87.0	86.7	86.3	86.1	85.8	85.3
80°	70.4	70.2	70.1	69.9	69.7	69.6	69.2	68.9	68.6	68.2	67.8
82.5°	52.4	52.3	52.3	52.3	52.2	52.1	51.9	51.7	51.6	51.4	50.8
85°	28.8	28.7	28.6	28.4	28.3	28.1	27.9	27.8	27.6	27.4	27.0
87.5°	10.3	10.3	10.3	10.4	10.4	10.6	10.8	11.1	11.4	11.7	11.2
90°	0.6	2.0	3.4	4.8	6.3	8.3	10.9	13.6	16.2	18.9	18.6
92.5°	9.6	10.7	11.7	12.7	13.8	14.6	15.3	15.8	16.5	17.1	17.2
95°	28.0	29.1	30.3	31.6	32.7	33.5	33.6	33.9	34.1	34.4	34.4
97.5°	51.1	52.1	53.2	54.2	55.2	56.0	56.5	56.9	57.4	57.9	57.9
100°	68.2	69.2	70.1	71.2	72.1	72.8	73.1	73.4	73.8	74.2	74.2
102.5°	86.3	87.1	87.8	88.6	89.4	90.0	90.5	90.9	91.3	91.8	91.9
105°	115.6	115.9	116.3	116.6	117.0	117.3	117.5	117.7	118.0	118.3	118.5
107.5°	145.1	145.5	146.1	146.6	147.1	147.4	147.4	147.4	147.4	147.4	147.5
110°	163.9	164.7	165.3	166.1	166.8	167.1	167.1	167.1	167.1	167.1	167.1



TEST NUMBER: P331301-830

CATALOG NUMBER: SA2XXDIP-C485D530U830-4F0-1E-UDD-F1

CANDELA DISTRIBUTION (continued):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	184.5	185.3	186.0	186.7	187.5	187.8	187.7	187.6	187.5	187.4	187.1
115°	215.0	215.7	216.4	217.2	217.8	218.1	217.8	217.6	217.4	217.2	217.1
117.5°	245.3	246.3	247.2	248.2	249.1	249.3	248.6	247.9	247.2	246.6	246.3
120°	265.5	266.5	267.4	268.3	269.4	269.4	268.3	267.4	266.5	265.5	265.5
122.5°	284.0	285.1	286.3	287.5	288.6	288.8	288.1	287.5	286.8	286.2	285.9
125°	312.8	313.9	315.0	316.0	317.1	317.4	317.1	316.8	316.4	316.0	315.7
127.5°	340.8	342.2	343.6	345.0	346.3	346.8	346.4	345.9	345.5	345.1	344.6
130°	358.5	360.1	361.6	363.2	364.7	365.3	365.1	364.9	364.7	364.4	364.2
132.5°	378.2	379.6	380.8	382.1	383.3	384.0	384.1	384.1	384.2	384.2	383.7
135°	404.7	406.0	407.4	408.7	410.0	410.8	410.9	411.2	411.5	411.7	411.6
137.5°	432.5	433.7	434.7	435.8	436.9	437.5	437.9	438.2	438.5	438.8	438.7
140°	449.3	450.4	451.5	452.5	453.6	454.5	455.1	455.6	456.3	456.9	456.9
142.5°	466.6	467.6	468.7	469.8	470.8	471.6	472.0	472.4	472.8	473.2	473.3
145°	491.3	492.1	492.9	493.8	494.6	495.4	496.1	496.8	497.6	498.2	498.3
147.5°	513.3	514.3	515.3	516.3	517.3	518.0	518.5	519.0	519.4	520.0	520.2
150°	528.4	529.0	529.8	530.5	531.2	531.8	532.3	532.7	533.2	533.8	534.0
152.5°	541.7	542.4	543.1	543.8	544.5	545.2	545.7	546.3	546.9	547.5	547.9
155°	561.7	562.0	562.4	562.7	563.1	563.5	563.8	564.2	564.5	564.9	565.5
157.5°	578.7	579.0	579.2	579.5	579.8	579.9	580.1	580.4	580.6	580.8	581.6
160°	589.1	589.3	589.6	589.7	590.0	590.2	590.3	590.4	590.6	590.7	591.4
162.5°	598.5	598.6	598.6	598.7	598.7	598.8	598.9	599.1	599.2	599.3	600.1
165°	611.1	611.0	610.9	610.8	610.7	610.6	610.6	610.6	610.6	610.6	611.4
167.5°	621.6	621.3	620.9	620.6	620.2	620.0	620.0	620.0	619.9	619.9	620.8
170°	627.3	626.9	626.5	626.1	625.8	625.6	625.5	625.3	625.2	625.1	625.9
172.5°	631.1	630.7	630.4	630.0	629.7	629.4	629.3	629.2	629.1	629.0	629.8
175°	635.8	635.5	635.1	634.8	634.4	634.1	633.9	633.7	633.4	633.1	634.0
177.5°	637.8	637.4	637.2	636.9	636.6	636.4	636.2	636.0	635.8	635.7	636.2
180°	636.9	636.9	636.9	636.9	636.9	636.9	636.9	636.9	636.9	636.9	636.9



TEST NUMBER: P331301-830

CATALOG NUMBER: SA2XXDIP-C485D530U830-4F0-1E-UDD-F1

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°
0°	732.1	732.1	732.1	732.1	732.1	732.1	732.1	732.1
2.5°	729.0	730.2	731.4	732.0	731.7	731.4	731.2	730.9
5°	724.1	725.3	726.5	727.0	726.7	726.3	726.0	725.8
7.5°	715.9	717.1	718.4	718.8	718.5	718.1	717.7	717.5
10°	708.5	709.8	711.1	711.4	711.0	710.5	710.0	709.5
12.5°	699.9	700.8	701.6	701.9	701.5	701.3	700.9	700.5
15°	684.8	685.4	686.0	685.9	685.1	684.4	683.6	682.8
17.5°	666.8	667.5	668.3	668.2	667.4	666.8	666.0	665.2
20°	652.8	653.3	653.7	653.7	653.0	652.3	651.8	651.1
22.5°	637.9	638.0	638.1	638.0	637.6	637.3	636.9	636.5
25°	613.8	614.1	614.3	614.3	614.1	613.8	613.4	613.1
27.5°	589.9	589.5	589.0	588.4	587.7	586.9	586.2	585.4
30°	571.4	570.9	570.4	569.9	569.2	568.6	568.0	567.3
32.5°	553.2	552.3	551.5	550.7	550.1	549.5	548.8	548.2
35°	524.0	523.0	522.1	521.2	520.5	519.6	518.9	518.1
37.5°	494.6	493.5	492.4	491.3	490.6	489.8	489.1	488.4
40°	474.5	473.1	471.6	470.6	470.0	469.4	468.7	468.1
42.5°	454.5	453.0	451.4	450.3	449.3	448.5	447.6	446.7
45°	423.9	422.2	420.4	419.2	418.6	418.0	417.4	416.7
47.5°	392.0	390.1	388.3	387.0	386.1	385.2	384.3	383.3
50°	371.6	369.3	367.1	365.6	364.9	364.1	363.3	362.5
52.5°	350.3	348.5	346.7	345.3	344.2	343.2	342.1	341.1
55°	318.7	316.8	314.9	313.6	312.7	312.0	311.2	310.5
57.5°	285.8	283.9	282.1	280.9	280.2	279.7	279.1	278.4
60°	264.0	262.3	260.6	259.5	259.0	258.5	258.1	257.6
62.5°	243.5	241.9	240.3	239.2	238.6	238.0	237.4	236.8
65°	211.9	210.5	209.1	207.9	207.2	206.4	205.7	204.8
67.5°	180.7	179.6	178.5	177.7	177.0	176.3	175.8	175.1
70°	160.4	159.3	158.3	157.4	156.7	156.1	155.5	154.9
72.5°	141.3	140.2	139.1	138.3	137.8	137.2	136.8	136.3
75°	111.4	110.6	109.6	109.2	109.6	109.9	110.2	110.6
77.5°	84.8	84.4	83.9	83.4	82.9	82.6	82.1	81.6
80°	67.3	66.8	66.4	66.0	65.7	65.4	65.0	64.8
82.5°	50.2	49.6	49.0	48.6	48.6	48.5	48.4	48.4
85°	26.5	26.0	25.5	25.3	25.1	25.0	24.8	24.6
87.5°	10.8	10.4	10.0	9.7	9.6	9.5	9.4	9.3
90°	18.4	18.1	17.8	17.8	17.9	18.0	18.2	18.3
92.5°	17.2	17.2	17.2	17.3	17.3	17.3	17.4	17.4
95°	34.4	34.4	34.4	34.3	34.0	33.8	33.6	33.4
97.5°	57.9	57.9	57.9	57.8	57.8	57.8	57.8	57.7
100°	74.2	74.2	74.2	74.1	74.0	73.9	73.8	73.6
102.5°	92.0	92.1	92.2	92.2	92.1	91.9	91.8	91.7
105°	118.8	118.9	119.2	119.3	119.3	119.3	119.3	119.3
107.5°	147.6	147.7	147.8	147.5	146.9	146.5	145.9	145.3
110°	167.1	167.1	167.1	167.0	166.6	166.3	165.9	165.5



TEST NUMBER: P331301-830

CATALOG NUMBER: SA2XXDIP-C485D530U830-4F0-1E-UDD-F1

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°
112.5°	186.8	186.5	186.2	186.0	185.7	185.4	185.1	184.9
115°	216.9	216.8	216.7	216.4	216.0	215.7	215.4	215.0
117.5°	246.0	245.7	245.4	245.2	244.8	244.4	244.0	243.6
120°	265.5	265.5	265.5	265.3	264.9	264.7	264.3	263.9
122.5°	285.6	285.3	285.0	284.7	284.5	284.2	284.0	283.7
125°	315.3	315.0	314.6	314.3	314.2	314.1	314.0	313.9
127.5°	344.2	343.7	343.4	342.9	342.5	342.1	341.8	341.4
130°	363.9	363.7	363.4	363.1	362.6	362.1	361.7	361.2
132.5°	383.1	382.6	382.1	381.6	381.3	380.9	380.5	380.1
135°	411.5	411.3	411.2	410.9	410.7	410.3	409.9	409.5
137.5°	438.6	438.5	438.4	438.1	437.6	437.2	436.7	436.2
140°	456.9	456.9	456.9	456.7	456.1	455.6	455.2	454.7
142.5°	473.3	473.4	473.5	473.3	472.9	472.4	471.9	471.5
145°	498.5	498.6	498.7	498.5	498.0	497.6	497.1	496.6
147.5°	520.5	520.8	521.0	520.9	520.5	520.0	519.5	519.1
150°	534.4	534.8	535.2	535.2	534.8	534.4	534.0	533.8
152.5°	548.4	548.8	549.3	549.3	548.8	548.4	547.9	547.5
155°	566.1	566.7	567.3	567.4	567.0	566.7	566.3	566.0
157.5°	582.4	583.2	584.1	584.2	583.6	583.1	582.5	581.8
160°	592.1	592.9	593.5	593.7	593.2	592.8	592.2	591.7
162.5°	600.9	601.7	602.6	602.7	602.1	601.5	601.0	600.4
165°	612.3	613.1	613.9	614.1	613.4	612.8	612.3	611.6
167.5°	621.6	622.5	623.3	623.4	622.7	622.2	621.5	620.9
170°	626.8	627.6	628.4	628.5	627.7	627.1	626.3	625.7
172.5°	630.7	631.5	632.3	632.4	631.7	630.9	630.2	629.5
175°	634.8	635.7	636.5	636.6	635.8	635.1	634.4	633.7
177.5°	636.8	637.3	637.9	637.9	637.3	636.8	636.2	635.7
180°	636.9	636.9	636.9	636.9	636.9	636.9	636.9	636.9

(END OF REPORT)