

Scaled data based on original data using  
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State  
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P331304-830

Luminaire Tested: **SA2XXDIP-C485D725U830-4F0-1E-UDD-A1**

Issue Date: 10/7/2019

**Test Information**

Test Method: LM-79-08  
Report Number: P331304-830  
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-8,  
Test Lab: INNOVATION CENTER  
Issue Date: 10/7/2019  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: NEO-RAY  
Catalog Number: SA2XXDIP-C485D725U830-4F0-1E-UDD-A1  
Description: DEFINE 2 DIRECT-INDIRECT PENDANT LED LUMINAIRE  
DOWNLIGHT 485 LUMENS PER FOOT, ASYMMETRIC DIFFUSER  
UPLIGHT 725 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER  
Light Source: -  
Ballast/Driver: ELECTRONIC DRIVER

**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 4465.3 lumens  
Efficiency: N/A  
Efficacy: 116.3 lumens/watt  
Spacing Criteria (0/90/45): 1.08 / 1.16 / 1.23  
Luminous Opening: Rectangular (W 4' x L: 0.17' x H: 0')  
CIE Type: General Diffuse


Input Watts (W): 38.4  
Input Voltage (V): 120  
Input Current (Ain): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 25 FT



TEST NUMBER: P331304-830

CATALOG NUMBER: SA2XXDIP-C485D725U830-4F0-1E-UDD-A1

### Luminous Intensity Polar Plot





TEST NUMBER: P331304-830

CATALOG NUMBER: SA2XXDIP-C485D725U830-4F0-1E-UDD-A1

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20					20					20					20					20	
RC	80					70					50					30					10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0	
RCR																						
0	106	106	106	106	97	97	97	97	81	81	81	66	66	66	52	52	52	45				
1	97	93	89	86	89	85	82	79	71	69	67	58	57	55	46	45	45	39				
2	89	82	76	71	81	75	70	66	63	59	56	52	49	47	41	40	38	33				
3	81	72	65	60	74	67	60	56	56	51	48	46	43	40	37	35	33	29				
4	75	64	57	51	68	59	53	47	50	45	41	41	38	35	33	31	29	25				
5	69	57	50	44	63	53	46	41	45	40	36	37	34	30	30	28	25	22				
6	63	52	44	38	58	48	41	36	41	35	31	34	30	27	28	25	23	20				
7	59	47	39	34	54	43	36	32	37	32	28	31	27	24	25	22	20	18				
8	54	42	35	30	50	39	33	28	34	29	25	28	24	21	23	20	18	16				
9	51	39	32	27	47	36	30	25	31	26	22	26	22	19	22	19	17	14				
10	47	36	29	24	44	33	27	23	29	24	20	24	20	18	20	17	15	13				

**AVERAGE LUMINANCE (cd/sqm):**

	0°	90°	180°	270°
0°	14788	14788	14788	14788
5°	16579	14885	13190	14885
10°	18998	14762	11416	14762
15°	21018	14492	10084	14492
20°	20697	14201	9194	14201
25°	18661	13814	8630	13814
30°	15422	13196	8216	13196
35°	11239	12552	7924	12552
40°	8977	11788	7761	11788
45°	7846	10908	7540	10908
50°	7375	10052	7392	10052
55°	6798	9185	7192	9185
60°	6229	8263	6888	8263
65°	5673	7435	6590	7435
70°	5150	6628	6151	6628
75°	4566	5733	5446	5733
80°	3924	4751	4379	4751
85°	3520	3520	2594	3520



TEST NUMBER: P331304-830

CATALOG NUMBER: SA2XXDIP-C485D725U830-4F0-1E-UDD-A1

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	87.2	2.0
10°-20°	253.6	5.7
20°-30°	368.0	8.2
30°-40°	388.4	8.7
40°-50°	343.9	7.7
50°-60°	274.4	6.1
60°-70°	186.5	4.2
70°-80°	95.6	2.1
80°-90°	26.5	0.6
90°-100°	55.3	1.2
100°-110°	171.8	3.8
110°-120°	293.7	6.6
120°-130°	386.2	8.6
130°-140°	433.5	9.7
140°-150°	425.0	9.5
150°-160°	356.5	8.0
160°-170°	236.5	5.3
170°-180°	82.6	1.9
0°-30°	708.8	15.9
0°-40°	1097.2	24.6
0°-60°	1715.5	38.4
0°-90°	2024.2	45.3
90°-120°	520.8	11.7
90°-150°	1765.5	39.5
90°-180°	2441.0	54.7
0°-180°	4465.3	100.0

**CANDELA DISTRIBUTION:**

	0°	90°	180°	270°	360°	Flux
0°	916	916	916	916	916	
5°	1023	918	814	918	1023	102
15°	1257	867	603	867	1257	347
25°	1048	775	484	775	1048	473
35°	570	637	402	637	570	371
45°	344	478	330	478	344	270
55°	242	326	256	326	242	217
65°	148	195	172	195	148	148
75°	73	92	87	92	73	78
85°	19	19	14	19	19	21
90°	25	1	25	1	25	12
95°	46	38	46	38	46	51
105°	164	158	164	158	164	172
115°	295	295	295	295	295	291
125°	430	429	430	429	430	384
135°	561	555	561	555	561	432
145°	681	673	681	673	681	425
155°	776	770	776	770	776	357
165°	838	838	838	838	838	236
175°	869	872	869	872	869	83
180°	873	873	873	873	873	



TEST NUMBER: P331304-830

CATALOG NUMBER: SA2XXDIP-C485D725U830-4F0-1E-UDD-A1

**CANDELA DISTRIBUTION (FULL):**

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	915.9	915.9	915.9	915.9	915.9	915.9	915.9	915.9	915.9	915.9	915.9
2.5°	958.2	958.5	958.9	954.5	953.9	953.9	950.0	946.6	942.6	937.3	937.8
5°	1022.9	1026.8	1028.2	1024.0	1017.7	1016.9	1011.0	1001.1	991.9	984.6	979.3
7.5°	1100.2	1101.7	1098.3	1092.8	1088.1	1079.6	1068.5	1057.5	1042.3	1028.2	1017.9
10°	1158.8	1160.9	1154.9	1146.8	1140.1	1130.3	1114.1	1097.5	1077.5	1058.1	1042.6
12.5°	1203.2	1208.5	1200.8	1199.8	1188.3	1174.8	1155.5	1147.1	1118.9	1091.9	1075.3
15°	1257.4	1257.0	1257.7	1251.0	1242.6	1240.5	1220.0	1197.9	1158.1	1142.3	1114.7
17.5°	1241.7	1247.1	1249.5	1249.4	1249.2	1247.9	1241.3	1227.4	1207.4	1181.8	1150.1
20°	1204.6	1211.5	1212.7	1220.8	1225.3	1231.3	1233.8	1229.9	1217.6	1196.1	1168.7
22.5°	1147.1	1149.1	1152.4	1165.0	1174.9	1189.9	1197.7	1210.7	1206.0	1195.5	1172.6
25°	1047.5	1044.1	1056.3	1062.7	1085.5	1109.5	1126.7	1145.8	1162.6	1172.9	1166.2
27.5°	928.0	922.7	941.2	958.0	976.6	1002.5	1029.4	1061.1	1087.5	1120.6	1131.9
30°	827.2	830.4	848.0	865.9	894.1	930.7	960.9	995.8	1033.5	1070.4	1096.1
32.5°	718.5	730.7	741.8	769.3	794.1	834.9	879.3	922.8	969.9	1011.8	1051.6
35°	570.2	584.3	599.8	619.9	654.7	695.2	738.5	797.3	861.4	918.7	965.9
37.5°	479.9	477.8	486.6	501.1	529.3	562.0	611.8	670.0	745.4	812.8	879.3
40°	425.9	424.5	430.8	444.2	465.7	489.7	533.3	584.3	654.4	736.7	816.0
42.5°	388.7	389.6	393.1	402.6	417.3	437.0	469.7	513.1	577.2	654.8	739.9
45°	343.6	346.0	349.9	354.5	362.9	379.1	397.4	428.4	479.1	543.8	627.6
47.5°	311.0	311.1	315.0	319.1	324.0	333.2	348.2	367.6	403.3	456.1	528.1
50°	293.6	291.1	293.9	297.1	302.4	308.7	318.6	336.9	360.8	403.4	463.5
52.5°	272.2	272.2	274.8	276.0	280.7	287.0	296.1	308.7	330.4	363.7	413.2
55°	241.5	243.3	244.7	246.8	251.0	255.5	262.6	271.1	287.9	312.9	349.5
57.5°	212.6	213.2	214.6	218.6	221.3	225.5	232.1	239.9	250.8	269.4	296.9
60°	192.9	192.9	195.7	197.5	201.0	205.2	210.5	217.9	227.7	242.9	265.0
62.5°	174.8	174.6	175.7	178.6	181.3	185.2	190.5	196.8	206.0	219.5	237.7
65°	148.5	147.9	150.0	150.6	153.4	157.3	161.6	168.2	175.7	185.5	201.7
67.5°	123.2	124.0	125.2	126.5	128.1	132.1	135.0	139.7	145.9	154.1	165.1
70°	109.1	109.1	109.1	110.2	112.3	114.4	117.3	121.1	127.1	134.1	143.9
72.5°	93.3	94.4	95.6	95.0	97.6	98.9	102.3	104.4	110.2	114.7	123.4
75°	73.2	73.2	73.2	74.9	76.1	77.1	79.2	81.3	84.2	89.7	94.3
77.5°	54.7	54.5	54.9	55.2	56.4	57.7	58.2	60.2	62.8	65.4	69.3
80°	42.2	43.0	43.3	44.0	44.0	44.7	45.1	47.5	49.3	51.1	53.5
82.5°	32.7	32.8	32.9	33.0	33.3	33.7	34.6	35.4	36.0	37.5	39.4
85°	19.0	18.7	18.7	19.3	19.0	19.0	19.7	20.5	20.5	20.7	21.9
87.5°	12.3	12.3	12.5	12.3	12.2	12.5	12.5	12.3	12.7	13.0	12.6
90°	25.1	24.9	24.7	24.6	24.4	24.5	24.8	25.2	25.4	25.8	22.1
92.5°	23.8	23.8	23.8	23.8	23.8	23.7	23.7	23.6	23.5	23.5	22.6
95°	45.7	46.0	46.4	46.7	47.0	47.1	47.1	47.1	47.1	47.1	46.8
97.5°	79.1	79.2	79.2	79.3	79.3	79.3	79.3	79.3	79.3	79.3	78.6
100°	100.9	101.1	101.2	101.4	101.6	101.7	101.7	101.7	101.7	101.7	101.1
102.5°	125.6	125.8	126.0	126.2	126.3	126.4	126.2	126.1	125.9	125.8	125.2
105°	163.5	163.5	163.5	163.5	163.5	163.4	163.1	162.8	162.4	162.1	161.7
107.5°	199.3	200.0	200.8	201.5	202.3	202.6	202.4	202.3	202.2	202.0	202.0
110°	226.9	227.4	227.9	228.4	228.8	229.1	229.1	229.1	229.1	229.1	229.1



TEST NUMBER: P331304-830

CATALOG NUMBER: SA2XXDIP-C485D725U830-4F0-1E-UDD-A1

**CANDELA DISTRIBUTION (continued):**

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	253.4	253.8	254.1	254.5	254.9	255.2	255.6	256.0	256.5	256.8	256.9
115°	294.7	295.2	295.7	296.1	296.6	297.0	297.2	297.3	297.5	297.7	297.9
117.5°	334.0	334.5	335.0	335.5	336.0	336.4	336.9	337.2	337.6	338.0	338.9
120°	361.7	362.2	362.7	363.2	363.7	363.9	363.9	363.9	363.9	363.9	365.2
122.5°	388.9	389.2	389.6	389.9	390.3	390.7	391.1	391.4	391.8	392.2	393.1
125°	430.3	430.5	430.6	430.7	430.9	431.2	431.7	432.3	432.7	433.2	433.7
127.5°	468.0	468.5	469.0	469.6	470.0	470.6	471.2	471.8	472.4	473.0	473.5
130°	495.1	495.8	496.4	497.0	497.7	498.2	498.5	498.9	499.2	499.5	499.8
132.5°	521.0	521.5	522.1	522.5	523.1	523.8	524.4	525.2	525.9	526.6	526.5
135°	561.4	561.8	562.4	562.9	563.4	563.6	563.8	564.0	564.2	564.3	564.0
137.5°	597.9	598.6	599.3	599.9	600.6	601.0	601.1	601.2	601.3	601.4	601.1
140°	623.3	624.0	624.6	625.3	625.8	626.2	626.2	626.2	626.2	626.2	625.4
142.5°	646.3	647.0	647.5	648.2	648.8	649.1	649.0	648.8	648.8	648.7	648.1
145°	680.7	681.4	682.0	682.7	683.3	683.6	683.4	683.2	683.2	683.0	681.9
147.5°	711.5	712.2	712.8	713.4	714.1	714.2	713.8	713.4	713.0	712.8	712.1
150°	731.6	732.1	732.5	733.0	733.6	733.6	733.0	732.5	732.1	731.6	730.9
152.5°	750.5	751.0	751.7	752.3	752.9	752.9	752.3	751.7	751.0	750.5	749.6
155°	775.8	776.3	776.7	777.2	777.8	777.6	776.7	775.9	775.1	774.3	773.8
157.5°	797.6	798.3	799.2	799.9	800.7	800.6	799.5	798.3	797.2	796.1	795.8
160°	811.2	811.8	812.5	813.1	813.8	813.6	812.7	811.6	810.7	809.6	809.5
162.5°	822.9	823.7	824.5	825.3	826.0	826.0	824.8	823.7	822.6	821.4	821.3
165°	838.4	839.2	840.0	840.8	841.7	841.5	840.4	839.2	838.1	836.9	836.9
167.5°	851.1	852.0	852.8	853.7	854.5	854.3	853.2	852.1	850.9	849.7	849.8
170°	857.5	858.6	859.5	860.5	861.5	861.4	860.3	859.1	858.0	856.8	857.0
172.5°	862.9	863.8	864.8	865.8	866.8	866.7	865.5	864.4	863.3	862.1	862.3
175°	868.6	869.6	870.5	871.6	872.5	872.4	871.3	870.2	869.0	867.9	868.2
177.5°	871.3	872.0	872.8	873.6	874.4	874.4	873.6	872.8	872.0	871.3	871.5
180°	873.0	873.0	873.0	873.0	873.0	873.0	873.0	873.0	873.0	873.0	873.0



TEST NUMBER: P331304-830

CATALOG NUMBER: SA2XXDIP-C485D725U830-4F0-1E-UDD-A1

**CANDELA DISTRIBUTION (continued):**

	55°	60°	65°	70°	75°	80°	85°	90°	95°	100°	105°
0°	915.9	915.9	915.9	915.9	915.9	915.9	915.9	915.9	915.9	915.9	915.9
2.5°	939.8	937.5	936.1	931.1	926.6	922.1	920.7	921.2	915.0	909.2	906.6
5°	976.5	969.4	962.7	953.2	942.0	929.6	923.3	918.4	906.1	892.7	885.0
7.5°	1009.3	999.2	986.3	968.5	952.1	932.6	920.3	909.5	891.4	872.5	861.0
10°	1029.3	1015.5	999.0	977.1	957.1	933.5	917.0	900.4	879.3	856.8	842.7
12.5°	1046.4	1027.9	1011.6	983.6	959.9	930.4	910.8	887.5	865.3	838.5	824.6
15°	1087.3	1053.2	1022.2	990.5	961.3	920.1	898.3	867.0	837.7	804.6	788.8
17.5°	1118.9	1080.5	1031.8	991.6	957.4	911.8	879.8	842.3	807.7	769.9	748.4
20°	1137.0	1093.0	1040.5	992.7	951.8	899.8	864.9	826.5	786.0	743.4	720.2
22.5°	1147.6	1101.5	1049.5	988.4	940.6	889.9	846.0	804.0	762.9	717.0	692.6
25°	1151.0	1108.8	1053.9	984.9	926.4	869.1	816.2	775.4	725.9	682.9	647.3
27.5°	1134.3	1104.0	1051.2	978.3	910.2	843.1	784.3	738.0	685.6	639.0	603.2
30°	1113.7	1096.1	1044.7	971.5	897.2	825.1	760.3	707.8	655.8	608.6	572.0
32.5°	1081.9	1078.1	1032.9	962.0	883.4	802.3	735.3	682.2	624.5	578.2	543.3
35°	1019.4	1036.3	1007.8	940.6	857.4	769.9	697.3	636.8	576.9	532.5	499.8
37.5°	935.7	977.6	970.2	909.2	822.4	734.5	654.4	591.2	534.1	489.4	457.2
40°	877.9	931.4	939.1	885.2	797.7	707.2	622.4	559.3	503.7	462.9	430.5
42.5°	816.0	878.4	899.8	856.6	770.6	678.4	593.6	528.4	473.3	433.6	404.9
45°	712.1	794.8	833.2	808.5	725.5	631.1	543.8	477.7	427.7	390.4	368.2
47.5°	615.0	705.4	757.1	748.3	675.2	581.8	495.6	432.1	383.4	353.6	333.8
50°	546.3	639.2	701.5	704.4	639.2	546.7	460.1	400.2	355.5	327.7	311.5
52.5°	486.6	575.3	643.3	658.2	599.0	510.0	428.2	368.7	329.3	303.8	289.3
55°	408.7	483.6	559.0	586.4	538.9	454.4	378.7	326.3	289.4	271.7	259.1
57.5°	339.8	402.3	471.8	502.2	472.9	400.6	329.6	284.1	254.1	238.7	228.9
60°	303.4	352.7	414.6	450.9	425.6	361.2	299.2	255.9	231.3	217.5	208.4
62.5°	269.7	313.3	365.6	398.8	385.0	324.2	268.8	230.5	209.3	196.4	189.8
65°	222.4	256.9	297.5	328.1	319.0	272.8	227.4	194.6	177.8	167.6	162.3
67.5°	183.1	208.1	236.2	263.0	255.6	222.9	186.5	161.0	148.4	139.6	136.5
70°	158.4	177.4	202.4	223.9	217.9	191.1	162.3	140.4	129.5	122.2	118.9
72.5°	134.8	150.3	169.5	187.0	182.9	160.7	136.7	120.2	111.8	105.0	102.4
75°	101.7	113.7	125.4	137.0	135.9	118.7	104.5	91.9	85.2	79.9	78.9
77.5°	75.1	81.8	89.7	96.6	94.7	84.8	73.8	66.5	61.6	58.1	57.5
80°	57.4	61.3	66.9	71.8	69.4	65.1	56.4	51.1	47.5	44.0	42.6
82.5°	41.6	45.5	48.8	51.6	49.7	45.7	40.2	36.7	34.6	32.1	31.6
85°	21.9	23.9	25.4	26.0	25.4	22.9	20.5	19.0	17.2	16.2	15.8
87.5°	12.2	11.4	10.7	10.7	9.5	9.1	7.5	6.3	6.4	6.6	6.4
90°	18.6	15.0	11.4	8.6	6.6	4.7	2.7	0.8	2.7	4.7	6.6
92.5°	21.7	20.8	20.0	18.9	17.4	16.0	14.5	13.1	14.5	16.0	17.4
95°	46.5	46.2	45.8	44.9	43.3	41.6	40.0	38.3	40.0	41.6	43.3
97.5°	78.0	77.4	76.8	75.8	74.3	72.9	71.4	70.0	71.4	72.9	74.3
100°	100.7	100.2	99.7	98.8	97.5	96.1	94.9	93.6	94.9	96.1	97.5
102.5°	124.6	123.9	123.4	122.5	121.5	120.5	119.3	118.3	119.3	120.5	121.5
105°	161.5	161.1	160.8	160.3	159.9	159.4	158.9	158.4	158.9	159.4	159.9
107.5°	202.0	202.0	202.0	201.6	201.0	200.2	199.5	198.8	199.5	200.2	201.0
110°	229.1	229.1	229.1	228.7	227.6	226.7	225.6	224.7	225.6	226.7	227.6





TEST NUMBER: P331304-830

CATALOG NUMBER: SA2XXDIP-C485D725U830-4F0-1E-UDD-A1

**CANDELA DISTRIBUTION (continued):**

	55°	60°	65°	70°	75°	80°	85°	90°	95°	100°	105°
112.5°	257.1	257.2	257.3	256.9	255.9	255.0	254.0	253.0	254.0	255.0	255.9
115°	298.3	298.6	299.0	298.6	297.7	296.6	295.7	294.7	295.7	296.6	297.7
117.5°	339.9	340.7	341.7	341.5	340.2	338.8	337.5	336.2	337.5	338.8	340.2
120°	366.6	367.9	369.2	369.2	367.9	366.6	365.2	363.9	365.2	366.6	367.9
122.5°	394.1	395.0	395.9	395.6	394.0	392.5	390.9	389.3	390.9	392.5	394.0
125°	434.1	434.7	435.2	434.7	433.2	431.7	430.3	428.8	430.3	431.7	433.2
127.5°	474.2	474.8	475.3	474.7	472.9	471.0	469.1	467.2	469.1	471.0	472.9
130°	500.1	500.5	500.8	499.9	497.8	495.7	493.5	491.4	493.5	495.7	497.8
132.5°	526.5	526.4	526.3	525.5	523.7	522.0	520.3	518.5	520.3	522.0	523.7
135°	563.6	563.4	563.0	561.9	560.2	558.4	556.6	554.8	556.6	558.4	560.2
137.5°	600.6	600.2	599.7	598.8	597.4	595.9	594.4	593.0	594.4	595.9	597.4
140°	624.6	623.8	622.9	621.8	620.3	618.9	617.4	616.0	617.4	618.9	620.3
142.5°	647.5	647.0	646.4	645.4	643.9	642.4	640.9	639.5	640.9	642.4	643.9
145°	681.0	680.0	679.0	678.0	676.8	675.7	674.5	673.4	674.5	675.7	676.8
147.5°	711.4	710.8	710.1	709.1	707.7	706.3	704.9	703.6	704.9	706.3	707.7
150°	730.3	729.6	729.0	728.1	727.2	726.1	725.2	724.2	725.2	726.1	727.2
152.5°	748.9	748.1	747.2	746.4	745.5	744.4	743.5	742.4	743.5	744.4	745.5
155°	773.4	772.8	772.3	771.8	771.4	770.9	770.3	769.9	770.3	770.9	771.4
157.5°	795.5	795.2	794.9	794.7	794.3	794.0	793.6	793.3	793.6	794.0	794.3
160°	809.4	809.2	809.0	808.8	808.4	808.1	807.8	807.5	807.8	808.1	808.4
162.5°	821.1	821.0	820.8	820.7	820.6	820.6	820.5	820.4	820.5	820.6	820.6
165°	836.9	836.9	836.9	837.0	837.2	837.4	837.5	837.6	837.5	837.4	837.2
167.5°	849.8	849.9	849.9	850.2	850.6	851.1	851.6	852.1	851.6	851.1	850.6
170°	857.1	857.3	857.4	857.8	858.3	858.8	859.3	859.8	859.3	858.8	858.3
172.5°	862.4	862.6	862.8	863.1	863.6	864.1	864.6	865.1	864.6	864.1	863.6
175°	868.6	868.8	869.2	869.6	870.1	870.5	871.1	871.6	871.1	870.5	870.1
177.5°	871.8	872.0	872.3	872.6	873.0	873.5	873.8	874.2	873.8	873.5	873.0
180°	873.0	873.0	873.0	873.0	873.0	873.0	873.0	873.0	873.0	873.0	873.0



TEST NUMBER: P331304-830

CATALOG NUMBER: SA2XXDIP-C485D725U830-4F0-1E-UDD-A1

**CANDELA DISTRIBUTION (continued):**

	110°	115°	120°	125°	130°	135°	140°	145°	150°	155°	160°
0°	915.9	915.9	915.9	915.9	915.9	915.9	915.9	915.9	915.9	915.9	915.9
2.5°	903.8	902.1	896.2	893.1	888.1	883.3	880.1	881.6	882.7	882.1	881.3
5°	877.9	871.2	861.0	852.2	845.8	834.2	829.3	826.9	824.7	822.3	819.8
7.5°	847.1	836.5	821.9	809.4	797.5	783.1	774.9	769.9	764.8	759.2	754.3
10°	825.1	810.3	794.8	777.2	763.2	750.1	738.5	730.8	723.7	717.0	712.1
12.5°	802.0	784.9	765.8	741.8	726.2	707.6	705.9	692.2	681.2	677.0	671.3
15°	765.3	741.3	717.0	688.5	676.2	659.3	648.8	638.2	628.7	622.0	620.2
17.5°	723.5	692.5	668.4	647.9	627.7	610.4	600.7	592.2	584.4	575.4	574.3
20°	691.6	665.0	638.6	620.6	599.8	582.2	570.2	561.8	555.1	549.8	545.3
22.5°	661.6	632.3	608.1	588.4	568.0	553.7	544.3	536.2	530.7	524.8	520.5
25°	613.2	590.3	563.9	541.8	524.8	515.7	507.9	500.9	497.4	493.5	488.6
27.5°	570.9	545.4	520.8	503.6	488.7	480.6	475.1	470.3	467.0	464.8	461.9
30°	541.0	515.3	496.0	479.1	466.7	458.6	455.2	452.3	448.5	447.0	445.6
32.5°	512.3	489.2	472.6	458.0	446.2	440.9	437.7	435.2	432.2	430.7	427.9
35°	471.6	452.3	436.1	428.0	418.5	414.0	411.5	407.9	405.2	403.8	403.4
37.5°	433.5	416.6	406.0	395.6	391.5	388.7	385.4	383.0	382.1	381.9	381.5
40°	408.7	394.9	385.4	377.0	375.2	371.0	368.2	366.1	366.1	366.5	366.1
42.5°	386.2	373.8	365.4	358.2	356.1	353.5	350.7	350.6	351.2	352.3	351.2
45°	352.0	343.2	337.2	333.7	329.8	327.3	327.0	328.1	328.4	328.8	329.8
47.5°	320.6	314.7	309.3	305.5	303.8	303.3	302.9	304.7	306.4	307.1	308.7
50°	302.0	295.3	290.8	288.3	286.9	286.2	286.9	289.0	290.4	292.2	293.2
52.5°	281.2	276.4	273.3	271.4	270.8	271.3	271.4	273.8	276.1	276.6	277.2
55°	252.4	248.8	248.2	245.0	246.4	246.0	247.8	249.2	251.3	253.4	253.8
57.5°	223.7	220.8	219.0	219.2	219.6	221.2	222.6	225.2	227.4	229.6	229.9
60°	204.5	203.1	202.1	202.1	202.7	204.9	206.6	209.1	210.5	211.9	212.9
62.5°	187.1	185.7	184.5	185.1	187.0	188.2	190.3	191.6	193.0	194.4	194.9
65°	159.5	158.7	159.9	160.5	160.9	162.6	165.1	166.2	167.6	168.2	170.7
67.5°	134.0	134.2	134.0	135.1	137.0	137.5	139.8	142.3	142.6	143.9	145.5
70°	116.9	117.5	118.3	118.9	120.7	121.4	123.2	124.2	125.6	126.7	127.8
72.5°	101.1	101.2	102.0	101.8	103.3	104.8	106.3	107.4	108.8	110.1	111.1
75°	77.8	77.8	78.5	78.9	80.6	82.4	82.0	82.8	84.2	85.6	86.2
77.5°	56.8	56.1	56.8	57.1	57.7	59.2	59.5	60.5	62.1	61.6	62.4
80°	43.3	42.2	43.3	43.6	43.6	45.4	45.4	46.1	47.1	46.1	47.1
82.5°	30.9	30.4	31.2	31.3	31.9	31.9	32.4	32.6	33.6	33.2	33.6
85°	15.5	15.2	15.5	15.2	15.5	15.8	15.8	15.5	15.5	16.2	15.2
87.5°	6.5	6.8	7.3	7.9	8.4	8.9	8.5	8.4	8.3	7.7	7.7
90°	8.6	11.4	15.0	18.6	22.1	25.8	25.4	25.2	24.8	24.5	24.4
92.5°	18.9	20.0	20.8	21.7	22.6	23.5	23.5	23.6	23.7	23.7	23.8
95°	44.9	45.8	46.2	46.5	46.8	47.1	47.1	47.1	47.1	47.1	47.0
97.5°	75.8	76.8	77.4	78.0	78.6	79.3	79.3	79.3	79.3	79.3	79.3
100°	98.8	99.7	100.2	100.7	101.1	101.7	101.7	101.7	101.7	101.7	101.6
102.5°	122.5	123.4	123.9	124.6	125.2	125.8	125.9	126.1	126.2	126.4	126.3
105°	160.3	160.8	161.1	161.5	161.7	162.1	162.4	162.8	163.1	163.4	163.5
107.5°	201.6	202.0	202.0	202.0	202.0	202.0	202.2	202.3	202.4	202.6	202.3
110°	228.7	229.1	229.1	229.1	229.1	229.1	229.1	229.1	229.1	229.1	228.8



TEST NUMBER: P331304-830

CATALOG NUMBER: SA2XXDIP-C485D725U830-4F0-1E-UDD-A1

**CANDELA DISTRIBUTION (continued):**

	110°	115°	120°	125°	130°	135°	140°	145°	150°	155°	160°
112.5°	256.9	257.3	257.2	257.1	256.9	256.8	256.5	256.0	255.6	255.2	254.9
115°	298.6	299.0	298.6	298.3	297.9	297.7	297.5	297.3	297.2	297.0	296.6
117.5°	341.5	341.7	340.7	339.9	338.9	338.0	337.6	337.2	336.9	336.4	336.0
120°	369.2	369.2	367.9	366.6	365.2	363.9	363.9	363.9	363.9	363.9	363.7
122.5°	395.6	395.9	395.0	394.1	393.1	392.2	391.8	391.4	391.1	390.7	390.3
125°	434.7	435.2	434.7	434.1	433.7	433.2	432.7	432.3	431.7	431.2	430.9
127.5°	474.7	475.3	474.8	474.2	473.5	473.0	472.4	471.8	471.2	470.6	470.0
130°	499.9	500.8	500.5	500.1	499.8	499.5	499.2	498.9	498.5	498.2	497.7
132.5°	525.5	526.3	526.4	526.5	526.5	526.6	525.9	525.2	524.4	523.8	523.1
135°	561.9	563.0	563.4	563.6	564.0	564.3	564.2	564.0	563.8	563.6	563.4
137.5°	598.8	599.7	600.2	600.6	601.1	601.4	601.3	601.2	601.1	601.0	600.6
140°	621.8	622.9	623.8	624.6	625.4	626.2	626.2	626.2	626.2	626.2	625.8
142.5°	645.4	646.4	647.0	647.5	648.1	648.7	648.8	648.8	649.0	649.1	648.8
145°	678.0	679.0	680.0	681.0	681.9	683.0	683.2	683.2	683.4	683.6	683.3
147.5°	709.1	710.1	710.8	711.4	712.1	712.8	713.0	713.4	713.8	714.2	714.1
150°	728.1	729.0	729.6	730.3	730.9	731.6	732.1	732.5	733.0	733.6	733.6
152.5°	746.4	747.2	748.1	748.9	749.6	750.5	751.0	751.7	752.3	752.9	752.9
155°	771.8	772.3	772.8	773.4	773.8	774.3	775.1	775.9	776.7	777.6	777.8
157.5°	794.7	794.9	795.2	795.5	795.8	796.1	797.2	798.3	799.5	800.6	800.7
160°	808.8	809.0	809.2	809.4	809.5	809.6	810.7	811.6	812.7	813.6	813.8
162.5°	820.7	820.8	821.0	821.1	821.3	821.4	822.6	823.7	824.8	826.0	826.0
165°	837.0	836.9	836.9	836.9	836.9	836.9	838.1	839.2	840.4	841.5	841.7
167.5°	850.2	849.9	849.9	849.8	849.8	849.7	850.9	852.1	853.2	854.3	854.5
170°	857.8	857.4	857.3	857.1	857.0	856.8	858.0	859.1	860.3	861.4	861.5
172.5°	863.1	862.8	862.6	862.4	862.3	862.1	863.3	864.4	865.5	866.7	866.8
175°	869.6	869.2	868.8	868.6	868.2	867.9	869.0	870.2	871.3	872.4	872.5
177.5°	872.6	872.3	872.0	871.8	871.5	871.3	872.0	872.8	873.6	874.4	874.4
180°	873.0	873.0	873.0	873.0	873.0	873.0	873.0	873.0	873.0	873.0	873.0



TEST NUMBER: P331304-830  
 CATALOG NUMBER: SA2XXDIP-C485D725U830-4F0-1E-UDD-A1

**CANDELA DISTRIBUTION (continued):**

	165°	170°	175°	180°	185°	190°	195°	200°	205°	210°	215°
0°	915.9	915.9	915.9	915.9	915.9	915.9	915.9	915.9	915.9	915.9	915.9
2.5°	878.4	877.9	877.9	875.3	877.9	877.9	878.4	881.3	882.1	882.7	881.6
5°	814.9	813.8	812.1	813.8	812.1	813.8	814.9	819.8	822.3	824.7	826.9
7.5°	752.1	747.8	747.2	743.0	747.2	747.8	752.1	754.3	759.2	764.8	769.9
10°	706.2	703.3	702.9	696.3	702.9	703.3	706.2	712.1	717.0	723.7	730.8
12.5°	671.2	664.4	665.8	661.9	665.8	664.4	671.2	671.3	677.0	681.2	692.2
15°	610.7	610.7	609.4	603.3	609.4	610.7	610.7	620.2	622.0	628.7	638.2
17.5°	567.3	566.6	563.2	564.9	563.2	566.6	567.3	574.3	575.4	584.4	592.2
20°	541.4	539.2	535.1	535.1	535.1	539.2	541.4	545.3	549.8	555.1	561.8
22.5°	516.9	516.7	512.3	513.7	512.3	516.7	516.9	520.5	524.8	530.7	536.2
25°	488.2	485.4	483.3	484.4	483.3	485.4	488.2	488.6	493.5	497.4	500.9
27.5°	461.1	459.5	459.4	456.5	459.4	459.5	461.1	461.9	464.8	467.0	470.3
30°	445.3	441.8	442.4	440.7	442.4	441.8	445.3	445.6	447.0	448.5	452.3
32.5°	427.3	426.0	425.3	423.8	425.3	426.0	427.3	427.9	430.7	432.2	435.2
35°	402.7	403.0	401.2	402.0	401.2	403.0	402.7	403.4	403.8	405.2	407.9
37.5°	381.3	382.4	381.5	381.7	381.5	382.4	381.3	381.5	381.9	382.1	383.0
40°	367.1	367.1	367.1	368.2	367.1	367.1	367.1	366.1	366.5	366.1	366.1
42.5°	353.6	353.1	352.5	352.4	352.5	353.1	353.6	351.2	352.3	351.2	350.6
45°	330.5	331.6	332.0	330.2	332.0	331.6	330.5	329.8	328.8	328.4	328.1
47.5°	309.6	309.7	309.6	311.1	309.6	309.7	309.6	308.7	307.1	306.4	304.7
50°	295.0	294.3	295.0	294.3	295.0	294.3	295.0	293.2	292.2	290.4	289.0
52.5°	279.5	279.7	279.2	279.1	279.2	279.7	279.5	277.2	276.6	276.1	273.8
55°	255.2	255.9	255.5	255.5	255.5	255.9	255.2	253.8	253.4	251.3	249.2
57.5°	230.1	230.7	231.2	229.6	231.2	230.7	230.1	229.9	229.6	227.4	225.2
60°	212.6	214.3	214.1	213.3	214.1	214.3	212.6	212.9	211.9	210.5	209.1
62.5°	196.5	197.2	197.1	197.0	197.1	197.2	196.5	194.9	194.4	193.0	191.6
65°	171.7	172.5	171.4	172.5	171.4	172.5	171.7	170.7	168.2	167.6	166.2
67.5°	145.1	145.3	146.1	146.6	146.1	145.3	145.1	145.5	143.9	142.6	142.3
70°	128.5	128.1	129.2	130.3	129.2	128.1	128.5	127.8	126.7	125.6	124.2
72.5°	111.0	111.8	111.4	112.3	111.4	111.8	111.0	111.1	110.1	108.8	107.4
75°	85.6	86.6	86.2	87.3	86.2	86.6	85.6	86.2	85.6	84.2	82.8
77.5°	61.8	61.9	61.8	62.4	61.8	61.9	61.8	62.4	61.6	62.1	60.5
80°	47.1	46.5	45.7	47.1	45.7	46.5	47.1	47.1	46.1	47.1	46.1
82.5°	32.8	33.3	32.5	32.5	32.5	33.3	32.8	33.6	33.2	33.6	32.6
85°	15.2	14.8	14.0	14.0	14.0	14.8	15.2	15.2	16.2	15.5	15.5
87.5°	7.7	7.4	7.5	7.3	7.5	7.4	7.7	7.7	7.7	8.3	8.4
90°	24.6	24.7	24.9	25.1	24.9	24.7	24.6	24.4	24.5	24.8	25.2
92.5°	23.8	23.8	23.8	23.8	23.8	23.8	23.8	23.8	23.7	23.7	23.6
95°	46.7	46.4	46.0	45.7	46.0	46.4	46.7	47.0	47.1	47.1	47.1
97.5°	79.3	79.2	79.2	79.1	79.2	79.2	79.3	79.3	79.3	79.3	79.3
100°	101.4	101.2	101.1	100.9	101.1	101.2	101.4	101.6	101.7	101.7	101.7
102.5°	126.2	126.0	125.8	125.6	125.8	126.0	126.2	126.3	126.4	126.2	126.1
105°	163.5	163.5	163.5	163.5	163.5	163.5	163.5	163.5	163.4	163.1	162.8
107.5°	201.5	200.8	200.0	199.3	200.0	200.8	201.5	202.3	202.6	202.4	202.3
110°	228.4	227.9	227.4	226.9	227.4	227.9	228.4	228.8	229.1	229.1	229.1



TEST NUMBER: P331304-830

CATALOG NUMBER: SA2XXDIP-C485D725U830-4F0-1E-UDD-A1

**CANDELA DISTRIBUTION (continued):**

	165°	170°	175°	180°	185°	190°	195°	200°	205°	210°	215°
112.5°	254.5	254.1	253.8	253.4	253.8	254.1	254.5	254.9	255.2	255.6	256.0
115°	296.1	295.7	295.2	294.7	295.2	295.7	296.1	296.6	297.0	297.2	297.3
117.5°	335.5	335.0	334.5	334.0	334.5	335.0	335.5	336.0	336.4	336.9	337.2
120°	363.2	362.7	362.2	361.7	362.2	362.7	363.2	363.7	363.9	363.9	363.9
122.5°	389.9	389.6	389.2	388.9	389.2	389.6	389.9	390.3	390.7	391.1	391.4
125°	430.7	430.6	430.5	430.3	430.5	430.6	430.7	430.9	431.2	431.7	432.3
127.5°	469.6	469.0	468.5	468.0	468.5	469.0	469.6	470.0	470.6	471.2	471.8
130°	497.0	496.4	495.8	495.1	495.8	496.4	497.0	497.7	498.2	498.5	498.9
132.5°	522.5	522.1	521.5	521.0	521.5	522.1	522.5	523.1	523.8	524.4	525.2
135°	562.9	562.4	561.8	561.4	561.8	562.4	562.9	563.4	563.6	563.8	564.0
137.5°	599.9	599.3	598.6	597.9	598.6	599.3	599.9	600.6	601.0	601.1	601.2
140°	625.3	624.6	624.0	623.3	624.0	624.6	625.3	625.8	626.2	626.2	626.2
142.5°	648.2	647.5	647.0	646.3	647.0	647.5	648.2	648.8	649.1	649.0	648.8
145°	682.7	682.0	681.4	680.7	681.4	682.0	682.7	683.3	683.6	683.4	683.2
147.5°	713.4	712.8	712.2	711.5	712.2	712.8	713.4	714.1	714.2	713.8	713.4
150°	733.0	732.5	732.1	731.6	732.1	732.5	733.0	733.6	733.6	733.0	732.5
152.5°	752.3	751.7	751.0	750.5	751.0	751.7	752.3	752.9	752.9	752.3	751.7
155°	777.2	776.7	776.3	775.8	776.3	776.7	777.2	777.8	777.6	776.7	775.9
157.5°	799.9	799.2	798.3	797.6	798.3	799.2	799.9	800.7	800.6	799.5	798.3
160°	813.1	812.5	811.8	811.2	811.8	812.5	813.1	813.8	813.6	812.7	811.6
162.5°	825.3	824.5	823.7	822.9	823.7	824.5	825.3	826.0	826.0	824.8	823.7
165°	840.8	840.0	839.2	838.4	839.2	840.0	840.8	841.7	841.5	840.4	839.2
167.5°	853.7	852.8	852.0	851.1	852.0	852.8	853.7	854.5	854.3	853.2	852.1
170°	860.5	859.5	858.6	857.5	858.6	859.5	860.5	861.5	861.4	860.3	859.1
172.5°	865.8	864.8	863.8	862.9	863.8	864.8	865.8	866.8	866.7	865.5	864.4
175°	871.6	870.5	869.6	868.6	869.6	870.5	871.6	872.5	872.4	871.3	870.2
177.5°	873.6	872.8	872.0	871.3	872.0	872.8	873.6	874.4	874.4	873.6	872.8
180°	873.0	873.0	873.0	873.0	873.0	873.0	873.0	873.0	873.0	873.0	873.0



TEST NUMBER: P331304-830

CATALOG NUMBER: SA2XXDIP-C485D725U830-4F0-1E-UDD-A1

**CANDELA DISTRIBUTION (continued):**

	220°	225°	230°	235°	240°	245°	250°	255°	260°	265°	270°
0°	915.9	915.9	915.9	915.9	915.9	915.9	915.9	915.9	915.9	915.9	915.9
2.5°	880.1	883.3	888.1	893.1	896.2	902.1	903.8	906.6	909.2	915.0	921.2
5°	829.3	834.2	845.8	852.2	861.0	871.2	877.9	885.0	892.7	906.1	918.4
7.5°	774.9	783.1	797.5	809.4	821.9	836.5	847.1	861.0	872.5	891.4	909.5
10°	738.5	750.1	763.2	777.2	794.8	810.3	825.1	842.7	856.8	879.3	900.4
12.5°	705.9	707.6	726.2	741.8	765.8	784.9	802.0	824.6	838.5	865.3	887.5
15°	648.8	659.3	676.2	688.5	717.0	741.3	765.3	788.8	804.6	837.7	867.0
17.5°	600.7	610.4	627.7	647.9	668.4	692.5	723.5	748.4	769.9	807.7	842.3
20°	570.2	582.2	599.8	620.6	638.6	665.0	691.6	720.2	743.4	786.0	826.5
22.5°	544.3	553.7	568.0	588.4	608.1	632.3	661.6	692.6	717.0	762.9	804.0
25°	507.9	515.7	524.8	541.8	563.9	590.3	613.2	647.3	682.9	725.9	775.4
27.5°	475.1	480.6	488.7	503.6	520.8	545.4	570.9	603.2	639.0	685.6	738.0
30°	455.2	458.6	466.7	479.1	496.0	515.3	541.0	572.0	608.6	655.8	707.8
32.5°	437.7	440.9	446.2	458.0	472.6	489.2	512.3	543.3	578.2	624.5	682.2
35°	411.5	414.0	418.5	428.0	436.1	452.3	471.6	499.8	532.5	576.9	636.8
37.5°	385.4	388.7	391.5	395.6	406.0	416.6	433.5	457.2	489.4	534.1	591.2
40°	368.2	371.0	375.2	377.0	385.4	394.9	408.7	430.5	462.9	503.7	559.3
42.5°	350.7	353.5	356.1	358.2	365.4	373.8	386.2	404.9	433.6	473.3	528.4
45°	327.0	327.3	329.8	333.7	337.2	343.2	352.0	368.2	390.4	427.7	477.7
47.5°	302.9	303.3	303.8	305.5	309.3	314.7	320.6	333.8	353.6	383.4	432.1
50°	286.9	286.2	286.9	288.3	290.8	295.3	302.0	311.5	327.7	355.5	400.2
52.5°	271.4	271.3	270.8	271.4	273.3	276.4	281.2	289.3	303.8	329.3	368.7
55°	247.8	246.0	246.4	245.0	248.2	248.8	252.4	259.1	271.7	289.4	326.3
57.5°	222.6	221.2	219.6	219.2	219.0	220.8	223.7	228.9	238.7	254.1	284.1
60°	206.6	204.9	202.7	202.1	202.1	203.1	204.5	208.4	217.5	231.3	255.9
62.5°	190.3	188.2	187.0	185.1	184.5	185.7	187.1	189.8	196.4	209.3	230.5
65°	165.1	162.6	160.9	160.5	159.9	158.7	159.5	162.3	167.6	177.8	194.6
67.5°	139.8	137.5	137.0	135.1	134.0	134.2	134.0	136.5	139.6	148.4	161.0
70°	123.2	121.4	120.7	118.9	118.3	117.5	116.9	118.9	122.2	129.5	140.4
72.5°	106.3	104.8	103.3	101.8	102.0	101.2	101.1	102.4	105.0	111.8	120.2
75°	82.0	82.4	80.6	78.9	78.5	77.8	77.8	78.9	79.9	85.2	91.9
77.5°	59.5	59.2	57.7	57.1	56.8	56.1	56.8	57.5	58.1	61.6	66.5
80°	45.4	45.4	43.6	43.6	43.3	42.2	43.3	42.6	44.0	47.5	51.1
82.5°	32.4	31.9	31.9	31.3	31.2	30.4	30.9	31.6	32.1	34.6	36.7
85°	15.8	15.8	15.5	15.2	15.5	15.2	15.5	15.8	16.2	17.2	19.0
87.5°	8.5	8.9	8.4	7.9	7.3	6.8	6.5	6.4	6.6	6.4	6.3
90°	25.4	25.8	22.1	18.6	15.0	11.4	8.6	6.6	4.7	2.7	0.8
92.5°	23.5	23.5	22.6	21.7	20.8	20.0	18.9	17.4	16.0	14.5	13.1
95°	47.1	47.1	46.8	46.5	46.2	45.8	44.9	43.3	41.6	40.0	38.3
97.5°	79.3	79.3	78.6	78.0	77.4	76.8	75.8	74.3	72.9	71.4	70.0
100°	101.7	101.7	101.1	100.7	100.2	99.7	98.8	97.5	96.1	94.9	93.6
102.5°	125.9	125.8	125.2	124.6	123.9	123.4	122.5	121.5	120.5	119.3	118.3
105°	162.4	162.1	161.7	161.5	161.1	160.8	160.3	159.9	159.4	158.9	158.4
107.5°	202.2	202.0	202.0	202.0	202.0	202.0	201.6	201.0	200.2	199.5	198.8
110°	229.1	229.1	229.1	229.1	229.1	229.1	228.7	227.6	226.7	225.6	224.7



TEST NUMBER: P331304-830

CATALOG NUMBER: SA2XXDIP-C485D725U830-4F0-1E-UDD-A1

**CANDELA DISTRIBUTION (continued):**

	220°	225°	230°	235°	240°	245°	250°	255°	260°	265°	270°
112.5°	256.5	256.8	256.9	257.1	257.2	257.3	256.9	255.9	255.0	254.0	253.0
115°	297.5	297.7	297.9	298.3	298.6	299.0	298.6	297.7	296.6	295.7	294.7
117.5°	337.6	338.0	338.9	339.9	340.7	341.7	341.5	340.2	338.8	337.5	336.2
120°	363.9	363.9	365.2	366.6	367.9	369.2	369.2	367.9	366.6	365.2	363.9
122.5°	391.8	392.2	393.1	394.1	395.0	395.9	395.6	394.0	392.5	390.9	389.3
125°	432.7	433.2	433.7	434.1	434.7	435.2	434.7	433.2	431.7	430.3	428.8
127.5°	472.4	473.0	473.5	474.2	474.8	475.3	474.7	472.9	471.0	469.1	467.2
130°	499.2	499.5	499.8	500.1	500.5	500.8	499.9	497.8	495.7	493.5	491.4
132.5°	525.9	526.6	526.5	526.5	526.4	526.3	525.5	523.7	522.0	520.3	518.5
135°	564.2	564.3	564.0	563.6	563.4	563.0	561.9	560.2	558.4	556.6	554.8
137.5°	601.3	601.4	601.1	600.6	600.2	599.7	598.8	597.4	595.9	594.4	593.0
140°	626.2	626.2	625.4	624.6	623.8	622.9	621.8	620.3	618.9	617.4	616.0
142.5°	648.8	648.7	648.1	647.5	647.0	646.4	645.4	643.9	642.4	640.9	639.5
145°	683.2	683.0	681.9	681.0	680.0	679.0	678.0	676.8	675.7	674.5	673.4
147.5°	713.0	712.8	712.1	711.4	710.8	710.1	709.1	707.7	706.3	704.9	703.6
150°	732.1	731.6	730.9	730.3	729.6	729.0	728.1	727.2	726.1	725.2	724.2
152.5°	751.0	750.5	749.6	748.9	748.1	747.2	746.4	745.5	744.4	743.5	742.4
155°	775.1	774.3	773.8	773.4	772.8	772.3	771.8	771.4	770.9	770.3	769.9
157.5°	797.2	796.1	795.8	795.5	795.2	794.9	794.7	794.3	794.0	793.6	793.3
160°	810.7	809.6	809.5	809.4	809.2	809.0	808.8	808.4	808.1	807.8	807.5
162.5°	822.6	821.4	821.3	821.1	821.0	820.8	820.7	820.6	820.6	820.5	820.4
165°	838.1	836.9	836.9	836.9	836.9	836.9	837.0	837.2	837.4	837.5	837.6
167.5°	850.9	849.7	849.8	849.8	849.9	849.9	850.2	850.6	851.1	851.6	852.1
170°	858.0	856.8	857.0	857.1	857.3	857.4	857.8	858.3	858.8	859.3	859.8
172.5°	863.3	862.1	862.3	862.4	862.6	862.8	863.1	863.6	864.1	864.6	865.1
175°	869.0	867.9	868.2	868.6	868.8	869.2	869.6	870.1	870.5	871.1	871.6
177.5°	872.0	871.3	871.5	871.8	872.0	872.3	872.6	873.0	873.5	873.8	874.2
180°	873.0	873.0	873.0	873.0	873.0	873.0	873.0	873.0	873.0	873.0	873.0



TEST NUMBER: P331304-830

CATALOG NUMBER: SA2XXDIP-C485D725U830-4F0-1E-UDD-A1

**CANDELA DISTRIBUTION (continued):**

	275°	280°	285°	290°	295°	300°	305°	310°	315°	320°	325°
0°	915.9	915.9	915.9	915.9	915.9	915.9	915.9	915.9	915.9	915.9	915.9
2.5°	920.7	922.1	926.6	931.1	936.1	937.5	939.8	937.8	937.3	942.6	946.6
5°	923.3	929.6	942.0	953.2	962.7	969.4	976.5	979.3	984.6	991.9	1001.1
7.5°	920.3	932.6	952.1	968.5	986.3	999.2	1009.3	1017.9	1028.2	1042.3	1057.5
10°	917.0	933.5	957.1	977.1	999.0	1015.5	1029.3	1042.6	1058.1	1077.5	1097.5
12.5°	910.8	930.4	959.9	983.6	1011.6	1027.9	1046.4	1075.3	1091.9	1118.9	1147.1
15°	898.3	920.1	961.3	990.5	1022.2	1053.2	1087.3	1114.7	1142.3	1158.1	1197.9
17.5°	879.8	911.8	957.4	991.6	1031.8	1080.5	1118.9	1150.1	1181.8	1207.4	1227.4
20°	864.9	899.8	951.8	992.7	1040.5	1093.0	1137.0	1168.7	1196.1	1217.6	1229.9
22.5°	846.0	889.9	940.6	988.4	1049.5	1101.5	1147.6	1172.6	1195.5	1206.0	1210.7
25°	816.2	869.1	926.4	984.9	1053.9	1108.8	1151.0	1166.2	1172.9	1162.6	1145.8
27.5°	784.3	843.1	910.2	978.3	1051.2	1104.0	1134.3	1131.9	1120.6	1087.5	1061.1
30°	760.3	825.1	897.2	971.5	1044.7	1096.1	1113.7	1096.1	1070.4	1033.5	995.8
32.5°	735.3	802.3	883.4	962.0	1032.9	1078.1	1081.9	1051.6	1011.8	969.9	922.8
35°	697.3	769.9	857.4	940.6	1007.8	1036.3	1019.4	965.9	918.7	861.4	797.3
37.5°	654.4	734.5	822.4	909.2	970.2	977.6	935.7	879.3	812.8	745.4	670.0
40°	622.4	707.2	797.7	885.2	939.1	931.4	877.9	816.0	736.7	654.4	584.3
42.5°	593.6	678.4	770.6	856.6	899.8	878.4	816.0	739.9	654.8	577.2	513.1
45°	543.8	631.1	725.5	808.5	833.2	794.8	712.1	627.6	543.8	479.1	428.4
47.5°	495.6	581.8	675.2	748.3	757.1	705.4	615.0	528.1	456.1	403.3	367.6
50°	460.1	546.7	639.2	704.4	701.5	639.2	546.3	463.5	403.4	360.8	336.9
52.5°	428.2	510.0	599.0	658.2	643.3	575.3	486.6	413.2	363.7	330.4	308.7
55°	378.7	454.4	538.9	586.4	559.0	483.6	408.7	349.5	312.9	287.9	271.1
57.5°	329.6	400.6	472.9	502.2	471.8	402.3	339.8	296.9	269.4	250.8	239.9
60°	299.2	361.2	425.6	450.9	414.6	352.7	303.4	265.0	242.9	227.7	217.9
62.5°	268.8	324.2	385.0	398.8	365.6	313.3	269.7	237.7	219.5	206.0	196.8
65°	227.4	272.8	319.0	328.1	297.5	256.9	222.4	201.7	185.5	175.7	168.2
67.5°	186.5	222.9	255.6	263.0	236.2	208.1	183.1	165.1	154.1	145.9	139.7
70°	162.3	191.1	217.9	223.9	202.4	177.4	158.4	143.9	134.1	127.1	121.1
72.5°	136.7	160.7	182.9	187.0	169.5	150.3	134.8	123.4	114.7	110.2	104.4
75°	104.5	118.7	135.9	137.0	125.4	113.7	101.7	94.3	89.7	84.2	81.3
77.5°	73.8	84.8	94.7	96.6	89.7	81.8	75.1	69.3	65.4	62.8	60.2
80°	56.4	65.1	69.4	71.8	66.9	61.3	57.4	53.5	51.1	49.3	47.5
82.5°	40.2	45.7	49.7	51.6	48.8	45.5	41.6	39.4	37.5	36.0	35.4
85°	20.5	22.9	25.4	26.0	25.4	23.9	21.9	21.9	20.7	20.5	20.5
87.5°	7.5	9.1	9.5	10.7	10.7	11.4	12.2	12.6	13.0	12.7	12.3
90°	2.7	4.7	6.6	8.6	11.4	15.0	18.6	22.1	25.8	25.4	25.2
92.5°	14.5	16.0	17.4	18.9	20.0	20.8	21.7	22.6	23.5	23.5	23.6
95°	40.0	41.6	43.3	44.9	45.8	46.2	46.5	46.8	47.1	47.1	47.1
97.5°	71.4	72.9	74.3	75.8	76.8	77.4	78.0	78.6	79.3	79.3	79.3
100°	94.9	96.1	97.5	98.8	99.7	100.2	100.7	101.1	101.7	101.7	101.7
102.5°	119.3	120.5	121.5	122.5	123.4	123.9	124.6	125.2	125.8	125.9	126.1
105°	158.9	159.4	159.9	160.3	160.8	161.1	161.5	161.7	162.1	162.4	162.8
107.5°	199.5	200.2	201.0	201.6	202.0	202.0	202.0	202.0	202.0	202.2	202.3
110°	225.6	226.7	227.6	228.7	229.1	229.1	229.1	229.1	229.1	229.1	229.1





TEST NUMBER: P331304-830

CATALOG NUMBER: SA2XXDIP-C485D725U830-4F0-1E-UDD-A1

**CANDELA DISTRIBUTION (continued):**

	275°	280°	285°	290°	295°	300°	305°	310°	315°	320°	325°
112.5°	254.0	255.0	255.9	256.9	257.3	257.2	257.1	256.9	256.8	256.5	256.0
115°	295.7	296.6	297.7	298.6	299.0	298.6	298.3	297.9	297.7	297.5	297.3
117.5°	337.5	338.8	340.2	341.5	341.7	340.7	339.9	338.9	338.0	337.6	337.2
120°	365.2	366.6	367.9	369.2	369.2	367.9	366.6	365.2	363.9	363.9	363.9
122.5°	390.9	392.5	394.0	395.6	395.9	395.0	394.1	393.1	392.2	391.8	391.4
125°	430.3	431.7	433.2	434.7	435.2	434.7	434.1	433.7	433.2	432.7	432.3
127.5°	469.1	471.0	472.9	474.7	475.3	474.8	474.2	473.5	473.0	472.4	471.8
130°	493.5	495.7	497.8	499.9	500.8	500.5	500.1	499.8	499.5	499.2	498.9
132.5°	520.3	522.0	523.7	525.5	526.3	526.4	526.5	526.5	526.6	525.9	525.2
135°	556.6	558.4	560.2	561.9	563.0	563.4	563.6	564.0	564.3	564.2	564.0
137.5°	594.4	595.9	597.4	598.8	599.7	600.2	600.6	601.1	601.4	601.3	601.2
140°	617.4	618.9	620.3	621.8	622.9	623.8	624.6	625.4	626.2	626.2	626.2
142.5°	640.9	642.4	643.9	645.4	646.4	647.0	647.5	648.1	648.7	648.8	648.8
145°	674.5	675.7	676.8	678.0	679.0	680.0	681.0	681.9	683.0	683.2	683.2
147.5°	704.9	706.3	707.7	709.1	710.1	710.8	711.4	712.1	712.8	713.0	713.4
150°	725.2	726.1	727.2	728.1	729.0	729.6	730.3	730.9	731.6	732.1	732.5
152.5°	743.5	744.4	745.5	746.4	747.2	748.1	748.9	749.6	750.5	751.0	751.7
155°	770.3	770.9	771.4	771.8	772.3	772.8	773.4	773.8	774.3	775.1	775.9
157.5°	793.6	794.0	794.3	794.7	794.9	795.2	795.5	795.8	796.1	797.2	798.3
160°	807.8	808.1	808.4	808.8	809.0	809.2	809.4	809.5	809.6	810.7	811.6
162.5°	820.5	820.6	820.6	820.7	820.8	821.0	821.1	821.3	821.4	822.6	823.7
165°	837.5	837.4	837.2	837.0	836.9	836.9	836.9	836.9	836.9	838.1	839.2
167.5°	851.6	851.1	850.6	850.2	849.9	849.9	849.8	849.8	849.7	850.9	852.1
170°	859.3	858.8	858.3	857.8	857.4	857.3	857.1	857.0	856.8	858.0	859.1
172.5°	864.6	864.1	863.6	863.1	862.8	862.6	862.4	862.3	862.1	863.3	864.4
175°	871.1	870.5	870.1	869.6	869.2	868.8	868.6	868.2	867.9	869.0	870.2
177.5°	873.8	873.5	873.0	872.6	872.3	872.0	871.8	871.5	871.3	872.0	872.8
180°	873.0	873.0	873.0	873.0	873.0	873.0	873.0	873.0	873.0	873.0	873.0



TEST NUMBER: P331304-830

CATALOG NUMBER: SA2XXDIP-C485D725U830-4F0-1E-UDD-A1

**CANDELA DISTRIBUTION (continued):**

	330°	335°	340°	345°	350°	355°	360°
0°	915.9	915.9	915.9	915.9	915.9	915.9	915.9
2.5°	950.0	953.9	953.9	954.5	958.9	958.5	958.2
5°	1011.0	1016.9	1017.7	1024.0	1028.2	1026.8	1022.9
7.5°	1068.5	1079.6	1088.1	1092.8	1098.3	1101.7	1100.2
10°	1114.1	1130.3	1140.1	1146.8	1154.9	1160.9	1158.8
12.5°	1155.5	1174.8	1188.3	1199.8	1200.8	1208.5	1203.2
15°	1220.0	1240.5	1242.6	1251.0	1257.7	1257.0	1257.4
17.5°	1241.3	1247.9	1249.2	1249.4	1249.5	1247.1	1241.7
20°	1233.8	1231.3	1225.3	1220.8	1212.7	1211.5	1204.6
22.5°	1197.7	1189.9	1174.9	1165.0	1152.4	1149.1	1147.1
25°	1126.7	1109.5	1085.5	1062.7	1056.3	1044.1	1047.5
27.5°	1029.4	1002.5	976.6	958.0	941.2	922.7	928.0
30°	960.9	930.7	894.1	865.9	848.0	830.4	827.2
32.5°	879.3	834.9	794.1	769.3	741.8	730.7	718.5
35°	738.5	695.2	654.7	619.9	599.8	584.3	570.2
37.5°	611.8	562.0	529.3	501.1	486.6	477.8	479.9
40°	533.3	489.7	465.7	444.2	430.8	424.5	425.9
42.5°	469.7	437.0	417.3	402.6	393.1	389.6	388.7
45°	397.4	379.1	362.9	354.5	349.9	346.0	343.6
47.5°	348.2	333.2	324.0	319.1	315.0	311.1	311.0
50°	318.6	308.7	302.4	297.1	293.9	291.1	293.6
52.5°	296.1	287.0	280.7	276.0	274.8	272.2	272.2
55°	262.6	255.5	251.0	246.8	244.7	243.3	241.5
57.5°	232.1	225.5	221.3	218.6	214.6	213.2	212.6
60°	210.5	205.2	201.0	197.5	195.7	192.9	192.9
62.5°	190.5	185.2	181.3	178.6	175.7	174.6	174.8
65°	161.6	157.3	153.4	150.6	150.0	147.9	148.5
67.5°	135.0	132.1	128.1	126.5	125.2	124.0	123.2
70°	117.3	114.4	112.3	110.2	109.1	109.1	109.1
72.5°	102.3	98.9	97.6	95.0	95.6	94.4	93.3
75°	79.2	77.1	76.1	74.9	73.2	73.2	73.2
77.5°	58.2	57.7	56.4	55.2	54.9	54.5	54.7
80°	45.1	44.7	44.0	44.0	43.3	43.0	42.2
82.5°	34.6	33.7	33.3	33.0	32.9	32.8	32.7
85°	19.7	19.0	19.0	19.3	18.7	18.7	19.0
87.5°	12.5	12.5	12.2	12.3	12.5	12.3	12.3
90°	24.8	24.5	24.4	24.6	24.7	24.9	25.1
92.5°	23.7	23.7	23.8	23.8	23.8	23.8	23.8
95°	47.1	47.1	47.0	46.7	46.4	46.0	45.7
97.5°	79.3	79.3	79.3	79.3	79.2	79.2	79.1
100°	101.7	101.7	101.6	101.4	101.2	101.1	100.9
102.5°	126.2	126.4	126.3	126.2	126.0	125.8	125.6
105°	163.1	163.4	163.5	163.5	163.5	163.5	163.5
107.5°	202.4	202.6	202.3	201.5	200.8	200.0	199.3
110°	229.1	229.1	228.8	228.4	227.9	227.4	226.9



TEST NUMBER: P331304-830

CATALOG NUMBER: SA2XXDIP-C485D725U830-4F0-1E-UDD-A1

**CANDELA DISTRIBUTION (continued):**

	330°	335°	340°	345°	350°	355°	360°
112.5°	255.6	255.2	254.9	254.5	254.1	253.8	253.4
115°	297.2	297.0	296.6	296.1	295.7	295.2	294.7
117.5°	336.9	336.4	336.0	335.5	335.0	334.5	334.0
120°	363.9	363.9	363.7	363.2	362.7	362.2	361.7
122.5°	391.1	390.7	390.3	389.9	389.6	389.2	388.9
125°	431.7	431.2	430.9	430.7	430.6	430.5	430.3
127.5°	471.2	470.6	470.0	469.6	469.0	468.5	468.0
130°	498.5	498.2	497.7	497.0	496.4	495.8	495.1
132.5°	524.4	523.8	523.1	522.5	522.1	521.5	521.0
135°	563.8	563.6	563.4	562.9	562.4	561.8	561.4
137.5°	601.1	601.0	600.6	599.9	599.3	598.6	597.9
140°	626.2	626.2	625.8	625.3	624.6	624.0	623.3
142.5°	649.0	649.1	648.8	648.2	647.5	647.0	646.3
145°	683.4	683.6	683.3	682.7	682.0	681.4	680.7
147.5°	713.8	714.2	714.1	713.4	712.8	712.2	711.5
150°	733.0	733.6	733.6	733.0	732.5	732.1	731.6
152.5°	752.3	752.9	752.9	752.3	751.7	751.0	750.5
155°	776.7	777.6	777.8	777.2	776.7	776.3	775.8
157.5°	799.5	800.6	800.7	799.9	799.2	798.3	797.6
160°	812.7	813.6	813.8	813.1	812.5	811.8	811.2
162.5°	824.8	826.0	826.0	825.3	824.5	823.7	822.9
165°	840.4	841.5	841.7	840.8	840.0	839.2	838.4
167.5°	853.2	854.3	854.5	853.7	852.8	852.0	851.1
170°	860.3	861.4	861.5	860.5	859.5	858.6	857.5
172.5°	865.5	866.7	866.8	865.8	864.8	863.8	862.9
175°	871.3	872.4	872.5	871.6	870.5	869.6	868.6
177.5°	873.6	874.4	874.4	873.6	872.8	872.0	871.3
180°	873.0	873.0	873.0	873.0	873.0	873.0	873.0

(END OF REPORT)