

Scaled data based on original data using  
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State  
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P333211-840

Luminaire Tested: **S125DIP-S850D365U840-4F0-1E-UDD-F**

Issue Date: 3/3/2020

**Test Information**

Test Method: LM-79-08  
Report Number: P333211-840  
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-7,  
Test Lab: INNOVATION CENTER  
Issue Date: 3/3/2020  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: NEO-RAY  
Catalog Number: S125DIP-S850D365U840-4F0-1E-UDD-F  
Description: DEFINE 5 DIRECT-INDIRECT PENDANT LED LUMINAIRE  
DOWNLIGHT 850 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER  
UPLIGHT 365 LUMENS PER FOOT, NO LENS  
Light Source: -  
Ballast/Driver: ELECTRONIC DRIVER

**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 4929.5 lumens  
Efficiency: N/A  
Efficacy: 140.8 lumens/watt  
Spacing Criteria (0/90/45): 1.21 / 1.18 / 1.31  
Luminous Opening: Rectangular (W 0.42' x L: 4' x H: 0')  
CIE Type: Semi-Direct


Input Watts (W): 35  
Input Voltage (V): 120  
Input Current (A<sub>in</sub>): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 25 FT



TEST NUMBER: P333211-840

CATALOG NUMBER: S125DIP-S850D365U840-4F0-1E-UDD-F

### Luminous Intensity Polar Plot





TEST NUMBER: P333211-840

CATALOG NUMBER: S125DIP-S850D365U840-4F0-1E-UDD-F

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	112	112	112	112	106	106	106	106	94	94	94	84	84	84	74	74	74	70
1	102	98	94	90	96	93	89	86	83	80	78	74	72	70	66	64	63	59
2	93	85	79	73	88	81	75	70	73	68	64	65	61	58	58	55	53	49
3	85	75	67	61	80	71	64	59	64	59	54	57	53	49	51	48	45	42
4	78	66	58	52	73	63	56	50	57	51	46	51	46	42	46	42	39	36
5	71	59	51	45	67	56	49	43	51	45	40	46	41	37	41	37	34	31
6	66	53	45	39	62	51	43	38	46	40	35	42	36	32	37	33	30	27
7	61	48	40	34	58	46	38	33	42	35	31	38	33	29	34	30	26	24
8	57	44	36	30	54	42	35	29	38	32	27	35	29	26	31	27	24	22
9	53	40	32	27	50	38	31	26	35	29	25	32	27	23	29	25	21	19
10	50	37	30	25	47	35	28	24	32	26	22	30	25	21	27	23	20	18

**AVERAGE LUMINANCE (cd/sqm):**

	0°	45°	90°
0°	8561	8561	8561
5°	8581	8499	8554
10°	8529	8439	8487
15°	8436	8338	8372
20°	8304	8195	8210
25°	8161	8027	8020
30°	7986	7845	7806
35°	7798	7649	7541
40°	7605	7436	7331
45°	7395	7242	7099
50°	7166	7007	6797
55°	6944	6742	6554
60°	6679	6475	6245
65°	6363	6154	5946
70°	6060	5784	5586
75°	5522	5340	5155
80°	4917	4839	4720
85°	4276	4357	4113



TEST NUMBER: P333211-840

CATALOG NUMBER: S125DIP-S850D365U840-4F0-1E-UDD-F

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	125.0	2.5
10°-20°	353.1	7.2
20°-30°	521.3	10.6
30°-40°	608.3	12.3
40°-50°	611.0	12.4
50°-60°	536.3	10.9
60°-70°	399.6	8.1
70°-80°	228.5	4.6
80°-90°	67.5	1.4
90°-100°	17.5	0.4
100°-110°	107.8	2.2
110°-120°	195.6	4.0
120°-130°	251.0	5.1
130°-140°	270.0	5.5
140°-150°	253.4	5.1
150°-160°	205.0	4.2
160°-170°	132.6	2.7
170°-180°	45.7	0.9
0°-30°	999.4	20.3
0°-40°	1607.8	32.6
0°-60°	2755.1	55.9
0°-90°	3450.7	70.0
90°-120°	321.0	6.5
90°-150°	1095.4	22.2
90°-180°	1479.0	30.0
0°-180°	4929.5	100.0

**CANDELA DISTRIBUTION:**

	0°	22.5°	45°	67.5°	90°	Flux
0°	1326	1326	1326	1326	1326	
5°	1324	1321	1311	1320	1319	125
15°	1262	1258	1247	1252	1252	355
25°	1145	1140	1126	1128	1125	527
35°	989	984	970	965	956	618
45°	810	805	793	781	777	624
55°	617	613	599	590	582	550
65°	416	414	403	394	389	413
75°	221	219	214	211	207	236
85°	58	59	59	58	56	64
90°	0	3	6	7	9	4
95°	20	19	6	7	8	26
105°	105	106	106	106	106	111
115°	197	199	199	198	196	195
125°	280	283	283	281	280	250
135°	350	351	351	350	348	269
145°	405	406	406	406	404	253
155°	446	444	445	446	443	206
165°	471	469	469	471	468	133
175°	482	480	480	482	479	46
180°	482	482	482	482	482	



TEST NUMBER: P333211-840

CATALOG NUMBER: S125DIP-S850D365U840-4F0-1E-UDD-F

**CANDELA DISTRIBUTION (FULL):**

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	1325.6	1325.6	1325.6	1325.6	1325.6	1325.6	1325.6	1325.6	1325.6	1325.6	1325.6
2.5°	1329.1	1328.5	1328.0	1327.4	1326.8	1325.5	1323.7	1321.9	1320.0	1318.2	1320.0
5°	1323.6	1323.1	1322.6	1322.2	1321.7	1320.3	1318.0	1315.7	1313.3	1311.0	1313.1
7.5°	1311.4	1311.0	1310.5	1310.0	1309.6	1308.1	1305.5	1302.9	1300.4	1297.8	1299.8
10°	1300.5	1300.1	1299.6	1299.1	1298.7	1297.2	1294.5	1292.0	1289.5	1286.9	1288.8
12.5°	1287.1	1286.3	1285.5	1284.5	1283.7	1282.1	1279.8	1277.4	1275.0	1272.6	1274.1
15°	1261.7	1261.0	1260.3	1259.6	1258.9	1257.3	1254.8	1252.1	1249.6	1247.0	1248.2
17.5°	1232.5	1231.5	1230.5	1229.5	1228.5	1226.6	1224.0	1221.3	1218.6	1216.0	1217.4
20°	1208.2	1207.8	1207.3	1206.8	1206.4	1204.6	1201.5	1198.5	1195.5	1192.4	1194.2
22.5°	1183.9	1183.1	1182.2	1181.3	1180.5	1178.7	1175.9	1173.0	1170.1	1167.3	1168.4
25°	1145.3	1144.2	1143.0	1141.8	1140.6	1138.5	1135.5	1132.5	1129.4	1126.4	1126.9
27.5°	1100.1	1099.5	1098.8	1098.1	1097.4	1095.5	1092.4	1089.2	1086.1	1083.0	1083.1
30°	1070.9	1070.2	1069.4	1068.7	1068.0	1065.9	1062.5	1058.9	1055.4	1052.0	1051.5
32.5°	1038.9	1037.8	1036.8	1035.7	1034.7	1032.6	1029.5	1026.3	1023.2	1020.1	1019.3
35°	989.1	988.1	987.1	986.2	985.3	983.2	980.0	976.6	973.4	970.2	969.0
37.5°	937.3	936.0	934.8	933.7	932.5	930.4	927.4	924.2	921.2	918.2	916.4
40°	902.0	900.8	899.7	898.5	897.3	895.1	891.8	888.6	885.3	882.0	880.0
42.5°	864.2	863.2	862.2	861.3	860.3	858.2	855.0	851.6	848.4	845.2	843.2
45°	809.7	808.7	807.8	806.9	806.0	804.1	801.3	798.5	795.7	792.9	790.1
47.5°	750.9	751.0	751.0	751.0	751.1	749.5	746.1	742.8	739.4	736.1	733.2
50°	713.2	712.5	711.8	711.0	710.4	708.6	705.9	703.1	700.2	697.4	694.4
52.5°	674.6	674.1	673.6	673.1	672.6	670.8	667.8	664.8	661.9	658.8	656.2
55°	616.7	616.0	615.3	614.6	613.9	611.9	608.6	605.4	602.1	598.8	596.7
57.5°	555.6	555.3	554.9	554.5	554.2	552.6	549.9	547.1	544.3	541.6	538.9
60°	517.1	516.1	515.2	514.2	513.3	511.6	509.0	506.4	503.9	501.3	499.0
62.5°	476.8	476.1	475.3	474.5	473.8	472.3	470.2	468.0	465.7	463.5	461.1
65°	416.4	415.9	415.5	415.0	414.5	413.0	410.4	407.9	405.3	402.7	400.6
67.5°	357.9	356.9	355.9	354.9	354.0	352.4	350.6	348.7	346.8	344.9	343.1
70°	320.9	319.7	318.6	317.4	316.3	314.7	312.6	310.4	308.3	306.3	304.9
72.5°	280.6	279.8	279.0	278.3	277.5	276.4	275.1	273.7	272.4	271.0	269.4
75°	221.3	220.9	220.4	219.9	219.4	218.6	217.4	216.3	215.1	214.0	213.3
77.5°	166.5	166.3	166.2	166.0	165.8	165.4	164.7	164.1	163.4	162.8	162.4
80°	132.2	132.2	132.2	132.2	132.2	131.9	131.5	131.0	130.5	130.1	129.9
82.5°	101.9	101.6	101.2	100.8	100.5	100.2	100.1	100.1	100.0	99.9	99.5
85°	57.7	58.0	58.2	58.4	58.6	58.8	58.8	58.8	58.8	58.8	58.5
87.5°	22.7	22.8	23.0	23.1	23.2	23.2	23.2	23.1	23.0	22.9	23.0
90°	0.4	1.0	1.6	2.2	2.9	3.5	4.0	4.6	5.2	5.8	6.1
92.5°	5.5	5.0	4.6	4.1	3.7	3.7	4.2	4.7	5.3	5.8	6.1
95°	20.3	20.1	19.9	19.6	19.4	17.8	14.7	11.7	8.7	5.8	6.1
97.5°	42.5	42.9	43.3	43.7	44.2	41.4	35.4	29.5	23.5	17.6	15.3
100°	59.6	59.9	60.1	60.3	60.6	60.8	61.2	61.5	61.8	62.1	50.3
102.5°	77.1	77.4	77.7	78.0	78.3	78.5	78.7	78.9	79.1	79.3	77.1
105°	104.9	105.2	105.6	105.9	106.2	106.3	106.3	106.3	106.3	106.3	106.3
107.5°	133.9	133.9	133.9	133.9	133.9	134.0	134.2	134.3	134.5	134.6	134.6
110°	152.8	152.8	152.8	152.8	152.8	152.9	153.0	153.2	153.3	153.5	153.3



TEST NUMBER: P333211-840

CATALOG NUMBER: S125DIP-S850D365U840-4F0-1E-UDD-F

**CANDELA DISTRIBUTION (continued):**

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	170.5	170.7	170.9	171.1	171.3	171.4	171.5	171.6	171.7	171.8	171.5
115°	197.0	197.4	197.8	198.2	198.6	198.8	198.9	199.0	199.1	199.1	198.8
117.5°	224.5	224.5	224.5	224.5	224.5	224.6	224.9	225.2	225.5	225.8	225.4
120°	241.7	241.6	241.6	241.5	241.4	241.5	241.7	241.9	242.2	242.4	242.3
122.5°	256.8	257.1	257.4	257.7	258.0	258.2	258.3	258.4	258.5	258.6	258.5
125°	280.2	280.7	281.3	281.9	282.5	282.8	282.8	282.8	282.8	282.8	282.4
127.5°	302.6	303.0	303.4	303.8	304.2	304.4	304.3	304.3	304.2	304.2	304.0
130°	316.3	316.7	317.1	317.5	317.9	318.1	318.2	318.2	318.3	318.4	318.2
132.5°	330.0	330.4	330.9	331.3	331.8	331.9	331.8	331.6	331.4	331.2	331.2
135°	349.5	349.9	350.4	350.9	351.3	351.5	351.3	351.2	351.0	350.9	350.7
137.5°	367.4	367.8	368.2	368.6	369.0	369.2	369.0	368.9	368.7	368.6	368.6
140°	379.1	379.3	379.4	379.6	379.7	379.8	379.7	379.6	379.5	379.5	379.6
142.5°	389.7	389.8	389.9	389.9	390.0	390.1	390.3	390.4	390.5	390.6	390.6
145°	405.2	405.4	405.5	405.7	405.8	405.9	405.9	405.9	405.9	405.9	406.0
147.5°	418.7	418.7	418.7	418.6	418.6	418.6	418.7	418.8	418.9	419.0	419.1
150°	427.3	427.2	427.0	426.8	426.7	426.7	426.8	427.0	427.2	427.3	427.5
152.5°	435.6	435.3	434.8	434.5	434.1	434.0	434.2	434.4	434.5	434.7	434.8
155°	446.3	445.8	445.2	444.7	444.3	444.1	444.3	444.4	444.6	444.7	445.0
157.5°	454.4	454.1	453.8	453.5	453.3	453.1	453.1	453.2	453.2	453.2	453.4
160°	460.1	459.7	459.2	458.7	458.3	458.1	458.1	458.2	458.3	458.4	458.7
162.5°	464.7	464.2	463.7	463.2	462.8	462.6	462.7	462.7	462.8	462.9	463.3
165°	470.8	470.4	469.9	469.4	469.0	468.8	468.8	468.9	469.0	469.1	469.5
167.5°	475.4	474.9	474.4	473.9	473.4	473.2	473.3	473.4	473.5	473.5	474.1
170°	478.0	477.5	476.9	476.4	475.7	475.5	475.6	475.6	475.7	475.8	476.5
172.5°	479.7	479.2	478.6	478.1	477.5	477.3	477.4	477.6	477.7	477.9	478.4
175°	481.5	481.1	480.6	480.1	479.7	479.5	479.5	479.6	479.7	479.8	480.4
177.5°	482.4	482.0	481.6	481.3	480.9	480.7	480.8	480.9	480.9	481.0	481.4
180°	481.5	481.5	481.5	481.5	481.5	481.5	481.5	481.5	481.5	481.5	481.5



TEST NUMBER: P333211-840

CATALOG NUMBER: S125DIP-S850D365U840-4F0-1E-UDD-F

**CANDELA DISTRIBUTION (continued):**

	55°	60°	65°	70°	75°	80°	85°	90°
0°	1325.6	1325.6	1325.6	1325.6	1325.6	1325.6	1325.6	1325.6
2.5°	1321.9	1323.7	1325.5	1326.5	1326.3	1326.1	1325.9	1325.6
5°	1315.2	1317.3	1319.4	1320.3	1320.1	1319.9	1319.6	1319.4
7.5°	1301.9	1303.9	1306.0	1306.9	1306.7	1306.5	1306.2	1306.0
10°	1290.6	1292.5	1294.3	1295.2	1294.9	1294.6	1294.4	1294.2
12.5°	1275.6	1277.1	1278.6	1279.3	1279.3	1279.2	1279.2	1279.1
15°	1249.4	1250.5	1251.7	1252.2	1252.2	1252.2	1252.2	1252.2
17.5°	1218.9	1220.3	1221.7	1221.9	1220.7	1219.6	1218.4	1217.3
20°	1195.8	1197.4	1199.0	1199.2	1198.1	1196.9	1195.8	1194.6
22.5°	1169.4	1170.5	1171.6	1171.7	1170.9	1170.1	1169.3	1168.6
25°	1127.3	1127.8	1128.3	1128.1	1127.5	1126.8	1126.1	1125.4
27.5°	1083.2	1083.3	1083.4	1083.1	1082.4	1081.7	1081.0	1080.3
30°	1051.1	1050.6	1050.1	1049.6	1048.8	1048.1	1047.4	1046.7
32.5°	1018.3	1017.5	1016.7	1015.6	1014.4	1013.1	1011.9	1010.7
35°	967.9	966.6	965.5	964.0	962.1	960.3	958.4	956.5
37.5°	914.6	912.9	911.2	909.8	908.8	907.7	906.7	905.5
40°	877.9	875.8	873.6	872.2	871.5	870.9	870.2	869.5
42.5°	841.3	839.4	837.5	836.0	835.0	833.8	832.7	831.7
45°	787.3	784.5	781.7	779.9	779.3	778.6	777.9	777.2
47.5°	730.3	727.5	724.7	722.5	720.8	719.2	717.5	715.9
50°	691.4	688.3	685.3	683.0	681.4	679.7	678.1	676.5
52.5°	653.6	650.9	648.2	646.0	644.2	642.4	640.6	638.7
55°	594.7	592.6	590.5	588.7	586.9	585.3	583.7	582.1
57.5°	536.2	533.5	530.8	529.0	528.1	527.3	526.3	525.4
60°	496.7	494.3	492.0	490.0	488.4	486.8	485.1	483.5
62.5°	458.6	456.1	453.5	451.6	450.4	449.1	447.9	446.6
65°	398.6	396.5	394.4	392.8	391.9	391.0	390.0	389.1
67.5°	341.3	339.5	337.8	336.6	336.1	335.5	334.9	334.4
70°	303.5	302.1	300.6	299.5	298.5	297.6	296.7	295.8
72.5°	267.8	266.3	264.7	263.4	262.5	261.6	260.6	259.6
75°	212.6	211.9	211.2	210.4	209.4	208.4	207.5	206.6
77.5°	162.0	161.5	161.1	160.6	159.9	159.3	158.6	157.9
80°	129.6	129.4	129.2	128.8	128.4	127.8	127.3	126.9
82.5°	99.0	98.6	98.2	98.0	97.9	97.8	97.7	97.6
85°	58.3	58.1	57.8	57.5	57.0	56.6	56.0	55.5
87.5°	23.1	23.2	23.2	23.1	22.8	22.5	22.2	21.8
90°	6.5	6.9	7.3	7.6	7.9	8.1	8.3	8.6
92.5°	6.5	6.9	7.3	7.6	7.7	7.8	7.9	8.0
95°	6.5	6.9	7.3	7.5	7.5	7.5	7.5	7.5
97.5°	13.1	10.8	8.6	7.5	7.5	7.5	7.5	7.5
100°	38.5	26.7	14.8	8.8	8.5	8.2	7.8	7.5
102.5°	74.7	72.5	70.3	66.4	61.1	55.7	50.3	44.9
105°	106.3	106.3	106.3	106.3	106.2	106.1	106.1	106.0
107.5°	134.7	134.7	134.7	134.6	134.4	134.1	133.9	133.6
110°	153.0	152.8	152.6	152.5	152.6	152.6	152.7	152.8





TEST NUMBER: P333211-840

CATALOG NUMBER: S125DIP-S850D365U840-4F0-1E-UDD-F

**CANDELA DISTRIBUTION (continued):**

	55°	60°	65°	70°	75°	80°	85°	90°
112.5°	171.2	170.9	170.6	170.4	170.3	170.2	170.1	170.0
115°	198.5	198.2	197.9	197.5	197.0	196.6	196.1	195.6
117.5°	225.0	224.6	224.2	223.9	223.7	223.5	223.3	223.1
120°	242.1	241.9	241.8	241.5	241.1	240.7	240.2	239.8
122.5°	258.3	258.2	258.0	257.7	257.2	256.8	256.3	255.9
125°	282.1	281.8	281.4	281.1	280.9	280.7	280.4	280.2
127.5°	303.8	303.6	303.5	303.1	302.5	301.8	301.3	300.7
130°	317.9	317.7	317.5	317.1	316.8	316.4	316.0	315.6
132.5°	331.1	331.1	331.0	330.8	330.4	330.0	329.6	329.3
135°	350.6	350.4	350.2	349.9	349.5	349.0	348.5	348.0
137.5°	368.7	368.7	368.7	368.5	368.1	367.7	367.3	366.9
140°	379.8	379.9	380.1	379.9	379.5	379.0	378.5	378.0
142.5°	390.6	390.7	390.7	390.5	390.0	389.5	389.1	388.6
145°	406.1	406.1	406.2	406.0	405.6	405.1	404.6	404.0
147.5°	419.2	419.3	419.4	419.2	418.6	418.0	417.5	416.9
150°	427.6	427.8	427.9	427.7	427.1	426.5	425.8	425.2
152.5°	435.0	435.2	435.4	435.2	434.5	434.0	433.4	432.8
155°	445.2	445.5	445.8	445.6	444.9	444.2	443.6	443.0
157.5°	453.7	453.9	454.2	454.0	453.4	452.7	452.1	451.5
160°	459.0	459.3	459.6	459.5	458.8	458.2	457.6	457.0
162.5°	463.8	464.2	464.7	464.5	463.8	463.1	462.5	461.8
165°	470.0	470.5	471.0	470.9	470.3	469.6	469.0	468.4
167.5°	474.7	475.2	475.8	475.7	475.0	474.3	473.6	472.9
170°	477.1	477.8	478.4	478.4	477.7	477.0	476.2	475.4
172.5°	479.0	479.6	480.1	480.1	479.4	478.6	477.9	477.2
175°	481.0	481.7	482.3	482.3	481.5	480.8	480.1	479.4
177.5°	481.9	482.3	482.7	482.7	482.2	481.7	481.2	480.7
180°	481.5	481.5	481.5	481.5	481.5	481.5	481.5	481.5

(END OF REPORT)