

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P333213-840

Luminaire Tested: **S125DIP-S850D365U840-4F0-1E-UDD-F4**

Issue Date: 3/3/2020

Test Information

Test Method: LM-79-08
Report Number: P333213-840
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-19,
Test Lab: INNOVATION CENTER
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: NEO-RAY
Catalog Number: S125DIP-S850D365U840-4F0-1E-UDD-F4
Description: DEFINE 5 DIRECT-INDIRECT PENDANT LED LUMINAIRE
DOWNLIGHT 850 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER
UPLIGHT 365 LUMENS PER FOOT, BATWING OPTIC
Light Source: -
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 4778.2 lumens
Efficiency: N/A
Efficacy: 136.5 lumens/watt
Spacing Criteria (0/90/45): 1.21 / 1.18 / 1.31
Luminous Opening: Rectangular (W 0.42' x L: 4' x H: 0')
CIE Type: Semi-Direct


Input Watts (W): 35
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P333213-840

CATALOG NUMBER: S125DIP-S850D365U840-4F0-1E-UDD-F4

Luminous Intensity Polar Plot





TEST NUMBER: P333213-840

CATALOG NUMBER: S125DIP-S850D365U840-4F0-1E-UDD-F4

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	112	112	112	112	107	107	107	107	96	96	96	86	86	86	77	77	77	72
1	103	98	94	90	97	93	90	86	84	81	79	75	73	71	68	66	65	61
2	93	86	79	74	88	81	76	71	74	69	65	66	63	60	59	57	54	51
3	85	75	68	62	81	72	65	59	65	59	55	59	54	50	53	49	46	43
4	78	67	59	52	74	64	56	50	58	52	47	52	47	43	47	43	40	37
5	72	60	51	45	68	57	49	43	52	45	40	47	42	38	42	38	35	32
6	66	54	45	39	63	51	43	38	47	40	35	42	37	33	38	34	31	28
7	61	49	40	34	58	46	39	33	42	36	31	39	33	29	35	31	27	25
8	57	44	36	31	54	42	35	30	39	32	28	35	30	26	32	28	24	22
9	53	40	33	27	50	39	32	27	36	29	25	33	27	24	30	25	22	20
10	50	37	30	25	47	36	29	24	33	27	23	30	25	21	28	23	20	18

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	8561	8561	8561
5°	8581	8499	8554
10°	8529	8439	8487
15°	8436	8338	8372
20°	8304	8195	8210
25°	8161	8027	8020
30°	7986	7845	7806
35°	7798	7649	7541
40°	7605	7436	7331
45°	7395	7242	7099
50°	7166	7007	6797
55°	6944	6742	6554
60°	6679	6475	6245
65°	6363	6154	5946
70°	6060	5784	5586
75°	5522	5340	5155
80°	4917	4839	4720
85°	4276	4357	4113



TEST NUMBER: P333213-840

CATALOG NUMBER: S125DIP-S850D365U840-4F0-1E-UDD-F4

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	125.0	2.6
10°-20°	353.1	7.4
20°-30°	521.3	10.9
30°-40°	608.3	12.7
40°-50°	611.0	12.8
50°-60°	536.3	11.2
60°-70°	399.6	8.4
70°-80°	228.5	4.8
80°-90°	67.5	1.4
90°-100°	128.3	2.7
100°-110°	275.8	5.8
110°-120°	258.9	5.4
120°-130°	209.8	4.4
130°-140°	168.4	3.5
140°-150°	127.0	2.7
150°-160°	89.4	1.9
160°-170°	52.7	1.1
170°-180°	17.1	0.4
0°-30°	999.4	20.9
0°-40°	1607.8	33.6
0°-60°	2755.1	57.7
0°-90°	3450.7	72.2
90°-120°	663.0	13.9
90°-150°	1168.2	24.4
90°-180°	1328.0	27.8
0°-180°	4778.2	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	1326	1326	1326	1326	1326	
5°	1324	1321	1311	1320	1319	125
15°	1262	1258	1247	1252	1252	355
25°	1145	1140	1126	1128	1125	527
35°	989	984	970	965	956	618
45°	810	805	793	781	777	624
55°	617	613	599	590	582	550
65°	416	414	403	394	389	413
75°	221	219	214	211	207	236
85°	58	59	59	58	56	64
90°	0	3	6	8	8	4
95°	12	35	316	143	84	13
105°	40	56	259	510	473	43
115°	72	87	208	448	527	71
125°	100	117	199	356	415	89
135°	117	141	198	299	345	91
145°	136	156	198	247	272	85
155°	156	167	194	219	228	72
165°	170	175	186	197	200	48
175°	177	177	178	180	180	17
180°	177	177	177	177	177	



TEST NUMBER: P333213-840

CATALOG NUMBER: S125DIP-S850D365U840-4F0-1E-UDD-F4

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	1325.6	1325.6	1325.6	1325.6	1325.6	1325.6	1325.6	1325.6	1325.6	1325.6	1325.6
2.5°	1329.1	1328.5	1328.0	1327.4	1326.8	1325.5	1323.7	1321.9	1320.0	1318.2	1320.0
5°	1323.6	1323.1	1322.6	1322.2	1321.7	1320.3	1318.0	1315.7	1313.3	1311.0	1313.1
7.5°	1311.4	1311.0	1310.5	1310.0	1309.6	1308.1	1305.5	1302.9	1300.4	1297.8	1299.8
10°	1300.5	1300.1	1299.6	1299.1	1298.7	1297.2	1294.5	1292.0	1289.5	1286.9	1288.8
12.5°	1287.1	1286.3	1285.5	1284.5	1283.7	1282.1	1279.8	1277.4	1275.0	1272.6	1274.1
15°	1261.7	1261.0	1260.3	1259.6	1258.9	1257.3	1254.8	1252.1	1249.6	1247.0	1248.2
17.5°	1232.5	1231.5	1230.5	1229.5	1228.5	1226.6	1224.0	1221.3	1218.6	1216.0	1217.4
20°	1208.2	1207.8	1207.3	1206.8	1206.4	1204.6	1201.5	1198.5	1195.5	1192.4	1194.2
22.5°	1183.9	1183.1	1182.2	1181.3	1180.5	1178.7	1175.9	1173.0	1170.1	1167.3	1168.4
25°	1145.3	1144.2	1143.0	1141.8	1140.6	1138.5	1135.5	1132.5	1129.4	1126.4	1126.9
27.5°	1100.1	1099.5	1098.8	1098.1	1097.4	1095.5	1092.4	1089.2	1086.1	1083.0	1083.1
30°	1070.9	1070.2	1069.4	1068.7	1068.0	1065.9	1062.5	1058.9	1055.4	1052.0	1051.5
32.5°	1038.9	1037.8	1036.8	1035.7	1034.7	1032.6	1029.5	1026.3	1023.2	1020.1	1019.3
35°	989.1	988.1	987.1	986.2	985.3	983.2	980.0	976.6	973.4	970.2	969.0
37.5°	937.3	936.0	934.8	933.7	932.5	930.4	927.4	924.2	921.2	918.2	916.4
40°	902.0	900.8	899.7	898.5	897.3	895.1	891.8	888.6	885.3	882.0	880.0
42.5°	864.2	863.2	862.2	861.3	860.3	858.2	855.0	851.6	848.4	845.2	843.2
45°	809.7	808.7	807.8	806.9	806.0	804.1	801.3	798.5	795.7	792.9	790.1
47.5°	750.9	751.0	751.0	751.0	751.1	749.5	746.1	742.8	739.4	736.1	733.2
50°	713.2	712.5	711.8	711.0	710.4	708.6	705.9	703.1	700.2	697.4	694.4
52.5°	674.6	674.1	673.6	673.1	672.6	670.8	667.8	664.8	661.9	658.8	656.2
55°	616.7	616.0	615.3	614.6	613.9	611.9	608.6	605.4	602.1	598.8	596.7
57.5°	555.6	555.3	554.9	554.5	554.2	552.6	549.9	547.1	544.3	541.6	538.9
60°	517.1	516.1	515.2	514.2	513.3	511.6	509.0	506.4	503.9	501.3	499.0
62.5°	476.8	476.1	475.3	474.5	473.8	472.3	470.2	468.0	465.7	463.5	461.1
65°	416.4	415.9	415.5	415.0	414.5	413.0	410.4	407.9	405.3	402.7	400.6
67.5°	357.9	356.9	355.9	354.9	354.0	352.4	350.6	348.7	346.8	344.9	343.1
70°	320.9	319.7	318.6	317.4	316.3	314.7	312.6	310.4	308.3	306.3	304.9
72.5°	280.6	279.8	279.0	278.3	277.5	276.4	275.1	273.7	272.4	271.0	269.4
75°	221.3	220.9	220.4	219.9	219.4	218.6	217.4	216.3	215.1	214.0	213.3
77.5°	166.5	166.3	166.2	166.0	165.8	165.4	164.7	164.1	163.4	162.8	162.4
80°	132.2	132.2	132.2	132.2	132.2	131.9	131.5	131.0	130.5	130.1	129.9
82.5°	101.9	101.6	101.2	100.8	100.5	100.2	100.1	100.1	100.0	99.9	99.5
85°	57.7	58.0	58.2	58.4	58.6	58.8	58.8	58.8	58.8	58.8	58.5
87.5°	22.7	22.8	22.9	23.1	23.2	23.2	23.1	23.1	23.0	22.9	23.0
90°	0.4	0.7	1.4	2.1	2.8	3.5	3.9	4.6	4.9	5.8	6.1
92.5°	4.3	5.3	8.3	12.7	18.9	29.3	48.8	81.4	116.9	115.0	93.1
95°	11.8	12.1	14.9	18.9	26.8	42.8	81.0	159.6	258.0	316.2	309.4
97.5°	19.6	20.0	22.0	26.0	33.0	44.5	69.8	127.3	230.5	337.7	391.5
100°	24.9	25.7	27.2	31.0	37.9	48.6	69.3	115.6	205.6	322.2	411.5
102.5°	31.0	31.4	32.5	36.8	43.0	53.4	71.8	110.8	186.7	295.2	399.5
105°	40.3	40.3	42.1	45.6	51.4	61.4	77.1	108.9	168.4	258.7	361.2
107.5°	49.5	50.2	51.9	54.8	60.8	69.8	84.9	112.1	160.8	233.7	322.0
110°	56.0	56.8	58.2	61.4	66.8	76.0	90.7	115.3	158.4	222.0	299.8



TEST NUMBER: P333213-840

CATALOG NUMBER: S125DIP-S850D365U840-4F0-1E-UDD-F4

CANDELA DISTRIBUTION (continued):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	62.6	63.3	64.4	67.7	73.0	82.0	96.0	119.3	158.4	215.1	283.3
115°	72.1	72.8	73.9	77.1	82.4	91.4	104.6	125.2	159.6	207.7	265.2
117.5°	80.7	81.7	82.9	86.0	92.2	100.8	113.3	132.1	161.9	204.1	254.4
120°	86.3	87.5	88.9	92.1	98.2	107.0	119.6	136.7	164.2	202.4	248.4
122.5°	92.4	93.1	94.3	97.6	104.1	113.1	125.5	141.8	166.1	201.0	243.3
125°	100.0	100.7	102.4	105.6	112.4	121.7	133.5	148.9	169.6	199.1	236.3
127.5°	105.8	106.9	109.2	113.3	120.5	129.8	141.1	155.2	173.3	198.3	229.8
130°	109.6	110.7	113.5	118.2	125.6	134.9	145.9	159.6	175.6	197.7	225.6
132.5°	112.4	113.8	117.2	122.4	130.2	139.5	150.6	163.3	178.1	197.7	222.2
135°	117.0	118.5	122.8	128.5	136.0	145.6	156.6	168.4	181.7	197.7	218.0
137.5°	122.9	124.0	127.9	133.7	141.1	151.0	161.1	172.3	184.9	198.1	214.4
140°	126.3	127.4	131.7	137.4	144.2	153.8	164.2	174.9	186.3	198.4	212.7
142.5°	130.4	131.1	135.1	140.9	147.3	156.4	166.1	176.3	187.1	198.7	211.3
145°	136.3	137.0	140.6	145.6	152.1	160.3	169.6	178.4	188.0	198.4	209.1
147.5°	142.6	143.0	146.1	150.8	156.3	163.5	171.7	179.8	188.4	197.5	206.9
150°	146.3	147.0	149.6	154.2	159.2	165.2	173.1	180.6	188.4	196.6	205.2
152.5°	150.4	150.8	153.0	157.0	161.8	167.2	174.5	181.2	188.1	195.5	203.2
155°	155.6	155.6	157.7	161.3	164.9	169.9	175.9	181.7	187.3	193.5	199.9
157.5°	160.4	160.3	162.0	165.0	168.1	172.0	177.1	182.0	186.4	191.3	196.7
160°	163.5	163.1	164.5	167.0	169.9	173.1	177.7	182.0	185.6	189.9	194.2
162.5°	166.0	165.7	167.1	169.4	171.6	174.2	178.3	181.8	184.7	188.1	191.9
165°	169.9	169.2	170.3	172.0	173.5	175.6	178.4	181.3	183.5	185.6	188.4
167.5°	172.5	172.1	172.8	173.7	174.7	176.1	178.4	180.5	181.5	183.1	185.1
170°	174.2	173.8	174.2	174.9	175.6	176.6	178.4	179.9	180.6	181.7	183.1
172.5°	175.3	174.7	175.0	175.7	176.1	176.6	178.1	179.4	179.5	180.0	181.1
175°	176.6	175.9	176.3	176.6	176.6	176.6	177.7	178.4	178.1	178.1	178.4
177.5°	177.3	176.7	176.7	177.0	176.7	176.7	177.3	177.6	177.0	177.0	177.3
180°	177.0	177.0	177.0	177.0	177.0	177.0	177.0	177.0	177.0	177.0	177.0



TEST NUMBER: P333213-840

CATALOG NUMBER: S125DIP-S850D365U840-4F0-1E-UDD-F4

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°
0°	1325.6	1325.6	1325.6	1325.6	1325.6	1325.6	1325.6	1325.6
2.5°	1321.9	1323.7	1325.5	1326.5	1326.3	1326.1	1325.9	1325.6
5°	1315.2	1317.3	1319.4	1320.3	1320.1	1319.9	1319.6	1319.4
7.5°	1301.9	1303.9	1306.0	1306.9	1306.7	1306.5	1306.2	1306.0
10°	1290.6	1292.5	1294.3	1295.2	1294.9	1294.6	1294.4	1294.2
12.5°	1275.6	1277.1	1278.6	1279.3	1279.3	1279.2	1279.2	1279.1
15°	1249.4	1250.5	1251.7	1252.2	1252.2	1252.2	1252.2	1252.2
17.5°	1218.9	1220.3	1221.7	1221.9	1220.7	1219.6	1218.4	1217.3
20°	1195.8	1197.4	1199.0	1199.2	1198.1	1196.9	1195.8	1194.6
22.5°	1169.4	1170.5	1171.6	1171.7	1170.9	1170.1	1169.3	1168.6
25°	1127.3	1127.8	1128.3	1128.1	1127.5	1126.8	1126.1	1125.4
27.5°	1083.2	1083.3	1083.4	1083.1	1082.4	1081.7	1081.0	1080.3
30°	1051.1	1050.6	1050.1	1049.6	1048.8	1048.1	1047.4	1046.7
32.5°	1018.3	1017.5	1016.7	1015.6	1014.4	1013.1	1011.9	1010.7
35°	967.9	966.6	965.5	964.0	962.1	960.3	958.4	956.5
37.5°	914.6	912.9	911.2	909.8	908.8	907.7	906.7	905.5
40°	877.9	875.8	873.6	872.2	871.5	870.9	870.2	869.5
42.5°	841.3	839.4	837.5	836.0	835.0	833.8	832.7	831.7
45°	787.3	784.5	781.7	779.9	779.3	778.6	777.9	777.2
47.5°	730.3	727.5	724.7	722.5	720.8	719.2	717.5	715.9
50°	691.4	688.3	685.3	683.0	681.4	679.7	678.1	676.5
52.5°	653.6	650.9	648.2	646.0	644.2	642.4	640.6	638.7
55°	594.7	592.6	590.5	588.7	586.9	585.3	583.7	582.1
57.5°	536.2	533.5	530.8	529.0	528.1	527.3	526.3	525.4
60°	496.7	494.3	492.0	490.0	488.4	486.8	485.1	483.5
62.5°	458.6	456.1	453.5	451.6	450.4	449.1	447.9	446.6
65°	398.6	396.5	394.4	392.8	391.9	391.0	390.0	389.1
67.5°	341.3	339.5	337.8	336.6	336.1	335.5	334.9	334.4
70°	303.5	302.1	300.6	299.5	298.5	297.6	296.7	295.8
72.5°	267.8	266.3	264.7	263.4	262.5	261.6	260.6	259.6
75°	212.6	211.9	211.2	210.4	209.4	208.4	207.5	206.6
77.5°	162.0	161.5	161.1	160.6	159.9	159.3	158.6	157.9
80°	129.6	129.4	129.2	128.8	128.4	127.8	127.3	126.9
82.5°	99.0	98.6	98.2	98.0	97.9	97.8	97.7	97.6
85°	58.3	58.1	57.8	57.5	57.0	56.6	56.0	55.5
87.5°	23.1	23.1	23.2	23.2	22.8	22.4	22.1	21.8
90°	6.5	6.8	7.2	7.9	7.9	7.9	8.2	8.2
92.5°	63.2	45.8	34.5	29.3	24.7	23.8	23.3	22.7
95°	256.6	202.4	158.4	128.5	103.1	92.4	89.6	83.9
97.5°	382.1	344.2	301.3	259.6	237.6	217.6	207.3	202.7
100°	439.0	421.5	384.8	347.6	323.0	297.3	284.1	278.4
102.5°	458.1	468.9	451.3	426.2	399.8	381.5	367.2	362.9
105°	446.9	495.7	511.4	507.6	496.0	484.3	477.2	472.9
107.5°	406.6	471.8	512.1	530.8	536.5	536.5	534.1	531.3
110°	376.9	444.7	495.0	525.3	541.4	548.2	550.7	550.7



TEST NUMBER: P333213-840

CATALOG NUMBER: S125DIP-S850D365U840-4F0-1E-UDD-F4

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°
112.5°	353.5	417.9	468.8	504.5	528.0	539.7	545.8	548.5
115°	324.1	379.4	428.3	467.2	495.0	512.1	522.1	526.7
117.5°	305.1	352.7	394.9	430.6	458.4	476.2	486.0	488.9
120°	294.8	337.6	376.9	408.3	434.7	451.8	461.5	464.3
122.5°	287.1	326.8	361.7	391.1	414.8	430.4	440.1	442.6
125°	275.9	312.3	343.4	369.0	389.0	403.6	411.5	415.1
127.5°	264.5	298.4	327.4	351.4	369.6	382.5	389.9	391.5
130°	257.3	288.7	316.6	339.8	357.6	369.4	376.6	378.7
132.5°	250.1	279.6	304.9	327.2	345.1	356.8	363.3	365.8
135°	241.0	265.5	288.4	308.7	324.5	336.2	342.6	344.8
137.5°	233.1	253.0	272.0	289.2	303.3	314.0	319.9	322.2
140°	228.7	245.5	262.0	276.9	290.1	299.4	304.8	306.6
142.5°	225.1	239.2	253.4	266.4	277.6	285.5	290.5	292.1
145°	220.3	231.3	242.4	252.0	260.5	266.6	270.5	272.0
147.5°	215.6	224.6	233.2	240.4	247.2	252.1	254.3	255.0
150°	213.1	221.0	227.7	234.1	239.4	243.8	245.2	245.5
152.5°	210.3	217.2	223.4	228.4	232.9	236.3	237.7	238.1
155°	205.9	211.7	216.6	220.6	224.1	226.6	227.7	228.0
157.5°	201.7	206.3	210.3	213.3	216.1	218.1	219.1	219.0
160°	198.8	202.4	205.9	208.4	211.0	212.7	213.4	213.1
162.5°	195.6	198.9	202.0	204.2	206.1	207.5	207.7	207.6
165°	191.3	193.8	195.9	197.7	199.1	199.9	199.9	199.9
167.5°	187.1	188.8	190.5	191.8	192.5	193.1	192.8	192.7
170°	184.9	185.9	187.0	187.7	188.4	188.8	188.8	188.4
172.5°	182.3	183.4	184.2	184.6	184.7	185.4	184.8	184.4
175°	179.6	179.6	180.3	180.3	180.3	180.6	179.9	179.6
177.5°	177.6	177.8	177.8	177.8	177.6	177.8	177.0	177.0
180°	177.0	177.0	177.0	177.0	177.0	177.0	177.0	177.0

(END OF REPORT)