

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P331315-830

Luminaire Tested: **SA2XXDIP-C485D925U830-4F0-1E-UDD-D**

Issue Date: 10/7/2019

Test Information

Test Method: LM-79-08
Report Number: P331315-830
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-2,
Test Lab: INNOVATION CENTER
Issue Date: 10/7/2019
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: NEO-RAY
Catalog Number: SA2XXDIP-C485D925U830-4F0-1E-UDD-D
Description: DEFINE 2 DIRECT-INDIRECT PENDANT LED LUMINAIRE
DOWNLIGHT 485 LUMENS PER FOOT, DROP SATIN WHITE DIFFUSER
UPLIGHT 925 LUMENS PER FOOT, NO LENS
Light Source: -
Ballast/Driver: ELECTRONIC DRIVER

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 5342.2 lumens
Efficiency: N/A
Efficacy: 120.1 lumens/watt
Spacing Criteria (0/90/45): 1.21 / 1.32 / 1.42
Luminous Opening: Rectangular w/ Sides (W: 0.17' x L: 4' x H: 0.08')
CIE Type: Semi-Indirect

Input Watts (W): 44.5
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P331315-830
CATALOG NUMBER: SA2XXDIP-C485D925U830-4F0-1E-UDD-D

Luminous Intensity Polar Plot





TEST NUMBER: P331315-830

CATALOG NUMBER: SA2XXDIP-C485D925U830-4F0-1E-UDD-D

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	103	103	103	103	92	92	92	92	73	73	73	55	55	55	39	39	39	31
1	93	88	84	80	83	79	76	72	62	60	58	47	45	44	33	32	31	24
2	84	76	70	65	75	68	63	59	54	50	47	41	38	36	28	26	25	19
3	76	67	59	53	68	60	54	48	47	43	39	35	32	30	25	23	21	16
4	70	59	51	45	62	53	46	41	42	37	33	31	28	25	22	20	18	13
5	64	52	44	38	57	47	40	35	37	32	28	28	24	22	19	17	15	12
6	58	46	38	33	52	42	35	30	33	28	24	25	21	19	18	15	13	10
7	54	42	34	28	48	38	31	26	30	25	21	23	19	16	16	14	12	9
8	50	38	30	25	45	34	27	23	27	22	19	21	17	14	15	12	10	8
9	46	34	27	22	41	31	25	20	25	20	16	19	15	13	13	11	9	7
10	43	31	24	19	39	28	22	18	23	18	15	17	14	12	12	10	8	6

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	7842	7842	7842
5°	7880	7549	7520
10°	7831	7327	7244
15°	7723	7090	6952
20°	7587	6836	6671
25°	7453	6592	6417
30°	7262	6342	6160
35°	7069	6100	5981
40°	6869	5895	5801
45°	6677	5709	5648
50°	6471	5541	5495
55°	6254	5363	5341
60°	5990	5177	5178
65°	5716	4959	4983
70°	5407	4723	4775
75°	5013	4495	4582
80°	4391	4260	4385
85°	3800	4054	4232



TEST NUMBER: P331315-830

CATALOG NUMBER: SA2XXDIP-C485D925U830-4F0-1E-UDD-D

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	46.0	0.9
10°-20°	132.0	2.5
20°-30°	200.0	3.7
30°-40°	243.6	4.6
40°-50°	262.1	4.9
50°-60°	254.5	4.8
60°-70°	222.2	4.2
70°-80°	171.1	3.2
80°-90°	117.7	2.2
90°-100°	118.8	2.2
100°-110°	203.3	3.8
110°-120°	427.1	8.0
120°-130°	663.4	12.4
130°-140°	691.8	13.0
140°-150°	636.3	11.9
150°-160°	510.3	9.6
160°-170°	328.8	6.2
170°-180°	113.2	2.1
0°-30°	378.0	7.1
0°-40°	621.6	11.6
0°-60°	1138.1	21.3
0°-90°	1649.2	30.9
90°-120°	749.2	14.0
90°-150°	2740.7	51.3
90°-180°	3693.0	69.1
0°-180°	5342.2	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	486	486	486	486	486	
5°	487	485	481	485	484	46
15°	465	466	466	472	472	131
25°	422	427	434	442	444	194
35°	364	376	389	404	410	227
45°	298	318	342	363	371	230
55°	229	255	291	315	325	204
65°	156	191	232	260	270	155
75°	87	126	171	200	210	92
85°	25	69	114	142	153	27
90°	8	58	110	141	153	7
95°	62	69	114	144	153	73
105°	265	298	113	146	158	284
115°	498	522	573	214	142	490
125°	701	714	751	775	785	625
135°	867	880	895	918	923	669
145°	1005	1005	1018	1028	1028	628
155°	1106	1099	1109	1113	1107	509
165°	1166	1161	1163	1168	1163	329
175°	1192	1187	1188	1193	1185	113
180°	1190	1190	1190	1190	1190	



TEST NUMBER: P331315-830

CATALOG NUMBER: SA2XXDIP-C485D925U830-4F0-1E-UDD-D

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	485.7	485.7	485.7	485.7	485.7	485.7	485.7	485.7	485.7	485.7	485.7
2.5°	488.5	488.1	487.8	487.4	487.0	486.4	485.5	484.7	483.8	482.9	483.5
5°	487.1	486.6	486.2	485.7	485.2	484.6	483.6	482.7	481.7	480.8	481.7
7.5°	482.8	482.4	482.1	481.8	481.5	481.0	480.2	479.6	478.8	478.1	479.2
10°	479.4	479.1	478.7	478.4	478.2	477.8	477.3	476.8	476.4	475.9	477.1
12.5°	473.7	473.8	473.9	473.9	474.0	473.8	473.5	473.2	472.8	472.5	473.7
15°	464.6	464.9	465.2	465.5	465.8	466.0	466.0	466.0	466.0	466.0	467.4
17.5°	452.8	453.5	454.1	454.8	455.4	456.0	456.5	456.9	457.5	458.0	459.4
20°	444.9	445.6	446.5	447.2	448.0	448.7	449.3	450.0	450.6	451.2	452.9
22.5°	436.4	437.3	438.3	439.1	440.1	440.9	441.9	442.7	443.6	444.5	446.2
25°	422.4	423.5	424.5	425.7	426.7	428.0	429.4	430.8	432.3	433.6	435.5
27.5°	405.5	407.3	409.1	410.9	412.6	414.3	415.9	417.6	419.2	420.9	423.3
30°	394.2	396.2	398.2	400.3	402.4	404.4	406.4	408.4	410.5	412.5	415.0
32.5°	381.8	384.1	386.3	388.7	391.0	393.3	395.7	398.1	400.5	402.9	405.8
35°	363.9	366.6	369.3	371.9	374.6	377.4	380.3	383.3	386.3	389.3	392.7
37.5°	344.5	347.6	350.6	353.7	356.8	360.2	364.1	367.9	371.7	375.6	379.5
40°	331.6	335.0	338.5	341.9	345.3	349.1	353.4	357.6	361.8	366.1	370.1
42.5°	319.1	322.6	326.0	329.5	332.9	337.1	342.0	346.8	351.7	356.5	360.9
45°	298.5	302.7	306.9	311.1	315.4	320.2	325.6	331.1	336.7	342.1	346.9
47.5°	278.1	282.7	287.3	291.8	296.4	302.0	308.4	314.8	321.2	327.6	332.7
50°	264.0	268.8	273.7	278.5	283.3	289.3	296.3	303.4	310.5	317.4	322.8
52.5°	250.4	255.5	260.6	265.8	270.9	277.1	284.6	291.9	299.4	306.8	312.2
55°	228.8	234.4	240.1	245.6	251.3	258.2	266.4	274.5	282.6	290.7	296.3
57.5°	207.4	213.8	220.1	226.4	232.8	240.1	248.4	256.7	264.9	273.2	279.4
60°	192.2	198.9	205.7	212.4	219.0	226.9	235.8	244.7	253.6	262.6	268.5
62.5°	178.6	185.6	192.7	199.6	206.6	214.5	223.4	232.3	241.3	250.2	256.5
65°	156.3	163.9	171.6	179.3	186.9	195.4	204.6	213.9	223.1	232.3	238.7
67.5°	135.7	143.7	151.7	159.8	167.8	176.4	186.0	195.4	204.8	214.2	220.7
70°	121.1	129.2	137.3	145.4	153.6	162.5	172.2	181.9	191.6	201.3	208.0
72.5°	107.5	115.9	124.3	132.7	141.1	150.2	160.0	169.8	179.6	189.5	196.1
75°	86.6	95.4	104.1	112.8	121.6	131.0	141.0	151.0	161.1	171.1	177.8
77.5°	66.4	75.5	84.6	93.8	103.0	112.6	122.8	133.0	143.2	153.4	160.0
80°	52.8	62.3	71.9	81.4	91.0	100.9	111.0	121.1	131.3	141.5	148.1
82.5°	41.6	51.0	60.3	69.7	79.2	89.1	99.3	109.6	119.9	130.3	136.8
85°	25.4	35.1	44.8	54.5	64.1	74.0	84.0	94.0	104.1	114.0	120.6
87.5°	13.9	23.8	33.5	43.2	53.0	63.0	73.3	83.6	94.0	104.2	110.8
90°	7.9	19.0	30.3	41.5	52.6	64.0	75.5	87.1	98.6	110.1	117.3
92.5°	23.8	32.1	40.3	48.6	56.9	66.3	76.6	87.0	97.5	107.8	114.4
95°	61.5	62.6	63.6	64.7	65.7	71.6	82.4	93.0	103.8	114.5	121.4
97.5°	115.9	104.7	93.5	82.2	71.0	71.4	83.5	95.6	107.7	119.8	126.4
100°	157.3	136.9	116.5	96.0	75.6	71.4	83.4	95.5	107.4	119.4	126.8
102.5°	202.2	201.9	201.7	201.4	201.1	191.6	173.0	154.3	135.6	116.9	124.5
105°	265.2	275.5	285.8	296.1	306.3	289.4	245.3	201.2	157.1	113.0	120.6
107.5°	337.9	346.2	354.4	362.7	370.9	347.6	292.8	238.0	183.1	128.3	131.4
110°	384.2	391.3	398.4	405.6	412.7	392.5	344.9	297.3	249.7	202.0	187.9



TEST NUMBER: P331315-830

CATALOG NUMBER: SA2XXDIP-C485D925U830-4F0-1E-UDD-D

CANDELA DISTRIBUTION (continued):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	428.2	434.4	440.6	446.8	453.0	452.9	446.5	440.2	433.8	427.4	362.6
115°	497.8	502.8	507.7	512.7	517.6	526.0	537.9	549.7	561.6	573.3	489.5
117.5°	559.2	564.0	568.7	573.5	578.2	585.6	595.3	605.1	614.9	624.7	607.9
120°	604.6	608.2	611.7	615.2	618.7	625.3	635.0	644.7	654.4	664.0	670.7
122.5°	643.3	646.5	649.8	653.1	656.4	662.8	672.4	682.0	691.7	701.3	706.9
125°	701.3	703.7	706.2	708.7	711.2	716.8	725.4	734.1	742.7	751.3	756.9
127.5°	754.4	757.1	759.7	762.2	764.9	769.5	776.3	783.1	789.8	796.5	802.4
130°	788.2	791.1	794.0	796.9	799.8	804.0	809.4	814.7	820.1	825.5	831.4
132.5°	822.7	825.1	827.6	830.0	832.5	835.9	840.6	845.3	849.9	854.5	860.0
135°	866.7	869.8	872.8	875.9	878.9	882.1	885.4	888.6	891.9	895.2	900.4
137.5°	912.0	914.1	916.2	918.3	920.4	922.7	925.4	928.0	930.7	933.3	938.1
140°	941.6	942.9	944.3	945.7	947.1	949.0	951.4	953.8	956.2	958.7	962.9
142.5°	966.4	967.6	968.8	970.1	971.3	973.1	975.5	978.1	980.5	983.0	986.6
145°	1004.6	1004.4	1004.2	1004.0	1003.8	1005.3	1008.6	1011.8	1015.1	1018.3	1020.6
147.5°	1038.5	1037.7	1037.1	1036.3	1035.6	1036.8	1040.0	1043.3	1046.5	1049.7	1050.8
150°	1060.5	1059.2	1057.8	1056.5	1055.2	1056.0	1059.1	1062.2	1065.3	1068.3	1069.4
152.5°	1079.1	1077.6	1076.1	1074.7	1073.2	1073.8	1076.8	1079.7	1082.6	1085.5	1086.7
155°	1106.2	1104.5	1102.7	1101.0	1099.3	1099.6	1101.8	1104.2	1106.5	1108.7	1109.8
157.5°	1127.3	1125.9	1124.5	1122.9	1121.5	1121.6	1123.2	1124.8	1126.4	1128.0	1129.4
160°	1139.7	1138.6	1137.5	1136.2	1135.1	1135.1	1136.2	1137.5	1138.6	1139.7	1140.9
162.5°	1150.8	1149.6	1148.5	1147.3	1146.1	1146.0	1147.1	1148.0	1149.1	1150.1	1151.3
165°	1165.5	1164.4	1163.3	1162.1	1160.9	1160.6	1161.2	1161.8	1162.4	1163.0	1164.3
167.5°	1176.6	1175.4	1174.3	1173.1	1172.0	1171.7	1172.2	1172.7	1173.3	1173.8	1175.2
170°	1182.8	1181.6	1180.4	1179.3	1178.2	1177.8	1178.2	1178.6	1178.9	1179.3	1180.6
172.5°	1186.8	1185.7	1184.6	1183.5	1182.3	1181.9	1182.3	1182.7	1183.1	1183.5	1184.8
175°	1192.2	1190.9	1189.6	1188.2	1186.8	1186.4	1186.8	1187.1	1187.5	1187.9	1189.3
177.5°	1193.1	1192.0	1191.0	1189.9	1188.8	1188.4	1188.5	1188.6	1188.8	1188.9	1190.1
180°	1189.7	1189.7	1189.7	1189.7	1189.7	1189.7	1189.7	1189.7	1189.7	1189.7	1189.7



TEST NUMBER: P331315-830

CATALOG NUMBER: SA2XXDIP-C485D925U830-4F0-1E-UDD-D

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°
0°	485.7	485.7	485.7	485.7	485.7	485.7	485.7	485.7
2.5°	484.2	484.7	485.4	485.6	485.3	485.1	484.8	484.6
5°	482.7	483.6	484.6	484.9	484.7	484.7	484.5	484.3
7.5°	480.3	481.5	482.6	483.1	483.0	482.8	482.6	482.5
10°	478.3	479.6	480.9	481.5	481.3	481.1	481.0	480.8
12.5°	474.9	476.3	477.5	478.1	477.9	477.7	477.6	477.4
15°	468.8	470.2	471.6	472.2	472.1	471.9	471.7	471.6
17.5°	460.9	462.4	463.8	464.6	464.6	464.6	464.6	464.6
20°	454.7	456.4	458.1	458.9	458.9	458.9	458.9	458.9
22.5°	447.9	449.6	451.4	452.3	452.6	452.8	453.1	453.4
25°	437.3	439.2	441.1	442.3	442.8	443.3	443.7	444.2
27.5°	425.7	428.1	430.5	431.8	432.2	432.5	432.8	433.2
30°	417.5	420.0	422.5	424.0	424.4	424.9	425.4	425.8
32.5°	408.7	411.5	414.4	416.3	417.2	418.0	418.9	419.7
35°	396.2	399.6	403.0	405.3	406.4	407.5	408.6	409.7
37.5°	383.2	387.1	390.9	393.3	394.5	395.7	396.8	398.0
40°	374.2	378.2	382.3	385.0	386.4	387.9	389.3	390.7
42.5°	365.3	369.8	374.2	377.2	378.5	379.9	381.4	382.8
45°	351.9	356.7	361.5	364.7	366.3	367.9	369.4	371.0
47.5°	337.7	342.8	347.9	351.3	353.0	354.7	356.5	358.2
50°	328.1	333.4	338.7	342.2	344.0	345.7	347.4	349.1
52.5°	317.6	323.1	328.6	332.2	334.0	335.9	337.7	339.6
55°	302.0	307.6	313.2	317.1	319.1	321.1	323.2	325.2
57.5°	285.4	291.4	297.6	301.6	303.7	305.8	307.8	309.9
60°	274.5	280.4	286.3	290.4	292.6	294.8	297.0	299.2
62.5°	262.8	269.1	275.4	279.7	281.7	283.8	285.9	287.9
65°	245.2	251.6	258.0	262.2	264.2	266.3	268.2	270.3
67.5°	227.2	233.7	240.2	244.5	246.6	248.7	250.9	253.0
70°	214.8	221.5	228.2	232.5	234.4	236.3	238.2	240.1
72.5°	202.7	209.3	215.9	220.4	222.5	224.8	227.1	229.3
75°	184.5	191.2	197.9	202.4	204.3	206.4	208.4	210.5
77.5°	166.7	173.4	180.1	184.5	186.7	188.9	191.1	193.3
80°	154.7	161.2	167.8	172.1	174.4	176.5	178.7	180.9
82.5°	143.4	150.0	156.5	160.8	162.9	164.9	167.0	169.1
85°	127.1	133.7	140.3	144.7	146.8	149.1	151.3	153.4
87.5°	117.3	123.9	130.5	134.9	137.0	139.0	141.1	143.2
90°	124.6	131.8	139.0	143.7	146.0	148.3	150.5	152.8
92.5°	121.1	127.7	134.3	138.7	140.8	142.9	145.1	147.1
95°	128.3	135.3	142.1	146.4	148.1	149.8	151.5	153.2
97.5°	132.9	139.5	146.0	150.3	152.4	154.5	156.6	158.6
100°	134.1	141.4	148.7	153.4	155.5	157.7	159.8	161.8
102.5°	132.2	139.9	147.5	152.5	154.7	156.9	159.2	161.5
105°	128.2	135.8	143.4	148.4	150.9	153.4	155.9	158.3
107.5°	134.5	137.6	140.7	143.5	146.0	148.5	151.0	153.4
110°	173.8	159.7	145.5	139.7	142.2	144.7	147.1	149.7



TEST NUMBER: P331315-830

CATALOG NUMBER: SA2XXDIP-C485D925U830-4F0-1E-UDD-D

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°
112.5°	297.8	233.1	168.3	137.0	139.4	141.8	144.1	146.4
115°	405.6	321.7	237.9	189.9	177.9	165.8	153.7	141.7
117.5°	591.2	574.4	557.6	527.4	483.7	440.0	396.3	352.7
120°	677.4	684.1	690.8	682.0	658.0	633.9	609.7	585.6
122.5°	712.6	718.2	723.9	724.9	721.3	717.8	714.3	710.7
125°	762.4	768.0	773.5	777.3	779.3	781.3	783.3	785.2
127.5°	808.2	814.0	819.8	823.5	825.0	826.5	828.0	829.4
130°	837.3	843.1	848.9	852.4	853.5	854.5	855.5	856.7
132.5°	865.3	870.8	876.2	879.5	880.5	881.6	882.6	883.7
135°	905.7	910.9	916.1	919.1	919.9	920.8	921.7	922.6
137.5°	942.8	947.6	952.3	955.0	955.4	955.7	956.2	956.6
140°	967.0	971.3	975.5	977.6	977.6	977.6	977.6	977.6
142.5°	990.1	993.7	997.3	999.0	998.8	998.7	998.5	998.4
145°	1022.9	1025.2	1027.5	1028.5	1028.3	1028.1	1028.0	1027.8
147.5°	1051.9	1053.0	1054.1	1054.5	1054.0	1053.7	1053.2	1052.8
150°	1070.5	1071.8	1072.9	1073.0	1072.0	1071.0	1070.1	1069.1
152.5°	1087.8	1088.9	1090.1	1090.1	1088.7	1087.5	1086.3	1085.0
155°	1111.1	1112.2	1113.3	1113.1	1111.6	1110.0	1108.5	1107.0
157.5°	1130.6	1131.9	1133.2	1133.1	1131.6	1130.1	1128.6	1127.2
160°	1142.0	1143.2	1144.3	1144.2	1142.8	1141.5	1140.2	1138.9
162.5°	1152.6	1154.0	1155.3	1155.1	1153.5	1151.8	1150.2	1148.5
165°	1165.6	1167.0	1168.3	1168.3	1167.0	1165.6	1164.3	1163.0
167.5°	1176.5	1177.8	1179.2	1178.9	1177.2	1175.5	1173.8	1172.1
170°	1182.0	1183.4	1184.7	1184.5	1182.8	1181.0	1179.3	1177.6
172.5°	1186.1	1187.5	1188.8	1188.6	1186.8	1185.2	1183.5	1181.8
175°	1190.6	1191.9	1193.3	1193.0	1191.1	1189.2	1187.2	1185.3
177.5°	1191.1	1192.2	1193.3	1193.1	1191.8	1190.3	1188.9	1187.6
180°	1189.7	1189.7	1189.7	1189.7	1189.7	1189.7	1189.7	1189.7

(END OF REPORT)