

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P331318-830

Luminaire Tested: **SA2XXDIP-C485D925U830-4F0-1E-UDD-F**

Issue Date: 10/7/2019

Test Information

Test Method: LM-79-08
Report Number: P331318-830
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-2,
Test Lab: INNOVATION CENTER
Issue Date: 10/7/2019
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: NEO-RAY
Catalog Number: SA2XXDIP-C485D925U830-4F0-1E-UDD-F
Description: DEFINE 2 DIRECT-INDIRECT PENDANT LED LUMINAIRE
DOWNLIGHT 485 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER
UPLIGHT 925 LUMENS PER FOOT, NO LENS
Light Source: -
Ballast/Driver: ELECTRONIC DRIVER

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 5351.7 lumens
Efficiency: N/A
Efficacy: 120.3 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 1.16 / 1.3
Luminous Opening: Rectangular (W 0.17' x L: 4' x H: 0')
CIE Type: Semi-Indirect

Input Watts (W): 44.5
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P331318-830
CATALOG NUMBER: SA2XXDIP-C485D925U830-4F0-1E-UDD-F

Luminous Intensity Polar Plot





TEST NUMBER: P331318-830

CATALOG NUMBER: SA2XXDIP-C485D925U830-4F0-1E-UDD-F

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	104	104	104	104	94	94	94	94	75	75	75	58	58	58	42	42	42	35
1	94	90	86	83	85	82	78	75	66	63	61	51	49	48	37	36	36	29
2	86	79	73	68	77	71	66	62	57	54	51	45	42	40	33	31	30	25
3	78	69	62	56	70	63	57	52	51	46	43	39	36	34	29	27	25	21
4	72	61	53	48	64	55	49	44	45	40	36	35	32	29	26	24	22	18
5	66	54	46	41	59	49	43	37	40	35	31	31	28	25	23	21	19	16
6	60	49	41	35	54	44	37	32	36	31	27	28	25	22	21	19	17	14
7	56	44	36	31	50	40	33	28	33	28	24	26	22	19	19	17	15	12
8	52	40	32	27	47	36	30	25	30	25	21	24	20	17	18	15	13	11
9	48	36	29	24	43	33	27	22	27	22	19	22	18	15	16	14	12	10
10	45	33	26	21	40	30	24	20	25	20	17	20	16	14	15	13	11	9

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	11820	11820	11820
5°	11866	11694	11763
10°	11795	11576	11632
15°	11649	11425	11413
20°	11442	11201	11187
25°	11236	10922	10922
30°	10972	10670	10577
35°	10724	10364	10212
40°	10416	10060	9866
45°	10111	9757	9515
50°	9779	9442	9105
55°	9433	9073	8740
60°	9045	8638	8318
65°	8630	8202	7824
70°	8105	7676	7312
75°	7380	7068	6900
80°	6546	6341	6025
85°	5335	5076	4557



TEST NUMBER: P331318-830

CATALOG NUMBER: SA2XXDIP-C485D925U830-4F0-1E-UDD-F

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	68.8	1.3
10°-20°	193.7	3.6
20°-30°	284.7	5.3
30°-40°	330.7	6.2
40°-50°	330.4	6.2
50°-60°	288.1	5.4
60°-70°	213.0	4.0
70°-80°	120.7	2.3
80°-90°	35.4	0.7
90°-100°	39.7	0.7
100°-110°	145.5	2.7
110°-120°	389.0	7.3
120°-130°	642.1	12.0
130°-140°	682.9	12.8
140°-150°	634.7	11.9
150°-160°	510.3	9.5
160°-170°	328.8	6.1
170°-180°	113.2	2.1
0°-30°	547.2	10.2
0°-40°	878.0	16.4
0°-60°	1496.4	28.0
0°-90°	1865.4	34.9
90°-120°	574.2	10.7
90°-150°	2533.9	47.3
90°-180°	3486.0	65.1
0°-180°	5351.7	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	732	732	732	732	732	
5°	732	729	722	727	726	69
15°	697	692	684	686	683	196
25°	631	625	613	614	613	290
35°	544	537	526	522	518	340
45°	443	438	427	420	417	342
55°	335	331	322	314	310	299
65°	226	222	215	208	205	223
75°	118	117	113	109	111	126
85°	29	28	27	25	25	33
90°	1	10	17	21	23	4
95°	56	29	34	38	37	68
105°	262	273	52	62	65	280
115°	495	510	531	151	71	487
125°	700	711	727	733	736	624
135°	866	879	888	896	894	669
145°	1005	1005	1018	1024	1020	628
155°	1106	1099	1109	1113	1107	509
165°	1166	1161	1163	1168	1163	329
175°	1192	1187	1188	1193	1185	113
180°	1190	1190	1190	1190	1190	



TEST NUMBER: P331318-830

CATALOG NUMBER: SA2XXDIP-C485D925U830-4F0-1E-UDD-F

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	732.1	732.1	732.1	732.1	732.1	732.1	732.1	732.1	732.1	732.1	732.1
2.5°	735.5	734.8	734.2	733.6	732.9	732.0	730.6	729.2	727.8	726.4	727.7
5°	732.1	731.4	730.8	730.2	729.6	728.4	726.7	725.0	723.2	721.5	722.7
7.5°	725.6	724.6	723.7	722.6	721.7	720.4	718.6	716.9	715.1	713.3	714.6
10°	719.4	718.3	717.2	716.1	715.0	713.5	711.6	709.8	707.9	706.1	707.3
12.5°	711.0	710.0	709.0	708.0	707.1	705.7	703.8	701.9	700.0	698.1	699.0
15°	696.9	696.0	695.0	694.1	693.1	691.6	689.6	687.6	685.5	683.5	684.1
17.5°	678.8	678.0	677.0	676.1	675.1	673.6	671.6	669.5	667.4	665.3	666.1
20°	665.9	665.0	664.0	663.1	662.1	660.6	658.4	656.2	654.0	651.9	652.3
22.5°	653.0	651.7	650.4	649.0	647.7	646.0	643.9	641.9	639.8	637.7	637.8
25°	630.7	629.4	628.2	627.0	625.8	623.8	621.1	618.4	615.8	613.1	613.4
27.5°	605.4	604.3	603.1	602.0	600.9	599.3	597.2	595.0	593.0	590.9	590.4
30°	588.5	587.2	586.0	584.8	583.4	581.6	579.3	577.0	574.7	572.3	571.8
32.5°	570.4	569.5	568.4	567.4	566.5	564.7	562.2	559.8	557.3	554.9	554.0
35°	544.1	542.5	541.0	539.4	537.9	535.8	533.4	530.8	528.3	525.8	524.9
37.5°	514.4	513.0	511.7	510.3	508.9	507.0	504.4	502.0	499.5	497.0	495.8
40°	494.2	492.9	491.6	490.4	489.2	487.3	484.7	482.3	479.8	477.3	475.9
42.5°	474.5	473.2	471.9	470.7	469.5	467.6	465.1	462.6	460.1	457.5	456.0
45°	442.8	441.7	440.5	439.5	438.4	436.7	434.3	432.0	429.6	427.3	425.6
47.5°	411.2	410.2	409.2	408.1	407.1	405.4	402.9	400.5	398.0	395.6	393.8
50°	389.3	388.5	387.7	386.9	386.2	384.7	382.5	380.3	378.1	375.9	373.7
52.5°	367.9	366.8	365.8	364.8	363.7	362.2	360.1	358.1	356.0	353.9	352.1
55°	335.1	334.1	333.2	332.2	331.3	329.9	328.0	326.1	324.2	322.3	320.6
57.5°	302.1	301.3	300.6	299.9	299.2	297.7	295.7	293.6	291.5	289.5	287.6
60°	280.1	279.6	278.9	278.2	277.7	276.3	274.1	271.8	269.7	267.5	265.8
62.5°	258.7	257.8	256.7	255.7	254.8	253.4	251.8	250.1	248.4	246.7	245.1
65°	225.9	225.0	224.0	223.1	222.3	220.9	219.4	217.8	216.2	214.7	213.3
67.5°	192.6	191.8	191.1	190.3	189.5	188.5	187.1	185.7	184.3	182.9	181.8
70°	171.7	171.2	170.5	169.8	169.3	168.2	166.8	165.4	164.0	162.6	161.6
72.5°	150.3	149.8	149.1	148.5	147.9	147.1	146.2	145.2	144.4	143.5	142.3
75°	118.3	117.9	117.6	117.3	117.0	116.5	115.6	114.9	114.1	113.3	112.4
77.5°	89.5	89.0	88.5	87.9	87.4	87.0	86.7	86.3	86.1	85.8	85.3
80°	70.4	70.2	70.1	69.9	69.7	69.6	69.2	68.9	68.6	68.2	67.8
82.5°	52.4	52.3	52.3	52.3	52.2	52.1	51.9	51.7	51.6	51.4	50.8
85°	28.8	28.7	28.6	28.4	28.3	28.1	27.9	27.8	27.6	27.4	27.0
87.5°	10.3	10.5	10.7	10.8	11.0	11.1	11.1	11.2	11.3	11.3	11.1
90°	0.8	2.9	5.1	7.2	9.2	11.1	12.6	14.1	15.6	17.2	18.2
92.5°	17.3	17.2	17.0	16.8	16.6	16.9	17.7	18.5	19.2	20.0	20.5
95°	56.0	49.7	43.4	37.0	30.7	28.2	29.6	30.9	32.2	33.6	34.5
97.5°	111.0	93.2	75.5	57.7	39.9	32.5	35.6	38.7	41.8	45.0	45.7
100°	152.4	126.1	99.9	73.7	47.5	36.1	39.3	42.6	45.8	49.1	50.6
102.5°	197.8	192.3	186.7	181.2	175.6	159.3	132.1	104.8	77.7	50.4	52.4
105°	261.6	267.4	273.1	278.9	284.6	261.4	209.2	156.9	104.7	52.5	54.6
107.5°	334.5	339.1	343.7	348.4	353.1	324.0	261.4	198.8	136.1	73.5	71.4
110°	381.4	385.4	389.4	393.4	397.4	371.7	316.5	261.2	205.9	150.6	131.5



TEST NUMBER: P331318-830

CATALOG NUMBER: SA2XXDIP-C485D925U830-4F0-1E-UDD-F

CANDELA DISTRIBUTION (continued):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	425.4	429.0	432.5	436.1	439.6	434.6	420.9	407.3	393.6	379.9	310.2
115°	494.9	498.2	501.4	504.7	507.9	512.0	516.8	521.6	526.3	531.1	442.5
117.5°	557.1	560.7	564.4	568.1	571.7	575.1	578.4	581.7	585.0	588.2	566.8
120°	602.6	605.4	608.3	611.1	614.1	617.2	620.7	624.1	627.5	630.9	633.3
122.5°	641.1	644.1	647.1	650.2	653.2	656.6	660.3	664.1	667.9	671.7	673.0
125°	699.8	702.3	704.8	707.3	709.8	712.8	716.5	720.1	723.8	727.4	728.8
127.5°	753.0	755.8	758.6	761.3	764.0	766.8	769.5	772.2	775.0	777.7	779.6
130°	786.8	789.9	792.9	796.0	799.0	801.6	803.7	805.8	807.9	810.0	812.1
132.5°	821.2	823.8	826.4	829.1	831.6	834.0	836.1	838.2	840.3	842.4	844.2
135°	866.0	869.0	872.1	875.2	878.3	880.6	882.3	884.1	885.8	887.5	889.4
137.5°	911.3	913.4	915.6	917.7	919.8	921.9	923.8	925.8	927.7	929.7	931.5
140°	940.8	942.4	944.0	945.5	947.0	948.9	950.9	953.0	955.2	957.2	958.9
142.5°	965.6	967.0	968.5	969.8	971.2	973.1	975.4	977.9	980.3	982.7	984.3
145°	1004.6	1004.4	1004.2	1004.0	1003.8	1005.3	1008.6	1011.8	1015.1	1018.3	1019.6
147.5°	1038.5	1037.7	1037.1	1036.3	1035.6	1036.8	1040.0	1043.3	1046.5	1049.7	1050.7
150°	1060.5	1059.2	1057.8	1056.5	1055.2	1056.0	1059.1	1062.2	1065.3	1068.3	1069.4
152.5°	1079.1	1077.6	1076.1	1074.7	1073.2	1073.8	1076.8	1079.7	1082.6	1085.5	1086.7
155°	1106.2	1104.5	1102.7	1101.0	1099.3	1099.6	1101.8	1104.2	1106.5	1108.7	1109.8
157.5°	1127.3	1125.9	1124.5	1122.9	1121.5	1121.6	1123.2	1124.8	1126.4	1128.0	1129.4
160°	1139.7	1138.6	1137.5	1136.2	1135.1	1135.1	1136.2	1137.5	1138.6	1139.7	1140.9
162.5°	1150.8	1149.6	1148.5	1147.3	1146.1	1146.0	1147.1	1148.0	1149.1	1150.1	1151.3
165°	1165.5	1164.4	1163.3	1162.1	1160.9	1160.6	1161.2	1161.8	1162.4	1163.0	1164.3
167.5°	1176.6	1175.4	1174.3	1173.1	1172.0	1171.7	1172.2	1172.7	1173.3	1173.8	1175.2
170°	1182.8	1181.6	1180.4	1179.3	1178.2	1177.8	1178.2	1178.6	1178.9	1179.3	1180.6
172.5°	1186.8	1185.7	1184.6	1183.5	1182.3	1181.9	1182.3	1182.7	1183.1	1183.5	1184.8
175°	1192.2	1190.9	1189.6	1188.2	1186.8	1186.4	1186.8	1187.1	1187.5	1187.9	1189.3
177.5°	1193.1	1192.0	1191.0	1189.9	1188.8	1188.4	1188.5	1188.6	1188.8	1188.9	1190.1
180°	1189.7	1189.7	1189.7	1189.7	1189.7	1189.7	1189.7	1189.7	1189.7	1189.7	1189.7



TEST NUMBER: P331318-830

CATALOG NUMBER: SA2XXDIP-C485D925U830-4F0-1E-UDD-F

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°
0°	732.1	732.1	732.1	732.1	732.1	732.1	732.1	732.1
2.5°	729.0	730.2	731.4	732.0	731.7	731.4	731.2	730.9
5°	724.1	725.3	726.5	727.0	726.7	726.3	726.0	725.8
7.5°	715.9	717.1	718.4	718.8	718.5	718.1	717.7	717.5
10°	708.5	709.8	711.1	711.4	711.0	710.5	710.0	709.5
12.5°	699.9	700.8	701.6	701.9	701.5	701.3	700.9	700.5
15°	684.8	685.4	686.0	685.9	685.1	684.4	683.6	682.8
17.5°	666.8	667.5	668.3	668.2	667.4	666.8	666.0	665.2
20°	652.8	653.3	653.7	653.7	653.0	652.3	651.8	651.1
22.5°	637.9	638.0	638.1	638.0	637.6	637.3	636.9	636.5
25°	613.8	614.1	614.3	614.3	614.1	613.8	613.4	613.1
27.5°	589.9	589.5	589.0	588.4	587.7	586.9	586.2	585.4
30°	571.4	570.9	570.4	569.9	569.2	568.6	568.0	567.3
32.5°	553.2	552.3	551.5	550.7	550.1	549.5	548.8	548.2
35°	524.0	523.0	522.1	521.2	520.5	519.6	518.9	518.1
37.5°	494.6	493.5	492.4	491.3	490.6	489.8	489.1	488.4
40°	474.5	473.1	471.6	470.6	470.0	469.4	468.7	468.1
42.5°	454.5	453.0	451.4	450.3	449.3	448.5	447.6	446.7
45°	423.9	422.2	420.4	419.2	418.6	418.0	417.4	416.7
47.5°	392.0	390.1	388.3	387.0	386.1	385.2	384.3	383.3
50°	371.6	369.3	367.1	365.6	364.9	364.1	363.3	362.5
52.5°	350.3	348.5	346.7	345.3	344.2	343.2	342.1	341.1
55°	318.7	316.8	314.9	313.6	312.7	312.0	311.2	310.5
57.5°	285.8	283.9	282.1	280.9	280.2	279.7	279.1	278.4
60°	264.0	262.3	260.6	259.5	259.0	258.5	258.1	257.6
62.5°	243.5	241.9	240.3	239.2	238.6	238.0	237.4	236.8
65°	211.9	210.5	209.1	207.9	207.2	206.4	205.7	204.8
67.5°	180.7	179.6	178.5	177.7	177.0	176.3	175.8	175.1
70°	160.4	159.3	158.3	157.4	156.7	156.1	155.5	154.9
72.5°	141.3	140.2	139.1	138.3	137.8	137.2	136.8	136.3
75°	111.4	110.6	109.6	109.2	109.6	109.9	110.2	110.6
77.5°	84.8	84.4	83.9	83.4	82.9	82.6	82.1	81.6
80°	67.3	66.8	66.4	66.0	65.7	65.4	65.0	64.8
82.5°	50.2	49.6	49.0	48.6	48.6	48.5	48.4	48.4
85°	26.5	26.0	25.5	25.3	25.1	25.0	24.8	24.6
87.5°	10.9	10.7	10.6	10.5	10.5	10.4	10.4	10.3
90°	19.1	20.1	21.0	21.7	22.1	22.4	22.9	23.3
92.5°	20.9	21.5	22.0	22.3	22.5	22.8	23.0	23.3
95°	35.4	36.5	37.4	37.8	37.6	37.4	37.2	37.0
97.5°	46.5	47.2	48.0	48.4	48.7	48.9	49.2	49.4
100°	52.1	53.6	55.2	56.2	56.6	56.9	57.3	57.7
102.5°	54.4	56.5	58.4	59.7	60.2	60.7	61.3	61.8
105°	56.7	58.8	60.9	62.4	63.2	63.9	64.7	65.4
107.5°	69.2	67.1	64.9	64.3	65.0	65.8	66.5	67.3
110°	112.4	93.2	74.1	64.9	65.7	66.4	67.2	68.1



TEST NUMBER: P331318-830

CATALOG NUMBER: SA2XXDIP-C485D925U830-4F0-1E-UDD-F

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°
112.5°	240.4	170.6	100.9	66.3	66.8	67.5	68.1	68.7
115°	354.0	265.4	176.8	125.6	111.9	98.1	84.4	70.6
117.5°	545.4	524.1	502.6	469.2	424.0	378.7	333.5	288.2
120°	635.6	637.9	640.2	628.4	602.6	576.7	550.9	525.1
122.5°	674.4	675.7	677.1	675.3	670.3	665.2	660.3	655.3
125°	730.1	731.4	732.7	733.7	734.2	734.8	735.5	736.0
127.5°	781.6	783.5	785.5	786.5	786.6	786.7	786.8	786.9
130°	814.3	816.3	818.4	819.4	819.3	819.0	818.8	818.6
132.5°	846.0	847.8	849.6	850.4	850.2	850.0	849.8	849.6
135°	891.4	893.2	895.1	895.9	895.5	895.1	894.8	894.4
137.5°	933.4	935.3	937.2	937.8	937.2	936.5	935.9	935.2
140°	960.6	962.4	964.1	964.5	963.6	962.6	961.7	960.6
142.5°	985.8	987.4	989.0	989.3	988.4	987.4	986.5	985.4
145°	1021.1	1022.4	1023.7	1023.9	1022.9	1022.0	1021.1	1020.1
147.5°	1051.7	1052.6	1053.7	1053.8	1052.9	1052.2	1051.3	1050.6
150°	1070.5	1071.8	1072.9	1073.0	1072.0	1071.0	1070.1	1069.1
152.5°	1087.8	1088.9	1090.1	1090.1	1088.7	1087.5	1086.3	1085.0
155°	1111.1	1112.2	1113.3	1113.1	1111.6	1110.0	1108.5	1107.0
157.5°	1130.6	1131.9	1133.2	1133.1	1131.6	1130.1	1128.6	1127.2
160°	1142.0	1143.2	1144.3	1144.2	1142.8	1141.5	1140.2	1138.9
162.5°	1152.6	1154.0	1155.3	1155.1	1153.5	1151.8	1150.2	1148.5
165°	1165.6	1167.0	1168.3	1168.3	1167.0	1165.6	1164.3	1163.0
167.5°	1176.5	1177.8	1179.2	1178.9	1177.2	1175.5	1173.8	1172.1
170°	1182.0	1183.4	1184.7	1184.5	1182.8	1181.0	1179.3	1177.6
172.5°	1186.1	1187.5	1188.8	1188.6	1186.8	1185.2	1183.5	1181.8
175°	1190.6	1191.9	1193.3	1193.0	1191.1	1189.2	1187.2	1185.3
177.5°	1191.1	1192.2	1193.3	1193.1	1191.8	1190.3	1188.9	1187.6
180°	1189.7	1189.7	1189.7	1189.7	1189.7	1189.7	1189.7	1189.7

(END OF REPORT)