

Scaled data based on original data using  
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State  
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P333224-840

Luminaire Tested: **S125DIP-S850D810U840-4F0-1E-UDD-A1**

Issue Date: 3/3/2020

**Test Information**

Test Method: LM-79-08  
Report Number: P333224-840  
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-11,  
Test Lab: INNOVATION CENTER  
Issue Date: 3/3/2020  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: NEO-RAY  
Catalog Number: S125DIP-S850D810U840-4F0-1E-UDD-A1  
Description: DEFINE 5 DIRECT-INDIRECT PENDANT LED LUMINAIRE  
DOWNLIGHT 850 LUMENS PER FOOT, ASYMMETRIC DIFFUSER  
UPLIGHT 810 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER  
Light Source: -  
Ballast/Driver: ELECTRONIC DRIVER

**Summary**


Lumens per Lamp: N/A  
Luminaire Lumens: 6319.9 lumens  
Efficiency: N/A  
Efficacy: 137.7 lumens/watt  
Spacing Criteria (0/90/45): 1.43 / 1.23 / 1.52  
Luminous Opening: Rectangular (W 4' x L: 0.42' x H: 0')  
CIE Type: General Diffuse  
  
Input Watts (W): 45.9  
Input Voltage (V): 120  
Input Current (Ain): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 25 FT



TEST NUMBER: P333224-840

CATALOG NUMBER: S125DIP-S850D810U840-4F0-1E-UDD-A1

### Luminous Intensity Polar Plot





TEST NUMBER: P333224-840

CATALOG NUMBER: S125DIP-S850D810U840-4F0-1E-UDD-A1

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	108	108	108	108	101	101	101	101	86	86	86	73	73	73	61	61	61	55
1	99	95	91	88	92	88	85	82	76	74	71	65	63	61	54	53	52	47
2	91	83	77	72	84	78	72	68	67	63	59	57	54	52	48	46	44	40
3	83	73	66	60	77	68	62	57	59	54	50	51	47	44	43	40	38	34
4	76	65	57	51	70	61	54	48	53	47	43	45	41	38	38	35	33	29
5	70	58	50	44	64	54	47	42	47	42	37	41	36	33	35	31	29	25
6	64	52	44	38	59	49	42	36	43	37	32	37	32	29	31	28	25	22
7	59	47	39	33	55	44	37	32	39	33	29	33	29	26	29	25	22	20
8	55	43	35	30	51	40	33	28	35	30	25	31	26	23	26	23	20	18
9	51	39	32	26	48	37	30	25	32	27	23	28	24	20	24	21	18	16
10	48	36	29	24	45	34	27	23	30	24	21	26	22	18	22	19	16	14

**AVERAGE LUMINANCE (cd/sqm):**

	0°	90°	180°	270°
0°	7979	7979	7979	7979
5°	9240	8006	7010	8006
10°	10750	7965	6142	7965
15°	11900	7906	5666	7906
20°	13320	7813	5283	7813
25°	15605	7709	5097	7709
30°	16855	7607	4935	7607
35°	13858	7413	4829	7413
40°	9850	7144	4713	7144
45°	7567	6783	4646	6783
50°	6459	6333	4636	6333
55°	5751	5892	4677	5892
60°	5187	5412	4795	5412
65°	4792	4927	4919	4927
70°	4358	4426	4991	4426
75°	3848	3898	4946	3898
80°	3239	3176	4526	3176
85°	2564	2290	3653	2290



TEST NUMBER: P333224-840

CATALOG NUMBER: S125DIP-S850D810U840-4F0-1E-UDD-A1

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	118.9	1.9
10°-20°	354.1	5.6
20°-30°	575.0	9.1
30°-40°	701.4	11.1
40°-50°	638.1	10.1
50°-60°	508.2	8.0
60°-70°	354.0	5.6
70°-80°	188.8	3.0
80°-90°	49.9	0.8
90°-100°	68.0	1.1
100°-110°	200.7	3.2
110°-120°	339.9	5.4
120°-130°	447.4	7.1
130°-140°	501.3	7.9
140°-150°	491.3	7.8
150°-160°	412.7	6.5
160°-170°	274.3	4.3
170°-180°	96.0	1.5
0°-30°	1048.1	16.6
0°-40°	1749.5	27.7
0°-60°	2895.8	45.8
0°-90°	3488.4	55.2
90°-120°	608.6	9.6
90°-150°	2048.6	32.4
90°-180°	2832.0	44.8
0°-180°	6319.9	100.0

**CANDELA DISTRIBUTION:**

	0°	90°	180°	270°	360°	Flux
0°	1236	1236	1236	1236	1236	
5°	1425	1235	1081	1235	1425	144
15°	1780	1182	847	1182	1780	509
25°	2190	1082	715	1082	2190	1000
35°	1758	940	612	940	1758	1076
45°	828	743	509	743	828	663
55°	511	523	415	523	511	460
65°	314	322	322	322	314	311
75°	154	156	198	156	154	166
85°	35	31	49	31	35	40
90°	19	1	19	1	19	12
95°	68	51	68	51	68	69
105°	196	180	196	180	196	207
115°	344	340	344	340	344	340
125°	500	497	500	497	500	446
135°	648	646	648	646	648	500
145°	786	782	786	782	786	490
155°	895	895	895	895	895	412
165°	971	974	971	974	971	274
175°	1008	1012	1008	1012	1008	96
180°	1015	1015	1015	1015	1015	



TEST NUMBER: P333224-840

CATALOG NUMBER: S125DIP-S850D810U840-4F0-1E-UDD-A1

**CANDELA DISTRIBUTION (FULL):**

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	1235.5	1235.5	1235.5	1235.5	1235.5	1235.5	1235.5	1235.5	1235.5	1235.5	1235.5
2.5°	1306.8	1305.0	1303.4	1300.0	1302.5	1295.5	1292.0	1286.2	1279.1	1276.6	1273.6
5°	1425.2	1427.8	1430.5	1419.5	1420.6	1413.2	1396.4	1382.8	1371.8	1357.7	1347.7
7.5°	1567.9	1561.7	1561.2	1554.1	1541.8	1532.0	1514.3	1491.9	1470.2	1445.4	1424.9
10°	1639.2	1639.7	1635.0	1626.6	1613.6	1604.1	1581.0	1558.9	1532.3	1500.8	1478.2
12.5°	1692.9	1695.1	1689.1	1677.8	1671.4	1650.2	1632.1	1606.0	1574.2	1549.0	1514.7
15°	1779.8	1773.9	1769.8	1755.7	1744.6	1722.6	1693.7	1666.5	1631.8	1599.8	1567.9
17.5°	1863.4	1868.0	1860.2	1847.2	1813.1	1787.4	1748.7	1711.3	1668.3	1625.4	1587.2
20°	1938.1	1942.3	1930.3	1907.7	1866.8	1841.1	1790.2	1742.0	1692.1	1637.1	1595.2
22.5°	2031.2	2027.9	2011.7	1977.3	1941.9	1894.4	1839.3	1780.6	1718.2	1656.0	1600.2
25°	2189.8	2167.8	2157.8	2115.4	2068.7	1998.9	1923.4	1837.4	1759.8	1677.5	1606.2
27.5°	2277.6	2270.8	2259.7	2230.1	2181.0	2106.5	2017.4	1912.6	1803.1	1699.2	1605.9
30°	2260.1	2261.1	2262.2	2252.7	2221.3	2165.2	2076.6	1963.8	1833.7	1716.8	1608.8
32.5°	2104.1	2123.1	2141.3	2162.9	2171.7	2161.0	2105.5	2003.7	1869.9	1737.0	1607.1
35°	1757.7	1763.5	1822.7	1881.5	1961.2	2023.1	2064.5	2019.4	1906.6	1754.0	1605.1
37.5°	1370.5	1398.9	1439.9	1506.2	1621.2	1724.2	1856.7	1917.6	1881.3	1759.6	1601.4
40°	1168.3	1194.6	1221.2	1288.9	1385.9	1510.8	1661.2	1789.7	1819.6	1742.0	1588.8
42.5°	1012.3	1033.0	1062.7	1113.6	1194.7	1305.1	1449.0	1616.9	1720.2	1690.8	1562.5
45°	828.5	841.6	864.7	905.0	963.8	1050.4	1177.2	1360.8	1520.7	1573.7	1499.8
47.5°	709.1	709.0	727.0	754.9	797.3	870.8	964.6	1108.4	1279.3	1405.6	1399.8
50°	642.9	640.3	654.4	678.5	712.1	760.8	850.5	965.3	1129.5	1272.6	1312.5
52.5°	585.8	586.1	594.8	612.7	640.8	682.5	749.4	852.9	993.2	1140.1	1215.2
55°	510.8	508.7	518.6	530.7	551.1	578.3	626.6	705.8	819.6	964.3	1061.9
57.5°	441.9	447.7	451.7	460.1	477.1	495.3	536.0	594.1	684.4	808.6	911.7
60°	401.6	407.5	410.6	419.0	432.6	448.4	479.8	527.0	603.0	710.0	812.2
62.5°	365.6	370.1	371.1	378.7	389.8	405.2	429.9	469.5	529.6	623.2	723.4
65°	313.6	313.6	315.7	323.6	328.8	342.4	361.3	390.1	438.4	511.3	596.7
67.5°	263.5	266.0	265.4	268.9	273.8	284.3	297.8	321.6	357.4	410.6	479.0
70°	230.8	232.8	232.3	234.9	240.1	247.0	258.0	280.5	306.2	351.8	410.6
72.5°	201.4	202.2	200.9	204.3	207.4	213.4	225.7	237.7	261.8	300.2	348.5
75°	154.2	155.2	156.2	158.3	161.5	164.6	171.0	183.0	198.7	227.6	258.5
77.5°	115.5	113.6	116.1	115.8	117.5	120.0	125.5	131.9	144.8	163.1	187.0
80°	87.1	87.6	87.6	88.1	90.7	92.3	97.0	101.7	111.7	125.3	142.1
82.5°	63.5	64.9	64.1	65.0	67.3	68.4	71.0	74.8	80.7	91.4	103.5
85°	34.6	32.0	33.0	34.1	34.1	34.6	36.7	38.3	41.4	45.6	50.3
87.5°	13.8	14.5	14.9	14.8	15.1	14.9	16.5	16.3	17.4	18.5	19.9
90°	19.0	18.4	17.9	17.4	16.9	16.2	15.2	14.3	13.5	12.6	11.4
92.5°	37.3	36.9	36.5	36.2	35.7	34.9	33.8	32.6	31.5	30.3	28.8
95°	67.9	67.6	67.3	66.9	66.6	65.7	64.5	63.2	62.0	60.8	59.1
97.5°	103.0	102.8	102.5	102.3	102.1	101.5	100.3	99.2	98.0	96.8	94.4
100°	129.5	129.2	128.8	128.5	128.2	127.1	125.5	124.0	122.4	120.8	118.6
102.5°	156.0	155.5	155.0	154.6	154.1	153.0	151.3	149.6	147.8	146.1	144.9
105°	195.8	195.3	194.8	194.3	193.7	193.0	191.9	190.9	189.8	188.7	187.6
107.5°	236.6	236.6	236.6	236.7	236.7	236.5	235.9	235.4	234.9	234.4	233.6
110°	266.9	267.1	267.2	267.4	267.6	267.4	266.9	266.4	265.9	265.3	264.8



TEST NUMBER: P333224-840

CATALOG NUMBER: S125DIP-S850D810U840-4F0-1E-UDD-A1

**CANDELA DISTRIBUTION (continued):**

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	296.6	296.9	297.2	297.5	297.9	297.9	297.6	297.4	297.2	296.9	296.3
115°	343.6	343.7	343.9	344.1	344.2	344.4	344.6	344.8	344.9	345.1	344.8
117.5°	389.3	390.0	390.7	391.4	392.1	392.4	392.2	392.1	391.9	391.8	391.5
120°	420.9	421.6	422.3	423.0	423.7	424.0	424.0	424.0	424.0	424.0	423.8
122.5°	452.5	453.0	453.6	454.1	454.7	455.0	455.2	455.3	455.4	455.7	455.1
125°	499.9	500.1	500.2	500.4	500.6	500.8	501.2	501.5	501.9	502.2	502.0
127.5°	545.3	545.7	546.0	546.4	546.7	547.0	547.1	547.3	547.5	547.8	547.5
130°	575.6	576.0	576.3	576.7	577.0	577.3	577.5	577.6	577.8	578.0	577.6
132.5°	604.1	604.6	605.1	605.6	606.0	606.4	606.5	606.7	606.9	607.1	607.1
135°	648.3	649.0	649.7	650.5	651.2	651.5	651.5	651.5	651.5	651.5	651.3
137.5°	691.6	692.5	693.4	694.2	695.1	695.4	695.2	695.0	694.8	694.6	694.2
140°	719.4	720.2	721.1	722.1	722.9	723.2	722.8	722.5	722.2	721.8	721.2
142.5°	745.9	746.8	747.7	748.5	749.4	749.7	749.5	749.3	749.1	748.9	748.2
145°	785.7	786.3	786.8	787.3	787.8	788.1	788.1	788.1	788.1	788.1	787.6
147.5°	819.7	820.9	822.0	823.2	824.5	824.9	824.5	823.9	823.5	823.1	822.7
150°	845.0	845.3	845.7	846.0	846.4	846.6	846.6	846.6	846.6	846.6	845.9
152.5°	865.8	866.5	867.1	867.7	868.3	868.4	868.0	867.6	867.2	866.8	866.5
155°	895.4	896.4	897.3	898.1	899.0	899.1	898.4	897.7	897.0	896.3	896.1
157.5°	920.3	921.4	922.6	923.7	924.9	925.1	924.4	923.7	923.0	922.3	922.1
160°	937.4	938.2	939.1	940.0	940.9	940.9	940.2	939.6	938.9	938.2	938.0
162.5°	951.9	952.9	953.9	954.9	955.9	956.0	955.2	954.3	953.5	952.7	952.6
165°	971.3	972.3	973.4	974.4	975.5	975.6	975.0	974.3	973.6	972.9	972.7
167.5°	986.7	987.8	989.0	990.1	991.1	991.2	990.1	989.1	988.0	986.9	986.9
170°	995.0	996.2	997.4	998.7	999.9	1000.0	999.0	997.8	996.8	995.7	995.7
172.5°	1001.9	1003.0	1004.1	1005.2	1006.3	1006.3	1005.2	1004.2	1003.1	1002.1	1002.1
175°	1008.5	1009.7	1010.9	1012.1	1013.3	1013.4	1012.4	1011.3	1010.3	1009.2	1009.2
177.5°	1012.2	1013.2	1014.2	1015.1	1016.1	1016.2	1015.3	1014.5	1013.7	1012.8	1013.0
180°	1014.7	1014.7	1014.7	1014.7	1014.7	1014.7	1014.7	1014.7	1014.7	1014.7	1014.7



TEST NUMBER: P333224-840

CATALOG NUMBER: S125DIP-S850D810U840-4F0-1E-UDD-A1

**CANDELA DISTRIBUTION (continued):**

	55°	60°	65°	70°	75°	80°	85°	90°	95°	100°	105°
0°	1235.5	1235.5	1235.5	1235.5	1235.5	1235.5	1235.5	1235.5	1235.5	1235.5	1235.5
2.5°	1271.1	1268.2	1264.8	1258.9	1251.8	1248.0	1242.1	1238.4	1230.8	1224.6	1217.8
5°	1335.5	1321.9	1309.4	1293.1	1275.3	1263.7	1250.1	1234.9	1219.2	1203.0	1185.1
7.5°	1402.4	1378.3	1352.0	1323.8	1296.3	1270.9	1246.7	1222.8	1200.6	1173.8	1151.0
10°	1447.2	1416.8	1384.3	1346.0	1308.9	1276.4	1243.3	1214.5	1185.1	1153.7	1125.8
12.5°	1492.2	1451.7	1405.7	1363.7	1318.9	1279.7	1240.8	1204.0	1167.1	1132.3	1099.8
15°	1523.9	1488.1	1445.7	1385.9	1335.5	1281.6	1230.2	1182.5	1137.9	1099.1	1058.2
17.5°	1544.7	1498.7	1453.2	1395.8	1329.8	1269.4	1211.2	1156.6	1106.3	1057.1	1017.7
20°	1548.5	1501.3	1453.6	1397.5	1329.8	1260.6	1202.4	1136.8	1082.9	1032.0	983.7
22.5°	1547.2	1493.8	1441.8	1384.0	1318.1	1254.4	1184.0	1117.1	1058.5	1008.5	958.2
25°	1535.4	1478.2	1413.2	1355.0	1290.0	1222.3	1151.0	1081.8	1022.0	964.8	915.0
27.5°	1525.5	1451.4	1377.8	1309.9	1247.1	1185.1	1116.8	1045.9	979.7	921.7	874.7
30°	1513.4	1432.1	1349.2	1278.4	1214.0	1153.7	1089.1	1020.0	950.7	894.0	843.7
32.5°	1502.5	1407.8	1320.3	1243.2	1174.9	1116.3	1056.8	991.0	923.0	865.6	815.2
35°	1481.4	1371.8	1271.6	1184.6	1111.7	1051.4	1001.6	940.2	877.8	822.2	774.0
37.5°	1454.6	1324.5	1217.1	1125.8	1045.9	982.4	936.0	888.9	829.0	775.5	731.8
40°	1433.6	1291.0	1177.2	1083.9	1001.1	934.9	892.0	847.4	797.6	747.8	701.7
42.5°	1407.2	1260.8	1137.0	1036.5	954.4	890.1	845.0	807.1	763.2	716.7	673.9
45°	1358.7	1206.1	1071.9	963.8	880.9	817.5	770.8	742.6	709.5	665.4	629.2
47.5°	1287.3	1140.3	1001.5	890.0	804.5	745.7	702.0	674.8	651.5	618.7	585.9
50°	1223.9	1091.3	950.7	840.0	754.6	695.3	655.0	630.3	610.4	585.2	557.4
52.5°	1153.0	1029.6	900.8	791.4	706.8	648.3	608.8	587.1	570.6	552.5	525.1
55°	1040.4	935.5	816.0	712.1	634.0	576.8	542.2	523.3	509.7	496.0	479.3
57.5°	916.3	834.2	728.3	633.5	561.5	509.5	477.2	458.8	448.3	441.2	431.3
60°	829.0	758.8	667.5	581.0	510.8	464.6	433.1	419.0	410.1	404.2	397.0
62.5°	748.1	690.4	605.8	526.8	465.4	421.8	393.7	380.0	371.4	368.6	362.5
65°	628.7	584.2	514.4	448.9	396.5	359.2	335.6	322.4	317.2	314.1	314.7
67.5°	511.2	484.0	428.0	372.1	330.2	299.0	280.1	270.0	267.4	263.3	263.2
70°	439.4	419.0	371.8	323.1	285.8	261.7	244.9	234.4	231.8	229.6	229.1
72.5°	376.1	358.2	317.2	278.1	244.7	223.5	209.6	203.4	199.0	197.8	197.7
75°	282.7	272.7	240.1	209.2	186.1	171.5	162.1	156.2	153.1	152.6	153.1
77.5°	201.0	192.3	171.6	149.7	135.1	124.0	116.0	114.0	110.5	110.6	110.0
80°	151.0	145.2	132.2	114.8	102.8	93.3	89.2	85.4	84.4	82.8	84.4
82.5°	109.5	103.3	94.4	83.4	73.4	67.8	63.5	62.4	61.8	61.0	61.4
85°	54.0	54.5	49.3	40.9	36.7	33.5	30.9	30.9	30.4	29.9	30.4
87.5°	20.5	19.4	17.5	16.0	13.6	12.0	11.3	11.5	10.5	10.4	11.1
90°	10.2	9.0	7.7	6.4	5.0	3.6	2.2	0.8	2.2	3.6	5.0
92.5°	27.3	25.8	24.2	23.0	22.0	21.1	20.1	19.1	20.1	21.1	22.0
95°	57.3	55.5	53.8	52.7	52.4	52.0	51.7	51.3	51.7	52.0	52.4
97.5°	92.0	89.6	87.2	85.8	85.7	85.5	85.4	85.3	85.4	85.5	85.7
100°	116.2	114.0	111.7	110.6	110.6	110.6	110.6	110.6	110.6	110.6	110.6
102.5°	143.8	142.6	141.5	140.6	139.9	139.2	138.5	137.7	138.5	139.2	139.9
105°	186.6	185.6	184.5	183.6	182.7	181.8	181.0	180.1	181.0	181.8	182.7
107.5°	232.8	232.0	231.2	230.4	229.4	228.5	227.6	226.8	227.6	228.5	229.4
110°	264.3	263.8	263.3	262.6	261.7	260.7	259.9	259.0	259.9	260.7	261.7





TEST NUMBER: P333224-840

CATALOG NUMBER: S125DIP-S850D810U840-4F0-1E-UDD-A1

**CANDELA DISTRIBUTION (continued):**

	55°	60°	65°	70°	75°	80°	85°	90°	95°	100°	105°
112.5°	295.6	294.9	294.3	293.7	293.3	292.8	292.4	291.9	292.4	292.8	293.3
115°	344.4	344.1	343.7	343.2	342.4	341.7	341.0	340.3	341.0	341.7	342.4
117.5°	391.2	390.9	390.6	390.2	389.9	389.6	389.3	389.0	389.3	389.6	389.9
120°	423.7	423.5	423.3	422.8	421.9	421.1	420.2	419.3	420.2	421.1	421.9
122.5°	454.7	454.2	453.8	453.4	453.1	452.8	452.5	452.1	452.5	452.8	453.1
125°	501.9	501.7	501.5	500.9	499.9	498.8	497.8	496.7	497.8	498.8	499.9
127.5°	547.2	547.0	546.8	546.4	545.8	545.2	544.7	544.1	544.7	545.2	545.8
130°	577.3	576.9	576.6	576.0	575.1	574.3	573.4	572.5	573.4	574.3	575.1
132.5°	607.2	607.3	607.3	606.7	605.2	603.8	602.4	601.0	602.4	603.8	605.2
135°	651.2	651.0	650.8	650.2	649.1	648.0	647.0	645.9	647.0	648.0	649.1
137.5°	693.8	693.5	693.1	692.4	691.4	690.3	689.3	688.3	689.3	690.3	691.4
140°	720.7	720.1	719.6	718.9	718.1	717.2	716.3	715.5	716.3	717.2	718.1
142.5°	747.6	746.9	746.3	745.6	744.8	744.1	743.4	742.7	743.4	744.1	744.8
145°	787.0	786.5	786.0	785.4	784.7	784.0	783.3	782.5	783.3	784.0	784.7
147.5°	822.3	821.9	821.4	821.0	820.7	820.3	819.9	819.5	819.9	820.3	820.7
150°	845.2	844.4	843.7	843.4	843.6	843.8	843.9	844.1	843.9	843.8	843.6
152.5°	866.2	865.9	865.7	865.4	865.2	864.8	864.6	864.3	864.6	864.8	865.2
155°	896.0	895.8	895.5	895.4	895.4	895.4	895.4	895.4	895.4	895.4	895.4
157.5°	922.0	921.8	921.6	921.7	922.1	922.5	922.9	923.3	922.9	922.5	922.1
160°	937.8	937.6	937.5	937.6	938.2	938.7	939.2	939.7	939.2	938.7	938.2
162.5°	952.6	952.5	952.5	952.7	953.1	953.4	953.8	954.2	953.8	953.4	953.1
165°	972.5	972.3	972.2	972.3	972.6	973.0	973.3	973.7	973.3	973.0	972.6
167.5°	986.9	986.9	986.9	987.2	988.0	988.7	989.4	990.1	989.4	988.7	988.0
170°	995.7	995.7	995.7	996.1	996.8	997.5	998.3	999.0	998.3	997.5	996.8
172.5°	1002.1	1002.1	1002.1	1002.4	1003.1	1003.8	1004.5	1005.2	1004.5	1003.8	1003.1
175°	1009.2	1009.2	1009.2	1009.6	1010.3	1011.0	1011.7	1012.4	1011.7	1011.0	1010.3
177.5°	1013.1	1013.3	1013.4	1013.7	1014.3	1014.9	1015.4	1016.0	1015.4	1014.9	1014.3
180°	1014.7	1014.7	1014.7	1014.7	1014.7	1014.7	1014.7	1014.7	1014.7	1014.7	1014.7



TEST NUMBER: P333224-840

CATALOG NUMBER: S125DIP-S850D810U840-4F0-1E-UDD-A1

**CANDELA DISTRIBUTION (continued):**

	110°	115°	120°	125°	130°	135°	140°	145°	150°	155°	160°
0°	1235.5	1235.5	1235.5	1235.5	1235.5	1235.5	1235.5	1235.5	1235.5	1235.5	1235.5
2.5°	1214.1	1209.4	1205.7	1197.3	1192.7	1186.4	1181.3	1186.8	1180.9	1183.5	1179.6
5°	1176.2	1161.5	1151.0	1135.8	1122.7	1110.6	1101.8	1100.1	1095.9	1093.9	1087.5
7.5°	1130.6	1112.3	1094.3	1074.4	1057.5	1040.5	1029.6	1020.6	1014.6	1006.7	1001.4
10°	1103.8	1079.1	1058.2	1034.1	1013.1	994.7	980.1	972.7	965.9	955.9	952.3
12.5°	1070.7	1045.2	1019.6	993.8	973.7	953.2	940.6	929.5	924.8	913.5	912.4
15°	1031.0	992.7	967.5	941.3	913.4	896.7	886.2	874.1	868.9	861.0	855.3
17.5°	983.5	949.4	917.9	890.7	866.9	852.7	839.7	831.4	822.4	817.3	807.9
20°	949.2	916.7	885.1	856.3	838.0	821.7	811.2	803.3	794.0	791.3	781.8
22.5°	920.2	884.3	854.1	829.9	809.8	791.5	780.1	774.9	768.3	760.2	758.3
25°	873.1	835.9	810.2	786.1	768.2	751.4	743.6	736.8	730.4	724.7	722.6
27.5°	832.4	799.1	768.6	746.8	731.3	716.0	709.0	700.7	696.2	691.6	685.9
30°	803.9	769.8	743.1	722.1	705.3	691.7	684.3	678.5	674.4	670.1	667.0
32.5°	774.5	743.0	717.0	696.5	679.7	669.4	662.9	658.8	654.2	649.1	645.2
35°	735.7	701.0	675.9	658.1	645.0	637.1	629.8	626.1	620.9	620.9	616.6
37.5°	692.0	662.1	639.9	623.6	611.9	604.8	596.8	594.3	591.0	588.8	587.3
40°	666.0	638.1	617.2	601.0	588.3	582.6	576.3	572.1	570.0	567.3	566.3
42.5°	639.1	612.6	592.5	577.4	566.5	561.6	555.7	552.8	548.6	545.1	544.5
45°	598.3	572.6	554.3	542.2	532.8	527.0	523.3	517.1	514.9	510.8	510.2
47.5°	559.6	534.9	516.9	507.1	498.8	494.0	488.3	482.0	479.6	477.5	477.3
50°	530.7	508.2	491.3	481.9	474.0	467.3	461.4	457.3	455.7	455.7	456.8
52.5°	501.3	482.1	467.9	456.4	448.9	441.6	436.3	433.7	431.3	433.8	435.8
55°	458.3	438.9	428.4	417.4	410.1	401.6	399.1	398.0	396.5	400.6	402.7
57.5°	412.8	399.2	386.9	376.0	369.4	364.6	361.0	360.3	363.2	365.3	372.1
60°	383.8	368.1	357.1	348.7	340.8	337.7	336.7	335.6	337.7	343.5	352.3
62.5°	351.9	339.2	327.3	321.0	315.3	310.0	309.8	310.4	314.7	321.2	330.1
65°	305.2	294.2	286.3	278.9	274.3	271.1	272.2	274.3	278.9	287.9	297.8
67.5°	257.7	250.1	243.1	237.1	232.6	232.6	233.7	236.8	242.4	252.7	261.8
70°	227.0	218.6	212.9	210.3	206.6	204.5	207.6	212.9	217.6	227.0	234.9
72.5°	196.4	189.3	184.8	183.0	181.5	179.8	180.8	186.4	192.9	202.3	211.5
75°	151.0	148.3	145.2	143.2	141.6	142.6	143.7	149.0	154.2	164.1	174.6
77.5°	110.2	107.4	105.6	105.1	104.2	104.7	107.8	111.6	116.7	124.0	131.9
80°	83.4	82.3	81.3	80.8	80.8	81.3	85.4	88.1	92.8	99.7	105.9
82.5°	60.7	60.1	59.9	59.8	60.2	60.3	62.8	66.2	70.2	75.3	80.8
85°	32.0	30.9	32.5	33.0	32.0	33.5	34.6	36.7	38.3	40.9	43.5
87.5°	11.8	12.8	12.7	13.3	13.6	14.6	14.4	16.3	17.3	18.4	18.1
90°	6.4	7.7	9.0	10.2	11.4	12.6	13.5	14.3	15.2	16.2	16.9
92.5°	23.0	24.2	25.8	27.3	28.8	30.3	31.5	32.6	33.8	34.9	35.7
95°	52.7	53.8	55.5	57.3	59.1	60.8	62.0	63.2	64.5	65.7	66.6
97.5°	85.8	87.2	89.6	92.0	94.4	96.8	98.0	99.2	100.3	101.5	102.1
100°	110.6	111.7	114.0	116.2	118.6	120.8	122.4	124.0	125.5	127.1	128.2
102.5°	140.6	141.5	142.6	143.8	144.9	146.1	147.8	149.6	151.3	153.0	154.1
105°	183.6	184.5	185.6	186.6	187.6	188.7	189.8	190.9	191.9	193.0	193.7
107.5°	230.4	231.2	232.0	232.8	233.6	234.4	234.9	235.4	235.9	236.5	236.7
110°	262.6	263.3	263.8	264.3	264.8	265.3	265.9	266.4	266.9	267.4	267.6



TEST NUMBER: P333224-840

CATALOG NUMBER: S125DIP-S850D810U840-4F0-1E-UDD-A1

**CANDELA DISTRIBUTION (continued):**

	110°	115°	120°	125°	130°	135°	140°	145°	150°	155°	160°
112.5°	293.7	294.3	294.9	295.6	296.3	296.9	297.2	297.4	297.6	297.9	297.9
115°	343.2	343.7	344.1	344.4	344.8	345.1	344.9	344.8	344.6	344.4	344.2
117.5°	390.2	390.6	390.9	391.2	391.5	391.8	391.9	392.1	392.2	392.4	392.1
120°	422.8	423.3	423.5	423.7	423.8	424.0	424.0	424.0	424.0	424.0	423.7
122.5°	453.4	453.8	454.2	454.7	455.1	455.7	455.4	455.3	455.2	455.0	454.7
125°	500.9	501.5	501.7	501.9	502.0	502.2	501.9	501.5	501.2	500.8	500.6
127.5°	546.4	546.8	547.0	547.2	547.5	547.8	547.5	547.3	547.1	547.0	546.7
130°	576.0	576.6	576.9	577.3	577.6	578.0	577.8	577.6	577.5	577.3	577.0
132.5°	606.7	607.3	607.3	607.2	607.1	607.1	606.9	606.7	606.5	606.4	606.0
135°	650.2	650.8	651.0	651.2	651.3	651.5	651.5	651.5	651.5	651.5	651.2
137.5°	692.4	693.1	693.5	693.8	694.2	694.6	694.8	695.0	695.2	695.4	695.1
140°	718.9	719.6	720.1	720.7	721.2	721.8	722.2	722.5	722.8	723.2	722.9
142.5°	745.6	746.3	746.9	747.6	748.2	748.9	749.1	749.3	749.5	749.7	749.4
145°	785.4	786.0	786.5	787.0	787.6	788.1	788.1	788.1	788.1	788.1	787.8
147.5°	821.0	821.4	821.9	822.3	822.7	823.1	823.5	823.9	824.5	824.9	824.5
150°	843.4	843.7	844.4	845.2	845.9	846.6	846.6	846.6	846.6	846.6	846.4
152.5°	865.4	865.7	865.9	866.2	866.5	866.8	867.2	867.6	868.0	868.4	868.3
155°	895.4	895.5	895.8	896.0	896.1	896.3	897.0	897.7	898.4	899.1	899.0
157.5°	921.7	921.6	921.8	922.0	922.1	922.3	923.0	923.7	924.4	925.1	924.9
160°	937.6	937.5	937.6	937.8	938.0	938.2	938.9	939.6	940.2	940.9	940.9
162.5°	952.7	952.5	952.5	952.6	952.6	952.7	953.5	954.3	955.2	956.0	955.9
165°	972.3	972.2	972.3	972.5	972.7	972.9	973.6	974.3	975.0	975.6	975.5
167.5°	987.2	986.9	986.9	986.9	986.9	986.9	988.0	989.1	990.1	991.2	991.1
170°	996.1	995.7	995.7	995.7	995.7	995.7	996.8	997.8	999.0	1000.0	999.9
172.5°	1002.4	1002.1	1002.1	1002.1	1002.1	1002.1	1003.1	1004.2	1005.2	1006.3	1006.3
175°	1009.6	1009.2	1009.2	1009.2	1009.2	1009.2	1010.3	1011.3	1012.4	1013.4	1013.3
177.5°	1013.7	1013.4	1013.3	1013.1	1013.0	1012.8	1013.7	1014.5	1015.3	1016.2	1016.1
180°	1014.7	1014.7	1014.7	1014.7	1014.7	1014.7	1014.7	1014.7	1014.7	1014.7	1014.7



TEST NUMBER: P333224-840

CATALOG NUMBER: S125DIP-S850D810U840-4F0-1E-UDD-A1

**CANDELA DISTRIBUTION (continued):**

	165°	170°	175°	180°	185°	190°	195°	200°	205°	210°	215°
0°	1235.5	1235.5	1235.5	1235.5	1235.5	1235.5	1235.5	1235.5	1235.5	1235.5	1235.5
2.5°	1177.1	1180.0	1177.5	1180.9	1177.5	1180.0	1177.1	1179.6	1183.5	1180.9	1186.8
5°	1084.9	1080.3	1083.4	1081.3	1083.4	1080.3	1084.9	1087.5	1093.9	1095.9	1100.1
7.5°	999.8	995.2	990.2	987.7	990.2	995.2	999.8	1001.4	1006.7	1014.6	1020.6
10°	946.5	940.7	940.2	936.5	940.2	940.7	946.5	952.3	955.9	965.9	972.7
12.5°	907.5	902.1	896.2	894.6	896.2	902.1	907.5	912.4	913.5	924.8	929.5
15°	852.1	847.9	844.2	847.4	844.2	847.9	852.1	855.3	861.0	868.9	874.1
17.5°	806.1	802.6	801.9	798.1	801.9	802.6	806.1	807.9	817.3	822.4	831.4
20°	777.1	774.5	775.6	768.7	775.6	774.5	777.1	781.8	791.3	794.0	803.3
22.5°	754.1	748.9	748.3	746.9	748.3	748.9	754.1	758.3	760.2	768.3	774.9
25°	717.9	715.3	712.7	715.3	712.7	715.3	717.9	722.6	724.7	730.4	736.8
27.5°	686.3	683.2	682.5	682.8	682.5	683.2	686.3	685.9	691.6	696.2	700.7
30°	667.0	661.8	662.3	661.8	662.3	661.8	667.0	667.0	670.1	674.4	678.5
32.5°	646.0	642.5	641.8	640.8	641.8	642.5	646.0	645.2	649.1	654.2	658.8
35°	615.1	615.1	612.5	612.5	612.5	615.1	615.1	616.6	620.9	620.9	626.1
37.5°	586.0	585.5	583.9	584.2	583.9	585.5	586.0	587.3	588.8	591.0	594.3
40°	564.2	563.7	562.1	559.0	562.1	563.7	564.2	566.3	567.3	570.0	572.1
42.5°	543.2	541.5	540.8	539.7	540.8	541.5	543.2	544.5	545.1	548.6	552.8
45°	510.2	510.2	509.2	508.7	509.2	510.2	510.2	510.2	510.8	514.9	517.1
47.5°	478.2	479.1	481.1	480.8	481.1	479.1	478.2	477.3	477.5	479.6	482.0
50°	458.8	459.4	460.9	461.4	460.9	459.4	458.8	456.8	455.7	455.7	457.3
52.5°	437.5	440.5	442.4	442.1	442.4	440.5	437.5	435.8	433.8	431.3	433.7
55°	407.5	411.1	414.8	415.4	414.8	411.1	407.5	402.7	400.6	396.5	398.0
57.5°	377.8	382.9	386.8	388.0	386.8	382.9	377.8	372.1	365.3	363.2	360.3
60°	357.6	364.5	369.2	371.2	369.2	364.5	357.6	352.3	343.5	337.7	335.6
62.5°	338.3	346.0	350.7	351.1	350.7	346.0	338.3	330.1	321.2	314.7	310.4
65°	306.8	314.7	318.8	321.9	318.8	314.7	306.8	297.8	287.9	278.9	274.3
67.5°	272.8	280.6	285.3	287.8	285.3	280.6	272.8	261.8	252.7	242.4	236.8
70°	248.0	255.9	262.2	264.3	262.2	255.9	248.0	234.9	227.0	217.6	212.9
72.5°	223.7	230.8	235.8	238.2	235.8	230.8	223.7	211.5	202.3	192.9	186.4
75°	181.5	190.9	195.6	198.2	195.6	190.9	181.5	174.6	164.1	154.2	149.0
77.5°	139.9	148.6	151.4	152.7	151.4	148.6	139.9	131.9	124.0	116.7	111.6
80°	112.2	117.4	121.1	121.7	121.1	117.4	112.2	105.9	99.7	92.8	88.1
82.5°	86.2	90.6	91.8	93.1	91.8	90.6	86.2	80.8	75.3	70.2	66.2
85°	47.2	49.3	49.8	49.3	49.8	49.3	47.2	43.5	40.9	38.3	36.7
87.5°	19.0	18.7	18.8	19.7	18.8	18.7	19.0	18.1	18.4	17.3	16.3
90°	17.4	17.9	18.4	19.0	18.4	17.9	17.4	16.9	16.2	15.2	14.3
92.5°	36.2	36.5	36.9	37.3	36.9	36.5	36.2	35.7	34.9	33.8	32.6
95°	66.9	67.3	67.6	67.9	67.6	67.3	66.9	66.6	65.7	64.5	63.2
97.5°	102.3	102.5	102.8	103.0	102.8	102.5	102.3	102.1	101.5	100.3	99.2
100°	128.5	128.8	129.2	129.5	129.2	128.8	128.5	128.2	127.1	125.5	124.0
102.5°	154.6	155.0	155.5	156.0	155.5	155.0	154.6	154.1	153.0	151.3	149.6
105°	194.3	194.8	195.3	195.8	195.3	194.8	194.3	193.7	193.0	191.9	190.9
107.5°	236.7	236.6	236.6	236.6	236.6	236.6	236.7	236.7	236.5	235.9	235.4
110°	267.4	267.2	267.1	266.9	267.1	267.2	267.4	267.6	267.4	266.9	266.4



TEST NUMBER: P333224-840

CATALOG NUMBER: S125DIP-S850D810U840-4F0-1E-UDD-A1

**CANDELA DISTRIBUTION (continued):**

	165°	170°	175°	180°	185°	190°	195°	200°	205°	210°	215°
112.5°	297.5	297.2	296.9	296.6	296.9	297.2	297.5	297.9	297.9	297.6	297.4
115°	344.1	343.9	343.7	343.6	343.7	343.9	344.1	344.2	344.4	344.6	344.8
117.5°	391.4	390.7	390.0	389.3	390.0	390.7	391.4	392.1	392.4	392.2	392.1
120°	423.0	422.3	421.6	420.9	421.6	422.3	423.0	423.7	424.0	424.0	424.0
122.5°	454.1	453.6	453.0	452.5	453.0	453.6	454.1	454.7	455.0	455.2	455.3
125°	500.4	500.2	500.1	499.9	500.1	500.2	500.4	500.6	500.8	501.2	501.5
127.5°	546.4	546.0	545.7	545.3	545.7	546.0	546.4	546.7	547.0	547.1	547.3
130°	576.7	576.3	576.0	575.6	576.0	576.3	576.7	577.0	577.3	577.5	577.6
132.5°	605.6	605.1	604.6	604.1	604.6	605.1	605.6	606.0	606.4	606.5	606.7
135°	650.5	649.7	649.0	648.3	649.0	649.7	650.5	651.2	651.5	651.5	651.5
137.5°	694.2	693.4	692.5	691.6	692.5	693.4	694.2	695.1	695.4	695.2	695.0
140°	722.1	721.1	720.2	719.4	720.2	721.1	722.1	722.9	723.2	722.8	722.5
142.5°	748.5	747.7	746.8	745.9	746.8	747.7	748.5	749.4	749.7	749.5	749.3
145°	787.3	786.8	786.3	785.7	786.3	786.8	787.3	787.8	788.1	788.1	788.1
147.5°	823.2	822.0	820.9	819.7	820.9	822.0	823.2	824.5	824.9	824.5	823.9
150°	846.0	845.7	845.3	845.0	845.3	845.7	846.0	846.4	846.6	846.6	846.6
152.5°	867.7	867.1	866.5	865.8	866.5	867.1	867.7	868.3	868.4	868.0	867.6
155°	898.1	897.3	896.4	895.4	896.4	897.3	898.1	899.0	899.1	898.4	897.7
157.5°	923.7	922.6	921.4	920.3	921.4	922.6	923.7	924.9	925.1	924.4	923.7
160°	940.0	939.1	938.2	937.4	938.2	939.1	940.0	940.9	940.9	940.2	939.6
162.5°	954.9	953.9	952.9	951.9	952.9	953.9	954.9	955.9	956.0	955.2	954.3
165°	974.4	973.4	972.3	971.3	972.3	973.4	974.4	975.5	975.6	975.0	974.3
167.5°	990.1	989.0	987.8	986.7	987.8	989.0	990.1	991.1	991.2	990.1	989.1
170°	998.7	997.4	996.2	995.0	996.2	997.4	998.7	999.9	1000.0	999.0	997.8
172.5°	1005.2	1004.1	1003.0	1001.9	1003.0	1004.1	1005.2	1006.3	1006.3	1005.2	1004.2
175°	1012.1	1010.9	1009.7	1008.5	1009.7	1010.9	1012.1	1013.3	1013.4	1012.4	1011.3
177.5°	1015.1	1014.2	1013.2	1012.2	1013.2	1014.2	1015.1	1016.1	1016.2	1015.3	1014.5
180°	1014.7	1014.7	1014.7	1014.7	1014.7	1014.7	1014.7	1014.7	1014.7	1014.7	1014.7



TEST NUMBER: P333224-840

CATALOG NUMBER: S125DIP-S850D810U840-4F0-1E-UDD-A1

**CANDELA DISTRIBUTION (continued):**

	220°	225°	230°	235°	240°	245°	250°	255°	260°	265°	270°
0°	1235.5	1235.5	1235.5	1235.5	1235.5	1235.5	1235.5	1235.5	1235.5	1235.5	1235.5
2.5°	1181.3	1186.4	1192.7	1197.3	1205.7	1209.4	1214.1	1217.8	1224.6	1230.8	1238.4
5°	1101.8	1110.6	1122.7	1135.8	1151.0	1161.5	1176.2	1185.1	1203.0	1219.2	1234.9
7.5°	1029.6	1040.5	1057.5	1074.4	1094.3	1112.3	1130.6	1151.0	1173.8	1200.6	1222.8
10°	980.1	994.7	1013.1	1034.1	1058.2	1079.1	1103.8	1125.8	1153.7	1185.1	1214.5
12.5°	940.6	953.2	973.7	993.8	1019.6	1045.2	1070.7	1099.8	1132.3	1167.1	1204.0
15°	886.2	896.7	913.4	941.3	967.5	992.7	1031.0	1058.2	1099.1	1137.9	1182.5
17.5°	839.7	852.7	866.9	890.7	917.9	949.4	983.5	1017.7	1057.1	1106.3	1156.6
20°	811.2	821.7	838.0	856.3	885.1	916.7	949.2	983.7	1032.0	1082.9	1136.8
22.5°	780.1	791.5	809.8	829.9	854.1	884.3	920.2	958.2	1008.5	1058.5	1117.1
25°	743.6	751.4	768.2	786.1	810.2	835.9	873.1	915.0	964.8	1022.0	1081.8
27.5°	709.0	716.0	731.3	746.8	768.6	799.1	832.4	874.7	921.7	979.7	1045.9
30°	684.3	691.7	705.3	722.1	743.1	769.8	803.9	843.7	894.0	950.7	1020.0
32.5°	662.9	669.4	679.7	696.5	717.0	743.0	774.5	815.2	865.6	923.0	991.0
35°	629.8	637.1	645.0	658.1	675.9	701.0	735.7	774.0	822.2	877.8	940.2
37.5°	596.8	604.8	611.9	623.6	639.9	662.1	692.0	731.8	775.5	829.0	888.9
40°	576.3	582.6	588.3	601.0	617.2	638.1	666.0	701.7	747.8	797.6	847.4
42.5°	555.7	561.6	566.5	577.4	592.5	612.6	639.1	673.9	716.7	763.2	807.1
45°	523.3	527.0	532.8	542.2	554.3	572.6	598.3	629.2	665.4	709.5	742.6
47.5°	488.3	494.0	498.8	507.1	516.9	534.9	559.6	585.9	618.7	651.5	674.8
50°	461.4	467.3	474.0	481.9	491.3	508.2	530.7	557.4	585.2	610.4	630.3
52.5°	436.3	441.6	448.9	456.4	467.9	482.1	501.3	525.1	552.5	570.6	587.1
55°	399.1	401.6	410.1	417.4	428.4	438.9	458.3	479.3	496.0	509.7	523.3
57.5°	361.0	364.6	369.4	376.0	386.9	399.2	412.8	431.3	441.2	448.3	458.8
60°	336.7	337.7	340.8	348.7	357.1	368.1	383.8	397.0	404.2	410.1	419.0
62.5°	309.8	310.0	315.3	321.0	327.3	339.2	351.9	362.5	368.6	371.4	380.0
65°	272.2	271.1	274.3	278.9	286.3	294.2	305.2	314.7	314.1	317.2	322.4
67.5°	233.7	232.6	232.6	237.1	243.1	250.1	257.7	263.2	263.3	267.4	270.0
70°	207.6	204.5	206.6	210.3	212.9	218.6	227.0	229.1	229.6	231.8	234.4
72.5°	180.8	179.8	181.5	183.0	184.8	189.3	196.4	197.7	197.8	199.0	203.4
75°	143.7	142.6	141.6	143.2	145.2	148.3	151.0	153.1	152.6	153.1	156.2
77.5°	107.8	104.7	104.2	105.1	105.6	107.4	110.2	110.0	110.6	110.5	114.0
80°	85.4	81.3	80.8	80.8	81.3	82.3	83.4	84.4	82.8	84.4	85.4
82.5°	62.8	60.3	60.2	59.8	59.9	60.1	60.7	61.4	61.0	61.8	62.4
85°	34.6	33.5	32.0	33.0	32.5	30.9	32.0	30.4	29.9	30.4	30.9
87.5°	14.4	14.6	13.6	13.3	12.7	12.8	11.8	11.1	10.4	10.5	11.5
90°	13.5	12.6	11.4	10.2	9.0	7.7	6.4	5.0	3.6	2.2	0.8
92.5°	31.5	30.3	28.8	27.3	25.8	24.2	23.0	22.0	21.1	20.1	19.1
95°	62.0	60.8	59.1	57.3	55.5	53.8	52.7	52.4	52.0	51.7	51.3
97.5°	98.0	96.8	94.4	92.0	89.6	87.2	85.8	85.7	85.5	85.4	85.3
100°	122.4	120.8	118.6	116.2	114.0	111.7	110.6	110.6	110.6	110.6	110.6
102.5°	147.8	146.1	144.9	143.8	142.6	141.5	140.6	139.9	139.2	138.5	137.7
105°	189.8	188.7	187.6	186.6	185.6	184.5	183.6	182.7	181.8	181.0	180.1
107.5°	234.9	234.4	233.6	232.8	232.0	231.2	230.4	229.4	228.5	227.6	226.8
110°	265.9	265.3	264.8	264.3	263.8	263.3	262.6	261.7	260.7	259.9	259.0



TEST NUMBER: P333224-840

CATALOG NUMBER: S125DIP-S850D810U840-4F0-1E-UDD-A1

**CANDELA DISTRIBUTION (continued):**

	220°	225°	230°	235°	240°	245°	250°	255°	260°	265°	270°
112.5°	297.2	296.9	296.3	295.6	294.9	294.3	293.7	293.3	292.8	292.4	291.9
115°	344.9	345.1	344.8	344.4	344.1	343.7	343.2	342.4	341.7	341.0	340.3
117.5°	391.9	391.8	391.5	391.2	390.9	390.6	390.2	389.9	389.6	389.3	389.0
120°	424.0	424.0	423.8	423.7	423.5	423.3	422.8	421.9	421.1	420.2	419.3
122.5°	455.4	455.7	455.1	454.7	454.2	453.8	453.4	453.1	452.8	452.5	452.1
125°	501.9	502.2	502.0	501.9	501.7	501.5	500.9	499.9	498.8	497.8	496.7
127.5°	547.5	547.8	547.5	547.2	547.0	546.8	546.4	545.8	545.2	544.7	544.1
130°	577.8	578.0	577.6	577.3	576.9	576.6	576.0	575.1	574.3	573.4	572.5
132.5°	606.9	607.1	607.1	607.2	607.3	607.3	606.7	605.2	603.8	602.4	601.0
135°	651.5	651.5	651.3	651.2	651.0	650.8	650.2	649.1	648.0	647.0	645.9
137.5°	694.8	694.6	694.2	693.8	693.5	693.1	692.4	691.4	690.3	689.3	688.3
140°	722.2	721.8	721.2	720.7	720.1	719.6	718.9	718.1	717.2	716.3	715.5
142.5°	749.1	748.9	748.2	747.6	746.9	746.3	745.6	744.8	744.1	743.4	742.7
145°	788.1	788.1	787.6	787.0	786.5	786.0	785.4	784.7	784.0	783.3	782.5
147.5°	823.5	823.1	822.7	822.3	821.9	821.4	821.0	820.7	820.3	819.9	819.5
150°	846.6	846.6	845.9	845.2	844.4	843.7	843.4	843.6	843.8	843.9	844.1
152.5°	867.2	866.8	866.5	866.2	865.9	865.7	865.4	865.2	864.8	864.6	864.3
155°	897.0	896.3	896.1	896.0	895.8	895.5	895.4	895.4	895.4	895.4	895.4
157.5°	923.0	922.3	922.1	922.0	921.8	921.6	921.7	922.1	922.5	922.9	923.3
160°	938.9	938.2	938.0	937.8	937.6	937.5	937.6	938.2	938.7	939.2	939.7
162.5°	953.5	952.7	952.6	952.6	952.5	952.5	952.7	953.1	953.4	953.8	954.2
165°	973.6	972.9	972.7	972.5	972.3	972.2	972.3	972.6	973.0	973.3	973.7
167.5°	988.0	986.9	986.9	986.9	986.9	986.9	987.2	988.0	988.7	989.4	990.1
170°	996.8	995.7	995.7	995.7	995.7	995.7	996.1	996.8	997.5	998.3	999.0
172.5°	1003.1	1002.1	1002.1	1002.1	1002.1	1002.1	1002.4	1003.1	1003.8	1004.5	1005.2
175°	1010.3	1009.2	1009.2	1009.2	1009.2	1009.2	1009.6	1010.3	1011.0	1011.7	1012.4
177.5°	1013.7	1012.8	1013.0	1013.1	1013.3	1013.4	1013.7	1014.3	1014.9	1015.4	1016.0
180°	1014.7	1014.7	1014.7	1014.7	1014.7	1014.7	1014.7	1014.7	1014.7	1014.7	1014.7



TEST NUMBER: P333224-840

CATALOG NUMBER: S125DIP-S850D810U840-4F0-1E-UDD-A1

**CANDELA DISTRIBUTION (continued):**

	275°	280°	285°	290°	295°	300°	305°	310°	315°	320°	325°
0°	1235.5	1235.5	1235.5	1235.5	1235.5	1235.5	1235.5	1235.5	1235.5	1235.5	1235.5
2.5°	1242.1	1248.0	1251.8	1258.9	1264.8	1268.2	1271.1	1273.6	1276.6	1279.1	1286.2
5°	1250.1	1263.7	1275.3	1293.1	1309.4	1321.9	1335.5	1347.7	1357.7	1371.8	1382.8
7.5°	1246.7	1270.9	1296.3	1323.8	1352.0	1378.3	1402.4	1424.9	1445.4	1470.2	1491.9
10°	1243.3	1276.4	1308.9	1346.0	1384.3	1416.8	1447.2	1478.2	1500.8	1532.3	1558.9
12.5°	1240.8	1279.7	1318.9	1363.7	1405.7	1451.7	1492.2	1514.7	1549.0	1574.2	1606.0
15°	1230.2	1281.6	1335.5	1385.9	1445.7	1488.1	1523.9	1567.9	1599.8	1631.8	1666.5
17.5°	1211.2	1269.4	1329.8	1395.8	1453.2	1498.7	1544.7	1587.2	1625.4	1668.3	1711.3
20°	1202.4	1260.6	1329.8	1397.5	1453.6	1501.3	1548.5	1595.2	1637.1	1692.1	1742.0
22.5°	1184.0	1254.4	1318.1	1384.0	1441.8	1493.8	1547.2	1600.2	1656.0	1718.2	1780.6
25°	1151.0	1222.3	1290.0	1355.0	1413.2	1478.2	1535.4	1606.2	1677.5	1759.8	1837.4
27.5°	1116.8	1185.1	1247.1	1309.9	1377.8	1451.4	1525.5	1605.9	1699.2	1803.1	1912.6
30°	1089.1	1153.7	1214.0	1278.4	1349.2	1432.1	1513.4	1608.8	1716.8	1833.7	1963.8
32.5°	1056.8	1116.3	1174.9	1243.2	1320.3	1407.8	1502.5	1607.1	1737.0	1869.9	2003.7
35°	1001.6	1051.4	1111.7	1184.6	1271.6	1371.8	1481.4	1605.1	1754.0	1906.6	2019.4
37.5°	936.0	982.4	1045.9	1125.8	1217.1	1324.5	1454.6	1601.4	1759.6	1881.3	1917.6
40°	892.0	934.9	1001.1	1083.9	1177.2	1291.0	1433.6	1588.8	1742.0	1819.6	1789.7
42.5°	845.0	890.1	954.4	1036.5	1137.0	1260.8	1407.2	1562.5	1690.8	1720.2	1616.9
45°	770.8	817.5	880.9	963.8	1071.9	1206.1	1358.7	1499.8	1573.7	1520.7	1360.8
47.5°	702.0	745.7	804.5	890.0	1001.5	1140.3	1287.3	1399.8	1405.6	1279.3	1108.4
50°	655.0	695.3	754.6	840.0	950.7	1091.3	1223.9	1312.5	1272.6	1129.5	965.3
52.5°	608.8	648.3	706.8	791.4	900.8	1029.6	1153.0	1215.2	1140.1	993.2	852.9
55°	542.2	576.8	634.0	712.1	816.0	935.5	1040.4	1061.9	964.3	819.6	705.8
57.5°	477.2	509.5	561.5	633.5	728.3	834.2	916.3	911.7	808.6	684.4	594.1
60°	433.1	464.6	510.8	581.0	667.5	758.8	829.0	812.2	710.0	603.0	527.0
62.5°	393.7	421.8	465.4	526.8	605.8	690.4	748.1	723.4	623.2	529.6	469.5
65°	335.6	359.2	396.5	448.9	514.4	584.2	628.7	596.7	511.3	438.4	390.1
67.5°	280.1	299.0	330.2	372.1	428.0	484.0	511.2	479.0	410.6	357.4	321.6
70°	244.9	261.7	285.8	323.1	371.8	419.0	439.4	410.6	351.8	306.2	280.5
72.5°	209.6	223.5	244.7	278.1	317.2	358.2	376.1	348.5	300.2	261.8	237.7
75°	162.1	171.5	186.1	209.2	240.1	272.7	282.7	258.5	227.6	198.7	183.0
77.5°	116.0	124.0	135.1	149.7	171.6	192.3	201.0	187.0	163.1	144.8	131.9
80°	89.2	93.3	102.8	114.8	132.2	145.2	151.0	142.1	125.3	111.7	101.7
82.5°	63.5	67.8	73.4	83.4	94.4	103.3	109.5	103.5	91.4	80.7	74.8
85°	30.9	33.5	36.7	40.9	49.3	54.5	54.0	50.3	45.6	41.4	38.3
87.5°	11.3	12.0	13.6	16.0	17.5	19.4	20.5	19.9	18.5	17.4	16.3
90°	2.2	3.6	5.0	6.4	7.7	9.0	10.2	11.4	12.6	13.5	14.3
92.5°	20.1	21.1	22.0	23.0	24.2	25.8	27.3	28.8	30.3	31.5	32.6
95°	51.7	52.0	52.4	52.7	53.8	55.5	57.3	59.1	60.8	62.0	63.2
97.5°	85.4	85.5	85.7	85.8	87.2	89.6	92.0	94.4	96.8	98.0	99.2
100°	110.6	110.6	110.6	110.6	111.7	114.0	116.2	118.6	120.8	122.4	124.0
102.5°	138.5	139.2	139.9	140.6	141.5	142.6	143.8	144.9	146.1	147.8	149.6
105°	181.0	181.8	182.7	183.6	184.5	185.6	186.6	187.6	188.7	189.8	190.9
107.5°	227.6	228.5	229.4	230.4	231.2	232.0	232.8	233.6	234.4	234.9	235.4
110°	259.9	260.7	261.7	262.6	263.3	263.8	264.3	264.8	265.3	265.9	266.4





TEST NUMBER: P333224-840

CATALOG NUMBER: S125DIP-S850D810U840-4F0-1E-UDD-A1

**CANDELA DISTRIBUTION (continued):**

	275°	280°	285°	290°	295°	300°	305°	310°	315°	320°	325°
112.5°	292.4	292.8	293.3	293.7	294.3	294.9	295.6	296.3	296.9	297.2	297.4
115°	341.0	341.7	342.4	343.2	343.7	344.1	344.4	344.8	345.1	344.9	344.8
117.5°	389.3	389.6	389.9	390.2	390.6	390.9	391.2	391.5	391.8	391.9	392.1
120°	420.2	421.1	421.9	422.8	423.3	423.5	423.7	423.8	424.0	424.0	424.0
122.5°	452.5	452.8	453.1	453.4	453.8	454.2	454.7	455.1	455.7	455.4	455.3
125°	497.8	498.8	499.9	500.9	501.5	501.7	501.9	502.0	502.2	501.9	501.5
127.5°	544.7	545.2	545.8	546.4	546.8	547.0	547.2	547.5	547.8	547.5	547.3
130°	573.4	574.3	575.1	576.0	576.6	576.9	577.3	577.6	578.0	577.8	577.6
132.5°	602.4	603.8	605.2	606.7	607.3	607.3	607.2	607.1	607.1	606.9	606.7
135°	647.0	648.0	649.1	650.2	650.8	651.0	651.2	651.3	651.5	651.5	651.5
137.5°	689.3	690.3	691.4	692.4	693.1	693.5	693.8	694.2	694.6	694.8	695.0
140°	716.3	717.2	718.1	718.9	719.6	720.1	720.7	721.2	721.8	722.2	722.5
142.5°	743.4	744.1	744.8	745.6	746.3	746.9	747.6	748.2	748.9	749.1	749.3
145°	783.3	784.0	784.7	785.4	786.0	786.5	787.0	787.6	788.1	788.1	788.1
147.5°	819.9	820.3	820.7	821.0	821.4	821.9	822.3	822.7	823.1	823.5	823.9
150°	843.9	843.8	843.6	843.4	843.7	844.4	845.2	845.9	846.6	846.6	846.6
152.5°	864.6	864.8	865.2	865.4	865.7	865.9	866.2	866.5	866.8	867.2	867.6
155°	895.4	895.4	895.4	895.4	895.5	895.8	896.0	896.1	896.3	897.0	897.7
157.5°	922.9	922.5	922.1	921.7	921.6	921.8	922.0	922.1	922.3	923.0	923.7
160°	939.2	938.7	938.2	937.6	937.5	937.6	937.8	938.0	938.2	938.9	939.6
162.5°	953.8	953.4	953.1	952.7	952.5	952.5	952.6	952.6	952.7	953.5	954.3
165°	973.3	973.0	972.6	972.3	972.2	972.3	972.5	972.7	972.9	973.6	974.3
167.5°	989.4	988.7	988.0	987.2	986.9	986.9	986.9	986.9	986.9	988.0	989.1
170°	998.3	997.5	996.8	996.1	995.7	995.7	995.7	995.7	995.7	996.8	997.8
172.5°	1004.5	1003.8	1003.1	1002.4	1002.1	1002.1	1002.1	1002.1	1002.1	1003.1	1004.2
175°	1011.7	1011.0	1010.3	1009.6	1009.2	1009.2	1009.2	1009.2	1009.2	1010.3	1011.3
177.5°	1015.4	1014.9	1014.3	1013.7	1013.4	1013.3	1013.1	1013.0	1012.8	1013.7	1014.5
180°	1014.7	1014.7	1014.7	1014.7	1014.7	1014.7	1014.7	1014.7	1014.7	1014.7	1014.7



TEST NUMBER: P333224-840

CATALOG NUMBER: S125DIP-S850D810U840-4F0-1E-UDD-A1

**CANDELA DISTRIBUTION (continued):**

	330°	335°	340°	345°	350°	355°	360°
0°	1235.5	1235.5	1235.5	1235.5	1235.5	1235.5	1235.5
2.5°	1292.0	1295.5	1302.5	1300.0	1303.4	1305.0	1306.8
5°	1396.4	1413.2	1420.6	1419.5	1430.5	1427.8	1425.2
7.5°	1514.3	1532.0	1541.8	1554.1	1561.2	1561.7	1567.9
10°	1581.0	1604.1	1613.6	1626.6	1635.0	1639.7	1639.2
12.5°	1632.1	1650.2	1671.4	1677.8	1689.1	1695.1	1692.9
15°	1693.7	1722.6	1744.6	1755.7	1769.8	1773.9	1779.8
17.5°	1748.7	1787.4	1813.1	1847.2	1860.2	1868.0	1863.4
20°	1790.2	1841.1	1866.8	1907.7	1930.3	1942.3	1938.1
22.5°	1839.3	1894.4	1941.9	1977.3	2011.7	2027.9	2031.2
25°	1923.4	1998.9	2068.7	2115.4	2157.8	2167.8	2189.8
27.5°	2017.4	2106.5	2181.0	2230.1	2259.7	2270.8	2277.6
30°	2076.6	2165.2	2221.3	2252.7	2262.2	2261.1	2260.1
32.5°	2105.5	2161.0	2171.7	2162.9	2141.3	2123.1	2104.1
35°	2064.5	2023.1	1961.2	1881.5	1822.7	1763.5	1757.7
37.5°	1856.7	1724.2	1621.2	1506.2	1439.9	1398.9	1370.5
40°	1661.2	1510.8	1385.9	1288.9	1221.2	1194.6	1168.3
42.5°	1449.0	1305.1	1194.7	1113.6	1062.7	1033.0	1012.3
45°	1177.2	1050.4	963.8	905.0	864.7	841.6	828.5
47.5°	964.6	870.8	797.3	754.9	727.0	709.0	709.1
50°	850.5	760.8	712.1	678.5	654.4	640.3	642.9
52.5°	749.4	682.5	640.8	612.7	594.8	586.1	585.8
55°	626.6	578.3	551.1	530.7	518.6	508.7	510.8
57.5°	536.0	495.3	477.1	460.1	451.7	447.7	441.9
60°	479.8	448.4	432.6	419.0	410.6	407.5	401.6
62.5°	429.9	405.2	389.8	378.7	371.1	370.1	365.6
65°	361.3	342.4	328.8	323.6	315.7	313.6	313.6
67.5°	297.8	284.3	273.8	268.9	265.4	266.0	263.5
70°	258.0	247.0	240.1	234.9	232.3	232.8	230.8
72.5°	225.7	213.4	207.4	204.3	200.9	202.2	201.4
75°	171.0	164.6	161.5	158.3	156.2	155.2	154.2
77.5°	125.5	120.0	117.5	115.8	116.1	113.6	115.5
80°	97.0	92.3	90.7	88.1	87.6	87.6	87.1
82.5°	71.0	68.4	67.3	65.0	64.1	64.9	63.5
85°	36.7	34.6	34.1	34.1	33.0	32.0	34.6
87.5°	16.5	14.9	15.1	14.8	14.9	14.5	13.8
90°	15.2	16.2	16.9	17.4	17.9	18.4	19.0
92.5°	33.8	34.9	35.7	36.2	36.5	36.9	37.3
95°	64.5	65.7	66.6	66.9	67.3	67.6	67.9
97.5°	100.3	101.5	102.1	102.3	102.5	102.8	103.0
100°	125.5	127.1	128.2	128.5	128.8	129.2	129.5
102.5°	151.3	153.0	154.1	154.6	155.0	155.5	156.0
105°	191.9	193.0	193.7	194.3	194.8	195.3	195.8
107.5°	235.9	236.5	236.7	236.7	236.6	236.6	236.6
110°	266.9	267.4	267.6	267.4	267.2	267.1	266.9



TEST NUMBER: P333224-840

CATALOG NUMBER: S125DIP-S850D810U840-4F0-1E-UDD-A1

**CANDELA DISTRIBUTION (continued):**

	330°	335°	340°	345°	350°	355°	360°
112.5°	297.6	297.9	297.9	297.5	297.2	296.9	296.6
115°	344.6	344.4	344.2	344.1	343.9	343.7	343.6
117.5°	392.2	392.4	392.1	391.4	390.7	390.0	389.3
120°	424.0	424.0	423.7	423.0	422.3	421.6	420.9
122.5°	455.2	455.0	454.7	454.1	453.6	453.0	452.5
125°	501.2	500.8	500.6	500.4	500.2	500.1	499.9
127.5°	547.1	547.0	546.7	546.4	546.0	545.7	545.3
130°	577.5	577.3	577.0	576.7	576.3	576.0	575.6
132.5°	606.5	606.4	606.0	605.6	605.1	604.6	604.1
135°	651.5	651.5	651.2	650.5	649.7	649.0	648.3
137.5°	695.2	695.4	695.1	694.2	693.4	692.5	691.6
140°	722.8	723.2	722.9	722.1	721.1	720.2	719.4
142.5°	749.5	749.7	749.4	748.5	747.7	746.8	745.9
145°	788.1	788.1	787.8	787.3	786.8	786.3	785.7
147.5°	824.5	824.9	824.5	823.2	822.0	820.9	819.7
150°	846.6	846.6	846.4	846.0	845.7	845.3	845.0
152.5°	868.0	868.4	868.3	867.7	867.1	866.5	865.8
155°	898.4	899.1	899.0	898.1	897.3	896.4	895.4
157.5°	924.4	925.1	924.9	923.7	922.6	921.4	920.3
160°	940.2	940.9	940.9	940.0	939.1	938.2	937.4
162.5°	955.2	956.0	955.9	954.9	953.9	952.9	951.9
165°	975.0	975.6	975.5	974.4	973.4	972.3	971.3
167.5°	990.1	991.2	991.1	990.1	989.0	987.8	986.7
170°	999.0	1000.0	999.9	998.7	997.4	996.2	995.0
172.5°	1005.2	1006.3	1006.3	1005.2	1004.1	1003.0	1001.9
175°	1012.4	1013.4	1013.3	1012.1	1010.9	1009.7	1008.5
177.5°	1015.3	1016.2	1016.1	1015.1	1014.2	1013.2	1012.2
180°	1014.7	1014.7	1014.7	1014.7	1014.7	1014.7	1014.7

(END OF REPORT)