

Scaled data based on original data using  
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State  
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P331338-830

Luminaire Tested: **SA2XXDIP-C675D330U830-4F0-1E-UDD-F4**

Issue Date: 10/7/2019

**Test Information**

Test Method: LM-79-08  
Report Number: P331338-830  
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-16,  
Test Lab: INNOVATION CENTER  
Issue Date: 10/7/2019  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: NEO-RAY  
Catalog Number: SA2XXDIP-C675D330U830-4F0-1E-UDD-F4  
Description: DEFINE 2 DIRECT-INDIRECT PENDANT LED LUMINAIRE  
DOWNLIGHT 675 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER  
UPLIGHT 330 LUMENS PER FOOT, BATWING OPTIC  
Light Source: -  
Ballast/Driver: ELECTRONIC DRIVER

**Summary**


Lumens per Lamp: N/A  
Luminaire Lumens: 3752.5 lumens  
Efficiency: N/A  
Efficacy: 107.2 lumens/watt  
Spacing Criteria (0/90/45): 1.2 / 1.16 / 1.3  
Luminous Opening: Rectangular (W 0.17' x L: 4' x H: 0')  
CIE Type: Semi-Direct

Input Watts (W): 35  
Input Voltage (V): 120  
Input Current (Ain): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 25 FT



TEST NUMBER: P331338-830  
CATALOG NUMBER: SA2XXDIP-C675D330U830-4F0-1E-UDD-F4

### Luminous Intensity Polar Plot





TEST NUMBER: P331338-830

CATALOG NUMBER: SA2XXDIP-C675D330U830-4F0-1E-UDD-F4

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	111	111	111	111	105	105	105	105	93	93	93	82	82	82	73	73	73	68
1	102	97	93	90	96	92	88	85	82	79	77	73	71	69	64	63	61	57
2	93	85	79	73	87	80	75	70	72	67	64	64	60	57	56	54	52	48
3	85	75	67	61	79	71	64	59	63	58	54	56	52	49	50	47	44	41
4	77	66	58	52	73	63	56	50	56	50	46	50	46	42	45	41	38	35
5	71	59	51	45	67	56	49	43	51	44	40	45	40	36	40	36	33	30
6	66	53	45	39	62	51	43	37	46	39	35	41	36	32	37	32	29	27
7	61	48	40	34	57	46	38	33	41	35	31	37	32	28	33	29	26	24
8	57	44	36	30	53	42	34	29	38	32	27	34	29	25	31	27	23	21
9	53	40	32	27	50	38	31	26	35	29	25	32	26	23	28	24	21	19
10	49	37	29	25	47	35	28	24	32	26	22	29	24	21	26	22	19	17

**AVERAGE LUMINANCE (cd/sqm):**

	0°	45°	90°
0°	16157	16157	16157
5°	16219	15985	16078
10°	16123	15823	15901
15°	15921	15616	15600
20°	15639	15309	15292
25°	15358	14931	14931
30°	14997	14585	14458
35°	14661	14168	13957
40°	14235	13748	13487
45°	13819	13337	13006
50°	13366	12906	12446
55°	12892	12405	11944
60°	12368	11806	11370
65°	11801	11213	10697
70°	11084	10494	9994
75°	10081	9669	9426
80°	8945	8675	8229
85°	7317	6947	6224



TEST NUMBER: P331338-830

CATALOG NUMBER: SA2XXDIP-C675D330U830-4F0-1E-UDD-F4

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	94.1	2.5
10°-20°	264.8	7.1
20°-30°	389.2	10.4
30°-40°	452.1	12.0
40°-50°	451.6	12.0
50°-60°	393.8	10.5
60°-70°	291.2	7.8
70°-80°	164.9	4.4
80°-90°	45.9	1.2
90°-100°	69.2	1.8
100°-110°	235.0	6.3
110°-120°	249.6	6.7
120°-130°	205.5	5.5
130°-140°	165.0	4.4
140°-150°	124.7	3.3
150°-160°	87.6	2.3
160°-170°	51.6	1.4
170°-180°	16.8	0.4
0°-30°	748.0	19.9
0°-40°	1200.1	32.0
0°-60°	2045.4	54.5
0°-90°	2547.4	67.9
90°-120°	553.8	14.8
90°-150°	1049.0	28.0
90°-180°	1205.0	32.1
0°-180°	3752.5	100.0

**CANDELA DISTRIBUTION:**

	0°	22.5°	45°	67.5°	90°	Flux
0°	1001	1001	1001	1001	1001	
5°	1001	996	986	993	992	95
15°	952	946	934	938	933	268
25°	862	854	838	840	838	396
35°	744	734	719	713	708	464
45°	605	598	584	574	570	467
55°	458	452	441	430	424	409
65°	309	303	294	285	280	305
75°	162	160	155	150	151	173
85°	40	38	38	35	34	45
90°	0	4	11	11	11	3
95°	12	29	130	49	38	12
105°	41	61	247	441	375	43
115°	72	90	206	426	494	71
125°	100	118	198	345	401	89
135°	117	140	196	290	332	91
145°	134	154	195	242	265	84
155°	152	164	190	214	223	70
165°	166	171	182	192	196	47
175°	173	173	174	177	176	16
180°	173	173	173	173	173	



TEST NUMBER: P331338-830

CATALOG NUMBER: SA2XXDIP-C675D330U830-4F0-1E-UDD-F4

**CANDELA DISTRIBUTION (FULL):**

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	1000.7	1000.7	1000.7	1000.7	1000.7	1000.7	1000.7	1000.7	1000.7	1000.7	1000.7
2.5°	1005.3	1004.5	1003.6	1002.8	1001.9	1000.5	998.6	996.7	994.9	993.0	994.7
5°	1000.7	999.8	999.0	998.2	997.3	995.7	993.3	991.0	988.6	986.3	988.0
7.5°	991.8	990.5	989.2	987.9	986.6	984.7	982.3	979.9	977.5	975.1	976.8
10°	983.4	981.8	980.3	978.8	977.4	975.3	972.8	970.3	967.6	965.1	966.8
12.5°	971.9	970.5	969.1	967.8	966.5	964.6	962.0	959.4	956.9	954.3	955.5
15°	952.5	951.3	950.0	948.8	947.4	945.4	942.6	939.8	937.1	934.2	935.2
17.5°	927.9	926.6	925.4	924.1	922.8	920.8	917.9	915.1	912.3	909.5	910.5
20°	910.2	909.0	907.7	906.3	905.1	903.0	899.9	897.0	894.0	891.0	891.6
22.5°	892.5	890.7	888.9	887.1	885.3	883.1	880.2	877.4	874.6	871.8	871.9
25°	862.1	860.4	858.8	857.0	855.3	852.6	848.9	845.4	841.7	838.1	838.5
27.5°	827.5	826.0	824.4	822.8	821.3	819.2	816.2	813.4	810.5	807.7	807.0
30°	804.4	802.7	801.0	799.3	797.6	795.1	791.9	788.7	785.5	782.3	781.7
32.5°	779.8	778.4	777.0	775.6	774.3	771.9	768.5	765.2	761.8	758.4	757.2
35°	743.8	741.7	739.5	737.4	735.2	732.4	729.1	725.6	722.2	718.8	717.5
37.5°	703.1	701.3	699.4	697.5	695.7	693.0	689.6	686.2	682.8	679.3	677.7
40°	675.4	673.7	672.0	670.3	668.6	666.1	662.6	659.2	655.8	652.3	650.4
42.5°	648.6	646.8	645.1	643.4	641.7	639.1	635.7	632.3	628.9	625.5	623.3
45°	605.2	603.7	602.2	600.8	599.3	596.9	593.7	590.5	587.3	584.1	581.7
47.5°	562.1	560.7	559.3	557.9	556.5	554.1	550.7	547.4	544.1	540.7	538.3
50°	532.1	531.0	530.0	528.9	527.8	525.8	522.8	519.8	516.8	513.8	510.9
52.5°	502.8	501.4	500.0	498.6	497.2	495.1	492.3	489.5	486.6	483.8	481.4
55°	458.0	456.8	455.4	454.1	452.9	450.9	448.4	445.8	443.3	440.7	438.1
57.5°	412.9	412.0	410.9	409.9	408.9	407.0	404.2	401.3	398.5	395.7	393.1
60°	383.0	382.1	381.3	380.4	379.6	377.6	374.7	371.6	368.6	365.6	363.3
62.5°	353.7	352.3	351.0	349.6	348.3	346.4	344.1	341.8	339.5	337.1	335.0
65°	308.9	307.6	306.3	305.0	303.7	302.0	299.9	297.7	295.6	293.5	291.5
67.5°	263.3	262.2	261.2	260.1	259.1	257.7	255.7	253.8	251.9	250.0	248.5
70°	234.8	233.9	233.1	232.2	231.4	230.0	228.0	226.1	224.2	222.3	220.7
72.5°	205.6	204.6	203.8	202.9	202.1	201.0	199.8	198.6	197.4	196.0	194.6
75°	161.6	161.2	160.8	160.3	159.9	159.2	158.2	157.0	156.0	155.0	153.6
77.5°	122.4	121.7	120.9	120.2	119.5	118.9	118.5	118.0	117.6	117.2	116.6
80°	96.2	96.0	95.8	95.6	95.4	95.0	94.6	94.2	93.8	93.3	92.7
82.5°	71.6	71.5	71.5	71.4	71.4	71.3	71.0	70.8	70.5	70.2	69.5
85°	39.5	39.2	39.0	38.8	38.5	38.4	38.2	38.0	37.7	37.5	36.9
87.5°	13.9	13.8	13.7	13.5	13.3	13.1	13.1	13.3	13.3	13.0	12.4
90°	0.4	1.3	2.6	3.3	4.0	5.0	6.7	9.0	11.0	11.3	11.0
92.5°	4.1	5.8	8.3	9.7	12.0	15.1	22.6	33.3	42.7	43.3	36.6
95°	11.7	13.0	16.3	19.3	24.6	32.6	48.0	76.9	115.6	130.5	114.2
97.5°	18.9	20.7	24.3	28.8	35.0	44.0	63.2	103.7	167.9	222.8	233.8
100°	25.6	26.7	29.6	35.0	41.7	51.0	68.6	109.2	181.2	263.1	311.0
102.5°	31.8	32.5	35.5	40.8	47.8	57.1	73.4	109.5	176.1	264.4	339.8
105°	40.6	41.9	44.3	49.3	56.6	66.0	81.6	111.2	166.2	246.8	335.4
107.5°	50.2	51.3	53.5	58.2	65.4	74.8	90.0	115.8	161.3	227.8	306.1
110°	56.6	58.0	59.9	64.3	71.3	81.0	95.6	119.5	160.2	218.8	287.8



TEST NUMBER: P331338-830

CATALOG NUMBER: SA2XXDIP-C675D330U830-4F0-1E-UDD-F4

**CANDELA DISTRIBUTION (continued):**

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	62.5	63.8	66.1	70.1	76.8	86.8	100.9	123.6	160.4	212.9	274.9
115°	71.6	73.2	75.3	79.3	86.0	94.9	109.2	129.5	161.8	206.5	259.1
117.5°	81.1	82.4	84.4	87.9	94.3	103.7	116.9	135.9	164.3	203.3	249.1
120°	86.9	88.2	90.3	93.2	99.9	109.2	122.2	140.3	165.9	201.5	243.7
122.5°	92.6	93.6	95.6	98.9	105.5	115.1	127.2	143.9	167.7	200.4	239.2
125°	99.9	100.9	102.9	106.9	113.6	122.9	134.9	149.9	170.5	198.5	232.8
127.5°	105.8	107.1	109.9	114.3	120.6	130.3	141.9	155.4	173.3	197.4	226.8
130°	109.2	110.6	113.9	118.6	125.3	134.5	146.2	158.8	175.5	196.8	222.8
132.5°	112.4	114.0	117.6	122.5	129.5	138.8	150.0	162.3	177.7	196.5	219.6
135°	117.3	118.6	122.5	127.5	135.3	144.5	155.2	166.8	180.2	196.1	215.1
137.5°	121.8	123.4	127.3	132.7	140.3	148.9	159.5	170.3	182.5	196.0	212.0
140°	125.3	126.6	130.5	135.9	143.2	151.8	161.8	172.2	183.5	195.9	210.1
142.5°	128.7	129.8	133.5	138.8	145.9	154.0	163.7	173.8	184.3	195.9	208.3
145°	133.8	135.3	138.6	143.5	150.2	157.5	166.5	175.9	185.1	195.1	205.9
147.5°	139.5	140.4	143.6	148.3	153.8	160.3	168.8	177.0	185.4	194.0	203.3
150°	143.2	144.2	146.8	151.2	156.2	162.2	169.8	177.5	185.1	193.1	201.1
152.5°	146.9	147.4	150.1	153.8	158.6	164.0	170.9	177.8	184.6	191.8	199.3
155°	152.2	152.5	154.5	158.2	161.8	166.8	172.5	178.1	183.8	189.5	195.9
157.5°	156.6	156.9	158.5	161.7	164.7	168.8	173.6	178.1	182.3	187.1	192.6
160°	159.5	159.9	161.2	163.8	166.5	170.2	174.2	178.1	181.5	185.5	190.1
162.5°	162.5	162.2	163.6	165.7	168.1	171.0	174.5	177.9	180.7	184.2	188.0
165°	165.9	165.5	166.2	168.1	169.8	171.8	174.8	177.2	179.2	181.5	184.5
167.5°	168.6	168.2	168.8	170.1	171.4	172.6	174.7	176.7	177.7	179.2	181.1
170°	170.5	169.8	170.2	171.2	171.8	172.9	174.5	176.2	176.8	177.9	179.2
172.5°	171.5	171.2	171.0	172.0	172.4	173.1	174.3	175.4	175.8	176.3	177.3
175°	172.9	172.5	172.2	172.9	172.9	173.1	173.8	174.5	174.2	174.5	174.8
177.5°	173.4	172.9	172.7	173.1	173.1	173.1	173.4	174.0	173.4	173.1	173.4
180°	173.1	173.1	173.1	173.1	173.1	173.1	173.1	173.1	173.1	173.1	173.1



TEST NUMBER: P331338-830

CATALOG NUMBER: SA2XXDIP-C675D330U830-4F0-1E-UDD-F4

**CANDELA DISTRIBUTION (continued):**

	55°	60°	65°	70°	75°	80°	85°	90°
0°	1000.7	1000.7	1000.7	1000.7	1000.7	1000.7	1000.7	1000.7
2.5°	996.4	998.2	999.8	1000.5	1000.1	999.8	999.5	999.2
5°	989.7	991.4	993.1	993.7	993.3	992.9	992.5	992.0
7.5°	978.5	980.2	981.9	982.5	982.0	981.7	981.2	980.7
10°	968.5	970.3	971.9	972.4	971.9	971.2	970.5	969.9
12.5°	956.7	957.9	959.1	959.4	958.9	958.6	958.1	957.6
15°	936.0	936.9	937.7	937.6	936.5	935.5	934.4	933.3
17.5°	911.4	912.4	913.4	913.4	912.4	911.3	910.3	909.3
20°	892.3	893.0	893.5	893.4	892.6	891.7	890.9	890.0
22.5°	872.0	872.1	872.2	872.0	871.6	871.0	870.5	870.1
25°	839.0	839.3	839.8	839.8	839.3	839.0	838.5	838.1
27.5°	806.3	805.8	805.1	804.3	803.2	802.2	801.2	800.1
30°	781.0	780.3	779.7	778.9	778.1	777.2	776.4	775.5
32.5°	756.1	755.0	753.8	752.8	752.0	751.1	750.2	749.3
35°	716.2	714.9	713.6	712.5	711.4	710.3	709.3	708.1
37.5°	676.2	674.6	673.0	671.7	670.6	669.6	668.6	667.6
40°	648.6	646.6	644.7	643.3	642.4	641.6	640.7	639.9
42.5°	621.2	619.2	617.1	615.4	614.2	613.0	611.8	610.6
45°	579.4	577.0	574.7	573.1	572.2	571.4	570.5	569.6
47.5°	535.8	533.3	530.8	529.0	527.7	526.5	525.3	524.1
50°	507.8	504.8	501.8	499.8	498.7	497.7	496.6	495.5
52.5°	478.8	476.4	473.9	471.9	470.5	469.1	467.7	466.3
55°	435.5	433.0	430.5	428.6	427.5	426.5	425.4	424.3
57.5°	390.6	388.0	385.6	383.9	383.0	382.3	381.4	380.6
60°	360.9	358.5	356.2	354.8	354.1	353.5	352.8	352.1
62.5°	332.8	330.6	328.5	327.0	326.1	325.3	324.5	323.7
65°	289.6	287.7	285.8	284.3	283.2	282.1	281.1	280.0
67.5°	246.9	245.5	244.0	242.8	242.0	241.1	240.3	239.4
70°	219.2	217.8	216.3	215.1	214.2	213.4	212.5	211.7
72.5°	193.1	191.6	190.1	189.0	188.3	187.7	187.0	186.2
75°	152.3	151.1	149.8	149.4	149.8	150.2	150.6	151.1
77.5°	115.9	115.3	114.6	114.0	113.4	112.8	112.3	111.6
80°	92.1	91.4	90.8	90.2	89.8	89.4	89.0	88.5
82.5°	68.6	67.8	67.0	66.5	66.4	66.4	66.3	66.2
85°	36.3	35.6	35.0	34.5	34.3	34.1	33.9	33.6
87.5°	11.9	11.2	10.8	10.6	10.4	10.3	10.1	9.9
90°	10.7	10.0	10.7	11.0	11.0	11.0	11.0	11.0
92.5°	29.0	24.9	22.1	20.1	19.8	18.8	18.9	18.5
95°	87.3	66.9	53.0	45.6	41.3	38.6	37.6	38.0
97.5°	203.6	166.5	130.5	106.5	90.6	82.4	77.6	74.7
100°	304.1	262.8	217.2	176.8	149.2	134.9	125.3	119.2
102.5°	369.9	360.5	327.2	284.5	254.4	230.0	217.9	209.8
105°	404.6	442.2	446.6	435.6	414.9	394.3	379.9	375.3
107.5°	379.6	436.3	470.9	487.0	489.7	488.5	485.6	479.5
110°	358.0	417.6	460.2	487.6	501.9	508.2	511.2	510.9





TEST NUMBER: P331338-830

CATALOG NUMBER: SA2XXDIP-C675D330U830-4F0-1E-UDD-F4

**CANDELA DISTRIBUTION (continued):**

	55°	60°	65°	70°	75°	80°	85°	90°
112.5°	338.3	395.5	441.0	472.4	492.3	502.8	508.5	510.3
115°	314.1	365.3	409.0	443.3	466.9	482.2	490.9	493.9
117.5°	295.8	340.8	380.4	412.6	436.7	452.9	461.9	464.5
120°	286.7	328.0	363.4	393.6	417.0	432.6	442.2	445.6
122.5°	279.6	317.4	350.8	378.1	399.1	414.5	423.1	425.8
125°	269.1	303.4	332.7	357.7	377.0	389.6	397.9	400.7
127.5°	258.7	289.8	317.4	340.4	357.3	369.2	376.4	378.5
130°	252.1	280.8	307.1	329.0	345.3	356.7	363.4	366.0
132.5°	245.7	272.2	296.4	317.1	333.1	344.4	350.5	353.0
135°	236.8	258.7	280.8	299.4	313.7	324.7	330.7	332.1
137.5°	229.7	248.1	265.5	281.7	294.8	304.3	309.5	311.5
140°	225.1	241.1	256.5	271.1	281.7	290.4	295.4	297.4
142.5°	221.4	235.0	248.2	260.4	270.5	278.4	282.9	283.2
145°	216.1	227.2	237.4	247.1	255.1	260.8	264.1	265.0
147.5°	212.1	220.7	228.8	235.8	242.4	246.9	249.2	249.9
150°	209.2	216.5	223.5	229.4	234.4	238.5	240.4	240.8
152.5°	206.2	213.0	219.0	224.1	228.1	231.5	233.0	233.1
155°	202.2	207.5	212.4	216.1	219.8	222.2	223.5	222.8
157.5°	197.5	201.9	206.0	209.0	211.5	213.5	214.1	214.1
160°	194.4	198.1	201.8	204.2	206.5	208.1	208.5	208.5
162.5°	191.5	194.7	197.8	199.6	202.0	203.1	203.4	203.1
165°	187.2	189.5	191.8	193.1	194.4	195.9	195.9	195.5
167.5°	182.9	184.7	186.3	187.6	188.1	188.9	188.8	188.4
170°	180.9	181.8	183.1	183.8	184.2	185.1	184.8	184.2
172.5°	178.4	179.2	180.2	180.6	181.0	181.4	181.1	180.7
175°	175.9	176.2	176.5	176.8	176.8	177.2	176.8	176.2
177.5°	174.0	174.0	174.3	174.3	174.3	174.3	174.0	173.4
180°	173.1	173.1	173.1	173.1	173.1	173.1	173.1	173.1

(END OF REPORT)