

Scaled data based on original data using  
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State  
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P331339-830

Luminaire Tested: **SA2XXDIP-C675D530U830-4F0-1E-UDD-A**

Issue Date: 10/7/2019

**Test Information**

Test Method: LM-79-08  
Report Number: P331339-830  
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-2,  
Test Lab: INNOVATION CENTER  
Issue Date: 10/7/2019  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: NEO-RAY  
Catalog Number: SA2XXDIP-C675D530U830-4F0-1E-UDD-A  
Description: DEFINE 2 DIRECT-INDIRECT PENDANT LED LUMINAIRE  
DOWNLIGHT 675 LUMENS PER FOOT, ASYMMETRIC DIFFUSER  
UPLIGHT 530 LUMENS PER FOOT, NO LENS  
Light Source: -  
Ballast/Driver: ELECTRONIC DRIVER

**Summary**


Lumens per Lamp: N/A  
Luminaire Lumens: 4755.9 lumens  
Efficiency: N/A  
Efficacy: 118.0 lumens/watt  
Spacing Criteria (0/90/45): 1.08 / 1.16 / 1.23  
Luminous Opening: Rectangular (W 4' x L: 0.17' x H: 0')  
CIE Type: General Diffuse

Input Watts (W): 40.3  
Input Voltage (V): 120  
Input Current (Ain): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 25 FT



TEST NUMBER: P331339-830  
CATALOG NUMBER: SA2XXDIP-C675D530U830-4F0-1E-UDD-A

### Luminous Intensity Polar Plot





TEST NUMBER: P331339-830

CATALOG NUMBER: SA2XXDIP-C675D530U830-4F0-1E-UDD-A

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20					20					20					20					20	
RC	80					70					50					30					10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0	
RCR																						
0	109	109	109	109	102	102	102	102	88	88	88	75	75	75	64	64	64	58				
1	100	96	92	89	93	90	86	84	78	76	73	67	65	64	57	56	55	50				
2	92	84	79	74	85	79	74	69	69	65	62	60	57	54	51	49	47	43				
3	84	75	68	62	78	70	64	59	61	56	53	53	50	46	46	43	41	37				
4	77	67	59	53	72	63	56	50	55	50	45	48	44	40	41	38	36	32				
5	71	60	52	46	66	56	49	44	49	44	39	43	39	35	37	34	31	28				
6	66	54	46	40	61	51	44	38	45	39	35	39	35	31	34	31	28	25				
7	61	49	41	35	57	46	39	34	41	35	31	36	31	28	31	28	25	23				
8	57	45	37	32	53	42	35	30	37	32	28	33	28	25	29	25	23	20				
9	53	41	33	28	49	39	32	27	34	29	25	31	26	23	27	23	21	19				
10	50	38	30	26	46	36	29	25	32	26	23	28	24	21	25	21	19	17				

**AVERAGE LUMINANCE (cd/sqm):**

	0°	90°	180°	270°
0°	20215	20215	20215	20215
5°	22663	20345	18029	20345
10°	25968	20179	15603	20179
15°	28727	19809	13785	19809
20°	28290	19411	12565	19411
25°	25509	18884	11794	18884
30°	21080	18040	11231	18040
35°	15364	17156	10831	17156
40°	12271	16115	10608	16115
45°	10723	14908	10305	14908
50°	10078	13742	10105	13742
55°	9292	12555	9833	12555
60°	8512	11296	9416	11296
65°	7755	10166	9005	10166
70°	7039	9064	8403	9064
75°	6245	7829	7442	7829
80°	5374	6481	5997	6481
85°	4817	4817	3557	4817



TEST NUMBER: P331339-830

CATALOG NUMBER: SA2XXDIP-C675D530U830-4F0-1E-UDD-A

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	119.2	2.5
10°-20°	346.6	7.3
20°-30°	503.1	10.6
30°-40°	530.9	11.2
40°-50°	470.0	9.9
50°-60°	375.1	7.9
60°-70°	254.9	5.4
70°-80°	130.7	2.7
80°-90°	33.2	0.7
90°-100°	22.7	0.5
100°-110°	83.2	1.7
110°-120°	222.3	4.7
120°-130°	366.9	7.7
130°-140°	390.2	8.2
140°-150°	362.7	7.6
150°-160°	291.6	6.1
160°-170°	187.9	4.0
170°-180°	64.7	1.4
0°-30°	968.9	20.4
0°-40°	1499.8	31.5
0°-60°	2344.9	49.3
0°-90°	2763.7	58.1
90°-120°	328.1	6.9
90°-150°	1447.9	30.4
90°-180°	1992.0	41.9
0°-180°	4755.9	100.0

**CANDELA DISTRIBUTION:**

	0°	90°	180°	270°	360°	Flux
0°	1252	1252	1252	1252	1252	
5°	1398	1255	1112	1255	1398	140
15°	1719	1185	825	1185	1719	474
25°	1432	1060	662	1060	1432	647
35°	780	870	550	870	780	507
45°	470	653	451	653	470	369
55°	330	446	349	446	330	296
65°	203	266	236	266	203	202
75°	100	126	119	126	100	107
85°	26	26	19	26	26	29
90°	13	0	13	0	13	7
95°	21	32	21	32	21	20
105°	37	150	37	150	37	39
115°	40	283	40	283	40	101
125°	421	400	421	400	421	364
135°	511	495	511	495	511	394
145°	583	574	583	574	583	365
155°	632	632	632	632	632	292
165°	664	666	664	666	664	188
175°	677	681	677	681	677	65
180°	680	680	680	680	680	



TEST NUMBER: P331339-830

CATALOG NUMBER: SA2XXDIP-C675D530U830-4F0-1E-UDD-A

**CANDELA DISTRIBUTION (FULL):**

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	1252.0	1252.0	1252.0	1252.0	1252.0	1252.0	1252.0	1252.0	1252.0	1252.0	1252.0
2.5°	1309.7	1310.0	1310.9	1304.7	1303.9	1303.9	1298.5	1293.9	1288.5	1281.2	1282.0
5°	1398.3	1403.5	1405.4	1399.7	1391.0	1390.1	1381.9	1368.4	1355.8	1345.8	1338.6
7.5°	1503.9	1506.0	1501.3	1493.6	1487.2	1475.7	1460.5	1445.6	1424.7	1405.5	1391.3
10°	1583.9	1586.9	1578.7	1567.6	1558.5	1545.0	1522.9	1500.2	1472.8	1446.3	1425.1
12.5°	1644.7	1651.9	1641.4	1639.9	1624.3	1605.8	1579.4	1568.0	1529.4	1492.5	1469.8
15°	1718.6	1718.2	1719.2	1710.1	1698.5	1695.5	1667.6	1637.4	1583.0	1561.3	1523.8
17.5°	1697.3	1704.6	1708.0	1707.9	1707.6	1705.8	1696.9	1677.7	1650.5	1615.3	1572.0
20°	1646.5	1656.1	1657.6	1668.7	1674.9	1683.1	1686.4	1681.1	1664.3	1634.9	1597.4
22.5°	1568.0	1570.7	1575.2	1592.4	1606.0	1626.5	1637.2	1655.0	1648.5	1634.2	1602.8
25°	1431.9	1427.1	1444.0	1452.6	1483.8	1516.6	1540.2	1566.1	1589.2	1603.2	1594.0
27.5°	1268.5	1261.3	1286.5	1309.5	1334.9	1370.4	1407.1	1450.5	1486.6	1531.7	1547.2
30°	1130.7	1135.0	1159.1	1183.6	1222.1	1272.1	1313.5	1361.2	1412.7	1463.2	1498.3
32.5°	982.1	998.8	1014.0	1051.6	1085.4	1141.3	1201.9	1261.5	1325.7	1383.1	1437.5
35°	779.5	798.7	819.9	847.3	894.9	950.3	1009.5	1089.8	1177.4	1255.8	1320.3
37.5°	656.1	653.0	665.2	684.9	723.6	768.2	836.3	915.8	1018.8	1111.0	1201.9
40°	582.2	580.2	588.9	607.2	636.6	669.3	729.0	798.7	894.5	1007.0	1115.3
42.5°	531.4	532.5	537.3	550.3	570.3	597.3	642.0	701.3	789.0	895.0	1011.3
45°	469.6	473.0	478.2	484.6	496.1	518.2	543.2	585.6	654.9	743.4	857.9
47.5°	425.2	425.3	430.6	436.1	443.0	455.4	475.9	502.4	551.3	623.4	721.8
50°	401.2	397.9	401.8	406.0	413.3	422.0	435.5	460.4	493.1	551.4	633.7
52.5°	372.0	372.1	375.6	377.2	383.7	392.3	404.6	422.0	451.6	497.1	564.8
55°	330.1	332.4	334.4	337.2	343.1	349.3	358.9	370.5	393.6	427.7	477.8
57.5°	290.6	291.3	293.3	298.8	302.5	308.2	317.4	327.8	342.9	368.2	405.8
60°	263.6	263.6	267.5	269.9	274.8	280.5	287.8	297.8	311.3	332.0	362.3
62.5°	239.0	238.7	240.2	244.1	247.8	253.2	260.4	269.0	281.6	300.0	325.0
65°	203.0	202.1	205.0	205.9	209.8	215.1	220.8	230.0	240.1	253.5	275.7
67.5°	168.4	169.6	171.1	173.0	175.0	180.6	184.5	191.0	199.4	210.7	225.6
70°	149.1	149.1	149.1	150.6	153.4	156.4	160.2	165.5	173.7	183.3	196.8
72.5°	127.6	129.1	130.6	129.8	133.5	135.2	139.8	142.8	150.6	156.7	168.7
75°	100.1	100.1	100.1	102.5	104.0	105.4	108.3	111.1	115.0	122.7	128.9
77.5°	74.6	74.5	74.9	75.5	77.1	78.8	79.6	82.3	85.9	89.4	94.7
80°	57.8	58.7	59.2	60.1	60.1	61.1	61.5	64.9	67.4	69.7	73.1
82.5°	44.7	44.9	45.0	45.1	45.5	46.1	47.3	48.4	49.3	51.3	53.9
85°	26.0	25.5	25.5	26.5	26.0	26.0	27.0	27.9	27.9	28.4	29.8
87.5°	12.6	12.6	13.0	12.5	12.5	12.8	12.7	12.2	12.4	12.7	12.9
90°	13.3	13.1	12.8	12.6	12.4	12.1	11.5	10.9	10.4	9.8	9.0
92.5°	13.3	13.2	13.0	12.9	12.7	12.5	12.3	12.0	11.7	11.4	10.9
95°	21.1	21.3	21.4	21.5	21.6	21.4	20.8	20.3	19.7	19.2	18.4
97.5°	28.3	28.1	28.0	27.8	27.7	27.4	27.0	26.6	26.1	25.6	23.9
100°	33.0	32.7	32.5	32.3	32.0	31.6	30.6	29.8	28.9	28.0	26.2
102.5°	35.3	35.0	34.7	34.4	34.1	33.4	32.2	31.1	30.0	28.8	44.4
105°	37.4	36.9	36.5	36.1	35.6	34.8	33.6	32.4	31.2	30.0	59.9
107.5°	38.5	38.0	37.6	37.1	36.8	37.1	38.4	39.6	40.8	42.0	77.8
110°	38.8	38.5	38.0	37.5	37.1	42.3	53.3	64.2	75.1	86.1	117.6



TEST NUMBER: P331339-830

CATALOG NUMBER: SA2XXDIP-C675D530U830-4F0-1E-UDD-A

**CANDELA DISTRIBUTION (continued):**

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	39.2	38.9	38.5	38.2	37.9	57.6	97.5	137.3	177.2	217.2	224.9
115°	40.3	48.2	56.1	63.9	71.8	101.0	151.7	202.3	252.9	303.5	300.8
117.5°	164.7	190.6	216.4	242.2	268.2	287.2	299.4	311.7	324.0	336.1	334.3
120°	300.0	314.8	329.6	344.3	359.1	365.8	364.5	363.2	361.8	360.5	358.5
122.5°	374.4	377.3	380.1	383.0	385.9	386.9	386.2	385.3	384.6	383.8	381.6
125°	420.6	420.3	419.9	419.6	419.2	418.7	417.9	417.2	416.4	415.7	413.6
127.5°	449.7	449.6	449.6	449.5	449.4	448.8	447.7	446.6	445.4	444.4	442.8
130°	467.8	467.9	468.0	468.1	468.3	467.7	466.5	465.2	464.1	462.9	461.7
132.5°	485.5	485.6	485.7	485.8	485.9	485.5	484.5	483.4	482.4	481.4	480.1
135°	511.0	511.3	511.5	511.7	512.0	511.5	510.4	509.3	508.2	507.1	506.1
137.5°	534.4	534.8	535.1	535.5	535.8	535.6	534.4	533.4	532.3	531.2	530.1
140°	548.9	549.5	550.1	550.5	551.1	550.9	549.9	548.9	548.0	547.0	545.7
142.5°	563.1	563.6	564.2	564.8	565.3	565.1	564.2	563.4	562.4	561.6	560.2
145°	582.9	583.4	584.0	584.6	585.0	584.9	584.2	583.4	582.7	581.9	580.0
147.5°	600.3	600.8	601.2	601.7	602.1	602.1	601.5	601.0	600.4	599.8	597.9
150°	611.0	611.4	612.0	612.6	613.1	613.0	612.4	611.7	611.1	610.4	608.7
152.5°	620.0	620.7	621.4	622.2	622.8	622.9	622.3	621.6	620.9	620.3	618.6
155°	632.5	633.5	634.3	635.2	636.0	636.2	635.6	634.9	634.2	633.6	632.3
157.5°	644.0	644.9	645.7	646.6	647.5	647.5	646.8	646.0	645.3	644.6	643.7
160°	650.7	651.5	652.3	653.1	653.8	653.8	653.2	652.5	652.0	651.3	650.6
162.5°	656.3	657.2	658.2	659.1	660.1	660.2	659.4	658.6	657.9	657.1	656.6
165°	664.5	665.3	666.1	666.8	667.6	667.6	666.8	666.1	665.3	664.5	664.2
167.5°	669.8	670.7	671.8	672.7	673.7	673.8	673.1	672.2	671.5	670.7	670.4
170°	672.9	673.9	674.9	675.8	676.8	676.9	676.2	675.4	674.7	673.9	673.6
172.5°	675.2	676.3	677.2	678.3	679.2	679.3	678.5	677.8	677.0	676.3	676.0
175°	677.3	678.4	679.5	680.6	681.7	681.8	681.1	680.3	679.6	678.8	678.5
177.5°	678.6	679.4	680.1	681.0	681.7	681.8	681.3	680.6	680.0	679.4	679.3
180°	679.8	679.8	679.8	679.8	679.8	679.8	679.8	679.8	679.8	679.8	679.8



TEST NUMBER: P331339-830

CATALOG NUMBER: SA2XXDIP-C675D530U830-4F0-1E-UDD-A

**CANDELA DISTRIBUTION (continued):**

	55°	60°	65°	70°	75°	80°	85°	90°	95°	100°	105°
0°	1252.0	1252.0	1252.0	1252.0	1252.0	1252.0	1252.0	1252.0	1252.0	1252.0	1252.0
2.5°	1284.7	1281.6	1279.7	1272.7	1266.6	1260.5	1258.5	1259.2	1250.8	1242.7	1239.3
5°	1334.7	1325.1	1316.0	1303.0	1287.6	1270.7	1262.1	1255.3	1238.5	1220.2	1209.7
7.5°	1379.6	1365.8	1348.2	1323.7	1301.4	1274.9	1258.0	1243.1	1218.4	1192.7	1176.9
10°	1406.9	1388.1	1365.5	1335.7	1308.2	1276.0	1253.4	1230.8	1201.9	1171.1	1151.9
12.5°	1430.4	1405.0	1382.8	1344.5	1312.1	1271.8	1244.9	1213.1	1182.7	1146.1	1127.3
15°	1486.3	1439.6	1397.2	1354.0	1314.0	1257.7	1227.9	1185.1	1145.1	1099.9	1078.3
17.5°	1529.5	1477.1	1410.3	1355.3	1308.7	1246.4	1202.6	1151.3	1104.1	1052.3	1022.9
20°	1554.2	1493.9	1422.3	1356.9	1301.0	1229.8	1182.2	1129.7	1074.4	1016.2	984.4
22.5°	1568.8	1505.5	1434.6	1351.0	1285.6	1216.4	1156.4	1098.9	1042.8	980.1	946.7
25°	1573.4	1515.6	1440.6	1346.2	1266.4	1188.0	1115.8	1060.0	992.1	933.4	884.9
27.5°	1550.5	1509.1	1436.9	1337.2	1244.2	1152.4	1072.0	1008.8	937.2	873.5	824.6
30°	1522.4	1498.3	1428.0	1327.9	1226.4	1127.8	1039.2	967.6	896.4	831.9	781.8
32.5°	1478.8	1473.7	1411.9	1314.8	1207.6	1096.6	1005.0	932.6	853.7	790.3	742.6
35°	1393.5	1416.5	1377.5	1285.6	1172.1	1052.3	953.2	870.4	788.6	728.0	683.2
37.5°	1278.9	1336.2	1326.1	1242.8	1124.2	1004.0	894.6	808.0	730.1	668.9	625.0
40°	1200.0	1273.1	1283.7	1210.1	1090.3	966.7	850.6	764.6	688.5	632.7	588.4
42.5°	1115.3	1200.8	1229.8	1170.8	1053.3	927.4	811.4	722.2	647.0	592.7	553.5
45°	973.4	1086.5	1138.9	1105.2	991.6	862.7	743.4	652.9	584.6	533.6	503.3
47.5°	840.7	964.2	1034.7	1022.8	923.0	795.3	677.4	590.6	524.1	483.3	456.2
50°	746.8	873.7	958.9	962.8	873.7	747.2	628.9	547.1	486.0	448.0	425.8
52.5°	665.2	786.4	879.3	899.7	818.7	697.2	585.4	504.0	450.2	415.2	395.4
55°	558.6	661.1	764.0	801.6	736.6	621.1	517.7	446.0	395.5	371.5	354.1
57.5°	464.4	549.9	645.0	686.5	646.4	547.5	450.5	388.3	347.3	326.2	312.9
60°	414.7	482.1	566.8	616.3	581.7	493.7	409.0	349.8	316.1	297.4	284.8
62.5°	368.5	428.2	499.8	545.2	526.3	443.3	367.4	315.2	286.1	268.4	259.5
65°	304.1	351.3	406.6	448.5	435.9	372.9	310.9	266.1	243.0	229.0	221.8
67.5°	250.4	284.5	322.8	359.5	349.4	304.7	255.0	220.1	202.8	190.9	186.5
70°	216.5	242.5	276.6	306.0	297.8	261.3	221.8	192.0	177.1	166.9	162.6
72.5°	184.2	205.6	231.6	255.6	250.1	219.7	186.8	164.3	152.8	143.5	139.9
75°	139.0	155.4	171.3	187.2	185.7	162.1	142.9	125.5	116.4	109.2	107.7
77.5°	102.6	111.8	122.6	132.1	129.4	115.9	100.9	91.0	84.2	79.4	78.6
80°	78.4	83.7	91.4	98.1	94.8	89.0	77.0	69.7	64.9	60.1	58.2
82.5°	56.8	62.2	66.8	70.4	67.9	62.5	55.0	50.1	47.2	44.0	43.2
85°	29.8	32.7	34.7	35.6	34.7	31.3	27.9	26.0	23.6	22.1	21.7
87.5°	13.2	13.0	12.8	13.4	12.0	11.8	10.0	8.6	8.4	8.3	7.7
90°	8.1	7.3	6.3	5.3	4.1	2.9	1.7	0.5	1.7	2.9	4.1
92.5°	10.6	10.1	9.7	9.5	9.6	9.7	9.8	9.9	9.8	9.7	9.6
95°	17.6	16.9	16.1	17.5	21.1	24.8	28.4	32.0	28.4	24.8	21.1
97.5°	22.1	20.4	18.6	22.8	33.0	43.2	53.3	63.4	53.3	43.2	33.0
100°	24.3	22.4	20.6	27.1	42.1	57.1	72.1	87.1	72.1	57.1	42.1
102.5°	59.9	75.5	91.0	100.4	103.5	106.7	109.9	113.0	109.9	106.7	103.5
105°	89.7	119.5	149.4	162.7	159.4	156.1	152.8	149.5	152.8	156.1	159.4
107.5°	113.6	149.4	185.1	201.7	199.1	196.4	193.8	191.1	193.8	196.4	199.1
110°	149.3	180.9	212.4	227.1	224.8	222.5	220.2	217.9	220.2	222.5	224.8





TEST NUMBER: P331339-830

CATALOG NUMBER: SA2XXDIP-C675D530U830-4F0-1E-UDD-A

**CANDELA DISTRIBUTION (continued):**

	55°	60°	65°	70°	75°	80°	85°	90°	95°	100°	105°
112.5°	232.7	240.5	248.4	251.2	249.2	247.1	245.2	243.1	245.2	247.1	249.2
115°	298.0	295.3	292.6	290.3	288.4	286.5	284.6	282.9	284.6	286.5	288.4
117.5°	332.4	330.5	328.7	326.7	324.6	322.5	320.5	318.4	320.5	322.5	324.6
120°	356.7	354.7	352.7	350.9	349.2	347.6	345.9	344.3	345.9	347.6	349.2
122.5°	379.5	377.3	375.2	373.2	371.6	369.9	368.1	366.4	368.1	369.9	371.6
125°	411.5	409.4	407.4	405.6	404.2	402.7	401.3	399.9	401.3	402.7	404.2
127.5°	441.3	439.7	438.2	436.6	435.0	433.5	431.9	430.3	431.9	433.5	435.0
130°	460.4	459.3	458.1	456.6	454.9	453.1	451.3	449.6	451.3	453.1	454.9
132.5°	479.0	477.8	476.5	475.2	473.7	472.2	470.7	469.3	470.7	472.2	473.7
135°	505.2	504.2	503.2	501.8	500.1	498.3	496.6	494.8	496.6	498.3	500.1
137.5°	529.0	527.9	526.8	525.6	524.3	523.1	521.9	520.8	521.9	523.1	524.3
140°	544.6	543.4	542.2	541.1	540.3	539.4	538.5	537.6	538.5	539.4	540.3
142.5°	558.7	557.4	556.0	555.0	554.1	553.4	552.6	551.8	552.6	553.4	554.1
145°	578.2	576.4	574.5	573.6	573.7	573.8	573.9	574.0	573.9	573.8	573.7
147.5°	596.2	594.3	592.5	591.7	592.2	592.6	593.0	593.4	593.0	592.6	592.2
150°	606.9	605.2	603.4	602.9	603.7	604.5	605.2	606.0	605.2	604.5	603.7
152.5°	617.0	615.3	613.6	613.2	614.1	614.9	615.8	616.6	615.8	614.9	614.1
155°	630.9	629.6	628.3	628.1	629.1	630.1	631.1	632.1	631.1	630.1	629.1
157.5°	642.7	641.8	640.9	640.8	641.7	642.5	643.4	644.1	643.4	642.5	641.7
160°	650.0	649.3	648.7	648.7	649.3	650.0	650.6	651.3	650.6	650.0	649.3
162.5°	656.0	655.4	654.9	655.0	655.5	656.2	656.9	657.5	656.9	656.2	655.5
165°	663.8	663.5	663.3	663.4	664.0	664.7	665.3	666.0	665.3	664.7	664.0
167.5°	670.1	669.8	669.5	669.7	670.3	671.0	671.7	672.3	671.7	671.0	670.3
170°	673.4	673.3	673.0	673.3	673.9	674.6	675.2	675.8	675.2	674.6	673.9
172.5°	675.8	675.6	675.3	675.6	676.3	676.9	677.6	678.3	677.6	676.9	676.3
175°	678.3	678.2	678.0	678.2	679.0	679.8	680.5	681.3	680.5	679.8	679.0
177.5°	679.2	679.1	679.0	679.3	680.0	680.5	681.2	681.7	681.2	680.5	680.0
180°	679.8	679.8	679.8	679.8	679.8	679.8	679.8	679.8	679.8	679.8	679.8



TEST NUMBER: P331339-830  
 CATALOG NUMBER: SA2XXDIP-C675D530U830-4F0-1E-UDD-A

**CANDELA DISTRIBUTION (continued):**

	110°	115°	120°	125°	130°	135°	140°	145°	150°	155°	160°
0°	1252.0	1252.0	1252.0	1252.0	1252.0	1252.0	1252.0	1252.0	1252.0	1252.0	1252.0
2.5°	1235.4	1233.1	1225.0	1220.8	1213.8	1207.3	1203.1	1205.0	1206.5	1205.8	1204.6
5°	1200.0	1190.8	1176.9	1164.9	1156.2	1140.3	1133.6	1130.2	1127.4	1124.0	1120.6
7.5°	1157.8	1143.4	1123.4	1106.3	1090.1	1070.4	1059.1	1052.3	1045.5	1037.8	1031.1
10°	1127.8	1107.6	1086.5	1062.3	1043.1	1025.3	1009.5	998.9	989.3	980.1	973.4
12.5°	1096.3	1073.0	1046.8	1013.9	992.7	967.2	964.8	946.1	931.1	925.5	917.6
15°	1046.0	1013.3	980.1	941.1	924.3	901.2	886.7	872.3	859.3	850.2	847.8
17.5°	988.9	946.6	913.6	885.6	858.0	834.3	821.0	809.5	798.8	786.6	784.9
20°	945.5	908.9	872.8	848.3	819.9	795.8	779.5	767.9	758.7	751.6	745.3
22.5°	904.3	864.2	831.2	804.4	776.4	757.0	744.0	732.9	725.3	717.3	711.4
25°	838.2	806.9	770.8	740.5	717.4	704.9	694.3	684.7	679.9	674.6	667.9
27.5°	780.3	745.6	711.8	688.3	668.1	657.0	649.4	642.9	638.4	635.3	631.5
30°	739.5	704.4	678.0	654.9	638.0	627.0	622.2	618.3	613.0	611.1	609.2
32.5°	700.3	668.6	646.0	625.9	609.9	602.7	598.2	594.8	590.7	588.7	584.8
35°	644.7	618.3	596.2	585.0	572.1	565.8	562.5	557.6	553.8	551.9	551.4
37.5°	592.5	569.5	555.0	540.7	535.3	531.4	526.8	523.5	522.4	522.1	521.6
40°	558.6	539.9	526.9	515.3	512.9	507.1	503.3	500.4	500.4	500.9	500.4
42.5°	527.8	511.0	499.5	489.6	486.7	483.2	479.4	479.2	480.0	481.6	480.0
45°	481.2	469.1	460.9	456.1	450.8	447.4	447.0	448.5	448.9	449.4	450.8
47.5°	438.2	430.3	422.8	417.5	415.2	414.6	414.1	416.6	418.9	419.7	422.0
50°	412.8	403.7	397.5	394.1	392.1	391.2	392.1	395.0	396.9	399.4	400.8
52.5°	384.4	377.9	373.5	371.0	370.2	370.8	371.0	374.3	377.3	378.1	378.9
55°	345.0	340.2	339.2	334.9	336.8	336.3	338.7	340.6	343.6	346.4	346.9
57.5°	305.8	301.9	299.3	299.6	300.2	302.4	304.3	307.7	310.9	313.9	314.1
60°	279.6	277.6	276.2	276.2	277.1	280.0	282.5	285.8	287.8	289.6	291.1
62.5°	255.7	253.7	252.3	253.1	255.6	257.3	260.1	261.9	263.8	265.8	266.5
65°	217.9	217.0	218.5	219.4	219.9	222.3	225.6	227.1	229.0	230.0	233.4
67.5°	183.2	183.4	183.2	184.5	187.4	187.9	191.1	194.4	194.8	196.7	198.9
70°	159.8	160.7	161.6	162.6	165.0	166.0	168.4	169.8	171.7	173.2	174.7
72.5°	138.2	138.4	139.3	139.1	141.2	143.3	145.3	146.8	148.6	150.5	151.9
75°	106.3	106.3	107.3	107.7	110.2	112.6	112.1	113.1	115.0	116.9	117.9
77.5°	77.7	76.6	77.7	78.1	78.9	81.0	81.3	82.7	84.8	84.2	85.3
80°	59.2	57.8	59.2	59.7	59.7	62.1	62.1	63.1	64.5	63.1	64.5
82.5°	42.2	41.6	42.6	42.7	43.5	43.5	44.4	44.6	46.0	45.3	46.0
85°	21.2	20.7	21.2	20.7	21.2	21.7	21.7	21.2	21.2	22.1	20.7
87.5°	7.6	7.4	7.3	7.4	7.2	7.0	6.7	6.8	6.9	6.2	6.3
90°	5.3	6.3	7.3	8.1	9.0	9.8	10.4	10.9	11.5	12.1	12.4
92.5°	9.5	9.7	10.1	10.6	10.9	11.4	11.7	12.0	12.3	12.5	12.7
95°	17.5	16.1	16.9	17.6	18.4	19.2	19.7	20.3	20.8	21.4	21.6
97.5°	22.8	18.6	20.4	22.1	23.9	25.6	26.1	26.6	27.0	27.4	27.7
100°	27.1	20.6	22.4	24.3	26.2	28.0	28.9	29.8	30.6	31.6	32.0
102.5°	100.4	91.0	75.5	59.9	44.4	28.8	30.0	31.1	32.2	33.4	34.1
105°	162.7	149.4	119.5	89.7	59.9	30.0	31.2	32.4	33.6	34.8	35.6
107.5°	201.7	185.1	149.4	113.6	77.8	42.0	40.8	39.6	38.4	37.1	36.8
110°	227.1	212.4	180.9	149.3	117.6	86.1	75.1	64.2	53.3	42.3	37.1



TEST NUMBER: P331339-830

CATALOG NUMBER: SA2XXDIP-C675D530U830-4F0-1E-UDD-A

**CANDELA DISTRIBUTION (continued):**

	110°	115°	120°	125°	130°	135°	140°	145°	150°	155°	160°
112.5°	251.2	248.4	240.5	232.7	224.9	217.2	177.2	137.3	97.5	57.6	37.9
115°	290.3	292.6	295.3	298.0	300.8	303.5	252.9	202.3	151.7	101.0	71.8
117.5°	326.7	328.7	330.5	332.4	334.3	336.1	324.0	311.7	299.4	287.2	268.2
120°	350.9	352.7	354.7	356.7	358.5	360.5	361.8	363.2	364.5	365.8	359.1
122.5°	373.2	375.2	377.3	379.5	381.6	383.8	384.6	385.3	386.2	386.9	385.9
125°	405.6	407.4	409.4	411.5	413.6	415.7	416.4	417.2	417.9	418.7	419.2
127.5°	436.6	438.2	439.7	441.3	442.8	444.4	445.4	446.6	447.7	448.8	449.4
130°	456.6	458.1	459.3	460.4	461.7	462.9	464.1	465.2	466.5	467.7	468.3
132.5°	475.2	476.5	477.8	479.0	480.1	481.4	482.4	483.4	484.5	485.5	485.9
135°	501.8	503.2	504.2	505.2	506.1	507.1	508.2	509.3	510.4	511.5	512.0
137.5°	525.6	526.8	527.9	529.0	530.1	531.2	532.3	533.4	534.4	535.6	535.8
140°	541.1	542.2	543.4	544.6	545.7	547.0	548.0	548.9	549.9	550.9	551.1
142.5°	555.0	556.0	557.4	558.7	560.2	561.6	562.4	563.4	564.2	565.1	565.3
145°	573.6	574.5	576.4	578.2	580.0	581.9	582.7	583.4	584.2	584.9	585.0
147.5°	591.7	592.5	594.3	596.2	597.9	599.8	600.4	601.0	601.5	602.1	602.1
150°	602.9	603.4	605.2	606.9	608.7	610.4	611.1	611.7	612.4	613.0	613.1
152.5°	613.2	613.6	615.3	617.0	618.6	620.3	620.9	621.6	622.3	622.9	622.8
155°	628.1	628.3	629.6	630.9	632.3	633.6	634.2	634.9	635.6	636.2	636.0
157.5°	640.8	640.9	641.8	642.7	643.7	644.6	645.3	646.0	646.8	647.5	647.5
160°	648.7	648.7	649.3	650.0	650.6	651.3	652.0	652.5	653.2	653.8	653.8
162.5°	655.0	654.9	655.4	656.0	656.6	657.1	657.9	658.6	659.4	660.2	660.1
165°	663.4	663.3	663.5	663.8	664.2	664.5	665.3	666.1	666.8	667.6	667.6
167.5°	669.7	669.5	669.8	670.1	670.4	670.7	671.5	672.2	673.1	673.8	673.7
170°	673.3	673.0	673.3	673.4	673.6	673.9	674.7	675.4	676.2	676.9	676.8
172.5°	675.6	675.3	675.6	675.8	676.0	676.3	677.0	677.8	678.5	679.3	679.2
175°	678.2	678.0	678.2	678.3	678.5	678.8	679.6	680.3	681.1	681.8	681.7
177.5°	679.3	679.0	679.1	679.2	679.3	679.4	680.0	680.6	681.3	681.8	681.7
180°	679.8	679.8	679.8	679.8	679.8	679.8	679.8	679.8	679.8	679.8	679.8



TEST NUMBER: P331339-830  
 CATALOG NUMBER: SA2XXDIP-C675D530U830-4F0-1E-UDD-A

**CANDELA DISTRIBUTION (continued):**

	165°	170°	175°	180°	185°	190°	195°	200°	205°	210°	215°
0°	1252.0	1252.0	1252.0	1252.0	1252.0	1252.0	1252.0	1252.0	1252.0	1252.0	1252.0
2.5°	1200.8	1200.0	1200.0	1196.6	1200.0	1200.0	1200.8	1204.6	1205.8	1206.5	1205.0
5°	1113.9	1112.4	1110.0	1112.4	1110.0	1112.4	1113.9	1120.6	1124.0	1127.4	1130.2
7.5°	1027.9	1022.2	1021.3	1015.6	1021.3	1022.2	1027.9	1031.1	1037.8	1045.5	1052.3
10°	965.2	961.3	960.8	951.7	960.8	961.3	965.2	973.4	980.1	989.3	998.9
12.5°	917.5	908.2	910.0	904.7	910.0	908.2	917.5	917.6	925.5	931.1	946.1
15°	834.8	834.8	832.8	824.7	832.8	834.8	834.8	847.8	850.2	859.3	872.3
17.5°	775.4	774.5	769.9	772.1	769.9	774.5	775.4	784.9	786.6	798.8	809.5
20°	740.0	737.2	731.3	731.3	731.3	737.2	740.0	745.3	751.6	758.7	767.9
22.5°	706.5	706.3	700.2	702.1	700.2	706.3	706.5	711.4	717.3	725.3	732.9
25°	667.3	663.5	660.6	662.0	660.6	663.5	667.3	667.9	674.6	679.9	684.7
27.5°	630.2	628.1	627.9	624.0	627.9	628.1	630.2	631.5	635.3	638.4	642.9
30°	608.7	603.9	604.8	602.4	604.8	603.9	608.7	609.2	611.1	613.0	618.3
32.5°	584.0	582.3	581.4	579.3	581.4	582.3	584.0	584.8	588.7	590.7	594.8
35°	550.4	550.9	548.6	549.5	548.6	550.9	550.4	551.4	551.9	553.8	557.6
37.5°	521.1	522.6	521.5	521.8	521.5	522.6	521.1	521.6	522.1	522.4	523.5
40°	501.8	501.8	501.8	503.3	501.8	501.8	501.8	500.4	500.9	500.4	500.4
42.5°	483.3	482.6	481.8	481.7	481.8	482.6	483.3	480.0	481.6	480.0	479.2
45°	451.8	453.3	453.7	451.3	453.7	453.3	451.8	450.8	449.4	448.9	448.5
47.5°	423.2	423.4	423.2	425.4	423.2	423.4	423.2	422.0	419.7	418.9	416.6
50°	403.2	402.3	403.2	402.3	403.2	402.3	403.2	400.8	399.4	396.9	395.0
52.5°	382.0	382.2	381.6	381.4	381.6	382.2	382.0	378.9	378.1	377.3	374.3
55°	348.8	349.8	349.3	349.3	349.3	349.8	348.8	346.9	346.4	343.6	340.6
57.5°	314.5	315.4	316.0	313.9	316.0	315.4	314.5	314.1	313.9	310.9	307.7
60°	290.6	293.0	292.6	291.6	292.6	293.0	290.6	291.1	289.6	287.8	285.8
62.5°	268.7	269.6	269.5	269.3	269.5	269.6	268.7	266.5	265.8	263.8	261.9
65°	234.8	235.7	234.3	235.7	234.3	235.7	234.8	233.4	230.0	229.0	227.1
67.5°	198.3	198.6	199.7	200.4	199.7	198.6	198.3	198.9	196.7	194.8	194.4
70°	175.6	175.1	176.5	178.0	176.5	175.1	175.6	174.7	173.2	171.7	169.8
72.5°	151.7	152.8	152.3	153.4	152.3	152.8	151.7	151.9	150.5	148.6	146.8
75°	116.9	118.4	117.9	119.3	117.9	118.4	116.9	117.9	116.9	115.0	113.1
77.5°	84.5	84.6	84.5	85.3	84.5	84.6	84.5	85.3	84.2	84.8	82.7
80°	64.5	63.5	62.6	64.5	62.6	63.5	64.5	64.5	63.1	64.5	63.1
82.5°	44.9	45.4	44.5	44.5	44.5	45.4	44.9	46.0	45.3	46.0	44.6
85°	20.7	20.2	19.2	19.2	19.2	20.2	20.7	20.7	22.1	21.2	21.2
87.5°	6.4	6.0	6.0	5.7	6.0	6.0	6.4	6.3	6.2	6.9	6.8
90°	12.6	12.8	13.1	13.3	13.1	12.8	12.6	12.4	12.1	11.5	10.9
92.5°	12.9	13.0	13.2	13.3	13.2	13.0	12.9	12.7	12.5	12.3	12.0
95°	21.5	21.4	21.3	21.1	21.3	21.4	21.5	21.6	21.4	20.8	20.3
97.5°	27.8	28.0	28.1	28.3	28.1	28.0	27.8	27.7	27.4	27.0	26.6
100°	32.3	32.5	32.7	33.0	32.7	32.5	32.3	32.0	31.6	30.6	29.8
102.5°	34.4	34.7	35.0	35.3	35.0	34.7	34.4	34.1	33.4	32.2	31.1
105°	36.1	36.5	36.9	37.4	36.9	36.5	36.1	35.6	34.8	33.6	32.4
107.5°	37.1	37.6	38.0	38.5	38.0	37.6	37.1	36.8	37.1	38.4	39.6
110°	37.5	38.0	38.5	38.8	38.5	38.0	37.5	37.1	42.3	53.3	64.2



TEST NUMBER: P331339-830

CATALOG NUMBER: SA2XXDIP-C675D530U830-4F0-1E-UDD-A

**CANDELA DISTRIBUTION (continued):**

	165°	170°	175°	180°	185°	190°	195°	200°	205°	210°	215°
112.5°	38.2	38.5	38.9	39.2	38.9	38.5	38.2	37.9	57.6	97.5	137.3
115°	63.9	56.1	48.2	40.3	48.2	56.1	63.9	71.8	101.0	151.7	202.3
117.5°	242.2	216.4	190.6	164.7	190.6	216.4	242.2	268.2	287.2	299.4	311.7
120°	344.3	329.6	314.8	300.0	314.8	329.6	344.3	359.1	365.8	364.5	363.2
122.5°	383.0	380.1	377.3	374.4	377.3	380.1	383.0	385.9	386.9	386.2	385.3
125°	419.6	419.9	420.3	420.6	420.3	419.9	419.6	419.2	418.7	417.9	417.2
127.5°	449.5	449.6	449.6	449.7	449.6	449.6	449.5	449.4	448.8	447.7	446.6
130°	468.1	468.0	467.9	467.8	467.9	468.0	468.1	468.3	467.7	466.5	465.2
132.5°	485.8	485.7	485.6	485.5	485.6	485.7	485.8	485.9	485.5	484.5	483.4
135°	511.7	511.5	511.3	511.0	511.3	511.5	511.7	512.0	511.5	510.4	509.3
137.5°	535.5	535.1	534.8	534.4	534.8	535.1	535.5	535.8	535.6	534.4	533.4
140°	550.5	550.1	549.5	548.9	549.5	550.1	550.5	551.1	550.9	549.9	548.9
142.5°	564.8	564.2	563.6	563.1	563.6	564.2	564.8	565.3	565.1	564.2	563.4
145°	584.6	584.0	583.4	582.9	583.4	584.0	584.6	585.0	584.9	584.2	583.4
147.5°	601.7	601.2	600.8	600.3	600.8	601.2	601.7	602.1	602.1	601.5	601.0
150°	612.6	612.0	611.4	611.0	611.4	612.0	612.6	613.1	613.0	612.4	611.7
152.5°	622.2	621.4	620.7	620.0	620.7	621.4	622.2	622.8	622.9	622.3	621.6
155°	635.2	634.3	633.5	632.5	633.5	634.3	635.2	636.0	636.2	635.6	634.9
157.5°	646.6	645.7	644.9	644.0	644.9	645.7	646.6	647.5	647.5	646.8	646.0
160°	653.1	652.3	651.5	650.7	651.5	652.3	653.1	653.8	653.8	653.2	652.5
162.5°	659.1	658.2	657.2	656.3	657.2	658.2	659.1	660.1	660.2	659.4	658.6
165°	666.8	666.1	665.3	664.5	665.3	666.1	666.8	667.6	667.6	666.8	666.1
167.5°	672.7	671.8	670.7	669.8	670.7	671.8	672.7	673.7	673.8	673.1	672.2
170°	675.8	674.9	673.9	672.9	673.9	674.9	675.8	676.8	676.9	676.2	675.4
172.5°	678.3	677.2	676.3	675.2	676.3	677.2	678.3	679.2	679.3	678.5	677.8
175°	680.6	679.5	678.4	677.3	678.4	679.5	680.6	681.7	681.8	681.1	680.3
177.5°	681.0	680.1	679.4	678.6	679.4	680.1	681.0	681.7	681.8	681.3	680.6
180°	679.8	679.8	679.8	679.8	679.8	679.8	679.8	679.8	679.8	679.8	679.8



TEST NUMBER: P331339-830

CATALOG NUMBER: SA2XXDIP-C675D530U830-4F0-1E-UDD-A

**CANDELA DISTRIBUTION (continued):**

	220°	225°	230°	235°	240°	245°	250°	255°	260°	265°	270°
0°	1252.0	1252.0	1252.0	1252.0	1252.0	1252.0	1252.0	1252.0	1252.0	1252.0	1252.0
2.5°	1203.1	1207.3	1213.8	1220.8	1225.0	1233.1	1235.4	1239.3	1242.7	1250.8	1259.2
5°	1133.6	1140.3	1156.2	1164.9	1176.9	1190.8	1200.0	1209.7	1220.2	1238.5	1255.3
7.5°	1059.1	1070.4	1090.1	1106.3	1123.4	1143.4	1157.8	1176.9	1192.7	1218.4	1243.1
10°	1009.5	1025.3	1043.1	1062.3	1086.5	1107.6	1127.8	1151.9	1171.1	1201.9	1230.8
12.5°	964.8	967.2	992.7	1013.9	1046.8	1073.0	1096.3	1127.3	1146.1	1182.7	1213.1
15°	886.7	901.2	924.3	941.1	980.1	1013.3	1046.0	1078.3	1099.9	1145.1	1185.1
17.5°	821.0	834.3	858.0	885.6	913.6	946.6	988.9	1022.9	1052.3	1104.1	1151.3
20°	779.5	795.8	819.9	848.3	872.8	908.9	945.5	984.4	1016.2	1074.4	1129.7
22.5°	744.0	757.0	776.4	804.4	831.2	864.2	904.3	946.7	980.1	1042.8	1098.9
25°	694.3	704.9	717.4	740.5	770.8	806.9	838.2	884.9	933.4	992.1	1060.0
27.5°	649.4	657.0	668.1	688.3	711.8	745.6	780.3	824.6	873.5	937.2	1008.8
30°	622.2	627.0	638.0	654.9	678.0	704.4	739.5	781.8	831.9	896.4	967.6
32.5°	598.2	602.7	609.9	625.9	646.0	668.6	700.3	742.6	790.3	853.7	932.6
35°	562.5	565.8	572.1	585.0	596.2	618.3	644.7	683.2	728.0	788.6	870.4
37.5°	526.8	531.4	535.3	540.7	555.0	569.5	592.5	625.0	668.9	730.1	808.0
40°	503.3	507.1	512.9	515.3	526.9	539.9	558.6	588.4	632.7	688.5	764.6
42.5°	479.4	483.2	486.7	489.6	499.5	511.0	527.8	553.5	592.7	647.0	722.2
45°	447.0	447.4	450.8	456.1	460.9	469.1	481.2	503.3	533.6	584.6	652.9
47.5°	414.1	414.6	415.2	417.5	422.8	430.3	438.2	456.2	483.3	524.1	590.6
50°	392.1	391.2	392.1	394.1	397.5	403.7	412.8	425.8	448.0	486.0	547.1
52.5°	371.0	370.8	370.2	371.0	373.5	377.9	384.4	395.4	415.2	450.2	504.0
55°	338.7	336.3	336.8	334.9	339.2	340.2	345.0	354.1	371.5	395.5	446.0
57.5°	304.3	302.4	300.2	299.6	299.3	301.9	305.8	312.9	326.2	347.3	388.3
60°	282.5	280.0	277.1	276.2	276.2	277.6	279.6	284.8	297.4	316.1	349.8
62.5°	260.1	257.3	255.6	253.1	252.3	253.7	255.7	259.5	268.4	286.1	315.2
65°	225.6	222.3	219.9	219.4	218.5	217.0	217.9	221.8	229.0	243.0	266.1
67.5°	191.1	187.9	187.4	184.5	183.2	183.4	183.2	186.5	190.9	202.8	220.1
70°	168.4	166.0	165.0	162.6	161.6	160.7	159.8	162.6	166.9	177.1	192.0
72.5°	145.3	143.3	141.2	139.1	139.3	138.4	138.2	139.9	143.5	152.8	164.3
75°	112.1	112.6	110.2	107.7	107.3	106.3	106.3	107.7	109.2	116.4	125.5
77.5°	81.3	81.0	78.9	78.1	77.7	76.6	77.7	78.6	79.4	84.2	91.0
80°	62.1	62.1	59.7	59.7	59.2	57.8	59.2	58.2	60.1	64.9	69.7
82.5°	44.4	43.5	43.5	42.7	42.6	41.6	42.2	43.2	44.0	47.2	50.1
85°	21.7	21.7	21.2	20.7	21.2	20.7	21.2	21.7	22.1	23.6	26.0
87.5°	6.7	7.0	7.2	7.4	7.3	7.4	7.6	7.7	8.3	8.4	8.6
90°	10.4	9.8	9.0	8.1	7.3	6.3	5.3	4.1	2.9	1.7	0.5
92.5°	11.7	11.4	10.9	10.6	10.1	9.7	9.5	9.6	9.7	9.8	9.9
95°	19.7	19.2	18.4	17.6	16.9	16.1	17.5	21.1	24.8	28.4	32.0
97.5°	26.1	25.6	23.9	22.1	20.4	18.6	22.8	33.0	43.2	53.3	63.4
100°	28.9	28.0	26.2	24.3	22.4	20.6	27.1	42.1	57.1	72.1	87.1
102.5°	30.0	28.8	44.4	59.9	75.5	91.0	100.4	103.5	106.7	109.9	113.0
105°	31.2	30.0	59.9	89.7	119.5	149.4	162.7	159.4	156.1	152.8	149.5
107.5°	40.8	42.0	77.8	113.6	149.4	185.1	201.7	199.1	196.4	193.8	191.1
110°	75.1	86.1	117.6	149.3	180.9	212.4	227.1	224.8	222.5	220.2	217.9



TEST NUMBER: P331339-830

CATALOG NUMBER: SA2XXDIP-C675D530U830-4F0-1E-UDD-A

**CANDELA DISTRIBUTION (continued):**

	220°	225°	230°	235°	240°	245°	250°	255°	260°	265°	270°
112.5°	177.2	217.2	224.9	232.7	240.5	248.4	251.2	249.2	247.1	245.2	243.1
115°	252.9	303.5	300.8	298.0	295.3	292.6	290.3	288.4	286.5	284.6	282.9
117.5°	324.0	336.1	334.3	332.4	330.5	328.7	326.7	324.6	322.5	320.5	318.4
120°	361.8	360.5	358.5	356.7	354.7	352.7	350.9	349.2	347.6	345.9	344.3
122.5°	384.6	383.8	381.6	379.5	377.3	375.2	373.2	371.6	369.9	368.1	366.4
125°	416.4	415.7	413.6	411.5	409.4	407.4	405.6	404.2	402.7	401.3	399.9
127.5°	445.4	444.4	442.8	441.3	439.7	438.2	436.6	435.0	433.5	431.9	430.3
130°	464.1	462.9	461.7	460.4	459.3	458.1	456.6	454.9	453.1	451.3	449.6
132.5°	482.4	481.4	480.1	479.0	477.8	476.5	475.2	473.7	472.2	470.7	469.3
135°	508.2	507.1	506.1	505.2	504.2	503.2	501.8	500.1	498.3	496.6	494.8
137.5°	532.3	531.2	530.1	529.0	527.9	526.8	525.6	524.3	523.1	521.9	520.8
140°	548.0	547.0	545.7	544.6	543.4	542.2	541.1	540.3	539.4	538.5	537.6
142.5°	562.4	561.6	560.2	558.7	557.4	556.0	555.0	554.1	553.4	552.6	551.8
145°	582.7	581.9	580.0	578.2	576.4	574.5	573.6	573.7	573.8	573.9	574.0
147.5°	600.4	599.8	597.9	596.2	594.3	592.5	591.7	592.2	592.6	593.0	593.4
150°	611.1	610.4	608.7	606.9	605.2	603.4	602.9	603.7	604.5	605.2	606.0
152.5°	620.9	620.3	618.6	617.0	615.3	613.6	613.2	614.1	614.9	615.8	616.6
155°	634.2	633.6	632.3	630.9	629.6	628.3	628.1	629.1	630.1	631.1	632.1
157.5°	645.3	644.6	643.7	642.7	641.8	640.9	640.8	641.7	642.5	643.4	644.1
160°	652.0	651.3	650.6	650.0	649.3	648.7	648.7	649.3	650.0	650.6	651.3
162.5°	657.9	657.1	656.6	656.0	655.4	654.9	655.0	655.5	656.2	656.9	657.5
165°	665.3	664.5	664.2	663.8	663.5	663.3	663.4	664.0	664.7	665.3	666.0
167.5°	671.5	670.7	670.4	670.1	669.8	669.5	669.7	670.3	671.0	671.7	672.3
170°	674.7	673.9	673.6	673.4	673.3	673.0	673.3	673.9	674.6	675.2	675.8
172.5°	677.0	676.3	676.0	675.8	675.6	675.3	675.6	676.3	676.9	677.6	678.3
175°	679.6	678.8	678.5	678.3	678.2	678.0	678.2	679.0	679.8	680.5	681.3
177.5°	680.0	679.4	679.3	679.2	679.1	679.0	679.3	680.0	680.5	681.2	681.7
180°	679.8	679.8	679.8	679.8	679.8	679.8	679.8	679.8	679.8	679.8	679.8



TEST NUMBER: P331339-830

CATALOG NUMBER: SA2XXDIP-C675D530U830-4F0-1E-UDD-A

**CANDELA DISTRIBUTION (continued):**

	275°	280°	285°	290°	295°	300°	305°	310°	315°	320°	325°
0°	1252.0	1252.0	1252.0	1252.0	1252.0	1252.0	1252.0	1252.0	1252.0	1252.0	1252.0
2.5°	1258.5	1260.5	1266.6	1272.7	1279.7	1281.6	1284.7	1282.0	1281.2	1288.5	1293.9
5°	1262.1	1270.7	1287.6	1303.0	1316.0	1325.1	1334.7	1338.6	1345.8	1355.8	1368.4
7.5°	1258.0	1274.9	1301.4	1323.7	1348.2	1365.8	1379.6	1391.3	1405.5	1424.7	1445.6
10°	1253.4	1276.0	1308.2	1335.7	1365.5	1388.1	1406.9	1425.1	1446.3	1472.8	1500.2
12.5°	1244.9	1271.8	1312.1	1344.5	1382.8	1405.0	1430.4	1469.8	1492.5	1529.4	1568.0
15°	1227.9	1257.7	1314.0	1354.0	1397.2	1439.6	1486.3	1523.8	1561.3	1583.0	1637.4
17.5°	1202.6	1246.4	1308.7	1355.3	1410.3	1477.1	1529.5	1572.0	1615.3	1650.5	1677.7
20°	1182.2	1229.8	1301.0	1356.9	1422.3	1493.9	1554.2	1597.4	1634.9	1664.3	1681.1
22.5°	1156.4	1216.4	1285.6	1351.0	1434.6	1505.5	1568.8	1602.8	1634.2	1648.5	1655.0
25°	1115.8	1188.0	1266.4	1346.2	1440.6	1515.6	1573.4	1594.0	1603.2	1589.2	1566.1
27.5°	1072.0	1152.4	1244.2	1337.2	1436.9	1509.1	1550.5	1547.2	1531.7	1486.6	1450.5
30°	1039.2	1127.8	1226.4	1327.9	1428.0	1498.3	1522.4	1498.3	1463.2	1412.7	1361.2
32.5°	1005.0	1096.6	1207.6	1314.8	1411.9	1473.7	1478.8	1437.5	1383.1	1325.7	1261.5
35°	953.2	1052.3	1172.1	1285.6	1377.5	1416.5	1393.5	1320.3	1255.8	1177.4	1089.8
37.5°	894.6	1004.0	1124.2	1242.8	1326.1	1336.2	1278.9	1201.9	1111.0	1018.8	915.8
40°	850.6	966.7	1090.3	1210.1	1283.7	1273.1	1200.0	1115.3	1007.0	894.5	798.7
42.5°	811.4	927.4	1053.3	1170.8	1229.8	1200.8	1115.3	1011.3	895.0	789.0	701.3
45°	743.4	862.7	991.6	1105.2	1138.9	1086.5	973.4	857.9	743.4	654.9	585.6
47.5°	677.4	795.3	923.0	1022.8	1034.7	964.2	840.7	721.8	623.4	551.3	502.4
50°	628.9	747.2	873.7	962.8	958.9	873.7	746.8	633.7	551.4	493.1	460.4
52.5°	585.4	697.2	818.7	899.7	879.3	786.4	665.2	564.8	497.1	451.6	422.0
55°	517.7	621.1	736.6	801.6	764.0	661.1	558.6	477.8	427.7	393.6	370.5
57.5°	450.5	547.5	646.4	686.5	645.0	549.9	464.4	405.8	368.2	342.9	327.8
60°	409.0	493.7	581.7	616.3	566.8	482.1	414.7	362.3	332.0	311.3	297.8
62.5°	367.4	443.3	526.3	545.2	499.8	428.2	368.5	325.0	300.0	281.6	269.0
65°	310.9	372.9	435.9	448.5	406.6	351.3	304.1	275.7	253.5	240.1	230.0
67.5°	255.0	304.7	349.4	359.5	322.8	284.5	250.4	225.6	210.7	199.4	191.0
70°	221.8	261.3	297.8	306.0	276.6	242.5	216.5	196.8	183.3	173.7	165.5
72.5°	186.8	219.7	250.1	255.6	231.6	205.6	184.2	168.7	156.7	150.6	142.8
75°	142.9	162.1	185.7	187.2	171.3	155.4	139.0	128.9	122.7	115.0	111.1
77.5°	100.9	115.9	129.4	132.1	122.6	111.8	102.6	94.7	89.4	85.9	82.3
80°	77.0	89.0	94.8	98.1	91.4	83.7	78.4	73.1	69.7	67.4	64.9
82.5°	55.0	62.5	67.9	70.4	66.8	62.2	56.8	53.9	51.3	49.3	48.4
85°	27.9	31.3	34.7	35.6	34.7	32.7	29.8	29.8	28.4	27.9	27.9
87.5°	10.0	11.8	12.0	13.4	12.8	13.0	13.2	12.9	12.7	12.4	12.2
90°	1.7	2.9	4.1	5.3	6.3	7.3	8.1	9.0	9.8	10.4	10.9
92.5°	9.8	9.7	9.6	9.5	9.7	10.1	10.6	10.9	11.4	11.7	12.0
95°	28.4	24.8	21.1	17.5	16.1	16.9	17.6	18.4	19.2	19.7	20.3
97.5°	53.3	43.2	33.0	22.8	18.6	20.4	22.1	23.9	25.6	26.1	26.6
100°	72.1	57.1	42.1	27.1	20.6	22.4	24.3	26.2	28.0	28.9	29.8
102.5°	109.9	106.7	103.5	100.4	91.0	75.5	59.9	44.4	28.8	30.0	31.1
105°	152.8	156.1	159.4	162.7	149.4	119.5	89.7	59.9	30.0	31.2	32.4
107.5°	193.8	196.4	199.1	201.7	185.1	149.4	113.6	77.8	42.0	40.8	39.6
110°	220.2	222.5	224.8	227.1	212.4	180.9	149.3	117.6	86.1	75.1	64.2





TEST NUMBER: P331339-830  
 CATALOG NUMBER: SA2XXDIP-C675D530U830-4F0-1E-UDD-A

**CANDELA DISTRIBUTION (continued):**

	275°	280°	285°	290°	295°	300°	305°	310°	315°	320°	325°
112.5°	245.2	247.1	249.2	251.2	248.4	240.5	232.7	224.9	217.2	177.2	137.3
115°	284.6	286.5	288.4	290.3	292.6	295.3	298.0	300.8	303.5	252.9	202.3
117.5°	320.5	322.5	324.6	326.7	328.7	330.5	332.4	334.3	336.1	324.0	311.7
120°	345.9	347.6	349.2	350.9	352.7	354.7	356.7	358.5	360.5	361.8	363.2
122.5°	368.1	369.9	371.6	373.2	375.2	377.3	379.5	381.6	383.8	384.6	385.3
125°	401.3	402.7	404.2	405.6	407.4	409.4	411.5	413.6	415.7	416.4	417.2
127.5°	431.9	433.5	435.0	436.6	438.2	439.7	441.3	442.8	444.4	445.4	446.6
130°	451.3	453.1	454.9	456.6	458.1	459.3	460.4	461.7	462.9	464.1	465.2
132.5°	470.7	472.2	473.7	475.2	476.5	477.8	479.0	480.1	481.4	482.4	483.4
135°	496.6	498.3	500.1	501.8	503.2	504.2	505.2	506.1	507.1	508.2	509.3
137.5°	521.9	523.1	524.3	525.6	526.8	527.9	529.0	530.1	531.2	532.3	533.4
140°	538.5	539.4	540.3	541.1	542.2	543.4	544.6	545.7	547.0	548.0	548.9
142.5°	552.6	553.4	554.1	555.0	556.0	557.4	558.7	560.2	561.6	562.4	563.4
145°	573.9	573.8	573.7	573.6	574.5	576.4	578.2	580.0	581.9	582.7	583.4
147.5°	593.0	592.6	592.2	591.7	592.5	594.3	596.2	597.9	599.8	600.4	601.0
150°	605.2	604.5	603.7	602.9	603.4	605.2	606.9	608.7	610.4	611.1	611.7
152.5°	615.8	614.9	614.1	613.2	613.6	615.3	617.0	618.6	620.3	620.9	621.6
155°	631.1	630.1	629.1	628.1	628.3	629.6	630.9	632.3	633.6	634.2	634.9
157.5°	643.4	642.5	641.7	640.8	640.9	641.8	642.7	643.7	644.6	645.3	646.0
160°	650.6	650.0	649.3	648.7	648.7	649.3	650.0	650.6	651.3	652.0	652.5
162.5°	656.9	656.2	655.5	655.0	654.9	655.4	656.0	656.6	657.1	657.9	658.6
165°	665.3	664.7	664.0	663.4	663.3	663.5	663.8	664.2	664.5	665.3	666.1
167.5°	671.7	671.0	670.3	669.7	669.5	669.8	670.1	670.4	670.7	671.5	672.2
170°	675.2	674.6	673.9	673.3	673.0	673.3	673.4	673.6	673.9	674.7	675.4
172.5°	677.6	676.9	676.3	675.6	675.3	675.6	675.8	676.0	676.3	677.0	677.8
175°	680.5	679.8	679.0	678.2	678.0	678.2	678.3	678.5	678.8	679.6	680.3
177.5°	681.2	680.5	680.0	679.3	679.0	679.1	679.2	679.3	679.4	680.0	680.6
180°	679.8	679.8	679.8	679.8	679.8	679.8	679.8	679.8	679.8	679.8	679.8



TEST NUMBER: P331339-830  
 CATALOG NUMBER: SA2XXDIP-C675D530U830-4F0-1E-UDD-A

**CANDELA DISTRIBUTION (continued):**

	330°	335°	340°	345°	350°	355°	360°
0°	1252.0	1252.0	1252.0	1252.0	1252.0	1252.0	1252.0
2.5°	1298.5	1303.9	1303.9	1304.7	1310.9	1310.0	1309.7
5°	1381.9	1390.1	1391.0	1399.7	1405.4	1403.5	1398.3
7.5°	1460.5	1475.7	1487.2	1493.6	1501.3	1506.0	1503.9
10°	1522.9	1545.0	1558.5	1567.6	1578.7	1586.9	1583.9
12.5°	1579.4	1605.8	1624.3	1639.9	1641.4	1651.9	1644.7
15°	1667.6	1695.5	1698.5	1710.1	1719.2	1718.2	1718.6
17.5°	1696.9	1705.8	1707.6	1707.9	1708.0	1704.6	1697.3
20°	1686.4	1683.1	1674.9	1668.7	1657.6	1656.1	1646.5
22.5°	1637.2	1626.5	1606.0	1592.4	1575.2	1570.7	1568.0
25°	1540.2	1516.6	1483.8	1452.6	1444.0	1427.1	1431.9
27.5°	1407.1	1370.4	1334.9	1309.5	1286.5	1261.3	1268.5
30°	1313.5	1272.1	1222.1	1183.6	1159.1	1135.0	1130.7
32.5°	1201.9	1141.3	1085.4	1051.6	1014.0	998.8	982.1
35°	1009.5	950.3	894.9	847.3	819.9	798.7	779.5
37.5°	836.3	768.2	723.6	684.9	665.2	653.0	656.1
40°	729.0	669.3	636.6	607.2	588.9	580.2	582.2
42.5°	642.0	597.3	570.3	550.3	537.3	532.5	531.4
45°	543.2	518.2	496.1	484.6	478.2	473.0	469.6
47.5°	475.9	455.4	443.0	436.1	430.6	425.3	425.2
50°	435.5	422.0	413.3	406.0	401.8	397.9	401.2
52.5°	404.6	392.3	383.7	377.2	375.6	372.1	372.0
55°	358.9	349.3	343.1	337.2	334.4	332.4	330.1
57.5°	317.4	308.2	302.5	298.8	293.3	291.3	290.6
60°	287.8	280.5	274.8	269.9	267.5	263.6	263.6
62.5°	260.4	253.2	247.8	244.1	240.2	238.7	239.0
65°	220.8	215.1	209.8	205.9	205.0	202.1	203.0
67.5°	184.5	180.6	175.0	173.0	171.1	169.6	168.4
70°	160.2	156.4	153.4	150.6	149.1	149.1	149.1
72.5°	139.8	135.2	133.5	129.8	130.6	129.1	127.6
75°	108.3	105.4	104.0	102.5	100.1	100.1	100.1
77.5°	79.6	78.8	77.1	75.5	74.9	74.5	74.6
80°	61.5	61.1	60.1	60.1	59.2	58.7	57.8
82.5°	47.3	46.1	45.5	45.1	45.0	44.9	44.7
85°	27.0	26.0	26.0	26.5	25.5	25.5	26.0
87.5°	12.7	12.8	12.5	12.5	13.0	12.6	12.6
90°	11.5	12.1	12.4	12.6	12.8	13.1	13.3
92.5°	12.3	12.5	12.7	12.9	13.0	13.2	13.3
95°	20.8	21.4	21.6	21.5	21.4	21.3	21.1
97.5°	27.0	27.4	27.7	27.8	28.0	28.1	28.3
100°	30.6	31.6	32.0	32.3	32.5	32.7	33.0
102.5°	32.2	33.4	34.1	34.4	34.7	35.0	35.3
105°	33.6	34.8	35.6	36.1	36.5	36.9	37.4
107.5°	38.4	37.1	36.8	37.1	37.6	38.0	38.5
110°	53.3	42.3	37.1	37.5	38.0	38.5	38.8



TEST NUMBER: P331339-830

CATALOG NUMBER: SA2XXDIP-C675D530U830-4F0-1E-UDD-A

**CANDELA DISTRIBUTION (continued):**

	330°	335°	340°	345°	350°	355°	360°
112.5°	97.5	57.6	37.9	38.2	38.5	38.9	39.2
115°	151.7	101.0	71.8	63.9	56.1	48.2	40.3
117.5°	299.4	287.2	268.2	242.2	216.4	190.6	164.7
120°	364.5	365.8	359.1	344.3	329.6	314.8	300.0
122.5°	386.2	386.9	385.9	383.0	380.1	377.3	374.4
125°	417.9	418.7	419.2	419.6	419.9	420.3	420.6
127.5°	447.7	448.8	449.4	449.5	449.6	449.6	449.7
130°	466.5	467.7	468.3	468.1	468.0	467.9	467.8
132.5°	484.5	485.5	485.9	485.8	485.7	485.6	485.5
135°	510.4	511.5	512.0	511.7	511.5	511.3	511.0
137.5°	534.4	535.6	535.8	535.5	535.1	534.8	534.4
140°	549.9	550.9	551.1	550.5	550.1	549.5	548.9
142.5°	564.2	565.1	565.3	564.8	564.2	563.6	563.1
145°	584.2	584.9	585.0	584.6	584.0	583.4	582.9
147.5°	601.5	602.1	602.1	601.7	601.2	600.8	600.3
150°	612.4	613.0	613.1	612.6	612.0	611.4	611.0
152.5°	622.3	622.9	622.8	622.2	621.4	620.7	620.0
155°	635.6	636.2	636.0	635.2	634.3	633.5	632.5
157.5°	646.8	647.5	647.5	646.6	645.7	644.9	644.0
160°	653.2	653.8	653.8	653.1	652.3	651.5	650.7
162.5°	659.4	660.2	660.1	659.1	658.2	657.2	656.3
165°	666.8	667.6	667.6	666.8	666.1	665.3	664.5
167.5°	673.1	673.8	673.7	672.7	671.8	670.7	669.8
170°	676.2	676.9	676.8	675.8	674.9	673.9	672.9
172.5°	678.5	679.3	679.2	678.3	677.2	676.3	675.2
175°	681.1	681.8	681.7	680.6	679.5	678.4	677.3
177.5°	681.3	681.8	681.7	681.0	680.1	679.4	678.6
180°	679.8	679.8	679.8	679.8	679.8	679.8	679.8

(END OF REPORT)