

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P333635-840

Luminaire Tested: **S125RDIP-S1270D1205U840-4F0-1E-UDD-A1**

Issue Date: 3/3/2020

Test Information

Test Method: LM-79-08
Report Number: P333635-840
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-11,
Test Lab: INNOVATION CENTER
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: NEO-RAY
Catalog Number: S125RDIP-S1270D1205U840-4F0-1E-UDD-A1
Description: DEFINE 5 DIRECT-INDIRECT PENDANT LED LUMINAIRE
DOWNLIGHT 1270 LUMENS PER FOOT, ASYMMETRIC DIFFUSER, REGRESSED HOUSING
UPLIGHT 1205 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER
Light Source: -
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 9179.4 lumens
Efficiency: N/A
Efficacy: 128.0 lumens/watt
Spacing Criteria (0/90/45): 1.4 / 1.22 / 1.47
Luminous Opening: Rectangular (W 4' x L: 0.42' x H: 0')
CIE Type: General Diffuse


Input Watts (W): 71.7
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P333635-840

CATALOG NUMBER: S125RDIP-S1270D1205U840-4F0-1E-UDD-A1

Luminous Intensity Polar Plot





TEST NUMBER: P333635-840

CATALOG NUMBER: S125RDIP-S1270D1205U840-4F0-1E-UDD-A1

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	108	108	108	108	100	100	100	100	86	86	86	72	72	72	60	60	60	54
1	99	95	91	88	92	88	85	82	76	73	71	64	63	61	54	53	52	47
2	91	83	78	73	84	78	73	68	67	63	60	57	54	52	48	46	44	40
3	83	74	67	61	77	69	62	57	59	55	51	51	47	44	43	40	38	34
4	76	65	58	52	70	61	54	49	53	48	44	45	41	38	38	35	33	30
5	70	58	51	45	65	55	48	42	48	42	38	41	37	33	35	31	29	26
6	65	53	45	39	60	49	42	37	43	37	33	37	33	29	32	28	26	23
7	60	48	40	34	55	45	38	32	39	33	29	34	29	26	29	25	23	20
8	55	43	36	30	51	41	34	29	36	30	26	31	26	23	27	23	20	18
9	52	40	32	27	48	37	30	26	33	27	23	28	24	21	24	21	19	16
10	48	36	29	24	45	34	28	23	30	25	21	26	22	19	23	19	17	15

AVERAGE LUMINANCE (cd/sqm):

	0°	90°	180°	270°
0°	12385	12385	12385	12385
5°	14249	12401	10952	12401
10°	16344	12338	9664	12338
15°	17653	12211	8590	12211
20°	19467	12065	7932	12065
25°	22528	11870	7360	11870
30°	24515	11665	6986	11665
35°	20679	11427	6641	11427
40°	14441	10997	6345	10997
45°	10714	10418	6054	10418
50°	8542	9815	5805	9815
55°	7250	9067	5584	9067
60°	6263	8400	5227	8400
65°	5582	7674	4499	7674
70°	4904	7030	4101	7030
75°	4245	6089	3850	6089
80°	3217	5121	3217	5121
85°	2690	4024	3031	4024



TEST NUMBER: P333635-840

CATALOG NUMBER: S125RDIP-S1270D1205U840-4F0-1E-UDD-A1

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	183.9	2.0
10°-20°	538.9	5.9
20°-30°	854.5	9.3
30°-40°	1030.4	11.2
40°-50°	920.2	10.0
50°-60°	705.7	7.7
60°-70°	458.6	5.0
70°-80°	223.0	2.4
80°-90°	56.5	0.6
90°-100°	101.0	1.1
100°-110°	298.2	3.2
110°-120°	505.2	5.5
120°-130°	664.8	7.2
130°-140°	745.0	8.1
140°-150°	730.1	8.0
150°-160°	613.2	6.7
160°-170°	407.6	4.4
170°-180°	142.7	1.6
0°-30°	1577.3	17.2
0°-40°	2607.7	28.4
0°-60°	4233.5	46.1
0°-90°	4971.6	54.2
90°-120°	904.4	9.9
90°-150°	3044.3	33.2
90°-180°	4208.0	45.8
0°-180°	9179.4	100.0

CANDELA DISTRIBUTION:

	0°	90°	180°	270°	360°	Flux
0°	1918	1918	1918	1918	1918	
5°	2198	1913	1689	1913	2198	220
15°	2640	1826	1285	1826	2640	757
25°	3161	1666	1033	1666	3161	1452
35°	2623	1449	842	1449	2623	1584
45°	1173	1141	663	1141	1173	936
55°	644	805	496	805	644	584
65°	365	502	294	502	365	363
75°	170	244	154	244	170	181
85°	36	54	41	54	36	42
90°	28	1	28	1	28	18
95°	101	76	101	76	101	103
105°	291	268	291	268	291	308
115°	510	506	510	506	510	505
125°	743	738	743	738	743	663
135°	963	960	963	960	963	743
145°	1168	1163	1168	1163	1168	729
155°	1331	1331	1331	1331	1331	612
165°	1443	1447	1443	1447	1443	407
175°	1498	1504	1498	1504	1498	142
180°	1508	1508	1508	1508	1508	



TEST NUMBER: P333635-840

CATALOG NUMBER: S125RDIP-S1270D1205U840-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	1917.6	1917.6	1917.6	1917.6	1917.6	1917.6	1917.6	1917.6	1917.6	1917.6	1917.6
2.5°	2017.1	2015.9	2018.4	2011.4	2012.1	2001.4	2001.4	1993.2	1982.5	1974.3	1970.5
5°	2197.9	2199.5	2196.3	2184.4	2176.7	2164.8	2151.4	2127.8	2108.1	2089.2	2074.3
7.5°	2384.0	2385.1	2374.7	2371.1	2351.2	2336.7	2306.9	2274.8	2246.3	2210.2	2182.4
10°	2492.2	2491.5	2480.4	2471.8	2454.5	2432.5	2403.4	2365.5	2330.2	2290.8	2253.0
12.5°	2555.3	2553.2	2549.7	2539.2	2523.1	2503.7	2478.9	2441.8	2398.1	2355.0	2310.9
15°	2640.3	2634.7	2624.5	2611.1	2588.3	2565.5	2537.9	2504.9	2463.2	2414.4	2373.4
17.5°	2745.4	2745.6	2729.9	2711.3	2680.3	2640.0	2597.5	2544.1	2487.4	2433.7	2390.1
20°	2832.4	2829.9	2814.3	2778.0	2742.6	2692.2	2643.4	2578.1	2508.8	2438.7	2384.4
22.5°	2957.1	2950.9	2934.6	2887.0	2832.1	2767.1	2692.5	2612.7	2529.0	2449.4	2378.1
25°	3161.4	3156.6	3124.4	3069.3	2992.1	2892.2	2794.6	2685.1	2564.8	2460.0	2373.4
27.5°	3301.2	3296.0	3272.1	3226.3	3155.1	3049.9	2917.8	2771.6	2621.2	2477.2	2352.3
30°	3287.3	3299.1	3296.0	3274.8	3221.3	3126.7	3004.8	2840.2	2661.5	2492.2	2343.5
32.5°	3089.6	3100.2	3127.9	3169.6	3172.7	3134.9	3043.8	2891.8	2706.8	2514.4	2336.5
35°	2622.9	2637.2	2690.7	2774.9	2885.1	2977.2	2996.1	2914.3	2748.1	2541.1	2326.2
37.5°	2016.5	2094.0	2139.0	2227.7	2394.2	2563.6	2726.5	2786.5	2715.8	2530.1	2309.4
40°	1712.9	1731.8	1812.1	1912.1	2052.2	2228.6	2460.8	2628.5	2633.9	2504.9	2282.9
42.5°	1466.1	1490.1	1545.1	1625.0	1744.9	1921.3	2161.0	2382.3	2484.8	2435.6	2248.3
45°	1173.0	1191.0	1231.2	1292.6	1384.7	1530.3	1736.6	1992.4	2195.5	2275.0	2155.4
47.5°	963.5	973.3	1008.2	1055.0	1123.2	1229.3	1389.0	1611.0	1854.6	2025.5	2008.6
50°	850.2	861.2	888.0	923.4	980.9	1070.6	1198.1	1383.1	1634.3	1842.8	1884.6
52.5°	762.0	771.1	787.8	821.3	868.8	937.8	1040.7	1208.0	1434.0	1655.8	1752.3
55°	643.9	650.3	663.6	682.5	720.3	769.9	858.8	974.5	1157.2	1380.8	1522.5
57.5°	546.6	549.8	558.3	575.7	601.9	638.1	702.4	800.4	931.4	1132.8	1289.1
60°	484.9	488.1	499.1	510.9	531.4	564.4	614.8	683.3	809.2	975.3	1133.6
62.5°	435.8	437.7	442.4	454.2	472.2	497.7	537.3	593.2	693.4	839.3	988.8
65°	365.3	366.1	367.6	377.1	388.1	407.0	432.9	472.3	547.9	658.1	790.3
67.5°	297.6	298.6	304.2	307.5	319.0	328.9	344.2	374.3	427.5	501.8	604.6
70°	259.7	259.0	264.5	268.4	272.4	284.2	294.4	318.8	351.8	408.6	494.3
72.5°	224.5	222.5	224.8	226.2	231.5	239.4	249.7	264.7	290.1	329.2	394.9
75°	170.1	170.9	170.9	172.4	176.3	179.5	182.6	190.5	204.7	230.7	266.1
77.5°	119.4	118.1	121.4	121.9	124.2	127.6	130.4	133.5	139.4	150.1	168.3
80°	86.5	86.5	87.4	89.8	89.0	90.5	94.4	97.7	104.7	111.0	117.2
82.5°	66.4	65.8	66.6	67.1	67.0	68.5	69.9	70.5	73.2	76.3	80.8
85°	36.3	36.3	37.0	37.0	37.8	37.8	38.6	38.6	38.6	39.4	40.2
87.5°	19.5	18.7	17.9	17.8	18.3	19.3	18.4	17.5	17.3	17.0	17.3
90°	28.2	27.4	26.6	25.9	25.0	24.0	22.7	21.4	20.1	18.8	17.0
92.5°	55.3	54.8	54.2	53.6	53.1	51.9	50.2	48.5	46.8	45.0	42.8
95°	100.9	100.4	99.9	99.4	98.9	97.7	95.8	94.0	92.2	90.4	87.8
97.5°	153.0	152.7	152.4	152.1	151.8	150.8	149.1	147.3	145.6	143.9	140.3
100°	192.5	192.0	191.4	190.9	190.4	188.9	186.6	184.2	181.9	179.6	176.1
102.5°	231.9	231.2	230.5	229.7	228.9	227.3	224.8	222.2	219.6	217.1	215.4
105°	291.0	290.2	289.4	288.7	287.9	286.7	285.2	283.6	282.1	280.4	278.9
107.5°	351.5	351.6	351.7	351.7	351.8	351.4	350.6	349.8	349.1	348.3	347.1
110°	396.7	396.9	397.2	397.4	397.7	397.4	396.7	395.9	395.1	394.3	393.5



TEST NUMBER: P333635-840

CATALOG NUMBER: S125RDIP-S1270D1205U840-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	440.8	441.2	441.7	442.2	442.6	442.7	442.3	442.0	441.6	441.2	440.2
115°	510.5	510.7	511.0	511.3	511.5	511.8	512.0	512.3	512.6	512.8	512.3
117.5°	578.6	579.6	580.7	581.7	582.7	583.1	582.9	582.7	582.5	582.3	581.8
120°	625.5	626.5	627.5	628.6	629.7	630.2	630.2	630.2	630.2	630.2	630.0
122.5°	672.5	673.3	674.1	674.9	675.8	676.3	676.5	676.7	676.9	677.1	676.4
125°	742.9	743.1	743.4	743.7	743.9	744.3	744.8	745.3	745.8	746.4	746.1
127.5°	810.4	810.9	811.4	812.0	812.5	812.9	813.1	813.4	813.6	814.0	813.6
130°	855.5	856.0	856.6	857.1	857.6	858.0	858.2	858.5	858.8	859.0	858.5
132.5°	897.8	898.5	899.2	899.9	900.7	901.1	901.4	901.7	901.9	902.2	902.3
135°	963.4	964.5	965.5	966.5	967.7	968.2	968.2	968.2	968.2	968.2	967.9
137.5°	1027.7	1029.1	1030.4	1031.7	1033.0	1033.5	1033.2	1032.9	1032.5	1032.2	1031.7
140°	1069.0	1070.4	1071.7	1073.0	1074.3	1074.7	1074.2	1073.6	1073.1	1072.6	1071.8
142.5°	1108.5	1109.8	1111.2	1112.4	1113.7	1114.2	1113.9	1113.6	1113.3	1113.0	1112.0
145°	1167.6	1168.4	1169.2	1170.0	1170.7	1171.1	1171.1	1171.1	1171.1	1171.1	1170.3
147.5°	1218.1	1219.9	1221.6	1223.5	1225.2	1225.8	1225.2	1224.6	1223.9	1223.2	1222.6
150°	1255.7	1256.2	1256.7	1257.2	1257.8	1258.0	1258.0	1258.0	1258.0	1258.0	1257.0
152.5°	1286.7	1287.6	1288.5	1289.5	1290.4	1290.5	1289.9	1289.3	1288.7	1288.1	1287.7
155°	1330.8	1332.1	1333.3	1334.6	1336.0	1336.2	1335.0	1334.0	1333.0	1331.9	1331.7
157.5°	1367.7	1369.4	1371.1	1372.8	1374.5	1374.8	1373.8	1372.7	1371.7	1370.7	1370.4
160°	1393.0	1394.2	1395.5	1396.8	1398.2	1398.3	1397.2	1396.2	1395.1	1394.1	1393.9
162.5°	1414.5	1416.0	1417.5	1419.1	1420.6	1420.8	1419.5	1418.3	1416.9	1415.7	1415.6
165°	1443.4	1445.0	1446.5	1448.1	1449.7	1450.0	1448.9	1447.8	1446.8	1445.7	1445.5
167.5°	1466.4	1468.0	1469.7	1471.3	1472.9	1472.9	1471.4	1469.8	1468.2	1466.6	1466.6
170°	1478.6	1480.5	1482.3	1484.1	1485.9	1486.0	1484.5	1482.9	1481.4	1479.8	1479.8
172.5°	1488.9	1490.6	1492.2	1493.8	1495.4	1495.4	1493.9	1492.3	1490.8	1489.1	1489.1
175°	1498.5	1500.4	1502.3	1504.1	1505.9	1506.0	1504.4	1502.9	1501.3	1499.8	1499.8
177.5°	1504.2	1505.7	1507.1	1508.6	1510.1	1510.2	1508.9	1507.6	1506.4	1505.1	1505.3
180°	1507.9	1507.9	1507.9	1507.9	1507.9	1507.9	1507.9	1507.9	1507.9	1507.9	1507.9



TEST NUMBER: P333635-840

CATALOG NUMBER: S125RDIP-S1270D1205U840-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°	95°	100°	105°
0°	1917.6	1917.6	1917.6	1917.6	1917.6	1917.6	1917.6	1917.6	1917.6	1917.6	1917.6
2.5°	1970.5	1966.1	1957.9	1950.4	1941.0	1932.8	1927.0	1920.2	1911.4	1900.7	1891.8
5°	2057.7	2040.4	2017.6	1997.9	1972.8	1953.1	1932.6	1912.9	1893.2	1868.0	1846.0
7.5°	2154.4	2118.7	2083.9	2040.1	2000.4	1965.0	1931.0	1896.5	1862.8	1827.0	1792.6
10°	2213.6	2170.3	2122.3	2067.2	2016.8	1968.8	1924.7	1881.4	1835.7	1795.6	1752.3
12.5°	2269.1	2213.1	2158.2	2088.6	2028.1	1969.4	1913.4	1859.4	1810.6	1758.5	1712.0
15°	2319.1	2264.0	2202.6	2117.6	2033.4	1962.5	1896.3	1826.3	1765.6	1707.5	1655.5
17.5°	2338.4	2280.7	2209.4	2127.7	2035.6	1946.4	1861.3	1784.4	1713.1	1645.3	1586.8
20°	2330.9	2275.0	2201.8	2123.8	2025.5	1932.6	1840.5	1755.4	1676.0	1604.3	1542.2
22.5°	2312.7	2254.8	2184.1	2101.8	2008.4	1910.0	1811.5	1720.8	1637.5	1563.4	1495.5
25°	2285.2	2206.6	2134.1	2053.8	1964.9	1867.2	1765.6	1665.7	1576.8	1501.2	1427.2
27.5°	2256.7	2158.5	2066.4	1986.6	1892.6	1805.5	1707.6	1605.1	1511.6	1434.6	1358.7
30°	2230.9	2120.7	2019.1	1928.6	1839.7	1757.1	1664.2	1564.2	1468.1	1388.7	1311.5
32.5°	2198.8	2081.6	1970.0	1865.6	1779.9	1697.9	1613.8	1518.2	1424.7	1342.6	1264.3
35°	2158.5	2008.9	1887.7	1776.8	1681.4	1601.9	1526.4	1449.3	1355.5	1270.5	1194.2
37.5°	2105.6	1935.9	1795.6	1674.7	1574.3	1494.4	1434.7	1364.2	1278.7	1197.3	1126.5
40°	2073.5	1883.0	1729.5	1609.8	1504.3	1420.1	1364.2	1304.4	1226.5	1150.1	1079.2
42.5°	2030.6	1834.5	1662.7	1538.0	1431.9	1350.8	1294.3	1242.0	1176.7	1104.8	1028.9
45°	1946.7	1740.5	1560.2	1426.4	1319.4	1239.8	1187.1	1140.6	1091.1	1024.9	958.8
47.5°	1837.4	1642.4	1453.8	1307.7	1202.9	1129.0	1077.8	1041.2	1005.7	949.5	885.2
50°	1750.0	1561.9	1377.6	1235.9	1124.1	1054.1	1006.0	976.9	944.6	893.4	839.9
52.5°	1646.7	1478.6	1298.3	1153.4	1047.9	982.3	936.1	907.1	880.4	838.7	787.7
55°	1483.9	1336.7	1171.3	1039.9	943.1	877.0	832.8	805.3	789.6	754.2	714.0
57.5°	1296.1	1190.5	1044.8	918.1	832.4	767.1	734.8	711.3	693.6	668.5	640.2
60°	1165.1	1091.1	960.4	839.9	761.2	699.0	669.9	650.3	633.7	612.5	590.4
62.5°	1032.2	978.4	864.6	761.2	688.8	636.7	609.5	591.7	572.6	558.3	536.8
65°	854.1	806.1	727.4	646.3	579.4	537.7	518.0	502.2	490.4	474.6	459.7
67.5°	664.4	644.9	590.6	534.6	486.7	449.5	432.5	421.5	407.3	397.9	387.6
70°	547.9	538.5	499.9	462.9	418.0	392.8	377.1	372.3	355.1	345.6	338.5
72.5°	444.6	440.2	418.0	392.3	360.7	338.6	324.2	318.8	307.8	300.2	295.7
75°	304.7	306.2	302.3	285.8	274.0	259.7	247.2	244.0	236.2	229.8	225.9
77.5°	192.7	200.8	201.1	200.3	195.5	186.9	181.7	179.4	171.6	169.3	168.3
80°	132.3	140.9	148.8	147.9	146.4	144.1	140.2	137.7	133.8	131.5	129.9
82.5°	88.2	96.2	102.8	107.0	106.7	104.4	101.7	100.6	99.8	98.1	97.8
85°	41.7	43.3	45.6	51.2	55.1	55.8	55.1	54.3	51.9	52.7	53.5
87.5°	17.5	17.2	17.4	17.1	16.0	18.7	20.2	20.4	19.6	18.7	17.9
90°	15.1	13.3	11.5	9.5	7.5	5.4	3.2	1.2	3.2	5.4	7.5
92.5°	40.6	38.4	36.1	34.2	32.8	31.3	29.9	28.4	29.9	31.3	32.8
95°	85.1	82.5	79.9	78.4	77.9	77.4	76.7	76.2	76.7	77.4	77.9
97.5°	136.6	133.1	129.5	127.5	127.3	127.1	126.9	126.7	126.9	127.1	127.3
100°	172.8	169.4	166.0	164.3	164.3	164.3	164.3	164.3	164.3	164.3	164.3
102.5°	213.7	212.0	210.3	208.8	207.8	206.7	205.7	204.7	205.7	206.7	207.8
105°	277.3	275.8	274.2	272.8	271.5	270.1	268.8	267.5	268.8	270.1	271.5
107.5°	345.9	344.7	343.5	342.2	340.9	339.6	338.3	337.0	338.3	339.6	340.9
110°	392.7	391.9	391.1	390.1	388.8	387.5	386.2	385.0	386.2	387.5	388.8



TEST NUMBER: P333635-840

CATALOG NUMBER: S125RDIP-S1270D1205U840-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°	95°	100°	105°
112.5°	439.3	438.3	437.3	436.5	435.8	435.0	434.4	433.7	434.4	435.0	435.8
115°	511.8	511.3	510.7	510.0	508.9	507.9	506.9	505.7	506.9	507.9	508.9
117.5°	581.4	580.9	580.4	580.0	579.5	579.1	578.6	578.0	578.6	579.1	579.5
120°	629.7	629.3	629.1	628.3	627.0	625.7	624.4	623.1	624.4	625.7	627.0
122.5°	675.8	675.1	674.4	673.8	673.4	672.9	672.5	672.0	672.5	672.9	673.4
125°	745.8	745.6	745.3	744.4	742.9	741.2	739.7	738.1	739.7	741.2	742.9
127.5°	813.3	813.0	812.7	812.1	811.2	810.3	809.4	808.6	809.4	810.3	811.2
130°	858.0	857.5	857.0	856.0	854.7	853.4	852.1	850.8	852.1	853.4	854.7
132.5°	902.4	902.5	902.6	901.6	899.5	897.4	895.1	893.0	895.1	897.4	899.5
135°	967.7	967.3	967.1	966.2	964.6	963.1	961.5	960.0	961.5	963.1	964.6
137.5°	1031.1	1030.5	1030.0	1028.9	1027.3	1025.8	1024.3	1022.8	1024.3	1025.8	1027.3
140°	1071.1	1070.3	1069.4	1068.4	1067.1	1065.8	1064.5	1063.2	1064.5	1065.8	1067.1
142.5°	1111.0	1109.9	1109.0	1107.9	1106.8	1105.8	1104.7	1103.6	1104.7	1105.8	1106.8
145°	1169.6	1168.8	1168.0	1167.1	1166.1	1165.1	1164.0	1163.0	1164.0	1165.1	1166.1
147.5°	1222.0	1221.4	1220.7	1220.1	1219.6	1219.0	1218.4	1217.9	1218.4	1219.0	1219.6
150°	1255.9	1254.9	1253.8	1253.4	1253.7	1253.9	1254.3	1254.5	1254.3	1253.9	1253.7
152.5°	1287.2	1286.8	1286.4	1286.0	1285.7	1285.3	1284.9	1284.5	1284.9	1285.3	1285.7
155°	1331.4	1331.2	1330.9	1330.8	1330.8	1330.8	1330.8	1330.8	1330.8	1330.8	1330.8
157.5°	1370.2	1369.9	1369.6	1369.8	1370.4	1370.9	1371.5	1372.1	1371.5	1370.9	1370.4
160°	1393.6	1393.3	1393.1	1393.3	1394.1	1394.9	1395.7	1396.4	1395.7	1394.9	1394.1
162.5°	1415.6	1415.5	1415.5	1415.7	1416.3	1416.9	1417.5	1418.1	1417.5	1416.9	1416.3
165°	1445.2	1445.0	1444.7	1444.8	1445.4	1445.9	1446.4	1446.9	1446.4	1445.9	1445.4
167.5°	1466.6	1466.6	1466.6	1467.1	1468.2	1469.3	1470.3	1471.4	1470.3	1469.3	1468.2
170°	1479.8	1479.8	1479.8	1480.4	1481.4	1482.4	1483.5	1484.5	1483.5	1482.4	1481.4
172.5°	1489.1	1489.1	1489.1	1489.8	1490.8	1491.8	1492.9	1493.9	1492.9	1491.8	1490.8
175°	1499.8	1499.8	1499.8	1500.3	1501.3	1502.4	1503.4	1504.4	1503.4	1502.4	1501.3
177.5°	1505.6	1505.8	1506.0	1506.5	1507.3	1508.1	1509.0	1509.8	1509.0	1508.1	1507.3
180°	1507.9	1507.9	1507.9	1507.9	1507.9	1507.9	1507.9	1507.9	1507.9	1507.9	1507.9



TEST NUMBER: P333635-840

CATALOG NUMBER: S125RDIP-S1270D1205U840-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	110°	115°	120°	125°	130°	135°	140°	145°	150°	155°	160°
0°	1917.6	1917.6	1917.6	1917.6	1917.6	1917.6	1917.6	1917.6	1917.6	1917.6	1917.6
2.5°	1885.5	1876.7	1870.4	1857.7	1849.0	1845.2	1838.3	1836.3	1843.3	1838.3	1837.7
5°	1829.5	1806.6	1788.6	1770.4	1750.7	1738.2	1719.3	1716.1	1711.4	1704.2	1702.7
7.5°	1762.2	1732.5	1709.2	1679.3	1653.3	1632.3	1608.7	1597.5	1591.4	1582.3	1570.0
10°	1716.9	1681.4	1650.0	1620.0	1587.8	1561.9	1538.2	1520.0	1508.2	1497.2	1492.6
12.5°	1672.1	1636.1	1595.8	1559.6	1523.6	1494.4	1468.2	1456.5	1443.4	1430.5	1419.5
15°	1602.8	1554.7	1510.7	1468.9	1438.2	1406.7	1381.5	1364.2	1344.5	1339.1	1317.8
17.5°	1529.0	1482.0	1430.4	1386.4	1350.8	1316.2	1288.5	1268.8	1254.1	1233.8	1224.0
20°	1483.1	1427.2	1376.8	1336.7	1297.3	1256.4	1228.0	1211.5	1197.3	1180.8	1173.0
22.5°	1434.0	1379.4	1327.7	1280.6	1240.6	1200.3	1180.1	1163.1	1146.9	1131.7	1121.3
25°	1361.9	1306.8	1252.4	1203.7	1162.0	1132.8	1109.1	1089.4	1080.9	1065.9	1054.8
27.5°	1290.5	1231.9	1175.6	1126.9	1094.2	1065.4	1046.0	1030.5	1014.8	1001.8	992.2
30°	1244.6	1184.8	1123.4	1084.8	1050.2	1022.6	1001.3	986.3	974.5	962.7	955.6
32.5°	1198.6	1136.9	1082.4	1040.7	1007.9	984.1	962.3	948.0	935.5	922.4	914.1
35°	1124.9	1062.0	1017.8	976.9	944.6	922.6	907.7	887.2	877.0	867.5	858.8
37.5°	1056.4	997.8	950.2	914.2	886.3	864.3	845.0	833.9	821.3	812.8	805.7
40°	1006.0	952.5	909.2	871.4	851.0	826.6	808.5	794.3	784.9	773.9	766.0
42.5°	960.7	911.0	868.9	835.0	809.4	788.8	771.3	757.1	745.2	737.3	730.6
45°	896.7	847.1	806.1	774.6	751.0	731.3	713.2	706.1	690.3	681.0	677.8
47.5°	830.3	786.0	746.4	717.4	693.2	674.6	657.6	643.2	634.5	625.2	620.2
50°	785.7	743.2	706.1	677.8	654.2	633.7	617.9	608.5	596.7	588.0	581.8
52.5°	740.9	701.6	664.6	637.4	617.0	596.5	579.0	569.5	558.3	552.8	548.4
55°	677.0	635.3	603.8	577.0	555.7	536.8	520.4	510.9	503.8	498.3	496.8
57.5°	604.6	571.5	542.2	518.2	496.0	478.3	463.8	454.8	448.6	447.8	443.0
60°	557.3	527.5	500.7	474.6	455.8	439.3	426.7	416.5	410.1	409.3	407.8
62.5°	510.1	481.4	456.6	433.7	416.8	400.8	388.9	377.4	373.7	369.7	366.2
65°	440.0	414.0	393.6	375.5	357.4	344.0	332.2	325.1	316.5	311.7	303.1
67.5°	371.2	351.1	331.4	316.2	301.9	289.2	279.4	268.9	263.1	259.3	253.0
70°	325.9	310.1	290.4	274.0	263.0	252.7	244.8	233.0	229.0	225.9	222.8
72.5°	283.1	269.2	252.7	239.3	228.3	218.6	209.5	204.0	200.2	196.9	195.1
75°	222.8	209.4	195.2	185.8	177.9	170.1	165.3	161.4	159.8	159.1	155.8
77.5°	163.6	156.5	145.1	137.6	132.4	129.3	125.0	123.0	122.8	119.4	118.3
80°	125.1	121.2	111.8	108.7	104.7	101.6	99.2	95.2	91.3	89.8	87.4
82.5°	93.0	89.1	85.3	80.3	77.0	75.1	72.7	71.3	71.8	69.6	68.5
85°	49.6	45.6	44.1	43.3	41.7	43.3	42.5	41.7	40.9	40.2	40.9
87.5°	17.7	18.1	17.8	19.4	17.9	18.9	19.1	18.8	19.0	19.3	18.9
90°	9.5	11.5	13.3	15.1	17.0	18.8	20.1	21.4	22.7	24.0	25.0
92.5°	34.2	36.1	38.4	40.6	42.8	45.0	46.8	48.5	50.2	51.9	53.1
95°	78.4	79.9	82.5	85.1	87.8	90.4	92.2	94.0	95.8	97.7	98.9
97.5°	127.5	129.5	133.1	136.6	140.3	143.9	145.6	147.3	149.1	150.8	151.8
100°	164.3	166.0	169.4	172.8	176.1	179.6	181.9	184.2	186.6	188.9	190.4
102.5°	208.8	210.3	212.0	213.7	215.4	217.1	219.6	222.2	224.8	227.3	228.9
105°	272.8	274.2	275.8	277.3	278.9	280.4	282.1	283.6	285.2	286.7	287.9
107.5°	342.2	343.5	344.7	345.9	347.1	348.3	349.1	349.8	350.6	351.4	351.8
110°	390.1	391.1	391.9	392.7	393.5	394.3	395.1	395.9	396.7	397.4	397.7



TEST NUMBER: P333635-840

CATALOG NUMBER: S125RDIP-S1270D1205U840-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	110°	115°	120°	125°	130°	135°	140°	145°	150°	155°	160°
112.5°	436.5	437.3	438.3	439.3	440.2	441.2	441.6	442.0	442.3	442.7	442.6
115°	510.0	510.7	511.3	511.8	512.3	512.8	512.6	512.3	512.0	511.8	511.5
117.5°	580.0	580.4	580.9	581.4	581.8	582.3	582.5	582.7	582.9	583.1	582.7
120°	628.3	629.1	629.3	629.7	630.0	630.2	630.2	630.2	630.2	630.2	629.7
122.5°	673.8	674.4	675.1	675.8	676.4	677.1	676.9	676.7	676.5	676.3	675.8
125°	744.4	745.3	745.6	745.8	746.1	746.4	745.8	745.3	744.8	744.3	743.9
127.5°	812.1	812.7	813.0	813.3	813.6	814.0	813.6	813.4	813.1	812.9	812.5
130°	856.0	857.0	857.5	858.0	858.5	859.0	858.8	858.5	858.2	858.0	857.6
132.5°	901.6	902.6	902.5	902.4	902.3	902.2	901.9	901.7	901.4	901.1	900.7
135°	966.2	967.1	967.3	967.7	967.9	968.2	968.2	968.2	968.2	968.2	967.7
137.5°	1028.9	1030.0	1030.5	1031.1	1031.7	1032.2	1032.5	1032.9	1033.2	1033.5	1033.0
140°	1068.4	1069.4	1070.3	1071.1	1071.8	1072.6	1073.1	1073.6	1074.2	1074.7	1074.3
142.5°	1107.9	1109.0	1109.9	1111.0	1112.0	1113.0	1113.3	1113.6	1113.9	1114.2	1113.7
145°	1167.1	1168.0	1168.8	1169.6	1170.3	1171.1	1171.1	1171.1	1171.1	1171.1	1170.7
147.5°	1220.1	1220.7	1221.4	1222.0	1222.6	1223.2	1223.9	1224.6	1225.2	1225.8	1225.2
150°	1253.4	1253.8	1254.9	1255.9	1257.0	1258.0	1258.0	1258.0	1258.0	1258.0	1257.8
152.5°	1286.0	1286.4	1286.8	1287.2	1287.7	1288.1	1288.7	1289.3	1289.9	1290.5	1290.4
155°	1330.8	1330.9	1331.2	1331.4	1331.7	1331.9	1333.0	1334.0	1335.0	1336.2	1336.0
157.5°	1369.8	1369.6	1369.9	1370.2	1370.4	1370.7	1371.7	1372.7	1373.8	1374.8	1374.5
160°	1393.3	1393.1	1393.3	1393.6	1393.9	1394.1	1395.1	1396.2	1397.2	1398.3	1398.2
162.5°	1415.7	1415.5	1415.5	1415.6	1415.6	1415.7	1416.9	1418.3	1419.5	1420.8	1420.6
165°	1444.8	1444.7	1445.0	1445.2	1445.5	1445.7	1446.8	1447.8	1448.9	1450.0	1449.7
167.5°	1467.1	1466.6	1466.6	1466.6	1466.6	1466.6	1468.2	1469.8	1471.4	1472.9	1472.9
170°	1480.4	1479.8	1479.8	1479.8	1479.8	1479.8	1481.4	1482.9	1484.5	1486.0	1485.9
172.5°	1489.8	1489.1	1489.1	1489.1	1489.1	1489.1	1490.8	1492.3	1493.9	1495.4	1495.4
175°	1500.3	1499.8	1499.8	1499.8	1499.8	1499.8	1501.3	1502.9	1504.4	1506.0	1505.9
177.5°	1506.5	1506.0	1505.8	1505.6	1505.3	1505.1	1506.4	1507.6	1508.9	1510.2	1510.1
180°	1507.9	1507.9	1507.9	1507.9	1507.9	1507.9	1507.9	1507.9	1507.9	1507.9	1507.9



TEST NUMBER: P333635-840

CATALOG NUMBER: S125RDIP-S1270D1205U840-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	165°	170°	175°	180°	185°	190°	195°	200°	205°	210°	215°
0°	1917.6	1917.6	1917.6	1917.6	1917.6	1917.6	1917.6	1917.6	1917.6	1917.6	1917.6
2.5°	1837.0	1830.1	1828.2	1830.7	1828.2	1830.1	1837.0	1837.7	1838.3	1843.3	1836.3
5°	1694.9	1687.0	1690.9	1689.3	1690.9	1687.0	1694.9	1702.7	1704.2	1711.4	1716.1
7.5°	1569.8	1560.0	1549.6	1553.0	1549.6	1560.0	1569.8	1570.0	1582.3	1591.4	1597.5
10°	1482.3	1474.4	1469.7	1473.6	1469.7	1474.4	1482.3	1492.6	1497.2	1508.2	1520.0
12.5°	1408.7	1403.9	1399.8	1398.1	1399.8	1403.9	1408.7	1419.5	1430.5	1443.4	1456.5
15°	1308.3	1298.9	1294.9	1284.8	1294.9	1298.9	1308.3	1317.8	1339.1	1344.5	1364.2
17.5°	1215.9	1212.7	1202.5	1198.1	1202.5	1212.7	1215.9	1224.0	1233.8	1254.1	1268.8
20°	1161.1	1158.0	1147.7	1154.1	1147.7	1158.0	1161.1	1173.0	1180.8	1197.3	1211.5
22.5°	1115.8	1108.8	1105.5	1103.7	1105.5	1108.8	1115.8	1121.3	1131.7	1146.9	1163.1
25°	1051.7	1041.5	1037.5	1032.8	1037.5	1041.5	1051.7	1054.8	1065.9	1080.9	1089.4
27.5°	987.7	982.3	977.0	975.8	977.0	982.3	987.7	992.2	1001.8	1014.8	1030.5
30°	946.2	940.7	936.8	936.8	936.8	940.7	946.2	955.6	962.7	974.5	986.3
32.5°	909.1	904.8	900.9	900.3	900.9	904.8	909.1	914.1	922.4	935.5	948.0
35°	855.0	848.6	847.1	842.3	847.1	848.6	855.0	858.8	867.5	877.0	887.2
37.5°	798.7	793.5	793.3	792.8	793.3	793.5	798.7	805.7	812.8	821.3	833.9
40°	762.8	758.8	758.1	752.6	758.1	758.8	762.8	766.0	773.9	784.9	794.3
42.5°	724.4	722.4	719.6	717.3	719.6	722.4	724.4	730.6	737.3	745.2	757.1
45°	672.3	666.7	666.7	662.8	666.7	666.7	672.3	677.8	681.0	690.3	706.1
47.5°	618.4	614.2	614.6	610.6	614.6	614.2	618.4	620.2	625.2	634.5	643.2
50°	582.5	580.2	579.4	577.8	579.4	580.2	582.5	581.8	588.0	596.7	608.5
52.5°	546.6	545.5	548.6	545.0	548.6	545.5	546.6	548.4	552.8	558.3	569.5
55°	498.3	495.9	500.7	495.9	500.7	495.9	498.3	496.8	498.3	503.8	510.9
57.5°	442.7	440.5	444.7	442.4	444.7	440.5	442.7	443.0	447.8	448.6	454.8
60°	406.2	401.5	403.8	404.7	403.8	401.5	406.2	407.8	409.3	410.1	416.5
62.5°	362.7	359.9	361.6	358.0	361.6	359.9	362.7	366.2	369.7	373.7	377.4
65°	301.5	299.1	296.0	294.4	296.0	299.1	301.5	303.1	311.7	316.5	325.1
67.5°	253.3	247.6	247.5	248.7	247.5	247.6	253.3	253.0	259.3	263.1	268.9
70°	218.0	218.0	217.2	217.2	217.2	218.0	218.0	222.8	225.9	229.0	233.0
72.5°	193.5	192.9	191.5	190.9	191.5	192.9	193.5	195.1	196.9	200.2	204.0
75°	155.8	156.6	155.1	154.3	155.1	156.6	155.8	155.8	159.1	159.8	161.4
77.5°	115.1	111.8	113.5	111.8	113.5	111.8	115.1	118.3	119.4	122.8	123.0
80°	87.4	86.5	89.0	86.5	89.0	86.5	87.4	87.4	89.8	91.3	95.2
82.5°	69.1	68.4	69.5	67.7	69.5	68.4	69.1	68.5	69.6	71.8	71.3
85°	41.7	40.9	40.2	40.9	40.2	40.9	41.7	40.9	40.2	40.9	41.7
87.5°	19.7	19.2	19.3	19.5	19.3	19.2	19.7	18.9	19.3	19.0	18.8
90°	25.9	26.6	27.4	28.2	27.4	26.6	25.9	25.0	24.0	22.7	21.4
92.5°	53.6	54.2	54.8	55.3	54.8	54.2	53.6	53.1	51.9	50.2	48.5
95°	99.4	99.9	100.4	100.9	100.4	99.9	99.4	98.9	97.7	95.8	94.0
97.5°	152.1	152.4	152.7	153.0	152.7	152.4	152.1	151.8	150.8	149.1	147.3
100°	190.9	191.4	192.0	192.5	192.0	191.4	190.9	190.4	188.9	186.6	184.2
102.5°	229.7	230.5	231.2	231.9	231.2	230.5	229.7	228.9	227.3	224.8	222.2
105°	288.7	289.4	290.2	291.0	290.2	289.4	288.7	287.9	286.7	285.2	283.6
107.5°	351.7	351.7	351.6	351.5	351.6	351.7	351.7	351.8	351.4	350.6	349.8
110°	397.4	397.2	396.9	396.7	396.9	397.2	397.4	397.7	397.4	396.7	395.9



TEST NUMBER: P333635-840

CATALOG NUMBER: S125RDIP-S1270D1205U840-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	165°	170°	175°	180°	185°	190°	195°	200°	205°	210°	215°
112.5°	442.2	441.7	441.2	440.8	441.2	441.7	442.2	442.6	442.7	442.3	442.0
115°	511.3	511.0	510.7	510.5	510.7	511.0	511.3	511.5	511.8	512.0	512.3
117.5°	581.7	580.7	579.6	578.6	579.6	580.7	581.7	582.7	583.1	582.9	582.7
120°	628.6	627.5	626.5	625.5	626.5	627.5	628.6	629.7	630.2	630.2	630.2
122.5°	674.9	674.1	673.3	672.5	673.3	674.1	674.9	675.8	676.3	676.5	676.7
125°	743.7	743.4	743.1	742.9	743.1	743.4	743.7	743.9	744.3	744.8	745.3
127.5°	812.0	811.4	810.9	810.4	810.9	811.4	812.0	812.5	812.9	813.1	813.4
130°	857.1	856.6	856.0	855.5	856.0	856.6	857.1	857.6	858.0	858.2	858.5
132.5°	899.9	899.2	898.5	897.8	898.5	899.2	899.9	900.7	901.1	901.4	901.7
135°	966.5	965.5	964.5	963.4	964.5	965.5	966.5	967.7	968.2	968.2	968.2
137.5°	1031.7	1030.4	1029.1	1027.7	1029.1	1030.4	1031.7	1033.0	1033.5	1033.2	1032.9
140°	1073.0	1071.7	1070.4	1069.0	1070.4	1071.7	1073.0	1074.3	1074.7	1074.2	1073.6
142.5°	1112.4	1111.2	1109.8	1108.5	1109.8	1111.2	1112.4	1113.7	1114.2	1113.9	1113.6
145°	1170.0	1169.2	1168.4	1167.6	1168.4	1169.2	1170.0	1170.7	1171.1	1171.1	1171.1
147.5°	1223.5	1221.6	1219.9	1218.1	1219.9	1221.6	1223.5	1225.2	1225.8	1225.2	1224.6
150°	1257.2	1256.7	1256.2	1255.7	1256.2	1256.7	1257.2	1257.8	1258.0	1258.0	1258.0
152.5°	1289.5	1288.5	1287.6	1286.7	1287.6	1288.5	1289.5	1290.4	1290.5	1289.9	1289.3
155°	1334.6	1333.3	1332.1	1330.8	1332.1	1333.3	1334.6	1336.0	1336.2	1335.0	1334.0
157.5°	1372.8	1371.1	1369.4	1367.7	1369.4	1371.1	1372.8	1374.5	1374.8	1373.8	1372.7
160°	1396.8	1395.5	1394.2	1393.0	1394.2	1395.5	1396.8	1398.2	1398.3	1397.2	1396.2
162.5°	1419.1	1417.5	1416.0	1414.5	1416.0	1417.5	1419.1	1420.6	1420.8	1419.5	1418.3
165°	1448.1	1446.5	1445.0	1443.4	1445.0	1446.5	1448.1	1449.7	1450.0	1448.9	1447.8
167.5°	1471.3	1469.7	1468.0	1466.4	1468.0	1469.7	1471.3	1472.9	1472.9	1471.4	1469.8
170°	1484.1	1482.3	1480.5	1478.6	1480.5	1482.3	1484.1	1485.9	1486.0	1484.5	1482.9
172.5°	1493.8	1492.2	1490.6	1488.9	1490.6	1492.2	1493.8	1495.4	1495.4	1493.9	1492.3
175°	1504.1	1502.3	1500.4	1498.5	1500.4	1502.3	1504.1	1505.9	1506.0	1504.4	1502.9
177.5°	1508.6	1507.1	1505.7	1504.2	1505.7	1507.1	1508.6	1510.1	1510.2	1508.9	1507.6
180°	1507.9	1507.9	1507.9	1507.9	1507.9	1507.9	1507.9	1507.9	1507.9	1507.9	1507.9



TEST NUMBER: P333635-840

CATALOG NUMBER: S125RDIP-S1270D1205U840-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	220°	225°	230°	235°	240°	245°	250°	255°	260°	265°	270°
0°	1917.6	1917.6	1917.6	1917.6	1917.6	1917.6	1917.6	1917.6	1917.6	1917.6	1917.6
2.5°	1838.3	1845.2	1849.0	1857.7	1870.4	1876.7	1885.5	1891.8	1900.7	1911.4	1920.2
5°	1719.3	1738.2	1750.7	1770.4	1788.6	1806.6	1829.5	1846.0	1868.0	1893.2	1912.9
7.5°	1608.7	1632.3	1653.3	1679.3	1709.2	1732.5	1762.2	1792.6	1827.0	1862.8	1896.5
10°	1538.2	1561.9	1587.8	1620.0	1650.0	1681.4	1716.9	1752.3	1795.6	1835.7	1881.4
12.5°	1468.2	1494.4	1523.6	1559.6	1595.8	1636.1	1672.1	1712.0	1758.5	1810.6	1859.4
15°	1381.5	1406.7	1438.2	1468.9	1510.7	1554.7	1602.8	1655.5	1707.5	1765.6	1826.3
17.5°	1288.5	1316.2	1350.8	1386.4	1430.4	1482.0	1529.0	1586.8	1645.3	1713.1	1784.4
20°	1228.0	1256.4	1297.3	1336.7	1376.8	1427.2	1483.1	1542.2	1604.3	1676.0	1755.4
22.5°	1180.1	1200.3	1240.6	1280.6	1327.7	1379.4	1434.0	1495.5	1563.4	1637.5	1720.8
25°	1109.1	1132.8	1162.0	1203.7	1252.4	1306.8	1361.9	1427.2	1501.2	1576.8	1665.7
27.5°	1046.0	1065.4	1094.2	1126.9	1175.6	1231.9	1290.5	1358.7	1434.6	1511.6	1605.1
30°	1001.3	1022.6	1050.2	1084.8	1123.4	1184.8	1244.6	1311.5	1388.7	1468.1	1564.2
32.5°	962.3	984.1	1007.9	1040.7	1082.4	1136.9	1198.6	1264.3	1342.6	1424.7	1518.2
35°	907.7	922.6	944.6	976.9	1017.8	1062.0	1124.9	1194.2	1270.5	1355.5	1449.3
37.5°	845.0	864.3	886.3	914.2	950.2	997.8	1056.4	1126.5	1197.3	1278.7	1364.2
40°	808.5	826.6	851.0	871.4	909.2	952.5	1006.0	1079.2	1150.1	1226.5	1304.4
42.5°	771.3	788.8	809.4	835.0	868.9	911.0	960.7	1028.9	1104.8	1176.7	1242.0
45°	713.2	731.3	751.0	774.6	806.1	847.1	896.7	958.8	1024.9	1091.1	1140.6
47.5°	657.6	674.6	693.2	717.4	746.4	786.0	830.3	885.2	949.5	1005.7	1041.2
50°	617.9	633.7	654.2	677.8	706.1	743.2	785.7	839.9	893.4	944.6	976.9
52.5°	579.0	596.5	617.0	637.4	664.6	701.6	740.9	787.7	838.7	880.4	907.1
55°	520.4	536.8	555.7	577.0	603.8	635.3	677.0	714.0	754.2	789.6	805.3
57.5°	463.8	478.3	496.0	518.2	542.2	571.5	604.6	640.2	668.5	693.6	711.3
60°	426.7	439.3	455.8	474.6	500.7	527.5	557.3	590.4	612.5	633.7	650.3
62.5°	388.9	400.8	416.8	433.7	456.6	481.4	510.1	536.8	558.3	572.6	591.7
65°	332.2	344.0	357.4	375.5	393.6	414.0	440.0	459.7	474.6	490.4	502.2
67.5°	279.4	289.2	301.9	316.2	331.4	351.1	371.2	387.6	397.9	407.3	421.5
70°	244.8	252.7	263.0	274.0	290.4	310.1	325.9	338.5	345.6	355.1	372.3
72.5°	209.5	218.6	228.3	239.3	252.7	269.2	283.1	295.7	300.2	307.8	318.8
75°	165.3	170.1	177.9	185.8	195.2	209.4	222.8	225.9	229.8	236.2	244.0
77.5°	125.0	129.3	132.4	137.6	145.1	156.5	163.6	168.3	169.3	171.6	179.4
80°	99.2	101.6	104.7	108.7	111.8	121.2	125.1	129.9	131.5	133.8	137.7
82.5°	72.7	75.1	77.0	80.3	85.3	89.1	93.0	97.8	98.1	99.8	100.6
85°	42.5	43.3	41.7	43.3	44.1	45.6	49.6	53.5	52.7	51.9	54.3
87.5°	19.1	18.9	17.9	19.4	17.8	18.1	17.7	17.9	18.7	19.6	20.4
90°	20.1	18.8	17.0	15.1	13.3	11.5	9.5	7.5	5.4	3.2	1.2
92.5°	46.8	45.0	42.8	40.6	38.4	36.1	34.2	32.8	31.3	29.9	28.4
95°	92.2	90.4	87.8	85.1	82.5	79.9	78.4	77.9	77.4	76.7	76.2
97.5°	145.6	143.9	140.3	136.6	133.1	129.5	127.5	127.3	127.1	126.9	126.7
100°	181.9	179.6	176.1	172.8	169.4	166.0	164.3	164.3	164.3	164.3	164.3
102.5°	219.6	217.1	215.4	213.7	212.0	210.3	208.8	207.8	206.7	205.7	204.7
105°	282.1	280.4	278.9	277.3	275.8	274.2	272.8	271.5	270.1	268.8	267.5
107.5°	349.1	348.3	347.1	345.9	344.7	343.5	342.2	340.9	339.6	338.3	337.0
110°	395.1	394.3	393.5	392.7	391.9	391.1	390.1	388.8	387.5	386.2	385.0



TEST NUMBER: P333635-840

CATALOG NUMBER: S125RDIP-S1270D1205U840-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	220°	225°	230°	235°	240°	245°	250°	255°	260°	265°	270°
112.5°	441.6	441.2	440.2	439.3	438.3	437.3	436.5	435.8	435.0	434.4	433.7
115°	512.6	512.8	512.3	511.8	511.3	510.7	510.0	508.9	507.9	506.9	505.7
117.5°	582.5	582.3	581.8	581.4	580.9	580.4	580.0	579.5	579.1	578.6	578.0
120°	630.2	630.2	630.0	629.7	629.3	629.1	628.3	627.0	625.7	624.4	623.1
122.5°	676.9	677.1	676.4	675.8	675.1	674.4	673.8	673.4	672.9	672.5	672.0
125°	745.8	746.4	746.1	745.8	745.6	745.3	744.4	742.9	741.2	739.7	738.1
127.5°	813.6	814.0	813.6	813.3	813.0	812.7	812.1	811.2	810.3	809.4	808.6
130°	858.8	859.0	858.5	858.0	857.5	857.0	856.0	854.7	853.4	852.1	850.8
132.5°	901.9	902.2	902.3	902.4	902.5	902.6	901.6	899.5	897.4	895.1	893.0
135°	968.2	968.2	967.9	967.7	967.3	967.1	966.2	964.6	963.1	961.5	960.0
137.5°	1032.5	1032.2	1031.7	1031.1	1030.5	1030.0	1028.9	1027.3	1025.8	1024.3	1022.8
140°	1073.1	1072.6	1071.8	1071.1	1070.3	1069.4	1068.4	1067.1	1065.8	1064.5	1063.2
142.5°	1113.3	1113.0	1112.0	1111.0	1109.9	1109.0	1107.9	1106.8	1105.8	1104.7	1103.6
145°	1171.1	1171.1	1170.3	1169.6	1168.8	1168.0	1167.1	1166.1	1165.1	1164.0	1163.0
147.5°	1223.9	1223.2	1222.6	1222.0	1221.4	1220.7	1220.1	1219.6	1219.0	1218.4	1217.9
150°	1258.0	1258.0	1257.0	1255.9	1254.9	1253.8	1253.4	1253.7	1253.9	1254.3	1254.5
152.5°	1288.7	1288.1	1287.7	1287.2	1286.8	1286.4	1286.0	1285.7	1285.3	1284.9	1284.5
155°	1333.0	1331.9	1331.7	1331.4	1331.2	1330.9	1330.8	1330.8	1330.8	1330.8	1330.8
157.5°	1371.7	1370.7	1370.4	1370.2	1369.9	1369.6	1369.8	1370.4	1370.9	1371.5	1372.1
160°	1395.1	1394.1	1393.9	1393.6	1393.3	1393.1	1393.3	1394.1	1394.9	1395.7	1396.4
162.5°	1416.9	1415.7	1415.6	1415.6	1415.5	1415.5	1415.7	1416.3	1416.9	1417.5	1418.1
165°	1446.8	1445.7	1445.5	1445.2	1445.0	1444.7	1444.8	1445.4	1445.9	1446.4	1446.9
167.5°	1468.2	1466.6	1466.6	1466.6	1466.6	1466.6	1467.1	1468.2	1469.3	1470.3	1471.4
170°	1481.4	1479.8	1479.8	1479.8	1479.8	1479.8	1480.4	1481.4	1482.4	1483.5	1484.5
172.5°	1490.8	1489.1	1489.1	1489.1	1489.1	1489.1	1489.8	1490.8	1491.8	1492.9	1493.9
175°	1501.3	1499.8	1499.8	1499.8	1499.8	1499.8	1500.3	1501.3	1502.4	1503.4	1504.4
177.5°	1506.4	1505.1	1505.3	1505.6	1505.8	1506.0	1506.5	1507.3	1508.1	1509.0	1509.8
180°	1507.9	1507.9	1507.9	1507.9	1507.9	1507.9	1507.9	1507.9	1507.9	1507.9	1507.9



TEST NUMBER: P333635-840

CATALOG NUMBER: S125RDIP-S1270D1205U840-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	275°	280°	285°	290°	295°	300°	305°	310°	315°	320°	325°
0°	1917.6	1917.6	1917.6	1917.6	1917.6	1917.6	1917.6	1917.6	1917.6	1917.6	1917.6
2.5°	1927.0	1932.8	1941.0	1950.4	1957.9	1966.1	1970.5	1970.5	1974.3	1982.5	1993.2
5°	1932.6	1953.1	1972.8	1997.9	2017.6	2040.4	2057.7	2074.3	2089.2	2108.1	2127.8
7.5°	1931.0	1965.0	2000.4	2040.1	2083.9	2118.7	2154.4	2182.4	2210.2	2246.3	2274.8
10°	1924.7	1968.8	2016.8	2067.2	2122.3	2170.3	2213.6	2253.0	2290.8	2330.2	2365.5
12.5°	1913.4	1969.4	2028.1	2088.6	2158.2	2213.1	2269.1	2310.9	2355.0	2398.1	2441.8
15°	1896.3	1962.5	2033.4	2117.6	2202.6	2264.0	2319.1	2373.4	2414.4	2463.2	2504.9
17.5°	1861.3	1946.4	2035.6	2127.7	2209.4	2280.7	2338.4	2390.1	2433.7	2487.4	2544.1
20°	1840.5	1932.6	2025.5	2123.8	2201.8	2275.0	2330.9	2384.4	2438.7	2508.8	2578.1
22.5°	1811.5	1910.0	2008.4	2101.8	2184.1	2254.8	2312.7	2378.1	2449.4	2529.0	2612.7
25°	1765.6	1867.2	1964.9	2053.8	2134.1	2206.6	2285.2	2373.4	2460.0	2564.8	2685.1
27.5°	1707.6	1805.5	1892.6	1986.6	2066.4	2158.5	2256.7	2352.3	2477.2	2621.2	2771.6
30°	1664.2	1757.1	1839.7	1928.6	2019.1	2120.7	2230.9	2343.5	2492.2	2661.5	2840.2
32.5°	1613.8	1697.9	1779.9	1865.6	1970.0	2081.6	2198.8	2336.5	2514.4	2706.8	2891.8
35°	1526.4	1601.9	1681.4	1776.8	1887.7	2008.9	2158.5	2326.2	2541.1	2748.1	2914.3
37.5°	1434.7	1494.4	1574.3	1674.7	1795.6	1935.9	2105.6	2309.4	2530.1	2715.8	2786.5
40°	1364.2	1420.1	1504.3	1609.8	1729.5	1883.0	2073.5	2282.9	2504.9	2633.9	2628.5
42.5°	1294.3	1350.8	1431.9	1538.0	1662.7	1834.5	2030.6	2248.3	2435.6	2484.8	2382.3
45°	1187.1	1239.8	1319.4	1426.4	1560.2	1740.5	1946.7	2155.4	2275.0	2195.5	1992.4
47.5°	1077.8	1129.0	1202.9	1307.7	1453.8	1642.4	1837.4	2008.6	2025.5	1854.6	1611.0
50°	1006.0	1054.1	1124.1	1235.9	1377.6	1561.9	1750.0	1884.6	1842.8	1634.3	1383.1
52.5°	936.1	982.3	1047.9	1153.4	1298.3	1478.6	1646.7	1752.3	1655.8	1434.0	1208.0
55°	832.8	877.0	943.1	1039.9	1171.3	1336.7	1483.9	1522.5	1380.8	1157.2	974.5
57.5°	734.8	767.1	832.4	918.1	1044.8	1190.5	1296.1	1289.1	1132.8	931.4	800.4
60°	669.9	699.0	761.2	839.9	960.4	1091.1	1165.1	1133.6	975.3	809.2	683.3
62.5°	609.5	636.7	688.8	761.2	864.6	978.4	1032.2	988.8	839.3	693.4	593.2
65°	518.0	537.7	579.4	646.3	727.4	806.1	854.1	790.3	658.1	547.9	472.3
67.5°	432.5	449.5	486.7	534.6	590.6	644.9	664.4	604.6	501.8	427.5	374.3
70°	377.1	392.8	418.0	462.9	499.9	538.5	547.9	494.3	408.6	351.8	318.8
72.5°	324.2	338.6	360.7	392.3	418.0	440.2	444.6	394.9	329.2	290.1	264.7
75°	247.2	259.7	274.0	285.8	302.3	306.2	304.7	266.1	230.7	204.7	190.5
77.5°	181.7	186.9	195.5	200.3	201.1	200.8	192.7	168.3	150.1	139.4	133.5
80°	140.2	144.1	146.4	147.9	148.8	140.9	132.3	117.2	111.0	104.7	97.7
82.5°	101.7	104.4	106.7	107.0	102.8	96.2	88.2	80.8	76.3	73.2	70.5
85°	55.1	55.8	55.1	51.2	45.6	43.3	41.7	40.2	39.4	38.6	38.6
87.5°	20.2	18.7	16.0	17.1	17.4	17.2	17.5	17.3	17.0	17.3	17.5
90°	3.2	5.4	7.5	9.5	11.5	13.3	15.1	17.0	18.8	20.1	21.4
92.5°	29.9	31.3	32.8	34.2	36.1	38.4	40.6	42.8	45.0	46.8	48.5
95°	76.7	77.4	77.9	78.4	79.9	82.5	85.1	87.8	90.4	92.2	94.0
97.5°	126.9	127.1	127.3	127.5	129.5	133.1	136.6	140.3	143.9	145.6	147.3
100°	164.3	164.3	164.3	164.3	166.0	169.4	172.8	176.1	179.6	181.9	184.2
102.5°	205.7	206.7	207.8	208.8	210.3	212.0	213.7	215.4	217.1	219.6	222.2
105°	268.8	270.1	271.5	272.8	274.2	275.8	277.3	278.9	280.4	282.1	283.6
107.5°	338.3	339.6	340.9	342.2	343.5	344.7	345.9	347.1	348.3	349.1	349.8
110°	386.2	387.5	388.8	390.1	391.1	391.9	392.7	393.5	394.3	395.1	395.9



TEST NUMBER: P333635-840

CATALOG NUMBER: S125RDIP-S1270D1205U840-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	275°	280°	285°	290°	295°	300°	305°	310°	315°	320°	325°
112.5°	434.4	435.0	435.8	436.5	437.3	438.3	439.3	440.2	441.2	441.6	442.0
115°	506.9	507.9	508.9	510.0	510.7	511.3	511.8	512.3	512.8	512.6	512.3
117.5°	578.6	579.1	579.5	580.0	580.4	580.9	581.4	581.8	582.3	582.5	582.7
120°	624.4	625.7	627.0	628.3	629.1	629.3	629.7	630.0	630.2	630.2	630.2
122.5°	672.5	672.9	673.4	673.8	674.4	675.1	675.8	676.4	677.1	676.9	676.7
125°	739.7	741.2	742.9	744.4	745.3	745.6	745.8	746.1	746.4	745.8	745.3
127.5°	809.4	810.3	811.2	812.1	812.7	813.0	813.3	813.6	814.0	813.6	813.4
130°	852.1	853.4	854.7	856.0	857.0	857.5	858.0	858.5	859.0	858.8	858.5
132.5°	895.1	897.4	899.5	901.6	902.6	902.5	902.4	902.3	902.2	901.9	901.7
135°	961.5	963.1	964.6	966.2	967.1	967.3	967.7	967.9	968.2	968.2	968.2
137.5°	1024.3	1025.8	1027.3	1028.9	1030.0	1030.5	1031.1	1031.7	1032.2	1032.5	1032.9
140°	1064.5	1065.8	1067.1	1068.4	1069.4	1070.3	1071.1	1071.8	1072.6	1073.1	1073.6
142.5°	1104.7	1105.8	1106.8	1107.9	1109.0	1109.9	1111.0	1112.0	1113.0	1113.3	1113.6
145°	1164.0	1165.1	1166.1	1167.1	1168.0	1168.8	1169.6	1170.3	1171.1	1171.1	1171.1
147.5°	1218.4	1219.0	1219.6	1220.1	1220.7	1221.4	1222.0	1222.6	1223.2	1223.9	1224.6
150°	1254.3	1253.9	1253.7	1253.4	1253.8	1254.9	1255.9	1257.0	1258.0	1258.0	1258.0
152.5°	1284.9	1285.3	1285.7	1286.0	1286.4	1286.8	1287.2	1287.7	1288.1	1288.7	1289.3
155°	1330.8	1330.8	1330.8	1330.8	1330.9	1331.2	1331.4	1331.7	1331.9	1333.0	1334.0
157.5°	1371.5	1370.9	1370.4	1369.8	1369.6	1369.9	1370.2	1370.4	1370.7	1371.7	1372.7
160°	1395.7	1394.9	1394.1	1393.3	1393.1	1393.3	1393.6	1393.9	1394.1	1395.1	1396.2
162.5°	1417.5	1416.9	1416.3	1415.7	1415.5	1415.5	1415.6	1415.6	1415.7	1416.9	1418.3
165°	1446.4	1445.9	1445.4	1444.8	1444.7	1445.0	1445.2	1445.5	1445.7	1446.8	1447.8
167.5°	1470.3	1469.3	1468.2	1467.1	1466.6	1466.6	1466.6	1466.6	1466.6	1468.2	1469.8
170°	1483.5	1482.4	1481.4	1480.4	1479.8	1479.8	1479.8	1479.8	1479.8	1481.4	1482.9
172.5°	1492.9	1491.8	1490.8	1489.8	1489.1	1489.1	1489.1	1489.1	1489.1	1490.8	1492.3
175°	1503.4	1502.4	1501.3	1500.3	1499.8	1499.8	1499.8	1499.8	1499.8	1501.3	1502.9
177.5°	1509.0	1508.1	1507.3	1506.5	1506.0	1505.8	1505.6	1505.3	1505.1	1506.4	1507.6
180°	1507.9	1507.9	1507.9	1507.9	1507.9	1507.9	1507.9	1507.9	1507.9	1507.9	1507.9



TEST NUMBER: P333635-840

CATALOG NUMBER: S125RDIP-S1270D1205U840-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	330°	335°	340°	345°	350°	355°	360°
0°	1917.6	1917.6	1917.6	1917.6	1917.6	1917.6	1917.6
2.5°	2001.4	2001.4	2012.1	2011.4	2018.4	2015.9	2017.1
5°	2151.4	2164.8	2176.7	2184.4	2196.3	2199.5	2197.9
7.5°	2306.9	2336.7	2351.2	2371.1	2374.7	2385.1	2384.0
10°	2403.4	2432.5	2454.5	2471.8	2480.4	2491.5	2492.2
12.5°	2478.9	2503.7	2523.1	2539.2	2549.7	2553.2	2555.3
15°	2537.9	2565.5	2588.3	2611.1	2624.5	2634.7	2640.3
17.5°	2597.5	2640.0	2680.3	2711.3	2729.9	2745.6	2745.4
20°	2643.4	2692.2	2742.6	2778.0	2814.3	2829.9	2832.4
22.5°	2692.5	2767.1	2832.1	2887.0	2934.6	2950.9	2957.1
25°	2794.6	2892.2	2992.1	3069.3	3124.4	3156.6	3161.4
27.5°	2917.8	3049.9	3155.1	3226.3	3272.1	3296.0	3301.2
30°	3004.8	3126.7	3221.3	3274.8	3296.0	3299.1	3287.3
32.5°	3043.8	3134.9	3172.7	3169.6	3127.9	3100.2	3089.6
35°	2996.1	2977.2	2885.1	2774.9	2690.7	2637.2	2622.9
37.5°	2726.5	2563.6	2394.2	2227.7	2139.0	2094.0	2016.5
40°	2460.8	2228.6	2052.2	1912.1	1812.1	1731.8	1712.9
42.5°	2161.0	1921.3	1744.9	1625.0	1545.1	1490.1	1466.1
45°	1736.6	1530.3	1384.7	1292.6	1231.2	1191.0	1173.0
47.5°	1389.0	1229.3	1123.2	1055.0	1008.2	973.3	963.5
50°	1198.1	1070.6	980.9	923.4	888.0	861.2	850.2
52.5°	1040.7	937.8	868.8	821.3	787.8	771.1	762.0
55°	858.8	769.9	720.3	682.5	663.6	650.3	643.9
57.5°	702.4	638.1	601.9	575.7	558.3	549.8	546.6
60°	614.8	564.4	531.4	510.9	499.1	488.1	484.9
62.5°	537.3	497.7	472.2	454.2	442.4	437.7	435.8
65°	432.9	407.0	388.1	377.1	367.6	366.1	365.3
67.5°	344.2	328.9	319.0	307.5	304.2	298.6	297.6
70°	294.4	284.2	272.4	268.4	264.5	259.0	259.7
72.5°	249.7	239.4	231.5	226.2	224.8	222.5	224.5
75°	182.6	179.5	176.3	172.4	170.9	170.9	170.1
77.5°	130.4	127.6	124.2	121.9	121.4	118.1	119.4
80°	94.4	90.5	89.0	89.8	87.4	86.5	86.5
82.5°	69.9	68.5	67.0	67.1	66.6	65.8	66.4
85°	38.6	37.8	37.8	37.0	37.0	36.3	36.3
87.5°	18.4	19.3	18.3	17.8	17.9	18.7	19.5
90°	22.7	24.0	25.0	25.9	26.6	27.4	28.2
92.5°	50.2	51.9	53.1	53.6	54.2	54.8	55.3
95°	95.8	97.7	98.9	99.4	99.9	100.4	100.9
97.5°	149.1	150.8	151.8	152.1	152.4	152.7	153.0
100°	186.6	188.9	190.4	190.9	191.4	192.0	192.5
102.5°	224.8	227.3	228.9	229.7	230.5	231.2	231.9
105°	285.2	286.7	287.9	288.7	289.4	290.2	291.0
107.5°	350.6	351.4	351.8	351.7	351.7	351.6	351.5
110°	396.7	397.4	397.7	397.4	397.2	396.9	396.7



TEST NUMBER: P333635-840

CATALOG NUMBER: S125RDIP-S1270D1205U840-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	330°	335°	340°	345°	350°	355°	360°
112.5°	442.3	442.7	442.6	442.2	441.7	441.2	440.8
115°	512.0	511.8	511.5	511.3	511.0	510.7	510.5
117.5°	582.9	583.1	582.7	581.7	580.7	579.6	578.6
120°	630.2	630.2	629.7	628.6	627.5	626.5	625.5
122.5°	676.5	676.3	675.8	674.9	674.1	673.3	672.5
125°	744.8	744.3	743.9	743.7	743.4	743.1	742.9
127.5°	813.1	812.9	812.5	812.0	811.4	810.9	810.4
130°	858.2	858.0	857.6	857.1	856.6	856.0	855.5
132.5°	901.4	901.1	900.7	899.9	899.2	898.5	897.8
135°	968.2	968.2	967.7	966.5	965.5	964.5	963.4
137.5°	1033.2	1033.5	1033.0	1031.7	1030.4	1029.1	1027.7
140°	1074.2	1074.7	1074.3	1073.0	1071.7	1070.4	1069.0
142.5°	1113.9	1114.2	1113.7	1112.4	1111.2	1109.8	1108.5
145°	1171.1	1171.1	1170.7	1170.0	1169.2	1168.4	1167.6
147.5°	1225.2	1225.8	1225.2	1223.5	1221.6	1219.9	1218.1
150°	1258.0	1258.0	1257.8	1257.2	1256.7	1256.2	1255.7
152.5°	1289.9	1290.5	1290.4	1289.5	1288.5	1287.6	1286.7
155°	1335.0	1336.2	1336.0	1334.6	1333.3	1332.1	1330.8
157.5°	1373.8	1374.8	1374.5	1372.8	1371.1	1369.4	1367.7
160°	1397.2	1398.3	1398.2	1396.8	1395.5	1394.2	1393.0
162.5°	1419.5	1420.8	1420.6	1419.1	1417.5	1416.0	1414.5
165°	1448.9	1450.0	1449.7	1448.1	1446.5	1445.0	1443.4
167.5°	1471.4	1472.9	1472.9	1471.3	1469.7	1468.0	1466.4
170°	1484.5	1486.0	1485.9	1484.1	1482.3	1480.5	1478.6
172.5°	1493.9	1495.4	1495.4	1493.8	1492.2	1490.6	1488.9
175°	1504.4	1506.0	1505.9	1504.1	1502.3	1500.4	1498.5
177.5°	1508.9	1510.2	1510.1	1508.6	1507.1	1505.7	1504.2
180°	1507.9	1507.9	1507.9	1507.9	1507.9	1507.9	1507.9

(END OF REPORT)