

Scaled data based on original data using  
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State  
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P331418-830

Luminaire Tested: **SA2XXDIP-C865D1080U830-4F0-1E-UDD-F1**

Issue Date: 10/7/2019

**Test Information**

Test Method: LM-79-08  
Report Number: P331418-830  
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-8,  
Test Lab: INNOVATION CENTER  
Issue Date: 10/7/2019  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: NEO-RAY  
Catalog Number: SA2XXDIP-C865D1080U830-4F0-1E-UDD-F1  
Description: DEFINE 2 DIRECT-INDIRECT PENDANT LED LUMINAIRE  
DOWNLIGHT 865 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER  
UPLIGHT 1080 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER  
Light Source: -  
Ballast/Driver: ELECTRONIC DRIVER

**Summary**


Lumens per Lamp: N/A  
Luminaire Lumens: 6942.1 lumens  
Efficiency: N/A  
Efficacy: 106.1 lumens/watt  
Spacing Criteria (0/90/45): 1.2 / 1.16 / 1.3  
Luminous Opening: Rectangular (W 0.17' x L: 4' x H: 0')  
CIE Type: General Diffuse

Input Watts (W): 65.4  
Input Voltage (V): 120  
Input Current (Ain): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 25 FT



TEST NUMBER: P331418-830  
CATALOG NUMBER: SA2XXDIP-C865D1080U830-4F0-1E-UDD-F1

### Luminous Intensity Polar Plot





TEST NUMBER: P331418-830

CATALOG NUMBER: SA2XXDIP-C865D1080U830-4F0-1E-UDD-F1

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	107	107	107	107	98	98	98	98	82	82	82	67	67	67	54	54	54	48
1	97	93	89	86	89	86	82	79	72	70	67	59	58	56	48	47	46	40
2	89	81	75	70	81	75	70	65	63	59	56	52	49	47	42	40	38	34
3	81	71	64	58	74	66	59	54	56	51	47	46	43	40	37	35	33	29
4	74	63	55	49	68	58	51	46	49	44	40	41	37	34	33	30	28	24
5	68	56	48	42	62	52	45	40	44	39	34	37	33	29	30	27	25	21
6	62	50	42	37	57	47	40	34	40	34	30	33	29	26	27	24	22	19
7	58	46	38	32	53	42	35	30	36	30	26	30	26	23	25	22	19	17
8	54	41	34	28	49	38	31	27	33	27	23	28	23	20	23	20	17	15
9	50	38	30	25	46	35	28	24	30	25	21	25	21	18	21	18	16	13
10	47	35	27	23	43	32	26	21	28	23	19	24	19	17	20	16	14	12

**AVERAGE LUMINANCE (cd/sqm):**

	0°	45°	90°
0°	21001	21001	21001
5°	21081	20778	20900
10°	20956	20566	20669
15°	20697	20301	20277
20°	20330	19900	19878
25°	19963	19408	19408
30°	19494	18957	18793
35°	19056	18413	18143
40°	18506	17873	17530
45°	17961	17335	16908
50°	17372	16777	16179
55°	16757	16124	15527
60°	16075	15345	14783
65°	15339	14571	13903
70°	14408	13638	12987
75°	13107	12558	12246
80°	11632	11278	10702
85°	9503	9040	8096



TEST NUMBER: P331418-830

CATALOG NUMBER: SA2XXDIP-C865D1080U830-4F0-1E-UDD-F1

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	122.3	1.8
10°-20°	344.2	5.0
20°-30°	505.9	7.3
30°-40°	587.6	8.5
40°-50°	587.0	8.5
50°-60°	511.9	7.4
60°-70°	378.5	5.5
70°-80°	214.4	3.1
80°-90°	62.8	0.9
90°-100°	82.2	1.2
100°-110°	255.3	3.7
110°-120°	436.4	6.3
120°-130°	573.9	8.3
130°-140°	644.2	9.3
140°-150°	631.6	9.1
150°-160°	529.8	7.6
160°-170°	351.4	5.1
170°-180°	122.8	1.8
0°-30°	972.3	14.0
0°-40°	1559.9	22.5
0°-60°	2658.7	38.3
0°-90°	3314.4	47.7
90°-120°	774.0	11.1
90°-150°	2623.7	37.8
90°-180°	3628.0	52.3
0°-180°	6942.1	100.0

**CANDELA DISTRIBUTION:**

	0°	22.5°	45°	67.5°	90°	Flux
0°	1301	1301	1301	1301	1301	
5°	1301	1295	1282	1291	1290	123
15°	1238	1230	1214	1219	1213	348
25°	1121	1110	1089	1092	1089	515
35°	967	954	934	927	920	603
45°	787	777	759	746	740	607
55°	595	587	573	558	552	532
65°	402	394	381	370	364	397
75°	210	207	201	194	196	224
85°	51	50	49	45	44	59
90°	1	15	38	36	37	5
95°	57	67	70	70	68	65
105°	235	239	241	243	243	249
115°	438	444	442	441	438	433
125°	637	646	644	641	639	569
135°	824	836	839	837	834	637
145°	1001	1008	1015	1016	1012	625
155°	1144	1147	1151	1156	1153	526
165°	1245	1244	1244	1251	1246	351
175°	1295	1292	1290	1297	1291	123
180°	1297	1297	1297	1297	1297	



TEST NUMBER: P331418-830

CATALOG NUMBER: SA2XXDIP-C865D1080U830-4F0-1E-UDD-F1

**CANDELA DISTRIBUTION (FULL):**

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	1300.7	1300.7	1300.7	1300.7	1300.7	1300.7	1300.7	1300.7	1300.7	1300.7	1300.7
2.5°	1306.7	1305.6	1304.5	1303.4	1302.3	1300.5	1298.1	1295.6	1293.2	1290.7	1293.0
5°	1300.7	1299.6	1298.5	1297.4	1296.3	1294.2	1291.2	1288.1	1285.1	1282.0	1284.2
7.5°	1289.2	1287.5	1285.8	1284.0	1282.3	1279.9	1276.8	1273.7	1270.5	1267.4	1269.7
10°	1278.2	1276.3	1274.3	1272.3	1270.5	1267.8	1264.4	1261.1	1257.8	1254.4	1256.7
12.5°	1263.2	1261.5	1259.8	1258.0	1256.3	1253.8	1250.5	1247.1	1243.8	1240.5	1242.0
15°	1238.2	1236.5	1234.8	1233.2	1231.5	1228.9	1225.3	1221.6	1218.0	1214.5	1215.5
17.5°	1206.2	1204.5	1202.9	1201.2	1199.5	1196.8	1193.2	1189.5	1185.8	1182.1	1183.5
20°	1183.2	1181.5	1179.9	1178.2	1176.5	1173.7	1169.8	1165.9	1162.1	1158.2	1159.0
22.5°	1160.2	1157.8	1155.5	1153.1	1150.8	1147.8	1144.2	1140.5	1136.8	1133.1	1133.3
25°	1120.6	1118.4	1116.2	1114.0	1111.7	1108.2	1103.5	1098.8	1094.1	1089.4	1090.0
27.5°	1075.6	1073.7	1071.6	1069.6	1067.6	1064.7	1061.0	1057.2	1053.6	1049.8	1049.0
30°	1045.6	1043.4	1041.1	1039.0	1036.7	1033.5	1029.4	1025.2	1021.0	1016.8	1016.0
32.5°	1013.6	1011.8	1010.0	1008.2	1006.4	1003.3	999.0	994.6	990.2	985.8	984.3
35°	966.8	964.0	961.2	958.5	955.6	952.1	947.6	943.2	938.7	934.2	932.6
37.5°	914.0	911.5	909.1	906.6	904.3	900.8	896.4	891.9	887.4	883.0	880.9
40°	878.0	875.8	873.5	871.3	869.1	865.7	861.3	856.9	852.4	848.0	845.5
42.5°	843.0	840.7	838.5	836.3	834.1	830.8	826.3	821.9	817.4	812.9	810.2
45°	786.6	784.8	782.8	780.9	778.9	775.8	771.7	767.5	763.4	759.2	756.1
47.5°	730.7	728.9	727.0	725.2	723.3	720.2	715.9	711.5	707.2	702.9	699.6
50°	691.6	690.2	688.9	687.5	686.1	683.4	679.6	675.6	671.8	667.9	664.0
52.5°	653.7	651.8	650.0	648.1	646.3	643.6	639.9	636.2	632.5	628.9	625.7
55°	595.3	593.7	592.0	590.3	588.6	586.2	582.9	579.5	576.2	572.8	569.5
57.5°	536.8	535.5	534.1	532.8	531.5	529.0	525.3	521.6	517.9	514.3	511.0
60°	497.8	496.6	495.6	494.5	493.3	490.9	486.9	483.1	479.2	475.2	472.2
62.5°	459.8	458.0	456.2	454.4	452.6	450.3	447.2	444.2	441.2	438.3	435.5
65°	401.5	399.8	398.1	396.4	394.8	392.6	389.8	387.0	384.3	381.4	379.0
67.5°	342.2	340.8	339.5	338.2	336.9	335.0	332.4	329.9	327.4	324.9	323.0
70°	305.2	304.1	302.9	301.8	300.8	298.9	296.4	293.9	291.4	288.9	287.0
72.5°	267.1	266.1	264.9	263.8	262.7	261.4	259.8	258.2	256.5	254.9	253.0
75°	210.1	209.5	209.0	208.5	207.9	206.9	205.6	204.2	202.7	201.3	199.7
77.5°	159.1	158.2	157.2	156.3	155.3	154.6	154.0	153.4	152.9	152.3	151.5
80°	125.1	124.8	124.5	124.2	123.9	123.6	123.0	122.4	121.9	121.3	120.5
82.5°	93.0	93.0	92.9	92.8	92.8	92.7	92.3	92.0	91.6	91.3	90.2
85°	51.3	51.0	50.7	50.4	50.1	49.9	49.6	49.3	49.0	48.8	48.0
87.5°	18.2	18.4	18.5	18.7	18.8	19.1	19.8	20.5	21.0	21.7	20.9
90°	1.1	4.1	7.0	9.9	12.8	16.9	22.2	27.6	33.0	38.4	37.8
92.5°	19.5	21.6	23.8	25.9	28.1	29.8	31.0	32.3	33.6	34.8	34.9
95°	56.9	59.4	61.8	64.2	66.6	68.1	68.6	69.1	69.6	70.0	70.0
97.5°	104.1	106.1	108.3	110.5	112.5	114.1	115.0	115.9	116.9	117.8	117.8
100°	139.0	141.0	143.0	144.9	146.8	148.2	148.9	149.6	150.3	151.1	151.1
102.5°	175.9	177.4	179.0	180.5	182.1	183.3	184.3	185.1	186.1	187.0	187.2
105°	235.4	236.1	236.9	237.6	238.3	238.9	239.4	239.9	240.3	240.8	241.4
107.5°	295.4	296.4	297.6	298.6	299.6	300.2	300.2	300.2	300.2	300.2	300.4
110°	333.9	335.4	336.9	338.3	339.8	340.5	340.5	340.5	340.5	340.5	340.5



TEST NUMBER: P331418-830

CATALOG NUMBER: SA2XXDIP-C865D1080U830-4F0-1E-UDD-F1

**CANDELA DISTRIBUTION (continued):**

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	376.0	377.4	378.9	380.3	381.8	382.5	382.2	382.0	381.8	381.6	381.1
115°	437.9	439.4	440.8	442.3	443.7	444.2	443.7	443.3	442.8	442.3	442.1
117.5°	499.6	501.6	503.6	505.5	507.5	507.7	506.4	505.0	503.7	502.3	501.7
120°	540.8	542.8	544.8	546.7	548.7	548.7	546.7	544.8	542.8	540.8	540.8
122.5°	578.5	580.9	583.2	585.5	587.9	588.3	587.0	585.6	584.3	582.9	582.3
125°	637.2	639.4	641.6	643.8	645.9	646.7	645.9	645.3	644.5	643.8	643.0
127.5°	694.4	697.1	699.9	702.7	705.4	706.4	705.5	704.6	703.8	702.9	702.0
130°	730.3	733.4	736.6	739.7	742.9	744.2	743.8	743.3	742.8	742.3	741.8
132.5°	770.5	773.2	775.7	778.3	780.9	782.2	782.3	782.4	782.5	782.6	781.6
135°	824.4	827.1	829.8	832.5	835.1	836.7	837.2	837.6	838.2	838.7	838.4
137.5°	881.1	883.4	885.5	887.7	889.9	891.3	891.9	892.6	893.2	893.8	893.6
140°	915.3	917.5	919.6	921.9	924.1	925.8	927.0	928.2	929.4	930.6	930.6
142.5°	950.4	952.5	954.7	956.9	959.0	960.5	961.4	962.2	963.1	963.9	964.1
145°	1000.7	1002.4	1004.1	1005.8	1007.5	1009.1	1010.5	1012.0	1013.4	1014.9	1015.1
147.5°	1045.6	1047.6	1049.6	1051.7	1053.8	1055.3	1056.2	1057.2	1058.2	1059.1	1059.7
150°	1076.2	1077.7	1079.1	1080.6	1082.0	1083.3	1084.3	1085.2	1086.2	1087.2	1087.9
152.5°	1103.3	1104.8	1106.3	1107.8	1109.2	1110.5	1111.7	1112.9	1114.1	1115.2	1116.2
155°	1144.2	1144.8	1145.6	1146.3	1147.1	1147.7	1148.5	1149.2	1150.0	1150.7	1151.9
157.5°	1178.9	1179.4	1179.9	1180.3	1180.9	1181.3	1181.8	1182.2	1182.6	1183.1	1184.8
160°	1200.0	1200.4	1200.9	1201.4	1201.9	1202.2	1202.5	1202.8	1203.0	1203.2	1204.7
162.5°	1219.2	1219.3	1219.4	1219.5	1219.7	1219.7	1220.0	1220.2	1220.5	1220.8	1222.4
165°	1244.8	1244.6	1244.3	1244.1	1243.9	1243.8	1243.8	1243.8	1243.8	1243.8	1245.5
167.5°	1266.3	1265.6	1264.8	1264.1	1263.4	1263.0	1262.9	1262.9	1262.8	1262.8	1264.5
170°	1277.7	1277.0	1276.2	1275.4	1274.8	1274.3	1274.0	1273.8	1273.6	1273.3	1275.0
172.5°	1285.5	1284.9	1284.1	1283.4	1282.6	1282.1	1282.0	1281.7	1281.4	1281.2	1282.9
175°	1295.2	1294.5	1293.7	1293.0	1292.3	1291.7	1291.2	1290.7	1290.2	1289.7	1291.5
177.5°	1299.1	1298.5	1298.0	1297.4	1296.8	1296.3	1295.9	1295.5	1295.1	1294.8	1295.9
180°	1297.4	1297.4	1297.4	1297.4	1297.4	1297.4	1297.4	1297.4	1297.4	1297.4	1297.4



TEST NUMBER: P331418-830  
 CATALOG NUMBER: SA2XXDIP-C865D1080U830-4F0-1E-UDD-F1

**CANDELA DISTRIBUTION (continued):**

	55°	60°	65°	70°	75°	80°	85°	90°
0°	1300.7	1300.7	1300.7	1300.7	1300.7	1300.7	1300.7	1300.7
2.5°	1295.1	1297.4	1299.6	1300.5	1300.0	1299.6	1299.2	1298.7
5°	1286.4	1288.6	1290.9	1291.7	1291.2	1290.6	1290.1	1289.5
7.5°	1271.9	1274.1	1276.4	1277.1	1276.6	1275.9	1275.4	1274.7
10°	1258.9	1261.1	1263.4	1264.0	1263.2	1262.3	1261.5	1260.7
12.5°	1243.6	1245.1	1246.7	1247.2	1246.5	1245.9	1245.3	1244.7
15°	1216.6	1217.8	1218.9	1218.7	1217.4	1216.0	1214.6	1213.1
17.5°	1184.7	1186.0	1187.3	1187.2	1185.9	1184.6	1183.3	1181.9
20°	1159.8	1160.6	1161.5	1161.3	1160.3	1159.1	1158.0	1156.9
22.5°	1133.5	1133.6	1133.8	1133.6	1132.8	1132.2	1131.5	1130.9
25°	1090.5	1091.0	1091.6	1091.6	1091.0	1090.5	1090.0	1089.4
27.5°	1048.2	1047.4	1046.5	1045.5	1044.1	1042.7	1041.4	1040.1
30°	1015.1	1014.4	1013.5	1012.5	1011.4	1010.3	1009.2	1008.0
32.5°	982.8	981.3	979.8	978.5	977.4	976.3	975.2	974.0
35°	930.9	929.3	927.7	926.0	924.7	923.3	921.9	920.5
37.5°	878.9	876.8	874.8	873.1	871.8	870.4	869.1	867.7
40°	843.0	840.5	838.0	836.1	835.1	834.0	832.8	831.7
42.5°	807.5	804.7	802.1	799.9	798.3	796.8	795.2	793.7
45°	753.1	750.0	747.0	744.9	743.8	742.6	741.5	740.5
47.5°	696.4	693.2	690.0	687.6	686.0	684.4	682.8	681.2
50°	660.1	656.2	652.3	649.7	648.3	646.9	645.5	644.1
52.5°	622.4	619.2	616.0	613.4	611.6	609.7	607.9	606.1
55°	566.2	562.8	559.5	557.1	555.7	554.3	553.0	551.6
57.5°	507.7	504.4	501.1	499.0	497.9	496.9	495.9	494.7
60°	469.2	466.1	463.1	461.1	460.2	459.4	458.5	457.8
62.5°	432.5	429.7	426.9	425.0	423.9	422.8	421.8	420.8
65°	376.5	374.0	371.5	369.5	368.2	366.7	365.3	363.9
67.5°	321.0	319.1	317.2	315.7	314.5	313.4	312.3	311.1
70°	285.0	283.0	281.2	279.6	278.5	277.4	276.3	275.1
72.5°	251.0	249.0	247.1	245.7	244.8	243.9	243.0	242.1
75°	198.0	196.3	194.7	194.2	194.7	195.3	195.8	196.3
77.5°	150.7	149.9	149.0	148.2	147.4	146.7	145.9	145.1
80°	119.6	118.9	118.0	117.3	116.7	116.2	115.6	115.1
82.5°	89.2	88.1	87.1	86.5	86.3	86.2	86.1	86.1
85°	47.1	46.3	45.4	44.9	44.6	44.3	44.0	43.7
87.5°	20.2	19.4	18.6	18.2	18.0	17.8	17.6	17.4
90°	37.3	36.9	36.4	36.3	36.5	36.8	36.9	37.2
92.5°	35.0	35.1	35.3	35.3	35.3	35.3	35.4	35.4
95°	70.0	70.0	70.0	69.8	69.4	68.9	68.3	67.9
97.5°	117.8	117.8	117.8	117.8	117.7	117.7	117.6	117.6
100°	151.1	151.1	151.1	151.0	150.7	150.5	150.2	150.0
102.5°	187.4	187.6	187.8	187.8	187.5	187.3	187.0	186.8
105°	241.9	242.3	242.8	243.1	243.1	243.1	243.1	243.1
107.5°	300.6	300.8	301.0	300.5	299.4	298.3	297.2	296.1
110°	340.5	340.5	340.5	340.2	339.4	338.7	337.9	337.2





TEST NUMBER: P331418-830

CATALOG NUMBER: SA2XXDIP-C865D1080U830-4F0-1E-UDD-F1

**CANDELA DISTRIBUTION (continued):**

	55°	60°	65°	70°	75°	80°	85°	90°
112.5°	380.5	379.9	379.4	378.8	378.2	377.7	377.2	376.6
115°	441.9	441.6	441.3	440.8	440.2	439.4	438.7	437.9
117.5°	501.1	500.6	500.0	499.4	498.6	497.9	497.1	496.4
120°	540.8	540.8	540.8	540.5	539.8	539.0	538.3	537.5
122.5°	581.7	581.2	580.5	580.0	579.5	578.9	578.4	577.9
125°	642.3	641.6	640.8	640.4	640.1	639.9	639.6	639.4
127.5°	701.2	700.2	699.4	698.5	697.8	697.0	696.3	695.4
130°	741.3	740.8	740.4	739.6	738.7	737.6	736.7	735.7
132.5°	780.4	779.4	778.4	777.4	776.7	775.8	775.1	774.3
135°	838.2	837.9	837.6	837.2	836.4	835.8	835.0	834.2
137.5°	893.4	893.2	893.1	892.5	891.5	890.5	889.6	888.5
140°	930.6	930.6	930.6	930.1	929.2	928.2	927.2	926.2
142.5°	964.3	964.5	964.7	964.3	963.3	962.3	961.4	960.4
145°	1015.4	1015.7	1015.9	1015.5	1014.6	1013.6	1012.6	1011.6
147.5°	1060.3	1060.7	1061.3	1061.1	1060.2	1059.2	1058.3	1057.4
150°	1088.6	1089.4	1090.1	1090.1	1089.4	1088.6	1087.9	1087.2
152.5°	1117.1	1117.9	1118.9	1118.9	1117.9	1117.1	1116.2	1115.2
155°	1153.1	1154.3	1155.6	1155.7	1155.1	1154.3	1153.6	1152.8
157.5°	1186.4	1188.1	1189.7	1190.0	1188.7	1187.6	1186.5	1185.2
160°	1206.2	1207.6	1209.1	1209.3	1208.3	1207.4	1206.4	1205.4
162.5°	1224.1	1225.7	1227.4	1227.6	1226.4	1225.3	1224.1	1222.9
165°	1247.2	1248.9	1250.6	1250.8	1249.6	1248.4	1247.2	1245.9
167.5°	1266.2	1267.9	1269.6	1269.8	1268.6	1267.2	1266.0	1264.8
170°	1276.7	1278.4	1280.1	1280.3	1278.7	1277.3	1275.8	1274.4
172.5°	1284.6	1286.3	1288.0	1288.1	1286.7	1285.2	1283.7	1282.2
175°	1293.2	1294.9	1296.6	1296.7	1295.2	1293.7	1292.3	1290.8
177.5°	1297.1	1298.3	1299.4	1299.4	1298.3	1297.1	1295.9	1294.8
180°	1297.4	1297.4	1297.4	1297.4	1297.4	1297.4	1297.4	1297.4

(END OF REPORT)