

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P331381-830

Luminaire Tested: **SA2XXDIP-C865D330U830-4F0-1E-UDD-F**

Issue Date: 10/7/2019

Test Information

Test Method: LM-79-08
Report Number: P331381-830
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-2,
Test Lab: INNOVATION CENTER
Issue Date: 10/7/2019
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: NEO-RAY
Catalog Number: SA2XXDIP-C865D330U830-4F0-1E-UDD-F
Description: DEFINE 2 DIRECT-INDIRECT PENDANT LED LUMINAIRE
DOWNLIGHT 865 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER
UPLIGHT 330 LUMENS PER FOOT, NO LENS
Light Source: -
Ballast/Driver: ELECTRONIC DRIVER

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 4544.5 lumens
Efficiency: N/A
Efficacy: 104.5 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 1.16 / 1.3
Luminous Opening: Rectangular (W 0.17' x L: 4' x H: 0')
CIE Type: Semi-Direct

Input Watts (W): 43.5
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P331381-830
CATALOG NUMBER: SA2XXDIP-C865D330U830-4F0-1E-UDD-F

Luminous Intensity Polar Plot





TEST NUMBER: P331381-830

CATALOG NUMBER: SA2XXDIP-C865D330U830-4F0-1E-UDD-F

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	113	113	113	113	107	107	107	107	96	96	96	86	86	86	77	77	77	73
1	103	98	94	91	97	94	90	87	84	82	79	76	74	72	68	67	65	61
2	94	86	80	74	89	82	76	71	74	69	66	67	63	60	60	57	55	51
3	86	76	68	62	81	72	65	60	65	60	55	59	55	51	53	50	47	44
4	78	67	59	53	74	64	57	51	58	52	47	53	48	44	48	44	40	37
5	72	60	51	45	68	57	50	44	52	46	41	47	42	38	43	39	35	32
6	67	54	45	39	63	52	44	38	47	41	36	43	38	33	39	35	31	29
7	62	49	41	35	58	47	39	34	43	36	32	39	34	30	36	31	28	25
8	57	44	36	31	54	43	35	30	39	33	28	36	30	27	33	28	25	23
9	53	41	33	28	51	39	32	27	36	30	25	33	28	24	30	26	22	20
10	50	38	30	25	48	36	29	24	33	27	23	31	25	22	28	24	20	19

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	21001	21001	21001
5°	21081	20778	20900
10°	20956	20566	20669
15°	20697	20301	20277
20°	20330	19900	19878
25°	19963	19408	19408
30°	19494	18957	18793
35°	19056	18413	18143
40°	18506	17873	17530
45°	17961	17335	16908
50°	17372	16777	16179
55°	16757	16124	15527
60°	16075	15345	14783
65°	15339	14571	13903
70°	14408	13638	12987
75°	13107	12558	12246
80°	11632	11278	10702
85°	9503	9040	8096



TEST NUMBER: P331381-830

CATALOG NUMBER: SA2XXDIP-C865D330U830-4F0-1E-UDD-F

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	122.3	2.7
10°-20°	344.2	7.6
20°-30°	505.9	11.1
30°-40°	587.6	12.9
40°-50°	587.0	12.9
50°-60°	511.9	11.3
60°-70°	378.5	8.3
70°-80°	214.4	4.7
80°-90°	58.7	1.3
90°-100°	14.0	0.3
100°-110°	51.5	1.1
110°-120°	137.7	3.0
120°-130°	227.3	5.0
130°-140°	241.8	5.3
140°-150°	224.7	4.9
150°-160°	180.7	4.0
160°-170°	116.4	2.6
170°-180°	40.1	0.9
0°-30°	972.3	21.4
0°-40°	1559.9	34.3
0°-60°	2658.7	58.5
0°-90°	3310.3	72.8
90°-120°	203.3	4.5
90°-150°	897.1	19.7
90°-180°	1234.0	27.2
0°-180°	4544.5	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	1301	1301	1301	1301	1301	
5°	1301	1295	1282	1291	1290	123
15°	1238	1230	1214	1219	1213	348
25°	1121	1110	1089	1092	1089	515
35°	967	954	934	927	920	603
45°	787	777	759	746	740	607
55°	595	587	573	558	552	532
65°	402	394	381	370	364	397
75°	210	207	201	194	196	224
85°	51	50	49	45	44	59
90°	0	4	6	8	8	3
95°	20	10	12	13	13	24
105°	93	97	19	22	23	99
115°	175	181	188	54	25	172
125°	248	252	258	260	260	221
135°	307	311	314	317	317	237
145°	356	356	360	362	361	222
155°	392	389	392	394	392	180
165°	413	411	412	414	412	117
175°	422	420	421	422	420	40
180°	421	421	421	421	421	



TEST NUMBER: P331381-830

CATALOG NUMBER: SA2XXDIP-C865D330U830-4F0-1E-UDD-F

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	1300.7	1300.7	1300.7	1300.7	1300.7	1300.7	1300.7	1300.7	1300.7	1300.7	1300.7
2.5°	1306.7	1305.6	1304.5	1303.4	1302.3	1300.5	1298.1	1295.6	1293.2	1290.7	1293.0
5°	1300.7	1299.6	1298.5	1297.4	1296.3	1294.2	1291.2	1288.1	1285.1	1282.0	1284.2
7.5°	1289.2	1287.5	1285.8	1284.0	1282.3	1279.9	1276.8	1273.7	1270.5	1267.4	1269.7
10°	1278.2	1276.3	1274.3	1272.3	1270.5	1267.8	1264.4	1261.1	1257.8	1254.4	1256.7
12.5°	1263.2	1261.5	1259.8	1258.0	1256.3	1253.8	1250.5	1247.1	1243.8	1240.5	1242.0
15°	1238.2	1236.5	1234.8	1233.2	1231.5	1228.9	1225.3	1221.6	1218.0	1214.5	1215.5
17.5°	1206.2	1204.5	1202.9	1201.2	1199.5	1196.8	1193.2	1189.5	1185.8	1182.1	1183.5
20°	1183.2	1181.5	1179.9	1178.2	1176.5	1173.7	1169.8	1165.9	1162.1	1158.2	1159.0
22.5°	1160.2	1157.8	1155.5	1153.1	1150.8	1147.8	1144.2	1140.5	1136.8	1133.1	1133.3
25°	1120.6	1118.4	1116.2	1114.0	1111.7	1108.2	1103.5	1098.8	1094.1	1089.4	1090.0
27.5°	1075.6	1073.7	1071.6	1069.6	1067.6	1064.7	1061.0	1057.2	1053.6	1049.8	1049.0
30°	1045.6	1043.4	1041.1	1039.0	1036.7	1033.5	1029.4	1025.2	1021.0	1016.8	1016.0
32.5°	1013.6	1011.8	1010.0	1008.2	1006.4	1003.3	999.0	994.6	990.2	985.8	984.3
35°	966.8	964.0	961.2	958.5	955.6	952.1	947.6	943.2	938.7	934.2	932.6
37.5°	914.0	911.5	909.1	906.6	904.3	900.8	896.4	891.9	887.4	883.0	880.9
40°	878.0	875.8	873.5	871.3	869.1	865.7	861.3	856.9	852.4	848.0	845.5
42.5°	843.0	840.7	838.5	836.3	834.1	830.8	826.3	821.9	817.4	812.9	810.2
45°	786.6	784.8	782.8	780.9	778.9	775.8	771.7	767.5	763.4	759.2	756.1
47.5°	730.7	728.9	727.0	725.2	723.3	720.2	715.9	711.5	707.2	702.9	699.6
50°	691.6	690.2	688.9	687.5	686.1	683.4	679.6	675.6	671.8	667.9	664.0
52.5°	653.7	651.8	650.0	648.1	646.3	643.6	639.9	636.2	632.5	628.9	625.7
55°	595.3	593.7	592.0	590.3	588.6	586.2	582.9	579.5	576.2	572.8	569.5
57.5°	536.8	535.5	534.1	532.8	531.5	529.0	525.3	521.6	517.9	514.3	511.0
60°	497.8	496.6	495.6	494.5	493.3	490.9	486.9	483.1	479.2	475.2	472.2
62.5°	459.8	458.0	456.2	454.4	452.6	450.3	447.2	444.2	441.2	438.3	435.5
65°	401.5	399.8	398.1	396.4	394.8	392.6	389.8	387.0	384.3	381.4	379.0
67.5°	342.2	340.8	339.5	338.2	336.9	335.0	332.4	329.9	327.4	324.9	323.0
70°	305.2	304.1	302.9	301.8	300.8	298.9	296.4	293.9	291.4	288.9	287.0
72.5°	267.1	266.1	264.9	263.8	262.7	261.4	259.8	258.2	256.5	254.9	253.0
75°	210.1	209.5	209.0	208.5	207.9	206.9	205.6	204.2	202.7	201.3	199.7
77.5°	159.1	158.2	157.2	156.3	155.3	154.6	154.0	153.4	152.9	152.3	151.5
80°	125.1	124.8	124.5	124.2	123.9	123.6	123.0	122.4	121.9	121.3	120.5
82.5°	93.0	93.0	92.9	92.8	92.8	92.7	92.3	92.0	91.6	91.3	90.2
85°	51.3	51.0	50.7	50.4	50.1	49.9	49.6	49.3	49.0	48.8	48.0
87.5°	18.1	17.8	17.4	17.2	16.9	16.6	16.2	15.9	15.6	15.3	14.6
90°	0.3	1.0	1.8	2.5	3.3	4.0	4.4	5.0	5.6	6.1	6.4
92.5°	6.1	6.1	6.0	5.9	5.8	6.0	6.2	6.5	6.8	7.1	7.3
95°	19.8	17.5	15.4	13.1	10.8	10.0	10.5	10.9	11.4	11.9	12.3
97.5°	39.3	33.0	26.7	20.5	14.1	11.5	12.6	13.7	14.8	15.9	16.2
100°	53.9	44.7	35.3	26.1	16.9	12.7	13.9	15.1	16.2	17.3	17.9
102.5°	70.0	68.1	66.1	64.2	62.2	56.4	46.8	37.1	27.5	17.8	18.6
105°	92.7	94.6	96.7	98.8	100.8	92.6	74.1	55.6	37.0	18.6	19.3
107.5°	118.4	120.1	121.7	123.4	125.0	114.7	92.6	70.4	48.2	26.0	25.3
110°	135.0	136.4	137.9	139.3	140.7	131.6	112.1	92.5	72.9	53.3	46.6



TEST NUMBER: P331381-830

CATALOG NUMBER: SA2XXDIP-C865D330U830-4F0-1E-UDD-F

CANDELA DISTRIBUTION (continued):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	150.6	151.8	153.2	154.4	155.6	153.8	149.0	144.2	139.3	134.5	109.8
115°	175.2	176.3	177.6	178.7	179.8	181.3	182.9	184.6	186.3	188.0	156.7
117.5°	197.3	198.5	199.8	201.1	202.4	203.6	204.8	205.9	207.1	208.3	200.7
120°	213.3	214.3	215.4	216.4	217.4	218.5	219.7	220.9	222.2	223.4	224.2
122.5°	227.0	228.1	229.1	230.2	231.3	232.4	233.8	235.1	236.5	237.8	238.3
125°	247.8	248.6	249.5	250.4	251.3	252.4	253.6	255.0	256.2	257.5	258.0
127.5°	266.6	267.6	268.5	269.6	270.5	271.5	272.4	273.4	274.4	275.3	276.0
130°	278.5	279.7	280.7	281.8	282.9	283.8	284.6	285.3	286.1	286.8	287.5
132.5°	290.8	291.6	292.6	293.5	294.5	295.2	296.0	296.7	297.5	298.2	298.9
135°	306.6	307.6	308.8	309.8	310.9	311.8	312.4	313.0	313.6	314.2	314.9
137.5°	322.6	323.4	324.1	324.9	325.6	326.4	327.1	327.7	328.5	329.1	329.8
140°	333.1	333.7	334.1	334.7	335.3	335.9	336.7	337.4	338.2	338.8	339.5
142.5°	341.9	342.3	342.8	343.4	343.8	344.5	345.3	346.2	347.0	347.9	348.5
145°	355.6	355.6	355.5	355.4	355.3	355.9	357.0	358.3	359.4	360.5	361.0
147.5°	367.7	367.4	367.1	366.8	366.6	367.0	368.2	369.4	370.5	371.6	371.9
150°	375.4	374.9	374.5	374.0	373.5	373.9	374.9	376.1	377.1	378.2	378.6
152.5°	382.0	381.5	381.0	380.4	379.9	380.1	381.2	382.2	383.2	384.3	384.7
155°	391.6	391.0	390.4	389.7	389.2	389.3	390.1	390.9	391.7	392.5	392.9
157.5°	399.1	398.6	398.0	397.6	397.0	397.1	397.7	398.2	398.8	399.4	399.8
160°	403.5	403.1	402.7	402.3	401.9	401.9	402.3	402.7	403.1	403.5	403.9
162.5°	407.4	407.0	406.6	406.1	405.8	405.8	406.0	406.4	406.8	407.2	407.6
165°	412.6	412.3	411.8	411.4	411.0	410.9	411.1	411.3	411.5	411.7	412.2
167.5°	416.5	416.1	415.8	415.3	414.9	414.8	415.0	415.2	415.4	415.6	416.0
170°	418.8	418.3	417.9	417.5	417.1	417.0	417.1	417.3	417.4	417.5	418.0
172.5°	420.2	419.8	419.3	419.0	418.6	418.4	418.6	418.7	418.9	419.0	419.4
175°	422.1	421.6	421.1	420.7	420.2	420.0	420.2	420.3	420.5	420.6	421.0
177.5°	422.4	422.0	421.6	421.2	420.8	420.8	420.8	420.8	420.8	420.9	421.3
180°	421.1	421.1	421.1	421.1	421.1	421.1	421.1	421.1	421.1	421.1	421.1



TEST NUMBER: P331381-830

CATALOG NUMBER: SA2XXDIP-C865D330U830-4F0-1E-UDD-F

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°
0°	1300.7	1300.7	1300.7	1300.7	1300.7	1300.7	1300.7	1300.7
2.5°	1295.1	1297.4	1299.6	1300.5	1300.0	1299.6	1299.2	1298.7
5°	1286.4	1288.6	1290.9	1291.7	1291.2	1290.6	1290.1	1289.5
7.5°	1271.9	1274.1	1276.4	1277.1	1276.6	1275.9	1275.4	1274.7
10°	1258.9	1261.1	1263.4	1264.0	1263.2	1262.3	1261.5	1260.7
12.5°	1243.6	1245.1	1246.7	1247.2	1246.5	1245.9	1245.3	1244.7
15°	1216.6	1217.8	1218.9	1218.7	1217.4	1216.0	1214.6	1213.1
17.5°	1184.7	1186.0	1187.3	1187.2	1185.9	1184.6	1183.3	1181.9
20°	1159.8	1160.6	1161.5	1161.3	1160.3	1159.1	1158.0	1156.9
22.5°	1133.5	1133.6	1133.8	1133.6	1132.8	1132.2	1131.5	1130.9
25°	1090.5	1091.0	1091.6	1091.6	1091.0	1090.5	1090.0	1089.4
27.5°	1048.2	1047.4	1046.5	1045.5	1044.1	1042.7	1041.4	1040.1
30°	1015.1	1014.4	1013.5	1012.5	1011.4	1010.3	1009.2	1008.0
32.5°	982.8	981.3	979.8	978.5	977.4	976.3	975.2	974.0
35°	930.9	929.3	927.7	926.0	924.7	923.3	921.9	920.5
37.5°	878.9	876.8	874.8	873.1	871.8	870.4	869.1	867.7
40°	843.0	840.5	838.0	836.1	835.1	834.0	832.8	831.7
42.5°	807.5	804.7	802.1	799.9	798.3	796.8	795.2	793.7
45°	753.1	750.0	747.0	744.9	743.8	742.6	741.5	740.5
47.5°	696.4	693.2	690.0	687.6	686.0	684.4	682.8	681.2
50°	660.1	656.2	652.3	649.7	648.3	646.9	645.5	644.1
52.5°	622.4	619.2	616.0	613.4	611.6	609.7	607.9	606.1
55°	566.2	562.8	559.5	557.1	555.7	554.3	553.0	551.6
57.5°	507.7	504.4	501.1	499.0	497.9	496.9	495.9	494.7
60°	469.2	466.1	463.1	461.1	460.2	459.4	458.5	457.8
62.5°	432.5	429.7	426.9	425.0	423.9	422.8	421.8	420.8
65°	376.5	374.0	371.5	369.5	368.2	366.7	365.3	363.9
67.5°	321.0	319.1	317.2	315.7	314.5	313.4	312.3	311.1
70°	285.0	283.0	281.2	279.6	278.5	277.4	276.3	275.1
72.5°	251.0	249.0	247.1	245.7	244.8	243.9	243.0	242.1
75°	198.0	196.3	194.7	194.2	194.7	195.3	195.8	196.3
77.5°	150.7	149.9	149.0	148.2	147.4	146.7	145.9	145.1
80°	119.6	118.9	118.0	117.3	116.7	116.2	115.6	115.1
82.5°	89.2	88.1	87.1	86.5	86.3	86.2	86.1	86.1
85°	47.1	46.3	45.4	44.9	44.6	44.3	44.0	43.7
87.5°	14.0	13.4	12.8	12.4	12.3	12.1	11.9	11.7
90°	6.8	7.1	7.4	7.7	7.8	7.9	8.1	8.2
92.5°	7.4	7.6	7.7	7.9	8.0	8.1	8.1	8.2
95°	12.5	12.9	13.2	13.4	13.3	13.2	13.2	13.1
97.5°	16.5	16.7	17.0	17.2	17.2	17.3	17.4	17.5
100°	18.5	19.0	19.5	19.9	20.0	20.2	20.3	20.5
102.5°	19.2	20.0	20.6	21.1	21.3	21.5	21.7	21.9
105°	20.1	20.8	21.6	22.1	22.3	22.6	22.9	23.2
107.5°	24.5	23.8	23.0	22.7	23.0	23.3	23.6	23.8
110°	39.8	33.0	26.2	23.0	23.3	23.6	23.8	24.0



TEST NUMBER: P331381-830

CATALOG NUMBER: SA2XXDIP-C865D330U830-4F0-1E-UDD-F

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°
112.5°	85.1	60.4	35.7	23.5	23.7	23.8	24.1	24.3
115°	125.4	94.0	62.6	44.5	39.6	34.8	29.9	25.0
117.5°	193.1	185.5	178.0	166.2	150.1	134.1	118.1	102.1
120°	225.0	225.8	226.6	222.4	213.3	204.2	195.0	185.9
122.5°	238.7	239.2	239.7	239.0	237.3	235.5	233.8	232.0
125°	258.4	258.9	259.4	259.8	260.0	260.1	260.3	260.5
127.5°	276.7	277.4	278.1	278.4	278.5	278.5	278.5	278.6
130°	288.2	289.0	289.7	290.1	290.0	289.9	289.9	289.8
132.5°	299.5	300.1	300.8	301.0	301.0	301.0	300.9	300.8
135°	315.6	316.2	316.9	317.2	317.1	316.9	316.8	316.6
137.5°	330.5	331.1	331.8	332.0	331.8	331.6	331.3	331.1
140°	340.1	340.7	341.3	341.5	341.1	340.8	340.4	340.1
142.5°	349.0	349.6	350.2	350.2	349.9	349.6	349.2	348.8
145°	361.5	361.9	362.4	362.5	362.1	361.8	361.5	361.1
147.5°	372.3	372.7	373.1	373.1	372.8	372.5	372.2	371.9
150°	379.0	379.4	379.8	379.8	379.6	379.2	378.8	378.5
152.5°	385.1	385.5	385.9	385.9	385.4	385.0	384.6	384.1
155°	393.3	393.7	394.2	394.1	393.5	393.0	392.5	391.9
157.5°	400.3	400.8	401.1	401.1	400.6	400.1	399.5	399.1
160°	404.4	404.7	405.1	405.1	404.6	404.2	403.7	403.2
162.5°	408.0	408.5	409.0	409.0	408.3	407.7	407.2	406.6
165°	412.6	413.1	413.6	413.6	413.1	412.6	412.2	411.7
167.5°	416.5	417.0	417.5	417.4	416.8	416.1	415.6	414.9
170°	418.5	419.0	419.4	419.3	418.8	418.1	417.5	416.9
172.5°	419.9	420.4	420.8	420.8	420.2	419.6	419.0	418.4
175°	421.5	422.0	422.4	422.4	421.7	421.0	420.3	419.6
177.5°	421.7	422.1	422.4	422.4	421.9	421.4	420.9	420.5
180°	421.1	421.1	421.1	421.1	421.1	421.1	421.1	421.1

(END OF REPORT)