

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P333627-840

Luminaire Tested: **S125RDIP-S1270D810U840-4F0-1E-UDD-F4**

Issue Date: 3/3/2020

Test Information

Test Method: LM-79-08
Report Number: P333627-840
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-19,
Test Lab: INNOVATION CENTER
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: NEO-RAY
Catalog Number: S125RDIP-S1270D810U840-4F0-1E-UDD-F4
Description: DEFINE 5 DIRECT-INDIRECT PENDANT LED LUMINAIRE
DOWNLIGHT 1270 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER, REGRESSED
HOUSING
UPLIGHT 810 LUMENS PER FOOT, BATWING OPTIC
Light Source: -
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 7864.1 lumens
Efficiency: N/A
Efficacy: 129.6 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 1.11 / 1.25
Luminous Opening: Rectangular (W 0.42' x L: 4' x H: 0')
CIE Type: Semi-Direct


Input Watts (W): 60.7
Input Voltage (V): 120
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P333627-840

CATALOG NUMBER: S125RDIP-S1270D810U840-4F0-1E-UDD-F4

Luminous Intensity Polar Plot





TEST NUMBER: P333627-840

CATALOG NUMBER: S125RDIP-S1270D810U840-4F0-1E-UDD-F4

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	110	110	110	110	103	103	103	103	90	90	90	79	79	79	68	68	68	63
1	101	97	93	89	94	91	87	84	80	77	75	70	68	66	60	59	58	53
2	92	85	79	73	86	80	74	70	70	66	62	61	58	56	53	51	49	45
3	84	75	67	61	79	70	64	59	62	57	53	55	51	47	48	45	42	38
4	77	66	58	52	72	63	55	50	55	50	45	49	44	41	43	39	36	33
5	71	59	51	45	66	56	49	43	50	44	39	44	39	36	39	35	32	29
6	66	53	45	39	61	50	43	38	45	39	34	40	35	31	35	31	28	26
7	61	48	40	35	57	46	38	33	41	35	31	36	31	28	32	28	25	23
8	56	44	36	31	53	42	35	30	37	31	27	33	28	25	30	26	23	20
9	53	40	33	28	49	38	31	27	34	29	25	31	26	22	27	23	21	18
10	49	37	30	25	46	35	28	24	32	26	22	28	24	20	25	21	19	17

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	13464	13464	13464
5°	13494	13341	13422
10°	13392	13217	13217
15°	13233	12948	12843
20°	13029	12575	12423
25°	12790	12207	11938
30°	12493	11777	11401
35°	12191	11334	10800
40°	11907	10871	10208
45°	11562	10355	9563
50°	11216	9792	8890
55°	10815	9254	8173
60°	10413	8603	7403
65°	9938	7844	6521
70°	9396	6898	5620
75°	8644	5814	4674
80°	7613	4567	3924
85°	6417	3735	3505



TEST NUMBER: P333627-840

CATALOG NUMBER: S125RDIP-S1270D810U840-4F0-1E-UDD-F4

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	196.0	2.5
10°-20°	547.8	7.0
20°-30°	794.4	10.1
30°-40°	905.3	11.5
40°-50°	882.5	11.2
50°-60°	742.8	9.4
60°-70°	520.7	6.6
70°-80°	267.7	3.4
80°-90°	69.8	0.9
90°-100°	283.9	3.6
100°-110°	610.3	7.8
110°-120°	572.7	7.3
120°-130°	464.2	5.9
130°-140°	372.5	4.7
140°-150°	281.1	3.6
150°-160°	197.9	2.5
160°-170°	116.6	1.5
170°-180°	37.9	0.5
0°-30°	1538.2	19.6
0°-40°	2443.5	31.1
0°-60°	4068.9	51.7
0°-90°	4927.0	62.7
90°-120°	1466.9	18.7
90°-150°	2584.6	32.9
90°-180°	2937.0	37.3
0°-180°	7864.1	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	2085	2085	2085	2085	2085	
5°	2082	2075	2058	2073	2070	197
15°	1979	1968	1937	1934	1921	558
25°	1795	1769	1713	1693	1675	826
35°	1546	1507	1438	1393	1370	968
45°	1266	1218	1134	1073	1047	976
55°	960	908	822	754	726	859
65°	650	595	513	452	427	644
75°	346	298	233	200	187	367
85°	87	59	50	49	47	97
90°	1	7	13	17	18	6
95°	26	77	700	317	186	28
105°	89	125	572	1127	1046	94
115°	160	192	460	991	1166	157
125°	221	259	441	788	918	196
135°	259	311	438	660	763	201
145°	302	346	439	547	602	189
155°	344	370	428	484	504	158
165°	376	386	411	436	442	106
175°	391	391	394	399	397	37
180°	392	392	392	392	392	



TEST NUMBER: P333627-840

CATALOG NUMBER: S125RDIP-S1270D810U840-4F0-1E-UDD-F4

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	2084.7	2084.7	2084.7	2084.7	2084.7	2084.7	2084.7	2084.7	2084.7	2084.7	2084.7
2.5°	2088.4	2087.6	2086.7	2085.9	2085.1	2083.3	2080.4	2077.6	2074.9	2072.0	2074.9
5°	2081.5	2080.1	2078.7	2077.3	2075.9	2073.3	2069.4	2065.6	2061.7	2057.9	2061.3
7.5°	2061.0	2059.7	2058.4	2057.0	2055.7	2052.8	2048.1	2043.5	2038.9	2034.3	2036.7
10°	2042.1	2041.0	2040.0	2039.0	2037.9	2035.0	2030.0	2025.2	2020.2	2015.4	2016.4
12.5°	2020.7	2019.4	2018.0	2016.7	2015.4	2011.4	2004.9	1998.3	1991.7	1985.1	1985.9
15°	1979.1	1977.0	1975.0	1972.9	1970.8	1966.0	1958.6	1951.4	1944.0	1936.6	1936.3
17.5°	1932.2	1929.0	1925.8	1922.6	1919.3	1913.1	1903.9	1894.6	1885.4	1876.1	1874.4
20°	1895.7	1892.2	1888.6	1885.2	1881.7	1874.3	1863.2	1852.0	1840.8	1829.6	1827.9
22.5°	1855.4	1851.9	1848.4	1844.9	1841.4	1833.8	1822.0	1810.3	1798.5	1786.8	1783.3
25°	1794.9	1789.7	1784.4	1779.2	1773.9	1764.8	1751.9	1739.0	1726.0	1713.0	1708.5
27.5°	1725.7	1719.3	1712.9	1706.6	1700.2	1690.1	1676.2	1662.3	1648.5	1634.7	1628.3
30°	1675.3	1668.6	1661.9	1655.4	1648.7	1638.0	1623.3	1608.6	1593.9	1579.2	1571.1
32.5°	1626.2	1618.4	1610.6	1602.9	1595.1	1583.7	1568.7	1553.8	1538.7	1523.8	1514.9
35°	1546.2	1537.7	1529.3	1521.0	1512.6	1500.5	1484.7	1469.1	1453.3	1437.5	1427.3
37.5°	1467.7	1457.5	1447.3	1437.1	1426.8	1413.6	1397.5	1381.2	1364.9	1348.7	1336.6
40°	1412.3	1401.8	1391.3	1380.8	1370.4	1356.7	1339.9	1323.1	1306.3	1289.5	1276.3
42.5°	1354.4	1343.6	1332.8	1322.0	1311.3	1297.2	1279.9	1262.5	1245.2	1227.8	1215.1
45°	1265.9	1255.8	1245.6	1235.5	1225.3	1210.6	1191.3	1172.2	1152.9	1133.7	1119.6
47.5°	1174.3	1163.6	1152.9	1142.2	1131.5	1116.4	1097.0	1077.6	1058.2	1038.8	1024.4
50°	1116.3	1104.8	1093.2	1081.7	1070.2	1054.4	1034.4	1014.5	994.5	974.6	959.9
52.5°	1053.3	1041.5	1029.7	1017.8	1006.0	990.7	971.9	953.1	934.2	915.4	899.6
55°	960.5	949.3	938.1	926.9	915.6	900.3	880.7	861.1	841.5	821.9	806.2
57.5°	866.6	854.6	842.6	830.7	818.7	803.3	784.5	765.5	746.6	727.7	712.4
60°	806.2	793.9	781.6	769.4	757.2	741.5	722.7	703.8	684.9	666.0	650.7
62.5°	741.9	730.2	718.5	706.8	695.2	679.7	660.6	641.4	622.2	603.0	588.8
65°	650.3	638.3	626.5	614.6	602.7	587.4	569.0	550.4	531.8	513.3	499.3
67.5°	559.3	547.3	535.4	523.6	511.7	496.9	479.1	461.3	443.5	425.8	412.9
70°	497.6	485.6	473.7	461.8	450.0	435.3	417.8	400.3	382.7	365.3	354.5
72.5°	437.1	425.5	413.8	402.2	390.6	376.6	360.2	343.9	327.5	311.1	301.1
75°	346.4	335.9	325.4	314.9	304.4	291.9	277.1	262.5	247.7	233.0	225.3
77.5°	256.3	247.9	239.5	231.2	222.8	212.7	200.9	189.1	177.4	165.6	160.3
80°	204.7	196.3	187.9	179.5	171.1	162.0	152.2	142.4	132.6	122.8	119.7
82.5°	154.3	146.7	139.2	131.6	124.1	116.9	110.2	103.5	96.7	90.1	88.6
85°	86.6	80.3	74.0	67.7	61.4	57.4	55.6	53.9	52.1	50.4	50.0
87.5°	29.1	27.4	25.7	24.0	22.4	21.6	21.5	21.5	21.4	21.4	21.6
90°	0.8	1.6	3.1	4.7	6.4	7.9	8.7	10.3	11.0	12.6	13.4
92.5°	9.6	11.7	18.3	28.1	41.7	64.7	107.9	180.2	258.6	254.6	206.1
95°	26.1	26.9	33.1	41.8	59.2	94.7	179.3	352.9	570.9	699.6	684.6
97.5°	43.2	44.2	48.7	57.4	72.9	98.6	154.4	281.8	509.8	747.1	866.2
100°	55.2	56.9	60.0	68.7	83.7	107.3	153.2	255.8	454.8	713.1	910.4
102.5°	68.6	69.5	72.0	81.3	95.0	118.2	158.9	245.1	413.1	653.0	883.9
105°	89.3	89.3	93.2	101.1	113.7	135.8	170.6	240.9	372.7	572.5	799.1
107.5°	109.5	111.0	114.8	121.3	134.4	154.3	187.9	248.1	355.7	517.1	712.6
110°	124.0	125.5	128.7	135.8	147.6	168.1	200.6	255.1	350.6	491.1	663.3



TEST NUMBER: P333627-840

CATALOG NUMBER: S125RDIP-S1270D810U840-4F0-1E-UDD-F4

CANDELA DISTRIBUTION (continued):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	138.5	140.1	142.6	149.7	161.6	181.5	212.6	263.9	350.6	475.9	626.6
115°	159.5	161.1	163.5	170.6	182.4	202.2	231.4	277.1	352.9	459.6	586.6
117.5°	178.4	180.9	183.4	190.5	203.9	223.0	250.6	292.4	358.2	451.5	562.8
120°	191.1	193.5	196.6	203.7	217.1	236.9	264.5	302.5	363.2	447.7	549.6
122.5°	204.4	206.1	208.6	215.7	230.5	250.1	277.8	313.8	367.6	444.5	538.2
125°	221.1	222.7	226.6	233.7	248.7	269.2	295.3	329.2	375.1	440.6	522.7
127.5°	234.2	236.6	241.7	250.6	266.6	287.1	312.3	343.5	383.4	438.7	508.5
130°	242.4	244.8	251.1	261.4	277.9	298.5	323.0	352.9	388.5	437.5	499.1
132.5°	248.7	251.8	259.3	270.8	288.0	308.6	333.1	361.1	394.2	437.5	491.5
135°	259.0	262.2	271.7	284.3	300.8	322.1	346.7	372.7	401.9	437.5	482.4
137.5°	272.0	274.3	283.2	295.8	312.0	334.0	356.3	381.2	409.0	438.4	474.4
140°	279.5	281.9	291.3	304.0	319.0	340.3	363.2	386.9	412.1	439.0	470.6
142.5°	288.3	290.1	298.9	311.5	326.0	346.0	367.6	390.1	414.0	439.7	467.5
145°	301.6	303.2	311.1	322.1	336.4	354.6	375.1	394.8	416.2	439.0	462.7
147.5°	315.5	316.5	323.3	333.6	345.9	361.8	379.8	397.7	416.9	437.0	457.8
150°	323.8	325.3	330.8	341.1	352.1	365.6	382.9	399.5	416.9	435.0	454.0
152.5°	332.5	333.6	338.4	347.4	357.9	370.0	386.1	400.8	416.3	432.5	449.6
155°	344.3	344.3	349.0	356.9	364.8	375.9	389.3	401.9	414.5	428.0	442.2
157.5°	354.7	354.6	358.3	365.1	372.0	380.4	391.9	402.7	412.5	423.2	435.3
160°	361.6	360.8	364.1	369.5	375.9	382.9	393.2	402.7	410.6	420.1	429.6
162.5°	367.3	366.6	369.7	374.6	379.6	385.5	394.5	402.0	408.7	416.3	424.4
165°	375.9	374.3	376.7	380.6	383.7	388.5	394.8	401.1	405.9	410.6	416.9
167.5°	381.5	380.7	382.1	384.4	386.6	389.6	394.8	399.2	401.4	405.1	409.5
170°	385.4	384.6	385.4	386.9	388.5	390.8	394.8	398.0	399.5	401.9	405.1
172.5°	387.9	386.5	387.2	388.8	389.7	390.8	394.2	396.7	397.0	398.1	400.6
175°	390.8	389.3	390.1	390.8	390.8	390.8	393.2	394.8	394.0	394.0	394.8
177.5°	392.2	391.0	391.0	391.6	391.0	391.0	392.2	392.9	391.6	391.6	392.2
180°	391.6	391.6	391.6	391.6	391.6	391.6	391.6	391.6	391.6	391.6	391.6



TEST NUMBER: P333627-840

CATALOG NUMBER: S125RDIP-S1270D810U840-4F0-1E-UDD-F4

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°
0°	2084.7	2084.7	2084.7	2084.7	2084.7	2084.7	2084.7	2084.7
2.5°	2077.6	2080.4	2083.3	2084.5	2084.3	2084.0	2083.7	2083.4
5°	2064.9	2068.4	2071.8	2073.3	2072.5	2071.8	2071.1	2070.4
7.5°	2039.1	2041.6	2044.1	2044.9	2044.1	2043.4	2042.6	2041.8
10°	2017.4	2018.5	2019.5	2019.5	2018.5	2017.4	2016.4	2015.4
12.5°	1986.7	1987.4	1988.2	1987.8	1986.2	1984.6	1983.0	1981.4
15°	1935.9	1935.6	1935.2	1933.5	1930.4	1927.2	1924.0	1920.9
17.5°	1872.7	1870.9	1869.2	1867.0	1864.4	1861.8	1859.3	1856.6
20°	1826.0	1824.3	1822.6	1820.1	1816.9	1813.8	1810.7	1807.6
22.5°	1779.9	1776.5	1773.0	1770.0	1767.5	1764.8	1762.2	1759.7
25°	1703.9	1699.4	1694.9	1690.6	1686.8	1682.9	1679.1	1675.3
27.5°	1621.9	1615.6	1609.2	1604.2	1600.4	1596.7	1593.0	1589.3
30°	1563.2	1555.1	1547.0	1541.5	1538.3	1535.1	1532.0	1528.8
32.5°	1506.0	1497.1	1488.2	1481.8	1477.8	1473.8	1469.9	1465.8
35°	1417.2	1407.0	1396.9	1389.4	1384.5	1379.6	1374.7	1369.8
37.5°	1324.3	1312.2	1300.0	1291.5	1286.8	1282.0	1277.3	1272.5
40°	1262.9	1249.6	1236.4	1227.6	1223.4	1219.2	1215.0	1210.8
42.5°	1202.3	1189.6	1176.9	1167.4	1161.2	1155.1	1148.9	1142.8
45°	1105.6	1091.7	1077.6	1068.0	1062.8	1057.5	1052.3	1047.0
47.5°	1010.1	995.6	981.2	971.1	965.2	959.5	953.6	947.9
50°	945.2	930.5	915.8	905.8	900.6	895.3	890.1	884.8
52.5°	883.7	868.0	852.1	841.6	836.4	831.1	825.9	820.6
55°	790.4	774.7	758.9	748.2	742.7	737.0	731.4	725.9
57.5°	696.9	681.6	666.1	656.0	651.0	646.0	641.1	636.1
60°	635.2	619.9	604.4	594.1	588.9	583.6	578.3	573.1
62.5°	574.5	560.2	545.9	536.1	530.9	525.6	520.4	515.1
65°	485.3	471.3	457.3	447.7	442.4	437.2	431.9	426.7
67.5°	400.1	387.3	374.6	366.0	361.8	357.6	353.5	349.2
70°	343.6	332.8	321.9	314.4	310.1	306.0	301.7	297.6
72.5°	291.1	281.1	271.0	264.7	261.9	259.1	256.3	253.5
75°	217.6	210.0	202.3	197.1	194.7	192.3	189.9	187.3
77.5°	154.8	149.5	144.1	140.5	138.7	136.8	135.0	133.2
80°	116.5	113.4	110.2	108.3	107.6	106.8	106.2	105.5
82.5°	87.2	85.6	84.2	83.2	82.8	82.4	82.0	81.6
85°	49.7	49.4	49.0	48.7	48.3	48.0	47.6	47.3
87.5°	21.7	21.9	22.0	22.2	21.9	21.7	21.5	21.3
90°	14.2	15.0	15.8	17.4	17.4	17.4	18.2	18.2
92.5°	140.0	101.6	76.4	64.7	54.6	52.7	51.6	50.4
95°	567.7	447.7	350.6	284.3	228.2	204.5	198.2	185.5
97.5°	845.6	761.3	666.7	574.5	525.7	481.5	458.6	448.5
100°	971.2	932.5	851.2	769.1	714.6	657.7	628.5	615.9
102.5°	1013.5	1037.4	998.4	942.8	884.5	844.0	812.3	802.8
105°	988.6	1096.8	1131.6	1122.9	1097.5	1071.5	1055.7	1046.2
107.5°	899.5	1043.9	1133.1	1174.3	1187.1	1186.9	1181.7	1175.4
110°	833.8	983.8	1095.2	1162.3	1197.8	1212.8	1218.4	1218.4



TEST NUMBER: P333627-840

CATALOG NUMBER: S125RDIP-S1270D810U840-4F0-1E-UDD-F4

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°
112.5°	782.0	924.4	1037.0	1116.2	1168.1	1193.9	1207.6	1213.4
115°	717.0	839.4	947.6	1033.6	1095.2	1133.1	1155.2	1165.5
117.5°	675.0	780.4	873.6	952.6	1014.2	1053.3	1075.3	1081.6
120°	652.2	747.0	833.8	903.3	961.7	999.7	1021.0	1027.2
122.5°	635.2	723.0	800.3	865.5	917.6	952.3	973.6	979.3
125°	610.4	690.9	759.6	816.5	860.7	893.0	910.4	918.3
127.5°	585.1	660.2	724.4	777.6	817.7	846.3	862.7	866.2
130°	569.3	638.8	700.3	751.7	791.2	817.3	833.0	837.8
132.5°	553.5	618.5	674.5	723.9	763.4	789.4	804.0	809.3
135°	533.0	587.4	638.0	683.0	717.7	743.8	758.0	762.8
137.5°	515.6	559.7	601.7	639.9	671.1	694.7	707.8	713.1
140°	506.1	543.2	579.6	612.7	642.0	662.5	674.3	678.2
142.5°	498.0	529.4	560.6	589.4	614.2	631.6	642.8	646.0
145°	487.2	511.7	536.1	557.4	576.4	589.9	598.5	601.7
147.5°	477.1	497.0	515.7	531.9	546.8	557.6	562.7	564.1
150°	471.4	488.8	503.7	518.0	529.9	539.3	542.5	543.2
152.5°	465.0	480.6	494.3	505.3	515.3	522.9	526.0	526.8
155°	455.7	468.3	479.3	488.0	495.8	501.4	503.7	504.5
157.5°	446.2	456.6	465.0	471.9	478.1	482.6	484.8	484.6
160°	439.8	447.7	455.7	461.1	466.7	470.6	472.2	471.4
162.5°	432.8	440.1	446.8	451.6	456.0	459.2	459.6	459.4
165°	423.2	428.8	433.5	437.5	440.6	442.2	442.2	442.2
167.5°	414.0	417.7	421.3	424.1	425.8	427.2	426.6	426.4
170°	409.0	411.4	413.7	415.4	416.9	417.7	417.7	416.9
172.5°	403.3	405.7	407.5	408.4	408.7	410.1	408.9	408.1
175°	397.2	397.2	398.8	398.8	398.8	399.5	398.0	397.2
177.5°	392.9	393.5	393.5	393.5	392.9	393.5	391.6	391.6
180°	391.6	391.6	391.6	391.6	391.6	391.6	391.6	391.6

(END OF REPORT)