

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P333514-840

Luminaire Tested: **S125RDIP-S375D1205U840-4F0-1E-UDD-A**

Issue Date: 3/3/2020

Test Information

Test Method: LM-79-08
Report Number: P333514-840
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-7,
Test Lab: INNOVATION CENTER
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: NEO-RAY
Catalog Number: S125RDIP-S375D1205U840-4F0-1E-UDD-A
Description: DEFINE 5 DIRECT-INDIRECT PENDANT LED LUMINAIRE
DOWNLIGHT 375 LUMENS PER FOOT, ASYMMETRIC DIFFUSER, REGRESSED HOUSING
UPLIGHT 1205 LUMENS PER FOOT, NO LENS
Light Source: -
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 6337.9 lumens
Efficiency: N/A
Efficacy: 150.2 lumens/watt
Spacing Criteria (0/90/45): 1.4 / 1.22 / 1.47
Luminous Opening: Rectangular (W 4' x L: 0.42' x H: 0')
CIE Type: Semi-Indirect


Input Watts (W): 42.2
Input Voltage (V): 120
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P333514-840

CATALOG NUMBER: S125RDIP-S375D1205U840-4F0-1E-UDD-A

Luminous Intensity Polar Plot





TEST NUMBER: P333514-840

CATALOG NUMBER: S125RDIP-S375D1205U840-4F0-1E-UDD-A

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	101	101	101	101	90	90	90	90	68	68	68	49	49	49	32	32	32	23
1	92	88	84	81	82	78	75	73	60	58	56	43	42	41	28	28	27	20
2	84	77	71	66	74	69	64	60	53	50	47	38	36	35	25	24	23	17
3	77	68	61	55	68	60	55	50	47	43	40	34	32	29	22	21	20	15
4	70	60	52	47	62	53	47	42	41	37	34	30	28	25	20	18	17	13
5	64	53	46	40	57	48	41	36	37	32	29	27	24	22	18	16	15	11
6	59	48	40	34	52	43	36	31	33	29	25	25	21	19	16	15	13	10
7	54	43	35	30	48	38	32	27	30	25	22	22	19	17	15	13	12	9
8	50	39	31	26	45	35	28	24	27	23	19	20	17	15	14	12	10	8
9	47	35	28	23	42	32	25	21	25	20	17	19	15	13	13	11	9	7
10	44	32	25	21	39	29	23	19	23	18	15	17	14	12	12	10	8	6

AVERAGE LUMINANCE (cd/sqm):

	0°	90°	180°	270°
0°	3672	3672	3672	3672
5°	4224	3676	3247	3676
10°	4845	3657	2865	3657
15°	5233	3620	2546	3620
20°	5770	3577	2351	3577
25°	6678	3518	2182	3518
30°	7267	3457	2071	3457
35°	6130	3387	1968	3387
40°	4281	3260	1881	3260
45°	3176	3088	1795	3088
50°	2533	2910	1721	2910
55°	2149	2688	1655	2688
60°	1856	2490	1550	2490
65°	1655	2275	1334	2275
70°	1456	2085	1216	2085
75°	1258	1804	1140	1804
80°	956	1517	956	1517
85°	793	1193	897	1193



TEST NUMBER: P333514-840

CATALOG NUMBER: S125RDIP-S375D1205U840-4F0-1E-UDD-A

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	54.5	0.9
10°-20°	159.7	2.5
20°-30°	253.3	4.0
30°-40°	305.4	4.8
40°-50°	272.8	4.3
50°-60°	209.2	3.3
60°-70°	135.9	2.1
70°-80°	66.1	1.0
80°-90°	19.1	0.3
90°-100°	57.5	0.9
100°-110°	354.6	5.6
110°-120°	643.1	10.1
120°-130°	825.3	13.0
130°-140°	887.7	14.0
140°-150°	833.2	13.1
150°-160°	674.0	10.6
160°-170°	435.9	6.9
170°-180°	150.4	2.4
0°-30°	467.5	7.4
0°-40°	773.0	12.2
0°-60°	1254.9	19.8
0°-90°	1476.0	23.3
90°-120°	1055.2	16.6
90°-150°	3601.6	56.8
90°-180°	4862.0	76.7
0°-180°	6337.9	100.0

CANDELA DISTRIBUTION:

	0°	90°	180°	270°	360°	Flux
0°	568	568	568	568	568	
5°	652	567	501	567	652	65
15°	783	541	381	541	783	224
25°	937	494	306	494	937	430
35°	778	430	250	430	778	470
45°	348	338	196	338	348	277
55°	191	239	147	239	191	173
65°	108	149	87	149	108	108
75°	50	72	46	72	50	54
85°	11	16	12	16	11	13
90°	28	1	28	1	28	13
95°	25	67	25	67	25	20
105°	349	345	349	345	349	315
115°	643	648	643	648	643	638
125°	921	921	921	921	921	820
135°	1144	1149	1144	1149	1144	883
145°	1329	1332	1329	1332	1329	830
155°	1456	1467	1456	1467	1456	671
165°	1540	1548	1540	1548	1540	435
175°	1576	1583	1576	1583	1576	150
180°	1583	1583	1583	1583	1583	



TEST NUMBER: P333514-840

CATALOG NUMBER: S125RDIP-S375D1205U840-4F0-1E-UDD-A

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	568.5	568.5	568.5	568.5	568.5	568.5	568.5	568.5	568.5	568.5	568.5
2.5°	597.9	597.5	598.3	596.2	596.4	593.3	593.3	590.9	587.6	585.2	584.1
5°	651.5	652.0	651.1	647.5	645.2	641.7	637.7	630.8	624.9	619.2	614.9
7.5°	706.7	707.0	703.9	702.9	696.9	692.7	683.9	674.3	665.9	655.1	646.9
10°	738.8	738.5	735.3	732.7	727.6	721.0	712.4	701.3	690.7	679.0	667.8
12.5°	757.4	756.8	755.8	752.7	747.9	742.1	734.8	723.8	710.8	698.1	685.0
15°	782.6	781.0	778.0	774.0	767.2	760.4	752.3	742.6	730.1	715.7	703.6
17.5°	813.9	813.9	809.2	803.7	794.5	782.5	769.9	754.2	737.3	721.4	708.5
20°	839.6	838.9	834.2	823.4	812.9	798.0	783.6	764.2	743.7	722.9	706.8
22.5°	876.6	874.7	869.9	855.8	839.5	820.2	798.1	774.5	749.6	726.1	704.9
25°	937.2	935.7	926.1	909.8	887.0	857.3	828.4	796.0	760.2	729.2	703.6
27.5°	978.6	977.0	969.9	956.3	935.2	904.0	864.9	821.5	777.0	734.3	697.3
30°	974.4	978.0	977.0	970.7	954.8	926.9	890.7	841.9	788.9	738.8	694.7
32.5°	915.8	919.0	927.2	939.6	940.5	929.3	902.2	857.2	802.3	745.3	692.6
35°	777.5	781.7	797.6	822.5	855.3	882.5	888.1	863.8	814.6	753.3	689.5
37.5°	597.7	620.7	634.1	660.4	709.7	759.9	808.2	826.0	805.1	749.9	684.6
40°	507.8	513.3	537.1	566.8	608.3	660.6	729.4	779.1	780.7	742.6	676.7
42.5°	434.5	441.7	458.0	481.7	517.3	569.5	640.6	706.2	736.5	722.0	666.4
45°	347.7	353.0	365.0	383.1	410.4	453.6	514.7	590.6	650.8	674.4	638.9
47.5°	285.6	288.5	298.8	312.8	333.0	364.4	411.7	477.6	549.8	600.4	595.4
50°	252.1	255.3	263.2	273.7	290.7	317.3	355.2	410.0	484.4	546.2	558.7
52.5°	225.9	228.6	233.6	243.5	257.5	277.9	308.5	358.1	425.1	490.8	519.5
55°	190.9	192.8	196.7	202.3	213.5	228.2	254.6	288.9	343.1	409.3	451.3
57.5°	162.1	163.0	165.5	170.7	178.4	189.1	208.2	237.2	276.1	335.8	382.1
60°	143.7	144.7	147.9	151.5	157.5	167.3	182.3	202.6	239.8	289.1	336.0
62.5°	129.2	129.8	131.2	134.6	140.0	147.5	159.3	175.8	205.5	248.8	293.1
65°	108.3	108.5	109.0	111.8	115.0	120.7	128.4	140.0	162.4	195.1	234.3
67.5°	88.2	88.6	90.2	91.2	94.5	97.5	102.0	110.9	126.7	148.8	179.3
70°	77.1	76.7	78.4	79.6	80.7	84.2	87.3	94.5	104.3	121.1	146.5
72.5°	66.6	65.9	66.7	67.1	68.6	71.0	74.0	78.5	86.0	97.6	117.0
75°	50.4	50.6	50.6	51.1	52.3	53.2	54.1	56.5	60.7	68.4	78.9
77.5°	35.3	35.0	36.0	36.2	36.9	37.9	38.7	39.6	41.3	44.4	49.9
80°	25.7	25.7	25.9	26.6	26.4	26.9	28.0	29.0	31.0	32.9	34.7
82.5°	19.7	19.5	19.7	19.9	19.8	20.3	20.7	20.9	21.7	22.6	23.9
85°	10.7	10.7	11.0	11.0	11.2	11.2	11.4	11.4	11.4	11.7	11.9
87.5°	9.7	9.4	9.1	8.9	8.9	9.1	8.7	8.2	8.0	7.7	7.5
90°	28.2	27.4	26.6	25.9	25.0	24.0	22.7	21.4	20.1	18.8	17.0
92.5°	26.3	26.0	25.5	25.1	24.8	24.0	22.7	21.4	20.1	18.8	17.2
95°	24.6	24.6	24.6	24.6	24.6	24.0	22.7	21.4	20.1	18.8	28.7
97.5°	24.6	24.6	24.6	24.6	24.6	28.3	35.6	43.0	50.4	57.8	77.4
100°	24.6	25.7	26.8	27.8	28.8	48.8	87.7	126.5	165.3	204.2	203.2
102.5°	147.6	165.4	183.1	200.9	218.6	231.2	238.5	245.8	253.2	260.5	259.9
105°	348.6	348.8	349.1	349.3	349.6	349.7	349.7	349.7	349.7	349.7	349.7
107.5°	439.4	440.2	441.0	441.7	442.5	442.9	442.8	442.8	442.7	442.7	442.2
110°	502.3	502.1	501.8	501.5	501.3	501.5	502.3	503.1	503.9	504.6	504.1



TEST NUMBER: P333514-840

CATALOG NUMBER: S125RDIP-S375D1205U840-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	558.7	559.1	559.4	559.8	560.1	560.8	561.8	562.8	563.8	564.7	564.4
115°	643.2	644.7	646.3	647.8	649.4	650.8	651.8	652.8	653.9	654.9	654.6
117.5°	733.3	734.0	734.7	735.3	736.0	737.0	738.4	739.7	741.1	742.5	741.4
120°	788.7	790.0	791.3	792.6	794.0	794.9	795.4	795.9	796.4	796.9	796.1
122.5°	841.3	842.8	844.2	845.8	847.3	848.4	848.9	849.4	849.9	850.4	850.1
125°	921.3	922.1	922.9	923.6	924.4	925.3	926.3	927.5	928.5	929.5	929.5
127.5°	988.7	990.6	992.5	994.5	996.4	997.6	998.3	998.8	999.4	1000.0	1000.1
130°	1037.5	1038.8	1040.2	1041.4	1042.7	1043.8	1044.5	1045.3	1046.1	1046.9	1046.6
132.5°	1082.6	1083.9	1085.2	1086.5	1087.8	1088.5	1088.6	1088.8	1089.0	1089.1	1089.7
135°	1144.3	1145.9	1147.4	1149.0	1150.5	1151.7	1152.2	1152.7	1153.2	1153.7	1154.2
137.5°	1206.3	1207.6	1209.0	1210.3	1211.7	1212.3	1212.2	1212.1	1212.0	1211.9	1212.3
140°	1242.9	1244.5	1246.1	1247.6	1249.1	1249.7	1249.1	1248.6	1248.1	1247.6	1247.9
142.5°	1277.7	1279.2	1280.8	1282.3	1283.9	1284.6	1284.5	1284.4	1284.3	1284.2	1283.8
145°	1328.6	1330.1	1331.7	1333.2	1334.8	1335.4	1335.2	1334.9	1334.7	1334.4	1334.4
147.5°	1370.6	1372.5	1374.3	1376.2	1378.1	1378.9	1378.6	1378.3	1378.0	1377.7	1377.4
150°	1397.9	1399.9	1402.0	1404.1	1406.1	1406.9	1406.4	1405.9	1405.3	1404.8	1404.3
152.5°	1423.2	1425.0	1426.9	1428.8	1430.7	1431.4	1430.9	1430.3	1429.8	1429.3	1428.8
155°	1456.5	1458.5	1460.7	1462.8	1464.8	1465.5	1464.7	1463.9	1463.2	1462.4	1461.9
157.5°	1484.4	1486.5	1488.6	1490.7	1492.8	1493.4	1492.6	1491.8	1490.9	1490.1	1490.1
160°	1502.3	1504.4	1506.4	1508.5	1510.7	1511.2	1510.1	1509.0	1508.0	1506.9	1506.7
162.5°	1518.2	1520.6	1522.8	1525.1	1527.4	1527.8	1526.4	1524.9	1523.5	1522.0	1521.8
165°	1539.8	1541.9	1544.0	1546.1	1548.1	1548.4	1546.9	1545.3	1543.8	1542.2	1541.9
167.5°	1554.9	1557.2	1559.5	1561.9	1564.3	1564.5	1562.6	1560.7	1558.8	1557.0	1556.7
170°	1563.3	1565.7	1568.0	1570.3	1572.7	1572.9	1570.7	1568.6	1566.6	1564.5	1564.2
172.5°	1568.9	1571.2	1573.7	1576.0	1578.3	1578.5	1576.7	1574.8	1573.0	1571.0	1570.5
175°	1576.2	1578.5	1580.9	1583.3	1585.6	1585.7	1583.7	1581.5	1579.4	1577.4	1577.1
177.5°	1580.4	1582.1	1583.8	1585.5	1587.1	1587.2	1585.8	1584.3	1582.9	1581.3	1581.1
180°	1583.3	1583.3	1583.3	1583.3	1583.3	1583.3	1583.3	1583.3	1583.3	1583.3	1583.3



TEST NUMBER: P333514-840

CATALOG NUMBER: S125RDIP-S375D1205U840-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°	95°	100°	105°
0°	568.5	568.5	568.5	568.5	568.5	568.5	568.5	568.5	568.5	568.5	568.5
2.5°	584.1	582.8	580.4	578.1	575.3	572.9	571.2	569.2	566.5	563.4	560.8
5°	610.0	604.8	598.0	592.2	584.7	579.0	572.9	567.0	561.2	553.7	547.1
7.5°	638.6	628.0	617.7	604.7	593.0	582.5	572.4	562.2	552.2	541.6	531.4
10°	656.2	643.3	629.1	612.8	597.8	583.6	570.6	557.6	544.1	532.3	519.5
12.5°	672.6	656.0	639.7	619.1	601.2	583.8	567.1	551.2	536.7	521.3	507.5
15°	687.4	671.1	652.9	627.7	602.7	581.7	562.1	541.4	523.4	506.1	490.7
17.5°	693.2	676.0	654.9	630.7	603.4	576.9	551.7	529.0	507.8	487.7	470.4
20°	690.9	674.4	652.7	629.5	600.4	572.9	545.5	520.4	496.8	475.5	457.2
22.5°	685.5	668.4	647.4	623.0	595.3	566.1	536.9	510.1	485.4	463.4	443.3
25°	677.4	654.1	632.6	608.7	582.4	553.5	523.4	493.7	467.4	444.9	423.0
27.5°	668.9	639.9	612.5	588.9	561.0	535.2	506.1	475.7	448.1	425.3	402.7
30°	661.3	628.6	598.5	571.7	545.3	520.8	493.3	463.6	435.2	411.6	388.8
32.5°	651.8	617.0	584.0	553.0	527.6	503.3	478.4	450.0	422.3	398.0	374.8
35°	639.9	595.5	559.6	526.6	498.5	474.8	452.4	429.6	401.8	376.6	354.0
37.5°	624.2	573.8	532.3	496.4	466.7	443.0	425.3	404.3	379.0	355.0	334.0
40°	614.6	558.2	512.7	477.2	446.0	420.9	404.3	386.7	363.6	340.9	319.9
42.5°	602.0	543.8	492.9	456.0	424.4	400.4	383.6	368.2	348.8	327.5	305.0
45°	577.0	515.9	462.5	422.8	391.1	367.5	351.8	338.1	323.5	303.8	284.2
47.5°	544.7	486.9	430.9	387.6	356.6	334.7	319.5	308.6	298.1	281.4	262.5
50°	518.8	462.9	408.4	366.4	333.3	312.5	298.2	289.6	280.0	264.9	248.9
52.5°	488.1	438.3	384.9	341.9	310.6	291.1	277.5	268.8	260.9	248.6	233.5
55°	439.9	396.2	347.2	308.2	279.5	259.9	246.9	238.7	234.1	223.6	211.7
57.5°	384.2	352.9	309.7	272.2	246.7	227.4	217.8	210.9	205.6	198.1	189.8
60°	345.4	323.5	284.7	248.9	225.6	207.2	198.5	192.8	187.8	181.6	175.0
62.5°	306.0	290.0	256.3	225.6	204.2	188.7	180.7	175.4	169.8	165.5	159.2
65°	253.2	238.9	215.6	191.6	171.8	159.4	153.5	148.9	145.4	140.7	136.2
67.5°	196.9	191.2	175.0	158.4	144.2	133.2	128.2	124.9	120.8	118.0	114.9
70°	162.4	159.6	148.1	137.2	123.9	116.4	111.8	110.4	105.2	102.4	100.4
72.5°	131.8	130.5	123.9	116.3	106.9	100.4	96.1	94.5	91.2	89.0	87.7
75°	90.3	90.8	89.6	84.7	81.2	77.1	73.3	72.3	70.0	68.2	67.0
77.5°	57.2	59.5	59.6	59.4	58.0	55.4	53.8	53.1	50.9	50.2	49.9
80°	39.2	41.8	44.1	43.8	43.4	42.7	41.5	40.8	39.7	39.0	38.5
82.5°	26.2	28.5	30.5	31.7	31.6	30.9	30.2	29.8	29.6	29.1	29.0
85°	12.3	12.8	13.5	15.1	16.4	16.6	16.4	16.1	15.5	15.7	15.9
87.5°	7.3	7.0	6.8	6.4	5.8	6.3	6.5	6.2	6.3	6.3	6.4
90°	15.1	13.3	11.5	9.5	7.5	5.4	3.2	1.2	3.2	5.4	7.5
92.5°	15.6	13.9	12.3	12.2	13.7	15.1	16.7	18.1	16.7	15.1	13.7
95°	38.6	48.5	58.5	63.7	64.5	65.3	66.1	66.9	66.1	65.3	64.5
97.5°	96.9	116.5	136.2	145.3	143.9	142.5	141.1	139.7	141.1	142.5	143.9
100°	202.2	201.1	200.1	199.1	198.3	197.5	196.8	196.0	196.8	197.5	198.3
102.5°	259.3	258.6	258.0	257.2	256.2	255.3	254.3	253.3	254.3	255.3	256.2
105°	349.7	349.7	349.7	349.2	348.2	347.1	346.1	345.1	346.1	347.1	348.2
107.5°	441.6	441.1	440.6	440.4	440.4	440.4	440.4	440.4	440.4	440.4	440.4
110°	503.6	503.1	502.6	502.3	502.3	502.3	502.3	502.3	502.3	502.3	502.3



TEST NUMBER: P333514-840

CATALOG NUMBER: S125RDIP-S375D1205U840-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°	95°	100°	105°
112.5°	564.1	563.8	563.5	563.0	562.4	561.8	561.2	560.6	561.2	561.8	562.4
115°	654.4	654.1	653.9	653.1	651.8	650.5	649.1	647.8	649.1	650.5	651.8
117.5°	740.4	739.5	738.5	738.0	738.1	738.1	738.2	738.2	738.2	738.1	738.1
120°	795.4	794.6	793.8	793.6	793.8	794.1	794.3	794.6	794.3	794.1	793.8
122.5°	849.7	849.3	849.0	848.3	847.3	846.3	845.4	844.3	845.4	846.3	847.3
125°	929.5	929.5	929.5	928.6	926.8	924.9	923.1	921.3	923.1	924.9	926.8
127.5°	1000.3	1000.4	1000.6	1000.0	998.7	997.3	996.1	994.8	996.1	997.3	998.7
130°	1046.4	1046.1	1045.8	1045.1	1043.8	1042.5	1041.2	1039.9	1041.2	1042.5	1043.8
132.5°	1090.3	1090.9	1091.5	1091.0	1089.4	1087.9	1086.4	1084.9	1086.4	1087.9	1089.4
135°	1154.8	1155.3	1155.8	1155.3	1153.7	1152.2	1150.5	1149.0	1150.5	1152.2	1153.7
137.5°	1212.8	1213.4	1213.8	1213.4	1211.9	1210.6	1209.3	1207.9	1209.3	1210.6	1211.9
140°	1248.1	1248.4	1248.6	1248.5	1248.0	1247.5	1247.0	1246.4	1247.0	1247.5	1248.0
142.5°	1283.4	1283.1	1282.7	1282.4	1282.1	1281.8	1281.4	1281.1	1281.4	1281.8	1282.1
145°	1334.4	1334.4	1334.4	1334.1	1333.6	1333.1	1332.6	1332.1	1332.6	1333.1	1333.6
147.5°	1377.0	1376.6	1376.3	1376.2	1376.3	1376.4	1376.5	1376.6	1376.5	1376.4	1376.3
150°	1403.8	1403.3	1402.8	1402.8	1403.3	1403.8	1404.3	1404.8	1404.3	1403.8	1403.3
152.5°	1428.3	1427.7	1427.1	1427.4	1428.7	1429.8	1431.0	1432.1	1431.0	1429.8	1428.7
155°	1461.3	1460.8	1460.3	1460.8	1462.4	1463.9	1465.5	1467.0	1465.5	1463.9	1462.4
157.5°	1490.0	1490.0	1489.9	1490.3	1491.3	1492.2	1493.1	1494.1	1493.1	1492.2	1491.3
160°	1506.4	1506.2	1505.9	1506.6	1508.1	1509.7	1511.3	1512.9	1511.3	1509.7	1508.1
162.5°	1521.5	1521.2	1521.0	1521.6	1523.2	1524.7	1526.3	1527.8	1526.3	1524.7	1523.2
165°	1541.7	1541.4	1541.2	1541.8	1543.4	1544.9	1546.5	1548.0	1546.5	1544.9	1543.4
167.5°	1556.4	1556.2	1555.9	1556.6	1558.2	1559.8	1561.5	1563.1	1561.5	1559.8	1558.2
170°	1564.0	1563.7	1563.5	1564.2	1566.0	1567.8	1569.7	1571.6	1569.7	1567.8	1566.0
172.5°	1570.1	1569.6	1569.1	1569.8	1571.7	1573.5	1575.3	1577.1	1575.3	1573.5	1571.7
175°	1576.9	1576.6	1576.3	1577.0	1578.5	1580.1	1581.7	1583.3	1581.7	1580.1	1578.5
177.5°	1580.9	1580.7	1580.5	1581.0	1582.4	1583.6	1584.8	1586.1	1584.8	1583.6	1582.4
180°	1583.3	1583.3	1583.3	1583.3	1583.3	1583.3	1583.3	1583.3	1583.3	1583.3	1583.3



TEST NUMBER: P333514-840

CATALOG NUMBER: S125RDIP-S375D1205U840-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	110°	115°	120°	125°	130°	135°	140°	145°	150°	155°	160°
0°	568.5	568.5	568.5	568.5	568.5	568.5	568.5	568.5	568.5	568.5	568.5
2.5°	558.9	556.3	554.4	550.7	548.1	546.9	544.9	544.3	546.4	544.9	544.7
5°	542.3	535.5	530.2	524.8	519.0	515.2	509.6	508.7	507.3	505.2	504.7
7.5°	522.4	513.5	506.6	497.8	490.1	483.8	476.9	473.5	471.7	469.0	465.3
10°	509.0	498.5	489.1	480.2	470.7	462.9	456.0	450.6	447.1	443.8	442.4
12.5°	495.6	484.9	473.0	462.3	451.6	443.0	435.3	431.7	427.9	424.0	420.8
15°	475.0	460.9	447.8	435.5	426.4	417.0	409.5	404.3	398.6	396.9	390.6
17.5°	453.2	439.3	423.9	411.0	400.4	390.1	381.9	376.1	371.7	365.7	362.8
20°	439.6	423.0	408.1	396.2	384.6	372.4	364.1	359.1	355.0	350.0	347.7
22.5°	425.1	408.9	393.5	379.6	367.8	355.8	349.8	344.8	340.0	335.5	332.3
25°	403.6	387.4	371.2	356.8	344.5	335.8	328.8	323.0	320.4	316.0	312.7
27.5°	382.5	365.2	348.5	334.1	324.4	315.8	310.0	305.5	300.8	297.0	294.1
30°	368.9	351.2	333.0	321.5	311.2	303.2	296.8	292.4	288.9	285.4	283.3
32.5°	355.3	337.0	320.8	308.5	298.8	291.8	285.3	280.9	277.3	273.5	270.9
35°	333.5	314.8	301.7	289.6	280.0	273.5	269.0	263.0	259.9	257.1	254.6
37.5°	313.2	295.8	281.7	271.0	262.7	256.2	250.4	247.2	243.5	241.0	238.8
40°	298.2	282.4	269.5	258.3	252.3	245.0	239.6	235.4	232.7	229.3	227.0
42.5°	284.8	270.0	257.5	247.5	239.9	233.8	228.6	224.4	220.9	218.5	216.6
45°	265.8	251.1	238.9	229.6	222.6	216.8	211.4	209.3	204.6	201.9	200.9
47.5°	246.1	233.0	221.3	212.7	205.5	200.0	194.9	190.7	188.0	185.3	183.8
50°	232.9	220.3	209.3	200.9	193.9	187.8	183.2	180.4	176.8	174.3	172.5
52.5°	219.6	207.9	197.0	188.9	182.9	176.8	171.6	168.8	165.5	163.9	162.6
55°	200.7	188.3	178.9	171.1	164.7	159.2	154.2	151.5	149.4	147.7	147.2
57.5°	179.3	169.5	160.8	153.6	147.0	141.8	137.4	134.8	133.0	132.7	131.3
60°	165.2	156.3	148.5	140.7	135.1	130.2	126.4	123.4	121.6	121.4	120.9
62.5°	151.2	142.7	135.3	128.6	123.5	118.9	115.2	111.9	110.8	109.6	108.6
65°	130.5	122.7	116.6	111.3	105.9	102.0	98.5	96.3	93.8	92.4	89.9
67.5°	110.1	104.1	98.3	93.7	89.5	85.7	82.8	79.7	78.0	76.9	75.0
70°	96.6	91.9	86.1	81.2	78.0	74.9	72.6	69.1	67.9	67.0	66.0
72.5°	83.9	79.8	74.9	70.9	67.7	64.8	62.1	60.5	59.3	58.4	57.9
75°	66.0	62.1	57.9	55.0	52.7	50.4	49.0	47.9	47.4	47.2	46.3
77.5°	48.5	46.4	43.0	40.8	39.3	38.3	37.1	36.5	36.4	35.3	35.0
80°	37.1	36.0	33.1	32.2	31.0	30.1	29.4	28.3	27.1	26.6	25.9
82.5°	27.6	26.5	25.2	23.8	22.8	22.2	21.6	21.1	21.3	20.6	20.3
85°	14.7	13.5	13.0	12.8	12.3	12.8	12.6	12.3	12.1	11.9	12.1
87.5°	6.6	7.0	7.2	7.9	7.7	8.3	8.5	8.6	8.8	9.1	9.1
90°	9.5	11.5	13.3	15.1	17.0	18.8	20.1	21.4	22.7	24.0	25.0
92.5°	12.2	12.3	13.9	15.6	17.2	18.8	20.1	21.4	22.7	24.0	24.8
95°	63.7	58.5	48.5	38.6	28.7	18.8	20.1	21.4	22.7	24.0	24.6
97.5°	145.3	136.2	116.5	96.9	77.4	57.8	50.4	43.0	35.6	28.3	24.6
100°	199.1	200.1	201.1	202.2	203.2	204.2	165.3	126.5	87.7	48.8	28.8
102.5°	257.2	258.0	258.6	259.3	259.9	260.5	253.2	245.8	238.5	231.2	218.6
105°	349.2	349.7	349.7	349.7	349.7	349.7	349.7	349.7	349.7	349.7	349.6
107.5°	440.4	440.6	441.1	441.6	442.2	442.7	442.7	442.8	442.8	442.9	442.5
110°	502.3	502.6	503.1	503.6	504.1	504.6	503.9	503.1	502.3	501.5	501.3



TEST NUMBER: P333514-840

CATALOG NUMBER: S125RDIP-S375D1205U840-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	110°	115°	120°	125°	130°	135°	140°	145°	150°	155°	160°
112.5°	563.0	563.5	563.8	564.1	564.4	564.7	563.8	562.8	561.8	560.8	560.1
115°	653.1	653.9	654.1	654.4	654.6	654.9	653.9	652.8	651.8	650.8	649.4
117.5°	738.0	738.5	739.5	740.4	741.4	742.5	741.1	739.7	738.4	737.0	736.0
120°	793.6	793.8	794.6	795.4	796.1	796.9	796.4	795.9	795.4	794.9	794.0
122.5°	848.3	849.0	849.3	849.7	850.1	850.4	849.9	849.4	848.9	848.4	847.3
125°	928.6	929.5	929.5	929.5	929.5	929.5	928.5	927.5	926.3	925.3	924.4
127.5°	1000.0	1000.6	1000.4	1000.3	1000.1	1000.0	999.4	998.8	998.3	997.6	996.4
130°	1045.1	1045.8	1046.1	1046.4	1046.6	1046.9	1046.1	1045.3	1044.5	1043.8	1042.7
132.5°	1091.0	1091.5	1090.9	1090.3	1089.7	1089.1	1089.0	1088.8	1088.6	1088.5	1087.8
135°	1155.3	1155.8	1155.3	1154.8	1154.2	1153.7	1153.2	1152.7	1152.2	1151.7	1150.5
137.5°	1213.4	1213.8	1213.4	1212.8	1212.3	1211.9	1212.0	1212.1	1212.2	1212.3	1211.7
140°	1248.5	1248.6	1248.4	1248.1	1247.9	1247.6	1248.1	1248.6	1249.1	1249.7	1249.1
142.5°	1282.4	1282.7	1283.1	1283.4	1283.8	1284.2	1284.3	1284.4	1284.5	1284.6	1283.9
145°	1334.1	1334.4	1334.4	1334.4	1334.4	1334.4	1334.7	1334.9	1335.2	1335.4	1334.8
147.5°	1376.2	1376.3	1376.6	1377.0	1377.4	1377.7	1378.0	1378.3	1378.6	1378.9	1378.1
150°	1402.8	1402.8	1403.3	1403.8	1404.3	1404.8	1405.3	1405.9	1406.4	1406.9	1406.1
152.5°	1427.4	1427.1	1427.7	1428.3	1428.8	1429.3	1429.8	1430.3	1430.9	1431.4	1430.7
155°	1460.8	1460.3	1460.8	1461.3	1461.9	1462.4	1463.2	1463.9	1464.7	1465.5	1464.8
157.5°	1490.3	1489.9	1490.0	1490.0	1490.1	1490.1	1490.9	1491.8	1492.6	1493.4	1492.8
160°	1506.6	1505.9	1506.2	1506.4	1506.7	1506.9	1508.0	1509.0	1510.1	1511.2	1510.7
162.5°	1521.6	1521.0	1521.2	1521.5	1521.8	1522.0	1523.5	1524.9	1526.4	1527.8	1527.4
165°	1541.8	1541.2	1541.4	1541.7	1541.9	1542.2	1543.8	1545.3	1546.9	1548.4	1548.1
167.5°	1556.6	1555.9	1556.2	1556.4	1556.7	1557.0	1558.8	1560.7	1562.6	1564.5	1564.3
170°	1564.2	1563.5	1563.7	1564.0	1564.2	1564.5	1566.6	1568.6	1570.7	1572.9	1572.7
172.5°	1569.8	1569.1	1569.6	1570.1	1570.5	1571.0	1573.0	1574.8	1576.7	1578.5	1578.3
175°	1577.0	1576.3	1576.6	1576.9	1577.1	1577.4	1579.4	1581.5	1583.7	1585.7	1585.6
177.5°	1581.0	1580.5	1580.7	1580.9	1581.1	1581.3	1582.9	1584.3	1585.8	1587.2	1587.1
180°	1583.3	1583.3	1583.3	1583.3	1583.3	1583.3	1583.3	1583.3	1583.3	1583.3	1583.3



TEST NUMBER: P333514-840

CATALOG NUMBER: S125RDIP-S375D1205U840-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	165°	170°	175°	180°	185°	190°	195°	200°	205°	210°	215°
0°	568.5	568.5	568.5	568.5	568.5	568.5	568.5	568.5	568.5	568.5	568.5
2.5°	544.5	542.5	541.9	542.7	541.9	542.5	544.5	544.7	544.9	546.4	544.3
5°	502.4	500.1	501.2	500.8	501.2	500.1	502.4	504.7	505.2	507.3	508.7
7.5°	465.3	462.4	459.4	460.3	459.4	462.4	465.3	465.3	469.0	471.7	473.5
10°	439.4	437.1	435.7	436.9	435.7	437.1	439.4	442.4	443.8	447.1	450.6
12.5°	417.6	416.2	415.0	414.4	415.0	416.2	417.6	420.8	424.0	427.9	431.7
15°	387.8	385.1	383.8	380.8	383.8	385.1	387.8	390.6	396.9	398.6	404.3
17.5°	360.4	359.5	356.5	355.2	356.5	359.5	360.4	362.8	365.7	371.7	376.1
20°	344.2	343.3	340.2	342.0	340.2	343.3	344.2	347.7	350.0	355.0	359.1
22.5°	330.7	328.7	327.7	327.2	327.7	328.7	330.7	332.3	335.5	340.0	344.8
25°	311.7	308.7	307.5	306.2	307.5	308.7	311.7	312.7	316.0	320.4	323.0
27.5°	292.8	291.1	289.6	289.2	289.6	291.1	292.8	294.1	297.0	300.8	305.5
30°	280.4	278.8	277.7	277.7	277.7	278.8	280.4	283.3	285.4	288.9	292.4
32.5°	269.4	268.2	267.0	266.8	267.0	268.2	269.4	270.9	273.5	277.3	280.9
35°	253.4	251.6	251.1	249.6	251.1	251.6	253.4	254.6	257.1	259.9	263.0
37.5°	236.7	235.2	235.2	235.0	235.2	235.2	236.7	238.8	241.0	243.5	247.2
40°	226.1	224.9	224.7	223.1	224.7	224.9	226.1	227.0	229.3	232.7	235.4
42.5°	214.7	214.1	213.3	212.6	213.3	214.1	214.7	216.6	218.5	220.9	224.4
45°	199.2	197.6	197.6	196.5	197.6	197.6	199.2	200.9	201.9	204.6	209.3
47.5°	183.3	182.1	182.2	181.0	182.2	182.1	183.3	183.8	185.3	188.0	190.7
50°	172.7	172.0	171.8	171.3	171.8	172.0	172.7	172.5	174.3	176.8	180.4
52.5°	162.1	161.7	162.6	161.6	162.6	161.7	162.1	162.6	163.9	165.5	168.8
55°	147.7	147.0	148.5	147.0	148.5	147.0	147.7	147.2	147.7	149.4	151.5
57.5°	131.3	130.6	131.9	131.2	131.9	130.6	131.3	131.3	132.7	133.0	134.8
60°	120.4	119.0	119.7	120.0	119.7	119.0	120.4	120.9	121.4	121.6	123.4
62.5°	107.6	106.6	107.2	106.1	107.2	106.6	107.6	108.6	109.6	110.8	111.9
65°	89.4	88.7	87.8	87.3	87.8	88.7	89.4	89.9	92.4	93.8	96.3
67.5°	75.1	73.4	73.3	73.7	73.3	73.4	75.1	75.0	76.9	78.0	79.7
70°	64.6	64.6	64.4	64.4	64.4	64.6	64.6	66.0	67.0	67.9	69.1
72.5°	57.4	57.2	56.8	56.6	56.8	57.2	57.4	57.9	58.4	59.3	60.5
75°	46.3	46.5	45.9	45.7	45.9	46.5	46.3	46.3	47.2	47.4	47.9
77.5°	34.1	33.1	33.6	33.1	33.6	33.1	34.1	35.0	35.3	36.4	36.5
80°	25.9	25.7	26.4	25.7	26.4	25.7	25.9	25.9	26.6	27.1	28.3
82.5°	20.5	20.3	20.6	20.1	20.6	20.3	20.5	20.3	20.6	21.3	21.1
85°	12.3	12.1	11.9	12.1	11.9	12.1	12.3	12.1	11.9	12.1	12.3
87.5°	9.5	9.4	9.6	9.7	9.6	9.4	9.5	9.1	9.1	8.8	8.6
90°	25.9	26.6	27.4	28.2	27.4	26.6	25.9	25.0	24.0	22.7	21.4
92.5°	25.1	25.5	26.0	26.3	26.0	25.5	25.1	24.8	24.0	22.7	21.4
95°	24.6	24.6	24.6	24.6	24.6	24.6	24.6	24.6	24.0	22.7	21.4
97.5°	24.6	24.6	24.6	24.6	24.6	24.6	24.6	24.6	28.3	35.6	43.0
100°	27.8	26.8	25.7	24.6	25.7	26.8	27.8	28.8	48.8	87.7	126.5
102.5°	200.9	183.1	165.4	147.6	165.4	183.1	200.9	218.6	231.2	238.5	245.8
105°	349.3	349.1	348.8	348.6	348.8	349.1	349.3	349.6	349.7	349.7	349.7
107.5°	441.7	441.0	440.2	439.4	440.2	441.0	441.7	442.5	442.9	442.8	442.8
110°	501.5	501.8	502.1	502.3	502.1	501.8	501.5	501.3	501.5	502.3	503.1



TEST NUMBER: P333514-840

CATALOG NUMBER: S125RDIP-S375D1205U840-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	165°	170°	175°	180°	185°	190°	195°	200°	205°	210°	215°
112.5°	559.8	559.4	559.1	558.7	559.1	559.4	559.8	560.1	560.8	561.8	562.8
115°	647.8	646.3	644.7	643.2	644.7	646.3	647.8	649.4	650.8	651.8	652.8
117.5°	735.3	734.7	734.0	733.3	734.0	734.7	735.3	736.0	737.0	738.4	739.7
120°	792.6	791.3	790.0	788.7	790.0	791.3	792.6	794.0	794.9	795.4	795.9
122.5°	845.8	844.2	842.8	841.3	842.8	844.2	845.8	847.3	848.4	848.9	849.4
125°	923.6	922.9	922.1	921.3	922.1	922.9	923.6	924.4	925.3	926.3	927.5
127.5°	994.5	992.5	990.6	988.7	990.6	992.5	994.5	996.4	997.6	998.3	998.8
130°	1041.4	1040.2	1038.8	1037.5	1038.8	1040.2	1041.4	1042.7	1043.8	1044.5	1045.3
132.5°	1086.5	1085.2	1083.9	1082.6	1083.9	1085.2	1086.5	1087.8	1088.5	1088.6	1088.8
135°	1149.0	1147.4	1145.9	1144.3	1145.9	1147.4	1149.0	1150.5	1151.7	1152.2	1152.7
137.5°	1210.3	1209.0	1207.6	1206.3	1207.6	1209.0	1210.3	1211.7	1212.3	1212.2	1212.1
140°	1247.6	1246.1	1244.5	1242.9	1244.5	1246.1	1247.6	1249.1	1249.7	1249.1	1248.6
142.5°	1282.3	1280.8	1279.2	1277.7	1279.2	1280.8	1282.3	1283.9	1284.6	1284.5	1284.4
145°	1333.2	1331.7	1330.1	1328.6	1330.1	1331.7	1333.2	1334.8	1335.4	1335.2	1334.9
147.5°	1376.2	1374.3	1372.5	1370.6	1372.5	1374.3	1376.2	1378.1	1378.9	1378.6	1378.3
150°	1404.1	1402.0	1399.9	1397.9	1399.9	1402.0	1404.1	1406.1	1406.9	1406.4	1405.9
152.5°	1428.8	1426.9	1425.0	1423.2	1425.0	1426.9	1428.8	1430.7	1431.4	1430.9	1430.3
155°	1462.8	1460.7	1458.5	1456.5	1458.5	1460.7	1462.8	1464.8	1465.5	1464.7	1463.9
157.5°	1490.7	1488.6	1486.5	1484.4	1486.5	1488.6	1490.7	1492.8	1493.4	1492.6	1491.8
160°	1508.5	1506.4	1504.4	1502.3	1504.4	1506.4	1508.5	1510.7	1511.2	1510.1	1509.0
162.5°	1525.1	1522.8	1520.6	1518.2	1520.6	1522.8	1525.1	1527.4	1527.8	1526.4	1524.9
165°	1546.1	1544.0	1541.9	1539.8	1541.9	1544.0	1546.1	1548.1	1548.4	1546.9	1545.3
167.5°	1561.9	1559.5	1557.2	1554.9	1557.2	1559.5	1561.9	1564.3	1564.5	1562.6	1560.7
170°	1570.3	1568.0	1565.7	1563.3	1565.7	1568.0	1570.3	1572.7	1572.9	1570.7	1568.6
172.5°	1576.0	1573.7	1571.2	1568.9	1571.2	1573.7	1576.0	1578.3	1578.5	1576.7	1574.8
175°	1583.3	1580.9	1578.5	1576.2	1578.5	1580.9	1583.3	1585.6	1585.7	1583.7	1581.5
177.5°	1585.5	1583.8	1582.1	1580.4	1582.1	1583.8	1585.5	1587.1	1587.2	1585.8	1584.3
180°	1583.3	1583.3	1583.3	1583.3	1583.3	1583.3	1583.3	1583.3	1583.3	1583.3	1583.3



TEST NUMBER: P333514-840

CATALOG NUMBER: S125RDIP-S375D1205U840-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	220°	225°	230°	235°	240°	245°	250°	255°	260°	265°	270°
0°	568.5	568.5	568.5	568.5	568.5	568.5	568.5	568.5	568.5	568.5	568.5
2.5°	544.9	546.9	548.1	550.7	554.4	556.3	558.9	560.8	563.4	566.5	569.2
5°	509.6	515.2	519.0	524.8	530.2	535.5	542.3	547.1	553.7	561.2	567.0
7.5°	476.9	483.8	490.1	497.8	506.6	513.5	522.4	531.4	541.6	552.2	562.2
10°	456.0	462.9	470.7	480.2	489.1	498.5	509.0	519.5	532.3	544.1	557.6
12.5°	435.3	443.0	451.6	462.3	473.0	484.9	495.6	507.5	521.3	536.7	551.2
15°	409.5	417.0	426.4	435.5	447.8	460.9	475.0	490.7	506.1	523.4	541.4
17.5°	381.9	390.1	400.4	411.0	423.9	439.3	453.2	470.4	487.7	507.8	529.0
20°	364.1	372.4	384.6	396.2	408.1	423.0	439.6	457.2	475.5	496.8	520.4
22.5°	349.8	355.8	367.8	379.6	393.5	408.9	425.1	443.3	463.4	485.4	510.1
25°	328.8	335.8	344.5	356.8	371.2	387.4	403.6	423.0	444.9	467.4	493.7
27.5°	310.0	315.8	324.4	334.1	348.5	365.2	382.5	402.7	425.3	448.1	475.7
30°	296.8	303.2	311.2	321.5	333.0	351.2	368.9	388.8	411.6	435.2	463.6
32.5°	285.3	291.8	298.8	308.5	320.8	337.0	355.3	374.8	398.0	422.3	450.0
35°	269.0	273.5	280.0	289.6	301.7	314.8	333.5	354.0	376.6	401.8	429.6
37.5°	250.4	256.2	262.7	271.0	281.7	295.8	313.2	334.0	355.0	379.0	404.3
40°	239.6	245.0	252.3	258.3	269.5	282.4	298.2	319.9	340.9	363.6	386.7
42.5°	228.6	233.8	239.9	247.5	257.5	270.0	284.8	305.0	327.5	348.8	368.2
45°	211.4	216.8	222.6	229.6	238.9	251.1	265.8	284.2	303.8	323.5	338.1
47.5°	194.9	200.0	205.5	212.7	221.3	233.0	246.1	262.5	281.4	298.1	308.6
50°	183.2	187.8	193.9	200.9	209.3	220.3	232.9	248.9	264.9	280.0	289.6
52.5°	171.6	176.8	182.9	188.9	197.0	207.9	219.6	233.5	248.6	260.9	268.8
55°	154.2	159.2	164.7	171.1	178.9	188.3	200.7	211.7	223.6	234.1	238.7
57.5°	137.4	141.8	147.0	153.6	160.8	169.5	179.3	189.8	198.1	205.6	210.9
60°	126.4	130.2	135.1	140.7	148.5	156.3	165.2	175.0	181.6	187.8	192.8
62.5°	115.2	118.9	123.5	128.6	135.3	142.7	151.2	159.2	165.5	169.8	175.4
65°	98.5	102.0	105.9	111.3	116.6	122.7	130.5	136.2	140.7	145.4	148.9
67.5°	82.8	85.7	89.5	93.7	98.3	104.1	110.1	114.9	118.0	120.8	124.9
70°	72.6	74.9	78.0	81.2	86.1	91.9	96.6	100.4	102.4	105.2	110.4
72.5°	62.1	64.8	67.7	70.9	74.9	79.8	83.9	87.7	89.0	91.2	94.5
75°	49.0	50.4	52.7	55.0	57.9	62.1	66.0	67.0	68.2	70.0	72.3
77.5°	37.1	38.3	39.3	40.8	43.0	46.4	48.5	49.9	50.2	50.9	53.1
80°	29.4	30.1	31.0	32.2	33.1	36.0	37.1	38.5	39.0	39.7	40.8
82.5°	21.6	22.2	22.8	23.8	25.2	26.5	27.6	29.0	29.1	29.6	29.8
85°	12.6	12.8	12.3	12.8	13.0	13.5	14.7	15.9	15.7	15.5	16.1
87.5°	8.5	8.3	7.7	7.9	7.2	7.0	6.6	6.4	6.3	6.3	6.2
90°	20.1	18.8	17.0	15.1	13.3	11.5	9.5	7.5	5.4	3.2	1.2
92.5°	20.1	18.8	17.2	15.6	13.9	12.3	12.2	13.7	15.1	16.7	18.1
95°	20.1	18.8	28.7	38.6	48.5	58.5	63.7	64.5	65.3	66.1	66.9
97.5°	50.4	57.8	77.4	96.9	116.5	136.2	145.3	143.9	142.5	141.1	139.7
100°	165.3	204.2	203.2	202.2	201.1	200.1	199.1	198.3	197.5	196.8	196.0
102.5°	253.2	260.5	259.9	259.3	258.6	258.0	257.2	256.2	255.3	254.3	253.3
105°	349.7	349.7	349.7	349.7	349.7	349.7	349.2	348.2	347.1	346.1	345.1
107.5°	442.7	442.7	442.2	441.6	441.1	440.6	440.4	440.4	440.4	440.4	440.4
110°	503.9	504.6	504.1	503.6	503.1	502.6	502.3	502.3	502.3	502.3	502.3



TEST NUMBER: P333514-840

CATALOG NUMBER: S125RDIP-S375D1205U840-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	220°	225°	230°	235°	240°	245°	250°	255°	260°	265°	270°
112.5°	563.8	564.7	564.4	564.1	563.8	563.5	563.0	562.4	561.8	561.2	560.6
115°	653.9	654.9	654.6	654.4	654.1	653.9	653.1	651.8	650.5	649.1	647.8
117.5°	741.1	742.5	741.4	740.4	739.5	738.5	738.0	738.1	738.1	738.2	738.2
120°	796.4	796.9	796.1	795.4	794.6	793.8	793.6	793.8	794.1	794.3	794.6
122.5°	849.9	850.4	850.1	849.7	849.3	849.0	848.3	847.3	846.3	845.4	844.3
125°	928.5	929.5	929.5	929.5	929.5	929.5	928.6	926.8	924.9	923.1	921.3
127.5°	999.4	1000.0	1000.1	1000.3	1000.4	1000.6	1000.0	998.7	997.3	996.1	994.8
130°	1046.1	1046.9	1046.6	1046.4	1046.1	1045.8	1045.1	1043.8	1042.5	1041.2	1039.9
132.5°	1089.0	1089.1	1089.7	1090.3	1090.9	1091.5	1091.0	1089.4	1087.9	1086.4	1084.9
135°	1153.2	1153.7	1154.2	1154.8	1155.3	1155.8	1155.3	1153.7	1152.2	1150.5	1149.0
137.5°	1212.0	1211.9	1212.3	1212.8	1213.4	1213.8	1213.4	1211.9	1210.6	1209.3	1207.9
140°	1248.1	1247.6	1247.9	1248.1	1248.4	1248.6	1248.5	1248.0	1247.5	1247.0	1246.4
142.5°	1284.3	1284.2	1283.8	1283.4	1283.1	1282.7	1282.4	1282.1	1281.8	1281.4	1281.1
145°	1334.7	1334.4	1334.4	1334.4	1334.4	1334.4	1334.1	1333.6	1333.1	1332.6	1332.1
147.5°	1378.0	1377.7	1377.4	1377.0	1376.6	1376.3	1376.2	1376.3	1376.4	1376.5	1376.6
150°	1405.3	1404.8	1404.3	1403.8	1403.3	1402.8	1402.8	1403.3	1403.8	1404.3	1404.8
152.5°	1429.8	1429.3	1428.8	1428.3	1427.7	1427.1	1427.4	1428.7	1429.8	1431.0	1432.1
155°	1463.2	1462.4	1461.9	1461.3	1460.8	1460.3	1460.8	1462.4	1463.9	1465.5	1467.0
157.5°	1490.9	1490.1	1490.1	1490.0	1490.0	1489.9	1490.3	1491.3	1492.2	1493.1	1494.1
160°	1508.0	1506.9	1506.7	1506.4	1506.2	1505.9	1506.6	1508.1	1509.7	1511.3	1512.9
162.5°	1523.5	1522.0	1521.8	1521.5	1521.2	1521.0	1521.6	1523.2	1524.7	1526.3	1527.8
165°	1543.8	1542.2	1541.9	1541.7	1541.4	1541.2	1541.8	1543.4	1544.9	1546.5	1548.0
167.5°	1558.8	1557.0	1556.7	1556.4	1556.2	1555.9	1556.6	1558.2	1559.8	1561.5	1563.1
170°	1566.6	1564.5	1564.2	1564.0	1563.7	1563.5	1564.2	1566.0	1567.8	1569.7	1571.6
172.5°	1573.0	1571.0	1570.5	1570.1	1569.6	1569.1	1569.8	1571.7	1573.5	1575.3	1577.1
175°	1579.4	1577.4	1577.1	1576.9	1576.6	1576.3	1577.0	1578.5	1580.1	1581.7	1583.3
177.5°	1582.9	1581.3	1581.1	1580.9	1580.7	1580.5	1581.0	1582.4	1583.6	1584.8	1586.1
180°	1583.3	1583.3	1583.3	1583.3	1583.3	1583.3	1583.3	1583.3	1583.3	1583.3	1583.3



TEST NUMBER: P333514-840

CATALOG NUMBER: S125RDIP-S375D1205U840-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	275°	280°	285°	290°	295°	300°	305°	310°	315°	320°	325°
0°	568.5	568.5	568.5	568.5	568.5	568.5	568.5	568.5	568.5	568.5	568.5
2.5°	571.2	572.9	575.3	578.1	580.4	582.8	584.1	584.1	585.2	587.6	590.9
5°	572.9	579.0	584.7	592.2	598.0	604.8	610.0	614.9	619.2	624.9	630.8
7.5°	572.4	582.5	593.0	604.7	617.7	628.0	638.6	646.9	655.1	665.9	674.3
10°	570.6	583.6	597.8	612.8	629.1	643.3	656.2	667.8	679.0	690.7	701.3
12.5°	567.1	583.8	601.2	619.1	639.7	656.0	672.6	685.0	698.1	710.8	723.8
15°	562.1	581.7	602.7	627.7	652.9	671.1	687.4	703.6	715.7	730.1	742.6
17.5°	551.7	576.9	603.4	630.7	654.9	676.0	693.2	708.5	721.4	737.3	754.2
20°	545.5	572.9	600.4	629.5	652.7	674.4	690.9	706.8	722.9	743.7	764.2
22.5°	536.9	566.1	595.3	623.0	647.4	668.4	685.5	704.9	726.1	749.6	774.5
25°	523.4	553.5	582.4	608.7	632.6	654.1	677.4	703.6	729.2	760.2	796.0
27.5°	506.1	535.2	561.0	588.9	612.5	639.9	668.9	697.3	734.3	777.0	821.5
30°	493.3	520.8	545.3	571.7	598.5	628.6	661.3	694.7	738.8	788.9	841.9
32.5°	478.4	503.3	527.6	553.0	584.0	617.0	651.8	692.6	745.3	802.3	857.2
35°	452.4	474.8	498.5	526.6	559.6	595.5	639.9	689.5	753.3	814.6	863.8
37.5°	425.3	443.0	466.7	496.4	532.3	573.8	624.2	684.6	749.9	805.1	826.0
40°	404.3	420.9	446.0	477.2	512.7	558.2	614.6	676.7	742.6	780.7	779.1
42.5°	383.6	400.4	424.4	456.0	492.9	543.8	602.0	666.4	722.0	736.5	706.2
45°	351.8	367.5	391.1	422.8	462.5	515.9	577.0	638.9	674.4	650.8	590.6
47.5°	319.5	334.7	356.6	387.6	430.9	486.9	544.7	595.4	600.4	549.8	477.6
50°	298.2	312.5	333.3	366.4	408.4	462.9	518.8	558.7	546.2	484.4	410.0
52.5°	277.5	291.1	310.6	341.9	384.9	438.3	488.1	519.5	490.8	425.1	358.1
55°	246.9	259.9	279.5	308.2	347.2	396.2	439.9	451.3	409.3	343.1	288.9
57.5°	217.8	227.4	246.7	272.2	309.7	352.9	384.2	382.1	335.8	276.1	237.2
60°	198.5	207.2	225.6	248.9	284.7	323.5	345.4	336.0	289.1	239.8	202.6
62.5°	180.7	188.7	204.2	225.6	256.3	290.0	306.0	293.1	248.8	205.5	175.8
65°	153.5	159.4	171.8	191.6	215.6	238.9	253.2	234.3	195.1	162.4	140.0
67.5°	128.2	133.2	144.2	158.4	175.0	191.2	196.9	179.3	148.8	126.7	110.9
70°	111.8	116.4	123.9	137.2	148.1	159.6	162.4	146.5	121.1	104.3	94.5
72.5°	96.1	100.4	106.9	116.3	123.9	130.5	131.8	117.0	97.6	86.0	78.5
75°	73.3	77.1	81.2	84.7	89.6	90.8	90.3	78.9	68.4	60.7	56.5
77.5°	53.8	55.4	58.0	59.4	59.6	59.5	57.2	49.9	44.4	41.3	39.6
80°	41.5	42.7	43.4	43.8	44.1	41.8	39.2	34.7	32.9	31.0	29.0
82.5°	30.2	30.9	31.6	31.7	30.5	28.5	26.2	23.9	22.6	21.7	20.9
85°	16.4	16.6	16.4	15.1	13.5	12.8	12.3	11.9	11.7	11.4	11.4
87.5°	6.5	6.3	5.8	6.4	6.8	7.0	7.3	7.5	7.7	8.0	8.2
90°	3.2	5.4	7.5	9.5	11.5	13.3	15.1	17.0	18.8	20.1	21.4
92.5°	16.7	15.1	13.7	12.2	12.3	13.9	15.6	17.2	18.8	20.1	21.4
95°	66.1	65.3	64.5	63.7	58.5	48.5	38.6	28.7	18.8	20.1	21.4
97.5°	141.1	142.5	143.9	145.3	136.2	116.5	96.9	77.4	57.8	50.4	43.0
100°	196.8	197.5	198.3	199.1	200.1	201.1	202.2	203.2	204.2	165.3	126.5
102.5°	254.3	255.3	256.2	257.2	258.0	258.6	259.3	259.9	260.5	253.2	245.8
105°	346.1	347.1	348.2	349.2	349.7	349.7	349.7	349.7	349.7	349.7	349.7
107.5°	440.4	440.4	440.4	440.4	440.6	441.1	441.6	442.2	442.7	442.7	442.8
110°	502.3	502.3	502.3	502.3	502.6	503.1	503.6	504.1	504.6	503.9	503.1



TEST NUMBER: P333514-840

CATALOG NUMBER: S125RDIP-S375D1205U840-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	275°	280°	285°	290°	295°	300°	305°	310°	315°	320°	325°
112.5°	561.2	561.8	562.4	563.0	563.5	563.8	564.1	564.4	564.7	563.8	562.8
115°	649.1	650.5	651.8	653.1	653.9	654.1	654.4	654.6	654.9	653.9	652.8
117.5°	738.2	738.1	738.1	738.0	738.5	739.5	740.4	741.4	742.5	741.1	739.7
120°	794.3	794.1	793.8	793.6	793.8	794.6	795.4	796.1	796.9	796.4	795.9
122.5°	845.4	846.3	847.3	848.3	849.0	849.3	849.7	850.1	850.4	849.9	849.4
125°	923.1	924.9	926.8	928.6	929.5	929.5	929.5	929.5	929.5	928.5	927.5
127.5°	996.1	997.3	998.7	1000.0	1000.6	1000.4	1000.3	1000.1	1000.0	999.4	998.8
130°	1041.2	1042.5	1043.8	1045.1	1045.8	1046.1	1046.4	1046.6	1046.9	1046.1	1045.3
132.5°	1086.4	1087.9	1089.4	1091.0	1091.5	1090.9	1090.3	1089.7	1089.1	1089.0	1088.8
135°	1150.5	1152.2	1153.7	1155.3	1155.8	1155.3	1154.8	1154.2	1153.7	1153.2	1152.7
137.5°	1209.3	1210.6	1211.9	1213.4	1213.8	1213.4	1212.8	1212.3	1211.9	1212.0	1212.1
140°	1247.0	1247.5	1248.0	1248.5	1248.6	1248.4	1248.1	1247.9	1247.6	1248.1	1248.6
142.5°	1281.4	1281.8	1282.1	1282.4	1282.7	1283.1	1283.4	1283.8	1284.2	1284.3	1284.4
145°	1332.6	1333.1	1333.6	1334.1	1334.4	1334.4	1334.4	1334.4	1334.4	1334.7	1334.9
147.5°	1376.5	1376.4	1376.3	1376.2	1376.3	1376.6	1377.0	1377.4	1377.7	1378.0	1378.3
150°	1404.3	1403.8	1403.3	1402.8	1402.8	1403.3	1403.8	1404.3	1404.8	1405.3	1405.9
152.5°	1431.0	1429.8	1428.7	1427.4	1427.1	1427.7	1428.3	1428.8	1429.3	1429.8	1430.3
155°	1465.5	1463.9	1462.4	1460.8	1460.3	1460.8	1461.3	1461.9	1462.4	1463.2	1463.9
157.5°	1493.1	1492.2	1491.3	1490.3	1489.9	1490.0	1490.0	1490.1	1490.1	1490.9	1491.8
160°	1511.3	1509.7	1508.1	1506.6	1505.9	1506.2	1506.4	1506.7	1506.9	1508.0	1509.0
162.5°	1526.3	1524.7	1523.2	1521.6	1521.0	1521.2	1521.5	1521.8	1522.0	1523.5	1524.9
165°	1546.5	1544.9	1543.4	1541.8	1541.2	1541.4	1541.7	1541.9	1542.2	1543.8	1545.3
167.5°	1561.5	1559.8	1558.2	1556.6	1555.9	1556.2	1556.4	1556.7	1557.0	1558.8	1560.7
170°	1569.7	1567.8	1566.0	1564.2	1563.5	1563.7	1564.0	1564.2	1564.5	1566.6	1568.6
172.5°	1575.3	1573.5	1571.7	1569.8	1569.1	1569.6	1570.1	1570.5	1571.0	1573.0	1574.8
175°	1581.7	1580.1	1578.5	1577.0	1576.3	1576.6	1576.9	1577.1	1577.4	1579.4	1581.5
177.5°	1584.8	1583.6	1582.4	1581.0	1580.5	1580.7	1580.9	1581.1	1581.3	1582.9	1584.3
180°	1583.3	1583.3	1583.3	1583.3	1583.3	1583.3	1583.3	1583.3	1583.3	1583.3	1583.3



TEST NUMBER: P333514-840

CATALOG NUMBER: S125RDIP-S375D1205U840-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	330°	335°	340°	345°	350°	355°	360°
0°	568.5	568.5	568.5	568.5	568.5	568.5	568.5
2.5°	593.3	593.3	596.4	596.2	598.3	597.5	597.9
5°	637.7	641.7	645.2	647.5	651.1	652.0	651.5
7.5°	683.9	692.7	696.9	702.9	703.9	707.0	706.7
10°	712.4	721.0	727.6	732.7	735.3	738.5	738.8
12.5°	734.8	742.1	747.9	752.7	755.8	756.8	757.4
15°	752.3	760.4	767.2	774.0	778.0	781.0	782.6
17.5°	769.9	782.5	794.5	803.7	809.2	813.9	813.9
20°	783.6	798.0	812.9	823.4	834.2	838.9	839.6
22.5°	798.1	820.2	839.5	855.8	869.9	874.7	876.6
25°	828.4	857.3	887.0	909.8	926.1	935.7	937.2
27.5°	864.9	904.0	935.2	956.3	969.9	977.0	978.6
30°	890.7	926.9	954.8	970.7	977.0	978.0	974.4
32.5°	902.2	929.3	940.5	939.6	927.2	919.0	915.8
35°	888.1	882.5	855.3	822.5	797.6	781.7	777.5
37.5°	808.2	759.9	709.7	660.4	634.1	620.7	597.7
40°	729.4	660.6	608.3	566.8	537.1	513.3	507.8
42.5°	640.6	569.5	517.3	481.7	458.0	441.7	434.5
45°	514.7	453.6	410.4	383.1	365.0	353.0	347.7
47.5°	411.7	364.4	333.0	312.8	298.8	288.5	285.6
50°	355.2	317.3	290.7	273.7	263.2	255.3	252.1
52.5°	308.5	277.9	257.5	243.5	233.6	228.6	225.9
55°	254.6	228.2	213.5	202.3	196.7	192.8	190.9
57.5°	208.2	189.1	178.4	170.7	165.5	163.0	162.1
60°	182.3	167.3	157.5	151.5	147.9	144.7	143.7
62.5°	159.3	147.5	140.0	134.6	131.2	129.8	129.2
65°	128.4	120.7	115.0	111.8	109.0	108.5	108.3
67.5°	102.0	97.5	94.5	91.2	90.2	88.6	88.2
70°	87.3	84.2	80.7	79.6	78.4	76.7	77.1
72.5°	74.0	71.0	68.6	67.1	66.7	65.9	66.6
75°	54.1	53.2	52.3	51.1	50.6	50.6	50.4
77.5°	38.7	37.9	36.9	36.2	36.0	35.0	35.3
80°	28.0	26.9	26.4	26.6	25.9	25.7	25.7
82.5°	20.7	20.3	19.8	19.9	19.7	19.5	19.7
85°	11.4	11.2	11.2	11.0	11.0	10.7	10.7
87.5°	8.7	9.1	8.9	8.9	9.1	9.4	9.7
90°	22.7	24.0	25.0	25.9	26.6	27.4	28.2
92.5°	22.7	24.0	24.8	25.1	25.5	26.0	26.3
95°	22.7	24.0	24.6	24.6	24.6	24.6	24.6
97.5°	35.6	28.3	24.6	24.6	24.6	24.6	24.6
100°	87.7	48.8	28.8	27.8	26.8	25.7	24.6
102.5°	238.5	231.2	218.6	200.9	183.1	165.4	147.6
105°	349.7	349.7	349.6	349.3	349.1	348.8	348.6
107.5°	442.8	442.9	442.5	441.7	441.0	440.2	439.4
110°	502.3	501.5	501.3	501.5	501.8	502.1	502.3



TEST NUMBER: P333514-840

CATALOG NUMBER: S125RDIP-S375D1205U840-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	330°	335°	340°	345°	350°	355°	360°
112.5°	561.8	560.8	560.1	559.8	559.4	559.1	558.7
115°	651.8	650.8	649.4	647.8	646.3	644.7	643.2
117.5°	738.4	737.0	736.0	735.3	734.7	734.0	733.3
120°	795.4	794.9	794.0	792.6	791.3	790.0	788.7
122.5°	848.9	848.4	847.3	845.8	844.2	842.8	841.3
125°	926.3	925.3	924.4	923.6	922.9	922.1	921.3
127.5°	998.3	997.6	996.4	994.5	992.5	990.6	988.7
130°	1044.5	1043.8	1042.7	1041.4	1040.2	1038.8	1037.5
132.5°	1088.6	1088.5	1087.8	1086.5	1085.2	1083.9	1082.6
135°	1152.2	1151.7	1150.5	1149.0	1147.4	1145.9	1144.3
137.5°	1212.2	1212.3	1211.7	1210.3	1209.0	1207.6	1206.3
140°	1249.1	1249.7	1249.1	1247.6	1246.1	1244.5	1242.9
142.5°	1284.5	1284.6	1283.9	1282.3	1280.8	1279.2	1277.7
145°	1335.2	1335.4	1334.8	1333.2	1331.7	1330.1	1328.6
147.5°	1378.6	1378.9	1378.1	1376.2	1374.3	1372.5	1370.6
150°	1406.4	1406.9	1406.1	1404.1	1402.0	1399.9	1397.9
152.5°	1430.9	1431.4	1430.7	1428.8	1426.9	1425.0	1423.2
155°	1464.7	1465.5	1464.8	1462.8	1460.7	1458.5	1456.5
157.5°	1492.6	1493.4	1492.8	1490.7	1488.6	1486.5	1484.4
160°	1510.1	1511.2	1510.7	1508.5	1506.4	1504.4	1502.3
162.5°	1526.4	1527.8	1527.4	1525.1	1522.8	1520.6	1518.2
165°	1546.9	1548.4	1548.1	1546.1	1544.0	1541.9	1539.8
167.5°	1562.6	1564.5	1564.3	1561.9	1559.5	1557.2	1554.9
170°	1570.7	1572.9	1572.7	1570.3	1568.0	1565.7	1563.3
172.5°	1576.7	1578.5	1578.3	1576.0	1573.7	1571.2	1568.9
175°	1583.7	1585.7	1585.6	1583.3	1580.9	1578.5	1576.2
177.5°	1585.8	1587.2	1587.1	1585.5	1583.8	1582.1	1580.4
180°	1583.3	1583.3	1583.3	1583.3	1583.3	1583.3	1583.3

(END OF REPORT)