

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P331395-830

Luminaire Tested: **SA2XXDIP-C865D725U830-4F0-1E-UDD-A4**

Issue Date: 10/7/2019

Test Information

Test Method: LM-79-08
Report Number: P331395-830
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-16,
Test Lab: INNOVATION CENTER
Issue Date: 10/7/2019
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: NEO-RAY
Catalog Number: SA2XXDIP-C865D725U830-4F0-1E-UDD-A4
Description: DEFINE 2 DIRECT-INDIRECT PENDANT LED LUMINAIRE
DOWNLIGHT 865 LUMENS PER FOOT, ASYMMETRIC DIFFUSER
UPLIGHT 725 LUMENS PER FOOT, BATWING OPTIC
Light Source: -
Ballast/Driver: ELECTRONIC DRIVER

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 6259.8 lumens
Efficiency: N/A
Efficacy: 115.1 lumens/watt
Spacing Criteria (0/90/45): 1.08 / 1.16 / 1.23
Luminous Opening: Rectangular (W 4' x L: 0.17' x H: 0')
CIE Type: General Diffuse

Input Watts (W): 54.4
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P331395-830
CATALOG NUMBER: SA2XXDIP-C865D725U830-4F0-1E-UDD-A4

Luminous Intensity Polar Plot





TEST NUMBER: P331395-830

CATALOG NUMBER: SA2XXDIP-C865D725U830-4F0-1E-UDD-A4

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20					20					20					20					20	
RC	80					70					50					30					10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0	
RCR																						
0	109	109	109	109	101	101	101	101	87	87	87	75	75	75	63	63	63	57				57
1	100	96	92	89	93	89	86	83	78	75	73	67	65	63	56	55	54	49				49
2	91	84	78	73	85	79	74	69	69	65	61	59	56	54	50	48	47	42				42
3	84	75	68	62	78	70	64	59	61	56	52	53	49	46	45	42	40	36				36
4	77	66	59	53	72	62	56	50	55	49	45	47	43	40	41	38	35	32				32
5	71	60	52	46	66	56	49	44	49	44	39	43	39	35	37	34	31	28				28
6	66	54	46	40	61	51	43	38	45	39	35	39	34	31	34	30	28	25				25
7	61	49	41	35	57	46	39	34	41	35	31	36	31	28	31	27	25	22				22
8	57	44	37	32	53	42	35	30	37	32	28	33	28	25	29	25	22	20				20
9	53	41	33	28	49	38	32	27	34	29	25	30	26	23	27	23	20	18				18
10	49	37	30	26	46	35	29	25	32	26	23	28	24	21	25	21	19	17				17

AVERAGE LUMINANCE (cd/sqm):

	0°	90°	180°	270°
0°	26274	26274	26274	26274
5°	29457	26446	23436	26446
10°	33755	26230	20282	26230
15°	37342	25748	17919	25748
20°	36773	25232	16333	25232
25°	33157	24545	15330	24545
30°	27401	23448	14600	23448
35°	19969	22300	14079	22300
40°	15951	20946	13789	20946
45°	13938	19379	13394	19379
50°	13102	17862	13132	17862
55°	12076	16321	12780	16321
60°	11066	14683	12239	14683
65°	10082	13211	11706	13211
70°	9153	11783	10924	11783
75°	8116	10181	9676	10181
80°	6974	8433	7792	8433
85°	6243	6243	4631	6243



TEST NUMBER: P331395-830

CATALOG NUMBER: SA2XXDIP-C865D725U830-4F0-1E-UDD-A4

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	155.0	2.5
10°-20°	450.6	7.2
20°-30°	653.9	10.4
30°-40°	690.0	11.0
40°-50°	611.0	9.8
50°-60°	487.6	7.8
60°-70°	331.4	5.3
70°-80°	169.9	2.7
80°-90°	44.4	0.7
90°-100°	153.2	2.4
100°-110°	519.8	8.3
110°-120°	552.3	8.8
120°-130°	454.6	7.3
130°-140°	365.1	5.8
140°-150°	275.9	4.4
150°-160°	193.9	3.1
160°-170°	114.1	1.8
170°-180°	37.1	0.6
0°-30°	1259.4	20.1
0°-40°	1949.5	31.1
0°-60°	3048.0	48.7
0°-90°	3593.7	57.4
90°-120°	1225.3	19.6
90°-150°	2320.9	37.1
90°-180°	2666.0	42.6
0°-180°	6259.8	100.0

CANDELA DISTRIBUTION:

	0°	90°	180°	270°	360°	Flux
0°	1627	1627	1627	1627	1627	
5°	1818	1632	1446	1632	1818	181
15°	2234	1540	1072	1540	2234	616
25°	1861	1378	860	1378	1861	841
35°	1013	1131	714	1131	1013	659
45°	610	849	587	849	610	480
55°	429	580	454	580	429	385
65°	264	346	306	346	264	262
75°	130	163	155	163	130	139
85°	34	34	25	34	34	38
90°	24	1	24	1	24	15
95°	84	26	84	26	84	109
105°	830	90	830	90	830	803
115°	1093	158	1093	158	1093	1070
125°	886	221	886	221	886	801
135°	735	259	735	259	735	571
145°	586	296	586	296	586	372
155°	493	337	493	337	493	230
165°	432	367	432	367	432	124
175°	390	382	390	382	390	38
180°	383	383	383	383	383	



TEST NUMBER: P331395-830

CATALOG NUMBER: SA2XXDIP-C865D725U830-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	1627.3	1627.3	1627.3	1627.3	1627.3	1627.3	1627.3	1627.3	1627.3	1627.3	1627.3
2.5°	1702.4	1702.9	1703.9	1695.9	1694.9	1694.9	1687.9	1681.9	1674.9	1665.4	1666.4
5°	1817.5	1824.4	1826.8	1819.4	1808.1	1806.9	1796.2	1778.7	1762.5	1749.3	1739.9
7.5°	1954.8	1957.6	1951.4	1941.5	1933.2	1918.2	1898.4	1879.1	1851.9	1827.0	1808.5
10°	2058.9	2062.7	2052.0	2037.6	2025.7	2008.2	1979.4	1950.0	1914.4	1880.0	1852.5
12.5°	2138.0	2147.2	2133.5	2131.7	2111.3	2087.3	2053.0	2038.2	1988.0	1940.0	1910.5
15°	2234.0	2233.4	2234.7	2222.7	2207.7	2203.9	2167.8	2128.4	2057.7	2029.5	1980.8
17.5°	2206.2	2215.7	2220.2	2220.0	2219.6	2217.2	2205.6	2180.8	2145.3	2099.7	2043.3
20°	2140.2	2152.7	2154.6	2169.0	2177.1	2187.7	2192.1	2185.2	2163.3	2125.2	2076.4
22.5°	2038.2	2041.6	2047.5	2069.9	2087.5	2114.2	2128.1	2151.2	2142.8	2124.2	2083.4
25°	1861.2	1855.0	1876.9	1888.1	1928.8	1971.3	2002.0	2035.7	2065.8	2083.9	2072.0
27.5°	1648.9	1639.5	1672.3	1702.1	1735.1	1781.2	1829.0	1885.4	1932.3	1990.9	2011.1
30°	1469.7	1475.4	1506.7	1538.5	1588.6	1653.6	1707.4	1769.3	1836.3	1901.9	1947.6
32.5°	1276.6	1298.3	1318.1	1366.9	1411.0	1483.5	1562.3	1639.7	1723.2	1797.8	1868.5
35°	1013.1	1038.2	1065.7	1101.4	1163.3	1235.2	1312.1	1416.5	1530.4	1632.4	1716.2
37.5°	852.8	848.9	864.6	890.3	940.5	998.5	1087.1	1190.3	1324.3	1444.1	1562.3
40°	756.8	754.2	765.5	789.3	827.5	870.0	947.5	1038.2	1162.6	1309.0	1449.7
42.5°	690.7	692.2	698.4	715.2	741.4	776.4	834.4	911.6	1025.6	1163.4	1314.7
45°	610.4	614.8	621.7	629.8	644.8	673.5	706.1	761.1	851.2	966.3	1115.1
47.5°	552.6	552.7	559.8	566.8	575.8	592.0	618.5	653.1	716.6	810.3	938.3
50°	521.6	517.3	522.3	527.8	537.2	548.5	566.0	598.5	641.0	716.7	823.7
52.5°	483.6	483.7	488.2	490.3	498.7	510.0	525.9	548.5	587.0	646.2	734.1
55°	429.0	432.2	434.7	438.4	445.9	454.0	466.6	481.5	511.6	556.0	621.0
57.5°	377.8	378.7	381.3	388.4	393.1	400.7	412.6	426.1	445.6	478.5	527.4
60°	342.7	342.7	347.7	350.8	357.1	364.6	374.0	387.1	404.6	431.5	471.0
62.5°	310.8	310.2	312.2	317.4	322.1	329.1	338.5	349.6	366.1	390.0	422.4
65°	263.9	262.7	266.5	267.7	272.7	279.6	287.1	299.0	312.1	329.6	358.4
67.5°	218.9	220.4	222.4	224.8	227.5	234.8	239.8	248.2	259.3	273.8	293.3
70°	193.9	193.9	193.9	195.8	199.5	203.3	208.3	215.2	225.7	238.3	255.8
72.5°	165.9	167.9	169.8	168.7	173.5	175.8	181.7	185.6	195.8	203.8	219.2
75°	130.1	130.1	130.1	133.2	135.1	137.0	140.7	144.5	149.5	159.5	167.6
77.5°	97.1	96.8	97.5	98.2	100.2	102.5	103.6	107.0	111.6	116.2	123.1
80°	75.0	76.3	76.9	78.1	78.1	79.5	80.0	84.5	87.6	90.7	95.1
82.5°	58.1	58.2	58.4	58.6	59.2	59.9	61.5	63.0	64.0	66.6	70.0
85°	33.7	33.2	33.2	34.4	33.7	33.7	35.1	36.3	36.3	36.9	38.7
87.5°	17.9	17.9	18.4	17.9	17.9	18.2	17.9	17.7	18.4	19.0	19.4
90°	24.3	24.3	24.3	24.3	24.3	23.6	22.1	23.6	24.3	25.1	24.3
92.5°	40.8	42.0	41.4	43.7	44.4	48.9	55.1	64.3	80.9	95.8	94.4
95°	84.0	83.2	85.5	91.3	100.9	117.2	148.1	193.0	252.7	288.8	255.7
97.5°	165.3	171.5	182.3	200.4	235.6	288.8	368.5	450.4	517.3	493.0	371.4
100°	263.7	277.0	298.4	330.1	391.2	480.4	581.4	672.7	688.2	582.0	400.8
102.5°	464.2	482.1	508.8	562.9	629.3	723.8	797.7	818.3	751.8	585.0	389.6
105°	830.4	840.7	872.3	918.0	963.7	988.1	978.5	895.2	742.0	545.9	367.7
107.5°	1060.6	1074.4	1080.7	1083.3	1077.5	1041.8	965.2	839.8	677.2	504.1	356.8
110°	1130.2	1131.0	1124.4	1110.3	1078.6	1018.2	924.0	792.0	636.6	484.1	354.4



TEST NUMBER: P331395-830

CATALOG NUMBER: SA2XXDIP-C865D725U830-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	1129.1	1125.1	1112.6	1089.1	1045.1	975.8	875.0	748.5	608.3	471.1	355.0
115°	1092.7	1086.0	1066.9	1032.9	980.6	904.7	808.2	694.7	573.3	456.9	358.1
117.5°	1027.7	1022.1	1001.9	966.1	912.8	841.6	754.0	654.4	551.1	449.9	363.4
120°	985.8	978.5	957.1	922.5	870.9	803.8	725.8	634.3	539.3	445.7	366.9
122.5°	942.2	936.0	917.0	883.0	836.7	776.1	702.2	618.5	529.3	443.4	371.1
125°	886.4	880.4	862.0	834.1	791.3	736.0	671.2	595.3	515.0	439.1	377.2
127.5°	837.4	832.7	816.8	790.6	753.3	702.3	641.1	572.5	501.7	436.6	383.6
130°	809.7	803.8	789.1	764.0	727.9	679.3	621.1	557.7	492.9	435.5	388.3
132.5°	780.8	775.5	762.0	737.0	701.4	655.7	602.3	543.6	485.9	434.9	393.0
135°	734.6	731.6	718.4	694.1	662.3	621.1	572.5	523.9	476.0	433.9	398.6
137.5°	689.2	684.8	673.2	652.2	623.3	587.4	548.7	508.1	469.0	433.9	403.6
140°	658.0	653.6	642.4	623.3	599.7	567.3	533.5	498.0	465.0	433.2	406.0
142.5°	626.7	625.8	616.0	598.6	576.2	549.0	519.9	489.8	460.8	433.2	407.7
145°	586.4	584.3	576.9	564.4	546.7	525.4	502.5	478.2	455.3	431.8	409.6
147.5°	552.7	551.4	546.4	536.4	521.8	506.1	488.3	469.2	449.8	429.1	410.3
150°	532.7	532.0	527.5	518.7	507.7	494.4	478.9	462.7	445.0	427.3	409.6
152.5°	515.6	515.5	512.2	504.5	495.9	484.4	471.3	456.2	440.9	424.4	408.5
155°	492.9	494.4	491.4	486.3	478.2	470.0	459.0	447.2	433.2	419.2	406.7
157.5°	473.6	473.6	472.3	468.0	462.2	455.9	446.7	436.8	426.0	414.0	403.3
160°	461.2	461.2	460.5	456.9	451.7	446.5	438.4	430.3	420.8	410.4	401.5
162.5°	449.4	450.1	449.3	446.8	441.7	437.6	430.7	423.8	415.9	407.5	399.8
165°	432.5	433.2	433.2	430.3	427.3	424.4	419.2	414.1	408.2	401.5	396.4
167.5°	416.9	417.7	417.9	416.3	415.0	412.3	408.8	404.8	400.5	396.4	393.0
170°	407.5	408.9	409.6	407.5	406.7	405.2	402.3	400.1	396.4	393.4	391.2
172.5°	399.8	400.7	401.4	400.4	399.6	398.8	396.4	394.7	392.3	389.9	388.9
175°	389.7	391.2	392.0	391.2	391.2	390.5	389.7	389.0	386.8	386.1	385.3
177.5°	383.7	384.9	385.5	385.5	385.5	385.5	384.9	384.9	383.7	383.1	383.7
180°	383.1	383.1	383.1	383.1	383.1	383.1	383.1	383.1	383.1	383.1	383.1



TEST NUMBER: P331395-830

CATALOG NUMBER: SA2XXDIP-C865D725U830-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°	95°	100°	105°
0°	1627.3	1627.3	1627.3	1627.3	1627.3	1627.3	1627.3	1627.3	1627.3	1627.3	1627.3
2.5°	1669.9	1665.8	1663.4	1654.4	1646.3	1638.3	1635.9	1636.8	1625.9	1615.3	1610.8
5°	1734.9	1722.4	1710.5	1693.7	1673.7	1651.7	1640.5	1631.7	1609.9	1586.1	1572.3
7.5°	1793.2	1775.3	1752.5	1720.7	1691.5	1657.1	1635.2	1615.8	1583.8	1550.3	1529.7
10°	1828.7	1804.3	1774.9	1736.2	1700.5	1658.6	1629.2	1599.9	1562.3	1522.3	1497.2
12.5°	1859.3	1826.4	1797.4	1747.7	1705.5	1653.1	1618.3	1576.8	1537.3	1489.8	1465.3
15°	1931.9	1871.2	1816.2	1759.9	1708.0	1634.8	1596.1	1540.4	1488.5	1429.7	1401.6
17.5°	1988.1	1920.0	1833.2	1761.7	1701.1	1620.1	1563.2	1496.5	1435.1	1367.9	1329.6
20°	2020.2	1941.9	1848.7	1763.7	1691.1	1598.6	1536.6	1468.5	1396.6	1320.9	1279.6
22.5°	2039.1	1956.9	1864.7	1756.1	1671.1	1581.0	1503.2	1428.4	1355.6	1273.8	1230.6
25°	2045.1	1970.1	1872.5	1749.9	1646.2	1544.2	1450.4	1377.8	1289.6	1213.3	1150.2
27.5°	2015.3	1961.5	1867.7	1738.1	1617.2	1498.0	1393.5	1311.3	1218.2	1135.4	1071.9
30°	1978.9	1947.6	1856.2	1726.2	1594.2	1466.0	1350.9	1257.7	1165.2	1081.4	1016.3
32.5°	1922.3	1915.5	1835.2	1709.1	1569.7	1425.5	1306.4	1212.2	1109.7	1027.3	965.3
35°	1811.2	1841.3	1790.5	1671.1	1523.5	1367.8	1239.0	1131.4	1025.1	946.2	888.1
37.5°	1662.4	1736.9	1723.6	1615.4	1461.2	1305.0	1162.8	1050.4	949.0	869.5	812.4
40°	1559.8	1654.8	1668.6	1572.9	1417.2	1256.5	1105.8	993.8	894.9	822.5	764.9
42.5°	1449.7	1560.8	1598.6	1521.9	1369.1	1205.4	1054.7	938.8	840.9	770.4	719.3
45°	1265.3	1412.2	1480.4	1436.6	1289.0	1121.3	966.3	848.7	759.9	693.6	654.2
47.5°	1092.7	1253.3	1345.0	1329.6	1199.8	1033.8	880.4	767.6	681.2	628.3	593.0
50°	970.6	1135.8	1246.4	1251.5	1135.8	971.3	817.5	711.1	631.7	582.3	553.5
52.5°	864.6	1022.2	1142.9	1169.4	1064.2	906.3	760.9	655.1	585.1	539.7	514.0
55°	726.1	859.3	993.2	1042.0	957.5	807.4	673.0	579.8	514.1	482.9	460.3
57.5°	603.7	714.7	838.3	892.2	840.2	711.7	585.6	504.7	451.4	424.0	406.8
60°	539.1	626.7	736.8	801.2	756.1	641.7	531.6	454.7	410.9	386.5	370.2
62.5°	479.1	556.7	649.7	708.6	684.1	576.2	477.6	409.6	371.8	349.0	337.2
65°	395.3	456.6	528.5	582.9	566.7	484.7	404.1	345.8	315.8	297.7	288.3
67.5°	325.5	369.8	419.6	467.3	454.2	396.2	331.3	286.1	263.7	248.1	242.4
70°	281.4	315.2	359.6	397.8	387.1	339.6	288.3	249.6	230.2	217.1	211.4
72.5°	239.4	267.2	301.0	332.2	325.1	285.6	242.8	213.5	198.6	186.5	181.9
75°	180.8	202.0	222.6	243.3	241.4	210.8	185.8	163.2	151.4	141.9	140.1
77.5°	133.5	145.3	159.4	171.6	168.2	150.7	131.1	118.2	109.4	103.2	102.2
80°	102.0	108.9	118.9	127.6	123.2	115.7	100.1	90.7	84.5	78.1	75.7
82.5°	73.9	80.8	86.8	91.5	88.2	81.2	71.5	65.1	61.5	57.1	56.2
85°	38.7	42.5	45.1	46.3	45.1	40.6	36.3	33.7	30.6	28.7	28.2
87.5°	18.9	18.0	17.2	17.8	16.0	15.6	13.1	11.1	11.1	11.2	10.5
90°	19.9	14.7	11.0	8.9	7.4	5.9	2.9	0.8	2.9	5.9	7.4
92.5°	73.5	50.1	33.5	26.5	21.5	18.3	13.0	9.0	13.0	18.3	21.5
95°	170.2	106.1	72.2	54.5	42.7	36.1	28.7	25.8	28.7	36.1	42.7
97.5°	229.3	140.0	97.4	77.4	63.8	53.8	46.0	42.0	46.0	53.8	63.8
100°	241.7	151.7	112.7	92.1	77.4	65.6	58.9	56.7	58.9	65.6	77.4
102.5°	242.2	162.4	126.3	105.7	90.3	78.5	71.9	70.3	71.9	78.5	90.3
105°	246.1	180.5	145.9	125.3	109.1	98.0	92.8	89.9	92.8	98.0	109.1
107.5°	256.3	199.1	165.5	144.7	128.7	118.5	113.5	111.1	113.5	118.5	128.7
110°	264.5	211.4	179.1	157.7	142.2	132.6	128.2	125.3	128.2	132.6	142.2



TEST NUMBER: P331395-830

CATALOG NUMBER: SA2XXDIP-C865D725U830-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°	95°	100°	105°
112.5°	273.3	223.3	192.0	170.0	155.1	146.2	141.2	138.2	141.2	146.2	155.1
115°	286.6	241.7	210.0	190.1	175.3	166.5	162.1	158.4	162.1	166.5	175.3
117.5°	300.8	258.6	229.3	208.7	194.5	186.7	182.3	179.4	182.3	186.7	194.5
120°	310.2	270.4	241.7	221.0	206.3	199.6	195.3	192.3	195.3	199.6	206.3
122.5°	318.5	281.6	254.7	233.4	218.7	211.4	207.1	204.7	207.1	211.4	218.7
125°	331.6	298.4	271.8	251.3	236.5	227.6	223.3	221.0	223.3	227.6	236.5
127.5°	343.7	314.1	288.2	267.0	252.9	243.2	237.0	234.0	237.0	243.2	252.9
130°	351.5	323.5	297.7	277.0	262.3	251.9	244.6	241.7	244.6	251.9	262.3
132.5°	359.1	331.7	307.1	286.4	271.2	260.2	252.3	248.7	252.3	260.2	271.2
135°	369.1	343.4	319.8	299.2	282.2	271.2	262.3	259.4	262.3	271.2	282.2
137.5°	376.8	352.8	329.5	310.4	293.5	281.7	272.9	269.4	272.9	281.7	293.5
140°	380.9	358.1	336.0	316.8	300.6	288.8	279.9	277.0	279.9	288.8	300.6
142.5°	384.5	362.2	340.7	322.7	307.1	295.3	287.1	284.6	287.1	295.3	307.1
145°	389.0	368.4	348.5	332.2	317.5	306.5	299.2	296.1	299.2	306.5	317.5
147.5°	391.5	373.4	354.7	340.3	328.0	317.8	310.8	308.6	310.8	317.8	328.0
150°	392.7	375.8	358.8	345.5	334.5	324.9	319.1	316.8	319.1	324.9	334.5
152.5°	393.3	378.1	363.0	350.8	340.4	332.0	326.1	325.1	326.1	332.0	340.4
155°	394.2	381.6	369.1	358.1	350.0	341.9	337.4	336.7	337.4	341.9	350.0
157.5°	394.2	384.2	373.5	364.3	357.8	350.7	347.1	346.5	347.1	350.7	357.8
160°	394.2	385.3	376.5	368.4	362.5	356.6	353.6	352.9	353.6	356.6	362.5
162.5°	393.6	386.0	378.2	371.9	366.6	361.9	358.9	359.4	358.9	361.9	366.6
165°	392.0	386.8	380.2	375.8	372.1	367.7	366.2	366.9	366.2	367.7	372.1
167.5°	391.0	386.6	381.8	379.0	376.4	373.5	372.2	373.2	372.2	373.5	376.4
170°	389.7	386.1	382.4	380.2	378.7	376.5	375.8	377.2	375.8	376.5	378.7
172.5°	388.0	385.5	383.0	381.4	380.5	378.2	378.7	379.6	378.7	378.2	380.5
175°	386.1	384.6	383.1	382.4	382.4	380.9	381.6	382.4	381.6	380.9	382.4
177.5°	384.9	383.7	383.1	383.1	383.1	381.9	382.6	383.7	382.6	381.9	383.1
180°	383.1	383.1	383.1	383.1	383.1	383.1	383.1	383.1	383.1	383.1	383.1



TEST NUMBER: P331395-830

CATALOG NUMBER: SA2XXDIP-C865D725U830-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	110°	115°	120°	125°	130°	135°	140°	145°	150°	155°	160°
0°	1627.3	1627.3	1627.3	1627.3	1627.3	1627.3	1627.3	1627.3	1627.3	1627.3	1627.3
2.5°	1605.8	1602.8	1592.3	1586.9	1577.8	1569.3	1563.8	1566.3	1568.3	1567.3	1565.8
5°	1559.8	1547.9	1529.7	1514.1	1502.9	1482.2	1473.5	1469.1	1465.4	1460.9	1456.6
7.5°	1505.1	1486.3	1460.2	1437.9	1416.9	1391.3	1376.7	1367.9	1359.0	1349.1	1340.3
10°	1466.0	1439.7	1412.2	1380.9	1355.9	1332.8	1312.1	1298.4	1285.9	1273.9	1265.3
12.5°	1424.9	1394.7	1360.7	1317.9	1290.3	1257.3	1254.1	1229.8	1210.3	1203.0	1192.7
15°	1359.7	1317.1	1273.9	1223.3	1201.5	1171.4	1152.6	1133.9	1117.0	1105.1	1102.0
17.5°	1285.5	1230.5	1187.5	1151.1	1115.2	1084.5	1067.2	1052.3	1038.3	1022.5	1020.3
20°	1229.0	1181.4	1134.5	1102.6	1065.7	1034.4	1013.1	998.2	986.3	976.9	968.7
22.5°	1175.4	1123.4	1080.4	1045.6	1009.2	983.9	967.1	952.6	942.7	932.4	924.7
25°	1089.5	1048.9	1001.9	962.5	932.5	916.2	902.5	889.9	883.7	876.8	868.1
27.5°	1014.3	969.1	925.3	894.8	868.4	853.9	844.2	835.7	829.8	825.8	820.8
30°	961.3	915.6	881.2	851.2	829.3	814.9	808.7	803.7	796.8	794.3	791.8
32.5°	910.2	869.1	839.7	813.7	792.8	783.4	777.7	773.2	767.8	765.3	760.3
35°	838.1	803.7	774.9	760.5	743.7	735.5	731.1	724.9	719.8	717.4	716.7
37.5°	770.2	740.3	721.3	702.9	695.7	690.7	684.8	680.4	678.9	678.5	678.0
40°	726.1	701.7	684.9	669.9	666.7	659.2	654.2	650.4	650.4	651.1	650.4
42.5°	686.1	664.2	649.3	636.3	632.6	628.2	623.2	622.9	624.0	626.0	624.0
45°	625.4	609.8	599.2	592.9	586.0	581.6	581.0	582.9	583.5	584.2	586.0
47.5°	569.7	559.2	549.6	542.7	539.7	538.9	538.2	541.5	544.5	545.6	548.5
50°	536.6	524.7	516.6	512.2	509.7	508.5	509.7	513.5	515.9	519.1	520.9
52.5°	499.5	491.2	485.6	482.2	481.2	481.9	482.2	486.4	490.5	491.5	492.5
55°	448.5	442.1	440.9	435.3	437.8	437.2	440.3	442.8	446.6	450.3	450.9
57.5°	397.4	392.4	389.0	389.6	390.3	393.0	395.7	400.0	404.1	408.0	408.4
60°	363.4	360.9	359.0	359.0	360.2	364.0	367.1	371.5	374.0	376.5	378.3
62.5°	332.3	329.9	328.0	328.9	332.2	334.5	338.1	340.4	343.0	345.4	346.4
65°	283.3	282.1	284.0	285.2	285.8	289.0	293.3	295.2	297.7	299.0	303.3
67.5°	238.2	238.4	238.2	239.9	243.6	244.3	248.5	252.8	253.3	255.7	258.5
70°	207.6	208.9	210.2	211.4	214.5	215.7	218.9	220.7	223.3	225.2	227.1
72.5°	179.6	179.8	181.2	180.9	183.5	186.2	188.9	190.8	193.2	195.7	197.5
75°	138.2	138.2	139.5	140.1	143.3	146.4	145.7	146.9	149.5	151.9	153.3
77.5°	100.9	99.5	100.9	101.6	102.5	105.2	105.7	107.4	110.3	109.4	110.8
80°	76.9	75.0	76.9	77.6	77.6	80.7	80.7	81.9	83.8	81.9	83.8
82.5°	55.0	54.0	55.4	55.5	56.6	56.6	57.7	57.9	59.8	58.9	59.8
85°	27.5	26.9	27.5	26.9	27.5	28.2	28.2	27.5	27.5	28.7	26.9
87.5°	10.3	10.2	10.5	11.5	11.9	11.5	10.8	10.7	10.5	9.7	9.9
90°	8.9	11.0	14.7	19.9	24.3	25.1	24.3	23.6	22.1	23.6	24.3
92.5°	26.5	33.5	50.1	73.5	94.4	95.8	80.9	64.3	55.1	48.9	44.4
95°	54.5	72.2	106.1	170.2	255.7	288.8	252.7	193.0	148.1	117.2	100.9
97.5°	77.4	97.4	140.0	229.3	371.4	493.0	517.3	450.4	368.5	288.8	235.6
100°	92.1	112.7	151.7	241.7	400.8	582.0	688.2	672.7	581.4	480.4	391.2
102.5°	105.7	126.3	162.4	242.2	389.6	585.0	751.8	818.3	797.7	723.8	629.3
105°	125.3	145.9	180.5	246.1	367.7	545.9	742.0	895.2	978.5	988.1	963.7
107.5°	144.7	165.5	199.1	256.3	356.8	504.1	677.2	839.8	965.2	1041.8	1077.5
110°	157.7	179.1	211.4	264.5	354.4	484.1	636.6	792.0	924.0	1018.2	1078.6



TEST NUMBER: P331395-830

CATALOG NUMBER: SA2XXDIP-C865D725U830-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	110°	115°	120°	125°	130°	135°	140°	145°	150°	155°	160°
112.5°	170.0	192.0	223.3	273.3	355.0	471.1	608.3	748.5	875.0	975.8	1045.1
115°	190.1	210.0	241.7	286.6	358.1	456.9	573.3	694.7	808.2	904.7	980.6
117.5°	208.7	229.3	258.6	300.8	363.4	449.9	551.1	654.4	754.0	841.6	912.8
120°	221.0	241.7	270.4	310.2	366.9	445.7	539.3	634.3	725.8	803.8	870.9
122.5°	233.4	254.7	281.6	318.5	371.1	443.4	529.3	618.5	702.2	776.1	836.7
125°	251.3	271.8	298.4	331.6	377.2	439.1	515.0	595.3	671.2	736.0	791.3
127.5°	267.0	288.2	314.1	343.7	383.6	436.6	501.7	572.5	641.1	702.3	753.3
130°	277.0	297.7	323.5	351.5	388.3	435.5	492.9	557.7	621.1	679.3	727.9
132.5°	286.4	307.1	331.7	359.1	393.0	434.9	485.9	543.6	602.3	655.7	701.4
135°	299.2	319.8	343.4	369.1	398.6	433.9	476.0	523.9	572.5	621.1	662.3
137.5°	310.4	329.5	352.8	376.8	403.6	433.9	469.0	508.1	548.7	587.4	623.3
140°	316.8	336.0	358.1	380.9	406.0	433.2	465.0	498.0	533.5	567.3	599.7
142.5°	322.7	340.7	362.2	384.5	407.7	433.2	460.8	489.8	519.9	549.0	576.2
145°	332.2	348.5	368.4	389.0	409.6	431.8	455.3	478.2	502.5	525.4	546.7
147.5°	340.3	354.7	373.4	391.5	410.3	429.1	449.8	469.2	488.3	506.1	521.8
150°	345.5	358.8	375.8	392.7	409.6	427.3	445.0	462.7	478.9	494.4	507.7
152.5°	350.8	363.0	378.1	393.3	408.5	424.4	440.9	456.2	471.3	484.4	495.9
155°	358.1	369.1	381.6	394.2	406.7	419.2	433.2	447.2	459.0	470.0	478.2
157.5°	364.3	373.5	384.2	394.2	403.3	414.0	426.0	436.8	446.7	455.9	462.2
160°	368.4	376.5	385.3	394.2	401.5	410.4	420.8	430.3	438.4	446.5	451.7
162.5°	371.9	378.2	386.0	393.6	399.8	407.5	415.9	423.8	430.7	437.6	441.7
165°	375.8	380.2	386.8	392.0	396.4	401.5	408.2	414.1	419.2	424.4	427.3
167.5°	379.0	381.8	386.6	391.0	393.0	396.4	400.5	404.8	408.8	412.3	415.0
170°	380.2	382.4	386.1	389.7	391.2	393.4	396.4	400.1	402.3	405.2	406.7
172.5°	381.4	383.0	385.5	388.0	388.9	389.9	392.3	394.7	396.4	398.8	399.6
175°	382.4	383.1	384.6	386.1	385.3	386.1	386.8	389.0	389.7	390.5	391.2
177.5°	383.1	383.1	383.7	384.9	383.7	383.1	383.7	384.9	384.9	385.5	385.5
180°	383.1	383.1	383.1	383.1	383.1	383.1	383.1	383.1	383.1	383.1	383.1



TEST NUMBER: P331395-830

CATALOG NUMBER: SA2XXDIP-C865D725U830-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	165°	170°	175°	180°	185°	190°	195°	200°	205°	210°	215°
0°	1627.3	1627.3	1627.3	1627.3	1627.3	1627.3	1627.3	1627.3	1627.3	1627.3	1627.3
2.5°	1560.8	1559.8	1559.8	1555.3	1559.8	1559.8	1560.8	1565.8	1567.3	1568.3	1566.3
5°	1447.8	1446.0	1442.8	1446.0	1442.8	1446.0	1447.8	1456.6	1460.9	1465.4	1469.1
7.5°	1336.1	1328.6	1327.5	1320.1	1327.5	1328.6	1336.1	1340.3	1349.1	1359.0	1367.9
10°	1254.6	1249.6	1249.0	1237.1	1249.0	1249.6	1254.6	1265.3	1273.9	1285.9	1298.4
12.5°	1192.6	1180.5	1182.9	1176.0	1182.9	1180.5	1192.6	1192.7	1203.0	1210.3	1229.8
15°	1085.1	1085.1	1082.6	1072.0	1082.6	1085.1	1085.1	1102.0	1105.1	1117.0	1133.9
17.5°	1008.0	1006.6	1000.7	1003.7	1000.7	1006.6	1008.0	1020.3	1022.5	1038.3	1052.3
20°	961.9	958.2	950.6	950.6	950.6	958.2	961.9	968.7	976.9	986.3	998.2
22.5°	918.4	918.1	910.1	912.6	910.1	918.1	918.4	924.7	932.4	942.7	952.6
25°	867.4	862.4	858.8	860.5	858.8	862.4	867.4	868.1	876.8	883.7	889.9
27.5°	819.2	816.4	816.1	811.1	816.1	816.4	819.2	820.8	825.8	829.8	835.7
30°	791.2	784.9	786.2	783.1	786.2	784.9	791.2	791.8	794.3	796.8	803.7
32.5°	759.1	756.9	755.6	753.0	755.6	756.9	759.1	760.3	765.3	767.8	773.2
35°	715.5	716.1	712.9	714.3	712.9	716.1	715.5	716.7	717.4	719.8	724.9
37.5°	677.3	679.3	677.9	678.3	677.9	679.3	677.3	678.0	678.5	678.9	680.4
40°	652.3	652.3	652.3	654.2	652.3	652.3	652.3	650.4	651.1	650.4	650.4
42.5°	628.3	627.3	626.3	626.1	626.3	627.3	628.3	624.0	626.0	624.0	622.9
45°	587.3	589.2	589.7	586.6	589.7	589.2	587.3	586.0	584.2	583.5	582.9
47.5°	550.2	550.4	550.2	552.9	550.2	550.4	550.2	548.5	545.6	544.5	541.5
50°	524.1	522.8	524.1	522.8	524.1	522.8	524.1	520.9	519.1	515.9	513.5
52.5°	496.6	496.8	496.1	495.9	496.1	496.8	496.6	492.5	491.5	490.5	486.4
55°	453.5	454.7	454.0	454.0	454.0	454.7	453.5	450.9	450.3	446.6	442.8
57.5°	408.8	409.9	410.8	408.0	410.8	409.9	408.8	408.4	408.0	404.1	400.0
60°	377.8	380.9	380.2	379.0	380.2	380.9	377.8	378.3	376.5	374.0	371.5
62.5°	349.2	350.3	350.2	350.0	350.2	350.3	349.2	346.4	345.4	343.0	340.4
65°	305.2	306.4	304.5	306.4	304.5	306.4	305.2	303.3	299.0	297.7	295.2
67.5°	257.8	258.2	259.6	260.4	259.6	258.2	257.8	258.5	255.7	253.3	252.8
70°	228.3	227.6	229.5	231.4	229.5	227.6	228.3	227.1	225.2	223.3	220.7
72.5°	197.3	198.6	198.0	199.3	198.0	198.6	197.3	197.5	195.7	193.2	190.8
75°	151.9	153.8	153.3	155.1	153.3	153.8	151.9	153.3	151.9	149.5	146.9
77.5°	109.8	110.1	109.8	110.8	109.8	110.1	109.8	110.8	109.4	110.3	107.4
80°	83.8	82.6	81.3	83.8	81.3	82.6	83.8	83.8	81.9	83.8	81.9
82.5°	58.2	59.0	57.8	57.8	57.8	59.0	58.2	59.8	58.9	59.8	57.9
85°	26.9	26.3	25.0	25.0	25.0	26.3	26.9	26.9	28.7	27.5	27.5
87.5°	9.9	9.3	9.3	8.9	9.3	9.3	9.9	9.9	9.7	10.5	10.7
90°	24.3	24.3	24.3	24.3	24.3	24.3	24.3	24.3	23.6	22.1	23.6
92.5°	43.7	41.4	42.0	40.8	42.0	41.4	43.7	44.4	48.9	55.1	64.3
95°	91.3	85.5	83.2	84.0	83.2	85.5	91.3	100.9	117.2	148.1	193.0
97.5°	200.4	182.3	171.5	165.3	171.5	182.3	200.4	235.6	288.8	368.5	450.4
100°	330.1	298.4	277.0	263.7	277.0	298.4	330.1	391.2	480.4	581.4	672.7
102.5°	562.9	508.8	482.1	464.2	482.1	508.8	562.9	629.3	723.8	797.7	818.3
105°	918.0	872.3	840.7	830.4	840.7	872.3	918.0	963.7	988.1	978.5	895.2
107.5°	1083.3	1080.7	1074.4	1060.6	1074.4	1080.7	1083.3	1077.5	1041.8	965.2	839.8
110°	1110.3	1124.4	1131.0	1130.2	1131.0	1124.4	1110.3	1078.6	1018.2	924.0	792.0



TEST NUMBER: P331395-830

CATALOG NUMBER: SA2XXDIP-C865D725U830-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	165°	170°	175°	180°	185°	190°	195°	200°	205°	210°	215°
112.5°	1089.1	1112.6	1125.1	1129.1	1125.1	1112.6	1089.1	1045.1	975.8	875.0	748.5
115°	1032.9	1066.9	1086.0	1092.7	1086.0	1066.9	1032.9	980.6	904.7	808.2	694.7
117.5°	966.1	1001.9	1022.1	1027.7	1022.1	1001.9	966.1	912.8	841.6	754.0	654.4
120°	922.5	957.1	978.5	985.8	978.5	957.1	922.5	870.9	803.8	725.8	634.3
122.5°	883.0	917.0	936.0	942.2	936.0	917.0	883.0	836.7	776.1	702.2	618.5
125°	834.1	862.0	880.4	886.4	880.4	862.0	834.1	791.3	736.0	671.2	595.3
127.5°	790.6	816.8	832.7	837.4	832.7	816.8	790.6	753.3	702.3	641.1	572.5
130°	764.0	789.1	803.8	809.7	803.8	789.1	764.0	727.9	679.3	621.1	557.7
132.5°	737.0	762.0	775.5	780.8	775.5	762.0	737.0	701.4	655.7	602.3	543.6
135°	694.1	718.4	731.6	734.6	731.6	718.4	694.1	662.3	621.1	572.5	523.9
137.5°	652.2	673.2	684.8	689.2	684.8	673.2	652.2	623.3	587.4	548.7	508.1
140°	623.3	642.4	653.6	658.0	653.6	642.4	623.3	599.7	567.3	533.5	498.0
142.5°	598.6	616.0	625.8	626.7	625.8	616.0	598.6	576.2	549.0	519.9	489.8
145°	564.4	576.9	584.3	586.4	584.3	576.9	564.4	546.7	525.4	502.5	478.2
147.5°	536.4	546.4	551.4	552.7	551.4	546.4	536.4	521.8	506.1	488.3	469.2
150°	518.7	527.5	532.0	532.7	532.0	527.5	518.7	507.7	494.4	478.9	462.7
152.5°	504.5	512.2	515.5	515.6	515.5	512.2	504.5	495.9	484.4	471.3	456.2
155°	486.3	491.4	494.4	492.9	494.4	491.4	486.3	478.2	470.0	459.0	447.2
157.5°	468.0	472.3	473.6	473.6	473.6	472.3	468.0	462.2	455.9	446.7	436.8
160°	456.9	460.5	461.2	461.2	461.2	460.5	456.9	451.7	446.5	438.4	430.3
162.5°	446.8	449.3	450.1	449.4	450.1	449.3	446.8	441.7	437.6	430.7	423.8
165°	430.3	433.2	433.2	432.5	433.2	433.2	430.3	427.3	424.4	419.2	414.1
167.5°	416.3	417.9	417.7	416.9	417.7	417.9	416.3	415.0	412.3	408.8	404.8
170°	407.5	409.6	408.9	407.5	408.9	409.6	407.5	406.7	405.2	402.3	400.1
172.5°	400.4	401.4	400.7	399.8	400.7	401.4	400.4	399.6	398.8	396.4	394.7
175°	391.2	392.0	391.2	389.7	391.2	392.0	391.2	391.2	390.5	389.7	389.0
177.5°	385.5	385.5	384.9	383.7	384.9	385.5	385.5	385.5	385.5	384.9	384.9
180°	383.1	383.1	383.1	383.1	383.1	383.1	383.1	383.1	383.1	383.1	383.1



TEST NUMBER: P331395-830

CATALOG NUMBER: SA2XXDIP-C865D725U830-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	220°	225°	230°	235°	240°	245°	250°	255°	260°	265°	270°
0°	1627.3	1627.3	1627.3	1627.3	1627.3	1627.3	1627.3	1627.3	1627.3	1627.3	1627.3
2.5°	1563.8	1569.3	1577.8	1586.9	1592.3	1602.8	1605.8	1610.8	1615.3	1625.9	1636.8
5°	1473.5	1482.2	1502.9	1514.1	1529.7	1547.9	1559.8	1572.3	1586.1	1609.9	1631.7
7.5°	1376.7	1391.3	1416.9	1437.9	1460.2	1486.3	1505.1	1529.7	1550.3	1583.8	1615.8
10°	1312.1	1332.8	1355.9	1380.9	1412.2	1439.7	1466.0	1497.2	1522.3	1562.3	1599.9
12.5°	1254.1	1257.3	1290.3	1317.9	1360.7	1394.7	1424.9	1465.3	1489.8	1537.3	1576.8
15°	1152.6	1171.4	1201.5	1223.3	1273.9	1317.1	1359.7	1401.6	1429.7	1488.5	1540.4
17.5°	1067.2	1084.5	1115.2	1151.1	1187.5	1230.5	1285.5	1329.6	1367.9	1435.1	1496.5
20°	1013.1	1034.4	1065.7	1102.6	1134.5	1181.4	1229.0	1279.6	1320.9	1396.6	1468.5
22.5°	967.1	983.9	1009.2	1045.6	1080.4	1123.4	1175.4	1230.6	1273.8	1355.6	1428.4
25°	902.5	916.2	932.5	962.5	1001.9	1048.9	1089.5	1150.2	1213.3	1289.6	1377.8
27.5°	844.2	853.9	868.4	894.8	925.3	969.1	1014.3	1071.9	1135.4	1218.2	1311.3
30°	808.7	814.9	829.3	851.2	881.2	915.6	961.3	1016.3	1081.4	1165.2	1257.7
32.5°	777.7	783.4	792.8	813.7	839.7	869.1	910.2	965.3	1027.3	1109.7	1212.2
35°	731.1	735.5	743.7	760.5	774.9	803.7	838.1	888.1	946.2	1025.1	1131.4
37.5°	684.8	690.7	695.7	702.9	721.3	740.3	770.2	812.4	869.5	949.0	1050.4
40°	654.2	659.2	666.7	669.9	684.9	701.7	726.1	764.9	822.5	894.9	993.8
42.5°	623.2	628.2	632.6	636.3	649.3	664.2	686.1	719.3	770.4	840.9	938.8
45°	581.0	581.6	586.0	592.9	599.2	609.8	625.4	654.2	693.6	759.9	848.7
47.5°	538.2	538.9	539.7	542.7	549.6	559.2	569.7	593.0	628.3	681.2	767.6
50°	509.7	508.5	509.7	512.2	516.6	524.7	536.6	553.5	582.3	631.7	711.1
52.5°	482.2	481.9	481.2	482.2	485.6	491.2	499.5	514.0	539.7	585.1	655.1
55°	440.3	437.2	437.8	435.3	440.9	442.1	448.5	460.3	482.9	514.1	579.8
57.5°	395.7	393.0	390.3	389.6	389.0	392.4	397.4	406.8	424.0	451.4	504.7
60°	367.1	364.0	360.2	359.0	359.0	360.9	363.4	370.2	386.5	410.9	454.7
62.5°	338.1	334.5	332.2	328.9	328.0	329.9	332.3	337.2	349.0	371.8	409.6
65°	293.3	289.0	285.8	285.2	284.0	282.1	283.3	288.3	297.7	315.8	345.8
67.5°	248.5	244.3	243.6	239.9	238.2	238.4	238.2	242.4	248.1	263.7	286.1
70°	218.9	215.7	214.5	211.4	210.2	208.9	207.6	211.4	217.1	230.2	249.6
72.5°	188.9	186.2	183.5	180.9	181.2	179.8	179.6	181.9	186.5	198.6	213.5
75°	145.7	146.4	143.3	140.1	139.5	138.2	138.2	140.1	141.9	151.4	163.2
77.5°	105.7	105.2	102.5	101.6	100.9	99.5	100.9	102.2	103.2	109.4	118.2
80°	80.7	80.7	77.6	77.6	76.9	75.0	76.9	75.7	78.1	84.5	90.7
82.5°	57.7	56.6	56.6	55.5	55.4	54.0	55.0	56.2	57.1	61.5	65.1
85°	28.2	28.2	27.5	26.9	27.5	26.9	27.5	28.2	28.7	30.6	33.7
87.5°	10.8	11.5	11.9	11.5	10.5	10.2	10.3	10.5	11.2	11.1	11.1
90°	24.3	25.1	24.3	19.9	14.7	11.0	8.9	7.4	5.9	2.9	0.8
92.5°	80.9	95.8	94.4	73.5	50.1	33.5	26.5	21.5	18.3	13.0	9.0
95°	252.7	288.8	255.7	170.2	106.1	72.2	54.5	42.7	36.1	28.7	25.8
97.5°	517.3	493.0	371.4	229.3	140.0	97.4	77.4	63.8	53.8	46.0	42.0
100°	688.2	582.0	400.8	241.7	151.7	112.7	92.1	77.4	65.6	58.9	56.7
102.5°	751.8	585.0	389.6	242.2	162.4	126.3	105.7	90.3	78.5	71.9	70.3
105°	742.0	545.9	367.7	246.1	180.5	145.9	125.3	109.1	98.0	92.8	89.9
107.5°	677.2	504.1	356.8	256.3	199.1	165.5	144.7	128.7	118.5	113.5	111.1
110°	636.6	484.1	354.4	264.5	211.4	179.1	157.7	142.2	132.6	128.2	125.3



TEST NUMBER: P331395-830

CATALOG NUMBER: SA2XXDIP-C865D725U830-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	220°	225°	230°	235°	240°	245°	250°	255°	260°	265°	270°
112.5°	608.3	471.1	355.0	273.3	223.3	192.0	170.0	155.1	146.2	141.2	138.2
115°	573.3	456.9	358.1	286.6	241.7	210.0	190.1	175.3	166.5	162.1	158.4
117.5°	551.1	449.9	363.4	300.8	258.6	229.3	208.7	194.5	186.7	182.3	179.4
120°	539.3	445.7	366.9	310.2	270.4	241.7	221.0	206.3	199.6	195.3	192.3
122.5°	529.3	443.4	371.1	318.5	281.6	254.7	233.4	218.7	211.4	207.1	204.7
125°	515.0	439.1	377.2	331.6	298.4	271.8	251.3	236.5	227.6	223.3	221.0
127.5°	501.7	436.6	383.6	343.7	314.1	288.2	267.0	252.9	243.2	237.0	234.0
130°	492.9	435.5	388.3	351.5	323.5	297.7	277.0	262.3	251.9	244.6	241.7
132.5°	485.9	434.9	393.0	359.1	331.7	307.1	286.4	271.2	260.2	252.3	248.7
135°	476.0	433.9	398.6	369.1	343.4	319.8	299.2	282.2	271.2	262.3	259.4
137.5°	469.0	433.9	403.6	376.8	352.8	329.5	310.4	293.5	281.7	272.9	269.4
140°	465.0	433.2	406.0	380.9	358.1	336.0	316.8	300.6	288.8	279.9	277.0
142.5°	460.8	433.2	407.7	384.5	362.2	340.7	322.7	307.1	295.3	287.1	284.6
145°	455.3	431.8	409.6	389.0	368.4	348.5	332.2	317.5	306.5	299.2	296.1
147.5°	449.8	429.1	410.3	391.5	373.4	354.7	340.3	328.0	317.8	310.8	308.6
150°	445.0	427.3	409.6	392.7	375.8	358.8	345.5	334.5	324.9	319.1	316.8
152.5°	440.9	424.4	408.5	393.3	378.1	363.0	350.8	340.4	332.0	326.1	325.1
155°	433.2	419.2	406.7	394.2	381.6	369.1	358.1	350.0	341.9	337.4	336.7
157.5°	426.0	414.0	403.3	394.2	384.2	373.5	364.3	357.8	350.7	347.1	346.5
160°	420.8	410.4	401.5	394.2	385.3	376.5	368.4	362.5	356.6	353.6	352.9
162.5°	415.9	407.5	399.8	393.6	386.0	378.2	371.9	366.6	361.9	358.9	359.4
165°	408.2	401.5	396.4	392.0	386.8	380.2	375.8	372.1	367.7	366.2	366.9
167.5°	400.5	396.4	393.0	391.0	386.6	381.8	379.0	376.4	373.5	372.2	373.2
170°	396.4	393.4	391.2	389.7	386.1	382.4	380.2	378.7	376.5	375.8	377.2
172.5°	392.3	389.9	388.9	388.0	385.5	383.0	381.4	380.5	378.2	378.7	379.6
175°	386.8	386.1	385.3	386.1	384.6	383.1	382.4	382.4	380.9	381.6	382.4
177.5°	383.7	383.1	383.7	384.9	383.7	383.1	383.1	383.1	381.9	382.6	383.7
180°	383.1	383.1	383.1	383.1	383.1	383.1	383.1	383.1	383.1	383.1	383.1



TEST NUMBER: P331395-830

CATALOG NUMBER: SA2XXDIP-C865D725U830-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	275°	280°	285°	290°	295°	300°	305°	310°	315°	320°	325°
0°	1627.3	1627.3	1627.3	1627.3	1627.3	1627.3	1627.3	1627.3	1627.3	1627.3	1627.3
2.5°	1635.9	1638.3	1646.3	1654.4	1663.4	1665.8	1669.9	1666.4	1665.4	1674.9	1681.9
5°	1640.5	1651.7	1673.7	1693.7	1710.5	1722.4	1734.9	1739.9	1749.3	1762.5	1778.7
7.5°	1635.2	1657.1	1691.5	1720.7	1752.5	1775.3	1793.2	1808.5	1827.0	1851.9	1879.1
10°	1629.2	1658.6	1700.5	1736.2	1774.9	1804.3	1828.7	1852.5	1880.0	1914.4	1950.0
12.5°	1618.3	1653.1	1705.5	1747.7	1797.4	1826.4	1859.3	1910.5	1940.0	1988.0	2038.2
15°	1596.1	1634.8	1708.0	1759.9	1816.2	1871.2	1931.9	1980.8	2029.5	2057.7	2128.4
17.5°	1563.2	1620.1	1701.1	1761.7	1833.2	1920.0	1988.1	2043.3	2099.7	2145.3	2180.8
20°	1536.6	1598.6	1691.1	1763.7	1848.7	1941.9	2020.2	2076.4	2125.2	2163.3	2185.2
22.5°	1503.2	1581.0	1671.1	1756.1	1864.7	1956.9	2039.1	2083.4	2124.2	2142.8	2151.2
25°	1450.4	1544.2	1646.2	1749.9	1872.5	1970.1	2045.1	2072.0	2083.9	2065.8	2035.7
27.5°	1393.5	1498.0	1617.2	1738.1	1867.7	1961.5	2015.3	2011.1	1990.9	1932.3	1885.4
30°	1350.9	1466.0	1594.2	1726.2	1856.2	1947.6	1978.9	1947.6	1901.9	1836.3	1769.3
32.5°	1306.4	1425.5	1569.7	1709.1	1835.2	1915.5	1922.3	1868.5	1797.8	1723.2	1639.7
35°	1239.0	1367.8	1523.5	1671.1	1790.5	1841.3	1811.2	1716.2	1632.4	1530.4	1416.5
37.5°	1162.8	1305.0	1461.2	1615.4	1723.6	1736.9	1662.4	1562.3	1444.1	1324.3	1190.3
40°	1105.8	1256.5	1417.2	1572.9	1668.6	1654.8	1559.8	1449.7	1309.0	1162.6	1038.2
42.5°	1054.7	1205.4	1369.1	1521.9	1598.6	1560.8	1449.7	1314.7	1163.4	1025.6	911.6
45°	966.3	1121.3	1289.0	1436.6	1480.4	1412.2	1265.3	1115.1	966.3	851.2	761.1
47.5°	880.4	1033.8	1199.8	1329.6	1345.0	1253.3	1092.7	938.3	810.3	716.6	653.1
50°	817.5	971.3	1135.8	1251.5	1246.4	1135.8	970.6	823.7	716.7	641.0	598.5
52.5°	760.9	906.3	1064.2	1169.4	1142.9	1022.2	864.6	734.1	646.2	587.0	548.5
55°	673.0	807.4	957.5	1042.0	993.2	859.3	726.1	621.0	556.0	511.6	481.5
57.5°	585.6	711.7	840.2	892.2	838.3	714.7	603.7	527.4	478.5	445.6	426.1
60°	531.6	641.7	756.1	801.2	736.8	626.7	539.1	471.0	431.5	404.6	387.1
62.5°	477.6	576.2	684.1	708.6	649.7	556.7	479.1	422.4	390.0	366.1	349.6
65°	404.1	484.7	566.7	582.9	528.5	456.6	395.3	358.4	329.6	312.1	299.0
67.5°	331.3	396.2	454.2	467.3	419.6	369.8	325.5	293.3	273.8	259.3	248.2
70°	288.3	339.6	387.1	397.8	359.6	315.2	281.4	255.8	238.3	225.7	215.2
72.5°	242.8	285.6	325.1	332.2	301.0	267.2	239.4	219.2	203.8	195.8	185.6
75°	185.8	210.8	241.4	243.3	222.6	202.0	180.8	167.6	159.5	149.5	144.5
77.5°	131.1	150.7	168.2	171.6	159.4	145.3	133.5	123.1	116.2	111.6	107.0
80°	100.1	115.7	123.2	127.6	118.9	108.9	102.0	95.1	90.7	87.6	84.5
82.5°	71.5	81.2	88.2	91.5	86.8	80.8	73.9	70.0	66.6	64.0	63.0
85°	36.3	40.6	45.1	46.3	45.1	42.5	38.7	38.7	36.9	36.3	36.3
87.5°	13.1	15.6	16.0	17.8	17.2	18.0	18.9	19.4	19.0	18.4	17.7
90°	2.9	5.9	7.4	8.9	11.0	14.7	19.9	24.3	25.1	24.3	23.6
92.5°	13.0	18.3	21.5	26.5	33.5	50.1	73.5	94.4	95.8	80.9	64.3
95°	28.7	36.1	42.7	54.5	72.2	106.1	170.2	255.7	288.8	252.7	193.0
97.5°	46.0	53.8	63.8	77.4	97.4	140.0	229.3	371.4	493.0	517.3	450.4
100°	58.9	65.6	77.4	92.1	112.7	151.7	241.7	400.8	582.0	688.2	672.7
102.5°	71.9	78.5	90.3	105.7	126.3	162.4	242.2	389.6	585.0	751.8	818.3
105°	92.8	98.0	109.1	125.3	145.9	180.5	246.1	367.7	545.9	742.0	895.2
107.5°	113.5	118.5	128.7	144.7	165.5	199.1	256.3	356.8	504.1	677.2	839.8
110°	128.2	132.6	142.2	157.7	179.1	211.4	264.5	354.4	484.1	636.6	792.0



TEST NUMBER: P331395-830

CATALOG NUMBER: SA2XXDIP-C865D725U830-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	275°	280°	285°	290°	295°	300°	305°	310°	315°	320°	325°
112.5°	141.2	146.2	155.1	170.0	192.0	223.3	273.3	355.0	471.1	608.3	748.5
115°	162.1	166.5	175.3	190.1	210.0	241.7	286.6	358.1	456.9	573.3	694.7
117.5°	182.3	186.7	194.5	208.7	229.3	258.6	300.8	363.4	449.9	551.1	654.4
120°	195.3	199.6	206.3	221.0	241.7	270.4	310.2	366.9	445.7	539.3	634.3
122.5°	207.1	211.4	218.7	233.4	254.7	281.6	318.5	371.1	443.4	529.3	618.5
125°	223.3	227.6	236.5	251.3	271.8	298.4	331.6	377.2	439.1	515.0	595.3
127.5°	237.0	243.2	252.9	267.0	288.2	314.1	343.7	383.6	436.6	501.7	572.5
130°	244.6	251.9	262.3	277.0	297.7	323.5	351.5	388.3	435.5	492.9	557.7
132.5°	252.3	260.2	271.2	286.4	307.1	331.7	359.1	393.0	434.9	485.9	543.6
135°	262.3	271.2	282.2	299.2	319.8	343.4	369.1	398.6	433.9	476.0	523.9
137.5°	272.9	281.7	293.5	310.4	329.5	352.8	376.8	403.6	433.9	469.0	508.1
140°	279.9	288.8	300.6	316.8	336.0	358.1	380.9	406.0	433.2	465.0	498.0
142.5°	287.1	295.3	307.1	322.7	340.7	362.2	384.5	407.7	433.2	460.8	489.8
145°	299.2	306.5	317.5	332.2	348.5	368.4	389.0	409.6	431.8	455.3	478.2
147.5°	310.8	317.8	328.0	340.3	354.7	373.4	391.5	410.3	429.1	449.8	469.2
150°	319.1	324.9	334.5	345.5	358.8	375.8	392.7	409.6	427.3	445.0	462.7
152.5°	326.1	332.0	340.4	350.8	363.0	378.1	393.3	408.5	424.4	440.9	456.2
155°	337.4	341.9	350.0	358.1	369.1	381.6	394.2	406.7	419.2	433.2	447.2
157.5°	347.1	350.7	357.8	364.3	373.5	384.2	394.2	403.3	414.0	426.0	436.8
160°	353.6	356.6	362.5	368.4	376.5	385.3	394.2	401.5	410.4	420.8	430.3
162.5°	358.9	361.9	366.6	371.9	378.2	386.0	393.6	399.8	407.5	415.9	423.8
165°	366.2	367.7	372.1	375.8	380.2	386.8	392.0	396.4	401.5	408.2	414.1
167.5°	372.2	373.5	376.4	379.0	381.8	386.6	391.0	393.0	396.4	400.5	404.8
170°	375.8	376.5	378.7	380.2	382.4	386.1	389.7	391.2	393.4	396.4	400.1
172.5°	378.7	378.2	380.5	381.4	383.0	385.5	388.0	388.9	389.9	392.3	394.7
175°	381.6	380.9	382.4	382.4	383.1	384.6	386.1	385.3	386.1	386.8	389.0
177.5°	382.6	381.9	383.1	383.1	383.1	383.7	384.9	383.7	383.1	383.7	384.9
180°	383.1	383.1	383.1	383.1	383.1	383.1	383.1	383.1	383.1	383.1	383.1



TEST NUMBER: P331395-830

CATALOG NUMBER: SA2XXDIP-C865D725U830-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	330°	335°	340°	345°	350°	355°	360°
0°	1627.3	1627.3	1627.3	1627.3	1627.3	1627.3	1627.3
2.5°	1687.9	1694.9	1694.9	1695.9	1703.9	1702.9	1702.4
5°	1796.2	1806.9	1808.1	1819.4	1826.8	1824.4	1817.5
7.5°	1898.4	1918.2	1933.2	1941.5	1951.4	1957.6	1954.8
10°	1979.4	2008.2	2025.7	2037.6	2052.0	2062.7	2058.9
12.5°	2053.0	2087.3	2111.3	2131.7	2133.5	2147.2	2138.0
15°	2167.8	2203.9	2207.7	2222.7	2234.7	2233.4	2234.0
17.5°	2205.6	2217.2	2219.6	2220.0	2220.2	2215.7	2206.2
20°	2192.1	2187.7	2177.1	2169.0	2154.6	2152.7	2140.2
22.5°	2128.1	2114.2	2087.5	2069.9	2047.5	2041.6	2038.2
25°	2002.0	1971.3	1928.8	1888.1	1876.9	1855.0	1861.2
27.5°	1829.0	1781.2	1735.1	1702.1	1672.3	1639.5	1648.9
30°	1707.4	1653.6	1588.6	1538.5	1506.7	1475.4	1469.7
32.5°	1562.3	1483.5	1411.0	1366.9	1318.1	1298.3	1276.6
35°	1312.1	1235.2	1163.3	1101.4	1065.7	1038.2	1013.1
37.5°	1087.1	998.5	940.5	890.3	864.6	848.9	852.8
40°	947.5	870.0	827.5	789.3	765.5	754.2	756.8
42.5°	834.4	776.4	741.4	715.2	698.4	692.2	690.7
45°	706.1	673.5	644.8	629.8	621.7	614.8	610.4
47.5°	618.5	592.0	575.8	566.8	559.8	552.7	552.6
50°	566.0	548.5	537.2	527.8	522.3	517.3	521.6
52.5°	525.9	510.0	498.7	490.3	488.2	483.7	483.6
55°	466.6	454.0	445.9	438.4	434.7	432.2	429.0
57.5°	412.6	400.7	393.1	388.4	381.3	378.7	377.8
60°	374.0	364.6	357.1	350.8	347.7	342.7	342.7
62.5°	338.5	329.1	322.1	317.4	312.2	310.2	310.8
65°	287.1	279.6	272.7	267.7	266.5	262.7	263.9
67.5°	239.8	234.8	227.5	224.8	222.4	220.4	218.9
70°	208.3	203.3	199.5	195.8	193.9	193.9	193.9
72.5°	181.7	175.8	173.5	168.7	169.8	167.9	165.9
75°	140.7	137.0	135.1	133.2	130.1	130.1	130.1
77.5°	103.6	102.5	100.2	98.2	97.5	96.8	97.1
80°	80.0	79.5	78.1	78.1	76.9	76.3	75.0
82.5°	61.5	59.9	59.2	58.6	58.4	58.2	58.1
85°	35.1	33.7	33.7	34.4	33.2	33.2	33.7
87.5°	17.9	18.2	17.9	17.9	18.4	17.9	17.9
90°	22.1	23.6	24.3	24.3	24.3	24.3	24.3
92.5°	55.1	48.9	44.4	43.7	41.4	42.0	40.8
95°	148.1	117.2	100.9	91.3	85.5	83.2	84.0
97.5°	368.5	288.8	235.6	200.4	182.3	171.5	165.3
100°	581.4	480.4	391.2	330.1	298.4	277.0	263.7
102.5°	797.7	723.8	629.3	562.9	508.8	482.1	464.2
105°	978.5	988.1	963.7	918.0	872.3	840.7	830.4
107.5°	965.2	1041.8	1077.5	1083.3	1080.7	1074.4	1060.6
110°	924.0	1018.2	1078.6	1110.3	1124.4	1131.0	1130.2



TEST NUMBER: P331395-830

CATALOG NUMBER: SA2XXDIP-C865D725U830-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	330°	335°	340°	345°	350°	355°	360°
112.5°	875.0	975.8	1045.1	1089.1	1112.6	1125.1	1129.1
115°	808.2	904.7	980.6	1032.9	1066.9	1086.0	1092.7
117.5°	754.0	841.6	912.8	966.1	1001.9	1022.1	1027.7
120°	725.8	803.8	870.9	922.5	957.1	978.5	985.8
122.5°	702.2	776.1	836.7	883.0	917.0	936.0	942.2
125°	671.2	736.0	791.3	834.1	862.0	880.4	886.4
127.5°	641.1	702.3	753.3	790.6	816.8	832.7	837.4
130°	621.1	679.3	727.9	764.0	789.1	803.8	809.7
132.5°	602.3	655.7	701.4	737.0	762.0	775.5	780.8
135°	572.5	621.1	662.3	694.1	718.4	731.6	734.6
137.5°	548.7	587.4	623.3	652.2	673.2	684.8	689.2
140°	533.5	567.3	599.7	623.3	642.4	653.6	658.0
142.5°	519.9	549.0	576.2	598.6	616.0	625.8	626.7
145°	502.5	525.4	546.7	564.4	576.9	584.3	586.4
147.5°	488.3	506.1	521.8	536.4	546.4	551.4	552.7
150°	478.9	494.4	507.7	518.7	527.5	532.0	532.7
152.5°	471.3	484.4	495.9	504.5	512.2	515.5	515.6
155°	459.0	470.0	478.2	486.3	491.4	494.4	492.9
157.5°	446.7	455.9	462.2	468.0	472.3	473.6	473.6
160°	438.4	446.5	451.7	456.9	460.5	461.2	461.2
162.5°	430.7	437.6	441.7	446.8	449.3	450.1	449.4
165°	419.2	424.4	427.3	430.3	433.2	433.2	432.5
167.5°	408.8	412.3	415.0	416.3	417.9	417.7	416.9
170°	402.3	405.2	406.7	407.5	409.6	408.9	407.5
172.5°	396.4	398.8	399.6	400.4	401.4	400.7	399.8
175°	389.7	390.5	391.2	391.2	392.0	391.2	389.7
177.5°	384.9	385.5	385.5	385.5	385.5	384.9	383.7
180°	383.1	383.1	383.1	383.1	383.1	383.1	383.1

(END OF REPORT)