

Scaled data based on original data using  
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State  
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P331399-830

Luminaire Tested: **SA2XXDIP-C865D725U830-4F0-1E-UDD-F**

Issue Date: 10/7/2019

**Test Information**

Test Method: LM-79-08  
Report Number: P331399-830  
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-2,  
Test Lab: INNOVATION CENTER  
Issue Date: 10/7/2019  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: NEO-RAY  
Catalog Number: SA2XXDIP-C865D725U830-4F0-1E-UDD-F  
Description: DEFINE 2 DIRECT-INDIRECT PENDANT LED LUMINAIRE  
DOWNLIGHT 865 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER  
UPLIGHT 725 LUMENS PER FOOT, NO LENS  
Light Source: -  
Ballast/Driver: ELECTRONIC DRIVER


**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 6042.2 lumens  
Efficiency: N/A  
Efficacy: 111.1 lumens/watt  
Spacing Criteria (0/90/45): 1.2 / 1.16 / 1.3  
Luminous Opening: Rectangular (W 0.17' x L: 4' x H: 0')  
CIE Type: General Diffuse  
  
Input Watts (W): 54.4  
Input Voltage (V): 120  
Input Current (Ain): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 25 FT



TEST NUMBER: P331399-830  
CATALOG NUMBER: SA2XXDIP-C865D725U830-4F0-1E-UDD-F

### Luminous Intensity Polar Plot





TEST NUMBER: P331399-830

CATALOG NUMBER: SA2XXDIP-C865D725U830-4F0-1E-UDD-F

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	108	108	108	108	101	101	101	101	86	86	86	73	73	73	61	61	61	55
1	99	94	91	87	92	88	84	81	75	73	71	64	62	61	54	52	51	46
2	90	83	76	71	83	77	71	67	66	62	59	56	53	51	47	45	43	39
3	82	73	65	59	76	68	61	56	58	53	49	50	46	43	42	39	37	33
4	75	64	56	50	69	60	53	47	52	46	42	44	40	37	37	34	32	28
5	69	57	49	43	64	54	46	41	46	41	36	40	35	32	34	30	28	24
6	64	51	43	37	59	48	41	35	42	36	32	36	31	28	31	27	24	21
7	59	46	38	33	54	44	36	31	38	32	28	33	28	25	28	24	22	19
8	55	42	34	29	51	40	33	28	35	29	25	30	25	22	26	22	19	17
9	51	39	31	26	47	36	29	25	32	26	22	28	23	20	24	20	17	15
10	48	35	28	23	44	33	27	22	29	24	20	26	21	18	22	18	16	14

**AVERAGE LUMINANCE (cd/sqm):**

	0°	45°	90°
0°	21001	21001	21001
5°	21081	20778	20900
10°	20956	20566	20669
15°	20697	20301	20277
20°	20330	19900	19878
25°	19963	19408	19408
30°	19494	18957	18793
35°	19056	18413	18143
40°	18506	17873	17530
45°	17961	17335	16908
50°	17372	16777	16179
55°	16757	16124	15527
60°	16075	15345	14783
65°	15339	14571	13903
70°	14408	13638	12987
75°	13107	12558	12246
80°	11632	11278	10702
85°	9503	9040	8096



TEST NUMBER: P331399-830

CATALOG NUMBER: SA2XXDIP-C865D725U830-4F0-1E-UDD-F

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	122.3	2.0
10°-20°	344.2	5.7
20°-30°	505.9	8.4
30°-40°	587.6	9.7
40°-50°	587.0	9.7
50°-60°	511.9	8.5
60°-70°	378.5	6.3
70°-80°	214.4	3.5
80°-90°	59.9	1.0
90°-100°	31.1	0.5
100°-110°	114.0	1.9
110°-120°	304.7	5.0
120°-130°	502.9	8.3
130°-140°	534.9	8.9
140°-150°	497.1	8.2
150°-160°	399.7	6.6
160°-170°	257.6	4.3
170°-180°	88.7	1.5
0°-30°	972.3	16.1
0°-40°	1559.9	25.8
0°-60°	2658.7	44.0
0°-90°	3311.5	54.8
90°-120°	449.7	7.4
90°-150°	1984.7	32.8
90°-180°	2731.0	45.2
0°-180°	6042.2	100.0

**CANDELA DISTRIBUTION:**

	0°	22.5°	45°	67.5°	90°	Flux
0°	1301	1301	1301	1301	1301	
5°	1301	1295	1282	1291	1290	123
15°	1238	1230	1214	1219	1213	348
25°	1121	1110	1089	1092	1089	515
35°	967	954	934	927	920	603
45°	787	777	759	746	740	607
55°	595	587	573	558	552	532
65°	402	394	381	370	364	397
75°	210	207	201	194	196	224
85°	51	50	49	45	44	59
90°	1	8	14	17	18	5
95°	44	23	26	29	29	54
105°	205	214	41	48	51	219
115°	388	399	416	118	55	382
125°	548	557	570	574	576	489
135°	678	689	695	701	700	524
145°	787	787	798	802	799	492
155°	866	861	868	872	867	399
165°	913	909	911	915	911	258
175°	934	929	930	934	928	89
180°	932	932	932	932	932	



TEST NUMBER: P331399-830

CATALOG NUMBER: SA2XXDIP-C865D725U830-4F0-1E-UDD-F

**CANDELA DISTRIBUTION (FULL):**

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	1300.7	1300.7	1300.7	1300.7	1300.7	1300.7	1300.7	1300.7	1300.7	1300.7	1300.7
2.5°	1306.7	1305.6	1304.5	1303.4	1302.3	1300.5	1298.1	1295.6	1293.2	1290.7	1293.0
5°	1300.7	1299.6	1298.5	1297.4	1296.3	1294.2	1291.2	1288.1	1285.1	1282.0	1284.2
7.5°	1289.2	1287.5	1285.8	1284.0	1282.3	1279.9	1276.8	1273.7	1270.5	1267.4	1269.7
10°	1278.2	1276.3	1274.3	1272.3	1270.5	1267.8	1264.4	1261.1	1257.8	1254.4	1256.7
12.5°	1263.2	1261.5	1259.8	1258.0	1256.3	1253.8	1250.5	1247.1	1243.8	1240.5	1242.0
15°	1238.2	1236.5	1234.8	1233.2	1231.5	1228.9	1225.3	1221.6	1218.0	1214.5	1215.5
17.5°	1206.2	1204.5	1202.9	1201.2	1199.5	1196.8	1193.2	1189.5	1185.8	1182.1	1183.5
20°	1183.2	1181.5	1179.9	1178.2	1176.5	1173.7	1169.8	1165.9	1162.1	1158.2	1159.0
22.5°	1160.2	1157.8	1155.5	1153.1	1150.8	1147.8	1144.2	1140.5	1136.8	1133.1	1133.3
25°	1120.6	1118.4	1116.2	1114.0	1111.7	1108.2	1103.5	1098.8	1094.1	1089.4	1090.0
27.5°	1075.6	1073.7	1071.6	1069.6	1067.6	1064.7	1061.0	1057.2	1053.6	1049.8	1049.0
30°	1045.6	1043.4	1041.1	1039.0	1036.7	1033.5	1029.4	1025.2	1021.0	1016.8	1016.0
32.5°	1013.6	1011.8	1010.0	1008.2	1006.4	1003.3	999.0	994.6	990.2	985.8	984.3
35°	966.8	964.0	961.2	958.5	955.6	952.1	947.6	943.2	938.7	934.2	932.6
37.5°	914.0	911.5	909.1	906.6	904.3	900.8	896.4	891.9	887.4	883.0	880.9
40°	878.0	875.8	873.5	871.3	869.1	865.7	861.3	856.9	852.4	848.0	845.5
42.5°	843.0	840.7	838.5	836.3	834.1	830.8	826.3	821.9	817.4	812.9	810.2
45°	786.6	784.8	782.8	780.9	778.9	775.8	771.7	767.5	763.4	759.2	756.1
47.5°	730.7	728.9	727.0	725.2	723.3	720.2	715.9	711.5	707.2	702.9	699.6
50°	691.6	690.2	688.9	687.5	686.1	683.4	679.6	675.6	671.8	667.9	664.0
52.5°	653.7	651.8	650.0	648.1	646.3	643.6	639.9	636.2	632.5	628.9	625.7
55°	595.3	593.7	592.0	590.3	588.6	586.2	582.9	579.5	576.2	572.8	569.5
57.5°	536.8	535.5	534.1	532.8	531.5	529.0	525.3	521.6	517.9	514.3	511.0
60°	497.8	496.6	495.6	494.5	493.3	490.9	486.9	483.1	479.2	475.2	472.2
62.5°	459.8	458.0	456.2	454.4	452.6	450.3	447.2	444.2	441.2	438.3	435.5
65°	401.5	399.8	398.1	396.4	394.8	392.6	389.8	387.0	384.3	381.4	379.0
67.5°	342.2	340.8	339.5	338.2	336.9	335.0	332.4	329.9	327.4	324.9	323.0
70°	305.2	304.1	302.9	301.8	300.8	298.9	296.4	293.9	291.4	288.9	287.0
72.5°	267.1	266.1	264.9	263.8	262.7	261.4	259.8	258.2	256.5	254.9	253.0
75°	210.1	209.5	209.0	208.5	207.9	206.9	205.6	204.2	202.7	201.3	199.7
77.5°	159.1	158.2	157.2	156.3	155.3	154.6	154.0	153.4	152.9	152.3	151.5
80°	125.1	124.8	124.5	124.2	123.9	123.6	123.0	122.4	121.9	121.3	120.5
82.5°	93.0	93.0	92.9	92.8	92.8	92.7	92.3	92.0	91.6	91.3	90.2
85°	51.3	51.0	50.7	50.4	50.1	49.9	49.6	49.3	49.0	48.8	48.0
87.5°	18.2	18.0	17.9	17.8	17.7	17.5	17.3	17.2	16.9	16.7	16.2
90°	0.7	2.4	4.0	5.7	7.3	8.7	9.9	11.1	12.3	13.5	14.2
92.5°	13.6	13.5	13.3	13.2	13.0	13.3	13.9	14.4	15.1	15.6	16.0
95°	43.8	38.9	33.9	29.0	24.0	22.1	23.2	24.2	25.3	26.3	27.1
97.5°	87.0	73.0	59.1	45.1	31.2	25.4	27.9	30.3	32.8	35.2	35.8
100°	119.3	98.8	78.3	57.8	37.2	28.3	30.8	33.4	35.9	38.5	39.6
102.5°	155.0	150.6	146.3	141.9	137.5	124.7	103.4	82.1	60.8	39.5	41.1
105°	205.0	209.4	214.0	218.5	222.9	204.7	163.8	122.9	82.0	41.1	42.8
107.5°	262.0	265.6	269.3	272.9	276.5	253.8	204.7	155.7	106.6	57.6	55.9
110°	298.7	301.8	305.0	308.1	311.2	291.2	247.9	204.6	161.3	118.0	103.0



TEST NUMBER: P331399-830

CATALOG NUMBER: SA2XXDIP-C865D725U830-4F0-1E-UDD-F

**CANDELA DISTRIBUTION (continued):**

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	333.2	336.0	338.7	341.6	344.3	340.4	329.7	319.0	308.3	297.6	243.0
115°	387.7	390.2	392.8	395.3	397.8	401.1	404.7	408.5	412.3	416.0	346.7
117.5°	436.4	439.2	442.1	444.9	447.7	450.4	453.1	455.6	458.2	460.8	444.0
120°	471.9	474.2	476.5	478.7	481.0	483.4	486.2	488.8	491.5	494.2	496.0
122.5°	502.2	504.5	506.9	509.3	511.6	514.3	517.3	520.2	523.1	526.0	527.1
125°	548.2	550.1	552.0	554.0	555.9	558.4	561.2	564.0	566.8	569.8	570.8
127.5°	589.8	592.0	594.2	596.3	598.4	600.6	602.8	604.8	607.0	609.1	610.7
130°	616.2	618.7	621.0	623.4	625.8	627.8	629.5	631.1	632.8	634.4	636.1
132.5°	643.2	645.3	647.3	649.3	651.4	653.2	654.9	656.5	658.2	659.8	661.2
135°	678.3	680.7	683.1	685.5	687.9	689.8	691.1	692.4	693.8	695.1	696.6
137.5°	713.8	715.4	717.1	718.8	720.5	722.1	723.6	725.1	726.6	728.2	729.6
140°	737.0	738.1	739.3	740.6	741.7	743.2	744.8	746.5	748.1	749.8	751.1
142.5°	756.4	757.4	758.6	759.6	760.6	762.1	764.0	765.9	767.8	769.7	770.9
145°	786.8	786.6	786.6	786.4	786.3	787.4	789.9	792.5	795.0	797.6	798.7
147.5°	813.4	812.8	812.3	811.7	811.2	812.1	814.6	817.1	819.6	822.2	822.9
150°	830.7	829.6	828.6	827.6	826.4	827.2	829.5	831.9	834.3	836.7	837.6
152.5°	845.2	844.0	842.9	841.7	840.6	841.1	843.4	845.6	847.9	850.2	851.1
155°	866.4	865.1	863.7	862.3	861.0	861.2	863.0	864.8	866.6	868.4	869.3
157.5°	883.0	881.8	880.7	879.6	878.4	878.4	879.8	881.0	882.2	883.5	884.6
160°	892.7	891.7	890.9	889.9	889.1	889.1	889.9	890.9	891.7	892.7	893.6
162.5°	901.4	900.4	899.6	898.6	897.7	897.7	898.4	899.2	900.0	900.8	901.8
165°	912.9	912.0	911.2	910.2	909.3	909.1	909.6	910.0	910.4	910.9	911.9
167.5°	921.5	920.7	919.7	918.9	917.9	917.7	918.1	918.5	919.0	919.4	920.4
170°	926.4	925.5	924.6	923.7	922.8	922.5	922.8	923.1	923.4	923.7	924.7
172.5°	929.6	928.7	927.8	926.9	926.0	925.8	926.0	926.3	926.6	926.9	928.0
175°	933.8	932.7	931.7	930.7	929.6	929.3	929.5	929.8	930.1	930.5	931.5
177.5°	934.5	933.7	932.8	932.0	931.1	930.8	930.9	931.0	931.1	931.2	932.1
180°	931.8	931.8	931.8	931.8	931.8	931.8	931.8	931.8	931.8	931.8	931.8



TEST NUMBER: P331399-830

CATALOG NUMBER: SA2XXDIP-C865D725U830-4F0-1E-UDD-F

**CANDELA DISTRIBUTION (continued):**

	55°	60°	65°	70°	75°	80°	85°	90°
0°	1300.7	1300.7	1300.7	1300.7	1300.7	1300.7	1300.7	1300.7
2.5°	1295.1	1297.4	1299.6	1300.5	1300.0	1299.6	1299.2	1298.7
5°	1286.4	1288.6	1290.9	1291.7	1291.2	1290.6	1290.1	1289.5
7.5°	1271.9	1274.1	1276.4	1277.1	1276.6	1275.9	1275.4	1274.7
10°	1258.9	1261.1	1263.4	1264.0	1263.2	1262.3	1261.5	1260.7
12.5°	1243.6	1245.1	1246.7	1247.2	1246.5	1245.9	1245.3	1244.7
15°	1216.6	1217.8	1218.9	1218.7	1217.4	1216.0	1214.6	1213.1
17.5°	1184.7	1186.0	1187.3	1187.2	1185.9	1184.6	1183.3	1181.9
20°	1159.8	1160.6	1161.5	1161.3	1160.3	1159.1	1158.0	1156.9
22.5°	1133.5	1133.6	1133.8	1133.6	1132.8	1132.2	1131.5	1130.9
25°	1090.5	1091.0	1091.6	1091.6	1091.0	1090.5	1090.0	1089.4
27.5°	1048.2	1047.4	1046.5	1045.5	1044.1	1042.7	1041.4	1040.1
30°	1015.1	1014.4	1013.5	1012.5	1011.4	1010.3	1009.2	1008.0
32.5°	982.8	981.3	979.8	978.5	977.4	976.3	975.2	974.0
35°	930.9	929.3	927.7	926.0	924.7	923.3	921.9	920.5
37.5°	878.9	876.8	874.8	873.1	871.8	870.4	869.1	867.7
40°	843.0	840.5	838.0	836.1	835.1	834.0	832.8	831.7
42.5°	807.5	804.7	802.1	799.9	798.3	796.8	795.2	793.7
45°	753.1	750.0	747.0	744.9	743.8	742.6	741.5	740.5
47.5°	696.4	693.2	690.0	687.6	686.0	684.4	682.8	681.2
50°	660.1	656.2	652.3	649.7	648.3	646.9	645.5	644.1
52.5°	622.4	619.2	616.0	613.4	611.6	609.7	607.9	606.1
55°	566.2	562.8	559.5	557.1	555.7	554.3	553.0	551.6
57.5°	507.7	504.4	501.1	499.0	497.9	496.9	495.9	494.7
60°	469.2	466.1	463.1	461.1	460.2	459.4	458.5	457.8
62.5°	432.5	429.7	426.9	425.0	423.9	422.8	421.8	420.8
65°	376.5	374.0	371.5	369.5	368.2	366.7	365.3	363.9
67.5°	321.0	319.1	317.2	315.7	314.5	313.4	312.3	311.1
70°	285.0	283.0	281.2	279.6	278.5	277.4	276.3	275.1
72.5°	251.0	249.0	247.1	245.7	244.8	243.9	243.0	242.1
75°	198.0	196.3	194.7	194.2	194.7	195.3	195.8	196.3
77.5°	150.7	149.9	149.0	148.2	147.4	146.7	145.9	145.1
80°	119.6	118.9	118.0	117.3	116.7	116.2	115.6	115.1
82.5°	89.2	88.1	87.1	86.5	86.3	86.2	86.1	86.1
85°	47.1	46.3	45.4	44.9	44.6	44.3	44.0	43.7
87.5°	15.6	15.2	14.6	14.3	14.1	13.9	13.9	13.7
90°	15.0	15.7	16.5	17.0	17.3	17.6	17.9	18.2
92.5°	16.4	16.8	17.2	17.5	17.6	17.8	18.0	18.2
95°	27.8	28.6	29.3	29.6	29.4	29.3	29.1	29.0
97.5°	36.4	36.9	37.6	38.0	38.2	38.4	38.5	38.7
100°	40.8	42.0	43.3	44.0	44.3	44.6	44.9	45.1
102.5°	42.6	44.2	45.7	46.8	47.1	47.6	48.0	48.4
105°	44.4	46.1	47.7	48.8	49.5	50.0	50.6	51.3
107.5°	54.2	52.5	50.9	50.3	50.9	51.6	52.1	52.7
110°	88.0	73.0	58.1	50.9	51.5	52.0	52.7	53.3





TEST NUMBER: P331399-830

CATALOG NUMBER: SA2XXDIP-C865D725U830-4F0-1E-UDD-F

**CANDELA DISTRIBUTION (continued):**

	55°	60°	65°	70°	75°	80°	85°	90°
112.5°	188.3	133.7	79.0	51.8	52.4	52.9	53.3	53.8
115°	277.3	207.9	138.6	98.4	87.7	76.8	66.1	55.3
117.5°	427.3	410.4	393.6	367.5	332.1	296.6	261.2	225.7
120°	497.9	499.6	501.4	492.2	471.9	451.8	431.5	411.3
122.5°	528.2	529.2	530.4	529.0	525.0	521.0	517.2	513.2
125°	571.8	572.9	573.9	574.7	575.1	575.6	576.0	576.5
127.5°	612.2	613.7	615.2	616.0	616.1	616.2	616.3	616.4
130°	637.7	639.4	641.0	641.8	641.7	641.5	641.3	641.2
132.5°	662.6	664.0	665.4	666.1	665.9	665.8	665.6	665.4
135°	698.1	699.6	701.2	701.7	701.4	701.2	700.8	700.5
137.5°	731.1	732.5	734.1	734.5	734.1	733.5	733.0	732.4
140°	752.4	753.8	755.2	755.4	754.7	753.9	753.2	752.4
142.5°	772.1	773.4	774.6	774.9	774.1	773.4	772.6	771.8
145°	799.7	800.8	801.8	801.9	801.3	800.5	799.7	799.0
147.5°	823.7	824.5	825.3	825.4	824.7	824.1	823.5	822.8
150°	838.5	839.4	840.3	840.4	839.6	838.9	838.1	837.4
152.5°	852.0	852.9	853.8	853.8	852.8	851.8	850.8	849.8
155°	870.2	871.1	872.0	871.9	870.6	869.5	868.3	867.0
157.5°	885.5	886.6	887.6	887.5	886.4	885.1	884.0	882.9
160°	894.5	895.4	896.3	896.2	895.1	894.1	893.1	892.0
162.5°	902.8	903.8	904.8	904.7	903.4	902.1	900.9	899.6
165°	912.9	914.1	915.1	915.1	914.1	912.9	911.9	910.9
167.5°	921.5	922.6	923.6	923.4	922.1	920.8	919.4	918.0
170°	925.8	926.8	927.9	927.7	926.4	925.0	923.7	922.4
172.5°	929.1	930.1	931.1	930.9	929.6	928.3	926.9	925.6
175°	932.6	933.6	934.6	934.4	932.9	931.4	929.9	928.4
177.5°	932.9	933.8	934.6	934.5	933.4	932.4	931.2	930.2
180°	931.8	931.8	931.8	931.8	931.8	931.8	931.8	931.8

(END OF REPORT)