

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P333507-840

Luminaire Tested: **S125RDIP-S375D810U840-4F0-1E-UDD-F4**

Issue Date: 3/3/2020

Test Information

Test Method: LM-79-08
Report Number: P333507-840
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-19,
Test Lab: INNOVATION CENTER
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: NEO-RAY
Catalog Number: S125RDIP-S375D810U840-4F0-1E-UDD-F4
Description: DEFINE 5 DIRECT-INDIRECT PENDANT LED LUMINAIRE
DOWNLIGHT 375 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER, REGRESSED
HOUSING
UPLIGHT 810 LUMENS PER FOOT, BATWING OPTIC
Light Source: -
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 4399.0 lumens
Efficiency: N/A
Efficacy: 141.0 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 1.11 / 1.25
Luminous Opening: Rectangular (W 0.42' x L: 4' x H: 0')
CIE Type: Semi-Indirect


Input Watts (W): 31.2
Input Voltage (V): 120
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P333507-840

CATALOG NUMBER: S125RDIP-S375D810U840-4F0-1E-UDD-F4

Luminous Intensity Polar Plot





TEST NUMBER: P333507-840

CATALOG NUMBER: S125RDIP-S375D810U840-4F0-1E-UDD-F4

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10
RCR																	
0	103	103	103	103	93	93	93	93	74	74	74	57	57	57	41	41	41
1	94	90	86	83	85	81	78	75	65	63	61	50	49	47	36	35	35
2	86	79	73	68	77	71	66	62	57	54	51	44	42	40	32	31	29
3	78	69	62	57	70	63	57	52	50	46	43	39	36	34	28	27	25
4	72	61	54	48	64	56	49	44	45	40	36	35	32	29	25	23	22
5	66	55	47	41	59	50	43	38	40	35	31	31	28	25	23	21	19
6	60	49	41	35	54	44	38	33	36	31	27	28	25	22	21	19	17
7	56	44	36	31	50	40	33	29	33	28	24	26	22	19	19	17	15
8	52	40	32	27	47	36	30	25	30	25	21	23	20	17	18	15	13
9	48	36	29	24	43	33	27	22	27	22	19	22	18	15	16	14	12
10	45	33	26	22	41	30	24	20	25	20	17	20	16	14	15	13	11

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	3991	3991	3991
5°	4000	3955	3979
10°	3970	3918	3918
15°	3922	3839	3807
20°	3862	3727	3682
25°	3792	3619	3539
30°	3703	3491	3380
35°	3613	3360	3202
40°	3530	3222	3026
45°	3428	3070	2834
50°	3325	2903	2635
55°	3206	2743	2423
60°	3086	2550	2195
65°	2946	2326	1932
70°	2783	2045	1665
75°	2563	1724	1385
80°	2258	1354	1164
85°	1904	1104	1037



TEST NUMBER: P333507-840

CATALOG NUMBER: S125RDIP-S375D810U840-4F0-1E-UDD-F4

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	58.1	1.3
10°-20°	162.4	3.7
20°-30°	235.5	5.4
30°-40°	268.4	6.1
40°-50°	261.6	5.9
50°-60°	220.2	5.0
60°-70°	154.3	3.5
70°-80°	79.3	1.8
80°-90°	22.2	0.5
90°-100°	283.9	6.5
100°-110°	610.3	13.9
110°-120°	572.7	13.0
120°-130°	464.2	10.6
130°-140°	372.5	8.5
140°-150°	281.1	6.4
150°-160°	197.9	4.5
160°-170°	116.6	2.7
170°-180°	37.9	0.9
0°-30°	456.0	10.4
0°-40°	724.3	16.5
0°-60°	1206.1	27.4
0°-90°	1462.0	33.2
90°-120°	1466.9	33.3
90°-150°	2584.6	58.8
90°-180°	2937.0	66.8
0°-180°	4399.0	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	618	618	618	618	618	
5°	617	615	610	614	614	58
15°	587	584	574	573	569	165
25°	532	524	508	502	497	245
35°	458	447	426	413	406	287
45°	375	361	336	318	310	289
55°	285	269	244	223	215	255
65°	193	176	152	134	126	191
75°	103	88	69	59	56	109
85°	26	18	15	14	14	29
90°	1	7	13	17	18	3
95°	26	77	700	317	186	28
105°	89	125	572	1127	1046	94
115°	160	192	460	991	1166	157
125°	221	259	441	788	918	196
135°	259	311	438	660	763	201
145°	302	346	439	547	602	189
155°	344	370	428	484	504	158
165°	376	386	411	436	442	106
175°	391	391	394	399	397	37
180°	392	392	392	392	392	



TEST NUMBER: P333507-840

CATALOG NUMBER: S125RDIP-S375D810U840-4F0-1E-UDD-F4

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	617.9	617.9	617.9	617.9	617.9	617.9	617.9	617.9	617.9	617.9	617.9
2.5°	619.0	618.8	618.5	618.3	618.0	617.5	616.7	615.8	615.0	614.2	615.0
5°	617.0	616.6	616.2	615.7	615.3	614.6	613.4	612.3	611.2	610.0	611.1
7.5°	611.0	610.6	610.2	609.8	609.4	608.4	607.1	605.7	604.4	603.0	603.7
10°	605.3	605.0	604.7	604.4	604.1	603.2	601.8	600.3	598.8	597.4	597.7
12.5°	599.0	598.5	598.2	597.8	597.4	596.2	594.3	592.4	590.4	588.4	588.7
15°	586.6	586.0	585.4	584.8	584.2	582.8	580.6	578.5	576.2	574.1	574.0
17.5°	572.8	571.8	570.9	569.9	569.0	567.1	564.3	561.6	558.9	556.1	555.6
20°	561.9	560.9	559.9	558.9	557.7	555.6	552.3	549.0	545.6	542.3	541.8
22.5°	550.0	549.0	548.0	546.8	545.8	543.6	540.1	536.6	533.1	529.7	528.7
25°	532.1	530.5	529.0	527.4	525.8	523.1	519.3	515.4	511.6	507.8	506.4
27.5°	511.5	509.7	507.8	505.8	503.9	501.0	496.9	492.7	488.7	484.5	482.6
30°	496.6	494.6	492.6	490.7	488.7	485.5	481.2	476.9	472.5	468.1	465.7
32.5°	482.0	479.7	477.5	475.1	472.8	469.5	465.0	460.6	456.2	451.7	449.1
35°	458.3	455.9	453.3	450.8	448.4	444.7	440.1	435.5	430.8	426.2	423.1
37.5°	435.0	432.0	429.0	426.0	422.9	419.0	414.2	409.4	404.7	399.8	396.2
40°	418.7	415.6	412.4	409.3	406.2	402.1	397.2	392.2	387.2	382.2	378.3
42.5°	401.4	398.3	395.1	391.9	388.7	384.6	379.4	374.3	369.1	364.0	360.2
45°	375.3	372.2	369.2	366.2	363.2	358.8	353.1	347.5	341.7	336.1	331.8
47.5°	348.1	344.9	341.7	338.5	335.4	330.9	325.2	319.4	313.7	307.9	303.7
50°	330.9	327.5	324.1	320.6	317.2	312.6	306.6	300.7	294.8	288.9	284.6
52.5°	312.3	308.7	305.2	301.7	298.2	293.7	288.1	282.5	276.9	271.4	266.7
55°	284.7	281.3	278.0	274.8	271.5	266.9	261.1	255.2	249.4	243.6	238.9
57.5°	256.9	253.4	249.7	246.2	242.7	238.1	232.5	226.9	221.4	215.7	211.2
60°	238.9	235.3	231.7	228.0	224.4	219.8	214.2	208.6	203.0	197.4	192.9
62.5°	219.9	216.4	213.0	209.5	206.0	201.5	195.8	190.2	184.4	178.7	174.5
65°	192.8	189.2	185.7	182.2	178.6	174.1	168.6	163.2	157.6	152.2	148.0
67.5°	165.8	162.3	158.8	155.2	151.7	147.2	142.0	136.7	131.5	126.2	122.4
70°	147.4	144.0	140.5	136.9	133.4	129.1	123.8	118.7	113.5	108.3	105.0
72.5°	129.6	126.1	122.7	119.3	115.8	111.6	106.7	101.9	97.0	92.2	89.3
75°	102.7	99.6	96.4	93.3	90.3	86.5	82.1	77.8	73.4	69.1	66.8
77.5°	75.9	73.5	71.0	68.5	66.0	63.0	59.6	56.0	52.6	49.1	47.5
80°	60.7	58.2	55.7	53.2	50.7	48.1	45.1	42.2	39.3	36.4	35.4
82.5°	45.7	43.5	41.3	39.0	36.8	34.6	32.7	30.7	28.7	26.7	26.3
85°	25.7	23.8	21.9	20.1	18.2	17.0	16.5	16.0	15.5	14.9	14.8
87.5°	8.8	8.3	8.1	7.8	7.6	7.5	7.6	7.8	7.9	8.1	8.3
90°	0.8	1.6	3.1	4.7	6.4	7.9	8.7	10.3	11.0	12.6	13.4
92.5°	9.6	11.7	18.3	28.1	41.7	64.7	107.9	180.2	258.6	254.6	206.1
95°	26.1	26.9	33.1	41.8	59.2	94.7	179.3	352.9	570.9	699.6	684.6
97.5°	43.2	44.2	48.7	57.4	72.9	98.6	154.4	281.8	509.8	747.1	866.2
100°	55.2	56.9	60.0	68.7	83.7	107.3	153.2	255.8	454.8	713.1	910.4
102.5°	68.6	69.5	72.0	81.3	95.0	118.2	158.9	245.1	413.1	653.0	883.9
105°	89.3	89.3	93.2	101.1	113.7	135.8	170.6	240.9	372.7	572.5	799.1
107.5°	109.5	111.0	114.8	121.3	134.4	154.3	187.9	248.1	355.7	517.1	712.6
110°	124.0	125.5	128.7	135.8	147.6	168.1	200.6	255.1	350.6	491.1	663.3



TEST NUMBER: P333507-840

CATALOG NUMBER: S125RDIP-S375D810U840-4F0-1E-UDD-F4

CANDELA DISTRIBUTION (continued):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	138.5	140.1	142.6	149.7	161.6	181.5	212.6	263.9	350.6	475.9	626.6
115°	159.5	161.1	163.5	170.6	182.4	202.2	231.4	277.1	352.9	459.6	586.6
117.5°	178.4	180.9	183.4	190.5	203.9	223.0	250.6	292.4	358.2	451.5	562.8
120°	191.1	193.5	196.6	203.7	217.1	236.9	264.5	302.5	363.2	447.7	549.6
122.5°	204.4	206.1	208.6	215.7	230.5	250.1	277.8	313.8	367.6	444.5	538.2
125°	221.1	222.7	226.6	233.7	248.7	269.2	295.3	329.2	375.1	440.6	522.7
127.5°	234.2	236.6	241.7	250.6	266.6	287.1	312.3	343.5	383.4	438.7	508.5
130°	242.4	244.8	251.1	261.4	277.9	298.5	323.0	352.9	388.5	437.5	499.1
132.5°	248.7	251.8	259.3	270.8	288.0	308.6	333.1	361.1	394.2	437.5	491.5
135°	259.0	262.2	271.7	284.3	300.8	322.1	346.7	372.7	401.9	437.5	482.4
137.5°	272.0	274.3	283.2	295.8	312.0	334.0	356.3	381.2	409.0	438.4	474.4
140°	279.5	281.9	291.3	304.0	319.0	340.3	363.2	386.9	412.1	439.0	470.6
142.5°	288.3	290.1	298.9	311.5	326.0	346.0	367.6	390.1	414.0	439.7	467.5
145°	301.6	303.2	311.1	322.1	336.4	354.6	375.1	394.8	416.2	439.0	462.7
147.5°	315.5	316.5	323.3	333.6	345.9	361.8	379.8	397.7	416.9	437.0	457.8
150°	323.8	325.3	330.8	341.1	352.1	365.6	382.9	399.5	416.9	435.0	454.0
152.5°	332.5	333.6	338.4	347.4	357.9	370.0	386.1	400.8	416.3	432.5	449.6
155°	344.3	344.3	349.0	356.9	364.8	375.9	389.3	401.9	414.5	428.0	442.2
157.5°	354.7	354.6	358.3	365.1	372.0	380.4	391.9	402.7	412.5	423.2	435.3
160°	361.6	360.8	364.1	369.5	375.9	382.9	393.2	402.7	410.6	420.1	429.6
162.5°	367.3	366.6	369.7	374.6	379.6	385.5	394.5	402.0	408.7	416.3	424.4
165°	375.9	374.3	376.7	380.6	383.7	388.5	394.8	401.1	405.9	410.6	416.9
167.5°	381.5	380.7	382.1	384.4	386.6	389.6	394.8	399.2	401.4	405.1	409.5
170°	385.4	384.6	385.4	386.9	388.5	390.8	394.8	398.0	399.5	401.9	405.1
172.5°	387.9	386.5	387.2	388.8	389.7	390.8	394.2	396.7	397.0	398.1	400.6
175°	390.8	389.3	390.1	390.8	390.8	390.8	393.2	394.8	394.0	394.0	394.8
177.5°	392.2	391.0	391.0	391.6	391.0	391.0	392.2	392.9	391.6	391.6	392.2
180°	391.6	391.6	391.6	391.6	391.6	391.6	391.6	391.6	391.6	391.6	391.6



TEST NUMBER: P333507-840

CATALOG NUMBER: S125RDIP-S375D810U840-4F0-1E-UDD-F4

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°
0°	617.9	617.9	617.9	617.9	617.9	617.9	617.9	617.9
2.5°	615.8	616.7	617.5	617.9	617.8	617.7	617.6	617.5
5°	612.1	613.1	614.1	614.6	614.4	614.1	613.9	613.7
7.5°	604.4	605.2	605.9	606.1	605.9	605.7	605.5	605.2
10°	598.0	598.3	598.6	598.6	598.3	598.0	597.7	597.4
12.5°	588.9	589.2	589.4	589.3	588.8	588.2	587.8	587.3
15°	573.8	573.7	573.6	573.1	572.2	571.3	570.4	569.4
17.5°	555.1	554.6	554.1	553.4	552.7	551.9	551.1	550.4
20°	541.3	540.8	540.3	539.6	538.6	537.7	536.7	535.8
22.5°	527.6	526.5	525.5	524.6	523.9	523.1	522.4	521.6
25°	505.1	503.7	502.4	501.2	500.0	498.9	497.8	496.6
27.5°	480.8	478.9	477.0	475.5	474.4	473.3	472.2	471.1
30°	463.3	461.0	458.6	457.0	456.0	455.0	454.1	453.2
32.5°	446.5	443.8	441.1	439.3	438.1	436.9	435.7	434.5
35°	420.1	417.1	414.0	411.8	410.4	409.0	407.5	406.1
37.5°	392.5	389.0	385.4	382.8	381.4	380.0	378.6	377.2
40°	374.4	370.4	366.5	363.9	362.6	361.4	360.1	358.9
42.5°	356.4	352.6	348.8	346.1	344.3	342.3	340.5	338.7
45°	327.7	323.6	319.4	316.6	315.1	313.5	311.9	310.3
47.5°	299.4	295.1	290.8	287.8	286.1	284.4	282.7	280.9
50°	280.1	275.8	271.5	268.5	267.0	265.4	263.9	262.3
52.5°	262.0	257.3	252.6	249.4	247.9	246.4	244.8	243.3
55°	234.3	229.6	225.0	221.8	220.2	218.4	216.8	215.2
57.5°	206.6	202.1	197.4	194.4	193.0	191.5	190.1	188.5
60°	188.3	183.7	179.2	176.1	174.5	173.0	171.5	169.9
62.5°	170.3	166.0	161.8	159.0	157.3	155.8	154.3	152.7
65°	143.8	139.7	135.5	132.7	131.2	129.6	128.1	126.4
67.5°	118.6	114.8	111.0	108.5	107.2	106.0	104.7	103.5
70°	101.9	98.7	95.4	93.2	91.9	90.7	89.5	88.2
72.5°	86.2	83.3	80.4	78.5	77.7	76.9	75.9	75.1
75°	64.5	62.2	60.0	58.5	57.8	57.0	56.2	55.5
77.5°	45.9	44.3	42.7	41.6	41.1	40.6	40.0	39.5
80°	34.5	33.6	32.7	32.1	31.9	31.7	31.5	31.3
82.5°	25.9	25.3	24.9	24.6	24.5	24.4	24.3	24.1
85°	14.7	14.6	14.5	14.4	14.3	14.2	14.1	14.0
87.5°	8.5	8.6	8.8	9.0	9.0	8.9	9.0	8.9
90°	14.2	15.0	15.8	17.4	17.4	17.4	18.2	18.2
92.5°	140.0	101.6	76.4	64.7	54.6	52.7	51.6	50.4
95°	567.7	447.7	350.6	284.3	228.2	204.5	198.2	185.5
97.5°	845.6	761.3	666.7	574.5	525.7	481.5	458.6	448.5
100°	971.2	932.5	851.2	769.1	714.6	657.7	628.5	615.9
102.5°	1013.5	1037.4	998.4	942.8	884.5	844.0	812.3	802.8
105°	988.6	1096.8	1131.6	1122.9	1097.5	1071.5	1055.7	1046.2
107.5°	899.5	1043.9	1133.1	1174.3	1187.1	1186.9	1181.7	1175.4
110°	833.8	983.8	1095.2	1162.3	1197.8	1212.8	1218.4	1218.4



TEST NUMBER: P333507-840

CATALOG NUMBER: S125RDIP-S375D810U840-4F0-1E-UDD-F4

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°
112.5°	782.0	924.4	1037.0	1116.2	1168.1	1193.9	1207.6	1213.4
115°	717.0	839.4	947.6	1033.6	1095.2	1133.1	1155.2	1165.5
117.5°	675.0	780.4	873.6	952.6	1014.2	1053.3	1075.3	1081.6
120°	652.2	747.0	833.8	903.3	961.7	999.7	1021.0	1027.2
122.5°	635.2	723.0	800.3	865.5	917.6	952.3	973.6	979.3
125°	610.4	690.9	759.6	816.5	860.7	893.0	910.4	918.3
127.5°	585.1	660.2	724.4	777.6	817.7	846.3	862.7	866.2
130°	569.3	638.8	700.3	751.7	791.2	817.3	833.0	837.8
132.5°	553.5	618.5	674.5	723.9	763.4	789.4	804.0	809.3
135°	533.0	587.4	638.0	683.0	717.7	743.8	758.0	762.8
137.5°	515.6	559.7	601.7	639.9	671.1	694.7	707.8	713.1
140°	506.1	543.2	579.6	612.7	642.0	662.5	674.3	678.2
142.5°	498.0	529.4	560.6	589.4	614.2	631.6	642.8	646.0
145°	487.2	511.7	536.1	557.4	576.4	589.9	598.5	601.7
147.5°	477.1	497.0	515.7	531.9	546.8	557.6	562.7	564.1
150°	471.4	488.8	503.7	518.0	529.9	539.3	542.5	543.2
152.5°	465.0	480.6	494.3	505.3	515.3	522.9	526.0	526.8
155°	455.7	468.3	479.3	488.0	495.8	501.4	503.7	504.5
157.5°	446.2	456.6	465.0	471.9	478.1	482.6	484.8	484.6
160°	439.8	447.7	455.7	461.1	466.7	470.6	472.2	471.4
162.5°	432.8	440.1	446.8	451.6	456.0	459.2	459.6	459.4
165°	423.2	428.8	433.5	437.5	440.6	442.2	442.2	442.2
167.5°	414.0	417.7	421.3	424.1	425.8	427.2	426.6	426.4
170°	409.0	411.4	413.7	415.4	416.9	417.7	417.7	416.9
172.5°	403.3	405.7	407.5	408.4	408.7	410.1	408.9	408.1
175°	397.2	397.2	398.8	398.8	398.8	399.5	398.0	397.2
177.5°	392.9	393.5	393.5	393.5	392.9	393.5	391.6	391.6
180°	391.6	391.6	391.6	391.6	391.6	391.6	391.6	391.6

(END OF REPORT)