

Scaled data based on original data using  
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State  
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P333544-840

Luminaire Tested: **S125RDIP-S610D1205U840-4F0-1E-UDD-A**

Issue Date: 3/3/2020

**Test Information**

Test Method: LM-79-08  
Report Number: P333544-840  
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-7,  
Test Lab: INNOVATION CENTER  
Issue Date: 3/3/2020  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: NEO-RAY  
Catalog Number: S125RDIP-S610D1205U840-4F0-1E-UDD-A  
Description: DEFINE 5 DIRECT-INDIRECT PENDANT LED LUMINAIRE  
DOWNLIGHT 610 LUMENS PER FOOT, ASYMMETRIC DIFFUSER, REGRESSED HOUSING  
UPLIGHT 1205 LUMENS PER FOOT, NO LENS  
Light Source: -  
Ballast/Driver: ELECTRONIC DRIVER

**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 7286.3 lumens  
Efficiency: N/A  
Efficacy: 147.5 lumens/watt  
Spacing Criteria (0/90/45): 1.4 / 1.22 / 1.47  
Luminous Opening: Rectangular (W 4' x L: 0.42' x H: 0')  
CIE Type: Semi-Indirect


Input Watts (W): 49.4  
Input Voltage (V): 120  
Input Current (Ain): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 25 FT



TEST NUMBER: P333544-840

CATALOG NUMBER: S125RDIP-S610D1205U840-4F0-1E-UDD-A

### Luminous Intensity Polar Plot





TEST NUMBER: P333544-840

CATALOG NUMBER: S125RDIP-S610D1205U840-4F0-1E-UDD-A

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	103	103	103	103	93	93	93	93	74	74	74	57	57	57	41	41	41	33
1	94	90	87	83	85	82	78	76	65	63	61	50	49	48	36	36	35	29
2	86	79	73	68	77	72	67	62	57	54	51	44	42	40	32	31	30	24
3	79	70	63	57	71	63	57	52	51	47	43	39	37	34	29	27	26	21
4	72	62	54	48	65	56	49	44	45	41	37	35	32	29	26	24	22	18
5	66	55	47	41	59	50	43	38	40	36	32	32	28	26	23	21	19	16
6	61	49	41	36	55	45	38	33	36	31	28	29	25	22	21	19	17	14
7	56	44	37	31	51	40	34	29	33	28	24	26	22	20	19	17	15	12
8	52	40	33	28	47	37	30	26	30	25	22	24	20	18	18	15	14	11
9	48	37	29	24	44	33	27	23	27	23	19	22	18	16	16	14	12	10
10	45	33	26	22	41	31	24	20	25	20	17	20	17	14	15	13	11	9

**AVERAGE LUMINANCE (cd/sqm):**

	0°	90°	180°	270°
0°	6035	6035	6035	6035
5°	6944	6043	5337	6043
10°	7965	6013	4709	6013
15°	8603	5951	4186	5951
20°	9487	5880	3865	5880
25°	10979	5784	3587	5784
30°	11946	5684	3404	5684
35°	10078	5568	3236	5568
40°	7038	5359	3092	5359
45°	5221	5076	2951	5076
50°	4163	4784	2829	4784
55°	3533	4418	2721	4418
60°	3052	4093	2547	4093
65°	2720	3741	2193	3741
70°	2391	3427	1998	3427
75°	2069	2969	1876	2969
80°	1570	2499	1570	2499
85°	1312	1964	1482	1964



TEST NUMBER: P333544-840

CATALOG NUMBER: S125RDIP-S610D1205U840-4F0-1E-UDD-A

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	89.6	1.2
10°-20°	262.6	3.6
20°-30°	416.4	5.7
30°-40°	502.1	6.9
40°-50°	448.4	6.2
50°-60°	343.9	4.7
60°-70°	223.5	3.1
70°-80°	108.6	1.5
80°-90°	29.2	0.4
90°-100°	57.5	0.8
100°-110°	354.6	4.9
110°-120°	643.1	8.8
120°-130°	825.3	11.3
130°-140°	887.7	12.2
140°-150°	833.2	11.4
150°-160°	674.0	9.3
160°-170°	435.9	6.0
170°-180°	150.4	2.1
0°-30°	768.6	10.5
0°-40°	1270.8	17.4
0°-60°	2063.1	28.3
0°-90°	2424.4	33.3
90°-120°	1055.2	14.5
90°-150°	3601.6	49.4
90°-180°	4862.0	66.7
0°-180°	7286.3	100.0

**CANDELA DISTRIBUTION:**

	0°	90°	180°	270°	360°	Flux
0°	934	934	934	934	934	
5°	1071	932	823	932	1071	107
15°	1287	890	626	890	1287	369
25°	1541	812	503	812	1541	707
35°	1278	706	410	706	1278	772
45°	572	556	323	556	572	456
55°	314	392	242	392	314	285
65°	178	245	144	245	178	177
75°	83	119	75	119	83	88
85°	18	26	20	26	18	21
90°	28	1	28	1	28	13
95°	25	67	25	67	25	20
105°	349	345	349	345	349	315
115°	643	648	643	648	643	638
125°	921	921	921	921	921	820
135°	1144	1149	1144	1149	1144	883
145°	1329	1332	1329	1332	1329	830
155°	1456	1467	1456	1467	1456	671
165°	1540	1548	1540	1548	1540	435
175°	1576	1583	1576	1583	1576	150
180°	1583	1583	1583	1583	1583	



TEST NUMBER: P333544-840

CATALOG NUMBER: S125RDIP-S610D1205U840-4F0-1E-UDD-A

**CANDELA DISTRIBUTION (FULL):**

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	934.5	934.5	934.5	934.5	934.5	934.5	934.5	934.5	934.5	934.5	934.5
2.5°	983.0	982.4	983.6	980.2	980.6	975.3	975.3	971.3	966.1	962.1	960.3
5°	1071.1	1071.9	1070.3	1064.5	1060.7	1054.9	1048.4	1036.9	1027.3	1018.1	1010.9
7.5°	1161.7	1162.3	1157.2	1155.5	1145.8	1138.7	1124.3	1108.6	1094.7	1077.0	1063.6
10°	1214.6	1214.2	1208.8	1204.6	1196.1	1185.4	1171.1	1152.8	1135.5	1116.3	1097.9
12.5°	1245.3	1244.3	1242.5	1237.4	1229.6	1220.0	1208.0	1189.9	1168.6	1147.6	1126.2
15°	1286.7	1283.9	1279.0	1272.4	1261.3	1250.2	1236.8	1220.7	1200.3	1176.6	1156.6
17.5°	1337.9	1338.0	1330.3	1321.3	1306.2	1286.5	1265.8	1239.8	1212.1	1186.0	1164.8
20°	1380.3	1379.1	1371.4	1353.8	1336.6	1312.0	1288.2	1256.4	1222.6	1188.4	1162.0
22.5°	1441.0	1438.0	1430.1	1406.8	1380.1	1348.5	1312.1	1273.2	1232.4	1193.7	1158.9
25°	1540.7	1538.3	1522.6	1495.7	1458.1	1409.4	1361.8	1308.5	1249.8	1198.8	1156.6
27.5°	1608.7	1606.2	1594.6	1572.3	1537.5	1486.3	1421.9	1350.7	1277.4	1207.2	1146.3
30°	1601.9	1607.7	1606.2	1595.9	1569.7	1523.7	1464.3	1384.1	1297.0	1214.6	1142.1
32.5°	1505.6	1510.8	1524.3	1544.6	1546.1	1527.7	1483.3	1409.3	1319.1	1225.3	1138.6
35°	1278.2	1285.2	1311.2	1352.2	1405.9	1450.9	1460.1	1420.2	1339.2	1238.3	1133.6
37.5°	982.7	1020.5	1042.4	1085.6	1166.7	1249.3	1328.7	1358.0	1323.5	1232.9	1125.4
40°	834.8	843.9	883.1	931.8	1000.1	1086.0	1199.2	1280.9	1283.5	1220.7	1112.5
42.5°	714.5	726.1	753.0	791.8	850.3	936.2	1053.1	1160.9	1210.8	1186.9	1095.6
45°	571.6	580.4	600.0	629.9	674.8	745.8	846.3	971.0	1070.0	1108.6	1050.4
47.5°	469.6	474.3	491.3	514.1	547.3	599.1	676.8	785.1	903.8	987.0	978.9
50°	414.3	419.7	432.7	450.0	478.0	521.7	583.9	674.0	796.4	898.1	918.4
52.5°	371.3	375.8	384.0	400.3	423.3	457.0	507.2	588.8	698.8	806.9	853.9
55°	313.8	316.9	323.4	332.5	351.0	375.2	418.5	474.9	563.9	672.9	741.9
57.5°	266.4	267.9	272.1	280.5	293.3	310.9	342.2	390.1	453.9	552.0	628.2
60°	236.3	237.8	243.2	248.9	258.9	275.1	299.6	333.0	394.4	475.3	552.4
62.5°	212.4	213.3	215.6	221.4	230.0	242.6	261.9	289.1	337.9	409.0	481.8
65°	178.0	178.3	179.2	183.8	189.1	198.3	211.0	230.1	267.0	320.7	385.2
67.5°	145.0	145.5	148.2	149.9	155.4	160.3	167.7	182.4	208.3	244.5	294.6
70°	126.6	126.2	128.9	130.8	132.7	138.5	143.5	155.3	171.5	199.1	241.0
72.5°	109.4	108.5	109.6	110.3	112.8	116.7	121.7	129.0	141.4	160.5	192.4
75°	82.9	83.2	83.2	84.0	85.9	87.5	89.0	92.8	99.8	112.4	129.7
77.5°	58.2	57.6	59.2	59.4	60.5	62.2	63.5	65.0	67.9	73.1	82.0
80°	42.2	42.2	42.6	43.7	43.3	44.1	46.0	47.6	51.0	54.1	57.2
82.5°	32.4	32.1	32.4	32.7	32.6	33.3	34.0	34.3	35.6	37.2	39.4
85°	17.7	17.7	18.1	18.1	18.4	18.4	18.8	18.8	18.8	19.2	19.6
87.5°	12.4	11.9	11.4	11.3	11.4	11.8	11.3	10.7	10.5	10.2	10.1
90°	28.2	27.4	26.6	25.9	25.0	24.0	22.7	21.4	20.1	18.8	17.0
92.5°	26.3	26.0	25.5	25.1	24.8	24.0	22.7	21.4	20.1	18.8	17.2
95°	24.6	24.6	24.6	24.6	24.6	24.0	22.7	21.4	20.1	18.8	28.7
97.5°	24.6	24.6	24.6	24.6	24.6	28.3	35.6	43.0	50.4	57.8	77.4
100°	24.6	25.7	26.8	27.8	28.8	48.8	87.7	126.5	165.3	204.2	203.2
102.5°	147.6	165.4	183.1	200.9	218.6	231.2	238.5	245.8	253.2	260.5	259.9
105°	348.6	348.8	349.1	349.3	349.6	349.7	349.7	349.7	349.7	349.7	349.7
107.5°	439.4	440.2	441.0	441.7	442.5	442.9	442.8	442.8	442.7	442.7	442.2
110°	502.3	502.1	501.8	501.5	501.3	501.5	502.3	503.1	503.9	504.6	504.1



TEST NUMBER: P333544-840

CATALOG NUMBER: S125RDIP-S610D1205U840-4F0-1E-UDD-A

**CANDELA DISTRIBUTION (continued):**

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	558.7	559.1	559.4	559.8	560.1	560.8	561.8	562.8	563.8	564.7	564.4
115°	643.2	644.7	646.3	647.8	649.4	650.8	651.8	652.8	653.9	654.9	654.6
117.5°	733.3	734.0	734.7	735.3	736.0	737.0	738.4	739.7	741.1	742.5	741.4
120°	788.7	790.0	791.3	792.6	794.0	794.9	795.4	795.9	796.4	796.9	796.1
122.5°	841.3	842.8	844.2	845.8	847.3	848.4	848.9	849.4	849.9	850.4	850.1
125°	921.3	922.1	922.9	923.6	924.4	925.3	926.3	927.5	928.5	929.5	929.5
127.5°	988.7	990.6	992.5	994.5	996.4	997.6	998.3	998.8	999.4	1000.0	1000.1
130°	1037.5	1038.8	1040.2	1041.4	1042.7	1043.8	1044.5	1045.3	1046.1	1046.9	1046.6
132.5°	1082.6	1083.9	1085.2	1086.5	1087.8	1088.5	1088.6	1088.8	1089.0	1089.1	1089.7
135°	1144.3	1145.9	1147.4	1149.0	1150.5	1151.7	1152.2	1152.7	1153.2	1153.7	1154.2
137.5°	1206.3	1207.6	1209.0	1210.3	1211.7	1212.3	1212.2	1212.1	1212.0	1211.9	1212.3
140°	1242.9	1244.5	1246.1	1247.6	1249.1	1249.7	1249.1	1248.6	1248.1	1247.6	1247.9
142.5°	1277.7	1279.2	1280.8	1282.3	1283.9	1284.6	1284.5	1284.4	1284.3	1284.2	1283.8
145°	1328.6	1330.1	1331.7	1333.2	1334.8	1335.4	1335.2	1334.9	1334.7	1334.4	1334.4
147.5°	1370.6	1372.5	1374.3	1376.2	1378.1	1378.9	1378.6	1378.3	1378.0	1377.7	1377.4
150°	1397.9	1399.9	1402.0	1404.1	1406.1	1406.9	1406.4	1405.9	1405.3	1404.8	1404.3
152.5°	1423.2	1425.0	1426.9	1428.8	1430.7	1431.4	1430.9	1430.3	1429.8	1429.3	1428.8
155°	1456.5	1458.5	1460.7	1462.8	1464.8	1465.5	1464.7	1463.9	1463.2	1462.4	1461.9
157.5°	1484.4	1486.5	1488.6	1490.7	1492.8	1493.4	1492.6	1491.8	1490.9	1490.1	1490.1
160°	1502.3	1504.4	1506.4	1508.5	1510.7	1511.2	1510.1	1509.0	1508.0	1506.9	1506.7
162.5°	1518.2	1520.6	1522.8	1525.1	1527.4	1527.8	1526.4	1524.9	1523.5	1522.0	1521.8
165°	1539.8	1541.9	1544.0	1546.1	1548.1	1548.4	1546.9	1545.3	1543.8	1542.2	1541.9
167.5°	1554.9	1557.2	1559.5	1561.9	1564.3	1564.5	1562.6	1560.7	1558.8	1557.0	1556.7
170°	1563.3	1565.7	1568.0	1570.3	1572.7	1572.9	1570.7	1568.6	1566.6	1564.5	1564.2
172.5°	1568.9	1571.2	1573.7	1576.0	1578.3	1578.5	1576.7	1574.8	1573.0	1571.0	1570.5
175°	1576.2	1578.5	1580.9	1583.3	1585.6	1585.7	1583.7	1581.5	1579.4	1577.4	1577.1
177.5°	1580.4	1582.1	1583.8	1585.5	1587.1	1587.2	1585.8	1584.3	1582.9	1581.3	1581.1
180°	1583.3	1583.3	1583.3	1583.3	1583.3	1583.3	1583.3	1583.3	1583.3	1583.3	1583.3



TEST NUMBER: P333544-840

CATALOG NUMBER: S125RDIP-S610D1205U840-4F0-1E-UDD-A

**CANDELA DISTRIBUTION (continued):**

	55°	60°	65°	70°	75°	80°	85°	90°	95°	100°	105°
0°	934.5	934.5	934.5	934.5	934.5	934.5	934.5	934.5	934.5	934.5	934.5
2.5°	960.3	958.2	954.1	950.5	945.8	941.9	939.1	935.7	931.4	926.2	921.9
5°	1002.8	994.3	983.2	973.6	961.4	951.8	941.8	932.2	922.6	910.3	899.6
7.5°	1049.9	1032.5	1015.5	994.2	974.8	957.6	941.0	924.2	907.8	890.4	873.5
10°	1078.7	1057.6	1034.2	1007.3	982.8	959.5	938.0	916.9	894.6	875.0	853.9
12.5°	1105.7	1078.5	1051.8	1017.8	988.4	959.8	932.4	906.2	882.3	857.0	834.2
15°	1130.1	1103.3	1073.4	1032.0	990.9	956.3	924.1	890.0	860.5	832.0	806.8
17.5°	1139.5	1111.5	1076.6	1036.8	992.0	948.6	907.1	869.6	834.9	801.7	773.3
20°	1135.9	1108.6	1073.0	1035.0	987.0	941.8	896.9	855.5	816.7	781.8	751.5
22.5°	1127.0	1098.8	1064.4	1024.3	978.8	930.7	882.8	838.6	798.0	761.8	728.8
25°	1113.7	1075.3	1040.0	1000.9	957.6	910.0	860.5	811.7	768.4	731.5	695.5
27.5°	1099.7	1051.9	1007.0	968.1	922.3	879.9	832.1	782.2	736.6	699.1	662.2
30°	1087.2	1033.5	984.0	939.9	896.6	856.3	810.9	762.2	715.5	676.7	639.1
32.5°	1071.6	1014.4	960.1	909.2	867.4	827.4	786.4	739.8	694.3	654.3	616.1
35°	1051.9	979.0	919.9	865.9	819.4	780.6	743.9	706.2	660.6	619.1	582.0
37.5°	1026.1	943.4	875.0	816.1	767.2	728.2	699.2	664.8	623.2	583.5	549.0
40°	1010.5	917.7	842.8	784.5	733.1	692.1	664.8	635.6	597.6	560.5	525.9
42.5°	989.6	894.0	810.3	749.5	697.8	658.3	630.8	605.3	573.4	538.4	501.4
45°	948.7	848.2	760.3	695.1	643.0	604.2	578.5	555.8	531.7	499.5	467.3
47.5°	895.4	800.4	708.4	637.2	586.1	550.2	525.2	507.4	490.1	462.7	431.4
50°	852.8	761.1	671.4	602.3	547.9	513.6	490.3	476.1	460.3	435.5	409.3
52.5°	802.4	720.6	632.7	562.1	510.7	478.7	456.2	442.0	429.0	408.7	383.8
55°	723.2	651.4	570.8	506.8	459.6	427.4	405.9	392.4	384.8	367.5	347.9
57.5°	631.6	580.2	509.2	447.4	405.7	373.8	358.1	346.7	338.0	325.8	311.9
60°	567.7	531.7	468.0	409.3	370.9	340.6	326.5	316.9	308.8	298.4	287.7
62.5°	503.0	476.8	421.4	370.9	335.7	310.2	297.0	288.3	279.0	272.1	261.7
65°	416.3	392.8	354.5	315.0	282.4	262.1	252.5	244.8	239.0	231.4	224.0
67.5°	323.8	314.3	287.8	260.5	237.1	219.0	210.8	205.4	198.4	193.9	188.8
70°	267.0	262.4	243.6	225.6	203.7	191.5	183.8	181.5	173.0	168.4	164.9
72.5°	216.7	214.5	203.7	191.2	175.8	165.0	157.9	155.3	150.0	146.3	144.1
75°	148.5	149.3	147.3	139.3	133.5	126.6	120.5	119.0	115.1	112.0	110.1
77.5°	93.9	97.9	98.0	97.6	95.3	91.1	88.6	87.4	83.6	82.5	82.0
80°	64.4	68.7	72.5	72.1	71.4	70.2	68.3	67.2	65.2	64.0	63.3
82.5°	42.9	46.9	50.1	52.2	52.0	50.9	49.6	49.0	48.7	47.8	47.7
85°	20.3	21.1	22.2	24.9	26.9	27.3	26.9	26.5	25.3	25.8	26.1
87.5°	10.1	9.7	9.7	9.3	8.6	9.7	10.2	10.1	9.9	9.7	9.5
90°	15.1	13.3	11.5	9.5	7.5	5.4	3.2	1.2	3.2	5.4	7.5
92.5°	15.6	13.9	12.3	12.2	13.7	15.1	16.7	18.1	16.7	15.1	13.7
95°	38.6	48.5	58.5	63.7	64.5	65.3	66.1	66.9	66.1	65.3	64.5
97.5°	96.9	116.5	136.2	145.3	143.9	142.5	141.1	139.7	141.1	142.5	143.9
100°	202.2	201.1	200.1	199.1	198.3	197.5	196.8	196.0	196.8	197.5	198.3
102.5°	259.3	258.6	258.0	257.2	256.2	255.3	254.3	253.3	254.3	255.3	256.2
105°	349.7	349.7	349.7	349.2	348.2	347.1	346.1	345.1	346.1	347.1	348.2
107.5°	441.6	441.1	440.6	440.4	440.4	440.4	440.4	440.4	440.4	440.4	440.4
110°	503.6	503.1	502.6	502.3	502.3	502.3	502.3	502.3	502.3	502.3	502.3





TEST NUMBER: P333544-840

CATALOG NUMBER: S125RDIP-S610D1205U840-4F0-1E-UDD-A

**CANDELA DISTRIBUTION (continued):**

	55°	60°	65°	70°	75°	80°	85°	90°	95°	100°	105°
112.5°	564.1	563.8	563.5	563.0	562.4	561.8	561.2	560.6	561.2	561.8	562.4
115°	654.4	654.1	653.9	653.1	651.8	650.5	649.1	647.8	649.1	650.5	651.8
117.5°	740.4	739.5	738.5	738.0	738.1	738.1	738.2	738.2	738.2	738.1	738.1
120°	795.4	794.6	793.8	793.6	793.8	794.1	794.3	794.6	794.3	794.1	793.8
122.5°	849.7	849.3	849.0	848.3	847.3	846.3	845.4	844.3	845.4	846.3	847.3
125°	929.5	929.5	929.5	928.6	926.8	924.9	923.1	921.3	923.1	924.9	926.8
127.5°	1000.3	1000.4	1000.6	1000.0	998.7	997.3	996.1	994.8	996.1	997.3	998.7
130°	1046.4	1046.1	1045.8	1045.1	1043.8	1042.5	1041.2	1039.9	1041.2	1042.5	1043.8
132.5°	1090.3	1090.9	1091.5	1091.0	1089.4	1087.9	1086.4	1084.9	1086.4	1087.9	1089.4
135°	1154.8	1155.3	1155.8	1155.3	1153.7	1152.2	1150.5	1149.0	1150.5	1152.2	1153.7
137.5°	1212.8	1213.4	1213.8	1213.4	1211.9	1210.6	1209.3	1207.9	1209.3	1210.6	1211.9
140°	1248.1	1248.4	1248.6	1248.5	1248.0	1247.5	1247.0	1246.4	1247.0	1247.5	1248.0
142.5°	1283.4	1283.1	1282.7	1282.4	1282.1	1281.8	1281.4	1281.1	1281.4	1281.8	1282.1
145°	1334.4	1334.4	1334.4	1334.1	1333.6	1333.1	1332.6	1332.1	1332.6	1333.1	1333.6
147.5°	1377.0	1376.6	1376.3	1376.2	1376.3	1376.4	1376.5	1376.6	1376.5	1376.4	1376.3
150°	1403.8	1403.3	1402.8	1402.8	1403.3	1403.8	1404.3	1404.8	1404.3	1403.8	1403.3
152.5°	1428.3	1427.7	1427.1	1427.4	1428.7	1429.8	1431.0	1432.1	1431.0	1429.8	1428.7
155°	1461.3	1460.8	1460.3	1460.8	1462.4	1463.9	1465.5	1467.0	1465.5	1463.9	1462.4
157.5°	1490.0	1490.0	1489.9	1490.3	1491.3	1492.2	1493.1	1494.1	1493.1	1492.2	1491.3
160°	1506.4	1506.2	1505.9	1506.6	1508.1	1509.7	1511.3	1512.9	1511.3	1509.7	1508.1
162.5°	1521.5	1521.2	1521.0	1521.6	1523.2	1524.7	1526.3	1527.8	1526.3	1524.7	1523.2
165°	1541.7	1541.4	1541.2	1541.8	1543.4	1544.9	1546.5	1548.0	1546.5	1544.9	1543.4
167.5°	1556.4	1556.2	1555.9	1556.6	1558.2	1559.8	1561.5	1563.1	1561.5	1559.8	1558.2
170°	1564.0	1563.7	1563.5	1564.2	1566.0	1567.8	1569.7	1571.6	1569.7	1567.8	1566.0
172.5°	1570.1	1569.6	1569.1	1569.8	1571.7	1573.5	1575.3	1577.1	1575.3	1573.5	1571.7
175°	1576.9	1576.6	1576.3	1577.0	1578.5	1580.1	1581.7	1583.3	1581.7	1580.1	1578.5
177.5°	1580.9	1580.7	1580.5	1581.0	1582.4	1583.6	1584.8	1586.1	1584.8	1583.6	1582.4
180°	1583.3	1583.3	1583.3	1583.3	1583.3	1583.3	1583.3	1583.3	1583.3	1583.3	1583.3



TEST NUMBER: P333544-840

CATALOG NUMBER: S125RDIP-S610D1205U840-4F0-1E-UDD-A

**CANDELA DISTRIBUTION (continued):**

	110°	115°	120°	125°	130°	135°	140°	145°	150°	155°	160°
0°	934.5	934.5	934.5	934.5	934.5	934.5	934.5	934.5	934.5	934.5	934.5
2.5°	918.9	914.5	911.5	905.3	901.0	899.2	895.9	894.9	898.3	895.9	895.5
5°	891.5	880.4	871.6	862.7	853.1	847.1	837.8	836.3	833.9	830.5	829.8
7.5°	858.8	844.2	832.9	818.3	805.7	795.5	784.0	778.5	775.5	771.0	765.1
10°	836.7	819.4	804.1	789.5	773.8	761.1	749.6	740.7	735.0	729.6	727.3
12.5°	814.9	797.3	777.7	760.0	742.5	728.2	715.5	709.7	703.4	697.1	691.8
15°	781.0	757.6	736.2	715.8	700.8	685.5	673.3	664.8	655.2	652.6	642.2
17.5°	745.2	722.2	697.0	675.6	658.3	641.4	627.9	618.3	611.1	601.2	596.4
20°	722.8	695.5	671.0	651.4	632.2	612.3	598.4	590.4	583.5	575.4	571.6
22.5°	698.8	672.2	647.0	624.1	604.6	584.9	575.1	566.7	559.0	551.5	546.4
25°	663.7	636.8	610.4	586.5	566.2	552.0	540.5	530.9	526.7	519.4	514.0
27.5°	628.9	600.4	572.9	549.2	533.2	519.2	509.8	502.2	494.5	488.2	483.5
30°	606.5	577.3	547.4	528.7	511.7	498.4	488.0	480.7	474.9	469.2	465.7
32.5°	584.1	554.0	527.5	507.2	491.2	479.6	469.0	461.9	455.9	449.5	445.5
35°	548.2	517.5	496.0	476.1	460.3	449.6	442.3	432.3	427.4	422.7	418.5
37.5°	514.8	486.3	463.0	445.6	431.9	421.2	411.8	406.4	400.3	396.2	392.6
40°	490.3	464.1	443.1	424.6	414.7	402.8	393.9	387.1	382.4	377.1	373.2
42.5°	468.2	443.9	423.4	406.9	394.5	384.4	375.9	369.0	363.1	359.3	356.1
45°	437.0	412.7	392.8	377.5	366.0	356.4	347.6	344.1	336.4	331.8	330.3
47.5°	404.7	383.0	363.8	349.6	337.8	328.7	320.4	313.5	309.2	304.7	302.3
50°	382.8	362.1	344.1	330.3	318.8	308.8	301.1	296.5	290.7	286.6	283.5
52.5°	361.0	341.8	323.9	310.6	300.6	290.7	282.2	277.5	272.1	269.3	267.2
55°	329.9	309.6	294.3	281.1	270.8	261.7	253.6	248.9	245.5	242.9	242.1
57.5°	294.6	278.5	264.3	252.5	241.8	233.1	226.0	221.7	218.6	218.2	215.9
60°	271.6	257.0	244.0	231.4	222.1	214.1	207.9	203.0	199.9	199.4	198.7
62.5°	248.6	234.6	222.5	211.4	203.1	195.3	189.6	183.9	182.1	180.2	178.4
65°	214.4	201.8	191.8	183.0	174.2	167.6	161.9	158.4	154.2	151.9	147.7
67.5°	180.9	171.1	161.5	154.1	147.1	141.0	136.2	131.1	128.3	126.3	123.3
70°	158.9	151.2	141.6	133.5	128.2	123.1	119.3	113.5	111.6	110.1	108.6
72.5°	137.9	131.2	123.1	116.6	111.3	106.5	102.1	99.5	97.6	95.9	95.0
75°	108.6	102.0	95.1	90.5	86.7	82.9	80.6	78.7	77.9	77.5	75.9
77.5°	79.7	76.2	70.7	67.1	64.5	63.0	60.9	59.9	59.9	58.2	57.7
80°	61.0	59.1	54.4	52.9	51.0	49.5	48.4	46.5	44.5	43.7	42.6
82.5°	45.3	43.4	41.6	39.1	37.6	36.6	35.4	34.7	34.9	33.9	33.3
85°	24.1	22.2	21.5	21.1	20.3	21.1	20.7	20.3	20.0	19.6	20.0
87.5°	9.6	10.0	10.0	11.0	10.4	11.1	11.4	11.3	11.6	11.8	11.7
90°	9.5	11.5	13.3	15.1	17.0	18.8	20.1	21.4	22.7	24.0	25.0
92.5°	12.2	12.3	13.9	15.6	17.2	18.8	20.1	21.4	22.7	24.0	24.8
95°	63.7	58.5	48.5	38.6	28.7	18.8	20.1	21.4	22.7	24.0	24.6
97.5°	145.3	136.2	116.5	96.9	77.4	57.8	50.4	43.0	35.6	28.3	24.6
100°	199.1	200.1	201.1	202.2	203.2	204.2	165.3	126.5	87.7	48.8	28.8
102.5°	257.2	258.0	258.6	259.3	259.9	260.5	253.2	245.8	238.5	231.2	218.6
105°	349.2	349.7	349.7	349.7	349.7	349.7	349.7	349.7	349.7	349.7	349.6
107.5°	440.4	440.6	441.1	441.6	442.2	442.7	442.7	442.8	442.8	442.9	442.5
110°	502.3	502.6	503.1	503.6	504.1	504.6	503.9	503.1	502.3	501.5	501.3



TEST NUMBER: P333544-840

CATALOG NUMBER: S125RDIP-S610D1205U840-4F0-1E-UDD-A

**CANDELA DISTRIBUTION (continued):**

	110°	115°	120°	125°	130°	135°	140°	145°	150°	155°	160°
112.5°	563.0	563.5	563.8	564.1	564.4	564.7	563.8	562.8	561.8	560.8	560.1
115°	653.1	653.9	654.1	654.4	654.6	654.9	653.9	652.8	651.8	650.8	649.4
117.5°	738.0	738.5	739.5	740.4	741.4	742.5	741.1	739.7	738.4	737.0	736.0
120°	793.6	793.8	794.6	795.4	796.1	796.9	796.4	795.9	795.4	794.9	794.0
122.5°	848.3	849.0	849.3	849.7	850.1	850.4	849.9	849.4	848.9	848.4	847.3
125°	928.6	929.5	929.5	929.5	929.5	929.5	928.5	927.5	926.3	925.3	924.4
127.5°	1000.0	1000.6	1000.4	1000.3	1000.1	1000.0	999.4	998.8	998.3	997.6	996.4
130°	1045.1	1045.8	1046.1	1046.4	1046.6	1046.9	1046.1	1045.3	1044.5	1043.8	1042.7
132.5°	1091.0	1091.5	1090.9	1090.3	1089.7	1089.1	1089.0	1088.8	1088.6	1088.5	1087.8
135°	1155.3	1155.8	1155.3	1154.8	1154.2	1153.7	1153.2	1152.7	1152.2	1151.7	1150.5
137.5°	1213.4	1213.8	1213.4	1212.8	1212.3	1211.9	1212.0	1212.1	1212.2	1212.3	1211.7
140°	1248.5	1248.6	1248.4	1248.1	1247.9	1247.6	1248.1	1248.6	1249.1	1249.7	1249.1
142.5°	1282.4	1282.7	1283.1	1283.4	1283.8	1284.2	1284.3	1284.4	1284.5	1284.6	1283.9
145°	1334.1	1334.4	1334.4	1334.4	1334.4	1334.4	1334.7	1334.9	1335.2	1335.4	1334.8
147.5°	1376.2	1376.3	1376.6	1377.0	1377.4	1377.7	1378.0	1378.3	1378.6	1378.9	1378.1
150°	1402.8	1402.8	1403.3	1403.8	1404.3	1404.8	1405.3	1405.9	1406.4	1406.9	1406.1
152.5°	1427.4	1427.1	1427.7	1428.3	1428.8	1429.3	1429.8	1430.3	1430.9	1431.4	1430.7
155°	1460.8	1460.3	1460.8	1461.3	1461.9	1462.4	1463.2	1463.9	1464.7	1465.5	1464.8
157.5°	1490.3	1489.9	1490.0	1490.0	1490.1	1490.1	1490.9	1491.8	1492.6	1493.4	1492.8
160°	1506.6	1505.9	1506.2	1506.4	1506.7	1506.9	1508.0	1509.0	1510.1	1511.2	1510.7
162.5°	1521.6	1521.0	1521.2	1521.5	1521.8	1522.0	1523.5	1524.9	1526.4	1527.8	1527.4
165°	1541.8	1541.2	1541.4	1541.7	1541.9	1542.2	1543.8	1545.3	1546.9	1548.4	1548.1
167.5°	1556.6	1555.9	1556.2	1556.4	1556.7	1557.0	1558.8	1560.7	1562.6	1564.5	1564.3
170°	1564.2	1563.5	1563.7	1564.0	1564.2	1564.5	1566.6	1568.6	1570.7	1572.9	1572.7
172.5°	1569.8	1569.1	1569.6	1570.1	1570.5	1571.0	1573.0	1574.8	1576.7	1578.5	1578.3
175°	1577.0	1576.3	1576.6	1576.9	1577.1	1577.4	1579.4	1581.5	1583.7	1585.7	1585.6
177.5°	1581.0	1580.5	1580.7	1580.9	1581.1	1581.3	1582.9	1584.3	1585.8	1587.2	1587.1
180°	1583.3	1583.3	1583.3	1583.3	1583.3	1583.3	1583.3	1583.3	1583.3	1583.3	1583.3



TEST NUMBER: P333544-840

CATALOG NUMBER: S125RDIP-S610D1205U840-4F0-1E-UDD-A

**CANDELA DISTRIBUTION (continued):**

	165°	170°	175°	180°	185°	190°	195°	200°	205°	210°	215°
0°	934.5	934.5	934.5	934.5	934.5	934.5	934.5	934.5	934.5	934.5	934.5
2.5°	895.2	891.8	890.9	892.1	890.9	891.8	895.2	895.5	895.9	898.3	894.9
5°	826.0	822.1	824.0	823.2	824.0	822.1	826.0	829.8	830.5	833.9	836.3
7.5°	765.0	760.2	755.2	756.8	755.2	760.2	765.0	765.1	771.0	775.5	778.5
10°	722.4	718.5	716.2	718.1	716.2	718.5	722.4	727.3	729.6	735.0	740.7
12.5°	686.4	684.2	682.2	681.4	682.2	684.2	686.4	691.8	697.1	703.4	709.7
15°	637.5	633.0	631.1	626.1	631.1	633.0	637.5	642.2	652.6	655.2	664.8
17.5°	592.5	591.0	586.0	583.9	586.0	591.0	592.5	596.4	601.2	611.1	618.3
20°	565.8	564.3	559.4	562.4	559.4	564.3	565.8	571.6	575.4	583.5	590.4
22.5°	543.7	540.4	538.8	537.9	538.8	540.4	543.7	546.4	551.5	559.0	566.7
25°	512.5	507.6	505.6	503.3	505.6	507.6	512.5	514.0	519.4	526.7	530.9
27.5°	481.4	478.7	476.2	475.5	476.2	478.7	481.4	483.5	488.2	494.5	502.2
30°	461.1	458.4	456.5	456.5	456.5	458.4	461.1	465.7	469.2	474.9	480.7
32.5°	443.0	440.9	439.0	438.7	439.0	440.9	443.0	445.5	449.5	455.9	461.9
35°	416.6	413.5	412.7	410.5	412.7	413.5	416.6	418.5	422.7	427.4	432.3
37.5°	389.2	386.7	386.6	386.4	386.6	386.7	389.2	392.6	396.2	400.3	406.4
40°	371.7	369.8	369.4	366.8	369.4	369.8	371.7	373.2	377.1	382.4	387.1
42.5°	353.0	352.0	350.7	349.5	350.7	352.0	353.0	356.1	359.3	363.1	369.0
45°	327.6	325.0	325.0	323.1	325.0	325.0	327.6	330.3	331.8	336.4	344.1
47.5°	301.3	299.3	299.5	297.5	299.5	299.3	301.3	302.3	304.7	309.2	313.5
50°	283.9	282.8	282.4	281.6	282.4	282.8	283.9	283.5	286.6	290.7	296.5
52.5°	266.4	265.9	267.3	265.6	267.3	265.9	266.4	267.2	269.3	272.1	277.5
55°	242.9	241.7	244.0	241.7	244.0	241.7	242.9	242.1	242.9	245.5	248.9
57.5°	215.7	214.7	216.7	215.6	216.7	214.7	215.7	215.9	218.2	218.6	221.7
60°	197.9	195.6	196.8	197.2	196.8	195.6	197.9	198.7	199.4	199.9	203.0
62.5°	176.7	175.4	176.2	174.5	176.2	175.4	176.7	178.4	180.2	182.1	183.9
65°	146.9	145.8	144.2	143.5	144.2	145.8	146.9	147.7	151.9	154.2	158.4
67.5°	123.4	120.7	120.6	121.2	120.6	120.7	123.4	123.3	126.3	128.3	131.1
70°	106.2	106.2	105.8	105.8	105.8	106.2	106.2	108.6	110.1	111.6	113.5
72.5°	94.3	94.0	93.3	93.0	93.3	94.0	94.3	95.0	95.9	97.6	99.5
75°	75.9	76.3	75.5	75.2	75.5	76.3	75.9	75.9	77.5	77.9	78.7
77.5°	56.0	54.4	55.3	54.4	55.3	54.4	56.0	57.7	58.2	59.9	59.9
80°	42.6	42.2	43.3	42.2	43.3	42.2	42.6	42.6	43.7	44.5	46.5
82.5°	33.7	33.3	33.8	33.0	33.8	33.3	33.7	33.3	33.9	34.9	34.7
85°	20.3	20.0	19.6	20.0	19.6	20.0	20.3	20.0	19.6	20.0	20.3
87.5°	12.2	12.1	12.2	12.4	12.2	12.1	12.2	11.7	11.8	11.6	11.3
90°	25.9	26.6	27.4	28.2	27.4	26.6	25.9	25.0	24.0	22.7	21.4
92.5°	25.1	25.5	26.0	26.3	26.0	25.5	25.1	24.8	24.0	22.7	21.4
95°	24.6	24.6	24.6	24.6	24.6	24.6	24.6	24.6	24.0	22.7	21.4
97.5°	24.6	24.6	24.6	24.6	24.6	24.6	24.6	24.6	28.3	35.6	43.0
100°	27.8	26.8	25.7	24.6	25.7	26.8	27.8	28.8	48.8	87.7	126.5
102.5°	200.9	183.1	165.4	147.6	165.4	183.1	200.9	218.6	231.2	238.5	245.8
105°	349.3	349.1	348.8	348.6	348.8	349.1	349.3	349.6	349.7	349.7	349.7
107.5°	441.7	441.0	440.2	439.4	440.2	441.0	441.7	442.5	442.9	442.8	442.8
110°	501.5	501.8	502.1	502.3	502.1	501.8	501.5	501.3	501.5	502.3	503.1



TEST NUMBER: P333544-840

CATALOG NUMBER: S125RDIP-S610D1205U840-4F0-1E-UDD-A

**CANDELA DISTRIBUTION (continued):**

	165°	170°	175°	180°	185°	190°	195°	200°	205°	210°	215°
112.5°	559.8	559.4	559.1	558.7	559.1	559.4	559.8	560.1	560.8	561.8	562.8
115°	647.8	646.3	644.7	643.2	644.7	646.3	647.8	649.4	650.8	651.8	652.8
117.5°	735.3	734.7	734.0	733.3	734.0	734.7	735.3	736.0	737.0	738.4	739.7
120°	792.6	791.3	790.0	788.7	790.0	791.3	792.6	794.0	794.9	795.4	795.9
122.5°	845.8	844.2	842.8	841.3	842.8	844.2	845.8	847.3	848.4	848.9	849.4
125°	923.6	922.9	922.1	921.3	922.1	922.9	923.6	924.4	925.3	926.3	927.5
127.5°	994.5	992.5	990.6	988.7	990.6	992.5	994.5	996.4	997.6	998.3	998.8
130°	1041.4	1040.2	1038.8	1037.5	1038.8	1040.2	1041.4	1042.7	1043.8	1044.5	1045.3
132.5°	1086.5	1085.2	1083.9	1082.6	1083.9	1085.2	1086.5	1087.8	1088.5	1088.6	1088.8
135°	1149.0	1147.4	1145.9	1144.3	1145.9	1147.4	1149.0	1150.5	1151.7	1152.2	1152.7
137.5°	1210.3	1209.0	1207.6	1206.3	1207.6	1209.0	1210.3	1211.7	1212.3	1212.2	1212.1
140°	1247.6	1246.1	1244.5	1242.9	1244.5	1246.1	1247.6	1249.1	1249.7	1249.1	1248.6
142.5°	1282.3	1280.8	1279.2	1277.7	1279.2	1280.8	1282.3	1283.9	1284.6	1284.5	1284.4
145°	1333.2	1331.7	1330.1	1328.6	1330.1	1331.7	1333.2	1334.8	1335.4	1335.2	1334.9
147.5°	1376.2	1374.3	1372.5	1370.6	1372.5	1374.3	1376.2	1378.1	1378.9	1378.6	1378.3
150°	1404.1	1402.0	1399.9	1397.9	1399.9	1402.0	1404.1	1406.1	1406.9	1406.4	1405.9
152.5°	1428.8	1426.9	1425.0	1423.2	1425.0	1426.9	1428.8	1430.7	1431.4	1430.9	1430.3
155°	1462.8	1460.7	1458.5	1456.5	1458.5	1460.7	1462.8	1464.8	1465.5	1464.7	1463.9
157.5°	1490.7	1488.6	1486.5	1484.4	1486.5	1488.6	1490.7	1492.8	1493.4	1492.6	1491.8
160°	1508.5	1506.4	1504.4	1502.3	1504.4	1506.4	1508.5	1510.7	1511.2	1510.1	1509.0
162.5°	1525.1	1522.8	1520.6	1518.2	1520.6	1522.8	1525.1	1527.4	1527.8	1526.4	1524.9
165°	1546.1	1544.0	1541.9	1539.8	1541.9	1544.0	1546.1	1548.1	1548.4	1546.9	1545.3
167.5°	1561.9	1559.5	1557.2	1554.9	1557.2	1559.5	1561.9	1564.3	1564.5	1562.6	1560.7
170°	1570.3	1568.0	1565.7	1563.3	1565.7	1568.0	1570.3	1572.7	1572.9	1570.7	1568.6
172.5°	1576.0	1573.7	1571.2	1568.9	1571.2	1573.7	1576.0	1578.3	1578.5	1576.7	1574.8
175°	1583.3	1580.9	1578.5	1576.2	1578.5	1580.9	1583.3	1585.6	1585.7	1583.7	1581.5
177.5°	1585.5	1583.8	1582.1	1580.4	1582.1	1583.8	1585.5	1587.1	1587.2	1585.8	1584.3
180°	1583.3	1583.3	1583.3	1583.3	1583.3	1583.3	1583.3	1583.3	1583.3	1583.3	1583.3



TEST NUMBER: P333544-840

CATALOG NUMBER: S125RDIP-S610D1205U840-4F0-1E-UDD-A

**CANDELA DISTRIBUTION (continued):**

	220°	225°	230°	235°	240°	245°	250°	255°	260°	265°	270°
0°	934.5	934.5	934.5	934.5	934.5	934.5	934.5	934.5	934.5	934.5	934.5
2.5°	895.9	899.2	901.0	905.3	911.5	914.5	918.9	921.9	926.2	931.4	935.7
5°	837.8	847.1	853.1	862.7	871.6	880.4	891.5	899.6	910.3	922.6	932.2
7.5°	784.0	795.5	805.7	818.3	832.9	844.2	858.8	873.5	890.4	907.8	924.2
10°	749.6	761.1	773.8	789.5	804.1	819.4	836.7	853.9	875.0	894.6	916.9
12.5°	715.5	728.2	742.5	760.0	777.7	797.3	814.9	834.2	857.0	882.3	906.2
15°	673.3	685.5	700.8	715.8	736.2	757.6	781.0	806.8	832.0	860.5	890.0
17.5°	627.9	641.4	658.3	675.6	697.0	722.2	745.2	773.3	801.7	834.9	869.6
20°	598.4	612.3	632.2	651.4	671.0	695.5	722.8	751.5	781.8	816.7	855.5
22.5°	575.1	584.9	604.6	624.1	647.0	672.2	698.8	728.8	761.8	798.0	838.6
25°	540.5	552.0	566.2	586.5	610.4	636.8	663.7	695.5	731.5	768.4	811.7
27.5°	509.8	519.2	533.2	549.2	572.9	600.4	628.9	662.2	699.1	736.6	782.2
30°	488.0	498.4	511.7	528.7	547.4	577.3	606.5	639.1	676.7	715.5	762.2
32.5°	469.0	479.6	491.2	507.2	527.5	554.0	584.1	616.1	654.3	694.3	739.8
35°	442.3	449.6	460.3	476.1	496.0	517.5	548.2	582.0	619.1	660.6	706.2
37.5°	411.8	421.2	431.9	445.6	463.0	486.3	514.8	549.0	583.5	623.2	664.8
40°	393.9	402.8	414.7	424.6	443.1	464.1	490.3	525.9	560.5	597.6	635.6
42.5°	375.9	384.4	394.5	406.9	423.4	443.9	468.2	501.4	538.4	573.4	605.3
45°	347.6	356.4	366.0	377.5	392.8	412.7	437.0	467.3	499.5	531.7	555.8
47.5°	320.4	328.7	337.8	349.6	363.8	383.0	404.7	431.4	462.7	490.1	507.4
50°	301.1	308.8	318.8	330.3	344.1	362.1	382.8	409.3	435.5	460.3	476.1
52.5°	282.2	290.7	300.6	310.6	323.9	341.8	361.0	383.8	408.7	429.0	442.0
55°	253.6	261.7	270.8	281.1	294.3	309.6	329.9	347.9	367.5	384.8	392.4
57.5°	226.0	233.1	241.8	252.5	264.3	278.5	294.6	311.9	325.8	338.0	346.7
60°	207.9	214.1	222.1	231.4	244.0	257.0	271.6	287.7	298.4	308.8	316.9
62.5°	189.6	195.3	203.1	211.4	222.5	234.6	248.6	261.7	272.1	279.0	288.3
65°	161.9	167.6	174.2	183.0	191.8	201.8	214.4	224.0	231.4	239.0	244.8
67.5°	136.2	141.0	147.1	154.1	161.5	171.1	180.9	188.8	193.9	198.4	205.4
70°	119.3	123.1	128.2	133.5	141.6	151.2	158.9	164.9	168.4	173.0	181.5
72.5°	102.1	106.5	111.3	116.6	123.1	131.2	137.9	144.1	146.3	150.0	155.3
75°	80.6	82.9	86.7	90.5	95.1	102.0	108.6	110.1	112.0	115.1	119.0
77.5°	60.9	63.0	64.5	67.1	70.7	76.2	79.7	82.0	82.5	83.6	87.4
80°	48.4	49.5	51.0	52.9	54.4	59.1	61.0	63.3	64.0	65.2	67.2
82.5°	35.4	36.6	37.6	39.1	41.6	43.4	45.3	47.7	47.8	48.7	49.0
85°	20.7	21.1	20.3	21.1	21.5	22.2	24.1	26.1	25.8	25.3	26.5
87.5°	11.4	11.1	10.4	11.0	10.0	10.0	9.6	9.5	9.7	9.9	10.1
90°	20.1	18.8	17.0	15.1	13.3	11.5	9.5	7.5	5.4	3.2	1.2
92.5°	20.1	18.8	17.2	15.6	13.9	12.3	12.2	13.7	15.1	16.7	18.1
95°	20.1	18.8	28.7	38.6	48.5	58.5	63.7	64.5	65.3	66.1	66.9
97.5°	50.4	57.8	77.4	96.9	116.5	136.2	145.3	143.9	142.5	141.1	139.7
100°	165.3	204.2	203.2	202.2	201.1	200.1	199.1	198.3	197.5	196.8	196.0
102.5°	253.2	260.5	259.9	259.3	258.6	258.0	257.2	256.2	255.3	254.3	253.3
105°	349.7	349.7	349.7	349.7	349.7	349.7	349.2	348.2	347.1	346.1	345.1
107.5°	442.7	442.7	442.2	441.6	441.1	440.6	440.4	440.4	440.4	440.4	440.4
110°	503.9	504.6	504.1	503.6	503.1	502.6	502.3	502.3	502.3	502.3	502.3



TEST NUMBER: P333544-840

CATALOG NUMBER: S125RDIP-S610D1205U840-4F0-1E-UDD-A

**CANDELA DISTRIBUTION (continued):**

	220°	225°	230°	235°	240°	245°	250°	255°	260°	265°	270°
112.5°	563.8	564.7	564.4	564.1	563.8	563.5	563.0	562.4	561.8	561.2	560.6
115°	653.9	654.9	654.6	654.4	654.1	653.9	653.1	651.8	650.5	649.1	647.8
117.5°	741.1	742.5	741.4	740.4	739.5	738.5	738.0	738.1	738.1	738.2	738.2
120°	796.4	796.9	796.1	795.4	794.6	793.8	793.6	793.8	794.1	794.3	794.6
122.5°	849.9	850.4	850.1	849.7	849.3	849.0	848.3	847.3	846.3	845.4	844.3
125°	928.5	929.5	929.5	929.5	929.5	929.5	928.6	926.8	924.9	923.1	921.3
127.5°	999.4	1000.0	1000.1	1000.3	1000.4	1000.6	1000.0	998.7	997.3	996.1	994.8
130°	1046.1	1046.9	1046.6	1046.4	1046.1	1045.8	1045.1	1043.8	1042.5	1041.2	1039.9
132.5°	1089.0	1089.1	1089.7	1090.3	1090.9	1091.5	1091.0	1089.4	1087.9	1086.4	1084.9
135°	1153.2	1153.7	1154.2	1154.8	1155.3	1155.8	1155.3	1153.7	1152.2	1150.5	1149.0
137.5°	1212.0	1211.9	1212.3	1212.8	1213.4	1213.8	1213.4	1211.9	1210.6	1209.3	1207.9
140°	1248.1	1247.6	1247.9	1248.1	1248.4	1248.6	1248.5	1248.0	1247.5	1247.0	1246.4
142.5°	1284.3	1284.2	1283.8	1283.4	1283.1	1282.7	1282.4	1282.1	1281.8	1281.4	1281.1
145°	1334.7	1334.4	1334.4	1334.4	1334.4	1334.4	1334.1	1333.6	1333.1	1332.6	1332.1
147.5°	1378.0	1377.7	1377.4	1377.0	1376.6	1376.3	1376.2	1376.3	1376.4	1376.5	1376.6
150°	1405.3	1404.8	1404.3	1403.8	1403.3	1402.8	1402.8	1403.3	1403.8	1404.3	1404.8
152.5°	1429.8	1429.3	1428.8	1428.3	1427.7	1427.1	1427.4	1428.7	1429.8	1431.0	1432.1
155°	1463.2	1462.4	1461.9	1461.3	1460.8	1460.3	1460.8	1462.4	1463.9	1465.5	1467.0
157.5°	1490.9	1490.1	1490.1	1490.0	1490.0	1489.9	1490.3	1491.3	1492.2	1493.1	1494.1
160°	1508.0	1506.9	1506.7	1506.4	1506.2	1505.9	1506.6	1508.1	1509.7	1511.3	1512.9
162.5°	1523.5	1522.0	1521.8	1521.5	1521.2	1521.0	1521.6	1523.2	1524.7	1526.3	1527.8
165°	1543.8	1542.2	1541.9	1541.7	1541.4	1541.2	1541.8	1543.4	1544.9	1546.5	1548.0
167.5°	1558.8	1557.0	1556.7	1556.4	1556.2	1555.9	1556.6	1558.2	1559.8	1561.5	1563.1
170°	1566.6	1564.5	1564.2	1564.0	1563.7	1563.5	1564.2	1566.0	1567.8	1569.7	1571.6
172.5°	1573.0	1571.0	1570.5	1570.1	1569.6	1569.1	1569.8	1571.7	1573.5	1575.3	1577.1
175°	1579.4	1577.4	1577.1	1576.9	1576.6	1576.3	1577.0	1578.5	1580.1	1581.7	1583.3
177.5°	1582.9	1581.3	1581.1	1580.9	1580.7	1580.5	1581.0	1582.4	1583.6	1584.8	1586.1
180°	1583.3	1583.3	1583.3	1583.3	1583.3	1583.3	1583.3	1583.3	1583.3	1583.3	1583.3



TEST NUMBER: P333544-840

CATALOG NUMBER: S125RDIP-S610D1205U840-4F0-1E-UDD-A

**CANDELA DISTRIBUTION (continued):**

	275°	280°	285°	290°	295°	300°	305°	310°	315°	320°	325°
0°	934.5	934.5	934.5	934.5	934.5	934.5	934.5	934.5	934.5	934.5	934.5
2.5°	939.1	941.9	945.8	950.5	954.1	958.2	960.3	960.3	962.1	966.1	971.3
5°	941.8	951.8	961.4	973.6	983.2	994.3	1002.8	1010.9	1018.1	1027.3	1036.9
7.5°	941.0	957.6	974.8	994.2	1015.5	1032.5	1049.9	1063.6	1077.0	1094.7	1108.6
10°	938.0	959.5	982.8	1007.3	1034.2	1057.6	1078.7	1097.9	1116.3	1135.5	1152.8
12.5°	932.4	959.8	988.4	1017.8	1051.8	1078.5	1105.7	1126.2	1147.6	1168.6	1189.9
15°	924.1	956.3	990.9	1032.0	1073.4	1103.3	1130.1	1156.6	1176.6	1200.3	1220.7
17.5°	907.1	948.6	992.0	1036.8	1076.6	1111.5	1139.5	1164.8	1186.0	1212.1	1239.8
20°	896.9	941.8	987.0	1035.0	1073.0	1108.6	1135.9	1162.0	1188.4	1222.6	1256.4
22.5°	882.8	930.7	978.8	1024.3	1064.4	1098.8	1127.0	1158.9	1193.7	1232.4	1273.2
25°	860.5	910.0	957.6	1000.9	1040.0	1075.3	1113.7	1156.6	1198.8	1249.8	1308.5
27.5°	832.1	879.9	922.3	968.1	1007.0	1051.9	1099.7	1146.3	1207.2	1277.4	1350.7
30°	810.9	856.3	896.6	939.9	984.0	1033.5	1087.2	1142.1	1214.6	1297.0	1384.1
32.5°	786.4	827.4	867.4	909.2	960.1	1014.4	1071.6	1138.6	1225.3	1319.1	1409.3
35°	743.9	780.6	819.4	865.9	919.9	979.0	1051.9	1133.6	1238.3	1339.2	1420.2
37.5°	699.2	728.2	767.2	816.1	875.0	943.4	1026.1	1125.4	1232.9	1323.5	1358.0
40°	664.8	692.1	733.1	784.5	842.8	917.7	1010.5	1112.5	1220.7	1283.5	1280.9
42.5°	630.8	658.3	697.8	749.5	810.3	894.0	989.6	1095.6	1186.9	1210.8	1160.9
45°	578.5	604.2	643.0	695.1	760.3	848.2	948.7	1050.4	1108.6	1070.0	971.0
47.5°	525.2	550.2	586.1	637.2	708.4	800.4	895.4	978.9	987.0	903.8	785.1
50°	490.3	513.6	547.9	602.3	671.4	761.1	852.8	918.4	898.1	796.4	674.0
52.5°	456.2	478.7	510.7	562.1	632.7	720.6	802.4	853.9	806.9	698.8	588.8
55°	405.9	427.4	459.6	506.8	570.8	651.4	723.2	741.9	672.9	563.9	474.9
57.5°	358.1	373.8	405.7	447.4	509.2	580.2	631.6	628.2	552.0	453.9	390.1
60°	326.5	340.6	370.9	409.3	468.0	531.7	567.7	552.4	475.3	394.4	333.0
62.5°	297.0	310.2	335.7	370.9	421.4	476.8	503.0	481.8	409.0	337.9	289.1
65°	252.5	262.1	282.4	315.0	354.5	392.8	416.3	385.2	320.7	267.0	230.1
67.5°	210.8	219.0	237.1	260.5	287.8	314.3	323.8	294.6	244.5	208.3	182.4
70°	183.8	191.5	203.7	225.6	243.6	262.4	267.0	241.0	199.1	171.5	155.3
72.5°	157.9	165.0	175.8	191.2	203.7	214.5	216.7	192.4	160.5	141.4	129.0
75°	120.5	126.6	133.5	139.3	147.3	149.3	148.5	129.7	112.4	99.8	92.8
77.5°	88.6	91.1	95.3	97.6	98.0	97.9	93.9	82.0	73.1	67.9	65.0
80°	68.3	70.2	71.4	72.1	72.5	68.7	64.4	57.2	54.1	51.0	47.6
82.5°	49.6	50.9	52.0	52.2	50.1	46.9	42.9	39.4	37.2	35.6	34.3
85°	26.9	27.3	26.9	24.9	22.2	21.1	20.3	19.6	19.2	18.8	18.8
87.5°	10.2	9.7	8.6	9.3	9.7	9.7	10.1	10.1	10.2	10.5	10.7
90°	3.2	5.4	7.5	9.5	11.5	13.3	15.1	17.0	18.8	20.1	21.4
92.5°	16.7	15.1	13.7	12.2	12.3	13.9	15.6	17.2	18.8	20.1	21.4
95°	66.1	65.3	64.5	63.7	58.5	48.5	38.6	28.7	18.8	20.1	21.4
97.5°	141.1	142.5	143.9	145.3	136.2	116.5	96.9	77.4	57.8	50.4	43.0
100°	196.8	197.5	198.3	199.1	200.1	201.1	202.2	203.2	204.2	165.3	126.5
102.5°	254.3	255.3	256.2	257.2	258.0	258.6	259.3	259.9	260.5	253.2	245.8
105°	346.1	347.1	348.2	349.2	349.7	349.7	349.7	349.7	349.7	349.7	349.7
107.5°	440.4	440.4	440.4	440.4	440.6	441.1	441.6	442.2	442.7	442.7	442.8
110°	502.3	502.3	502.3	502.3	502.6	503.1	503.6	504.1	504.6	503.9	503.1





TEST NUMBER: P333544-840

CATALOG NUMBER: S125RDIP-S610D1205U840-4F0-1E-UDD-A

**CANDELA DISTRIBUTION (continued):**

	275°	280°	285°	290°	295°	300°	305°	310°	315°	320°	325°
112.5°	561.2	561.8	562.4	563.0	563.5	563.8	564.1	564.4	564.7	563.8	562.8
115°	649.1	650.5	651.8	653.1	653.9	654.1	654.4	654.6	654.9	653.9	652.8
117.5°	738.2	738.1	738.1	738.0	738.5	739.5	740.4	741.4	742.5	741.1	739.7
120°	794.3	794.1	793.8	793.6	793.8	794.6	795.4	796.1	796.9	796.4	795.9
122.5°	845.4	846.3	847.3	848.3	849.0	849.3	849.7	850.1	850.4	849.9	849.4
125°	923.1	924.9	926.8	928.6	929.5	929.5	929.5	929.5	929.5	928.5	927.5
127.5°	996.1	997.3	998.7	1000.0	1000.6	1000.4	1000.3	1000.1	1000.0	999.4	998.8
130°	1041.2	1042.5	1043.8	1045.1	1045.8	1046.1	1046.4	1046.6	1046.9	1046.1	1045.3
132.5°	1086.4	1087.9	1089.4	1091.0	1091.5	1090.9	1090.3	1089.7	1089.1	1089.0	1088.8
135°	1150.5	1152.2	1153.7	1155.3	1155.8	1155.3	1154.8	1154.2	1153.7	1153.2	1152.7
137.5°	1209.3	1210.6	1211.9	1213.4	1213.8	1213.4	1212.8	1212.3	1211.9	1212.0	1212.1
140°	1247.0	1247.5	1248.0	1248.5	1248.6	1248.4	1248.1	1247.9	1247.6	1248.1	1248.6
142.5°	1281.4	1281.8	1282.1	1282.4	1282.7	1283.1	1283.4	1283.8	1284.2	1284.3	1284.4
145°	1332.6	1333.1	1333.6	1334.1	1334.4	1334.4	1334.4	1334.4	1334.4	1334.7	1334.9
147.5°	1376.5	1376.4	1376.3	1376.2	1376.3	1376.6	1377.0	1377.4	1377.7	1378.0	1378.3
150°	1404.3	1403.8	1403.3	1402.8	1402.8	1403.3	1403.8	1404.3	1404.8	1405.3	1405.9
152.5°	1431.0	1429.8	1428.7	1427.4	1427.1	1427.7	1428.3	1428.8	1429.3	1429.8	1430.3
155°	1465.5	1463.9	1462.4	1460.8	1460.3	1460.8	1461.3	1461.9	1462.4	1463.2	1463.9
157.5°	1493.1	1492.2	1491.3	1490.3	1489.9	1490.0	1490.0	1490.1	1490.1	1490.9	1491.8
160°	1511.3	1509.7	1508.1	1506.6	1505.9	1506.2	1506.4	1506.7	1506.9	1508.0	1509.0
162.5°	1526.3	1524.7	1523.2	1521.6	1521.0	1521.2	1521.5	1521.8	1522.0	1523.5	1524.9
165°	1546.5	1544.9	1543.4	1541.8	1541.2	1541.4	1541.7	1541.9	1542.2	1543.8	1545.3
167.5°	1561.5	1559.8	1558.2	1556.6	1555.9	1556.2	1556.4	1556.7	1557.0	1558.8	1560.7
170°	1569.7	1567.8	1566.0	1564.2	1563.5	1563.7	1564.0	1564.2	1564.5	1566.6	1568.6
172.5°	1575.3	1573.5	1571.7	1569.8	1569.1	1569.6	1570.1	1570.5	1571.0	1573.0	1574.8
175°	1581.7	1580.1	1578.5	1577.0	1576.3	1576.6	1576.9	1577.1	1577.4	1579.4	1581.5
177.5°	1584.8	1583.6	1582.4	1581.0	1580.5	1580.7	1580.9	1581.1	1581.3	1582.9	1584.3
180°	1583.3	1583.3	1583.3	1583.3	1583.3	1583.3	1583.3	1583.3	1583.3	1583.3	1583.3



TEST NUMBER: P333544-840

CATALOG NUMBER: S125RDIP-S610D1205U840-4F0-1E-UDD-A

**CANDELA DISTRIBUTION (continued):**

	330°	335°	340°	345°	350°	355°	360°
0°	934.5	934.5	934.5	934.5	934.5	934.5	934.5
2.5°	975.3	975.3	980.6	980.2	983.6	982.4	983.0
5°	1048.4	1054.9	1060.7	1064.5	1070.3	1071.9	1071.1
7.5°	1124.3	1138.7	1145.8	1155.5	1157.2	1162.3	1161.7
10°	1171.1	1185.4	1196.1	1204.6	1208.8	1214.2	1214.6
12.5°	1208.0	1220.0	1229.6	1237.4	1242.5	1244.3	1245.3
15°	1236.8	1250.2	1261.3	1272.4	1279.0	1283.9	1286.7
17.5°	1265.8	1286.5	1306.2	1321.3	1330.3	1338.0	1337.9
20°	1288.2	1312.0	1336.6	1353.8	1371.4	1379.1	1380.3
22.5°	1312.1	1348.5	1380.1	1406.8	1430.1	1438.0	1441.0
25°	1361.8	1409.4	1458.1	1495.7	1522.6	1538.3	1540.7
27.5°	1421.9	1486.3	1537.5	1572.3	1594.6	1606.2	1608.7
30°	1464.3	1523.7	1569.7	1595.9	1606.2	1607.7	1601.9
32.5°	1483.3	1527.7	1546.1	1544.6	1524.3	1510.8	1505.6
35°	1460.1	1450.9	1405.9	1352.2	1311.2	1285.2	1278.2
37.5°	1328.7	1249.3	1166.7	1085.6	1042.4	1020.5	982.7
40°	1199.2	1086.0	1000.1	931.8	883.1	843.9	834.8
42.5°	1053.1	936.2	850.3	791.8	753.0	726.1	714.5
45°	846.3	745.8	674.8	629.9	600.0	580.4	571.6
47.5°	676.8	599.1	547.3	514.1	491.3	474.3	469.6
50°	583.9	521.7	478.0	450.0	432.7	419.7	414.3
52.5°	507.2	457.0	423.3	400.3	384.0	375.8	371.3
55°	418.5	375.2	351.0	332.5	323.4	316.9	313.8
57.5°	342.2	310.9	293.3	280.5	272.1	267.9	266.4
60°	299.6	275.1	258.9	248.9	243.2	237.8	236.3
62.5°	261.9	242.6	230.0	221.4	215.6	213.3	212.4
65°	211.0	198.3	189.1	183.8	179.2	178.3	178.0
67.5°	167.7	160.3	155.4	149.9	148.2	145.5	145.0
70°	143.5	138.5	132.7	130.8	128.9	126.2	126.6
72.5°	121.7	116.7	112.8	110.3	109.6	108.5	109.4
75°	89.0	87.5	85.9	84.0	83.2	83.2	82.9
77.5°	63.5	62.2	60.5	59.4	59.2	57.6	58.2
80°	46.0	44.1	43.3	43.7	42.6	42.2	42.2
82.5°	34.0	33.3	32.6	32.7	32.4	32.1	32.4
85°	18.8	18.4	18.4	18.1	18.1	17.7	17.7
87.5°	11.3	11.8	11.4	11.3	11.4	11.9	12.4
90°	22.7	24.0	25.0	25.9	26.6	27.4	28.2
92.5°	22.7	24.0	24.8	25.1	25.5	26.0	26.3
95°	22.7	24.0	24.6	24.6	24.6	24.6	24.6
97.5°	35.6	28.3	24.6	24.6	24.6	24.6	24.6
100°	87.7	48.8	28.8	27.8	26.8	25.7	24.6
102.5°	238.5	231.2	218.6	200.9	183.1	165.4	147.6
105°	349.7	349.7	349.6	349.3	349.1	348.8	348.6
107.5°	442.8	442.9	442.5	441.7	441.0	440.2	439.4
110°	502.3	501.5	501.3	501.5	501.8	502.1	502.3



TEST NUMBER: P333544-840

CATALOG NUMBER: S125RDIP-S610D1205U840-4F0-1E-UDD-A

**CANDELA DISTRIBUTION (continued):**

	330°	335°	340°	345°	350°	355°	360°
112.5°	561.8	560.8	560.1	559.8	559.4	559.1	558.7
115°	651.8	650.8	649.4	647.8	646.3	644.7	643.2
117.5°	738.4	737.0	736.0	735.3	734.7	734.0	733.3
120°	795.4	794.9	794.0	792.6	791.3	790.0	788.7
122.5°	848.9	848.4	847.3	845.8	844.2	842.8	841.3
125°	926.3	925.3	924.4	923.6	922.9	922.1	921.3
127.5°	998.3	997.6	996.4	994.5	992.5	990.6	988.7
130°	1044.5	1043.8	1042.7	1041.4	1040.2	1038.8	1037.5
132.5°	1088.6	1088.5	1087.8	1086.5	1085.2	1083.9	1082.6
135°	1152.2	1151.7	1150.5	1149.0	1147.4	1145.9	1144.3
137.5°	1212.2	1212.3	1211.7	1210.3	1209.0	1207.6	1206.3
140°	1249.1	1249.7	1249.1	1247.6	1246.1	1244.5	1242.9
142.5°	1284.5	1284.6	1283.9	1282.3	1280.8	1279.2	1277.7
145°	1335.2	1335.4	1334.8	1333.2	1331.7	1330.1	1328.6
147.5°	1378.6	1378.9	1378.1	1376.2	1374.3	1372.5	1370.6
150°	1406.4	1406.9	1406.1	1404.1	1402.0	1399.9	1397.9
152.5°	1430.9	1431.4	1430.7	1428.8	1426.9	1425.0	1423.2
155°	1464.7	1465.5	1464.8	1462.8	1460.7	1458.5	1456.5
157.5°	1492.6	1493.4	1492.8	1490.7	1488.6	1486.5	1484.4
160°	1510.1	1511.2	1510.7	1508.5	1506.4	1504.4	1502.3
162.5°	1526.4	1527.8	1527.4	1525.1	1522.8	1520.6	1518.2
165°	1546.9	1548.4	1548.1	1546.1	1544.0	1541.9	1539.8
167.5°	1562.6	1564.5	1564.3	1561.9	1559.5	1557.2	1554.9
170°	1570.7	1572.9	1572.7	1570.3	1568.0	1565.7	1563.3
172.5°	1576.7	1578.5	1578.3	1576.0	1573.7	1571.2	1568.9
175°	1583.7	1585.7	1585.6	1583.3	1580.9	1578.5	1576.2
177.5°	1585.8	1587.2	1587.1	1585.5	1583.8	1582.1	1580.4
180°	1583.3	1583.3	1583.3	1583.3	1583.3	1583.3	1583.3

(END OF REPORT)